

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031225

Luminaire Tested: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031225
REPORT IS A COMBINATION OF REPORTS P994651 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8272.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44			37
1	95	91	88	84	86	83	80	77	67	65	63	53	51	50	39	39	38			32
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	35	34	33			27
3	80	71	64	58	72	64	59	54	53	48	45	42	39	36	32	30	28			24
4	73	63	55	50	66	57	51	46	47	42	39	37	34	32	28	26	25			21
5	67	56	48	43	61	51	45	40	42	37	33	34	30	28	26	24	22			18
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19			16
7	57	45	38	33	52	42	35	30	35	30	26	28	24	22	22	19	17			14
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16			13
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14			12
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13119	13119	13119	13119
5°	13130	15110	13163	11210
10°	13014	18240	13070	9791
15°	12879	20701	12879	8634
20°	12616	22330	12686	7659
25°	12422	21214	12398	6988
30°	12197	14699	12171	6333
35°	11926	9438	11873	5838
40°	11589	6664	11533	5346
45°	11003	5333	10988	4868
50°	10284	4461	10249	4307
55°	9473	3676	9397	3652
60°	8677	3039	8592	3106
65°	7745	2432	7796	2632
70°	6885	1690	7068	2128
75°	5835	1253	6075	1637
80°	4647	831	5044	1227
85°	3304	392	3612	762

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 17515 cd/sqm

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	1.4
10°-20°	374.7	4.5
20°-30°	590.1	7.1
30°-40°	613.6	7.4
40°-50°	525.0	6.3
50°-60°	400.3	4.8
60°-70°	256.4	3.1
70°-80°	122.9	1.5
80°-90°	35.7	0.4
90°-100°	60.5	0.7
100°-110°	292.7	3.5
110°-120°	717.2	8.7
120°-130°	910.5	11.0
130°-140°	972.7	11.8
140°-150°	909.6	11.0
150°-160°	733.7	8.9
160°-170°	473.5	5.7
170°-180°	163.2	2.0
0°-30°	1084.5	13.1
0°-40°	1698.2	20.5
0°-60°	2623.4	31.7
0°-90°	3038.4	36.7
90°-120°	1070.5	12.9
90°-150°	3863.3	46.7
90°-180°	5234.0	63.3
0°-180°	8272.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1219	1219	1219	1219	1219	
5°	1218	1447	1221	1074	1218	116
15°	1164	2057	1164	858	1164	327
25°	1058	2119	1056	698	1058	487
35°	924	919	919	569	924	578
45°	741	490	740	448	741	570
55°	523	308	519	306	523	468
65°	320	177	322	192	320	320
75°	153	75	160	98	153	166
85°	34	18	38	34	34	38
90°	1	38	1	38	1	6
95°	78	48	78	48	78	93
105°	380	56	380	56	380	403
115°	713	750	713	750	713	704
125°	1005	1025	1005	1025	1005	898
135°	1251	1264	1251	1264	1251	963
145°	1444	1458	1444	1458	1444	904
155°	1590	1588	1590	1588	1590	733
165°	1677	1673	1677	1673	1677	474
175°	1717	1710	1717	1710	1717	163
180°	1717	1717	1717	1717	1717	

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4FO-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1222.0	1230.3	1236.6	1240.8	1251.2	1257.5	1262.7	1272.1	1272.1	1274.2	1278.3
5°	1217.8	1235.5	1248.1	1264.8	1286.7	1297.1	1311.7	1324.2	1342.0	1351.4	1360.8
7.5°	1208.4	1233.5	1259.5	1284.6	1316.9	1337.8	1352.4	1384.8	1407.7	1435.9	1457.8
10°	1195.9	1230.3	1263.7	1302.3	1346.2	1377.5	1399.4	1442.2	1486.0	1525.6	1559.0
12.5°	1180.2	1222.0	1270.0	1316.9	1378.5	1409.8	1445.3	1498.5	1561.1	1611.2	1656.1
15°	1163.5	1211.5	1265.8	1323.2	1400.4	1444.3	1495.4	1560.1	1630.0	1702.0	1763.6
17.5°	1137.5	1198.0	1258.5	1342.0	1432.8	1458.9	1502.7	1591.4	1678.0	1742.7	1817.8
20°	1111.4	1179.2	1255.4	1330.5	1428.6	1489.1	1529.8	1623.7	1716.6	1794.9	1866.9
22.5°	1087.4	1158.3	1237.6	1332.6	1424.4	1484.9	1536.1	1634.2	1741.7	1829.3	1918.0
25°	1058.1	1135.4	1223.0	1312.8	1424.4	1470.3	1526.7	1640.4	1754.2	1855.4	1965.0
27.5°	1026.8	1105.1	1191.7	1283.5	1385.8	1453.6	1509.0	1631.0	1769.8	1878.4	1991.1
30°	995.5	1075.9	1159.4	1241.8	1356.6	1421.3	1484.9	1619.6	1778.2	1902.4	1989.0
32.5°	965.3	1033.1	1115.5	1195.9	1309.6	1380.6	1452.6	1608.1	1781.3	1885.7	1927.4
35°	923.5	994.5	1061.3	1146.8	1261.6	1331.6	1416.1	1607.0	1767.7	1832.4	1811.6
37.5°	884.9	944.4	1008.1	1084.2	1202.2	1292.9	1380.6	1579.9	1722.9	1727.0	1609.1
40°	842.1	891.2	944.4	1024.8	1152.1	1241.8	1336.8	1538.2	1641.5	1579.9	1372.2
42.5°	793.1	836.9	878.7	956.9	1095.7	1195.9	1298.2	1486.0	1523.6	1381.6	1165.6
45°	740.9	776.4	815.0	897.4	1036.2	1135.4	1237.6	1405.6	1367.0	1166.7	961.1
47.5°	686.6	716.9	754.5	829.6	972.6	1073.8	1170.8	1290.9	1192.8	977.8	805.6
50°	632.4	656.4	692.9	770.1	907.9	999.7	1089.5	1167.7	1030.0	839.0	665.8
52.5°	579.2	597.9	635.5	701.3	834.8	922.5	987.2	1017.4	877.6	692.9	578.1
55°	522.8	543.7	568.7	635.5	768.0	832.7	875.5	874.5	730.5	587.5	477.9
57.5°	468.5	487.3	509.2	576.0	683.5	727.3	763.9	746.1	609.4	481.1	410.1
60°	420.5	431.0	455.0	511.3	592.7	630.3	651.2	620.9	497.8	405.9	339.1
62.5°	368.4	378.8	398.6	451.9	501.9	521.8	539.5	500.9	411.2	330.8	290.1
65°	320.4	333.9	346.5	389.2	416.4	440.4	438.3	405.9	321.4	269.2	235.8
67.5°	278.6	283.8	294.3	320.4	332.9	350.6	351.7	315.1	258.8	219.1	199.3
70°	233.8	239.0	246.3	258.8	267.1	271.3	269.2	236.9	195.1	171.1	153.4
72.5°	195.1	194.1	199.3	199.3	207.7	206.6	200.4	175.3	148.2	128.4	117.9
75°	153.4	154.4	155.5	153.4	150.3	146.1	140.9	122.1	104.4	95.0	85.6
77.5°	120.0	117.9	119.0	111.7	107.5	103.3	96.0	86.6	72.0	69.9	65.7
80°	85.6	84.5	83.5	80.4	71.0	66.8	61.6	56.4	53.2	51.1	50.1
82.5°	57.4	57.4	55.3	49.0	43.8	40.7	39.7	37.6	34.4	34.4	33.4
85°	34.4	33.4	31.3	25.0	21.9	21.9	21.9	21.9	19.8	19.8	18.8
87.5°	13.6	12.5	9.4	9.4	8.3	8.3	8.3	7.3	7.3	6.3	6.3
90°	1.3	4.1	6.9	9.8	12.6	14.0	15.8	19.5	23.2	26.9	30.6
92.5°	29.3	27.6	25.9	24.2	22.5	21.7	23.0	25.5	28.1	30.6	33.2
95°	77.8	66.2	54.6	42.9	31.3	25.5	27.1	30.2	33.3	36.4	39.5
97.5°	141.6	133.7	125.7	117.8	109.9	105.9	98.7	84.2	69.7	55.3	40.8
100°	215.5	221.2	226.9	232.6	238.3	241.1	219.0	174.8	130.5	86.3	42.1
102.5°	299.7	303.4	307.1	310.8	314.5	316.3	291.6	242.3	193.0	143.7	94.4
105°	380.1	383.2	386.3	389.4	392.5	394.1	381.3	355.8	330.3	304.8	279.3
107.5°	465.5	468.1	470.6	473.2	475.7	477.0	479.1	483.4	487.6	491.9	496.1
110°	551.0	553.3	555.5	557.8	560.1	561.2	562.8	565.9	569.0	572.1	575.2

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	632.6	634.6	636.6	638.5	640.5	641.5	643.1	646.2	649.3	652.5	655.6
115°	713.0	714.7	716.4	718.1	719.8	720.6	721.9	724.4	727.0	729.5	732.1
117.5°	792.0	794.0	796.0	798.0	800.0	801.0	801.7	803.1	804.5	805.9	807.3
120°	864.7	867.3	869.8	872.4	874.9	876.2	876.6	877.5	878.3	879.2	880.0
122.5°	938.7	940.7	942.7	944.6	946.6	947.6	948.2	949.3	950.4	951.6	952.7
125°	1005.0	1007.3	1009.5	1011.8	1014.1	1015.2	1015.8	1016.9	1018.0	1019.2	1020.3
127.5°	1071.4	1073.7	1075.9	1078.2	1080.5	1081.6	1082.3	1083.7	1085.1	1086.5	1087.9
130°	1132.6	1134.9	1137.1	1139.4	1141.7	1142.8	1143.4	1144.5	1145.6	1146.8	1147.9
132.5°	1191.2	1193.5	1195.8	1198.1	1200.4	1201.5	1201.9	1202.8	1203.6	1204.5	1205.3
135°	1251.2	1252.9	1254.6	1256.3	1258.0	1258.8	1259.4	1260.5	1261.6	1262.8	1263.9
137.5°	1302.2	1304.5	1306.7	1309.0	1311.3	1312.4	1312.7	1313.3	1313.8	1314.4	1315.0
140°	1353.2	1354.9	1356.6	1358.3	1360.0	1360.9	1361.3	1362.2	1363.0	1363.9	1364.7
142.5°	1400.4	1402.1	1403.8	1405.5	1407.2	1408.1	1408.5	1409.4	1410.2	1411.1	1411.9
145°	1443.8	1445.8	1447.8	1449.7	1451.7	1452.7	1453.0	1453.6	1454.1	1454.7	1455.3
147.5°	1485.9	1487.3	1488.7	1490.1	1491.5	1492.2	1492.5	1493.1	1493.6	1494.2	1494.8
150°	1524.1	1525.0	1525.8	1526.7	1527.6	1528.0	1528.3	1528.8	1529.4	1529.9	1530.5
152.5°	1558.6	1558.9	1559.1	1559.4	1559.7	1559.8	1559.9	1560.2	1560.5	1560.8	1561.1
155°	1590.5	1589.9	1589.3	1588.8	1588.2	1587.9	1588.0	1588.3	1588.6	1588.9	1589.2
157.5°	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1615.9	1615.6	1615.3	1615.0	1614.7
160°	1638.9	1638.6	1638.3	1638.0	1637.7	1637.6	1637.5	1637.2	1636.9	1636.7	1636.4
162.5°	1660.6	1659.8	1658.9	1658.1	1657.2	1656.8	1656.7	1656.4	1656.1	1655.8	1655.5
165°	1677.2	1676.4	1675.5	1674.7	1673.8	1673.4	1673.3	1673.0	1672.7	1672.4	1672.1
167.5°	1691.2	1690.1	1688.9	1687.8	1686.7	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1
170°	1702.7	1701.6	1700.4	1699.3	1698.2	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6
172.5°	1710.3	1708.9	1707.5	1706.1	1704.7	1704.0	1704.1	1704.4	1704.7	1704.9	1705.2
175°	1716.7	1715.3	1713.9	1712.4	1711.0	1710.3	1710.4	1710.7	1711.0	1711.3	1711.6
177.5°	1719.3	1717.9	1716.5	1715.0	1713.6	1712.9	1713.0	1713.3	1713.6	1713.9	1714.2
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4FO-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1286.7	1286.7	1296.1	1305.5	1300.2	1303.4	1314.9	1310.7	1319.0	1318.0	1321.1
5°	1383.7	1395.2	1404.6	1424.4	1427.6	1424.4	1444.3	1449.5	1458.9	1447.4	1452.6
7.5°	1493.3	1517.3	1540.3	1569.5	1578.9	1581.0	1591.4	1606.0	1618.5	1595.6	1607.0
10°	1599.7	1636.3	1683.2	1709.3	1732.3	1740.6	1749.0	1758.4	1773.0	1786.5	1776.1
12.5°	1714.5	1767.7	1812.6	1859.6	1887.8	1884.6	1908.6	1914.9	1926.4	1929.5	1933.7
15°	1808.4	1883.6	1911.8	1981.7	1987.9	2008.8	2035.9	2059.9	2063.1	2056.8	2056.8
17.5°	1898.2	1962.9	2013.0	2069.3	2080.8	2098.5	2133.0	2144.5	2148.6	2147.6	2147.6
20°	1971.2	2014.0	2098.5	2145.5	2164.3	2187.2	2211.2	2225.9	2229.0	2233.2	2226.9
22.5°	2019.2	2083.9	2152.8	2191.4	2207.1	2215.4	2231.1	2235.3	2230.0	2231.1	2232.1
25°	2056.8	2120.5	2162.2	2172.6	2171.6	2161.2	2149.7	2129.9	2127.8	2119.4	2102.7
27.5°	2067.2	2091.2	2086.0	2043.2	2000.5	1996.3	1927.4	1889.8	1847.1	1853.3	1829.3
30°	2010.9	1979.6	1905.5	1797.0	1752.1	1679.0	1601.8	1521.5	1490.2	1455.7	1519.4
32.5°	1873.1	1761.5	1630.0	1489.1	1414.0	1349.3	1266.9	1208.4	1175.0	1146.8	1201.1
35°	1665.5	1491.2	1316.9	1183.4	1121.8	1063.4	986.1	956.9	915.2	919.4	924.6
37.5°	1398.3	1206.3	1074.8	943.4	902.7	878.7	822.3	777.4	762.8	758.6	758.6
40°	1147.9	990.3	873.4	770.1	738.8	719.0	674.1	653.3	637.6	633.4	638.6
42.5°	949.6	815.0	724.2	655.3	633.4	608.4	589.6	563.5	560.4	553.1	562.5
45°	797.3	680.4	612.6	562.5	543.7	534.3	513.4	497.8	491.5	490.5	497.8
47.5°	676.2	585.4	525.9	494.6	480.0	470.6	452.9	446.6	440.4	442.5	439.3
50°	567.7	499.9	461.2	433.1	423.7	414.3	402.8	396.5	393.4	393.4	392.4
52.5°	487.3	431.0	405.9	379.8	375.7	370.5	357.9	353.8	348.5	347.5	351.7
55°	417.4	378.8	353.8	338.1	333.9	323.5	318.3	313.1	309.9	307.8	308.9
57.5°	356.9	327.7	311.0	297.4	290.1	285.9	276.5	275.5	273.4	273.4	272.4
60°	306.8	285.9	266.1	257.8	252.5	247.3	246.3	240.0	236.9	239.0	237.9
62.5°	259.8	243.1	231.7	222.3	219.1	215.0	211.8	209.8	206.6	207.7	207.7
65°	217.1	203.5	195.1	186.8	185.7	181.6	180.5	178.4	178.4	177.4	179.5
67.5°	178.4	169.1	161.7	156.5	153.4	154.4	150.3	147.1	147.1	146.1	149.2
70°	141.9	136.7	129.4	123.1	119.0	119.0	113.7	112.7	112.7	112.7	111.7
72.5°	109.6	100.2	97.0	95.0	95.0	95.0	92.9	92.9	91.8	92.9	91.8
75°	81.4	80.4	78.3	77.2	77.2	76.2	75.1	75.1	75.1	75.1	75.1
77.5°	63.7	63.7	61.6	60.5	60.5	60.5	59.5	59.5	58.4	58.4	58.4
80°	47.0	47.0	44.9	44.9	44.9	43.8	43.8	43.8	44.9	43.8	43.8
82.5°	32.3	32.3	31.3	32.3	31.3	30.3	30.3	30.3	29.2	30.3	30.3
85°	18.8	18.8	17.7	16.7	17.7	17.7	16.7	17.7	16.7	17.7	16.7
87.5°	7.3	6.3	6.3	6.3	5.2	6.3	5.2	5.2	6.3	5.2	6.3
90°	31.7	32.9	34.0	35.1	35.7	36.0	36.6	37.1	37.7	38.3	37.7
92.5°	35.2	37.2	39.1	41.1	42.1	42.2	42.5	42.8	43.1	43.4	43.1
95°	41.5	43.5	45.5	47.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5
97.5°	43.1	45.3	47.6	49.9	51.0	51.1	51.4	51.7	52.0	52.3	52.0
100°	44.4	46.6	48.9	51.2	52.3	52.4	52.7	53.0	53.3	53.6	53.3
102.5°	85.0	75.7	66.3	57.0	52.3	52.6	53.1	53.7	54.2	54.8	54.2
105°	229.1	179.0	128.8	78.7	53.6	53.9	54.4	55.0	55.5	56.1	55.5
107.5°	452.5	408.8	365.2	321.5	299.7	281.1	244.0	206.9	169.7	132.6	169.7
110°	565.8	556.5	547.1	537.8	533.1	512.8	472.3	431.8	391.2	350.7	391.2

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	658.1	660.7	663.2	665.7	667.0	666.7	666.2	665.6	665.1	664.5	665.1
115°	734.9	737.7	740.6	743.4	744.8	745.4	746.5	747.6	748.8	749.9	748.8
117.5°	809.6	811.8	814.1	816.4	817.5	817.6	817.9	818.2	818.5	818.8	818.5
120°	882.3	884.5	886.8	889.1	890.2	890.2	890.2	890.2	890.2	890.2	890.2
122.5°	954.1	955.5	957.0	958.4	959.1	959.2	959.5	959.8	960.1	960.4	960.1
125°	1020.9	1021.5	1022.0	1022.6	1022.9	1023.2	1023.7	1024.3	1024.8	1025.4	1024.8
127.5°	1088.8	1089.6	1090.5	1091.4	1091.8	1091.5	1090.9	1090.4	1089.8	1089.2	1089.8
130°	1149.0	1150.2	1151.3	1152.4	1153.0	1152.7	1152.1	1151.6	1151.0	1150.4	1151.0
132.5°	1206.4	1207.6	1208.7	1209.8	1210.4	1210.0	1209.1	1208.3	1207.4	1206.6	1207.4
135°	1264.8	1265.6	1266.5	1267.4	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1264.8
137.5°	1316.4	1317.8	1319.2	1320.6	1321.3	1321.0	1320.5	1319.9	1319.4	1318.8	1319.4
140°	1365.8	1367.0	1368.1	1369.2	1369.8	1369.5	1369.0	1368.4	1367.9	1367.3	1367.9
142.5°	1412.7	1413.6	1414.4	1415.3	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1412.7
145°	1455.9	1456.4	1457.0	1457.5	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8
147.5°	1495.4	1495.9	1496.5	1497.0	1497.3	1496.6	1495.2	1493.8	1492.4	1491.0	1492.4
150°	1531.1	1531.7	1532.2	1532.8	1533.1	1532.7	1531.8	1530.9	1530.1	1529.2	1530.1
152.5°	1562.2	1563.4	1564.5	1565.6	1566.2	1565.5	1564.1	1562.6	1561.2	1559.8	1561.2
155°	1590.6	1592.0	1593.5	1594.9	1595.6	1594.7	1593.0	1591.3	1589.6	1587.9	1589.6
157.5°	1616.4	1618.1	1619.8	1621.5	1622.3	1621.2	1618.9	1616.6	1614.4	1612.1	1614.4
160°	1638.1	1639.8	1641.5	1643.2	1644.0	1643.0	1641.0	1639.1	1637.1	1635.1	1637.1
162.5°	1657.5	1659.5	1661.4	1663.4	1664.4	1663.6	1661.9	1660.2	1658.5	1656.8	1658.5
165°	1674.4	1676.6	1678.9	1681.2	1682.3	1681.3	1679.3	1677.4	1675.4	1673.4	1675.4
167.5°	1688.4	1690.6	1692.9	1695.2	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1688.4
170°	1699.9	1702.1	1704.4	1706.7	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1699.9
172.5°	1707.5	1709.7	1712.0	1714.3	1715.4	1714.1	1711.6	1709.1	1706.5	1704.0	1706.5
175°	1713.6	1715.6	1717.5	1719.5	1720.5	1719.4	1717.1	1714.8	1712.6	1710.3	1712.6
177.5°	1716.5	1718.7	1721.0	1723.3	1724.4	1723.0	1720.1	1717.3	1714.4	1711.6	1714.4
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1315.9	1309.6	1305.5	1302.3	1299.2	1308.6	1296.1	1282.5	1273.1	1266.9	1264.8
5°	1453.6	1440.1	1428.6	1419.2	1421.3	1421.3	1399.4	1375.4	1354.5	1343.0	1330.5
7.5°	1613.3	1598.7	1575.7	1570.5	1566.3	1540.3	1518.3	1474.5	1448.4	1422.3	1399.4
10°	1771.9	1753.1	1731.2	1723.9	1713.5	1681.1	1647.7	1591.4	1559.0	1511.0	1480.8
12.5°	1920.1	1897.1	1875.2	1870.0	1854.4	1826.2	1768.8	1710.4	1655.0	1603.9	1550.7
15°	2044.3	2038.0	2004.6	1983.8	1949.3	1910.7	1898.2	1818.9	1749.0	1695.7	1599.7
17.5°	2148.6	2119.4	2088.1	2074.5	2061.0	2016.1	1971.2	1889.8	1814.7	1736.4	1674.9
20°	2232.1	2199.8	2177.9	2158.0	2151.8	2100.6	2029.7	1957.7	1875.2	1787.6	1707.2
22.5°	2236.3	2232.1	2217.5	2206.0	2193.5	2160.1	2103.8	2014.0	1926.4	1830.4	1725.0
25°	2149.7	2143.4	2185.2	2174.7	2183.1	2170.6	2140.3	2065.2	1962.9	1850.2	1743.7
27.5°	1888.8	1952.5	2018.2	2041.2	2056.8	2101.7	2116.3	2074.5	1992.1	1872.1	1753.1
30°	1534.0	1618.5	1725.0	1782.4	1826.2	1909.7	2018.2	2031.8	1993.2	1897.1	1751.1
32.5°	1204.2	1281.5	1367.0	1434.9	1493.3	1664.4	1810.5	1915.9	1934.7	1884.6	1756.3
35°	970.5	1003.9	1085.3	1150.0	1229.3	1375.4	1547.6	1717.7	1832.4	1838.7	1740.6
37.5°	800.4	818.1	889.1	925.6	972.6	1100.9	1261.6	1483.9	1662.4	1746.9	1696.8
40°	662.6	703.3	744.0	764.9	798.3	887.0	1041.4	1215.7	1436.9	1593.5	1629.0
42.5°	575.0	592.7	618.8	648.0	668.9	746.1	849.4	1009.1	1208.4	1426.5	1524.6
45°	507.2	513.4	540.6	559.3	581.2	635.5	708.6	842.1	1017.4	1232.4	1399.4
47.5°	450.8	463.3	477.9	489.4	504.0	545.8	608.4	705.4	859.9	1051.9	1231.4
50°	400.7	408.0	426.8	432.0	442.5	471.7	519.7	593.8	721.1	874.5	1060.2
52.5°	353.8	367.3	374.6	381.9	391.3	415.3	446.6	507.2	603.2	747.2	904.7
55°	317.2	321.4	331.8	338.1	345.4	362.1	389.2	434.1	509.2	624.0	773.3
57.5°	281.8	281.8	292.2	297.4	304.7	317.2	341.2	375.7	429.9	515.5	652.2
60°	244.2	245.2	253.6	259.8	261.9	274.4	294.3	321.4	363.2	425.8	537.4
62.5°	210.8	216.0	220.2	222.3	229.6	236.9	253.6	272.4	301.6	356.9	436.2
65°	182.6	183.7	186.8	188.9	192.0	200.4	212.9	225.4	250.4	291.1	355.8
67.5°	150.3	154.4	158.6	158.6	161.7	165.9	178.4	188.9	207.7	231.7	275.5
70°	112.7	114.8	121.1	124.2	128.4	135.7	141.9	148.2	162.8	180.5	213.9
72.5°	93.9	93.9	96.0	97.0	97.0	102.3	111.7	117.9	125.2	137.7	160.7
75°	75.1	75.1	78.3	77.2	79.3	81.4	82.4	86.6	90.8	100.2	113.7
77.5°	59.5	60.5	60.5	61.6	61.6	62.6	63.7	65.7	67.8	73.0	79.3
80°	43.8	44.9	44.9	45.9	45.9	47.0	48.0	49.0	51.1	53.2	56.4
82.5°	30.3	31.3	31.3	32.3	31.3	32.3	33.4	33.4	34.4	36.5	37.6
85°	17.7	17.7	18.8	17.7	17.7	17.7	18.8	18.8	19.8	23.0	23.0
87.5°	5.2	6.3	5.2	6.3	6.3	6.3	6.3	7.3	7.3	8.3	9.4
90°	37.1	36.6	36.0	35.7	35.1	34.0	32.9	31.7	30.6	26.9	23.2
92.5°	42.8	42.5	42.2	42.1	41.1	39.1	37.2	35.2	33.2	30.6	28.1
95°	48.5	48.5	48.5	48.5	47.5	45.5	43.5	41.5	39.5	36.4	33.3
97.5°	51.7	51.4	51.1	51.0	49.9	47.6	45.3	43.1	40.8	55.3	69.7
100°	53.0	52.7	52.4	52.3	51.2	48.9	46.6	44.4	42.1	86.3	130.5
102.5°	53.7	53.1	52.6	52.3	57.0	66.3	75.7	85.0	94.4	143.7	193.0
105°	55.0	54.4	53.9	53.6	78.7	128.8	179.0	229.1	279.3	304.8	330.3
107.5°	206.9	244.0	281.1	299.7	321.5	365.2	408.8	452.5	496.1	491.9	487.6
110°	431.8	472.3	512.8	533.1	537.8	547.1	556.5	565.8	575.2	572.1	569.0

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	665.6	666.2	666.7	667.0	665.7	663.2	660.7	658.1	655.6	652.5	649.3
115°	747.6	746.5	745.4	744.8	743.4	740.6	737.7	734.9	732.1	729.5	727.0
117.5°	818.2	817.9	817.6	817.5	816.4	814.1	811.8	809.6	807.3	805.9	804.5
120°	890.2	890.2	890.2	890.2	889.1	886.8	884.5	882.3	880.0	879.2	878.3
122.5°	959.8	959.5	959.2	959.1	958.4	957.0	955.5	954.1	952.7	951.6	950.4
125°	1024.3	1023.7	1023.2	1022.9	1022.6	1022.0	1021.5	1020.9	1020.3	1019.2	1018.0
127.5°	1090.4	1090.9	1091.5	1091.8	1091.4	1090.5	1089.6	1088.8	1087.9	1086.5	1085.1
130°	1151.6	1152.1	1152.7	1153.0	1152.4	1151.3	1150.2	1149.0	1147.9	1146.8	1145.6
132.5°	1208.3	1209.1	1210.0	1210.4	1209.8	1208.7	1207.6	1206.4	1205.3	1204.5	1203.6
135°	1265.6	1266.5	1267.4	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1262.8	1261.6
137.5°	1319.9	1320.5	1321.0	1321.3	1320.6	1319.2	1317.8	1316.4	1315.0	1314.4	1313.8
140°	1368.4	1369.0	1369.5	1369.8	1369.2	1368.1	1367.0	1365.8	1364.7	1363.9	1363.0
142.5°	1413.6	1414.4	1415.3	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1411.1	1410.2
145°	1457.8	1457.8	1457.8	1457.8	1457.5	1457.0	1456.4	1455.9	1455.3	1454.7	1454.1
147.5°	1493.8	1495.2	1496.6	1497.3	1497.0	1496.5	1495.9	1495.4	1494.8	1494.2	1493.6
150°	1530.9	1531.8	1532.7	1533.1	1532.8	1532.2	1531.7	1531.1	1530.5	1529.9	1529.4
152.5°	1562.6	1564.1	1565.5	1566.2	1565.6	1564.5	1563.4	1562.2	1561.1	1560.8	1560.5
155°	1591.3	1593.0	1594.7	1595.6	1594.9	1593.5	1592.0	1590.6	1589.2	1588.9	1588.6
157.5°	1616.6	1618.9	1621.2	1622.3	1621.5	1619.8	1618.1	1616.4	1614.7	1615.0	1615.3
160°	1639.1	1641.0	1643.0	1644.0	1643.2	1641.5	1639.8	1638.1	1636.4	1636.7	1636.9
162.5°	1660.2	1661.9	1663.6	1664.4	1663.4	1661.4	1659.5	1657.5	1655.5	1655.8	1656.1
165°	1677.4	1679.3	1681.3	1682.3	1681.2	1678.9	1676.6	1674.4	1672.1	1672.4	1672.7
167.5°	1690.6	1692.9	1695.2	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1686.1	1686.1
170°	1702.1	1704.4	1706.7	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1697.6	1697.6
172.5°	1709.1	1711.6	1714.1	1715.4	1714.3	1712.0	1709.7	1707.5	1705.2	1704.9	1704.7
175°	1714.8	1717.1	1719.4	1720.5	1719.5	1717.5	1715.6	1713.6	1711.6	1711.3	1711.0
177.5°	1717.3	1720.1	1723.0	1724.4	1723.3	1721.0	1718.7	1716.5	1714.2	1713.9	1713.6
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1261.6	1256.4	1251.2	1251.2	1239.7	1229.3	1224.1	1226.2	1219.9	1211.5	1203.2
5°	1316.9	1296.1	1291.9	1280.4	1264.8	1242.8	1231.4	1220.9	1208.4	1191.7	1176.1
7.5°	1368.1	1340.9	1326.3	1314.9	1284.6	1254.3	1229.3	1212.6	1190.7	1165.6	1146.8
10°	1434.9	1384.8	1369.1	1343.0	1300.2	1257.5	1228.2	1201.1	1170.8	1141.6	1116.6
12.5°	1488.1	1430.7	1401.5	1375.4	1320.1	1265.8	1216.8	1183.4	1146.8	1114.5	1082.1
15°	1548.6	1483.9	1432.8	1401.5	1331.6	1265.8	1210.5	1163.5	1122.8	1083.2	1055.0
17.5°	1577.8	1496.4	1473.5	1428.6	1327.4	1261.6	1193.8	1143.7	1094.7	1048.8	1015.4
20°	1623.7	1528.8	1471.4	1441.1	1351.4	1254.3	1175.0	1117.6	1066.5	1017.4	982.0
22.5°	1626.9	1523.6	1486.0	1428.6	1318.0	1232.4	1158.3	1088.4	1028.9	983.0	946.5
25°	1619.6	1514.2	1462.0	1416.1	1324.2	1219.9	1124.9	1056.1	997.6	944.4	901.6
27.5°	1616.4	1487.0	1438.0	1392.1	1288.8	1183.4	1105.1	1026.8	960.1	913.1	869.3
30°	1612.3	1457.8	1398.3	1345.1	1250.2	1155.2	1061.3	993.4	929.8	870.3	826.5
32.5°	1585.1	1418.2	1357.6	1301.3	1199.0	1104.1	1030.0	958.0	889.1	833.8	794.1
35°	1576.8	1381.6	1302.3	1241.8	1141.6	1057.1	978.8	919.4	854.7	799.3	752.4
37.5°	1552.8	1344.1	1258.5	1181.3	1076.9	996.6	939.2	879.7	817.1	757.6	720.0
40°	1511.0	1300.2	1203.2	1123.9	1016.4	935.0	881.8	838.0	776.4	723.2	677.3
42.5°	1449.5	1255.4	1151.0	1067.5	948.6	872.4	828.6	786.8	734.6	679.3	641.8
45°	1378.5	1195.9	1098.8	1006.0	884.9	810.8	764.9	739.9	691.9	644.9	601.1
47.5°	1281.5	1134.3	1038.3	942.3	819.2	747.2	710.6	685.6	652.2	601.1	565.6
50°	1159.4	1055.0	964.2	878.7	754.5	685.6	649.1	630.3	602.1	565.6	531.2
52.5°	1023.7	963.2	888.0	808.7	688.7	624.0	590.6	576.0	555.2	520.7	491.5
55°	887.0	860.9	809.8	731.5	619.9	566.6	537.4	518.6	503.0	477.9	452.9
57.5°	764.9	752.4	716.9	656.4	562.5	507.2	482.1	469.6	457.1	438.3	413.2
60°	638.6	652.2	615.7	585.4	499.9	451.9	429.9	416.4	410.1	393.4	377.8
62.5°	529.1	541.6	520.7	497.8	437.2	394.5	380.9	368.4	364.2	349.6	333.9
65°	429.9	445.6	429.9	417.4	380.9	345.4	328.7	322.5	318.3	308.9	296.4
67.5°	342.3	357.9	350.6	335.0	323.5	294.3	284.9	278.6	276.5	269.2	258.8
70°	257.8	279.7	281.8	272.4	261.9	248.4	242.1	240.0	234.8	228.5	222.3
72.5°	185.7	210.8	211.8	211.8	205.6	205.6	199.3	196.2	196.2	189.9	182.6
75°	136.7	153.4	155.5	157.6	160.7	163.8	159.7	159.7	158.6	152.4	149.2
77.5°	90.8	105.4	110.6	117.9	122.1	122.1	124.2	126.3	124.2	121.1	119.0
80°	58.4	68.9	75.1	79.3	85.6	88.7	91.8	92.9	90.8	89.7	86.6
82.5°	38.6	41.7	44.9	50.1	57.4	62.6	62.6	61.6	63.7	62.6	61.6
85°	21.9	24.0	25.0	26.1	30.3	35.5	36.5	37.6	39.7	37.6	35.5
87.5°	8.3	9.4	9.4	9.4	11.5	12.5	15.7	19.8	18.8	16.7	16.7
90°	19.5	15.8	14.0	12.6	9.8	6.9	4.1	1.3	4.1	6.9	9.8
92.5°	25.5	23.0	21.7	22.5	24.2	25.9	27.6	29.3	27.6	25.9	24.2
95°	30.2	27.1	25.5	31.3	42.9	54.6	66.2	77.8	66.2	54.6	42.9
97.5°	84.2	98.7	105.9	109.9	117.8	125.7	133.7	141.6	133.7	125.7	117.8
100°	174.8	219.0	241.1	238.3	232.6	226.9	221.2	215.5	221.2	226.9	232.6
102.5°	242.3	291.6	316.3	314.5	310.8	307.1	303.4	299.7	303.4	307.1	310.8
105°	355.8	381.3	394.1	392.5	389.4	386.3	383.2	380.1	383.2	386.3	389.4
107.5°	483.4	479.1	477.0	475.7	473.2	470.6	468.1	465.5	468.1	470.6	473.2
110°	565.9	562.8	561.2	560.1	557.8	555.5	553.3	551.0	553.3	555.5	557.8

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	646.2	643.1	641.5	640.5	638.5	636.6	634.6	632.6	634.6	636.6	638.5
115°	724.4	721.9	720.6	719.8	718.1	716.4	714.7	713.0	714.7	716.4	718.1
117.5°	803.1	801.7	801.0	800.0	798.0	796.0	794.0	792.0	794.0	796.0	798.0
120°	877.5	876.6	876.2	874.9	872.4	869.8	867.3	864.7	867.3	869.8	872.4
122.5°	949.3	948.2	947.6	946.6	944.6	942.7	940.7	938.7	940.7	942.7	944.6
125°	1016.9	1015.8	1015.2	1014.1	1011.8	1009.5	1007.3	1005.0	1007.3	1009.5	1011.8
127.5°	1083.7	1082.3	1081.6	1080.5	1078.2	1075.9	1073.7	1071.4	1073.7	1075.9	1078.2
130°	1144.5	1143.4	1142.8	1141.7	1139.4	1137.1	1134.9	1132.6	1134.9	1137.1	1139.4
132.5°	1202.8	1201.9	1201.5	1200.4	1198.1	1195.8	1193.5	1191.2	1193.5	1195.8	1198.1
135°	1260.5	1259.4	1258.8	1258.0	1256.3	1254.6	1252.9	1251.2	1252.9	1254.6	1256.3
137.5°	1313.3	1312.7	1312.4	1311.3	1309.0	1306.7	1304.5	1302.2	1304.5	1306.7	1309.0
140°	1362.2	1361.3	1360.9	1360.0	1358.3	1356.6	1354.9	1353.2	1354.9	1356.6	1358.3
142.5°	1409.4	1408.5	1408.1	1407.2	1405.5	1403.8	1402.1	1400.4	1402.1	1403.8	1405.5
145°	1453.6	1453.0	1452.7	1451.7	1449.7	1447.8	1445.8	1443.8	1445.8	1447.8	1449.7
147.5°	1493.1	1492.5	1492.2	1491.5	1490.1	1488.7	1487.3	1485.9	1487.3	1488.7	1490.1
150°	1528.8	1528.3	1528.0	1527.6	1526.7	1525.8	1525.0	1524.1	1525.0	1525.8	1526.7
152.5°	1560.2	1559.9	1559.8	1559.7	1559.4	1559.1	1558.9	1558.6	1558.9	1559.1	1559.4
155°	1588.3	1588.0	1587.9	1588.2	1588.8	1589.3	1589.9	1590.5	1589.9	1589.3	1588.8
157.5°	1615.6	1615.9	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0
160°	1637.2	1637.5	1637.6	1637.7	1638.0	1638.3	1638.6	1638.9	1638.6	1638.3	1638.0
162.5°	1656.4	1656.7	1656.8	1657.2	1658.1	1658.9	1659.8	1660.6	1659.8	1658.9	1658.1
165°	1673.0	1673.3	1673.4	1673.8	1674.7	1675.5	1676.4	1677.2	1676.4	1675.5	1674.7
167.5°	1686.1	1686.1	1686.1	1686.7	1687.8	1688.9	1690.1	1691.2	1690.1	1688.9	1687.8
170°	1697.6	1697.6	1697.6	1698.2	1699.3	1700.4	1701.6	1702.7	1701.6	1700.4	1699.3
172.5°	1704.4	1704.1	1704.0	1704.7	1706.1	1707.5	1708.9	1710.3	1708.9	1707.5	1706.1
175°	1710.7	1710.4	1710.3	1711.0	1712.4	1713.9	1715.3	1716.7	1715.3	1713.9	1712.4
177.5°	1713.3	1713.0	1712.9	1713.6	1715.0	1716.5	1717.9	1719.3	1717.9	1716.5	1715.0
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1203.2	1198.0	1195.9	1190.7	1178.2	1169.8	1160.4	1154.1	1155.2	1150.0	1153.1
5°	1165.6	1164.6	1157.3	1146.8	1129.1	1119.7	1103.0	1094.7	1090.5	1091.5	1085.3
7.5°	1134.3	1124.9	1119.7	1103.0	1086.3	1066.5	1052.9	1045.6	1039.4	1033.1	1028.9
10°	1098.8	1090.5	1082.1	1064.4	1041.4	1022.7	1003.9	996.6	987.2	983.0	979.9
12.5°	1061.3	1056.1	1045.6	1024.8	998.7	980.9	959.0	954.8	942.3	934.0	931.9
15°	1026.8	1023.7	1004.9	980.9	954.8	937.1	918.3	905.8	884.9	889.1	881.8
17.5°	990.3	976.7	965.3	932.9	920.4	893.3	871.4	865.1	850.5	841.1	831.7
20°	949.6	941.3	926.7	905.8	875.5	844.2	827.5	817.1	808.7	794.1	790.0
22.5°	911.0	900.6	888.0	860.9	834.8	808.7	785.8	776.4	766.0	755.5	749.3
25°	880.7	865.1	851.5	818.1	792.0	770.1	755.5	739.9	725.3	719.0	716.9
27.5°	833.8	824.4	810.8	779.5	755.5	731.5	718.0	707.5	691.9	684.6	678.3
30°	803.5	784.7	769.1	744.0	720.0	694.0	681.4	668.9	659.5	650.1	642.8
32.5°	762.8	748.2	735.7	710.6	686.6	662.6	649.1	630.3	625.1	617.8	609.4
35°	723.2	713.8	700.2	673.1	647.0	630.3	615.7	597.9	591.7	586.5	579.2
37.5°	685.6	672.0	662.6	636.6	613.6	593.8	582.3	567.7	563.5	557.2	552.0
40°	653.3	639.7	630.3	604.2	580.2	559.3	552.0	537.4	531.2	523.9	520.7
42.5°	616.7	605.3	592.7	573.9	548.9	528.0	513.4	505.1	496.7	493.6	487.3
45°	578.1	567.7	558.3	537.4	511.3	496.7	484.2	472.7	466.5	461.2	457.1
47.5°	544.7	535.3	522.8	499.9	479.0	465.4	452.9	441.4	435.2	428.9	423.7
50°	506.1	500.9	487.3	465.4	445.6	429.9	418.5	408.0	403.8	396.5	388.2
52.5°	471.7	462.3	450.8	433.1	415.3	396.5	380.9	374.6	367.3	363.2	355.8
55°	431.0	424.7	412.2	396.5	377.8	362.1	350.6	342.3	332.9	328.7	319.3
57.5°	396.5	385.1	378.8	359.0	341.2	325.6	317.2	308.9	298.5	292.2	288.0
60°	359.0	348.5	339.1	322.5	309.9	293.2	280.7	273.4	266.1	257.8	253.6
62.5°	322.5	314.1	302.6	289.1	273.4	259.8	250.4	240.0	235.8	227.5	224.4
65°	282.8	276.5	267.1	251.5	239.0	227.5	218.1	209.8	205.6	202.4	200.4
67.5°	247.3	239.0	232.7	219.1	205.6	196.2	191.0	185.7	180.5	177.4	174.3
70°	210.8	204.5	198.3	185.7	176.4	168.0	163.8	159.7	156.5	153.4	150.3
72.5°	173.2	170.1	163.8	155.5	148.2	141.9	138.8	133.6	130.4	125.2	123.1
75°	143.0	137.7	134.6	127.3	121.1	115.8	111.7	105.4	101.2	99.1	98.1
77.5°	112.7	110.6	106.4	100.2	97.0	91.8	85.6	83.5	81.4	81.4	80.4
80°	84.5	81.4	78.3	73.0	69.9	65.7	65.7	65.7	64.7	65.7	64.7
82.5°	57.4	55.3	53.2	50.1	49.0	49.0	50.1	50.1	50.1	50.1	50.1
85°	33.4	33.4	33.4	34.4	33.4	33.4	34.4	35.5	34.4	34.4	33.4
87.5°	15.7	15.7	16.7	16.7	17.7	17.7	17.7	17.7	17.7	17.7	18.8
90°	12.6	14.0	15.8	19.5	23.2	26.9	30.6	31.7	32.9	34.0	35.1
92.5°	22.5	21.7	23.0	25.5	28.1	30.6	33.2	35.2	37.2	39.1	41.1
95°	31.3	25.5	27.1	30.2	33.3	36.4	39.5	41.5	43.5	45.5	47.5
97.5°	109.9	105.9	98.7	84.2	69.7	55.3	40.8	43.1	45.3	47.6	49.9
100°	238.3	241.1	219.0	174.8	130.5	86.3	42.1	44.4	46.6	48.9	51.2
102.5°	314.5	316.3	291.6	242.3	193.0	143.7	94.4	85.0	75.7	66.3	57.0
105°	392.5	394.1	381.3	355.8	330.3	304.8	279.3	229.1	179.0	128.8	78.7
107.5°	475.7	477.0	479.1	483.4	487.6	491.9	496.1	452.5	408.8	365.2	321.5
110°	560.1	561.2	562.8	565.9	569.0	572.1	575.2	565.8	556.5	547.1	537.8

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	640.5	641.5	643.1	646.2	649.3	652.5	655.6	658.1	660.7	663.2	665.7
115°	719.8	720.6	721.9	724.4	727.0	729.5	732.1	734.9	737.7	740.6	743.4
117.5°	800.0	801.0	801.7	803.1	804.5	805.9	807.3	809.6	811.8	814.1	816.4
120°	874.9	876.2	876.6	877.5	878.3	879.2	880.0	882.3	884.5	886.8	889.1
122.5°	946.6	947.6	948.2	949.3	950.4	951.6	952.7	954.1	955.5	957.0	958.4
125°	1014.1	1015.2	1015.8	1016.9	1018.0	1019.2	1020.3	1020.9	1021.5	1022.0	1022.6
127.5°	1080.5	1081.6	1082.3	1083.7	1085.1	1086.5	1087.9	1088.8	1089.6	1090.5	1091.4
130°	1141.7	1142.8	1143.4	1144.5	1145.6	1146.8	1147.9	1149.0	1150.2	1151.3	1152.4
132.5°	1200.4	1201.5	1201.9	1202.8	1203.6	1204.5	1205.3	1206.4	1207.6	1208.7	1209.8
135°	1258.0	1258.8	1259.4	1260.5	1261.6	1262.8	1263.9	1264.8	1265.6	1266.5	1267.4
137.5°	1311.3	1312.4	1312.7	1313.3	1313.8	1314.4	1315.0	1316.4	1317.8	1319.2	1320.6
140°	1360.0	1360.9	1361.3	1362.2	1363.0	1363.9	1364.7	1365.8	1367.0	1368.1	1369.2
142.5°	1407.2	1408.1	1408.5	1409.4	1410.2	1411.1	1411.9	1412.7	1413.6	1414.4	1415.3
145°	1451.7	1452.7	1453.0	1453.6	1454.1	1454.7	1455.3	1455.9	1456.4	1457.0	1457.5
147.5°	1491.5	1492.2	1492.5	1493.1	1493.6	1494.2	1494.8	1495.4	1495.9	1496.5	1497.0
150°	1527.6	1528.0	1528.3	1528.8	1529.4	1529.9	1530.5	1531.1	1531.7	1532.2	1532.8
152.5°	1559.7	1559.8	1559.9	1560.2	1560.5	1560.8	1561.1	1562.2	1563.4	1564.5	1565.6
155°	1588.2	1587.9	1588.0	1588.3	1588.6	1588.9	1589.2	1590.6	1592.0	1593.5	1594.9
157.5°	1616.0	1616.0	1615.9	1615.6	1615.3	1615.0	1614.7	1616.4	1618.1	1619.8	1621.5
160°	1637.7	1637.6	1637.5	1637.2	1636.9	1636.7	1636.4	1638.1	1639.8	1641.5	1643.2
162.5°	1657.2	1656.8	1656.7	1656.4	1656.1	1655.8	1655.5	1657.5	1659.5	1661.4	1663.4
165°	1673.8	1673.4	1673.3	1673.0	1672.7	1672.4	1672.1	1674.4	1676.6	1678.9	1681.2
167.5°	1686.7	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1	1688.4	1690.6	1692.9	1695.2
170°	1698.2	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6	1699.9	1702.1	1704.4	1706.7
172.5°	1704.7	1704.0	1704.1	1704.4	1704.7	1704.9	1705.2	1707.5	1709.7	1712.0	1714.3
175°	1711.0	1710.3	1710.4	1710.7	1711.0	1711.3	1711.6	1713.6	1715.6	1717.5	1719.5
177.5°	1713.6	1712.9	1713.0	1713.3	1713.6	1713.9	1714.2	1716.5	1718.7	1721.0	1723.3
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1152.1	1153.1	1150.0	1143.7	1142.7	1144.8	1151.0	1148.9	1143.7	1153.1	1144.8
5°	1088.4	1083.2	1081.1	1083.2	1076.9	1073.8	1080.1	1076.9	1080.1	1081.1	1084.2
7.5°	1026.8	1027.9	1021.6	1022.7	1014.3	1016.4	1016.4	1016.4	1019.5	1021.6	1025.8
10°	973.6	975.7	968.4	969.4	963.2	959.0	962.1	968.4	968.4	968.4	970.5
12.5°	930.8	921.4	916.2	915.2	907.9	905.8	912.0	914.1	919.4	919.4	922.5
15°	877.6	875.5	871.4	871.4	853.6	857.8	859.9	867.2	877.6	869.3	871.4
17.5°	829.6	824.4	819.2	817.1	815.0	808.7	817.1	816.0	822.3	823.3	826.5
20°	786.8	782.7	772.2	773.3	775.3	766.0	771.2	771.2	777.4	783.7	791.0
22.5°	745.1	740.9	735.7	737.8	731.5	729.4	729.4	734.6	742.0	747.2	746.1
25°	712.7	705.4	702.3	699.2	696.0	698.1	695.0	700.2	705.4	708.6	705.4
27.5°	676.2	673.1	666.8	663.7	658.5	660.6	662.6	666.8	669.9	669.9	673.1
30°	640.7	636.6	634.5	631.3	631.3	627.2	628.2	632.4	635.5	638.6	642.8
32.5°	606.3	603.2	600.0	600.0	597.9	596.9	595.9	602.1	602.1	608.4	608.4
35°	578.1	572.9	572.9	567.7	569.8	568.7	566.6	570.8	571.9	576.0	575.0
37.5°	546.8	546.8	544.7	539.5	535.3	536.4	541.6	541.6	544.7	543.7	546.8
40°	515.5	513.4	513.4	510.3	509.2	508.2	509.2	510.3	515.5	514.5	515.5
42.5°	484.2	485.2	480.0	480.0	480.0	476.9	477.9	479.0	481.1	483.2	486.3
45°	453.9	451.9	450.8	448.7	446.6	447.7	446.6	450.8	449.8	451.9	455.0
47.5°	421.6	418.5	417.4	413.2	413.2	415.3	414.3	417.4	418.5	421.6	419.5
50°	390.3	386.1	383.0	384.0	377.8	379.8	379.8	383.0	386.1	387.2	389.2
52.5°	353.8	352.7	351.7	346.5	345.4	344.4	345.4	346.5	350.6	353.8	354.8
55°	318.3	317.2	311.0	308.9	305.8	305.8	307.8	308.9	316.2	317.2	321.4
57.5°	285.9	282.8	275.5	274.4	274.4	274.4	271.3	275.5	277.6	282.8	282.8
60°	250.4	250.4	244.2	244.2	245.2	244.2	244.2	245.2	245.2	249.4	251.5
62.5°	222.3	221.2	221.2	219.1	218.1	219.1	218.1	218.1	219.1	222.3	225.4
65°	197.2	196.2	195.1	194.1	192.0	192.0	193.1	195.1	195.1	197.2	198.3
67.5°	173.2	173.2	171.1	171.1	170.1	169.1	170.1	169.1	173.2	173.2	174.3
70°	149.2	148.2	145.1	144.0	140.9	141.9	141.9	145.1	146.1	148.2	150.3
72.5°	120.0	120.0	117.9	115.8	116.9	114.8	114.8	115.8	115.8	119.0	120.0
75°	99.1	97.0	96.0	97.0	96.0	98.1	96.0	96.0	98.1	98.1	98.1
77.5°	81.4	81.4	80.4	80.4	81.4	80.4	81.4	81.4	81.4	80.4	81.4
80°	66.8	65.7	65.7	65.7	64.7	64.7	64.7	64.7	64.7	64.7	64.7
82.5°	50.1	50.1	49.0	50.1	50.1	49.0	50.1	49.0	49.0	50.1	50.1
85°	33.4	35.5	33.4	33.4	34.4	34.4	35.5	34.4	35.5	33.4	34.4
87.5°	17.7	18.8	18.8	17.7	17.7	18.8	18.8	18.8	19.8	17.7	18.8
90°	35.7	36.0	36.6	37.1	37.7	38.3	37.7	37.1	36.6	36.0	35.7
92.5°	42.1	42.2	42.5	42.8	43.1	43.4	43.1	42.8	42.5	42.2	42.1
95°	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5
97.5°	51.0	51.1	51.4	51.7	52.0	52.3	52.0	51.7	51.4	51.1	51.0
100°	52.3	52.4	52.7	53.0	53.3	53.6	53.3	53.0	52.7	52.4	52.3
102.5°	52.3	52.6	53.1	53.7	54.2	54.8	54.2	53.7	53.1	52.6	52.3
105°	53.6	53.9	54.4	55.0	55.5	56.1	55.5	55.0	54.4	53.9	53.6
107.5°	299.7	281.1	244.0	206.9	169.7	132.6	169.7	206.9	244.0	281.1	299.7
110°	533.1	512.8	472.3	431.8	391.2	350.7	391.2	431.8	472.3	512.8	533.1

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	667.0	666.7	666.2	665.6	665.1	664.5	665.1	665.6	666.2	666.7	667.0
115°	744.8	745.4	746.5	747.6	748.8	749.9	748.8	747.6	746.5	745.4	744.8
117.5°	817.5	817.6	817.9	818.2	818.5	818.8	818.5	818.2	817.9	817.6	817.5
120°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
122.5°	959.1	959.2	959.5	959.8	960.1	960.4	960.1	959.8	959.5	959.2	959.1
125°	1022.9	1023.2	1023.7	1024.3	1024.8	1025.4	1024.8	1024.3	1023.7	1023.2	1022.9
127.5°	1091.8	1091.5	1090.9	1090.4	1089.8	1089.2	1089.8	1090.4	1090.9	1091.5	1091.8
130°	1153.0	1152.7	1152.1	1151.6	1151.0	1150.4	1151.0	1151.6	1152.1	1152.7	1153.0
132.5°	1210.4	1210.0	1209.1	1208.3	1207.4	1206.6	1207.4	1208.3	1209.1	1210.0	1210.4
135°	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1264.8	1265.6	1266.5	1267.4	1267.8
137.5°	1321.3	1321.0	1320.5	1319.9	1319.4	1318.8	1319.4	1319.9	1320.5	1321.0	1321.3
140°	1369.8	1369.5	1369.0	1368.4	1367.9	1367.3	1367.9	1368.4	1369.0	1369.5	1369.8
142.5°	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1412.7	1413.6	1414.4	1415.3	1415.7
145°	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8
147.5°	1497.3	1496.6	1495.2	1493.8	1492.4	1491.0	1492.4	1493.8	1495.2	1496.6	1497.3
150°	1533.1	1532.7	1531.8	1530.9	1530.1	1529.2	1530.1	1530.9	1531.8	1532.7	1533.1
152.5°	1566.2	1565.5	1564.1	1562.6	1561.2	1559.8	1561.2	1562.6	1564.1	1565.5	1566.2
155°	1595.6	1594.7	1593.0	1591.3	1589.6	1587.9	1589.6	1591.3	1593.0	1594.7	1595.6
157.5°	1622.3	1621.2	1618.9	1616.6	1614.4	1612.1	1614.4	1616.6	1618.9	1621.2	1622.3
160°	1644.0	1643.0	1641.0	1639.1	1637.1	1635.1	1637.1	1639.1	1641.0	1643.0	1644.0
162.5°	1664.4	1663.6	1661.9	1660.2	1658.5	1656.8	1658.5	1660.2	1661.9	1663.6	1664.4
165°	1682.3	1681.3	1679.3	1677.4	1675.4	1673.4	1675.4	1677.4	1679.3	1681.3	1682.3
167.5°	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1688.4	1690.6	1692.9	1695.2	1696.3
170°	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1699.9	1702.1	1704.4	1706.7	1707.8
172.5°	1715.4	1714.1	1711.6	1709.1	1706.5	1704.0	1706.5	1709.1	1711.6	1714.1	1715.4
175°	1720.5	1719.4	1717.1	1714.8	1712.6	1710.3	1712.6	1714.8	1717.1	1719.4	1720.5
177.5°	1724.4	1723.0	1720.1	1717.3	1714.4	1711.6	1714.4	1717.3	1720.1	1723.0	1724.4
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1153.1	1157.3	1153.1	1144.8	1153.1	1158.3	1163.5	1171.9	1176.1	1176.1	1182.3
5°	1087.4	1095.7	1092.6	1090.5	1098.8	1104.1	1112.4	1122.8	1134.3	1141.6	1150.0
7.5°	1028.9	1034.1	1039.4	1039.4	1047.7	1059.2	1071.7	1084.2	1098.8	1109.3	1115.5
10°	977.8	982.0	985.1	989.3	1001.8	1014.3	1031.0	1046.7	1059.2	1070.7	1081.1
12.5°	928.7	935.0	942.3	945.4	954.8	970.5	986.1	1004.9	1024.8	1036.2	1046.7
15°	881.8	884.9	893.3	902.7	911.0	927.7	947.5	967.4	984.1	1001.8	1011.2
17.5°	833.8	834.8	856.7	851.5	878.7	894.3	904.7	923.5	950.7	965.3	979.9
20°	786.8	797.3	806.7	811.9	826.5	844.2	874.5	889.1	911.0	924.6	937.1
22.5°	750.3	766.0	766.0	778.5	785.8	802.5	824.4	852.6	876.6	886.0	903.7
25°	718.0	725.3	737.8	742.0	755.5	770.1	784.7	815.0	841.1	853.6	866.1
27.5°	676.2	685.6	702.3	702.3	720.0	735.7	753.4	773.3	799.3	817.1	830.7
30°	643.9	653.3	660.6	672.0	679.3	694.0	725.3	739.9	762.8	778.5	795.2
32.5°	613.6	620.9	627.2	639.7	648.0	664.7	681.4	707.5	727.3	742.0	759.7
35°	580.2	587.5	595.9	605.3	617.8	633.4	649.1	671.0	690.8	704.4	719.0
37.5°	548.9	554.1	566.6	572.9	583.3	597.9	617.8	640.7	658.5	668.9	683.5
40°	518.6	522.8	532.2	543.7	551.0	562.5	583.3	603.2	625.1	637.6	649.1
42.5°	486.3	491.5	499.9	511.3	522.8	535.3	546.8	569.8	589.6	600.0	612.6
45°	458.1	461.2	467.5	479.0	490.5	499.9	517.6	538.5	557.2	565.6	579.2
47.5°	424.7	427.8	437.2	442.5	455.0	467.5	485.2	506.1	522.8	531.2	543.7
50°	390.3	393.4	399.7	411.2	419.5	433.1	448.7	466.5	487.3	498.8	506.1
52.5°	356.9	363.2	368.4	377.8	388.2	401.8	416.4	433.1	450.8	462.3	470.6
55°	323.5	328.7	335.0	340.2	352.7	365.2	381.9	397.6	413.2	423.7	433.1
57.5°	285.9	293.2	299.5	309.9	319.3	329.8	348.5	361.1	379.8	387.2	395.5
60°	253.6	260.9	266.1	274.4	282.8	296.4	308.9	324.5	340.2	349.6	360.0
62.5°	226.4	229.6	232.7	241.1	249.4	261.9	274.4	290.1	306.8	312.0	320.4
65°	199.3	202.4	207.7	215.0	221.2	228.5	242.1	254.6	270.3	278.6	281.8
67.5°	176.4	179.5	180.5	185.7	191.0	199.3	206.6	219.1	233.8	239.0	245.2
70°	150.3	155.5	156.5	160.7	162.8	168.0	176.4	185.7	197.2	206.6	211.8
72.5°	120.0	127.3	129.4	135.7	138.8	144.0	150.3	157.6	164.9	169.1	173.2
75°	98.1	100.2	101.2	106.4	111.7	119.0	122.1	126.3	132.5	137.7	141.9
77.5°	81.4	82.4	83.5	83.5	84.5	88.7	95.0	100.2	104.4	106.4	109.6
80°	65.7	64.7	64.7	65.7	65.7	65.7	67.8	75.1	77.2	82.4	81.4
82.5°	51.1	49.0	50.1	49.0	49.0	49.0	49.0	50.1	50.1	53.2	55.3
85°	33.4	34.4	33.4	33.4	32.3	33.4	32.3	32.3	31.3	31.3	30.3
87.5°	17.7	18.8	17.7	17.7	16.7	17.7	16.7	16.7	15.7	15.7	13.6
90°	35.1	34.0	32.9	31.7	30.6	26.9	23.2	19.5	15.8	14.0	12.6
92.5°	41.1	39.1	37.2	35.2	33.2	30.6	28.1	25.5	23.0	21.7	22.5
95°	47.5	45.5	43.5	41.5	39.5	36.4	33.3	30.2	27.1	25.5	31.3
97.5°	49.9	47.6	45.3	43.1	40.8	55.3	69.7	84.2	98.7	105.9	109.9
100°	51.2	48.9	46.6	44.4	42.1	86.3	130.5	174.8	219.0	241.1	238.3
102.5°	57.0	66.3	75.7	85.0	94.4	143.7	193.0	242.3	291.6	316.3	314.5
105°	78.7	128.8	179.0	229.1	279.3	304.8	330.3	355.8	381.3	394.1	392.5
107.5°	321.5	365.2	408.8	452.5	496.1	491.9	487.6	483.4	479.1	477.0	475.7
110°	537.8	547.1	556.5	565.8	575.2	572.1	569.0	565.9	562.8	561.2	560.1

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	665.7	663.2	660.7	658.1	655.6	652.5	649.3	646.2	643.1	641.5	640.5
115°	743.4	740.6	737.7	734.9	732.1	729.5	727.0	724.4	721.9	720.6	719.8
117.5°	816.4	814.1	811.8	809.6	807.3	805.9	804.5	803.1	801.7	801.0	800.0
120°	889.1	886.8	884.5	882.3	880.0	879.2	878.3	877.5	876.6	876.2	874.9
122.5°	958.4	957.0	955.5	954.1	952.7	951.6	950.4	949.3	948.2	947.6	946.6
125°	1022.6	1022.0	1021.5	1020.9	1020.3	1019.2	1018.0	1016.9	1015.8	1015.2	1014.1
127.5°	1091.4	1090.5	1089.6	1088.8	1087.9	1086.5	1085.1	1083.7	1082.3	1081.6	1080.5
130°	1152.4	1151.3	1150.2	1149.0	1147.9	1146.8	1145.6	1144.5	1143.4	1142.8	1141.7
132.5°	1209.8	1208.7	1207.6	1206.4	1205.3	1204.5	1203.6	1202.8	1201.9	1201.5	1200.4
135°	1267.4	1266.5	1265.6	1264.8	1263.9	1262.8	1261.6	1260.5	1259.4	1258.8	1258.0
137.5°	1320.6	1319.2	1317.8	1316.4	1315.0	1314.4	1313.8	1313.3	1312.7	1312.4	1311.3
140°	1369.2	1368.1	1367.0	1365.8	1364.7	1363.9	1363.0	1362.2	1361.3	1360.9	1360.0
142.5°	1415.3	1414.4	1413.6	1412.7	1411.9	1411.1	1410.2	1409.4	1408.5	1408.1	1407.2
145°	1457.5	1457.0	1456.4	1455.9	1455.3	1454.7	1454.1	1453.6	1453.0	1452.7	1451.7
147.5°	1497.0	1496.5	1495.9	1495.4	1494.8	1494.2	1493.6	1493.1	1492.5	1492.2	1491.5
150°	1532.8	1532.2	1531.7	1531.1	1530.5	1529.9	1529.4	1528.8	1528.3	1528.0	1527.6
152.5°	1565.6	1564.5	1563.4	1562.2	1561.1	1560.8	1560.5	1560.2	1559.9	1559.8	1559.7
155°	1594.9	1593.5	1592.0	1590.6	1589.2	1588.9	1588.6	1588.3	1588.0	1587.9	1588.2
157.5°	1621.5	1619.8	1618.1	1616.4	1614.7	1615.0	1615.3	1615.6	1615.9	1616.0	1616.0
160°	1643.2	1641.5	1639.8	1638.1	1636.4	1636.7	1636.9	1637.2	1637.5	1637.6	1637.7
162.5°	1663.4	1661.4	1659.5	1657.5	1655.5	1655.8	1656.1	1656.4	1656.7	1656.8	1657.2
165°	1681.2	1678.9	1676.6	1674.4	1672.1	1672.4	1672.7	1673.0	1673.3	1673.4	1673.8
167.5°	1695.2	1692.9	1690.6	1688.4	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1	1686.7
170°	1706.7	1704.4	1702.1	1699.9	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6	1698.2
172.5°	1714.3	1712.0	1709.7	1707.5	1705.2	1704.9	1704.7	1704.4	1704.1	1704.0	1704.7
175°	1719.5	1717.5	1715.6	1713.6	1711.6	1711.3	1711.0	1710.7	1710.4	1710.3	1711.0
177.5°	1723.3	1721.0	1718.7	1716.5	1714.2	1713.9	1713.6	1713.3	1713.0	1712.9	1713.6
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1218.8	1218.8	1218.8	1218.8
2.5°	1187.5	1194.8	1209.5	1222.0
5°	1162.5	1174.0	1195.9	1217.8
7.5°	1132.2	1150.0	1178.2	1208.4
10°	1103.0	1126.0	1160.4	1195.9
12.5°	1073.8	1097.8	1134.3	1180.2
15°	1039.4	1064.4	1108.2	1163.5
17.5°	1009.1	1042.5	1082.1	1137.5
20°	976.7	1001.8	1052.9	1111.4
22.5°	936.1	977.8	1025.8	1087.4
25°	903.7	940.2	988.2	1058.1
27.5°	864.0	906.8	965.3	1026.8
30°	831.7	867.2	921.4	995.5
32.5°	794.1	835.9	892.2	965.3
35°	760.7	796.2	849.4	923.5
37.5°	721.1	759.7	819.2	884.9
40°	686.6	724.2	780.6	842.1
42.5°	644.9	684.6	740.9	793.1
45°	611.5	648.0	692.9	740.9
47.5°	570.8	609.4	653.3	686.6
50°	534.3	569.8	604.2	632.4
52.5°	494.6	527.0	558.3	579.2
55°	458.1	483.2	508.2	522.8
57.5°	415.3	439.3	460.2	468.5
60°	377.8	397.6	411.2	420.5
62.5°	338.1	352.7	363.2	368.4
65°	299.5	309.9	315.1	320.4
67.5°	259.8	269.2	272.4	278.6
70°	218.1	228.5	230.6	233.8
72.5°	186.8	186.8	191.0	195.1
75°	149.2	151.3	153.4	153.4
77.5°	116.9	116.9	119.0	120.0
80°	85.6	86.6	86.6	85.6
82.5°	58.4	60.5	58.4	57.4
85°	32.3	36.5	34.4	34.4
87.5°	13.6	13.6	15.7	13.6
90°	9.8	6.9	4.1	1.3
92.5°	24.2	25.9	27.6	29.3
95°	42.9	54.6	66.2	77.8
97.5°	117.8	125.7	133.7	141.6
100°	232.6	226.9	221.2	215.5
102.5°	310.8	307.1	303.4	299.7
105°	389.4	386.3	383.2	380.1
107.5°	473.2	470.6	468.1	465.5
110°	557.8	555.5	553.3	551.0

TEST NUMBER: P1031225

CATALOG NUMBER: S123RDIW-B775D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	638.5	636.6	634.6	632.6
115°	718.1	716.4	714.7	713.0
117.5°	798.0	796.0	794.0	792.0
120°	872.4	869.8	867.3	864.7
122.5°	944.6	942.7	940.7	938.7
125°	1011.8	1009.5	1007.3	1005.0
127.5°	1078.2	1075.9	1073.7	1071.4
130°	1139.4	1137.1	1134.9	1132.6
132.5°	1198.1	1195.8	1193.5	1191.2
135°	1256.3	1254.6	1252.9	1251.2
137.5°	1309.0	1306.7	1304.5	1302.2
140°	1358.3	1356.6	1354.9	1353.2
142.5°	1405.5	1403.8	1402.1	1400.4
145°	1449.7	1447.8	1445.8	1443.8
147.5°	1490.1	1488.7	1487.3	1485.9
150°	1526.7	1525.8	1525.0	1524.1
152.5°	1559.4	1559.1	1558.9	1558.6
155°	1588.8	1589.3	1589.9	1590.5
157.5°	1616.0	1616.0	1616.0	1616.0
160°	1638.0	1638.3	1638.6	1638.9
162.5°	1658.1	1658.9	1659.8	1660.6
165°	1674.7	1675.5	1676.4	1677.2
167.5°	1687.8	1688.9	1690.1	1691.2
170°	1699.3	1700.4	1701.6	1702.7
172.5°	1706.1	1707.5	1708.9	1710.3
175°	1712.4	1713.9	1715.3	1716.7
177.5°	1715.0	1716.5	1717.9	1719.3
180°	1716.7	1716.7	1716.7	1716.7

(END OF REPORT)