

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031709

Luminaire Tested: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031709
REPORT IS A COMBINATION OF REPORTS P991549 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1030UB35-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6029.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40	40	40
1	96	92	88	84	87	83	80	77	68	66	64	54	53	52	41	41	40	34	34	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29	29	29
3	80	71	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	24	24	24
4	73	62	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25	21	21	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18	18	18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16	16	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14	14	14
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	17	15	13	13	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	19	16	14	12	12	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11	11	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8509	8509	8509	8509
5°	8515	9805	8540	7317
10°	8461	11865	8469	6390
15°	8344	14071	8412	5752
20°	8243	16200	8260	5292
25°	8093	16608	8112	5053
30°	7987	13721	7987	4896
35°	7854	9177	7805	4758
40°	7696	6625	7601	4545
45°	7497	5247	7282	4281
50°	7013	4457	6765	4022
55°	6481	3916	6219	3732
60°	5943	3409	5627	3429
65°	5352	2920	5093	3024
70°	4738	2423	4420	2550
75°	4051	1827	3789	1969
80°	3203	1219	2953	1293
85°	2209	561	1767	510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13723 cd/sqm

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.7	1.3
10°-20°	249.7	4.1
20°-30°	420.2	7.0
30°-40°	474.8	7.9
40°-50°	425.3	7.1
50°-60°	343.3	5.7
60°-70°	239.2	4.0
70°-80°	125.6	2.1
80°-90°	32.9	0.5
90°-100°	84.6	1.4
100°-110°	256.0	4.2
110°-120°	435.8	7.2
120°-130°	573.3	9.5
130°-140°	644.4	10.7
140°-150°	633.5	10.5
150°-160°	533.3	8.8
160°-170°	355.1	5.9
170°-180°	124.3	2.1
0°-30°	747.6	12.4
0°-40°	1222.5	20.3
0°-60°	1991.1	33.0
0°-90°	2388.8	39.6
90°-120°	776.3	12.9
90°-150°	2627.5	43.6
90°-180°	3640.0	60.4
0°-180°	6029.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	790	790	790	790	790	
5°	790	939	792	701	790	75
15°	754	1398	760	572	754	213
25°	689	1659	691	505	689	318
35°	608	894	604	464	608	381
45°	505	483	490	394	505	386
55°	358	328	343	312	358	320
65°	221	213	211	221	221	220
75°	106	110	100	118	106	114
85°	23	25	18	23	23	26
90°	1	31	1	31	1	6
95°	61	80	61	80	61	67
105°	232	246	232	246	232	249
115°	439	440	439	440	439	434
125°	642	635	642	635	642	572
135°	833	832	833	832	833	642
145°	1010	1010	1010	1010	1010	631
155°	1157	1155	1157	1155	1157	533
165°	1260	1256	1260	1256	1260	355
175°	1311	1306	1311	1306	1311	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	792.8	799.0	802.0	806.6	811.2	818.1	820.4	824.3	822.7	825.8	827.3
5°	789.8	800.5	809.7	821.2	831.9	839.6	847.2	859.5	868.7	870.2	877.1
7.5°	784.4	799.7	815.8	831.9	852.6	864.9	878.6	895.5	909.3	931.5	939.9
10°	777.5	799.0	822.0	844.2	872.5	891.7	908.5	936.9	965.2	988.2	1009.6
12.5°	766.8	793.6	823.5	856.4	893.2	915.4	938.4	975.9	1018.8	1054.1	1077.0
15°	753.8	787.5	825.8	861.0	901.6	943.0	967.5	1009.6	1070.9	1103.9	1162.8
17.5°	743.1	777.5	815.8	871.0	926.1	967.5	985.1	1062.5	1104.6	1159.8	1226.4
20°	726.2	769.9	818.9	874.0	945.3	970.6	1006.6	1084.7	1136.8	1208.8	1290.8
22.5°	708.6	755.3	814.3	871.7	951.4	978.2	1027.3	1089.3	1172.0	1243.3	1333.7
25°	689.4	740.0	799.7	867.9	946.1	985.1	1031.1	1107.7	1197.3	1286.9	1370.4
27.5°	670.3	725.4	787.5	855.7	931.5	977.5	1023.4	1103.1	1218.0	1315.3	1421.8
30°	651.9	707.0	769.1	838.8	918.5	962.9	1006.6	1106.2	1234.1	1343.6	1450.9
32.5°	632.0	688.7	753.8	812.0	892.4	939.9	989.0	1106.2	1244.0	1360.5	1458.5
35°	608.2	666.5	722.4	780.6	860.3	913.1	968.3	1098.5	1253.2	1365.8	1426.4
37.5°	585.3	636.6	684.8	741.5	825.0	881.7	945.3	1089.3	1248.6	1342.9	1359.7
40°	559.2	610.5	649.6	702.5	790.5	856.4	920.8	1077.0	1228.7	1288.5	1239.4
42.5°	533.9	574.5	608.2	659.6	755.3	819.7	889.4	1054.8	1189.7	1201.9	1091.6
45°	504.8	533.9	563.8	622.0	717.0	782.9	860.3	1022.7	1126.8	1091.6	952.2
47.5°	467.3	493.3	526.3	579.9	676.4	744.6	818.1	981.3	1035.7	962.1	809.7
50°	431.3	453.5	484.1	536.2	633.5	700.2	778.3	916.2	943.0	827.3	697.9
52.5°	395.3	412.1	442.0	494.1	591.4	655.7	727.0	849.5	834.2	710.1	595.2
55°	357.7	372.3	400.6	452.0	542.4	603.6	671.8	767.6	727.7	609.8	517.8
57.5°	321.0	336.3	365.4	408.3	493.3	553.1	607.5	682.5	622.8	528.6	447.4
60°	288.0	301.1	323.3	365.4	442.8	491.0	540.8	592.1	542.4	451.2	389.1
62.5°	253.6	265.8	286.5	324.8	391.4	434.3	474.2	516.3	461.2	394.5	339.4
65°	221.4	231.3	250.5	285.7	340.1	375.4	407.5	436.6	392.2	330.9	289.6
67.5°	192.3	200.7	216.8	248.2	294.2	319.4	345.5	370.0	332.5	283.4	248.2
70°	160.9	167.8	182.3	205.3	242.1	268.1	287.3	305.6	271.9	232.9	209.1
72.5°	133.3	140.2	149.4	173.1	198.4	214.5	235.2	245.1	226.0	193.8	170.1
75°	106.5	111.8	120.3	135.6	159.3	170.1	183.1	190.7	173.1	151.7	137.1
77.5°	83.5	85.8	91.9	102.6	118.7	131.0	141.0	145.5	133.3	119.5	107.2
80°	59.0	62.0	66.6	75.8	88.1	91.9	98.1	103.4	95.8	83.5	75.8
82.5°	39.1	42.9	45.2	49.0	56.7	61.3	62.8	67.4	60.5	55.9	52.9
85°	23.0	24.5	25.3	27.6	31.4	33.7	36.0	36.8	35.2	34.5	31.4
87.5°	11.5	11.5	11.5	13.0	13.8	15.3	16.1	16.1	16.1	15.3	14.6
90°	1.0	3.3	5.6	7.9	10.2	11.4	12.9	15.9	18.8	21.8	24.8
92.5°	31.0	32.4	33.8	35.1	36.5	37.2	37.9	39.2	40.6	41.9	43.3
95°	60.9	62.5	64.1	65.7	67.3	68.1	69.0	70.9	72.7	74.6	76.4
97.5°	100.1	101.3	102.4	103.6	104.7	105.3	106.0	107.4	108.7	110.1	111.5
100°	140.4	141.8	143.1	144.5	145.8	146.5	147.1	148.2	149.4	150.5	151.7
102.5°	186.8	187.5	188.2	188.9	189.6	189.9	190.7	192.3	193.9	195.5	197.1
105°	232.2	232.7	233.1	233.6	234.1	234.3	235.3	237.4	239.5	241.5	243.6
107.5°	285.9	286.1	286.3	286.6	286.8	286.9	287.4	288.3	289.2	290.1	291.0
110°	335.4	335.9	336.3	336.8	337.3	337.5	337.7	338.2	338.6	339.1	339.5

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	387.0	387.2	387.4	387.7	387.9	388.0	388.0	388.0	388.0	388.0	388.0
115°	438.6	439.3	440.0	440.7	441.4	441.7	441.5	441.0	440.5	440.1	439.6
117.5°	491.2	491.4	491.7	491.9	492.2	492.3	492.1	491.6	491.1	490.7	490.2
120°	539.8	541.2	542.5	543.9	545.2	545.9	545.3	544.2	543.1	541.9	540.8
122.5°	590.3	591.2	592.1	593.0	593.9	594.4	594.2	593.7	593.3	592.8	592.4
125°	641.9	642.6	643.3	644.0	644.7	645.0	644.8	644.3	643.9	643.4	643.0
127.5°	689.4	690.8	692.2	693.5	694.9	695.6	695.4	694.9	694.4	694.0	693.5
130°	736.9	738.7	740.5	742.4	744.2	745.1	744.8	744.1	743.4	742.7	742.0
132.5°	784.3	786.1	788.0	789.8	791.7	792.6	792.4	791.9	791.4	791.0	790.5
135°	832.8	834.2	835.6	836.9	838.3	839.0	838.9	838.7	838.4	838.2	838.0
137.5°	877.2	878.4	879.5	880.7	881.8	882.4	882.7	883.4	884.1	884.8	885.5
140°	923.7	924.8	926.0	927.1	928.2	928.8	928.9	929.2	929.4	929.7	929.9
142.5°	966.0	967.1	968.3	969.4	970.5	971.1	971.3	971.8	972.3	972.7	973.2
145°	1010.4	1010.8	1011.3	1011.7	1012.2	1012.4	1012.7	1013.4	1014.1	1014.8	1015.5
147.5°	1048.5	1049.4	1050.4	1051.3	1052.2	1052.7	1053.0	1053.7	1054.4	1055.1	1055.8
150°	1088.8	1089.3	1089.7	1090.2	1090.7	1090.9	1091.1	1091.6	1092.0	1092.5	1092.9
152.5°	1121.8	1122.5	1123.2	1123.9	1124.6	1124.9	1125.0	1125.2	1125.5	1125.7	1125.9
155°	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9	1157.0	1157.2	1157.5	1157.7	1157.9
157.5°	1186.8	1186.6	1186.4	1186.1	1185.9	1185.8	1185.9	1186.1	1186.4	1186.6	1186.8
160°	1214.7	1214.2	1213.8	1213.3	1212.8	1212.6	1212.6	1212.6	1212.6	1212.6	1212.6
162.5°	1239.5	1238.8	1238.1	1237.4	1236.7	1236.4	1236.5	1236.7	1237.0	1237.2	1237.4
165°	1260.1	1259.4	1258.7	1258.0	1257.3	1257.0	1257.0	1257.0	1257.0	1257.0	1257.0
167.5°	1277.7	1276.8	1275.8	1274.9	1274.0	1273.5	1273.6	1273.9	1274.1	1274.4	1274.6
170°	1292.1	1291.2	1290.3	1289.4	1288.5	1288.0	1288.0	1288.0	1288.0	1288.0	1288.0
172.5°	1303.5	1302.6	1301.6	1300.7	1299.8	1299.3	1299.3	1299.3	1299.3	1299.3	1299.3
175°	1310.7	1309.8	1308.8	1307.9	1307.0	1306.5	1306.5	1306.5	1306.5	1306.5	1306.5
177.5°	1314.8	1313.9	1313.0	1312.1	1311.2	1310.7	1310.7	1310.7	1310.7	1310.7	1310.7
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	832.7	834.2	839.6	843.4	851.1	850.3	850.3	849.5	847.2	851.1	853.4
5°	890.9	903.9	905.5	922.3	923.1	930.0	934.6	930.7	939.9	939.2	932.3
7.5°	962.9	980.5	989.0	1005.0	1023.4	1018.8	1036.4	1039.5	1038.0	1045.6	1051.0
10°	1041.8	1072.4	1093.9	1123.8	1131.4	1136.0	1147.5	1157.5	1177.4	1162.1	1172.0
12.5°	1132.2	1154.4	1182.8	1230.3	1254.0	1269.3	1274.7	1281.6	1295.4	1286.9	1287.7
15°	1208.0	1237.9	1286.2	1345.2	1352.1	1371.2	1366.6	1408.0	1427.9	1398.0	1414.9
17.5°	1286.9	1326.8	1384.2	1435.5	1464.7	1477.7	1489.9	1529.8	1528.2	1523.6	1527.5
20°	1337.5	1402.6	1473.9	1542.0	1550.5	1560.4	1593.4	1610.2	1607.1	1620.2	1628.6
22.5°	1408.7	1477.7	1553.5	1598.7	1617.9	1629.4	1655.4	1666.1	1670.7	1673.8	1668.4
25°	1468.5	1542.0	1597.9	1637.8	1649.3	1655.4	1663.8	1666.9	1664.6	1659.2	1663.8
27.5°	1509.1	1568.1	1606.4	1624.8	1618.6	1608.7	1592.6	1581.9	1558.1	1546.6	1560.4
30°	1525.9	1552.0	1563.5	1532.8	1502.2	1477.7	1447.0	1390.4	1345.9	1358.9	1341.3
32.5°	1499.1	1482.3	1427.1	1348.2	1324.5	1284.6	1198.1	1131.4	1133.7	1098.5	1113.0
35°	1420.2	1343.6	1239.4	1119.9	1088.5	1067.1	972.1	957.5	926.9	894.0	903.2
37.5°	1280.8	1169.0	1042.6	954.5	907.8	861.0	807.4	775.2	756.8	743.1	753.8
40°	1110.8	974.4	870.2	791.3	751.5	721.6	684.8	652.7	632.0	629.7	633.5
42.5°	943.8	828.8	733.1	658.0	645.0	609.8	586.0	560.7	554.6	544.7	550.0
45°	799.0	705.5	626.6	565.3	550.0	540.8	511.7	495.6	488.7	482.6	491.8
47.5°	694.0	596.0	538.5	501.8	486.4	471.1	455.0	444.3	438.9	439.7	438.9
50°	592.9	520.9	470.3	442.0	432.8	422.1	409.1	402.2	399.9	393.0	398.3
52.5°	510.2	458.1	422.9	396.0	389.1	381.5	370.8	366.9	361.6	360.0	360.0
55°	443.5	402.9	374.6	357.0	348.5	342.4	336.3	331.7	327.9	327.9	327.9
57.5°	391.4	356.2	335.5	320.2	317.1	311.0	304.1	304.1	298.8	298.0	300.3
60°	347.0	315.6	299.5	286.5	281.9	280.4	273.5	273.5	271.9	268.1	271.2
62.5°	301.8	278.8	265.0	255.1	250.5	250.5	245.1	241.3	241.3	242.1	240.5
65°	260.5	243.6	231.3	223.7	221.4	218.3	217.6	214.5	212.2	213.0	212.2
67.5°	223.7	210.7	202.2	196.1	192.3	190.7	188.4	188.4	186.9	187.7	183.8
70°	190.7	177.7	170.8	164.7	163.2	163.2	160.1	160.9	159.3	161.6	160.1
72.5°	157.0	147.1	141.7	139.4	137.9	137.1	135.6	134.1	133.3	134.8	134.1
75°	127.2	118.7	114.9	113.4	111.8	111.8	111.1	110.3	109.5	109.5	109.5
77.5°	98.8	93.5	88.9	90.4	88.1	88.9	86.6	86.6	87.3	86.6	86.6
80°	72.8	68.9	68.9	67.4	64.3	65.9	65.9	63.6	62.8	64.3	62.0
82.5°	48.3	47.5	46.0	45.2	43.7	44.4	43.7	42.9	42.1	43.7	42.1
85°	28.3	28.3	27.6	26.0	27.6	26.8	26.0	26.0	25.3	25.3	25.3
87.5°	14.6	13.0	13.0	12.3	13.0	11.5	12.3	11.5	10.7	11.5	10.7
90°	25.7	26.6	27.5	28.4	28.9	29.1	29.6	30.1	30.5	31.0	30.5
92.5°	44.0	44.7	45.4	46.1	46.4	46.2	45.7	45.3	44.8	44.4	44.8
95°	77.3	78.2	79.1	80.0	80.5	80.5	80.5	80.5	80.5	80.5	80.5
97.5°	112.6	113.8	114.9	116.0	116.6	116.5	116.3	116.0	115.8	115.6	115.8
100°	152.4	153.1	153.8	154.5	154.8	155.0	155.5	156.0	156.4	156.9	156.4
102.5°	197.8	198.5	199.2	199.9	200.2	200.1	199.9	199.6	199.4	199.2	199.4
105°	243.6	243.6	243.6	243.6	243.6	243.8	244.3	244.7	245.2	245.6	245.2
107.5°	291.7	292.4	293.1	293.8	294.1	294.0	293.8	293.5	293.3	293.1	293.3
110°	340.4	341.4	342.3	343.2	343.7	343.5	343.0	342.5	342.1	341.6	342.1

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	389.2	390.3	391.5	392.6	393.2	393.2	393.2	393.2	393.2	393.2	393.2
115°	439.8	440.1	440.3	440.6	440.7	440.6	440.3	440.1	439.8	439.6	439.8
117.5°	490.2	490.2	490.2	490.2	490.2	489.9	489.2	488.5	487.8	487.1	487.8
120°	540.6	540.4	540.1	539.9	539.8	539.6	539.1	538.6	538.2	537.7	538.2
122.5°	591.7	591.0	590.3	589.6	589.3	589.0	588.3	587.6	586.9	586.2	586.9
125°	642.1	641.1	640.2	639.3	638.8	638.3	637.4	636.5	635.6	634.7	635.6
127.5°	692.1	690.7	689.4	688.0	687.3	686.8	685.9	685.0	684.1	683.2	684.1
130°	741.1	740.2	739.3	738.4	737.9	737.1	735.5	733.9	732.3	730.7	732.3
132.5°	789.4	788.2	787.1	786.0	785.4	784.8	783.7	782.5	781.4	780.2	781.4
135°	837.1	836.2	835.3	834.4	833.9	833.7	833.2	832.7	832.3	831.8	832.3
137.5°	884.3	883.2	882.0	880.9	880.3	880.0	879.3	878.6	877.9	877.2	877.9
140°	929.7	929.4	929.2	928.9	928.8	928.0	926.4	924.8	923.2	921.6	923.2
142.5°	973.0	972.8	972.5	972.3	972.2	971.6	970.5	969.3	968.2	967.0	968.2
145°	1015.3	1015.1	1014.8	1014.6	1014.5	1014.0	1013.1	1012.2	1011.3	1010.4	1011.3
147.5°	1055.8	1055.8	1055.8	1055.8	1055.8	1055.1	1053.7	1052.4	1051.0	1049.6	1051.0
150°	1092.9	1092.9	1092.9	1092.9	1092.9	1092.2	1090.8	1089.5	1088.1	1086.7	1088.1
152.5°	1126.4	1126.8	1127.3	1127.8	1128.0	1127.4	1126.3	1125.1	1124.0	1122.8	1124.0
155°	1158.8	1159.8	1160.7	1161.6	1162.1	1161.3	1159.7	1158.0	1156.4	1154.8	1156.4
157.5°	1187.7	1188.7	1189.6	1190.5	1191.0	1190.3	1188.9	1187.6	1186.2	1184.8	1186.2
160°	1213.8	1214.9	1216.1	1217.2	1217.8	1217.3	1216.4	1215.5	1214.6	1213.7	1214.6
162.5°	1238.6	1239.7	1240.9	1242.0	1242.6	1241.8	1240.2	1238.5	1236.9	1235.3	1236.9
165°	1258.4	1259.8	1261.1	1262.5	1263.2	1262.4	1260.8	1259.2	1257.6	1256.0	1257.6
167.5°	1276.0	1277.3	1278.7	1280.0	1280.7	1280.0	1278.7	1277.3	1276.0	1274.6	1276.0
170°	1289.6	1291.2	1292.8	1294.4	1295.2	1294.4	1292.8	1291.2	1289.6	1288.0	1289.6
172.5°	1300.7	1302.1	1303.4	1304.8	1305.5	1304.7	1303.1	1301.5	1299.9	1298.3	1299.9
175°	1307.9	1309.3	1310.6	1312.0	1312.7	1311.9	1310.3	1308.7	1307.1	1305.5	1307.1
177.5°	1312.1	1313.5	1314.8	1316.2	1316.9	1316.1	1314.5	1312.8	1311.2	1309.6	1311.2
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	847.2	849.5	843.4	841.9	841.9	844.9	842.6	822.0	825.8	821.2	819.7
5°	940.7	936.1	930.0	926.9	923.1	912.3	911.6	887.8	883.2	867.9	861.0
7.5°	1043.3	1039.5	1021.1	1018.8	1017.3	1007.3	982.1	956.8	938.4	920.8	903.9
10°	1160.5	1149.1	1140.6	1123.8	1115.3	1101.6	1068.6	1044.9	1013.5	986.7	951.4
12.5°	1301.5	1288.5	1260.1	1247.9	1237.1	1198.8	1165.9	1139.1	1077.8	1059.4	1015.8
15°	1404.9	1377.3	1374.3	1347.5	1345.9	1303.8	1241.0	1211.9	1164.4	1097.0	1051.8
17.5°	1516.7	1492.2	1473.1	1440.9	1436.3	1396.5	1350.5	1279.3	1227.2	1162.8	1105.4
20°	1598.7	1585.7	1552.8	1539.7	1512.9	1479.2	1431.7	1343.6	1280.0	1215.7	1145.2
22.5°	1663.8	1650.8	1624.8	1607.1	1591.8	1548.2	1491.5	1416.4	1329.1	1244.8	1172.0
25°	1663.1	1659.2	1648.5	1640.1	1628.6	1596.4	1548.9	1476.9	1379.6	1286.9	1185.8
27.5°	1568.8	1579.6	1597.9	1607.1	1604.8	1600.2	1573.4	1512.9	1425.6	1315.3	1201.9
30°	1372.7	1411.8	1446.3	1492.2	1506.0	1539.7	1555.1	1520.6	1450.9	1348.2	1222.6
32.5°	1138.3	1195.0	1270.1	1295.4	1339.0	1404.1	1476.9	1489.9	1446.3	1367.4	1235.6
35°	933.8	980.5	1038.7	1078.6	1117.6	1223.4	1315.3	1394.9	1409.5	1357.4	1232.5
37.5°	772.9	805.9	857.2	890.9	926.9	1017.3	1146.0	1249.4	1322.2	1323.7	1224.1
40°	656.5	671.0	715.5	740.0	774.5	852.6	967.5	1102.3	1208.8	1257.8	1201.9
42.5°	556.1	575.3	612.1	630.4	652.7	720.8	796.7	924.6	1056.4	1161.3	1160.5
45°	496.4	510.2	527.0	542.4	567.6	608.2	694.8	790.5	916.9	1035.7	1082.4
47.5°	443.5	456.6	473.4	478.0	494.9	533.2	586.0	669.5	787.5	905.5	993.5
50°	399.1	409.8	421.3	429.7	437.4	468.8	508.6	579.1	673.3	787.5	897.0
52.5°	364.6	372.3	382.3	386.8	393.7	416.7	447.4	499.5	576.8	681.0	787.5
55°	332.5	337.8	343.9	351.6	354.7	371.5	395.3	439.7	497.2	590.6	691.7
57.5°	302.6	304.9	308.7	313.3	317.1	331.7	352.4	382.3	432.8	504.8	600.6
60°	268.9	275.0	277.3	281.9	284.2	295.7	311.8	337.1	376.1	438.2	510.2
62.5°	240.5	244.4	248.2	250.5	255.9	259.7	272.7	295.7	327.9	373.8	438.9
65°	215.3	216.8	219.1	221.4	222.9	227.5	239.8	255.1	279.6	320.2	370.8
67.5°	186.1	187.7	190.7	191.5	193.0	199.2	206.1	219.1	239.8	270.4	311.8
70°	157.8	160.1	161.6	163.2	165.5	167.8	175.4	186.1	202.2	223.7	255.9
72.5°	133.3	135.6	135.6	137.1	136.4	139.4	147.1	154.7	165.5	183.1	211.4
75°	108.8	108.8	110.3	111.1	111.8	114.9	118.0	124.1	132.5	146.3	163.9
77.5°	85.8	85.0	86.6	86.6	86.6	88.9	91.9	95.0	100.4	110.3	124.1
80°	62.8	62.8	64.3	65.1	63.6	64.3	65.9	68.9	72.8	79.7	87.3
82.5°	41.4	44.4	43.7	44.4	43.7	45.2	46.0	46.7	48.3	51.3	56.7
85°	25.3	25.3	25.3	26.0	25.3	26.0	26.0	26.0	26.8	28.3	30.6
87.5°	10.7	10.7	10.7	11.5	10.7	10.7	11.5	10.7	11.5	11.5	12.3
90°	30.1	29.6	29.1	28.9	28.4	27.5	26.6	25.7	24.8	21.8	18.8
92.5°	45.3	45.7	46.2	46.4	46.1	45.4	44.7	44.0	43.3	41.9	40.6
95°	80.5	80.5	80.5	80.5	80.0	79.1	78.2	77.3	76.4	74.6	72.7
97.5°	116.0	116.3	116.5	116.6	116.0	114.9	113.8	112.6	111.5	110.1	108.7
100°	156.0	155.5	155.0	154.8	154.5	153.8	153.1	152.4	151.7	150.5	149.4
102.5°	199.6	199.9	200.1	200.2	199.9	199.2	198.5	197.8	197.1	195.5	193.9
105°	244.7	244.3	243.8	243.6	243.6	243.6	243.6	243.6	243.6	241.5	239.5
107.5°	293.5	293.8	294.0	294.1	293.8	293.1	292.4	291.7	291.0	290.1	289.2
110°	342.5	343.0	343.5	343.7	343.2	342.3	341.4	340.4	339.5	339.1	338.6

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	393.2	393.2	393.2	393.2	392.6	391.5	390.3	389.2	388.0	388.0	388.0
115°	440.1	440.3	440.6	440.7	440.6	440.3	440.1	439.8	439.6	440.1	440.5
117.5°	488.5	489.2	489.9	490.2	490.2	490.2	490.2	490.2	490.2	490.7	491.1
120°	538.6	539.1	539.6	539.8	539.9	540.1	540.4	540.6	540.8	541.9	543.1
122.5°	587.6	588.3	589.0	589.3	589.6	590.3	591.0	591.7	592.4	592.8	593.3
125°	636.5	637.4	638.3	638.8	639.3	640.2	641.1	642.1	643.0	643.4	643.9
127.5°	685.0	685.9	686.8	687.3	688.0	689.4	690.7	692.1	693.5	694.0	694.4
130°	733.9	735.5	737.1	737.9	738.4	739.3	740.2	741.1	742.0	742.7	743.4
132.5°	782.5	783.7	784.8	785.4	786.0	787.1	788.2	789.4	790.5	791.0	791.4
135°	832.7	833.2	833.7	833.9	834.4	835.3	836.2	837.1	838.0	838.2	838.4
137.5°	878.6	879.3	880.0	880.3	880.9	882.0	883.2	884.3	885.5	884.8	884.1
140°	924.8	926.4	928.0	928.8	928.9	929.2	929.4	929.7	929.9	929.7	929.4
142.5°	969.3	970.5	971.6	972.2	972.3	972.5	972.8	973.0	973.2	972.7	972.3
145°	1012.2	1013.1	1014.0	1014.5	1014.6	1014.8	1015.1	1015.3	1015.5	1014.8	1014.1
147.5°	1052.4	1053.7	1055.1	1055.8	1055.8	1055.8	1055.8	1055.8	1055.8	1055.1	1054.4
150°	1089.5	1090.8	1092.2	1092.9	1092.9	1092.9	1092.9	1092.9	1092.9	1092.5	1092.0
152.5°	1125.1	1126.3	1127.4	1128.0	1127.8	1127.3	1126.8	1126.4	1125.9	1125.7	1125.5
155°	1158.0	1159.7	1161.3	1162.1	1161.6	1160.7	1159.8	1158.8	1157.9	1157.7	1157.5
157.5°	1187.6	1188.9	1190.3	1191.0	1190.5	1189.6	1188.7	1187.7	1186.8	1186.6	1186.4
160°	1215.5	1216.4	1217.3	1217.8	1217.2	1216.1	1214.9	1213.8	1212.6	1212.6	1212.6
162.5°	1238.5	1240.2	1241.8	1242.6	1242.0	1240.9	1239.7	1238.6	1237.4	1237.2	1237.0
165°	1259.2	1260.8	1262.4	1263.2	1262.5	1261.1	1259.8	1258.4	1257.0	1257.0	1257.0
167.5°	1277.3	1278.7	1280.0	1280.7	1280.0	1278.7	1277.3	1276.0	1274.6	1274.4	1274.1
170°	1291.2	1292.8	1294.4	1295.2	1294.4	1292.8	1291.2	1289.6	1288.0	1288.0	1288.0
172.5°	1301.5	1303.1	1304.7	1305.5	1304.8	1303.4	1302.1	1300.7	1299.3	1299.3	1299.3
175°	1308.7	1310.3	1311.9	1312.7	1312.0	1310.6	1309.3	1307.9	1306.5	1306.5	1306.5
177.5°	1312.8	1314.5	1316.1	1316.9	1316.2	1314.8	1313.5	1312.1	1310.7	1310.7	1310.7
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	812.0	809.7	809.7	808.2	803.6	795.1	794.4	795.9	791.3	786.7	779.8
5°	851.8	837.3	832.7	828.1	818.9	803.6	797.4	792.1	783.7	773.7	763.0
7.5°	885.5	864.9	858.7	850.3	831.9	810.5	796.7	785.2	773.7	759.9	746.9
10°	927.7	897.8	883.2	871.0	845.7	815.8	795.1	778.3	759.9	743.1	726.2
12.5°	975.2	926.9	922.3	892.4	863.3	818.9	793.6	769.1	744.6	723.9	706.3
15°	1015.0	962.1	943.0	923.1	867.2	812.0	787.5	759.9	731.6	709.3	683.3
17.5°	1040.3	996.6	956.0	929.2	871.0	822.0	774.5	743.1	713.2	682.5	661.1
20°	1070.9	1007.3	972.1	936.1	878.6	814.3	766.8	727.7	691.0	663.4	637.3
22.5°	1101.6	1015.8	986.7	947.6	880.2	806.6	753.0	713.9	671.8	644.2	615.9
25°	1098.5	1028.0	979.8	946.8	864.9	799.7	736.9	691.0	651.9	616.7	588.3
27.5°	1100.8	1014.2	965.2	926.9	854.1	789.8	720.1	671.8	631.2	594.4	564.6
30°	1101.6	993.5	950.6	904.7	834.2	766.0	700.9	651.9	609.0	569.2	542.4
32.5°	1099.3	976.7	923.1	881.7	802.8	743.1	678.7	626.6	583.0	546.2	520.9
35°	1093.9	956.8	894.7	842.6	770.6	710.1	658.0	604.4	557.7	524.0	494.9
37.5°	1079.3	935.3	864.9	813.5	733.1	671.8	625.9	581.4	536.2	496.4	471.9
40°	1068.6	906.2	835.0	779.1	692.5	632.7	594.4	552.3	507.9	471.9	448.1
42.5°	1044.1	878.6	804.3	737.7	652.7	591.4	555.4	521.7	483.4	448.1	426.7
45°	1004.3	848.8	766.8	699.4	609.0	550.8	517.8	490.3	456.6	422.9	401.4
47.5°	948.4	805.9	727.0	659.6	566.1	507.1	474.2	453.5	426.7	398.3	380.0
50°	887.8	759.1	686.4	619.7	524.7	467.3	435.1	416.0	398.3	372.3	354.7
52.5°	808.9	709.3	639.6	576.1	480.3	425.1	396.8	383.0	364.6	346.2	330.9
55°	732.3	645.0	587.5	527.0	436.6	385.3	357.7	343.2	332.5	317.1	304.9
57.5°	643.5	585.3	532.4	477.2	396.0	349.3	323.3	305.6	298.8	291.9	280.4
60°	561.5	517.1	474.2	428.2	353.9	311.8	286.5	272.7	265.8	261.2	253.6
62.5°	486.4	452.0	415.2	378.4	311.0	272.7	253.6	239.8	233.6	232.9	226.0
65°	414.4	389.9	360.0	324.0	271.2	237.5	219.1	210.7	203.8	203.8	198.4
67.5°	342.4	325.6	301.8	276.5	235.2	203.8	186.9	179.3	175.4	175.4	171.6
70°	285.0	273.5	252.0	229.8	193.8	170.1	157.0	150.1	147.8	148.6	145.5
72.5°	231.3	219.1	201.5	185.4	158.6	141.0	131.8	124.1	120.3	121.0	120.3
75°	179.3	173.1	157.8	145.5	124.1	111.8	103.4	99.6	96.5	97.3	95.8
77.5°	134.8	125.6	117.2	108.8	95.8	85.8	78.9	75.1	72.8	72.8	72.8
80°	91.9	90.4	83.5	78.9	68.2	60.5	55.2	54.4	52.1	52.1	52.1
82.5°	59.8	55.9	52.1	49.0	42.9	38.3	36.0	34.5	33.7	32.9	34.5
85°	32.9	30.6	29.1	26.0	23.7	21.4	19.2	18.4	17.6	18.4	17.6
87.5°	13.0	10.7	10.7	10.0	9.2	8.4	8.4	6.9	6.9	6.1	6.1
90°	15.9	12.9	11.4	10.2	7.9	5.6	3.3	1.0	3.3	5.6	7.9
92.5°	39.2	37.9	37.2	36.5	35.1	33.8	32.4	31.0	32.4	33.8	35.1
95°	70.9	69.0	68.1	67.3	65.7	64.1	62.5	60.9	62.5	64.1	65.7
97.5°	107.4	106.0	105.3	104.7	103.6	102.4	101.3	100.1	101.3	102.4	103.6
100°	148.2	147.1	146.5	145.8	144.5	143.1	141.8	140.4	141.8	143.1	144.5
102.5°	192.3	190.7	189.9	189.6	188.9	188.2	187.5	186.8	187.5	188.2	188.9
105°	237.4	235.3	234.3	234.1	233.6	233.1	232.7	232.2	232.7	233.1	233.6
107.5°	288.3	287.4	286.9	286.8	286.6	286.3	286.1	285.9	286.1	286.3	286.6
110°	338.2	337.7	337.5	337.3	336.8	336.3	335.9	335.4	335.9	336.3	336.8

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	388.0	388.0	388.0	387.9	387.7	387.4	387.2	387.0	387.2	387.4	387.7
115°	441.0	441.5	441.7	441.4	440.7	440.0	439.3	438.6	439.3	440.0	440.7
117.5°	491.6	492.1	492.3	492.2	491.9	491.7	491.4	491.2	491.4	491.7	491.9
120°	544.2	545.3	545.9	545.2	543.9	542.5	541.2	539.8	541.2	542.5	543.9
122.5°	593.7	594.2	594.4	593.9	593.0	592.1	591.2	590.3	591.2	592.1	593.0
125°	644.3	644.8	645.0	644.7	644.0	643.3	642.6	641.9	642.6	643.3	644.0
127.5°	694.9	695.4	695.6	694.9	693.5	692.2	690.8	689.4	690.8	692.2	693.5
130°	744.1	744.8	745.1	744.2	742.4	740.5	738.7	736.9	738.7	740.5	742.4
132.5°	791.9	792.4	792.6	791.7	789.8	788.0	786.1	784.3	786.1	788.0	789.8
135°	838.7	838.9	839.0	838.3	836.9	835.6	834.2	832.8	834.2	835.6	836.9
137.5°	883.4	882.7	882.4	881.8	880.7	879.5	878.4	877.2	878.4	879.5	880.7
140°	929.2	928.9	928.8	928.2	927.1	926.0	924.8	923.7	924.8	926.0	927.1
142.5°	971.8	971.3	971.1	970.5	969.4	968.3	967.1	966.0	967.1	968.3	969.4
145°	1013.4	1012.7	1012.4	1012.2	1011.7	1011.3	1010.8	1010.4	1010.8	1011.3	1011.7
147.5°	1053.7	1053.0	1052.7	1052.2	1051.3	1050.4	1049.4	1048.5	1049.4	1050.4	1051.3
150°	1091.6	1091.1	1090.9	1090.7	1090.2	1089.7	1089.3	1088.8	1089.3	1089.7	1090.2
152.5°	1125.2	1125.0	1124.9	1124.6	1123.9	1123.2	1122.5	1121.8	1122.5	1123.2	1123.9
155°	1157.2	1157.0	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9
157.5°	1186.1	1185.9	1185.8	1185.9	1186.1	1186.4	1186.6	1186.8	1186.6	1186.4	1186.1
160°	1212.6	1212.6	1212.6	1212.8	1213.3	1213.8	1214.2	1214.7	1214.2	1213.8	1213.3
162.5°	1236.7	1236.5	1236.4	1236.7	1237.4	1238.1	1238.8	1239.5	1238.8	1238.1	1237.4
165°	1257.0	1257.0	1257.0	1257.3	1258.0	1258.7	1259.4	1260.1	1259.4	1258.7	1258.0
167.5°	1273.9	1273.6	1273.5	1274.0	1274.9	1275.8	1276.8	1277.7	1276.8	1275.8	1274.9
170°	1288.0	1288.0	1288.0	1288.5	1289.4	1290.3	1291.2	1292.1	1291.2	1290.3	1289.4
172.5°	1299.3	1299.3	1299.3	1299.8	1300.7	1301.6	1302.6	1303.5	1302.6	1301.6	1300.7
175°	1306.5	1306.5	1306.5	1307.0	1307.9	1308.8	1309.8	1310.7	1309.8	1308.8	1307.9
177.5°	1310.7	1310.7	1310.7	1311.2	1312.1	1313.0	1313.9	1314.8	1313.9	1313.0	1312.1
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	778.3	777.5	779.1	774.5	766.8	763.0	752.2	749.9	749.2	749.9	750.7
5°	756.8	756.1	753.8	746.1	736.9	730.0	717.0	716.2	711.6	707.0	709.3
7.5°	736.2	733.1	728.5	718.5	706.3	698.6	687.9	680.2	674.1	670.3	667.2
10°	715.5	710.9	706.3	693.3	677.9	666.5	653.4	647.3	640.4	637.3	634.3
12.5°	688.7	684.1	675.6	660.3	651.1	636.6	623.6	617.4	613.6	607.5	603.6
15°	667.2	658.0	653.4	637.3	618.2	616.7	592.9	591.4	583.7	583.7	577.6
17.5°	642.7	635.8	627.4	611.3	597.5	583.7	571.5	566.9	560.0	558.4	555.4
20°	619.0	609.8	606.7	590.6	576.1	559.2	546.2	541.6	538.5	535.5	537.8
22.5°	594.4	586.8	579.1	564.6	553.8	537.0	529.3	524.7	520.1	518.6	519.4
25°	570.7	563.8	556.1	541.6	530.1	516.3	509.4	507.1	504.8	504.8	504.1
27.5°	547.7	540.8	533.9	520.9	509.4	499.5	494.1	491.8	489.5	491.0	492.6
30°	524.0	517.8	511.7	500.2	491.0	481.8	478.8	477.2	476.5	480.3	480.3
32.5°	502.5	497.2	492.6	481.8	472.6	465.0	462.7	463.5	464.2	466.5	468.0
35°	480.3	476.5	471.9	462.7	455.0	448.1	448.9	448.9	450.4	454.3	457.3
37.5°	460.4	455.0	451.2	443.5	437.4	431.3	433.6	435.9	437.4	442.0	443.5
40°	436.6	434.3	431.3	423.6	418.3	417.5	418.3	419.8	422.9	425.1	427.4
42.5°	417.5	414.4	410.6	404.5	399.9	400.6	401.4	402.9	404.5	408.3	410.6
45°	396.0	393.7	390.7	385.3	381.5	382.3	383.0	383.0	384.5	389.1	390.7
47.5°	372.3	373.1	369.2	363.9	361.6	361.6	361.6	363.1	366.9	368.5	369.2
50°	349.3	347.8	347.0	341.7	340.1	339.4	340.1	340.9	346.2	345.5	347.8
52.5°	324.8	324.8	324.0	321.0	318.7	318.7	317.1	321.0	322.5	324.0	326.3
55°	301.1	298.8	298.0	296.5	293.4	292.6	294.2	298.8	300.3	301.8	304.1
57.5°	275.0	275.0	273.5	271.2	271.2	271.2	271.2	274.2	276.5	278.1	282.7
60°	251.3	248.2	245.9	245.9	245.9	245.1	249.7	249.7	254.3	255.1	256.6
62.5°	222.9	221.4	219.9	220.6	219.9	221.4	222.9	226.0	226.7	229.0	231.3
65°	196.1	196.1	194.6	199.2	196.1	196.1	199.9	199.9	201.5	203.8	206.8
67.5°	170.1	170.8	169.3	169.3	170.8	171.6	172.4	175.4	176.2	179.3	183.1
70°	143.2	144.8	145.5	144.0	145.5	147.1	148.6	149.4	152.4	154.0	156.3
72.5°	119.5	121.0	118.7	119.5	120.3	121.8	122.6	124.1	125.6	130.2	131.8
75°	95.8	95.0	94.2	97.3	95.8	98.8	99.6	99.6	101.1	104.9	106.5
77.5°	73.5	73.5	74.3	72.8	75.1	74.3	75.1	77.4	79.7	79.7	85.8
80°	51.3	52.9	52.9	52.9	53.6	54.4	52.9	56.7	57.5	57.5	59.8
82.5°	32.9	33.7	32.9	34.5	34.5	36.0	35.2	36.0	37.5	39.1	39.8
85°	17.6	17.6	19.2	19.2	18.4	19.2	18.4	19.2	20.7	20.7	21.4
87.5°	6.1	6.1	6.1	6.1	6.9	6.1	6.9	6.9	6.1	6.1	8.4
90°	10.2	11.4	12.9	15.9	18.8	21.8	24.8	25.7	26.6	27.5	28.4
92.5°	36.5	37.2	37.9	39.2	40.6	41.9	43.3	44.0	44.7	45.4	46.1
95°	67.3	68.1	69.0	70.9	72.7	74.6	76.4	77.3	78.2	79.1	80.0
97.5°	104.7	105.3	106.0	107.4	108.7	110.1	111.5	112.6	113.8	114.9	116.0
100°	145.8	146.5	147.1	148.2	149.4	150.5	151.7	152.4	153.1	153.8	154.5
102.5°	189.6	189.9	190.7	192.3	193.9	195.5	197.1	197.8	198.5	199.2	199.9
105°	234.1	234.3	235.3	237.4	239.5	241.5	243.6	243.6	243.6	243.6	243.6
107.5°	286.8	286.9	287.4	288.3	289.2	290.1	291.0	291.7	292.4	293.1	293.8
110°	337.3	337.5	337.7	338.2	338.6	339.1	339.5	340.4	341.4	342.3	343.2

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	387.9	388.0	388.0	388.0	388.0	388.0	388.0	389.2	390.3	391.5	392.6
115°	441.4	441.7	441.5	441.0	440.5	440.1	439.6	439.8	440.1	440.3	440.6
117.5°	492.2	492.3	492.1	491.6	491.1	490.7	490.2	490.2	490.2	490.2	490.2
120°	545.2	545.9	545.3	544.2	543.1	541.9	540.8	540.6	540.4	540.1	539.9
122.5°	593.9	594.4	594.2	593.7	593.3	592.8	592.4	591.7	591.0	590.3	589.6
125°	644.7	645.0	644.8	644.3	643.9	643.4	643.0	642.1	641.1	640.2	639.3
127.5°	694.9	695.6	695.4	694.9	694.4	694.0	693.5	692.1	690.7	689.4	688.0
130°	744.2	745.1	744.8	744.1	743.4	742.7	742.0	741.1	740.2	739.3	738.4
132.5°	791.7	792.6	792.4	791.9	791.4	791.0	790.5	789.4	788.2	787.1	786.0
135°	838.3	839.0	838.9	838.7	838.4	838.2	838.0	837.1	836.2	835.3	834.4
137.5°	881.8	882.4	882.7	883.4	884.1	884.8	885.5	884.3	883.2	882.0	880.9
140°	928.2	928.8	928.9	929.2	929.4	929.7	929.9	929.7	929.4	929.2	928.9
142.5°	970.5	971.1	971.3	971.8	972.3	972.7	973.2	973.0	972.8	972.5	972.3
145°	1012.2	1012.4	1012.7	1013.4	1014.1	1014.8	1015.5	1015.3	1015.1	1014.8	1014.6
147.5°	1052.2	1052.7	1053.0	1053.7	1054.4	1055.1	1055.8	1055.8	1055.8	1055.8	1055.8
150°	1090.7	1090.9	1091.1	1091.6	1092.0	1092.5	1092.9	1092.9	1092.9	1092.9	1092.9
152.5°	1124.6	1124.9	1125.0	1125.2	1125.5	1125.7	1125.9	1126.4	1126.8	1127.3	1127.8
155°	1156.9	1156.9	1157.0	1157.2	1157.5	1157.7	1157.9	1158.8	1159.8	1160.7	1161.6
157.5°	1185.9	1185.8	1185.9	1186.1	1186.4	1186.6	1186.8	1187.7	1188.7	1189.6	1190.5
160°	1212.8	1212.6	1212.6	1212.6	1212.6	1212.6	1212.6	1213.8	1214.9	1216.1	1217.2
162.5°	1236.7	1236.4	1236.5	1236.7	1237.0	1237.2	1237.4	1238.6	1239.7	1240.9	1242.0
165°	1257.3	1257.0	1257.0	1257.0	1257.0	1257.0	1257.0	1258.4	1259.8	1261.1	1262.5
167.5°	1274.0	1273.5	1273.6	1273.9	1274.1	1274.4	1274.6	1276.0	1277.3	1278.7	1280.0
170°	1288.5	1288.0	1288.0	1288.0	1288.0	1288.0	1288.0	1289.6	1291.2	1292.8	1294.4
172.5°	1299.8	1299.3	1299.3	1299.3	1299.3	1299.3	1299.3	1300.7	1302.1	1303.4	1304.8
175°	1307.0	1306.5	1306.5	1306.5	1306.5	1306.5	1306.5	1307.9	1309.3	1310.6	1312.0
177.5°	1311.2	1310.7	1310.7	1310.7	1310.7	1310.7	1310.7	1312.1	1313.5	1314.8	1316.2
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	749.9	750.7	747.6	745.4	751.5	747.6	747.6	748.4	746.9	749.2	748.4
5°	707.8	708.6	703.2	704.8	701.7	700.9	700.2	704.8	704.0	703.2	704.8
7.5°	666.5	666.5	664.2	662.6	662.6	660.3	663.4	662.6	664.2	664.2	666.5
10°	632.0	633.5	629.7	625.9	625.1	625.9	625.9	626.6	627.4	632.7	632.0
12.5°	603.6	601.3	600.6	598.3	594.4	592.9	591.4	599.8	597.5	597.5	597.5
15°	572.2	577.6	576.8	569.9	568.4	571.5	569.9	569.9	577.6	576.8	576.1
17.5°	555.4	553.8	552.3	548.5	549.2	548.5	549.2	549.2	553.8	553.8	553.8
20°	536.2	533.2	533.2	531.6	531.6	529.3	532.4	533.2	536.2	536.2	537.0
22.5°	519.4	517.1	517.1	516.3	517.8	514.8	517.8	518.6	518.6	520.9	520.9
25°	504.8	503.3	503.3	504.8	504.8	504.8	504.8	507.9	505.6	506.3	505.6
27.5°	491.8	492.6	493.3	494.1	493.3	494.1	494.9	496.4	497.2	496.4	494.9
30°	479.5	481.8	482.6	482.6	484.1	484.9	485.7	485.7	486.4	484.1	485.7
32.5°	470.3	470.3	471.9	472.6	474.2	474.9	474.9	476.5	475.7	473.4	474.2
35°	457.3	457.3	460.4	461.9	464.2	463.5	464.2	464.2	465.0	463.5	461.2
37.5°	444.3	445.8	445.8	448.9	449.7	450.4	449.7	451.2	450.4	448.9	448.1
40°	429.0	428.2	429.0	431.3	432.0	432.0	432.0	433.6	433.6	433.6	432.8
42.5°	409.8	412.1	411.4	413.7	412.9	412.9	414.4	416.0	416.7	414.4	415.2
45°	391.4	391.4	393.0	393.0	393.7	393.7	396.8	395.3	396.8	395.3	396.0
47.5°	371.5	372.3	372.3	373.1	374.6	376.1	374.6	375.4	375.4	376.1	374.6
50°	349.3	349.3	350.8	353.1	356.2	354.7	353.9	357.0	354.7	354.7	353.1
52.5°	326.3	328.6	329.4	331.7	334.0	334.8	335.5	334.0	334.8	332.5	333.2
55°	304.1	304.9	307.9	310.2	312.5	312.5	311.8	312.5	313.3	310.2	310.2
57.5°	281.9	284.2	287.3	287.3	290.3	290.3	289.6	289.6	290.3	288.0	287.3
60°	258.2	260.5	264.3	264.3	268.9	269.6	268.1	266.6	266.6	264.3	265.0
62.5°	232.9	235.2	237.5	241.3	244.4	242.8	245.9	242.8	243.6	239.0	239.0
65°	210.7	211.4	215.3	219.1	219.1	220.6	219.1	219.9	217.6	217.6	214.5
67.5°	184.6	184.6	188.4	192.3	196.1	196.1	196.1	193.8	193.8	191.5	191.5
70°	161.6	160.9	164.7	167.0	169.3	170.1	168.5	167.8	166.2	163.9	163.2
72.5°	133.3	134.8	138.7	140.2	144.0	143.2	147.1	142.5	142.5	138.7	137.9
75°	108.0	109.5	113.4	115.7	118.0	118.0	120.3	118.0	114.9	113.4	112.6
77.5°	85.8	85.0	88.1	91.9	92.7	91.9	93.5	92.7	89.6	89.6	88.1
80°	61.3	63.6	66.6	65.9	68.9	68.2	68.2	66.6	66.6	64.3	65.9
82.5°	40.6	42.9	43.7	42.9	43.7	45.2	46.0	45.2	45.2	43.7	44.4
85°	21.4	21.4	23.0	23.7	23.0	23.0	23.7	26.0	24.5	23.0	24.5
87.5°	6.9	6.1	6.1	6.9	6.1	6.1	6.9	6.9	7.7	7.7	7.7
90°	28.9	29.1	29.6	30.1	30.5	31.0	30.5	30.1	29.6	29.1	28.9
92.5°	46.4	46.2	45.7	45.3	44.8	44.4	44.8	45.3	45.7	46.2	46.4
95°	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5
97.5°	116.6	116.5	116.3	116.0	115.8	115.6	115.8	116.0	116.3	116.5	116.6
100°	154.8	155.0	155.5	156.0	156.4	156.9	156.4	156.0	155.5	155.0	154.8
102.5°	200.2	200.1	199.9	199.6	199.4	199.2	199.4	199.6	199.9	200.1	200.2
105°	243.6	243.8	244.3	244.7	245.2	245.6	245.2	244.7	244.3	243.8	243.6
107.5°	294.1	294.0	293.8	293.5	293.3	293.1	293.3	293.5	293.8	294.0	294.1
110°	343.7	343.5	343.0	342.5	342.1	341.6	342.1	342.5	343.0	343.5	343.7

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	393.2	393.2	393.2	393.2	393.2	393.2	393.2	393.2	393.2	393.2	393.2
115°	440.7	440.6	440.3	440.1	439.8	439.6	439.8	440.1	440.3	440.6	440.7
117.5°	490.2	489.9	489.2	488.5	487.8	487.1	487.8	488.5	489.2	489.9	490.2
120°	539.8	539.6	539.1	538.6	538.2	537.7	538.2	538.6	539.1	539.6	539.8
122.5°	589.3	589.0	588.3	587.6	586.9	586.2	586.9	587.6	588.3	589.0	589.3
125°	638.8	638.3	637.4	636.5	635.6	634.7	635.6	636.5	637.4	638.3	638.8
127.5°	687.3	686.8	685.9	685.0	684.1	683.2	684.1	685.0	685.9	686.8	687.3
130°	737.9	737.1	735.5	733.9	732.3	730.7	732.3	733.9	735.5	737.1	737.9
132.5°	785.4	784.8	783.7	782.5	781.4	780.2	781.4	782.5	783.7	784.8	785.4
135°	833.9	833.7	833.2	832.7	832.3	831.8	832.3	832.7	833.2	833.7	833.9
137.5°	880.3	880.0	879.3	878.6	877.9	877.2	877.9	878.6	879.3	880.0	880.3
140°	928.8	928.0	926.4	924.8	923.2	921.6	923.2	924.8	926.4	928.0	928.8
142.5°	972.2	971.6	970.5	969.3	968.2	967.0	968.2	969.3	970.5	971.6	972.2
145°	1014.5	1014.0	1013.1	1012.2	1011.3	1010.4	1011.3	1012.2	1013.1	1014.0	1014.5
147.5°	1055.8	1055.1	1053.7	1052.4	1051.0	1049.6	1051.0	1052.4	1053.7	1055.1	1055.8
150°	1092.9	1092.2	1090.8	1089.5	1088.1	1086.7	1088.1	1089.5	1090.8	1092.2	1092.9
152.5°	1128.0	1127.4	1126.3	1125.1	1124.0	1122.8	1124.0	1125.1	1126.3	1127.4	1128.0
155°	1162.1	1161.3	1159.7	1158.0	1156.4	1154.8	1156.4	1158.0	1159.7	1161.3	1162.1
157.5°	1191.0	1190.3	1188.9	1187.6	1186.2	1184.8	1186.2	1187.6	1188.9	1190.3	1191.0
160°	1217.8	1217.3	1216.4	1215.5	1214.6	1213.7	1214.6	1215.5	1216.4	1217.3	1217.8
162.5°	1242.6	1241.8	1240.2	1238.5	1236.9	1235.3	1236.9	1238.5	1240.2	1241.8	1242.6
165°	1263.2	1262.4	1260.8	1259.2	1257.6	1256.0	1257.6	1259.2	1260.8	1262.4	1263.2
167.5°	1280.7	1280.0	1278.7	1277.3	1276.0	1274.6	1276.0	1277.3	1278.7	1280.0	1280.7
170°	1295.2	1294.4	1292.8	1291.2	1289.6	1288.0	1289.6	1291.2	1292.8	1294.4	1295.2
172.5°	1305.5	1304.7	1303.1	1301.5	1299.9	1298.3	1299.9	1301.5	1303.1	1304.7	1305.5
175°	1312.7	1311.9	1310.3	1308.7	1307.1	1305.5	1307.1	1308.7	1310.3	1311.9	1312.7
177.5°	1316.9	1316.1	1314.5	1312.8	1311.2	1309.6	1311.2	1312.8	1314.5	1316.1	1316.9
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	750.7	752.2	753.0	749.9	747.6	751.5	756.8	760.7	763.7	767.6	769.9
5°	706.3	711.6	711.6	713.2	715.5	719.3	729.3	736.2	742.3	746.9	750.7
7.5°	668.7	672.6	674.9	678.7	682.5	687.9	699.4	709.3	718.5	723.9	730.0
10°	635.0	638.1	641.9	644.2	651.1	658.8	673.3	681.8	692.5	700.9	708.6
12.5°	602.9	613.6	615.9	615.1	621.3	629.7	644.2	657.3	668.7	677.2	685.6
15°	579.9	583.7	588.3	587.5	600.6	602.9	615.1	630.4	645.8	651.1	658.8
17.5°	554.6	560.7	565.3	567.6	571.5	579.9	591.4	602.9	622.8	623.6	643.5
20°	534.7	540.8	543.9	546.9	549.2	559.2	569.2	582.2	598.3	606.7	617.4
22.5°	521.7	524.7	527.0	529.3	532.4	537.8	550.0	564.6	575.3	584.5	591.4
25°	506.3	509.4	512.5	514.0	516.3	519.4	528.6	540.1	555.4	561.5	568.4
27.5°	495.6	495.6	497.2	497.2	500.2	503.3	510.2	520.9	533.2	540.8	550.0
30°	484.1	483.4	484.1	483.4	482.6	487.2	493.3	502.5	510.9	520.1	526.3
32.5°	472.6	471.9	471.9	472.6	469.6	471.9	474.9	483.4	492.6	497.2	504.1
35°	460.4	458.9	458.9	458.9	457.3	455.8	458.9	466.5	472.6	478.8	484.1
37.5°	448.1	445.8	445.8	444.3	442.8	440.5	440.5	446.6	455.0	457.3	464.2
40°	431.3	431.3	429.7	429.0	427.4	425.9	423.6	429.0	436.6	438.9	444.3
42.5°	414.4	412.1	411.4	411.4	411.4	409.1	407.5	411.4	416.0	419.8	422.9
45°	395.3	393.7	394.5	393.7	392.2	391.4	390.7	392.2	397.6	399.1	402.9
47.5°	374.6	373.8	373.8	373.1	372.3	373.1	370.0	373.8	375.4	376.9	380.0
50°	353.1	352.4	351.6	350.8	350.8	351.6	350.8	350.8	353.9	355.4	358.5
52.5°	331.7	329.4	329.4	328.6	328.6	327.1	328.6	329.4	330.9	332.5	334.0
55°	308.7	308.7	306.4	306.4	304.9	304.9	305.6	304.9	307.9	309.5	309.5
57.5°	286.5	283.4	284.2	282.7	281.1	280.4	280.4	281.9	283.4	283.4	285.0
60°	262.7	259.7	258.9	255.9	257.4	255.1	255.9	255.9	258.9	257.4	258.9
62.5°	239.0	235.2	232.9	231.3	231.3	232.1	230.6	229.8	231.3	232.9	235.9
65°	213.7	211.4	209.1	206.8	206.8	206.1	207.6	205.3	204.5	205.3	206.8
67.5°	187.7	185.4	183.1	180.8	181.6	179.3	177.7	180.0	178.5	179.3	180.8
70°	162.4	160.9	156.3	154.7	154.0	154.7	154.0	152.4	154.7	154.0	154.7
72.5°	137.1	135.6	133.3	129.5	129.5	128.7	127.9	127.9	127.2	127.2	127.2
75°	112.6	109.5	107.2	106.5	104.9	104.2	103.4	101.9	102.6	103.4	101.9
77.5°	87.3	83.5	82.7	82.7	80.4	80.4	81.2	80.4	79.7	79.7	79.7
80°	64.3	61.3	61.3	59.8	58.2	58.2	58.2	58.2	57.5	56.7	57.5
82.5°	41.4	40.6	39.8	39.8	41.4	38.3	39.8	39.1	38.3	38.3	37.5
85°	23.0	23.7	23.0	23.7	22.2	23.0	23.0	23.0	22.2	23.0	21.4
87.5°	8.4	8.4	8.4	9.2	9.2	9.2	9.2	9.2	10.0	9.2	9.2
90°	28.4	27.5	26.6	25.7	24.8	21.8	18.8	15.9	12.9	11.4	10.2
92.5°	46.1	45.4	44.7	44.0	43.3	41.9	40.6	39.2	37.9	37.2	36.5
95°	80.0	79.1	78.2	77.3	76.4	74.6	72.7	70.9	69.0	68.1	67.3
97.5°	116.0	114.9	113.8	112.6	111.5	110.1	108.7	107.4	106.0	105.3	104.7
100°	154.5	153.8	153.1	152.4	151.7	150.5	149.4	148.2	147.1	146.5	145.8
102.5°	199.9	199.2	198.5	197.8	197.1	195.5	193.9	192.3	190.7	189.9	189.6
105°	243.6	243.6	243.6	243.6	243.6	241.5	239.5	237.4	235.3	234.3	234.1
107.5°	293.8	293.1	292.4	291.7	291.0	290.1	289.2	288.3	287.4	286.9	286.8
110°	343.2	342.3	341.4	340.4	339.5	339.1	338.6	338.2	337.7	337.5	337.3

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	392.6	391.5	390.3	389.2	388.0	388.0	388.0	388.0	388.0	388.0	387.9
115°	440.6	440.3	440.1	439.8	439.6	440.1	440.5	441.0	441.5	441.7	441.4
117.5°	490.2	490.2	490.2	490.2	490.2	490.7	491.1	491.6	492.1	492.3	492.2
120°	539.9	540.1	540.4	540.6	540.8	541.9	543.1	544.2	545.3	545.9	545.2
122.5°	589.6	590.3	591.0	591.7	592.4	592.8	593.3	593.7	594.2	594.4	593.9
125°	639.3	640.2	641.1	642.1	643.0	643.4	643.9	644.3	644.8	645.0	644.7
127.5°	688.0	689.4	690.7	692.1	693.5	694.0	694.4	694.9	695.4	695.6	694.9
130°	738.4	739.3	740.2	741.1	742.0	742.7	743.4	744.1	744.8	745.1	744.2
132.5°	786.0	787.1	788.2	789.4	790.5	791.0	791.4	791.9	792.4	792.6	791.7
135°	834.4	835.3	836.2	837.1	838.0	838.2	838.4	838.7	838.9	839.0	838.3
137.5°	880.9	882.0	883.2	884.3	885.5	884.8	884.1	883.4	882.7	882.4	881.8
140°	928.9	929.2	929.4	929.7	929.9	929.7	929.4	929.2	928.9	928.8	928.2
142.5°	972.3	972.5	972.8	973.0	973.2	972.7	972.3	971.8	971.3	971.1	970.5
145°	1014.6	1014.8	1015.1	1015.3	1015.5	1014.8	1014.1	1013.4	1012.7	1012.4	1012.2
147.5°	1055.8	1055.8	1055.8	1055.8	1055.8	1055.1	1054.4	1053.7	1053.0	1052.7	1052.2
150°	1092.9	1092.9	1092.9	1092.9	1092.9	1092.5	1092.0	1091.6	1091.1	1090.9	1090.7
152.5°	1127.8	1127.3	1126.8	1126.4	1125.9	1125.7	1125.5	1125.2	1125.0	1124.9	1124.6
155°	1161.6	1160.7	1159.8	1158.8	1157.9	1157.7	1157.5	1157.2	1157.0	1156.9	1156.9
157.5°	1190.5	1189.6	1188.7	1187.7	1186.8	1186.6	1186.4	1186.1	1185.9	1185.8	1185.9
160°	1217.2	1216.1	1214.9	1213.8	1212.6	1212.6	1212.6	1212.6	1212.6	1212.6	1212.8
162.5°	1242.0	1240.9	1239.7	1238.6	1237.4	1237.2	1237.0	1236.7	1236.5	1236.4	1236.7
165°	1262.5	1261.1	1259.8	1258.4	1257.0	1257.0	1257.0	1257.0	1257.0	1257.0	1257.3
167.5°	1280.0	1278.7	1277.3	1276.0	1274.6	1274.4	1274.1	1273.9	1273.6	1273.5	1274.0
170°	1294.4	1292.8	1291.2	1289.6	1288.0	1288.0	1288.0	1288.0	1288.0	1288.0	1288.5
172.5°	1304.8	1303.4	1302.1	1300.7	1299.3	1299.3	1299.3	1299.3	1299.3	1299.3	1299.8
175°	1312.0	1310.6	1309.3	1307.9	1306.5	1306.5	1306.5	1306.5	1306.5	1306.5	1307.0
177.5°	1316.2	1314.8	1313.5	1312.1	1310.7	1310.7	1310.7	1310.7	1310.7	1310.7	1311.2
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	790.5	790.5	790.5	790.5
2.5°	773.7	776.0	783.7	792.8
5°	758.4	764.5	775.2	789.8
7.5°	741.5	750.7	766.0	784.4
10°	722.4	735.4	754.5	777.5
12.5°	701.7	718.5	743.1	766.8
15°	688.7	705.5	727.7	753.8
17.5°	663.4	683.3	706.3	743.1
20°	637.3	659.6	689.4	726.2
22.5°	617.4	641.2	669.5	708.6
25°	593.7	618.2	648.8	689.4
27.5°	568.4	592.9	627.4	670.3
30°	549.2	573.0	605.9	651.9
32.5°	526.3	549.2	583.7	632.0
35°	500.2	526.3	559.2	608.2
37.5°	480.3	504.1	538.5	585.3
40°	458.9	479.5	513.2	559.2
42.5°	435.9	458.9	488.0	533.9
45°	414.4	431.3	461.2	504.8
47.5°	391.4	410.6	433.6	467.3
50°	366.9	383.0	408.3	431.3
52.5°	343.2	356.2	377.7	395.3
55°	317.9	330.9	347.0	357.7
57.5°	294.2	303.3	314.1	321.0
60°	265.0	274.2	281.1	288.0
62.5°	239.0	245.9	249.7	253.6
65°	212.2	216.0	218.3	221.4
67.5°	183.1	186.9	187.7	192.3
70°	156.3	157.0	158.6	160.9
72.5°	131.0	132.5	131.8	133.3
75°	104.9	106.5	104.9	106.5
77.5°	79.7	81.2	81.2	83.5
80°	57.5	58.2	59.0	59.0
82.5°	37.5	39.8	38.3	39.1
85°	21.4	22.2	22.2	23.0
87.5°	10.0	10.7	10.0	11.5
90°	7.9	5.6	3.3	1.0
92.5°	35.1	33.8	32.4	31.0
95°	65.7	64.1	62.5	60.9
97.5°	103.6	102.4	101.3	100.1
100°	144.5	143.1	141.8	140.4
102.5°	188.9	188.2	187.5	186.8
105°	233.6	233.1	232.7	232.2
107.5°	286.6	286.3	286.1	285.9
110°	336.8	336.3	335.9	335.4

TEST NUMBER: P1031709

CATALOG NUMBER: S123DIW-B560D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	387.7	387.4	387.2	387.0
115°	440.7	440.0	439.3	438.6
117.5°	491.9	491.7	491.4	491.2
120°	543.9	542.5	541.2	539.8
122.5°	593.0	592.1	591.2	590.3
125°	644.0	643.3	642.6	641.9
127.5°	693.5	692.2	690.8	689.4
130°	742.4	740.5	738.7	736.9
132.5°	789.8	788.0	786.1	784.3
135°	836.9	835.6	834.2	832.8
137.5°	880.7	879.5	878.4	877.2
140°	927.1	926.0	924.8	923.7
142.5°	969.4	968.3	967.1	966.0
145°	1011.7	1011.3	1010.8	1010.4
147.5°	1051.3	1050.4	1049.4	1048.5
150°	1090.2	1089.7	1089.3	1088.8
152.5°	1123.9	1123.2	1122.5	1121.8
155°	1156.9	1156.9	1156.9	1156.9
157.5°	1186.1	1186.4	1186.6	1186.8
160°	1213.3	1213.8	1214.2	1214.7
162.5°	1237.4	1238.1	1238.8	1239.5
165°	1258.0	1258.7	1259.4	1260.1
167.5°	1274.9	1275.8	1276.8	1277.7
170°	1289.4	1290.3	1291.2	1292.1
172.5°	1300.7	1301.6	1302.6	1303.5
175°	1307.9	1308.8	1309.8	1310.7
177.5°	1312.1	1313.0	1313.9	1314.8
180°	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)