

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031742

Luminaire Tested: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031742
REPORT IS A COMBINATION OF REPORTS P991624 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1320UB40-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6917.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	94	90	87	83	85	82	79	76	66	63	61	51	49	48	37	36	35
2	86	79	73	68	78	72	67	62	58	54	51	45	42	40	33	31	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	27	26
4	72	62	54	48	65	56	49	44	45	41	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	32	32	28	26	24	21	20
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	20	17	15
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8427	8427	8427	8427
5°	8433	9710	8457	7247
10°	8379	11751	8388	6328
15°	8263	13935	8331	5697
20°	8164	16043	8181	5241
25°	8016	16448	8034	5005
30°	7910	13589	7910	4849
35°	7780	9088	7730	4712
40°	7622	6560	7528	4502
45°	7426	5196	7210	4239
50°	6945	4413	6698	3984
55°	6420	3878	6159	3697
60°	5887	3376	5573	3395
65°	5299	2891	5043	2996
70°	4691	2400	4379	2525
75°	4013	1810	3751	1949
80°	3171	1208	2926	1280
85°	2190	554	1748	505

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13592 cd/sqm

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	1.1
10°-20°	247.3	3.6
20°-30°	416.1	6.0
30°-40°	470.3	6.8
40°-50°	421.2	6.1
50°-60°	340.0	4.9
60°-70°	236.9	3.4
70°-80°	124.3	1.8
80°-90°	33.3	0.5
90°-100°	105.7	1.5
100°-110°	320.0	4.6
110°-120°	544.7	7.9
120°-130°	716.6	10.4
130°-140°	805.5	11.6
140°-150°	791.9	11.4
150°-160°	666.7	9.6
160°-170°	443.9	6.4
170°-180°	155.4	2.2
0°-30°	740.4	10.7
0°-40°	1210.7	17.5
0°-60°	1971.9	28.5
0°-90°	2366.5	34.2
90°-120°	970.5	14.0
90°-150°	3284.6	47.5
90°-180°	4551.0	65.8
0°-180°	6917.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	783	783	783	783	783	
5°	782	930	784	694	782	74
15°	746	1384	753	566	746	211
25°	683	1643	684	500	683	315
35°	602	885	599	459	602	377
45°	500	478	486	390	500	382
55°	354	325	340	310	354	317
65°	219	211	209	218	219	218
75°	106	108	99	117	106	113
85°	23	25	18	23	23	26
90°	1	39	1	39	1	7
95°	76	101	76	101	76	84
105°	290	307	290	307	290	311
115°	548	550	548	550	548	543
125°	802	793	802	793	802	716
135°	1041	1040	1041	1040	1041	802
145°	1263	1263	1263	1263	1263	789
155°	1446	1444	1446	1444	1446	666
165°	1575	1570	1575	1570	1575	444
175°	1638	1632	1638	1632	1638	156
180°	1642	1642	1642	1642	1642	

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	785.2	791.3	794.3	798.9	803.4	810.2	812.5	816.3	814.8	817.8	819.3
5°	782.2	792.8	801.9	813.3	823.9	831.5	839.1	851.2	860.3	861.8	868.7
7.5°	776.9	792.0	808.0	823.9	844.4	856.5	870.2	886.9	900.5	922.5	930.9
10°	770.0	791.3	814.0	836.0	864.1	883.1	899.8	927.8	955.9	978.7	999.9
12.5°	759.4	786.0	815.5	848.2	884.6	906.6	929.3	966.5	1009.0	1043.9	1066.7
15°	746.5	779.9	817.8	852.7	892.9	933.9	958.2	999.9	1060.6	1093.2	1151.6
17.5°	735.9	770.0	808.0	862.6	917.2	958.2	975.6	1052.2	1094.0	1148.6	1214.6
20°	719.2	762.4	811.0	865.6	936.2	961.2	996.9	1074.2	1125.8	1197.2	1278.3
22.5°	701.8	748.0	806.4	863.3	942.2	968.8	1017.4	1078.8	1160.7	1231.3	1320.8
25°	682.8	732.9	792.0	859.6	936.9	975.6	1021.1	1097.0	1185.8	1274.5	1357.2
27.5°	663.8	718.4	779.9	847.4	922.5	968.0	1013.6	1092.5	1206.3	1302.6	1408.1
30°	645.6	700.2	761.7	830.7	909.6	953.6	996.9	1095.5	1222.2	1330.7	1436.9
32.5°	625.9	682.0	746.5	804.2	883.8	930.9	979.4	1095.5	1232.0	1347.4	1444.5
35°	602.4	660.0	715.4	773.1	852.0	904.3	958.9	1087.9	1241.2	1352.7	1412.6
37.5°	579.6	630.4	678.2	734.4	817.1	873.2	936.2	1078.8	1236.6	1329.9	1346.6
40°	553.8	604.6	643.3	695.7	782.9	848.2	911.9	1066.7	1216.9	1276.0	1227.5
42.5°	528.8	569.0	602.4	653.2	748.0	811.8	880.8	1044.7	1178.2	1190.3	1081.1
45°	500.0	528.8	558.4	616.0	710.1	775.3	852.0	1012.8	1116.0	1081.1	943.0
47.5°	462.8	488.6	521.2	574.3	669.9	737.4	810.2	971.8	1025.7	952.9	801.9
50°	427.1	449.1	479.5	531.1	627.4	693.4	770.8	907.3	933.9	819.3	691.1
52.5°	391.5	408.2	437.7	489.3	585.7	649.4	720.0	841.3	826.2	703.3	589.5
55°	354.3	368.7	396.8	447.6	537.1	597.8	665.3	760.2	720.7	603.9	512.8
57.5°	317.9	333.0	361.9	404.4	488.6	547.7	601.6	676.0	616.8	523.5	443.1
60°	285.3	298.1	320.2	361.9	438.5	486.3	535.6	586.4	537.1	446.8	385.4
62.5°	251.1	263.3	283.7	321.7	387.7	430.2	469.6	511.3	456.7	390.7	336.1
65°	219.2	229.1	248.1	283.0	336.8	371.7	403.6	432.4	388.4	327.7	286.8
67.5°	190.4	198.8	214.7	245.8	291.3	316.4	342.2	366.4	329.3	280.7	245.8
70°	159.3	166.1	180.6	203.3	239.7	265.5	284.5	302.7	269.3	230.6	207.1
72.5°	132.0	138.8	147.9	171.5	196.5	212.4	232.9	242.8	223.8	191.9	168.4
75°	105.5	110.8	119.1	134.3	157.8	168.4	181.3	188.9	171.5	150.2	135.8
77.5°	82.7	85.0	91.0	101.7	117.6	129.7	139.6	144.1	132.0	118.3	106.2
80°	58.4	61.5	66.0	75.1	87.2	91.0	97.1	102.4	94.8	82.7	75.1
82.5°	38.7	42.5	44.8	48.6	56.1	60.7	62.2	66.8	59.9	55.4	52.3
85°	22.8	24.3	25.0	27.3	31.1	33.4	35.7	36.4	34.9	34.1	31.1
87.5°	11.4	11.4	11.4	12.9	13.7	15.2	15.9	15.9	15.9	15.2	14.4
90°	1.3	4.2	7.0	9.9	12.8	14.2	16.1	19.8	23.5	27.3	31.0
92.5°	38.7	40.4	42.1	43.8	45.5	46.4	47.3	49.0	50.7	52.5	54.2
95°	76.1	78.1	80.1	82.1	84.1	85.1	86.3	88.6	90.9	93.2	95.5
97.5°	125.1	126.5	128.0	129.4	130.9	131.6	132.5	134.2	135.9	137.6	139.3
100°	175.5	177.2	178.9	180.6	182.3	183.2	183.9	185.3	186.8	188.2	189.6
102.5°	233.5	234.4	235.2	236.1	237.0	237.4	238.4	240.4	242.4	244.4	246.4
105°	290.3	290.9	291.5	292.0	292.6	292.9	294.2	296.8	299.3	301.9	304.5
107.5°	357.4	357.7	357.9	358.2	358.5	358.6	359.2	360.3	361.5	362.6	363.8
110°	419.3	419.9	420.5	421.0	421.6	421.9	422.2	422.7	423.3	423.8	424.4

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	483.8	484.1	484.4	484.7	485.0	485.1	485.1	485.1	485.1	485.1	485.1
115°	548.3	549.2	550.0	550.9	551.8	552.2	551.9	551.3	550.8	550.2	549.6
117.5°	614.1	614.4	614.7	615.0	615.3	615.4	615.1	614.5	614.0	613.4	612.8
120°	674.7	676.4	678.2	679.9	681.6	682.5	681.8	680.3	678.9	677.4	676.0
122.5°	737.9	739.1	740.2	741.4	742.5	743.1	742.8	742.2	741.7	741.1	740.5
125°	802.4	803.3	804.1	805.0	805.9	806.3	806.0	805.4	804.9	804.3	803.7
127.5°	861.8	863.5	865.2	866.9	868.6	869.5	869.2	868.7	868.1	867.6	867.0
130°	921.1	923.4	925.7	928.0	930.3	931.5	931.1	930.2	929.3	928.5	927.6
132.5°	980.5	982.8	985.1	987.4	989.7	990.8	990.5	989.9	989.4	988.8	988.2
135°	1041.1	1042.8	1044.6	1046.3	1048.0	1048.9	1048.8	1048.5	1048.2	1047.9	1047.6
137.5°	1096.6	1098.0	1099.4	1100.9	1102.3	1103.0	1103.4	1104.3	1105.2	1106.0	1106.9
140°	1154.6	1156.0	1157.5	1158.9	1160.4	1161.1	1161.2	1161.5	1161.8	1162.1	1162.4
142.5°	1207.5	1208.9	1210.4	1211.8	1213.3	1214.0	1214.3	1214.9	1215.4	1216.0	1216.6
145°	1263.0	1263.6	1264.2	1264.7	1265.3	1265.6	1266.0	1266.9	1267.8	1268.6	1269.5
147.5°	1310.7	1311.9	1313.0	1314.2	1315.3	1315.9	1316.3	1317.2	1318.1	1318.9	1319.8
150°	1361.1	1361.7	1362.2	1362.8	1363.3	1363.6	1363.9	1364.5	1365.0	1365.6	1366.2
152.5°	1402.3	1403.2	1404.0	1404.9	1405.8	1406.2	1406.3	1406.6	1406.9	1407.2	1407.5
155°	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2	1446.3	1446.6	1446.9	1447.2	1447.5
157.5°	1483.6	1483.3	1483.0	1482.7	1482.4	1482.3	1482.4	1482.7	1483.0	1483.3	1483.6
160°	1518.5	1517.9	1517.3	1516.8	1516.2	1515.9	1515.9	1515.9	1515.9	1515.9	1515.9
162.5°	1549.4	1548.5	1547.7	1546.8	1545.9	1545.5	1545.6	1545.9	1546.2	1546.5	1546.8
165°	1575.2	1574.3	1573.5	1572.6	1571.7	1571.3	1571.3	1571.3	1571.3	1571.3	1571.3
167.5°	1597.2	1596.0	1594.9	1593.7	1592.6	1592.0	1592.1	1592.4	1592.7	1593.0	1593.3
170°	1615.2	1614.1	1612.9	1611.8	1610.7	1610.1	1610.1	1610.1	1610.1	1610.1	1610.1
172.5°	1629.4	1628.2	1627.1	1625.9	1624.8	1624.2	1624.2	1624.2	1624.2	1624.2	1624.2
175°	1638.4	1637.3	1636.1	1635.0	1633.9	1633.3	1633.3	1633.3	1633.3	1633.3	1633.3
177.5°	1643.6	1642.4	1641.3	1640.1	1639.0	1638.4	1638.4	1638.4	1638.4	1638.4	1638.4
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	824.7	826.2	831.5	835.3	842.9	842.1	842.1	841.3	839.1	842.9	845.1
5°	882.3	895.2	896.7	913.4	914.2	921.0	925.6	921.8	930.9	930.1	923.3
7.5°	953.6	971.1	979.4	995.3	1013.6	1009.0	1026.5	1029.5	1028.0	1035.6	1040.9
10°	1031.8	1062.1	1083.4	1112.9	1120.5	1125.1	1136.5	1146.3	1166.0	1150.9	1160.7
12.5°	1121.3	1143.3	1171.4	1218.4	1241.9	1257.1	1262.4	1269.2	1282.9	1274.5	1275.3
15°	1196.4	1226.0	1273.8	1332.2	1339.0	1358.0	1353.4	1394.4	1414.1	1384.5	1401.2
17.5°	1274.5	1314.0	1370.9	1421.7	1450.5	1463.4	1475.6	1515.0	1513.5	1509.0	1512.7
20°	1324.6	1389.1	1459.6	1527.2	1535.5	1545.4	1578.0	1594.7	1591.6	1604.5	1612.9
22.5°	1395.2	1463.4	1538.5	1583.3	1602.3	1613.6	1639.4	1650.1	1654.6	1657.7	1652.3
25°	1454.3	1527.2	1582.5	1622.0	1633.4	1639.4	1647.8	1650.8	1648.5	1643.2	1647.8
27.5°	1494.5	1553.0	1590.9	1609.1	1603.0	1593.2	1577.2	1566.6	1543.1	1531.7	1545.4
30°	1511.2	1537.0	1548.4	1518.1	1487.7	1463.4	1433.1	1377.0	1332.9	1345.8	1328.4
32.5°	1484.7	1468.0	1413.4	1335.2	1311.7	1272.3	1186.5	1120.5	1122.8	1087.9	1102.3
35°	1406.5	1330.7	1227.5	1109.1	1078.0	1056.8	962.7	948.3	918.0	885.3	894.4
37.5°	1268.5	1157.7	1032.5	945.3	899.0	852.7	799.6	767.8	749.5	735.9	746.5
40°	1100.0	965.0	861.8	783.7	744.2	714.6	678.2	646.4	625.9	623.6	627.4
42.5°	934.7	820.9	726.0	651.7	638.8	603.9	580.4	555.3	549.3	539.4	544.7
45°	791.3	698.7	620.6	559.9	544.7	535.6	506.8	490.8	484.0	477.9	487.1
47.5°	687.3	590.2	533.3	496.9	481.7	466.6	450.6	440.0	434.7	435.5	434.7
50°	587.2	515.9	465.8	437.7	428.6	418.0	405.1	398.3	396.0	389.2	394.5
52.5°	505.3	453.7	418.8	392.2	385.4	377.8	367.2	363.4	358.1	356.6	356.6
55°	439.3	399.1	371.0	353.5	345.2	339.1	333.0	328.5	324.7	324.7	324.7
57.5°	387.7	352.8	332.3	317.1	314.1	308.0	301.2	301.2	295.9	295.1	297.4
60°	343.7	312.6	296.6	283.7	279.2	277.7	270.8	270.8	269.3	265.5	268.6
62.5°	298.9	276.1	262.5	252.6	248.1	248.1	242.8	239.0	239.0	239.7	238.2
65°	257.9	241.3	229.1	221.5	219.2	216.2	215.5	212.4	210.1	210.9	210.1
67.5°	221.5	208.6	200.3	194.2	190.4	188.9	186.6	186.6	185.1	185.9	182.1
70°	188.9	176.0	169.2	163.1	161.6	161.6	158.6	159.3	157.8	160.1	158.6
72.5°	155.5	145.7	140.4	138.1	136.6	135.8	134.3	132.8	132.0	133.5	132.8
75°	125.9	117.6	113.8	112.3	110.8	110.8	110.0	109.2	108.5	108.5	108.5
77.5°	97.9	92.6	88.0	89.5	87.2	88.0	85.7	85.7	86.5	85.7	85.7
80°	72.1	68.3	68.3	66.8	63.7	65.2	65.2	63.0	62.2	63.7	61.5
82.5°	47.8	47.0	45.5	44.8	43.2	44.0	43.2	42.5	41.7	43.2	41.7
85°	28.1	28.1	27.3	25.8	27.3	26.6	25.8	25.8	25.0	25.0	25.0
87.5°	14.4	12.9	12.9	12.1	12.9	11.4	12.1	11.4	10.6	11.4	10.6
90°	32.1	33.3	34.4	35.5	36.1	36.4	37.0	37.5	38.1	38.7	38.1
92.5°	55.1	55.9	56.8	57.7	58.1	57.8	57.2	56.7	56.1	55.5	56.1
95°	96.6	97.8	98.9	100.0	100.6	100.6	100.6	100.6	100.6	100.6	100.6
97.5°	140.7	142.2	143.6	145.1	145.8	145.7	145.4	145.1	144.8	144.5	144.8
100°	190.5	191.3	192.2	193.1	193.5	193.8	194.4	194.9	195.5	196.1	195.5
102.5°	247.3	248.1	249.0	249.9	250.3	250.2	249.9	249.6	249.3	249.0	249.3
105°	304.5	304.5	304.5	304.5	304.5	304.8	305.3	305.9	306.4	307.0	306.4
107.5°	364.7	365.5	366.4	367.3	367.7	367.6	367.3	367.0	366.7	366.4	366.7
110°	425.6	426.7	427.9	429.0	429.6	429.3	428.7	428.2	427.6	427.0	427.6

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	486.5	487.9	489.4	490.8	491.5	491.5	491.5	491.5	491.5	491.5	491.5
115°	549.9	550.2	550.5	550.8	550.9	550.8	550.5	550.2	549.9	549.6	549.9
117.5°	612.8	612.8	612.8	612.8	612.8	612.4	611.5	610.6	609.8	608.9	609.8
120°	675.7	675.4	675.1	674.8	674.7	674.4	673.8	673.3	672.7	672.1	672.7
122.5°	739.7	738.8	738.0	737.1	736.7	736.3	735.4	734.5	733.7	732.8	733.7
125°	802.6	801.4	800.3	799.2	798.6	798.0	796.9	795.7	794.6	793.4	794.6
127.5°	865.3	863.5	861.8	860.1	859.2	858.6	857.5	856.4	855.2	854.1	855.2
130°	926.4	925.3	924.1	923.0	922.4	921.4	919.4	917.4	915.4	913.4	915.4
132.5°	986.8	985.4	983.9	982.5	981.8	981.1	979.6	978.2	976.7	975.3	976.7
135°	1046.4	1045.3	1044.1	1043.0	1042.4	1042.1	1041.5	1041.0	1040.4	1039.8	1040.4
137.5°	1105.5	1104.1	1102.6	1101.2	1100.5	1100.1	1099.2	1098.3	1097.5	1096.6	1097.5
140°	1162.1	1161.8	1161.5	1161.2	1161.1	1160.1	1158.1	1156.1	1154.1	1152.1	1154.1
142.5°	1216.3	1216.0	1215.7	1215.4	1215.3	1214.6	1213.1	1211.7	1210.2	1208.8	1210.2
145°	1269.2	1268.9	1268.6	1268.3	1268.2	1267.6	1266.5	1265.3	1264.2	1263.0	1264.2
147.5°	1319.8	1319.8	1319.8	1319.8	1319.8	1318.9	1317.2	1315.5	1313.7	1312.0	1313.7
150°	1366.2	1366.2	1366.2	1366.2	1366.2	1365.3	1363.6	1361.9	1360.2	1358.5	1360.2
152.5°	1408.1	1408.7	1409.2	1409.8	1410.1	1409.4	1407.9	1406.5	1405.0	1403.6	1405.0
155°	1448.7	1449.8	1451.0	1452.1	1452.7	1451.7	1449.7	1447.6	1445.6	1443.6	1445.6
157.5°	1484.8	1485.9	1487.1	1488.2	1488.8	1487.9	1486.2	1484.5	1482.7	1481.0	1482.7
160°	1517.3	1518.7	1520.2	1521.6	1522.3	1521.7	1520.6	1519.5	1518.3	1517.2	1518.3
162.5°	1548.2	1549.7	1551.1	1552.6	1553.3	1552.3	1550.3	1548.3	1546.3	1544.3	1546.3
165°	1573.0	1574.8	1576.5	1578.2	1579.1	1578.1	1576.1	1574.1	1572.1	1570.1	1572.1
167.5°	1595.0	1596.7	1598.4	1600.1	1601.0	1600.1	1598.4	1596.7	1595.0	1593.3	1595.0
170°	1612.1	1614.1	1616.1	1618.1	1619.1	1618.1	1616.1	1614.1	1612.1	1610.1	1612.1
172.5°	1625.9	1627.7	1629.4	1631.1	1632.0	1631.0	1629.0	1627.0	1625.0	1623.0	1625.0
175°	1635.0	1636.7	1638.4	1640.1	1641.0	1640.0	1638.0	1636.0	1634.0	1632.0	1634.0
177.5°	1640.1	1641.9	1643.6	1645.3	1646.2	1645.2	1643.2	1641.1	1639.1	1637.1	1639.1
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	839.1	841.3	835.3	833.8	833.8	836.8	834.5	814.0	817.8	813.3	811.8
5°	931.6	927.1	921.0	918.0	914.2	903.6	902.8	879.3	874.7	859.6	852.7
7.5°	1033.3	1029.5	1011.3	1009.0	1007.5	997.6	972.6	947.6	929.3	911.9	895.2
10°	1149.4	1138.0	1129.6	1112.9	1104.6	1090.9	1058.3	1034.8	1003.7	977.1	942.2
12.5°	1288.9	1276.0	1248.0	1235.8	1225.2	1187.3	1154.7	1128.1	1067.4	1049.2	1006.0
15°	1391.4	1364.1	1361.0	1334.5	1332.9	1291.2	1229.0	1200.2	1153.1	1086.4	1041.6
17.5°	1502.1	1477.9	1458.9	1427.0	1422.5	1383.0	1337.5	1266.9	1215.4	1151.6	1094.7
20°	1583.3	1570.4	1537.8	1524.9	1498.3	1465.0	1417.9	1330.7	1267.7	1204.0	1134.2
22.5°	1647.8	1634.9	1609.1	1591.6	1576.5	1533.2	1477.1	1402.7	1316.3	1232.8	1160.7
25°	1647.0	1643.2	1632.6	1624.3	1612.9	1581.0	1534.0	1462.7	1366.3	1274.5	1174.4
27.5°	1553.7	1564.3	1582.5	1591.6	1589.4	1584.8	1558.3	1498.3	1411.8	1302.6	1190.3
30°	1359.5	1398.2	1432.3	1477.9	1491.5	1524.9	1540.1	1505.9	1436.9	1335.2	1210.8
32.5°	1127.4	1183.5	1257.8	1282.9	1326.1	1390.6	1462.7	1475.6	1432.3	1354.2	1223.7
35°	924.8	971.1	1028.7	1068.2	1106.9	1211.6	1302.6	1381.5	1395.9	1344.3	1220.7
37.5°	765.5	798.1	848.9	882.3	918.0	1007.5	1134.9	1237.4	1309.4	1310.9	1212.3
40°	650.2	664.6	708.6	732.9	767.0	844.4	958.2	1091.7	1197.2	1245.7	1190.3
42.5°	550.8	569.7	606.2	624.4	646.4	713.9	789.0	915.7	1046.2	1150.1	1149.4
45°	491.6	505.3	522.0	537.1	562.2	602.4	688.1	782.9	908.1	1025.7	1072.0
47.5°	439.3	452.2	468.8	473.4	490.1	528.0	580.4	663.1	779.9	896.7	984.0
50°	395.3	405.9	417.3	425.6	433.2	464.3	503.7	573.5	666.9	779.9	888.4
52.5°	361.1	368.7	378.6	383.1	389.9	412.7	443.1	494.6	571.3	674.4	779.9
55°	329.3	334.6	340.6	348.2	351.3	367.9	391.5	435.5	492.4	584.9	685.1
57.5°	299.7	301.9	305.7	310.3	314.1	328.5	349.0	378.6	428.6	500.0	594.8
60°	266.3	272.4	274.6	279.2	281.5	292.8	308.8	333.8	372.5	433.9	505.3
62.5°	238.2	242.0	245.8	248.1	253.4	257.2	270.1	292.8	324.7	370.2	434.7
65°	213.2	214.7	217.0	219.2	220.8	225.3	237.5	252.6	276.9	317.1	367.2
67.5°	184.4	185.9	188.9	189.7	191.2	197.2	204.1	217.0	237.5	267.8	308.8
70°	156.3	158.6	160.1	161.6	163.9	166.1	173.7	184.4	200.3	221.5	253.4
72.5°	132.0	134.3	134.3	135.8	135.0	138.1	145.7	153.2	163.9	181.3	209.4
75°	107.7	107.7	109.2	110.0	110.8	113.8	116.8	122.9	131.2	144.9	162.4
77.5°	85.0	84.2	85.7	85.7	85.7	88.0	91.0	94.1	99.4	109.2	122.9
80°	62.2	62.2	63.7	64.5	63.0	63.7	65.2	68.3	72.1	78.9	86.5
82.5°	41.0	44.0	43.2	44.0	43.2	44.8	45.5	46.3	47.8	50.8	56.1
85°	25.0	25.0	25.0	25.8	25.0	25.8	25.8	25.8	26.6	28.1	30.3
87.5°	10.6	10.6	10.6	11.4	10.6	10.6	11.4	10.6	11.4	11.4	12.1
90°	37.5	37.0	36.4	36.1	35.5	34.4	33.3	32.1	31.0	27.3	23.5
92.5°	56.7	57.2	57.8	58.1	57.7	56.8	55.9	55.1	54.2	52.5	50.7
95°	100.6	100.6	100.6	100.6	100.0	98.9	97.8	96.6	95.5	93.2	90.9
97.5°	145.1	145.4	145.7	145.8	145.1	143.6	142.2	140.7	139.3	137.6	135.9
100°	194.9	194.4	193.8	193.5	193.1	192.2	191.3	190.5	189.6	188.2	186.8
102.5°	249.6	249.9	250.2	250.3	249.9	249.0	248.1	247.3	246.4	244.4	242.4
105°	305.9	305.3	304.8	304.5	304.5	304.5	304.5	304.5	304.5	301.9	299.3
107.5°	367.0	367.3	367.6	367.7	367.3	366.4	365.5	364.7	363.8	362.6	361.5
110°	428.2	428.7	429.3	429.6	429.0	427.9	426.7	425.6	424.4	423.8	423.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	491.5	491.5	491.5	491.5	490.8	489.4	487.9	486.5	485.1	485.1	485.1
115°	550.2	550.5	550.8	550.9	550.8	550.5	550.2	549.9	549.6	550.2	550.8
117.5°	610.6	611.5	612.4	612.8	612.8	612.8	612.8	612.8	612.8	613.4	614.0
120°	673.3	673.8	674.4	674.7	674.8	675.1	675.4	675.7	676.0	677.4	678.9
122.5°	734.5	735.4	736.3	736.7	737.1	738.0	738.8	739.7	740.5	741.1	741.7
125°	795.7	796.9	798.0	798.6	799.2	800.3	801.4	802.6	803.7	804.3	804.9
127.5°	856.4	857.5	858.6	859.2	860.1	861.8	863.5	865.3	867.0	867.6	868.1
130°	917.4	919.4	921.4	922.4	923.0	924.1	925.3	926.4	927.6	928.5	929.3
132.5°	978.2	979.6	981.1	981.8	982.5	983.9	985.4	986.8	988.2	988.8	989.4
135°	1041.0	1041.5	1042.1	1042.4	1043.0	1044.1	1045.3	1046.4	1047.6	1047.9	1048.2
137.5°	1098.3	1099.2	1100.1	1100.5	1101.2	1102.6	1104.1	1105.5	1106.9	1106.0	1105.2
140°	1156.1	1158.1	1160.1	1161.1	1161.2	1161.5	1161.8	1162.1	1162.4	1162.1	1161.8
142.5°	1211.7	1213.1	1214.6	1215.3	1215.4	1215.7	1216.0	1216.3	1216.6	1216.0	1215.4
145°	1265.3	1266.5	1267.6	1268.2	1268.3	1268.6	1268.9	1269.2	1269.5	1268.6	1267.8
147.5°	1315.5	1317.2	1318.9	1319.8	1319.8	1319.8	1319.8	1319.8	1319.8	1318.9	1318.1
150°	1361.9	1363.6	1365.3	1366.2	1366.2	1366.2	1366.2	1366.2	1366.2	1365.6	1365.0
152.5°	1406.5	1407.9	1409.4	1410.1	1409.8	1409.2	1408.7	1408.1	1407.5	1407.2	1406.9
155°	1447.6	1449.7	1451.7	1452.7	1452.1	1451.0	1449.8	1448.7	1447.5	1447.2	1446.9
157.5°	1484.5	1486.2	1487.9	1488.8	1488.2	1487.1	1485.9	1484.8	1483.6	1483.3	1483.0
160°	1519.5	1520.6	1521.7	1522.3	1521.6	1520.2	1518.7	1517.3	1515.9	1515.9	1515.9
162.5°	1548.3	1550.3	1552.3	1553.3	1552.6	1551.1	1549.7	1548.2	1546.8	1546.5	1546.2
165°	1574.1	1576.1	1578.1	1579.1	1578.2	1576.5	1574.8	1573.0	1571.3	1571.3	1571.3
167.5°	1596.7	1598.4	1600.1	1601.0	1600.1	1598.4	1596.7	1595.0	1593.3	1593.0	1592.7
170°	1614.1	1616.1	1618.1	1619.1	1618.1	1616.1	1614.1	1612.1	1610.1	1610.1	1610.1
172.5°	1627.0	1629.0	1631.0	1632.0	1631.1	1629.4	1627.7	1625.9	1624.2	1624.2	1624.2
175°	1636.0	1638.0	1640.0	1641.0	1640.1	1638.4	1636.7	1635.0	1633.3	1633.3	1633.3
177.5°	1641.1	1643.2	1645.2	1646.2	1645.3	1643.6	1641.9	1640.1	1638.4	1638.4	1638.4
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	804.2	801.9	801.9	800.4	795.8	787.5	786.7	788.2	783.7	779.1	772.3
5°	843.6	829.2	824.7	820.1	811.0	795.8	789.8	784.4	776.1	766.2	755.6
7.5°	877.0	856.5	850.4	842.1	823.9	802.7	789.0	777.6	766.2	752.6	739.7
10°	918.7	889.1	874.7	862.6	837.6	808.0	787.5	770.8	752.6	735.9	719.2
12.5°	965.8	918.0	913.4	883.8	855.0	811.0	786.0	761.7	737.4	716.9	699.5
15°	1005.2	952.9	933.9	914.2	858.8	804.2	779.9	752.6	724.5	702.5	676.7
17.5°	1030.2	987.0	946.8	920.2	862.6	814.0	767.0	735.9	706.3	676.0	654.7
20°	1060.6	997.6	962.7	927.1	870.2	806.4	759.4	720.7	684.3	657.0	631.2
22.5°	1090.9	1006.0	977.1	938.5	871.7	798.9	745.8	707.1	665.3	638.0	610.0
25°	1087.9	1018.1	970.3	937.7	856.5	792.0	729.8	684.3	645.6	610.7	582.6
27.5°	1090.2	1004.5	955.9	918.0	845.9	782.2	713.1	665.3	625.1	588.7	559.1
30°	1090.9	984.0	941.5	896.0	826.2	758.7	694.2	645.6	603.1	563.7	537.1
32.5°	1088.7	967.3	914.2	873.2	795.1	735.9	672.2	620.6	577.3	540.9	515.9
35°	1083.4	947.6	886.1	834.5	763.2	703.3	651.7	598.6	552.3	518.9	490.1
37.5°	1068.9	926.3	856.5	805.7	726.0	665.3	619.8	575.8	531.1	491.6	467.3
40°	1058.3	897.5	826.9	771.5	685.8	626.6	588.7	547.0	503.0	467.3	443.8
42.5°	1034.0	870.2	796.6	730.6	646.4	585.7	550.0	516.6	478.7	443.8	422.6
45°	994.6	840.6	759.4	692.6	603.1	545.5	512.8	485.5	452.2	418.8	397.5
47.5°	939.2	798.1	720.0	653.2	560.6	502.2	469.6	449.1	422.6	394.5	376.3
50°	879.3	751.8	679.8	613.7	519.7	462.8	430.9	411.9	394.5	368.7	351.3
52.5°	801.1	702.5	633.5	570.5	475.7	421.1	393.0	379.3	361.1	342.9	327.7
55°	725.3	638.8	581.9	522.0	432.4	381.6	354.3	339.9	329.3	314.1	301.9
57.5°	637.3	579.6	527.3	472.6	392.2	345.9	320.2	302.7	295.9	289.0	277.7
60°	556.1	512.1	469.6	424.1	350.5	308.8	283.7	270.1	263.3	258.7	251.1
62.5°	481.7	447.6	411.2	374.8	308.0	270.1	251.1	237.5	231.4	230.6	223.8
65°	410.4	386.2	356.6	320.9	268.6	235.2	217.0	208.6	201.8	201.8	196.5
67.5°	339.1	322.4	298.9	273.9	232.9	201.8	185.1	177.5	173.7	173.7	169.9
70°	282.2	270.8	249.6	227.6	191.9	168.4	155.5	148.7	146.4	147.2	144.1
72.5°	229.1	217.0	199.5	183.6	157.0	139.6	130.5	122.9	119.1	119.9	119.1
75°	177.5	171.5	156.3	144.1	122.9	110.8	102.4	98.6	95.6	96.3	94.8
77.5°	133.5	124.4	116.1	107.7	94.8	85.0	78.1	74.3	72.1	72.1	72.1
80°	91.0	89.5	82.7	78.1	67.5	59.9	54.6	53.9	51.6	51.6	51.6
82.5°	59.2	55.4	51.6	48.6	42.5	37.9	35.7	34.1	33.4	32.6	34.1
85°	32.6	30.3	28.8	25.8	23.5	21.2	19.0	18.2	17.4	18.2	17.4
87.5°	12.9	10.6	10.6	9.9	9.1	8.3	8.3	6.8	6.8	6.1	6.1
90°	19.8	16.1	14.2	12.8	9.9	7.0	4.2	1.3	4.2	7.0	9.9
92.5°	49.0	47.3	46.4	45.5	43.8	42.1	40.4	38.7	40.4	42.1	43.8
95°	88.6	86.3	85.1	84.1	82.1	80.1	78.1	76.1	78.1	80.1	82.1
97.5°	134.2	132.5	131.6	130.9	129.4	128.0	126.5	125.1	126.5	128.0	129.4
100°	185.3	183.9	183.2	182.3	180.6	178.9	177.2	175.5	177.2	178.9	180.6
102.5°	240.4	238.4	237.4	237.0	236.1	235.2	234.4	233.5	234.4	235.2	236.1
105°	296.8	294.2	292.9	292.6	292.0	291.5	290.9	290.3	290.9	291.5	292.0
107.5°	360.3	359.2	358.6	358.5	358.2	357.9	357.7	357.4	357.7	357.9	358.2
110°	422.7	422.2	421.9	421.6	421.0	420.5	419.9	419.3	419.9	420.5	421.0

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	485.1	485.1	485.1	485.0	484.7	484.4	484.1	483.8	484.1	484.4	484.7
115°	551.3	551.9	552.2	551.8	550.9	550.0	549.2	548.3	549.2	550.0	550.9
117.5°	614.5	615.1	615.4	615.3	615.0	614.7	614.4	614.1	614.4	614.7	615.0
120°	680.3	681.8	682.5	681.6	679.9	678.2	676.4	674.7	676.4	678.2	679.9
122.5°	742.2	742.8	743.1	742.5	741.4	740.2	739.1	737.9	739.1	740.2	741.4
125°	805.4	806.0	806.3	805.9	805.0	804.1	803.3	802.4	803.3	804.1	805.0
127.5°	868.7	869.2	869.5	868.6	866.9	865.2	863.5	861.8	863.5	865.2	866.9
130°	930.2	931.1	931.5	930.3	928.0	925.7	923.4	921.1	923.4	925.7	928.0
132.5°	989.9	990.5	990.8	989.7	987.4	985.1	982.8	980.5	982.8	985.1	987.4
135°	1048.5	1048.8	1048.9	1048.0	1046.3	1044.6	1042.8	1041.1	1042.8	1044.6	1046.3
137.5°	1104.3	1103.4	1103.0	1102.3	1100.9	1099.4	1098.0	1096.6	1098.0	1099.4	1100.9
140°	1161.5	1161.2	1161.1	1160.4	1158.9	1157.5	1156.0	1154.6	1156.0	1157.5	1158.9
142.5°	1214.9	1214.3	1214.0	1213.3	1211.8	1210.4	1208.9	1207.5	1208.9	1210.4	1211.8
145°	1266.9	1266.0	1265.6	1265.3	1264.7	1264.2	1263.6	1263.0	1263.6	1264.2	1264.7
147.5°	1317.2	1316.3	1315.9	1315.3	1314.2	1313.0	1311.9	1310.7	1311.9	1313.0	1314.2
150°	1364.5	1363.9	1363.6	1363.3	1362.8	1362.2	1361.7	1361.1	1361.7	1362.2	1362.8
152.5°	1406.6	1406.3	1406.2	1405.8	1404.9	1404.0	1403.2	1402.3	1403.2	1404.0	1404.9
155°	1446.6	1446.3	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2
157.5°	1482.7	1482.4	1482.3	1482.4	1482.7	1483.0	1483.3	1483.6	1483.3	1483.0	1482.7
160°	1515.9	1515.9	1515.9	1516.2	1516.8	1517.3	1517.9	1518.5	1517.9	1517.3	1516.8
162.5°	1545.9	1545.6	1545.5	1545.9	1546.8	1547.7	1548.5	1549.4	1548.5	1547.7	1546.8
165°	1571.3	1571.3	1571.3	1571.7	1572.6	1573.5	1574.3	1575.2	1574.3	1573.5	1572.6
167.5°	1592.4	1592.1	1592.0	1592.6	1593.7	1594.9	1596.0	1597.2	1596.0	1594.9	1593.7
170°	1610.1	1610.1	1610.1	1610.7	1611.8	1612.9	1614.1	1615.2	1614.1	1612.9	1611.8
172.5°	1624.2	1624.2	1624.2	1624.8	1625.9	1627.1	1628.2	1629.4	1628.2	1627.1	1625.9
175°	1633.3	1633.3	1633.3	1633.9	1635.0	1636.1	1637.3	1638.4	1637.3	1636.1	1635.0
177.5°	1638.4	1638.4	1638.4	1639.0	1640.1	1641.3	1642.4	1643.6	1642.4	1641.3	1640.1
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	770.8	770.0	771.5	767.0	759.4	755.6	745.0	742.7	742.0	742.7	743.5
5°	749.5	748.8	746.5	738.9	729.8	723.0	710.1	709.3	704.8	700.2	702.5
7.5°	729.1	726.0	721.5	711.6	699.5	691.9	681.3	673.7	667.6	663.8	660.8
10°	708.6	704.0	699.5	686.6	671.4	660.0	647.1	641.1	634.2	631.2	628.2
12.5°	682.0	677.5	669.1	654.0	644.9	630.4	617.5	611.5	607.7	601.6	597.8
15°	660.8	651.7	647.1	631.2	612.2	610.7	587.2	585.7	578.1	578.1	572.0
17.5°	636.5	629.7	621.3	605.4	591.7	578.1	566.0	561.4	554.6	553.1	550.0
20°	613.0	603.9	600.9	584.9	570.5	553.8	540.9	536.4	533.3	530.3	532.6
22.5°	588.7	581.1	573.5	559.1	548.5	531.8	524.2	519.7	515.1	513.6	514.4
25°	565.2	558.4	550.8	536.4	525.0	511.3	504.5	502.2	500.0	500.0	499.2
27.5°	542.4	535.6	528.8	515.9	504.5	494.6	489.3	487.1	484.8	486.3	487.8
30°	518.9	512.8	506.8	495.4	486.3	477.2	474.2	472.6	471.9	475.7	475.7
32.5°	497.7	492.4	487.8	477.2	468.1	460.5	458.2	459.0	459.7	462.0	463.5
35°	475.7	471.9	467.3	458.2	450.6	443.8	444.6	444.6	446.1	449.9	452.9
37.5°	455.9	450.6	446.8	439.3	433.2	427.1	429.4	431.7	433.2	437.7	439.3
40°	432.4	430.2	427.1	419.5	414.2	413.5	414.2	415.7	418.8	421.1	423.3
42.5°	413.5	410.4	406.6	400.6	396.0	396.8	397.5	399.1	400.6	404.4	406.6
45°	392.2	389.9	386.9	381.6	377.8	378.6	379.3	379.3	380.8	385.4	386.9
47.5°	368.7	369.5	365.7	360.4	358.1	358.1	358.1	359.6	363.4	364.9	365.7
50°	345.9	344.4	343.7	338.4	336.8	336.1	336.8	337.6	342.9	342.2	344.4
52.5°	321.7	321.7	320.9	317.9	315.6	315.6	314.1	317.9	319.4	320.9	323.2
55°	298.1	295.9	295.1	293.6	290.6	289.8	291.3	295.9	297.4	298.9	301.2
57.5°	272.4	272.4	270.8	268.6	268.6	268.6	268.6	271.6	273.9	275.4	279.9
60°	248.8	245.8	243.5	243.5	243.5	242.8	247.3	247.3	251.9	252.6	254.1
62.5°	220.8	219.2	217.7	218.5	217.7	219.2	220.8	223.8	224.6	226.8	229.1
65°	194.2	194.2	192.7	197.2	194.2	194.2	198.0	198.0	199.5	201.8	204.8
67.5°	168.4	169.2	167.7	167.7	169.2	169.9	170.7	173.7	174.5	177.5	181.3
70°	141.9	143.4	144.1	142.6	144.1	145.7	147.2	147.9	151.0	152.5	154.8
72.5°	118.3	119.9	117.6	118.3	119.1	120.6	121.4	122.9	124.4	129.0	130.5
75°	94.8	94.1	93.3	96.3	94.8	97.9	98.6	98.6	100.1	103.9	105.5
77.5°	72.8	72.8	73.6	72.1	74.3	73.6	74.3	76.6	78.9	78.9	85.0
80°	50.8	52.3	52.3	52.3	53.1	53.9	52.3	56.1	56.9	56.9	59.2
82.5°	32.6	33.4	32.6	34.1	34.1	35.7	34.9	35.7	37.2	38.7	39.4
85°	17.4	17.4	19.0	19.0	18.2	19.0	18.2	19.0	20.5	20.5	21.2
87.5°	6.1	6.1	6.1	6.1	6.8	6.1	6.8	6.8	6.1	6.1	8.3
90°	12.8	14.2	16.1	19.8	23.5	27.3	31.0	32.1	33.3	34.4	35.5
92.5°	45.5	46.4	47.3	49.0	50.7	52.5	54.2	55.1	55.9	56.8	57.7
95°	84.1	85.1	86.3	88.6	90.9	93.2	95.5	96.6	97.8	98.9	100.0
97.5°	130.9	131.6	132.5	134.2	135.9	137.6	139.3	140.7	142.2	143.6	145.1
100°	182.3	183.2	183.9	185.3	186.8	188.2	189.6	190.5	191.3	192.2	193.1
102.5°	237.0	237.4	238.4	240.4	242.4	244.4	246.4	247.3	248.1	249.0	249.9
105°	292.6	292.9	294.2	296.8	299.3	301.9	304.5	304.5	304.5	304.5	304.5
107.5°	358.5	358.6	359.2	360.3	361.5	362.6	363.8	364.7	365.5	366.4	367.3
110°	421.6	421.9	422.2	422.7	423.3	423.8	424.4	425.6	426.7	427.9	429.0

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	485.0	485.1	485.1	485.1	485.1	485.1	485.1	486.5	487.9	489.4	490.8
115°	551.8	552.2	551.9	551.3	550.8	550.2	549.6	549.9	550.2	550.5	550.8
117.5°	615.3	615.4	615.1	614.5	614.0	613.4	612.8	612.8	612.8	612.8	612.8
120°	681.6	682.5	681.8	680.3	678.9	677.4	676.0	675.7	675.4	675.1	674.8
122.5°	742.5	743.1	742.8	742.2	741.7	741.1	740.5	739.7	738.8	738.0	737.1
125°	805.9	806.3	806.0	805.4	804.9	804.3	803.7	802.6	801.4	800.3	799.2
127.5°	868.6	869.5	869.2	868.7	868.1	867.6	867.0	865.3	863.5	861.8	860.1
130°	930.3	931.5	931.1	930.2	929.3	928.5	927.6	926.4	925.3	924.1	923.0
132.5°	989.7	990.8	990.5	989.9	989.4	988.8	988.2	986.8	985.4	983.9	982.5
135°	1048.0	1048.9	1048.8	1048.5	1048.2	1047.9	1047.6	1046.4	1045.3	1044.1	1043.0
137.5°	1102.3	1103.0	1103.4	1104.3	1105.2	1106.0	1106.9	1105.5	1104.1	1102.6	1101.2
140°	1160.4	1161.1	1161.2	1161.5	1161.8	1162.1	1162.4	1162.1	1161.8	1161.5	1161.2
142.5°	1213.3	1214.0	1214.3	1214.9	1215.4	1216.0	1216.6	1216.3	1216.0	1215.7	1215.4
145°	1265.3	1265.6	1266.0	1266.9	1267.8	1268.6	1269.5	1269.2	1268.9	1268.6	1268.3
147.5°	1315.3	1315.9	1316.3	1317.2	1318.1	1318.9	1319.8	1319.8	1319.8	1319.8	1319.8
150°	1363.3	1363.6	1363.9	1364.5	1365.0	1365.6	1366.2	1366.2	1366.2	1366.2	1366.2
152.5°	1405.8	1406.2	1406.3	1406.6	1406.9	1407.2	1407.5	1408.1	1408.7	1409.2	1409.8
155°	1446.2	1446.2	1446.3	1446.6	1446.9	1447.2	1447.5	1448.7	1449.8	1451.0	1452.1
157.5°	1482.4	1482.3	1482.4	1482.7	1483.0	1483.3	1483.6	1484.8	1485.9	1487.1	1488.2
160°	1516.2	1515.9	1515.9	1515.9	1515.9	1515.9	1515.9	1517.3	1518.7	1520.2	1521.6
162.5°	1545.9	1545.5	1545.6	1545.9	1546.2	1546.5	1546.8	1548.2	1549.7	1551.1	1552.6
165°	1571.7	1571.3	1571.3	1571.3	1571.3	1571.3	1571.3	1573.0	1574.8	1576.5	1578.2
167.5°	1592.6	1592.0	1592.1	1592.4	1592.7	1593.0	1593.3	1595.0	1596.7	1598.4	1600.1
170°	1610.7	1610.1	1610.1	1610.1	1610.1	1610.1	1610.1	1612.1	1614.1	1616.1	1618.1
172.5°	1624.8	1624.2	1624.2	1624.2	1624.2	1624.2	1624.2	1625.9	1627.7	1629.4	1631.1
175°	1633.9	1633.3	1633.3	1633.3	1633.3	1633.3	1633.3	1635.0	1636.7	1638.4	1640.1
177.5°	1639.0	1638.4	1638.4	1638.4	1638.4	1638.4	1638.4	1640.1	1641.9	1643.6	1645.3
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	742.7	743.5	740.4	738.2	744.2	740.4	740.4	741.2	739.7	742.0	741.2
5°	701.0	701.8	696.4	698.0	694.9	694.2	693.4	698.0	697.2	696.4	698.0
7.5°	660.0	660.0	657.7	656.2	656.2	654.0	657.0	656.2	657.7	657.7	660.0
10°	625.9	627.4	623.6	619.8	619.1	619.8	619.8	620.6	621.3	626.6	625.9
12.5°	597.8	595.5	594.8	592.5	588.7	587.2	585.7	594.0	591.7	591.7	591.7
15°	566.7	572.0	571.3	564.4	562.9	566.0	564.4	564.4	572.0	571.3	570.5
17.5°	550.0	548.5	547.0	543.2	544.0	543.2	544.0	544.0	548.5	548.5	548.5
20°	531.1	528.0	528.0	526.5	526.5	524.2	527.3	528.0	531.1	531.1	531.8
22.5°	514.4	512.1	512.1	511.3	512.8	509.8	512.8	513.6	513.6	515.9	515.9
25°	500.0	498.4	498.4	500.0	500.0	500.0	500.0	503.0	500.7	501.5	500.7
27.5°	487.1	487.8	488.6	489.3	488.6	489.3	490.1	491.6	492.4	491.6	490.1
30°	474.9	477.2	477.9	477.9	479.5	480.2	481.0	481.0	481.7	479.5	481.0
32.5°	465.8	465.8	467.3	468.1	469.6	470.4	470.4	471.9	471.1	468.8	469.6
35°	452.9	452.9	455.9	457.5	459.7	459.0	459.7	459.7	460.5	459.0	456.7
37.5°	440.0	441.5	441.5	444.6	445.3	446.1	445.3	446.8	446.1	444.6	443.8
40°	424.8	424.1	424.8	427.1	427.9	427.9	427.9	429.4	429.4	429.4	428.6
42.5°	405.9	408.2	407.4	409.7	408.9	408.9	410.4	411.9	412.7	410.4	411.2
45°	387.7	387.7	389.2	389.2	389.9	389.9	393.0	391.5	393.0	391.5	392.2
47.5°	367.9	368.7	368.7	369.5	371.0	372.5	371.0	371.7	371.7	372.5	371.0
50°	345.9	345.9	347.5	349.7	352.8	351.3	350.5	353.5	351.3	351.3	349.7
52.5°	323.2	325.5	326.2	328.5	330.8	331.5	332.3	330.8	331.5	329.3	330.0
55°	301.2	301.9	305.0	307.3	309.5	309.5	308.8	309.5	310.3	307.3	307.3
57.5°	279.2	281.5	284.5	284.5	287.5	287.5	286.8	286.8	287.5	285.3	284.5
60°	255.7	257.9	261.7	261.7	266.3	267.0	265.5	264.0	264.0	261.7	262.5
62.5°	230.6	232.9	235.2	239.0	242.0	240.5	243.5	240.5	241.3	236.7	236.7
65°	208.6	209.4	213.2	217.0	217.0	218.5	217.0	217.7	215.5	215.5	212.4
67.5°	182.8	182.8	186.6	190.4	194.2	194.2	194.2	191.9	191.9	189.7	189.7
70°	160.1	159.3	163.1	165.4	167.7	168.4	166.9	166.1	164.6	162.4	161.6
72.5°	132.0	133.5	137.3	138.8	142.6	141.9	145.7	141.1	141.1	137.3	136.6
75°	107.0	108.5	112.3	114.6	116.8	116.8	119.1	116.8	113.8	112.3	111.5
77.5°	85.0	84.2	87.2	91.0	91.8	91.0	92.6	91.8	88.8	88.8	87.2
80°	60.7	63.0	66.0	65.2	68.3	67.5	67.5	66.0	66.0	63.7	65.2
82.5°	40.2	42.5	43.2	42.5	43.2	44.8	45.5	44.8	44.8	43.2	44.0
85°	21.2	21.2	22.8	23.5	22.8	22.8	23.5	25.8	24.3	22.8	24.3
87.5°	6.8	6.1	6.1	6.8	6.1	6.1	6.8	6.8	7.6	7.6	7.6
90°	36.1	36.4	37.0	37.5	38.1	38.7	38.1	37.5	37.0	36.4	36.1
92.5°	58.1	57.8	57.2	56.7	56.1	55.5	56.1	56.7	57.2	57.8	58.1
95°	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6
97.5°	145.8	145.7	145.4	145.1	144.8	144.5	144.8	145.1	145.4	145.7	145.8
100°	193.5	193.8	194.4	194.9	195.5	196.1	195.5	194.9	194.4	193.8	193.5
102.5°	250.3	250.2	249.9	249.6	249.3	249.0	249.3	249.6	249.9	250.2	250.3
105°	304.5	304.8	305.3	305.9	306.4	307.0	306.4	305.9	305.3	304.8	304.5
107.5°	367.7	367.6	367.3	367.0	366.7	366.4	366.7	367.0	367.3	367.6	367.7
110°	429.6	429.3	428.7	428.2	427.6	427.0	427.6	428.2	428.7	429.3	429.6

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5
115°	550.9	550.8	550.5	550.2	549.9	549.6	549.9	550.2	550.5	550.8	550.9
117.5°	612.8	612.4	611.5	610.6	609.8	608.9	609.8	610.6	611.5	612.4	612.8
120°	674.7	674.4	673.8	673.3	672.7	672.1	672.7	673.3	673.8	674.4	674.7
122.5°	736.7	736.3	735.4	734.5	733.7	732.8	733.7	734.5	735.4	736.3	736.7
125°	798.6	798.0	796.9	795.7	794.6	793.4	794.6	795.7	796.9	798.0	798.6
127.5°	859.2	858.6	857.5	856.4	855.2	854.1	855.2	856.4	857.5	858.6	859.2
130°	922.4	921.4	919.4	917.4	915.4	913.4	915.4	917.4	919.4	921.4	922.4
132.5°	981.8	981.1	979.6	978.2	976.7	975.3	976.7	978.2	979.6	981.1	981.8
135°	1042.4	1042.1	1041.5	1041.0	1040.4	1039.8	1040.4	1041.0	1041.5	1042.1	1042.4
137.5°	1100.5	1100.1	1099.2	1098.3	1097.5	1096.6	1097.5	1098.3	1099.2	1100.1	1100.5
140°	1161.1	1160.1	1158.1	1156.1	1154.1	1152.1	1154.1	1156.1	1158.1	1160.1	1161.1
142.5°	1215.3	1214.6	1213.1	1211.7	1210.2	1208.8	1210.2	1211.7	1213.1	1214.6	1215.3
145°	1268.2	1267.6	1266.5	1265.3	1264.2	1263.0	1264.2	1265.3	1266.5	1267.6	1268.2
147.5°	1319.8	1318.9	1317.2	1315.5	1313.7	1312.0	1313.7	1315.5	1317.2	1318.9	1319.8
150°	1366.2	1365.3	1363.6	1361.9	1360.2	1358.5	1360.2	1361.9	1363.6	1365.3	1366.2
152.5°	1410.1	1409.4	1407.9	1406.5	1405.0	1403.6	1405.0	1406.5	1407.9	1409.4	1410.1
155°	1452.7	1451.7	1449.7	1447.6	1445.6	1443.6	1445.6	1447.6	1449.7	1451.7	1452.7
157.5°	1488.8	1487.9	1486.2	1484.5	1482.7	1481.0	1482.7	1484.5	1486.2	1487.9	1488.8
160°	1522.3	1521.7	1520.6	1519.5	1518.3	1517.2	1518.3	1519.5	1520.6	1521.7	1522.3
162.5°	1553.3	1552.3	1550.3	1548.3	1546.3	1544.3	1546.3	1548.3	1550.3	1552.3	1553.3
165°	1579.1	1578.1	1576.1	1574.1	1572.1	1570.1	1572.1	1574.1	1576.1	1578.1	1579.1
167.5°	1601.0	1600.1	1598.4	1596.7	1595.0	1593.3	1595.0	1596.7	1598.4	1600.1	1601.0
170°	1619.1	1618.1	1616.1	1614.1	1612.1	1610.1	1612.1	1614.1	1616.1	1618.1	1619.1
172.5°	1632.0	1631.0	1629.0	1627.0	1625.0	1623.0	1625.0	1627.0	1629.0	1631.0	1632.0
175°	1641.0	1640.0	1638.0	1636.0	1634.0	1632.0	1634.0	1636.0	1638.0	1640.0	1641.0
177.5°	1646.2	1645.2	1643.2	1641.1	1639.1	1637.1	1639.1	1641.1	1643.2	1645.2	1646.2
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	743.5	745.0	745.8	742.7	740.4	744.2	749.5	753.3	756.4	760.2	762.4
5°	699.5	704.8	704.8	706.3	708.6	712.4	722.2	729.1	735.1	739.7	743.5
7.5°	662.3	666.1	668.4	672.2	676.0	681.3	692.6	702.5	711.6	716.9	723.0
10°	628.9	632.0	635.7	638.0	644.9	652.4	666.9	675.2	685.8	694.2	701.8
12.5°	597.1	607.7	610.0	609.2	615.3	623.6	638.0	650.9	662.3	670.6	679.0
15°	574.3	578.1	582.6	581.9	594.8	597.1	609.2	624.4	639.5	644.9	652.4
17.5°	549.3	555.3	559.9	562.2	566.0	574.3	585.7	597.1	616.8	617.5	637.3
20°	529.5	535.6	538.6	541.7	544.0	553.8	563.7	576.6	592.5	600.9	611.5
22.5°	516.6	519.7	522.0	524.2	527.3	532.6	544.7	559.1	569.7	578.9	585.7
25°	501.5	504.5	507.5	509.1	511.3	514.4	523.5	534.8	550.0	556.1	562.9
27.5°	490.8	490.8	492.4	492.4	495.4	498.4	505.3	515.9	528.0	535.6	544.7
30°	479.5	478.7	479.5	478.7	477.9	482.5	488.6	497.7	506.0	515.1	521.2
32.5°	468.1	467.3	467.3	468.1	465.1	467.3	470.4	478.7	487.8	492.4	499.2
35°	455.9	454.4	454.4	454.4	452.9	451.4	454.4	462.0	468.1	474.2	479.5
37.5°	443.8	441.5	441.5	440.0	438.5	436.2	436.2	442.3	450.6	452.9	459.7
40°	427.1	427.1	425.6	424.8	423.3	421.8	419.5	424.8	432.4	434.7	440.0
42.5°	410.4	408.2	407.4	407.4	407.4	405.1	403.6	407.4	411.9	415.7	418.8
45°	391.5	389.9	390.7	389.9	388.4	387.7	386.9	388.4	393.7	395.3	399.1
47.5°	371.0	370.2	370.2	369.5	368.7	369.5	366.4	370.2	371.7	373.3	376.3
50°	349.7	349.0	348.2	347.5	347.5	348.2	347.5	347.5	350.5	352.0	355.0
52.5°	328.5	326.2	326.2	325.5	325.5	323.9	325.5	326.2	327.7	329.3	330.8
55°	305.7	305.7	303.5	303.5	301.9	301.9	302.7	301.9	305.0	306.5	306.5
57.5°	283.7	280.7	281.5	279.9	278.4	277.7	277.7	279.2	280.7	280.7	282.2
60°	260.2	257.2	256.4	253.4	254.9	252.6	253.4	253.4	256.4	254.9	256.4
62.5°	236.7	232.9	230.6	229.1	229.1	229.9	228.4	227.6	229.1	230.6	233.7
65°	211.7	209.4	207.1	204.8	204.8	204.1	205.6	203.3	202.6	203.3	204.8
67.5°	185.9	183.6	181.3	179.0	179.8	177.5	176.0	178.3	176.8	177.5	179.0
70°	160.8	159.3	154.8	153.2	152.5	153.2	152.5	151.0	153.2	152.5	153.2
72.5°	135.8	134.3	132.0	128.2	128.2	127.5	126.7	126.7	125.9	125.9	125.9
75°	111.5	108.5	106.2	105.5	103.9	103.2	102.4	100.9	101.7	102.4	100.9
77.5°	86.5	82.7	81.9	81.9	79.7	79.7	80.4	79.7	78.9	78.9	78.9
80°	63.7	60.7	60.7	59.2	57.7	57.7	57.7	57.7	56.9	56.1	56.9
82.5°	41.0	40.2	39.4	39.4	41.0	37.9	39.4	38.7	37.9	37.9	37.2
85°	22.8	23.5	22.8	23.5	22.0	22.8	22.8	22.8	22.0	22.8	21.2
87.5°	8.3	8.3	8.3	9.1	9.1	9.1	9.1	9.1	9.9	9.1	9.1
90°	35.5	34.4	33.3	32.1	31.0	27.3	23.5	19.8	16.1	14.2	12.8
92.5°	57.7	56.8	55.9	55.1	54.2	52.5	50.7	49.0	47.3	46.4	45.5
95°	100.0	98.9	97.8	96.6	95.5	93.2	90.9	88.6	86.3	85.1	84.1
97.5°	145.1	143.6	142.2	140.7	139.3	137.6	135.9	134.2	132.5	131.6	130.9
100°	193.1	192.2	191.3	190.5	189.6	188.2	186.8	185.3	183.9	183.2	182.3
102.5°	249.9	249.0	248.1	247.3	246.4	244.4	242.4	240.4	238.4	237.4	237.0
105°	304.5	304.5	304.5	304.5	304.5	301.9	299.3	296.8	294.2	292.9	292.6
107.5°	367.3	366.4	365.5	364.7	363.8	362.6	361.5	360.3	359.2	358.6	358.5
110°	429.0	427.9	426.7	425.6	424.4	423.8	423.3	422.7	422.2	421.9	421.6

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	490.8	489.4	487.9	486.5	485.1	485.1	485.1	485.1	485.1	485.1	485.0
115°	550.8	550.5	550.2	549.9	549.6	550.2	550.8	551.3	551.9	552.2	551.8
117.5°	612.8	612.8	612.8	612.8	612.8	613.4	614.0	614.5	615.1	615.4	615.3
120°	674.8	675.1	675.4	675.7	676.0	677.4	678.9	680.3	681.8	682.5	681.6
122.5°	737.1	738.0	738.8	739.7	740.5	741.1	741.7	742.2	742.8	743.1	742.5
125°	799.2	800.3	801.4	802.6	803.7	804.3	804.9	805.4	806.0	806.3	805.9
127.5°	860.1	861.8	863.5	865.3	867.0	867.6	868.1	868.7	869.2	869.5	868.6
130°	923.0	924.1	925.3	926.4	927.6	928.5	929.3	930.2	931.1	931.5	930.3
132.5°	982.5	983.9	985.4	986.8	988.2	988.8	989.4	989.9	990.5	990.8	989.7
135°	1043.0	1044.1	1045.3	1046.4	1047.6	1047.9	1048.2	1048.5	1048.8	1048.9	1048.0
137.5°	1101.2	1102.6	1104.1	1105.5	1106.9	1106.0	1105.2	1104.3	1103.4	1103.0	1102.3
140°	1161.2	1161.5	1161.8	1162.1	1162.4	1162.1	1161.8	1161.5	1161.2	1161.1	1160.4
142.5°	1215.4	1215.7	1216.0	1216.3	1216.6	1216.0	1215.4	1214.9	1214.3	1214.0	1213.3
145°	1268.3	1268.6	1268.9	1269.2	1269.5	1268.6	1267.8	1266.9	1266.0	1265.6	1265.3
147.5°	1319.8	1319.8	1319.8	1319.8	1319.8	1318.9	1318.1	1317.2	1316.3	1315.9	1315.3
150°	1366.2	1366.2	1366.2	1366.2	1366.2	1365.6	1365.0	1364.5	1363.9	1363.6	1363.3
152.5°	1409.8	1409.2	1408.7	1408.1	1407.5	1407.2	1406.9	1406.6	1406.3	1406.2	1405.8
155°	1452.1	1451.0	1449.8	1448.7	1447.5	1447.2	1446.9	1446.6	1446.3	1446.2	1446.2
157.5°	1488.2	1487.1	1485.9	1484.8	1483.6	1483.3	1483.0	1482.7	1482.4	1482.3	1482.4
160°	1521.6	1520.2	1518.7	1517.3	1515.9	1515.9	1515.9	1515.9	1515.9	1515.9	1516.2
162.5°	1552.6	1551.1	1549.7	1548.2	1546.8	1546.5	1546.2	1545.9	1545.6	1545.5	1545.9
165°	1578.2	1576.5	1574.8	1573.0	1571.3	1571.3	1571.3	1571.3	1571.3	1571.3	1571.7
167.5°	1600.1	1598.4	1596.7	1595.0	1593.3	1593.0	1592.7	1592.4	1592.1	1592.0	1592.6
170°	1618.1	1616.1	1614.1	1612.1	1610.1	1610.1	1610.1	1610.1	1610.1	1610.1	1610.7
172.5°	1631.1	1629.4	1627.7	1625.9	1624.2	1624.2	1624.2	1624.2	1624.2	1624.2	1624.8
175°	1640.1	1638.4	1636.7	1635.0	1633.3	1633.3	1633.3	1633.3	1633.3	1633.3	1633.9
177.5°	1645.3	1643.6	1641.9	1640.1	1638.4	1638.4	1638.4	1638.4	1638.4	1638.4	1639.0
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	782.9	782.9	782.9	782.9
2.5°	766.2	768.5	776.1	785.2
5°	751.1	757.1	767.8	782.2
7.5°	734.4	743.5	758.7	776.9
10°	715.4	728.3	747.3	770.0
12.5°	694.9	711.6	735.9	759.4
15°	682.0	698.7	720.7	746.5
17.5°	657.0	676.7	699.5	735.9
20°	631.2	653.2	682.8	719.2
22.5°	611.5	635.0	663.1	701.8
25°	588.0	612.2	642.6	682.8
27.5°	562.9	587.2	621.3	663.8
30°	544.0	567.5	600.1	645.6
32.5°	521.2	544.0	578.1	625.9
35°	495.4	521.2	553.8	602.4
37.5°	475.7	499.2	533.3	579.6
40°	454.4	474.9	508.3	553.8
42.5°	431.7	454.4	483.3	528.8
45°	410.4	427.1	456.7	500.0
47.5°	387.7	406.6	429.4	462.8
50°	363.4	379.3	404.4	427.1
52.5°	339.9	352.8	374.0	391.5
55°	314.8	327.7	343.7	354.3
57.5°	291.3	300.4	311.0	317.9
60°	262.5	271.6	278.4	285.3
62.5°	236.7	243.5	247.3	251.1
65°	210.1	213.9	216.2	219.2
67.5°	181.3	185.1	185.9	190.4
70°	154.8	155.5	157.0	159.3
72.5°	129.7	131.2	130.5	132.0
75°	103.9	105.5	103.9	105.5
77.5°	78.9	80.4	80.4	82.7
80°	56.9	57.7	58.4	58.4
82.5°	37.2	39.4	37.9	38.7
85°	21.2	22.0	22.0	22.8
87.5°	9.9	10.6	9.9	11.4
90°	9.9	7.0	4.2	1.3
92.5°	43.8	42.1	40.4	38.7
95°	82.1	80.1	78.1	76.1
97.5°	129.4	128.0	126.5	125.1
100°	180.6	178.9	177.2	175.5
102.5°	236.1	235.2	234.4	233.5
105°	292.0	291.5	290.9	290.3
107.5°	358.2	357.9	357.7	357.4
110°	421.0	420.5	419.9	419.3

TEST NUMBER: P1031742

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	484.7	484.4	484.1	483.8
115°	550.9	550.0	549.2	548.3
117.5°	615.0	614.7	614.4	614.1
120°	679.9	678.2	676.4	674.7
122.5°	741.4	740.2	739.1	737.9
125°	805.0	804.1	803.3	802.4
127.5°	866.9	865.2	863.5	861.8
130°	928.0	925.7	923.4	921.1
132.5°	987.4	985.1	982.8	980.5
135°	1046.3	1044.6	1042.8	1041.1
137.5°	1100.9	1099.4	1098.0	1096.6
140°	1158.9	1157.5	1156.0	1154.6
142.5°	1211.8	1210.4	1208.9	1207.5
145°	1264.7	1264.2	1263.6	1263.0
147.5°	1314.2	1313.0	1311.9	1310.7
150°	1362.8	1362.2	1361.7	1361.1
152.5°	1404.9	1404.0	1403.2	1402.3
155°	1446.2	1446.2	1446.2	1446.2
157.5°	1482.7	1483.0	1483.3	1483.6
160°	1516.8	1517.3	1517.9	1518.5
162.5°	1546.8	1547.7	1548.5	1549.4
165°	1572.6	1573.5	1574.3	1575.2
167.5°	1593.7	1594.9	1596.0	1597.2
170°	1611.8	1612.9	1614.1	1615.2
172.5°	1625.9	1627.1	1628.2	1629.4
175°	1635.0	1636.1	1637.3	1638.4
177.5°	1640.1	1641.3	1642.4	1643.6
180°	1642.3	1642.3	1642.3	1642.3

(END OF REPORT)