

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031828

Luminaire Tested: S123DIW-B560D755UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031828
REPORT IS A COMBINATION OF REPORTS P991821 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D755UB40-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5419.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	36
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8427	8427	8427	8427
5°	8433	9710	8457	7247
10°	8379	11751	8388	6328
15°	8263	13935	8331	5697
20°	8164	16043	8181	5241
25°	8016	16448	8034	5005
30°	7910	13589	7910	4849
35°	7780	9088	7730	4712
40°	7622	6560	7528	4502
45°	7426	5196	7210	4239
50°	6945	4413	6698	3984
55°	6420	3878	6159	3697
60°	5887	3376	5573	3395
65°	5299	2891	5043	2996
70°	4691	2400	4379	2525
75°	4013	1810	3751	1949
80°	3171	1208	2926	1280
85°	2190	554	1748	505

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13592 cd/sqm

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	1.4
10°-20°	247.3	4.6
20°-30°	416.1	7.7
30°-40°	470.3	8.7
40°-50°	421.2	7.8
50°-60°	340.0	6.3
60°-70°	236.9	4.4
70°-80°	124.3	2.3
80°-90°	31.8	0.6
90°-100°	35.3	0.7
100°-110°	170.8	3.2
110°-120°	418.5	7.7
120°-130°	531.3	9.8
130°-140°	567.6	10.5
140°-150°	530.8	9.8
150°-160°	428.1	7.9
160°-170°	276.3	5.1
170°-180°	95.2	1.8
0°-30°	740.4	13.7
0°-40°	1210.7	22.3
0°-60°	1971.9	36.4
0°-90°	2365.0	43.6
90°-120°	624.7	11.5
90°-150°	2254.4	41.6
90°-180°	3054.0	56.4
0°-180°	5419.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	783	783	783	783	783	
5°	782	930	784	694	782	74
15°	746	1384	753	566	746	211
25°	683	1643	684	500	683	315
35°	602	885	599	459	602	377
45°	500	478	486	390	500	382
55°	354	325	340	310	354	317
65°	219	211	209	218	219	218
75°	106	108	99	117	106	113
85°	23	25	18	23	23	26
90°	1	22	1	22	1	4
95°	45	28	45	28	45	54
105°	222	33	222	33	222	235
115°	416	438	416	438	416	411
125°	586	598	586	598	586	524
135°	730	738	730	738	730	562
145°	842	851	842	851	842	527
155°	928	927	928	927	928	428
165°	979	976	979	976	979	277
175°	1002	998	1002	998	1002	95
180°	1002	1002	1002	1002	1002	

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	785.2	791.3	794.3	798.9	803.4	810.2	812.5	816.3	814.8	817.8	819.3
5°	782.2	792.8	801.9	813.3	823.9	831.5	839.1	851.2	860.3	861.8	868.7
7.5°	776.9	792.0	808.0	823.9	844.4	856.5	870.2	886.9	900.5	922.5	930.9
10°	770.0	791.3	814.0	836.0	864.1	883.1	899.8	927.8	955.9	978.7	999.9
12.5°	759.4	786.0	815.5	848.2	884.6	906.6	929.3	966.5	1009.0	1043.9	1066.7
15°	746.5	779.9	817.8	852.7	892.9	933.9	958.2	999.9	1060.6	1093.2	1151.6
17.5°	735.9	770.0	808.0	862.6	917.2	958.2	975.6	1052.2	1094.0	1148.6	1214.6
20°	719.2	762.4	811.0	865.6	936.2	961.2	996.9	1074.2	1125.8	1197.2	1278.3
22.5°	701.8	748.0	806.4	863.3	942.2	968.8	1017.4	1078.8	1160.7	1231.3	1320.8
25°	682.8	732.9	792.0	859.6	936.9	975.6	1021.1	1097.0	1185.8	1274.5	1357.2
27.5°	663.8	718.4	779.9	847.4	922.5	968.0	1013.6	1092.5	1206.3	1302.6	1408.1
30°	645.6	700.2	761.7	830.7	909.6	953.6	996.9	1095.5	1222.2	1330.7	1436.9
32.5°	625.9	682.0	746.5	804.2	883.8	930.9	979.4	1095.5	1232.0	1347.4	1444.5
35°	602.4	660.0	715.4	773.1	852.0	904.3	958.9	1087.9	1241.2	1352.7	1412.6
37.5°	579.6	630.4	678.2	734.4	817.1	873.2	936.2	1078.8	1236.6	1329.9	1346.6
40°	553.8	604.6	643.3	695.7	782.9	848.2	911.9	1066.7	1216.9	1276.0	1227.5
42.5°	528.8	569.0	602.4	653.2	748.0	811.8	880.8	1044.7	1178.2	1190.3	1081.1
45°	500.0	528.8	558.4	616.0	710.1	775.3	852.0	1012.8	1116.0	1081.1	943.0
47.5°	462.8	488.6	521.2	574.3	669.9	737.4	810.2	971.8	1025.7	952.9	801.9
50°	427.1	449.1	479.5	531.1	627.4	693.4	770.8	907.3	933.9	819.3	691.1
52.5°	391.5	408.2	437.7	489.3	585.7	649.4	720.0	841.3	826.2	703.3	589.5
55°	354.3	368.7	396.8	447.6	537.1	597.8	665.3	760.2	720.7	603.9	512.8
57.5°	317.9	333.0	361.9	404.4	488.6	547.7	601.6	676.0	616.8	523.5	443.1
60°	285.3	298.1	320.2	361.9	438.5	486.3	535.6	586.4	537.1	446.8	385.4
62.5°	251.1	263.3	283.7	321.7	387.7	430.2	469.6	511.3	456.7	390.7	336.1
65°	219.2	229.1	248.1	283.0	336.8	371.7	403.6	432.4	388.4	327.7	286.8
67.5°	190.4	198.8	214.7	245.8	291.3	316.4	342.2	366.4	329.3	280.7	245.8
70°	159.3	166.1	180.6	203.3	239.7	265.5	284.5	302.7	269.3	230.6	207.1
72.5°	132.0	138.8	147.9	171.5	196.5	212.4	232.9	242.8	223.8	191.9	168.4
75°	105.5	110.8	119.1	134.3	157.8	168.4	181.3	188.9	171.5	150.2	135.8
77.5°	82.7	85.0	91.0	101.7	117.6	129.7	139.6	144.1	132.0	118.3	106.2
80°	58.4	61.5	66.0	75.1	87.2	91.0	97.1	102.4	94.8	82.7	75.1
82.5°	38.7	42.5	44.8	48.6	56.1	60.7	62.2	66.8	59.9	55.4	52.3
85°	22.8	24.3	25.0	27.3	31.1	33.4	35.7	36.4	34.9	34.1	31.1
87.5°	11.4	11.4	11.4	12.9	13.7	15.2	15.9	15.9	15.9	15.2	14.4
90°	0.7	2.4	4.0	5.7	7.4	8.2	9.3	11.4	13.6	15.7	17.9
92.5°	17.1	16.1	15.1	14.2	13.2	12.7	13.4	14.9	16.4	17.9	19.4
95°	45.4	38.6	31.8	25.1	18.3	14.9	15.8	17.6	19.5	21.3	23.1
97.5°	82.6	78.0	73.4	68.7	64.1	61.8	57.6	49.1	40.7	32.2	23.8
100°	125.8	129.1	132.4	135.7	139.0	140.7	127.8	102.0	76.2	50.4	24.6
102.5°	174.9	177.1	179.2	181.4	183.5	184.6	170.2	141.4	112.7	83.9	55.1
105°	221.8	223.6	225.4	227.3	229.1	230.0	222.6	207.7	192.8	177.9	163.0
107.5°	271.7	273.2	274.7	276.2	277.7	278.4	279.6	282.1	284.6	287.0	289.5
110°	321.5	322.8	324.2	325.5	326.8	327.5	328.4	330.2	332.1	333.9	335.7

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	369.2	370.4	371.5	372.7	373.8	374.4	375.3	377.1	379.0	380.8	382.6
115°	416.0	417.0	418.0	419.0	420.0	420.5	421.2	422.7	424.2	425.7	427.2
117.5°	462.2	463.4	464.5	465.7	466.8	467.4	467.8	468.6	469.5	470.3	471.1
120°	504.6	506.1	507.6	509.1	510.6	511.3	511.5	512.0	512.5	513.0	513.5
122.5°	547.8	549.0	550.1	551.3	552.4	553.0	553.3	554.0	554.7	555.3	556.0
125°	586.5	587.8	589.1	590.4	591.7	592.4	592.7	593.4	594.1	594.7	595.4
127.5°	625.2	626.5	627.8	629.1	630.4	631.1	631.5	632.4	633.2	634.1	634.9
130°	660.9	662.2	663.6	664.9	666.2	666.9	667.2	667.9	668.5	669.2	669.8
132.5°	695.1	696.4	697.8	699.1	700.4	701.1	701.3	701.8	702.3	702.8	703.3
135°	730.1	731.1	732.1	733.1	734.1	734.6	734.9	735.6	736.3	736.9	737.6
137.5°	759.9	761.2	762.5	763.8	765.1	765.8	766.0	766.3	766.6	767.0	767.3
140°	789.7	790.7	791.7	792.6	793.6	794.1	794.4	794.9	795.4	795.9	796.4
142.5°	817.2	818.2	819.2	820.2	821.2	821.7	821.9	822.4	822.9	823.4	823.9
145°	842.5	843.7	844.8	846.0	847.1	847.7	847.9	848.2	848.5	848.9	849.2
147.5°	867.1	867.9	868.7	869.6	870.4	870.8	871.0	871.3	871.6	872.0	872.3
150°	889.4	889.9	890.4	890.9	891.4	891.6	891.8	892.1	892.4	892.8	893.1
152.5°	909.5	909.7	909.8	910.0	910.1	910.2	910.3	910.5	910.6	910.8	911.0
155°	928.1	927.8	927.4	927.1	926.8	926.6	926.7	926.8	927.0	927.1	927.3
157.5°	943.0	943.0	943.0	943.0	943.0	943.0	942.9	942.7	942.6	942.4	942.2
160°	956.4	956.2	956.0	955.9	955.7	955.6	955.5	955.4	955.2	955.1	954.9
162.5°	969.0	968.5	968.0	967.5	967.0	966.8	966.7	966.6	966.4	966.3	966.1
165°	978.7	978.2	977.7	977.2	976.7	976.5	976.4	976.2	976.1	975.9	975.7
167.5°	986.9	986.2	985.6	984.9	984.2	983.9	983.9	983.9	983.9	983.9	983.9
170°	993.6	992.9	992.3	991.6	990.9	990.6	990.6	990.6	990.6	990.6	990.6
172.5°	998.1	997.3	996.4	995.6	994.7	994.3	994.4	994.6	994.7	994.9	995.1
175°	1001.8	1001.0	1000.2	999.3	998.5	998.1	998.2	998.3	998.5	998.6	998.8
177.5°	1003.3	1002.5	1001.6	1000.8	999.9	999.5	999.6	999.8	999.9	1000.1	1000.3
180°	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	824.7	826.2	831.5	835.3	842.9	842.1	842.1	841.3	839.1	842.9	845.1
5°	882.3	895.2	896.7	913.4	914.2	921.0	925.6	921.8	930.9	930.1	923.3
7.5°	953.6	971.1	979.4	995.3	1013.6	1009.0	1026.5	1029.5	1028.0	1035.6	1040.9
10°	1031.8	1062.1	1083.4	1112.9	1120.5	1125.1	1136.5	1146.3	1166.0	1150.9	1160.7
12.5°	1121.3	1143.3	1171.4	1218.4	1241.9	1257.1	1262.4	1269.2	1282.9	1274.5	1275.3
15°	1196.4	1226.0	1273.8	1332.2	1339.0	1358.0	1353.4	1394.4	1414.1	1384.5	1401.2
17.5°	1274.5	1314.0	1370.9	1421.7	1450.5	1463.4	1475.6	1515.0	1513.5	1509.0	1512.7
20°	1324.6	1389.1	1459.6	1527.2	1535.5	1545.4	1578.0	1594.7	1591.6	1604.5	1612.9
22.5°	1395.2	1463.4	1538.5	1583.3	1602.3	1613.6	1639.4	1650.1	1654.6	1657.7	1652.3
25°	1454.3	1527.2	1582.5	1622.0	1633.4	1639.4	1647.8	1650.8	1648.5	1643.2	1647.8
27.5°	1494.5	1553.0	1590.9	1609.1	1603.0	1593.2	1577.2	1566.6	1543.1	1531.7	1545.4
30°	1511.2	1537.0	1548.4	1518.1	1487.7	1463.4	1433.1	1377.0	1332.9	1345.8	1328.4
32.5°	1484.7	1468.0	1413.4	1335.2	1311.7	1272.3	1186.5	1120.5	1122.8	1087.9	1102.3
35°	1406.5	1330.7	1227.5	1109.1	1078.0	1056.8	962.7	948.3	918.0	885.3	894.4
37.5°	1268.5	1157.7	1032.5	945.3	899.0	852.7	799.6	767.8	749.5	735.9	746.5
40°	1100.0	965.0	861.8	783.7	744.2	714.6	678.2	646.4	625.9	623.6	627.4
42.5°	934.7	820.9	726.0	651.7	638.8	603.9	580.4	555.3	549.3	539.4	544.7
45°	791.3	698.7	620.6	559.9	544.7	535.6	506.8	490.8	484.0	477.9	487.1
47.5°	687.3	590.2	533.3	496.9	481.7	466.6	450.6	440.0	434.7	435.5	434.7
50°	587.2	515.9	465.8	437.7	428.6	418.0	405.1	398.3	396.0	389.2	394.5
52.5°	505.3	453.7	418.8	392.2	385.4	377.8	367.2	363.4	358.1	356.6	356.6
55°	439.3	399.1	371.0	353.5	345.2	339.1	333.0	328.5	324.7	324.7	324.7
57.5°	387.7	352.8	332.3	317.1	314.1	308.0	301.2	301.2	295.9	295.1	297.4
60°	343.7	312.6	296.6	283.7	279.2	277.7	270.8	270.8	269.3	265.5	268.6
62.5°	298.9	276.1	262.5	252.6	248.1	248.1	242.8	239.0	239.0	239.7	238.2
65°	257.9	241.3	229.1	221.5	219.2	216.2	215.5	212.4	210.1	210.9	210.1
67.5°	221.5	208.6	200.3	194.2	190.4	188.9	186.6	186.6	185.1	185.9	182.1
70°	188.9	176.0	169.2	163.1	161.6	161.6	158.6	159.3	157.8	160.1	158.6
72.5°	155.5	145.7	140.4	138.1	136.6	135.8	134.3	132.8	132.0	133.5	132.8
75°	125.9	117.6	113.8	112.3	110.8	110.8	110.0	109.2	108.5	108.5	108.5
77.5°	97.9	92.6	88.0	89.5	87.2	88.0	85.7	85.7	86.5	85.7	85.7
80°	72.1	68.3	68.3	66.8	63.7	65.2	65.2	63.0	62.2	63.7	61.5
82.5°	47.8	47.0	45.5	44.8	43.2	44.0	43.2	42.5	41.7	43.2	41.7
85°	28.1	28.1	27.3	25.8	27.3	26.6	25.8	25.8	25.0	25.0	25.0
87.5°	14.4	12.9	12.9	12.1	12.9	11.4	12.1	11.4	10.6	11.4	10.6
90°	18.5	19.2	19.8	20.5	20.8	21.0	21.3	21.6	22.0	22.3	22.0
92.5°	20.6	21.7	22.9	24.0	24.6	24.7	24.8	25.0	25.1	25.3	25.1
95°	24.3	25.4	26.6	27.7	28.3	28.3	28.3	28.3	28.3	28.3	28.3
97.5°	25.1	26.5	27.8	29.1	29.8	29.9	30.0	30.2	30.3	30.5	30.3
100°	25.9	27.2	28.5	29.8	30.5	30.6	30.8	30.9	31.1	31.3	31.1
102.5°	49.6	44.2	38.7	33.2	30.5	30.7	31.0	31.3	31.7	32.0	31.7
105°	133.7	104.5	75.2	45.9	31.3	31.5	31.8	32.1	32.4	32.7	32.4
107.5°	264.0	238.6	213.1	187.6	174.9	164.1	142.4	120.7	99.1	77.4	99.1
110°	330.2	324.8	319.3	313.8	311.1	299.3	275.6	252.0	228.3	204.7	228.3

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	384.1	385.5	387.0	388.5	389.2	389.0	388.7	388.4	388.1	387.8	388.1
115°	428.8	430.5	432.1	433.8	434.6	434.9	435.6	436.3	436.9	437.6	436.9
117.5°	472.4	473.8	475.1	476.4	477.1	477.2	477.3	477.5	477.6	477.8	477.6
120°	514.8	516.2	517.5	518.8	519.5	519.5	519.5	519.5	519.5	519.5	519.5
122.5°	556.8	557.6	558.5	559.3	559.7	559.8	559.9	560.1	560.2	560.4	560.2
125°	595.7	596.1	596.4	596.7	596.9	597.1	597.4	597.7	598.1	598.4	598.1
127.5°	635.4	635.9	636.4	636.9	637.1	636.9	636.6	636.3	635.9	635.6	635.9
130°	670.5	671.1	671.8	672.5	672.8	672.6	672.3	672.0	671.6	671.3	671.6
132.5°	704.0	704.6	705.3	706.0	706.3	706.1	705.6	705.1	704.6	704.1	704.6
135°	738.1	738.6	739.1	739.6	739.8	739.6	739.1	738.6	738.1	737.6	738.1
137.5°	768.1	769.0	769.8	770.7	771.1	770.9	770.6	770.3	769.9	769.6	769.9
140°	797.0	797.7	798.3	799.0	799.3	799.1	798.8	798.5	798.1	797.8	798.1
142.5°	824.4	824.9	825.4	825.9	826.1	825.9	825.4	824.9	824.4	823.9	824.4
145°	849.5	849.9	850.2	850.5	850.7	850.7	850.7	850.7	850.7	850.7	850.7
147.5°	872.6	873.0	873.3	873.6	873.8	873.4	872.5	871.7	870.8	870.0	870.8
150°	893.4	893.8	894.1	894.4	894.6	894.4	893.9	893.4	892.9	892.4	892.9
152.5°	911.7	912.3	913.0	913.7	914.0	913.6	912.7	911.9	911.0	910.2	911.0
155°	928.1	929.0	929.8	930.7	931.1	930.6	929.6	928.6	927.6	926.6	927.6
157.5°	943.2	944.2	945.2	946.2	946.7	946.0	944.7	943.4	942.0	940.7	942.0
160°	955.9	956.9	957.9	958.9	959.4	958.8	957.6	956.5	955.3	954.1	955.3
162.5°	967.3	968.4	969.6	970.7	971.3	970.8	969.8	968.8	967.8	966.8	967.8
165°	977.0	978.4	979.7	981.0	981.7	981.1	980.0	978.8	977.7	976.5	977.7
167.5°	985.2	986.6	987.9	989.2	989.9	989.2	987.9	986.6	985.2	983.9	985.2
170°	991.9	993.3	994.6	995.9	996.6	995.9	994.6	993.3	991.9	990.6	991.9
172.5°	996.4	997.7	999.0	1000.3	1001.0	1000.3	998.8	997.3	995.8	994.3	995.8
175°	1000.0	1001.1	1002.3	1003.4	1004.0	1003.3	1002.0	1000.7	999.4	998.1	999.4
177.5°	1001.6	1002.9	1004.2	1005.5	1006.2	1005.4	1003.7	1002.1	1000.4	998.8	1000.4
180°	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	839.1	841.3	835.3	833.8	833.8	836.8	834.5	814.0	817.8	813.3	811.8
5°	931.6	927.1	921.0	918.0	914.2	903.6	902.8	879.3	874.7	859.6	852.7
7.5°	1033.3	1029.5	1011.3	1009.0	1007.5	997.6	972.6	947.6	929.3	911.9	895.2
10°	1149.4	1138.0	1129.6	1112.9	1104.6	1090.9	1058.3	1034.8	1003.7	977.1	942.2
12.5°	1288.9	1276.0	1248.0	1235.8	1225.2	1187.3	1154.7	1128.1	1067.4	1049.2	1006.0
15°	1391.4	1364.1	1361.0	1334.5	1332.9	1291.2	1229.0	1200.2	1153.1	1086.4	1041.6
17.5°	1502.1	1477.9	1458.9	1427.0	1422.5	1383.0	1337.5	1266.9	1215.4	1151.6	1094.7
20°	1583.3	1570.4	1537.8	1524.9	1498.3	1465.0	1417.9	1330.7	1267.7	1204.0	1134.2
22.5°	1647.8	1634.9	1609.1	1591.6	1576.5	1533.2	1477.1	1402.7	1316.3	1232.8	1160.7
25°	1647.0	1643.2	1632.6	1624.3	1612.9	1581.0	1534.0	1462.7	1366.3	1274.5	1174.4
27.5°	1553.7	1564.3	1582.5	1591.6	1589.4	1584.8	1558.3	1498.3	1411.8	1302.6	1190.3
30°	1359.5	1398.2	1432.3	1477.9	1491.5	1524.9	1540.1	1505.9	1436.9	1335.2	1210.8
32.5°	1127.4	1183.5	1257.8	1282.9	1326.1	1390.6	1462.7	1475.6	1432.3	1354.2	1223.7
35°	924.8	971.1	1028.7	1068.2	1106.9	1211.6	1302.6	1381.5	1395.9	1344.3	1220.7
37.5°	765.5	798.1	848.9	882.3	918.0	1007.5	1134.9	1237.4	1309.4	1310.9	1212.3
40°	650.2	664.6	708.6	732.9	767.0	844.4	958.2	1091.7	1197.2	1245.7	1190.3
42.5°	550.8	569.7	606.2	624.4	646.4	713.9	789.0	915.7	1046.2	1150.1	1149.4
45°	491.6	505.3	522.0	537.1	562.2	602.4	688.1	782.9	908.1	1025.7	1072.0
47.5°	439.3	452.2	468.8	473.4	490.1	528.0	580.4	663.1	779.9	896.7	984.0
50°	395.3	405.9	417.3	425.6	433.2	464.3	503.7	573.5	666.9	779.9	888.4
52.5°	361.1	368.7	378.6	383.1	389.9	412.7	443.1	494.6	571.3	674.4	779.9
55°	329.3	334.6	340.6	348.2	351.3	367.9	391.5	435.5	492.4	584.9	685.1
57.5°	299.7	301.9	305.7	310.3	314.1	328.5	349.0	378.6	428.6	500.0	594.8
60°	266.3	272.4	274.6	279.2	281.5	292.8	308.8	333.8	372.5	433.9	505.3
62.5°	238.2	242.0	245.8	248.1	253.4	257.2	270.1	292.8	324.7	370.2	434.7
65°	213.2	214.7	217.0	219.2	220.8	225.3	237.5	252.6	276.9	317.1	367.2
67.5°	184.4	185.9	188.9	189.7	191.2	197.2	204.1	217.0	237.5	267.8	308.8
70°	156.3	158.6	160.1	161.6	163.9	166.1	173.7	184.4	200.3	221.5	253.4
72.5°	132.0	134.3	134.3	135.8	135.0	138.1	145.7	153.2	163.9	181.3	209.4
75°	107.7	107.7	109.2	110.0	110.8	113.8	116.8	122.9	131.2	144.9	162.4
77.5°	85.0	84.2	85.7	85.7	85.7	88.0	91.0	94.1	99.4	109.2	122.9
80°	62.2	62.2	63.7	64.5	63.0	63.7	65.2	68.3	72.1	78.9	86.5
82.5°	41.0	44.0	43.2	44.0	43.2	44.8	45.5	46.3	47.8	50.8	56.1
85°	25.0	25.0	25.0	25.8	25.0	25.8	25.8	25.8	26.6	28.1	30.3
87.5°	10.6	10.6	10.6	11.4	10.6	10.6	11.4	10.6	11.4	11.4	12.1
90°	21.6	21.3	21.0	20.8	20.5	19.8	19.2	18.5	17.9	15.7	13.6
92.5°	25.0	24.8	24.7	24.6	24.0	22.9	21.7	20.6	19.4	17.9	16.4
95°	28.3	28.3	28.3	28.3	27.7	26.6	25.4	24.3	23.1	21.3	19.5
97.5°	30.2	30.0	29.9	29.8	29.1	27.8	26.5	25.1	23.8	32.2	40.7
100°	30.9	30.8	30.6	30.5	29.8	28.5	27.2	25.9	24.6	50.4	76.2
102.5°	31.3	31.0	30.7	30.5	33.2	38.7	44.2	49.6	55.1	83.9	112.7
105°	32.1	31.8	31.5	31.3	45.9	75.2	104.5	133.7	163.0	177.9	192.8
107.5°	120.7	142.4	164.1	174.9	187.6	213.1	238.6	264.0	289.5	287.0	284.6
110°	252.0	275.6	299.3	311.1	313.8	319.3	324.8	330.2	335.7	333.9	332.1

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	388.4	388.7	389.0	389.2	388.5	387.0	385.5	384.1	382.6	380.8	379.0
115°	436.3	435.6	434.9	434.6	433.8	432.1	430.5	428.8	427.2	425.7	424.2
117.5°	477.5	477.3	477.2	477.1	476.4	475.1	473.8	472.4	471.1	470.3	469.5
120°	519.5	519.5	519.5	519.5	518.8	517.5	516.2	514.8	513.5	513.0	512.5
122.5°	560.1	559.9	559.8	559.7	559.3	558.5	557.6	556.8	556.0	555.3	554.7
125°	597.7	597.4	597.1	596.9	596.7	596.4	596.1	595.7	595.4	594.7	594.1
127.5°	636.3	636.6	636.9	637.1	636.9	636.4	635.9	635.4	634.9	634.1	633.2
130°	672.0	672.3	672.6	672.8	672.5	671.8	671.1	670.5	669.8	669.2	668.5
132.5°	705.1	705.6	706.1	706.3	706.0	705.3	704.6	704.0	703.3	702.8	702.3
135°	738.6	739.1	739.6	739.8	739.6	739.1	738.6	738.1	737.6	736.9	736.3
137.5°	770.3	770.6	770.9	771.1	770.7	769.8	769.0	768.1	767.3	767.0	766.6
140°	798.5	798.8	799.1	799.3	799.0	798.3	797.7	797.0	796.4	795.9	795.4
142.5°	824.9	825.4	825.9	826.1	825.9	825.4	824.9	824.4	823.9	823.4	822.9
145°	850.7	850.7	850.7	850.7	850.5	850.2	849.9	849.5	849.2	848.9	848.5
147.5°	871.7	872.5	873.4	873.8	873.6	873.3	873.0	872.6	872.3	872.0	871.6
150°	893.4	893.9	894.4	894.6	894.4	894.1	893.8	893.4	893.1	892.8	892.4
152.5°	911.9	912.7	913.6	914.0	913.7	913.0	912.3	911.7	911.0	910.8	910.6
155°	928.6	929.6	930.6	931.1	930.7	929.8	929.0	928.1	927.3	927.1	927.0
157.5°	943.4	944.7	946.0	946.7	946.2	945.2	944.2	943.2	942.2	942.4	942.6
160°	956.5	957.6	958.8	959.4	958.9	957.9	956.9	955.9	954.9	955.1	955.2
162.5°	968.8	969.8	970.8	971.3	970.7	969.6	968.4	967.3	966.1	966.3	966.4
165°	978.8	980.0	981.1	981.7	981.0	979.7	978.4	977.0	975.7	975.9	976.1
167.5°	986.6	987.9	989.2	989.9	989.2	987.9	986.6	985.2	983.9	983.9	983.9
170°	993.3	994.6	995.9	996.6	995.9	994.6	993.3	991.9	990.6	990.6	990.6
172.5°	997.3	998.8	1000.3	1001.0	1000.3	999.0	997.7	996.4	995.1	994.9	994.7
175°	1000.7	1002.0	1003.3	1004.0	1003.4	1002.3	1001.1	1000.0	998.8	998.6	998.5
177.5°	1002.1	1003.7	1005.4	1006.2	1005.5	1004.2	1002.9	1001.6	1000.3	1000.1	999.9
180°	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	804.2	801.9	801.9	800.4	795.8	787.5	786.7	788.2	783.7	779.1	772.3
5°	843.6	829.2	824.7	820.1	811.0	795.8	789.8	784.4	776.1	766.2	755.6
7.5°	877.0	856.5	850.4	842.1	823.9	802.7	789.0	777.6	766.2	752.6	739.7
10°	918.7	889.1	874.7	862.6	837.6	808.0	787.5	770.8	752.6	735.9	719.2
12.5°	965.8	918.0	913.4	883.8	855.0	811.0	786.0	761.7	737.4	716.9	699.5
15°	1005.2	952.9	933.9	914.2	858.8	804.2	779.9	752.6	724.5	702.5	676.7
17.5°	1030.2	987.0	946.8	920.2	862.6	814.0	767.0	735.9	706.3	676.0	654.7
20°	1060.6	997.6	962.7	927.1	870.2	806.4	759.4	720.7	684.3	657.0	631.2
22.5°	1090.9	1006.0	977.1	938.5	871.7	798.9	745.8	707.1	665.3	638.0	610.0
25°	1087.9	1018.1	970.3	937.7	856.5	792.0	729.8	684.3	645.6	610.7	582.6
27.5°	1090.2	1004.5	955.9	918.0	845.9	782.2	713.1	665.3	625.1	588.7	559.1
30°	1090.9	984.0	941.5	896.0	826.2	758.7	694.2	645.6	603.1	563.7	537.1
32.5°	1088.7	967.3	914.2	873.2	795.1	735.9	672.2	620.6	577.3	540.9	515.9
35°	1083.4	947.6	886.1	834.5	763.2	703.3	651.7	598.6	552.3	518.9	490.1
37.5°	1068.9	926.3	856.5	805.7	726.0	665.3	619.8	575.8	531.1	491.6	467.3
40°	1058.3	897.5	826.9	771.5	685.8	626.6	588.7	547.0	503.0	467.3	443.8
42.5°	1034.0	870.2	796.6	730.6	646.4	585.7	550.0	516.6	478.7	443.8	422.6
45°	994.6	840.6	759.4	692.6	603.1	545.5	512.8	485.5	452.2	418.8	397.5
47.5°	939.2	798.1	720.0	653.2	560.6	502.2	469.6	449.1	422.6	394.5	376.3
50°	879.3	751.8	679.8	613.7	519.7	462.8	430.9	411.9	394.5	368.7	351.3
52.5°	801.1	702.5	633.5	570.5	475.7	421.1	393.0	379.3	361.1	342.9	327.7
55°	725.3	638.8	581.9	522.0	432.4	381.6	354.3	339.9	329.3	314.1	301.9
57.5°	637.3	579.6	527.3	472.6	392.2	345.9	320.2	302.7	295.9	289.0	277.7
60°	556.1	512.1	469.6	424.1	350.5	308.8	283.7	270.1	263.3	258.7	251.1
62.5°	481.7	447.6	411.2	374.8	308.0	270.1	251.1	237.5	231.4	230.6	223.8
65°	410.4	386.2	356.6	320.9	268.6	235.2	217.0	208.6	201.8	201.8	196.5
67.5°	339.1	322.4	298.9	273.9	232.9	201.8	185.1	177.5	173.7	173.7	169.9
70°	282.2	270.8	249.6	227.6	191.9	168.4	155.5	148.7	146.4	147.2	144.1
72.5°	229.1	217.0	199.5	183.6	157.0	139.6	130.5	122.9	119.1	119.9	119.1
75°	177.5	171.5	156.3	144.1	122.9	110.8	102.4	98.6	95.6	96.3	94.8
77.5°	133.5	124.4	116.1	107.7	94.8	85.0	78.1	74.3	72.1	72.1	72.1
80°	91.0	89.5	82.7	78.1	67.5	59.9	54.6	53.9	51.6	51.6	51.6
82.5°	59.2	55.4	51.6	48.6	42.5	37.9	35.7	34.1	33.4	32.6	34.1
85°	32.6	30.3	28.8	25.8	23.5	21.2	19.0	18.2	17.4	18.2	17.4
87.5°	12.9	10.6	10.6	9.9	9.1	8.3	8.3	6.8	6.8	6.1	6.1
90°	11.4	9.3	8.2	7.4	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	14.9	13.4	12.7	13.2	14.2	15.1	16.1	17.1	16.1	15.1	14.2
95°	17.6	15.8	14.9	18.3	25.1	31.8	38.6	45.4	38.6	31.8	25.1
97.5°	49.1	57.6	61.8	64.1	68.7	73.4	78.0	82.6	78.0	73.4	68.7
100°	102.0	127.8	140.7	139.0	135.7	132.4	129.1	125.8	129.1	132.4	135.7
102.5°	141.4	170.2	184.6	183.5	181.4	179.2	177.1	174.9	177.1	179.2	181.4
105°	207.7	222.6	230.0	229.1	227.3	225.4	223.6	221.8	223.6	225.4	227.3
107.5°	282.1	279.6	278.4	277.7	276.2	274.7	273.2	271.7	273.2	274.7	276.2
110°	330.2	328.4	327.5	326.8	325.5	324.2	322.8	321.5	322.8	324.2	325.5

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	377.1	375.3	374.4	373.8	372.7	371.5	370.4	369.2	370.4	371.5	372.7
115°	422.7	421.2	420.5	420.0	419.0	418.0	417.0	416.0	417.0	418.0	419.0
117.5°	468.6	467.8	467.4	466.8	465.7	464.5	463.4	462.2	463.4	464.5	465.7
120°	512.0	511.5	511.3	510.6	509.1	507.6	506.1	504.6	506.1	507.6	509.1
122.5°	554.0	553.3	553.0	552.4	551.3	550.1	549.0	547.8	549.0	550.1	551.3
125°	593.4	592.7	592.4	591.7	590.4	589.1	587.8	586.5	587.8	589.1	590.4
127.5°	632.4	631.5	631.1	630.4	629.1	627.8	626.5	625.2	626.5	627.8	629.1
130°	667.9	667.2	666.9	666.2	664.9	663.6	662.2	660.9	662.2	663.6	664.9
132.5°	701.8	701.3	701.1	700.4	699.1	697.8	696.4	695.1	696.4	697.8	699.1
135°	735.6	734.9	734.6	734.1	733.1	732.1	731.1	730.1	731.1	732.1	733.1
137.5°	766.3	766.0	765.8	765.1	763.8	762.5	761.2	759.9	761.2	762.5	763.8
140°	794.9	794.4	794.1	793.6	792.6	791.7	790.7	789.7	790.7	791.7	792.6
142.5°	822.4	821.9	821.7	821.2	820.2	819.2	818.2	817.2	818.2	819.2	820.2
145°	848.2	847.9	847.7	847.1	846.0	844.8	843.7	842.5	843.7	844.8	846.0
147.5°	871.3	871.0	870.8	870.4	869.6	868.7	867.9	867.1	867.9	868.7	869.6
150°	892.1	891.8	891.6	891.4	890.9	890.4	889.9	889.4	889.9	890.4	890.9
152.5°	910.5	910.3	910.2	910.1	910.0	909.8	909.7	909.5	909.7	909.8	910.0
155°	926.8	926.7	926.6	926.8	927.1	927.4	927.8	928.1	927.8	927.4	927.1
157.5°	942.7	942.9	943.0	943.0	943.0	943.0	943.0	943.0	943.0	943.0	943.0
160°	955.4	955.5	955.6	955.7	955.9	956.0	956.2	956.4	956.2	956.0	955.9
162.5°	966.6	966.7	966.8	967.0	967.5	968.0	968.5	969.0	968.5	968.0	967.5
165°	976.2	976.4	976.5	976.7	977.2	977.7	978.2	978.7	978.2	977.7	977.2
167.5°	983.9	983.9	983.9	984.2	984.9	985.6	986.2	986.9	986.2	985.6	984.9
170°	990.6	990.6	990.6	990.9	991.6	992.3	992.9	993.6	992.9	992.3	991.6
172.5°	994.6	994.4	994.3	994.7	995.6	996.4	997.3	998.1	997.3	996.4	995.6
175°	998.3	998.2	998.1	998.5	999.3	1000.2	1001.0	1001.8	1001.0	1000.2	999.3
177.5°	999.8	999.6	999.5	999.9	1000.8	1001.6	1002.5	1003.3	1002.5	1001.6	1000.8
180°	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	770.8	770.0	771.5	767.0	759.4	755.6	745.0	742.7	742.0	742.7	743.5
5°	749.5	748.8	746.5	738.9	729.8	723.0	710.1	709.3	704.8	700.2	702.5
7.5°	729.1	726.0	721.5	711.6	699.5	691.9	681.3	673.7	667.6	663.8	660.8
10°	708.6	704.0	699.5	686.6	671.4	660.0	647.1	641.1	634.2	631.2	628.2
12.5°	682.0	677.5	669.1	654.0	644.9	630.4	617.5	611.5	607.7	601.6	597.8
15°	660.8	651.7	647.1	631.2	612.2	610.7	587.2	585.7	578.1	578.1	572.0
17.5°	636.5	629.7	621.3	605.4	591.7	578.1	566.0	561.4	554.6	553.1	550.0
20°	613.0	603.9	600.9	584.9	570.5	553.8	540.9	536.4	533.3	530.3	532.6
22.5°	588.7	581.1	573.5	559.1	548.5	531.8	524.2	519.7	515.1	513.6	514.4
25°	565.2	558.4	550.8	536.4	525.0	511.3	504.5	502.2	500.0	500.0	499.2
27.5°	542.4	535.6	528.8	515.9	504.5	494.6	489.3	487.1	484.8	486.3	487.8
30°	518.9	512.8	506.8	495.4	486.3	477.2	474.2	472.6	471.9	475.7	475.7
32.5°	497.7	492.4	487.8	477.2	468.1	460.5	458.2	459.0	459.7	462.0	463.5
35°	475.7	471.9	467.3	458.2	450.6	443.8	444.6	444.6	446.1	449.9	452.9
37.5°	455.9	450.6	446.8	439.3	433.2	427.1	429.4	431.7	433.2	437.7	439.3
40°	432.4	430.2	427.1	419.5	414.2	413.5	414.2	415.7	418.8	421.1	423.3
42.5°	413.5	410.4	406.6	400.6	396.0	396.8	397.5	399.1	400.6	404.4	406.6
45°	392.2	389.9	386.9	381.6	377.8	378.6	379.3	379.3	380.8	385.4	386.9
47.5°	368.7	369.5	365.7	360.4	358.1	358.1	358.1	359.6	363.4	364.9	365.7
50°	345.9	344.4	343.7	338.4	336.8	336.1	336.8	337.6	342.9	342.2	344.4
52.5°	321.7	321.7	320.9	317.9	315.6	315.6	314.1	317.9	319.4	320.9	323.2
55°	298.1	295.9	295.1	293.6	290.6	289.8	291.3	295.9	297.4	298.9	301.2
57.5°	272.4	272.4	270.8	268.6	268.6	268.6	268.6	271.6	273.9	275.4	279.9
60°	248.8	245.8	243.5	243.5	243.5	242.8	247.3	247.3	251.9	252.6	254.1
62.5°	220.8	219.2	217.7	218.5	217.7	219.2	220.8	223.8	224.6	226.8	229.1
65°	194.2	194.2	192.7	197.2	194.2	194.2	198.0	198.0	199.5	201.8	204.8
67.5°	168.4	169.2	167.7	167.7	169.2	169.9	170.7	173.7	174.5	177.5	181.3
70°	141.9	143.4	144.1	142.6	144.1	145.7	147.2	147.9	151.0	152.5	154.8
72.5°	118.3	119.9	117.6	118.3	119.1	120.6	121.4	122.9	124.4	129.0	130.5
75°	94.8	94.1	93.3	96.3	94.8	97.9	98.6	98.6	100.1	103.9	105.5
77.5°	72.8	72.8	73.6	72.1	74.3	73.6	74.3	76.6	78.9	78.9	85.0
80°	50.8	52.3	52.3	52.3	53.1	53.9	52.3	56.1	56.9	56.9	59.2
82.5°	32.6	33.4	32.6	34.1	34.1	35.7	34.9	35.7	37.2	38.7	39.4
85°	17.4	17.4	19.0	19.0	18.2	19.0	18.2	19.0	20.5	20.5	21.2
87.5°	6.1	6.1	6.1	6.1	6.8	6.1	6.8	6.8	6.1	6.1	8.3
90°	7.4	8.2	9.3	11.4	13.6	15.7	17.9	18.5	19.2	19.8	20.5
92.5°	13.2	12.7	13.4	14.9	16.4	17.9	19.4	20.6	21.7	22.9	24.0
95°	18.3	14.9	15.8	17.6	19.5	21.3	23.1	24.3	25.4	26.6	27.7
97.5°	64.1	61.8	57.6	49.1	40.7	32.2	23.8	25.1	26.5	27.8	29.1
100°	139.0	140.7	127.8	102.0	76.2	50.4	24.6	25.9	27.2	28.5	29.8
102.5°	183.5	184.6	170.2	141.4	112.7	83.9	55.1	49.6	44.2	38.7	33.2
105°	229.1	230.0	222.6	207.7	192.8	177.9	163.0	133.7	104.5	75.2	45.9
107.5°	277.7	278.4	279.6	282.1	284.6	287.0	289.5	264.0	238.6	213.1	187.6
110°	326.8	327.5	328.4	330.2	332.1	333.9	335.7	330.2	324.8	319.3	313.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	373.8	374.4	375.3	377.1	379.0	380.8	382.6	384.1	385.5	387.0	388.5
115°	420.0	420.5	421.2	422.7	424.2	425.7	427.2	428.8	430.5	432.1	433.8
117.5°	466.8	467.4	467.8	468.6	469.5	470.3	471.1	472.4	473.8	475.1	476.4
120°	510.6	511.3	511.5	512.0	512.5	513.0	513.5	514.8	516.2	517.5	518.8
122.5°	552.4	553.0	553.3	554.0	554.7	555.3	556.0	556.8	557.6	558.5	559.3
125°	591.7	592.4	592.7	593.4	594.1	594.7	595.4	595.7	596.1	596.4	596.7
127.5°	630.4	631.1	631.5	632.4	633.2	634.1	634.9	635.4	635.9	636.4	636.9
130°	666.2	666.9	667.2	667.9	668.5	669.2	669.8	670.5	671.1	671.8	672.5
132.5°	700.4	701.1	701.3	701.8	702.3	702.8	703.3	704.0	704.6	705.3	706.0
135°	734.1	734.6	734.9	735.6	736.3	736.9	737.6	738.1	738.6	739.1	739.6
137.5°	765.1	765.8	766.0	766.3	766.6	767.0	767.3	768.1	769.0	769.8	770.7
140°	793.6	794.1	794.4	794.9	795.4	795.9	796.4	797.0	797.7	798.3	799.0
142.5°	821.2	821.7	821.9	822.4	822.9	823.4	823.9	824.4	824.9	825.4	825.9
145°	847.1	847.7	847.9	848.2	848.5	848.9	849.2	849.5	849.9	850.2	850.5
147.5°	870.4	870.8	871.0	871.3	871.6	872.0	872.3	872.6	873.0	873.3	873.6
150°	891.4	891.6	891.8	892.1	892.4	892.8	893.1	893.4	893.8	894.1	894.4
152.5°	910.1	910.2	910.3	910.5	910.6	910.8	911.0	911.7	912.3	913.0	913.7
155°	926.8	926.6	926.7	926.8	927.0	927.1	927.3	928.1	929.0	929.8	930.7
157.5°	943.0	943.0	942.9	942.7	942.6	942.4	942.2	943.2	944.2	945.2	946.2
160°	955.7	955.6	955.5	955.4	955.2	955.1	954.9	955.9	956.9	957.9	958.9
162.5°	967.0	966.8	966.7	966.6	966.4	966.3	966.1	967.3	968.4	969.6	970.7
165°	976.7	976.5	976.4	976.2	976.1	975.9	975.7	977.0	978.4	979.7	981.0
167.5°	984.2	983.9	983.9	983.9	983.9	983.9	983.9	985.2	986.6	987.9	989.2
170°	990.9	990.6	990.6	990.6	990.6	990.6	990.6	991.9	993.3	994.6	995.9
172.5°	994.7	994.3	994.4	994.6	994.7	994.9	995.1	996.4	997.7	999.0	1000.3
175°	998.5	998.1	998.2	998.3	998.5	998.6	998.8	1000.0	1001.1	1002.3	1003.4
177.5°	999.9	999.5	999.6	999.8	999.9	1000.1	1000.3	1001.6	1002.9	1004.2	1005.5
180°	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	742.7	743.5	740.4	738.2	744.2	740.4	740.4	741.2	739.7	742.0	741.2
5°	701.0	701.8	696.4	698.0	694.9	694.2	693.4	698.0	697.2	696.4	698.0
7.5°	660.0	660.0	657.7	656.2	656.2	654.0	657.0	656.2	657.7	657.7	660.0
10°	625.9	627.4	623.6	619.8	619.1	619.8	619.8	620.6	621.3	626.6	625.9
12.5°	597.8	595.5	594.8	592.5	588.7	587.2	585.7	594.0	591.7	591.7	591.7
15°	566.7	572.0	571.3	564.4	562.9	566.0	564.4	564.4	572.0	571.3	570.5
17.5°	550.0	548.5	547.0	543.2	544.0	543.2	544.0	544.0	548.5	548.5	548.5
20°	531.1	528.0	528.0	526.5	526.5	524.2	527.3	528.0	531.1	531.1	531.8
22.5°	514.4	512.1	512.1	511.3	512.8	509.8	512.8	513.6	513.6	515.9	515.9
25°	500.0	498.4	498.4	500.0	500.0	500.0	500.0	503.0	500.7	501.5	500.7
27.5°	487.1	487.8	488.6	489.3	488.6	489.3	490.1	491.6	492.4	491.6	490.1
30°	474.9	477.2	477.9	477.9	479.5	480.2	481.0	481.0	481.7	479.5	481.0
32.5°	465.8	465.8	467.3	468.1	469.6	470.4	470.4	471.9	471.1	468.8	469.6
35°	452.9	452.9	455.9	457.5	459.7	459.0	459.7	459.7	460.5	459.0	456.7
37.5°	440.0	441.5	441.5	444.6	445.3	446.1	445.3	446.8	446.1	444.6	443.8
40°	424.8	424.1	424.8	427.1	427.9	427.9	427.9	429.4	429.4	429.4	428.6
42.5°	405.9	408.2	407.4	409.7	408.9	408.9	410.4	411.9	412.7	410.4	411.2
45°	387.7	387.7	389.2	389.2	389.9	389.9	393.0	391.5	393.0	391.5	392.2
47.5°	367.9	368.7	368.7	369.5	371.0	372.5	371.0	371.7	371.7	372.5	371.0
50°	345.9	345.9	347.5	349.7	352.8	351.3	350.5	353.5	351.3	351.3	349.7
52.5°	323.2	325.5	326.2	328.5	330.8	331.5	332.3	330.8	331.5	329.3	330.0
55°	301.2	301.9	305.0	307.3	309.5	309.5	308.8	309.5	310.3	307.3	307.3
57.5°	279.2	281.5	284.5	284.5	287.5	287.5	286.8	286.8	287.5	285.3	284.5
60°	255.7	257.9	261.7	261.7	266.3	267.0	265.5	264.0	264.0	261.7	262.5
62.5°	230.6	232.9	235.2	239.0	242.0	240.5	243.5	240.5	241.3	236.7	236.7
65°	208.6	209.4	213.2	217.0	217.0	218.5	217.0	217.7	215.5	215.5	212.4
67.5°	182.8	182.8	186.6	190.4	194.2	194.2	194.2	191.9	191.9	189.7	189.7
70°	160.1	159.3	163.1	165.4	167.7	168.4	166.9	166.1	164.6	162.4	161.6
72.5°	132.0	133.5	137.3	138.8	142.6	141.9	145.7	141.1	141.1	137.3	136.6
75°	107.0	108.5	112.3	114.6	116.8	116.8	119.1	116.8	113.8	112.3	111.5
77.5°	85.0	84.2	87.2	91.0	91.8	91.0	92.6	91.8	88.8	88.8	87.2
80°	60.7	63.0	66.0	65.2	68.3	67.5	67.5	66.0	66.0	63.7	65.2
82.5°	40.2	42.5	43.2	42.5	43.2	44.8	45.5	44.8	44.8	43.2	44.0
85°	21.2	21.2	22.8	23.5	22.8	22.8	23.5	25.8	24.3	22.8	24.3
87.5°	6.8	6.1	6.1	6.8	6.1	6.1	6.8	6.8	7.6	7.6	7.6
90°	20.8	21.0	21.3	21.6	22.0	22.3	22.0	21.6	21.3	21.0	20.8
92.5°	24.6	24.7	24.8	25.0	25.1	25.3	25.1	25.0	24.8	24.7	24.6
95°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3
97.5°	29.8	29.9	30.0	30.2	30.3	30.5	30.3	30.2	30.0	29.9	29.8
100°	30.5	30.6	30.8	30.9	31.1	31.3	31.1	30.9	30.8	30.6	30.5
102.5°	30.5	30.7	31.0	31.3	31.7	32.0	31.7	31.3	31.0	30.7	30.5
105°	31.3	31.5	31.8	32.1	32.4	32.7	32.4	32.1	31.8	31.5	31.3
107.5°	174.9	164.1	142.4	120.7	99.1	77.4	99.1	120.7	142.4	164.1	174.9
110°	311.1	299.3	275.6	252.0	228.3	204.7	228.3	252.0	275.6	299.3	311.1

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	389.2	389.0	388.7	388.4	388.1	387.8	388.1	388.4	388.7	389.0	389.2
115°	434.6	434.9	435.6	436.3	436.9	437.6	436.9	436.3	435.6	434.9	434.6
117.5°	477.1	477.2	477.3	477.5	477.6	477.8	477.6	477.5	477.3	477.2	477.1
120°	519.5	519.5	519.5	519.5	519.5	519.5	519.5	519.5	519.5	519.5	519.5
122.5°	559.7	559.8	559.9	560.1	560.2	560.4	560.2	560.1	559.9	559.8	559.7
125°	596.9	597.1	597.4	597.7	598.1	598.4	598.1	597.7	597.4	597.1	596.9
127.5°	637.1	636.9	636.6	636.3	635.9	635.6	635.9	636.3	636.6	636.9	637.1
130°	672.8	672.6	672.3	672.0	671.6	671.3	671.6	672.0	672.3	672.6	672.8
132.5°	706.3	706.1	705.6	705.1	704.6	704.1	704.6	705.1	705.6	706.1	706.3
135°	739.8	739.6	739.1	738.6	738.1	737.6	738.1	738.6	739.1	739.6	739.8
137.5°	771.1	770.9	770.6	770.3	769.9	769.6	769.9	770.3	770.6	770.9	771.1
140°	799.3	799.1	798.8	798.5	798.1	797.8	798.1	798.5	798.8	799.1	799.3
142.5°	826.1	825.9	825.4	824.9	824.4	823.9	824.4	824.9	825.4	825.9	826.1
145°	850.7	850.7	850.7	850.7	850.7	850.7	850.7	850.7	850.7	850.7	850.7
147.5°	873.8	873.4	872.5	871.7	870.8	870.0	870.8	871.7	872.5	873.4	873.8
150°	894.6	894.4	893.9	893.4	892.9	892.4	892.9	893.4	893.9	894.4	894.6
152.5°	914.0	913.6	912.7	911.9	911.0	910.2	911.0	911.9	912.7	913.6	914.0
155°	931.1	930.6	929.6	928.6	927.6	926.6	927.6	928.6	929.6	930.6	931.1
157.5°	946.7	946.0	944.7	943.4	942.0	940.7	942.0	943.4	944.7	946.0	946.7
160°	959.4	958.8	957.6	956.5	955.3	954.1	955.3	956.5	957.6	958.8	959.4
162.5°	971.3	970.8	969.8	968.8	967.8	966.8	967.8	968.8	969.8	970.8	971.3
165°	981.7	981.1	980.0	978.8	977.7	976.5	977.7	978.8	980.0	981.1	981.7
167.5°	989.9	989.2	987.9	986.6	985.2	983.9	985.2	986.6	987.9	989.2	989.9
170°	996.6	995.9	994.6	993.3	991.9	990.6	991.9	993.3	994.6	995.9	996.6
172.5°	1001.0	1000.3	998.8	997.3	995.8	994.3	995.8	997.3	998.8	1000.3	1001.0
175°	1004.0	1003.3	1002.0	1000.7	999.4	998.1	999.4	1000.7	1002.0	1003.3	1004.0
177.5°	1006.2	1005.4	1003.7	1002.1	1000.4	998.8	1000.4	1002.1	1003.7	1005.4	1006.2
180°	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	743.5	745.0	745.8	742.7	740.4	744.2	749.5	753.3	756.4	760.2	762.4
5°	699.5	704.8	704.8	706.3	708.6	712.4	722.2	729.1	735.1	739.7	743.5
7.5°	662.3	666.1	668.4	672.2	676.0	681.3	692.6	702.5	711.6	716.9	723.0
10°	628.9	632.0	635.7	638.0	644.9	652.4	666.9	675.2	685.8	694.2	701.8
12.5°	597.1	607.7	610.0	609.2	615.3	623.6	638.0	650.9	662.3	670.6	679.0
15°	574.3	578.1	582.6	581.9	594.8	597.1	609.2	624.4	639.5	644.9	652.4
17.5°	549.3	555.3	559.9	562.2	566.0	574.3	585.7	597.1	616.8	617.5	637.3
20°	529.5	535.6	538.6	541.7	544.0	553.8	563.7	576.6	592.5	600.9	611.5
22.5°	516.6	519.7	522.0	524.2	527.3	532.6	544.7	559.1	569.7	578.9	585.7
25°	501.5	504.5	507.5	509.1	511.3	514.4	523.5	534.8	550.0	556.1	562.9
27.5°	490.8	490.8	492.4	492.4	495.4	498.4	505.3	515.9	528.0	535.6	544.7
30°	479.5	478.7	479.5	478.7	477.9	482.5	488.6	497.7	506.0	515.1	521.2
32.5°	468.1	467.3	467.3	468.1	465.1	467.3	470.4	478.7	487.8	492.4	499.2
35°	455.9	454.4	454.4	454.4	452.9	451.4	454.4	462.0	468.1	474.2	479.5
37.5°	443.8	441.5	441.5	440.0	438.5	436.2	436.2	442.3	450.6	452.9	459.7
40°	427.1	427.1	425.6	424.8	423.3	421.8	419.5	424.8	432.4	434.7	440.0
42.5°	410.4	408.2	407.4	407.4	407.4	405.1	403.6	407.4	411.9	415.7	418.8
45°	391.5	389.9	390.7	389.9	388.4	387.7	386.9	388.4	393.7	395.3	399.1
47.5°	371.0	370.2	370.2	369.5	368.7	369.5	366.4	370.2	371.7	373.3	376.3
50°	349.7	349.0	348.2	347.5	347.5	348.2	347.5	347.5	350.5	352.0	355.0
52.5°	328.5	326.2	326.2	325.5	325.5	323.9	325.5	326.2	327.7	329.3	330.8
55°	305.7	305.7	303.5	303.5	301.9	301.9	302.7	301.9	305.0	306.5	306.5
57.5°	283.7	280.7	281.5	279.9	278.4	277.7	277.7	279.2	280.7	280.7	282.2
60°	260.2	257.2	256.4	253.4	254.9	252.6	253.4	253.4	256.4	254.9	256.4
62.5°	236.7	232.9	230.6	229.1	229.1	229.9	228.4	227.6	229.1	230.6	233.7
65°	211.7	209.4	207.1	204.8	204.8	204.1	205.6	203.3	202.6	203.3	204.8
67.5°	185.9	183.6	181.3	179.0	179.8	177.5	176.0	178.3	176.8	177.5	179.0
70°	160.8	159.3	154.8	153.2	152.5	153.2	152.5	151.0	153.2	152.5	153.2
72.5°	135.8	134.3	132.0	128.2	128.2	127.5	126.7	126.7	125.9	125.9	125.9
75°	111.5	108.5	106.2	105.5	103.9	103.2	102.4	100.9	101.7	102.4	100.9
77.5°	86.5	82.7	81.9	81.9	79.7	79.7	80.4	79.7	78.9	78.9	78.9
80°	63.7	60.7	60.7	59.2	57.7	57.7	57.7	57.7	56.9	56.1	56.9
82.5°	41.0	40.2	39.4	39.4	41.0	37.9	39.4	38.7	37.9	37.9	37.2
85°	22.8	23.5	22.8	23.5	22.0	22.8	22.8	22.8	22.0	22.8	21.2
87.5°	8.3	8.3	8.3	9.1	9.1	9.1	9.1	9.1	9.9	9.1	9.1
90°	20.5	19.8	19.2	18.5	17.9	15.7	13.6	11.4	9.3	8.2	7.4
92.5°	24.0	22.9	21.7	20.6	19.4	17.9	16.4	14.9	13.4	12.7	13.2
95°	27.7	26.6	25.4	24.3	23.1	21.3	19.5	17.6	15.8	14.9	18.3
97.5°	29.1	27.8	26.5	25.1	23.8	32.2	40.7	49.1	57.6	61.8	64.1
100°	29.8	28.5	27.2	25.9	24.6	50.4	76.2	102.0	127.8	140.7	139.0
102.5°	33.2	38.7	44.2	49.6	55.1	83.9	112.7	141.4	170.2	184.6	183.5
105°	45.9	75.2	104.5	133.7	163.0	177.9	192.8	207.7	222.6	230.0	229.1
107.5°	187.6	213.1	238.6	264.0	289.5	287.0	284.6	282.1	279.6	278.4	277.7
110°	313.8	319.3	324.8	330.2	335.7	333.9	332.1	330.2	328.4	327.5	326.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	388.5	387.0	385.5	384.1	382.6	380.8	379.0	377.1	375.3	374.4	373.8
115°	433.8	432.1	430.5	428.8	427.2	425.7	424.2	422.7	421.2	420.5	420.0
117.5°	476.4	475.1	473.8	472.4	471.1	470.3	469.5	468.6	467.8	467.4	466.8
120°	518.8	517.5	516.2	514.8	513.5	513.0	512.5	512.0	511.5	511.3	510.6
122.5°	559.3	558.5	557.6	556.8	556.0	555.3	554.7	554.0	553.3	553.0	552.4
125°	596.7	596.4	596.1	595.7	595.4	594.7	594.1	593.4	592.7	592.4	591.7
127.5°	636.9	636.4	635.9	635.4	634.9	634.1	633.2	632.4	631.5	631.1	630.4
130°	672.5	671.8	671.1	670.5	669.8	669.2	668.5	667.9	667.2	666.9	666.2
132.5°	706.0	705.3	704.6	704.0	703.3	702.8	702.3	701.8	701.3	701.1	700.4
135°	739.6	739.1	738.6	738.1	737.6	736.9	736.3	735.6	734.9	734.6	734.1
137.5°	770.7	769.8	769.0	768.1	767.3	767.0	766.6	766.3	766.0	765.8	765.1
140°	799.0	798.3	797.7	797.0	796.4	795.9	795.4	794.9	794.4	794.1	793.6
142.5°	825.9	825.4	824.9	824.4	823.9	823.4	822.9	822.4	821.9	821.7	821.2
145°	850.5	850.2	849.9	849.5	849.2	848.9	848.5	848.2	847.9	847.7	847.1
147.5°	873.6	873.3	873.0	872.6	872.3	872.0	871.6	871.3	871.0	870.8	870.4
150°	894.4	894.1	893.8	893.4	893.1	892.8	892.4	892.1	891.8	891.6	891.4
152.5°	913.7	913.0	912.3	911.7	911.0	910.8	910.6	910.5	910.3	910.2	910.1
155°	930.7	929.8	929.0	928.1	927.3	927.1	927.0	926.8	926.7	926.6	926.8
157.5°	946.2	945.2	944.2	943.2	942.2	942.4	942.6	942.7	942.9	943.0	943.0
160°	958.9	957.9	956.9	955.9	954.9	955.1	955.2	955.4	955.5	955.6	955.7
162.5°	970.7	969.6	968.4	967.3	966.1	966.3	966.4	966.6	966.7	966.8	967.0
165°	981.0	979.7	978.4	977.0	975.7	975.9	976.1	976.2	976.4	976.5	976.7
167.5°	989.2	987.9	986.6	985.2	983.9	983.9	983.9	983.9	983.9	983.9	984.2
170°	995.9	994.6	993.3	991.9	990.6	990.6	990.6	990.6	990.6	990.6	990.9
172.5°	1000.3	999.0	997.7	996.4	995.1	994.9	994.7	994.6	994.4	994.3	994.7
175°	1003.4	1002.3	1001.1	1000.0	998.8	998.6	998.5	998.3	998.2	998.1	998.5
177.5°	1005.5	1004.2	1002.9	1001.6	1000.3	1000.1	999.9	999.8	999.6	999.5	999.9
180°	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	782.9	782.9	782.9	782.9
2.5°	766.2	768.5	776.1	785.2
5°	751.1	757.1	767.8	782.2
7.5°	734.4	743.5	758.7	776.9
10°	715.4	728.3	747.3	770.0
12.5°	694.9	711.6	735.9	759.4
15°	682.0	698.7	720.7	746.5
17.5°	657.0	676.7	699.5	735.9
20°	631.2	653.2	682.8	719.2
22.5°	611.5	635.0	663.1	701.8
25°	588.0	612.2	642.6	682.8
27.5°	562.9	587.2	621.3	663.8
30°	544.0	567.5	600.1	645.6
32.5°	521.2	544.0	578.1	625.9
35°	495.4	521.2	553.8	602.4
37.5°	475.7	499.2	533.3	579.6
40°	454.4	474.9	508.3	553.8
42.5°	431.7	454.4	483.3	528.8
45°	410.4	427.1	456.7	500.0
47.5°	387.7	406.6	429.4	462.8
50°	363.4	379.3	404.4	427.1
52.5°	339.9	352.8	374.0	391.5
55°	314.8	327.7	343.7	354.3
57.5°	291.3	300.4	311.0	317.9
60°	262.5	271.6	278.4	285.3
62.5°	236.7	243.5	247.3	251.1
65°	210.1	213.9	216.2	219.2
67.5°	181.3	185.1	185.9	190.4
70°	154.8	155.5	157.0	159.3
72.5°	129.7	131.2	130.5	132.0
75°	103.9	105.5	103.9	105.5
77.5°	78.9	80.4	80.4	82.7
80°	56.9	57.7	58.4	58.4
82.5°	37.2	39.4	37.9	38.7
85°	21.2	22.0	22.0	22.8
87.5°	9.9	10.6	9.9	11.4
90°	5.7	4.0	2.4	0.7
92.5°	14.2	15.1	16.1	17.1
95°	25.1	31.8	38.6	45.4
97.5°	68.7	73.4	78.0	82.6
100°	135.7	132.4	129.1	125.8
102.5°	181.4	179.2	177.1	174.9
105°	227.3	225.4	223.6	221.8
107.5°	276.2	274.7	273.2	271.7
110°	325.5	324.2	322.8	321.5

TEST NUMBER: P1031828

CATALOG NUMBER: S123DIW-B560D755UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	372.7	371.5	370.4	369.2
115°	419.0	418.0	417.0	416.0
117.5°	465.7	464.5	463.4	462.2
120°	509.1	507.6	506.1	504.6
122.5°	551.3	550.1	549.0	547.8
125°	590.4	589.1	587.8	586.5
127.5°	629.1	627.8	626.5	625.2
130°	664.9	663.6	662.2	660.9
132.5°	699.1	697.8	696.4	695.1
135°	733.1	732.1	731.1	730.1
137.5°	763.8	762.5	761.2	759.9
140°	792.6	791.7	790.7	789.7
142.5°	820.2	819.2	818.2	817.2
145°	846.0	844.8	843.7	842.5
147.5°	869.6	868.7	867.9	867.1
150°	890.9	890.4	889.9	889.4
152.5°	910.0	909.8	909.7	909.5
155°	927.1	927.4	927.8	928.1
157.5°	943.0	943.0	943.0	943.0
160°	955.9	956.0	956.2	956.4
162.5°	967.5	968.0	968.5	969.0
165°	977.2	977.7	978.2	978.7
167.5°	984.9	985.6	986.2	986.9
170°	991.6	992.3	992.9	993.6
172.5°	995.6	996.4	997.3	998.1
175°	999.3	1000.2	1001.0	1001.8
177.5°	1000.8	1001.6	1002.5	1003.3
180°	1001.8	1001.8	1001.8	1001.8

(END OF REPORT)