

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031862

Luminaire Tested: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031862
REPORT IS A COMBINATION OF REPORTS P991897 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B775D1030UB50-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6640.0 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11241	11241	11241	11241
5°	11248	12953	11282	9666
10°	11177	15673	11189	8442
15°	11023	18588	11113	7598
20°	10889	21401	10913	6992
25°	10693	21940	10716	6675
30°	10552	18127	10552	6468
35°	10377	12123	10311	6284
40°	10166	8751	10041	6004
45°	9904	6932	9619	5655
50°	9264	5887	8936	5313
55°	8563	5173	8215	4931
60°	7851	4504	7435	4530
65°	7071	3856	6728	3995
70°	6258	3201	5840	3369
75°	5352	2414	5006	2599
80°	4229	1612	3898	1709
85°	2920	740	2334	674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18129 cd/sqm

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	1.5
10°-20°	329.9	5.0
20°-30°	555.1	8.4
30°-40°	627.3	9.4
40°-50°	561.8	8.5
50°-60°	453.5	6.8
60°-70°	316.0	4.8
70°-80°	165.9	2.5
80°-90°	42.4	0.6
90°-100°	81.0	1.2
100°-110°	245.1	3.7
110°-120°	417.2	6.3
120°-130°	548.9	8.3
130°-140°	617.0	9.3
140°-150°	606.5	9.1
150°-160°	510.7	7.7
160°-170°	340.0	5.1
170°-180°	119.0	1.8
0°-30°	987.7	14.9
0°-40°	1615.0	24.3
0°-60°	2630.3	39.6
0°-90°	3154.7	47.5
90°-120°	743.3	11.2
90°-150°	2515.7	37.9
90°-180°	3485.0	52.5
0°-180°	6640.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1044	1044	1044	1044	1044	
5°	1043	1241	1046	926	1043	99
15°	996	1847	1004	755	996	281
25°	911	2192	913	667	911	420
35°	804	1181	798	612	804	503
45°	667	638	648	520	667	510
55°	473	433	453	413	473	423
65°	292	281	278	291	292	291
75°	141	145	132	156	141	151
85°	30	33	24	30	30	35
90°	1	30	1	30	1	6
95°	58	77	58	77	58	64
105°	222	235	222	235	222	238
115°	420	421	420	421	420	416
125°	615	608	615	608	615	548
135°	797	796	797	796	797	614
145°	967	967	967	967	967	604
155°	1108	1106	1108	1106	1108	510
165°	1206	1202	1206	1202	1206	340
175°	1255	1250	1255	1250	1255	119
180°	1258	1258	1258	1258	1258	

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1047.4	1055.5	1059.5	1065.6	1071.7	1080.8	1083.8	1088.9	1086.8	1090.9	1092.9
5°	1043.3	1057.5	1069.6	1084.8	1099.0	1109.1	1119.2	1135.4	1147.6	1149.6	1158.7
7.5°	1036.2	1056.5	1077.7	1099.0	1126.3	1142.5	1160.7	1183.0	1201.2	1230.5	1241.7
10°	1027.1	1055.5	1085.8	1115.2	1152.6	1177.9	1200.2	1237.6	1275.1	1305.4	1333.8
12.5°	1013.0	1048.4	1087.9	1131.4	1179.9	1209.3	1239.7	1289.2	1345.9	1392.5	1422.8
15°	995.8	1040.3	1090.9	1137.4	1191.1	1245.7	1278.1	1333.8	1414.7	1458.2	1536.2
17.5°	981.6	1027.1	1077.7	1150.6	1223.5	1278.1	1301.4	1403.6	1459.2	1532.1	1620.2
20°	959.3	1017.0	1081.8	1154.6	1248.8	1282.2	1329.7	1432.9	1501.8	1596.9	1705.2
22.5°	936.1	997.8	1075.7	1151.6	1256.9	1292.3	1357.0	1439.0	1548.3	1642.4	1761.8
25°	910.8	977.6	1056.5	1146.6	1249.8	1301.4	1362.1	1463.3	1581.7	1700.1	1810.4
27.5°	885.5	958.3	1040.3	1130.4	1230.5	1291.3	1352.0	1457.2	1609.0	1737.5	1878.2
30°	861.2	934.0	1016.0	1108.1	1213.3	1272.0	1329.7	1461.3	1630.3	1775.0	1916.7
32.5°	834.9	909.8	995.8	1072.7	1178.9	1241.7	1306.4	1461.3	1643.4	1797.2	1926.8
35°	803.5	880.4	954.3	1031.2	1136.4	1206.3	1279.1	1451.2	1655.6	1804.3	1884.3
37.5°	773.1	840.9	904.7	979.6	1089.9	1164.8	1248.8	1439.0	1649.5	1774.0	1796.2
40°	738.7	806.5	858.1	928.0	1044.3	1131.4	1216.4	1422.8	1623.2	1702.1	1637.4
42.5°	705.3	759.0	803.5	871.3	997.8	1082.8	1174.9	1393.5	1571.6	1587.8	1442.0
45°	666.9	705.3	744.8	821.7	947.2	1034.2	1136.4	1351.0	1488.6	1442.0	1257.9
47.5°	617.3	651.7	695.2	766.1	893.6	983.6	1080.8	1296.3	1368.2	1271.0	1069.6
50°	569.7	599.1	639.6	708.4	836.9	924.9	1028.2	1210.3	1245.7	1092.9	921.9
52.5°	522.2	544.4	583.9	652.7	781.2	866.2	960.4	1122.3	1102.0	938.1	786.3
55°	472.6	491.8	529.3	597.1	716.5	797.4	887.5	1014.0	961.4	805.5	684.1
57.5°	424.0	444.3	482.7	539.4	651.7	730.6	802.5	901.7	822.7	698.3	591.0
60°	380.5	397.7	427.0	482.7	584.9	648.7	714.4	782.2	716.5	596.0	514.1
62.5°	335.0	351.2	378.5	429.1	517.1	573.8	626.4	682.1	609.2	521.2	448.3
65°	292.5	305.6	330.9	377.5	449.3	495.9	538.4	576.8	518.1	437.2	382.5
67.5°	254.0	265.1	286.4	327.9	388.6	422.0	456.4	488.8	439.2	374.4	327.9
70°	212.5	221.6	240.8	271.2	319.8	354.2	379.5	403.8	359.2	307.6	276.3
72.5°	176.1	185.2	197.3	228.7	262.1	283.3	310.7	323.8	298.5	256.0	224.7
75°	140.7	147.7	158.9	179.1	210.5	224.7	241.9	252.0	228.7	200.4	181.1
77.5°	110.3	113.3	121.4	135.6	156.9	173.0	186.2	192.3	176.1	157.9	141.7
80°	77.9	82.0	88.0	100.2	116.4	121.4	129.5	136.6	126.5	110.3	100.2
82.5°	51.6	56.7	59.7	64.8	74.9	81.0	83.0	89.1	79.9	73.9	69.8
85°	30.4	32.4	33.4	36.4	41.5	44.5	47.6	48.6	46.6	45.5	41.5
87.5°	15.2	15.2	15.2	17.2	18.2	20.2	21.3	21.3	21.3	20.2	19.2
90°	1.0	3.2	5.4	7.6	9.8	10.9	12.3	15.2	18.0	20.9	23.7
92.5°	29.6	30.9	32.3	33.6	34.9	35.6	36.3	37.6	38.9	40.2	41.5
95°	58.3	59.8	61.4	62.9	64.4	65.2	66.1	67.8	69.6	71.3	73.1
97.5°	95.8	96.9	98.0	99.1	100.2	100.8	101.5	102.8	104.1	105.4	106.7
100°	134.4	135.7	137.0	138.3	139.6	140.3	140.9	142.0	143.1	144.2	145.3
102.5°	178.8	179.5	180.1	180.8	181.5	181.8	182.6	184.1	185.6	187.2	188.7
105°	222.3	222.7	223.2	223.6	224.1	224.3	225.3	227.3	229.2	231.2	233.2
107.5°	273.7	273.9	274.1	274.4	274.6	274.7	275.1	276.0	276.9	277.7	278.6
110°	321.1	321.5	322.0	322.4	322.9	323.1	323.3	323.8	324.2	324.7	325.1

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	370.5	370.7	370.9	371.2	371.4	371.5	371.5	371.5	371.5	371.5	371.5
115°	420.0	420.6	421.3	421.9	422.6	422.9	422.7	422.2	421.8	421.3	420.9
117.5°	470.3	470.5	470.7	471.0	471.2	471.3	471.1	470.7	470.2	469.8	469.4
120°	516.8	518.1	519.4	520.7	522.0	522.7	522.2	521.1	520.0	518.9	517.8
122.5°	565.2	566.1	567.0	567.9	568.8	569.2	569.0	568.5	568.1	567.6	567.2
125°	614.6	615.3	615.9	616.6	617.3	617.6	617.4	616.9	616.5	616.0	615.6
127.5°	660.1	661.4	662.7	664.0	665.3	666.0	665.8	665.3	664.9	664.4	664.0
130°	705.5	707.3	709.0	710.8	712.5	713.4	713.1	712.4	711.8	711.1	710.5
132.5°	751.0	752.8	754.5	756.3	758.0	758.9	758.7	758.2	757.8	757.3	756.9
135°	797.4	798.7	800.0	801.3	802.6	803.3	803.2	803.0	802.8	802.6	802.4
137.5°	839.9	841.0	842.1	843.2	844.3	844.8	845.1	845.8	846.5	847.1	847.8
140°	884.4	885.5	886.6	887.7	888.8	889.3	889.4	889.6	889.9	890.1	890.3
142.5°	924.9	926.0	927.1	928.2	929.3	929.8	930.0	930.5	930.9	931.4	931.8
145°	967.4	967.8	968.2	968.7	969.1	969.3	969.6	970.3	971.0	971.6	972.3
147.5°	1003.9	1004.8	1005.7	1006.6	1007.5	1007.9	1008.2	1008.9	1009.5	1010.2	1010.8
150°	1042.5	1042.9	1043.3	1043.8	1044.2	1044.4	1044.6	1045.1	1045.5	1046.0	1046.4
152.5°	1074.1	1074.7	1075.4	1076.0	1076.7	1077.0	1077.1	1077.3	1077.6	1077.8	1078.0
155°	1107.7	1107.7	1107.7	1107.7	1107.7	1107.7	1107.8	1108.0	1108.3	1108.5	1108.7
157.5°	1136.3	1136.1	1135.9	1135.6	1135.4	1135.3	1135.4	1135.6	1135.9	1136.1	1136.3
160°	1163.0	1162.6	1162.1	1161.7	1161.2	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0
162.5°	1186.7	1186.1	1185.4	1184.8	1184.1	1183.8	1183.9	1184.1	1184.4	1184.6	1184.8
165°	1206.5	1205.8	1205.2	1204.5	1203.8	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5
167.5°	1223.3	1222.4	1221.5	1220.6	1219.7	1219.3	1219.4	1219.6	1219.9	1220.1	1220.3
170°	1237.1	1236.2	1235.4	1234.5	1233.6	1233.2	1233.2	1233.2	1233.2	1233.2	1233.2
172.5°	1248.0	1247.1	1246.2	1245.3	1244.4	1244.0	1244.0	1244.0	1244.0	1244.0	1244.0
175°	1254.9	1254.0	1253.2	1252.3	1251.4	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0
177.5°	1258.9	1258.0	1257.1	1256.2	1255.3	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9
180°	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1100.0	1102.0	1109.1	1114.2	1124.3	1123.3	1123.3	1122.3	1119.2	1124.3	1127.3
5°	1176.9	1194.1	1196.1	1218.4	1219.4	1228.5	1234.6	1229.5	1241.7	1240.7	1231.6
7.5°	1272.0	1295.3	1306.4	1327.7	1352.0	1345.9	1369.2	1373.2	1371.2	1381.3	1388.4
10°	1376.3	1416.7	1445.1	1484.5	1494.7	1500.7	1515.9	1529.1	1555.4	1535.1	1548.3
12.5°	1495.7	1525.0	1562.5	1625.2	1656.6	1676.8	1683.9	1693.0	1711.2	1700.1	1701.1
15°	1595.9	1635.3	1699.1	1777.0	1786.1	1811.4	1805.3	1860.0	1886.3	1846.8	1869.1
17.5°	1700.1	1752.7	1828.6	1896.4	1934.9	1952.1	1968.3	2020.9	2018.9	2012.8	2017.9
20°	1766.9	1852.9	1947.0	2037.1	2048.2	2061.4	2104.9	2127.1	2123.1	2140.3	2151.4
22.5°	1861.0	1952.1	2052.3	2112.0	2137.3	2152.4	2186.8	2201.0	2207.1	2211.1	2204.1
25°	1939.9	2037.1	2111.0	2163.6	2178.8	2186.8	2198.0	2202.0	2199.0	2191.9	2198.0
27.5°	1993.6	2071.5	2122.1	2146.4	2138.3	2125.1	2103.9	2089.7	2058.3	2043.2	2061.4
30°	2015.8	2050.2	2065.4	2024.9	1984.5	1952.1	1911.6	1836.7	1778.0	1795.2	1771.9
32.5°	1980.4	1958.1	1885.3	1781.1	1749.7	1697.1	1582.7	1494.7	1497.7	1451.2	1470.4
35°	1876.2	1775.0	1637.4	1479.5	1438.0	1409.7	1284.2	1265.0	1224.5	1181.0	1193.1
37.5°	1692.0	1544.3	1377.3	1260.9	1199.2	1137.4	1066.6	1024.1	999.8	981.6	995.8
40°	1467.3	1287.2	1149.6	1045.4	992.7	953.3	904.7	862.2	834.9	831.8	836.9
42.5°	1246.7	1094.9	968.4	869.3	852.1	805.5	774.2	740.8	732.7	719.5	726.6
45°	1055.5	932.0	827.8	746.8	726.6	714.4	676.0	654.7	645.6	637.5	649.7
47.5°	916.8	787.3	711.4	662.8	642.6	622.4	601.1	586.9	579.9	580.9	579.9
50°	783.3	688.1	621.3	583.9	571.8	557.6	540.4	531.3	528.2	519.1	526.2
52.5°	674.0	605.2	558.6	523.2	514.1	504.0	489.8	484.7	477.6	475.6	475.6
55°	585.9	532.3	494.8	471.6	460.4	452.3	444.3	438.2	433.1	433.1	433.1
57.5°	517.1	470.6	443.2	423.0	419.0	410.9	401.7	401.7	394.7	393.7	396.7
60°	458.4	416.9	395.7	378.5	372.4	370.4	361.3	361.3	359.2	354.2	358.2
62.5°	398.7	368.4	350.1	337.0	330.9	330.9	323.8	318.8	318.8	319.8	317.8
65°	344.1	321.8	305.6	295.5	292.5	288.4	287.4	283.3	280.3	281.3	280.3
67.5°	295.5	278.3	267.2	259.1	254.0	252.0	248.9	248.9	246.9	247.9	242.9
70°	252.0	234.8	225.7	217.6	215.5	215.5	211.5	212.5	210.5	213.5	211.5
72.5°	207.5	194.3	187.2	184.2	182.2	181.1	179.1	177.1	176.1	178.1	177.1
75°	168.0	156.9	151.8	149.8	147.7	147.7	146.7	145.7	144.7	144.7	144.7
77.5°	130.5	123.5	117.4	119.4	116.4	117.4	114.4	114.4	115.4	114.4	114.4
80°	96.1	91.1	91.1	89.1	85.0	87.0	87.0	84.0	83.0	85.0	82.0
82.5°	63.8	62.7	60.7	59.7	57.7	58.7	57.7	56.7	55.7	57.7	55.7
85°	37.4	37.4	36.4	34.4	36.4	35.4	34.4	34.4	33.4	33.4	33.4
87.5°	19.2	17.2	17.2	16.2	17.2	15.2	16.2	15.2	14.2	15.2	14.2
90°	24.6	25.5	26.4	27.3	27.7	27.9	28.3	28.8	29.2	29.6	29.2
92.5°	42.2	42.8	43.5	44.2	44.5	44.3	43.8	43.4	42.9	42.5	42.9
95°	74.0	74.9	75.8	76.7	77.1	77.1	77.1	77.1	77.1	77.1	77.1
97.5°	107.8	108.9	110.0	111.1	111.7	111.6	111.4	111.1	110.9	110.7	110.9
100°	145.9	146.6	147.2	147.9	148.2	148.4	148.9	149.3	149.8	150.2	149.8
102.5°	189.4	190.0	190.7	191.4	191.7	191.6	191.4	191.1	190.9	190.7	190.9
105°	233.2	233.2	233.2	233.2	233.2	233.4	233.9	234.3	234.8	235.2	234.8
107.5°	279.3	279.9	280.6	281.3	281.6	281.5	281.3	281.0	280.8	280.6	280.8
110°	326.0	326.8	327.7	328.6	329.0	328.8	328.4	327.9	327.5	327.1	327.5

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	372.6	373.7	374.8	375.9	376.5	376.5	376.5	376.5	376.5	376.5	376.5
115°	421.1	421.3	421.6	421.8	421.9	421.8	421.6	421.3	421.1	420.9	421.1
117.5°	469.4	469.4	469.4	469.4	469.4	469.1	468.4	467.7	467.1	466.4	467.1
120°	517.6	517.4	517.1	516.9	516.8	516.6	516.1	515.7	515.2	514.8	515.2
122.5°	566.5	565.9	565.2	564.5	564.2	563.9	563.2	562.6	561.9	561.3	561.9
125°	614.7	613.8	612.9	612.0	611.6	611.2	610.3	609.4	608.6	607.7	608.6
127.5°	662.7	661.4	660.1	658.8	658.1	657.7	656.8	655.9	655.0	654.1	655.0
130°	709.6	708.7	707.8	706.9	706.5	705.7	704.2	702.7	701.1	699.6	701.1
132.5°	755.8	754.7	753.6	752.5	752.0	751.4	750.3	749.2	748.1	747.0	748.1
135°	801.5	800.6	799.7	798.8	798.4	798.2	797.7	797.3	796.8	796.4	796.8
137.5°	846.7	845.6	844.5	843.4	842.9	842.6	841.9	841.2	840.6	839.9	840.6
140°	890.1	889.9	889.6	889.4	889.3	888.5	887.0	885.5	883.9	882.4	883.9
142.5°	931.6	931.4	931.1	930.9	930.8	930.3	929.2	928.1	927.0	925.9	927.0
145°	972.1	971.9	971.6	971.4	971.3	970.9	970.0	969.1	968.3	967.4	968.3
147.5°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.1	1008.8	1007.5	1006.2	1004.9	1006.2
150°	1046.4	1046.4	1046.4	1046.4	1046.4	1045.7	1044.4	1043.1	1041.8	1040.5	1041.8
152.5°	1078.4	1078.9	1079.3	1079.8	1080.0	1079.5	1078.4	1077.3	1076.2	1075.1	1076.2
155°	1109.6	1110.4	1111.3	1112.2	1112.6	1111.8	1110.3	1108.8	1107.2	1105.7	1107.2
157.5°	1137.2	1138.1	1139.0	1139.9	1140.3	1139.6	1138.3	1137.0	1135.7	1134.4	1135.7
160°	1162.1	1163.2	1164.3	1165.4	1166.0	1165.6	1164.7	1163.8	1162.9	1162.0	1162.9
162.5°	1185.9	1187.0	1188.1	1189.2	1189.7	1188.9	1187.4	1185.9	1184.3	1182.8	1184.3
165°	1204.8	1206.2	1207.5	1208.8	1209.5	1208.7	1207.2	1205.6	1204.1	1202.5	1204.1
167.5°	1221.6	1223.0	1224.3	1225.6	1226.3	1225.6	1224.3	1223.0	1221.6	1220.3	1221.6
170°	1234.7	1236.3	1237.8	1239.3	1240.1	1239.3	1237.8	1236.3	1234.7	1233.2	1234.7
172.5°	1245.3	1246.7	1248.0	1249.3	1250.0	1249.2	1247.7	1246.2	1244.6	1243.1	1244.6
175°	1252.3	1253.6	1254.9	1256.2	1256.9	1256.1	1254.6	1253.1	1251.5	1250.0	1251.5
177.5°	1256.2	1257.5	1258.8	1260.1	1260.8	1260.0	1258.5	1257.0	1255.4	1253.9	1255.4
180°	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1119.2	1122.3	1114.2	1112.1	1112.1	1116.2	1113.2	1085.8	1090.9	1084.8	1082.8
5°	1242.7	1236.6	1228.5	1224.5	1219.4	1205.2	1204.2	1172.9	1166.8	1146.6	1137.4
7.5°	1378.3	1373.2	1348.9	1345.9	1343.9	1330.7	1297.3	1263.9	1239.7	1216.4	1194.1
10°	1533.1	1517.9	1506.8	1484.5	1473.4	1455.2	1411.7	1380.3	1338.8	1303.4	1256.9
12.5°	1719.3	1702.1	1664.7	1648.5	1634.3	1583.7	1540.2	1504.8	1423.8	1399.5	1341.9
15°	1855.9	1819.5	1815.5	1780.0	1778.0	1722.4	1639.4	1600.9	1538.2	1449.1	1389.4
17.5°	2003.7	1971.3	1946.0	1903.5	1897.4	1844.8	1784.1	1690.0	1621.2	1536.2	1460.3
20°	2112.0	2094.8	2051.2	2034.0	1998.6	1954.1	1891.4	1775.0	1691.0	1606.0	1512.9
22.5°	2198.0	2180.8	2146.4	2123.1	2102.9	2045.2	1970.3	1871.1	1755.8	1644.4	1548.3
25°	2197.0	2191.9	2177.7	2166.6	2151.4	2108.9	2046.2	1951.1	1822.5	1700.1	1566.5
27.5°	2072.5	2086.7	2111.0	2123.1	2120.1	2114.0	2078.6	1998.6	1883.3	1737.5	1587.8
30°	1813.4	1865.0	1910.6	1971.3	1989.5	2034.0	2054.3	2008.7	1916.7	1781.1	1615.1
32.5°	1503.8	1578.7	1677.8	1711.2	1768.9	1854.9	1951.1	1968.3	1910.6	1806.4	1632.3
35°	1233.6	1295.3	1372.2	1424.8	1476.5	1616.1	1737.5	1842.8	1862.0	1793.2	1628.2
37.5°	1021.1	1064.6	1132.4	1176.9	1224.5	1343.9	1513.9	1650.5	1746.6	1748.7	1617.1
40°	867.3	886.5	945.2	977.6	1023.1	1126.3	1278.1	1456.2	1596.9	1661.6	1587.8
42.5°	734.7	760.0	808.6	832.8	862.2	952.3	1052.4	1221.4	1395.5	1534.1	1533.1
45°	655.8	674.0	696.2	716.5	749.9	803.5	917.8	1044.3	1211.3	1368.2	1429.9
47.5°	585.9	603.1	625.4	631.5	653.7	704.3	774.2	884.5	1040.3	1196.1	1312.5
50°	527.2	541.4	556.6	567.7	577.8	619.3	671.9	765.0	889.5	1040.3	1185.0
52.5°	481.7	491.8	505.0	511.0	520.1	550.5	591.0	659.8	762.0	899.6	1040.3
55°	439.2	446.3	454.4	464.5	468.5	490.8	522.2	580.9	656.8	780.2	913.8
57.5°	399.7	402.8	407.8	413.9	419.0	438.2	465.5	505.0	571.8	666.9	793.4
60°	355.2	363.3	366.3	372.4	375.4	390.6	411.9	445.3	496.9	578.8	674.0
62.5°	317.8	322.8	327.9	330.9	338.0	343.1	360.3	390.6	433.1	493.8	579.9
65°	284.4	286.4	289.4	292.5	294.5	300.6	316.7	337.0	369.4	423.0	489.8
67.5°	245.9	247.9	252.0	253.0	255.0	263.1	272.2	289.4	316.7	357.2	411.9
70°	208.5	211.5	213.5	215.5	218.6	221.6	231.7	245.9	267.2	295.5	338.0
72.5°	176.1	179.1	179.1	181.1	180.1	184.2	194.3	204.4	218.6	241.9	279.3
75°	143.7	143.7	145.7	146.7	147.7	151.8	155.8	163.9	175.1	193.3	216.6
77.5°	113.3	112.3	114.4	114.4	114.4	117.4	121.4	125.5	132.6	145.7	163.9
80°	83.0	83.0	85.0	86.0	84.0	85.0	87.0	91.1	96.1	105.2	115.4
82.5°	54.6	58.7	57.7	58.7	57.7	59.7	60.7	61.7	63.8	67.8	74.9
85°	33.4	33.4	33.4	34.4	33.4	34.4	34.4	34.4	35.4	37.4	40.5
87.5°	14.2	14.2	14.2	15.2	14.2	14.2	15.2	14.2	15.2	15.2	16.2
90°	28.8	28.3	27.9	27.7	27.3	26.4	25.5	24.6	23.7	20.9	18.0
92.5°	43.4	43.8	44.3	44.5	44.2	43.5	42.8	42.2	41.5	40.2	38.9
95°	77.1	77.1	77.1	77.1	76.7	75.8	74.9	74.0	73.1	71.3	69.6
97.5°	111.1	111.4	111.6	111.7	111.1	110.0	108.9	107.8	106.7	105.4	104.1
100°	149.3	148.9	148.4	148.2	147.9	147.2	146.6	145.9	145.3	144.2	143.1
102.5°	191.1	191.4	191.6	191.7	191.4	190.7	190.0	189.4	188.7	187.2	185.6
105°	234.3	233.9	233.4	233.2	233.2	233.2	233.2	233.2	233.2	231.2	229.2
107.5°	281.0	281.3	281.5	281.6	281.3	280.6	279.9	279.3	278.6	277.7	276.9
110°	327.9	328.4	328.8	329.0	328.6	327.7	326.8	326.0	325.1	324.7	324.2

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	376.5	376.5	376.5	376.5	375.9	374.8	373.7	372.6	371.5	371.5	371.5
115°	421.3	421.6	421.8	421.9	421.8	421.6	421.3	421.1	420.9	421.3	421.8
117.5°	467.7	468.4	469.1	469.4	469.4	469.4	469.4	469.4	469.4	469.8	470.2
120°	515.7	516.1	516.6	516.8	516.9	517.1	517.4	517.6	517.8	518.9	520.0
122.5°	562.6	563.2	563.9	564.2	564.5	565.2	565.9	566.5	567.2	567.6	568.1
125°	609.4	610.3	611.2	611.6	612.0	612.9	613.8	614.7	615.6	616.0	616.5
127.5°	655.9	656.8	657.7	658.1	658.8	660.1	661.4	662.7	664.0	664.4	664.9
130°	702.7	704.2	705.7	706.5	706.9	707.8	708.7	709.6	710.5	711.1	711.8
132.5°	749.2	750.3	751.4	752.0	752.5	753.6	754.7	755.8	756.9	757.3	757.8
135°	797.3	797.7	798.2	798.4	798.8	799.7	800.6	801.5	802.4	802.6	802.8
137.5°	841.2	841.9	842.6	842.9	843.4	844.5	845.6	846.7	847.8	847.1	846.5
140°	885.5	887.0	888.5	889.3	889.4	889.6	889.9	890.1	890.3	890.1	889.9
142.5°	928.1	929.2	930.3	930.8	930.9	931.1	931.4	931.6	931.8	931.4	930.9
145°	969.1	970.0	970.9	971.3	971.4	971.6	971.9	972.1	972.3	971.6	971.0
147.5°	1007.5	1008.8	1010.1	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.2	1009.5
150°	1043.1	1044.4	1045.7	1046.4	1046.4	1046.4	1046.4	1046.4	1046.4	1046.0	1045.5
152.5°	1077.3	1078.4	1079.5	1080.0	1079.8	1079.3	1078.9	1078.4	1078.0	1077.8	1077.6
155°	1108.8	1110.3	1111.8	1112.6	1112.2	1111.3	1110.4	1109.6	1108.7	1108.5	1108.3
157.5°	1137.0	1138.3	1139.6	1140.3	1139.9	1139.0	1138.1	1137.2	1136.3	1136.1	1135.9
160°	1163.8	1164.7	1165.6	1166.0	1165.4	1164.3	1163.2	1162.1	1161.0	1161.0	1161.0
162.5°	1185.9	1187.4	1188.9	1189.7	1189.2	1188.1	1187.0	1185.9	1184.8	1184.6	1184.4
165°	1205.6	1207.2	1208.7	1209.5	1208.8	1207.5	1206.2	1204.8	1203.5	1203.5	1203.5
167.5°	1223.0	1224.3	1225.6	1226.3	1225.6	1224.3	1223.0	1221.6	1220.3	1220.1	1219.9
170°	1236.3	1237.8	1239.3	1240.1	1239.3	1237.8	1236.3	1234.7	1233.2	1233.2	1233.2
172.5°	1246.2	1247.7	1249.2	1250.0	1249.3	1248.0	1246.7	1245.3	1244.0	1244.0	1244.0
175°	1253.1	1254.6	1256.1	1256.9	1256.2	1254.9	1253.6	1252.3	1251.0	1251.0	1251.0
177.5°	1257.0	1258.5	1260.0	1260.8	1260.1	1258.8	1257.5	1256.2	1254.9	1254.9	1254.9
180°	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1072.7	1069.6	1069.6	1067.6	1061.5	1050.4	1049.4	1051.4	1045.4	1039.3	1030.2
5°	1125.3	1106.1	1100.0	1093.9	1081.8	1061.5	1053.5	1046.4	1035.2	1022.1	1007.9
7.5°	1169.8	1142.5	1134.4	1123.3	1099.0	1070.7	1052.4	1037.3	1022.1	1003.9	986.7
10°	1225.5	1186.0	1166.8	1150.6	1117.2	1077.7	1050.4	1028.2	1003.9	981.6	959.3
12.5°	1288.2	1224.5	1218.4	1178.9	1140.5	1081.8	1048.4	1016.0	983.6	956.3	933.0
15°	1340.8	1271.0	1245.7	1219.4	1145.5	1072.7	1040.3	1003.9	966.4	937.1	902.7
17.5°	1374.2	1316.6	1262.9	1227.5	1150.6	1085.8	1023.1	981.6	942.1	901.7	873.3
20°	1414.7	1330.7	1284.2	1236.6	1160.7	1075.7	1013.0	961.4	912.8	876.4	842.0
22.5°	1455.2	1341.9	1303.4	1251.8	1162.7	1065.6	994.8	943.1	887.5	851.1	813.6
25°	1451.2	1358.1	1294.3	1250.8	1142.5	1056.5	973.5	912.8	861.2	814.6	777.2
27.5°	1454.2	1339.8	1275.1	1224.5	1128.3	1043.3	951.2	887.5	833.9	785.3	745.8
30°	1455.2	1312.5	1255.8	1195.1	1102.0	1012.0	925.9	861.2	804.5	751.9	716.5
32.5°	1452.2	1290.3	1219.4	1164.8	1060.5	981.6	896.6	827.8	770.1	721.5	688.1
35°	1445.1	1263.9	1182.0	1113.2	1018.0	938.1	869.3	798.4	736.7	692.2	653.7
37.5°	1425.9	1235.6	1142.5	1074.7	968.4	887.5	826.8	768.1	708.4	655.8	623.4
40°	1411.7	1197.2	1103.0	1029.2	914.8	835.9	785.3	729.6	670.9	623.4	592.0
42.5°	1379.3	1160.7	1062.6	974.5	862.2	781.2	733.7	689.1	638.5	592.0	563.7
45°	1326.7	1121.3	1013.0	923.9	804.5	727.6	684.1	647.7	603.1	558.6	530.3
47.5°	1252.8	1064.6	960.4	871.3	747.8	669.9	626.4	599.1	563.7	526.2	501.9
50°	1172.9	1002.9	906.7	818.7	693.2	617.3	574.8	549.5	526.2	491.8	468.5
52.5°	1068.6	937.1	845.0	761.0	634.5	561.6	524.2	506.0	481.7	457.4	437.2
55°	967.4	852.1	776.2	696.2	576.8	509.0	472.6	453.4	439.2	419.0	402.8
57.5°	850.0	773.1	703.3	630.5	523.2	461.5	427.0	403.8	394.7	385.6	370.4
60°	741.8	683.1	626.4	565.7	467.5	411.9	378.5	360.3	351.2	345.1	335.0
62.5°	642.6	597.1	548.5	499.9	410.9	360.3	335.0	316.7	308.6	307.6	298.5
65°	547.5	515.1	475.6	428.1	358.2	313.7	289.4	278.3	269.2	269.2	262.1
67.5°	452.3	430.1	398.7	365.3	310.7	269.2	246.9	236.8	231.7	231.7	226.7
70°	376.4	361.3	332.9	303.6	256.0	224.7	207.5	198.3	195.3	196.3	192.3
72.5°	305.6	289.4	266.1	244.9	209.5	186.2	174.1	163.9	158.9	159.9	158.9
75°	236.8	228.7	208.5	192.3	163.9	147.7	136.6	131.6	127.5	128.5	126.5
77.5°	178.1	166.0	154.8	143.7	126.5	113.3	104.2	99.2	96.1	96.1	96.1
80°	121.4	119.4	110.3	104.2	90.1	79.9	72.9	71.8	68.8	68.8	68.8
82.5°	78.9	73.9	68.8	64.8	56.7	50.6	47.6	45.5	44.5	43.5	45.5
85°	43.5	40.5	38.5	34.4	31.4	28.3	25.3	24.3	23.3	24.3	23.3
87.5°	17.2	14.2	14.2	13.2	12.1	11.1	11.1	9.1	9.1	8.1	8.1
90°	15.2	12.3	10.9	9.8	7.6	5.4	3.2	1.0	3.2	5.4	7.6
92.5°	37.6	36.3	35.6	34.9	33.6	32.3	30.9	29.6	30.9	32.3	33.6
95°	67.8	66.1	65.2	64.4	62.9	61.4	59.8	58.3	59.8	61.4	62.9
97.5°	102.8	101.5	100.8	100.2	99.1	98.0	96.9	95.8	96.9	98.0	99.1
100°	142.0	140.9	140.3	139.6	138.3	137.0	135.7	134.4	135.7	137.0	138.3
102.5°	184.1	182.6	181.8	181.5	180.8	180.1	179.5	178.8	179.5	180.1	180.8
105°	227.3	225.3	224.3	224.1	223.6	223.2	222.7	222.3	222.7	223.2	223.6
107.5°	276.0	275.1	274.7	274.6	274.4	274.1	273.9	273.7	273.9	274.1	274.4
110°	323.8	323.3	323.1	322.9	322.4	322.0	321.5	321.1	321.5	322.0	322.4

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	371.5	371.5	371.5	371.4	371.2	370.9	370.7	370.5	370.7	370.9	371.2
115°	422.2	422.7	422.9	422.6	421.9	421.3	420.6	420.0	420.6	421.3	421.9
117.5°	470.7	471.1	471.3	471.2	471.0	470.7	470.5	470.3	470.5	470.7	471.0
120°	521.1	522.2	522.7	522.0	520.7	519.4	518.1	516.8	518.1	519.4	520.7
122.5°	568.5	569.0	569.2	568.8	567.9	567.0	566.1	565.2	566.1	567.0	567.9
125°	616.9	617.4	617.6	617.3	616.6	615.9	615.3	614.6	615.3	615.9	616.6
127.5°	665.3	665.8	666.0	665.3	664.0	662.7	661.4	660.1	661.4	662.7	664.0
130°	712.4	713.1	713.4	712.5	710.8	709.0	707.3	705.5	707.3	709.0	710.8
132.5°	758.2	758.7	758.9	758.0	756.3	754.5	752.8	751.0	752.8	754.5	756.3
135°	803.0	803.2	803.3	802.6	801.3	800.0	798.7	797.4	798.7	800.0	801.3
137.5°	845.8	845.1	844.8	844.3	843.2	842.1	841.0	839.9	841.0	842.1	843.2
140°	889.6	889.4	889.3	888.8	887.7	886.6	885.5	884.4	885.5	886.6	887.7
142.5°	930.5	930.0	929.8	929.3	928.2	927.1	926.0	924.9	926.0	927.1	928.2
145°	970.3	969.6	969.3	969.1	968.7	968.2	967.8	967.4	967.8	968.2	968.7
147.5°	1008.9	1008.2	1007.9	1007.5	1006.6	1005.7	1004.8	1003.9	1004.8	1005.7	1006.6
150°	1045.1	1044.6	1044.4	1044.2	1043.8	1043.3	1042.9	1042.5	1042.9	1043.3	1043.8
152.5°	1077.3	1077.1	1077.0	1076.7	1076.0	1075.4	1074.7	1074.1	1074.7	1075.4	1076.0
155°	1108.0	1107.8	1107.7	1107.7	1107.7	1107.7	1107.7	1107.7	1107.7	1107.7	1107.7
157.5°	1135.6	1135.4	1135.3	1135.4	1135.6	1135.9	1136.1	1136.3	1136.1	1135.9	1135.6
160°	1161.0	1161.0	1161.0	1161.2	1161.7	1162.1	1162.6	1163.0	1162.6	1162.1	1161.7
162.5°	1184.1	1183.9	1183.8	1184.1	1184.8	1185.4	1186.1	1186.7	1186.1	1185.4	1184.8
165°	1203.5	1203.5	1203.5	1203.8	1204.5	1205.2	1205.8	1206.5	1205.8	1205.2	1204.5
167.5°	1219.6	1219.4	1219.3	1219.7	1220.6	1221.5	1222.4	1223.3	1222.4	1221.5	1220.6
170°	1233.2	1233.2	1233.2	1233.6	1234.5	1235.4	1236.2	1237.1	1236.2	1235.4	1234.5
172.5°	1244.0	1244.0	1244.0	1244.4	1245.3	1246.2	1247.1	1248.0	1247.1	1246.2	1245.3
175°	1251.0	1251.0	1251.0	1251.4	1252.3	1253.2	1254.0	1254.9	1254.0	1253.2	1252.3
177.5°	1254.9	1254.9	1254.9	1255.3	1256.2	1257.1	1258.0	1258.9	1258.0	1257.1	1256.2
180°	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1028.2	1027.1	1029.2	1023.1	1013.0	1007.9	993.7	990.7	989.7	990.7	991.7
5°	999.8	998.8	995.8	985.7	973.5	964.4	947.2	946.2	940.1	934.0	937.1
7.5°	972.5	968.4	962.4	949.2	933.0	922.9	908.7	898.6	890.5	885.5	881.4
10°	945.2	939.1	933.0	915.8	895.6	880.4	863.2	855.1	846.0	842.0	837.9
12.5°	909.8	903.7	892.6	872.3	860.2	840.9	823.7	815.6	810.6	802.5	797.4
15°	881.4	869.3	863.2	842.0	816.7	814.6	783.3	781.2	771.1	771.1	763.0
17.5°	849.0	839.9	828.8	807.5	789.3	771.1	754.9	748.9	739.7	737.7	733.7
20°	817.7	805.5	801.5	780.2	761.0	738.7	721.5	715.5	711.4	707.4	710.4
22.5°	785.3	775.2	765.0	745.8	731.6	709.4	699.3	693.2	687.1	685.1	686.1
25°	753.9	744.8	734.7	715.5	700.3	682.1	673.0	669.9	666.9	666.9	665.9
27.5°	723.6	714.4	705.3	688.1	673.0	659.8	652.7	649.7	646.6	648.7	650.7
30°	692.2	684.1	676.0	660.8	648.7	636.5	632.5	630.5	629.4	634.5	634.5
32.5°	663.8	656.8	650.7	636.5	624.4	614.3	611.2	612.2	613.2	616.3	618.3
35°	634.5	629.4	623.4	611.2	601.1	592.0	593.0	593.0	595.0	600.1	604.1
37.5°	608.2	601.1	596.0	585.9	577.8	569.7	572.8	575.8	577.8	583.9	585.9
40°	576.8	573.8	569.7	559.6	552.5	551.5	552.5	554.6	558.6	561.6	564.7
42.5°	551.5	547.5	542.4	534.3	528.2	529.3	530.3	532.3	534.3	539.4	542.4
45°	523.2	520.1	516.1	509.0	504.0	505.0	506.0	506.0	508.0	514.1	516.1
47.5°	491.8	492.8	487.8	480.7	477.6	477.6	477.6	479.7	484.7	486.8	487.8
50°	461.5	459.4	458.4	451.3	449.3	448.3	449.3	450.3	457.4	456.4	459.4
52.5°	429.1	429.1	428.1	424.0	421.0	421.0	419.0	424.0	426.0	428.1	431.1
55°	397.7	394.7	393.7	391.6	387.6	386.6	388.6	394.7	396.7	398.7	401.7
57.5°	363.3	363.3	361.3	358.2	358.2	358.2	358.2	362.3	365.3	367.3	373.4
60°	331.9	327.9	324.8	324.8	324.8	323.8	329.9	329.9	336.0	337.0	339.0
62.5°	294.5	292.5	290.4	291.4	290.4	292.5	294.5	298.5	299.5	302.6	305.6
65°	259.1	259.1	257.0	263.1	259.1	259.1	264.1	264.1	266.1	269.2	273.2
67.5°	224.7	225.7	223.6	223.6	225.7	226.7	227.7	231.7	232.8	236.8	241.9
70°	189.2	191.3	192.3	190.2	192.3	194.3	196.3	197.3	201.4	203.4	206.4
72.5°	157.9	159.9	156.9	157.9	158.9	160.9	161.9	163.9	166.0	172.0	174.1
75°	126.5	125.5	124.5	128.5	126.5	130.5	131.6	131.6	133.6	138.6	140.7
77.5°	97.1	97.1	98.2	96.1	99.2	98.2	99.2	102.2	105.2	105.2	113.3
80°	67.8	69.8	69.8	69.8	70.8	71.8	69.8	74.9	75.9	75.9	78.9
82.5°	43.5	44.5	43.5	45.5	45.5	47.6	46.6	47.6	49.6	51.6	52.6
85°	23.3	23.3	25.3	25.3	24.3	25.3	24.3	25.3	27.3	27.3	28.3
87.5°	8.1	8.1	8.1	8.1	9.1	8.1	9.1	9.1	8.1	8.1	11.1
90°	9.8	10.9	12.3	15.2	18.0	20.9	23.7	24.6	25.5	26.4	27.3
92.5°	34.9	35.6	36.3	37.6	38.9	40.2	41.5	42.2	42.8	43.5	44.2
95°	64.4	65.2	66.1	67.8	69.6	71.3	73.1	74.0	74.9	75.8	76.7
97.5°	100.2	100.8	101.5	102.8	104.1	105.4	106.7	107.8	108.9	110.0	111.1
100°	139.6	140.3	140.9	142.0	143.1	144.2	145.3	145.9	146.6	147.2	147.9
102.5°	181.5	181.8	182.6	184.1	185.6	187.2	188.7	189.4	190.0	190.7	191.4
105°	224.1	224.3	225.3	227.3	229.2	231.2	233.2	233.2	233.2	233.2	233.2
107.5°	274.6	274.7	275.1	276.0	276.9	277.7	278.6	279.3	279.9	280.6	281.3
110°	322.9	323.1	323.3	323.8	324.2	324.7	325.1	326.0	326.8	327.7	328.6

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	371.4	371.5	371.5	371.5	371.5	371.5	371.5	372.6	373.7	374.8	375.9
115°	422.6	422.9	422.7	422.2	421.8	421.3	420.9	421.1	421.3	421.6	421.8
117.5°	471.2	471.3	471.1	470.7	470.2	469.8	469.4	469.4	469.4	469.4	469.4
120°	522.0	522.7	522.2	521.1	520.0	518.9	517.8	517.6	517.4	517.1	516.9
122.5°	568.8	569.2	569.0	568.5	568.1	567.6	567.2	566.5	565.9	565.2	564.5
125°	617.3	617.6	617.4	616.9	616.5	616.0	615.6	614.7	613.8	612.9	612.0
127.5°	665.3	666.0	665.8	665.3	664.9	664.4	664.0	662.7	661.4	660.1	658.8
130°	712.5	713.4	713.1	712.4	711.8	711.1	710.5	709.6	708.7	707.8	706.9
132.5°	758.0	758.9	758.7	758.2	757.8	757.3	756.9	755.8	754.7	753.6	752.5
135°	802.6	803.3	803.2	803.0	802.8	802.6	802.4	801.5	800.6	799.7	798.8
137.5°	844.3	844.8	845.1	845.8	846.5	847.1	847.8	846.7	845.6	844.5	843.4
140°	888.8	889.3	889.4	889.6	889.9	890.1	890.3	890.1	889.9	889.6	889.4
142.5°	929.3	929.8	930.0	930.5	930.9	931.4	931.8	931.6	931.4	931.1	930.9
145°	969.1	969.3	969.6	970.3	971.0	971.6	972.3	972.1	971.9	971.6	971.4
147.5°	1007.5	1007.9	1008.2	1008.9	1009.5	1010.2	1010.8	1010.8	1010.8	1010.8	1010.8
150°	1044.2	1044.4	1044.6	1045.1	1045.5	1046.0	1046.4	1046.4	1046.4	1046.4	1046.4
152.5°	1076.7	1077.0	1077.1	1077.3	1077.6	1077.8	1078.0	1078.4	1078.9	1079.3	1079.8
155°	1107.7	1107.7	1107.8	1108.0	1108.3	1108.5	1108.7	1109.6	1110.4	1111.3	1112.2
157.5°	1135.4	1135.3	1135.4	1135.6	1135.9	1136.1	1136.3	1137.2	1138.1	1139.0	1139.9
160°	1161.2	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1162.1	1163.2	1164.3	1165.4
162.5°	1184.1	1183.8	1183.9	1184.1	1184.4	1184.6	1184.8	1185.9	1187.0	1188.1	1189.2
165°	1203.8	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1204.8	1206.2	1207.5	1208.8
167.5°	1219.7	1219.3	1219.4	1219.6	1219.9	1220.1	1220.3	1221.6	1223.0	1224.3	1225.6
170°	1233.6	1233.2	1233.2	1233.2	1233.2	1233.2	1233.2	1234.7	1236.3	1237.8	1239.3
172.5°	1244.4	1244.0	1244.0	1244.0	1244.0	1244.0	1244.0	1245.3	1246.7	1248.0	1249.3
175°	1251.4	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1252.3	1253.6	1254.9	1256.2
177.5°	1255.3	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1256.2	1257.5	1258.8	1260.1
180°	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	990.7	991.7	987.7	984.6	992.7	987.7	987.7	988.7	986.7	989.7	988.7
5°	935.1	936.1	929.0	931.0	927.0	925.9	924.9	931.0	930.0	929.0	931.0
7.5°	880.4	880.4	877.4	875.3	875.3	872.3	876.4	875.3	877.4	877.4	880.4
10°	834.9	836.9	831.8	826.8	825.8	826.8	826.8	827.8	828.8	835.9	834.9
12.5°	797.4	794.4	793.4	790.3	785.3	783.3	781.2	792.4	789.3	789.3	789.3
15°	755.9	763.0	762.0	752.9	750.9	754.9	752.9	752.9	763.0	762.0	761.0
17.5°	733.7	731.6	729.6	724.6	725.6	724.6	725.6	725.6	731.6	731.6	731.6
20°	708.4	704.3	704.3	702.3	702.3	699.3	703.3	704.3	708.4	708.4	709.4
22.5°	686.1	683.1	683.1	682.1	684.1	680.0	684.1	685.1	685.1	688.1	688.1
25°	666.9	664.9	664.9	666.9	666.9	666.9	666.9	670.9	667.9	668.9	667.9
27.5°	649.7	650.7	651.7	652.7	651.7	652.7	653.7	655.8	656.8	655.8	653.7
30°	633.5	636.5	637.5	637.5	639.6	640.6	641.6	641.6	642.6	639.6	641.6
32.5°	621.3	621.3	623.4	624.4	626.4	627.4	627.4	629.4	628.4	625.4	626.4
35°	604.1	604.1	608.2	610.2	613.2	612.2	613.2	613.2	614.3	612.2	609.2
37.5°	586.9	589.0	589.0	593.0	594.0	595.0	594.0	596.0	595.0	593.0	592.0
40°	566.7	565.7	566.7	569.7	570.7	570.7	570.7	572.8	572.8	572.8	571.8
42.5°	541.4	544.4	543.4	546.5	545.4	545.4	547.5	549.5	550.5	547.5	548.5
45°	517.1	517.1	519.1	519.1	520.1	520.1	524.2	522.2	524.2	522.2	523.2
47.5°	490.8	491.8	491.8	492.8	494.8	496.9	494.8	495.9	495.9	496.9	494.8
50°	461.5	461.5	463.5	466.5	470.6	468.5	467.5	471.6	468.5	468.5	466.5
52.5°	431.1	434.1	435.1	438.2	441.2	442.2	443.2	441.2	442.2	439.2	440.2
55°	401.7	402.8	406.8	409.8	412.9	412.9	411.9	412.9	413.9	409.8	409.8
57.5°	372.4	375.4	379.5	379.5	383.5	383.5	382.5	382.5	383.5	380.5	379.5
60°	341.0	344.1	349.1	349.1	355.2	356.2	354.2	352.2	352.2	349.1	350.1
62.5°	307.6	310.7	313.7	318.8	322.8	320.8	324.8	320.8	321.8	315.7	315.7
65°	278.3	279.3	284.4	289.4	289.4	291.4	289.4	290.4	287.4	287.4	283.3
67.5°	243.9	243.9	248.9	254.0	259.1	259.1	259.1	256.0	256.0	253.0	253.0
70°	213.5	212.5	217.6	220.6	223.6	224.7	222.6	221.6	219.6	216.6	215.5
72.5°	176.1	178.1	183.2	185.2	190.2	189.2	194.3	188.2	188.2	183.2	182.2
75°	142.7	144.7	149.8	152.8	155.8	155.8	158.9	155.8	151.8	149.8	148.8
77.5°	113.3	112.3	116.4	121.4	122.4	121.4	123.5	122.4	118.4	118.4	116.4
80°	81.0	84.0	88.0	87.0	91.1	90.1	90.1	88.0	88.0	85.0	87.0
82.5°	53.6	56.7	57.7	56.7	57.7	59.7	60.7	59.7	59.7	57.7	58.7
85°	28.3	28.3	30.4	31.4	30.4	30.4	31.4	34.4	32.4	30.4	32.4
87.5°	9.1	8.1	8.1	9.1	8.1	8.1	9.1	9.1	10.1	10.1	10.1
90°	27.7	27.9	28.3	28.8	29.2	29.6	29.2	28.8	28.3	27.9	27.7
92.5°	44.5	44.3	43.8	43.4	42.9	42.5	42.9	43.4	43.8	44.3	44.5
95°	77.1	77.1	77.1	77.1	77.1	77.1	77.1	77.1	77.1	77.1	77.1
97.5°	111.7	111.6	111.4	111.1	110.9	110.7	110.9	111.1	111.4	111.6	111.7
100°	148.2	148.4	148.9	149.3	149.8	150.2	149.8	149.3	148.9	148.4	148.2
102.5°	191.7	191.6	191.4	191.1	190.9	190.7	190.9	191.1	191.4	191.6	191.7
105°	233.2	233.4	233.9	234.3	234.8	235.2	234.8	234.3	233.9	233.4	233.2
107.5°	281.6	281.5	281.3	281.0	280.8	280.6	280.8	281.0	281.3	281.5	281.6
110°	329.0	328.8	328.4	327.9	327.5	327.1	327.5	327.9	328.4	328.8	329.0

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	376.5	376.5	376.5	376.5	376.5	376.5	376.5	376.5	376.5	376.5	376.5
115°	421.9	421.8	421.6	421.3	421.1	420.9	421.1	421.3	421.6	421.8	421.9
117.5°	469.4	469.1	468.4	467.7	467.1	466.4	467.1	467.7	468.4	469.1	469.4
120°	516.8	516.6	516.1	515.7	515.2	514.8	515.2	515.7	516.1	516.6	516.8
122.5°	564.2	563.9	563.2	562.6	561.9	561.3	561.9	562.6	563.2	563.9	564.2
125°	611.6	611.2	610.3	609.4	608.6	607.7	608.6	609.4	610.3	611.2	611.6
127.5°	658.1	657.7	656.8	655.9	655.0	654.1	655.0	655.9	656.8	657.7	658.1
130°	706.5	705.7	704.2	702.7	701.1	699.6	701.1	702.7	704.2	705.7	706.5
132.5°	752.0	751.4	750.3	749.2	748.1	747.0	748.1	749.2	750.3	751.4	752.0
135°	798.4	798.2	797.7	797.3	796.8	796.4	796.8	797.3	797.7	798.2	798.4
137.5°	842.9	842.6	841.9	841.2	840.6	839.9	840.6	841.2	841.9	842.6	842.9
140°	889.3	888.5	887.0	885.5	883.9	882.4	883.9	885.5	887.0	888.5	889.3
142.5°	930.8	930.3	929.2	928.1	927.0	925.9	927.0	928.1	929.2	930.3	930.8
145°	971.3	970.9	970.0	969.1	968.3	967.4	968.3	969.1	970.0	970.9	971.3
147.5°	1010.8	1010.1	1008.8	1007.5	1006.2	1004.9	1006.2	1007.5	1008.8	1010.1	1010.8
150°	1046.4	1045.7	1044.4	1043.1	1041.8	1040.5	1041.8	1043.1	1044.4	1045.7	1046.4
152.5°	1080.0	1079.5	1078.4	1077.3	1076.2	1075.1	1076.2	1077.3	1078.4	1079.5	1080.0
155°	1112.6	1111.8	1110.3	1108.8	1107.2	1105.7	1107.2	1108.8	1110.3	1111.8	1112.6
157.5°	1140.3	1139.6	1138.3	1137.0	1135.7	1134.4	1135.7	1137.0	1138.3	1139.6	1140.3
160°	1166.0	1165.6	1164.7	1163.8	1162.9	1162.0	1162.9	1163.8	1164.7	1165.6	1166.0
162.5°	1189.7	1188.9	1187.4	1185.9	1184.3	1182.8	1184.3	1185.9	1187.4	1188.9	1189.7
165°	1209.5	1208.7	1207.2	1205.6	1204.1	1202.5	1204.1	1205.6	1207.2	1208.7	1209.5
167.5°	1226.3	1225.6	1224.3	1223.0	1221.6	1220.3	1221.6	1223.0	1224.3	1225.6	1226.3
170°	1240.1	1239.3	1237.8	1236.3	1234.7	1233.2	1234.7	1236.3	1237.8	1239.3	1240.1
172.5°	1250.0	1249.2	1247.7	1246.2	1244.6	1243.1	1244.6	1246.2	1247.7	1249.2	1250.0
175°	1256.9	1256.1	1254.6	1253.1	1251.5	1250.0	1251.5	1253.1	1254.6	1256.1	1256.9
177.5°	1260.8	1260.0	1258.5	1257.0	1255.4	1253.9	1255.4	1257.0	1258.5	1260.0	1260.8
180°	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	991.7	993.7	994.8	990.7	987.7	992.7	999.8	1004.9	1008.9	1014.0	1017.0
5°	933.0	940.1	940.1	942.1	945.2	950.2	963.4	972.5	980.6	986.7	991.7
7.5°	883.4	888.5	891.5	896.6	901.7	908.7	923.9	937.1	949.2	956.3	964.4
10°	838.9	843.0	848.0	851.1	860.2	870.3	889.5	900.6	914.8	925.9	936.1
12.5°	796.4	810.6	813.6	812.6	820.7	831.8	851.1	868.3	883.4	894.6	905.7
15°	766.1	771.1	777.2	776.2	793.4	796.4	812.6	832.8	853.1	860.2	870.3
17.5°	732.7	740.8	746.8	749.9	754.9	766.1	781.2	796.4	822.7	823.7	850.0
20°	706.3	714.4	718.5	722.5	725.6	738.7	751.9	769.1	790.3	801.5	815.6
22.5°	689.1	693.2	696.2	699.3	703.3	710.4	726.6	745.8	760.0	772.1	781.2
25°	668.9	673.0	677.0	679.0	682.1	686.1	698.3	713.4	733.7	741.8	750.9
27.5°	654.7	654.7	656.8	656.8	660.8	664.9	674.0	688.1	704.3	714.4	726.6
30°	639.6	638.5	639.6	638.5	637.5	643.6	651.7	663.8	675.0	687.1	695.2
32.5°	624.4	623.4	623.4	624.4	620.3	623.4	627.4	638.5	650.7	656.8	665.9
35°	608.2	606.2	606.2	606.2	604.1	602.1	606.2	616.3	624.4	632.5	639.6
37.5°	592.0	589.0	589.0	586.9	584.9	581.9	581.9	590.0	601.1	604.1	613.2
40°	569.7	569.7	567.7	566.7	564.7	562.7	559.6	566.7	576.8	579.9	586.9
42.5°	547.5	544.4	543.4	543.4	543.4	540.4	538.4	543.4	549.5	554.6	558.6
45°	522.2	520.1	521.2	520.1	518.1	517.1	516.1	518.1	525.2	527.2	532.3
47.5°	494.8	493.8	493.8	492.8	491.8	492.8	488.8	493.8	495.9	497.9	501.9
50°	466.5	465.5	464.5	463.5	463.5	464.5	463.5	463.5	467.5	469.6	473.6
52.5°	438.2	435.1	435.1	434.1	434.1	432.1	434.1	435.1	437.2	439.2	441.2
55°	407.8	407.8	404.8	404.8	402.8	402.8	403.8	402.8	406.8	408.8	408.8
57.5°	378.5	374.4	375.4	373.4	371.4	370.4	370.4	372.4	374.4	374.4	376.4
60°	347.1	343.1	342.0	338.0	340.0	337.0	338.0	338.0	342.0	340.0	342.0
62.5°	315.7	310.7	307.6	305.6	305.6	306.6	304.6	303.6	305.6	307.6	311.7
65°	282.3	279.3	276.3	273.2	273.2	272.2	274.2	271.2	270.2	271.2	273.2
67.5°	247.9	244.9	241.9	238.8	239.8	236.8	234.8	237.8	235.8	236.8	238.8
70°	214.5	212.5	206.4	204.4	203.4	204.4	203.4	201.4	204.4	203.4	204.4
72.5°	181.1	179.1	176.1	171.0	171.0	170.0	169.0	169.0	168.0	168.0	168.0
75°	148.8	144.7	141.7	140.7	138.6	137.6	136.6	134.6	135.6	136.6	134.6
77.5°	115.4	110.3	109.3	109.3	106.3	106.3	107.3	106.3	105.2	105.2	105.2
80°	85.0	81.0	81.0	78.9	76.9	76.9	76.9	76.9	75.9	74.9	75.9
82.5°	54.6	53.6	52.6	52.6	54.6	50.6	52.6	51.6	50.6	50.6	49.6
85°	30.4	31.4	30.4	31.4	29.3	30.4	30.4	30.4	29.3	30.4	28.3
87.5°	11.1	11.1	11.1	12.1	12.1	12.1	12.1	12.1	13.2	12.1	12.1
90°	27.3	26.4	25.5	24.6	23.7	20.9	18.0	15.2	12.3	10.9	9.8
92.5°	44.2	43.5	42.8	42.2	41.5	40.2	38.9	37.6	36.3	35.6	34.9
95°	76.7	75.8	74.9	74.0	73.1	71.3	69.6	67.8	66.1	65.2	64.4
97.5°	111.1	110.0	108.9	107.8	106.7	105.4	104.1	102.8	101.5	100.8	100.2
100°	147.9	147.2	146.6	145.9	145.3	144.2	143.1	142.0	140.9	140.3	139.6
102.5°	191.4	190.7	190.0	189.4	188.7	187.2	185.6	184.1	182.6	181.8	181.5
105°	233.2	233.2	233.2	233.2	233.2	231.2	229.2	227.3	225.3	224.3	224.1
107.5°	281.3	280.6	279.9	279.3	278.6	277.7	276.9	276.0	275.1	274.7	274.6
110°	328.6	327.7	326.8	326.0	325.1	324.7	324.2	323.8	323.3	323.1	322.9

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	375.9	374.8	373.7	372.6	371.5	371.5	371.5	371.5	371.5	371.5	371.4
115°	421.8	421.6	421.3	421.1	420.9	421.3	421.8	422.2	422.7	422.9	422.6
117.5°	469.4	469.4	469.4	469.4	469.4	469.8	470.2	470.7	471.1	471.3	471.2
120°	516.9	517.1	517.4	517.6	517.8	518.9	520.0	521.1	522.2	522.7	522.0
122.5°	564.5	565.2	565.9	566.5	567.2	567.6	568.1	568.5	569.0	569.2	568.8
125°	612.0	612.9	613.8	614.7	615.6	616.0	616.5	616.9	617.4	617.6	617.3
127.5°	658.8	660.1	661.4	662.7	664.0	664.4	664.9	665.3	665.8	666.0	665.3
130°	706.9	707.8	708.7	709.6	710.5	711.1	711.8	712.4	713.1	713.4	712.5
132.5°	752.5	753.6	754.7	755.8	756.9	757.3	757.8	758.2	758.7	758.9	758.0
135°	798.8	799.7	800.6	801.5	802.4	802.6	802.8	803.0	803.2	803.3	802.6
137.5°	843.4	844.5	845.6	846.7	847.8	847.1	846.5	845.8	845.1	844.8	844.3
140°	889.4	889.6	889.9	890.1	890.3	890.1	889.9	889.6	889.4	889.3	888.8
142.5°	930.9	931.1	931.4	931.6	931.8	931.4	930.9	930.5	930.0	929.8	929.3
145°	971.4	971.6	971.9	972.1	972.3	971.6	971.0	970.3	969.6	969.3	969.1
147.5°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.2	1009.5	1008.9	1008.2	1007.9	1007.5
150°	1046.4	1046.4	1046.4	1046.4	1046.4	1046.0	1045.5	1045.1	1044.6	1044.4	1044.2
152.5°	1079.8	1079.3	1078.9	1078.4	1078.0	1077.8	1077.6	1077.3	1077.1	1077.0	1076.7
155°	1112.2	1111.3	1110.4	1109.6	1108.7	1108.5	1108.3	1108.0	1107.8	1107.7	1107.7
157.5°	1139.9	1139.0	1138.1	1137.2	1136.3	1136.1	1135.9	1135.6	1135.4	1135.3	1135.4
160°	1165.4	1164.3	1163.2	1162.1	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.2
162.5°	1189.2	1188.1	1187.0	1185.9	1184.8	1184.6	1184.4	1184.1	1183.9	1183.8	1184.1
165°	1208.8	1207.5	1206.2	1204.8	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.8
167.5°	1225.6	1224.3	1223.0	1221.6	1220.3	1220.1	1219.9	1219.6	1219.4	1219.3	1219.7
170°	1239.3	1237.8	1236.3	1234.7	1233.2	1233.2	1233.2	1233.2	1233.2	1233.2	1233.6
172.5°	1249.3	1248.0	1246.7	1245.3	1244.0	1244.0	1244.0	1244.0	1244.0	1244.0	1244.4
175°	1256.2	1254.9	1253.6	1252.3	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.4
177.5°	1260.1	1258.8	1257.5	1256.2	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1255.3
180°	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9	1257.9

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1044.3	1044.3	1044.3	1044.3
2.5°	1022.1	1025.1	1035.2	1047.4
5°	1001.8	1009.9	1024.1	1043.3
7.5°	979.6	991.7	1012.0	1036.2
10°	954.3	971.5	996.8	1027.1
12.5°	927.0	949.2	981.6	1013.0
15°	909.8	932.0	961.4	995.8
17.5°	876.4	902.7	933.0	981.6
20°	842.0	871.3	910.8	959.3
22.5°	815.6	847.0	884.5	936.1
25°	784.3	816.7	857.1	910.8
27.5°	750.9	783.3	828.8	885.5
30°	725.6	756.9	800.5	861.2
32.5°	695.2	725.6	771.1	834.9
35°	660.8	695.2	738.7	803.5
37.5°	634.5	665.9	711.4	773.1
40°	606.2	633.5	678.0	738.7
42.5°	575.8	606.2	644.6	705.3
45°	547.5	569.7	609.2	666.9
47.5°	517.1	542.4	572.8	617.3
50°	484.7	506.0	539.4	569.7
52.5°	453.4	470.6	498.9	522.2
55°	420.0	437.2	458.4	472.6
57.5°	388.6	400.7	414.9	424.0
60°	350.1	362.3	371.4	380.5
62.5°	315.7	324.8	329.9	335.0
65°	280.3	285.4	288.4	292.5
67.5°	241.9	246.9	247.9	254.0
70°	206.4	207.5	209.5	212.5
72.5°	173.0	175.1	174.1	176.1
75°	138.6	140.7	138.6	140.7
77.5°	105.2	107.3	107.3	110.3
80°	75.9	76.9	77.9	77.9
82.5°	49.6	52.6	50.6	51.6
85°	28.3	29.3	29.3	30.4
87.5°	13.2	14.2	13.2	15.2
90°	7.6	5.4	3.2	1.0
92.5°	33.6	32.3	30.9	29.6
95°	62.9	61.4	59.8	58.3
97.5°	99.1	98.0	96.9	95.8
100°	138.3	137.0	135.7	134.4
102.5°	180.8	180.1	179.5	178.8
105°	223.6	223.2	222.7	222.3
107.5°	274.4	274.1	273.9	273.7
110°	322.4	322.0	321.5	321.1

TEST NUMBER: P1031862

CATALOG NUMBER: S123DIW-B775D1030UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	371.2	370.9	370.7	370.5
115°	421.9	421.3	420.6	420.0
117.5°	471.0	470.7	470.5	470.3
120°	520.7	519.4	518.1	516.8
122.5°	567.9	567.0	566.1	565.2
125°	616.6	615.9	615.3	614.6
127.5°	664.0	662.7	661.4	660.1
130°	710.8	709.0	707.3	705.5
132.5°	756.3	754.5	752.8	751.0
135°	801.3	800.0	798.7	797.4
137.5°	843.2	842.1	841.0	839.9
140°	887.7	886.6	885.5	884.4
142.5°	928.2	927.1	926.0	924.9
145°	968.7	968.2	967.8	967.4
147.5°	1006.6	1005.7	1004.8	1003.9
150°	1043.8	1043.3	1042.9	1042.5
152.5°	1076.0	1075.4	1074.7	1074.1
155°	1107.7	1107.7	1107.7	1107.7
157.5°	1135.6	1135.9	1136.1	1136.3
160°	1161.7	1162.1	1162.6	1163.0
162.5°	1184.8	1185.4	1186.1	1186.7
165°	1204.5	1205.2	1205.8	1206.5
167.5°	1220.6	1221.5	1222.4	1223.3
170°	1234.5	1235.4	1236.2	1237.1
172.5°	1245.3	1246.2	1247.1	1248.0
175°	1252.3	1253.2	1254.0	1254.9
177.5°	1256.2	1257.1	1258.0	1258.9
180°	1257.9	1257.9	1257.9	1257.9

(END OF REPORT)