

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032164

Luminaire Tested: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032164
REPORT IS A COMBINATION OF REPORTS P994141 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1165D755UB35-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7689.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	97	93	90	94	90	87	84	79	77	74	68	67	65	59	58	56
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	50	49
3	85	76	68	63	79	71	65	60	62	58	54	55	51	48	47	45	42
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37
5	72	60	52	47	67	57	50	45	50	45	40	44	40	37	39	35	33
6	66	54	47	41	62	51	44	39	46	40	36	40	36	32	35	32	29
7	61	49	42	36	57	47	40	35	42	36	32	37	32	29	32	29	26
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21
10	50	38	31	26	47	36	30	25	32	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19894	19894	19894	19894
5°	19909	22912	19960	16998
10°	19732	27657	19819	14847
15°	19530	31390	19530	13091
20°	19129	33859	19237	11613
25°	18837	32168	18799	10596
30°	18495	22288	18457	9602
35°	18085	14310	18002	8853
40°	17573	10105	17487	8107
45°	16684	8086	16662	7381
50°	15593	6764	15541	6532
55°	14363	5575	14249	5537
60°	13159	4609	13026	4709
65°	11744	3688	11818	3991
70°	10437	2562	10716	3227
75°	8848	1900	9209	2481
80°	7047	1261	7644	1860
85°	5014	596	5475	1157

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26558 cd/sqm

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.5	2.4
10°-20°	568.1	7.4
20°-30°	894.8	11.6
30°-40°	930.5	12.1
40°-50°	796.0	10.4
50°-60°	606.9	7.9
60°-70°	388.8	5.1
70°-80°	186.3	2.4
80°-90°	51.0	0.7
90°-100°	35.7	0.5
100°-110°	172.5	2.2
110°-120°	422.8	5.5
120°-130°	536.7	7.0
130°-140°	573.4	7.5
140°-150°	536.2	7.0
150°-160°	432.5	5.6
160°-170°	279.1	3.6
170°-180°	96.2	1.3
0°-30°	1644.5	21.4
0°-40°	2574.9	33.5
0°-60°	3977.9	51.7
0°-90°	4604.0	59.9
90°-120°	631.0	8.2
90°-150°	2277.2	29.6
90°-180°	3085.0	40.1
0°-180°	7689.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1848	1848	1848	1848	1848	
5°	1847	2195	1851	1628	1847	175
15°	1764	3119	1764	1301	1764	496
25°	1604	3214	1601	1059	1604	739
35°	1400	1394	1394	862	1400	876
45°	1123	744	1122	679	1123	865
55°	793	467	786	464	793	710
65°	486	269	489	291	486	485
75°	233	114	242	149	233	251
85°	52	27	57	52	52	58
90°	1	23	1	23	1	5
95°	46	29	46	29	46	55
105°	224	33	224	33	224	238
115°	420	442	420	442	420	415
125°	592	604	592	604	592	529
135°	738	745	738	745	738	568
145°	851	859	851	859	851	533
155°	938	936	938	936	938	432
165°	989	986	989	986	989	279
175°	1012	1008	1012	1008	1012	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1852.9	1865.6	1875.1	1881.4	1897.2	1906.7	1914.6	1928.9	1928.9	1932.0	1938.3
5°	1846.6	1873.5	1892.5	1917.8	1951.0	1966.8	1989.0	2008.0	2034.9	2049.1	2063.3
7.5°	1832.3	1870.3	1909.9	1947.8	1996.9	2028.5	2050.7	2099.7	2134.6	2177.3	2210.5
10°	1813.3	1865.6	1916.2	1974.7	2041.2	2088.7	2121.9	2186.8	2253.2	2313.4	2364.0
12.5°	1789.6	1852.9	1925.7	1996.9	2090.2	2137.7	2191.5	2272.2	2367.2	2443.1	2511.1
15°	1764.3	1837.1	1919.4	2006.4	2123.5	2189.9	2267.5	2365.6	2471.6	2580.8	2674.1
17.5°	1724.7	1816.5	1908.3	2034.9	2172.5	2212.1	2278.5	2413.0	2544.4	2642.5	2756.4
20°	1685.2	1788.0	1903.5	2017.5	2166.2	2258.0	2319.7	2462.1	2602.9	2721.6	2830.8
22.5°	1648.8	1756.4	1876.6	2020.6	2159.9	2251.6	2329.2	2477.9	2640.9	2773.8	2908.3
25°	1604.5	1721.6	1854.5	1990.6	2159.9	2229.5	2314.9	2487.4	2659.9	2813.4	2979.5
27.5°	1557.0	1675.7	1807.0	1946.3	2101.3	2204.2	2288.0	2473.2	2683.6	2848.2	3019.1
30°	1509.5	1631.4	1758.0	1883.0	2057.0	2155.1	2251.6	2455.8	2696.3	2884.6	3015.9
32.5°	1463.6	1566.5	1691.5	1813.3	1985.8	2093.4	2202.6	2438.4	2701.0	2859.3	2922.5
35°	1400.4	1508.0	1609.2	1739.0	1913.0	2019.0	2147.2	2436.8	2680.5	2778.6	2746.9
37.5°	1341.8	1432.0	1528.5	1644.0	1822.8	1960.5	2093.4	2395.6	2612.4	2618.7	2439.9
40°	1276.9	1351.3	1432.0	1553.8	1746.9	1883.0	2027.0	2332.3	2489.0	2395.6	2080.8
42.5°	1202.6	1269.0	1332.3	1451.0	1661.4	1813.3	1968.4	2253.2	2310.2	2095.0	1767.5
45°	1123.4	1177.2	1235.8	1360.8	1571.2	1721.6	1876.6	2131.4	2072.8	1769.0	1457.3
47.5°	1041.2	1087.1	1144.0	1257.9	1474.7	1628.2	1775.4	1957.3	1808.6	1482.6	1221.6
50°	958.9	995.3	1050.7	1167.8	1376.6	1515.9	1651.9	1770.6	1561.8	1272.2	1009.5
52.5°	878.2	906.7	963.6	1063.3	1265.9	1398.8	1496.9	1542.8	1330.7	1050.7	876.6
55°	792.7	824.4	862.4	963.6	1164.6	1262.7	1327.6	1326.0	1107.6	890.8	724.7
57.5°	710.5	738.9	772.2	873.4	1036.4	1102.9	1158.3	1131.4	924.1	729.5	621.9
60°	637.7	653.5	689.9	775.3	898.8	955.7	987.4	941.5	754.8	615.5	514.3
62.5°	558.6	574.4	604.4	685.1	761.1	791.2	818.1	759.5	623.4	501.6	439.9
65°	485.8	506.3	525.3	590.2	631.3	667.7	664.6	615.5	487.4	408.2	357.6
67.5°	422.5	430.4	446.2	485.8	504.8	531.7	533.2	477.9	392.4	332.3	302.2
70°	354.4	362.4	373.4	392.4	405.1	411.4	408.2	359.2	295.9	259.5	232.6
72.5°	295.9	294.3	302.2	302.2	314.9	313.3	303.8	265.8	224.7	194.6	178.8
75°	232.6	234.2	235.8	232.6	227.9	221.5	213.6	185.1	158.2	144.0	129.8
77.5°	182.0	178.8	180.4	169.3	163.0	156.6	145.6	131.3	109.2	106.0	99.7
80°	129.8	128.2	126.6	121.8	107.6	101.3	93.4	85.4	80.7	77.5	76.0
82.5°	87.0	87.0	83.9	74.4	66.5	61.7	60.1	57.0	52.2	52.2	50.6
85°	52.2	50.6	47.5	38.0	33.2	33.2	33.2	33.2	30.1	30.1	28.5
87.5°	20.6	19.0	14.2	14.2	12.7	12.7	12.7	11.1	11.1	9.5	9.5
90°	0.8	2.5	4.1	5.8	7.5	8.3	9.4	11.5	13.7	15.8	18.0
92.5°	17.3	16.3	15.3	14.3	13.3	12.8	13.5	15.0	16.5	18.0	19.5
95°	45.9	39.0	32.2	25.3	18.4	15.0	15.9	17.8	19.6	21.5	23.3
97.5°	83.5	78.8	74.1	69.4	64.7	62.4	58.1	49.6	41.1	32.6	24.1
100°	127.1	130.4	133.8	137.1	140.4	142.1	129.1	103.0	76.9	50.9	24.8
102.5°	176.7	178.9	181.0	183.2	185.3	186.4	171.9	142.8	113.7	84.7	55.6
105°	224.0	225.8	227.7	229.5	231.4	232.3	224.8	209.7	194.7	179.6	164.6
107.5°	274.4	275.9	277.4	278.9	280.4	281.2	282.5	285.0	287.5	290.0	292.5
110°	324.8	326.1	327.5	328.8	330.1	330.8	331.7	333.6	335.4	337.3	339.1

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	372.9	374.1	375.3	376.4	377.6	378.2	379.1	380.9	382.8	384.6	386.4
115°	420.3	421.3	422.3	423.3	424.3	424.8	425.5	427.0	428.5	430.0	431.5
117.5°	466.9	468.1	469.2	470.4	471.5	472.1	472.5	473.4	474.2	475.1	475.9
120°	509.7	511.2	512.7	514.2	515.7	516.5	516.7	517.2	517.7	518.2	518.7
122.5°	553.3	554.5	555.7	556.8	558.0	558.6	558.9	559.6	560.3	560.9	561.6
125°	592.4	593.7	595.1	596.4	597.7	598.4	598.7	599.4	600.1	600.7	601.4
127.5°	631.5	632.8	634.2	635.5	636.8	637.5	637.9	638.8	639.6	640.5	641.3
130°	667.6	668.9	670.3	671.6	672.9	673.6	673.9	674.6	675.3	675.9	676.6
132.5°	702.2	703.5	704.9	706.2	707.5	708.2	708.5	709.0	709.5	710.0	710.5
135°	737.5	738.5	739.5	740.5	741.5	742.0	742.3	743.0	743.7	744.3	745.0
137.5°	767.6	768.9	770.3	771.6	772.9	773.6	773.8	774.1	774.4	774.8	775.1
140°	797.7	798.7	799.7	800.7	801.7	802.2	802.4	802.9	803.4	803.9	804.4
142.5°	825.5	826.5	827.5	828.5	829.5	830.0	830.3	830.8	831.3	831.8	832.3
145°	851.1	852.3	853.4	854.6	855.7	856.3	856.5	856.8	857.1	857.5	857.8
147.5°	875.9	876.7	877.5	878.4	879.2	879.6	879.8	880.1	880.4	880.8	881.1
150°	898.4	898.9	899.4	899.9	900.4	900.7	900.9	901.2	901.5	901.9	902.2
152.5°	918.7	918.9	919.1	919.2	919.4	919.5	919.6	919.7	919.9	920.0	920.2
155°	937.5	937.2	936.8	936.5	936.2	936.0	936.1	936.3	936.4	936.6	936.8
157.5°	952.5	952.5	952.5	952.5	952.5	952.5	952.4	952.3	952.1	952.0	951.8
160°	966.1	965.9	965.7	965.6	965.4	965.3	965.2	965.1	964.9	964.8	964.6
162.5°	978.9	978.4	977.9	977.4	976.9	976.6	976.5	976.4	976.2	976.1	975.9
165°	988.6	988.1	987.6	987.1	986.6	986.4	986.3	986.1	986.0	985.8	985.6
167.5°	996.9	996.2	995.6	994.9	994.2	993.9	993.9	993.9	993.9	993.9	993.9
170°	1003.7	1003.0	1002.4	1001.7	1001.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
172.5°	1008.2	1007.4	1006.5	1005.7	1004.8	1004.4	1004.5	1004.7	1004.8	1005.0	1005.2
175°	1011.9	1011.1	1010.3	1009.4	1008.6	1008.2	1008.3	1008.4	1008.6	1008.7	1008.9
177.5°	1013.4	1012.6	1011.8	1010.9	1010.1	1009.7	1009.8	1009.9	1010.1	1010.2	1010.4
180°	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1951.0	1951.0	1965.2	1979.5	1971.6	1976.3	1993.7	1987.4	2000.1	1998.5	2003.2
5°	2098.2	2115.6	2129.8	2159.9	2164.6	2159.9	2189.9	2197.8	2212.1	2194.7	2202.6
7.5°	2264.3	2300.7	2335.5	2379.8	2394.1	2397.2	2413.0	2435.2	2454.2	2419.4	2436.8
10°	2425.7	2481.1	2552.3	2591.8	2626.7	2639.3	2652.0	2666.2	2688.4	2708.9	2693.1
12.5°	2599.8	2680.5	2748.5	2819.7	2862.4	2857.7	2894.1	2903.6	2921.0	2925.7	2932.0
15°	2742.2	2856.1	2898.8	3004.8	3014.3	3046.0	3087.1	3123.5	3128.3	3118.8	3118.8
17.5°	2878.2	2976.3	3052.3	3137.7	3155.1	3182.0	3234.3	3251.7	3258.0	3256.4	3256.4
20°	2989.0	3053.9	3182.0	3253.3	3281.7	3316.5	3352.9	3375.1	3379.8	3386.2	3376.7
22.5°	3061.8	3159.9	3264.3	3322.9	3346.6	3359.3	3383.0	3389.3	3381.4	3383.0	3384.6
25°	3118.8	3215.3	3278.6	3294.4	3292.8	3277.0	3259.6	3229.5	3226.4	3213.7	3188.4
27.5°	3134.6	3171.0	3163.1	3098.2	3033.3	3027.0	2922.5	2865.6	2800.7	2810.2	2773.8
30°	3049.1	3001.7	2889.3	2724.8	2656.7	2546.0	2428.9	2307.0	2259.6	2207.3	2303.9
32.5°	2840.3	2671.0	2471.6	2258.0	2144.0	2045.9	1920.9	1832.3	1781.7	1739.0	1821.3
35°	2525.4	2261.1	1996.9	1794.4	1701.0	1612.4	1495.3	1451.0	1387.7	1394.0	1401.9
37.5°	2120.3	1829.2	1629.8	1430.4	1368.7	1332.3	1246.9	1178.8	1156.7	1150.3	1150.3
40°	1740.6	1501.6	1324.4	1167.8	1120.3	1090.2	1022.2	990.5	966.8	960.5	968.4
42.5°	1439.9	1235.8	1098.1	993.7	960.5	922.5	894.0	854.5	849.7	838.6	852.9
45°	1208.9	1031.7	928.8	852.9	824.4	810.1	778.5	754.8	745.3	743.7	754.8
47.5°	1025.3	887.7	797.5	750.0	727.9	713.6	686.7	677.2	667.7	670.9	666.2
50°	860.8	757.9	699.4	656.7	642.4	628.2	610.8	601.3	596.5	596.5	595.0
52.5°	738.9	653.5	615.5	576.0	569.6	561.7	542.7	536.4	528.5	526.9	533.2
55°	632.9	574.4	536.4	512.7	506.3	490.5	482.6	474.7	469.9	466.8	468.4
57.5°	541.2	496.8	471.5	451.0	439.9	433.6	419.3	417.7	414.6	414.6	413.0
60°	465.2	433.6	403.5	390.8	382.9	375.0	373.4	363.9	359.2	362.4	360.8
62.5°	394.0	368.7	351.3	337.0	332.3	326.0	321.2	318.0	313.3	314.9	314.9
65°	329.1	308.6	295.9	283.2	281.7	275.3	273.7	270.6	270.6	269.0	272.2
67.5°	270.6	256.3	245.3	237.3	232.6	234.2	227.9	223.1	223.1	221.5	226.3
70°	215.2	207.3	196.2	186.7	180.4	180.4	172.5	170.9	170.9	170.9	169.3
72.5°	166.1	151.9	147.2	144.0	144.0	144.0	140.8	140.8	139.2	140.8	139.2
75°	123.4	121.8	118.7	117.1	117.1	115.5	113.9	113.9	113.9	113.9	113.9
77.5°	96.5	96.5	93.4	91.8	91.8	91.8	90.2	90.2	88.6	88.6	88.6
80°	71.2	71.2	68.0	68.0	68.0	66.5	66.5	66.5	68.0	66.5	66.5
82.5°	49.1	49.1	47.5	49.1	47.5	45.9	45.9	45.9	44.3	45.9	45.9
85°	28.5	28.5	26.9	25.3	26.9	26.9	25.3	26.9	25.3	26.9	25.3
87.5°	11.1	9.5	9.5	9.5	7.9	9.5	7.9	7.9	9.5	7.9	9.5
90°	18.7	19.4	20.1	20.8	21.1	21.3	21.6	21.9	22.3	22.6	22.3
92.5°	20.7	21.9	23.0	24.2	24.8	24.9	25.1	25.2	25.4	25.6	25.4
95°	24.5	25.7	26.8	28.0	28.6	28.6	28.6	28.6	28.6	28.6	28.6
97.5°	25.4	26.8	28.1	29.4	30.1	30.2	30.3	30.5	30.6	30.8	30.6
100°	26.1	27.5	28.8	30.1	30.8	30.9	31.1	31.2	31.4	31.6	31.4
102.5°	50.1	44.6	39.1	33.6	30.8	31.0	31.3	31.6	32.0	32.3	32.0
105°	135.0	105.5	75.9	46.4	31.6	31.8	32.1	32.4	32.8	33.1	32.8
107.5°	266.8	241.0	215.3	189.6	176.7	165.8	143.9	122.0	100.1	78.2	100.1
110°	333.6	328.1	322.6	317.1	314.3	302.3	278.4	254.5	230.6	206.7	230.6

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	387.9	389.4	390.9	392.4	393.2	393.0	392.7	392.4	392.0	391.7	392.0
115°	433.2	434.9	436.6	438.3	439.1	439.4	440.1	440.8	441.4	442.1	441.4
117.5°	477.2	478.6	479.9	481.2	481.9	482.0	482.2	482.3	482.5	482.7	482.5
120°	520.1	521.4	522.8	524.1	524.8	524.8	524.8	524.8	524.8	524.8	524.8
122.5°	562.4	563.3	564.1	565.0	565.4	565.5	565.6	565.8	565.9	566.1	565.9
125°	601.8	602.1	602.5	602.8	603.0	603.2	603.5	603.8	604.2	604.5	604.2
127.5°	641.8	642.3	642.8	643.3	643.6	643.4	643.1	642.7	642.4	642.0	642.4
130°	677.3	677.9	678.6	679.3	679.6	679.4	679.1	678.8	678.4	678.1	678.4
132.5°	711.2	711.8	712.5	713.2	713.5	713.2	712.7	712.2	711.7	711.2	711.7
135°	745.5	746.0	746.5	747.0	747.3	747.0	746.5	746.0	745.5	745.0	745.5
137.5°	775.9	776.8	777.6	778.5	778.9	778.7	778.4	778.1	777.7	777.4	777.7
140°	805.1	805.7	806.4	807.1	807.4	807.2	806.9	806.6	806.2	805.9	806.2
142.5°	832.8	833.3	833.8	834.3	834.5	834.3	833.8	833.3	832.8	832.3	832.8
145°	858.1	858.5	858.8	859.1	859.3	859.3	859.3	859.3	859.3	859.3	859.3
147.5°	881.4	881.8	882.1	882.4	882.6	882.2	881.4	880.5	879.7	878.9	879.7
150°	902.5	902.9	903.2	903.5	903.7	903.4	902.9	902.4	901.9	901.4	901.9
152.5°	920.9	921.5	922.2	922.9	923.2	922.8	922.0	921.1	920.3	919.5	920.3
155°	937.6	938.4	939.3	940.1	940.5	940.0	939.0	938.0	937.0	936.0	937.0
157.5°	952.8	953.8	954.8	955.8	956.3	955.6	954.3	953.0	951.6	950.3	951.6
160°	965.6	966.6	967.6	968.6	969.1	968.5	967.3	966.2	965.0	963.8	965.0
162.5°	977.1	978.2	979.4	980.5	981.1	980.6	979.6	978.6	977.6	976.6	977.6
165°	986.9	988.3	989.6	990.9	991.6	991.0	989.9	988.7	987.6	986.4	987.6
167.5°	995.2	996.6	997.9	999.2	999.9	999.2	997.9	996.6	995.2	993.9	995.2
170°	1002.0	1003.4	1004.7	1006.0	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1002.0
172.5°	1006.5	1007.9	1009.2	1010.5	1011.2	1010.4	1008.9	1007.4	1005.9	1004.4	1005.9
175°	1010.1	1011.3	1012.4	1013.6	1014.2	1013.5	1012.2	1010.9	1009.5	1008.2	1009.5
177.5°	1011.7	1013.1	1014.4	1015.7	1016.4	1015.6	1013.9	1012.2	1010.6	1008.9	1010.6
180°	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1995.3	1985.8	1979.5	1974.7	1970.0	1984.2	1965.2	1944.7	1930.4	1920.9	1917.8
5°	2204.2	2183.6	2166.2	2152.0	2155.1	2155.1	2121.9	2085.5	2053.9	2036.4	2017.5
7.5°	2446.3	2424.1	2389.3	2381.4	2375.1	2335.5	2302.3	2235.8	2196.3	2156.7	2121.9
10°	2686.8	2658.3	2625.1	2614.0	2598.2	2549.1	2498.5	2413.0	2364.0	2291.2	2245.3
12.5°	2911.5	2876.7	2843.4	2835.5	2811.8	2769.1	2682.0	2593.4	2509.6	2432.0	2351.3
15°	3099.8	3090.3	3039.6	3008.0	2955.8	2897.2	2878.2	2758.0	2652.0	2571.3	2425.7
17.5°	3258.0	3213.7	3166.2	3145.7	3125.1	3057.0	2989.0	2865.6	2751.7	2633.0	2539.6
20°	3384.6	3335.5	3302.3	3272.2	3262.7	3185.2	3077.6	2968.4	2843.4	2710.5	2588.7
22.5°	3390.9	3384.6	3362.4	3345.0	3326.0	3275.4	3190.0	3053.9	2921.0	2775.4	2615.6
25°	3259.6	3250.1	3313.4	3297.6	3310.2	3291.2	3245.3	3131.4	2976.3	2805.5	2644.1
27.5°	2864.0	2960.5	3060.2	3095.0	3118.8	3186.8	3208.9	3145.7	3020.7	2838.7	2658.3
30°	2326.0	2454.2	2615.6	2702.6	2769.1	2895.6	3060.2	3080.8	3022.2	2876.7	2655.1
32.5°	1826.0	1943.1	2072.8	2175.7	2264.3	2523.8	2745.3	2905.1	2933.6	2857.7	2663.0
35°	1471.6	1522.2	1645.6	1743.7	1864.0	2085.5	2346.6	2604.5	2778.6	2788.1	2639.3
37.5°	1213.6	1240.5	1348.1	1403.5	1474.7	1669.3	1913.0	2250.1	2520.6	2648.8	2572.9
40°	1004.8	1066.5	1128.2	1159.8	1210.5	1345.0	1579.2	1843.4	2178.9	2416.2	2470.0
42.5°	871.9	898.8	938.3	982.6	1014.3	1131.4	1288.0	1530.1	1832.3	2163.0	2311.8
45°	769.0	778.5	819.6	848.1	881.4	963.6	1074.4	1276.9	1542.8	1868.7	2121.9
47.5°	683.6	702.6	724.7	742.1	764.3	827.6	922.5	1069.6	1303.8	1595.0	1867.1
50°	607.6	618.7	647.2	655.1	670.9	715.2	788.0	900.3	1093.4	1326.0	1607.6
52.5°	536.4	557.0	568.1	579.1	593.4	629.8	677.2	769.0	914.6	1132.9	1371.9
55°	481.0	487.4	503.2	512.7	523.7	549.1	590.2	658.2	772.2	946.2	1172.5
57.5°	427.2	427.2	443.1	451.0	462.0	481.0	517.4	569.6	651.9	781.7	989.0
60°	370.3	371.8	384.5	394.0	397.2	416.2	446.2	487.4	550.6	645.6	814.9
62.5°	319.6	327.5	333.9	337.0	348.1	359.2	384.5	413.0	457.3	541.2	661.4
65°	276.9	278.5	283.2	286.4	291.1	303.8	322.8	341.8	379.8	441.5	539.6
67.5°	227.9	234.2	240.5	240.5	245.3	251.6	270.6	286.4	314.9	351.3	417.7
70°	170.9	174.1	183.5	188.3	194.6	205.7	215.2	224.7	246.8	273.7	324.4
72.5°	142.4	142.4	145.6	147.2	147.2	155.1	169.3	178.8	189.9	208.9	243.7
75°	113.9	113.9	118.7	117.1	120.3	123.4	125.0	131.3	137.7	151.9	172.5
77.5°	90.2	91.8	91.8	93.4	93.4	94.9	96.5	99.7	102.9	110.8	120.3
80°	66.5	68.0	68.0	69.6	69.6	71.2	72.8	74.4	77.5	80.7	85.4
82.5°	45.9	47.5	47.5	49.1	47.5	49.1	50.6	50.6	52.2	55.4	57.0
85°	26.9	26.9	28.5	26.9	26.9	26.9	28.5	28.5	30.1	34.8	34.8
87.5°	7.9	9.5	7.9	9.5	9.5	9.5	9.5	11.1	11.1	12.7	14.2
90°	21.9	21.6	21.3	21.1	20.8	20.1	19.4	18.7	18.0	15.8	13.7
92.5°	25.2	25.1	24.9	24.8	24.2	23.0	21.9	20.7	19.5	18.0	16.5
95°	28.6	28.6	28.6	28.6	28.0	26.8	25.7	24.5	23.3	21.5	19.6
97.5°	30.5	30.3	30.2	30.1	29.4	28.1	26.8	25.4	24.1	32.6	41.1
100°	31.2	31.1	30.9	30.8	30.1	28.8	27.5	26.1	24.8	50.9	76.9
102.5°	31.6	31.3	31.0	30.8	33.6	39.1	44.6	50.1	55.6	84.7	113.7
105°	32.4	32.1	31.8	31.6	46.4	75.9	105.5	135.0	164.6	179.6	194.7
107.5°	122.0	143.9	165.8	176.7	189.6	215.3	241.0	266.8	292.5	290.0	287.5
110°	254.5	278.4	302.3	314.3	317.1	322.6	328.1	333.6	339.1	337.3	335.4

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	392.4	392.7	393.0	393.2	392.4	390.9	389.4	387.9	386.4	384.6	382.8
115°	440.8	440.1	439.4	439.1	438.3	436.6	434.9	433.2	431.5	430.0	428.5
117.5°	482.3	482.2	482.0	481.9	481.2	479.9	478.6	477.2	475.9	475.1	474.2
120°	524.8	524.8	524.8	524.8	524.1	522.8	521.4	520.1	518.7	518.2	517.7
122.5°	565.8	565.6	565.5	565.4	565.0	564.1	563.3	562.4	561.6	560.9	560.3
125°	603.8	603.5	603.2	603.0	602.8	602.5	602.1	601.8	601.4	600.7	600.1
127.5°	642.7	643.1	643.4	643.6	643.3	642.8	642.3	641.8	641.3	640.5	639.6
130°	678.8	679.1	679.4	679.6	679.3	678.6	677.9	677.3	676.6	675.9	675.3
132.5°	712.2	712.7	713.2	713.5	713.2	712.5	711.8	711.2	710.5	710.0	709.5
135°	746.0	746.5	747.0	747.3	747.0	746.5	746.0	745.5	745.0	744.3	743.7
137.5°	778.1	778.4	778.7	778.9	778.5	777.6	776.8	775.9	775.1	774.8	774.4
140°	806.6	806.9	807.2	807.4	807.1	806.4	805.7	805.1	804.4	803.9	803.4
142.5°	833.3	833.8	834.3	834.5	834.3	833.8	833.3	832.8	832.3	831.8	831.3
145°	859.3	859.3	859.3	859.3	859.1	858.8	858.5	858.1	857.8	857.5	857.1
147.5°	880.5	881.4	882.2	882.6	882.4	882.1	881.8	881.4	881.1	880.8	880.4
150°	902.4	902.9	903.4	903.7	903.5	903.2	902.9	902.5	902.2	901.9	901.5
152.5°	921.1	922.0	922.8	923.2	922.9	922.2	921.5	920.9	920.2	920.0	919.9
155°	938.0	939.0	940.0	940.5	940.1	939.3	938.4	937.6	936.8	936.6	936.4
157.5°	953.0	954.3	955.6	956.3	955.8	954.8	953.8	952.8	951.8	952.0	952.1
160°	966.2	967.3	968.5	969.1	968.6	967.6	966.6	965.6	964.6	964.8	964.9
162.5°	978.6	979.6	980.6	981.1	980.5	979.4	978.2	977.1	975.9	976.1	976.2
165°	988.7	989.9	991.0	991.6	990.9	989.6	988.3	986.9	985.6	985.8	986.0
167.5°	996.6	997.9	999.2	999.9	999.2	997.9	996.6	995.2	993.9	993.9	993.9
170°	1003.4	1004.7	1006.0	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1000.7	1000.7
172.5°	1007.4	1008.9	1010.4	1011.2	1010.5	1009.2	1007.9	1006.5	1005.2	1005.0	1004.8
175°	1010.9	1012.2	1013.5	1014.2	1013.6	1012.4	1011.3	1010.1	1008.9	1008.7	1008.6
177.5°	1012.2	1013.9	1015.6	1016.4	1015.7	1014.4	1013.1	1011.7	1010.4	1010.2	1010.1
180°	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1913.0	1905.1	1897.2	1897.2	1879.8	1864.0	1856.1	1859.2	1849.7	1837.1	1824.4
5°	1996.9	1965.2	1958.9	1941.5	1917.8	1884.5	1867.1	1851.3	1832.3	1807.0	1783.3
7.5°	2074.4	2033.3	2011.1	1993.7	1947.8	1902.0	1864.0	1838.7	1805.4	1767.5	1739.0
10°	2175.7	2099.7	2076.0	2036.4	1971.6	1906.7	1862.4	1821.3	1775.4	1731.1	1693.1
12.5°	2256.4	2169.4	2125.1	2085.5	2001.6	1919.4	1845.0	1794.4	1739.0	1689.9	1640.9
15°	2348.2	2250.1	2172.5	2125.1	2019.0	1919.4	1835.5	1764.3	1702.6	1642.4	1599.7
17.5°	2392.5	2269.0	2234.2	2166.2	2012.7	1913.0	1810.2	1734.2	1659.9	1590.2	1539.6
20°	2462.1	2318.1	2231.1	2185.2	2049.1	1902.0	1781.7	1694.7	1617.1	1542.8	1489.0
22.5°	2466.8	2310.2	2253.2	2166.2	1998.5	1868.7	1756.4	1650.4	1560.2	1490.5	1435.2
25°	2455.8	2295.9	2216.8	2147.2	2008.0	1849.7	1705.7	1601.3	1512.7	1432.0	1367.1
27.5°	2451.0	2254.8	2180.4	2110.8	1954.2	1794.4	1675.7	1557.0	1455.7	1384.5	1318.1
30°	2444.7	2210.5	2120.3	2039.6	1895.6	1751.6	1609.2	1506.4	1409.8	1319.7	1253.2
32.5°	2403.5	2150.4	2058.6	1973.2	1818.1	1674.1	1561.8	1452.6	1348.1	1264.3	1204.1
35°	2390.9	2095.0	1974.7	1883.0	1731.1	1602.9	1484.2	1394.0	1295.9	1212.1	1140.9
37.5°	2354.5	2038.0	1908.3	1791.2	1633.0	1511.1	1424.1	1333.9	1239.0	1148.8	1091.8
40°	2291.2	1971.6	1824.4	1704.2	1541.2	1417.8	1337.1	1270.6	1177.2	1096.5	1026.9
42.5°	2197.8	1903.5	1745.3	1618.7	1438.3	1322.8	1256.4	1193.1	1114.0	1030.1	973.1
45°	2090.2	1813.3	1666.2	1525.4	1341.8	1229.5	1159.8	1121.9	1049.1	977.9	911.4
47.5°	1943.1	1720.0	1574.4	1428.8	1242.1	1132.9	1077.6	1039.6	989.0	911.4	857.6
50°	1758.0	1599.7	1462.1	1332.3	1144.0	1039.6	984.2	955.7	913.0	857.6	805.4
52.5°	1552.3	1460.5	1346.6	1226.3	1044.3	946.2	895.6	873.4	841.8	789.6	745.3
55°	1345.0	1305.4	1227.9	1109.2	939.9	859.2	814.9	786.4	762.7	724.7	686.7
57.5°	1159.8	1140.9	1087.1	995.3	852.9	769.0	731.0	712.0	693.1	664.6	626.6
60°	968.4	989.0	933.6	887.7	757.9	685.1	651.9	631.3	621.9	596.5	572.8
62.5°	802.2	821.2	789.6	754.8	663.0	598.1	577.5	558.6	552.2	530.1	506.3
65°	651.9	675.7	651.9	632.9	577.5	523.7	498.4	488.9	482.6	468.4	449.4
67.5°	519.0	542.7	531.7	507.9	490.5	446.2	432.0	422.5	419.3	408.2	392.4
70°	390.8	424.1	427.2	413.0	397.2	376.6	367.1	363.9	356.0	346.5	337.0
72.5°	281.7	319.6	321.2	321.2	311.7	311.7	302.2	297.5	297.5	288.0	276.9
75°	207.3	232.6	235.8	238.9	243.7	248.4	242.1	242.1	240.5	231.0	226.3
77.5°	137.7	159.8	167.7	178.8	185.1	185.1	188.3	191.5	188.3	183.5	180.4
80°	88.6	104.4	113.9	120.3	129.8	134.5	139.2	140.8	137.7	136.1	131.3
82.5°	58.5	63.3	68.0	76.0	87.0	94.9	94.9	93.4	96.5	94.9	93.4
85°	33.2	36.4	38.0	39.6	45.9	53.8	55.4	57.0	60.1	57.0	53.8
87.5°	12.7	14.2	14.2	14.2	17.4	19.0	23.7	30.1	28.5	25.3	25.3
90°	11.5	9.4	8.3	7.5	5.8	4.1	2.5	0.8	2.5	4.1	5.8
92.5°	15.0	13.5	12.8	13.3	14.3	15.3	16.3	17.3	16.3	15.3	14.3
95°	17.8	15.9	15.0	18.4	25.3	32.2	39.0	45.9	39.0	32.2	25.3
97.5°	49.6	58.1	62.4	64.7	69.4	74.1	78.8	83.5	78.8	74.1	69.4
100°	103.0	129.1	142.1	140.4	137.1	133.8	130.4	127.1	130.4	133.8	137.1
102.5°	142.8	171.9	186.4	185.3	183.2	181.0	178.9	176.7	178.9	181.0	183.2
105°	209.7	224.8	232.3	231.4	229.5	227.7	225.8	224.0	225.8	227.7	229.5
107.5°	285.0	282.5	281.2	280.4	278.9	277.4	275.9	274.4	275.9	277.4	278.9
110°	333.6	331.7	330.8	330.1	328.8	327.5	326.1	324.8	326.1	327.5	328.8

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	380.9	379.1	378.2	377.6	376.4	375.3	374.1	372.9	374.1	375.3	376.4
115°	427.0	425.5	424.8	424.3	423.3	422.3	421.3	420.3	421.3	422.3	423.3
117.5°	473.4	472.5	472.1	471.5	470.4	469.2	468.1	466.9	468.1	469.2	470.4
120°	517.2	516.7	516.5	515.7	514.2	512.7	511.2	509.7	511.2	512.7	514.2
122.5°	559.6	558.9	558.6	558.0	556.8	555.7	554.5	553.3	554.5	555.7	556.8
125°	599.4	598.7	598.4	597.7	596.4	595.1	593.7	592.4	593.7	595.1	596.4
127.5°	638.8	637.9	637.5	636.8	635.5	634.2	632.8	631.5	632.8	634.2	635.5
130°	674.6	673.9	673.6	672.9	671.6	670.3	668.9	667.6	668.9	670.3	671.6
132.5°	709.0	708.5	708.2	707.5	706.2	704.9	703.5	702.2	703.5	704.9	706.2
135°	743.0	742.3	742.0	741.5	740.5	739.5	738.5	737.5	738.5	739.5	740.5
137.5°	774.1	773.8	773.6	772.9	771.6	770.3	768.9	767.6	768.9	770.3	771.6
140°	802.9	802.4	802.2	801.7	800.7	799.7	798.7	797.7	798.7	799.7	800.7
142.5°	830.8	830.3	830.0	829.5	828.5	827.5	826.5	825.5	826.5	827.5	828.5
145°	856.8	856.5	856.3	855.7	854.6	853.4	852.3	851.1	852.3	853.4	854.6
147.5°	880.1	879.8	879.6	879.2	878.4	877.5	876.7	875.9	876.7	877.5	878.4
150°	901.2	900.9	900.7	900.4	899.9	899.4	898.9	898.4	898.9	899.4	899.9
152.5°	919.7	919.6	919.5	919.4	919.2	919.1	918.9	918.7	918.9	919.1	919.2
155°	936.3	936.1	936.0	936.2	936.5	936.8	937.2	937.5	937.2	936.8	936.5
157.5°	952.3	952.4	952.5	952.5	952.5	952.5	952.5	952.5	952.5	952.5	952.5
160°	965.1	965.2	965.3	965.4	965.6	965.7	965.9	966.1	965.9	965.7	965.6
162.5°	976.4	976.5	976.6	976.9	977.4	977.9	978.4	978.9	978.4	977.9	977.4
165°	986.1	986.3	986.4	986.6	987.1	987.6	988.1	988.6	988.1	987.6	987.1
167.5°	993.9	993.9	993.9	994.2	994.9	995.6	996.2	996.9	996.2	995.6	994.9
170°	1000.7	1000.7	1000.7	1001.0	1001.7	1002.4	1003.0	1003.7	1003.0	1002.4	1001.7
172.5°	1004.7	1004.5	1004.4	1004.8	1005.7	1006.5	1007.4	1008.2	1007.4	1006.5	1005.7
175°	1008.4	1008.3	1008.2	1008.6	1009.4	1010.3	1011.1	1011.9	1011.1	1010.3	1009.4
177.5°	1009.9	1009.8	1009.7	1010.1	1010.9	1011.8	1012.6	1013.4	1012.6	1011.8	1010.9
180°	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1824.4	1816.5	1813.3	1805.4	1786.4	1773.8	1759.5	1750.0	1751.6	1743.7	1748.5
5°	1767.5	1765.9	1754.8	1739.0	1712.1	1697.8	1672.5	1659.9	1653.5	1655.1	1645.6
7.5°	1720.0	1705.7	1697.8	1672.5	1647.2	1617.1	1596.6	1585.5	1576.0	1566.5	1560.2
10°	1666.2	1653.5	1640.9	1614.0	1579.2	1550.7	1522.2	1511.1	1496.9	1490.5	1485.8
12.5°	1609.2	1601.3	1585.5	1553.8	1514.3	1487.4	1454.2	1447.8	1428.8	1416.2	1413.0
15°	1557.0	1552.3	1523.8	1487.4	1447.8	1420.9	1392.4	1373.5	1341.8	1348.1	1337.1
17.5°	1501.6	1481.1	1463.6	1414.6	1395.6	1354.5	1321.2	1311.7	1289.6	1275.4	1261.1
20°	1439.9	1427.3	1405.1	1373.5	1327.6	1280.1	1254.8	1239.0	1226.3	1204.1	1197.8
22.5°	1381.4	1365.5	1346.6	1305.4	1265.9	1226.3	1191.5	1177.2	1161.4	1145.6	1136.1
25°	1335.5	1311.7	1291.2	1240.5	1201.0	1167.8	1145.6	1121.9	1099.7	1090.2	1087.1
27.5°	1264.3	1250.0	1229.5	1182.0	1145.6	1109.2	1088.6	1072.8	1049.1	1038.0	1028.5
30°	1218.4	1189.9	1166.2	1128.2	1091.8	1052.2	1033.3	1014.3	1000.0	985.8	974.7
32.5°	1156.7	1134.5	1115.5	1077.6	1041.2	1004.8	984.2	955.7	947.8	936.7	924.1
35°	1096.5	1082.3	1061.7	1020.6	981.0	955.7	933.6	906.7	897.2	889.3	878.2
37.5°	1039.6	1019.0	1004.8	965.2	930.4	900.3	882.9	860.8	854.5	845.0	837.0
40°	990.5	970.0	955.7	916.2	879.8	848.1	837.0	814.9	805.4	794.3	789.6
42.5°	935.2	917.7	898.8	870.3	832.3	800.7	778.5	765.8	753.2	748.4	738.9
45°	876.6	860.8	846.5	814.9	775.3	753.2	734.2	716.8	707.3	699.4	693.1
47.5°	826.0	811.7	792.7	757.9	726.3	705.7	686.7	669.3	659.8	650.3	642.4
50°	767.4	759.5	738.9	705.7	675.7	651.9	634.5	618.7	612.4	601.3	588.6
52.5°	715.2	701.0	683.6	656.7	629.8	601.3	577.5	568.1	557.0	550.6	539.6
55°	653.5	644.0	625.0	601.3	572.8	549.1	531.7	519.0	504.8	498.4	484.2
57.5°	601.3	583.9	574.4	544.3	517.4	493.7	481.0	468.4	452.5	443.1	436.7
60°	544.3	528.5	514.3	488.9	469.9	444.6	425.6	414.6	403.5	390.8	384.5
62.5°	488.9	476.3	458.9	438.3	414.6	394.0	379.8	363.9	357.6	344.9	340.2
65°	428.8	419.3	405.1	381.3	362.4	344.9	330.7	318.0	311.7	307.0	303.8
67.5°	375.0	362.4	352.9	332.3	311.7	297.5	289.6	281.7	273.7	269.0	264.2
70°	319.6	310.1	300.6	281.7	267.4	254.8	248.4	242.1	237.3	232.6	227.9
72.5°	262.7	257.9	248.4	235.8	224.7	215.2	210.4	202.5	197.8	189.9	186.7
75°	216.8	208.9	204.1	193.0	183.5	175.6	169.3	159.8	153.5	150.3	148.7
77.5°	170.9	167.7	161.4	151.9	147.2	139.2	129.8	126.6	123.4	123.4	121.8
80°	128.2	123.4	118.7	110.8	106.0	99.7	99.7	99.7	98.1	99.7	98.1
82.5°	87.0	83.9	80.7	76.0	74.4	74.4	76.0	76.0	76.0	76.0	76.0
85°	50.6	50.6	50.6	52.2	50.6	50.6	52.2	53.8	52.2	52.2	50.6
87.5°	23.7	23.7	25.3	25.3	26.9	26.9	26.9	26.9	26.9	26.9	28.5
90°	7.5	8.3	9.4	11.5	13.7	15.8	18.0	18.7	19.4	20.1	20.8
92.5°	13.3	12.8	13.5	15.0	16.5	18.0	19.5	20.7	21.9	23.0	24.2
95°	18.4	15.0	15.9	17.8	19.6	21.5	23.3	24.5	25.7	26.8	28.0
97.5°	64.7	62.4	58.1	49.6	41.1	32.6	24.1	25.4	26.8	28.1	29.4
100°	140.4	142.1	129.1	103.0	76.9	50.9	24.8	26.1	27.5	28.8	30.1
102.5°	185.3	186.4	171.9	142.8	113.7	84.7	55.6	50.1	44.6	39.1	33.6
105°	231.4	232.3	224.8	209.7	194.7	179.6	164.6	135.0	105.5	75.9	46.4
107.5°	280.4	281.2	282.5	285.0	287.5	290.0	292.5	266.8	241.0	215.3	189.6
110°	330.1	330.8	331.7	333.6	335.4	337.3	339.1	333.6	328.1	322.6	317.1

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	377.6	378.2	379.1	380.9	382.8	384.6	386.4	387.9	389.4	390.9	392.4
115°	424.3	424.8	425.5	427.0	428.5	430.0	431.5	433.2	434.9	436.6	438.3
117.5°	471.5	472.1	472.5	473.4	474.2	475.1	475.9	477.2	478.6	479.9	481.2
120°	515.7	516.5	516.7	517.2	517.7	518.2	518.7	520.1	521.4	522.8	524.1
122.5°	558.0	558.6	558.9	559.6	560.3	560.9	561.6	562.4	563.3	564.1	565.0
125°	597.7	598.4	598.7	599.4	600.1	600.7	601.4	601.8	602.1	602.5	602.8
127.5°	636.8	637.5	637.9	638.8	639.6	640.5	641.3	641.8	642.3	642.8	643.3
130°	672.9	673.6	673.9	674.6	675.3	675.9	676.6	677.3	677.9	678.6	679.3
132.5°	707.5	708.2	708.5	709.0	709.5	710.0	710.5	711.2	711.8	712.5	713.2
135°	741.5	742.0	742.3	743.0	743.7	744.3	745.0	745.5	746.0	746.5	747.0
137.5°	772.9	773.6	773.8	774.1	774.4	774.8	775.1	775.9	776.8	777.6	778.5
140°	801.7	802.2	802.4	802.9	803.4	803.9	804.4	805.1	805.7	806.4	807.1
142.5°	829.5	830.0	830.3	830.8	831.3	831.8	832.3	832.8	833.3	833.8	834.3
145°	855.7	856.3	856.5	856.8	857.1	857.5	857.8	858.1	858.5	858.8	859.1
147.5°	879.2	879.6	879.8	880.1	880.4	880.8	881.1	881.4	881.8	882.1	882.4
150°	900.4	900.7	900.9	901.2	901.5	901.9	902.2	902.5	902.9	903.2	903.5
152.5°	919.4	919.5	919.6	919.7	919.9	920.0	920.2	920.9	921.5	922.2	922.9
155°	936.2	936.0	936.1	936.3	936.4	936.6	936.8	937.6	938.4	939.3	940.1
157.5°	952.5	952.5	952.4	952.3	952.1	952.0	951.8	952.8	953.8	954.8	955.8
160°	965.4	965.3	965.2	965.1	964.9	964.8	964.6	965.6	966.6	967.6	968.6
162.5°	976.9	976.6	976.5	976.4	976.2	976.1	975.9	977.1	978.2	979.4	980.5
165°	986.6	986.4	986.3	986.1	986.0	985.8	985.6	986.9	988.3	989.6	990.9
167.5°	994.2	993.9	993.9	993.9	993.9	993.9	993.9	995.2	996.6	997.9	999.2
170°	1001.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1002.0	1003.4	1004.7	1006.0
172.5°	1004.8	1004.4	1004.5	1004.7	1004.8	1005.0	1005.2	1006.5	1007.9	1009.2	1010.5
175°	1008.6	1008.2	1008.3	1008.4	1008.6	1008.7	1008.9	1010.1	1011.3	1012.4	1013.6
177.5°	1010.1	1009.7	1009.8	1009.9	1010.1	1010.2	1010.4	1011.7	1013.1	1014.4	1015.7
180°	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1746.9	1748.5	1743.7	1734.2	1732.6	1735.8	1745.3	1742.1	1734.2	1748.5	1735.8
5°	1650.4	1642.4	1639.3	1642.4	1633.0	1628.2	1637.7	1633.0	1637.7	1639.3	1644.0
7.5°	1557.0	1558.6	1549.1	1550.7	1538.0	1541.2	1541.2	1541.2	1545.9	1549.1	1555.4
10°	1476.3	1479.5	1468.4	1470.0	1460.5	1454.2	1458.9	1468.4	1468.4	1468.4	1471.6
12.5°	1411.4	1397.2	1389.3	1387.7	1376.6	1373.5	1382.9	1386.1	1394.0	1394.0	1398.8
15°	1330.7	1327.6	1321.2	1321.2	1294.3	1300.7	1303.8	1314.9	1330.7	1318.1	1321.2
17.5°	1257.9	1250.0	1242.1	1239.0	1235.8	1226.3	1239.0	1237.4	1246.9	1248.5	1253.2
20°	1193.1	1186.7	1170.9	1172.5	1175.7	1161.4	1169.3	1169.3	1178.8	1188.3	1199.4
22.5°	1129.8	1123.4	1115.5	1118.7	1109.2	1106.0	1106.0	1114.0	1125.0	1132.9	1131.4
25°	1080.7	1069.6	1064.9	1060.2	1055.4	1058.6	1053.8	1061.7	1069.6	1074.4	1069.6
27.5°	1025.3	1020.6	1011.1	1006.4	998.4	1001.6	1004.8	1011.1	1015.9	1015.9	1020.6
30°	971.5	965.2	962.1	957.3	957.3	951.0	952.6	958.9	963.6	968.4	974.7
32.5°	919.3	914.6	909.8	909.8	906.7	905.1	903.5	913.0	913.0	922.5	922.5
35°	876.6	868.7	868.7	860.8	863.9	862.4	859.2	865.5	867.1	873.4	871.9
37.5°	829.1	829.1	826.0	818.1	811.7	813.3	821.2	821.2	826.0	824.4	829.1
40°	781.7	778.5	778.5	773.8	772.2	770.6	772.2	773.8	781.7	780.1	781.7
42.5°	734.2	735.8	727.9	727.9	727.9	723.1	724.7	726.3	729.5	732.6	737.4
45°	688.3	685.1	683.6	680.4	677.2	678.8	677.2	683.6	682.0	685.1	689.9
47.5°	639.3	634.5	632.9	626.6	626.6	629.8	628.2	632.9	634.5	639.3	636.1
50°	591.8	585.5	580.7	582.3	572.8	576.0	576.0	580.7	585.5	587.0	590.2
52.5°	536.4	534.8	533.2	525.3	523.7	522.2	523.7	525.3	531.7	536.4	538.0
55°	482.6	481.0	471.5	468.4	463.6	463.6	466.8	468.4	479.4	481.0	487.4
57.5°	433.6	428.8	417.7	416.2	416.2	416.2	411.4	417.7	420.9	428.8	428.8
60°	379.8	379.8	370.3	370.3	371.8	370.3	370.3	371.8	371.8	378.2	381.3
62.5°	337.0	335.5	335.5	332.3	330.7	332.3	330.7	330.7	332.3	337.0	341.8
65°	299.1	297.5	295.9	294.3	291.1	291.1	292.7	295.9	295.9	299.1	300.6
67.5°	262.7	262.7	259.5	259.5	257.9	256.3	257.9	256.3	262.7	262.7	264.2
70°	226.3	224.7	219.9	218.4	213.6	215.2	215.2	219.9	221.5	224.7	227.9
72.5°	182.0	182.0	178.8	175.6	177.2	174.1	174.1	175.6	175.6	180.4	182.0
75°	150.3	147.2	145.6	147.2	145.6	148.7	145.6	145.6	148.7	148.7	148.7
77.5°	123.4	123.4	121.8	121.8	123.4	121.8	123.4	123.4	123.4	121.8	123.4
80°	101.3	99.7	99.7	99.7	98.1	98.1	98.1	98.1	98.1	98.1	98.1
82.5°	76.0	76.0	74.4	76.0	76.0	74.4	76.0	74.4	74.4	76.0	76.0
85°	50.6	53.8	50.6	50.6	52.2	52.2	53.8	52.2	53.8	50.6	52.2
87.5°	26.9	28.5	28.5	26.9	26.9	28.5	28.5	28.5	30.1	26.9	28.5
90°	21.1	21.3	21.6	21.9	22.3	22.6	22.3	21.9	21.6	21.3	21.1
92.5°	24.8	24.9	25.1	25.2	25.4	25.6	25.4	25.2	25.1	24.9	24.8
95°	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6
97.5°	30.1	30.2	30.3	30.5	30.6	30.8	30.6	30.5	30.3	30.2	30.1
100°	30.8	30.9	31.1	31.2	31.4	31.6	31.4	31.2	31.1	30.9	30.8
102.5°	30.8	31.0	31.3	31.6	32.0	32.3	32.0	31.6	31.3	31.0	30.8
105°	31.6	31.8	32.1	32.4	32.8	33.1	32.8	32.4	32.1	31.8	31.6
107.5°	176.7	165.8	143.9	122.0	100.1	78.2	100.1	122.0	143.9	165.8	176.7
110°	314.3	302.3	278.4	254.5	230.6	206.7	230.6	254.5	278.4	302.3	314.3

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	393.2	393.0	392.7	392.4	392.0	391.7	392.0	392.4	392.7	393.0	393.2
115°	439.1	439.4	440.1	440.8	441.4	442.1	441.4	440.8	440.1	439.4	439.1
117.5°	481.9	482.0	482.2	482.3	482.5	482.7	482.5	482.3	482.2	482.0	481.9
120°	524.8	524.8	524.8	524.8	524.8	524.8	524.8	524.8	524.8	524.8	524.8
122.5°	565.4	565.5	565.6	565.8	565.9	566.1	565.9	565.8	565.6	565.5	565.4
125°	603.0	603.2	603.5	603.8	604.2	604.5	604.2	603.8	603.5	603.2	603.0
127.5°	643.6	643.4	643.1	642.7	642.4	642.0	642.4	642.7	643.1	643.4	643.6
130°	679.6	679.4	679.1	678.8	678.4	678.1	678.4	678.8	679.1	679.4	679.6
132.5°	713.5	713.2	712.7	712.2	711.7	711.2	711.7	712.2	712.7	713.2	713.5
135°	747.3	747.0	746.5	746.0	745.5	745.0	745.5	746.0	746.5	747.0	747.3
137.5°	778.9	778.7	778.4	778.1	777.7	777.4	777.7	778.1	778.4	778.7	778.9
140°	807.4	807.2	806.9	806.6	806.2	805.9	806.2	806.6	806.9	807.2	807.4
142.5°	834.5	834.3	833.8	833.3	832.8	832.3	832.8	833.3	833.8	834.3	834.5
145°	859.3	859.3	859.3	859.3	859.3	859.3	859.3	859.3	859.3	859.3	859.3
147.5°	882.6	882.2	881.4	880.5	879.7	878.9	879.7	880.5	881.4	882.2	882.6
150°	903.7	903.4	902.9	902.4	901.9	901.4	901.9	902.4	902.9	903.4	903.7
152.5°	923.2	922.8	922.0	921.1	920.3	919.5	920.3	921.1	922.0	922.8	923.2
155°	940.5	940.0	939.0	938.0	937.0	936.0	937.0	938.0	939.0	940.0	940.5
157.5°	956.3	955.6	954.3	953.0	951.6	950.3	951.6	953.0	954.3	955.6	956.3
160°	969.1	968.5	967.3	966.2	965.0	963.8	965.0	966.2	967.3	968.5	969.1
162.5°	981.1	980.6	979.6	978.6	977.6	976.6	977.6	978.6	979.6	980.6	981.1
165°	991.6	991.0	989.9	988.7	987.6	986.4	987.6	988.7	989.9	991.0	991.6
167.5°	999.9	999.2	997.9	996.6	995.2	993.9	995.2	996.6	997.9	999.2	999.9
170°	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1002.0	1003.4	1004.7	1006.0	1006.7
172.5°	1011.2	1010.4	1008.9	1007.4	1005.9	1004.4	1005.9	1007.4	1008.9	1010.4	1011.2
175°	1014.2	1013.5	1012.2	1010.9	1009.5	1008.2	1009.5	1010.9	1012.2	1013.5	1014.2
177.5°	1016.4	1015.6	1013.9	1012.2	1010.6	1008.9	1010.6	1012.2	1013.9	1015.6	1016.4
180°	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1748.5	1754.8	1748.5	1735.8	1748.5	1756.4	1764.3	1776.9	1783.3	1783.3	1792.8
5°	1648.8	1661.4	1656.7	1653.5	1666.2	1674.1	1686.8	1702.6	1720.0	1731.1	1743.7
7.5°	1560.2	1568.1	1576.0	1576.0	1588.7	1606.1	1625.0	1644.0	1666.2	1682.0	1691.5
10°	1482.6	1489.0	1493.7	1500.0	1519.0	1538.0	1563.3	1587.1	1606.1	1623.5	1639.3
12.5°	1408.3	1417.8	1428.8	1433.6	1447.8	1471.6	1495.3	1523.8	1553.8	1571.2	1587.1
15°	1337.1	1341.8	1354.5	1368.7	1381.4	1406.7	1436.7	1466.8	1492.1	1519.0	1533.3
17.5°	1264.3	1265.9	1299.1	1291.2	1332.3	1356.0	1371.9	1400.4	1441.5	1463.6	1485.8
20°	1193.1	1208.9	1223.1	1231.0	1253.2	1280.1	1326.0	1348.1	1381.4	1401.9	1420.9
22.5°	1137.7	1161.4	1161.4	1180.4	1191.5	1216.8	1250.0	1292.8	1329.2	1343.4	1370.3
25°	1088.6	1099.7	1118.7	1125.0	1145.6	1167.8	1189.9	1235.8	1275.4	1294.3	1313.3
27.5°	1025.3	1039.6	1064.9	1064.9	1091.8	1115.5	1142.4	1172.5	1212.1	1239.0	1259.5
30°	976.3	990.5	1001.6	1019.0	1030.1	1052.2	1099.7	1121.9	1156.7	1180.4	1205.7
32.5°	930.4	941.5	951.0	970.0	982.6	1007.9	1033.3	1072.8	1102.9	1125.0	1151.9
35°	879.8	890.8	903.5	917.7	936.7	960.5	984.2	1017.4	1047.5	1068.1	1090.2
37.5°	832.3	840.2	859.2	868.7	884.5	906.7	936.7	971.5	998.4	1014.3	1036.4
40°	786.4	792.7	807.0	824.4	835.5	852.9	884.5	914.6	947.8	966.8	984.2
42.5°	737.4	745.3	757.9	775.3	792.7	811.7	829.1	863.9	894.0	909.8	928.8
45°	694.6	699.4	708.9	726.3	743.7	757.9	784.8	816.5	845.0	857.6	878.2
47.5°	644.0	648.8	663.0	670.9	689.9	708.9	735.8	767.4	792.7	805.4	824.4
50°	591.8	596.5	606.0	623.4	636.1	656.7	680.4	707.3	738.9	756.3	767.4
52.5°	541.2	550.6	558.6	572.8	588.6	609.2	631.3	656.7	683.6	701.0	713.6
55°	490.5	498.4	507.9	515.8	534.8	553.8	579.1	602.9	626.6	642.4	656.7
57.5°	433.6	444.6	454.1	469.9	484.2	500.0	528.5	547.5	576.0	587.0	599.7
60°	384.5	395.6	403.5	416.2	428.8	449.4	468.4	492.1	515.8	530.1	545.9
62.5°	343.4	348.1	352.9	365.5	378.2	397.2	416.2	439.9	465.2	473.1	485.8
65°	302.2	307.0	314.9	326.0	335.5	346.5	367.1	386.1	409.8	422.5	427.2
67.5°	267.4	272.2	273.7	281.7	289.6	302.2	313.3	332.3	354.4	362.4	371.8
70°	227.9	235.8	237.3	243.7	246.8	254.8	267.4	281.7	299.1	313.3	321.2
72.5°	182.0	193.0	196.2	205.7	210.4	218.4	227.9	238.9	250.0	256.3	262.7
75°	148.7	151.9	153.5	161.4	169.3	180.4	185.1	191.5	201.0	208.9	215.2
77.5°	123.4	125.0	126.6	126.6	128.2	134.5	144.0	151.9	158.2	161.4	166.1
80°	99.7	98.1	98.1	99.7	99.7	99.7	102.9	113.9	117.1	125.0	123.4
82.5°	77.5	74.4	76.0	74.4	74.4	74.4	74.4	76.0	76.0	80.7	83.9
85°	50.6	52.2	50.6	50.6	49.1	50.6	49.1	49.1	47.5	47.5	45.9
87.5°	26.9	28.5	26.9	26.9	25.3	26.9	25.3	25.3	23.7	23.7	20.6
90°	20.8	20.1	19.4	18.7	18.0	15.8	13.7	11.5	9.4	8.3	7.5
92.5°	24.2	23.0	21.9	20.7	19.5	18.0	16.5	15.0	13.5	12.8	13.3
95°	28.0	26.8	25.7	24.5	23.3	21.5	19.6	17.8	15.9	15.0	18.4
97.5°	29.4	28.1	26.8	25.4	24.1	32.6	41.1	49.6	58.1	62.4	64.7
100°	30.1	28.8	27.5	26.1	24.8	50.9	76.9	103.0	129.1	142.1	140.4
102.5°	33.6	39.1	44.6	50.1	55.6	84.7	113.7	142.8	171.9	186.4	185.3
105°	46.4	75.9	105.5	135.0	164.6	179.6	194.7	209.7	224.8	232.3	231.4
107.5°	189.6	215.3	241.0	266.8	292.5	290.0	287.5	285.0	282.5	281.2	280.4
110°	317.1	322.6	328.1	333.6	339.1	337.3	335.4	333.6	331.7	330.8	330.1

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	392.4	390.9	389.4	387.9	386.4	384.6	382.8	380.9	379.1	378.2	377.6
115°	438.3	436.6	434.9	433.2	431.5	430.0	428.5	427.0	425.5	424.8	424.3
117.5°	481.2	479.9	478.6	477.2	475.9	475.1	474.2	473.4	472.5	472.1	471.5
120°	524.1	522.8	521.4	520.1	518.7	518.2	517.7	517.2	516.7	516.5	515.7
122.5°	565.0	564.1	563.3	562.4	561.6	560.9	560.3	559.6	558.9	558.6	558.0
125°	602.8	602.5	602.1	601.8	601.4	600.7	600.1	599.4	598.7	598.4	597.7
127.5°	643.3	642.8	642.3	641.8	641.3	640.5	639.6	638.8	637.9	637.5	636.8
130°	679.3	678.6	677.9	677.3	676.6	675.9	675.3	674.6	673.9	673.6	672.9
132.5°	713.2	712.5	711.8	711.2	710.5	710.0	709.5	709.0	708.5	708.2	707.5
135°	747.0	746.5	746.0	745.5	745.0	744.3	743.7	743.0	742.3	742.0	741.5
137.5°	778.5	777.6	776.8	775.9	775.1	774.8	774.4	774.1	773.8	773.6	772.9
140°	807.1	806.4	805.7	805.1	804.4	803.9	803.4	802.9	802.4	802.2	801.7
142.5°	834.3	833.8	833.3	832.8	832.3	831.8	831.3	830.8	830.3	830.0	829.5
145°	859.1	858.8	858.5	858.1	857.8	857.5	857.1	856.8	856.5	856.3	855.7
147.5°	882.4	882.1	881.8	881.4	881.1	880.8	880.4	880.1	879.8	879.6	879.2
150°	903.5	903.2	902.9	902.5	902.2	901.9	901.5	901.2	900.9	900.7	900.4
152.5°	922.9	922.2	921.5	920.9	920.2	920.0	919.9	919.7	919.6	919.5	919.4
155°	940.1	939.3	938.4	937.6	936.8	936.6	936.4	936.3	936.1	936.0	936.2
157.5°	955.8	954.8	953.8	952.8	951.8	952.0	952.1	952.3	952.4	952.5	952.5
160°	968.6	967.6	966.6	965.6	964.6	964.8	964.9	965.1	965.2	965.3	965.4
162.5°	980.5	979.4	978.2	977.1	975.9	976.1	976.2	976.4	976.5	976.6	976.9
165°	990.9	989.6	988.3	986.9	985.6	985.8	986.0	986.1	986.3	986.4	986.6
167.5°	999.2	997.9	996.6	995.2	993.9	993.9	993.9	993.9	993.9	993.9	994.2
170°	1006.0	1004.7	1003.4	1002.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1001.0
172.5°	1010.5	1009.2	1007.9	1006.5	1005.2	1005.0	1004.8	1004.7	1004.5	1004.4	1004.8
175°	1013.6	1012.4	1011.3	1010.1	1008.9	1008.7	1008.6	1008.4	1008.3	1008.2	1008.6
177.5°	1015.7	1014.4	1013.1	1011.7	1010.4	1010.2	1010.1	1009.9	1009.8	1009.7	1010.1
180°	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9	1011.9

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.2	1848.2	1848.2	1848.2
2.5°	1800.7	1811.8	1833.9	1852.9
5°	1762.7	1780.1	1813.3	1846.6
7.5°	1716.8	1743.7	1786.4	1832.3
10°	1672.5	1707.3	1759.5	1813.3
12.5°	1628.2	1664.6	1720.0	1789.6
15°	1576.0	1614.0	1680.4	1764.3
17.5°	1530.1	1580.7	1640.9	1724.7
20°	1481.1	1519.0	1596.6	1685.2
22.5°	1419.3	1482.6	1555.4	1648.8
25°	1370.3	1425.7	1498.5	1604.5
27.5°	1310.2	1375.0	1463.6	1557.0
30°	1261.1	1314.9	1397.2	1509.5
32.5°	1204.1	1267.4	1352.9	1463.6
35°	1153.5	1207.3	1288.0	1400.4
37.5°	1093.4	1151.9	1242.1	1341.8
40°	1041.2	1098.1	1183.6	1276.9
42.5°	977.9	1038.0	1123.4	1202.6
45°	927.2	982.6	1050.7	1123.4
47.5°	865.5	924.1	990.5	1041.2
50°	810.1	863.9	916.2	958.9
52.5°	750.0	799.1	846.5	878.2
55°	694.6	732.6	770.6	792.7
57.5°	629.8	666.2	697.8	710.5
60°	572.8	602.9	623.4	637.7
62.5°	512.7	534.8	550.6	558.6
65°	454.1	469.9	477.9	485.8
67.5°	394.0	408.2	413.0	422.5
70°	330.7	346.5	349.7	354.4
72.5°	283.2	283.2	289.6	295.9
75°	226.3	229.4	232.6	232.6
77.5°	177.2	177.2	180.4	182.0
80°	129.8	131.3	131.3	129.8
82.5°	88.6	91.8	88.6	87.0
85°	49.1	55.4	52.2	52.2
87.5°	20.6	20.6	23.7	20.6
90°	5.8	4.1	2.5	0.8
92.5°	14.3	15.3	16.3	17.3
95°	25.3	32.2	39.0	45.9
97.5°	69.4	74.1	78.8	83.5
100°	137.1	133.8	130.4	127.1
102.5°	183.2	181.0	178.9	176.7
105°	229.5	227.7	225.8	224.0
107.5°	278.9	277.4	275.9	274.4
110°	328.8	327.5	326.1	324.8

TEST NUMBER: P1032164

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	376.4	375.3	374.1	372.9
115°	423.3	422.3	421.3	420.3
117.5°	470.4	469.2	468.1	466.9
120°	514.2	512.7	511.2	509.7
122.5°	556.8	555.7	554.5	553.3
125°	596.4	595.1	593.7	592.4
127.5°	635.5	634.2	632.8	631.5
130°	671.6	670.3	668.9	667.6
132.5°	706.2	704.9	703.5	702.2
135°	740.5	739.5	738.5	737.5
137.5°	771.6	770.3	768.9	767.6
140°	800.7	799.7	798.7	797.7
142.5°	828.5	827.5	826.5	825.5
145°	854.6	853.4	852.3	851.1
147.5°	878.4	877.5	876.7	875.9
150°	899.9	899.4	898.9	898.4
152.5°	919.2	919.1	918.9	918.7
155°	936.5	936.8	937.2	937.5
157.5°	952.5	952.5	952.5	952.5
160°	965.6	965.7	965.9	966.1
162.5°	977.4	977.9	978.4	978.9
165°	987.1	987.6	988.1	988.6
167.5°	994.9	995.6	996.2	996.9
170°	1001.7	1002.4	1003.0	1003.7
172.5°	1005.7	1006.5	1007.4	1008.2
175°	1009.4	1010.3	1011.1	1011.9
177.5°	1010.9	1011.8	1012.6	1013.4
180°	1011.9	1011.9	1011.9	1011.9

(END OF REPORT)