

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032273

Luminaire Tested: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032273
REPORT IS A COMBINATION OF REPORTS P994380 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5796.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	96	91	88	85	87	83	80	77	68	66	64	54	52	51	41	40	39
2	87	80	75	70	79	73	68	64	60	56	53	48	45	43	36	35	33
3	80	71	64	59	72	65	59	54	53	49	45	42	40	37	32	31	29
4	73	63	56	50	66	58	51	46	47	43	39	38	35	32	29	27	25
5	67	56	49	43	61	52	45	40	43	38	34	34	31	28	27	24	22
6	62	51	43	37	56	46	40	35	38	33	30	31	27	25	24	22	20
7	57	46	38	33	52	42	35	31	35	30	26	28	25	22	22	20	18
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	20	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9510	9510	9510	9510
5°	9518	10953	9542	8126
10°	9434	13222	9475	7098
15°	9336	15006	9336	6258
20°	9145	16186	9196	5551
25°	9004	15378	8987	5066
30°	8841	10655	8823	4590
35°	8645	6841	8606	4232
40°	8401	4831	8359	3876
45°	7977	3865	7965	3528
50°	7454	3234	7430	3122
55°	6867	2665	6811	2647
60°	6289	2203	6227	2251
65°	5613	1763	5649	1908
70°	4989	1225	5124	1543
75°	4230	909	4401	1186
80°	3366	603	3654	889
85°	2401	286	2613	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12696 cd/sqm

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.5
10°-20°	271.6	4.7
20°-30°	427.8	7.4
30°-40°	444.8	7.7
40°-50°	380.6	6.6
50°-60°	290.1	5.0
60°-70°	185.9	3.2
70°-80°	89.1	1.5
80°-90°	26.2	0.5
90°-100°	83.5	1.4
100°-110°	252.7	4.4
110°-120°	430.1	7.4
120°-130°	565.9	9.8
130°-140°	636.1	11.0
140°-150°	625.3	10.8
150°-160°	526.5	9.1
160°-170°	350.5	6.0
170°-180°	122.7	2.1
0°-30°	786.1	13.6
0°-40°	1231.0	21.2
0°-60°	1901.6	32.8
0°-90°	2202.7	38.0
90°-120°	766.3	13.2
90°-150°	2593.6	44.7
90°-180°	3593.0	62.0
0°-180°	5796.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1049	885	778	883	84
15°	843	1491	843	622	843	237
25°	767	1536	766	506	767	353
35°	669	666	666	412	669	419
45°	537	356	536	324	537	414
55°	379	223	376	222	379	340
65°	232	129	234	139	232	232
75°	111	54	116	71	111	120
85°	25	13	27	25	25	28
90°	1	31	1	31	1	6
95°	60	80	60	80	60	66
105°	229	242	229	242	229	245
115°	433	434	433	434	433	428
125°	634	626	634	626	634	565
135°	822	821	822	821	822	633
145°	997	997	997	997	997	623
155°	1142	1140	1142	1140	1142	526
165°	1244	1240	1244	1240	1244	351
175°	1294	1289	1294	1289	1294	123
180°	1297	1297	1297	1297	1297	

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	885.8	891.8	896.4	899.4	907.0	911.5	915.3	922.1	922.1	923.6	926.6
5°	882.8	895.6	904.7	916.8	932.7	940.2	950.8	959.9	972.8	979.6	986.4
7.5°	876.0	894.1	913.0	931.2	954.6	969.7	980.3	1003.8	1020.4	1040.9	1056.7
10°	866.9	891.8	916.0	944.0	975.8	998.5	1014.4	1045.4	1077.2	1105.9	1130.1
12.5°	855.5	885.8	920.6	954.6	999.2	1021.9	1047.7	1086.2	1131.6	1167.9	1200.5
15°	843.4	878.2	917.6	959.2	1015.1	1046.9	1084.0	1130.9	1181.5	1233.7	1278.4
17.5°	824.5	868.4	912.3	972.8	1038.6	1057.5	1089.3	1153.6	1216.3	1263.2	1317.7
20°	805.6	854.8	910.0	964.5	1035.6	1079.4	1108.9	1177.0	1244.3	1301.1	1353.3
22.5°	788.2	839.6	897.1	966.0	1032.5	1076.4	1113.5	1184.6	1262.5	1326.0	1390.3
25°	767.0	823.0	886.5	951.6	1032.5	1065.8	1106.7	1189.1	1271.6	1344.9	1424.4
27.5°	744.3	801.1	863.8	930.4	1004.5	1053.7	1093.8	1182.3	1282.9	1361.6	1443.3
30°	721.6	779.9	840.4	900.2	983.4	1030.3	1076.4	1174.0	1289.0	1379.0	1441.8
32.5°	699.7	748.9	808.6	866.9	949.3	1000.8	1053.0	1165.7	1291.2	1366.9	1397.1
35°	669.4	720.9	769.3	831.3	914.5	965.2	1026.5	1164.9	1281.4	1328.3	1313.2
37.5°	641.5	684.6	730.7	785.9	871.4	937.2	1000.8	1145.2	1248.9	1251.9	1166.4
40°	610.4	646.0	684.6	742.8	835.1	900.2	969.0	1115.0	1189.9	1145.2	994.7
42.5°	574.9	606.7	636.9	693.6	794.3	866.9	941.0	1077.2	1104.4	1001.5	844.9
45°	537.1	562.8	590.8	650.5	751.1	823.0	897.1	1018.9	990.9	845.7	696.7
47.5°	497.7	519.7	546.9	601.4	705.0	778.4	848.7	935.7	864.6	708.8	584.0
50°	458.4	475.8	502.3	558.2	658.1	724.7	789.7	846.4	746.6	608.2	482.6
52.5°	419.8	433.4	460.7	508.3	605.1	668.7	715.6	737.5	636.2	502.3	419.1
55°	379.0	394.1	412.3	460.7	556.7	603.6	634.6	633.9	529.5	425.9	346.4
57.5°	339.6	353.3	369.1	417.6	495.5	527.2	553.7	540.9	441.8	348.7	297.3
60°	304.8	312.4	329.8	370.7	429.7	456.9	472.0	450.1	360.8	294.3	245.8
62.5°	267.0	274.6	289.0	327.5	363.8	378.2	391.1	363.1	298.0	239.8	210.3
65°	232.2	242.1	251.1	282.1	301.8	319.2	317.7	294.3	233.0	195.2	171.0
67.5°	202.0	205.7	213.3	232.2	241.3	254.2	254.9	228.4	187.6	158.9	144.5
70°	169.4	173.2	178.5	187.6	193.6	196.7	195.2	171.7	141.5	124.1	111.2
72.5°	141.5	140.7	144.5	144.5	150.5	149.8	145.2	127.1	107.4	93.0	85.5
75°	111.2	112.0	112.7	111.2	108.9	105.9	102.1	88.5	75.6	68.8	62.0
77.5°	87.0	85.5	86.2	80.9	77.9	74.9	69.6	62.8	52.2	50.7	47.7
80°	62.0	61.3	60.5	58.2	51.4	48.4	44.6	40.8	38.6	37.1	36.3
82.5°	41.6	41.6	40.1	35.6	31.8	29.5	28.7	27.2	25.0	25.0	24.2
85°	25.0	24.2	22.7	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.6
87.5°	9.8	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.5	4.5
90°	1.0	3.3	5.5	7.8	10.1	11.2	12.7	15.6	18.5	21.5	24.4
92.5°	30.6	32.0	33.3	34.7	36.0	36.7	37.4	38.7	40.1	41.4	42.8
95°	60.1	61.7	63.3	64.8	66.4	67.2	68.1	69.9	71.8	73.6	75.4
97.5°	98.8	99.9	101.1	102.2	103.3	103.9	104.6	105.9	107.3	108.6	110.0
100°	138.5	139.9	141.3	142.6	144.0	144.7	145.3	146.4	147.5	148.7	149.8
102.5°	184.4	185.1	185.7	186.4	187.1	187.4	188.2	189.8	191.4	193.0	194.6
105°	229.2	229.6	230.1	230.5	231.0	231.2	232.2	234.3	236.3	238.4	240.4
107.5°	282.2	282.4	282.6	282.9	283.1	283.2	283.7	284.6	285.5	286.4	287.3
110°	331.1	331.5	332.0	332.4	332.9	333.1	333.3	333.8	334.3	334.7	335.2

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	382.0	382.2	382.4	382.7	382.9	383.0	383.0	383.0	383.0	383.0	383.0
115°	433.0	433.7	434.3	435.0	435.7	436.0	435.8	435.3	434.9	434.4	434.0
117.5°	484.9	485.1	485.3	485.6	485.8	485.9	485.7	485.2	484.8	484.3	483.9
120°	532.8	534.2	535.5	536.9	538.2	538.9	538.3	537.2	536.1	534.9	533.8
122.5°	582.7	583.6	584.5	585.4	586.3	586.8	586.6	586.1	585.6	585.2	584.7
125°	633.6	634.3	635.0	635.7	636.4	636.7	636.5	636.0	635.6	635.1	634.7
127.5°	680.5	681.9	683.2	684.6	685.9	686.6	686.4	685.9	685.5	685.0	684.6
130°	727.4	729.2	731.0	732.8	734.6	735.5	735.2	734.5	733.8	733.2	732.5
132.5°	774.2	776.0	777.8	779.7	781.5	782.4	782.2	781.7	781.2	780.8	780.3
135°	822.1	823.5	824.8	826.2	827.5	828.2	828.1	827.9	827.6	827.4	827.2
137.5°	865.9	867.0	868.2	869.3	870.4	871.0	871.3	872.0	872.7	873.4	874.1
140°	911.7	912.8	914.0	915.1	916.2	916.8	916.9	917.2	917.4	917.7	917.9
142.5°	953.5	954.6	955.8	956.9	958.0	958.6	958.8	959.3	959.7	960.2	960.6
145°	997.3	997.8	998.2	998.7	999.2	999.4	999.7	1000.4	1001.1	1001.7	1002.4
147.5°	1035.0	1035.9	1036.8	1037.7	1038.6	1039.1	1039.4	1040.1	1040.8	1041.4	1042.1
150°	1074.7	1075.2	1075.6	1076.1	1076.6	1076.8	1077.0	1077.5	1077.9	1078.4	1078.8
152.5°	1107.3	1108.0	1108.7	1109.4	1110.1	1110.4	1110.5	1110.7	1111.0	1111.2	1111.4
155°	1142.0	1142.0	1142.0	1142.0	1142.0	1142.0	1142.1	1142.3	1142.6	1142.8	1143.0
157.5°	1171.5	1171.3	1171.1	1170.8	1170.6	1170.5	1170.6	1170.8	1171.1	1171.3	1171.5
160°	1199.0	1198.6	1198.1	1197.7	1197.2	1197.0	1197.0	1197.0	1197.0	1197.0	1197.0
162.5°	1223.5	1222.8	1222.1	1221.4	1220.7	1220.4	1220.5	1220.7	1221.0	1221.2	1221.4
165°	1243.8	1243.1	1242.5	1241.8	1241.1	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
167.5°	1261.2	1260.3	1259.4	1258.5	1257.6	1257.1	1257.2	1257.4	1257.7	1257.9	1258.1
170°	1275.4	1274.5	1273.6	1272.7	1271.8	1271.4	1271.4	1271.4	1271.4	1271.4	1271.4
172.5°	1286.6	1285.7	1284.8	1283.9	1283.0	1282.6	1282.6	1282.6	1282.6	1282.6	1282.6
175°	1293.8	1292.9	1292.0	1291.1	1290.2	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7
177.5°	1297.8	1296.9	1296.0	1295.1	1294.2	1293.8	1293.8	1293.8	1293.8	1293.8	1293.8
180°	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8



TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	932.7	932.7	939.5	946.3	942.5	944.8	953.1	950.1	956.1	955.4	957.6
5°	1003.0	1011.4	1018.2	1032.5	1034.8	1032.5	1046.9	1050.7	1057.5	1049.2	1053.0
7.5°	1082.5	1099.9	1116.5	1137.7	1144.5	1146.0	1153.6	1164.2	1173.2	1156.6	1164.9
10°	1159.6	1186.1	1220.1	1239.0	1255.7	1261.7	1267.8	1274.6	1285.2	1295.0	1287.5
12.5°	1242.8	1281.4	1313.9	1348.0	1368.4	1366.1	1383.5	1388.1	1396.4	1398.6	1401.7
15°	1310.9	1365.4	1385.8	1436.5	1441.0	1456.1	1475.8	1493.2	1495.5	1490.9	1490.9
17.5°	1376.0	1422.9	1459.2	1500.0	1508.3	1521.2	1546.2	1554.5	1557.5	1556.7	1556.7
20°	1428.9	1459.9	1521.2	1555.2	1568.8	1585.5	1602.9	1613.5	1615.7	1618.8	1614.2
22.5°	1463.7	1510.6	1560.5	1588.5	1599.9	1605.9	1617.3	1620.3	1616.5	1617.3	1618.0
25°	1490.9	1537.1	1567.3	1574.9	1574.1	1566.6	1558.3	1543.9	1542.4	1536.3	1524.2
27.5°	1498.5	1515.9	1512.1	1481.1	1450.1	1447.1	1397.1	1369.9	1338.9	1343.4	1326.0
30°	1457.6	1435.0	1381.2	1302.6	1270.1	1217.1	1161.1	1102.9	1080.2	1055.2	1101.4
32.5°	1357.8	1276.9	1181.5	1079.4	1025.0	978.1	918.3	876.0	851.7	831.3	870.7
35°	1207.3	1080.9	954.6	857.8	813.2	770.8	714.8	693.6	663.4	666.4	670.2
37.5°	1013.6	874.4	779.1	683.8	654.3	636.9	596.1	563.5	553.0	549.9	549.9
40°	832.1	717.9	633.1	558.2	535.6	521.2	488.7	473.5	462.2	459.2	462.9
42.5°	688.4	590.8	525.0	475.0	459.2	441.0	427.4	408.5	406.2	400.9	407.7
45°	577.9	493.2	444.0	407.7	394.1	387.3	372.2	360.8	356.3	355.5	360.8
47.5°	490.2	424.4	381.2	358.5	348.0	341.2	328.3	323.8	319.2	320.7	318.5
50°	411.5	362.3	334.3	313.9	307.1	300.3	292.0	287.4	285.2	285.2	284.4
52.5°	353.3	312.4	294.3	275.3	272.3	268.5	259.5	256.4	252.6	251.9	254.9
55°	302.6	274.6	256.4	245.1	242.1	234.5	230.7	226.9	224.7	223.1	223.9
57.5°	258.7	237.5	225.4	215.6	210.3	207.3	200.5	199.7	198.2	198.2	197.4
60°	222.4	207.3	192.9	186.8	183.1	179.3	178.5	174.0	171.7	173.2	172.5
62.5°	188.4	176.2	167.9	161.1	158.9	155.8	153.6	152.0	149.8	150.5	150.5
65°	157.3	147.5	141.5	135.4	134.6	131.6	130.9	129.4	129.4	128.6	130.1
67.5°	129.4	122.5	117.2	113.5	111.2	112.0	108.9	106.7	106.7	105.9	108.2
70°	102.9	99.1	93.8	89.3	86.2	86.2	82.5	81.7	81.7	81.7	80.9
72.5°	79.4	72.6	70.3	68.8	68.8	68.8	67.3	67.3	66.6	67.3	66.6
75°	59.0	58.2	56.7	56.0	56.0	55.2	54.5	54.5	54.5	54.5	54.5
77.5°	46.1	46.1	44.6	43.9	43.9	43.9	43.1	43.1	42.4	42.4	42.4
80°	34.0	34.0	32.5	32.5	32.5	31.8	31.8	31.8	32.5	31.8	31.8
82.5°	23.4	23.4	22.7	23.4	22.7	21.9	21.9	21.9	21.2	21.9	21.9
85°	13.6	13.6	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.5	4.5	4.5	3.8	4.5	3.8	3.8	4.5	3.8	4.5
90°	25.3	26.2	27.1	28.0	28.5	28.7	29.2	29.7	30.1	30.6	30.1
92.5°	43.5	44.1	44.8	45.5	45.8	45.6	45.1	44.7	44.2	43.8	44.2
95°	76.3	77.2	78.1	79.0	79.5	79.5	79.5	79.5	79.5	79.5	79.5
97.5°	111.1	112.3	113.4	114.5	115.1	115.0	114.8	114.5	114.3	114.1	114.3
100°	150.5	151.1	151.8	152.5	152.8	153.0	153.5	153.9	154.4	154.8	154.4
102.5°	195.3	195.9	196.6	197.3	197.6	197.5	197.3	197.0	196.8	196.6	196.8
105°	240.4	240.4	240.4	240.4	240.4	240.6	241.1	241.6	242.0	242.5	242.0
107.5°	288.0	288.6	289.3	290.0	290.3	290.2	290.0	289.7	289.5	289.3	289.5
110°	336.1	337.0	337.9	338.8	339.2	339.0	338.5	338.1	337.6	337.2	337.6

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	384.1	385.3	386.4	387.5	388.1	388.1	388.1	388.1	388.1	388.1	388.1
115°	434.2	434.4	434.7	434.9	435.0	434.9	434.7	434.4	434.2	434.0	434.2
117.5°	483.9	483.9	483.9	483.9	483.9	483.6	482.9	482.2	481.5	480.8	481.5
120°	533.6	533.4	533.1	532.9	532.8	532.6	532.1	531.6	531.2	530.7	531.2
122.5°	584.0	583.4	582.7	582.0	581.7	581.4	580.7	580.0	579.3	578.6	579.3
125°	633.8	632.9	632.0	631.1	630.6	630.1	629.2	628.3	627.4	626.5	627.4
127.5°	683.2	681.9	680.5	679.2	678.5	678.0	677.1	676.2	675.3	674.4	675.3
130°	731.6	730.7	729.8	728.9	728.4	727.6	726.0	724.4	722.8	721.2	722.8
132.5°	779.2	778.0	776.9	775.8	775.2	774.6	773.5	772.4	771.2	770.1	771.2
135°	826.3	825.4	824.5	823.6	823.1	822.9	822.4	822.0	821.5	821.1	821.5
137.5°	873.0	871.8	870.7	869.6	869.0	868.7	868.0	867.3	866.6	865.9	866.6
140°	917.7	917.4	917.2	916.9	916.8	916.0	914.4	912.9	911.3	909.7	911.3
142.5°	960.4	960.2	959.9	959.7	959.6	959.0	957.9	956.8	955.6	954.5	955.6
145°	1002.2	1002.0	1001.7	1001.5	1001.4	1000.9	1000.0	999.1	998.2	997.3	998.2
147.5°	1042.1	1042.1	1042.1	1042.1	1042.1	1041.4	1040.1	1038.7	1037.4	1036.0	1037.4
150°	1078.8	1078.8	1078.8	1078.8	1078.8	1078.1	1076.8	1075.4	1074.1	1072.7	1074.1
152.5°	1111.9	1112.3	1112.8	1113.3	1113.5	1112.9	1111.8	1110.7	1109.5	1108.4	1109.5
155°	1143.9	1144.8	1145.7	1146.6	1147.1	1146.3	1144.7	1143.1	1141.5	1139.9	1141.5
157.5°	1172.4	1173.3	1174.2	1175.1	1175.6	1174.9	1173.6	1172.2	1170.9	1169.5	1170.9
160°	1198.1	1199.3	1200.4	1201.5	1202.1	1201.6	1200.7	1199.8	1198.9	1198.0	1198.9
162.5°	1222.5	1223.7	1224.8	1225.9	1226.5	1225.7	1224.1	1222.6	1221.0	1219.4	1221.0
165°	1242.2	1243.5	1244.9	1246.2	1246.9	1246.1	1244.5	1243.0	1241.4	1239.8	1241.4
167.5°	1259.5	1260.8	1262.2	1263.5	1264.2	1263.5	1262.2	1260.8	1259.5	1258.1	1259.5
170°	1273.0	1274.6	1276.1	1277.7	1278.5	1277.7	1276.1	1274.6	1273.0	1271.4	1273.0
172.5°	1284.0	1285.3	1286.7	1288.0	1288.7	1287.9	1286.3	1284.7	1283.1	1281.5	1283.1
175°	1291.1	1292.4	1293.8	1295.1	1295.8	1295.0	1293.4	1291.9	1290.3	1288.7	1290.3
177.5°	1295.2	1296.5	1297.9	1299.2	1299.9	1299.1	1297.5	1295.9	1294.3	1292.7	1294.3
180°	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	953.9	949.3	946.3	944.0	941.8	948.6	939.5	929.7	922.8	918.3	916.8
5°	1053.7	1043.9	1035.6	1028.7	1030.3	1030.3	1014.4	997.0	981.9	973.5	964.5
7.5°	1169.4	1158.9	1142.2	1138.4	1135.4	1116.5	1100.6	1068.8	1049.9	1031.0	1014.4
10°	1284.4	1270.8	1254.9	1249.6	1242.1	1218.6	1194.4	1153.6	1130.1	1095.3	1073.4
12.5°	1391.8	1375.2	1359.3	1355.5	1344.2	1323.8	1282.2	1239.8	1199.7	1162.6	1124.1
15°	1481.9	1477.3	1453.1	1438.0	1413.0	1385.0	1376.0	1318.5	1267.8	1229.2	1159.6
17.5°	1557.5	1536.3	1513.6	1503.8	1494.0	1461.4	1428.9	1369.9	1315.4	1258.7	1214.1
20°	1618.0	1594.6	1578.7	1564.3	1559.8	1522.7	1471.3	1419.1	1359.3	1295.8	1237.5
22.5°	1621.0	1618.0	1607.4	1599.1	1590.0	1565.8	1525.0	1459.9	1396.4	1326.8	1250.4
25°	1558.3	1553.7	1584.0	1576.4	1582.5	1573.4	1551.4	1497.0	1422.9	1341.2	1264.0
27.5°	1369.1	1415.3	1462.9	1479.6	1490.9	1523.5	1534.0	1503.8	1444.0	1357.0	1270.8
30°	1112.0	1173.2	1250.4	1292.0	1323.8	1384.3	1462.9	1472.8	1444.8	1375.2	1269.3
32.5°	872.9	928.9	990.9	1040.1	1082.5	1206.5	1312.4	1388.8	1402.4	1366.1	1273.1
35°	703.5	727.7	786.7	833.6	891.1	997.0	1121.8	1245.1	1328.3	1332.8	1261.7
37.5°	580.2	593.0	644.5	671.0	705.0	798.0	914.5	1075.6	1205.0	1266.3	1230.0
40°	480.3	509.8	539.3	554.5	578.7	643.0	754.9	881.2	1041.6	1155.1	1180.8
42.5°	416.8	429.7	448.6	469.7	484.9	540.9	615.7	731.5	876.0	1034.0	1105.1
45°	367.6	372.2	391.8	405.4	421.3	460.7	513.6	610.4	737.5	893.3	1014.4
47.5°	326.8	335.9	346.4	354.8	365.4	395.6	441.0	511.3	623.3	762.5	892.6
50°	290.5	295.8	309.4	313.2	320.7	341.9	376.7	430.4	522.7	633.9	768.5
52.5°	256.4	266.3	271.6	276.9	283.7	301.1	323.8	367.6	437.2	541.6	655.8
55°	230.0	233.0	240.5	245.1	250.4	262.5	282.1	314.7	369.1	452.3	560.5
57.5°	204.2	204.2	211.8	215.6	220.9	230.0	247.4	272.3	311.7	373.7	472.8
60°	177.0	177.8	183.8	188.4	189.9	198.9	213.3	233.0	263.2	308.6	389.6
62.5°	152.8	156.6	159.6	161.1	166.4	171.7	183.8	197.4	218.6	258.7	316.2
65°	132.4	133.1	135.4	136.9	139.2	145.2	154.3	163.4	181.5	211.0	257.9
67.5°	108.9	112.0	115.0	115.0	117.2	120.3	129.4	136.9	150.5	167.9	199.7
70°	81.7	83.2	87.7	90.0	93.0	98.3	102.9	107.4	118.0	130.9	155.1
72.5°	68.1	68.1	69.6	70.3	70.3	74.1	80.9	85.5	90.8	99.8	116.5
75°	54.5	54.5	56.7	56.0	57.5	59.0	59.8	62.8	65.8	72.6	82.5
77.5°	43.1	43.9	43.9	44.6	44.6	45.4	46.1	47.7	49.2	53.0	57.5
80°	31.8	32.5	32.5	33.3	33.3	34.0	34.8	35.6	37.1	38.6	40.8
82.5°	21.9	22.7	22.7	23.4	22.7	23.4	24.2	24.2	25.0	26.5	27.2
85°	12.9	12.9	13.6	12.9	12.9	12.9	13.6	13.6	14.4	16.6	16.6
87.5°	3.8	4.5	3.8	4.5	4.5	4.5	4.5	5.3	5.3	6.1	6.8
90°	29.7	29.2	28.7	28.5	28.0	27.1	26.2	25.3	24.4	21.5	18.5
92.5°	44.7	45.1	45.6	45.8	45.5	44.8	44.1	43.5	42.8	41.4	40.1
95°	79.5	79.5	79.5	79.5	79.0	78.1	77.2	76.3	75.4	73.6	71.8
97.5°	114.5	114.8	115.0	115.1	114.5	113.4	112.3	111.1	110.0	108.6	107.3
100°	153.9	153.5	153.0	152.8	152.5	151.8	151.1	150.5	149.8	148.7	147.5
102.5°	197.0	197.3	197.5	197.6	197.3	196.6	195.9	195.3	194.6	193.0	191.4
105°	241.6	241.1	240.6	240.4	240.4	240.4	240.4	240.4	240.4	238.4	236.3
107.5°	289.7	290.0	290.2	290.3	290.0	289.3	288.6	288.0	287.3	286.4	285.5
110°	338.1	338.5	339.0	339.2	338.8	337.9	337.0	336.1	335.2	334.7	334.3

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	388.1	388.1	388.1	388.1	387.5	386.4	385.3	384.1	383.0	383.0	383.0
115°	434.4	434.7	434.9	435.0	434.9	434.7	434.4	434.2	434.0	434.4	434.9
117.5°	482.2	482.9	483.6	483.9	483.9	483.9	483.9	483.9	483.9	484.3	484.8
120°	531.6	532.1	532.6	532.8	532.9	533.1	533.4	533.6	533.8	534.9	536.1
122.5°	580.0	580.7	581.4	581.7	582.0	582.7	583.4	584.0	584.7	585.2	585.6
125°	628.3	629.2	630.1	630.6	631.1	632.0	632.9	633.8	634.7	635.1	635.6
127.5°	676.2	677.1	678.0	678.5	679.2	680.5	681.9	683.2	684.6	685.0	685.5
130°	724.4	726.0	727.6	728.4	728.9	729.8	730.7	731.6	732.5	733.2	733.8
132.5°	772.4	773.5	774.6	775.2	775.8	776.9	778.0	779.2	780.3	780.8	781.2
135°	822.0	822.4	822.9	823.1	823.6	824.5	825.4	826.3	827.2	827.4	827.6
137.5°	867.3	868.0	868.7	869.0	869.6	870.7	871.8	873.0	874.1	873.4	872.7
140°	912.9	914.4	916.0	916.8	916.9	917.2	917.4	917.7	917.9	917.7	917.4
142.5°	956.8	957.9	959.0	959.6	959.7	959.9	960.2	960.4	960.6	960.2	959.7
145°	999.1	1000.0	1000.9	1001.4	1001.5	1001.7	1002.0	1002.2	1002.4	1001.7	1001.1
147.5°	1038.7	1040.1	1041.4	1042.1	1042.1	1042.1	1042.1	1042.1	1042.1	1041.4	1040.8
150°	1075.4	1076.8	1078.1	1078.8	1078.8	1078.8	1078.8	1078.8	1078.8	1078.4	1077.9
152.5°	1110.7	1111.8	1112.9	1113.5	1113.3	1112.8	1112.3	1111.9	1111.4	1111.2	1111.0
155°	1143.1	1144.7	1146.3	1147.1	1146.6	1145.7	1144.8	1143.9	1143.0	1142.8	1142.6
157.5°	1172.2	1173.6	1174.9	1175.6	1175.1	1174.2	1173.3	1172.4	1171.5	1171.3	1171.1
160°	1199.8	1200.7	1201.6	1202.1	1201.5	1200.4	1199.3	1198.1	1197.0	1197.0	1197.0
162.5°	1222.6	1224.1	1225.7	1226.5	1225.9	1224.8	1223.7	1222.5	1221.4	1221.2	1221.0
165°	1243.0	1244.5	1246.1	1246.9	1246.2	1244.9	1243.5	1242.2	1240.8	1240.8	1240.8
167.5°	1260.8	1262.2	1263.5	1264.2	1263.5	1262.2	1260.8	1259.5	1258.1	1257.9	1257.7
170°	1274.6	1276.1	1277.7	1278.5	1277.7	1276.1	1274.6	1273.0	1271.4	1271.4	1271.4
172.5°	1284.7	1286.3	1287.9	1288.7	1288.0	1286.7	1285.3	1284.0	1282.6	1282.6	1282.6
175°	1291.9	1293.4	1295.0	1295.8	1295.1	1293.8	1292.4	1291.1	1289.7	1289.7	1289.7
177.5°	1295.9	1297.5	1299.1	1299.9	1299.2	1297.9	1296.5	1295.2	1293.8	1293.8	1293.8
180°	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	914.5	910.7	907.0	907.0	898.6	891.1	887.3	888.8	884.3	878.2	872.2
5°	954.6	939.5	936.5	928.1	916.8	900.9	892.6	885.0	876.0	863.8	852.5
7.5°	991.7	972.0	961.4	953.1	931.2	909.2	891.1	879.0	863.1	844.9	831.3
10°	1040.1	1003.8	992.4	973.5	942.5	911.5	890.3	870.7	848.7	827.5	809.4
12.5°	1078.7	1037.1	1015.9	997.0	956.9	917.6	882.0	857.8	831.3	807.9	784.4
15°	1122.5	1075.6	1038.6	1015.9	965.2	917.6	877.5	843.4	813.9	785.2	764.8
17.5°	1143.7	1084.7	1068.1	1035.6	962.2	914.5	865.4	829.1	793.5	760.2	736.0
20°	1177.0	1108.2	1066.6	1044.6	979.6	909.2	851.7	810.1	773.1	737.5	711.8
22.5°	1179.3	1104.4	1077.2	1035.6	955.4	893.3	839.6	789.0	745.8	712.6	686.1
25°	1174.0	1097.6	1059.8	1026.5	959.9	884.3	815.4	765.5	723.2	684.6	653.6
27.5°	1171.7	1077.9	1042.4	1009.1	934.2	857.8	801.1	744.3	695.9	661.9	630.1
30°	1168.7	1056.7	1013.6	975.0	906.2	837.4	769.3	720.1	674.0	630.9	599.1
32.5°	1149.0	1028.0	984.1	943.3	869.1	800.3	746.6	694.4	644.5	604.4	575.6
35°	1143.0	1001.5	944.0	900.2	827.5	766.3	709.5	666.4	619.5	579.4	545.4
37.5°	1125.6	974.3	912.3	856.3	780.6	722.4	680.8	637.7	592.3	549.2	521.9
40°	1095.3	942.5	872.2	814.7	736.8	677.8	639.2	607.4	562.8	524.2	490.9
42.5°	1050.7	910.0	834.3	773.8	687.6	632.4	600.6	570.4	532.5	492.4	465.2
45°	999.2	866.9	796.5	729.2	641.5	587.7	554.5	536.3	501.5	467.5	435.7
47.5°	928.9	822.2	752.7	683.1	593.8	541.6	515.1	497.0	472.8	435.7	410.0
50°	840.4	764.8	698.9	636.9	546.9	497.0	470.5	456.9	436.5	410.0	385.0
52.5°	742.1	698.2	643.7	586.2	499.2	452.3	428.1	417.6	402.4	377.5	356.3
55°	643.0	624.1	587.0	530.3	449.3	410.7	389.6	375.9	364.6	346.4	328.3
57.5°	554.5	545.4	519.7	475.8	407.7	367.6	349.5	340.4	331.3	317.7	299.5
60°	462.9	472.8	446.3	424.4	362.3	327.5	311.7	301.8	297.3	285.2	273.8
62.5°	383.5	392.6	377.5	360.8	316.9	285.9	276.1	267.0	264.0	253.4	242.1
65°	311.7	323.0	311.7	302.6	276.1	250.4	238.3	233.7	230.7	223.9	214.8
67.5°	248.1	259.5	254.2	242.8	234.5	213.3	206.5	202.0	200.5	195.2	187.6
70°	186.8	202.7	204.2	197.4	189.9	180.0	175.5	174.0	170.2	165.7	161.1
72.5°	134.6	152.8	153.6	153.6	149.0	149.0	144.5	142.2	142.2	137.7	132.4
75°	99.1	111.2	112.7	114.2	116.5	118.8	115.7	115.7	115.0	110.4	108.2
77.5°	65.8	76.4	80.2	85.5	88.5	88.5	90.0	91.5	90.0	87.7	86.2
80°	42.4	49.9	54.5	57.5	62.0	64.3	66.6	67.3	65.8	65.1	62.8
82.5°	28.0	30.3	32.5	36.3	41.6	45.4	45.4	44.6	46.1	45.4	44.6
85°	15.9	17.4	18.2	18.9	21.9	25.7	26.5	27.2	28.7	27.2	25.7
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.3	14.4	13.6	12.1	12.1
90°	15.6	12.7	11.2	10.1	7.8	5.5	3.3	1.0	3.3	5.5	7.8
92.5°	38.7	37.4	36.7	36.0	34.7	33.3	32.0	30.6	32.0	33.3	34.7
95°	69.9	68.1	67.2	66.4	64.8	63.3	61.7	60.1	61.7	63.3	64.8
97.5°	105.9	104.6	103.9	103.3	102.2	101.1	99.9	98.8	99.9	101.1	102.2
100°	146.4	145.3	144.7	144.0	142.6	141.3	139.9	138.5	139.9	141.3	142.6
102.5°	189.8	188.2	187.4	187.1	186.4	185.7	185.1	184.4	185.1	185.7	186.4
105°	234.3	232.2	231.2	231.0	230.5	230.1	229.6	229.2	229.6	230.1	230.5
107.5°	284.6	283.7	283.2	283.1	282.9	282.6	282.4	282.2	282.4	282.6	282.9
110°	333.8	333.3	333.1	332.9	332.4	332.0	331.5	331.1	331.5	332.0	332.4

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	383.0	383.0	383.0	382.9	382.7	382.4	382.2	382.0	382.2	382.4	382.7
115°	435.3	435.8	436.0	435.7	435.0	434.3	433.7	433.0	433.7	434.3	435.0
117.5°	485.2	485.7	485.9	485.8	485.6	485.3	485.1	484.9	485.1	485.3	485.6
120°	537.2	538.3	538.9	538.2	536.9	535.5	534.2	532.8	534.2	535.5	536.9
122.5°	586.1	586.6	586.8	586.3	585.4	584.5	583.6	582.7	583.6	584.5	585.4
125°	636.0	636.5	636.7	636.4	635.7	635.0	634.3	633.6	634.3	635.0	635.7
127.5°	685.9	686.4	686.6	685.9	684.6	683.2	681.9	680.5	681.9	683.2	684.6
130°	734.5	735.2	735.5	734.6	732.8	731.0	729.2	727.4	729.2	731.0	732.8
132.5°	781.7	782.2	782.4	781.5	779.7	777.8	776.0	774.2	776.0	777.8	779.7
135°	827.9	828.1	828.2	827.5	826.2	824.8	823.5	822.1	823.5	824.8	826.2
137.5°	872.0	871.3	871.0	870.4	869.3	868.2	867.0	865.9	867.0	868.2	869.3
140°	917.2	916.9	916.8	916.2	915.1	914.0	912.8	911.7	912.8	914.0	915.1
142.5°	959.3	958.8	958.6	958.0	956.9	955.8	954.6	953.5	954.6	955.8	956.9
145°	1000.4	999.7	999.4	999.2	998.7	998.2	997.8	997.3	997.8	998.2	998.7
147.5°	1040.1	1039.4	1039.1	1038.6	1037.7	1036.8	1035.9	1035.0	1035.9	1036.8	1037.7
150°	1077.5	1077.0	1076.8	1076.6	1076.1	1075.6	1075.2	1074.7	1075.2	1075.6	1076.1
152.5°	1110.7	1110.5	1110.4	1110.1	1109.4	1108.7	1108.0	1107.3	1108.0	1108.7	1109.4
155°	1142.3	1142.1	1142.0	1142.0	1142.0	1142.0	1142.0	1142.0	1142.0	1142.0	1142.0
157.5°	1170.8	1170.6	1170.5	1170.6	1170.8	1171.1	1171.3	1171.5	1171.3	1171.1	1170.8
160°	1197.0	1197.0	1197.0	1197.2	1197.7	1198.1	1198.6	1199.0	1198.6	1198.1	1197.7
162.5°	1220.7	1220.5	1220.4	1220.7	1221.4	1222.1	1222.8	1223.5	1222.8	1222.1	1221.4
165°	1240.8	1240.8	1240.8	1241.1	1241.8	1242.5	1243.1	1243.8	1243.1	1242.5	1241.8
167.5°	1257.4	1257.2	1257.1	1257.6	1258.5	1259.4	1260.3	1261.2	1260.3	1259.4	1258.5
170°	1271.4	1271.4	1271.4	1271.8	1272.7	1273.6	1274.5	1275.4	1274.5	1273.6	1272.7
172.5°	1282.6	1282.6	1282.6	1283.0	1283.9	1284.8	1285.7	1286.6	1285.7	1284.8	1283.9
175°	1289.7	1289.7	1289.7	1290.2	1291.1	1292.0	1292.9	1293.8	1292.9	1292.0	1291.1
177.5°	1293.8	1293.8	1293.8	1294.2	1295.1	1296.0	1296.9	1297.8	1296.9	1296.0	1295.1
180°	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	872.2	868.4	866.9	863.1	854.0	848.0	841.2	836.6	837.4	833.6	835.9
5°	844.9	844.2	838.9	831.3	818.5	811.7	799.6	793.5	790.5	791.2	786.7
7.5°	822.2	815.4	811.7	799.6	787.4	773.1	763.2	757.9	753.4	748.9	745.8
10°	796.5	790.5	784.4	771.6	754.9	741.3	727.7	722.4	715.6	712.6	710.3
12.5°	769.3	765.5	757.9	742.8	723.9	711.0	695.2	692.1	683.1	677.0	675.5
15°	744.3	742.1	728.4	711.0	692.1	679.3	665.7	656.6	641.5	644.5	639.2
17.5°	717.9	708.0	699.7	676.3	667.2	647.5	631.6	627.1	616.5	609.7	602.9
20°	688.4	682.3	671.7	656.6	634.6	612.0	599.9	592.3	586.2	575.6	572.6
22.5°	660.4	652.8	643.7	624.1	605.1	586.2	569.6	562.8	555.2	547.7	543.1
25°	638.4	627.1	617.2	593.0	574.1	558.2	547.7	536.3	525.7	521.2	519.7
27.5°	604.4	597.6	587.7	565.1	547.7	530.3	520.4	512.9	501.5	496.2	491.7
30°	582.5	568.8	557.5	539.3	521.9	503.0	494.0	484.9	478.1	471.3	466.0
32.5°	553.0	542.4	533.3	515.1	497.7	480.3	470.5	456.9	453.1	447.8	441.8
35°	524.2	517.4	507.6	487.9	469.0	456.9	446.3	433.4	428.9	425.1	419.8
37.5°	497.0	487.1	480.3	461.4	444.8	430.4	422.1	411.5	408.5	403.9	400.2
40°	473.5	463.7	456.9	438.0	420.6	405.4	400.2	389.6	385.0	379.7	377.5
42.5°	447.1	438.7	429.7	416.0	397.9	382.8	372.2	366.1	360.1	357.8	353.3
45°	419.1	411.5	404.7	389.6	370.7	360.1	351.0	342.7	338.1	334.3	331.3
47.5°	394.9	388.1	379.0	362.3	347.2	337.4	328.3	320.0	315.4	310.9	307.1
50°	366.9	363.1	353.3	337.4	323.0	311.7	303.3	295.8	292.7	287.4	281.4
52.5°	341.9	335.1	326.8	313.9	301.1	287.4	276.1	271.6	266.3	263.2	257.9
55°	312.4	307.9	298.8	287.4	273.8	262.5	254.2	248.1	241.3	238.3	231.5
57.5°	287.4	279.1	274.6	260.2	247.4	236.0	230.0	223.9	216.3	211.8	208.8
60°	260.2	252.6	245.8	233.7	224.7	212.6	203.5	198.2	192.9	186.8	183.8
62.5°	233.7	227.7	219.4	209.5	198.2	188.4	181.5	174.0	171.0	164.9	162.6
65°	205.0	200.5	193.6	182.3	173.2	164.9	158.1	152.0	149.0	146.7	145.2
67.5°	179.3	173.2	168.7	158.9	149.0	142.2	138.4	134.6	130.9	128.6	126.3
70°	152.8	148.3	143.7	134.6	127.8	121.8	118.8	115.7	113.5	111.2	108.9
72.5°	125.6	123.3	118.8	112.7	107.4	102.9	100.6	96.8	94.6	90.8	89.3
75°	103.6	99.8	97.6	92.3	87.7	84.0	80.9	76.4	73.4	71.9	71.1
77.5°	81.7	80.2	77.2	72.6	70.3	66.6	62.0	60.5	59.0	59.0	58.2
80°	61.3	59.0	56.7	53.0	50.7	47.7	47.7	47.7	46.9	47.7	46.9
82.5°	41.6	40.1	38.6	36.3	35.6	35.6	36.3	36.3	36.3	36.3	36.3
85°	24.2	24.2	24.2	25.0	24.2	24.2	25.0	25.7	25.0	25.0	24.2
87.5°	11.3	11.3	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.6
90°	10.1	11.2	12.7	15.6	18.5	21.5	24.4	25.3	26.2	27.1	28.0
92.5°	36.0	36.7	37.4	38.7	40.1	41.4	42.8	43.5	44.1	44.8	45.5
95°	66.4	67.2	68.1	69.9	71.8	73.6	75.4	76.3	77.2	78.1	79.0
97.5°	103.3	103.9	104.6	105.9	107.3	108.6	110.0	111.1	112.3	113.4	114.5
100°	144.0	144.7	145.3	146.4	147.5	148.7	149.8	150.5	151.1	151.8	152.5
102.5°	187.1	187.4	188.2	189.8	191.4	193.0	194.6	195.3	195.9	196.6	197.3
105°	231.0	231.2	232.2	234.3	236.3	238.4	240.4	240.4	240.4	240.4	240.4
107.5°	283.1	283.2	283.7	284.6	285.5	286.4	287.3	288.0	288.6	289.3	290.0
110°	332.9	333.1	333.3	333.8	334.3	334.7	335.2	336.1	337.0	337.9	338.8

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	382.9	383.0	383.0	383.0	383.0	383.0	383.0	384.1	385.3	386.4	387.5
115°	435.7	436.0	435.8	435.3	434.9	434.4	434.0	434.2	434.4	434.7	434.9
117.5°	485.8	485.9	485.7	485.2	484.8	484.3	483.9	483.9	483.9	483.9	483.9
120°	538.2	538.9	538.3	537.2	536.1	534.9	533.8	533.6	533.4	533.1	532.9
122.5°	586.3	586.8	586.6	586.1	585.6	585.2	584.7	584.0	583.4	582.7	582.0
125°	636.4	636.7	636.5	636.0	635.6	635.1	634.7	633.8	632.9	632.0	631.1
127.5°	685.9	686.6	686.4	685.9	685.5	685.0	684.6	683.2	681.9	680.5	679.2
130°	734.6	735.5	735.2	734.5	733.8	733.2	732.5	731.6	730.7	729.8	728.9
132.5°	781.5	782.4	782.2	781.7	781.2	780.8	780.3	779.2	778.0	776.9	775.8
135°	827.5	828.2	828.1	827.9	827.6	827.4	827.2	826.3	825.4	824.5	823.6
137.5°	870.4	871.0	871.3	872.0	872.7	873.4	874.1	873.0	871.8	870.7	869.6
140°	916.2	916.8	916.9	917.2	917.4	917.7	917.9	917.7	917.4	917.2	916.9
142.5°	958.0	958.6	958.8	959.3	959.7	960.2	960.6	960.4	960.2	959.9	959.7
145°	999.2	999.4	999.7	1000.4	1001.1	1001.7	1002.4	1002.2	1002.0	1001.7	1001.5
147.5°	1038.6	1039.1	1039.4	1040.1	1040.8	1041.4	1042.1	1042.1	1042.1	1042.1	1042.1
150°	1076.6	1076.8	1077.0	1077.5	1077.9	1078.4	1078.8	1078.8	1078.8	1078.8	1078.8
152.5°	1110.1	1110.4	1110.5	1110.7	1111.0	1111.2	1111.4	1111.9	1112.3	1112.8	1113.3
155°	1142.0	1142.0	1142.1	1142.3	1142.6	1142.8	1143.0	1143.9	1144.8	1145.7	1146.6
157.5°	1170.6	1170.5	1170.6	1170.8	1171.1	1171.3	1171.5	1172.4	1173.3	1174.2	1175.1
160°	1197.2	1197.0	1197.0	1197.0	1197.0	1197.0	1197.0	1198.1	1199.3	1200.4	1201.5
162.5°	1220.7	1220.4	1220.5	1220.7	1221.0	1221.2	1221.4	1222.5	1223.7	1224.8	1225.9
165°	1241.1	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1242.2	1243.5	1244.9	1246.2
167.5°	1257.6	1257.1	1257.2	1257.4	1257.7	1257.9	1258.1	1259.5	1260.8	1262.2	1263.5
170°	1271.8	1271.4	1271.4	1271.4	1271.4	1271.4	1271.4	1273.0	1274.6	1276.1	1277.7
172.5°	1283.0	1282.6	1282.6	1282.6	1282.6	1282.6	1282.6	1284.0	1285.3	1286.7	1288.0
175°	1290.2	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1291.1	1292.4	1293.8	1295.1
177.5°	1294.2	1293.8	1293.8	1293.8	1293.8	1293.8	1293.8	1295.2	1296.5	1297.9	1299.2
180°	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.1	835.9	833.6	829.1	828.3	829.8	834.3	832.8	829.1	835.9	829.8
5°	789.0	785.2	783.7	785.2	780.6	778.4	782.9	780.6	782.9	783.7	785.9
7.5°	744.3	745.1	740.5	741.3	735.3	736.8	736.8	736.8	739.0	740.5	743.6
10°	705.8	707.3	702.0	702.7	698.2	695.2	697.4	702.0	702.0	702.0	703.5
12.5°	674.7	667.9	664.1	663.4	658.1	656.6	661.1	662.6	666.4	666.4	668.7
15°	636.2	634.6	631.6	631.6	618.8	621.8	623.3	628.6	636.2	630.1	631.6
17.5°	601.4	597.6	593.8	592.3	590.8	586.2	592.3	591.5	596.1	596.8	599.1
20°	570.4	567.3	559.8	560.5	562.0	555.2	559.0	559.0	563.5	568.1	573.4
22.5°	540.1	537.1	533.3	534.8	530.3	528.7	528.7	532.5	537.8	541.6	540.9
25°	516.6	511.3	509.1	506.8	504.5	506.1	503.8	507.6	511.3	513.6	511.3
27.5°	490.2	487.9	483.4	481.1	477.3	478.8	480.3	483.4	485.6	485.6	487.9
30°	464.5	461.4	459.9	457.6	457.6	454.6	455.4	458.4	460.7	462.9	466.0
32.5°	439.5	437.2	434.9	434.9	433.4	432.7	431.9	436.5	436.5	441.0	441.0
35°	419.1	415.3	415.3	411.5	413.0	412.3	410.7	413.8	414.5	417.6	416.8
37.5°	396.4	396.4	394.9	391.1	388.1	388.8	392.6	392.6	394.9	394.1	396.4
40°	373.7	372.2	372.2	369.9	369.1	368.4	369.1	369.9	373.7	372.9	373.7
42.5°	351.0	351.7	348.0	348.0	348.0	345.7	346.4	347.2	348.7	350.2	352.5
45°	329.0	327.5	326.8	325.3	323.8	324.5	323.8	326.8	326.0	327.5	329.8
47.5°	305.6	303.3	302.6	299.5	299.5	301.1	300.3	302.6	303.3	305.6	304.1
50°	282.9	279.9	277.6	278.4	273.8	275.3	275.3	277.6	279.9	280.6	282.1
52.5°	256.4	255.7	254.9	251.1	250.4	249.6	250.4	251.1	254.2	256.4	257.2
55°	230.7	230.0	225.4	223.9	221.6	221.6	223.1	223.9	229.2	230.0	233.0
57.5°	207.3	205.0	199.7	198.9	198.9	198.9	196.7	199.7	201.2	205.0	205.0
60°	181.5	181.5	177.0	177.0	177.8	177.0	177.0	177.8	177.8	180.8	182.3
62.5°	161.1	160.4	160.4	158.9	158.1	158.9	158.1	158.1	158.9	161.1	163.4
65°	143.0	142.2	141.5	140.7	139.2	139.2	139.9	141.5	141.5	143.0	143.7
67.5°	125.6	125.6	124.1	124.1	123.3	122.5	123.3	122.5	125.6	125.6	126.3
70°	108.2	107.4	105.1	104.4	102.1	102.9	102.9	105.1	105.9	107.4	108.9
72.5°	87.0	87.0	85.5	84.0	84.7	83.2	83.2	84.0	84.0	86.2	87.0
75°	71.9	70.3	69.6	70.3	69.6	71.1	69.6	69.6	71.1	71.1	71.1
77.5°	59.0	59.0	58.2	58.2	59.0	58.2	59.0	59.0	59.0	58.2	59.0
80°	48.4	47.7	47.7	47.7	46.9	46.9	46.9	46.9	46.9	46.9	46.9
82.5°	36.3	36.3	35.6	36.3	36.3	35.6	36.3	35.6	35.6	36.3	36.3
85°	24.2	25.7	24.2	24.2	25.0	25.0	25.7	25.0	25.7	24.2	25.0
87.5°	12.9	13.6	13.6	12.9	12.9	13.6	13.6	13.6	14.4	12.9	13.6
90°	28.5	28.7	29.2	29.7	30.1	30.6	30.1	29.7	29.2	28.7	28.5
92.5°	45.8	45.6	45.1	44.7	44.2	43.8	44.2	44.7	45.1	45.6	45.8
95°	79.5	79.5	79.5	79.5	79.5	79.5	79.5	79.5	79.5	79.5	79.5
97.5°	115.1	115.0	114.8	114.5	114.3	114.1	114.3	114.5	114.8	115.0	115.1
100°	152.8	153.0	153.5	153.9	154.4	154.8	154.4	153.9	153.5	153.0	152.8
102.5°	197.6	197.5	197.3	197.0	196.8	196.6	196.8	197.0	197.3	197.5	197.6
105°	240.4	240.6	241.1	241.6	242.0	242.5	242.0	241.6	241.1	240.6	240.4
107.5°	290.3	290.2	290.0	289.7	289.5	289.3	289.5	289.7	290.0	290.2	290.3
110°	339.2	339.0	338.5	338.1	337.6	337.2	337.6	338.1	338.5	339.0	339.2

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	388.1	388.1	388.1	388.1	388.1	388.1	388.1	388.1	388.1	388.1	388.1
115°	435.0	434.9	434.7	434.4	434.2	434.0	434.2	434.4	434.7	434.9	435.0
117.5°	483.9	483.6	482.9	482.2	481.5	480.8	481.5	482.2	482.9	483.6	483.9
120°	532.8	532.6	532.1	531.6	531.2	530.7	531.2	531.6	532.1	532.6	532.8
122.5°	581.7	581.4	580.7	580.0	579.3	578.6	579.3	580.0	580.7	581.4	581.7
125°	630.6	630.1	629.2	628.3	627.4	626.5	627.4	628.3	629.2	630.1	630.6
127.5°	678.5	678.0	677.1	676.2	675.3	674.4	675.3	676.2	677.1	678.0	678.5
130°	728.4	727.6	726.0	724.4	722.8	721.2	722.8	724.4	726.0	727.6	728.4
132.5°	775.2	774.6	773.5	772.4	771.2	770.1	771.2	772.4	773.5	774.6	775.2
135°	823.1	822.9	822.4	822.0	821.5	821.1	821.5	822.0	822.4	822.9	823.1
137.5°	869.0	868.7	868.0	867.3	866.6	865.9	866.6	867.3	868.0	868.7	869.0
140°	916.8	916.0	914.4	912.9	911.3	909.7	911.3	912.9	914.4	916.0	916.8
142.5°	959.6	959.0	957.9	956.8	955.6	954.5	955.6	956.8	957.9	959.0	959.6
145°	1001.4	1000.9	1000.0	999.1	998.2	997.3	998.2	999.1	1000.0	1000.9	1001.4
147.5°	1042.1	1041.4	1040.1	1038.7	1037.4	1036.0	1037.4	1038.7	1040.1	1041.4	1042.1
150°	1078.8	1078.1	1076.8	1075.4	1074.1	1072.7	1074.1	1075.4	1076.8	1078.1	1078.8
152.5°	1113.5	1112.9	1111.8	1110.7	1109.5	1108.4	1109.5	1110.7	1111.8	1112.9	1113.5
155°	1147.1	1146.3	1144.7	1143.1	1141.5	1139.9	1141.5	1143.1	1144.7	1146.3	1147.1
157.5°	1175.6	1174.9	1173.6	1172.2	1170.9	1169.5	1170.9	1172.2	1173.6	1174.9	1175.6
160°	1202.1	1201.6	1200.7	1199.8	1198.9	1198.0	1198.9	1199.8	1200.7	1201.6	1202.1
162.5°	1226.5	1225.7	1224.1	1222.6	1221.0	1219.4	1221.0	1222.6	1224.1	1225.7	1226.5
165°	1246.9	1246.1	1244.5	1243.0	1241.4	1239.8	1241.4	1243.0	1244.5	1246.1	1246.9
167.5°	1264.2	1263.5	1262.2	1260.8	1259.5	1258.1	1259.5	1260.8	1262.2	1263.5	1264.2
170°	1278.5	1277.7	1276.1	1274.6	1273.0	1271.4	1273.0	1274.6	1276.1	1277.7	1278.5
172.5°	1288.7	1287.9	1286.3	1284.7	1283.1	1281.5	1283.1	1284.7	1286.3	1287.9	1288.7
175°	1295.8	1295.0	1293.4	1291.9	1290.3	1288.7	1290.3	1291.9	1293.4	1295.0	1295.8
177.5°	1299.9	1299.1	1297.5	1295.9	1294.3	1292.7	1294.3	1295.9	1297.5	1299.1	1299.9
180°	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.9	838.9	835.9	829.8	835.9	839.6	843.4	849.5	852.5	852.5	857.0
5°	788.2	794.3	792.0	790.5	796.5	800.3	806.4	813.9	822.2	827.5	833.6
7.5°	745.8	749.6	753.4	753.4	759.5	767.8	776.9	785.9	796.5	804.1	808.6
10°	708.8	711.8	714.1	717.1	726.2	735.3	747.4	758.7	767.8	776.1	783.7
12.5°	673.2	677.8	683.1	685.3	692.1	703.5	714.8	728.4	742.8	751.1	758.7
15°	639.2	641.5	647.5	654.3	660.4	672.5	686.8	701.2	713.3	726.2	733.0
17.5°	604.4	605.1	621.0	617.2	636.9	648.3	655.8	669.4	689.1	699.7	710.3
20°	570.4	577.9	584.7	588.5	599.1	612.0	633.9	644.5	660.4	670.2	679.3
22.5°	543.9	555.2	555.2	564.3	569.6	581.7	597.6	618.0	635.4	642.2	655.1
25°	520.4	525.7	534.8	537.8	547.7	558.2	568.8	590.8	609.7	618.8	627.8
27.5°	490.2	497.0	509.1	509.1	521.9	533.3	546.1	560.5	579.4	592.3	602.1
30°	466.7	473.5	478.8	487.1	492.4	503.0	525.7	536.3	553.0	564.3	576.4
32.5°	444.8	450.1	454.6	463.7	469.7	481.8	494.0	512.9	527.2	537.8	550.7
35°	420.6	425.9	431.9	438.7	447.8	459.2	470.5	486.4	500.8	510.6	521.2
37.5°	397.9	401.7	410.7	415.3	422.8	433.4	447.8	464.5	477.3	484.9	495.5
40°	375.9	379.0	385.8	394.1	399.4	407.7	422.8	437.2	453.1	462.2	470.5
42.5°	352.5	356.3	362.3	370.7	379.0	388.1	396.4	413.0	427.4	434.9	444.0
45°	332.1	334.3	338.9	347.2	355.5	362.3	375.2	390.3	403.9	410.0	419.8
47.5°	307.9	310.1	316.9	320.7	329.8	338.9	351.7	366.9	379.0	385.0	394.1
50°	282.9	285.2	289.7	298.0	304.1	313.9	325.3	338.1	353.3	361.6	366.9
52.5°	258.7	263.2	267.0	273.8	281.4	291.2	301.8	313.9	326.8	335.1	341.2
55°	234.5	238.3	242.8	246.6	255.7	264.8	276.9	288.2	299.5	307.1	313.9
57.5°	207.3	212.6	217.1	224.7	231.5	239.0	252.6	261.7	275.3	280.6	286.7
60°	183.8	189.1	192.9	198.9	205.0	214.8	223.9	235.3	246.6	253.4	261.0
62.5°	164.1	166.4	168.7	174.7	180.8	189.9	198.9	210.3	222.4	226.2	232.2
65°	144.5	146.7	150.5	155.8	160.4	165.7	175.5	184.6	195.9	202.0	204.2
67.5°	127.8	130.1	130.9	134.6	138.4	144.5	149.8	158.9	169.4	173.2	177.8
70°	108.9	112.7	113.5	116.5	118.0	121.8	127.8	134.6	143.0	149.8	153.6
72.5°	87.0	92.3	93.8	98.3	100.6	104.4	108.9	114.2	119.5	122.5	125.6
75°	71.1	72.6	73.4	77.2	80.9	86.2	88.5	91.5	96.1	99.8	102.9
77.5°	59.0	59.8	60.5	60.5	61.3	64.3	68.8	72.6	75.6	77.2	79.4
80°	47.7	46.9	46.9	47.7	47.7	47.7	49.2	54.5	56.0	59.8	59.0
82.5°	37.1	35.6	36.3	35.6	35.6	35.6	35.6	36.3	36.3	38.6	40.1
85°	24.2	25.0	24.2	24.2	23.4	24.2	23.4	23.4	22.7	22.7	21.9
87.5°	12.9	13.6	12.9	12.9	12.1	12.9	12.1	12.1	11.3	11.3	9.8
90°	28.0	27.1	26.2	25.3	24.4	21.5	18.5	15.6	12.7	11.2	10.1
92.5°	45.5	44.8	44.1	43.5	42.8	41.4	40.1	38.7	37.4	36.7	36.0
95°	79.0	78.1	77.2	76.3	75.4	73.6	71.8	69.9	68.1	67.2	66.4
97.5°	114.5	113.4	112.3	111.1	110.0	108.6	107.3	105.9	104.6	103.9	103.3
100°	152.5	151.8	151.1	150.5	149.8	148.7	147.5	146.4	145.3	144.7	144.0
102.5°	197.3	196.6	195.9	195.3	194.6	193.0	191.4	189.8	188.2	187.4	187.1
105°	240.4	240.4	240.4	240.4	240.4	238.4	236.3	234.3	232.2	231.2	231.0
107.5°	290.0	289.3	288.6	288.0	287.3	286.4	285.5	284.6	283.7	283.2	283.1
110°	338.8	337.9	337.0	336.1	335.2	334.7	334.3	333.8	333.3	333.1	332.9

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	387.5	386.4	385.3	384.1	383.0	383.0	383.0	383.0	383.0	383.0	382.9
115°	434.9	434.7	434.4	434.2	434.0	434.4	434.9	435.3	435.8	436.0	435.7
117.5°	483.9	483.9	483.9	483.9	483.9	484.3	484.8	485.2	485.7	485.9	485.8
120°	532.9	533.1	533.4	533.6	533.8	534.9	536.1	537.2	538.3	538.9	538.2
122.5°	582.0	582.7	583.4	584.0	584.7	585.2	585.6	586.1	586.6	586.8	586.3
125°	631.1	632.0	632.9	633.8	634.7	635.1	635.6	636.0	636.5	636.7	636.4
127.5°	679.2	680.5	681.9	683.2	684.6	685.0	685.5	685.9	686.4	686.6	685.9
130°	728.9	729.8	730.7	731.6	732.5	733.2	733.8	734.5	735.2	735.5	734.6
132.5°	775.8	776.9	778.0	779.2	780.3	780.8	781.2	781.7	782.2	782.4	781.5
135°	823.6	824.5	825.4	826.3	827.2	827.4	827.6	827.9	828.1	828.2	827.5
137.5°	869.6	870.7	871.8	873.0	874.1	873.4	872.7	872.0	871.3	871.0	870.4
140°	916.9	917.2	917.4	917.7	917.9	917.7	917.4	917.2	916.9	916.8	916.2
142.5°	959.7	959.9	960.2	960.4	960.6	960.2	959.7	959.3	958.8	958.6	958.0
145°	1001.5	1001.7	1002.0	1002.2	1002.4	1001.7	1001.1	1000.4	999.7	999.4	999.2
147.5°	1042.1	1042.1	1042.1	1042.1	1042.1	1041.4	1040.8	1040.1	1039.4	1039.1	1038.6
150°	1078.8	1078.8	1078.8	1078.8	1078.8	1078.4	1077.9	1077.5	1077.0	1076.8	1076.6
152.5°	1113.3	1112.8	1112.3	1111.9	1111.4	1111.2	1111.0	1110.7	1110.5	1110.4	1110.1
155°	1146.6	1145.7	1144.8	1143.9	1143.0	1142.8	1142.6	1142.3	1142.1	1142.0	1142.0
157.5°	1175.1	1174.2	1173.3	1172.4	1171.5	1171.3	1171.1	1170.8	1170.6	1170.5	1170.6
160°	1201.5	1200.4	1199.3	1198.1	1197.0	1197.0	1197.0	1197.0	1197.0	1197.0	1197.2
162.5°	1225.9	1224.8	1223.7	1222.5	1221.4	1221.2	1221.0	1220.7	1220.5	1220.4	1220.7
165°	1246.2	1244.9	1243.5	1242.2	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1241.1
167.5°	1263.5	1262.2	1260.8	1259.5	1258.1	1257.9	1257.7	1257.4	1257.2	1257.1	1257.6
170°	1277.7	1276.1	1274.6	1273.0	1271.4	1271.4	1271.4	1271.4	1271.4	1271.4	1271.8
172.5°	1288.0	1286.7	1285.3	1284.0	1282.6	1282.6	1282.6	1282.6	1282.6	1282.6	1283.0
175°	1295.1	1293.8	1292.4	1291.1	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1290.2
177.5°	1299.2	1297.9	1296.5	1295.2	1293.8	1293.8	1293.8	1293.8	1293.8	1293.8	1294.2
180°	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8	1296.8

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.5	883.5	883.5	883.5
2.5°	860.8	866.1	876.7	885.8
5°	842.7	851.0	866.9	882.8
7.5°	820.7	833.6	854.0	876.0
10°	799.6	816.2	841.2	866.9
12.5°	778.4	795.8	822.2	855.5
15°	753.4	771.6	803.3	843.4
17.5°	731.5	755.7	784.4	824.5
20°	708.0	726.2	763.2	805.6
22.5°	678.5	708.8	743.6	788.2
25°	655.1	681.5	716.3	767.0
27.5°	626.3	657.3	699.7	744.3
30°	602.9	628.6	667.9	721.6
32.5°	575.6	605.9	646.8	699.7
35°	551.4	577.2	615.7	669.4
37.5°	522.7	550.7	593.8	641.5
40°	497.7	525.0	565.8	610.4
42.5°	467.5	496.2	537.1	574.9
45°	443.3	469.7	502.3	537.1
47.5°	413.8	441.8	473.5	497.7
50°	387.3	413.0	438.0	458.4
52.5°	358.5	382.0	404.7	419.8
55°	332.1	350.2	368.4	379.0
57.5°	301.1	318.5	333.6	339.6
60°	273.8	288.2	298.0	304.8
62.5°	245.1	255.7	263.2	267.0
65°	217.1	224.7	228.4	232.2
67.5°	188.4	195.2	197.4	202.0
70°	158.1	165.7	167.2	169.4
72.5°	135.4	135.4	138.4	141.5
75°	108.2	109.7	111.2	111.2
77.5°	84.7	84.7	86.2	87.0
80°	62.0	62.8	62.8	62.0
82.5°	42.4	43.9	42.4	41.6
85°	23.4	26.5	25.0	25.0
87.5°	9.8	9.8	11.3	9.8
90°	7.8	5.5	3.3	1.0
92.5°	34.7	33.3	32.0	30.6
95°	64.8	63.3	61.7	60.1
97.5°	102.2	101.1	99.9	98.8
100°	142.6	141.3	139.9	138.5
102.5°	186.4	185.7	185.1	184.4
105°	230.5	230.1	229.6	229.2
107.5°	282.9	282.6	282.4	282.2
110°	332.4	332.0	331.5	331.1

TEST NUMBER: P1032273

CATALOG NUMBER: S123RDIW-B560D1030UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	382.7	382.4	382.2	382.0
115°	435.0	434.3	433.7	433.0
117.5°	485.6	485.3	485.1	484.9
120°	536.9	535.5	534.2	532.8
122.5°	585.4	584.5	583.6	582.7
125°	635.7	635.0	634.3	633.6
127.5°	684.6	683.2	681.9	680.5
130°	732.8	731.0	729.2	727.4
132.5°	779.7	777.8	776.0	774.2
135°	826.2	824.8	823.5	822.1
137.5°	869.3	868.2	867.0	865.9
140°	915.1	914.0	912.8	911.7
142.5°	956.9	955.8	954.6	953.5
145°	998.7	998.2	997.8	997.3
147.5°	1037.7	1036.8	1035.9	1035.0
150°	1076.1	1075.6	1075.2	1074.7
152.5°	1109.4	1108.7	1108.0	1107.3
155°	1142.0	1142.0	1142.0	1142.0
157.5°	1170.8	1171.1	1171.3	1171.5
160°	1197.7	1198.1	1198.6	1199.0
162.5°	1221.4	1222.1	1222.8	1223.5
165°	1241.8	1242.5	1243.1	1243.8
167.5°	1258.5	1259.4	1260.3	1261.2
170°	1272.7	1273.6	1274.5	1275.4
172.5°	1283.9	1284.8	1285.7	1286.6
175°	1291.1	1292.0	1292.9	1293.8
177.5°	1295.1	1296.0	1296.9	1297.8
180°	1296.8	1296.8	1296.8	1296.8

(END OF REPORT)