

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032372

Luminaire Tested: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032372
REPORT IS A COMBINATION OF REPORTS P994619 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D1030UB30-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7244.0 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	97	92	89	86	88	85	82	79	70	68	66	57	55	54	44	43	42
2	88	81	76	71	80	75	70	65	62	58	55	50	48	46	39	38	36
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32
4	74	64	56	51	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	26	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	17
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13232	13232	13232	13232
5°	13242	15240	13276	11306
10°	13125	18396	13182	9875
15°	12990	20879	12990	8707
20°	12724	22521	12795	7724
25°	12529	21397	12504	7048
30°	12302	14825	12277	6387
35°	12028	9518	11974	5888
40°	11689	6721	11631	5393
45°	11098	5379	11082	4909
50°	10371	4500	10337	4344
55°	9554	3708	9478	3683
60°	8751	3065	8664	3132
65°	7810	2453	7861	2656
70°	6944	1705	7130	2146
75°	5885	1265	6124	1650
80°	4685	838	5087	1238
85°	3333	397	3640	769

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 17665 cd/sqm

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	1.7
10°-20°	377.9	5.2
20°-30°	595.2	8.2
30°-40°	618.9	8.5
40°-50°	529.5	7.3
50°-60°	403.7	5.6
60°-70°	258.6	3.6
70°-80°	123.9	1.7
80°-90°	35.3	0.5
90°-100°	48.4	0.7
100°-110°	233.8	3.2
110°-120°	572.9	7.9
120°-130°	727.3	10.0
130°-140°	776.9	10.7
140°-150°	726.5	10.0
150°-160°	586.0	8.1
160°-170°	378.2	5.2
170°-180°	130.3	1.8
0°-30°	1093.8	15.1
0°-40°	1712.7	23.6
0°-60°	2645.9	36.5
0°-90°	3063.7	42.3
90°-120°	855.0	11.8
90°-150°	3085.8	42.6
90°-180°	4180.0	57.7
0°-180°	7244.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1229	1229	1229	1229	1229	
5°	1228	1460	1231	1083	1228	116
15°	1174	2074	1174	865	1174	330
25°	1067	2138	1065	704	1067	492
35°	931	927	927	574	931	583
45°	747	495	746	452	747	575
55°	527	310	523	308	527	472
65°	323	179	325	194	323	323
75°	155	76	161	99	155	167
85°	35	18	38	35	35	39
90°	1	31	1	31	1	5
95°	62	39	62	39	62	74
105°	304	45	304	45	304	322
115°	570	599	570	599	570	562
125°	803	819	803	819	803	717
135°	999	1010	999	1010	999	769
145°	1153	1164	1153	1164	1153	722
155°	1270	1268	1270	1268	1270	585
165°	1340	1337	1340	1337	1340	379
175°	1371	1366	1371	1366	1371	130
180°	1371	1371	1371	1371	1371	

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1232.4	1240.9	1247.2	1251.4	1261.9	1268.2	1273.5	1283.0	1283.0	1285.1	1289.3
5°	1228.2	1246.1	1258.8	1275.6	1297.7	1308.2	1323.0	1335.6	1353.5	1363.0	1372.4
7.5°	1218.8	1244.0	1270.3	1295.6	1328.2	1349.3	1364.0	1396.6	1419.8	1448.2	1470.3
10°	1206.1	1240.9	1274.5	1313.5	1357.7	1389.3	1411.4	1454.5	1498.7	1538.7	1572.4
12.5°	1190.3	1232.4	1280.9	1328.2	1390.3	1421.9	1457.7	1511.4	1574.5	1625.0	1670.3
15°	1173.5	1221.9	1276.7	1334.5	1412.4	1456.6	1508.2	1573.4	1644.0	1716.6	1778.7
17.5°	1147.2	1208.2	1269.3	1353.5	1445.0	1471.4	1515.6	1605.0	1692.4	1757.6	1833.4
20°	1120.9	1189.3	1266.1	1341.9	1440.8	1501.9	1542.9	1637.7	1731.3	1810.3	1882.9
22.5°	1096.7	1168.2	1248.2	1344.0	1436.6	1497.7	1549.2	1648.2	1756.6	1845.0	1934.4
25°	1067.2	1145.1	1233.5	1324.0	1436.6	1482.9	1539.8	1654.5	1769.2	1871.3	1981.8
27.5°	1035.6	1114.6	1201.9	1294.5	1397.7	1466.1	1521.9	1645.0	1785.0	1894.5	2008.1
30°	1004.1	1085.1	1169.3	1252.4	1368.2	1433.5	1497.7	1633.4	1793.4	1918.7	2006.0
32.5°	973.5	1041.9	1125.1	1206.1	1320.9	1392.4	1465.0	1621.9	1796.6	1901.8	1943.9
35°	931.4	1003.0	1070.4	1156.7	1272.4	1343.0	1428.2	1620.8	1782.9	1848.1	1827.1
37.5°	892.5	952.5	1016.7	1093.5	1212.5	1304.0	1392.4	1593.4	1737.6	1741.8	1622.9
40°	849.3	898.8	952.5	1033.5	1161.9	1252.4	1348.2	1551.3	1655.5	1593.4	1384.0
42.5°	799.9	844.1	886.2	965.1	1105.1	1206.1	1309.3	1498.7	1536.6	1393.5	1175.6
45°	747.3	783.0	822.0	905.1	1045.1	1145.1	1248.2	1417.7	1378.7	1176.7	969.3
47.5°	692.5	723.0	760.9	836.7	980.9	1083.0	1180.9	1301.9	1203.0	986.2	812.5
50°	637.8	662.0	698.8	776.7	915.7	1008.3	1098.8	1177.7	1038.8	846.2	671.5
52.5°	584.1	603.1	641.0	707.3	842.0	930.4	995.6	1026.2	885.1	698.8	583.1
55°	527.3	548.3	573.6	641.0	774.6	839.9	883.0	882.0	736.7	592.5	482.0
57.5°	472.6	491.5	513.6	581.0	689.4	733.6	770.4	752.5	614.6	485.2	413.6
60°	424.1	434.7	458.9	515.7	597.8	635.7	656.7	626.2	502.0	409.4	342.1
62.5°	371.5	382.0	402.0	455.7	506.2	526.2	544.1	505.2	414.7	333.6	292.6
65°	323.1	336.8	349.4	392.6	419.9	444.1	442.0	409.4	324.2	271.5	237.9
67.5°	281.0	286.3	296.8	323.1	335.7	353.6	354.7	317.8	261.0	221.0	201.0
70°	235.8	241.0	248.4	261.0	269.4	273.6	271.5	238.9	196.8	172.6	154.7
72.5°	196.8	195.8	201.0	201.0	209.4	208.4	202.1	176.8	149.5	129.5	118.9
75°	154.7	155.8	156.8	154.7	151.6	147.3	142.1	123.1	105.2	95.8	86.3
77.5°	121.0	118.9	120.0	112.6	108.4	104.2	96.8	87.4	72.6	70.5	66.3
80°	86.3	85.3	84.2	81.0	71.6	67.4	62.1	56.8	53.7	51.6	50.5
82.5°	57.9	57.9	55.8	49.5	44.2	41.0	40.0	37.9	34.7	34.7	33.7
85°	34.7	33.7	31.6	25.3	22.1	22.1	22.1	22.1	20.0	20.0	18.9
87.5°	13.7	12.6	9.5	9.5	8.4	8.4	8.4	7.4	7.4	6.3	6.3
90°	1.0	3.3	5.5	7.8	10.1	11.2	12.7	15.6	18.5	21.5	24.4
92.5°	23.4	22.0	20.7	19.3	18.0	17.3	18.3	20.4	22.4	24.5	26.5
95°	62.1	52.8	43.6	34.3	25.0	20.4	21.6	24.1	26.6	29.1	31.6
97.5°	113.1	106.8	100.4	94.1	87.8	84.6	78.8	67.3	55.7	44.2	32.6
100°	172.2	176.7	181.2	185.7	190.2	192.5	174.8	139.5	104.2	68.9	33.6
102.5°	239.4	242.3	245.3	248.2	251.1	252.6	232.9	193.5	154.2	114.8	75.4
105°	303.6	306.1	308.6	311.1	313.6	314.8	304.6	284.2	263.9	243.5	223.1
107.5°	371.8	373.8	375.9	377.9	380.0	381.0	382.7	386.1	389.5	392.9	396.3
110°	440.1	441.9	443.7	445.5	447.3	448.2	449.4	451.9	454.4	456.9	459.4

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	505.3	506.9	508.5	510.0	511.6	512.4	513.6	516.1	518.6	521.1	523.6
115°	569.5	570.9	572.2	573.6	574.9	575.6	576.6	578.7	580.7	582.8	584.8
117.5°	632.6	634.2	635.8	637.4	639.0	639.8	640.4	641.5	642.6	643.8	644.9
120°	690.7	692.7	694.8	696.8	698.9	699.9	700.2	700.9	701.6	702.2	702.9
122.5°	749.8	751.4	753.0	754.5	756.1	756.9	757.4	758.3	759.2	760.1	761.0
125°	802.8	804.6	806.4	808.2	810.0	810.9	811.4	812.3	813.2	814.1	815.0
127.5°	855.7	857.5	859.3	861.2	863.0	863.9	864.5	865.6	866.7	867.9	869.0
130°	904.6	906.4	908.2	910.1	911.9	912.8	913.3	914.2	915.1	916.0	916.9
132.5°	951.5	953.3	955.1	956.9	958.7	959.6	959.9	960.6	961.3	962.0	962.7
135°	999.4	1000.8	1002.1	1003.5	1004.8	1005.5	1006.0	1006.9	1007.8	1008.7	1009.6
137.5°	1040.1	1041.9	1043.7	1045.6	1047.4	1048.3	1048.5	1049.0	1049.4	1049.9	1050.3
140°	1080.9	1082.3	1083.6	1085.0	1086.3	1087.0	1087.3	1088.0	1088.7	1089.3	1090.0
142.5°	1118.6	1120.0	1121.3	1122.7	1124.0	1124.7	1125.0	1125.7	1126.4	1127.0	1127.7
145°	1153.2	1154.8	1156.4	1157.9	1159.5	1160.3	1160.5	1161.0	1161.5	1161.9	1162.4
147.5°	1186.8	1187.9	1189.1	1190.2	1191.3	1191.9	1192.1	1192.6	1193.1	1193.5	1194.0
150°	1217.4	1218.1	1218.7	1219.4	1220.1	1220.4	1220.6	1221.1	1221.6	1222.0	1222.5
152.5°	1244.9	1245.1	1245.3	1245.6	1245.8	1245.9	1246.0	1246.2	1246.5	1246.7	1246.9
155°	1270.4	1269.9	1269.5	1269.0	1268.5	1268.3	1268.4	1268.6	1268.9	1269.1	1269.3
157.5°	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7	1290.6	1290.4	1290.1	1289.9	1289.7
160°	1309.1	1308.9	1308.7	1308.4	1308.2	1308.1	1308.0	1307.7	1307.5	1307.2	1307.0
162.5°	1326.4	1325.7	1325.0	1324.3	1323.6	1323.3	1323.2	1323.0	1322.7	1322.5	1322.3
165°	1339.6	1338.9	1338.3	1337.6	1336.9	1336.6	1336.5	1336.3	1336.0	1335.8	1335.6
167.5°	1350.8	1349.9	1349.0	1348.1	1347.2	1346.8	1346.8	1346.8	1346.8	1346.8	1346.8
170°	1360.0	1359.1	1358.2	1357.3	1356.4	1355.9	1355.9	1355.9	1355.9	1355.9	1355.9
172.5°	1366.1	1365.0	1363.8	1362.7	1361.6	1361.0	1361.1	1361.3	1361.6	1361.8	1362.0
175°	1371.2	1370.1	1368.9	1367.8	1366.7	1366.1	1366.2	1366.4	1366.7	1366.9	1367.1
177.5°	1373.3	1372.2	1371.0	1369.9	1368.8	1368.2	1368.3	1368.5	1368.8	1369.0	1369.2
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1297.7	1297.7	1307.2	1316.6	1311.4	1314.5	1326.1	1321.9	1330.3	1329.3	1332.4
5°	1395.6	1407.2	1416.6	1436.6	1439.8	1436.6	1456.6	1461.9	1471.4	1459.8	1465.0
7.5°	1506.1	1530.3	1553.5	1582.9	1592.4	1594.5	1605.0	1619.8	1632.4	1609.2	1620.8
10°	1613.4	1650.3	1697.6	1724.0	1747.1	1755.5	1763.9	1773.4	1788.2	1801.8	1791.3
12.5°	1729.2	1782.9	1828.1	1875.5	1903.9	1900.8	1925.0	1931.3	1942.9	1946.0	1950.2
15°	1823.9	1899.7	1928.1	1998.6	2005.0	2026.0	2053.4	2077.6	2080.7	2074.4	2074.4
17.5°	1914.5	1979.7	2030.2	2087.1	2098.6	2116.5	2151.3	2162.8	2167.0	2166.0	2166.0
20°	1988.1	2031.3	2116.5	2163.9	2182.8	2206.0	2230.2	2244.9	2248.1	2252.3	2246.0
22.5°	2036.5	2101.8	2171.3	2210.2	2226.0	2234.4	2250.2	2254.4	2249.1	2250.2	2251.2
25°	2074.4	2138.6	2180.7	2191.3	2190.2	2179.7	2168.1	2148.1	2146.0	2137.6	2120.7
27.5°	2085.0	2109.2	2103.9	2060.7	2017.6	2013.4	1943.9	1906.0	1862.9	1869.2	1845.0
30°	2028.1	1996.5	1921.8	1812.4	1767.1	1693.4	1615.5	1534.5	1502.9	1468.2	1532.4
32.5°	1889.2	1776.6	1644.0	1501.9	1426.1	1360.8	1277.7	1218.8	1185.1	1156.7	1211.4
35°	1679.7	1504.0	1328.2	1193.5	1131.4	1072.5	994.6	965.1	923.0	927.2	932.5
37.5°	1410.3	1216.7	1084.0	951.4	910.4	886.2	829.3	784.1	769.4	765.1	765.1
40°	1157.7	998.8	880.9	776.7	745.2	725.2	679.9	658.8	643.1	638.9	644.1
42.5°	957.8	822.0	730.4	661.0	638.9	613.6	594.6	568.3	565.2	557.8	567.3
45°	804.1	686.2	617.8	567.3	548.3	538.9	517.8	502.0	495.7	494.7	502.0
47.5°	682.0	590.4	530.4	498.9	484.1	474.7	456.8	450.5	444.1	446.2	443.1
50°	572.5	504.1	465.2	436.8	427.3	417.8	406.3	399.9	396.8	396.8	395.7
52.5°	491.5	434.7	409.4	383.1	378.9	373.6	361.0	356.8	351.5	350.5	354.7
55°	421.0	382.0	356.8	341.0	336.8	326.3	321.0	315.7	312.6	310.5	311.5
57.5°	359.9	330.5	313.6	300.0	292.6	288.4	278.9	277.9	275.7	275.7	274.7
60°	309.4	288.4	268.4	260.0	254.7	249.4	248.4	242.1	238.9	241.0	240.0
62.5°	262.1	245.2	233.6	224.2	221.0	216.8	213.7	211.5	208.4	209.4	209.4
65°	218.9	205.2	196.8	188.4	187.3	183.1	182.1	180.0	180.0	178.9	181.0
67.5°	180.0	170.5	163.1	157.9	154.7	155.8	151.6	148.4	148.4	147.3	150.5
70°	143.1	137.9	130.5	124.2	120.0	120.0	114.7	113.7	113.7	113.7	112.6
72.5°	110.5	101.0	97.9	95.8	95.8	95.8	93.7	93.7	92.6	93.7	92.6
75°	82.1	81.0	78.9	77.9	77.9	76.8	75.8	75.8	75.8	75.8	75.8
77.5°	64.2	64.2	62.1	61.0	61.0	61.0	60.0	60.0	58.9	58.9	58.9
80°	47.4	47.4	45.3	45.3	45.3	44.2	44.2	44.2	45.3	44.2	44.2
82.5°	32.6	32.6	31.6	32.6	31.6	30.5	30.5	30.5	29.5	30.5	30.5
85°	18.9	18.9	17.9	16.8	17.9	17.9	16.8	17.9	16.8	17.9	16.8
87.5°	7.4	6.3	6.3	6.3	5.3	6.3	5.3	5.3	6.3	5.3	6.3
90°	25.3	26.2	27.1	28.0	28.5	28.7	29.2	29.7	30.1	30.6	30.1
92.5°	28.1	29.7	31.2	32.8	33.6	33.7	33.9	34.2	34.4	34.6	34.4
95°	33.2	34.8	36.3	37.9	38.7	38.7	38.7	38.7	38.7	38.7	38.7
97.5°	34.4	36.2	38.0	39.8	40.7	40.8	41.1	41.3	41.6	41.8	41.6
100°	35.4	37.2	39.1	40.9	41.8	41.9	42.1	42.4	42.6	42.8	42.6
102.5°	67.9	60.5	53.0	45.5	41.8	42.0	42.5	42.9	43.4	43.8	43.4
105°	183.0	143.0	102.9	62.8	42.8	43.0	43.5	43.9	44.4	44.8	44.4
107.5°	361.4	326.6	291.7	256.8	239.4	224.6	194.9	165.2	135.6	105.9	135.6
110°	451.9	444.5	437.0	429.5	425.8	409.6	377.3	344.9	312.6	280.2	312.6

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	525.6	527.7	529.7	531.8	532.8	532.6	532.1	531.7	531.2	530.8	531.2
115°	587.0	589.3	591.5	593.8	594.9	595.4	596.3	597.2	598.1	599.0	598.1
117.5°	646.7	648.5	650.3	652.1	653.0	653.1	653.3	653.6	653.8	654.0	653.8
120°	704.7	706.5	708.4	710.2	711.1	711.1	711.1	711.1	711.1	711.1	711.1
122.5°	762.1	763.3	764.4	765.5	766.1	766.2	766.4	766.7	766.9	767.1	766.9
125°	815.4	815.9	816.3	816.8	817.0	817.2	817.7	818.2	818.6	819.1	818.6
127.5°	869.7	870.3	871.0	871.7	872.0	871.8	871.3	870.9	870.4	870.0	870.4
130°	917.8	918.7	919.6	920.5	920.9	920.7	920.2	919.8	919.3	918.9	919.3
132.5°	963.6	964.5	965.4	966.3	966.8	966.5	965.8	965.1	964.4	963.7	964.4
135°	1010.3	1010.9	1011.6	1012.3	1012.6	1012.3	1011.6	1010.9	1010.3	1009.6	1010.3
137.5°	1051.4	1052.6	1053.7	1054.8	1055.4	1055.2	1054.7	1054.3	1053.8	1053.4	1053.8
140°	1090.9	1091.8	1092.7	1093.6	1094.1	1093.9	1093.4	1093.0	1092.5	1092.1	1092.5
142.5°	1128.4	1129.1	1129.8	1130.5	1130.8	1130.5	1129.8	1129.1	1128.4	1127.7	1128.4
145°	1162.8	1163.3	1163.7	1164.2	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4
147.5°	1194.4	1194.9	1195.3	1195.8	1196.0	1195.4	1194.3	1193.2	1192.0	1190.9	1192.0
150°	1222.9	1223.4	1223.8	1224.3	1224.5	1224.2	1223.5	1222.8	1222.2	1221.5	1222.2
152.5°	1247.8	1248.7	1249.6	1250.5	1251.0	1250.4	1249.3	1248.2	1247.0	1245.9	1247.0
155°	1270.4	1271.6	1272.7	1273.8	1274.4	1273.7	1272.4	1271.0	1269.7	1268.3	1269.7
157.5°	1291.1	1292.4	1293.8	1295.1	1295.8	1294.9	1293.1	1291.3	1289.5	1287.7	1289.5
160°	1308.4	1309.7	1311.1	1312.4	1313.1	1312.3	1310.7	1309.2	1307.6	1306.0	1307.6
162.5°	1323.9	1325.5	1327.0	1328.6	1329.4	1328.7	1327.4	1326.0	1324.7	1323.3	1324.7
165°	1337.4	1339.2	1341.0	1342.8	1343.7	1342.9	1341.3	1339.8	1338.2	1336.6	1338.2
167.5°	1348.6	1350.4	1352.2	1354.0	1354.9	1354.0	1352.2	1350.4	1348.6	1346.8	1348.6
170°	1357.7	1359.5	1361.4	1363.2	1364.1	1363.2	1361.4	1359.5	1357.7	1355.9	1357.7
172.5°	1363.8	1365.6	1367.5	1369.3	1370.2	1369.2	1367.1	1365.1	1363.0	1361.0	1363.0
175°	1368.7	1370.3	1371.9	1373.5	1374.3	1373.4	1371.6	1369.7	1367.9	1366.1	1367.9
177.5°	1371.0	1372.8	1374.6	1376.4	1377.3	1376.2	1373.9	1371.6	1369.4	1367.1	1369.4
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1327.2	1320.9	1316.6	1313.5	1310.3	1319.8	1307.2	1293.5	1284.0	1277.7	1275.6
5°	1466.1	1452.4	1440.8	1431.4	1433.5	1433.5	1411.4	1387.2	1366.1	1354.5	1341.9
7.5°	1627.1	1612.4	1589.2	1584.0	1579.8	1553.5	1531.4	1487.1	1460.8	1434.5	1411.4
10°	1787.1	1768.2	1746.1	1738.7	1728.2	1695.5	1661.9	1605.0	1572.4	1524.0	1493.5
12.5°	1936.6	1913.4	1891.3	1886.0	1870.2	1841.8	1783.9	1725.0	1669.2	1617.7	1564.0
15°	2061.8	2055.5	2021.8	2000.8	1966.0	1927.1	1914.5	1834.5	1763.9	1710.3	1613.4
17.5°	2167.0	2137.6	2106.0	2092.3	2078.6	2033.4	1988.1	1906.0	1830.3	1751.3	1689.2
20°	2251.2	2218.6	2196.5	2176.5	2170.2	2118.6	2047.1	1974.4	1891.3	1802.9	1721.8
22.5°	2255.5	2251.2	2236.5	2224.9	2212.3	2178.6	2121.8	2031.3	1942.9	1846.0	1739.7
25°	2168.1	2161.8	2203.9	2193.4	2201.8	2189.1	2158.6	2082.8	1979.7	1866.0	1758.7
27.5°	1905.0	1969.2	2035.5	2058.6	2074.4	2119.7	2134.4	2092.3	2009.2	1888.1	1768.2
30°	1547.1	1632.4	1739.7	1797.6	1841.8	1926.0	2035.5	2049.2	2010.2	1913.4	1766.1
32.5°	1214.6	1292.4	1378.7	1447.2	1506.1	1678.7	1826.0	1932.3	1951.3	1900.8	1771.3
35°	978.8	1012.5	1094.6	1159.8	1239.8	1387.2	1560.8	1732.4	1848.1	1854.5	1755.5
37.5°	807.2	825.1	896.7	933.5	980.9	1110.4	1272.4	1496.6	1676.6	1761.8	1711.3
40°	668.3	709.4	750.4	771.5	805.1	894.6	1050.4	1226.1	1449.3	1607.1	1642.9
42.5°	579.9	597.8	624.1	653.6	674.6	752.5	856.7	1017.7	1218.8	1438.7	1537.7
45°	511.5	517.8	545.2	564.1	586.2	641.0	714.6	849.3	1026.2	1243.0	1411.4
47.5°	454.7	467.3	482.0	493.6	508.3	550.4	613.6	711.5	867.2	1060.9	1241.9
50°	404.2	411.5	430.5	435.7	446.2	475.7	524.1	598.9	727.3	882.0	1069.3
52.5°	356.8	370.5	377.8	385.2	394.7	418.9	450.5	511.5	608.3	753.6	912.5
55°	320.0	324.2	334.7	341.0	348.4	365.2	392.6	437.8	513.6	629.4	779.9
57.5°	284.2	284.2	294.7	300.0	307.3	320.0	344.2	378.9	433.6	519.9	657.8
60°	246.3	247.3	255.8	262.1	264.2	276.8	296.8	324.2	366.3	429.4	542.0
62.5°	212.6	217.9	222.1	224.2	231.5	238.9	255.8	274.7	304.2	359.9	439.9
65°	184.2	185.2	188.4	190.5	193.7	202.1	214.7	227.3	252.6	293.6	358.9
67.5°	151.6	155.8	160.0	160.0	163.1	167.3	180.0	190.5	209.4	233.6	277.9
70°	113.7	115.8	122.1	125.2	129.5	136.8	143.1	149.5	164.2	182.1	215.8
72.5°	94.7	94.7	96.8	97.9	97.9	103.1	112.6	118.9	126.3	138.9	162.1
75°	75.8	75.8	78.9	77.9	80.0	82.1	83.1	87.4	91.6	101.0	114.7
77.5°	60.0	61.0	61.0	62.1	62.1	63.1	64.2	66.3	68.4	73.7	80.0
80°	44.2	45.3	45.3	46.3	46.3	47.4	48.4	49.5	51.6	53.7	56.8
82.5°	30.5	31.6	31.6	32.6	31.6	32.6	33.7	33.7	34.7	36.8	37.9
85°	17.9	17.9	18.9	17.9	17.9	17.9	18.9	18.9	20.0	23.2	23.2
87.5°	5.3	6.3	5.3	6.3	6.3	6.3	6.3	7.4	7.4	8.4	9.5
90°	29.7	29.2	28.7	28.5	28.0	27.1	26.2	25.3	24.4	21.5	18.5
92.5°	34.2	33.9	33.7	33.6	32.8	31.2	29.7	28.1	26.5	24.5	22.4
95°	38.7	38.7	38.7	38.7	37.9	36.3	34.8	33.2	31.6	29.1	26.6
97.5°	41.3	41.1	40.8	40.7	39.8	38.0	36.2	34.4	32.6	44.2	55.7
100°	42.4	42.1	41.9	41.8	40.9	39.1	37.2	35.4	33.6	68.9	104.2
102.5°	42.9	42.5	42.0	41.8	45.5	53.0	60.5	67.9	75.4	114.8	154.2
105°	43.9	43.5	43.0	42.8	62.8	102.9	143.0	183.0	223.1	243.5	263.9
107.5°	165.2	194.9	224.6	239.4	256.8	291.7	326.6	361.4	396.3	392.9	389.5
110°	344.9	377.3	409.6	425.8	429.5	437.0	444.5	451.9	459.4	456.9	454.4

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	531.7	532.1	532.6	532.8	531.8	529.7	527.7	525.6	523.6	521.1	518.6
115°	597.2	596.3	595.4	594.9	593.8	591.5	589.3	587.0	584.8	582.8	580.7
117.5°	653.6	653.3	653.1	653.0	652.1	650.3	648.5	646.7	644.9	643.8	642.6
120°	711.1	711.1	711.1	711.1	710.2	708.4	706.5	704.7	702.9	702.2	701.6
122.5°	766.7	766.4	766.2	766.1	765.5	764.4	763.3	762.1	761.0	760.1	759.2
125°	818.2	817.7	817.2	817.0	816.8	816.3	815.9	815.4	815.0	814.1	813.2
127.5°	870.9	871.3	871.8	872.0	871.7	871.0	870.3	869.7	869.0	867.9	866.7
130°	919.8	920.2	920.7	920.9	920.5	919.6	918.7	917.8	916.9	916.0	915.1
132.5°	965.1	965.8	966.5	966.8	966.3	965.4	964.5	963.6	962.7	962.0	961.3
135°	1010.9	1011.6	1012.3	1012.6	1012.3	1011.6	1010.9	1010.3	1009.6	1008.7	1007.8
137.5°	1054.3	1054.7	1055.2	1055.4	1054.8	1053.7	1052.6	1051.4	1050.3	1049.9	1049.4
140°	1093.0	1093.4	1093.9	1094.1	1093.6	1092.7	1091.8	1090.9	1090.0	1089.3	1088.7
142.5°	1129.1	1129.8	1130.5	1130.8	1130.5	1129.8	1129.1	1128.4	1127.7	1127.0	1126.4
145°	1164.4	1164.4	1164.4	1164.4	1164.2	1163.7	1163.3	1162.8	1162.4	1161.9	1161.5
147.5°	1193.2	1194.3	1195.4	1196.0	1195.8	1195.3	1194.9	1194.4	1194.0	1193.5	1193.1
150°	1222.8	1223.5	1224.2	1224.5	1224.3	1223.8	1223.4	1222.9	1222.5	1222.0	1221.6
152.5°	1248.2	1249.3	1250.4	1251.0	1250.5	1249.6	1248.7	1247.8	1246.9	1246.7	1246.5
155°	1271.0	1272.4	1273.7	1274.4	1273.8	1272.7	1271.6	1270.4	1269.3	1269.1	1268.9
157.5°	1291.3	1293.1	1294.9	1295.8	1295.1	1293.8	1292.4	1291.1	1289.7	1289.9	1290.1
160°	1309.2	1310.7	1312.3	1313.1	1312.4	1311.1	1309.7	1308.4	1307.0	1307.2	1307.5
162.5°	1326.0	1327.4	1328.7	1329.4	1328.6	1327.0	1325.5	1323.9	1322.3	1322.5	1322.7
165°	1339.8	1341.3	1342.9	1343.7	1342.8	1341.0	1339.2	1337.4	1335.6	1335.8	1336.0
167.5°	1350.4	1352.2	1354.0	1354.9	1354.0	1352.2	1350.4	1348.6	1346.8	1346.8	1346.8
170°	1359.5	1361.4	1363.2	1364.1	1363.2	1361.4	1359.5	1357.7	1355.9	1355.9	1355.9
172.5°	1365.1	1367.1	1369.2	1370.2	1369.3	1367.5	1365.6	1363.8	1362.0	1361.8	1361.6
175°	1369.7	1371.6	1373.4	1374.3	1373.5	1371.9	1370.3	1368.7	1367.1	1366.9	1366.7
177.5°	1371.6	1373.9	1376.2	1377.3	1376.4	1374.6	1372.8	1371.0	1369.2	1369.0	1368.8
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1272.4	1267.2	1261.9	1261.9	1250.3	1239.8	1234.6	1236.7	1230.3	1221.9	1213.5
5°	1328.2	1307.2	1303.0	1291.4	1275.6	1253.5	1241.9	1231.4	1218.8	1201.9	1186.1
7.5°	1379.8	1352.4	1337.7	1326.1	1295.6	1265.1	1239.8	1223.0	1200.9	1175.6	1156.7
10°	1447.2	1396.6	1380.8	1354.5	1311.4	1268.2	1238.8	1211.4	1180.9	1151.4	1126.1
12.5°	1500.8	1442.9	1413.5	1387.2	1331.4	1276.7	1227.2	1193.5	1156.7	1124.0	1091.4
15°	1561.9	1496.6	1445.0	1413.5	1343.0	1276.7	1220.9	1173.5	1132.5	1092.5	1064.1
17.5°	1591.3	1509.2	1486.1	1440.8	1338.7	1272.4	1204.0	1153.5	1104.0	1057.7	1024.1
20°	1637.7	1541.9	1484.0	1453.5	1363.0	1265.1	1185.1	1127.2	1075.6	1026.2	990.4
22.5°	1640.8	1536.6	1498.7	1440.8	1329.3	1243.0	1168.2	1097.7	1037.7	991.4	954.6
25°	1633.4	1527.1	1474.5	1428.2	1335.6	1230.3	1134.6	1065.1	1006.2	952.5	909.3
27.5°	1630.3	1499.8	1450.3	1404.0	1299.8	1193.5	1114.6	1035.6	968.3	920.9	876.7
30°	1626.1	1470.3	1410.3	1356.6	1260.9	1165.1	1070.4	1002.0	937.8	877.8	833.6
32.5°	1598.7	1430.3	1369.3	1312.4	1209.3	1113.5	1038.8	966.2	896.7	840.9	800.9
35°	1590.3	1393.5	1313.5	1252.4	1151.4	1066.2	987.2	927.2	862.0	806.2	758.8
37.5°	1566.1	1355.6	1269.3	1191.4	1086.2	1005.1	947.2	887.2	824.1	764.1	726.2
40°	1524.0	1311.4	1213.5	1133.5	1025.1	943.0	889.3	845.1	783.0	729.4	683.1
42.5°	1461.9	1266.1	1160.9	1076.7	956.7	879.9	835.7	793.6	740.9	685.2	647.3
45°	1390.3	1206.1	1108.3	1014.6	892.5	817.8	771.5	746.2	697.8	650.4	606.2
47.5°	1292.4	1144.0	1047.2	950.4	826.2	753.6	716.7	691.5	657.8	606.2	570.4
50°	1169.3	1064.1	972.5	886.2	760.9	691.5	654.6	635.7	607.3	570.4	535.7
52.5°	1032.5	971.4	895.7	815.7	694.6	629.4	595.7	581.0	559.9	525.2	495.7
55°	894.6	868.3	816.7	737.8	625.2	571.5	542.0	523.1	507.3	482.0	456.8
57.5°	771.5	758.8	723.0	662.0	567.3	511.5	486.2	473.6	461.0	442.0	416.8
60°	644.1	657.8	621.0	590.4	504.1	455.7	433.6	419.9	413.6	396.8	381.0
62.5°	533.6	546.2	525.2	502.0	441.0	397.8	384.2	371.5	367.3	352.6	336.8
65°	433.6	449.4	433.6	421.0	384.2	348.4	331.5	325.2	321.0	311.5	298.9
67.5°	345.2	361.0	353.6	337.8	326.3	296.8	287.3	281.0	278.9	271.5	261.0
70°	260.0	282.1	284.2	274.7	264.2	250.5	244.2	242.1	236.8	230.5	224.2
72.5°	187.3	212.6	213.7	213.7	207.3	207.3	201.0	197.9	197.9	191.6	184.2
75°	137.9	154.7	156.8	158.9	162.1	165.2	161.0	161.0	160.0	153.7	150.5
77.5°	91.6	106.3	111.6	118.9	123.1	123.1	125.2	127.3	125.2	122.1	120.0
80°	58.9	69.5	75.8	80.0	86.3	89.5	92.6	93.7	91.6	90.5	87.4
82.5°	38.9	42.1	45.3	50.5	57.9	63.1	63.1	62.1	64.2	63.1	62.1
85°	22.1	24.2	25.3	26.3	30.5	35.8	36.8	37.9	40.0	37.9	35.8
87.5°	8.4	9.5	9.5	9.5	11.6	12.6	15.8	20.0	18.9	16.8	16.8
90°	15.6	12.7	11.2	10.1	7.8	5.5	3.3	1.0	3.3	5.5	7.8
92.5°	20.4	18.3	17.3	18.0	19.3	20.7	22.0	23.4	22.0	20.7	19.3
95°	24.1	21.6	20.4	25.0	34.3	43.6	52.8	62.1	52.8	43.6	34.3
97.5°	67.3	78.8	84.6	87.8	94.1	100.4	106.8	113.1	106.8	100.4	94.1
100°	139.5	174.8	192.5	190.2	185.7	181.2	176.7	172.2	176.7	181.2	185.7
102.5°	193.5	232.9	252.6	251.1	248.2	245.3	242.3	239.4	242.3	245.3	248.2
105°	284.2	304.6	314.8	313.6	311.1	308.6	306.1	303.6	306.1	308.6	311.1
107.5°	386.1	382.7	381.0	380.0	377.9	375.9	373.8	371.8	373.8	375.9	377.9
110°	451.9	449.4	448.2	447.3	445.5	443.7	441.9	440.1	441.9	443.7	445.5

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	516.1	513.6	512.4	511.6	510.0	508.5	506.9	505.3	506.9	508.5	510.0
115°	578.7	576.6	575.6	574.9	573.6	572.2	570.9	569.5	570.9	572.2	573.6
117.5°	641.5	640.4	639.8	639.0	637.4	635.8	634.2	632.6	634.2	635.8	637.4
120°	700.9	700.2	699.9	698.9	696.8	694.8	692.7	690.7	692.7	694.8	696.8
122.5°	758.3	757.4	756.9	756.1	754.5	753.0	751.4	749.8	751.4	753.0	754.5
125°	812.3	811.4	810.9	810.0	808.2	806.4	804.6	802.8	804.6	806.4	808.2
127.5°	865.6	864.5	863.9	863.0	861.2	859.3	857.5	855.7	857.5	859.3	861.2
130°	914.2	913.3	912.8	911.9	910.1	908.2	906.4	904.6	906.4	908.2	910.1
132.5°	960.6	959.9	959.6	958.7	956.9	955.1	953.3	951.5	953.3	955.1	956.9
135°	1006.9	1006.0	1005.5	1004.8	1003.5	1002.1	1000.8	999.4	1000.8	1002.1	1003.5
137.5°	1049.0	1048.5	1048.3	1047.4	1045.6	1043.7	1041.9	1040.1	1041.9	1043.7	1045.6
140°	1088.0	1087.3	1087.0	1086.3	1085.0	1083.6	1082.3	1080.9	1082.3	1083.6	1085.0
142.5°	1125.7	1125.0	1124.7	1124.0	1122.7	1121.3	1120.0	1118.6	1120.0	1121.3	1122.7
145°	1161.0	1160.5	1160.3	1159.5	1157.9	1156.4	1154.8	1153.2	1154.8	1156.4	1157.9
147.5°	1192.6	1192.1	1191.9	1191.3	1190.2	1189.1	1187.9	1186.8	1187.9	1189.1	1190.2
150°	1221.1	1220.6	1220.4	1220.1	1219.4	1218.7	1218.1	1217.4	1218.1	1218.7	1219.4
152.5°	1246.2	1246.0	1245.9	1245.8	1245.6	1245.3	1245.1	1244.9	1245.1	1245.3	1245.6
155°	1268.6	1268.4	1268.3	1268.5	1269.0	1269.5	1269.9	1270.4	1269.9	1269.5	1269.0
157.5°	1290.4	1290.6	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7
160°	1307.7	1308.0	1308.1	1308.2	1308.4	1308.7	1308.9	1309.1	1308.9	1308.7	1308.4
162.5°	1323.0	1323.2	1323.3	1323.6	1324.3	1325.0	1325.7	1326.4	1325.7	1325.0	1324.3
165°	1336.3	1336.5	1336.6	1336.9	1337.6	1338.3	1338.9	1339.6	1338.9	1338.3	1337.6
167.5°	1346.8	1346.8	1346.8	1347.2	1348.1	1349.0	1349.9	1350.8	1349.9	1349.0	1348.1
170°	1355.9	1355.9	1355.9	1356.4	1357.3	1358.2	1359.1	1360.0	1359.1	1358.2	1357.3
172.5°	1361.3	1361.1	1361.0	1361.6	1362.7	1363.8	1365.0	1366.1	1365.0	1363.8	1362.7
175°	1366.4	1366.2	1366.1	1366.7	1367.8	1368.9	1370.1	1371.2	1370.1	1368.9	1367.8
177.5°	1368.5	1368.3	1368.2	1368.8	1369.9	1371.0	1372.2	1373.3	1372.2	1371.0	1369.9
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1213.5	1208.2	1206.1	1200.9	1188.2	1179.8	1170.4	1164.0	1165.1	1159.8	1163.0
5°	1175.6	1174.6	1167.2	1156.7	1138.8	1129.3	1112.5	1104.0	1099.8	1100.9	1094.6
7.5°	1144.0	1134.6	1129.3	1112.5	1095.6	1075.6	1061.9	1054.6	1048.3	1041.9	1037.7
10°	1108.3	1099.8	1091.4	1073.5	1050.4	1031.4	1012.5	1005.1	995.6	991.4	988.3
12.5°	1070.4	1065.1	1054.6	1033.5	1007.2	989.3	967.2	963.0	950.4	942.0	939.9
15°	1035.6	1032.5	1013.5	989.3	963.0	945.1	926.2	913.5	892.5	896.7	889.3
17.5°	998.8	985.1	973.5	940.9	928.3	900.9	878.8	872.5	857.8	848.3	838.8
20°	957.8	949.3	934.6	913.5	883.0	851.5	834.6	824.1	815.7	800.9	796.7
22.5°	918.8	908.3	895.7	868.3	842.0	815.7	792.5	783.0	772.5	762.0	755.7
25°	888.3	872.5	858.8	825.1	798.8	776.7	762.0	746.2	731.5	725.2	723.0
27.5°	840.9	831.5	817.8	786.2	762.0	737.8	724.1	713.6	697.8	690.4	684.1
30°	810.4	791.5	775.7	750.4	726.2	699.9	687.3	674.6	665.2	655.7	648.3
32.5°	769.4	754.6	742.0	716.7	692.5	668.3	654.6	635.7	630.4	623.1	614.6
35°	729.4	719.9	706.2	678.8	652.5	635.7	621.0	603.1	596.8	591.5	584.1
37.5°	691.5	677.8	668.3	642.0	618.9	598.9	587.3	572.5	568.3	562.0	556.8
40°	658.8	645.2	635.7	609.4	585.2	564.1	556.8	542.0	535.7	528.3	525.2
42.5°	622.0	610.4	597.8	578.9	553.6	532.6	517.8	509.4	501.0	497.8	491.5
45°	583.1	572.5	563.1	542.0	515.7	501.0	488.3	476.8	470.5	465.2	461.0
47.5°	549.4	539.9	527.3	504.1	483.1	469.4	456.8	445.2	438.9	432.6	427.3
50°	510.5	505.2	491.5	469.4	449.4	433.6	422.0	411.5	407.3	399.9	391.5
52.5°	475.7	466.2	454.7	436.8	418.9	399.9	384.2	377.8	370.5	366.3	358.9
55°	434.7	428.4	415.7	399.9	381.0	365.2	353.6	345.2	335.7	331.5	322.1
57.5°	399.9	388.4	382.0	362.1	344.2	328.4	320.0	311.5	301.0	294.7	290.5
60°	362.1	351.5	342.1	325.2	312.6	295.7	283.1	275.7	268.4	260.0	255.8
62.5°	325.2	316.8	305.2	291.5	275.7	262.1	252.6	242.1	237.9	229.4	226.3
65°	285.2	278.9	269.4	253.6	241.0	229.4	220.0	211.5	207.3	204.2	202.1
67.5°	249.4	241.0	234.7	221.0	207.3	197.9	192.6	187.3	182.1	178.9	175.8
70°	212.6	206.3	200.0	187.3	177.9	169.4	165.2	161.0	157.9	154.7	151.6
72.5°	174.7	171.6	165.2	156.8	149.5	143.1	140.0	134.7	131.6	126.3	124.2
75°	144.2	138.9	135.8	128.4	122.1	116.8	112.6	106.3	102.1	100.0	98.9
77.5°	113.7	111.6	107.4	101.0	97.9	92.6	86.3	84.2	82.1	82.1	81.0
80°	85.3	82.1	78.9	73.7	70.5	66.3	66.3	66.3	65.3	66.3	65.3
82.5°	57.9	55.8	53.7	50.5	49.5	49.5	50.5	50.5	50.5	50.5	50.5
85°	33.7	33.7	33.7	34.7	33.7	33.7	34.7	35.8	34.7	34.7	33.7
87.5°	15.8	15.8	16.8	16.8	17.9	17.9	17.9	17.9	17.9	17.9	18.9
90°	10.1	11.2	12.7	15.6	18.5	21.5	24.4	25.3	26.2	27.1	28.0
92.5°	18.0	17.3	18.3	20.4	22.4	24.5	26.5	28.1	29.7	31.2	32.8
95°	25.0	20.4	21.6	24.1	26.6	29.1	31.6	33.2	34.8	36.3	37.9
97.5°	87.8	84.6	78.8	67.3	55.7	44.2	32.6	34.4	36.2	38.0	39.8
100°	190.2	192.5	174.8	139.5	104.2	68.9	33.6	35.4	37.2	39.1	40.9
102.5°	251.1	252.6	232.9	193.5	154.2	114.8	75.4	67.9	60.5	53.0	45.5
105°	313.6	314.8	304.6	284.2	263.9	243.5	223.1	183.0	143.0	102.9	62.8
107.5°	380.0	381.0	382.7	386.1	389.5	392.9	396.3	361.4	326.6	291.7	256.8
110°	447.3	448.2	449.4	451.9	454.4	456.9	459.4	451.9	444.5	437.0	429.5

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	511.6	512.4	513.6	516.1	518.6	521.1	523.6	525.6	527.7	529.7	531.8
115°	574.9	575.6	576.6	578.7	580.7	582.8	584.8	587.0	589.3	591.5	593.8
117.5°	639.0	639.8	640.4	641.5	642.6	643.8	644.9	646.7	648.5	650.3	652.1
120°	698.9	699.9	700.2	700.9	701.6	702.2	702.9	704.7	706.5	708.4	710.2
122.5°	756.1	756.9	757.4	758.3	759.2	760.1	761.0	762.1	763.3	764.4	765.5
125°	810.0	810.9	811.4	812.3	813.2	814.1	815.0	815.4	815.9	816.3	816.8
127.5°	863.0	863.9	864.5	865.6	866.7	867.9	869.0	869.7	870.3	871.0	871.7
130°	911.9	912.8	913.3	914.2	915.1	916.0	916.9	917.8	918.7	919.6	920.5
132.5°	958.7	959.6	959.9	960.6	961.3	962.0	962.7	963.6	964.5	965.4	966.3
135°	1004.8	1005.5	1006.0	1006.9	1007.8	1008.7	1009.6	1010.3	1010.9	1011.6	1012.3
137.5°	1047.4	1048.3	1048.5	1049.0	1049.4	1049.9	1050.3	1051.4	1052.6	1053.7	1054.8
140°	1086.3	1087.0	1087.3	1088.0	1088.7	1089.3	1090.0	1090.9	1091.8	1092.7	1093.6
142.5°	1124.0	1124.7	1125.0	1125.7	1126.4	1127.0	1127.7	1128.4	1129.1	1129.8	1130.5
145°	1159.5	1160.3	1160.5	1161.0	1161.5	1161.9	1162.4	1162.8	1163.3	1163.7	1164.2
147.5°	1191.3	1191.9	1192.1	1192.6	1193.1	1193.5	1194.0	1194.4	1194.9	1195.3	1195.8
150°	1220.1	1220.4	1220.6	1221.1	1221.6	1222.0	1222.5	1222.9	1223.4	1223.8	1224.3
152.5°	1245.8	1245.9	1246.0	1246.2	1246.5	1246.7	1246.9	1247.8	1248.7	1249.6	1250.5
155°	1268.5	1268.3	1268.4	1268.6	1268.9	1269.1	1269.3	1270.4	1271.6	1272.7	1273.8
157.5°	1290.7	1290.7	1290.6	1290.4	1290.1	1289.9	1289.7	1291.1	1292.4	1293.8	1295.1
160°	1308.2	1308.1	1308.0	1307.7	1307.5	1307.2	1307.0	1308.4	1309.7	1311.1	1312.4
162.5°	1323.6	1323.3	1323.2	1323.0	1322.7	1322.5	1322.3	1323.9	1325.5	1327.0	1328.6
165°	1336.9	1336.6	1336.5	1336.3	1336.0	1335.8	1335.6	1337.4	1339.2	1341.0	1342.8
167.5°	1347.2	1346.8	1346.8	1346.8	1346.8	1346.8	1346.8	1348.6	1350.4	1352.2	1354.0
170°	1356.4	1355.9	1355.9	1355.9	1355.9	1355.9	1355.9	1357.7	1359.5	1361.4	1363.2
172.5°	1361.6	1361.0	1361.1	1361.3	1361.6	1361.8	1362.0	1363.8	1365.6	1367.5	1369.3
175°	1366.7	1366.1	1366.2	1366.4	1366.7	1366.9	1367.1	1368.7	1370.3	1371.9	1373.5
177.5°	1368.8	1368.2	1368.3	1368.5	1368.8	1369.0	1369.2	1371.0	1372.8	1374.6	1376.4
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1161.9	1163.0	1159.8	1153.5	1152.5	1154.6	1160.9	1158.8	1153.5	1163.0	1154.6
5°	1097.7	1092.5	1090.4	1092.5	1086.2	1083.0	1089.3	1086.2	1089.3	1090.4	1093.5
7.5°	1035.6	1036.7	1030.4	1031.4	1023.0	1025.1	1025.1	1025.1	1028.3	1030.4	1034.6
10°	982.0	984.1	976.7	977.7	971.4	967.2	970.4	976.7	976.7	976.7	978.8
12.5°	938.8	929.3	924.1	923.0	915.7	913.5	919.9	922.0	927.2	927.2	930.4
15°	885.1	883.0	878.8	878.8	860.9	865.1	867.2	874.6	885.1	876.7	878.8
17.5°	836.7	831.5	826.2	824.1	822.0	815.7	824.1	823.0	829.3	830.4	833.6
20°	793.6	789.4	778.8	779.9	782.0	772.5	777.8	777.8	784.1	790.4	797.8
22.5°	751.5	747.3	742.0	744.1	737.8	735.7	735.7	740.9	748.3	753.6	752.5
25°	718.8	711.5	708.3	705.2	702.0	704.1	700.9	706.2	711.5	714.6	711.5
27.5°	682.0	678.8	672.5	669.4	664.1	666.2	668.3	672.5	675.7	675.7	678.8
30°	646.2	642.0	639.9	636.7	636.7	632.5	633.6	637.8	641.0	644.1	648.3
32.5°	611.5	608.3	605.2	605.2	603.1	602.0	601.0	607.3	607.3	613.6	613.6
35°	583.1	577.8	577.8	572.5	574.7	573.6	571.5	575.7	576.8	581.0	579.9
37.5°	551.5	551.5	549.4	544.1	539.9	541.0	546.2	546.2	549.4	548.3	551.5
40°	519.9	517.8	517.8	514.7	513.6	512.6	513.6	514.7	519.9	518.9	519.9
42.5°	488.3	489.4	484.1	484.1	484.1	481.0	482.0	483.1	485.2	487.3	490.5
45°	457.8	455.7	454.7	452.6	450.5	451.5	450.5	454.7	453.6	455.7	458.9
47.5°	425.2	422.0	421.0	416.8	416.8	418.9	417.8	421.0	422.0	425.2	423.1
50°	393.6	389.4	386.3	387.3	381.0	383.1	383.1	386.3	389.4	390.5	392.6
52.5°	356.8	355.7	354.7	349.4	348.4	347.3	348.4	349.4	353.6	356.8	357.8
55°	321.0	320.0	313.6	311.5	308.4	308.4	310.5	311.5	318.9	320.0	324.2
57.5°	288.4	285.2	277.9	276.8	276.8	276.8	273.6	277.9	280.0	285.2	285.2
60°	252.6	252.6	246.3	246.3	247.3	246.3	246.3	247.3	247.3	251.5	253.6
62.5°	224.2	223.1	223.1	221.0	220.0	221.0	220.0	220.0	221.0	224.2	227.3
65°	198.9	197.9	196.8	195.8	193.7	193.7	194.7	196.8	196.8	198.9	200.0
67.5°	174.7	174.7	172.6	172.6	171.6	170.5	171.6	170.5	174.7	174.7	175.8
70°	150.5	149.5	146.3	145.2	142.1	143.1	143.1	146.3	147.3	149.5	151.6
72.5°	121.0	121.0	118.9	116.8	117.9	115.8	115.8	116.8	116.8	120.0	121.0
75°	100.0	97.9	96.8	97.9	96.8	98.9	96.8	96.8	98.9	98.9	98.9
77.5°	82.1	82.1	81.0	81.0	82.1	81.0	82.1	82.1	82.1	81.0	82.1
80°	67.4	66.3	66.3	66.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
82.5°	50.5	50.5	49.5	50.5	50.5	49.5	50.5	49.5	49.5	50.5	50.5
85°	33.7	35.8	33.7	33.7	34.7	34.7	35.8	34.7	35.8	33.7	34.7
87.5°	17.9	18.9	18.9	17.9	17.9	18.9	18.9	18.9	20.0	17.9	18.9
90°	28.5	28.7	29.2	29.7	30.1	30.6	30.1	29.7	29.2	28.7	28.5
92.5°	33.6	33.7	33.9	34.2	34.4	34.6	34.4	34.2	33.9	33.7	33.6
95°	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7
97.5°	40.7	40.8	41.1	41.3	41.6	41.8	41.6	41.3	41.1	40.8	40.7
100°	41.8	41.9	42.1	42.4	42.6	42.8	42.6	42.4	42.1	41.9	41.8
102.5°	41.8	42.0	42.5	42.9	43.4	43.8	43.4	42.9	42.5	42.0	41.8
105°	42.8	43.0	43.5	43.9	44.4	44.8	44.4	43.9	43.5	43.0	42.8
107.5°	239.4	224.6	194.9	165.2	135.6	105.9	135.6	165.2	194.9	224.6	239.4
110°	425.8	409.6	377.3	344.9	312.6	280.2	312.6	344.9	377.3	409.6	425.8

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	532.8	532.6	532.1	531.7	531.2	530.8	531.2	531.7	532.1	532.6	532.8
115°	594.9	595.4	596.3	597.2	598.1	599.0	598.1	597.2	596.3	595.4	594.9
117.5°	653.0	653.1	653.3	653.6	653.8	654.0	653.8	653.6	653.3	653.1	653.0
120°	711.1	711.1	711.1	711.1	711.1	711.1	711.1	711.1	711.1	711.1	711.1
122.5°	766.1	766.2	766.4	766.7	766.9	767.1	766.9	766.7	766.4	766.2	766.1
125°	817.0	817.2	817.7	818.2	818.6	819.1	818.6	818.2	817.7	817.2	817.0
127.5°	872.0	871.8	871.3	870.9	870.4	870.0	870.4	870.9	871.3	871.8	872.0
130°	920.9	920.7	920.2	919.8	919.3	918.9	919.3	919.8	920.2	920.7	920.9
132.5°	966.8	966.5	965.8	965.1	964.4	963.7	964.4	965.1	965.8	966.5	966.8
135°	1012.6	1012.3	1011.6	1010.9	1010.3	1009.6	1010.3	1010.9	1011.6	1012.3	1012.6
137.5°	1055.4	1055.2	1054.7	1054.3	1053.8	1053.4	1053.8	1054.3	1054.7	1055.2	1055.4
140°	1094.1	1093.9	1093.4	1093.0	1092.5	1092.1	1092.5	1093.0	1093.4	1093.9	1094.1
142.5°	1130.8	1130.5	1129.8	1129.1	1128.4	1127.7	1128.4	1129.1	1129.8	1130.5	1130.8
145°	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4
147.5°	1196.0	1195.4	1194.3	1193.2	1192.0	1190.9	1192.0	1193.2	1194.3	1195.4	1196.0
150°	1224.5	1224.2	1223.5	1222.8	1222.2	1221.5	1222.2	1222.8	1223.5	1224.2	1224.5
152.5°	1251.0	1250.4	1249.3	1248.2	1247.0	1245.9	1247.0	1248.2	1249.3	1250.4	1251.0
155°	1274.4	1273.7	1272.4	1271.0	1269.7	1268.3	1269.7	1271.0	1272.4	1273.7	1274.4
157.5°	1295.8	1294.9	1293.1	1291.3	1289.5	1287.7	1289.5	1291.3	1293.1	1294.9	1295.8
160°	1313.1	1312.3	1310.7	1309.2	1307.6	1306.0	1307.6	1309.2	1310.7	1312.3	1313.1
162.5°	1329.4	1328.7	1327.4	1326.0	1324.7	1323.3	1324.7	1326.0	1327.4	1328.7	1329.4
165°	1343.7	1342.9	1341.3	1339.8	1338.2	1336.6	1338.2	1339.8	1341.3	1342.9	1343.7
167.5°	1354.9	1354.0	1352.2	1350.4	1348.6	1346.8	1348.6	1350.4	1352.2	1354.0	1354.9
170°	1364.1	1363.2	1361.4	1359.5	1357.7	1355.9	1357.7	1359.5	1361.4	1363.2	1364.1
172.5°	1370.2	1369.2	1367.1	1365.1	1363.0	1361.0	1363.0	1365.1	1367.1	1369.2	1370.2
175°	1374.3	1373.4	1371.6	1369.7	1367.9	1366.1	1367.9	1369.7	1371.6	1373.4	1374.3
177.5°	1377.3	1376.2	1373.9	1371.6	1369.4	1367.1	1369.4	1371.6	1373.9	1376.2	1377.3
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1163.0	1167.2	1163.0	1154.6	1163.0	1168.2	1173.5	1181.9	1186.1	1186.1	1192.5
5°	1096.7	1105.1	1101.9	1099.8	1108.3	1113.5	1121.9	1132.5	1144.0	1151.4	1159.8
7.5°	1037.7	1043.0	1048.3	1048.3	1056.7	1068.3	1080.9	1093.5	1108.3	1118.8	1125.1
10°	986.2	990.4	993.5	997.7	1010.4	1023.0	1039.8	1055.6	1068.3	1079.8	1090.4
12.5°	936.7	943.0	950.4	953.5	963.0	978.8	994.6	1013.5	1033.5	1045.1	1055.6
15°	889.3	892.5	900.9	910.4	918.8	935.6	955.6	975.6	992.5	1010.4	1019.8
17.5°	840.9	842.0	864.1	858.8	886.2	902.0	912.5	931.4	958.8	973.5	988.3
20°	793.6	804.1	813.6	818.8	833.6	851.5	882.0	896.7	918.8	932.5	945.1
22.5°	756.7	772.5	772.5	785.1	792.5	809.4	831.5	859.9	884.1	893.6	911.4
25°	724.1	731.5	744.1	748.3	762.0	776.7	791.5	822.0	848.3	860.9	873.6
27.5°	682.0	691.5	708.3	708.3	726.2	742.0	759.9	779.9	806.2	824.1	837.8
30°	649.4	658.8	666.2	677.8	685.2	699.9	731.5	746.2	769.4	785.1	802.0
32.5°	618.9	626.2	632.5	645.2	653.6	670.4	687.3	713.6	733.6	748.3	766.2
35°	585.2	592.5	601.0	610.4	623.1	638.9	654.6	676.7	696.7	710.4	725.2
37.5°	553.6	558.9	571.5	577.8	588.3	603.1	623.1	646.2	664.1	674.6	689.4
40°	523.1	527.3	536.8	548.3	555.7	567.3	588.3	608.3	630.4	643.1	654.6
42.5°	490.5	495.7	504.1	515.7	527.3	539.9	551.5	574.7	594.6	605.2	617.8
45°	462.0	465.2	471.5	483.1	494.7	504.1	522.0	543.1	562.0	570.4	584.1
47.5°	428.4	431.5	441.0	446.2	458.9	471.5	489.4	510.5	527.3	535.7	548.3
50°	393.6	396.8	403.1	414.7	423.1	436.8	452.6	470.5	491.5	503.1	510.5
52.5°	359.9	366.3	371.5	381.0	391.5	405.2	419.9	436.8	454.7	466.2	474.7
55°	326.3	331.5	337.8	343.1	355.7	368.4	385.2	401.0	416.8	427.3	436.8
57.5°	288.4	295.7	302.1	312.6	322.1	332.6	351.5	364.2	383.1	390.5	398.9
60°	255.8	263.1	268.4	276.8	285.2	298.9	311.5	327.3	343.1	352.6	363.1
62.5°	228.4	231.5	234.7	243.1	251.5	264.2	276.8	292.6	309.4	314.7	323.1
65°	201.0	204.2	209.4	216.8	223.1	230.5	244.2	256.8	272.6	281.0	284.2
67.5°	177.9	181.0	182.1	187.3	192.6	201.0	208.4	221.0	235.8	241.0	247.3
70°	151.6	156.8	157.9	162.1	164.2	169.4	177.9	187.3	198.9	208.4	213.7
72.5°	121.0	128.4	130.5	136.8	140.0	145.2	151.6	158.9	166.3	170.5	174.7
75°	98.9	101.0	102.1	107.4	112.6	120.0	123.1	127.3	133.7	138.9	143.1
77.5°	82.1	83.1	84.2	84.2	85.3	89.5	95.8	101.0	105.2	107.4	110.5
80°	66.3	65.3	65.3	66.3	66.3	66.3	68.4	75.8	77.9	83.1	82.1
82.5°	51.6	49.5	50.5	49.5	49.5	49.5	49.5	50.5	50.5	53.7	55.8
85°	33.7	34.7	33.7	33.7	32.6	33.7	32.6	32.6	31.6	31.6	30.5
87.5°	17.9	18.9	17.9	17.9	16.8	17.9	16.8	16.8	15.8	15.8	13.7
90°	28.0	27.1	26.2	25.3	24.4	21.5	18.5	15.6	12.7	11.2	10.1
92.5°	32.8	31.2	29.7	28.1	26.5	24.5	22.4	20.4	18.3	17.3	18.0
95°	37.9	36.3	34.8	33.2	31.6	29.1	26.6	24.1	21.6	20.4	25.0
97.5°	39.8	38.0	36.2	34.4	32.6	44.2	55.7	67.3	78.8	84.6	87.8
100°	40.9	39.1	37.2	35.4	33.6	68.9	104.2	139.5	174.8	192.5	190.2
102.5°	45.5	53.0	60.5	67.9	75.4	114.8	154.2	193.5	232.9	252.6	251.1
105°	62.8	102.9	143.0	183.0	223.1	243.5	263.9	284.2	304.6	314.8	313.6
107.5°	256.8	291.7	326.6	361.4	396.3	392.9	389.5	386.1	382.7	381.0	380.0
110°	429.5	437.0	444.5	451.9	459.4	456.9	454.4	451.9	449.4	448.2	447.3

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	531.8	529.7	527.7	525.6	523.6	521.1	518.6	516.1	513.6	512.4	511.6
115°	593.8	591.5	589.3	587.0	584.8	582.8	580.7	578.7	576.6	575.6	574.9
117.5°	652.1	650.3	648.5	646.7	644.9	643.8	642.6	641.5	640.4	639.8	639.0
120°	710.2	708.4	706.5	704.7	702.9	702.2	701.6	700.9	700.2	699.9	698.9
122.5°	765.5	764.4	763.3	762.1	761.0	760.1	759.2	758.3	757.4	756.9	756.1
125°	816.8	816.3	815.9	815.4	815.0	814.1	813.2	812.3	811.4	810.9	810.0
127.5°	871.7	871.0	870.3	869.7	869.0	867.9	866.7	865.6	864.5	863.9	863.0
130°	920.5	919.6	918.7	917.8	916.9	916.0	915.1	914.2	913.3	912.8	911.9
132.5°	966.3	965.4	964.5	963.6	962.7	962.0	961.3	960.6	959.9	959.6	958.7
135°	1012.3	1011.6	1010.9	1010.3	1009.6	1008.7	1007.8	1006.9	1006.0	1005.5	1004.8
137.5°	1054.8	1053.7	1052.6	1051.4	1050.3	1049.9	1049.4	1049.0	1048.5	1048.3	1047.4
140°	1093.6	1092.7	1091.8	1090.9	1090.0	1089.3	1088.7	1088.0	1087.3	1087.0	1086.3
142.5°	1130.5	1129.8	1129.1	1128.4	1127.7	1127.0	1126.4	1125.7	1125.0	1124.7	1124.0
145°	1164.2	1163.7	1163.3	1162.8	1162.4	1161.9	1161.5	1161.0	1160.5	1160.3	1159.5
147.5°	1195.8	1195.3	1194.9	1194.4	1194.0	1193.5	1193.1	1192.6	1192.1	1191.9	1191.3
150°	1224.3	1223.8	1223.4	1222.9	1222.5	1222.0	1221.6	1221.1	1220.6	1220.4	1220.1
152.5°	1250.5	1249.6	1248.7	1247.8	1246.9	1246.7	1246.5	1246.2	1246.0	1245.9	1245.8
155°	1273.8	1272.7	1271.6	1270.4	1269.3	1269.1	1268.9	1268.6	1268.4	1268.3	1268.5
157.5°	1295.1	1293.8	1292.4	1291.1	1289.7	1289.9	1290.1	1290.4	1290.6	1290.7	1290.7
160°	1312.4	1311.1	1309.7	1308.4	1307.0	1307.2	1307.5	1307.7	1308.0	1308.1	1308.2
162.5°	1328.6	1327.0	1325.5	1323.9	1322.3	1322.5	1322.7	1323.0	1323.2	1323.3	1323.6
165°	1342.8	1341.0	1339.2	1337.4	1335.6	1335.8	1336.0	1336.3	1336.5	1336.6	1336.9
167.5°	1354.0	1352.2	1350.4	1348.6	1346.8	1346.8	1346.8	1346.8	1346.8	1346.8	1347.2
170°	1363.2	1361.4	1359.5	1357.7	1355.9	1355.9	1355.9	1355.9	1355.9	1355.9	1356.4
172.5°	1369.3	1367.5	1365.6	1363.8	1362.0	1361.8	1361.6	1361.3	1361.1	1361.0	1361.6
175°	1373.5	1371.9	1370.3	1368.7	1367.1	1366.9	1366.7	1366.4	1366.2	1366.1	1366.7
177.5°	1376.4	1374.6	1372.8	1371.0	1369.2	1369.0	1368.8	1368.5	1368.3	1368.2	1368.8
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1229.3	1229.3	1229.3	1229.3
2.5°	1197.7	1205.1	1219.8	1232.4
5°	1172.5	1184.0	1206.1	1228.2
7.5°	1141.9	1159.8	1188.2	1218.8
10°	1112.5	1135.6	1170.4	1206.1
12.5°	1083.0	1107.2	1144.0	1190.3
15°	1048.3	1073.5	1117.7	1173.5
17.5°	1017.7	1051.4	1091.4	1147.2
20°	985.1	1010.4	1061.9	1120.9
22.5°	944.1	986.2	1034.6	1096.7
25°	911.4	948.3	996.7	1067.2
27.5°	871.4	914.6	973.5	1035.6
30°	838.8	874.6	929.3	1004.1
32.5°	800.9	843.0	899.9	973.5
35°	767.3	803.0	856.7	931.4
37.5°	727.3	766.2	826.2	892.5
40°	692.5	730.4	787.3	849.3
42.5°	650.4	690.4	747.3	799.9
45°	616.7	653.6	698.8	747.3
47.5°	575.7	614.6	658.8	692.5
50°	538.9	574.7	609.4	637.8
52.5°	498.9	531.5	563.1	584.1
55°	462.0	487.3	512.6	527.3
57.5°	418.9	443.1	464.1	472.6
60°	381.0	401.0	414.7	424.1
62.5°	341.0	355.7	366.3	371.5
65°	302.1	312.6	317.8	323.1
67.5°	262.1	271.5	274.7	281.0
70°	220.0	230.5	232.6	235.8
72.5°	188.4	188.4	192.6	196.8
75°	150.5	152.6	154.7	154.7
77.5°	117.9	117.9	120.0	121.0
80°	86.3	87.4	87.4	86.3
82.5°	58.9	61.0	58.9	57.9
85°	32.6	36.8	34.7	34.7
87.5°	13.7	13.7	15.8	13.7
90°	7.8	5.5	3.3	1.0
92.5°	19.3	20.7	22.0	23.4
95°	34.3	43.6	52.8	62.1
97.5°	94.1	100.4	106.8	113.1
100°	185.7	181.2	176.7	172.2
102.5°	248.2	245.3	242.3	239.4
105°	311.1	308.6	306.1	303.6
107.5°	377.9	375.9	373.8	371.8
110°	445.5	443.7	441.9	440.1

TEST NUMBER: P1032372

CATALOG NUMBER: S123RDIW-B775D1030UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	510.0	508.5	506.9	505.3
115°	573.6	572.2	570.9	569.5
117.5°	637.4	635.8	634.2	632.6
120°	696.8	694.8	692.7	690.7
122.5°	754.5	753.0	751.4	749.8
125°	808.2	806.4	804.6	802.8
127.5°	861.2	859.3	857.5	855.7
130°	910.1	908.2	906.4	904.6
132.5°	956.9	955.1	953.3	951.5
135°	1003.5	1002.1	1000.8	999.4
137.5°	1045.6	1043.7	1041.9	1040.1
140°	1085.0	1083.6	1082.3	1080.9
142.5°	1122.7	1121.3	1120.0	1118.6
145°	1157.9	1156.4	1154.8	1153.2
147.5°	1190.2	1189.1	1187.9	1186.8
150°	1219.4	1218.7	1218.1	1217.4
152.5°	1245.6	1245.3	1245.1	1244.9
155°	1269.0	1269.5	1269.9	1270.4
157.5°	1290.7	1290.7	1290.7	1290.7
160°	1308.4	1308.7	1308.9	1309.1
162.5°	1324.3	1325.0	1325.7	1326.4
165°	1337.6	1338.3	1338.9	1339.6
167.5°	1348.1	1349.0	1349.9	1350.8
170°	1357.3	1358.2	1359.1	1360.0
172.5°	1362.7	1363.8	1365.0	1366.1
175°	1367.8	1368.9	1370.1	1371.2
177.5°	1369.9	1371.0	1372.2	1373.3
180°	1371.2	1371.2	1371.2	1371.2

(END OF REPORT)