

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032631

Luminaire Tested: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032631
REPORT IS A COMBINATION OF REPORTS P997357 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6907.0 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	88	84	81	81	78	75	72	59	57	56	43	41	40	27	27	26			19
2	83	76	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22			16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	21	20	19			14
4	70	59	52	46	61	53	47	42	41	37	33	30	27	25	19	18	16			12
5	64	53	45	39	56	47	41	36	36	32	28	27	24	21	17	16	14			10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	16	14	12			9
7	54	42	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11			8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10			7
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9			7
10	43	32	25	20	38	29	23	19	22	18	15	17	14	12	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4536	4536	4536	4536
5°	4525	5204	4551	3911
10°	4491	6071	4525	3430
15°	4437	6999	4468	3069
20°	4380	7590	4412	2752
25°	4296	7503	4337	2518
30°	4214	6201	4265	2397
35°	4098	4621	4143	2324
40°	3964	3481	4003	2288
45°	3759	2794	3806	2239
50°	3515	2354	3565	2216
55°	3226	2049	3277	2191
60°	2947	1804	3033	2154
65°	2685	1552	2709	2064
70°	2376	1278	2427	1901
75°	2072	982	2058	1615
80°	1629	644	1612	1226
85°	1070	289	1004	715

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5865 cd/sqm

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	0.8
10°-20°	167.1	2.4
20°-30°	265.5	3.8
30°-40°	295.0	4.3
40°-50°	268.3	3.9
50°-60°	219.2	3.2
60°-70°	156.5	2.3
70°-80°	86.1	1.2
80°-90°	26.8	0.4
90°-100°	57.6	0.8
100°-110°	379.3	5.5
110°-120°	724.2	10.5
120°-130°	919.4	13.3
130°-140°	983.6	14.2
140°-150°	919.7	13.3
150°-160°	741.6	10.7
160°-170°	478.3	6.9
170°-180°	164.8	2.4
0°-30°	486.7	7.0
0°-40°	781.7	11.3
0°-60°	1269.2	18.4
0°-90°	1538.6	22.3
90°-120°	1161.0	16.8
90°-150°	3983.6	57.7
90°-180°	5368.0	77.7
0°-180°	6907.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	556	556	556	556	556	
5°	554	653	557	490	554	53
15°	529	896	533	393	529	149
25°	483	952	488	319	483	223
35°	419	563	424	283	419	262
45°	334	316	338	253	334	258
55°	235	206	239	221	235	211
65°	147	133	148	176	147	145
75°	72	66	71	109	72	76
85°	15	14	14	34	15	17
90°	4	39	4	39	4	5
95°	71	38	71	38	71	88
105°	391	370	391	370	391	409
115°	729	734	729	734	729	718
125°	1025	1033	1025	1033	1025	915
135°	1272	1281	1272	1281	1272	980
145°	1466	1474	1466	1474	1466	916
155°	1608	1606	1608	1606	1608	741
165°	1696	1688	1696	1688	1696	479
175°	1735	1724	1735	1724	1735	165
180°	1735	1735	1735	1735	1735	

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	556.3	561.8	564.1	566.0	571.9	573.8	574.2	577.0	579.3	579.8	579.8
5°	554.0	562.7	569.6	576.1	585.8	589.9	595.0	600.5	607.9	612.5	614.8
7.5°	550.3	563.2	573.8	584.8	598.2	606.5	611.1	625.9	636.0	644.3	654.4
10°	544.8	561.3	576.6	592.7	611.6	621.7	631.9	649.8	664.1	680.2	693.2
12.5°	536.5	558.1	576.6	599.1	622.6	634.6	646.6	677.9	694.5	708.8	731.9
15°	529.1	550.7	577.0	600.1	629.1	647.1	664.6	684.9	711.1	742.0	764.1
17.5°	520.8	548.0	572.4	604.7	636.9	654.0	668.3	699.6	736.5	766.9	787.2
20°	509.3	536.9	569.2	603.3	641.5	654.9	673.8	715.7	748.9	778.9	812.1
22.5°	495.9	528.2	562.3	595.0	634.6	662.7	683.5	720.3	760.4	795.0	832.3
25°	483.0	518.0	548.0	592.7	634.6	653.5	677.0	720.8	764.6	806.5	844.8
27.5°	469.2	501.9	542.4	577.9	625.4	646.1	671.5	719.4	766.0	807.9	848.9
30°	454.0	489.0	522.6	564.6	610.7	637.4	660.9	713.0	760.4	804.2	842.5
32.5°	436.9	470.1	506.0	545.7	594.1	621.3	650.8	704.2	754.9	792.7	822.2
35°	418.9	452.6	483.9	524.5	574.2	601.4	630.0	689.0	739.2	770.1	787.2
37.5°	399.1	430.9	461.8	501.9	551.7	580.7	609.7	666.9	714.4	740.2	735.6
40°	380.2	408.8	437.4	475.2	527.2	558.1	583.5	641.1	682.6	693.6	678.4
42.5°	358.6	383.0	410.6	449.4	500.0	529.1	560.9	613.4	644.3	639.7	613.9
45°	334.1	355.8	383.4	419.9	471.5	501.4	528.2	577.9	600.5	589.0	542.0
47.5°	310.6	331.8	354.4	390.8	441.1	466.4	493.6	538.3	551.2	526.8	479.8
50°	285.3	302.8	326.3	360.9	407.9	434.6	457.2	493.1	497.7	467.8	418.9
52.5°	260.9	275.6	298.2	332.3	376.1	397.3	419.4	451.2	447.5	416.6	369.6
55°	235.0	248.9	269.6	301.0	339.7	359.9	378.8	407.0	399.1	367.3	326.3
57.5°	213.4	223.1	243.3	272.4	304.2	326.3	342.4	364.6	352.6	320.8	282.5
60°	188.5	200.5	217.5	241.0	272.4	287.1	301.4	316.2	307.9	277.4	243.3
62.5°	165.9	175.1	189.9	212.5	236.9	250.3	265.5	274.7	266.4	238.3	209.7
65°	146.6	153.9	165.5	183.9	207.4	218.5	227.2	236.0	229.1	202.8	182.0
67.5°	125.4	131.8	141.5	156.2	176.1	183.9	192.2	198.2	190.3	172.8	152.5
70°	106.5	111.1	120.3	131.3	145.2	152.5	159.5	165.5	158.5	143.8	128.6
72.5°	87.1	90.8	99.1	106.9	119.4	124.4	129.5	134.1	131.8	118.0	105.5
75°	71.9	73.3	78.8	85.3	93.1	98.6	102.3	105.1	103.2	92.2	84.3
77.5°	54.4	56.2	60.4	65.4	72.4	75.6	77.9	80.7	78.3	69.6	64.1
80°	39.6	40.1	42.4	47.0	51.6	52.1	54.4	58.1	56.7	50.7	46.5
82.5°	25.3	26.7	27.7	30.4	33.6	34.6	35.9	36.9	36.4	32.7	31.3
85°	14.7	14.7	15.7	17.5	18.4	19.8	20.3	20.7	21.7	19.4	18.0
87.5°	6.5	6.9	6.9	7.4	8.3	8.3	8.8	9.2	9.7	9.2	7.8
90°	3.9	7.1	10.3	13.4	16.6	18.2	19.3	21.6	23.9	26.2	28.5
92.5°	19.5	18.9	18.3	17.8	17.2	16.9	18.0	20.3	22.6	24.9	27.2
95°	71.4	61.6	51.8	41.9	32.1	27.2	27.3	27.6	27.9	28.2	28.5
97.5°	136.2	142.6	148.9	155.3	161.6	164.8	149.7	119.4	89.1	58.8	28.5
100°	212.8	218.0	223.2	228.4	233.6	236.2	216.3	176.5	136.7	96.9	57.1
102.5°	298.5	301.9	305.4	308.8	312.3	314.0	315.7	319.2	322.7	326.1	329.6
105°	390.6	392.3	394.1	395.8	397.5	398.4	399.1	400.6	402.0	403.5	404.9
107.5°	474.9	475.8	476.6	477.5	478.4	478.8	479.8	481.8	483.9	485.9	487.9
110°	560.6	561.5	562.3	563.2	564.1	564.5	565.4	567.1	568.8	570.5	572.2

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	643.6	645.3	647.1	648.8	650.5	651.4	651.7	652.3	652.8	653.4	654.0
115°	729.3	730.2	731.0	731.9	732.8	733.2	733.1	732.8	732.5	732.2	731.9
117.5°	805.8	807.0	808.1	809.3	810.4	811.0	811.4	812.3	813.2	814.0	814.9
120°	883.7	884.9	886.0	887.2	888.3	888.9	888.8	888.5	888.2	887.9	887.6
122.5°	956.3	956.9	957.5	958.0	958.6	958.9	959.2	959.8	960.3	960.9	961.5
125°	1025.1	1026.3	1027.4	1028.6	1029.7	1030.3	1030.0	1029.4	1028.9	1028.3	1027.7
127.5°	1091.3	1091.6	1091.9	1092.2	1092.5	1092.6	1093.3	1094.8	1096.2	1097.7	1099.1
130°	1154.9	1155.2	1155.5	1155.8	1156.1	1156.2	1156.6	1157.5	1158.4	1159.2	1160.1
132.5°	1213.3	1213.9	1214.5	1215.0	1215.6	1215.9	1216.5	1217.6	1218.8	1219.9	1221.1
135°	1271.7	1271.4	1271.1	1270.8	1270.5	1270.4	1271.0	1272.1	1273.3	1274.4	1275.6
137.5°	1323.6	1323.6	1323.6	1323.6	1323.6	1323.6	1324.3	1325.8	1327.2	1328.7	1330.1
140°	1374.2	1374.8	1375.4	1375.9	1376.5	1376.8	1377.1	1377.7	1378.2	1378.8	1379.4
142.5°	1419.6	1420.8	1421.9	1423.1	1424.2	1424.8	1424.9	1425.2	1425.5	1425.8	1426.1
145°	1466.3	1467.2	1468.0	1468.9	1469.8	1470.2	1470.2	1470.2	1470.2	1470.2	1470.2
147.5°	1502.6	1504.3	1506.1	1507.8	1509.5	1510.4	1510.3	1510.0	1509.7	1509.4	1509.1
150°	1542.9	1544.1	1545.2	1546.4	1547.5	1548.1	1548.0	1547.7	1547.4	1547.1	1546.8
152.5°	1576.6	1577.5	1578.3	1579.2	1580.1	1580.5	1580.2	1579.6	1579.1	1578.5	1577.9
155°	1607.7	1608.0	1608.3	1608.6	1608.9	1609.0	1608.6	1607.7	1606.8	1606.0	1605.1
157.5°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1634.4	1633.3	1632.1	1631.0	1629.8
160°	1658.3	1657.5	1656.6	1655.8	1654.9	1654.5	1654.4	1654.1	1653.8	1653.5	1653.2
162.5°	1679.1	1677.9	1676.8	1675.6	1674.5	1673.9	1673.8	1673.5	1673.2	1672.9	1672.6
165°	1696.0	1694.6	1693.1	1691.7	1690.2	1689.5	1689.5	1689.5	1689.5	1689.5	1689.5
167.5°	1710.3	1708.9	1707.4	1706.0	1704.5	1703.8	1703.7	1703.4	1703.1	1702.8	1702.5
170°	1721.9	1720.2	1718.4	1716.7	1715.0	1714.1	1714.2	1714.5	1714.8	1715.1	1715.4
172.5°	1729.7	1728.0	1726.2	1724.5	1722.8	1721.9	1722.0	1722.3	1722.6	1722.9	1723.2
175°	1734.9	1733.2	1731.4	1729.7	1728.0	1727.1	1727.2	1727.5	1727.8	1728.1	1728.4
177.5°	1738.8	1736.8	1734.8	1732.7	1730.7	1729.7	1730.0	1730.6	1731.1	1731.7	1732.3
180°	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	581.2	589.5	593.1	594.1	599.1	595.9	597.3	596.8	600.5	601.0	601.0
5°	623.6	633.2	636.5	641.1	648.0	649.8	648.4	651.2	656.3	652.6	658.1
7.5°	668.3	678.9	686.2	696.4	698.7	704.7	708.4	711.6	712.5	713.0	713.9
10°	709.7	723.1	733.3	750.3	754.0	757.2	773.3	766.9	775.2	772.4	773.3
12.5°	743.4	769.7	778.0	806.5	809.3	820.4	819.4	829.6	831.4	835.1	831.4
15°	787.6	818.1	831.4	847.5	856.8	869.7	872.0	885.8	891.3	896.4	891.3
17.5°	828.2	844.3	878.4	891.3	897.3	904.2	921.7	926.8	935.1	931.9	941.1
20°	848.5	871.5	907.5	929.6	938.8	945.3	960.0	967.8	971.1	971.1	972.0
22.5°	866.4	899.6	926.4	951.7	960.0	964.6	973.4	979.4	980.7	981.7	982.6
25°	882.6	912.5	934.2	948.5	951.7	951.7	956.8	953.1	947.1	951.7	954.5
27.5°	882.6	903.8	913.5	918.5	918.5	906.1	898.7	883.5	870.6	866.9	875.2
30°	867.8	877.5	864.1	851.7	842.0	833.7	804.7	781.6	777.0	773.8	786.3
32.5°	833.7	821.3	795.0	759.1	744.8	725.9	703.3	685.8	675.2	671.5	668.7
35°	773.3	741.1	707.0	658.6	648.4	624.5	593.6	580.7	563.2	562.7	568.7
37.5°	707.4	657.7	620.8	574.7	560.4	535.1	506.0	492.7	480.7	471.5	482.5
40°	630.5	587.2	530.9	493.1	472.9	459.5	435.1	420.3	414.8	410.2	417.1
42.5°	558.6	511.1	467.3	428.6	412.0	396.8	380.7	366.4	362.2	361.8	366.9
45°	487.1	440.6	400.0	366.9	356.3	347.0	331.4	327.2	320.3	315.7	318.0
47.5°	430.0	382.1	348.4	323.1	313.9	306.0	295.9	289.0	283.0	281.1	283.9
50°	373.8	341.5	306.9	285.7	278.8	271.5	263.6	257.2	254.4	252.6	254.4
52.5°	328.6	294.0	270.5	253.5	246.6	241.0	235.5	232.7	229.1	230.0	231.8
55°	288.0	257.6	237.8	225.4	221.2	218.9	212.0	208.8	207.4	206.5	207.4
57.5°	249.8	227.7	212.9	202.3	196.8	195.4	189.9	189.9	188.5	187.1	187.6
60°	219.4	200.5	186.2	177.9	177.0	174.7	171.0	170.5	167.3	168.7	169.1
62.5°	188.5	173.3	163.6	158.5	155.3	154.4	152.1	151.6	150.2	150.7	149.8
65°	164.1	151.6	141.9	137.8	136.4	136.0	134.1	132.7	131.8	132.7	131.8
67.5°	139.6	131.3	124.0	119.8	118.0	117.5	116.1	115.2	115.7	114.3	115.2
70°	116.6	108.3	103.7	101.4	100.5	99.1	99.1	99.1	99.1	98.2	97.7
72.5°	98.2	89.9	86.6	85.3	84.3	83.9	82.5	83.0	82.5	82.0	83.9
75°	77.9	72.8	69.6	68.2	69.1	67.7	66.4	67.3	65.9	66.4	68.2
77.5°	59.0	56.7	54.8	53.9	53.0	52.1	52.1	51.2	51.2	51.2	51.2
80°	42.9	42.4	39.2	38.7	38.7	37.8	37.8	37.8	37.8	37.3	37.8
82.5°	28.6	28.1	27.2	26.7	25.8	26.3	26.3	25.3	25.3	24.9	25.3
85°	16.6	16.6	15.7	15.2	14.7	15.2	14.3	13.8	14.3	13.8	14.3
87.5°	7.8	6.9	7.4	6.9	6.0	6.5	5.5	6.0	5.5	5.1	6.0
90°	30.2	32.0	33.7	35.4	36.3	36.6	37.2	37.7	38.3	38.9	38.3
92.5°	28.9	30.7	32.4	34.1	35.0	35.0	35.0	35.0	35.0	35.0	35.0
95°	30.2	32.0	33.7	35.4	36.3	36.4	36.7	37.0	37.3	37.6	37.3
97.5°	29.9	31.4	32.8	34.3	35.0	35.1	35.4	35.7	36.0	36.3	36.0
100°	52.2	47.3	42.4	37.5	35.0	35.1	35.4	35.7	36.0	36.3	36.0
102.5°	264.7	199.8	134.9	70.0	37.6	37.6	37.6	37.6	37.6	37.6	37.6
105°	407.5	410.1	412.6	415.2	416.5	411.3	400.9	390.6	380.2	369.8	380.2
107.5°	489.3	490.8	492.2	493.7	494.4	495.0	496.1	497.3	498.4	499.6	498.4
110°	572.8	573.4	573.9	574.5	574.8	575.2	576.1	577.0	577.8	578.7	577.8

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	653.7	653.4	653.1	652.8	652.7	653.3	654.4	655.6	656.7	657.9	656.7
115°	732.5	733.0	733.6	734.1	734.4	734.4	734.4	734.4	734.4	734.4	734.4
117.5°	814.6	814.3	814.0	813.7	813.6	813.6	813.6	813.6	813.6	813.6	813.6
120°	888.2	888.8	889.3	889.9	890.2	889.9	889.3	888.8	888.2	887.6	888.2
122.5°	961.8	962.1	962.4	962.7	962.8	962.5	961.9	961.4	960.8	960.2	960.8
125°	1028.6	1029.4	1030.3	1031.2	1031.6	1031.7	1032.0	1032.3	1032.6	1032.9	1032.6
127.5°	1098.8	1098.5	1098.2	1097.9	1097.8	1097.7	1097.4	1097.1	1096.8	1096.5	1096.8
130°	1160.4	1160.7	1161.0	1161.3	1161.4	1161.4	1161.4	1161.4	1161.4	1161.4	1161.4
132.5°	1221.4	1221.7	1222.0	1222.3	1222.4	1222.3	1222.0	1221.7	1221.4	1221.1	1221.4
135°	1276.2	1276.7	1277.3	1277.8	1278.1	1278.4	1279.0	1279.5	1280.1	1280.7	1280.1
137.5°	1330.7	1331.2	1331.8	1332.3	1332.6	1332.5	1332.2	1331.9	1331.7	1331.4	1331.7
140°	1380.3	1381.1	1382.0	1382.9	1383.3	1383.4	1383.7	1384.0	1384.3	1384.6	1384.3
142.5°	1426.7	1427.3	1427.8	1428.4	1428.7	1428.7	1428.7	1428.7	1428.7	1428.7	1428.7
145°	1470.5	1470.8	1471.1	1471.4	1471.5	1471.8	1472.4	1472.9	1473.5	1474.1	1473.5
147.5°	1509.4	1509.7	1510.0	1510.3	1510.4	1510.5	1510.8	1511.1	1511.4	1511.7	1511.4
150°	1546.8	1546.8	1546.8	1546.8	1546.8	1546.9	1547.2	1547.5	1547.8	1548.1	1547.8
152.5°	1578.5	1579.1	1579.6	1580.2	1580.5	1580.4	1580.1	1579.8	1579.5	1579.2	1579.5
155°	1606.3	1607.4	1608.6	1609.7	1610.3	1609.9	1609.0	1608.1	1607.3	1606.4	1607.3
157.5°	1631.2	1632.7	1634.1	1635.6	1636.3	1635.6	1634.1	1632.7	1631.2	1629.8	1631.2
160°	1654.9	1656.6	1658.3	1660.0	1660.9	1660.0	1658.3	1656.6	1654.9	1653.2	1654.9
162.5°	1674.3	1676.1	1677.8	1679.5	1680.4	1679.4	1677.4	1675.3	1673.3	1671.3	1673.3
165°	1691.8	1694.1	1696.4	1698.7	1699.9	1698.6	1696.0	1693.4	1690.8	1688.2	1690.8
167.5°	1705.1	1707.7	1710.2	1712.8	1714.1	1712.7	1709.8	1706.9	1704.1	1701.2	1704.1
170°	1717.7	1720.0	1722.3	1724.6	1725.8	1724.4	1721.5	1718.6	1715.7	1712.8	1715.7
172.5°	1725.5	1727.8	1730.1	1732.4	1733.6	1732.0	1728.8	1725.7	1722.5	1719.3	1722.5
175°	1731.0	1733.6	1736.2	1738.8	1740.1	1738.4	1734.9	1731.4	1728.0	1724.5	1728.0
177.5°	1734.6	1736.9	1739.2	1741.5	1742.7	1741.0	1737.5	1734.0	1730.6	1727.1	1730.6
180°	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	600.1	598.7	596.8	596.8	594.5	594.5	590.8	584.4	578.9	577.0	577.9
5°	651.2	651.7	648.9	646.6	642.5	639.2	633.2	621.7	618.0	610.7	605.6
7.5°	709.7	707.9	702.8	699.1	698.2	690.8	677.9	664.1	653.1	645.7	635.1
10°	775.7	768.3	760.9	758.6	753.1	740.6	725.9	710.7	695.5	679.3	661.4
12.5°	831.0	816.7	816.2	810.7	800.1	793.2	775.7	754.0	727.7	709.7	689.5
15°	890.4	877.0	866.0	855.8	850.8	830.5	815.7	788.6	757.2	737.9	724.0
17.5°	932.8	926.8	907.9	903.3	896.4	872.9	849.4	822.7	795.5	768.3	730.9
20°	966.9	963.2	950.8	944.3	933.3	914.8	886.3	855.4	824.0	785.3	750.3
22.5°	981.7	977.1	966.9	961.4	954.5	938.8	914.4	879.3	838.3	803.8	766.4
25°	952.6	960.9	958.2	955.9	953.1	943.9	925.4	894.6	854.5	815.3	768.7
27.5°	887.2	901.5	915.3	917.1	921.7	925.4	918.1	895.9	862.3	820.8	769.7
30°	799.2	805.6	833.7	842.0	848.5	872.0	885.8	880.3	854.5	817.1	770.1
32.5°	686.2	703.3	731.9	751.7	769.2	795.5	831.4	845.7	836.5	806.1	759.5
35°	579.3	599.6	632.8	658.1	675.6	713.0	755.4	786.3	797.8	782.6	741.1
37.5°	491.8	516.2	545.7	555.4	575.6	621.7	680.2	723.1	751.2	752.6	720.3
40°	425.8	438.3	461.8	476.5	496.4	535.1	592.2	648.9	691.3	705.6	688.5
42.5°	370.1	379.8	397.3	415.2	433.2	462.7	515.3	568.3	625.4	654.0	653.5
45°	325.8	336.0	348.0	362.7	375.2	407.0	448.4	502.8	552.1	596.4	607.4
47.5°	287.1	295.9	310.6	317.1	325.4	355.3	391.3	442.0	493.1	543.8	556.7
50°	258.6	265.9	276.1	280.2	289.4	311.6	341.0	382.1	438.8	485.3	509.3
52.5°	232.7	238.3	246.1	249.3	255.8	272.4	299.1	331.4	378.4	426.3	460.0
55°	210.6	214.3	219.8	223.5	228.1	242.9	262.7	291.7	332.3	373.8	406.5
57.5°	189.9	192.6	198.2	200.0	203.7	215.2	229.1	253.5	290.8	327.7	359.5
60°	170.5	172.4	175.6	179.7	182.5	190.3	203.2	223.5	253.5	287.1	312.9
62.5°	152.1	154.9	155.8	157.6	159.9	167.3	177.4	192.2	218.5	246.1	273.3
65°	133.2	135.5	137.3	137.8	140.1	145.6	154.9	167.8	184.8	208.8	234.1
67.5°	115.7	117.1	118.0	119.8	122.1	124.9	132.3	141.9	157.6	177.0	197.3
70°	99.5	99.5	100.9	101.4	104.2	107.4	110.6	119.8	133.7	149.3	163.1
72.5°	82.0	84.3	83.9	86.2	85.7	88.0	92.2	98.2	108.3	120.7	134.1
75°	66.8	68.2	68.2	68.2	69.1	71.0	73.3	78.8	86.6	96.8	104.6
77.5°	52.1	53.0	53.0	53.0	53.5	55.3	57.6	61.3	66.8	72.8	77.4
80°	37.3	38.3	38.3	39.2	39.2	39.6	41.9	43.8	46.5	51.2	55.8
82.5°	25.3	25.8	26.7	26.7	26.3	27.2	27.7	29.5	32.3	33.2	36.4
85°	13.8	14.3	14.7	14.7	15.2	16.1	15.7	17.5	17.5	19.4	20.3
87.5°	5.5	6.5	6.5	6.0	6.5	6.5	6.5	7.4	7.8	8.3	7.8
90°	37.7	37.2	36.6	36.3	35.4	33.7	32.0	30.2	28.5	26.2	23.9
92.5°	35.0	35.0	35.0	35.0	34.1	32.4	30.7	28.9	27.2	24.9	22.6
95°	37.0	36.7	36.4	36.3	35.4	33.7	32.0	30.2	28.5	28.2	27.9
97.5°	35.7	35.4	35.1	35.0	34.3	32.8	31.4	29.9	28.5	58.8	89.1
100°	35.7	35.4	35.1	35.0	37.5	42.4	47.3	52.2	57.1	96.9	136.7
102.5°	37.6	37.6	37.6	37.6	70.0	134.9	199.8	264.7	329.6	326.1	322.7
105°	390.6	400.9	411.3	416.5	415.2	412.6	410.1	407.5	404.9	403.5	402.0
107.5°	497.3	496.1	495.0	494.4	493.7	492.2	490.8	489.3	487.9	485.9	483.9
110°	577.0	576.1	575.2	574.8	574.5	573.9	573.4	572.8	572.2	570.5	568.8

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	655.6	654.4	653.3	652.7	652.8	653.1	653.4	653.7	654.0	653.4	652.8
115°	734.4	734.4	734.4	734.4	734.1	733.6	733.0	732.5	731.9	732.2	732.5
117.5°	813.6	813.6	813.6	813.6	813.7	814.0	814.3	814.6	814.9	814.0	813.2
120°	888.8	889.3	889.9	890.2	889.9	889.3	888.8	888.2	887.6	887.9	888.2
122.5°	961.4	961.9	962.5	962.8	962.7	962.4	962.1	961.8	961.5	960.9	960.3
125°	1032.3	1032.0	1031.7	1031.6	1031.2	1030.3	1029.4	1028.6	1027.7	1028.3	1028.9
127.5°	1097.1	1097.4	1097.7	1097.8	1097.9	1098.2	1098.5	1098.8	1099.1	1097.7	1096.2
130°	1161.4	1161.4	1161.4	1161.4	1161.3	1161.0	1160.7	1160.4	1160.1	1159.2	1158.4
132.5°	1221.7	1222.0	1222.3	1222.4	1222.3	1222.0	1221.7	1221.4	1221.1	1219.9	1218.8
135°	1279.5	1279.0	1278.4	1278.1	1277.8	1277.3	1276.7	1276.2	1275.6	1274.4	1273.3
137.5°	1331.9	1332.2	1332.5	1332.6	1332.3	1331.8	1331.2	1330.7	1330.1	1328.7	1327.2
140°	1384.0	1383.7	1383.4	1383.3	1382.9	1382.0	1381.1	1380.3	1379.4	1378.8	1378.2
142.5°	1428.7	1428.7	1428.7	1428.7	1428.4	1427.8	1427.3	1426.7	1426.1	1425.8	1425.5
145°	1472.9	1472.4	1471.8	1471.5	1471.4	1471.1	1470.8	1470.5	1470.2	1470.2	1470.2
147.5°	1511.1	1510.8	1510.5	1510.4	1510.3	1510.0	1509.7	1509.4	1509.1	1509.4	1509.7
150°	1547.5	1547.2	1546.9	1546.8	1546.8	1546.8	1546.8	1546.8	1546.8	1547.1	1547.4
152.5°	1579.8	1580.1	1580.4	1580.5	1580.2	1579.6	1579.1	1578.5	1577.9	1578.5	1579.1
155°	1608.1	1609.0	1609.9	1610.3	1609.7	1608.6	1607.4	1606.3	1605.1	1606.0	1606.8
157.5°	1632.7	1634.1	1635.6	1636.3	1635.6	1634.1	1632.7	1631.2	1629.8	1631.0	1632.1
160°	1656.6	1658.3	1660.0	1660.9	1660.0	1658.3	1656.6	1654.9	1653.2	1653.5	1653.8
162.5°	1675.3	1677.4	1679.4	1680.4	1679.5	1677.8	1676.1	1674.3	1672.6	1672.9	1673.2
165°	1693.4	1696.0	1698.6	1699.9	1698.7	1696.4	1694.1	1691.8	1689.5	1689.5	1689.5
167.5°	1706.9	1709.8	1712.7	1714.1	1712.8	1710.2	1707.7	1705.1	1702.5	1702.8	1703.1
170°	1718.6	1721.5	1724.4	1725.8	1724.6	1722.3	1720.0	1717.7	1715.4	1715.1	1714.8
172.5°	1725.7	1728.8	1732.0	1733.6	1732.4	1730.1	1727.8	1725.5	1723.2	1722.9	1722.6
175°	1731.4	1734.9	1738.4	1740.1	1738.8	1736.2	1733.6	1731.0	1728.4	1728.1	1727.8
177.5°	1734.0	1737.5	1741.0	1742.7	1741.5	1739.2	1736.9	1734.6	1732.3	1731.7	1731.1
180°	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	573.8	571.9	570.6	570.6	566.4	562.3	560.0	559.0	558.1	554.4	549.4
5°	597.3	591.3	587.2	583.0	576.1	568.7	561.3	557.2	551.2	542.9	536.9
7.5°	623.6	609.3	604.7	599.6	585.8	573.3	563.2	554.4	544.8	534.2	523.6
10°	645.7	630.5	620.3	611.6	593.6	577.0	561.8	548.9	536.5	522.6	509.7
12.5°	666.9	645.2	634.6	621.7	602.8	578.9	559.0	542.9	524.5	510.2	494.5
15°	696.4	660.0	642.5	634.2	608.8	580.7	556.7	532.8	517.6	495.9	482.1
17.5°	701.0	671.5	660.0	638.8	608.4	576.6	548.9	524.9	501.9	482.5	464.6
20°	717.1	678.4	660.0	646.6	606.5	574.2	543.8	513.0	490.8	470.1	449.8
22.5°	727.3	683.5	664.1	642.9	604.7	566.0	530.0	503.3	476.1	454.9	438.8
25°	724.5	680.7	659.0	639.2	592.7	554.0	521.7	487.6	462.3	439.2	418.0
27.5°	723.1	673.8	650.8	628.6	584.8	544.3	503.7	476.1	448.0	421.2	405.6
30°	719.4	665.0	638.3	614.3	568.7	526.3	491.8	459.5	431.4	407.0	386.2
32.5°	707.0	650.3	624.5	598.7	551.2	508.8	473.8	443.8	415.7	390.4	370.5
35°	690.4	632.8	604.7	577.5	530.0	487.1	454.9	423.5	397.3	372.8	354.0
37.5°	673.8	612.5	586.2	554.9	511.1	466.4	433.2	405.1	380.7	355.3	334.6
40°	649.8	588.5	559.5	532.8	481.6	439.7	409.3	383.9	359.9	336.0	318.5
42.5°	617.1	562.3	532.3	502.8	454.9	413.4	383.9	361.3	338.7	318.9	299.6
45°	583.9	530.5	503.7	477.5	425.4	386.2	359.0	338.3	319.4	297.7	282.1
47.5°	543.8	498.7	471.9	446.1	396.8	357.6	332.8	313.4	295.9	277.9	263.2
50°	502.8	463.6	439.2	412.5	365.5	330.0	305.6	289.4	275.1	258.1	246.1
52.5°	458.6	424.5	403.7	377.9	336.4	303.7	278.8	262.7	250.7	238.3	227.7
55°	411.6	386.7	364.6	343.8	304.6	275.1	253.0	238.7	230.4	218.9	209.7
57.5°	369.2	345.2	331.8	308.3	274.2	245.2	227.7	215.7	206.0	199.1	191.7
60°	324.9	305.6	290.8	273.8	243.8	219.4	200.9	194.0	183.9	178.8	175.6
62.5°	282.5	268.7	254.9	242.0	215.2	192.2	178.4	169.6	163.6	158.5	155.8
65°	242.4	229.5	219.8	208.3	186.2	167.8	154.9	147.9	141.9	140.6	137.3
67.5°	203.2	197.7	187.1	177.9	159.0	144.7	135.0	126.3	123.1	121.7	118.9
70°	170.1	163.6	155.3	147.5	133.2	120.7	112.0	108.8	104.2	103.7	100.5
72.5°	140.1	132.3	126.3	120.3	109.7	98.6	94.0	89.4	87.1	85.3	83.9
75°	111.1	105.5	101.4	96.3	87.1	79.7	73.3	71.4	70.1	69.6	68.7
77.5°	83.0	79.3	77.4	72.4	65.9	59.5	56.7	53.9	53.9	53.0	53.5
80°	59.0	56.7	54.4	51.6	46.1	43.3	41.0	39.2	38.3	37.8	38.3
82.5°	37.3	35.9	35.5	33.6	30.0	28.6	26.7	25.3	25.3	25.3	25.3
85°	20.7	20.7	20.7	18.0	16.6	15.2	14.3	13.8	13.8	13.8	14.3
87.5°	8.8	8.8	7.4	7.4	6.9	6.0	5.5	5.5	6.0	6.0	6.5
90°	21.6	19.3	18.2	16.6	13.4	10.3	7.1	3.9	7.1	10.3	13.4
92.5°	20.3	18.0	16.9	17.2	17.8	18.3	18.9	19.5	18.9	18.3	17.8
95°	27.6	27.3	27.2	32.1	41.9	51.8	61.6	71.4	61.6	51.8	41.9
97.5°	119.4	149.7	164.8	161.6	155.3	148.9	142.6	136.2	142.6	148.9	155.3
100°	176.5	216.3	236.2	233.6	228.4	223.2	218.0	212.8	218.0	223.2	228.4
102.5°	319.2	315.7	314.0	312.3	308.8	305.4	301.9	298.5	301.9	305.4	308.8
105°	400.6	399.1	398.4	397.5	395.8	394.1	392.3	390.6	392.3	394.1	395.8
107.5°	481.8	479.8	478.8	478.4	477.5	476.6	475.8	474.9	475.8	476.6	477.5
110°	567.1	565.4	564.5	564.1	563.2	562.3	561.5	560.6	561.5	562.3	563.2

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	652.3	651.7	651.4	650.5	648.8	647.1	645.3	643.6	645.3	647.1	648.8
115°	732.8	733.1	733.2	732.8	731.9	731.0	730.2	729.3	730.2	731.0	731.9
117.5°	812.3	811.4	811.0	810.4	809.3	808.1	807.0	805.8	807.0	808.1	809.3
120°	888.5	888.8	888.9	888.3	887.2	886.0	884.9	883.7	884.9	886.0	887.2
122.5°	959.8	959.2	958.9	958.6	958.0	957.5	956.9	956.3	956.9	957.5	958.0
125°	1029.4	1030.0	1030.3	1029.7	1028.6	1027.4	1026.3	1025.1	1026.3	1027.4	1028.6
127.5°	1094.8	1093.3	1092.6	1092.5	1092.2	1091.9	1091.6	1091.3	1091.6	1091.9	1092.2
130°	1157.5	1156.6	1156.2	1156.1	1155.8	1155.5	1155.2	1154.9	1155.2	1155.5	1155.8
132.5°	1217.6	1216.5	1215.9	1215.6	1215.0	1214.5	1213.9	1213.3	1213.9	1214.5	1215.0
135°	1272.1	1271.0	1270.4	1270.5	1270.8	1271.1	1271.4	1271.7	1271.4	1271.1	1270.8
137.5°	1325.8	1324.3	1323.6	1323.6	1323.6	1323.6	1323.6	1323.6	1323.6	1323.6	1323.6
140°	1377.7	1377.1	1376.8	1376.5	1375.9	1375.4	1374.8	1374.2	1374.8	1375.4	1375.9
142.5°	1425.2	1424.9	1424.8	1424.2	1423.1	1421.9	1420.8	1419.6	1420.8	1421.9	1423.1
145°	1470.2	1470.2	1470.2	1469.8	1468.9	1468.0	1467.2	1466.3	1467.2	1468.0	1468.9
147.5°	1510.0	1510.3	1510.4	1509.5	1507.8	1506.1	1504.3	1502.6	1504.3	1506.1	1507.8
150°	1547.7	1548.0	1548.1	1547.5	1546.4	1545.2	1544.1	1542.9	1544.1	1545.2	1546.4
152.5°	1579.6	1580.2	1580.5	1580.1	1579.2	1578.3	1577.5	1576.6	1577.5	1578.3	1579.2
155°	1607.7	1608.6	1609.0	1608.9	1608.6	1608.3	1608.0	1607.7	1608.0	1608.3	1608.6
157.5°	1633.3	1634.4	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
160°	1654.1	1654.4	1654.5	1654.9	1655.8	1656.6	1657.5	1658.3	1657.5	1656.6	1655.8
162.5°	1673.5	1673.8	1673.9	1674.5	1675.6	1676.8	1677.9	1679.1	1677.9	1676.8	1675.6
165°	1689.5	1689.5	1689.5	1690.2	1691.7	1693.1	1694.6	1696.0	1694.6	1693.1	1691.7
167.5°	1703.4	1703.7	1703.8	1704.5	1706.0	1707.4	1708.9	1710.3	1708.9	1707.4	1706.0
170°	1714.5	1714.2	1714.1	1715.0	1716.7	1718.4	1720.2	1721.9	1720.2	1718.4	1716.7
172.5°	1722.3	1722.0	1721.9	1722.8	1724.5	1726.2	1728.0	1729.7	1728.0	1726.2	1724.5
175°	1727.5	1727.2	1727.1	1728.0	1729.7	1731.4	1733.2	1734.9	1733.2	1731.4	1729.7
177.5°	1730.6	1730.0	1729.7	1730.7	1732.7	1734.8	1736.8	1738.8	1736.8	1734.8	1732.7
180°	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	548.0	546.1	547.1	542.4	538.3	532.3	527.2	526.3	525.4	528.2	526.3
5°	532.3	530.0	527.7	522.2	513.9	508.8	501.4	501.0	498.2	494.1	495.0
7.5°	515.3	513.9	510.6	501.9	494.5	485.8	479.8	474.7	472.4	468.7	467.3
10°	501.4	496.4	493.6	483.9	475.2	465.9	458.1	454.4	450.3	447.0	444.7
12.5°	482.5	481.2	473.3	465.5	458.1	447.5	441.5	430.9	425.4	428.2	427.2
15°	470.1	463.6	461.8	450.7	438.3	431.4	420.3	413.4	411.1	407.0	401.9
17.5°	453.5	449.4	442.9	432.8	418.5	408.8	401.0	394.5	391.7	386.2	382.1
20°	437.8	430.9	425.8	416.6	402.8	390.4	380.7	376.5	369.6	365.0	362.7
22.5°	423.5	418.5	411.1	397.3	385.3	373.3	361.8	355.8	349.3	346.6	342.9
25°	406.0	397.7	392.7	377.5	364.6	354.9	344.3	336.4	332.8	328.1	327.2
27.5°	389.0	381.1	375.2	361.8	346.1	333.7	327.2	321.7	315.2	315.2	312.9
30°	371.9	366.4	357.2	344.3	329.5	317.5	310.2	305.1	302.8	301.0	300.5
32.5°	354.9	347.5	342.0	324.5	313.4	302.3	296.8	292.7	289.9	289.4	289.9
35°	337.4	329.1	323.5	307.9	296.8	286.7	284.4	280.7	279.3	278.8	281.1
37.5°	318.9	312.5	305.6	292.7	280.2	274.2	269.6	268.2	267.8	270.5	271.5
40°	301.9	296.3	289.9	276.1	266.8	260.4	258.1	256.7	258.6	261.3	262.7
42.5°	285.7	277.9	272.8	260.4	252.1	248.4	245.6	245.6	247.5	250.7	253.0
45°	268.7	262.7	257.6	246.6	239.2	235.0	234.6	235.0	237.4	239.7	242.4
47.5°	252.1	246.1	240.6	231.4	224.9	222.6	222.1	222.6	226.3	229.5	232.7
50°	236.9	230.4	225.4	216.6	211.5	208.8	209.2	211.5	214.3	218.9	223.1
52.5°	218.9	214.3	209.7	201.9	197.3	195.4	196.8	198.6	203.7	206.9	212.0
55°	201.4	197.3	193.6	187.6	183.9	182.5	183.4	186.2	190.3	195.9	201.9
57.5°	185.3	180.7	177.0	172.8	168.7	169.1	169.6	173.3	178.4	183.4	190.3
60°	167.3	164.5	161.3	156.2	154.4	154.4	155.8	159.9	164.5	172.8	178.8
62.5°	151.2	147.5	145.2	141.9	139.2	139.6	142.9	146.6	152.1	159.0	166.8
65°	134.6	130.4	128.6	125.8	124.9	125.4	127.7	133.2	139.2	145.2	152.5
67.5°	116.1	114.8	112.9	110.1	111.1	111.5	113.8	118.4	124.9	130.9	139.2
70°	100.5	97.7	97.2	94.9	94.9	96.3	100.9	104.2	110.1	116.6	125.4
72.5°	83.9	81.6	81.6	79.7	81.1	82.5	84.8	89.4	94.9	101.4	108.8
75°	66.8	65.9	66.8	65.9	65.9	68.2	71.0	74.7	80.7	87.6	93.6
77.5°	51.6	51.6	51.2	52.5	52.5	53.9	57.6	61.3	65.9	71.4	77.9
80°	37.8	37.8	37.8	39.2	40.6	40.6	42.9	47.5	51.6	55.3	61.3
82.5°	25.8	25.8	25.8	26.7	28.6	28.6	31.3	34.1	38.7	41.9	44.7
85°	15.7	15.7	15.2	16.1	16.6	18.0	20.3	22.1	24.4	27.2	30.0
87.5°	6.9	6.9	7.4	7.8	8.3	9.2	10.1	11.1	13.4	14.3	15.7
90°	16.6	18.2	19.3	21.6	23.9	26.2	28.5	30.2	32.0	33.7	35.4
92.5°	17.2	16.9	18.0	20.3	22.6	24.9	27.2	28.9	30.7	32.4	34.1
95°	32.1	27.2	27.3	27.6	27.9	28.2	28.5	30.2	32.0	33.7	35.4
97.5°	161.6	164.8	149.7	119.4	89.1	58.8	28.5	29.9	31.4	32.8	34.3
100°	233.6	236.2	216.3	176.5	136.7	96.9	57.1	52.2	47.3	42.4	37.5
102.5°	312.3	314.0	315.7	319.2	322.7	326.1	329.6	264.7	199.8	134.9	70.0
105°	397.5	398.4	399.1	400.6	402.0	403.5	404.9	407.5	410.1	412.6	415.2
107.5°	478.4	478.8	479.8	481.8	483.9	485.9	487.9	489.3	490.8	492.2	493.7
110°	564.1	564.5	565.4	567.1	568.8	570.5	572.2	572.8	573.4	573.9	574.5

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	650.5	651.4	651.7	652.3	652.8	653.4	654.0	653.7	653.4	653.1	652.8
115°	732.8	733.2	733.1	732.8	732.5	732.2	731.9	732.5	733.0	733.6	734.1
117.5°	810.4	811.0	811.4	812.3	813.2	814.0	814.9	814.6	814.3	814.0	813.7
120°	888.3	888.9	888.8	888.5	888.2	887.9	887.6	888.2	888.8	889.3	889.9
122.5°	958.6	958.9	959.2	959.8	960.3	960.9	961.5	961.8	962.1	962.4	962.7
125°	1029.7	1030.3	1030.0	1029.4	1028.9	1028.3	1027.7	1028.6	1029.4	1030.3	1031.2
127.5°	1092.5	1092.6	1093.3	1094.8	1096.2	1097.7	1099.1	1098.8	1098.5	1098.2	1097.9
130°	1156.1	1156.2	1156.6	1157.5	1158.4	1159.2	1160.1	1160.4	1160.7	1161.0	1161.3
132.5°	1215.6	1215.9	1216.5	1217.6	1218.8	1219.9	1221.1	1221.4	1221.7	1222.0	1222.3
135°	1270.5	1270.4	1271.0	1272.1	1273.3	1274.4	1275.6	1276.2	1276.7	1277.3	1277.8
137.5°	1323.6	1323.6	1324.3	1325.8	1327.2	1328.7	1330.1	1330.7	1331.2	1331.8	1332.3
140°	1376.5	1376.8	1377.1	1377.7	1378.2	1378.8	1379.4	1380.3	1381.1	1382.0	1382.9
142.5°	1424.2	1424.8	1424.9	1425.2	1425.5	1425.8	1426.1	1426.7	1427.3	1427.8	1428.4
145°	1469.8	1470.2	1470.2	1470.2	1470.2	1470.2	1470.2	1470.5	1470.8	1471.1	1471.4
147.5°	1509.5	1510.4	1510.3	1510.0	1509.7	1509.4	1509.1	1509.4	1509.7	1510.0	1510.3
150°	1547.5	1548.1	1548.0	1547.7	1547.4	1547.1	1546.8	1546.8	1546.8	1546.8	1546.8
152.5°	1580.1	1580.5	1580.2	1579.6	1579.1	1578.5	1577.9	1578.5	1579.1	1579.6	1580.2
155°	1608.9	1609.0	1608.6	1607.7	1606.8	1606.0	1605.1	1606.3	1607.4	1608.6	1609.7
157.5°	1635.0	1635.0	1634.4	1633.3	1632.1	1631.0	1629.8	1631.2	1632.7	1634.1	1635.6
160°	1654.9	1654.5	1654.4	1654.1	1653.8	1653.5	1653.2	1654.9	1656.6	1658.3	1660.0
162.5°	1674.5	1673.9	1673.8	1673.5	1673.2	1672.9	1672.6	1674.3	1676.1	1677.8	1679.5
165°	1690.2	1689.5	1689.5	1689.5	1689.5	1689.5	1689.5	1691.8	1694.1	1696.4	1698.7
167.5°	1704.5	1703.8	1703.7	1703.4	1703.1	1702.8	1702.5	1705.1	1707.7	1710.2	1712.8
170°	1715.0	1714.1	1714.2	1714.5	1714.8	1715.1	1715.4	1717.7	1720.0	1722.3	1724.6
172.5°	1722.8	1721.9	1722.0	1722.3	1722.6	1722.9	1723.2	1725.5	1727.8	1730.1	1732.4
175°	1728.0	1727.1	1727.2	1727.5	1727.8	1728.1	1728.4	1731.0	1733.6	1736.2	1738.8
177.5°	1730.7	1729.7	1730.0	1730.6	1731.1	1731.7	1732.3	1734.6	1736.9	1739.2	1741.5
180°	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	524.9	524.5	522.2	523.1	520.3	521.2	522.6	523.1	524.9	523.6	523.1
5°	492.7	491.8	490.4	489.0	488.5	490.4	487.1	488.1	489.0	490.4	492.2
7.5°	466.4	465.9	464.6	462.3	461.3	460.4	460.9	464.1	463.6	463.2	466.4
10°	442.4	442.9	440.1	439.7	436.9	436.4	436.9	437.8	439.2	441.1	441.5
12.5°	417.6	423.5	418.5	416.6	412.5	414.8	415.7	411.6	413.9	415.2	422.2
15°	401.9	399.1	395.9	395.9	394.0	393.1	390.8	394.0	395.9	398.7	397.7
17.5°	380.2	375.6	373.8	371.9	372.4	374.2	369.2	376.5	376.5	377.9	375.6
20°	361.3	357.6	355.3	354.4	353.0	352.1	351.6	353.5	356.3	357.2	359.5
22.5°	341.5	341.5	337.8	336.4	335.5	334.1	336.4	335.1	336.9	338.7	342.4
25°	324.9	324.9	323.5	321.7	320.3	319.4	320.8	320.3	321.7	324.0	324.9
27.5°	311.6	310.2	309.7	309.2	308.8	309.2	308.8	310.2	311.6	312.0	311.1
30°	300.0	298.6	299.1	299.1	299.6	299.1	298.6	300.0	300.5	299.6	300.0
32.5°	289.4	289.4	290.4	290.8	290.8	291.3	291.7	290.8	291.3	289.9	290.4
35°	280.7	281.6	282.5	283.0	283.4	283.0	283.9	283.4	282.5	281.6	281.1
37.5°	271.9	272.8	274.7	275.1	276.5	277.0	276.1	276.1	275.6	273.8	272.8
40°	262.7	263.6	265.9	267.3	268.2	269.6	268.7	268.7	266.8	265.0	263.6
42.5°	253.9	255.8	258.1	259.5	261.3	261.3	261.3	260.4	258.1	256.2	254.9
45°	245.2	245.6	248.9	251.2	253.0	253.0	253.0	251.6	250.3	246.6	244.7
47.5°	235.5	236.9	240.6	242.9	244.7	245.2	245.2	243.8	241.0	237.8	235.5
50°	224.9	227.2	231.4	234.6	236.9	237.8	236.4	235.5	232.3	228.6	225.8
52.5°	214.8	217.5	222.6	225.4	228.6	229.1	228.6	227.2	223.5	218.5	216.1
55°	204.6	206.9	212.5	217.1	219.8	220.8	219.8	217.5	212.9	207.9	205.5
57.5°	193.6	196.8	202.8	207.4	210.6	211.1	210.2	207.9	204.2	197.7	194.5
60°	182.0	186.2	192.2	196.8	200.9	201.4	200.5	197.3	192.6	186.2	183.4
62.5°	170.5	173.7	180.7	185.7	189.0	191.3	189.4	186.2	181.6	175.1	171.0
65°	157.2	161.8	167.8	172.4	176.1	176.5	175.6	172.8	167.8	160.8	157.6
67.5°	144.3	147.5	153.5	159.5	160.8	162.2	160.8	158.1	153.9	147.9	143.3
70°	128.6	131.3	138.7	142.9	144.7	146.1	145.2	142.4	138.7	133.2	129.5
72.5°	112.9	115.2	122.1	125.4	129.0	128.6	128.1	126.3	121.2	117.5	115.2
75°	96.3	99.1	103.7	107.8	109.2	109.2	109.2	107.8	104.6	98.6	96.3
77.5°	81.1	82.5	86.2	88.5	89.9	90.3	89.9	87.6	85.7	81.6	80.2
80°	62.2	65.9	68.7	69.1	71.0	71.0	71.0	70.1	68.2	64.1	63.6
82.5°	47.0	47.9	50.7	52.1	53.0	52.5	52.5	50.7	50.2	47.9	47.0
85°	31.8	33.2	32.7	34.6	35.0	34.1	34.1	35.0	32.7	33.2	31.8
87.5°	17.5	17.5	18.4	18.0	19.8	19.8	18.9	19.4	18.4	18.0	17.5
90°	36.3	36.6	37.2	37.7	38.3	38.9	38.3	37.7	37.2	36.6	36.3
92.5°	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0
95°	36.3	36.4	36.7	37.0	37.3	37.6	37.3	37.0	36.7	36.4	36.3
97.5°	35.0	35.1	35.4	35.7	36.0	36.3	36.0	35.7	35.4	35.1	35.0
100°	35.0	35.1	35.4	35.7	36.0	36.3	36.0	35.7	35.4	35.1	35.0
102.5°	37.6	37.6	37.6	37.6	37.6	37.6	37.6	37.6	37.6	37.6	37.6
105°	416.5	411.3	400.9	390.6	380.2	369.8	380.2	390.6	400.9	411.3	416.5
107.5°	494.4	495.0	496.1	497.3	498.4	499.6	498.4	497.3	496.1	495.0	494.4
110°	574.8	575.2	576.1	577.0	577.8	578.7	577.8	577.0	576.1	575.2	574.8

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	652.7	653.3	654.4	655.6	656.7	657.9	656.7	655.6	654.4	653.3	652.7
115°	734.4	734.4	734.4	734.4	734.4	734.4	734.4	734.4	734.4	734.4	734.4
117.5°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6
120°	890.2	889.9	889.3	888.8	888.2	887.6	888.2	888.8	889.3	889.9	890.2
122.5°	962.8	962.5	961.9	961.4	960.8	960.2	960.8	961.4	961.9	962.5	962.8
125°	1031.6	1031.7	1032.0	1032.3	1032.6	1032.9	1032.6	1032.3	1032.0	1031.7	1031.6
127.5°	1097.8	1097.7	1097.4	1097.1	1096.8	1096.5	1096.8	1097.1	1097.4	1097.7	1097.8
130°	1161.4	1161.4	1161.4	1161.4	1161.4	1161.4	1161.4	1161.4	1161.4	1161.4	1161.4
132.5°	1222.4	1222.3	1222.0	1221.7	1221.4	1221.1	1221.4	1221.7	1222.0	1222.3	1222.4
135°	1278.1	1278.4	1279.0	1279.5	1280.1	1280.7	1280.1	1279.5	1279.0	1278.4	1278.1
137.5°	1332.6	1332.5	1332.2	1331.9	1331.7	1331.4	1331.7	1331.9	1332.2	1332.5	1332.6
140°	1383.3	1383.4	1383.7	1384.0	1384.3	1384.6	1384.3	1384.0	1383.7	1383.4	1383.3
142.5°	1428.7	1428.7	1428.7	1428.7	1428.7	1428.7	1428.7	1428.7	1428.7	1428.7	1428.7
145°	1471.5	1471.8	1472.4	1472.9	1473.5	1474.1	1473.5	1472.9	1472.4	1471.8	1471.5
147.5°	1510.4	1510.5	1510.8	1511.1	1511.4	1511.7	1511.4	1511.1	1510.8	1510.5	1510.4
150°	1546.8	1546.9	1547.2	1547.5	1547.8	1548.1	1547.8	1547.5	1547.2	1546.9	1546.8
152.5°	1580.5	1580.4	1580.1	1579.8	1579.5	1579.2	1579.5	1579.8	1580.1	1580.4	1580.5
155°	1610.3	1609.9	1609.0	1608.1	1607.3	1606.4	1607.3	1608.1	1609.0	1609.9	1610.3
157.5°	1636.3	1635.6	1634.1	1632.7	1631.2	1629.8	1631.2	1632.7	1634.1	1635.6	1636.3
160°	1660.9	1660.0	1658.3	1656.6	1654.9	1653.2	1654.9	1656.6	1658.3	1660.0	1660.9
162.5°	1680.4	1679.4	1677.4	1675.3	1673.3	1671.3	1673.3	1675.3	1677.4	1679.4	1680.4
165°	1699.9	1698.6	1696.0	1693.4	1690.8	1688.2	1690.8	1693.4	1696.0	1698.6	1699.9
167.5°	1714.1	1712.7	1709.8	1706.9	1704.1	1701.2	1704.1	1706.9	1709.8	1712.7	1714.1
170°	1725.8	1724.4	1721.5	1718.6	1715.7	1712.8	1715.7	1718.6	1721.5	1724.4	1725.8
172.5°	1733.6	1732.0	1728.8	1725.7	1722.5	1719.3	1722.5	1725.7	1728.8	1732.0	1733.6
175°	1740.1	1738.4	1734.9	1731.4	1728.0	1724.5	1728.0	1731.4	1734.9	1738.4	1740.1
177.5°	1742.7	1741.0	1737.5	1734.0	1730.6	1727.1	1730.6	1734.0	1737.5	1741.0	1742.7
180°	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	523.1	525.9	523.1	524.9	525.9	528.2	529.1	533.2	534.6	537.8	537.8
5°	491.8	493.1	493.6	495.4	497.3	501.9	505.1	511.1	518.0	518.9	523.1
7.5°	466.4	468.7	472.4	471.0	474.2	481.2	485.3	492.7	499.6	503.3	508.3
10°	443.8	446.6	448.0	449.4	455.3	461.3	467.8	472.9	482.1	487.6	491.8
12.5°	425.4	423.1	425.8	430.9	437.8	441.5	450.3	458.1	465.0	471.0	474.7
15°	401.4	403.3	406.0	414.8	416.6	425.8	429.1	437.8	450.7	456.3	460.9
17.5°	378.4	384.4	389.9	393.1	398.7	406.0	415.2	424.9	433.2	439.7	445.2
20°	359.9	365.9	369.2	371.5	377.0	387.1	395.9	407.9	418.5	423.5	430.9
22.5°	345.2	345.2	349.8	356.7	359.9	369.6	377.0	389.9	401.4	407.9	414.8
25°	326.8	329.5	333.2	339.2	343.8	351.6	362.2	373.3	385.8	391.3	400.0
27.5°	311.6	314.8	319.8	321.2	325.8	332.8	343.8	355.8	368.7	374.7	382.1
30°	300.0	301.9	303.7	306.5	310.6	316.6	325.8	336.4	352.1	356.7	365.9
32.5°	289.9	290.8	291.7	294.0	296.3	302.3	309.7	321.2	334.1	341.0	349.3
35°	280.7	279.8	280.2	281.6	283.9	286.2	294.0	303.7	315.7	324.0	330.4
37.5°	271.9	270.1	269.6	269.6	270.5	273.3	279.3	287.6	300.5	307.4	313.9
40°	262.2	260.4	259.5	259.0	258.6	260.4	265.0	273.3	283.4	289.9	297.3
42.5°	253.0	251.2	248.9	248.4	247.5	248.4	251.6	259.5	268.2	274.7	280.7
45°	243.8	240.6	237.8	236.0	236.4	235.0	237.4	243.3	253.5	257.6	263.6
47.5°	233.7	230.0	226.3	224.4	222.6	223.5	224.4	229.5	238.3	242.4	248.4
50°	224.0	218.9	214.8	212.5	211.1	210.2	211.1	216.1	222.6	226.3	231.4
52.5°	212.9	207.9	203.7	200.0	198.2	196.8	197.3	201.9	207.9	211.5	216.6
55°	202.8	196.3	190.8	186.2	184.8	184.3	183.9	187.1	192.2	195.9	200.0
57.5°	191.3	184.8	178.8	173.3	170.5	170.1	170.1	171.0	177.4	180.2	182.5
60°	179.7	172.8	166.4	161.3	157.2	155.8	155.3	157.2	160.4	163.1	166.4
62.5°	166.8	159.9	152.1	147.5	143.3	139.6	141.0	141.5	146.1	147.5	150.2
65°	154.4	146.6	140.1	132.7	128.1	125.8	124.9	125.8	129.5	130.0	131.8
67.5°	140.1	132.7	124.9	119.8	115.7	111.5	110.6	110.6	112.5	113.8	116.1
70°	126.3	118.9	110.1	104.6	100.5	96.8	95.4	94.9	96.3	97.2	99.5
72.5°	110.1	102.8	96.3	90.3	85.3	82.5	81.1	80.2	81.6	82.5	83.0
75°	93.1	87.1	80.7	74.7	71.4	68.7	66.8	65.4	66.4	66.4	66.4
77.5°	77.0	71.0	65.9	61.8	57.6	54.4	53.0	51.6	52.1	52.1	53.0
80°	59.9	55.8	51.6	47.9	44.2	41.5	40.6	39.2	38.3	37.8	37.8
82.5°	44.2	41.0	37.3	34.1	32.3	29.5	28.6	26.7	26.7	26.3	26.3
85°	29.5	27.7	24.0	21.7	20.3	18.9	18.0	17.1	15.7	15.7	15.2
87.5°	15.7	14.7	13.8	11.1	11.1	9.7	9.2	8.8	7.4	7.8	7.8
90°	35.4	33.7	32.0	30.2	28.5	26.2	23.9	21.6	19.3	18.2	16.6
92.5°	34.1	32.4	30.7	28.9	27.2	24.9	22.6	20.3	18.0	16.9	17.2
95°	35.4	33.7	32.0	30.2	28.5	28.2	27.9	27.6	27.3	27.2	32.1
97.5°	34.3	32.8	31.4	29.9	28.5	58.8	89.1	119.4	149.7	164.8	161.6
100°	37.5	42.4	47.3	52.2	57.1	96.9	136.7	176.5	216.3	236.2	233.6
102.5°	70.0	134.9	199.8	264.7	329.6	326.1	322.7	319.2	315.7	314.0	312.3
105°	415.2	412.6	410.1	407.5	404.9	403.5	402.0	400.6	399.1	398.4	397.5
107.5°	493.7	492.2	490.8	489.3	487.9	485.9	483.9	481.8	479.8	478.8	478.4
110°	574.5	573.9	573.4	572.8	572.2	570.5	568.8	567.1	565.4	564.5	564.1

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	652.8	653.1	653.4	653.7	654.0	653.4	652.8	652.3	651.7	651.4	650.5
115°	734.1	733.6	733.0	732.5	731.9	732.2	732.5	732.8	733.1	733.2	732.8
117.5°	813.7	814.0	814.3	814.6	814.9	814.0	813.2	812.3	811.4	811.0	810.4
120°	889.9	889.3	888.8	888.2	887.6	887.9	888.2	888.5	888.8	888.9	888.3
122.5°	962.7	962.4	962.1	961.8	961.5	960.9	960.3	959.8	959.2	958.9	958.6
125°	1031.2	1030.3	1029.4	1028.6	1027.7	1028.3	1028.9	1029.4	1030.0	1030.3	1029.7
127.5°	1097.9	1098.2	1098.5	1098.8	1099.1	1097.7	1096.2	1094.8	1093.3	1092.6	1092.5
130°	1161.3	1161.0	1160.7	1160.4	1160.1	1159.2	1158.4	1157.5	1156.6	1156.2	1156.1
132.5°	1222.3	1222.0	1221.7	1221.4	1221.1	1219.9	1218.8	1217.6	1216.5	1215.9	1215.6
135°	1277.8	1277.3	1276.7	1276.2	1275.6	1274.4	1273.3	1272.1	1271.0	1270.4	1270.5
137.5°	1332.3	1331.8	1331.2	1330.7	1330.1	1328.7	1327.2	1325.8	1324.3	1323.6	1323.6
140°	1382.9	1382.0	1381.1	1380.3	1379.4	1378.8	1378.2	1377.7	1377.1	1376.8	1376.5
142.5°	1428.4	1427.8	1427.3	1426.7	1426.1	1425.8	1425.5	1425.2	1424.9	1424.8	1424.2
145°	1471.4	1471.1	1470.8	1470.5	1470.2	1470.2	1470.2	1470.2	1470.2	1470.2	1469.8
147.5°	1510.3	1510.0	1509.7	1509.4	1509.1	1509.4	1509.7	1510.0	1510.3	1510.4	1509.5
150°	1546.8	1546.8	1546.8	1546.8	1546.8	1547.1	1547.4	1547.7	1548.0	1548.1	1547.5
152.5°	1580.2	1579.6	1579.1	1578.5	1577.9	1578.5	1579.1	1579.6	1580.2	1580.5	1580.1
155°	1609.7	1608.6	1607.4	1606.3	1605.1	1606.0	1606.8	1607.7	1608.6	1609.0	1608.9
157.5°	1635.6	1634.1	1632.7	1631.2	1629.8	1631.0	1632.1	1633.3	1634.4	1635.0	1635.0
160°	1660.0	1658.3	1656.6	1654.9	1653.2	1653.5	1653.8	1654.1	1654.4	1654.5	1654.9
162.5°	1679.5	1677.8	1676.1	1674.3	1672.6	1672.9	1673.2	1673.5	1673.8	1673.9	1674.5
165°	1698.7	1696.4	1694.1	1691.8	1689.5	1689.5	1689.5	1689.5	1689.5	1689.5	1690.2
167.5°	1712.8	1710.2	1707.7	1705.1	1702.5	1702.8	1703.1	1703.4	1703.7	1703.8	1704.5
170°	1724.6	1722.3	1720.0	1717.7	1715.4	1715.1	1714.8	1714.5	1714.2	1714.1	1715.0
172.5°	1732.4	1730.1	1727.8	1725.5	1723.2	1722.9	1722.6	1722.3	1722.0	1721.9	1722.8
175°	1738.8	1736.2	1733.6	1731.0	1728.4	1728.1	1727.8	1727.5	1727.2	1727.1	1728.0
177.5°	1741.5	1739.2	1736.9	1734.6	1732.3	1731.7	1731.1	1730.6	1730.0	1729.7	1730.7
180°	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9	1734.9

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	556.3	556.3	556.3	556.3
2.5°	541.1	545.7	549.8	556.3
5°	529.1	535.5	544.3	554.0
7.5°	515.3	525.4	536.9	550.3
10°	502.4	513.9	528.6	544.8
12.5°	489.0	502.8	518.9	536.5
15°	473.8	487.6	505.6	529.1
17.5°	460.0	476.5	495.9	520.8
20°	443.8	459.5	480.7	509.3
22.5°	429.5	447.5	471.0	495.9
25°	413.9	429.5	453.0	483.0
27.5°	398.2	417.6	440.1	469.2
30°	383.0	399.1	423.5	454.0
32.5°	366.4	385.8	408.3	436.9
35°	348.4	366.9	388.1	418.9
37.5°	332.3	350.3	371.9	399.1
40°	314.3	333.2	353.0	380.2
42.5°	296.8	313.9	333.7	358.6
45°	279.8	294.5	312.5	334.1
47.5°	262.2	274.7	291.3	310.6
50°	243.3	256.7	269.2	285.3
52.5°	225.8	237.4	247.5	260.9
55°	208.8	216.6	224.9	235.0
57.5°	190.8	196.8	202.8	213.4
60°	172.8	178.4	181.6	188.5
62.5°	155.3	157.6	161.8	165.9
65°	136.0	139.2	141.5	146.6
67.5°	118.4	119.8	122.1	125.4
70°	100.0	103.2	104.2	106.5
72.5°	84.3	85.7	86.6	87.1
75°	66.8	68.2	69.1	71.9
77.5°	52.5	52.1	53.9	54.4
80°	38.7	37.3	37.8	39.6
82.5°	25.3	25.8	25.3	25.3
85°	15.7	15.2	14.3	14.7
87.5°	6.9	6.9	6.5	6.5
90°	13.4	10.3	7.1	3.9
92.5°	17.8	18.3	18.9	19.5
95°	41.9	51.8	61.6	71.4
97.5°	155.3	148.9	142.6	136.2
100°	228.4	223.2	218.0	212.8
102.5°	308.8	305.4	301.9	298.5
105°	395.8	394.1	392.3	390.6
107.5°	477.5	476.6	475.8	474.9
110°	563.2	562.3	561.5	560.6

TEST NUMBER: P1032631

CATALOG NUMBER: S124DIW-B350D1340UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	648.8	647.1	645.3	643.6
115°	731.9	731.0	730.2	729.3
117.5°	809.3	808.1	807.0	805.8
120°	887.2	886.0	884.9	883.7
122.5°	958.0	957.5	956.9	956.3
125°	1028.6	1027.4	1026.3	1025.1
127.5°	1092.2	1091.9	1091.6	1091.3
130°	1155.8	1155.5	1155.2	1154.9
132.5°	1215.0	1214.5	1213.9	1213.3
135°	1270.8	1271.1	1271.4	1271.7
137.5°	1323.6	1323.6	1323.6	1323.6
140°	1375.9	1375.4	1374.8	1374.2
142.5°	1423.1	1421.9	1420.8	1419.6
145°	1468.9	1468.0	1467.2	1466.3
147.5°	1507.8	1506.1	1504.3	1502.6
150°	1546.4	1545.2	1544.1	1542.9
152.5°	1579.2	1578.3	1577.5	1576.6
155°	1608.6	1608.3	1608.0	1607.7
157.5°	1635.0	1635.0	1635.0	1635.0
160°	1655.8	1656.6	1657.5	1658.3
162.5°	1675.6	1676.8	1677.9	1679.1
165°	1691.7	1693.1	1694.6	1696.0
167.5°	1706.0	1707.4	1708.9	1710.3
170°	1716.7	1718.4	1720.2	1721.9
172.5°	1724.5	1726.2	1728.0	1729.7
175°	1729.7	1731.4	1733.2	1734.9
177.5°	1732.7	1734.8	1736.8	1738.8
180°	1734.9	1734.9	1734.9	1734.9

(END OF REPORT)