

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032659

Luminaire Tested: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032659
REPORT IS A COMBINATION OF REPORTS P997486 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3058.0 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55			48
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	49	47	46			41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39			35
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34			30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29			26
5	68	57	49	43	63	53	46	41	45	40	35	38	34	31	31	28	26			22
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23			20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20			18
8	54	42	34	29	50	39	32	28	34	28	24	29	24	21	24	21	18			16
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16			14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4362	4362	4362	4362
5°	4351	5004	4376	3760
10°	4318	5838	4351	3299
15°	4266	6730	4296	2951
20°	4211	7298	4241	2646
25°	4130	7214	4170	2421
30°	4052	5963	4101	2305
35°	3941	4444	3985	2235
40°	3812	3347	3849	2200
45°	3615	2687	3660	2153
50°	3379	2264	3428	2132
55°	3102	1970	3152	2107
60°	2834	1735	2917	2072
65°	2580	1492	2606	1985
70°	2285	1228	2334	1828
75°	1991	943	1980	1552
80°	1567	620	1551	1178
85°	1033	279	968	688

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5640 cd/sqm

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	1.7
10°-20°	160.7	5.3
20°-30°	255.3	8.3
30°-40°	283.6	9.3
40°-50°	257.9	8.4
50°-60°	210.8	6.9
60°-70°	150.5	4.9
70°-80°	82.8	2.7
80°-90°	23.6	0.8
90°-100°	37.1	1.2
100°-110°	111.2	3.6
110°-120°	189.0	6.2
120°-130°	249.2	8.1
130°-140°	279.9	9.2
140°-150°	275.1	9.0
150°-160°	231.4	7.6
160°-170°	154.0	5.0
170°-180°	53.9	1.8
0°-30°	468.0	15.3
0°-40°	751.6	24.6
0°-60°	1220.4	39.9
0°-90°	1477.2	48.3
90°-120°	337.3	11.0
90°-150°	1141.5	37.3
90°-180°	1581.0	51.7
0°-180°	3058.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	535	535	535	535	535	
5°	533	628	536	472	533	51
15°	509	862	512	378	509	144
25°	464	915	469	307	464	214
35°	403	541	407	272	403	252
45°	321	304	325	243	321	248
55°	226	198	230	212	226	203
65°	141	128	142	170	141	139
75°	69	64	69	105	69	73
85°	14	13	13	33	14	17
90°	1	13	1	13	1	3
95°	26	35	26	35	26	29
105°	103	108	103	108	103	109
115°	192	190	192	190	192	189
125°	280	278	280	278	280	249
135°	361	361	361	361	361	279
145°	438	439	438	439	438	274
155°	502	502	502	502	502	231
165°	547	546	547	546	547	154
175°	569	566	569	566	569	54
180°	570	570	570	570	570	

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	534.9	540.2	542.4	544.2	550.0	551.7	552.2	554.8	557.1	557.5	557.5
5°	532.7	541.1	547.7	553.9	563.3	567.2	572.1	577.4	584.5	589.0	591.2
7.5°	529.1	541.5	551.7	562.4	575.2	583.2	587.6	601.8	611.6	619.5	629.3
10°	523.8	539.8	554.4	569.9	588.1	597.8	607.6	624.9	638.6	654.1	666.5
12.5°	515.8	536.7	554.4	576.1	598.7	610.2	621.8	651.9	667.8	681.6	703.7
15°	508.7	529.6	554.8	577.0	604.9	622.2	639.0	658.5	683.8	713.5	734.8
17.5°	500.8	526.9	550.4	581.4	612.4	628.8	642.6	672.7	708.2	737.4	756.9
20°	489.7	516.3	547.3	580.1	616.9	629.7	647.9	688.2	720.1	748.9	780.8
22.5°	476.8	507.9	540.7	572.1	610.2	637.3	657.2	692.7	731.2	764.5	800.3
25°	464.4	498.1	526.9	569.9	610.2	628.4	651.0	693.1	735.2	775.5	812.3
27.5°	451.1	482.6	521.6	555.7	601.4	621.3	645.7	691.8	736.5	776.9	816.3
30°	436.5	470.2	502.5	542.9	587.2	612.9	635.5	685.6	731.2	773.3	810.1
32.5°	420.1	452.0	486.6	524.7	571.2	597.4	625.7	677.1	725.9	762.2	790.6
35°	402.8	435.2	465.3	504.3	552.2	578.3	605.8	662.5	710.8	740.5	756.9
37.5°	383.8	414.4	444.0	482.6	530.5	558.4	586.3	641.3	686.9	711.7	707.3
40°	365.6	393.1	420.6	456.9	507.0	536.7	561.0	616.4	656.3	667.0	652.3
42.5°	344.8	368.3	394.9	432.1	480.8	508.7	539.3	589.8	619.5	615.1	590.3
45°	321.3	342.1	368.7	403.7	453.4	482.2	507.9	555.7	577.4	566.4	521.2
47.5°	298.7	319.1	340.8	375.8	424.1	448.5	474.6	517.6	530.0	506.5	461.3
50°	274.3	291.2	313.8	347.0	392.2	417.9	439.6	474.2	478.6	449.8	402.8
52.5°	250.8	265.0	286.7	319.5	361.6	382.0	403.3	433.9	430.3	400.6	355.4
55°	226.0	239.3	259.2	289.4	326.6	346.1	364.3	391.3	383.8	353.2	313.8
57.5°	205.2	214.5	234.0	261.9	292.5	313.8	329.3	350.5	339.0	308.4	271.7
60°	181.3	192.8	209.2	231.8	261.9	276.1	289.8	304.0	296.0	266.8	234.0
62.5°	159.5	168.4	182.6	204.3	227.8	240.6	255.3	264.1	256.1	229.1	201.6
65°	140.9	148.0	159.1	176.8	199.4	210.1	218.5	226.9	220.3	195.0	175.0
67.5°	120.5	126.7	136.0	150.2	169.3	176.8	184.8	190.6	183.0	166.2	146.7
70°	102.4	106.8	115.7	126.3	139.6	146.7	153.3	159.1	152.4	138.3	123.6
72.5°	83.8	87.3	95.3	102.8	114.8	119.7	124.5	129.0	126.7	113.4	101.5
75°	69.1	70.5	75.8	82.0	89.5	94.8	98.4	101.0	99.3	88.6	81.1
77.5°	52.3	54.1	58.1	62.9	69.6	72.7	74.9	77.6	75.3	66.9	61.6
80°	38.1	38.6	40.8	45.2	49.6	50.1	52.3	55.8	54.5	48.7	44.8
82.5°	24.4	25.7	26.6	29.2	32.4	33.2	34.6	35.5	35.0	31.5	30.1
85°	14.2	14.2	15.1	16.8	17.7	19.1	19.5	19.9	20.8	18.6	17.3
87.5°	6.2	6.6	6.6	7.1	8.0	8.0	8.4	8.9	9.3	8.9	7.5
90°	1.3	2.4	3.5	4.6	5.7	6.2	6.6	7.4	8.1	8.9	9.7
92.5°	11.5	12.8	14.0	15.3	16.6	17.2	17.4	17.9	18.4	18.9	19.4
95°	26.4	27.3	28.2	29.1	30.0	30.4	30.7	31.4	32.1	32.8	33.5
97.5°	42.3	43.1	43.9	44.6	45.4	45.8	46.2	47.0	47.7	48.5	49.3
100°	61.7	62.1	62.5	62.8	63.2	63.4	63.8	64.7	65.6	66.5	67.4
102.5°	82.0	82.1	82.2	82.3	82.4	82.4	82.8	83.6	84.3	85.1	85.9
105°	102.7	102.8	102.9	103.0	103.1	103.1	103.3	103.7	104.1	104.5	104.9
107.5°	124.3	124.4	124.5	124.6	124.7	124.7	124.7	124.8	124.9	125.0	125.1
110°	146.3	146.5	146.7	146.9	147.1	147.2	147.1	147.0	146.9	146.8	146.7

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	169.2	169.2	169.2	169.2	169.2	169.2	169.1	168.9	168.7	168.5	168.3
115°	192.1	192.1	192.1	192.1	192.1	192.1	192.0	191.8	191.6	191.4	191.2
117.5°	213.7	213.7	213.7	213.7	213.7	213.7	213.7	213.6	213.5	213.4	213.3
120°	235.3	235.7	236.1	236.5	236.9	237.1	236.9	236.6	236.3	236.0	235.7
122.5°	257.8	257.9	258.0	258.1	258.2	258.2	258.2	258.1	258.0	257.9	257.8
125°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.7	279.6	279.5	279.4
127.5°	299.6	299.9	300.2	300.5	300.8	300.9	300.8	300.6	300.5	300.3	300.1
130°	320.8	321.1	321.4	321.7	322.0	322.1	322.1	322.1	322.1	322.1	322.1
132.5°	342.4	342.6	342.8	342.9	343.1	343.2	343.2	343.1	343.0	342.9	342.8
135°	360.9	361.5	362.1	362.6	363.2	363.5	363.5	363.5	363.5	363.5	363.5
137.5°	381.6	381.9	382.2	382.5	382.8	382.9	383.0	383.2	383.4	383.6	383.8
140°	402.3	402.5	402.7	402.9	403.1	403.2	403.2	403.2	403.2	403.2	403.2
142.5°	421.2	421.4	421.6	421.8	422.0	422.1	422.1	422.0	421.9	421.8	421.7
145°	438.4	438.8	439.2	439.6	440.0	440.2	440.2	440.3	440.4	440.5	440.6
147.5°	456.0	456.5	457.0	457.5	458.0	458.2	458.2	458.1	458.0	457.9	457.8
150°	471.9	472.3	472.7	473.1	473.5	473.7	473.7	473.7	473.7	473.7	473.7
152.5°	486.9	487.1	487.3	487.5	487.7	487.8	487.8	487.9	488.0	488.1	488.2
155°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.2	502.1	502.0	501.9
157.5°	515.5	515.3	515.1	514.9	514.7	514.6	514.6	514.6	514.6	514.6	514.6
160°	527.0	526.9	526.8	526.7	526.6	526.5	526.5	526.4	526.3	526.2	526.1
162.5°	537.6	537.3	537.0	536.7	536.4	536.2	536.2	536.1	536.0	535.9	535.8
165°	546.8	546.5	546.2	545.9	545.6	545.5	545.4	545.2	545.0	544.8	544.6
167.5°	554.3	553.9	553.5	553.1	552.7	552.5	552.5	552.5	552.5	552.5	552.5
170°	560.5	560.0	559.5	559.0	558.5	558.3	558.3	558.4	558.5	558.6	558.7
172.5°	564.9	564.5	564.1	563.7	563.3	563.1	563.1	563.1	563.1	563.1	563.1
175°	568.8	568.3	567.8	567.3	566.8	566.6	566.6	566.5	566.4	566.3	566.2
177.5°	570.6	570.1	569.6	569.1	568.6	568.4	568.4	568.4	568.4	568.4	568.4
180°	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	558.8	566.8	570.3	571.2	576.1	573.0	574.3	573.9	577.4	577.9	577.9
5°	599.6	608.9	612.0	616.4	623.1	624.9	623.5	626.2	631.1	627.5	632.8
7.5°	642.6	652.8	659.9	669.6	671.8	677.6	681.1	684.2	685.1	685.6	686.5
10°	682.5	695.3	705.1	721.5	725.0	728.1	743.6	737.4	745.4	742.7	743.6
12.5°	714.8	740.1	748.1	775.5	778.2	788.8	787.9	797.7	799.5	803.0	799.5
15°	757.4	786.6	799.5	815.0	823.8	836.2	838.5	851.8	857.1	861.9	857.1
17.5°	796.4	811.9	844.7	857.1	862.8	869.5	886.3	891.2	899.2	896.1	904.9
20°	815.9	838.0	872.6	893.9	902.7	908.9	923.1	930.6	933.7	933.7	934.6
22.5°	833.1	865.0	890.8	915.1	923.1	927.5	936.0	941.7	943.0	943.9	944.8
25°	848.7	877.5	898.3	912.0	915.1	915.1	920.0	916.5	910.7	915.1	917.8
27.5°	848.7	869.0	878.3	883.2	883.2	871.3	864.2	849.5	837.1	833.6	841.6
30°	834.5	843.8	830.9	819.0	809.7	801.7	773.8	751.6	747.2	744.1	756.0
32.5°	801.7	789.7	764.5	729.9	716.1	698.0	676.3	659.4	649.2	645.7	643.0
35°	743.6	712.6	679.8	633.3	623.5	600.5	570.8	558.4	541.5	541.1	546.9
37.5°	680.2	632.4	596.9	552.6	538.9	514.5	486.6	473.7	462.2	453.4	464.0
40°	606.2	564.6	510.5	474.2	454.7	441.8	418.3	404.2	398.8	394.4	401.1
42.5°	537.1	491.5	449.4	412.1	396.2	381.6	366.0	352.3	348.3	347.9	352.8
45°	468.4	423.7	384.7	352.8	342.6	333.7	318.6	314.6	308.0	303.6	305.8
47.5°	413.5	367.4	335.0	310.7	301.8	294.3	284.5	277.9	272.1	270.3	273.0
50°	359.4	328.4	295.1	274.8	268.1	261.0	253.5	247.3	244.6	242.9	244.6
52.5°	316.0	282.7	260.1	243.7	237.1	231.8	226.5	223.8	220.3	221.1	222.9
55°	277.0	247.7	228.7	216.7	212.7	210.5	203.9	200.8	199.4	198.5	199.4
57.5°	240.2	218.9	204.7	194.5	189.2	187.9	182.6	182.6	181.3	179.9	180.4
60°	210.9	192.8	179.0	171.1	170.2	168.0	164.4	164.0	160.9	162.2	162.6
62.5°	181.3	166.6	157.3	152.4	149.3	148.5	146.2	145.8	144.5	144.9	144.0
65°	157.8	145.8	136.5	132.5	131.2	130.7	129.0	127.6	126.7	127.6	126.7
67.5°	134.3	126.3	119.2	115.2	113.4	113.0	111.7	110.8	111.2	109.9	110.8
70°	112.1	104.1	99.7	97.5	96.6	95.3	95.3	95.3	95.3	94.4	93.9
72.5°	94.4	86.4	83.3	82.0	81.1	80.7	79.3	79.8	79.3	78.9	80.7
75°	74.9	70.0	66.9	65.6	66.5	65.1	63.8	64.7	63.4	63.8	65.6
77.5°	56.7	54.5	52.7	51.8	51.0	50.1	50.1	49.2	49.2	49.2	49.2
80°	41.2	40.8	37.7	37.2	37.2	36.3	36.3	36.3	36.3	35.9	36.3
82.5°	27.5	27.0	26.1	25.7	24.8	25.3	25.3	24.4	24.4	23.9	24.4
85°	16.0	16.0	15.1	14.6	14.2	14.6	13.7	13.3	13.7	13.3	13.7
87.5°	7.5	6.6	7.1	6.6	5.8	6.2	5.3	5.8	5.3	4.9	5.8
90°	10.3	10.9	11.4	12.0	12.3	12.4	12.6	12.8	13.0	13.2	13.0
92.5°	19.7	20.0	20.3	20.6	20.7	20.7	20.8	20.9	21.0	21.1	21.0
95°	33.8	34.1	34.4	34.7	34.8	34.8	34.8	34.8	34.8	34.8	34.8
97.5°	49.7	50.1	50.5	50.9	51.1	51.1	51.1	51.1	51.1	51.1	51.1
100°	67.6	67.8	68.0	68.2	68.3	68.3	68.3	68.3	68.3	68.3	68.3
102.5°	86.2	86.5	86.8	87.1	87.2	87.3	87.4	87.5	87.6	87.7	87.6
105°	105.2	105.5	105.8	106.1	106.2	106.3	106.6	106.9	107.2	107.5	107.2
107.5°	125.5	125.9	126.3	126.7	126.9	126.9	126.8	126.7	126.6	126.5	126.6
110°	146.5	146.3	146.1	145.9	145.8	146.0	146.3	146.6	146.9	147.2	146.9

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3
115°	191.1	191.0	190.9	190.8	190.8	190.7	190.6	190.5	190.4	190.3	190.4
117.5°	213.0	212.7	212.4	212.1	211.9	211.8	211.5	211.2	210.9	210.6	210.9
120°	235.2	234.7	234.2	233.7	233.5	233.6	233.8	234.0	234.2	234.4	234.2
122.5°	257.5	257.2	256.9	256.6	256.4	256.2	255.7	255.2	254.7	254.2	254.7
125°	279.2	279.0	278.8	278.6	278.5	278.4	278.2	278.0	277.8	277.6	277.8
127.5°	299.9	299.7	299.5	299.3	299.2	299.1	299.0	298.9	298.8	298.7	298.8
130°	321.9	321.7	321.5	321.3	321.2	321.0	320.6	320.3	319.9	319.5	319.9
132.5°	342.6	342.4	342.2	342.0	341.9	341.9	341.8	341.7	341.6	341.5	341.6
135°	363.3	363.1	362.9	362.7	362.6	362.5	362.2	361.9	361.6	361.3	361.6
137.5°	383.5	383.2	382.9	382.6	382.5	382.5	382.6	382.7	382.8	382.9	382.8
140°	403.1	403.0	402.9	402.8	402.7	402.7	402.6	402.5	402.4	402.3	402.4
142.5°	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7
145°	440.5	440.4	440.3	440.2	440.2	440.1	439.8	439.5	439.2	438.9	439.2
147.5°	457.7	457.6	457.5	457.4	457.4	457.3	457.2	457.1	457.0	456.9	457.0
150°	473.7	473.7	473.7	473.7	473.7	473.6	473.5	473.4	473.3	473.2	473.3
152.5°	488.5	488.8	489.1	489.4	489.5	489.4	489.1	488.8	488.5	488.2	488.5
155°	502.3	502.7	503.0	503.4	503.6	503.4	503.0	502.7	502.3	501.9	502.3
157.5°	514.9	515.2	515.5	515.8	516.0	515.8	515.5	515.2	514.9	514.6	514.9
160°	526.4	526.7	527.0	527.3	527.4	527.2	526.7	526.2	525.7	525.2	525.7
162.5°	536.4	537.0	537.5	538.1	538.4	538.2	537.7	537.2	536.7	536.2	536.7
165°	545.2	545.8	546.4	547.0	547.3	547.1	546.7	546.3	545.9	545.5	545.9
167.5°	553.1	553.7	554.3	554.9	555.2	554.9	554.3	553.7	553.1	552.5	553.1
170°	559.3	559.9	560.5	561.1	561.4	561.1	560.4	559.7	559.0	558.3	559.0
172.5°	563.8	564.5	565.2	565.9	566.2	565.9	565.2	564.5	563.8	563.1	563.8
175°	566.9	567.6	568.3	569.0	569.3	569.0	568.3	567.6	566.9	566.2	566.9
177.5°	569.1	569.8	570.5	571.2	571.5	571.1	570.3	569.6	568.8	568.0	568.8
180°	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	577.0	575.7	573.9	573.9	571.7	571.7	568.1	561.9	556.6	554.8	555.7
5°	626.2	626.6	624.0	621.8	617.8	614.7	608.9	597.8	594.3	587.2	582.3
7.5°	682.5	680.7	675.8	672.3	671.4	664.3	651.9	638.6	628.0	620.9	610.7
10°	745.8	738.7	731.7	729.4	724.1	712.2	698.0	683.4	668.7	653.2	635.9
12.5°	799.0	785.3	784.8	779.5	769.3	762.7	745.8	725.0	699.7	682.5	663.0
15°	856.2	843.3	832.7	822.9	818.1	798.6	784.4	758.2	728.1	709.5	696.2
17.5°	897.0	891.2	873.0	868.6	861.9	839.3	816.7	791.0	764.9	738.7	702.9
20°	929.7	926.2	914.2	908.0	897.4	879.7	852.2	822.5	792.4	755.1	721.5
22.5°	943.9	939.5	929.7	924.4	917.8	902.7	879.2	845.5	806.1	772.9	737.0
25°	916.0	924.0	921.3	919.1	916.5	907.6	889.9	860.2	821.6	783.9	739.2
27.5°	853.1	866.8	880.1	881.9	886.3	889.9	882.8	861.5	829.2	789.3	740.1
30°	768.4	774.6	801.7	809.7	815.9	838.5	851.8	846.4	821.6	785.7	740.5
32.5°	659.9	676.3	703.7	722.8	739.6	764.9	799.5	813.2	804.3	775.1	730.3
35°	557.1	576.6	608.5	632.8	649.7	685.6	726.3	756.0	767.1	752.5	712.6
37.5°	472.9	496.3	524.7	534.0	553.5	597.8	654.1	695.3	722.3	723.7	692.7
40°	409.5	421.4	444.0	458.2	477.3	514.5	569.5	624.0	664.7	678.5	662.1
42.5°	355.9	365.2	382.0	399.3	416.6	444.9	495.5	546.4	601.4	628.8	628.4
45°	313.3	323.1	334.6	348.8	360.7	391.3	431.2	483.5	530.9	573.4	584.1
47.5°	276.1	284.5	298.7	304.9	312.9	341.7	376.2	425.0	474.2	522.9	535.3
50°	248.6	255.7	265.5	269.4	278.3	299.6	327.9	367.4	421.9	466.6	489.7
52.5°	223.8	229.1	236.6	239.7	246.0	261.9	287.6	318.6	363.8	409.9	442.3
55°	202.5	206.1	211.4	214.9	219.4	233.5	252.6	280.5	319.5	359.4	390.9
57.5°	182.6	185.2	190.6	192.3	195.9	207.0	220.3	243.7	279.6	315.1	345.7
60°	164.0	165.7	168.8	172.8	175.5	183.0	195.4	214.9	243.7	276.1	300.9
62.5°	146.2	148.9	149.8	151.6	153.8	160.9	170.6	184.8	210.1	236.6	262.8
65°	128.1	130.3	132.1	132.5	134.7	140.0	148.9	161.3	177.7	200.8	225.1
67.5°	111.2	112.6	113.4	115.2	117.4	120.1	127.2	136.5	151.6	170.2	189.7
70°	95.7	95.7	97.1	97.5	100.2	103.3	106.4	115.2	128.5	143.6	156.9
72.5°	78.9	81.1	80.7	82.9	82.4	84.6	88.6	94.4	104.1	116.1	129.0
75°	64.3	65.6	65.6	65.6	66.5	68.2	70.5	75.8	83.3	93.1	100.6
77.5°	50.1	51.0	51.0	51.0	51.4	53.2	55.4	58.9	64.3	70.0	74.5
80°	35.9	36.8	36.8	37.7	37.7	38.1	40.3	42.1	44.8	49.2	53.6
82.5°	24.4	24.8	25.7	25.7	25.3	26.1	26.6	28.4	31.0	31.9	35.0
85°	13.3	13.7	14.2	14.2	14.6	15.5	15.1	16.8	16.8	18.6	19.5
87.5°	5.3	6.2	6.2	5.8	6.2	6.2	6.2	7.1	7.5	8.0	7.5
90°	12.8	12.6	12.4	12.3	12.0	11.4	10.9	10.3	9.7	8.9	8.1
92.5°	20.9	20.8	20.7	20.7	20.6	20.3	20.0	19.7	19.4	18.9	18.4
95°	34.8	34.8	34.8	34.8	34.7	34.4	34.1	33.8	33.5	32.8	32.1
97.5°	51.1	51.1	51.1	51.1	50.9	50.5	50.1	49.7	49.3	48.5	47.7
100°	68.3	68.3	68.3	68.3	68.2	68.0	67.8	67.6	67.4	66.5	65.6
102.5°	87.5	87.4	87.3	87.2	87.1	86.8	86.5	86.2	85.9	85.1	84.3
105°	106.9	106.6	106.3	106.2	106.1	105.8	105.5	105.2	104.9	104.5	104.1
107.5°	126.7	126.8	126.9	126.9	126.7	126.3	125.9	125.5	125.1	125.0	124.9
110°	146.6	146.3	146.0	145.8	145.9	146.1	146.3	146.5	146.7	146.8	146.9

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.5	168.7
115°	190.5	190.6	190.7	190.8	190.8	190.9	191.0	191.1	191.2	191.4	191.6
117.5°	211.2	211.5	211.8	211.9	212.1	212.4	212.7	213.0	213.3	213.4	213.5
120°	234.0	233.8	233.6	233.5	233.7	234.2	234.7	235.2	235.7	236.0	236.3
122.5°	255.2	255.7	256.2	256.4	256.6	256.9	257.2	257.5	257.8	257.9	258.0
125°	278.0	278.2	278.4	278.5	278.6	278.8	279.0	279.2	279.4	279.5	279.6
127.5°	298.9	299.0	299.1	299.2	299.3	299.5	299.7	299.9	300.1	300.3	300.5
130°	320.3	320.6	321.0	321.2	321.3	321.5	321.7	321.9	322.1	322.1	322.1
132.5°	341.7	341.8	341.9	341.9	342.0	342.2	342.4	342.6	342.8	342.9	343.0
135°	361.9	362.2	362.5	362.6	362.7	362.9	363.1	363.3	363.5	363.5	363.5
137.5°	382.7	382.6	382.5	382.5	382.6	382.9	383.2	383.5	383.8	383.6	383.4
140°	402.5	402.6	402.7	402.7	402.8	402.9	403.0	403.1	403.2	403.2	403.2
142.5°	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.8	421.9
145°	439.5	439.8	440.1	440.2	440.2	440.3	440.4	440.5	440.6	440.5	440.4
147.5°	457.1	457.2	457.3	457.4	457.4	457.5	457.6	457.7	457.8	457.9	458.0
150°	473.4	473.5	473.6	473.7	473.7	473.7	473.7	473.7	473.7	473.7	473.7
152.5°	488.8	489.1	489.4	489.5	489.4	489.1	488.8	488.5	488.2	488.1	488.0
155°	502.7	503.0	503.4	503.6	503.4	503.0	502.7	502.3	501.9	502.0	502.1
157.5°	515.2	515.5	515.8	516.0	515.8	515.5	515.2	514.9	514.6	514.6	514.6
160°	526.2	526.7	527.2	527.4	527.3	527.0	526.7	526.4	526.1	526.2	526.3
162.5°	537.2	537.7	538.2	538.4	538.1	537.5	537.0	536.4	535.8	535.9	536.0
165°	546.3	546.7	547.1	547.3	547.0	546.4	545.8	545.2	544.6	544.8	545.0
167.5°	553.7	554.3	554.9	555.2	554.9	554.3	553.7	553.1	552.5	552.5	552.5
170°	559.7	560.4	561.1	561.4	561.1	560.5	559.9	559.3	558.7	558.6	558.5
172.5°	564.5	565.2	565.9	566.2	565.9	565.2	564.5	563.8	563.1	563.1	563.1
175°	567.6	568.3	569.0	569.3	569.0	568.3	567.6	566.9	566.2	566.3	566.4
177.5°	569.6	570.3	571.1	571.5	571.2	570.5	569.8	569.1	568.4	568.4	568.4
180°	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	551.7	550.0	548.6	548.6	544.6	540.7	538.4	537.6	536.7	533.1	528.2
5°	574.3	568.6	564.6	560.6	553.9	546.9	539.8	535.8	530.0	522.0	516.3
7.5°	599.6	585.9	581.4	576.6	563.3	551.3	541.5	533.1	523.8	513.6	503.4
10°	620.9	606.2	596.5	588.1	570.8	554.8	540.2	527.8	515.8	502.5	490.1
12.5°	641.3	620.4	610.2	597.8	579.7	556.6	537.6	522.0	504.3	490.6	475.5
15°	669.6	634.6	617.8	609.8	585.4	558.4	535.3	512.3	497.7	476.8	463.5
17.5°	674.0	645.7	634.6	614.2	585.0	554.4	527.8	504.8	482.6	464.0	446.7
20°	689.6	652.3	634.6	621.8	583.2	552.2	522.9	493.2	472.0	452.0	432.5
22.5°	699.3	657.2	638.6	618.2	581.4	544.2	509.6	483.9	457.8	437.4	421.9
25°	696.6	654.5	633.7	614.7	569.9	532.7	501.7	468.9	444.5	422.3	401.9
27.5°	695.3	647.9	625.7	604.5	562.4	523.4	484.4	457.8	430.8	405.0	390.0
30°	691.8	639.5	613.8	590.7	546.9	506.1	472.9	441.8	414.8	391.3	371.4
32.5°	679.8	625.3	600.5	575.7	530.0	489.2	455.6	426.8	399.7	375.4	356.3
35°	663.9	608.5	581.4	555.3	509.6	468.4	437.4	407.3	382.0	358.5	340.3
37.5°	647.9	589.0	563.7	533.6	491.5	448.5	416.6	389.5	366.0	341.7	321.7
40°	624.9	565.9	538.0	512.3	463.1	422.8	393.5	369.2	346.1	323.1	306.2
42.5°	593.4	540.7	511.8	483.5	437.4	397.5	369.2	347.4	325.7	306.7	288.1
45°	561.5	510.1	484.4	459.1	409.0	371.4	345.2	325.3	307.1	286.3	271.2
47.5°	522.9	479.5	453.8	429.0	381.6	343.9	320.0	301.3	284.5	267.2	253.0
50°	483.5	445.8	422.3	396.6	351.4	317.3	293.8	278.3	264.6	248.2	236.6
52.5°	440.9	408.1	388.2	363.4	323.5	292.0	268.1	252.6	241.1	229.1	218.9
55°	395.7	371.8	350.5	330.6	292.9	264.6	243.3	229.6	221.6	210.5	201.6
57.5°	355.0	331.9	319.1	296.5	263.7	235.8	218.9	207.4	198.1	191.4	184.4
60°	312.4	293.8	279.6	263.2	234.4	210.9	193.2	186.6	176.8	171.9	168.8
62.5°	271.7	258.4	245.1	232.7	207.0	184.8	171.5	163.1	157.3	152.4	149.8
65°	233.1	220.7	211.4	200.3	179.0	161.3	148.9	142.3	136.5	135.2	132.1
67.5°	195.4	190.1	179.9	171.1	152.9	139.2	129.8	121.4	118.3	117.0	114.3
70°	163.5	157.3	149.3	141.8	128.1	116.1	107.7	104.6	100.2	99.7	96.6
72.5°	134.7	127.2	121.4	115.7	105.5	94.8	90.4	86.0	83.8	82.0	80.7
75°	106.8	101.5	97.5	92.6	83.8	76.7	70.5	68.7	67.4	66.9	66.0
77.5°	79.8	76.2	74.5	69.6	63.4	57.2	54.5	51.8	51.8	51.0	51.4
80°	56.7	54.5	52.3	49.6	44.3	41.7	39.4	37.7	36.8	36.3	36.8
82.5°	35.9	34.6	34.1	32.4	28.8	27.5	25.7	24.4	24.4	24.4	24.4
85°	19.9	19.9	19.9	17.3	16.0	14.6	13.7	13.3	13.3	13.3	13.7
87.5°	8.4	8.4	7.1	7.1	6.6	5.8	5.3	5.3	5.8	5.8	6.2
90°	7.4	6.6	6.2	5.7	4.6	3.5	2.4	1.3	2.4	3.5	4.6
92.5°	17.9	17.4	17.2	16.6	15.3	14.0	12.8	11.5	12.8	14.0	15.3
95°	31.4	30.7	30.4	30.0	29.1	28.2	27.3	26.4	27.3	28.2	29.1
97.5°	47.0	46.2	45.8	45.4	44.6	43.9	43.1	42.3	43.1	43.9	44.6
100°	64.7	63.8	63.4	63.2	62.8	62.5	62.1	61.7	62.1	62.5	62.8
102.5°	83.6	82.8	82.4	82.4	82.3	82.2	82.1	82.0	82.1	82.2	82.3
105°	103.7	103.3	103.1	103.1	103.0	102.9	102.8	102.7	102.8	102.9	103.0
107.5°	124.8	124.7	124.7	124.7	124.6	124.5	124.4	124.3	124.4	124.5	124.6
110°	147.0	147.1	147.2	147.1	146.9	146.7	146.5	146.3	146.5	146.7	146.9

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	168.9	169.1	169.2	169.2	169.2	169.2	169.2	169.2	169.2	169.2	169.2
115°	191.8	192.0	192.1	192.1	192.1	192.1	192.1	192.1	192.1	192.1	192.1
117.5°	213.6	213.7	213.7	213.7	213.7	213.7	213.7	213.7	213.7	213.7	213.7
120°	236.6	236.9	237.1	236.9	236.5	236.1	235.7	235.3	235.7	236.1	236.5
122.5°	258.1	258.2	258.2	258.2	258.1	258.0	257.9	257.8	257.9	258.0	258.1
125°	279.7	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8
127.5°	300.6	300.8	300.9	300.8	300.5	300.2	299.9	299.6	299.9	300.2	300.5
130°	322.1	322.1	322.1	322.0	321.7	321.4	321.1	320.8	321.1	321.4	321.7
132.5°	343.1	343.2	343.2	343.1	342.9	342.8	342.6	342.4	342.6	342.8	342.9
135°	363.5	363.5	363.5	363.2	362.6	362.1	361.5	360.9	361.5	362.1	362.6
137.5°	383.2	383.0	382.9	382.8	382.5	382.2	381.9	381.6	381.9	382.2	382.5
140°	403.2	403.2	403.2	403.1	402.9	402.7	402.5	402.3	402.5	402.7	402.9
142.5°	422.0	422.1	422.1	422.0	421.8	421.6	421.4	421.2	421.4	421.6	421.8
145°	440.3	440.2	440.2	440.0	439.6	439.2	438.8	438.4	438.8	439.2	439.6
147.5°	458.1	458.2	458.2	458.0	457.5	457.0	456.5	456.0	456.5	457.0	457.5
150°	473.7	473.7	473.7	473.5	473.1	472.7	472.3	471.9	472.3	472.7	473.1
152.5°	487.9	487.8	487.8	487.7	487.5	487.3	487.1	486.9	487.1	487.3	487.5
155°	502.2	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
157.5°	514.6	514.6	514.6	514.7	514.9	515.1	515.3	515.5	515.3	515.1	514.9
160°	526.4	526.5	526.5	526.6	526.7	526.8	526.9	527.0	526.9	526.8	526.7
162.5°	536.1	536.2	536.2	536.4	536.7	537.0	537.3	537.6	537.3	537.0	536.7
165°	545.2	545.4	545.5	545.6	545.9	546.2	546.5	546.8	546.5	546.2	545.9
167.5°	552.5	552.5	552.5	552.7	553.1	553.5	553.9	554.3	553.9	553.5	553.1
170°	558.4	558.3	558.3	558.5	559.0	559.5	560.0	560.5	560.0	559.5	559.0
172.5°	563.1	563.1	563.1	563.3	563.7	564.1	564.5	564.9	564.5	564.1	563.7
175°	566.5	566.6	566.6	566.8	567.3	567.8	568.3	568.8	568.3	567.8	567.3
177.5°	568.4	568.4	568.4	568.6	569.1	569.6	570.1	570.6	570.1	569.6	569.1
180°	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	526.9	525.1	526.0	521.6	517.6	511.8	507.0	506.1	505.2	507.9	506.1
5°	511.8	509.6	507.4	502.1	494.1	489.2	482.2	481.7	479.1	475.1	476.0
7.5°	495.5	494.1	491.0	482.6	475.5	467.1	461.3	456.5	454.2	450.7	449.4
10°	482.2	477.3	474.6	465.3	456.9	448.0	440.5	437.0	433.0	429.9	427.6
12.5°	464.0	462.7	455.1	447.6	440.5	430.3	424.5	414.4	409.0	411.7	410.8
15°	452.0	445.8	444.0	433.4	421.4	414.8	404.2	397.5	395.3	391.3	386.4
17.5°	436.1	432.1	425.9	416.1	402.4	393.1	385.5	379.3	376.7	371.4	367.4
20°	421.0	414.4	409.5	400.6	387.3	375.4	366.0	362.1	355.4	351.0	348.8
22.5°	407.3	402.4	395.3	382.0	370.5	359.0	347.9	342.1	335.9	333.3	329.7
25°	390.4	382.4	377.6	362.9	350.5	341.2	331.0	323.5	320.0	315.5	314.6
27.5°	374.0	366.5	360.7	347.9	332.8	320.8	314.6	309.3	303.1	303.1	300.9
30°	357.6	352.3	343.4	331.0	316.9	305.3	298.2	293.4	291.2	289.4	288.9
32.5°	341.2	334.1	328.8	312.0	301.3	290.7	285.4	281.4	278.7	278.3	278.7
35°	324.4	316.4	311.1	296.0	285.4	275.6	273.4	269.9	268.6	268.1	270.3
37.5°	306.7	300.5	293.8	281.4	269.4	263.7	259.2	257.9	257.5	260.1	261.0
40°	290.3	285.0	278.7	265.5	256.6	250.4	248.2	246.8	248.6	251.3	252.6
42.5°	274.8	267.2	262.4	250.4	242.4	238.9	236.2	236.2	238.0	241.1	243.3
45°	258.4	252.6	247.7	237.1	230.0	226.0	225.6	226.0	228.2	230.4	233.1
47.5°	242.4	236.6	231.3	222.5	216.3	214.0	213.6	214.0	217.6	220.7	223.8
50°	227.8	221.6	216.7	208.3	203.4	200.8	201.2	203.4	206.1	210.5	214.5
52.5°	210.5	206.1	201.6	194.1	189.7	187.9	189.2	191.0	195.9	199.0	203.9
55°	193.7	189.7	186.1	180.4	176.8	175.5	176.4	179.0	183.0	188.3	194.1
57.5°	178.2	173.7	170.2	166.2	162.2	162.6	163.1	166.6	171.5	176.4	183.0
60°	160.9	158.2	155.1	150.2	148.5	148.5	149.8	153.8	158.2	166.2	171.9
62.5°	145.4	141.8	139.6	136.5	133.8	134.3	137.4	140.9	146.2	152.9	160.4
65°	129.4	125.4	123.6	121.0	120.1	120.5	122.8	128.1	133.8	139.6	146.7
67.5°	111.7	110.3	108.6	105.9	106.8	107.2	109.5	113.9	120.1	125.9	133.8
70°	96.6	93.9	93.5	91.3	91.3	92.6	97.1	100.2	105.9	112.1	120.5
72.5°	80.7	78.4	78.4	76.7	78.0	79.3	81.5	86.0	91.3	97.5	104.6
75°	64.3	63.4	64.3	63.4	63.4	65.6	68.2	71.8	77.6	84.2	90.0
77.5°	49.6	49.6	49.2	50.5	50.5	51.8	55.4	58.9	63.4	68.7	74.9
80°	36.3	36.3	36.3	37.7	39.0	39.0	41.2	45.6	49.6	53.2	58.9
82.5°	24.8	24.8	24.8	25.7	27.5	27.5	30.1	32.8	37.2	40.3	43.0
85°	15.1	15.1	14.6	15.5	16.0	17.3	19.5	21.3	23.5	26.1	28.8
87.5°	6.6	6.6	7.1	7.5	8.0	8.9	9.7	10.6	12.9	13.7	15.1
90°	5.7	6.2	6.6	7.4	8.1	8.9	9.7	10.3	10.9	11.4	12.0
92.5°	16.6	17.2	17.4	17.9	18.4	18.9	19.4	19.7	20.0	20.3	20.6
95°	30.0	30.4	30.7	31.4	32.1	32.8	33.5	33.8	34.1	34.4	34.7
97.5°	45.4	45.8	46.2	47.0	47.7	48.5	49.3	49.7	50.1	50.5	50.9
100°	63.2	63.4	63.8	64.7	65.6	66.5	67.4	67.6	67.8	68.0	68.2
102.5°	82.4	82.4	82.8	83.6	84.3	85.1	85.9	86.2	86.5	86.8	87.1
105°	103.1	103.1	103.3	103.7	104.1	104.5	104.9	105.2	105.5	105.8	106.1
107.5°	124.7	124.7	124.7	124.8	124.9	125.0	125.1	125.5	125.9	126.3	126.7
110°	147.1	147.2	147.1	147.0	146.9	146.8	146.7	146.5	146.3	146.1	145.9

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	169.2	169.2	169.1	168.9	168.7	168.5	168.3	168.3	168.3	168.3	168.3
115°	192.1	192.1	192.0	191.8	191.6	191.4	191.2	191.1	191.0	190.9	190.8
117.5°	213.7	213.7	213.7	213.6	213.5	213.4	213.3	213.0	212.7	212.4	212.1
120°	236.9	237.1	236.9	236.6	236.3	236.0	235.7	235.2	234.7	234.2	233.7
122.5°	258.2	258.2	258.2	258.1	258.0	257.9	257.8	257.5	257.2	256.9	256.6
125°	279.8	279.8	279.8	279.7	279.6	279.5	279.4	279.2	279.0	278.8	278.6
127.5°	300.8	300.9	300.8	300.6	300.5	300.3	300.1	299.9	299.7	299.5	299.3
130°	322.0	322.1	322.1	322.1	322.1	322.1	322.1	321.9	321.7	321.5	321.3
132.5°	343.1	343.2	343.2	343.1	343.0	342.9	342.8	342.6	342.4	342.2	342.0
135°	363.2	363.5	363.5	363.5	363.5	363.5	363.5	363.3	363.1	362.9	362.7
137.5°	382.8	382.9	383.0	383.2	383.4	383.6	383.8	383.5	383.2	382.9	382.6
140°	403.1	403.2	403.2	403.2	403.2	403.2	403.2	403.1	403.0	402.9	402.8
142.5°	422.0	422.1	422.1	422.0	421.9	421.8	421.7	421.7	421.7	421.7	421.7
145°	440.0	440.2	440.2	440.3	440.4	440.5	440.6	440.5	440.4	440.3	440.2
147.5°	458.0	458.2	458.2	458.1	458.0	457.9	457.8	457.7	457.6	457.5	457.4
150°	473.5	473.7	473.7	473.7	473.7	473.7	473.7	473.7	473.7	473.7	473.7
152.5°	487.7	487.8	487.8	487.9	488.0	488.1	488.2	488.5	488.8	489.1	489.4
155°	502.3	502.3	502.3	502.2	502.1	502.0	501.9	502.3	502.7	503.0	503.4
157.5°	514.7	514.6	514.6	514.6	514.6	514.6	514.6	514.9	515.2	515.5	515.8
160°	526.6	526.5	526.5	526.4	526.3	526.2	526.1	526.4	526.7	527.0	527.3
162.5°	536.4	536.2	536.2	536.1	536.0	535.9	535.8	536.4	537.0	537.5	538.1
165°	545.6	545.5	545.4	545.2	545.0	544.8	544.6	545.2	545.8	546.4	547.0
167.5°	552.7	552.5	552.5	552.5	552.5	552.5	552.5	553.1	553.7	554.3	554.9
170°	558.5	558.3	558.3	558.4	558.5	558.6	558.7	559.3	559.9	560.5	561.1
172.5°	563.3	563.1	563.1	563.1	563.1	563.1	563.1	563.8	564.5	565.2	565.9
175°	566.8	566.6	566.6	566.5	566.4	566.3	566.2	566.9	567.6	568.3	569.0
177.5°	568.6	568.4	568.4	568.4	568.4	568.4	568.4	569.1	569.8	570.5	571.2
180°	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	504.8	504.3	502.1	503.0	500.3	501.2	502.5	503.0	504.8	503.4	503.0
5°	473.7	472.9	471.5	470.2	469.7	471.5	468.4	469.3	470.2	471.5	473.3
7.5°	448.5	448.0	446.7	444.5	443.6	442.7	443.2	446.3	445.8	445.4	448.5
10°	425.4	425.9	423.2	422.8	420.1	419.7	420.1	421.0	422.3	424.1	424.5
12.5°	401.5	407.3	402.4	400.6	396.6	398.8	399.7	395.7	398.0	399.3	405.9
15°	386.4	383.8	380.7	380.7	378.9	378.0	375.8	378.9	380.7	383.3	382.4
17.5°	365.6	361.2	359.4	357.6	358.1	359.8	355.0	362.1	362.1	363.4	361.2
20°	347.4	343.9	341.7	340.8	339.5	338.6	338.1	339.9	342.6	343.4	345.7
22.5°	328.4	328.4	324.8	323.5	322.6	321.3	323.5	322.2	323.9	325.7	329.3
25°	312.4	312.4	311.1	309.3	308.0	307.1	308.4	308.0	309.3	311.5	312.4
27.5°	299.6	298.2	297.8	297.4	296.9	297.4	296.9	298.2	299.6	300.0	299.1
30°	288.5	287.2	287.6	287.6	288.1	287.6	287.2	288.5	288.9	288.1	288.5
32.5°	278.3	278.3	279.2	279.6	279.6	280.1	280.5	279.6	280.1	278.7	279.2
35°	269.9	270.8	271.7	272.1	272.5	272.1	273.0	272.5	271.7	270.8	270.3
37.5°	261.5	262.4	264.1	264.6	265.9	266.3	265.5	265.5	265.0	263.2	262.4
40°	252.6	253.5	255.7	257.0	257.9	259.2	258.4	258.4	256.6	254.8	253.5
42.5°	244.2	246.0	248.2	249.5	251.3	251.3	251.3	250.4	248.2	246.4	245.1
45°	235.8	236.2	239.3	241.5	243.3	243.3	243.3	242.0	240.6	237.1	235.3
47.5°	226.5	227.8	231.3	233.5	235.3	235.8	235.8	234.4	231.8	228.7	226.5
50°	216.3	218.5	222.5	225.6	227.8	228.7	227.3	226.5	223.4	219.8	217.1
52.5°	206.5	209.2	214.0	216.7	219.8	220.3	219.8	218.5	214.9	210.1	207.8
55°	196.8	199.0	204.3	208.7	211.4	212.3	211.4	209.2	204.7	199.9	197.6
57.5°	186.1	189.2	195.0	199.4	202.5	203.0	202.1	199.9	196.3	190.1	187.0
60°	175.0	179.0	184.8	189.2	193.2	193.7	192.8	189.7	185.2	179.0	176.4
62.5°	164.0	167.1	173.7	178.6	181.7	183.9	182.1	179.0	174.6	168.4	164.4
65°	151.1	155.5	161.3	165.7	169.3	169.7	168.8	166.2	161.3	154.7	151.6
67.5°	138.7	141.8	147.6	153.3	154.7	156.0	154.7	152.0	148.0	142.3	137.8
70°	123.6	126.3	133.4	137.4	139.2	140.5	139.6	136.9	133.4	128.1	124.5
72.5°	108.6	110.8	117.4	120.5	124.1	123.6	123.2	121.4	116.6	113.0	110.8
75°	92.6	95.3	99.7	103.7	105.0	105.0	105.0	103.7	100.6	94.8	92.6
77.5°	78.0	79.3	82.9	85.1	86.4	86.9	86.4	84.2	82.4	78.4	77.1
80°	59.8	63.4	66.0	66.5	68.2	68.2	68.2	67.4	65.6	61.6	61.2
82.5°	45.2	46.1	48.7	50.1	51.0	50.5	50.5	48.7	48.3	46.1	45.2
85°	30.6	31.9	31.5	33.2	33.7	32.8	32.8	33.7	31.5	31.9	30.6
87.5°	16.8	16.8	17.7	17.3	19.1	19.1	18.2	18.6	17.7	17.3	16.8
90°	12.3	12.4	12.6	12.8	13.0	13.2	13.0	12.8	12.6	12.4	12.3
92.5°	20.7	20.7	20.8	20.9	21.0	21.1	21.0	20.9	20.8	20.7	20.7
95°	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8
97.5°	51.1	51.1	51.1	51.1	51.1	51.1	51.1	51.1	51.1	51.1	51.1
100°	68.3	68.3	68.3	68.3	68.3	68.3	68.3	68.3	68.3	68.3	68.3
102.5°	87.2	87.3	87.4	87.5	87.6	87.7	87.6	87.5	87.4	87.3	87.2
105°	106.2	106.3	106.6	106.9	107.2	107.5	107.2	106.9	106.6	106.3	106.2
107.5°	126.9	126.9	126.8	126.7	126.6	126.5	126.6	126.7	126.8	126.9	126.9
110°	145.8	146.0	146.3	146.6	146.9	147.2	146.9	146.6	146.3	146.0	145.8

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3	168.3
115°	190.8	190.7	190.6	190.5	190.4	190.3	190.4	190.5	190.6	190.7	190.8
117.5°	211.9	211.8	211.5	211.2	210.9	210.6	210.9	211.2	211.5	211.8	211.9
120°	233.5	233.6	233.8	234.0	234.2	234.4	234.2	234.0	233.8	233.6	233.5
122.5°	256.4	256.2	255.7	255.2	254.7	254.2	254.7	255.2	255.7	256.2	256.4
125°	278.5	278.4	278.2	278.0	277.8	277.6	277.8	278.0	278.2	278.4	278.5
127.5°	299.2	299.1	299.0	298.9	298.8	298.7	298.8	298.9	299.0	299.1	299.2
130°	321.2	321.0	320.6	320.3	319.9	319.5	319.9	320.3	320.6	321.0	321.2
132.5°	341.9	341.9	341.8	341.7	341.6	341.5	341.6	341.7	341.8	341.9	341.9
135°	362.6	362.5	362.2	361.9	361.6	361.3	361.6	361.9	362.2	362.5	362.6
137.5°	382.5	382.5	382.6	382.7	382.8	382.9	382.8	382.7	382.6	382.5	382.5
140°	402.7	402.7	402.6	402.5	402.4	402.3	402.4	402.5	402.6	402.7	402.7
142.5°	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7	421.7
145°	440.2	440.1	439.8	439.5	439.2	438.9	439.2	439.5	439.8	440.1	440.2
147.5°	457.4	457.3	457.2	457.1	457.0	456.9	457.0	457.1	457.2	457.3	457.4
150°	473.7	473.6	473.5	473.4	473.3	473.2	473.3	473.4	473.5	473.6	473.7
152.5°	489.5	489.4	489.1	488.8	488.5	488.2	488.5	488.8	489.1	489.4	489.5
155°	503.6	503.4	503.0	502.7	502.3	501.9	502.3	502.7	503.0	503.4	503.6
157.5°	516.0	515.8	515.5	515.2	514.9	514.6	514.9	515.2	515.5	515.8	516.0
160°	527.4	527.2	526.7	526.2	525.7	525.2	525.7	526.2	526.7	527.2	527.4
162.5°	538.4	538.2	537.7	537.2	536.7	536.2	536.7	537.2	537.7	538.2	538.4
165°	547.3	547.1	546.7	546.3	545.9	545.5	545.9	546.3	546.7	547.1	547.3
167.5°	555.2	554.9	554.3	553.7	553.1	552.5	553.1	553.7	554.3	554.9	555.2
170°	561.4	561.1	560.4	559.7	559.0	558.3	559.0	559.7	560.4	561.1	561.4
172.5°	566.2	565.9	565.2	564.5	563.8	563.1	563.8	564.5	565.2	565.9	566.2
175°	569.3	569.0	568.3	567.6	566.9	566.2	566.9	567.6	568.3	569.0	569.3
177.5°	571.5	571.1	570.3	569.6	568.8	568.0	568.8	569.6	570.3	571.1	571.5
180°	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	503.0	505.6	503.0	504.8	505.6	507.9	508.7	512.7	514.1	517.2	517.2
5°	472.9	474.2	474.6	476.4	478.2	482.6	485.7	491.5	498.1	499.0	503.0
7.5°	448.5	450.7	454.2	452.9	456.0	462.7	466.6	473.7	480.4	483.9	488.8
10°	426.8	429.4	430.8	432.1	437.8	443.6	449.8	454.7	463.5	468.9	472.9
12.5°	409.0	406.8	409.5	414.4	421.0	424.5	433.0	440.5	447.1	452.9	456.5
15°	386.0	387.8	390.4	398.8	400.6	409.5	412.6	421.0	433.4	438.7	443.2
17.5°	363.8	369.6	374.9	378.0	383.3	390.4	399.3	408.6	416.6	422.8	428.1
20°	346.1	351.9	355.0	357.2	362.5	372.3	380.7	392.2	402.4	407.3	414.4
22.5°	331.9	331.9	336.4	343.0	346.1	355.4	362.5	374.9	386.0	392.2	398.8
25°	314.2	316.9	320.4	326.2	330.6	338.1	348.3	359.0	370.9	376.2	384.7
27.5°	299.6	302.7	307.6	308.9	313.3	320.0	330.6	342.1	354.5	360.3	367.4
30°	288.5	290.3	292.0	294.7	298.7	304.5	313.3	323.5	338.6	343.0	351.9
32.5°	278.7	279.6	280.5	282.7	285.0	290.7	297.8	308.9	321.3	327.9	335.9
35°	269.9	269.0	269.4	270.8	273.0	275.2	282.7	292.0	303.6	311.5	317.7
37.5°	261.5	259.7	259.2	259.2	260.1	262.8	268.6	276.5	288.9	295.6	301.8
40°	252.2	250.4	249.5	249.1	248.6	250.4	254.8	262.8	272.5	278.7	285.8
42.5°	243.3	241.5	239.3	238.9	238.0	238.9	242.0	249.5	257.9	264.1	269.9
45°	234.4	231.3	228.7	226.9	227.3	226.0	228.2	234.0	243.7	247.7	253.5
47.5°	224.7	221.1	217.6	215.8	214.0	214.9	215.8	220.7	229.1	233.1	238.9
50°	215.4	210.5	206.5	204.3	203.0	202.1	203.0	207.8	214.0	217.6	222.5
52.5°	204.7	199.9	195.9	192.3	190.6	189.2	189.7	194.1	199.9	203.4	208.3
55°	195.0	188.8	183.5	179.0	177.7	177.3	176.8	179.9	184.8	188.3	192.3
57.5°	183.9	177.7	171.9	166.6	164.0	163.5	163.5	164.4	170.6	173.3	175.5
60°	172.8	166.2	160.0	155.1	151.1	149.8	149.3	151.1	154.2	156.9	160.0
62.5°	160.4	153.8	146.2	141.8	137.8	134.3	135.6	136.0	140.5	141.8	144.5
65°	148.5	140.9	134.7	127.6	123.2	121.0	120.1	121.0	124.5	125.0	126.7
67.5°	134.7	127.6	120.1	115.2	111.2	107.2	106.4	106.4	108.1	109.5	111.7
70°	121.4	114.3	105.9	100.6	96.6	93.1	91.7	91.3	92.6	93.5	95.7
72.5°	105.9	98.8	92.6	86.9	82.0	79.3	78.0	77.1	78.4	79.3	79.8
75°	89.5	83.8	77.6	71.8	68.7	66.0	64.3	62.9	63.8	63.8	63.8
77.5°	74.0	68.2	63.4	59.4	55.4	52.3	51.0	49.6	50.1	50.1	51.0
80°	57.6	53.6	49.6	46.1	42.5	39.9	39.0	37.7	36.8	36.3	36.3
82.5°	42.5	39.4	35.9	32.8	31.0	28.4	27.5	25.7	25.7	25.3	25.3
85°	28.4	26.6	23.0	20.8	19.5	18.2	17.3	16.4	15.1	15.1	14.6
87.5°	15.1	14.2	13.3	10.6	10.6	9.3	8.9	8.4	7.1	7.5	7.5
90°	12.0	11.4	10.9	10.3	9.7	8.9	8.1	7.4	6.6	6.2	5.7
92.5°	20.6	20.3	20.0	19.7	19.4	18.9	18.4	17.9	17.4	17.2	16.6
95°	34.7	34.4	34.1	33.8	33.5	32.8	32.1	31.4	30.7	30.4	30.0
97.5°	50.9	50.5	50.1	49.7	49.3	48.5	47.7	47.0	46.2	45.8	45.4
100°	68.2	68.0	67.8	67.6	67.4	66.5	65.6	64.7	63.8	63.4	63.2
102.5°	87.1	86.8	86.5	86.2	85.9	85.1	84.3	83.6	82.8	82.4	82.4
105°	106.1	105.8	105.5	105.2	104.9	104.5	104.1	103.7	103.3	103.1	103.1
107.5°	126.7	126.3	125.9	125.5	125.1	125.0	124.9	124.8	124.7	124.7	124.7
110°	145.9	146.1	146.3	146.5	146.7	146.8	146.9	147.0	147.1	147.2	147.1

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	168.3	168.3	168.3	168.3	168.3	168.5	168.7	168.9	169.1	169.2	169.2
115°	190.8	190.9	191.0	191.1	191.2	191.4	191.6	191.8	192.0	192.1	192.1
117.5°	212.1	212.4	212.7	213.0	213.3	213.4	213.5	213.6	213.7	213.7	213.7
120°	233.7	234.2	234.7	235.2	235.7	236.0	236.3	236.6	236.9	237.1	236.9
122.5°	256.6	256.9	257.2	257.5	257.8	257.9	258.0	258.1	258.2	258.2	258.2
125°	278.6	278.8	279.0	279.2	279.4	279.5	279.6	279.7	279.8	279.8	279.8
127.5°	299.3	299.5	299.7	299.9	300.1	300.3	300.5	300.6	300.8	300.9	300.8
130°	321.3	321.5	321.7	321.9	322.1	322.1	322.1	322.1	322.1	322.1	322.0
132.5°	342.0	342.2	342.4	342.6	342.8	342.9	343.0	343.1	343.2	343.2	343.1
135°	362.7	362.9	363.1	363.3	363.5	363.5	363.5	363.5	363.5	363.5	363.2
137.5°	382.6	382.9	383.2	383.5	383.8	383.6	383.4	383.2	383.0	382.9	382.8
140°	402.8	402.9	403.0	403.1	403.2	403.2	403.2	403.2	403.2	403.2	403.1
142.5°	421.7	421.7	421.7	421.7	421.7	421.8	421.9	422.0	422.1	422.1	422.0
145°	440.2	440.3	440.4	440.5	440.6	440.5	440.4	440.3	440.2	440.2	440.0
147.5°	457.4	457.5	457.6	457.7	457.8	457.9	458.0	458.1	458.2	458.2	458.0
150°	473.7	473.7	473.7	473.7	473.7	473.7	473.7	473.7	473.7	473.7	473.5
152.5°	489.4	489.1	488.8	488.5	488.2	488.1	488.0	487.9	487.8	487.8	487.7
155°	503.4	503.0	502.7	502.3	501.9	502.0	502.1	502.2	502.3	502.3	502.3
157.5°	515.8	515.5	515.2	514.9	514.6	514.6	514.6	514.6	514.6	514.6	514.7
160°	527.3	527.0	526.7	526.4	526.1	526.2	526.3	526.4	526.5	526.5	526.6
162.5°	538.1	537.5	537.0	536.4	535.8	535.9	536.0	536.1	536.2	536.2	536.4
165°	547.0	546.4	545.8	545.2	544.6	544.8	545.0	545.2	545.4	545.5	545.6
167.5°	554.9	554.3	553.7	553.1	552.5	552.5	552.5	552.5	552.5	552.5	552.7
170°	561.1	560.5	559.9	559.3	558.7	558.6	558.5	558.4	558.3	558.3	558.5
172.5°	565.9	565.2	564.5	563.8	563.1	563.1	563.1	563.1	563.1	563.1	563.3
175°	569.0	568.3	567.6	566.9	566.2	566.3	566.4	566.5	566.6	566.6	566.8
177.5°	571.2	570.5	569.8	569.1	568.4	568.4	568.4	568.4	568.4	568.4	568.6
180°	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7	569.7

TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	534.9	534.9	534.9	534.9
2.5°	520.3	524.7	528.7	534.9
5°	508.7	515.0	523.4	532.7
7.5°	495.5	505.2	516.3	529.1
10°	483.0	494.1	508.3	523.8
12.5°	470.2	483.5	499.0	515.8
15°	455.6	468.9	486.1	508.7
17.5°	442.3	458.2	476.8	500.8
20°	426.8	441.8	462.2	489.7
22.5°	413.0	430.3	452.9	476.8
25°	398.0	413.0	435.6	464.4
27.5°	382.9	401.5	423.2	451.1
30°	368.3	383.8	407.3	436.5
32.5°	352.3	370.9	392.6	420.1
35°	335.0	352.8	373.1	402.8
37.5°	319.5	336.8	357.6	383.8
40°	302.2	320.4	339.5	365.6
42.5°	285.4	301.8	320.8	344.8
45°	269.0	283.2	300.5	321.3
47.5°	252.2	264.1	280.1	298.7
50°	234.0	246.8	258.8	274.3
52.5°	217.1	228.2	238.0	250.8
55°	200.8	208.3	216.3	226.0
57.5°	183.5	189.2	195.0	205.2
60°	166.2	171.5	174.6	181.3
62.5°	149.3	151.6	155.5	159.5
65°	130.7	133.8	136.0	140.9
67.5°	113.9	115.2	117.4	120.5
70°	96.2	99.3	100.2	102.4
72.5°	81.1	82.4	83.3	83.8
75°	64.3	65.6	66.5	69.1
77.5°	50.5	50.1	51.8	52.3
80°	37.2	35.9	36.3	38.1
82.5°	24.4	24.8	24.4	24.4
85°	15.1	14.6	13.7	14.2
87.5°	6.6	6.6	6.2	6.2
90°	4.6	3.5	2.4	1.3
92.5°	15.3	14.0	12.8	11.5
95°	29.1	28.2	27.3	26.4
97.5°	44.6	43.9	43.1	42.3
100°	62.8	62.5	62.1	61.7
102.5°	82.3	82.2	82.1	82.0
105°	103.0	102.9	102.8	102.7
107.5°	124.6	124.5	124.4	124.3
110°	146.9	146.7	146.5	146.3



TEST NUMBER: P1032659

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	169.2	169.2	169.2	169.2
115°	192.1	192.1	192.1	192.1
117.5°	213.7	213.7	213.7	213.7
120°	236.5	236.1	235.7	235.3
122.5°	258.1	258.0	257.9	257.8
125°	279.8	279.8	279.8	279.8
127.5°	300.5	300.2	299.9	299.6
130°	321.7	321.4	321.1	320.8
132.5°	342.9	342.8	342.6	342.4
135°	362.6	362.1	361.5	360.9
137.5°	382.5	382.2	381.9	381.6
140°	402.9	402.7	402.5	402.3
142.5°	421.8	421.6	421.4	421.2
145°	439.6	439.2	438.8	438.4
147.5°	457.5	457.0	456.5	456.0
150°	473.1	472.7	472.3	471.9
152.5°	487.5	487.3	487.1	486.9
155°	502.3	502.3	502.3	502.3
157.5°	514.9	515.1	515.3	515.5
160°	526.7	526.8	526.9	527.0
162.5°	536.7	537.0	537.3	537.6
165°	545.9	546.2	546.5	546.8
167.5°	553.1	553.5	553.9	554.3
170°	559.0	559.5	560.0	560.5
172.5°	563.7	564.1	564.5	564.9
175°	567.3	567.8	568.3	568.8
177.5°	569.1	569.6	570.1	570.6
180°	569.7	569.7	569.7	569.7

(END OF REPORT)