

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032765

Luminaire Tested: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032765
REPORT IS A COMBINATION OF REPORTS P997950 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7748.0 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38
3	81	72	64	59	74	66	60	55	55	51	47	46	42	40	37	34	32
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16
10	47	35	28	23	43	32	26	22	28	23	19	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10434	10434	10434	10434
5°	10408	11971	10469	8995
10°	10330	13966	10410	7892
15°	10207	16100	10277	7061
20°	10074	17459	10147	6331
25°	9881	17259	9975	5792
30°	9693	14265	9811	5514
35°	9428	10631	9532	5345
40°	9119	8007	9207	5264
45°	8647	6427	8755	5151
50°	8084	5415	8202	5098
55°	7422	4713	7539	5039
60°	6778	4150	6977	4955
65°	6173	3571	6232	4748
70°	5464	2938	5582	4373
75°	4766	2258	4735	3716
80°	3751	1484	3706	2821
85°	2467	667	2314	1645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 13492 cd/sqm

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	1.6
10°-20°	384.4	5.0
20°-30°	610.7	7.9
30°-40°	678.5	8.8
40°-50°	617.1	8.0
50°-60°	504.3	6.5
60°-70°	359.9	4.6
70°-80°	198.1	2.6
80°-90°	56.3	0.7
90°-100°	45.2	0.6
100°-110°	297.7	3.8
110°-120°	568.5	7.3
120°-130°	721.7	9.3
130°-140°	772.1	10.0
140°-150°	721.9	9.3
150°-160°	582.2	7.5
160°-170°	375.5	4.8
170°-180°	129.4	1.7
0°-30°	1119.6	14.5
0°-40°	1798.1	23.2
0°-60°	2919.5	37.7
0°-90°	3533.8	45.6
90°-120°	911.4	11.8
90°-150°	3127.1	40.4
90°-180°	4214.0	54.4
0°-180°	7748.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1280	1280	1280	1280	1280	
5°	1274	1501	1282	1128	1274	121
15°	1217	2062	1226	904	1217	343
25°	1111	2189	1122	735	1111	512
35°	964	1294	974	651	964	602
45°	769	726	778	582	769	593
55°	541	475	549	508	541	486
65°	337	305	340	406	337	333
75°	165	153	164	251	165	174
85°	34	32	32	78	34	39
90°	3	31	3	31	3	5
95°	56	30	56	30	56	69
105°	307	290	307	290	307	321
115°	572	576	572	576	572	563
125°	805	811	805	811	805	719
135°	998	1005	998	1005	998	769
145°	1151	1157	1151	1157	1151	719
155°	1262	1261	1262	1261	1262	582
165°	1331	1325	1331	1325	1331	376
175°	1362	1354	1362	1354	1362	130
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
2.5°	1279.6	1292.3	1297.6	1301.9	1315.7	1319.9	1321.0	1327.3	1332.6	1333.7	1333.7
5°	1274.3	1294.5	1310.4	1325.2	1347.5	1357.0	1368.7	1381.4	1398.4	1409.0	1414.3
7.5°	1265.8	1295.5	1319.9	1345.3	1376.1	1395.2	1405.8	1439.7	1463.0	1482.1	1505.4
10°	1253.1	1291.3	1326.3	1363.4	1406.8	1430.2	1453.5	1494.8	1527.7	1564.8	1594.5
12.5°	1234.0	1283.9	1326.3	1378.2	1432.3	1459.8	1487.4	1559.5	1597.7	1630.5	1683.5
15°	1217.1	1266.9	1327.3	1380.3	1447.1	1488.5	1528.8	1575.4	1635.8	1706.9	1757.7
17.5°	1198.0	1260.5	1316.7	1390.9	1465.1	1504.4	1537.2	1609.3	1694.1	1764.1	1810.8
20°	1171.5	1235.1	1309.3	1387.7	1475.7	1506.5	1550.0	1646.4	1722.8	1791.7	1868.0
22.5°	1140.7	1214.9	1293.4	1368.7	1459.8	1524.5	1572.2	1657.0	1749.3	1828.8	1914.6
25°	1111.0	1191.6	1260.5	1363.4	1459.8	1503.3	1557.4	1658.1	1758.8	1855.3	1943.3
27.5°	1079.2	1154.5	1247.8	1329.4	1438.6	1486.3	1544.7	1654.9	1762.0	1858.5	1952.8
30°	1044.3	1124.8	1202.2	1298.7	1404.7	1466.2	1520.3	1640.1	1749.3	1850.0	1938.0
32.5°	1005.0	1081.4	1164.1	1255.2	1366.5	1429.1	1496.9	1619.9	1736.5	1823.5	1891.3
35°	963.7	1041.1	1113.2	1206.5	1321.0	1383.5	1449.2	1584.9	1700.5	1771.5	1810.8
37.5°	918.1	991.2	1062.3	1154.5	1269.0	1335.8	1402.6	1534.1	1643.2	1702.6	1692.0
40°	874.6	940.4	1006.1	1093.0	1212.8	1283.9	1342.2	1474.7	1570.1	1595.5	1560.6
42.5°	824.8	881.0	944.6	1033.7	1150.3	1217.1	1290.2	1411.1	1482.1	1471.5	1412.1
45°	768.6	818.4	882.1	965.8	1084.5	1153.5	1214.9	1329.4	1381.4	1354.9	1246.7
47.5°	714.5	763.3	815.3	899.0	1014.6	1072.9	1135.4	1238.3	1268.0	1211.8	1103.6
50°	656.2	696.5	750.6	830.1	938.2	999.7	1051.7	1134.4	1145.0	1076.1	963.7
52.5°	600.1	634.0	685.9	764.4	865.1	913.9	964.7	1037.9	1029.4	958.4	850.2
55°	540.7	572.5	620.2	692.3	781.3	828.0	871.5	936.1	918.1	844.9	750.6
57.5°	490.9	513.1	559.8	626.6	699.7	750.6	787.7	838.6	811.0	737.9	649.9
60°	433.6	461.2	500.4	554.5	626.6	660.5	693.3	727.3	708.2	638.2	559.8
62.5°	381.7	402.9	436.8	488.7	544.9	575.7	610.7	631.9	612.8	548.1	482.4
65°	337.1	354.1	380.6	423.0	477.1	502.5	522.7	542.8	526.9	466.5	418.8
67.5°	288.4	303.2	325.5	359.4	405.0	423.0	442.1	455.9	437.8	397.6	350.9
70°	244.9	255.5	276.7	302.1	334.0	350.9	366.8	380.6	364.7	330.8	295.8
72.5°	200.4	208.9	227.9	246.0	274.6	286.2	297.9	308.5	303.2	271.4	242.8
75°	165.4	168.6	181.3	196.1	214.2	226.9	235.4	241.7	237.5	212.0	194.0
77.5°	125.1	129.3	138.9	150.5	166.4	173.9	179.2	185.5	180.2	160.1	147.4
80°	91.2	92.2	97.5	108.1	118.7	119.8	125.1	133.6	130.4	116.6	107.1
82.5°	58.3	61.5	63.6	70.0	77.4	79.5	82.7	84.8	83.8	75.3	72.1
85°	33.9	33.9	36.0	40.3	42.4	45.6	46.6	47.7	49.8	44.5	41.3
87.5°	14.8	15.9	15.9	17.0	19.1	19.1	20.1	21.2	22.3	21.2	18.0
90°	3.1	5.6	8.1	10.6	13.1	14.3	15.2	17.0	18.8	20.6	22.4
92.5°	15.3	14.8	14.4	13.9	13.4	13.2	14.1	15.9	17.8	19.6	21.4
95°	56.0	48.3	40.6	32.9	25.2	21.4	21.5	21.7	22.0	22.2	22.4
97.5°	107.0	112.0	117.0	121.9	126.9	129.4	117.5	93.7	70.0	46.2	22.4
100°	167.1	171.2	175.2	179.3	183.4	185.4	169.8	138.5	107.3	76.0	44.8
102.5°	234.3	237.0	239.7	242.4	245.1	246.5	247.9	250.6	253.3	256.0	258.7
105°	306.6	308.0	309.3	310.7	312.0	312.7	313.3	314.4	315.5	316.7	317.8
107.5°	372.8	373.5	374.2	374.9	375.6	375.9	376.7	378.3	379.8	381.4	383.0
110°	440.0	440.7	441.4	442.1	442.8	443.1	443.8	445.1	446.5	447.8	449.2



TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	505.2	506.6	507.9	509.3	510.6	511.3	511.5	512.0	512.5	512.9	513.4
115°	572.5	573.2	573.8	574.5	575.2	575.5	575.4	575.2	574.9	574.7	574.5
117.5°	632.6	633.5	634.4	635.3	636.2	636.6	636.9	637.6	638.3	639.0	639.7
120°	693.7	694.6	695.5	696.4	697.3	697.8	697.7	697.4	697.2	696.9	696.7
122.5°	750.7	751.2	751.6	752.1	752.6	752.8	753.0	753.5	753.9	754.4	754.8
125°	804.7	805.6	806.5	807.4	808.3	808.8	808.6	808.1	807.6	807.2	806.7
127.5°	856.7	856.9	857.1	857.4	857.6	857.7	858.3	859.4	860.5	861.7	862.8
130°	906.6	906.8	907.0	907.3	907.5	907.6	907.9	908.6	909.3	909.9	910.6
132.5°	952.4	952.8	953.3	953.7	954.2	954.4	954.9	955.8	956.7	957.6	958.5
135°	998.2	998.0	997.8	997.5	997.3	997.2	997.7	998.6	999.5	1000.4	1001.3
137.5°	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0	1039.6	1040.7	1041.8	1043.0	1044.1
140°	1078.7	1079.2	1079.6	1080.1	1080.6	1080.8	1081.0	1081.5	1081.9	1082.4	1082.8
142.5°	1114.4	1115.3	1116.2	1117.1	1118.0	1118.4	1118.5	1118.8	1119.0	1119.3	1119.5
145°	1151.0	1151.7	1152.4	1153.1	1153.8	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1
147.5°	1179.6	1181.0	1182.3	1183.7	1185.0	1185.7	1185.6	1185.4	1185.1	1184.9	1184.7
150°	1211.1	1212.0	1212.9	1213.8	1214.7	1215.2	1215.1	1214.9	1214.6	1214.4	1214.2
152.5°	1237.6	1238.3	1239.0	1239.7	1240.4	1240.7	1240.5	1240.0	1239.5	1239.1	1238.6
155°	1262.1	1262.3	1262.5	1262.8	1263.0	1263.1	1262.8	1262.1	1261.4	1260.7	1260.0
157.5°	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5	1283.0	1282.1	1281.2	1280.3	1279.4
160°	1301.8	1301.1	1300.4	1299.7	1299.0	1298.7	1298.6	1298.4	1298.1	1297.9	1297.7
162.5°	1318.1	1317.2	1316.3	1315.4	1314.5	1314.0	1313.9	1313.7	1313.4	1313.2	1313.0
165°	1331.3	1330.2	1329.0	1327.9	1326.8	1326.2	1326.2	1326.2	1326.2	1326.2	1326.2
167.5°	1342.5	1341.4	1340.2	1339.1	1338.0	1337.4	1337.3	1337.1	1336.8	1336.6	1336.4
170°	1351.7	1350.3	1349.0	1347.6	1346.3	1345.6	1345.7	1345.9	1346.2	1346.4	1346.6
172.5°	1357.8	1356.4	1355.1	1353.7	1352.4	1351.7	1351.8	1352.0	1352.3	1352.5	1352.7
175°	1361.9	1360.5	1359.2	1357.8	1356.5	1355.8	1355.9	1356.1	1356.4	1356.6	1356.8
177.5°	1365.0	1363.4	1361.8	1360.2	1358.6	1357.8	1358.0	1358.5	1359.0	1359.4	1359.9
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
2.5°	1336.9	1355.9	1364.4	1366.5	1378.2	1370.8	1374.0	1372.9	1381.4	1382.4	1382.4
5°	1434.4	1456.7	1464.1	1474.7	1490.6	1494.8	1491.6	1498.0	1509.7	1501.2	1513.9
7.5°	1537.2	1561.6	1578.6	1601.9	1607.2	1621.0	1629.5	1636.9	1639.0	1640.1	1642.2
10°	1632.6	1663.4	1686.7	1725.9	1734.4	1741.8	1778.9	1764.1	1783.2	1776.8	1778.9
12.5°	1710.0	1770.5	1789.6	1855.3	1861.6	1887.1	1885.0	1908.3	1912.5	1921.0	1912.5
15°	1811.8	1881.8	1912.5	1949.6	1970.8	2000.5	2005.8	2037.6	2050.3	2062.0	2050.3
17.5°	1905.1	1942.2	2020.7	2050.3	2064.1	2080.0	2120.3	2132.0	2151.1	2143.6	2164.8
20°	1951.8	2004.8	2087.5	2138.3	2159.5	2174.4	2208.3	2226.3	2233.8	2233.8	2235.9
22.5°	1993.1	2069.4	2130.9	2189.2	2208.3	2218.9	2239.1	2252.8	2256.0	2258.1	2260.3
25°	2030.2	2099.1	2148.9	2181.8	2189.2	2189.2	2200.9	2192.4	2178.6	2189.2	2195.6
27.5°	2030.2	2079.0	2101.2	2112.9	2112.9	2084.3	2067.3	2032.3	2002.6	1994.2	2013.2
30°	1996.3	2018.5	1987.8	1959.2	1936.9	1917.8	1851.0	1798.0	1787.4	1780.0	1808.6
32.5°	1917.8	1889.2	1828.8	1746.1	1713.2	1669.8	1617.8	1577.5	1553.1	1544.7	1538.3
35°	1778.9	1704.7	1626.3	1515.0	1491.6	1436.5	1365.5	1335.8	1295.5	1294.5	1308.2
37.5°	1627.3	1512.8	1428.0	1322.0	1289.2	1230.8	1164.1	1133.3	1105.7	1084.5	1110.0
40°	1450.3	1350.6	1221.3	1134.4	1087.7	1057.0	1000.8	966.9	954.1	943.5	959.4
42.5°	1284.9	1175.7	1075.0	985.9	947.8	912.8	875.7	842.8	833.3	832.2	843.9
45°	1120.6	1013.5	920.2	843.9	819.5	798.3	762.3	752.7	736.8	726.2	731.5
47.5°	989.1	878.9	801.5	743.2	722.0	703.9	680.6	664.7	650.9	646.7	653.1
50°	859.8	785.6	706.1	657.3	641.4	624.4	606.4	591.6	585.2	581.0	585.2
52.5°	755.9	676.4	622.3	583.1	567.2	554.5	541.7	535.4	526.9	529.0	533.3
55°	662.6	592.6	547.0	518.4	508.9	503.6	487.7	480.3	477.1	475.0	477.1
57.5°	574.6	523.7	489.8	465.4	452.7	449.5	436.8	436.8	433.6	430.4	431.5
60°	504.6	461.2	428.3	409.2	407.1	401.8	393.3	392.3	384.8	388.0	389.1
62.5°	433.6	398.6	376.4	364.7	357.3	355.2	349.9	348.8	345.6	346.7	344.6
65°	377.4	348.8	326.5	317.0	313.8	312.7	308.5	305.3	303.2	305.3	303.2
67.5°	321.2	302.1	285.2	275.6	271.4	270.3	267.2	265.0	266.1	262.9	265.0
70°	268.2	249.1	238.5	233.2	231.1	227.9	227.9	227.9	227.9	225.8	224.8
72.5°	225.8	206.7	199.3	196.1	194.0	192.9	189.8	190.8	189.8	188.7	192.9
75°	179.2	167.5	160.1	156.9	159.0	155.8	152.7	154.8	151.6	152.7	156.9
77.5°	135.7	130.4	126.2	124.0	121.9	119.8	119.8	117.7	117.7	117.7	117.7
80°	98.6	97.5	90.1	89.1	89.1	86.9	86.9	86.9	86.9	85.9	86.9
82.5°	65.7	64.7	62.5	61.5	59.4	60.4	60.4	58.3	58.3	57.2	58.3
85°	38.2	38.2	36.0	35.0	33.9	35.0	32.9	31.8	32.9	31.8	32.9
87.5°	18.0	15.9	17.0	15.9	13.8	14.8	12.7	13.8	12.7	11.7	13.8
90°	23.8	25.1	26.5	27.8	28.5	28.7	29.2	29.7	30.1	30.6	30.1
92.5°	22.8	24.1	25.5	26.8	27.5	27.5	27.5	27.5	27.5	27.5	27.5
95°	23.8	25.1	26.5	27.8	28.5	28.6	28.8	29.1	29.3	29.5	29.3
97.5°	23.5	24.7	25.8	26.9	27.5	27.6	27.8	28.1	28.3	28.5	28.3
100°	41.0	37.1	33.3	29.4	27.5	27.6	27.8	28.1	28.3	28.5	28.3
102.5°	207.8	156.8	105.9	55.0	29.5	29.5	29.5	29.5	29.5	29.5	29.5
105°	319.8	321.9	323.9	326.0	327.0	322.9	314.8	306.6	298.5	290.3	298.5
107.5°	384.1	385.3	386.4	387.5	388.1	388.6	389.5	390.4	391.3	392.2	391.3
110°	449.6	450.1	450.5	451.0	451.2	451.5	452.2	452.9	453.6	454.3	453.6

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	513.2	513.0	512.7	512.5	512.4	512.8	513.7	514.6	515.5	516.4	515.5
115°	574.9	575.4	575.8	576.3	576.5	576.5	576.5	576.5	576.5	576.5	576.5
117.5°	639.5	639.3	639.0	638.8	638.7	638.7	638.7	638.7	638.7	638.7	638.7
120°	697.2	697.6	698.1	698.6	698.8	698.6	698.1	697.6	697.2	696.7	697.2
122.5°	755.0	755.2	755.5	755.7	755.8	755.6	755.1	754.7	754.2	753.8	754.2
125°	807.4	808.1	808.8	809.5	809.8	809.9	810.1	810.4	810.6	810.8	810.6
127.5°	862.6	862.4	862.1	861.9	861.8	861.7	861.4	861.2	860.9	860.7	860.9
130°	910.8	911.1	911.3	911.6	911.7	911.7	911.7	911.7	911.7	911.7	911.7
132.5°	958.7	958.9	959.2	959.4	959.5	959.4	959.2	958.9	958.7	958.5	958.7
135°	1001.7	1002.2	1002.6	1003.1	1003.3	1003.5	1004.0	1004.5	1004.9	1005.4	1004.9
137.5°	1044.5	1045.0	1045.4	1045.9	1046.1	1046.0	1045.8	1045.5	1045.3	1045.1	1045.3
140°	1083.5	1084.2	1084.9	1085.6	1085.9	1086.0	1086.2	1086.5	1086.7	1086.9	1086.7
142.5°	1119.9	1120.4	1120.8	1121.3	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5
145°	1154.3	1154.5	1154.8	1155.0	1155.1	1155.3	1155.8	1156.3	1156.7	1157.2	1156.7
147.5°	1184.9	1185.1	1185.4	1185.6	1185.7	1185.8	1186.0	1186.3	1186.5	1186.7	1186.5
150°	1214.2	1214.2	1214.2	1214.2	1214.2	1214.3	1214.5	1214.8	1215.0	1215.2	1215.0
152.5°	1239.1	1239.5	1240.0	1240.5	1240.7	1240.6	1240.4	1240.1	1239.9	1239.7	1239.9
155°	1260.9	1261.8	1262.7	1263.6	1264.1	1263.8	1263.1	1262.4	1261.8	1261.1	1261.8
157.5°	1280.5	1281.7	1282.8	1283.9	1284.5	1283.9	1282.8	1281.7	1280.5	1279.4	1280.5
160°	1299.1	1300.4	1301.8	1303.1	1303.8	1303.1	1301.8	1300.4	1299.1	1297.7	1299.1
162.5°	1314.4	1315.7	1317.1	1318.4	1319.1	1318.3	1316.7	1315.2	1313.6	1312.0	1313.6
165°	1328.0	1329.8	1331.7	1333.5	1334.4	1333.4	1331.3	1329.3	1327.2	1325.2	1327.2
167.5°	1338.4	1340.5	1342.5	1344.6	1345.6	1344.5	1342.2	1339.9	1337.7	1335.4	1337.7
170°	1348.4	1350.2	1352.1	1353.9	1354.8	1353.7	1351.4	1349.1	1346.9	1344.6	1346.9
172.5°	1354.5	1356.3	1358.2	1360.0	1360.9	1359.7	1357.2	1354.7	1352.2	1349.7	1352.2
175°	1358.8	1360.9	1362.9	1365.0	1366.0	1364.6	1361.9	1359.2	1356.4	1353.7	1356.4
177.5°	1361.7	1363.5	1365.3	1367.1	1368.0	1366.6	1363.9	1361.2	1358.5	1355.8	1358.5
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
2.5°	1380.3	1377.1	1372.9	1372.9	1367.6	1367.6	1359.1	1344.3	1331.6	1327.3	1329.4
5°	1498.0	1499.1	1492.7	1487.4	1477.9	1470.4	1456.7	1430.2	1421.7	1404.7	1393.1
7.5°	1632.6	1628.4	1616.7	1608.3	1606.1	1589.2	1559.5	1527.7	1502.2	1485.3	1460.9
10°	1784.2	1767.3	1750.3	1745.0	1732.3	1703.7	1669.8	1634.8	1599.8	1562.7	1521.3
12.5°	1911.5	1878.6	1877.5	1864.8	1840.4	1824.5	1784.2	1734.4	1674.0	1632.6	1586.0
15°	2048.2	2017.5	1992.0	1968.7	1957.1	1910.4	1876.5	1813.9	1741.8	1697.3	1665.5
17.5°	2145.8	2132.0	2088.5	2077.9	2062.0	2007.9	1953.9	1892.4	1829.8	1767.3	1681.4
20°	2224.2	2215.7	2187.1	2172.3	2146.8	2104.4	2038.7	1967.7	1895.6	1806.5	1725.9
22.5°	2258.1	2247.5	2224.2	2211.5	2195.6	2159.5	2103.4	2022.8	1928.4	1848.9	1763.0
25°	2191.4	2210.4	2204.1	2198.8	2192.4	2171.2	2128.8	2057.8	1965.5	1875.4	1768.3
27.5°	2040.8	2073.7	2105.5	2109.7	2120.3	2128.8	2111.8	2061.0	1983.6	1888.1	1770.5
30°	1838.3	1853.2	1917.8	1936.9	1951.8	2005.8	2037.6	2024.9	1965.5	1879.7	1771.5
32.5°	1578.6	1617.8	1683.5	1729.1	1769.4	1829.8	1912.5	1945.4	1924.2	1854.2	1747.1
35°	1332.6	1379.3	1455.6	1513.9	1554.2	1640.1	1737.6	1808.6	1835.1	1800.2	1704.7
37.5°	1131.2	1187.4	1255.2	1277.5	1324.1	1430.2	1564.8	1663.4	1728.1	1731.2	1657.0
40°	979.6	1008.2	1062.3	1096.2	1141.8	1230.8	1362.3	1492.7	1590.2	1623.1	1583.9
42.5°	851.3	873.6	913.9	955.2	996.6	1064.4	1185.3	1307.2	1438.6	1504.4	1503.3
45°	749.5	772.9	800.4	834.3	863.0	936.1	1031.5	1156.6	1270.1	1371.8	1397.3
47.5°	660.5	680.6	714.5	729.4	748.5	817.4	900.1	1016.7	1134.4	1251.0	1280.7
50°	594.7	611.7	635.0	644.6	665.8	716.7	784.5	878.9	1009.3	1116.3	1171.5
52.5°	535.4	548.1	566.1	573.5	588.4	626.6	688.0	762.3	870.4	980.6	1058.0
55°	484.5	493.0	505.7	514.2	524.8	558.7	604.3	671.1	764.4	859.8	935.1
57.5°	436.8	443.1	455.9	460.1	468.6	495.1	526.9	583.1	669.0	753.8	826.9
60°	392.3	396.5	403.9	413.5	419.8	437.8	467.5	514.2	583.1	660.5	719.8
62.5°	349.9	356.2	358.3	362.6	367.9	384.8	408.2	442.1	502.5	566.1	628.7
65°	306.4	311.7	315.9	317.0	322.3	335.0	356.2	385.9	425.1	480.3	538.6
67.5°	266.1	269.3	271.4	275.6	280.9	287.3	304.3	326.5	362.6	407.1	453.7
70°	229.0	229.0	232.2	233.2	239.6	247.0	254.4	275.6	307.4	343.5	375.3
72.5°	188.7	194.0	192.9	198.2	197.2	202.5	212.0	225.8	249.1	277.8	308.5
75°	153.7	156.9	156.9	156.9	159.0	163.3	168.6	181.3	199.3	222.6	240.7
77.5°	119.8	121.9	121.9	121.9	123.0	127.2	132.5	141.0	153.7	167.5	178.1
80°	85.9	88.0	88.0	90.1	90.1	91.2	96.5	100.7	107.1	117.7	128.3
82.5°	58.3	59.4	61.5	61.5	60.4	62.5	63.6	67.9	74.2	76.3	83.8
85°	31.8	32.9	33.9	33.9	35.0	37.1	36.0	40.3	40.3	44.5	46.6
87.5°	12.7	14.8	14.8	13.8	14.8	14.8	14.8	17.0	18.0	19.1	18.0
90°	29.7	29.2	28.7	28.5	27.8	26.5	25.1	23.8	22.4	20.6	18.8
92.5°	27.5	27.5	27.5	27.5	26.8	25.5	24.1	22.8	21.4	19.6	17.8
95°	29.1	28.8	28.6	28.5	27.8	26.5	25.1	23.8	22.4	22.2	22.0
97.5°	28.1	27.8	27.6	27.5	26.9	25.8	24.7	23.5	22.4	46.2	70.0
100°	28.1	27.8	27.6	27.5	29.4	33.3	37.1	41.0	44.8	76.0	107.3
102.5°	29.5	29.5	29.5	29.5	55.0	105.9	156.8	207.8	258.7	256.0	253.3
105°	306.6	314.8	322.9	327.0	326.0	323.9	321.9	319.8	317.8	316.7	315.5
107.5°	390.4	389.5	388.6	388.1	387.5	386.4	385.3	384.1	383.0	381.4	379.8
110°	452.9	452.2	451.5	451.2	451.0	450.5	450.1	449.6	449.2	447.8	446.5

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	514.6	513.7	512.8	512.4	512.5	512.7	513.0	513.2	513.4	512.9	512.5
115°	576.5	576.5	576.5	576.5	576.3	575.8	575.4	574.9	574.5	574.7	574.9
117.5°	638.7	638.7	638.7	638.7	638.8	639.0	639.3	639.5	639.7	639.0	638.3
120°	697.6	698.1	698.6	698.8	698.6	698.1	697.6	697.2	696.7	696.9	697.2
122.5°	754.7	755.1	755.6	755.8	755.7	755.5	755.2	755.0	754.8	754.4	753.9
125°	810.4	810.1	809.9	809.8	809.5	808.8	808.1	807.4	806.7	807.2	807.6
127.5°	861.2	861.4	861.7	861.8	861.9	862.1	862.4	862.6	862.8	861.7	860.5
130°	911.7	911.7	911.7	911.7	911.6	911.3	911.1	910.8	910.6	909.9	909.3
132.5°	958.9	959.2	959.4	959.5	959.4	959.2	958.9	958.7	958.5	957.6	956.7
135°	1004.5	1004.0	1003.5	1003.3	1003.1	1002.6	1002.2	1001.7	1001.3	1000.4	999.5
137.5°	1045.5	1045.8	1046.0	1046.1	1045.9	1045.4	1045.0	1044.5	1044.1	1043.0	1041.8
140°	1086.5	1086.2	1086.0	1085.9	1085.6	1084.9	1084.2	1083.5	1082.8	1082.4	1081.9
142.5°	1121.5	1121.5	1121.5	1121.5	1121.3	1120.8	1120.4	1119.9	1119.5	1119.3	1119.0
145°	1156.3	1155.8	1155.3	1155.1	1155.0	1154.8	1154.5	1154.3	1154.1	1154.1	1154.1
147.5°	1186.3	1186.0	1185.8	1185.7	1185.6	1185.4	1185.1	1184.9	1184.7	1184.9	1185.1
150°	1214.8	1214.5	1214.3	1214.2	1214.2	1214.2	1214.2	1214.2	1214.2	1214.4	1214.6
152.5°	1240.1	1240.4	1240.6	1240.7	1240.5	1240.0	1239.5	1239.1	1238.6	1239.1	1239.5
155°	1262.4	1263.1	1263.8	1264.1	1263.6	1262.7	1261.8	1260.9	1260.0	1260.7	1261.4
157.5°	1281.7	1282.8	1283.9	1284.5	1283.9	1282.8	1281.7	1280.5	1279.4	1280.3	1281.2
160°	1300.4	1301.8	1303.1	1303.8	1303.1	1301.8	1300.4	1299.1	1297.7	1297.9	1298.1
162.5°	1315.2	1316.7	1318.3	1319.1	1318.4	1317.1	1315.7	1314.4	1313.0	1313.2	1313.4
165°	1329.3	1331.3	1333.4	1334.4	1333.5	1331.7	1329.8	1328.0	1326.2	1326.2	1326.2
167.5°	1339.9	1342.2	1344.5	1345.6	1344.6	1342.5	1340.5	1338.4	1336.4	1336.6	1336.8
170°	1349.1	1351.4	1353.7	1354.8	1353.9	1352.1	1350.2	1348.4	1346.6	1346.4	1346.2
172.5°	1354.7	1357.2	1359.7	1360.9	1360.0	1358.2	1356.3	1354.5	1352.7	1352.5	1352.3
175°	1359.2	1361.9	1364.6	1366.0	1365.0	1362.9	1360.9	1358.8	1356.8	1356.6	1356.4
177.5°	1361.2	1363.9	1366.6	1368.0	1367.1	1365.3	1363.5	1361.7	1359.9	1359.4	1359.0
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
2.5°	1319.9	1315.7	1312.5	1312.5	1302.9	1293.4	1288.1	1286.0	1283.9	1275.4	1263.7
5°	1374.0	1360.2	1350.6	1341.1	1325.2	1308.2	1291.3	1281.7	1268.0	1248.9	1235.1
7.5°	1434.4	1401.5	1390.9	1379.3	1347.5	1318.8	1295.5	1275.4	1253.1	1228.7	1204.3
10°	1485.3	1450.3	1427.0	1406.8	1365.5	1327.3	1292.3	1262.7	1234.0	1202.2	1172.5
12.5°	1534.1	1484.2	1459.8	1430.2	1386.7	1331.6	1286.0	1248.9	1206.5	1173.6	1137.6
15°	1601.9	1518.1	1477.9	1458.8	1400.5	1335.8	1280.7	1225.5	1190.6	1140.7	1108.9
17.5°	1612.5	1544.7	1518.1	1469.4	1399.4	1326.3	1262.7	1207.5	1154.5	1110.0	1068.6
20°	1649.6	1560.6	1518.1	1487.4	1395.2	1321.0	1251.0	1180.0	1129.1	1081.4	1034.7
22.5°	1672.9	1572.2	1527.7	1478.9	1390.9	1301.9	1219.2	1157.7	1095.1	1046.4	1009.3
25°	1666.6	1565.9	1516.0	1470.4	1363.4	1274.3	1200.1	1121.6	1063.3	1010.3	961.6
27.5°	1663.4	1550.0	1496.9	1446.1	1345.3	1252.0	1158.8	1095.1	1030.5	969.0	932.9
30°	1654.9	1529.8	1468.3	1413.2	1308.2	1210.7	1131.2	1057.0	992.3	936.1	888.4
32.5°	1626.3	1495.9	1436.5	1377.1	1268.0	1170.4	1089.8	1020.9	956.3	898.0	852.4
35°	1588.1	1455.6	1390.9	1328.4	1219.2	1120.6	1046.4	974.3	913.9	857.7	814.2
37.5°	1550.0	1409.0	1348.5	1276.4	1175.7	1072.9	996.6	931.9	875.7	817.4	769.7
40°	1494.8	1353.8	1287.0	1225.5	1107.9	1011.4	941.4	883.1	828.0	772.9	732.6
42.5°	1419.6	1293.4	1224.5	1156.6	1046.4	951.0	883.1	831.2	779.2	733.6	689.1
45°	1343.2	1220.2	1158.8	1098.3	978.5	888.4	825.9	778.2	734.7	684.9	648.8
47.5°	1251.0	1147.1	1085.6	1026.2	912.8	822.7	765.4	720.9	680.6	639.3	605.4
50°	1156.6	1066.5	1010.3	948.8	840.7	759.1	702.9	665.8	632.9	593.7	566.1
52.5°	1054.9	976.4	928.7	869.3	773.9	698.6	641.4	604.3	576.7	548.1	523.7
55°	946.7	889.5	838.6	790.9	700.8	632.9	582.0	549.2	530.1	503.6	482.4
57.5°	849.2	794.1	763.3	709.2	630.8	564.0	523.7	496.2	473.9	458.0	441.0
60°	747.4	702.9	669.0	629.7	560.8	504.6	462.2	446.3	423.0	411.3	403.9
62.5°	649.9	618.1	586.3	556.6	495.1	442.1	410.3	390.1	376.4	364.7	358.3
65°	557.6	528.0	505.7	479.2	428.3	385.9	356.2	340.3	326.5	323.3	315.9
67.5°	467.5	454.8	430.4	409.2	365.8	332.9	310.6	290.5	283.1	279.9	273.5
70°	391.2	376.4	357.3	339.3	306.4	277.8	257.6	250.2	239.6	238.5	231.1
72.5°	322.3	304.3	290.5	276.7	252.3	226.9	216.3	205.7	200.4	196.1	192.9
75°	255.5	242.8	233.2	221.6	200.4	183.4	168.6	164.3	161.1	160.1	158.0
77.5°	190.8	182.3	178.1	166.4	151.6	136.8	130.4	124.0	124.0	121.9	123.0
80°	135.7	130.4	125.1	118.7	106.0	99.7	94.4	90.1	88.0	86.9	88.0
82.5°	85.9	82.7	81.6	77.4	68.9	65.7	61.5	58.3	58.3	58.3	58.3
85°	47.7	47.7	47.7	41.3	38.2	35.0	32.9	31.8	31.8	31.8	32.9
87.5°	20.1	20.1	17.0	17.0	15.9	13.8	12.7	12.7	13.8	13.8	14.8
90°	17.0	15.2	14.3	13.1	10.6	8.1	5.6	3.1	5.6	8.1	10.6
92.5°	15.9	14.1	13.2	13.4	13.9	14.4	14.8	15.3	14.8	14.4	13.9
95°	21.7	21.5	21.4	25.2	32.9	40.6	48.3	56.0	48.3	40.6	32.9
97.5°	93.7	117.5	129.4	126.9	121.9	117.0	112.0	107.0	112.0	117.0	121.9
100°	138.5	169.8	185.4	183.4	179.3	175.2	171.2	167.1	171.2	175.2	179.3
102.5°	250.6	247.9	246.5	245.1	242.4	239.7	237.0	234.3	237.0	239.7	242.4
105°	314.4	313.3	312.7	312.0	310.7	309.3	308.0	306.6	308.0	309.3	310.7
107.5°	378.3	376.7	375.9	375.6	374.9	374.2	373.5	372.8	373.5	374.2	374.9
110°	445.1	443.8	443.1	442.8	442.1	441.4	440.7	440.0	440.7	441.4	442.1

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	512.0	511.5	511.3	510.6	509.3	507.9	506.6	505.2	506.6	507.9	509.3
115°	575.2	575.4	575.5	575.2	574.5	573.8	573.2	572.5	573.2	573.8	574.5
117.5°	637.6	636.9	636.6	636.2	635.3	634.4	633.5	632.6	633.5	634.4	635.3
120°	697.4	697.7	697.8	697.3	696.4	695.5	694.6	693.7	694.6	695.5	696.4
122.5°	753.5	753.0	752.8	752.6	752.1	751.6	751.2	750.7	751.2	751.6	752.1
125°	808.1	808.6	808.8	808.3	807.4	806.5	805.6	804.7	805.6	806.5	807.4
127.5°	859.4	858.3	857.7	857.6	857.4	857.1	856.9	856.7	856.9	857.1	857.4
130°	908.6	907.9	907.6	907.5	907.3	907.0	906.8	906.6	906.8	907.0	907.3
132.5°	955.8	954.9	954.4	954.2	953.7	953.3	952.8	952.4	952.8	953.3	953.7
135°	998.6	997.7	997.2	997.3	997.5	997.8	998.0	998.2	998.0	997.8	997.5
137.5°	1040.7	1039.6	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0
140°	1081.5	1081.0	1080.8	1080.6	1080.1	1079.6	1079.2	1078.7	1079.2	1079.6	1080.1
142.5°	1118.8	1118.5	1118.4	1118.0	1117.1	1116.2	1115.3	1114.4	1115.3	1116.2	1117.1
145°	1154.1	1154.1	1154.1	1153.8	1153.1	1152.4	1151.7	1151.0	1151.7	1152.4	1153.1
147.5°	1185.4	1185.6	1185.7	1185.0	1183.7	1182.3	1181.0	1179.6	1181.0	1182.3	1183.7
150°	1214.9	1215.1	1215.2	1214.7	1213.8	1212.9	1212.0	1211.1	1212.0	1212.9	1213.8
152.5°	1240.0	1240.5	1240.7	1240.4	1239.7	1239.0	1238.3	1237.6	1238.3	1239.0	1239.7
155°	1262.1	1262.8	1263.1	1263.0	1262.8	1262.5	1262.3	1262.1	1262.3	1262.5	1262.8
157.5°	1282.1	1283.0	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5
160°	1298.4	1298.6	1298.7	1299.0	1299.7	1300.4	1301.1	1301.8	1301.1	1300.4	1299.7
162.5°	1313.7	1313.9	1314.0	1314.5	1315.4	1316.3	1317.2	1318.1	1317.2	1316.3	1315.4
165°	1326.2	1326.2	1326.2	1326.8	1327.9	1329.0	1330.2	1331.3	1330.2	1329.0	1327.9
167.5°	1337.1	1337.3	1337.4	1338.0	1339.1	1340.2	1341.4	1342.5	1341.4	1340.2	1339.1
170°	1345.9	1345.7	1345.6	1346.3	1347.6	1349.0	1350.3	1351.7	1350.3	1349.0	1347.6
172.5°	1352.0	1351.8	1351.7	1352.4	1353.7	1355.1	1356.4	1357.8	1356.4	1355.1	1353.7
175°	1356.1	1355.9	1355.8	1356.5	1357.8	1359.2	1360.5	1361.9	1360.5	1359.2	1357.8
177.5°	1358.5	1358.0	1357.8	1358.6	1360.2	1361.8	1363.4	1365.0	1363.4	1361.8	1360.2
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
2.5°	1260.5	1256.3	1258.4	1247.8	1238.3	1224.5	1212.8	1210.7	1208.6	1214.9	1210.7
5°	1224.5	1219.2	1213.9	1201.2	1182.1	1170.4	1153.5	1152.4	1146.0	1136.5	1138.6
7.5°	1185.3	1182.1	1174.7	1154.5	1137.6	1117.4	1103.6	1092.0	1086.7	1078.2	1075.0
10°	1153.5	1141.8	1135.4	1113.2	1093.0	1071.8	1053.8	1045.3	1035.8	1028.4	1023.1
12.5°	1110.0	1106.8	1088.8	1070.8	1053.8	1029.4	1015.6	991.2	978.5	984.9	982.8
15°	1081.4	1066.5	1062.3	1036.8	1008.2	992.3	966.9	951.0	945.7	936.1	924.5
17.5°	1043.2	1033.7	1018.8	995.5	962.6	940.4	922.3	907.5	901.1	888.4	878.9
20°	1007.2	991.2	979.6	958.4	926.6	898.0	875.7	866.2	850.2	839.6	834.3
22.5°	974.3	962.6	945.7	913.9	886.3	858.7	832.2	818.4	803.6	797.2	788.8
25°	934.0	914.9	903.3	868.3	838.6	816.3	791.9	773.9	765.4	754.8	752.7
27.5°	894.8	876.8	863.0	832.2	796.2	767.6	752.7	740.0	725.1	725.1	719.8
30°	855.5	842.8	821.6	791.9	758.0	730.5	713.5	701.8	696.5	692.3	691.2
32.5°	816.3	799.4	786.6	746.4	720.9	695.5	682.7	673.2	666.8	665.8	666.8
35°	776.0	757.0	744.2	708.2	682.7	659.4	654.1	645.6	642.5	641.4	646.7
37.5°	733.6	718.8	702.9	673.2	644.6	630.8	620.2	617.0	616.0	622.3	624.4
40°	694.4	681.7	666.8	635.0	613.8	599.0	593.7	590.5	594.7	601.1	604.3
42.5°	657.3	639.3	627.6	599.0	579.9	571.4	565.1	565.1	569.3	576.7	582.0
45°	618.1	604.3	592.6	567.2	550.2	540.7	539.6	540.7	546.0	551.3	557.6
47.5°	579.9	566.1	553.4	532.2	517.4	512.1	511.0	512.1	520.5	528.0	535.4
50°	544.9	530.1	518.4	498.3	486.6	480.3	481.3	486.6	493.0	503.6	513.1
52.5°	503.6	493.0	482.4	464.4	453.7	449.5	452.7	456.9	468.6	476.0	487.7
55°	463.3	453.7	445.3	431.5	423.0	419.8	421.9	428.3	437.8	450.6	464.4
57.5°	426.2	415.6	407.1	397.6	388.0	389.1	390.1	398.6	410.3	421.9	437.8
60°	384.8	378.5	371.1	359.4	355.2	355.2	358.3	367.9	378.5	397.6	411.3
62.5°	347.7	339.3	334.0	326.5	320.2	321.2	328.6	337.1	349.9	365.8	383.8
65°	309.6	300.0	295.8	289.4	287.3	288.4	293.7	306.4	320.2	334.0	350.9
67.5°	267.2	264.0	259.7	253.4	255.5	256.6	261.9	272.5	287.3	301.1	320.2
70°	231.1	224.8	223.7	218.4	218.4	221.6	232.2	239.6	253.4	268.2	288.4
72.5°	192.9	187.6	187.6	183.4	186.6	189.8	195.1	205.7	218.4	233.2	250.2
75°	153.7	151.6	153.7	151.6	151.6	156.9	163.3	171.7	185.5	201.4	215.2
77.5°	118.7	118.7	117.7	120.9	120.9	124.0	132.5	141.0	151.6	164.3	179.2
80°	86.9	86.9	86.9	90.1	93.3	93.3	98.6	109.2	118.7	127.2	141.0
82.5°	59.4	59.4	59.4	61.5	65.7	65.7	72.1	78.5	89.1	96.5	102.8
85°	36.0	36.0	35.0	37.1	38.2	41.3	46.6	50.9	56.2	62.5	68.9
87.5°	15.9	15.9	17.0	18.0	19.1	21.2	23.3	25.4	30.7	32.9	36.0
90°	13.1	14.3	15.2	17.0	18.8	20.6	22.4	23.8	25.1	26.5	27.8
92.5°	13.4	13.2	14.1	15.9	17.8	19.6	21.4	22.8	24.1	25.5	26.8
95°	25.2	21.4	21.5	21.7	22.0	22.2	22.4	23.8	25.1	26.5	27.8
97.5°	126.9	129.4	117.5	93.7	70.0	46.2	22.4	23.5	24.7	25.8	26.9
100°	183.4	185.4	169.8	138.5	107.3	76.0	44.8	41.0	37.1	33.3	29.4
102.5°	245.1	246.5	247.9	250.6	253.3	256.0	258.7	207.8	156.8	105.9	55.0
105°	312.0	312.7	313.3	314.4	315.5	316.7	317.8	319.8	321.9	323.9	326.0
107.5°	375.6	375.9	376.7	378.3	379.8	381.4	383.0	384.1	385.3	386.4	387.5
110°	442.8	443.1	443.8	445.1	446.5	447.8	449.2	449.6	450.1	450.5	451.0

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	510.6	511.3	511.5	512.0	512.5	512.9	513.4	513.2	513.0	512.7	512.5
115°	575.2	575.5	575.4	575.2	574.9	574.7	574.5	574.9	575.4	575.8	576.3
117.5°	636.2	636.6	636.9	637.6	638.3	639.0	639.7	639.5	639.3	639.0	638.8
120°	697.3	697.8	697.7	697.4	697.2	696.9	696.7	697.2	697.6	698.1	698.6
122.5°	752.6	752.8	753.0	753.5	753.9	754.4	754.8	755.0	755.2	755.5	755.7
125°	808.3	808.8	808.6	808.1	807.6	807.2	806.7	807.4	808.1	808.8	809.5
127.5°	857.6	857.7	858.3	859.4	860.5	861.7	862.8	862.6	862.4	862.1	861.9
130°	907.5	907.6	907.9	908.6	909.3	909.9	910.6	910.8	911.1	911.3	911.6
132.5°	954.2	954.4	954.9	955.8	956.7	957.6	958.5	958.7	958.9	959.2	959.4
135°	997.3	997.2	997.7	998.6	999.5	1000.4	1001.3	1001.7	1002.2	1002.6	1003.1
137.5°	1039.0	1039.0	1039.6	1040.7	1041.8	1043.0	1044.1	1044.5	1045.0	1045.4	1045.9
140°	1080.6	1080.8	1081.0	1081.5	1081.9	1082.4	1082.8	1083.5	1084.2	1084.9	1085.6
142.5°	1118.0	1118.4	1118.5	1118.8	1119.0	1119.3	1119.5	1119.9	1120.4	1120.8	1121.3
145°	1153.8	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1	1154.3	1154.5	1154.8	1155.0
147.5°	1185.0	1185.7	1185.6	1185.4	1185.1	1184.9	1184.7	1184.9	1185.1	1185.4	1185.6
150°	1214.7	1215.2	1215.1	1214.9	1214.6	1214.4	1214.2	1214.2	1214.2	1214.2	1214.2
152.5°	1240.4	1240.7	1240.5	1240.0	1239.5	1239.1	1238.6	1239.1	1239.5	1240.0	1240.5
155°	1263.0	1263.1	1262.8	1262.1	1261.4	1260.7	1260.0	1260.9	1261.8	1262.7	1263.6
157.5°	1283.5	1283.5	1283.0	1282.1	1281.2	1280.3	1279.4	1280.5	1281.7	1282.8	1283.9
160°	1299.0	1298.7	1298.6	1298.4	1298.1	1297.9	1297.7	1299.1	1300.4	1301.8	1303.1
162.5°	1314.5	1314.0	1313.9	1313.7	1313.4	1313.2	1313.0	1314.4	1315.7	1317.1	1318.4
165°	1326.8	1326.2	1326.2	1326.2	1326.2	1326.2	1326.2	1328.0	1329.8	1331.7	1333.5
167.5°	1338.0	1337.4	1337.3	1337.1	1336.8	1336.6	1336.4	1338.4	1340.5	1342.5	1344.6
170°	1346.3	1345.6	1345.7	1345.9	1346.2	1346.4	1346.6	1348.4	1350.2	1352.1	1353.9
172.5°	1352.4	1351.7	1351.8	1352.0	1352.3	1352.5	1352.7	1354.5	1356.3	1358.2	1360.0
175°	1356.5	1355.8	1355.9	1356.1	1356.4	1356.6	1356.8	1358.8	1360.9	1362.9	1365.0
177.5°	1358.6	1357.8	1358.0	1358.5	1359.0	1359.4	1359.9	1361.7	1363.5	1365.3	1367.1
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
2.5°	1207.5	1206.5	1201.2	1203.3	1196.9	1199.0	1202.2	1203.3	1207.5	1204.3	1203.3
5°	1133.3	1131.2	1128.0	1124.8	1123.8	1128.0	1120.6	1122.7	1124.8	1128.0	1132.3
7.5°	1072.9	1071.8	1068.6	1063.3	1061.2	1059.1	1060.2	1067.6	1066.5	1065.5	1072.9
10°	1017.8	1018.8	1012.5	1011.4	1005.0	1004.0	1005.0	1007.2	1010.3	1014.6	1015.6
12.5°	960.5	974.3	962.6	958.4	948.8	954.1	956.3	946.7	952.0	955.2	971.1
15°	924.5	918.1	910.7	910.7	906.4	904.3	899.0	906.4	910.7	917.0	914.9
17.5°	874.6	864.0	859.8	855.5	856.6	860.8	849.2	866.2	866.2	869.3	864.0
20°	831.2	822.7	817.4	815.3	812.1	810.0	808.9	813.1	819.5	821.6	826.9
22.5°	785.6	785.6	777.1	773.9	771.8	768.6	773.9	770.7	775.0	779.2	787.7
25°	747.4	747.4	744.2	740.0	736.8	734.7	737.9	736.8	740.0	745.3	747.4
27.5°	716.7	713.5	712.4	711.4	710.3	711.4	710.3	713.5	716.7	717.7	715.6
30°	690.2	687.0	688.0	688.0	689.1	688.0	687.0	690.2	691.2	689.1	690.2
32.5°	665.8	665.8	667.9	669.0	669.0	670.0	671.1	669.0	670.0	666.8	667.9
35°	645.6	647.8	649.9	650.9	652.0	650.9	653.1	652.0	649.9	647.8	646.7
37.5°	625.5	627.6	631.9	632.9	636.1	637.2	635.0	635.0	634.0	629.7	627.6
40°	604.3	606.4	611.7	614.9	617.0	620.2	618.1	618.1	613.8	609.6	606.4
42.5°	584.1	588.4	593.7	596.9	601.1	601.1	601.1	599.0	593.7	589.4	586.3
45°	564.0	565.1	572.5	577.8	582.0	582.0	582.0	578.8	575.7	567.2	562.9
47.5°	541.7	544.9	553.4	558.7	562.9	564.0	564.0	560.8	554.5	547.0	541.7
50°	517.4	522.7	532.2	539.6	544.9	547.0	543.9	541.7	534.3	525.8	519.5
52.5°	494.0	500.4	512.1	518.4	525.8	526.9	525.8	522.7	514.2	502.5	497.2
55°	470.7	476.0	488.7	499.3	505.7	507.8	505.7	500.4	489.8	478.1	472.8
57.5°	445.3	452.7	466.5	477.1	484.5	485.6	483.4	478.1	469.7	454.8	447.4
60°	418.8	428.3	442.1	452.7	462.2	463.3	461.2	453.7	443.1	428.3	421.9
62.5°	392.3	399.7	415.6	427.2	434.7	440.0	435.7	428.3	417.7	402.9	393.3
65°	361.5	372.1	385.9	396.5	405.0	406.0	403.9	397.6	385.9	370.0	362.6
67.5°	331.8	339.3	353.0	366.8	370.0	373.2	370.0	363.6	354.1	340.3	329.7
70°	295.8	302.1	319.1	328.6	332.9	336.1	334.0	327.6	319.1	306.4	297.9
72.5°	259.7	265.0	280.9	288.4	296.8	295.8	294.7	290.5	278.8	270.3	265.0
75°	221.6	227.9	238.5	248.1	251.3	251.3	251.3	248.1	240.7	226.9	221.6
77.5°	186.6	189.8	198.2	203.6	206.7	207.8	206.7	201.4	197.2	187.6	184.5
80°	143.1	151.6	158.0	159.0	163.3	163.3	163.3	161.1	156.9	147.4	146.3
82.5°	108.1	110.3	116.6	119.8	121.9	120.9	120.9	116.6	115.6	110.3	108.1
85°	73.2	76.3	75.3	79.5	80.6	78.5	78.5	80.6	75.3	76.3	73.2
87.5°	40.3	40.3	42.4	41.3	45.6	45.6	43.5	44.5	42.4	41.3	40.3
90°	28.5	28.7	29.2	29.7	30.1	30.6	30.1	29.7	29.2	28.7	28.5
92.5°	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5
95°	28.5	28.6	28.8	29.1	29.3	29.5	29.3	29.1	28.8	28.6	28.5
97.5°	27.5	27.6	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	27.5
100°	27.5	27.6	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	27.5
102.5°	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5
105°	327.0	322.9	314.8	306.6	298.5	290.3	298.5	306.6	314.8	322.9	327.0
107.5°	388.1	388.6	389.5	390.4	391.3	392.2	391.3	390.4	389.5	388.6	388.1
110°	451.2	451.5	452.2	452.9	453.6	454.3	453.6	452.9	452.2	451.5	451.2

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	512.4	512.8	513.7	514.6	515.5	516.4	515.5	514.6	513.7	512.8	512.4
115°	576.5	576.5	576.5	576.5	576.5	576.5	576.5	576.5	576.5	576.5	576.5
117.5°	638.7	638.7	638.7	638.7	638.7	638.7	638.7	638.7	638.7	638.7	638.7
120°	698.8	698.6	698.1	697.6	697.2	696.7	697.2	697.6	698.1	698.6	698.8
122.5°	755.8	755.6	755.1	754.7	754.2	753.8	754.2	754.7	755.1	755.6	755.8
125°	809.8	809.9	810.1	810.4	810.6	810.8	810.6	810.4	810.1	809.9	809.8
127.5°	861.8	861.7	861.4	861.2	860.9	860.7	860.9	861.2	861.4	861.7	861.8
130°	911.7	911.7	911.7	911.7	911.7	911.7	911.7	911.7	911.7	911.7	911.7
132.5°	959.5	959.4	959.2	958.9	958.7	958.5	958.7	958.9	959.2	959.4	959.5
135°	1003.3	1003.5	1004.0	1004.5	1004.9	1005.4	1004.9	1004.5	1004.0	1003.5	1003.3
137.5°	1046.1	1046.0	1045.8	1045.5	1045.3	1045.1	1045.3	1045.5	1045.8	1046.0	1046.1
140°	1085.9	1086.0	1086.2	1086.5	1086.7	1086.9	1086.7	1086.5	1086.2	1086.0	1085.9
142.5°	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5
145°	1155.1	1155.3	1155.8	1156.3	1156.7	1157.2	1156.7	1156.3	1155.8	1155.3	1155.1
147.5°	1185.7	1185.8	1186.0	1186.3	1186.5	1186.7	1186.5	1186.3	1186.0	1185.8	1185.7
150°	1214.2	1214.3	1214.5	1214.8	1215.0	1215.2	1215.0	1214.8	1214.5	1214.3	1214.2
152.5°	1240.7	1240.6	1240.4	1240.1	1239.9	1239.7	1239.9	1240.1	1240.4	1240.6	1240.7
155°	1264.1	1263.8	1263.1	1262.4	1261.8	1261.1	1261.8	1262.4	1263.1	1263.8	1264.1
157.5°	1284.5	1283.9	1282.8	1281.7	1280.5	1279.4	1280.5	1281.7	1282.8	1283.9	1284.5
160°	1303.8	1303.1	1301.8	1300.4	1299.1	1297.7	1299.1	1300.4	1301.8	1303.1	1303.8
162.5°	1319.1	1318.3	1316.7	1315.2	1313.6	1312.0	1313.6	1315.2	1316.7	1318.3	1319.1
165°	1334.4	1333.4	1331.3	1329.3	1327.2	1325.2	1327.2	1329.3	1331.3	1333.4	1334.4
167.5°	1345.6	1344.5	1342.2	1339.9	1337.7	1335.4	1337.7	1339.9	1342.2	1344.5	1345.6
170°	1354.8	1353.7	1351.4	1349.1	1346.9	1344.6	1346.9	1349.1	1351.4	1353.7	1354.8
172.5°	1360.9	1359.7	1357.2	1354.7	1352.2	1349.7	1352.2	1354.7	1357.2	1359.7	1360.9
175°	1366.0	1364.6	1361.9	1359.2	1356.4	1353.7	1356.4	1359.2	1361.9	1364.6	1366.0
177.5°	1368.0	1366.6	1363.9	1361.2	1358.5	1355.8	1358.5	1361.2	1363.9	1366.6	1368.0
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
2.5°	1203.3	1209.6	1203.3	1207.5	1209.6	1214.9	1217.1	1226.6	1229.8	1237.2	1237.2
5°	1131.2	1134.4	1135.4	1139.7	1143.9	1154.5	1161.9	1175.7	1191.6	1193.7	1203.3
7.5°	1072.9	1078.2	1086.7	1083.5	1090.9	1106.8	1116.3	1133.3	1149.2	1157.7	1169.4
10°	1020.9	1027.3	1030.5	1033.7	1047.4	1061.2	1076.1	1087.7	1108.9	1121.6	1131.2
12.5°	978.5	973.2	979.6	991.2	1007.2	1015.6	1035.8	1053.8	1069.7	1083.5	1092.0
15°	923.4	927.6	934.0	954.1	958.4	979.6	987.0	1007.2	1036.8	1049.6	1060.2
17.5°	870.4	884.2	896.9	904.3	917.0	934.0	955.2	977.5	996.6	1011.4	1024.1
20°	828.0	841.8	849.2	854.5	867.2	890.5	910.7	938.2	962.6	974.3	991.2
22.5°	794.1	794.1	804.7	820.6	828.0	850.2	867.2	896.9	923.4	938.2	954.1
25°	751.7	758.0	766.5	780.3	790.9	808.9	833.3	858.7	887.4	900.1	920.2
27.5°	716.7	724.1	735.8	738.9	749.5	765.4	790.9	818.4	848.1	861.9	878.9
30°	690.2	694.4	698.6	705.0	714.5	728.3	749.5	773.9	810.0	820.6	841.8
32.5°	666.8	669.0	671.1	676.4	681.7	695.5	712.4	738.9	768.6	784.5	803.6
35°	645.6	643.5	644.6	647.8	653.1	658.4	676.4	698.6	726.2	745.3	760.1
37.5°	625.5	621.3	620.2	620.2	622.3	628.7	642.5	661.5	691.2	707.1	722.0
40°	603.2	599.0	596.9	595.8	594.7	599.0	609.6	628.7	652.0	666.8	683.8
42.5°	582.0	577.8	572.5	571.4	569.3	571.4	578.8	596.9	617.0	631.9	645.6
45°	560.8	553.4	547.0	542.8	543.9	540.7	546.0	559.8	583.1	592.6	606.4
47.5°	537.5	529.0	520.5	516.3	512.1	514.2	516.3	528.0	548.1	557.6	571.4
50°	515.2	503.6	494.0	488.7	485.6	483.4	485.6	497.2	512.1	520.5	532.2
52.5°	489.8	478.1	468.6	460.1	455.9	452.7	453.7	464.4	478.1	486.6	498.3
55°	466.5	451.6	438.9	428.3	425.1	424.1	423.0	430.4	442.1	450.6	460.1
57.5°	440.0	425.1	411.3	398.6	392.3	391.2	391.2	393.3	408.2	414.5	419.8
60°	413.5	397.6	382.7	371.1	361.5	358.3	357.3	361.5	368.9	375.3	382.7
62.5°	383.8	367.9	349.9	339.3	329.7	321.2	324.4	325.5	336.1	339.3	345.6
65°	355.2	337.1	322.3	305.3	294.7	289.4	287.3	289.4	297.9	299.0	303.2
67.5°	322.3	305.3	287.3	275.6	266.1	256.6	254.4	254.4	258.7	261.9	267.2
70°	290.5	273.5	253.4	240.7	231.1	222.6	219.5	218.4	221.6	223.7	229.0
72.5°	253.4	236.4	221.6	207.8	196.1	189.8	186.6	184.5	187.6	189.8	190.8
75°	214.2	200.4	185.5	171.7	164.3	158.0	153.7	150.5	152.7	152.7	152.7
77.5°	177.0	163.3	151.6	142.1	132.5	125.1	121.9	118.7	119.8	119.8	121.9
80°	137.8	128.3	118.7	110.3	101.8	95.4	93.3	90.1	88.0	86.9	86.9
82.5°	101.8	94.4	85.9	78.5	74.2	67.9	65.7	61.5	61.5	60.4	60.4
85°	67.9	63.6	55.1	49.8	46.6	43.5	41.3	39.2	36.0	36.0	35.0
87.5°	36.0	33.9	31.8	25.4	25.4	22.3	21.2	20.1	17.0	18.0	18.0
90°	27.8	26.5	25.1	23.8	22.4	20.6	18.8	17.0	15.2	14.3	13.1
92.5°	26.8	25.5	24.1	22.8	21.4	19.6	17.8	15.9	14.1	13.2	13.4
95°	27.8	26.5	25.1	23.8	22.4	22.2	22.0	21.7	21.5	21.4	25.2
97.5°	26.9	25.8	24.7	23.5	22.4	46.2	70.0	93.7	117.5	129.4	126.9
100°	29.4	33.3	37.1	41.0	44.8	76.0	107.3	138.5	169.8	185.4	183.4
102.5°	55.0	105.9	156.8	207.8	258.7	256.0	253.3	250.6	247.9	246.5	245.1
105°	326.0	323.9	321.9	319.8	317.8	316.7	315.5	314.4	313.3	312.7	312.0
107.5°	387.5	386.4	385.3	384.1	383.0	381.4	379.8	378.3	376.7	375.9	375.6
110°	451.0	450.5	450.1	449.6	449.2	447.8	446.5	445.1	443.8	443.1	442.8

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	512.5	512.7	513.0	513.2	513.4	512.9	512.5	512.0	511.5	511.3	510.6
115°	576.3	575.8	575.4	574.9	574.5	574.7	574.9	575.2	575.4	575.5	575.2
117.5°	638.8	639.0	639.3	639.5	639.7	639.0	638.3	637.6	636.9	636.6	636.2
120°	698.6	698.1	697.6	697.2	696.7	696.9	697.2	697.4	697.7	697.8	697.3
122.5°	755.7	755.5	755.2	755.0	754.8	754.4	753.9	753.5	753.0	752.8	752.6
125°	809.5	808.8	808.1	807.4	806.7	807.2	807.6	808.1	808.6	808.8	808.3
127.5°	861.9	862.1	862.4	862.6	862.8	861.7	860.5	859.4	858.3	857.7	857.6
130°	911.6	911.3	911.1	910.8	910.6	909.9	909.3	908.6	907.9	907.6	907.5
132.5°	959.4	959.2	958.9	958.7	958.5	957.6	956.7	955.8	954.9	954.4	954.2
135°	1003.1	1002.6	1002.2	1001.7	1001.3	1000.4	999.5	998.6	997.7	997.2	997.3
137.5°	1045.9	1045.4	1045.0	1044.5	1044.1	1043.0	1041.8	1040.7	1039.6	1039.0	1039.0
140°	1085.6	1084.9	1084.2	1083.5	1082.8	1082.4	1081.9	1081.5	1081.0	1080.8	1080.6
142.5°	1121.3	1120.8	1120.4	1119.9	1119.5	1119.3	1119.0	1118.8	1118.5	1118.4	1118.0
145°	1155.0	1154.8	1154.5	1154.3	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1	1153.8
147.5°	1185.6	1185.4	1185.1	1184.9	1184.7	1184.9	1185.1	1185.4	1185.6	1185.7	1185.0
150°	1214.2	1214.2	1214.2	1214.2	1214.2	1214.4	1214.6	1214.9	1215.1	1215.2	1214.7
152.5°	1240.5	1240.0	1239.5	1239.1	1238.6	1239.1	1239.5	1240.0	1240.5	1240.7	1240.4
155°	1263.6	1262.7	1261.8	1260.9	1260.0	1260.7	1261.4	1262.1	1262.8	1263.1	1263.0
157.5°	1283.9	1282.8	1281.7	1280.5	1279.4	1280.3	1281.2	1282.1	1283.0	1283.5	1283.5
160°	1303.1	1301.8	1300.4	1299.1	1297.7	1297.9	1298.1	1298.4	1298.6	1298.7	1299.0
162.5°	1318.4	1317.1	1315.7	1314.4	1313.0	1313.2	1313.4	1313.7	1313.9	1314.0	1314.5
165°	1333.5	1331.7	1329.8	1328.0	1326.2	1326.2	1326.2	1326.2	1326.2	1326.2	1326.8
167.5°	1344.6	1342.5	1340.5	1338.4	1336.4	1336.6	1336.8	1337.1	1337.3	1337.4	1338.0
170°	1353.9	1352.1	1350.2	1348.4	1346.6	1346.4	1346.2	1345.9	1345.7	1345.6	1346.3
172.5°	1360.0	1358.2	1356.3	1354.5	1352.7	1352.5	1352.3	1352.0	1351.8	1351.7	1352.4
175°	1365.0	1362.9	1360.9	1358.8	1356.8	1356.6	1356.4	1356.1	1355.9	1355.8	1356.5
177.5°	1367.1	1365.3	1363.5	1361.7	1359.9	1359.4	1359.0	1358.5	1358.0	1357.8	1358.6
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1279.6	1279.6	1279.6	1279.6
2.5°	1244.6	1255.2	1264.8	1279.6
5°	1217.1	1231.9	1252.0	1274.3
7.5°	1185.3	1208.6	1235.1	1265.8
10°	1155.6	1182.1	1216.0	1253.1
12.5°	1124.8	1156.6	1193.7	1234.0
15°	1089.8	1121.6	1163.0	1217.1
17.5°	1058.0	1096.2	1140.7	1198.0
20°	1020.9	1057.0	1105.7	1171.5
22.5°	988.1	1029.4	1083.5	1140.7
25°	952.0	988.1	1042.1	1111.0
27.5°	916.0	960.5	1012.5	1079.2
30°	881.0	918.1	974.3	1044.3
32.5°	842.8	887.4	939.3	1005.0
35°	801.5	843.9	892.7	963.7
37.5°	764.4	805.7	855.5	918.1
40°	723.0	766.5	812.1	874.6
42.5°	682.7	722.0	767.6	824.8
45°	643.5	677.4	718.8	768.6
47.5°	603.2	631.9	670.0	714.5
50°	559.8	590.5	619.1	656.2
52.5°	519.5	546.0	569.3	600.1
55°	480.3	498.3	517.4	540.7
57.5°	438.9	452.7	466.5	490.9
60°	397.6	410.3	417.7	433.6
62.5°	357.3	362.6	372.1	381.7
65°	312.7	320.2	325.5	337.1
67.5°	272.5	275.6	280.9	288.4
70°	230.1	237.5	239.6	244.9
72.5°	194.0	197.2	199.3	200.4
75°	153.7	156.9	159.0	165.4
77.5°	120.9	119.8	124.0	125.1
80°	89.1	85.9	86.9	91.2
82.5°	58.3	59.4	58.3	58.3
85°	36.0	35.0	32.9	33.9
87.5°	15.9	15.9	14.8	14.8
90°	10.6	8.1	5.6	3.1
92.5°	13.9	14.4	14.8	15.3
95°	32.9	40.6	48.3	56.0
97.5°	121.9	117.0	112.0	107.0
100°	179.3	175.2	171.2	167.1
102.5°	242.4	239.7	237.0	234.3
105°	310.7	309.3	308.0	306.6
107.5°	374.9	374.2	373.5	372.8
110°	442.1	441.4	440.7	440.0



TEST NUMBER: P1032765

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	509.3	507.9	506.6	505.2
115°	574.5	573.8	573.2	572.5
117.5°	635.3	634.4	633.5	632.6
120°	696.4	695.5	694.6	693.7
122.5°	752.1	751.6	751.2	750.7
125°	807.4	806.5	805.6	804.7
127.5°	857.4	857.1	856.9	856.7
130°	907.3	907.0	906.8	906.6
132.5°	953.7	953.3	952.8	952.4
135°	997.5	997.8	998.0	998.2
137.5°	1039.0	1039.0	1039.0	1039.0
140°	1080.1	1079.6	1079.2	1078.7
142.5°	1117.1	1116.2	1115.3	1114.4
145°	1153.1	1152.4	1151.7	1151.0
147.5°	1183.7	1182.3	1181.0	1179.6
150°	1213.8	1212.9	1212.0	1211.1
152.5°	1239.7	1239.0	1238.3	1237.6
155°	1262.8	1262.5	1262.3	1262.1
157.5°	1283.5	1283.5	1283.5	1283.5
160°	1299.7	1300.4	1301.1	1301.8
162.5°	1315.4	1316.3	1317.2	1318.1
165°	1327.9	1329.0	1330.2	1331.3
167.5°	1339.1	1340.2	1341.4	1342.5
170°	1347.6	1349.0	1350.3	1351.7
172.5°	1353.7	1355.1	1356.4	1357.8
175°	1357.8	1359.2	1360.5	1361.9
177.5°	1360.2	1361.8	1363.4	1365.0
180°	1361.9	1361.9	1361.9	1361.9

(END OF REPORT)