

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033182

Luminaire Tested: S124DIW-B1020D470UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033182
REPORT IS A COMBINATION OF REPORTS P996847 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D470UB30-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6474.0 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75
1	103	98	94	91	97	93	90	87	84	81	79	75	73	71	67	65	64
2	94	86	80	75	89	82	76	72	74	69	66	66	63	60	59	57	55
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47
4	79	68	60	54	74	65	57	52	58	53	48	53	48	44	47	44	41
5	73	61	52	46	68	58	50	45	53	46	42	48	43	39	43	39	36
6	67	55	46	40	63	52	45	39	48	41	37	43	38	34	39	35	32
7	62	50	41	36	59	47	40	35	43	37	32	39	34	30	36	31	28
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23
10	50	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13526	13526	13526	13526
5°	13492	15517	13570	11660
10°	13391	18104	13493	10229
15°	13230	20870	13322	9153
20°	13058	22631	13153	8206
25°	12809	22372	12931	7507
30°	12564	18491	12717	7148
35°	12222	13779	12356	6930
40°	11820	10380	11935	6823
45°	11209	8331	11349	6677
50°	10479	7019	10631	6609
55°	9620	6108	9771	6531
60°	8787	5380	9043	6423
65°	8003	4629	8078	6155
70°	7081	3808	7235	5667
75°	6179	2926	6138	4816
80°	4861	1923	4804	3655
85°	3202	864	2998	2132

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 17489 cd/sqm

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	2.5
10°-20°	498.3	7.7
20°-30°	791.6	12.2
30°-40°	879.6	13.6
40°-50°	799.9	12.4
50°-60°	653.6	10.1
60°-70°	466.6	7.2
70°-80°	256.7	4.0
80°-90°	70.6	1.1
90°-100°	20.3	0.3
100°-110°	133.9	2.1
110°-120°	255.7	4.0
120°-130°	324.6	5.0
130°-140°	347.3	5.4
140°-150°	324.8	5.0
150°-160°	261.9	4.0
160°-170°	168.9	2.6
170°-180°	58.2	0.9
0°-30°	1451.2	22.4
0°-40°	2330.8	36.0
0°-60°	3784.3	58.5
0°-90°	4578.3	70.7
90°-120°	410.0	6.3
90°-150°	1406.7	21.7
90°-180°	1896.0	29.3
0°-180°	6474.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1659	1659	1659	1659	1659	
5°	1652	1946	1661	1462	1652	157
15°	1578	2673	1589	1172	1578	445
25°	1440	2838	1454	952	1440	664
35°	1249	1678	1263	844	1249	780
45°	996	941	1009	754	996	768
55°	701	616	712	658	701	630
65°	437	396	441	526	437	432
75°	214	198	213	326	214	225
85°	44	41	41	102	44	51
90°	1	14	1	14	1	4
95°	25	13	25	13	25	31
105°	138	131	138	131	138	144
115°	258	259	258	259	258	253
125°	362	365	362	365	362	323
135°	449	452	449	452	449	346
145°	518	520	518	520	518	324
155°	568	567	568	567	568	262
165°	599	596	599	596	599	169
175°	613	609	613	609	613	58
180°	613	613	613	613	613	

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1658.7	1675.2	1682.0	1687.5	1705.4	1710.9	1712.3	1720.5	1727.4	1728.8	1728.8
5°	1651.8	1677.9	1698.5	1717.8	1746.6	1759.0	1774.1	1790.6	1812.6	1826.3	1833.2
7.5°	1640.8	1679.3	1710.9	1743.9	1783.7	1808.5	1822.2	1866.2	1896.4	1921.2	1951.4
10°	1624.3	1673.8	1719.1	1767.2	1823.6	1853.8	1884.0	1937.6	1980.2	2028.3	2066.8
12.5°	1599.6	1664.2	1719.1	1786.5	1856.6	1892.3	1928.0	2021.5	2070.9	2113.5	2182.3
15°	1577.6	1642.2	1720.5	1789.2	1875.8	1929.4	1981.6	2042.1	2120.4	2212.5	2278.4
17.5°	1552.9	1633.9	1706.8	1803.0	1899.2	1950.0	1992.6	2086.1	2196.0	2286.7	2347.2
20°	1518.5	1601.0	1697.2	1798.8	1912.9	1952.8	2009.1	2134.2	2233.1	2322.4	2421.4
22.5°	1478.7	1574.9	1676.5	1774.1	1892.3	1976.1	2038.0	2147.9	2267.5	2370.5	2481.8
25°	1440.2	1544.6	1633.9	1767.2	1892.3	1948.6	2018.7	2149.3	2279.8	2404.9	2518.9
27.5°	1399.0	1496.5	1617.5	1723.3	1864.8	1926.6	2002.2	2145.1	2283.9	2409.0	2531.3
30°	1353.6	1458.0	1558.4	1683.4	1820.8	1900.5	1970.6	2125.9	2267.5	2398.0	2512.1
32.5°	1302.8	1401.7	1508.9	1627.1	1771.4	1852.4	1940.4	2099.8	2251.0	2363.6	2451.6
35°	1249.2	1349.5	1442.9	1563.9	1712.3	1793.4	1878.6	2054.5	2204.2	2296.3	2347.2
37.5°	1190.1	1284.9	1377.0	1496.5	1644.9	1731.5	1818.1	1988.5	2130.0	2207.0	2193.2
40°	1133.7	1218.9	1304.1	1416.8	1572.1	1664.2	1739.8	1911.5	2035.2	2068.2	2022.8
42.5°	1069.1	1142.0	1224.4	1339.9	1491.0	1577.6	1672.4	1829.1	1921.2	1907.4	1830.5
45°	996.3	1060.9	1143.3	1251.9	1405.8	1495.1	1574.9	1723.3	1790.6	1756.2	1616.1
47.5°	926.2	989.4	1056.8	1165.3	1315.1	1390.7	1471.8	1605.1	1643.6	1570.7	1430.6
50°	850.6	902.9	972.9	1076.0	1216.2	1295.9	1363.2	1470.4	1484.2	1394.8	1249.2
52.5°	777.8	821.8	889.1	990.8	1121.4	1184.6	1250.5	1345.4	1334.4	1242.3	1102.1
55°	700.8	742.1	803.9	897.4	1012.8	1073.3	1129.6	1213.4	1190.1	1095.2	972.9
57.5°	636.3	665.1	725.6	812.2	907.0	972.9	1021.0	1087.0	1051.3	956.5	842.4
60°	562.1	597.8	648.6	718.7	812.2	856.1	898.7	942.7	918.0	827.3	725.6
62.5°	494.7	522.2	566.2	633.5	706.3	746.2	791.5	819.0	794.3	710.5	625.3
65°	437.0	459.0	493.3	548.3	618.4	651.4	677.5	703.6	683.0	604.7	542.8
67.5°	373.8	393.0	421.9	465.9	525.0	548.3	573.0	590.9	567.6	515.3	454.9
70°	317.4	331.2	358.7	391.7	432.9	454.9	475.5	493.3	472.7	428.8	383.4
72.5°	259.7	270.7	295.5	318.8	355.9	371.0	386.2	399.9	393.0	351.8	314.7
75°	214.4	218.5	235.0	254.2	277.6	294.1	305.1	313.3	307.8	274.8	251.5
77.5°	162.2	167.7	180.0	195.1	215.8	225.4	232.2	240.5	233.6	207.5	191.0
80°	118.2	119.6	126.4	140.2	153.9	155.3	162.2	173.2	169.0	151.2	138.8
82.5°	75.6	79.7	82.5	90.7	100.3	103.1	107.2	109.9	108.6	97.6	93.4
85°	44.0	44.0	46.7	52.2	55.0	59.1	60.5	61.8	64.6	57.7	53.6
87.5°	19.2	20.6	20.6	22.0	24.7	24.7	26.1	27.5	28.9	27.5	23.4
90°	1.4	2.5	3.6	4.7	5.8	6.4	6.8	7.6	8.5	9.3	10.1
92.5°	6.9	6.7	6.5	6.3	6.1	6.0	6.4	7.2	8.0	8.8	9.6
95°	25.2	21.7	18.3	14.8	11.3	9.6	9.7	9.8	9.9	10.0	10.1
97.5°	48.1	50.3	52.6	54.8	57.1	58.2	52.9	42.2	31.5	20.8	10.1
100°	75.1	76.9	78.8	80.6	82.5	83.4	76.4	62.3	48.3	34.2	20.2
102.5°	105.4	106.6	107.8	109.1	110.3	110.9	111.5	112.7	114.0	115.2	116.4
105°	137.9	138.5	139.1	139.8	140.4	140.7	141.0	141.5	142.0	142.5	143.0
107.5°	167.7	168.0	168.3	168.6	168.9	169.1	169.5	170.2	170.9	171.6	172.3
110°	198.0	198.3	198.6	198.9	199.2	199.3	199.6	200.2	200.9	201.5	202.1

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	227.3	227.9	228.5	229.1	229.7	230.0	230.1	230.3	230.5	230.7	230.9
115°	257.5	257.8	258.1	258.4	258.7	258.9	258.8	258.7	258.6	258.5	258.4
117.5°	284.6	285.0	285.4	285.8	286.2	286.4	286.6	286.9	287.2	287.5	287.8
120°	312.0	312.4	312.8	313.3	313.7	313.9	313.8	313.7	313.6	313.5	313.4
122.5°	337.7	337.9	338.1	338.3	338.5	338.6	338.7	338.9	339.1	339.3	339.5
125°	362.0	362.4	362.8	363.2	363.6	363.8	363.7	363.5	363.3	363.1	362.9
127.5°	385.4	385.5	385.6	385.7	385.8	385.8	386.1	386.6	387.1	387.6	388.1
130°	407.8	407.9	408.0	408.1	408.2	408.3	408.5	408.8	409.1	409.4	409.7
132.5°	428.4	428.6	428.8	429.1	429.3	429.4	429.6	430.0	430.4	430.8	431.2
135°	449.1	449.0	448.9	448.8	448.7	448.6	448.8	449.2	449.6	450.0	450.4
137.5°	467.4	467.4	467.4	467.4	467.4	467.4	467.7	468.2	468.7	469.2	469.7
140°	485.3	485.5	485.7	485.9	486.1	486.2	486.3	486.5	486.7	486.9	487.1
142.5°	501.3	501.7	502.1	502.5	502.9	503.1	503.2	503.3	503.4	503.5	503.6
145°	517.8	518.1	518.4	518.7	519.0	519.2	519.2	519.2	519.2	519.2	519.2
147.5°	530.6	531.2	531.8	532.5	533.1	533.4	533.3	533.2	533.1	533.0	532.9
150°	544.8	545.2	545.6	546.1	546.5	546.7	546.6	546.5	546.4	546.3	546.2
152.5°	556.7	557.0	557.3	557.6	557.9	558.1	558.0	557.8	557.6	557.4	557.2
155°	567.7	567.8	567.9	568.0	568.1	568.2	568.0	567.7	567.4	567.1	566.8
157.5°	577.4	577.4	577.4	577.4	577.4	577.4	577.2	576.8	576.3	575.9	575.5
160°	585.6	585.3	585.0	584.7	584.4	584.2	584.2	584.1	584.0	583.9	583.8
162.5°	592.9	592.5	592.1	591.7	591.3	591.1	591.0	590.9	590.8	590.7	590.6
165°	598.9	598.4	597.9	597.4	596.9	596.6	596.6	596.6	596.6	596.6	596.6
167.5°	603.9	603.4	602.9	602.4	601.9	601.6	601.6	601.5	601.4	601.3	601.2
170°	608.1	607.5	606.9	606.2	605.6	605.3	605.4	605.5	605.6	605.7	605.8
172.5°	610.8	610.2	609.6	609.0	608.4	608.1	608.1	608.2	608.3	608.4	608.5
175°	612.6	612.0	611.4	610.8	610.2	609.9	610.0	610.1	610.2	610.3	610.4
177.5°	614.0	613.3	612.6	611.9	611.2	610.8	610.9	611.1	611.3	611.5	611.7
180°	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1732.9	1757.6	1768.6	1771.4	1786.5	1776.9	1781.0	1779.6	1790.6	1792.0	1792.0
5°	1859.3	1888.2	1897.8	1911.5	1932.1	1937.6	1933.5	1941.8	1956.9	1945.9	1962.4
7.5°	1992.6	2024.2	2046.2	2076.4	2083.3	2101.2	2112.2	2121.8	2124.5	2125.9	2128.7
10°	2116.3	2156.1	2186.4	2237.2	2248.2	2257.8	2305.9	2286.7	2311.4	2303.2	2305.9
12.5°	2216.6	2294.9	2319.7	2404.9	2413.1	2446.1	2443.4	2473.6	2479.1	2490.1	2479.1
15°	2348.5	2439.2	2479.1	2527.2	2554.7	2593.1	2600.0	2641.2	2657.7	2672.8	2657.7
17.5°	2469.5	2517.6	2619.3	2657.7	2675.6	2696.2	2748.4	2763.5	2788.3	2778.7	2806.1
20°	2529.9	2598.6	2705.8	2771.8	2799.3	2818.5	2862.5	2885.9	2895.5	2895.5	2898.2
22.5°	2583.5	2682.5	2762.2	2837.8	2862.5	2876.2	2902.3	2920.2	2924.3	2927.1	2929.8
25°	2631.6	2720.9	2785.5	2828.1	2837.8	2837.8	2852.9	2841.9	2824.0	2837.8	2846.0
27.5°	2631.6	2694.8	2723.7	2738.8	2738.8	2701.7	2679.7	2634.4	2595.9	2584.9	2609.6
30°	2587.6	2616.5	2576.7	2539.5	2510.7	2486.0	2399.4	2330.7	2316.9	2307.3	2344.4
32.5°	2486.0	2448.9	2370.5	2263.3	2220.7	2164.4	2097.1	2044.8	2013.2	2002.2	1994.0
35°	2305.9	2209.7	2108.0	1963.8	1933.5	1862.1	1770.0	1731.5	1679.3	1677.9	1695.8
37.5°	2109.4	1961.0	1851.1	1713.6	1671.0	1595.5	1508.9	1469.0	1433.3	1405.8	1438.8
40°	1879.9	1750.7	1583.1	1470.4	1409.9	1370.1	1297.3	1253.3	1236.8	1223.1	1243.7
42.5°	1665.5	1524.0	1393.5	1278.0	1228.5	1183.2	1135.1	1092.5	1080.1	1078.8	1093.9
45°	1452.5	1313.7	1192.8	1093.9	1062.3	1034.8	988.1	975.7	955.1	941.3	948.2
47.5°	1282.1	1139.2	1038.9	963.3	935.8	912.5	882.2	861.6	843.8	838.3	846.5
50°	1114.5	1018.3	915.2	852.0	831.4	809.4	786.1	766.8	758.6	753.1	758.6
52.5°	979.8	876.7	806.7	755.8	735.2	718.7	702.2	694.0	683.0	685.7	691.2
55°	858.9	768.2	709.1	672.0	659.6	652.8	632.1	622.5	618.4	615.6	618.4
57.5°	744.8	678.9	634.9	603.3	586.8	582.7	566.2	566.2	562.1	557.9	559.3
60°	654.1	597.8	555.2	530.4	527.7	520.8	509.8	508.5	498.8	503.0	504.3
62.5°	562.1	516.7	487.8	472.7	463.1	460.4	453.5	452.1	448.0	449.4	446.6
65°	489.2	452.1	423.3	410.9	406.8	405.4	399.9	395.8	393.0	395.8	393.0
67.5°	416.4	391.7	369.7	357.3	351.8	350.4	346.3	343.6	344.9	340.8	343.6
70°	347.7	322.9	309.2	302.3	299.6	295.5	295.5	295.5	295.5	292.7	291.3
72.5°	292.7	268.0	258.4	254.2	251.5	250.1	246.0	247.4	246.0	244.6	250.1
75°	232.2	217.1	207.5	203.4	206.1	202.0	197.9	200.6	196.5	197.9	203.4
77.5°	175.9	169.0	163.5	160.8	158.0	155.3	155.3	152.5	152.5	152.5	152.5
80°	127.8	126.4	116.8	115.4	115.4	112.7	112.7	112.7	112.7	111.3	112.7
82.5°	85.2	83.8	81.1	79.7	77.0	78.3	78.3	75.6	75.6	74.2	75.6
85°	49.5	49.5	46.7	45.3	44.0	45.3	42.6	41.2	42.6	41.2	42.6
87.5°	23.4	20.6	22.0	20.6	17.9	19.2	16.5	17.9	16.5	15.1	17.9
90°	10.7	11.3	11.9	12.5	12.8	12.9	13.1	13.3	13.5	13.7	13.5
92.5°	10.2	10.8	11.5	12.1	12.4	12.4	12.4	12.4	12.4	12.4	12.4
95°	10.7	11.3	11.9	12.5	12.8	12.9	13.0	13.1	13.2	13.3	13.2
97.5°	10.6	11.1	11.6	12.1	12.4	12.4	12.5	12.6	12.7	12.8	12.7
100°	18.5	16.7	15.0	13.3	12.4	12.4	12.5	12.6	12.7	12.8	12.7
102.5°	93.5	70.6	47.7	24.8	13.3	13.3	13.3	13.3	13.3	13.3	13.3
105°	143.9	144.8	145.7	146.6	147.1	145.3	141.6	137.9	134.3	130.6	134.3
107.5°	172.8	173.3	173.8	174.3	174.6	174.8	175.2	175.6	176.0	176.4	176.0
110°	202.3	202.5	202.7	202.9	203.0	203.2	203.5	203.8	204.1	204.4	204.1

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	230.8	230.7	230.6	230.5	230.5	230.7	231.1	231.5	231.9	232.3	231.9
115°	258.6	258.8	259.1	259.3	259.4	259.4	259.4	259.4	259.4	259.4	259.4
117.5°	287.7	287.6	287.5	287.4	287.3	287.3	287.3	287.3	287.3	287.3	287.3
120°	313.6	313.8	314.0	314.2	314.3	314.2	314.0	313.8	313.6	313.4	313.6
122.5°	339.6	339.7	339.8	339.9	340.0	339.9	339.7	339.5	339.3	339.1	339.3
125°	363.2	363.5	363.8	364.1	364.3	364.3	364.4	364.5	364.6	364.7	364.6
127.5°	388.0	387.9	387.8	387.7	387.7	387.6	387.5	387.4	387.3	387.2	387.3
130°	409.8	409.9	410.0	410.1	410.1	410.1	410.1	410.1	410.1	410.1	410.1
132.5°	431.3	431.4	431.5	431.6	431.6	431.6	431.5	431.4	431.3	431.2	431.3
135°	450.6	450.8	451.0	451.2	451.3	451.4	451.6	451.9	452.1	452.3	452.1
137.5°	469.9	470.1	470.3	470.5	470.6	470.5	470.4	470.3	470.2	470.1	470.2
140°	487.4	487.7	488.0	488.3	488.5	488.5	488.6	488.7	488.8	488.9	488.8
142.5°	503.8	504.0	504.2	504.4	504.5	504.5	504.5	504.5	504.5	504.5	504.5
145°	519.3	519.4	519.5	519.6	519.6	519.7	519.9	520.1	520.3	520.5	520.3
147.5°	533.0	533.1	533.2	533.3	533.4	533.4	533.5	533.6	533.7	533.8	533.7
150°	546.2	546.2	546.2	546.2	546.2	546.3	546.4	546.5	546.6	546.7	546.6
152.5°	557.4	557.6	557.8	558.0	558.1	558.1	558.0	557.9	557.8	557.7	557.8
155°	567.2	567.6	568.1	568.5	568.7	568.5	568.2	567.9	567.6	567.3	567.6
157.5°	576.0	576.5	577.0	577.5	577.8	577.5	577.0	576.5	576.0	575.5	576.0
160°	584.4	585.0	585.6	586.2	586.5	586.2	585.6	585.0	584.4	583.8	584.4
162.5°	591.2	591.8	592.5	593.1	593.4	593.0	592.3	591.6	590.9	590.2	590.9
165°	597.4	598.2	599.1	599.9	600.3	599.8	598.9	598.0	597.0	596.1	597.0
167.5°	602.1	603.0	603.9	604.8	605.3	604.8	603.8	602.7	601.7	600.7	601.7
170°	606.6	607.4	608.2	609.0	609.4	608.9	607.9	606.9	605.9	604.9	605.9
172.5°	609.3	610.1	611.0	611.8	612.2	611.6	610.5	609.4	608.2	607.1	608.2
175°	611.3	612.2	613.1	614.0	614.5	613.9	612.7	611.4	610.2	609.0	610.2
177.5°	612.5	613.3	614.2	615.0	615.4	614.8	613.6	612.3	611.1	609.9	611.1
180°	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1789.2	1785.1	1779.6	1779.6	1772.7	1772.7	1761.7	1742.5	1726.0	1720.5	1723.3
5°	1941.8	1943.1	1934.9	1928.0	1915.7	1906.0	1888.2	1853.8	1842.8	1820.8	1805.7
7.5°	2116.3	2110.8	2095.7	2084.7	2081.9	2059.9	2021.5	1980.2	1947.3	1925.3	1893.7
10°	2312.8	2290.8	2268.8	2262.0	2245.5	2208.4	2164.4	2119.0	2073.7	2025.6	1972.0
12.5°	2477.7	2435.1	2433.7	2417.2	2385.6	2365.0	2312.8	2248.2	2169.9	2116.3	2055.8
15°	2655.0	2615.1	2582.1	2551.9	2536.8	2476.3	2432.4	2351.3	2257.8	2200.1	2158.9
17.5°	2781.4	2763.5	2707.2	2693.5	2672.8	2602.8	2532.7	2453.0	2371.9	2290.8	2179.5
20°	2883.1	2872.1	2835.0	2815.8	2782.8	2727.8	2642.6	2550.5	2457.1	2341.7	2237.2
22.5°	2927.1	2913.3	2883.1	2866.6	2846.0	2799.3	2726.4	2622.0	2499.7	2396.6	2285.3
25°	2840.5	2865.2	2857.0	2850.1	2841.9	2814.4	2759.4	2667.4	2547.8	2431.0	2292.2
27.5°	2645.4	2688.0	2729.2	2734.7	2748.4	2759.4	2737.4	2671.5	2571.2	2447.5	2294.9
30°	2382.9	2402.1	2486.0	2510.7	2529.9	2600.0	2641.2	2624.8	2547.8	2436.5	2296.3
32.5°	2046.2	2097.1	2182.3	2241.3	2293.6	2371.9	2479.1	2521.7	2494.2	2403.5	2264.7
35°	1727.4	1787.9	1886.8	1962.4	2014.6	2125.9	2252.3	2344.4	2378.8	2333.4	2209.7
37.5°	1466.3	1539.1	1627.1	1655.9	1716.4	1853.8	2028.3	2156.1	2240.0	2244.1	2147.9
40°	1269.8	1306.9	1377.0	1420.9	1480.0	1595.5	1765.9	1934.9	2061.3	2103.9	2053.1
42.5°	1103.5	1132.4	1184.6	1238.2	1291.8	1379.7	1536.4	1694.4	1864.8	1950.0	1948.6
45°	971.6	1001.8	1037.5	1081.5	1118.6	1213.4	1337.1	1499.3	1646.3	1778.2	1811.2
47.5°	856.1	882.2	926.2	945.5	970.2	1059.5	1166.7	1317.9	1470.4	1621.6	1660.1
50°	770.9	792.9	823.2	835.5	863.0	929.0	1016.9	1139.2	1308.3	1447.0	1518.5
52.5°	694.0	710.5	733.8	743.5	762.7	812.2	891.9	988.1	1128.2	1271.1	1371.5
55°	628.0	639.0	655.5	666.5	680.2	724.2	783.3	869.9	990.8	1114.5	1212.1
57.5°	566.2	574.4	590.9	596.4	607.4	641.8	683.0	755.8	867.1	977.1	1071.9
60°	508.5	514.0	523.6	535.9	544.2	567.6	606.0	666.5	755.8	856.1	933.1
62.5°	453.5	461.7	464.5	470.0	476.9	498.8	529.1	573.0	651.4	733.8	814.9
65°	397.1	404.0	409.5	410.9	417.8	434.3	461.7	500.2	551.1	622.5	698.1
67.5°	344.9	349.1	351.8	357.3	364.2	372.4	394.4	423.3	470.0	527.7	588.2
70°	296.8	296.8	301.0	302.3	310.6	320.2	329.8	357.3	398.5	445.2	486.5
72.5°	244.6	251.5	250.1	257.0	255.6	262.5	274.8	292.7	322.9	360.0	399.9
75°	199.3	203.4	203.4	203.4	206.1	211.6	218.5	235.0	258.4	288.6	311.9
77.5°	155.3	158.0	158.0	158.0	159.4	164.9	171.8	182.8	199.3	217.1	230.9
80°	111.3	114.1	114.1	116.8	116.8	118.2	125.1	130.6	138.8	152.5	166.3
82.5°	75.6	77.0	79.7	79.7	78.3	81.1	82.5	87.9	96.2	98.9	108.6
85°	41.2	42.6	44.0	44.0	45.3	48.1	46.7	52.2	52.2	57.7	60.5
87.5°	16.5	19.2	19.2	17.9	19.2	19.2	19.2	22.0	23.4	24.7	23.4
90°	13.3	13.1	12.9	12.8	12.5	11.9	11.3	10.7	10.1	9.3	8.5
92.5°	12.4	12.4	12.4	12.4	12.1	11.5	10.8	10.2	9.6	8.8	8.0
95°	13.1	13.0	12.9	12.8	12.5	11.9	11.3	10.7	10.1	10.0	9.9
97.5°	12.6	12.5	12.4	12.4	12.1	11.6	11.1	10.6	10.1	20.8	31.5
100°	12.6	12.5	12.4	12.4	13.3	15.0	16.7	18.5	20.2	34.2	48.3
102.5°	13.3	13.3	13.3	13.3	24.8	47.7	70.6	93.5	116.4	115.2	114.0
105°	137.9	141.6	145.3	147.1	146.6	145.7	144.8	143.9	143.0	142.5	142.0
107.5°	175.6	175.2	174.8	174.6	174.3	173.8	173.3	172.8	172.3	171.6	170.9
110°	203.8	203.5	203.2	203.0	202.9	202.7	202.5	202.3	202.1	201.5	200.9

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	231.5	231.1	230.7	230.5	230.5	230.6	230.7	230.8	230.9	230.7	230.5
115°	259.4	259.4	259.4	259.4	259.3	259.1	258.8	258.6	258.4	258.5	258.6
117.5°	287.3	287.3	287.3	287.3	287.4	287.5	287.6	287.7	287.8	287.5	287.2
120°	313.8	314.0	314.2	314.3	314.2	314.0	313.8	313.6	313.4	313.5	313.6
122.5°	339.5	339.7	339.9	340.0	339.9	339.8	339.7	339.6	339.5	339.3	339.1
125°	364.5	364.4	364.3	364.3	364.1	363.8	363.5	363.2	362.9	363.1	363.3
127.5°	387.4	387.5	387.6	387.7	387.7	387.8	387.9	388.0	388.1	387.6	387.1
130°	410.1	410.1	410.1	410.1	410.1	410.0	409.9	409.8	409.7	409.4	409.1
132.5°	431.4	431.5	431.6	431.6	431.6	431.5	431.4	431.3	431.2	430.8	430.4
135°	451.9	451.6	451.4	451.3	451.2	451.0	450.8	450.6	450.4	450.0	449.6
137.5°	470.3	470.4	470.5	470.6	470.5	470.3	470.1	469.9	469.7	469.2	468.7
140°	488.7	488.6	488.5	488.5	488.3	488.0	487.7	487.4	487.1	486.9	486.7
142.5°	504.5	504.5	504.5	504.5	504.4	504.2	504.0	503.8	503.6	503.5	503.4
145°	520.1	519.9	519.7	519.6	519.6	519.5	519.4	519.3	519.2	519.2	519.2
147.5°	533.6	533.5	533.4	533.4	533.3	533.2	533.1	533.0	532.9	533.0	533.1
150°	546.5	546.4	546.3	546.2	546.2	546.2	546.2	546.2	546.2	546.3	546.4
152.5°	557.9	558.0	558.1	558.1	558.0	557.8	557.6	557.4	557.2	557.4	557.6
155°	567.9	568.2	568.5	568.7	568.5	568.1	567.6	567.2	566.8	567.1	567.4
157.5°	576.5	577.0	577.5	577.8	577.5	577.0	576.5	576.0	575.5	575.9	576.3
160°	585.0	585.6	586.2	586.5	586.2	585.6	585.0	584.4	583.8	583.9	584.0
162.5°	591.6	592.3	593.0	593.4	593.1	592.5	591.8	591.2	590.6	590.7	590.8
165°	598.0	598.9	599.8	600.3	599.9	599.1	598.2	597.4	596.6	596.6	596.6
167.5°	602.7	603.8	604.8	605.3	604.8	603.9	603.0	602.1	601.2	601.3	601.4
170°	606.9	607.9	608.9	609.4	609.0	608.2	607.4	606.6	605.8	605.7	605.6
172.5°	609.4	610.5	611.6	612.2	611.8	611.0	610.1	609.3	608.5	608.4	608.3
175°	611.4	612.7	613.9	614.5	614.0	613.1	612.2	611.3	610.4	610.3	610.2
177.5°	612.3	613.6	614.8	615.4	615.0	614.2	613.3	612.5	611.7	611.5	611.3
180°	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1710.9	1705.4	1701.3	1701.3	1688.9	1676.5	1669.7	1666.9	1664.2	1653.2	1638.1
5°	1781.0	1763.1	1750.7	1738.4	1717.8	1695.8	1673.8	1661.4	1643.6	1618.8	1601.0
7.5°	1859.3	1816.7	1803.0	1787.9	1746.6	1709.5	1679.3	1653.2	1624.3	1592.7	1561.1
10°	1925.3	1879.9	1849.7	1823.6	1770.0	1720.5	1675.2	1636.7	1599.6	1558.4	1519.9
12.5°	1988.5	1923.9	1892.3	1853.8	1797.5	1726.0	1666.9	1618.8	1563.9	1521.3	1474.5
15°	2076.4	1967.9	1915.7	1890.9	1815.3	1731.5	1660.1	1588.6	1543.2	1478.7	1437.4
17.5°	2090.2	2002.2	1967.9	1904.7	1814.0	1719.1	1636.7	1565.2	1496.5	1438.8	1385.2
20°	2138.3	2022.8	1967.9	1928.0	1808.5	1712.3	1621.6	1529.5	1463.5	1401.7	1341.2
22.5°	2168.5	2038.0	1980.2	1917.0	1803.0	1687.5	1580.3	1500.6	1419.6	1356.3	1308.3
25°	2160.3	2029.7	1965.1	1906.0	1767.2	1651.8	1555.6	1453.9	1378.3	1309.6	1246.4
27.5°	2156.1	2009.1	1940.4	1874.4	1743.9	1622.9	1502.0	1419.6	1335.7	1256.0	1209.3
30°	2145.1	1983.0	1903.3	1831.8	1695.8	1569.4	1466.3	1370.1	1286.3	1213.4	1151.6
32.5°	2108.0	1939.0	1862.1	1785.1	1643.6	1517.1	1412.7	1323.4	1239.5	1164.0	1104.9
35°	2058.6	1886.8	1803.0	1721.9	1580.3	1452.5	1356.3	1262.9	1184.6	1111.7	1055.4
37.5°	2009.1	1826.3	1748.0	1654.6	1524.0	1390.7	1291.8	1207.9	1135.1	1059.5	997.7
40°	1937.6	1754.9	1668.3	1588.6	1436.1	1311.0	1220.3	1144.7	1073.3	1001.8	949.6
42.5°	1840.1	1676.5	1587.2	1499.3	1356.3	1232.7	1144.7	1077.4	1010.0	951.0	893.2
45°	1741.1	1581.7	1502.0	1423.7	1268.4	1151.6	1070.5	1008.7	952.3	887.7	841.0
47.5°	1621.6	1486.9	1407.2	1330.2	1183.2	1066.4	992.2	934.5	882.2	828.7	784.7
50°	1499.3	1382.5	1309.6	1229.9	1089.8	983.9	911.1	863.0	820.4	769.6	733.8
52.5°	1367.3	1265.7	1203.8	1126.9	1003.2	905.6	831.4	783.3	747.6	710.5	678.9
55°	1227.2	1153.0	1087.0	1025.2	908.4	820.4	754.4	711.8	687.1	652.8	625.3
57.5°	1100.7	1029.3	989.4	919.3	817.7	731.1	678.9	643.1	614.3	593.7	571.7
60°	968.8	911.1	867.1	816.3	727.0	654.1	599.2	578.5	548.3	533.2	523.6
62.5°	842.4	801.2	759.9	721.5	641.8	573.0	531.8	505.7	487.8	472.7	464.5
65°	722.8	684.4	655.5	621.1	555.2	500.2	461.7	441.1	423.3	419.1	409.5
67.5°	606.0	589.5	557.9	530.4	474.1	431.5	402.6	376.5	366.9	362.8	354.5
70°	507.1	487.8	463.1	439.7	397.1	360.0	333.9	324.3	310.6	309.2	299.6
72.5°	417.8	394.4	376.5	358.7	327.1	294.1	280.3	266.6	259.7	254.2	250.1
75°	331.2	314.7	302.3	287.2	259.7	237.7	218.5	213.0	208.9	207.5	204.8
77.5°	247.4	236.4	230.9	215.8	196.5	177.3	169.0	160.8	160.8	158.0	159.4
80°	175.9	169.0	162.2	153.9	137.4	129.2	122.3	116.8	114.1	112.7	114.1
82.5°	111.3	107.2	105.8	100.3	89.3	85.2	79.7	75.6	75.6	75.6	75.6
85°	61.8	61.8	61.8	53.6	49.5	45.3	42.6	41.2	41.2	41.2	42.6
87.5°	26.1	26.1	22.0	22.0	20.6	17.9	16.5	16.5	17.9	17.9	19.2
90°	7.6	6.8	6.4	5.8	4.7	3.6	2.5	1.4	2.5	3.6	4.7
92.5°	7.2	6.4	6.0	6.1	6.3	6.5	6.7	6.9	6.7	6.5	6.3
95°	9.8	9.7	9.6	11.3	14.8	18.3	21.7	25.2	21.7	18.3	14.8
97.5°	42.2	52.9	58.2	57.1	54.8	52.6	50.3	48.1	50.3	52.6	54.8
100°	62.3	76.4	83.4	82.5	80.6	78.8	76.9	75.1	76.9	78.8	80.6
102.5°	112.7	111.5	110.9	110.3	109.1	107.8	106.6	105.4	106.6	107.8	109.1
105°	141.5	141.0	140.7	140.4	139.8	139.1	138.5	137.9	138.5	139.1	139.8
107.5°	170.2	169.5	169.1	168.9	168.6	168.3	168.0	167.7	168.0	168.3	168.6
110°	200.2	199.6	199.3	199.2	198.9	198.6	198.3	198.0	198.3	198.6	198.9

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	230.3	230.1	230.0	229.7	229.1	228.5	227.9	227.3	227.9	228.5	229.1
115°	258.7	258.8	258.9	258.7	258.4	258.1	257.8	257.5	257.8	258.1	258.4
117.5°	286.9	286.6	286.4	286.2	285.8	285.4	285.0	284.6	285.0	285.4	285.8
120°	313.7	313.8	313.9	313.7	313.3	312.8	312.4	312.0	312.4	312.8	313.3
122.5°	338.9	338.7	338.6	338.5	338.3	338.1	337.9	337.7	337.9	338.1	338.3
125°	363.5	363.7	363.8	363.6	363.2	362.8	362.4	362.0	362.4	362.8	363.2
127.5°	386.6	386.1	385.8	385.8	385.7	385.6	385.5	385.4	385.5	385.6	385.7
130°	408.8	408.5	408.3	408.2	408.1	408.0	407.9	407.8	407.9	408.0	408.1
132.5°	430.0	429.6	429.4	429.3	429.1	428.8	428.6	428.4	428.6	428.8	429.1
135°	449.2	448.8	448.6	448.7	448.8	448.9	449.0	449.1	449.0	448.9	448.8
137.5°	468.2	467.7	467.4	467.4	467.4	467.4	467.4	467.4	467.4	467.4	467.4
140°	486.5	486.3	486.2	486.1	485.9	485.7	485.5	485.3	485.5	485.7	485.9
142.5°	503.3	503.2	503.1	502.9	502.5	502.1	501.7	501.3	501.7	502.1	502.5
145°	519.2	519.2	519.2	519.0	518.7	518.4	518.1	517.8	518.1	518.4	518.7
147.5°	533.2	533.3	533.4	533.1	532.5	531.8	531.2	530.6	531.2	531.8	532.5
150°	546.5	546.6	546.7	546.5	546.1	545.6	545.2	544.8	545.2	545.6	546.1
152.5°	557.8	558.0	558.1	557.9	557.6	557.3	557.0	556.7	557.0	557.3	557.6
155°	567.7	568.0	568.2	568.1	568.0	567.9	567.8	567.7	567.8	567.9	568.0
157.5°	576.8	577.2	577.4	577.4	577.4	577.4	577.4	577.4	577.4	577.4	577.4
160°	584.1	584.2	584.2	584.4	584.7	585.0	585.3	585.6	585.3	585.0	584.7
162.5°	590.9	591.0	591.1	591.3	591.7	592.1	592.5	592.9	592.5	592.1	591.7
165°	596.6	596.6	596.6	596.9	597.4	597.9	598.4	598.9	598.4	597.9	597.4
167.5°	601.5	601.6	601.6	601.9	602.4	602.9	603.4	603.9	603.4	602.9	602.4
170°	605.5	605.4	605.3	605.6	606.2	606.9	607.5	608.1	607.5	606.9	606.2
172.5°	608.2	608.1	608.1	608.4	609.0	609.6	610.2	610.8	610.2	609.6	609.0
175°	610.1	610.0	609.9	610.2	610.8	611.4	612.0	612.6	612.0	611.4	610.8
177.5°	611.1	610.9	610.8	611.2	611.9	612.6	613.3	614.0	613.3	612.6	611.9
180°	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1633.9	1628.4	1631.2	1617.5	1605.1	1587.2	1572.1	1569.4	1566.6	1574.9	1569.4
5°	1587.2	1580.3	1573.5	1557.0	1532.2	1517.1	1495.1	1493.8	1485.5	1473.2	1475.9
7.5°	1536.4	1532.2	1522.6	1496.5	1474.5	1448.4	1430.6	1415.4	1408.6	1397.6	1393.5
10°	1495.1	1480.0	1471.8	1442.9	1416.8	1389.3	1366.0	1355.0	1342.6	1333.0	1326.1
12.5°	1438.8	1434.7	1411.3	1388.0	1366.0	1334.4	1316.5	1284.9	1268.4	1276.6	1273.9
15°	1401.7	1382.5	1377.0	1344.0	1306.9	1286.3	1253.3	1232.7	1225.8	1213.4	1198.3
17.5°	1352.2	1339.9	1320.6	1290.4	1247.8	1218.9	1195.6	1176.3	1168.1	1151.6	1139.2
20°	1305.5	1284.9	1269.8	1242.3	1201.1	1164.0	1135.1	1122.7	1102.1	1088.4	1081.5
22.5°	1262.9	1247.8	1225.8	1184.6	1148.8	1113.1	1078.8	1060.9	1041.7	1033.4	1022.4
25°	1210.7	1185.9	1170.8	1125.5	1087.0	1058.1	1026.5	1003.2	992.2	978.4	975.7
27.5°	1159.8	1136.5	1118.6	1078.8	1032.0	994.9	975.7	959.2	940.0	940.0	933.1
30°	1109.0	1092.5	1065.0	1026.5	982.6	946.8	924.8	909.7	902.9	897.4	896.0
32.5°	1058.1	1036.2	1019.7	967.4	934.5	901.5	885.0	872.6	864.4	863.0	864.4
35°	1005.9	981.2	964.7	918.0	885.0	854.8	847.9	836.9	832.8	831.4	838.3
37.5°	951.0	931.7	911.1	872.6	835.5	817.7	803.9	799.8	798.4	806.7	809.4
40°	900.1	883.6	864.4	823.2	795.7	776.4	769.6	765.4	770.9	779.2	783.3
42.5°	852.0	828.7	813.5	776.4	751.7	740.7	732.5	732.5	738.0	747.6	754.4
45°	801.2	783.3	768.2	735.2	713.2	700.8	699.5	700.8	707.7	714.6	722.8
47.5°	751.7	733.8	717.3	689.9	670.6	663.7	662.4	663.7	674.7	684.4	694.0
50°	706.3	687.1	672.0	645.9	630.8	622.5	623.9	630.8	639.0	652.8	665.1
52.5°	652.8	639.0	625.3	601.9	588.2	582.7	586.8	592.3	607.4	617.0	632.1
55°	600.5	588.2	577.2	559.3	548.3	544.2	546.9	555.2	567.6	584.0	601.9
57.5°	552.4	538.7	527.7	515.3	503.0	504.3	505.7	516.7	531.8	546.9	567.6
60°	498.8	490.6	481.0	465.9	460.4	460.4	464.5	476.9	490.6	515.3	533.2
62.5°	450.7	439.7	432.9	423.3	415.0	416.4	426.0	437.0	453.5	474.1	497.5
65°	401.3	388.9	383.4	375.2	372.4	373.8	380.7	397.1	415.0	432.9	454.9
67.5°	346.3	342.2	336.7	328.4	331.2	332.6	339.4	353.2	372.4	390.3	415.0
70°	299.6	291.3	290.0	283.1	283.1	287.2	301.0	310.6	328.4	347.7	373.8
72.5°	250.1	243.2	243.2	237.7	241.9	246.0	252.9	266.6	283.1	302.3	324.3
75°	199.3	196.5	199.3	196.5	196.5	203.4	211.6	222.6	240.5	261.1	279.0
77.5°	153.9	153.9	152.5	156.7	156.7	160.8	171.8	182.8	196.5	213.0	232.2
80°	112.7	112.7	112.7	116.8	120.9	120.9	127.8	141.5	153.9	164.9	182.8
82.5°	77.0	77.0	77.0	79.7	85.2	85.2	93.4	101.7	115.4	125.1	133.3
85°	46.7	46.7	45.3	48.1	49.5	53.6	60.5	66.0	72.8	81.1	89.3
87.5°	20.6	20.6	22.0	23.4	24.7	27.5	30.2	33.0	39.9	42.6	46.7
90°	5.8	6.4	6.8	7.6	8.5	9.3	10.1	10.7	11.3	11.9	12.5
92.5°	6.1	6.0	6.4	7.2	8.0	8.8	9.6	10.2	10.8	11.5	12.1
95°	11.3	9.6	9.7	9.8	9.9	10.0	10.1	10.7	11.3	11.9	12.5
97.5°	57.1	58.2	52.9	42.2	31.5	20.8	10.1	10.6	11.1	11.6	12.1
100°	82.5	83.4	76.4	62.3	48.3	34.2	20.2	18.5	16.7	15.0	13.3
102.5°	110.3	110.9	111.5	112.7	114.0	115.2	116.4	93.5	70.6	47.7	24.8
105°	140.4	140.7	141.0	141.5	142.0	142.5	143.0	143.9	144.8	145.7	146.6
107.5°	168.9	169.1	169.5	170.2	170.9	171.6	172.3	172.8	173.3	173.8	174.3
110°	199.2	199.3	199.6	200.2	200.9	201.5	202.1	202.3	202.5	202.7	202.9

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	229.7	230.0	230.1	230.3	230.5	230.7	230.9	230.8	230.7	230.6	230.5
115°	258.7	258.9	258.8	258.7	258.6	258.5	258.4	258.6	258.8	259.1	259.3
117.5°	286.2	286.4	286.6	286.9	287.2	287.5	287.8	287.7	287.6	287.5	287.4
120°	313.7	313.9	313.8	313.7	313.6	313.5	313.4	313.6	313.8	314.0	314.2
122.5°	338.5	338.6	338.7	338.9	339.1	339.3	339.5	339.6	339.7	339.8	339.9
125°	363.6	363.8	363.7	363.5	363.3	363.1	362.9	363.2	363.5	363.8	364.1
127.5°	385.8	385.8	386.1	386.6	387.1	387.6	388.1	388.0	387.9	387.8	387.7
130°	408.2	408.3	408.5	408.8	409.1	409.4	409.7	409.8	409.9	410.0	410.1
132.5°	429.3	429.4	429.6	430.0	430.4	430.8	431.2	431.3	431.4	431.5	431.6
135°	448.7	448.6	448.8	449.2	449.6	450.0	450.4	450.6	450.8	451.0	451.2
137.5°	467.4	467.4	467.7	468.2	468.7	469.2	469.7	469.9	470.1	470.3	470.5
140°	486.1	486.2	486.3	486.5	486.7	486.9	487.1	487.4	487.7	488.0	488.3
142.5°	502.9	503.1	503.2	503.3	503.4	503.5	503.6	503.8	504.0	504.2	504.4
145°	519.0	519.2	519.2	519.2	519.2	519.2	519.2	519.3	519.4	519.5	519.6
147.5°	533.1	533.4	533.3	533.2	533.1	533.0	532.9	533.0	533.1	533.2	533.3
150°	546.5	546.7	546.6	546.5	546.4	546.3	546.2	546.2	546.2	546.2	546.2
152.5°	557.9	558.1	558.0	557.8	557.6	557.4	557.2	557.4	557.6	557.8	558.0
155°	568.1	568.2	568.0	567.7	567.4	567.1	566.8	567.2	567.6	568.1	568.5
157.5°	577.4	577.4	577.2	576.8	576.3	575.9	575.5	576.0	576.5	577.0	577.5
160°	584.4	584.2	584.2	584.1	584.0	583.9	583.8	584.4	585.0	585.6	586.2
162.5°	591.3	591.1	591.0	590.9	590.8	590.7	590.6	591.2	591.8	592.5	593.1
165°	596.9	596.6	596.6	596.6	596.6	596.6	596.6	597.4	598.2	599.1	599.9
167.5°	601.9	601.6	601.6	601.5	601.4	601.3	601.2	602.1	603.0	603.9	604.8
170°	605.6	605.3	605.4	605.5	605.6	605.7	605.8	606.6	607.4	608.2	609.0
172.5°	608.4	608.1	608.1	608.2	608.3	608.4	608.5	609.3	610.1	611.0	611.8
175°	610.2	609.9	610.0	610.1	610.2	610.3	610.4	611.3	612.2	613.1	614.0
177.5°	611.2	610.8	610.9	611.1	611.3	611.5	611.7	612.5	613.3	614.2	615.0
180°	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1565.2	1563.9	1557.0	1559.7	1551.5	1554.2	1558.4	1559.7	1565.2	1561.1	1559.7
5°	1469.0	1466.3	1462.2	1458.0	1456.7	1462.2	1452.5	1455.3	1458.0	1462.2	1467.7
7.5°	1390.7	1389.3	1385.2	1378.3	1375.6	1372.8	1374.2	1383.8	1382.5	1381.1	1390.7
10°	1319.2	1320.6	1312.4	1311.0	1302.8	1301.4	1302.8	1305.5	1309.6	1315.1	1316.5
12.5°	1245.0	1262.9	1247.8	1242.3	1229.9	1236.8	1239.5	1227.2	1234.0	1238.2	1258.8
15°	1198.3	1190.1	1180.5	1180.5	1175.0	1172.2	1165.3	1175.0	1180.5	1188.7	1185.9
17.5°	1133.7	1120.0	1114.5	1109.0	1110.4	1115.9	1100.7	1122.7	1122.7	1126.9	1120.0
20°	1077.4	1066.4	1059.5	1056.8	1052.6	1049.9	1048.5	1054.0	1062.3	1065.0	1071.9
22.5°	1018.3	1018.3	1007.3	1003.2	1000.4	996.3	1003.2	999.1	1004.6	1010.0	1021.0
25°	968.8	968.8	964.7	959.2	955.1	952.3	956.5	955.1	959.2	966.1	968.8
27.5°	929.0	924.8	923.5	922.1	920.7	922.1	920.7	924.8	929.0	930.3	927.6
30°	894.6	890.5	891.9	891.9	893.2	891.9	890.5	894.6	896.0	893.2	894.6
32.5°	863.0	863.0	865.8	867.1	867.1	868.5	869.9	867.1	868.5	864.4	865.8
35°	836.9	839.6	842.4	843.8	845.1	843.8	846.5	845.1	842.4	839.6	838.3
37.5°	810.8	813.5	819.0	820.4	824.5	825.9	823.2	823.2	821.8	816.3	813.5
40°	783.3	786.1	792.9	797.0	799.8	803.9	801.2	801.2	795.7	790.2	786.1
42.5°	757.2	762.7	769.6	773.7	779.2	779.2	779.2	776.4	769.6	764.1	759.9
45°	731.1	732.5	742.1	748.9	754.4	754.4	754.4	750.3	746.2	735.2	729.7
47.5°	702.2	706.3	717.3	724.2	729.7	731.1	731.1	727.0	718.7	709.1	702.2
50°	670.6	677.5	689.9	699.5	706.3	709.1	705.0	702.2	692.6	681.6	673.4
52.5°	640.4	648.6	663.7	672.0	681.6	683.0	681.6	677.5	666.5	651.4	644.5
55°	610.2	617.0	633.5	647.3	655.5	658.2	655.5	648.6	634.9	619.8	612.9
57.5°	577.2	586.8	604.7	618.4	628.0	629.4	626.6	619.8	608.8	589.5	579.9
60°	542.8	555.2	573.0	586.8	599.2	600.5	597.8	588.2	574.4	555.2	546.9
62.5°	508.5	518.1	538.7	553.8	563.4	570.3	564.8	555.2	541.4	522.2	509.8
65°	468.6	482.3	500.2	514.0	525.0	526.3	523.6	515.3	500.2	479.6	470.0
67.5°	430.1	439.7	457.6	475.5	479.6	483.7	479.6	471.4	459.0	441.1	427.4
70°	383.4	391.7	413.6	426.0	431.5	435.6	432.9	424.6	413.6	397.1	386.2
72.5°	336.7	343.6	364.2	373.8	384.8	383.4	382.0	376.5	361.4	350.4	343.6
75°	287.2	295.5	309.2	321.6	325.7	325.7	325.7	321.6	311.9	294.1	287.2
77.5°	241.9	246.0	257.0	263.8	268.0	269.3	268.0	261.1	255.6	243.2	239.1
80°	185.5	196.5	204.8	206.1	211.6	211.6	211.6	208.9	203.4	191.0	189.6
82.5°	140.2	142.9	151.2	155.3	158.0	156.7	156.7	151.2	149.8	142.9	140.2
85°	94.8	98.9	97.6	103.1	104.4	101.7	101.7	104.4	97.6	98.9	94.8
87.5°	52.2	52.2	55.0	53.6	59.1	59.1	56.3	57.7	55.0	53.6	52.2
90°	12.8	12.9	13.1	13.3	13.5	13.7	13.5	13.3	13.1	12.9	12.8
92.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
95°	12.8	12.9	13.0	13.1	13.2	13.3	13.2	13.1	13.0	12.9	12.8
97.5°	12.4	12.4	12.5	12.6	12.7	12.8	12.7	12.6	12.5	12.4	12.4
100°	12.4	12.4	12.5	12.6	12.7	12.8	12.7	12.6	12.5	12.4	12.4
102.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3
105°	147.1	145.3	141.6	137.9	134.3	130.6	134.3	137.9	141.6	145.3	147.1
107.5°	174.6	174.8	175.2	175.6	176.0	176.4	176.0	175.6	175.2	174.8	174.6
110°	203.0	203.2	203.5	203.8	204.1	204.4	204.1	203.8	203.5	203.2	203.0

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	230.5	230.7	231.1	231.5	231.9	232.3	231.9	231.5	231.1	230.7	230.5
115°	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4	259.4
117.5°	287.3	287.3	287.3	287.3	287.3	287.3	287.3	287.3	287.3	287.3	287.3
120°	314.3	314.2	314.0	313.8	313.6	313.4	313.6	313.8	314.0	314.2	314.3
122.5°	340.0	339.9	339.7	339.5	339.3	339.1	339.3	339.5	339.7	339.9	340.0
125°	364.3	364.3	364.4	364.5	364.6	364.7	364.6	364.5	364.4	364.3	364.3
127.5°	387.7	387.6	387.5	387.4	387.3	387.2	387.3	387.4	387.5	387.6	387.7
130°	410.1	410.1	410.1	410.1	410.1	410.1	410.1	410.1	410.1	410.1	410.1
132.5°	431.6	431.6	431.5	431.4	431.3	431.2	431.3	431.4	431.5	431.6	431.6
135°	451.3	451.4	451.6	451.9	452.1	452.3	452.1	451.9	451.6	451.4	451.3
137.5°	470.6	470.5	470.4	470.3	470.2	470.1	470.2	470.3	470.4	470.5	470.6
140°	488.5	488.5	488.6	488.7	488.8	488.9	488.8	488.7	488.6	488.5	488.5
142.5°	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5
145°	519.6	519.7	519.9	520.1	520.3	520.5	520.3	520.1	519.9	519.7	519.6
147.5°	533.4	533.4	533.5	533.6	533.7	533.8	533.7	533.6	533.5	533.4	533.4
150°	546.2	546.3	546.4	546.5	546.6	546.7	546.6	546.5	546.4	546.3	546.2
152.5°	558.1	558.1	558.0	557.9	557.8	557.7	557.8	557.9	558.0	558.1	558.1
155°	568.7	568.5	568.2	567.9	567.6	567.3	567.6	567.9	568.2	568.5	568.7
157.5°	577.8	577.5	577.0	576.5	576.0	575.5	576.0	576.5	577.0	577.5	577.8
160°	586.5	586.2	585.6	585.0	584.4	583.8	584.4	585.0	585.6	586.2	586.5
162.5°	593.4	593.0	592.3	591.6	590.9	590.2	590.9	591.6	592.3	593.0	593.4
165°	600.3	599.8	598.9	598.0	597.0	596.1	597.0	598.0	598.9	599.8	600.3
167.5°	605.3	604.8	603.8	602.7	601.7	600.7	601.7	602.7	603.8	604.8	605.3
170°	609.4	608.9	607.9	606.9	605.9	604.9	605.9	606.9	607.9	608.9	609.4
172.5°	612.2	611.6	610.5	609.4	608.2	607.1	608.2	609.4	610.5	611.6	612.2
175°	614.5	613.9	612.7	611.4	610.2	609.0	610.2	611.4	612.7	613.9	614.5
177.5°	615.4	614.8	613.6	612.3	611.1	609.9	611.1	612.3	613.6	614.8	615.4
180°	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1559.7	1568.0	1559.7	1565.2	1568.0	1574.9	1577.6	1590.0	1594.1	1603.7	1603.7
5°	1466.3	1470.4	1471.8	1477.3	1482.8	1496.5	1506.1	1524.0	1544.6	1547.4	1559.7
7.5°	1390.7	1397.6	1408.6	1404.4	1414.1	1434.7	1447.0	1469.0	1489.6	1500.6	1515.8
10°	1323.4	1331.6	1335.7	1339.9	1357.7	1375.6	1394.8	1409.9	1437.4	1453.9	1466.3
12.5°	1268.4	1261.5	1269.8	1284.9	1305.5	1316.5	1342.6	1366.0	1386.6	1404.4	1415.4
15°	1196.9	1202.4	1210.7	1236.8	1242.3	1269.8	1279.4	1305.5	1344.0	1360.5	1374.2
17.5°	1128.2	1146.1	1162.6	1172.2	1188.7	1210.7	1238.2	1267.0	1291.8	1311.0	1327.5
20°	1073.3	1091.1	1100.7	1107.6	1124.1	1154.3	1180.5	1216.2	1247.8	1262.9	1284.9
22.5°	1029.3	1029.3	1043.0	1063.6	1073.3	1102.1	1124.1	1162.6	1196.9	1216.2	1236.8
25°	974.3	982.6	993.6	1011.4	1025.2	1048.5	1080.1	1113.1	1150.2	1166.7	1192.8
27.5°	929.0	938.6	953.7	957.8	971.6	992.2	1025.2	1060.9	1099.4	1117.2	1139.2
30°	894.6	900.1	905.6	913.9	926.2	944.1	971.6	1003.2	1049.9	1063.6	1091.1
32.5°	864.4	867.1	869.9	876.7	883.6	901.5	923.5	957.8	996.3	1016.9	1041.7
35°	836.9	834.1	835.5	839.6	846.5	853.4	876.7	905.6	941.3	966.1	985.3
37.5°	810.8	805.3	803.9	803.9	806.7	814.9	832.8	857.5	896.0	916.6	935.8
40°	781.9	776.4	773.7	772.3	770.9	776.4	790.2	814.9	845.1	864.4	886.4
42.5°	754.4	748.9	742.1	740.7	738.0	740.7	750.3	773.7	799.8	819.0	836.9
45°	727.0	717.3	709.1	703.6	705.0	700.8	707.7	725.6	755.8	768.2	786.1
47.5°	696.7	685.7	674.7	669.2	663.7	666.5	669.2	684.4	710.5	722.8	740.7
50°	667.9	652.8	640.4	633.5	629.4	626.6	629.4	644.5	663.7	674.7	689.9
52.5°	634.9	619.8	607.4	596.4	590.9	586.8	588.2	601.9	619.8	630.8	645.9
55°	604.7	585.4	568.9	555.2	551.1	549.7	548.3	557.9	573.0	584.0	596.4
57.5°	570.3	551.1	533.2	516.7	508.5	507.1	507.1	509.8	529.1	537.3	544.2
60°	535.9	515.3	496.1	481.0	468.6	464.5	463.1	468.6	478.2	486.5	496.1
62.5°	497.5	476.9	453.5	439.7	427.4	416.4	420.5	421.9	435.6	439.7	448.0
65°	460.4	437.0	417.8	395.8	382.0	375.2	372.4	375.2	386.2	387.5	393.0
67.5°	417.8	395.8	372.4	357.3	344.9	332.6	329.8	329.8	335.3	339.4	346.3
70°	376.5	354.5	328.4	311.9	299.6	288.6	284.5	283.1	287.2	290.0	296.8
72.5°	328.4	306.4	287.2	269.3	254.2	246.0	241.9	239.1	243.2	246.0	247.4
75°	277.6	259.7	240.5	222.6	213.0	204.8	199.3	195.1	197.9	197.9	197.9
77.5°	229.5	211.6	196.5	184.1	171.8	162.2	158.0	153.9	155.3	155.3	158.0
80°	178.6	166.3	153.9	142.9	131.9	123.7	120.9	116.8	114.1	112.7	112.7
82.5°	131.9	122.3	111.3	101.7	96.2	87.9	85.2	79.7	79.7	78.3	78.3
85°	87.9	82.5	71.5	64.6	60.5	56.3	53.6	50.8	46.7	46.7	45.3
87.5°	46.7	44.0	41.2	33.0	33.0	28.9	27.5	26.1	22.0	23.4	23.4
90°	12.5	11.9	11.3	10.7	10.1	9.3	8.5	7.6	6.8	6.4	5.8
92.5°	12.1	11.5	10.8	10.2	9.6	8.8	8.0	7.2	6.4	6.0	6.1
95°	12.5	11.9	11.3	10.7	10.1	10.0	9.9	9.8	9.7	9.6	11.3
97.5°	12.1	11.6	11.1	10.6	10.1	20.8	31.5	42.2	52.9	58.2	57.1
100°	13.3	15.0	16.7	18.5	20.2	34.2	48.3	62.3	76.4	83.4	82.5
102.5°	24.8	47.7	70.6	93.5	116.4	115.2	114.0	112.7	111.5	110.9	110.3
105°	146.6	145.7	144.8	143.9	143.0	142.5	142.0	141.5	141.0	140.7	140.4
107.5°	174.3	173.8	173.3	172.8	172.3	171.6	170.9	170.2	169.5	169.1	168.9
110°	202.9	202.7	202.5	202.3	202.1	201.5	200.9	200.2	199.6	199.3	199.2

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	230.5	230.6	230.7	230.8	230.9	230.7	230.5	230.3	230.1	230.0	229.7
115°	259.3	259.1	258.8	258.6	258.4	258.5	258.6	258.7	258.8	258.9	258.7
117.5°	287.4	287.5	287.6	287.7	287.8	287.5	287.2	286.9	286.6	286.4	286.2
120°	314.2	314.0	313.8	313.6	313.4	313.5	313.6	313.7	313.8	313.9	313.7
122.5°	339.9	339.8	339.7	339.6	339.5	339.3	339.1	338.9	338.7	338.6	338.5
125°	364.1	363.8	363.5	363.2	362.9	363.1	363.3	363.5	363.7	363.8	363.6
127.5°	387.7	387.8	387.9	388.0	388.1	387.6	387.1	386.6	386.1	385.8	385.8
130°	410.1	410.0	409.9	409.8	409.7	409.4	409.1	408.8	408.5	408.3	408.2
132.5°	431.6	431.5	431.4	431.3	431.2	430.8	430.4	430.0	429.6	429.4	429.3
135°	451.2	451.0	450.8	450.6	450.4	450.0	449.6	449.2	448.8	448.6	448.7
137.5°	470.5	470.3	470.1	469.9	469.7	469.2	468.7	468.2	467.7	467.4	467.4
140°	488.3	488.0	487.7	487.4	487.1	486.9	486.7	486.5	486.3	486.2	486.1
142.5°	504.4	504.2	504.0	503.8	503.6	503.5	503.4	503.3	503.2	503.1	502.9
145°	519.6	519.5	519.4	519.3	519.2	519.2	519.2	519.2	519.2	519.2	519.0
147.5°	533.3	533.2	533.1	533.0	532.9	533.0	533.1	533.2	533.3	533.4	533.1
150°	546.2	546.2	546.2	546.2	546.2	546.3	546.4	546.5	546.6	546.7	546.5
152.5°	558.0	557.8	557.6	557.4	557.2	557.4	557.6	557.8	558.0	558.1	557.9
155°	568.5	568.1	567.6	567.2	566.8	567.1	567.4	567.7	568.0	568.2	568.1
157.5°	577.5	577.0	576.5	576.0	575.5	575.9	576.3	576.8	577.2	577.4	577.4
160°	586.2	585.6	585.0	584.4	583.8	583.9	584.0	584.1	584.2	584.2	584.4
162.5°	593.1	592.5	591.8	591.2	590.6	590.7	590.8	590.9	591.0	591.1	591.3
165°	599.9	599.1	598.2	597.4	596.6	596.6	596.6	596.6	596.6	596.6	596.9
167.5°	604.8	603.9	603.0	602.1	601.2	601.3	601.4	601.5	601.6	601.6	601.9
170°	609.0	608.2	607.4	606.6	605.8	605.7	605.6	605.5	605.4	605.3	605.6
172.5°	611.8	611.0	610.1	609.3	608.5	608.4	608.3	608.2	608.1	608.1	608.4
175°	614.0	613.1	612.2	611.3	610.4	610.3	610.2	610.1	610.0	609.9	610.2
177.5°	615.0	614.2	613.3	612.5	611.7	611.5	611.3	611.1	610.9	610.8	611.2
180°	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6	612.6

TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1658.7	1658.7	1658.7	1658.7
2.5°	1613.3	1627.1	1639.4	1658.7
5°	1577.6	1596.8	1622.9	1651.8
7.5°	1536.4	1566.6	1601.0	1640.8
10°	1497.9	1532.2	1576.2	1624.3
12.5°	1458.0	1499.3	1547.4	1599.6
15°	1412.7	1453.9	1507.5	1577.6
17.5°	1371.5	1420.9	1478.7	1552.9
20°	1323.4	1370.1	1433.3	1518.5
22.5°	1280.8	1334.4	1404.4	1478.7
25°	1234.0	1280.8	1350.9	1440.2
27.5°	1187.3	1245.0	1312.4	1399.0
30°	1142.0	1190.1	1262.9	1353.6
32.5°	1092.5	1150.2	1217.6	1302.8
35°	1038.9	1093.9	1157.1	1249.2
37.5°	990.8	1044.4	1109.0	1190.1
40°	937.2	993.6	1052.6	1133.7
42.5°	885.0	935.8	994.9	1069.1
45°	834.1	878.1	931.7	996.3
47.5°	781.9	819.0	868.5	926.2
50°	725.6	765.4	802.5	850.6
52.5°	673.4	707.7	738.0	777.8
55°	622.5	645.9	670.6	700.8
57.5°	568.9	586.8	604.7	636.3
60°	515.3	531.8	541.4	562.1
62.5°	463.1	470.0	482.3	494.7
65°	405.4	415.0	421.9	437.0
67.5°	353.2	357.3	364.2	373.8
70°	298.2	307.8	310.6	317.4
72.5°	251.5	255.6	258.4	259.7
75°	199.3	203.4	206.1	214.4
77.5°	156.7	155.3	160.8	162.2
80°	115.4	111.3	112.7	118.2
82.5°	75.6	77.0	75.6	75.6
85°	46.7	45.3	42.6	44.0
87.5°	20.6	20.6	19.2	19.2
90°	4.7	3.6	2.5	1.4
92.5°	6.3	6.5	6.7	6.9
95°	14.8	18.3	21.7	25.2
97.5°	54.8	52.6	50.3	48.1
100°	80.6	78.8	76.9	75.1
102.5°	109.1	107.8	106.6	105.4
105°	139.8	139.1	138.5	137.9
107.5°	168.6	168.3	168.0	167.7
110°	198.9	198.6	198.3	198.0



TEST NUMBER: P1033182

CATALOG NUMBER: S124DIW-B1020D470UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	229.1	228.5	227.9	227.3
115°	258.4	258.1	257.8	257.5
117.5°	285.8	285.4	285.0	284.6
120°	313.3	312.8	312.4	312.0
122.5°	338.3	338.1	337.9	337.7
125°	363.2	362.8	362.4	362.0
127.5°	385.7	385.6	385.5	385.4
130°	408.1	408.0	407.9	407.8
132.5°	429.1	428.8	428.6	428.4
135°	448.8	448.9	449.0	449.1
137.5°	467.4	467.4	467.4	467.4
140°	485.9	485.7	485.5	485.3
142.5°	502.5	502.1	501.7	501.3
145°	518.7	518.4	518.1	517.8
147.5°	532.5	531.8	531.2	530.6
150°	546.1	545.6	545.2	544.8
152.5°	557.6	557.3	557.0	556.7
155°	568.0	567.9	567.8	567.7
157.5°	577.4	577.4	577.4	577.4
160°	584.7	585.0	585.3	585.6
162.5°	591.7	592.1	592.5	592.9
165°	597.4	597.9	598.4	598.9
167.5°	602.4	602.9	603.4	603.9
170°	606.2	606.9	607.5	608.1
172.5°	609.0	609.6	610.2	610.8
175°	610.8	611.4	612.0	612.6
177.5°	611.9	612.6	613.3	614.0
180°	612.6	612.6	612.6	612.6

(END OF REPORT)