

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033213

Luminaire Tested: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033213
REPORT IS A COMBINATION OF REPORTS P996914 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D770UB30-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7288.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	60	59	58
2	92	85	79	73	86	80	74	70	70	66	63	62	58	56	54	51	49
3	84	75	67	62	79	70	64	59	62	57	53	55	51	48	48	45	42
4	77	66	58	52	72	63	56	50	56	50	45	49	45	41	43	39	37
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	28	25
8	57	44	36	31	53	42	35	30	38	32	27	33	29	25	30	26	23
9	53	40	33	28	49	38	31	27	34	29	25	31	26	23	27	24	21
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13526	13526	13526	13526
5°	13492	15517	13570	11660
10°	13391	18104	13493	10229
15°	13230	20870	13322	9153
20°	13058	22631	13153	8206
25°	12809	22372	12931	7507
30°	12564	18491	12717	7148
35°	12222	13779	12356	6930
40°	11820	10380	11935	6823
45°	11209	8331	11349	6677
50°	10479	7019	10631	6609
55°	9620	6108	9771	6531
60°	8787	5380	9043	6423
65°	8003	4629	8078	6155
70°	7081	3808	7235	5667
75°	6179	2926	6138	4816
80°	4861	1923	4804	3655
85°	3202	864	2998	2132

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 17489 cd/sqm

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	2.2
10°-20°	498.3	6.8
20°-30°	791.6	10.9
30°-40°	879.6	12.1
40°-50°	799.9	11.0
50°-60°	653.6	9.0
60°-70°	466.6	6.4
70°-80°	256.7	3.5
80°-90°	71.5	1.0
90°-100°	63.6	0.9
100°-110°	190.6	2.6
110°-120°	323.8	4.4
120°-130°	427.1	5.9
130°-140°	479.7	6.6
140°-150°	471.4	6.5
150°-160°	396.5	5.4
160°-170°	263.8	3.6
170°-180°	92.4	1.3
0°-30°	1451.2	19.9
0°-40°	2330.8	32.0
0°-60°	3784.3	51.9
0°-90°	4579.1	62.8
90°-120°	578.0	7.9
90°-150°	1956.2	26.8
90°-180°	2709.0	37.2
0°-180°	7288.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1659	1659	1659	1659	1659	
5°	1652	1946	1661	1462	1652	157
15°	1578	2673	1589	1172	1578	445
25°	1440	2838	1454	952	1440	664
35°	1249	1678	1263	844	1249	780
45°	996	941	1009	754	996	768
55°	701	616	712	658	701	630
65°	437	396	441	526	437	432
75°	214	198	213	326	214	225
85°	44	41	41	102	44	51
90°	2	23	2	23	2	6
95°	45	60	45	60	45	49
105°	176	184	176	184	176	187
115°	329	326	329	326	329	325
125°	480	476	480	476	480	427
135°	618	619	618	619	618	478
145°	751	752	751	752	751	470
155°	861	860	861	860	861	396
165°	937	935	937	935	937	264
175°	975	970	975	970	975	93
180°	976	976	976	976	976	

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1658.7	1675.2	1682.0	1687.5	1705.4	1710.9	1712.3	1720.5	1727.4	1728.8	1728.8
5°	1651.8	1677.9	1698.5	1717.8	1746.6	1759.0	1774.1	1790.6	1812.6	1826.3	1833.2
7.5°	1640.8	1679.3	1710.9	1743.9	1783.7	1808.5	1822.2	1866.2	1896.4	1921.2	1951.4
10°	1624.3	1673.8	1719.1	1767.2	1823.6	1853.8	1884.0	1937.6	1980.2	2028.3	2066.8
12.5°	1599.6	1664.2	1719.1	1786.5	1856.6	1892.3	1928.0	2021.5	2070.9	2113.5	2182.3
15°	1577.6	1642.2	1720.5	1789.2	1875.8	1929.4	1981.6	2042.1	2120.4	2212.5	2278.4
17.5°	1552.9	1633.9	1706.8	1803.0	1899.2	1950.0	1992.6	2086.1	2196.0	2286.7	2347.2
20°	1518.5	1601.0	1697.2	1798.8	1912.9	1952.8	2009.1	2134.2	2233.1	2322.4	2421.4
22.5°	1478.7	1574.9	1676.5	1774.1	1892.3	1976.1	2038.0	2147.9	2267.5	2370.5	2481.8
25°	1440.2	1544.6	1633.9	1767.2	1892.3	1948.6	2018.7	2149.3	2279.8	2404.9	2518.9
27.5°	1399.0	1496.5	1617.5	1723.3	1864.8	1926.6	2002.2	2145.1	2283.9	2409.0	2531.3
30°	1353.6	1458.0	1558.4	1683.4	1820.8	1900.5	1970.6	2125.9	2267.5	2398.0	2512.1
32.5°	1302.8	1401.7	1508.9	1627.1	1771.4	1852.4	1940.4	2099.8	2251.0	2363.6	2451.6
35°	1249.2	1349.5	1442.9	1563.9	1712.3	1793.4	1878.6	2054.5	2204.2	2296.3	2347.2
37.5°	1190.1	1284.9	1377.0	1496.5	1644.9	1731.5	1818.1	1988.5	2130.0	2207.0	2193.2
40°	1133.7	1218.9	1304.1	1416.8	1572.1	1664.2	1739.8	1911.5	2035.2	2068.2	2022.8
42.5°	1069.1	1142.0	1224.4	1339.9	1491.0	1577.6	1672.4	1829.1	1921.2	1907.4	1830.5
45°	996.3	1060.9	1143.3	1251.9	1405.8	1495.1	1574.9	1723.3	1790.6	1756.2	1616.1
47.5°	926.2	989.4	1056.8	1165.3	1315.1	1390.7	1471.8	1605.1	1643.6	1570.7	1430.6
50°	850.6	902.9	972.9	1076.0	1216.2	1295.9	1363.2	1470.4	1484.2	1394.8	1249.2
52.5°	777.8	821.8	889.1	990.8	1121.4	1184.6	1250.5	1345.4	1334.4	1242.3	1102.1
55°	700.8	742.1	803.9	897.4	1012.8	1073.3	1129.6	1213.4	1190.1	1095.2	972.9
57.5°	636.3	665.1	725.6	812.2	907.0	972.9	1021.0	1087.0	1051.3	956.5	842.4
60°	562.1	597.8	648.6	718.7	812.2	856.1	898.7	942.7	918.0	827.3	725.6
62.5°	494.7	522.2	566.2	633.5	706.3	746.2	791.5	819.0	794.3	710.5	625.3
65°	437.0	459.0	493.3	548.3	618.4	651.4	677.5	703.6	683.0	604.7	542.8
67.5°	373.8	393.0	421.9	465.9	525.0	548.3	573.0	590.9	567.6	515.3	454.9
70°	317.4	331.2	358.7	391.7	432.9	454.9	475.5	493.3	472.7	428.8	383.4
72.5°	259.7	270.7	295.5	318.8	355.9	371.0	386.2	399.9	393.0	351.8	314.7
75°	214.4	218.5	235.0	254.2	277.6	294.1	305.1	313.3	307.8	274.8	251.5
77.5°	162.2	167.7	180.0	195.1	215.8	225.4	232.2	240.5	233.6	207.5	191.0
80°	118.2	119.6	126.4	140.2	153.9	155.3	162.2	173.2	169.0	151.2	138.8
82.5°	75.6	79.7	82.5	90.7	100.3	103.1	107.2	109.9	108.6	97.6	93.4
85°	44.0	44.0	46.7	52.2	55.0	59.1	60.5	61.8	64.6	57.7	53.6
87.5°	19.2	20.6	20.6	22.0	24.7	24.7	26.1	27.5	28.9	27.5	23.4
90°	2.3	4.1	6.0	7.8	9.7	10.6	11.3	12.6	13.9	15.3	16.6
92.5°	19.6	21.8	24.0	26.1	28.3	29.4	29.8	30.7	31.5	32.4	33.2
95°	45.3	46.8	48.3	49.8	51.3	52.1	52.7	53.9	55.0	56.2	57.4
97.5°	72.5	73.8	75.2	76.5	77.8	78.5	79.2	80.5	81.9	83.2	84.6
100°	105.7	106.4	107.0	107.7	108.4	108.7	109.5	111.0	112.5	114.0	115.5
102.5°	140.4	140.6	140.8	140.9	141.1	141.2	141.9	143.2	144.5	145.9	147.2
105°	175.9	176.1	176.3	176.4	176.6	176.7	177.0	177.7	178.4	179.0	179.7
107.5°	212.9	213.1	213.3	213.4	213.6	213.7	213.8	213.9	214.1	214.2	214.4
110°	250.7	251.0	251.4	251.7	252.0	252.2	252.1	251.9	251.8	251.6	251.4

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	289.9	289.9	289.9	289.9	289.9	289.9	289.7	289.4	289.1	288.7	288.4
115°	329.2	329.2	329.2	329.2	329.2	329.2	329.0	328.7	328.4	328.0	327.7
117.5°	366.2	366.2	366.2	366.2	366.2	366.2	366.1	366.0	365.8	365.7	365.5
120°	403.2	403.9	404.5	405.2	405.9	406.2	406.0	405.5	405.0	404.5	404.0
122.5°	441.7	441.9	442.1	442.2	442.4	442.5	442.4	442.2	442.1	441.9	441.7
125°	479.5	479.5	479.5	479.5	479.5	479.5	479.4	479.2	479.1	478.9	478.7
127.5°	513.5	514.0	514.5	515.0	515.5	515.7	515.5	515.2	514.9	514.5	514.2
130°	549.7	550.2	550.7	551.2	551.7	552.0	552.0	552.0	552.0	552.0	552.0
132.5°	586.7	587.0	587.4	587.7	588.0	588.2	588.1	587.9	587.8	587.6	587.4
135°	618.4	619.4	620.4	621.4	622.4	622.9	622.9	622.9	622.9	622.9	622.9
137.5°	653.9	654.4	654.9	655.4	655.9	656.2	656.4	656.7	657.0	657.4	657.7
140°	689.4	689.7	690.1	690.4	690.7	690.9	690.9	690.9	690.9	690.9	690.9
142.5°	721.9	722.2	722.6	722.9	723.2	723.4	723.3	723.1	723.0	722.8	722.6
145°	751.3	752.0	752.6	753.3	754.0	754.3	754.4	754.6	754.7	754.9	755.1
147.5°	781.5	782.3	783.2	784.0	784.9	785.3	785.2	785.0	784.9	784.7	784.5
150°	808.7	809.4	810.0	810.7	811.4	811.7	811.7	811.7	811.7	811.7	811.7
152.5°	834.4	834.7	835.1	835.4	835.7	835.9	836.0	836.1	836.3	836.4	836.6
155°	860.8	860.8	860.8	860.8	860.8	860.8	860.7	860.5	860.4	860.2	860.0
157.5°	883.4	883.1	882.7	882.4	882.1	881.9	881.9	881.9	881.9	881.9	881.9
160°	903.1	902.9	902.7	902.6	902.4	902.3	902.2	902.1	901.9	901.8	901.6
162.5°	921.2	920.7	920.2	919.7	919.2	918.9	918.8	918.7	918.5	918.4	918.2
165°	937.1	936.6	936.1	935.6	935.1	934.8	934.6	934.3	934.0	933.6	933.3
167.5°	949.9	949.2	948.6	947.9	947.2	946.9	946.9	946.9	946.9	946.9	946.9
170°	960.5	959.7	958.8	958.0	957.1	956.7	956.8	956.9	957.1	957.2	957.4
172.5°	968.0	967.3	966.7	966.0	965.3	965.0	965.0	965.0	965.0	965.0	965.0
175°	974.8	974.0	973.1	972.3	971.4	971.0	970.9	970.8	970.6	970.5	970.3
177.5°	977.8	977.0	976.1	975.3	974.4	974.0	974.0	974.0	974.0	974.0	974.0
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1732.9	1757.6	1768.6	1771.4	1786.5	1776.9	1781.0	1779.6	1790.6	1792.0	1792.0
5°	1859.3	1888.2	1897.8	1911.5	1932.1	1937.6	1933.5	1941.8	1956.9	1945.9	1962.4
7.5°	1992.6	2024.2	2046.2	2076.4	2083.3	2101.2	2112.2	2121.8	2124.5	2125.9	2128.7
10°	2116.3	2156.1	2186.4	2237.2	2248.2	2257.8	2305.9	2286.7	2311.4	2303.2	2305.9
12.5°	2216.6	2294.9	2319.7	2404.9	2413.1	2446.1	2443.4	2473.6	2479.1	2490.1	2479.1
15°	2348.5	2439.2	2479.1	2527.2	2554.7	2593.1	2600.0	2641.2	2657.7	2672.8	2657.7
17.5°	2469.5	2517.6	2619.3	2657.7	2675.6	2696.2	2748.4	2763.5	2788.3	2778.7	2806.1
20°	2529.9	2598.6	2705.8	2771.8	2799.3	2818.5	2862.5	2885.9	2895.5	2895.5	2898.2
22.5°	2583.5	2682.5	2762.2	2837.8	2862.5	2876.2	2902.3	2920.2	2924.3	2927.1	2929.8
25°	2631.6	2720.9	2785.5	2828.1	2837.8	2837.8	2852.9	2841.9	2824.0	2837.8	2846.0
27.5°	2631.6	2694.8	2723.7	2738.8	2738.8	2701.7	2679.7	2634.4	2595.9	2584.9	2609.6
30°	2587.6	2616.5	2576.7	2539.5	2510.7	2486.0	2399.4	2330.7	2316.9	2307.3	2344.4
32.5°	2486.0	2448.9	2370.5	2263.3	2220.7	2164.4	2097.1	2044.8	2013.2	2002.2	1994.0
35°	2305.9	2209.7	2108.0	1963.8	1933.5	1862.1	1770.0	1731.5	1679.3	1677.9	1695.8
37.5°	2109.4	1961.0	1851.1	1713.6	1671.0	1595.5	1508.9	1469.0	1433.3	1405.8	1438.8
40°	1879.9	1750.7	1583.1	1470.4	1409.9	1370.1	1297.3	1253.3	1236.8	1223.1	1243.7
42.5°	1665.5	1524.0	1393.5	1278.0	1228.5	1183.2	1135.1	1092.5	1080.1	1078.8	1093.9
45°	1452.5	1313.7	1192.8	1093.9	1062.3	1034.8	988.1	975.7	955.1	941.3	948.2
47.5°	1282.1	1139.2	1038.9	963.3	935.8	912.5	882.2	861.6	843.8	838.3	846.5
50°	1114.5	1018.3	915.2	852.0	831.4	809.4	786.1	766.8	758.6	753.1	758.6
52.5°	979.8	876.7	806.7	755.8	735.2	718.7	702.2	694.0	683.0	685.7	691.2
55°	858.9	768.2	709.1	672.0	659.6	652.8	632.1	622.5	618.4	615.6	618.4
57.5°	744.8	678.9	634.9	603.3	586.8	582.7	566.2	566.2	562.1	557.9	559.3
60°	654.1	597.8	555.2	530.4	527.7	520.8	509.8	508.5	498.8	503.0	504.3
62.5°	562.1	516.7	487.8	472.7	463.1	460.4	453.5	452.1	448.0	449.4	446.6
65°	489.2	452.1	423.3	410.9	406.8	405.4	399.9	395.8	393.0	395.8	393.0
67.5°	416.4	391.7	369.7	357.3	351.8	350.4	346.3	343.6	344.9	340.8	343.6
70°	347.7	322.9	309.2	302.3	299.6	295.5	295.5	295.5	295.5	292.7	291.3
72.5°	292.7	268.0	258.4	254.2	251.5	250.1	246.0	247.4	246.0	244.6	250.1
75°	232.2	217.1	207.5	203.4	206.1	202.0	197.9	200.6	196.5	197.9	203.4
77.5°	175.9	169.0	163.5	160.8	158.0	155.3	155.3	152.5	152.5	152.5	152.5
80°	127.8	126.4	116.8	115.4	115.4	112.7	112.7	112.7	112.7	111.3	112.7
82.5°	85.2	83.8	81.1	79.7	77.0	78.3	78.3	75.6	75.6	74.2	75.6
85°	49.5	49.5	46.7	45.3	44.0	45.3	42.6	41.2	42.6	41.2	42.6
87.5°	23.4	20.6	22.0	20.6	17.9	19.2	16.5	17.9	16.5	15.1	17.9
90°	17.6	18.6	19.6	20.6	21.1	21.3	21.6	22.0	22.3	22.7	22.3
92.5°	33.7	34.2	34.7	35.2	35.5	35.6	35.7	35.9	36.0	36.2	36.0
95°	57.9	58.4	58.9	59.4	59.7	59.7	59.7	59.7	59.7	59.7	59.7
97.5°	85.3	85.9	86.6	87.3	87.6	87.6	87.6	87.6	87.6	87.6	87.6
100°	115.8	116.2	116.5	116.8	117.0	117.0	117.0	117.0	117.0	117.0	117.0
102.5°	147.7	148.2	148.7	149.2	149.5	149.6	149.8	149.9	150.1	150.3	150.1
105°	180.2	180.7	181.2	181.7	182.0	182.2	182.7	183.2	183.7	184.2	183.7
107.5°	215.1	215.8	216.5	217.2	217.5	217.4	217.2	217.1	216.9	216.7	216.9
110°	251.1	250.7	250.4	250.1	249.9	250.2	250.7	251.2	251.7	252.2	251.7

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4
115°	327.5	327.3	327.2	327.0	326.9	326.8	326.7	326.5	326.4	326.2	326.4
117.5°	365.0	364.5	364.0	363.5	363.2	362.9	362.4	361.9	361.4	360.9	361.4
120°	403.2	402.3	401.5	400.6	400.2	400.4	400.7	401.0	401.4	401.7	401.4
122.5°	441.2	440.7	440.2	439.7	439.5	439.1	438.2	437.4	436.5	435.7	436.5
125°	478.4	478.0	477.7	477.4	477.2	477.0	476.7	476.4	476.0	475.7	476.0
127.5°	513.9	513.5	513.2	512.9	512.7	512.6	512.4	512.3	512.1	511.9	512.1
130°	551.7	551.3	551.0	550.7	550.5	550.2	549.5	548.8	548.1	547.4	548.1
132.5°	587.1	586.7	586.4	586.1	585.9	585.8	585.7	585.5	585.4	585.2	585.4
135°	622.6	622.2	621.9	621.6	621.4	621.2	620.7	620.2	619.7	619.2	619.7
137.5°	657.2	656.7	656.2	655.7	655.4	655.5	655.7	655.8	656.0	656.2	656.0
140°	690.7	690.5	690.4	690.2	690.1	690.0	689.9	689.7	689.6	689.4	689.6
142.5°	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6
145°	754.9	754.7	754.6	754.4	754.3	754.1	753.6	753.1	752.6	752.1	752.6
147.5°	784.3	784.2	784.0	783.9	783.8	783.7	783.5	783.4	783.2	783.0	783.2
150°	811.7	811.7	811.7	811.7	811.7	811.6	811.5	811.3	811.2	811.0	811.2
152.5°	837.1	837.6	838.1	838.6	838.9	838.6	838.1	837.6	837.1	836.6	837.1
155°	860.7	861.4	862.1	862.8	863.1	862.8	862.1	861.4	860.7	860.0	860.7
157.5°	882.4	882.9	883.4	883.9	884.2	883.9	883.4	882.9	882.4	881.9	882.4
160°	902.1	902.6	903.1	903.6	903.8	903.4	902.6	901.7	900.9	900.1	900.9
162.5°	919.2	920.2	921.2	922.2	922.7	922.3	921.4	920.6	919.7	918.9	919.7
165°	934.3	935.3	936.3	937.3	937.8	937.5	936.8	936.1	935.5	934.8	935.5
167.5°	947.9	948.9	949.9	950.9	951.4	950.9	949.9	948.9	947.9	946.9	947.9
170°	958.4	959.4	960.5	961.5	962.0	961.4	960.2	959.1	957.9	956.7	957.9
172.5°	966.2	967.4	968.5	969.7	970.3	969.7	968.5	967.4	966.2	965.0	966.2
175°	971.5	972.7	973.8	975.0	975.6	975.0	973.8	972.7	971.5	970.3	971.5
177.5°	975.2	976.4	977.5	978.7	979.3	978.6	977.3	976.0	974.6	973.3	974.6
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1789.2	1785.1	1779.6	1779.6	1772.7	1772.7	1761.7	1742.5	1726.0	1720.5	1723.3
5°	1941.8	1943.1	1934.9	1928.0	1915.7	1906.0	1888.2	1853.8	1842.8	1820.8	1805.7
7.5°	2116.3	2110.8	2095.7	2084.7	2081.9	2059.9	2021.5	1980.2	1947.3	1925.3	1893.7
10°	2312.8	2290.8	2268.8	2262.0	2245.5	2208.4	2164.4	2119.0	2073.7	2025.6	1972.0
12.5°	2477.7	2435.1	2433.7	2417.2	2385.6	2365.0	2312.8	2248.2	2169.9	2116.3	2055.8
15°	2655.0	2615.1	2582.1	2551.9	2536.8	2476.3	2432.4	2351.3	2257.8	2200.1	2158.9
17.5°	2781.4	2763.5	2707.2	2693.5	2672.8	2602.8	2532.7	2453.0	2371.9	2290.8	2179.5
20°	2883.1	2872.1	2835.0	2815.8	2782.8	2727.8	2642.6	2550.5	2457.1	2341.7	2237.2
22.5°	2927.1	2913.3	2883.1	2866.6	2846.0	2799.3	2726.4	2622.0	2499.7	2396.6	2285.3
25°	2840.5	2865.2	2857.0	2850.1	2841.9	2814.4	2759.4	2667.4	2547.8	2431.0	2292.2
27.5°	2645.4	2688.0	2729.2	2734.7	2748.4	2759.4	2737.4	2671.5	2571.2	2447.5	2294.9
30°	2382.9	2402.1	2486.0	2510.7	2529.9	2600.0	2641.2	2624.8	2547.8	2436.5	2296.3
32.5°	2046.2	2097.1	2182.3	2241.3	2293.6	2371.9	2479.1	2521.7	2494.2	2403.5	2264.7
35°	1727.4	1787.9	1886.8	1962.4	2014.6	2125.9	2252.3	2344.4	2378.8	2333.4	2209.7
37.5°	1466.3	1539.1	1627.1	1655.9	1716.4	1853.8	2028.3	2156.1	2240.0	2244.1	2147.9
40°	1269.8	1306.9	1377.0	1420.9	1480.0	1595.5	1765.9	1934.9	2061.3	2103.9	2053.1
42.5°	1103.5	1132.4	1184.6	1238.2	1291.8	1379.7	1536.4	1694.4	1864.8	1950.0	1948.6
45°	971.6	1001.8	1037.5	1081.5	1118.6	1213.4	1337.1	1499.3	1646.3	1778.2	1811.2
47.5°	856.1	882.2	926.2	945.5	970.2	1059.5	1166.7	1317.9	1470.4	1621.6	1660.1
50°	770.9	792.9	823.2	835.5	863.0	929.0	1016.9	1139.2	1308.3	1447.0	1518.5
52.5°	694.0	710.5	733.8	743.5	762.7	812.2	891.9	988.1	1128.2	1271.1	1371.5
55°	628.0	639.0	655.5	666.5	680.2	724.2	783.3	869.9	990.8	1114.5	1212.1
57.5°	566.2	574.4	590.9	596.4	607.4	641.8	683.0	755.8	867.1	977.1	1071.9
60°	508.5	514.0	523.6	535.9	544.2	567.6	606.0	666.5	755.8	856.1	933.1
62.5°	453.5	461.7	464.5	470.0	476.9	498.8	529.1	573.0	651.4	733.8	814.9
65°	397.1	404.0	409.5	410.9	417.8	434.3	461.7	500.2	551.1	622.5	698.1
67.5°	344.9	349.1	351.8	357.3	364.2	372.4	394.4	423.3	470.0	527.7	588.2
70°	296.8	296.8	301.0	302.3	310.6	320.2	329.8	357.3	398.5	445.2	486.5
72.5°	244.6	251.5	250.1	257.0	255.6	262.5	274.8	292.7	322.9	360.0	399.9
75°	199.3	203.4	203.4	203.4	206.1	211.6	218.5	235.0	258.4	288.6	311.9
77.5°	155.3	158.0	158.0	158.0	159.4	164.9	171.8	182.8	199.3	217.1	230.9
80°	111.3	114.1	114.1	116.8	116.8	118.2	125.1	130.6	138.8	152.5	166.3
82.5°	75.6	77.0	79.7	79.7	78.3	81.1	82.5	87.9	96.2	98.9	108.6
85°	41.2	42.6	44.0	44.0	45.3	48.1	46.7	52.2	52.2	57.7	60.5
87.5°	16.5	19.2	19.2	17.9	19.2	19.2	19.2	22.0	23.4	24.7	23.4
90°	22.0	21.6	21.3	21.1	20.6	19.6	18.6	17.6	16.6	15.3	13.9
92.5°	35.9	35.7	35.6	35.5	35.2	34.7	34.2	33.7	33.2	32.4	31.5
95°	59.7	59.7	59.7	59.7	59.4	58.9	58.4	57.9	57.4	56.2	55.0
97.5°	87.6	87.6	87.6	87.6	87.3	86.6	85.9	85.3	84.6	83.2	81.9
100°	117.0	117.0	117.0	117.0	116.8	116.5	116.2	115.8	115.5	114.0	112.5
102.5°	149.9	149.8	149.6	149.5	149.2	148.7	148.2	147.7	147.2	145.9	144.5
105°	183.2	182.7	182.2	182.0	181.7	181.2	180.7	180.2	179.7	179.0	178.4
107.5°	217.1	217.2	217.4	217.5	217.2	216.5	215.8	215.1	214.4	214.2	214.1
110°	251.2	250.7	250.2	249.9	250.1	250.4	250.7	251.1	251.4	251.6	251.8

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.7	289.1
115°	326.5	326.7	326.8	326.9	327.0	327.2	327.3	327.5	327.7	328.0	328.4
117.5°	361.9	362.4	362.9	363.2	363.5	364.0	364.5	365.0	365.5	365.7	365.8
120°	401.0	400.7	400.4	400.2	400.6	401.5	402.3	403.2	404.0	404.5	405.0
122.5°	437.4	438.2	439.1	439.5	439.7	440.2	440.7	441.2	441.7	441.9	442.1
125°	476.4	476.7	477.0	477.2	477.4	477.7	478.0	478.4	478.7	478.9	479.1
127.5°	512.3	512.4	512.6	512.7	512.9	513.2	513.5	513.9	514.2	514.5	514.9
130°	548.8	549.5	550.2	550.5	550.7	551.0	551.3	551.7	552.0	552.0	552.0
132.5°	585.5	585.7	585.8	585.9	586.1	586.4	586.7	587.1	587.4	587.6	587.8
135°	620.2	620.7	621.2	621.4	621.6	621.9	622.2	622.6	622.9	622.9	622.9
137.5°	655.8	655.7	655.5	655.4	655.7	656.2	656.7	657.2	657.7	657.4	657.0
140°	689.7	689.9	690.0	690.1	690.2	690.4	690.5	690.7	690.9	690.9	690.9
142.5°	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.8	723.0
145°	753.1	753.6	754.1	754.3	754.4	754.6	754.7	754.9	755.1	754.9	754.7
147.5°	783.4	783.5	783.7	783.8	783.9	784.0	784.2	784.3	784.5	784.7	784.9
150°	811.3	811.5	811.6	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7
152.5°	837.6	838.1	838.6	838.9	838.6	838.1	837.6	837.1	836.6	836.4	836.3
155°	861.4	862.1	862.8	863.1	862.8	862.1	861.4	860.7	860.0	860.2	860.4
157.5°	882.9	883.4	883.9	884.2	883.9	883.4	882.9	882.4	881.9	881.9	881.9
160°	901.7	902.6	903.4	903.8	903.6	903.1	902.6	902.1	901.6	901.8	901.9
162.5°	920.6	921.4	922.3	922.7	922.2	921.2	920.2	919.2	918.2	918.4	918.5
165°	936.1	936.8	937.5	937.8	937.3	936.3	935.3	934.3	933.3	933.6	934.0
167.5°	948.9	949.9	950.9	951.4	950.9	949.9	948.9	947.9	946.9	946.9	946.9
170°	959.1	960.2	961.4	962.0	961.5	960.5	959.4	958.4	957.4	957.2	957.1
172.5°	967.4	968.5	969.7	970.3	969.7	968.5	967.4	966.2	965.0	965.0	965.0
175°	972.7	973.8	975.0	975.6	975.0	973.8	972.7	971.5	970.3	970.5	970.6
177.5°	976.0	977.3	978.6	979.3	978.7	977.5	976.4	975.2	974.0	974.0	974.0
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1710.9	1705.4	1701.3	1701.3	1688.9	1676.5	1669.7	1666.9	1664.2	1653.2	1638.1
5°	1781.0	1763.1	1750.7	1738.4	1717.8	1695.8	1673.8	1661.4	1643.6	1618.8	1601.0
7.5°	1859.3	1816.7	1803.0	1787.9	1746.6	1709.5	1679.3	1653.2	1624.3	1592.7	1561.1
10°	1925.3	1879.9	1849.7	1823.6	1770.0	1720.5	1675.2	1636.7	1599.6	1558.4	1519.9
12.5°	1988.5	1923.9	1892.3	1853.8	1797.5	1726.0	1666.9	1618.8	1563.9	1521.3	1474.5
15°	2076.4	1967.9	1915.7	1890.9	1815.3	1731.5	1660.1	1588.6	1543.2	1478.7	1437.4
17.5°	2090.2	2002.2	1967.9	1904.7	1814.0	1719.1	1636.7	1565.2	1496.5	1438.8	1385.2
20°	2138.3	2022.8	1967.9	1928.0	1808.5	1712.3	1621.6	1529.5	1463.5	1401.7	1341.2
22.5°	2168.5	2038.0	1980.2	1917.0	1803.0	1687.5	1580.3	1500.6	1419.6	1356.3	1308.3
25°	2160.3	2029.7	1965.1	1906.0	1767.2	1651.8	1555.6	1453.9	1378.3	1309.6	1246.4
27.5°	2156.1	2009.1	1940.4	1874.4	1743.9	1622.9	1502.0	1419.6	1335.7	1256.0	1209.3
30°	2145.1	1983.0	1903.3	1831.8	1695.8	1569.4	1466.3	1370.1	1286.3	1213.4	1151.6
32.5°	2108.0	1939.0	1862.1	1785.1	1643.6	1517.1	1412.7	1323.4	1239.5	1164.0	1104.9
35°	2058.6	1886.8	1803.0	1721.9	1580.3	1452.5	1356.3	1262.9	1184.6	1111.7	1055.4
37.5°	2009.1	1826.3	1748.0	1654.6	1524.0	1390.7	1291.8	1207.9	1135.1	1059.5	997.7
40°	1937.6	1754.9	1668.3	1588.6	1436.1	1311.0	1220.3	1144.7	1073.3	1001.8	949.6
42.5°	1840.1	1676.5	1587.2	1499.3	1356.3	1232.7	1144.7	1077.4	1010.0	951.0	893.2
45°	1741.1	1581.7	1502.0	1423.7	1268.4	1151.6	1070.5	1008.7	952.3	887.7	841.0
47.5°	1621.6	1486.9	1407.2	1330.2	1183.2	1066.4	992.2	934.5	882.2	828.7	784.7
50°	1499.3	1382.5	1309.6	1229.9	1089.8	983.9	911.1	863.0	820.4	769.6	733.8
52.5°	1367.3	1265.7	1203.8	1126.9	1003.2	905.6	831.4	783.3	747.6	710.5	678.9
55°	1227.2	1153.0	1087.0	1025.2	908.4	820.4	754.4	711.8	687.1	652.8	625.3
57.5°	1100.7	1029.3	989.4	919.3	817.7	731.1	678.9	643.1	614.3	593.7	571.7
60°	968.8	911.1	867.1	816.3	727.0	654.1	599.2	578.5	548.3	533.2	523.6
62.5°	842.4	801.2	759.9	721.5	641.8	573.0	531.8	505.7	487.8	472.7	464.5
65°	722.8	684.4	655.5	621.1	555.2	500.2	461.7	441.1	423.3	419.1	409.5
67.5°	606.0	589.5	557.9	530.4	474.1	431.5	402.6	376.5	366.9	362.8	354.5
70°	507.1	487.8	463.1	439.7	397.1	360.0	333.9	324.3	310.6	309.2	299.6
72.5°	417.8	394.4	376.5	358.7	327.1	294.1	280.3	266.6	259.7	254.2	250.1
75°	331.2	314.7	302.3	287.2	259.7	237.7	218.5	213.0	208.9	207.5	204.8
77.5°	247.4	236.4	230.9	215.8	196.5	177.3	169.0	160.8	160.8	158.0	159.4
80°	175.9	169.0	162.2	153.9	137.4	129.2	122.3	116.8	114.1	112.7	114.1
82.5°	111.3	107.2	105.8	100.3	89.3	85.2	79.7	75.6	75.6	75.6	75.6
85°	61.8	61.8	61.8	53.6	49.5	45.3	42.6	41.2	41.2	41.2	42.6
87.5°	26.1	26.1	22.0	22.0	20.6	17.9	16.5	16.5	17.9	17.9	19.2
90°	12.6	11.3	10.6	9.7	7.8	6.0	4.1	2.3	4.1	6.0	7.8
92.5°	30.7	29.8	29.4	28.3	26.1	24.0	21.8	19.6	21.8	24.0	26.1
95°	53.9	52.7	52.1	51.3	49.8	48.3	46.8	45.3	46.8	48.3	49.8
97.5°	80.5	79.2	78.5	77.8	76.5	75.2	73.8	72.5	73.8	75.2	76.5
100°	111.0	109.5	108.7	108.4	107.7	107.0	106.4	105.7	106.4	107.0	107.7
102.5°	143.2	141.9	141.2	141.1	140.9	140.8	140.6	140.4	140.6	140.8	140.9
105°	177.7	177.0	176.7	176.6	176.4	176.3	176.1	175.9	176.1	176.3	176.4
107.5°	213.9	213.8	213.7	213.6	213.4	213.3	213.1	212.9	213.1	213.3	213.4
110°	251.9	252.1	252.2	252.0	251.7	251.4	251.0	250.7	251.0	251.4	251.7

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	289.4	289.7	289.9	289.9	289.9	289.9	289.9	289.9	289.9	289.9	289.9
115°	328.7	329.0	329.2	329.2	329.2	329.2	329.2	329.2	329.2	329.2	329.2
117.5°	366.0	366.1	366.2	366.2	366.2	366.2	366.2	366.2	366.2	366.2	366.2
120°	405.5	406.0	406.2	405.9	405.2	404.5	403.9	403.2	403.9	404.5	405.2
122.5°	442.2	442.4	442.5	442.4	442.2	442.1	441.9	441.7	441.9	442.1	442.2
125°	479.2	479.4	479.5	479.5	479.5	479.5	479.5	479.5	479.5	479.5	479.5
127.5°	515.2	515.5	515.7	515.5	515.0	514.5	514.0	513.5	514.0	514.5	515.0
130°	552.0	552.0	552.0	551.7	551.2	550.7	550.2	549.7	550.2	550.7	551.2
132.5°	587.9	588.1	588.2	588.0	587.7	587.4	587.0	586.7	587.0	587.4	587.7
135°	622.9	622.9	622.9	622.4	621.4	620.4	619.4	618.4	619.4	620.4	621.4
137.5°	656.7	656.4	656.2	655.9	655.4	654.9	654.4	653.9	654.4	654.9	655.4
140°	690.9	690.9	690.9	690.7	690.4	690.1	689.7	689.4	689.7	690.1	690.4
142.5°	723.1	723.3	723.4	723.2	722.9	722.6	722.2	721.9	722.2	722.6	722.9
145°	754.6	754.4	754.3	754.0	753.3	752.6	752.0	751.3	752.0	752.6	753.3
147.5°	785.0	785.2	785.3	784.9	784.0	783.2	782.3	781.5	782.3	783.2	784.0
150°	811.7	811.7	811.7	811.4	810.7	810.0	809.4	808.7	809.4	810.0	810.7
152.5°	836.1	836.0	835.9	835.7	835.4	835.1	834.7	834.4	834.7	835.1	835.4
155°	860.5	860.7	860.8	860.8	860.8	860.8	860.8	860.8	860.8	860.8	860.8
157.5°	881.9	881.9	881.9	882.1	882.4	882.7	883.1	883.4	883.1	882.7	882.4
160°	902.1	902.2	902.3	902.4	902.6	902.7	902.9	903.1	902.9	902.7	902.6
162.5°	918.7	918.8	918.9	919.2	919.7	920.2	920.7	921.2	920.7	920.2	919.7
165°	934.3	934.6	934.8	935.1	935.6	936.1	936.6	937.1	936.6	936.1	935.6
167.5°	946.9	946.9	946.9	947.2	947.9	948.6	949.2	949.9	949.2	948.6	947.9
170°	956.9	956.8	956.7	957.1	958.0	958.8	959.7	960.5	959.7	958.8	958.0
172.5°	965.0	965.0	965.0	965.3	966.0	966.7	967.3	968.0	967.3	966.7	966.0
175°	970.8	970.9	971.0	971.4	972.3	973.1	974.0	974.8	974.0	973.1	972.3
177.5°	974.0	974.0	974.0	974.4	975.3	976.1	977.0	977.8	977.0	976.1	975.3
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1633.9	1628.4	1631.2	1617.5	1605.1	1587.2	1572.1	1569.4	1566.6	1574.9	1569.4
5°	1587.2	1580.3	1573.5	1557.0	1532.2	1517.1	1495.1	1493.8	1485.5	1473.2	1475.9
7.5°	1536.4	1532.2	1522.6	1496.5	1474.5	1448.4	1430.6	1415.4	1408.6	1397.6	1393.5
10°	1495.1	1480.0	1471.8	1442.9	1416.8	1389.3	1366.0	1355.0	1342.6	1333.0	1326.1
12.5°	1438.8	1434.7	1411.3	1388.0	1366.0	1334.4	1316.5	1284.9	1268.4	1276.6	1273.9
15°	1401.7	1382.5	1377.0	1344.0	1306.9	1286.3	1253.3	1232.7	1225.8	1213.4	1198.3
17.5°	1352.2	1339.9	1320.6	1290.4	1247.8	1218.9	1195.6	1176.3	1168.1	1151.6	1139.2
20°	1305.5	1284.9	1269.8	1242.3	1201.1	1164.0	1135.1	1122.7	1102.1	1088.4	1081.5
22.5°	1262.9	1247.8	1225.8	1184.6	1148.8	1113.1	1078.8	1060.9	1041.7	1033.4	1022.4
25°	1210.7	1185.9	1170.8	1125.5	1087.0	1058.1	1026.5	1003.2	992.2	978.4	975.7
27.5°	1159.8	1136.5	1118.6	1078.8	1032.0	994.9	975.7	959.2	940.0	940.0	933.1
30°	1109.0	1092.5	1065.0	1026.5	982.6	946.8	924.8	909.7	902.9	897.4	896.0
32.5°	1058.1	1036.2	1019.7	967.4	934.5	901.5	885.0	872.6	864.4	863.0	864.4
35°	1005.9	981.2	964.7	918.0	885.0	854.8	847.9	836.9	832.8	831.4	838.3
37.5°	951.0	931.7	911.1	872.6	835.5	817.7	803.9	799.8	798.4	806.7	809.4
40°	900.1	883.6	864.4	823.2	795.7	776.4	769.6	765.4	770.9	779.2	783.3
42.5°	852.0	828.7	813.5	776.4	751.7	740.7	732.5	732.5	738.0	747.6	754.4
45°	801.2	783.3	768.2	735.2	713.2	700.8	699.5	700.8	707.7	714.6	722.8
47.5°	751.7	733.8	717.3	689.9	670.6	663.7	662.4	663.7	674.7	684.4	694.0
50°	706.3	687.1	672.0	645.9	630.8	622.5	623.9	630.8	639.0	652.8	665.1
52.5°	652.8	639.0	625.3	601.9	588.2	582.7	586.8	592.3	607.4	617.0	632.1
55°	600.5	588.2	577.2	559.3	548.3	544.2	546.9	555.2	567.6	584.0	601.9
57.5°	552.4	538.7	527.7	515.3	503.0	504.3	505.7	516.7	531.8	546.9	567.6
60°	498.8	490.6	481.0	465.9	460.4	460.4	464.5	476.9	490.6	515.3	533.2
62.5°	450.7	439.7	432.9	423.3	415.0	416.4	426.0	437.0	453.5	474.1	497.5
65°	401.3	388.9	383.4	375.2	372.4	373.8	380.7	397.1	415.0	432.9	454.9
67.5°	346.3	342.2	336.7	328.4	331.2	332.6	339.4	353.2	372.4	390.3	415.0
70°	299.6	291.3	290.0	283.1	283.1	287.2	301.0	310.6	328.4	347.7	373.8
72.5°	250.1	243.2	243.2	237.7	241.9	246.0	252.9	266.6	283.1	302.3	324.3
75°	199.3	196.5	199.3	196.5	196.5	203.4	211.6	222.6	240.5	261.1	279.0
77.5°	153.9	153.9	152.5	156.7	156.7	160.8	171.8	182.8	196.5	213.0	232.2
80°	112.7	112.7	112.7	116.8	120.9	120.9	127.8	141.5	153.9	164.9	182.8
82.5°	77.0	77.0	77.0	79.7	85.2	85.2	93.4	101.7	115.4	125.1	133.3
85°	46.7	46.7	45.3	48.1	49.5	53.6	60.5	66.0	72.8	81.1	89.3
87.5°	20.6	20.6	22.0	23.4	24.7	27.5	30.2	33.0	39.9	42.6	46.7
90°	9.7	10.6	11.3	12.6	13.9	15.3	16.6	17.6	18.6	19.6	20.6
92.5°	28.3	29.4	29.8	30.7	31.5	32.4	33.2	33.7	34.2	34.7	35.2
95°	51.3	52.1	52.7	53.9	55.0	56.2	57.4	57.9	58.4	58.9	59.4
97.5°	77.8	78.5	79.2	80.5	81.9	83.2	84.6	85.3	85.9	86.6	87.3
100°	108.4	108.7	109.5	111.0	112.5	114.0	115.5	115.8	116.2	116.5	116.8
102.5°	141.1	141.2	141.9	143.2	144.5	145.9	147.2	147.7	148.2	148.7	149.2
105°	176.6	176.7	177.0	177.7	178.4	179.0	179.7	180.2	180.7	181.2	181.7
107.5°	213.6	213.7	213.8	213.9	214.1	214.2	214.4	215.1	215.8	216.5	217.2
110°	252.0	252.2	252.1	251.9	251.8	251.6	251.4	251.1	250.7	250.4	250.1

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	289.9	289.9	289.7	289.4	289.1	288.7	288.4	288.4	288.4	288.4	288.4
115°	329.2	329.2	329.0	328.7	328.4	328.0	327.7	327.5	327.3	327.2	327.0
117.5°	366.2	366.2	366.1	366.0	365.8	365.7	365.5	365.0	364.5	364.0	363.5
120°	405.9	406.2	406.0	405.5	405.0	404.5	404.0	403.2	402.3	401.5	400.6
122.5°	442.4	442.5	442.4	442.2	442.1	441.9	441.7	441.2	440.7	440.2	439.7
125°	479.5	479.5	479.4	479.2	479.1	478.9	478.7	478.4	478.0	477.7	477.4
127.5°	515.5	515.7	515.5	515.2	514.9	514.5	514.2	513.9	513.5	513.2	512.9
130°	551.7	552.0	552.0	552.0	552.0	552.0	552.0	551.7	551.3	551.0	550.7
132.5°	588.0	588.2	588.1	587.9	587.8	587.6	587.4	587.1	586.7	586.4	586.1
135°	622.4	622.9	622.9	622.9	622.9	622.9	622.9	622.6	622.2	621.9	621.6
137.5°	655.9	656.2	656.4	656.7	657.0	657.4	657.7	657.2	656.7	656.2	655.7
140°	690.7	690.9	690.9	690.9	690.9	690.9	690.9	690.7	690.5	690.4	690.2
142.5°	723.2	723.4	723.3	723.1	723.0	722.8	722.6	722.6	722.6	722.6	722.6
145°	754.0	754.3	754.4	754.6	754.7	754.9	755.1	754.9	754.7	754.6	754.4
147.5°	784.9	785.3	785.2	785.0	784.9	784.7	784.5	784.3	784.2	784.0	783.9
150°	811.4	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7
152.5°	835.7	835.9	836.0	836.1	836.3	836.4	836.6	837.1	837.6	838.1	838.6
155°	860.8	860.8	860.7	860.5	860.4	860.2	860.0	860.7	861.4	862.1	862.8
157.5°	882.1	881.9	881.9	881.9	881.9	881.9	881.9	882.4	882.9	883.4	883.9
160°	902.4	902.3	902.2	902.1	901.9	901.8	901.6	902.1	902.6	903.1	903.6
162.5°	919.2	918.9	918.8	918.7	918.5	918.4	918.2	919.2	920.2	921.2	922.2
165°	935.1	934.8	934.6	934.3	934.0	933.6	933.3	934.3	935.3	936.3	937.3
167.5°	947.2	946.9	946.9	946.9	946.9	946.9	946.9	947.9	948.9	949.9	950.9
170°	957.1	956.7	956.8	956.9	957.1	957.2	957.4	958.4	959.4	960.5	961.5
172.5°	965.3	965.0	965.0	965.0	965.0	965.0	965.0	966.2	967.4	968.5	969.7
175°	971.4	971.0	970.9	970.8	970.6	970.5	970.3	971.5	972.7	973.8	975.0
177.5°	974.4	974.0	974.0	974.0	974.0	974.0	974.0	975.2	976.4	977.5	978.7
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1565.2	1563.9	1557.0	1559.7	1551.5	1554.2	1558.4	1559.7	1565.2	1561.1	1559.7
5°	1469.0	1466.3	1462.2	1458.0	1456.7	1462.2	1452.5	1455.3	1458.0	1462.2	1467.7
7.5°	1390.7	1389.3	1385.2	1378.3	1375.6	1372.8	1374.2	1383.8	1382.5	1381.1	1390.7
10°	1319.2	1320.6	1312.4	1311.0	1302.8	1301.4	1302.8	1305.5	1309.6	1315.1	1316.5
12.5°	1245.0	1262.9	1247.8	1242.3	1229.9	1236.8	1239.5	1227.2	1234.0	1238.2	1258.8
15°	1198.3	1190.1	1180.5	1180.5	1175.0	1172.2	1165.3	1175.0	1180.5	1188.7	1185.9
17.5°	1133.7	1120.0	1114.5	1109.0	1110.4	1115.9	1100.7	1122.7	1122.7	1126.9	1120.0
20°	1077.4	1066.4	1059.5	1056.8	1052.6	1049.9	1048.5	1054.0	1062.3	1065.0	1071.9
22.5°	1018.3	1018.3	1007.3	1003.2	1000.4	996.3	1003.2	999.1	1004.6	1010.0	1021.0
25°	968.8	968.8	964.7	959.2	955.1	952.3	956.5	955.1	959.2	966.1	968.8
27.5°	929.0	924.8	923.5	922.1	920.7	922.1	920.7	924.8	929.0	930.3	927.6
30°	894.6	890.5	891.9	891.9	893.2	891.9	890.5	894.6	896.0	893.2	894.6
32.5°	863.0	863.0	865.8	867.1	867.1	868.5	869.9	867.1	868.5	864.4	865.8
35°	836.9	839.6	842.4	843.8	845.1	843.8	846.5	845.1	842.4	839.6	838.3
37.5°	810.8	813.5	819.0	820.4	824.5	825.9	823.2	823.2	821.8	816.3	813.5
40°	783.3	786.1	792.9	797.0	799.8	803.9	801.2	801.2	795.7	790.2	786.1
42.5°	757.2	762.7	769.6	773.7	779.2	779.2	779.2	776.4	769.6	764.1	759.9
45°	731.1	732.5	742.1	748.9	754.4	754.4	754.4	750.3	746.2	735.2	729.7
47.5°	702.2	706.3	717.3	724.2	729.7	731.1	731.1	727.0	718.7	709.1	702.2
50°	670.6	677.5	689.9	699.5	706.3	709.1	705.0	702.2	692.6	681.6	673.4
52.5°	640.4	648.6	663.7	672.0	681.6	683.0	681.6	677.5	666.5	651.4	644.5
55°	610.2	617.0	633.5	647.3	655.5	658.2	655.5	648.6	634.9	619.8	612.9
57.5°	577.2	586.8	604.7	618.4	628.0	629.4	626.6	619.8	608.8	589.5	579.9
60°	542.8	555.2	573.0	586.8	599.2	600.5	597.8	588.2	574.4	555.2	546.9
62.5°	508.5	518.1	538.7	553.8	563.4	570.3	564.8	555.2	541.4	522.2	509.8
65°	468.6	482.3	500.2	514.0	525.0	526.3	523.6	515.3	500.2	479.6	470.0
67.5°	430.1	439.7	457.6	475.5	479.6	483.7	479.6	471.4	459.0	441.1	427.4
70°	383.4	391.7	413.6	426.0	431.5	435.6	432.9	424.6	413.6	397.1	386.2
72.5°	336.7	343.6	364.2	373.8	384.8	383.4	382.0	376.5	361.4	350.4	343.6
75°	287.2	295.5	309.2	321.6	325.7	325.7	325.7	321.6	311.9	294.1	287.2
77.5°	241.9	246.0	257.0	263.8	268.0	269.3	268.0	261.1	255.6	243.2	239.1
80°	185.5	196.5	204.8	206.1	211.6	211.6	211.6	208.9	203.4	191.0	189.6
82.5°	140.2	142.9	151.2	155.3	158.0	156.7	156.7	151.2	149.8	142.9	140.2
85°	94.8	98.9	97.6	103.1	104.4	101.7	101.7	104.4	97.6	98.9	94.8
87.5°	52.2	52.2	55.0	53.6	59.1	59.1	56.3	57.7	55.0	53.6	52.2
90°	21.1	21.3	21.6	22.0	22.3	22.7	22.3	22.0	21.6	21.3	21.1
92.5°	35.5	35.6	35.7	35.9	36.0	36.2	36.0	35.9	35.7	35.6	35.5
95°	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7
97.5°	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6
100°	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0
102.5°	149.5	149.6	149.8	149.9	150.1	150.3	150.1	149.9	149.8	149.6	149.5
105°	182.0	182.2	182.7	183.2	183.7	184.2	183.7	183.2	182.7	182.2	182.0
107.5°	217.5	217.4	217.2	217.1	216.9	216.7	216.9	217.1	217.2	217.4	217.5
110°	249.9	250.2	250.7	251.2	251.7	252.2	251.7	251.2	250.7	250.2	249.9

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4
115°	326.9	326.8	326.7	326.5	326.4	326.2	326.4	326.5	326.7	326.8	326.9
117.5°	363.2	362.9	362.4	361.9	361.4	360.9	361.4	361.9	362.4	362.9	363.2
120°	400.2	400.4	400.7	401.0	401.4	401.7	401.4	401.0	400.7	400.4	400.2
122.5°	439.5	439.1	438.2	437.4	436.5	435.7	436.5	437.4	438.2	439.1	439.5
125°	477.2	477.0	476.7	476.4	476.0	475.7	476.0	476.4	476.7	477.0	477.2
127.5°	512.7	512.6	512.4	512.3	512.1	511.9	512.1	512.3	512.4	512.6	512.7
130°	550.5	550.2	549.5	548.8	548.1	547.4	548.1	548.8	549.5	550.2	550.5
132.5°	585.9	585.8	585.7	585.5	585.4	585.2	585.4	585.5	585.7	585.8	585.9
135°	621.4	621.2	620.7	620.2	619.7	619.2	619.7	620.2	620.7	621.2	621.4
137.5°	655.4	655.5	655.7	655.8	656.0	656.2	656.0	655.8	655.7	655.5	655.4
140°	690.1	690.0	689.9	689.7	689.6	689.4	689.6	689.7	689.9	690.0	690.1
142.5°	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6
145°	754.3	754.1	753.6	753.1	752.6	752.1	752.6	753.1	753.6	754.1	754.3
147.5°	783.8	783.7	783.5	783.4	783.2	783.0	783.2	783.4	783.5	783.7	783.8
150°	811.7	811.6	811.5	811.3	811.2	811.0	811.2	811.3	811.5	811.6	811.7
152.5°	838.9	838.6	838.1	837.6	837.1	836.6	837.1	837.6	838.1	838.6	838.9
155°	863.1	862.8	862.1	861.4	860.7	860.0	860.7	861.4	862.1	862.8	863.1
157.5°	884.2	883.9	883.4	882.9	882.4	881.9	882.4	882.9	883.4	883.9	884.2
160°	903.8	903.4	902.6	901.7	900.9	900.1	900.9	901.7	902.6	903.4	903.8
162.5°	922.7	922.3	921.4	920.6	919.7	918.9	919.7	920.6	921.4	922.3	922.7
165°	937.8	937.5	936.8	936.1	935.5	934.8	935.5	936.1	936.8	937.5	937.8
167.5°	951.4	950.9	949.9	948.9	947.9	946.9	947.9	948.9	949.9	950.9	951.4
170°	962.0	961.4	960.2	959.1	957.9	956.7	957.9	959.1	960.2	961.4	962.0
172.5°	970.3	969.7	968.5	967.4	966.2	965.0	966.2	967.4	968.5	969.7	970.3
175°	975.6	975.0	973.8	972.7	971.5	970.3	971.5	972.7	973.8	975.0	975.6
177.5°	979.3	978.6	977.3	976.0	974.6	973.3	974.6	976.0	977.3	978.6	979.3
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1559.7	1568.0	1559.7	1565.2	1568.0	1574.9	1577.6	1590.0	1594.1	1603.7	1603.7
5°	1466.3	1470.4	1471.8	1477.3	1482.8	1496.5	1506.1	1524.0	1544.6	1547.4	1559.7
7.5°	1390.7	1397.6	1408.6	1404.4	1414.1	1434.7	1447.0	1469.0	1489.6	1500.6	1515.8
10°	1323.4	1331.6	1335.7	1339.9	1357.7	1375.6	1394.8	1409.9	1437.4	1453.9	1466.3
12.5°	1268.4	1261.5	1269.8	1284.9	1305.5	1316.5	1342.6	1366.0	1386.6	1404.4	1415.4
15°	1196.9	1202.4	1210.7	1236.8	1242.3	1269.8	1279.4	1305.5	1344.0	1360.5	1374.2
17.5°	1128.2	1146.1	1162.6	1172.2	1188.7	1210.7	1238.2	1267.0	1291.8	1311.0	1327.5
20°	1073.3	1091.1	1100.7	1107.6	1124.1	1154.3	1180.5	1216.2	1247.8	1262.9	1284.9
22.5°	1029.3	1029.3	1043.0	1063.6	1073.3	1102.1	1124.1	1162.6	1196.9	1216.2	1236.8
25°	974.3	982.6	993.6	1011.4	1025.2	1048.5	1080.1	1113.1	1150.2	1166.7	1192.8
27.5°	929.0	938.6	953.7	957.8	971.6	992.2	1025.2	1060.9	1099.4	1117.2	1139.2
30°	894.6	900.1	905.6	913.9	926.2	944.1	971.6	1003.2	1049.9	1063.6	1091.1
32.5°	864.4	867.1	869.9	876.7	883.6	901.5	923.5	957.8	996.3	1016.9	1041.7
35°	836.9	834.1	835.5	839.6	846.5	853.4	876.7	905.6	941.3	966.1	985.3
37.5°	810.8	805.3	803.9	803.9	806.7	814.9	832.8	857.5	896.0	916.6	935.8
40°	781.9	776.4	773.7	772.3	770.9	776.4	790.2	814.9	845.1	864.4	886.4
42.5°	754.4	748.9	742.1	740.7	738.0	740.7	750.3	773.7	799.8	819.0	836.9
45°	727.0	717.3	709.1	703.6	705.0	700.8	707.7	725.6	755.8	768.2	786.1
47.5°	696.7	685.7	674.7	669.2	663.7	666.5	669.2	684.4	710.5	722.8	740.7
50°	667.9	652.8	640.4	633.5	629.4	626.6	629.4	644.5	663.7	674.7	689.9
52.5°	634.9	619.8	607.4	596.4	590.9	586.8	588.2	601.9	619.8	630.8	645.9
55°	604.7	585.4	568.9	555.2	551.1	549.7	548.3	557.9	573.0	584.0	596.4
57.5°	570.3	551.1	533.2	516.7	508.5	507.1	507.1	509.8	529.1	537.3	544.2
60°	535.9	515.3	496.1	481.0	468.6	464.5	463.1	468.6	478.2	486.5	496.1
62.5°	497.5	476.9	453.5	439.7	427.4	416.4	420.5	421.9	435.6	439.7	448.0
65°	460.4	437.0	417.8	395.8	382.0	375.2	372.4	375.2	386.2	387.5	393.0
67.5°	417.8	395.8	372.4	357.3	344.9	332.6	329.8	329.8	335.3	339.4	346.3
70°	376.5	354.5	328.4	311.9	299.6	288.6	284.5	283.1	287.2	290.0	296.8
72.5°	328.4	306.4	287.2	269.3	254.2	246.0	241.9	239.1	243.2	246.0	247.4
75°	277.6	259.7	240.5	222.6	213.0	204.8	199.3	195.1	197.9	197.9	197.9
77.5°	229.5	211.6	196.5	184.1	171.8	162.2	158.0	153.9	155.3	155.3	158.0
80°	178.6	166.3	153.9	142.9	131.9	123.7	120.9	116.8	114.1	112.7	112.7
82.5°	131.9	122.3	111.3	101.7	96.2	87.9	85.2	79.7	79.7	78.3	78.3
85°	87.9	82.5	71.5	64.6	60.5	56.3	53.6	50.8	46.7	46.7	45.3
87.5°	46.7	44.0	41.2	33.0	33.0	28.9	27.5	26.1	22.0	23.4	23.4
90°	20.6	19.6	18.6	17.6	16.6	15.3	13.9	12.6	11.3	10.6	9.7
92.5°	35.2	34.7	34.2	33.7	33.2	32.4	31.5	30.7	29.8	29.4	28.3
95°	59.4	58.9	58.4	57.9	57.4	56.2	55.0	53.9	52.7	52.1	51.3
97.5°	87.3	86.6	85.9	85.3	84.6	83.2	81.9	80.5	79.2	78.5	77.8
100°	116.8	116.5	116.2	115.8	115.5	114.0	112.5	111.0	109.5	108.7	108.4
102.5°	149.2	148.7	148.2	147.7	147.2	145.9	144.5	143.2	141.9	141.2	141.1
105°	181.7	181.2	180.7	180.2	179.7	179.0	178.4	177.7	177.0	176.7	176.6
107.5°	217.2	216.5	215.8	215.1	214.4	214.2	214.1	213.9	213.8	213.7	213.6
110°	250.1	250.4	250.7	251.1	251.4	251.6	251.8	251.9	252.1	252.2	252.0

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	288.4	288.4	288.4	288.4	288.4	288.7	289.1	289.4	289.7	289.9	289.9
115°	327.0	327.2	327.3	327.5	327.7	328.0	328.4	328.7	329.0	329.2	329.2
117.5°	363.5	364.0	364.5	365.0	365.5	365.7	365.8	366.0	366.1	366.2	366.2
120°	400.6	401.5	402.3	403.2	404.0	404.5	405.0	405.5	406.0	406.2	405.9
122.5°	439.7	440.2	440.7	441.2	441.7	441.9	442.1	442.2	442.4	442.5	442.4
125°	477.4	477.7	478.0	478.4	478.7	478.9	479.1	479.2	479.4	479.5	479.5
127.5°	512.9	513.2	513.5	513.9	514.2	514.5	514.9	515.2	515.5	515.7	515.5
130°	550.7	551.0	551.3	551.7	552.0	552.0	552.0	552.0	552.0	552.0	551.7
132.5°	586.1	586.4	586.7	587.1	587.4	587.6	587.8	587.9	588.1	588.2	588.0
135°	621.6	621.9	622.2	622.6	622.9	622.9	622.9	622.9	622.9	622.9	622.4
137.5°	655.7	656.2	656.7	657.2	657.7	657.4	657.0	656.7	656.4	656.2	655.9
140°	690.2	690.4	690.5	690.7	690.9	690.9	690.9	690.9	690.9	690.9	690.7
142.5°	722.6	722.6	722.6	722.6	722.6	722.8	723.0	723.1	723.3	723.4	723.2
145°	754.4	754.6	754.7	754.9	755.1	754.9	754.7	754.6	754.4	754.3	754.0
147.5°	783.9	784.0	784.2	784.3	784.5	784.7	784.9	785.0	785.2	785.3	784.9
150°	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.4
152.5°	838.6	838.1	837.6	837.1	836.6	836.4	836.3	836.1	836.0	835.9	835.7
155°	862.8	862.1	861.4	860.7	860.0	860.2	860.4	860.5	860.7	860.8	860.8
157.5°	883.9	883.4	882.9	882.4	881.9	881.9	881.9	881.9	881.9	881.9	882.1
160°	903.6	903.1	902.6	902.1	901.6	901.8	901.9	902.1	902.2	902.3	902.4
162.5°	922.2	921.2	920.2	919.2	918.2	918.4	918.5	918.7	918.8	918.9	919.2
165°	937.3	936.3	935.3	934.3	933.3	933.6	934.0	934.3	934.6	934.8	935.1
167.5°	950.9	949.9	948.9	947.9	946.9	946.9	946.9	946.9	946.9	946.9	947.2
170°	961.5	960.5	959.4	958.4	957.4	957.2	957.1	956.9	956.8	956.7	957.1
172.5°	969.7	968.5	967.4	966.2	965.0	965.0	965.0	965.0	965.0	965.0	965.3
175°	975.0	973.8	972.7	971.5	970.3	970.5	970.6	970.8	970.9	971.0	971.4
177.5°	978.7	977.5	976.4	975.2	974.0	974.0	974.0	974.0	974.0	974.0	974.4
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1658.7	1658.7	1658.7	1658.7
2.5°	1613.3	1627.1	1639.4	1658.7
5°	1577.6	1596.8	1622.9	1651.8
7.5°	1536.4	1566.6	1601.0	1640.8
10°	1497.9	1532.2	1576.2	1624.3
12.5°	1458.0	1499.3	1547.4	1599.6
15°	1412.7	1453.9	1507.5	1577.6
17.5°	1371.5	1420.9	1478.7	1552.9
20°	1323.4	1370.1	1433.3	1518.5
22.5°	1280.8	1334.4	1404.4	1478.7
25°	1234.0	1280.8	1350.9	1440.2
27.5°	1187.3	1245.0	1312.4	1399.0
30°	1142.0	1190.1	1262.9	1353.6
32.5°	1092.5	1150.2	1217.6	1302.8
35°	1038.9	1093.9	1157.1	1249.2
37.5°	990.8	1044.4	1109.0	1190.1
40°	937.2	993.6	1052.6	1133.7
42.5°	885.0	935.8	994.9	1069.1
45°	834.1	878.1	931.7	996.3
47.5°	781.9	819.0	868.5	926.2
50°	725.6	765.4	802.5	850.6
52.5°	673.4	707.7	738.0	777.8
55°	622.5	645.9	670.6	700.8
57.5°	568.9	586.8	604.7	636.3
60°	515.3	531.8	541.4	562.1
62.5°	463.1	470.0	482.3	494.7
65°	405.4	415.0	421.9	437.0
67.5°	353.2	357.3	364.2	373.8
70°	298.2	307.8	310.6	317.4
72.5°	251.5	255.6	258.4	259.7
75°	199.3	203.4	206.1	214.4
77.5°	156.7	155.3	160.8	162.2
80°	115.4	111.3	112.7	118.2
82.5°	75.6	77.0	75.6	75.6
85°	46.7	45.3	42.6	44.0
87.5°	20.6	20.6	19.2	19.2
90°	7.8	6.0	4.1	2.3
92.5°	26.1	24.0	21.8	19.6
95°	49.8	48.3	46.8	45.3
97.5°	76.5	75.2	73.8	72.5
100°	107.7	107.0	106.4	105.7
102.5°	140.9	140.8	140.6	140.4
105°	176.4	176.3	176.1	175.9
107.5°	213.4	213.3	213.1	212.9
110°	251.7	251.4	251.0	250.7



TEST NUMBER: P1033213

CATALOG NUMBER: S124DIW-B1020D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	289.9	289.9	289.9	289.9
115°	329.2	329.2	329.2	329.2
117.5°	366.2	366.2	366.2	366.2
120°	405.2	404.5	403.9	403.2
122.5°	442.2	442.1	441.9	441.7
125°	479.5	479.5	479.5	479.5
127.5°	515.0	514.5	514.0	513.5
130°	551.2	550.7	550.2	549.7
132.5°	587.7	587.4	587.0	586.7
135°	621.4	620.4	619.4	618.4
137.5°	655.4	654.9	654.4	653.9
140°	690.4	690.1	689.7	689.4
142.5°	722.9	722.6	722.2	721.9
145°	753.3	752.6	752.0	751.3
147.5°	784.0	783.2	782.3	781.5
150°	810.7	810.0	809.4	808.7
152.5°	835.4	835.1	834.7	834.4
155°	860.8	860.8	860.8	860.8
157.5°	882.4	882.7	883.1	883.4
160°	902.6	902.7	902.9	903.1
162.5°	919.7	920.2	920.7	921.2
165°	935.6	936.1	936.6	937.1
167.5°	947.9	948.6	949.2	949.9
170°	958.0	958.8	959.7	960.5
172.5°	966.0	966.7	967.3	968.0
175°	972.3	973.1	974.0	974.8
177.5°	975.3	976.1	977.0	977.8
180°	976.3	976.3	976.3	976.3

(END OF REPORT)