

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033231

Luminaire Tested: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033231
REPORT IS A COMBINATION OF REPORTS P996941 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D770UB50-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7007.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	60	59	58
2	92	85	79	73	86	80	74	70	70	66	63	62	58	56	54	51	49
3	84	75	67	62	79	70	64	59	62	57	53	55	51	48	48	45	42
4	77	66	58	52	72	63	56	50	56	50	45	49	45	41	43	39	37
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	28	25
8	57	44	36	31	53	42	35	30	38	32	27	33	29	25	30	26	23
9	53	40	33	28	49	38	31	27	34	29	25	31	26	23	27	24	21
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13006	13006	13006	13006
5°	12973	14921	13048	11211
10°	12876	17407	12974	9836
15°	12721	20068	12810	8801
20°	12556	21760	12647	7890
25°	12316	21511	12434	7219
30°	12081	17780	12228	6873
35°	11751	13250	11880	6663
40°	11366	9981	11476	6560
45°	10778	8010	10912	6420
50°	10076	6749	10222	6355
55°	9250	5874	9396	6280
60°	8448	5172	8696	6175
65°	7695	4451	7769	5919
70°	6809	3662	6956	5450
75°	5939	2814	5902	4631
80°	4672	1848	4619	3515
85°	3078	830	2882	2050

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 16817 cd/sqm

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	2.2
10°-20°	479.1	6.8
20°-30°	761.1	10.9
30°-40°	845.7	12.1
40°-50°	769.1	11.0
50°-60°	628.5	9.0
60°-70°	448.6	6.4
70°-80°	246.9	3.5
80°-90°	68.7	1.0
90°-100°	61.2	0.9
100°-110°	183.2	2.6
110°-120°	311.3	4.4
120°-130°	410.5	5.9
130°-140°	461.1	6.6
140°-150°	453.2	6.5
150°-160°	381.1	5.4
160°-170°	253.6	3.6
170°-180°	88.8	1.3
0°-30°	1395.4	19.9
0°-40°	2241.2	32.0
0°-60°	3638.8	51.9
0°-90°	4403.0	62.8
90°-120°	555.7	7.9
90°-150°	1880.4	26.8
90°-180°	2604.0	37.2
0°-180°	7007.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1595	1595	1595	1595	1595	
5°	1588	1871	1598	1406	1588	151
15°	1517	2570	1528	1127	1517	428
25°	1385	2729	1398	916	1385	638
35°	1201	1613	1214	811	1201	750
45°	958	905	970	725	958	739
55°	674	592	684	633	674	606
65°	420	381	424	506	420	415
75°	206	190	205	313	206	216
85°	42	40	40	98	42	49
90°	2	22	2	22	2	6
95°	44	57	44	57	44	47
105°	169	177	169	177	169	179
115°	316	314	316	314	316	312
125°	461	457	461	457	461	411
135°	594	595	594	595	594	460
145°	722	723	722	723	722	452
155°	827	827	827	827	827	381
165°	901	899	901	899	901	254
175°	937	933	937	933	937	89
180°	938	938	938	938	938	

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1594.9	1610.8	1617.4	1622.6	1639.8	1645.1	1646.4	1654.4	1661.0	1662.3	1662.3
5°	1588.3	1613.4	1633.2	1651.7	1679.5	1691.4	1705.9	1721.7	1742.9	1756.1	1762.7
7.5°	1577.7	1614.7	1645.1	1676.8	1715.1	1738.9	1752.1	1794.4	1823.5	1847.3	1876.3
10°	1561.9	1609.4	1653.0	1699.3	1753.5	1782.5	1811.6	1863.1	1904.1	1950.3	1987.3
12.5°	1538.1	1600.2	1653.0	1717.8	1785.2	1819.5	1853.9	1943.7	1991.3	2032.3	2098.3
15°	1516.9	1579.0	1654.4	1720.4	1803.7	1855.2	1905.4	1963.6	2038.9	2127.4	2190.8
17.5°	1493.2	1571.1	1641.1	1733.6	1826.1	1875.0	1916.0	2005.8	2111.6	2198.8	2256.9
20°	1460.1	1539.4	1631.9	1729.7	1839.3	1877.7	1931.8	2052.1	2147.2	2233.1	2328.3
22.5°	1421.8	1514.3	1612.1	1705.9	1819.5	1900.1	1959.6	2065.3	2180.3	2279.4	2386.4
25°	1384.8	1485.2	1571.1	1699.3	1819.5	1873.7	1941.1	2066.6	2192.2	2312.4	2422.1
27.5°	1345.2	1439.0	1555.3	1657.0	1793.1	1852.6	1925.2	2062.7	2196.1	2316.4	2434.0
30°	1301.6	1402.0	1498.4	1618.7	1750.8	1827.5	1894.8	2044.2	2180.3	2305.8	2415.5
32.5°	1252.7	1347.8	1450.9	1564.5	1703.2	1781.2	1865.8	2019.1	2164.4	2272.8	2357.3
35°	1201.1	1297.6	1387.4	1503.7	1646.4	1724.4	1806.3	1975.5	2119.5	2208.0	2256.9
37.5°	1144.3	1235.5	1324.0	1439.0	1581.7	1664.9	1748.2	1912.0	2048.1	2122.1	2108.9
40°	1090.1	1172.1	1254.0	1362.3	1511.6	1600.2	1672.9	1838.0	1957.0	1988.7	1945.1
42.5°	1028.0	1098.1	1177.3	1288.3	1433.7	1516.9	1608.1	1758.7	1847.3	1834.1	1760.1
45°	958.0	1020.1	1099.4	1203.8	1351.8	1437.7	1514.3	1657.0	1721.7	1688.7	1553.9
47.5°	890.6	951.4	1016.1	1120.5	1264.6	1337.2	1415.2	1543.4	1580.4	1510.3	1375.5
50°	817.9	868.1	935.5	1034.6	1169.4	1246.1	1310.8	1413.9	1427.1	1341.2	1201.1
52.5°	747.9	790.2	854.9	952.7	1078.2	1139.0	1202.4	1293.6	1283.1	1194.5	1059.7
55°	673.9	713.5	773.0	862.9	973.9	1032.0	1086.2	1166.8	1144.3	1053.1	935.5
57.5°	611.8	639.5	697.7	780.9	872.1	935.5	981.8	1045.2	1010.8	919.7	810.0
60°	540.4	574.8	623.7	691.1	780.9	823.2	864.2	906.5	882.7	795.5	697.7
62.5°	475.7	502.1	544.4	609.2	679.2	717.5	761.1	787.5	763.8	683.1	601.2
65°	420.2	441.3	474.4	527.2	594.6	626.3	651.4	676.5	656.7	581.4	521.9
67.5°	359.4	377.9	405.7	447.9	504.8	527.2	551.0	568.2	545.7	495.5	437.4
70°	305.2	318.5	344.9	376.6	416.2	437.4	457.2	474.4	454.6	412.3	368.7
72.5°	249.7	260.3	284.1	306.6	342.2	356.8	371.3	384.5	377.9	338.3	302.6
75°	206.1	210.1	226.0	244.5	266.9	282.8	293.3	301.3	296.0	264.3	241.8
77.5°	155.9	161.2	173.1	187.6	207.5	216.7	223.3	231.2	224.6	199.5	183.7
80°	113.6	115.0	121.6	134.8	148.0	149.3	155.9	166.5	162.5	145.4	133.5
82.5°	72.7	76.6	79.3	87.2	96.5	99.1	103.1	105.7	104.4	93.8	89.9
85°	42.3	42.3	44.9	50.2	52.9	56.8	58.1	59.5	62.1	55.5	51.5
87.5°	18.5	19.8	19.8	21.1	23.8	23.8	25.1	26.4	27.7	26.4	22.5
90°	2.2	4.0	5.8	7.5	9.3	10.2	10.8	12.1	13.4	14.7	16.0
92.5°	18.9	21.0	23.1	25.2	27.3	28.3	28.7	29.5	30.3	31.1	31.9
95°	43.5	45.0	46.4	47.9	49.4	50.1	50.7	51.8	52.9	54.1	55.2
97.5°	69.7	71.0	72.3	73.6	74.9	75.5	76.1	77.4	78.7	80.0	81.3
100°	101.6	102.2	102.9	103.5	104.2	104.5	105.2	106.7	108.2	109.6	111.1
102.5°	135.0	135.2	135.3	135.5	135.6	135.7	136.3	137.6	138.9	140.2	141.5
105°	169.1	169.3	169.4	169.6	169.7	169.8	170.1	170.8	171.4	172.1	172.7
107.5°	204.7	204.9	205.0	205.2	205.3	205.4	205.5	205.6	205.8	205.9	206.1
110°	241.0	241.3	241.6	241.9	242.2	242.4	242.3	242.2	242.0	241.9	241.7

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	278.7	278.7	278.7	278.7	278.7	278.7	278.5	278.2	277.9	277.6	277.3
115°	316.5	316.5	316.5	316.5	316.5	316.5	316.3	316.0	315.7	315.3	315.0
117.5°	352.0	352.0	352.0	352.0	352.0	352.0	351.9	351.8	351.6	351.5	351.3
120°	387.6	388.2	388.9	389.5	390.2	390.5	390.3	389.8	389.3	388.8	388.3
122.5°	424.6	424.8	424.9	425.1	425.2	425.3	425.2	425.1	424.9	424.8	424.6
125°	460.9	460.9	460.9	460.9	460.9	460.9	460.8	460.7	460.5	460.4	460.2
127.5°	493.6	494.1	494.5	495.0	495.5	495.7	495.5	495.2	494.9	494.6	494.3
130°	528.4	528.9	529.4	529.9	530.4	530.6	530.6	530.6	530.6	530.6	530.6
132.5°	564.0	564.3	564.6	564.9	565.2	565.4	565.3	565.2	565.0	564.9	564.7
135°	594.5	595.5	596.4	597.4	598.3	598.8	598.8	598.8	598.8	598.8	598.8
137.5°	628.6	629.1	629.5	630.0	630.5	630.7	630.9	631.2	631.5	631.9	632.2
140°	662.7	663.0	663.3	663.6	663.9	664.1	664.1	664.1	664.1	664.1	664.1
142.5°	693.9	694.2	694.5	694.8	695.1	695.3	695.2	695.1	694.9	694.8	694.6
145°	722.2	722.8	723.5	724.1	724.8	725.1	725.2	725.3	725.5	725.6	725.8
147.5°	751.2	752.0	752.8	753.7	754.5	754.9	754.8	754.6	754.5	754.3	754.1
150°	777.4	778.0	778.7	779.3	780.0	780.3	780.3	780.3	780.3	780.3	780.3
152.5°	802.0	802.3	802.7	803.0	803.3	803.5	803.6	803.7	803.9	804.0	804.2
155°	827.4	827.4	827.4	827.4	827.4	827.4	827.3	827.2	827.0	826.9	826.7
157.5°	849.2	848.9	848.6	848.3	848.0	847.8	847.8	847.8	847.8	847.8	847.8
160°	868.1	867.9	867.8	867.6	867.5	867.4	867.3	867.1	867.0	866.8	866.6
162.5°	885.5	885.0	884.5	884.0	883.5	883.3	883.2	883.1	882.9	882.8	882.6
165°	900.8	900.3	899.8	899.3	898.8	898.6	898.4	898.1	897.8	897.4	897.1
167.5°	913.1	912.5	911.8	911.2	910.5	910.2	910.2	910.2	910.2	910.2	910.2
170°	923.3	922.5	921.7	920.8	920.0	919.6	919.7	919.9	920.0	920.2	920.4
172.5°	930.5	929.9	929.2	928.6	927.9	927.6	927.6	927.6	927.6	927.6	927.6
175°	937.0	936.2	935.4	934.6	933.8	933.4	933.3	933.2	933.0	932.9	932.7
177.5°	940.0	939.2	938.4	937.5	936.7	936.3	936.3	936.3	936.3	936.3	936.3
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1666.2	1690.0	1700.6	1703.2	1717.8	1708.5	1712.5	1711.2	1721.7	1723.1	1723.1
5°	1787.8	1815.6	1824.8	1838.0	1857.8	1863.1	1859.2	1867.1	1881.6	1871.1	1886.9
7.5°	1916.0	1946.4	1967.5	1996.6	2003.2	2020.4	2030.9	2040.2	2042.8	2044.2	2046.8
10°	2034.9	2073.2	2102.3	2151.2	2161.8	2171.0	2217.3	2198.8	2222.5	2214.6	2217.3
12.5°	2131.4	2206.7	2230.5	2312.4	2320.3	2352.0	2349.4	2378.5	2383.8	2394.3	2383.8
15°	2258.2	2345.4	2383.8	2430.0	2456.4	2493.4	2500.0	2539.7	2555.5	2570.1	2555.5
17.5°	2374.5	2420.8	2518.5	2555.5	2572.7	2592.5	2642.7	2657.3	2681.1	2671.8	2698.2
20°	2432.6	2498.7	2601.8	2665.2	2691.6	2710.1	2752.4	2774.9	2784.1	2784.1	2786.8
22.5°	2484.2	2579.3	2656.0	2728.6	2752.4	2765.6	2790.7	2807.9	2811.9	2814.5	2817.2
25°	2530.4	2616.3	2678.4	2719.4	2728.6	2728.6	2743.2	2732.6	2715.4	2728.6	2736.6
27.5°	2530.4	2591.2	2619.0	2633.5	2633.5	2597.8	2576.7	2533.1	2496.1	2485.5	2509.3
30°	2488.1	2515.9	2477.6	2441.9	2414.1	2390.4	2307.1	2241.0	2227.8	2218.6	2254.3
32.5°	2390.4	2354.7	2279.4	2176.3	2135.3	2081.2	2016.4	1966.2	1935.8	1925.2	1917.3
35°	2217.3	2124.8	2027.0	1888.2	1859.2	1790.5	1701.9	1664.9	1614.7	1613.4	1630.6
37.5°	2028.3	1885.6	1779.9	1647.8	1606.8	1534.1	1450.9	1412.5	1378.2	1351.8	1383.5
40°	1807.6	1683.4	1522.2	1413.9	1355.7	1317.4	1247.4	1205.1	1189.2	1176.0	1195.8
42.5°	1601.5	1465.4	1339.9	1228.9	1181.3	1137.7	1091.5	1050.5	1038.6	1037.3	1051.8
45°	1396.7	1263.2	1147.0	1051.8	1021.4	995.0	950.1	938.2	918.4	905.1	911.7
47.5°	1232.8	1095.4	999.0	926.3	899.9	877.4	848.3	828.5	811.3	806.0	814.0
50°	1071.6	979.1	880.0	819.3	799.4	778.3	755.8	737.3	729.4	724.1	729.4
52.5°	942.1	843.0	775.6	726.8	706.9	691.1	675.2	667.3	656.7	659.4	664.7
55°	825.9	738.6	681.8	646.2	634.3	627.7	607.8	598.6	594.6	592.0	594.6
57.5°	716.2	652.8	610.5	580.1	564.2	560.3	544.4	544.4	540.4	536.5	537.8
60°	629.0	574.8	533.8	510.0	507.4	500.8	490.2	488.9	479.7	483.6	484.9
62.5°	540.4	496.8	469.1	454.6	445.3	442.7	436.1	434.7	430.8	432.1	429.4
65°	470.4	434.7	407.0	395.1	391.1	389.8	384.5	380.6	377.9	380.6	377.9
67.5°	400.4	376.6	355.4	343.6	338.3	336.9	333.0	330.3	331.7	327.7	330.3
70°	334.3	310.5	297.3	290.7	288.1	284.1	284.1	284.1	284.1	281.5	280.1
72.5°	281.5	257.7	248.4	244.5	241.8	240.5	236.5	237.8	236.5	235.2	240.5
75°	223.3	208.8	199.5	195.6	198.2	194.2	190.3	192.9	189.0	190.3	195.6
77.5°	169.1	162.5	157.2	154.6	152.0	149.3	149.3	146.7	146.7	146.7	146.7
80°	122.9	121.6	112.3	111.0	111.0	108.4	108.4	108.4	108.4	107.0	108.4
82.5°	81.9	80.6	78.0	76.6	74.0	75.3	75.3	72.7	72.7	71.4	72.7
85°	47.6	47.6	44.9	43.6	42.3	43.6	41.0	39.6	41.0	39.6	41.0
87.5°	22.5	19.8	21.1	19.8	17.2	18.5	15.9	17.2	15.9	14.5	17.2
90°	17.0	17.9	18.9	19.8	20.3	20.5	20.8	21.1	21.5	21.8	21.5
92.5°	32.4	32.9	33.4	33.9	34.1	34.2	34.3	34.5	34.6	34.8	34.6
95°	55.7	56.1	56.6	57.1	57.3	57.3	57.3	57.3	57.3	57.3	57.3
97.5°	81.9	82.6	83.2	83.9	84.2	84.2	84.2	84.2	84.2	84.2	84.2
100°	111.4	111.7	112.0	112.3	112.5	112.5	112.5	112.5	112.5	112.5	112.5
102.5°	142.0	142.5	143.0	143.5	143.7	143.8	143.9	144.1	144.2	144.4	144.2
105°	173.2	173.7	174.2	174.7	174.9	175.1	175.6	176.1	176.6	177.1	176.6
107.5°	206.7	207.4	208.0	208.7	209.0	208.9	208.8	208.6	208.5	208.3	208.5
110°	241.4	241.1	240.8	240.5	240.3	240.5	241.0	241.5	241.9	242.4	241.9

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3
115°	314.8	314.7	314.5	314.4	314.3	314.2	314.1	313.9	313.8	313.6	313.8
117.5°	350.8	350.3	349.8	349.3	349.1	348.9	348.4	347.9	347.4	346.9	347.4
120°	387.5	386.7	385.9	385.1	384.7	384.9	385.2	385.5	385.8	386.1	385.8
122.5°	424.1	423.6	423.1	422.6	422.4	422.0	421.2	420.4	419.6	418.8	419.6
125°	459.9	459.5	459.2	458.9	458.7	458.5	458.2	457.9	457.6	457.3	457.6
127.5°	494.0	493.6	493.3	493.0	492.8	492.7	492.6	492.4	492.3	492.1	492.3
130°	530.3	529.9	529.6	529.3	529.1	528.8	528.1	527.5	526.8	526.2	526.8
132.5°	564.4	564.0	563.7	563.4	563.2	563.1	563.0	562.8	562.7	562.5	562.7
135°	598.5	598.2	597.9	597.6	597.4	597.2	596.7	596.2	595.7	595.2	595.7
137.5°	631.7	631.2	630.7	630.2	630.0	630.1	630.2	630.4	630.5	630.7	630.5
140°	663.9	663.8	663.6	663.5	663.4	663.3	663.2	663.0	662.9	662.7	662.9
142.5°	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6
145°	725.6	725.5	725.3	725.2	725.1	724.9	724.4	723.9	723.4	722.9	723.4
147.5°	753.9	753.8	753.6	753.5	753.4	753.3	753.2	753.0	752.9	752.7	752.9
150°	780.3	780.3	780.3	780.3	780.3	780.2	780.0	779.9	779.7	779.5	779.7
152.5°	804.7	805.2	805.7	806.2	806.4	806.2	805.7	805.2	804.7	804.2	804.7
155°	827.3	828.0	828.6	829.3	829.6	829.3	828.6	828.0	827.3	826.7	827.3
157.5°	848.3	848.7	849.2	849.7	849.9	849.7	849.2	848.7	848.3	847.8	848.3
160°	867.1	867.6	868.1	868.6	868.8	868.4	867.6	866.8	866.0	865.2	866.0
162.5°	883.6	884.6	885.5	886.5	887.0	886.6	885.8	884.9	884.1	883.3	884.1
165°	898.1	899.1	900.0	901.0	901.5	901.2	900.5	899.9	899.2	898.6	899.2
167.5°	911.2	912.1	913.1	914.0	914.5	914.0	913.1	912.1	911.2	910.2	911.2
170°	921.4	922.3	923.3	924.2	924.7	924.1	923.0	921.9	920.7	919.6	920.7
172.5°	928.7	929.9	931.0	932.1	932.7	932.1	931.0	929.9	928.7	927.6	928.7
175°	933.8	935.0	936.1	937.2	937.8	937.2	936.1	935.0	933.8	932.7	933.8
177.5°	937.4	938.6	939.7	940.8	941.4	940.8	939.5	938.2	936.9	935.6	936.9
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1720.4	1716.5	1711.2	1711.2	1704.6	1704.6	1694.0	1675.5	1659.6	1654.4	1657.0
5°	1867.1	1868.4	1860.5	1853.9	1842.0	1832.7	1815.6	1782.5	1772.0	1750.8	1736.3
7.5°	2034.9	2029.6	2015.1	2004.5	2001.9	1980.7	1943.7	1904.1	1872.4	1851.2	1820.9
10°	2223.9	2202.7	2181.6	2175.0	2159.1	2123.4	2081.2	2037.6	1994.0	1947.7	1896.2
12.5°	2382.4	2341.5	2340.1	2324.3	2293.9	2274.1	2223.9	2161.8	2086.4	2034.9	1976.8
15°	2552.9	2514.6	2482.9	2453.8	2439.3	2381.1	2338.8	2260.9	2171.0	2115.5	2075.9
17.5°	2674.5	2657.3	2603.1	2589.9	2570.1	2502.7	2435.3	2358.6	2280.7	2202.7	2095.7
20°	2772.2	2761.7	2726.0	2707.5	2675.8	2622.9	2541.0	2452.5	2362.6	2251.6	2151.2
22.5°	2814.5	2801.3	2772.2	2756.4	2736.6	2691.6	2621.6	2521.2	2403.6	2304.5	2197.4
25°	2731.3	2755.1	2747.1	2740.5	2732.6	2706.2	2653.3	2564.8	2449.8	2337.5	2204.0
27.5°	2543.6	2584.6	2624.2	2629.5	2642.7	2653.3	2632.2	2568.7	2472.3	2353.4	2206.7
30°	2291.3	2309.8	2390.4	2414.1	2432.6	2500.0	2539.7	2523.8	2449.8	2342.8	2208.0
32.5°	1967.5	2016.4	2098.3	2155.2	2205.4	2280.7	2383.8	2424.7	2398.3	2311.1	2177.6
35°	1661.0	1719.1	1814.2	1886.9	1937.1	2044.2	2165.7	2254.3	2287.3	2243.7	2124.8
37.5°	1409.9	1479.9	1564.5	1592.3	1650.4	1782.5	1950.3	2073.2	2153.8	2157.8	2065.3
40°	1220.9	1256.6	1324.0	1366.3	1423.1	1534.1	1698.0	1860.5	1982.1	2023.0	1974.1
42.5°	1061.1	1088.8	1139.0	1190.6	1242.1	1326.7	1477.3	1629.3	1793.1	1875.0	1873.7
45°	934.2	963.3	997.6	1039.9	1075.6	1166.8	1285.7	1441.6	1583.0	1709.9	1741.6
47.5°	823.2	848.3	890.6	909.1	932.9	1018.8	1121.8	1267.2	1413.9	1559.2	1596.2
50°	741.3	762.4	791.5	803.4	829.8	893.2	977.8	1095.4	1257.9	1391.4	1460.1
52.5°	667.3	683.1	705.6	714.9	733.4	780.9	857.6	950.1	1084.8	1222.3	1318.7
55°	603.9	614.4	630.3	640.9	654.1	696.4	753.2	836.4	952.7	1071.6	1165.4
57.5°	544.4	552.3	568.2	573.5	584.0	617.1	656.7	726.8	833.8	939.5	1030.7
60°	488.9	494.2	503.4	515.3	523.3	545.7	582.7	640.9	726.8	823.2	897.2
62.5°	436.1	444.0	446.6	451.9	458.5	479.7	508.7	551.0	626.3	705.6	783.6
65°	381.9	388.5	393.8	395.1	401.7	417.6	444.0	481.0	529.9	598.6	671.3
67.5°	331.7	335.6	338.3	343.6	350.2	358.1	379.2	407.0	451.9	507.4	565.5
70°	285.4	285.4	289.4	290.7	298.6	307.9	317.1	343.6	383.2	428.1	467.8
72.5°	235.2	241.8	240.5	247.1	245.8	252.4	264.3	281.5	310.5	346.2	384.5
75°	191.6	195.6	195.6	195.6	198.2	203.5	210.1	226.0	248.4	277.5	300.0
77.5°	149.3	152.0	152.0	152.0	153.3	158.6	165.2	175.7	191.6	208.8	222.0
80°	107.0	109.7	109.7	112.3	112.3	113.6	120.2	125.5	133.5	146.7	159.9
82.5°	72.7	74.0	76.6	76.6	75.3	78.0	79.3	84.6	92.5	95.1	104.4
85°	39.6	41.0	42.3	42.3	43.6	46.2	44.9	50.2	50.2	55.5	58.1
87.5°	15.9	18.5	18.5	17.2	18.5	18.5	18.5	21.1	22.5	23.8	22.5
90°	21.1	20.8	20.5	20.3	19.8	18.9	17.9	17.0	16.0	14.7	13.4
92.5°	34.5	34.3	34.2	34.1	33.9	33.4	32.9	32.4	31.9	31.1	30.3
95°	57.3	57.3	57.3	57.3	57.1	56.6	56.1	55.7	55.2	54.1	52.9
97.5°	84.2	84.2	84.2	84.2	83.9	83.2	82.6	81.9	81.3	80.0	78.7
100°	112.5	112.5	112.5	112.5	112.3	112.0	111.7	111.4	111.1	109.6	108.2
102.5°	144.1	143.9	143.8	143.7	143.5	143.0	142.5	142.0	141.5	140.2	138.9
105°	176.1	175.6	175.1	174.9	174.7	174.2	173.7	173.2	172.7	172.1	171.4
107.5°	208.6	208.8	208.9	209.0	208.7	208.0	207.4	206.7	206.1	205.9	205.8
110°	241.5	241.0	240.5	240.3	240.5	240.8	241.1	241.4	241.7	241.9	242.0

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.6	277.9
115°	313.9	314.1	314.2	314.3	314.4	314.5	314.7	314.8	315.0	315.3	315.7
117.5°	347.9	348.4	348.9	349.1	349.3	349.8	350.3	350.8	351.3	351.5	351.6
120°	385.5	385.2	384.9	384.7	385.1	385.9	386.7	387.5	388.3	388.8	389.3
122.5°	420.4	421.2	422.0	422.4	422.6	423.1	423.6	424.1	424.6	424.8	424.9
125°	457.9	458.2	458.5	458.7	458.9	459.2	459.5	459.9	460.2	460.4	460.5
127.5°	492.4	492.6	492.7	492.8	493.0	493.3	493.6	494.0	494.3	494.6	494.9
130°	527.5	528.1	528.8	529.1	529.3	529.6	529.9	530.3	530.6	530.6	530.6
132.5°	562.8	563.0	563.1	563.2	563.4	563.7	564.0	564.4	564.7	564.9	565.0
135°	596.2	596.7	597.2	597.4	597.6	597.9	598.2	598.5	598.8	598.8	598.8
137.5°	630.4	630.2	630.1	630.0	630.2	630.7	631.2	631.7	632.2	631.9	631.5
140°	663.0	663.2	663.3	663.4	663.5	663.6	663.8	663.9	664.1	664.1	664.1
142.5°	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.8	694.9
145°	723.9	724.4	724.9	725.1	725.2	725.3	725.5	725.6	725.8	725.6	725.5
147.5°	753.0	753.2	753.3	753.4	753.5	753.6	753.8	753.9	754.1	754.3	754.5
150°	779.9	780.0	780.2	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3
152.5°	805.2	805.7	806.2	806.4	806.2	805.7	805.2	804.7	804.2	804.0	803.9
155°	828.0	828.6	829.3	829.6	829.3	828.6	828.0	827.3	826.7	826.9	827.0
157.5°	848.7	849.2	849.7	849.9	849.7	849.2	848.7	848.3	847.8	847.8	847.8
160°	866.8	867.6	868.4	868.8	868.6	868.1	867.6	867.1	866.6	866.8	867.0
162.5°	884.9	885.8	886.6	887.0	886.5	885.5	884.6	883.6	882.6	882.8	882.9
165°	899.9	900.5	901.2	901.5	901.0	900.0	899.1	898.1	897.1	897.4	897.8
167.5°	912.1	913.1	914.0	914.5	914.0	913.1	912.1	911.2	910.2	910.2	910.2
170°	921.9	923.0	924.1	924.7	924.2	923.3	922.3	921.4	920.4	920.2	920.0
172.5°	929.9	931.0	932.1	932.7	932.1	931.0	929.9	928.7	927.6	927.6	927.6
175°	935.0	936.1	937.2	937.8	937.2	936.1	935.0	933.8	932.7	932.9	933.0
177.5°	938.2	939.5	940.8	941.4	940.8	939.7	938.6	937.4	936.3	936.3	936.3
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1645.1	1639.8	1635.9	1635.9	1624.0	1612.1	1605.5	1602.8	1600.2	1589.6	1575.1
5°	1712.5	1695.3	1683.4	1671.5	1651.7	1630.6	1609.4	1597.5	1580.4	1556.6	1539.4
7.5°	1787.8	1746.9	1733.6	1719.1	1679.5	1643.8	1614.7	1589.6	1561.9	1531.5	1501.1
10°	1851.2	1807.6	1778.6	1753.5	1701.9	1654.4	1610.8	1573.8	1538.1	1498.4	1461.4
12.5°	1912.0	1849.9	1819.5	1782.5	1728.4	1659.6	1602.8	1556.6	1503.7	1462.8	1417.8
15°	1996.6	1892.2	1842.0	1818.2	1745.5	1664.9	1596.2	1527.5	1483.9	1421.8	1382.2
17.5°	2009.8	1925.2	1892.2	1831.4	1744.2	1653.0	1573.8	1505.0	1439.0	1383.5	1331.9
20°	2056.1	1945.1	1892.2	1853.9	1738.9	1646.4	1559.2	1470.7	1407.3	1347.8	1289.7
22.5°	2085.1	1959.6	1904.1	1843.3	1733.6	1622.6	1519.6	1442.9	1365.0	1304.2	1257.9
25°	2077.2	1951.7	1889.6	1832.7	1699.3	1588.3	1495.8	1398.0	1325.3	1259.3	1198.5
27.5°	2073.2	1931.8	1865.8	1802.4	1676.8	1560.5	1444.3	1365.0	1284.4	1207.7	1162.8
30°	2062.7	1906.7	1830.1	1761.4	1630.6	1509.0	1409.9	1317.4	1236.8	1166.8	1107.3
32.5°	2027.0	1864.5	1790.5	1716.5	1580.4	1458.8	1358.4	1272.5	1191.9	1119.2	1062.4
35°	1979.4	1814.2	1733.6	1655.7	1519.6	1396.7	1304.2	1214.3	1139.0	1069.0	1014.8
37.5°	1931.8	1756.1	1680.8	1590.9	1465.4	1337.2	1242.1	1161.5	1091.5	1018.8	959.3
40°	1863.1	1687.4	1604.1	1527.5	1380.8	1260.6	1173.4	1100.7	1032.0	963.3	913.1
42.5°	1769.3	1612.1	1526.2	1441.6	1304.2	1185.3	1100.7	1036.0	971.2	914.4	858.9
45°	1674.2	1520.9	1444.3	1368.9	1219.6	1107.3	1029.3	969.9	915.7	853.6	808.7
47.5°	1559.2	1429.7	1353.1	1279.1	1137.7	1025.4	954.0	898.5	848.3	796.8	754.5
50°	1441.6	1329.3	1259.3	1182.6	1047.8	946.1	876.1	829.8	788.9	740.0	705.6
52.5°	1314.8	1217.0	1157.5	1083.5	964.6	870.8	799.4	753.2	718.8	683.1	652.8
55°	1180.0	1108.6	1045.2	985.7	873.4	788.9	725.4	684.5	660.7	627.7	601.2
57.5°	1058.4	989.7	951.4	884.0	786.2	703.0	652.8	618.4	590.7	570.8	549.7
60°	931.6	876.1	833.8	784.9	699.0	629.0	576.1	556.3	527.2	512.7	503.4
62.5°	810.0	770.4	730.7	693.7	617.1	551.0	511.4	486.3	469.1	454.6	446.6
65°	695.0	658.0	630.3	597.3	533.8	481.0	444.0	424.2	407.0	403.0	393.8
67.5°	582.7	566.9	536.5	510.0	455.9	414.9	387.2	362.1	352.8	348.8	340.9
70°	487.6	469.1	445.3	422.8	381.9	346.2	321.1	311.8	298.6	297.3	288.1
72.5°	401.7	379.2	362.1	344.9	314.5	282.8	269.6	256.3	249.7	244.5	240.5
75°	318.5	302.6	290.7	276.2	249.7	228.6	210.1	204.8	200.8	199.5	196.9
77.5°	237.8	227.3	222.0	207.5	189.0	170.5	162.5	154.6	154.6	152.0	153.3
80°	169.1	162.5	155.9	148.0	132.1	124.2	117.6	112.3	109.7	108.4	109.7
82.5°	107.0	103.1	101.7	96.5	85.9	81.9	76.6	72.7	72.7	72.7	72.7
85°	59.5	59.5	59.5	51.5	47.6	43.6	41.0	39.6	39.6	39.6	41.0
87.5°	25.1	25.1	21.1	21.1	19.8	17.2	15.9	15.9	17.2	17.2	18.5
90°	12.1	10.8	10.2	9.3	7.5	5.8	4.0	2.2	4.0	5.8	7.5
92.5°	29.5	28.7	28.3	27.3	25.2	23.1	21.0	18.9	21.0	23.1	25.2
95°	51.8	50.7	50.1	49.4	47.9	46.4	45.0	43.5	45.0	46.4	47.9
97.5°	77.4	76.1	75.5	74.9	73.6	72.3	71.0	69.7	71.0	72.3	73.6
100°	106.7	105.2	104.5	104.2	103.5	102.9	102.2	101.6	102.2	102.9	103.5
102.5°	137.6	136.3	135.7	135.6	135.5	135.3	135.2	135.0	135.2	135.3	135.5
105°	170.8	170.1	169.8	169.7	169.6	169.4	169.3	169.1	169.3	169.4	169.6
107.5°	205.6	205.5	205.4	205.3	205.2	205.0	204.9	204.7	204.9	205.0	205.2
110°	242.2	242.3	242.4	242.2	241.9	241.6	241.3	241.0	241.3	241.6	241.9

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	278.2	278.5	278.7	278.7	278.7	278.7	278.7	278.7	278.7	278.7	278.7
115°	316.0	316.3	316.5	316.5	316.5	316.5	316.5	316.5	316.5	316.5	316.5
117.5°	351.8	351.9	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0
120°	389.8	390.3	390.5	390.2	389.5	388.9	388.2	387.6	388.2	388.9	389.5
122.5°	425.1	425.2	425.3	425.2	425.1	424.9	424.8	424.6	424.8	424.9	425.1
125°	460.7	460.8	460.9	460.9	460.9	460.9	460.9	460.9	460.9	460.9	460.9
127.5°	495.2	495.5	495.7	495.5	495.0	494.5	494.1	493.6	494.1	494.5	495.0
130°	530.6	530.6	530.6	530.4	529.9	529.4	528.9	528.4	528.9	529.4	529.9
132.5°	565.2	565.3	565.4	565.2	564.9	564.6	564.3	564.0	564.3	564.6	564.9
135°	598.8	598.8	598.8	598.3	597.4	596.4	595.5	594.5	595.5	596.4	597.4
137.5°	631.2	630.9	630.7	630.5	630.0	629.5	629.1	628.6	629.1	629.5	630.0
140°	664.1	664.1	664.1	663.9	663.6	663.3	663.0	662.7	663.0	663.3	663.6
142.5°	695.1	695.2	695.3	695.1	694.8	694.5	694.2	693.9	694.2	694.5	694.8
145°	725.3	725.2	725.1	724.8	724.1	723.5	722.8	722.2	722.8	723.5	724.1
147.5°	754.6	754.8	754.9	754.5	753.7	752.8	752.0	751.2	752.0	752.8	753.7
150°	780.3	780.3	780.3	780.0	779.3	778.7	778.0	777.4	778.0	778.7	779.3
152.5°	803.7	803.6	803.5	803.3	803.0	802.7	802.3	802.0	802.3	802.7	803.0
155°	827.2	827.3	827.4	827.4	827.4	827.4	827.4	827.4	827.4	827.4	827.4
157.5°	847.8	847.8	847.8	848.0	848.3	848.6	848.9	849.2	848.9	848.6	848.3
160°	867.1	867.3	867.4	867.5	867.6	867.8	867.9	868.1	867.9	867.8	867.6
162.5°	883.1	883.2	883.3	883.5	884.0	884.5	885.0	885.5	885.0	884.5	884.0
165°	898.1	898.4	898.6	898.8	899.3	899.8	900.3	900.8	900.3	899.8	899.3
167.5°	910.2	910.2	910.2	910.5	911.2	911.8	912.5	913.1	912.5	911.8	911.2
170°	919.9	919.7	919.6	920.0	920.8	921.7	922.5	923.3	922.5	921.7	920.8
172.5°	927.6	927.6	927.6	927.9	928.6	929.2	929.9	930.5	929.9	929.2	928.6
175°	933.2	933.3	933.4	933.8	934.6	935.4	936.2	937.0	936.2	935.4	934.6
177.5°	936.3	936.3	936.3	936.7	937.5	938.4	939.2	940.0	939.2	938.4	937.5
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1571.1	1565.8	1568.5	1555.3	1543.4	1526.2	1511.6	1509.0	1506.4	1514.3	1509.0
5°	1526.2	1519.6	1513.0	1497.1	1473.3	1458.8	1437.7	1436.3	1428.4	1416.5	1419.2
7.5°	1477.3	1473.3	1464.1	1439.0	1417.8	1392.7	1375.5	1361.0	1354.4	1343.8	1339.9
10°	1437.7	1423.1	1415.2	1387.4	1362.3	1335.9	1313.4	1302.9	1291.0	1281.7	1275.1
12.5°	1383.5	1379.5	1357.0	1334.6	1313.4	1283.1	1265.9	1235.5	1219.6	1227.6	1224.9
15°	1347.8	1329.3	1324.0	1292.3	1256.6	1236.8	1205.1	1185.3	1178.7	1166.8	1152.2
17.5°	1300.2	1288.3	1269.8	1240.8	1199.8	1172.1	1149.6	1131.1	1123.2	1107.3	1095.4
20°	1255.3	1235.5	1220.9	1194.5	1154.9	1119.2	1091.5	1079.6	1059.7	1046.5	1039.9
22.5°	1214.3	1199.8	1178.7	1139.0	1104.7	1070.3	1037.3	1020.1	1001.6	993.7	983.1
25°	1164.1	1140.3	1125.8	1082.2	1045.2	1017.5	987.1	964.6	954.0	940.8	938.2
27.5°	1115.2	1092.8	1075.6	1037.3	992.4	956.7	938.2	922.3	903.8	903.8	897.2
30°	1066.3	1050.5	1024.1	987.1	944.8	910.4	889.3	874.7	868.1	862.9	861.5
32.5°	1017.5	996.3	980.5	930.2	898.5	866.8	851.0	839.1	831.1	829.8	831.1
35°	967.2	943.5	927.6	882.7	851.0	821.9	815.3	804.7	800.8	799.4	806.0
37.5°	914.4	895.9	876.1	839.1	803.4	786.2	773.0	769.0	767.7	775.6	778.3
40°	865.5	849.6	831.1	791.5	765.1	746.6	740.0	736.0	741.3	749.2	753.2
42.5°	819.3	796.8	782.3	746.6	722.8	712.2	704.3	704.3	709.6	718.8	725.4
45°	770.4	753.2	738.6	706.9	685.8	673.9	672.6	673.9	680.5	687.1	695.0
47.5°	722.8	705.6	689.8	663.3	644.8	638.2	636.9	638.2	648.8	658.0	667.3
50°	679.2	660.7	646.2	621.0	606.5	598.6	599.9	606.5	614.4	627.7	639.5
52.5°	627.7	614.4	601.2	578.8	565.5	560.3	564.2	569.5	584.0	593.3	607.8
55°	577.4	565.5	555.0	537.8	527.2	523.3	525.9	533.8	545.7	561.6	578.8
57.5°	531.2	518.0	507.4	495.5	483.6	484.9	486.3	496.8	511.4	525.9	545.7
60°	479.7	471.7	462.5	447.9	442.7	442.7	446.6	458.5	471.7	495.5	512.7
62.5°	433.4	422.8	416.2	407.0	399.1	400.4	409.6	420.2	436.1	455.9	478.3
65°	385.8	373.9	368.7	360.7	358.1	359.4	366.0	381.9	399.1	416.2	437.4
67.5°	333.0	329.0	323.7	315.8	318.5	319.8	326.4	339.6	358.1	375.3	399.1
70°	288.1	280.1	278.8	272.2	272.2	276.2	289.4	298.6	315.8	334.3	359.4
72.5°	240.5	233.9	233.9	228.6	232.6	236.5	243.1	256.3	272.2	290.7	311.8
75°	191.6	189.0	191.6	189.0	189.0	195.6	203.5	214.1	231.2	251.1	268.2
77.5°	148.0	148.0	146.7	150.6	150.6	154.6	165.2	175.7	189.0	204.8	223.3
80°	108.4	108.4	108.4	112.3	116.3	116.3	122.9	136.1	148.0	158.6	175.7
82.5°	74.0	74.0	74.0	76.6	81.9	81.9	89.9	97.8	111.0	120.2	128.2
85°	44.9	44.9	43.6	46.2	47.6	51.5	58.1	63.4	70.0	78.0	85.9
87.5°	19.8	19.8	21.1	22.5	23.8	26.4	29.1	31.7	38.3	41.0	44.9
90°	9.3	10.2	10.8	12.1	13.4	14.7	16.0	17.0	17.9	18.9	19.8
92.5°	27.3	28.3	28.7	29.5	30.3	31.1	31.9	32.4	32.9	33.4	33.9
95°	49.4	50.1	50.7	51.8	52.9	54.1	55.2	55.7	56.1	56.6	57.1
97.5°	74.9	75.5	76.1	77.4	78.7	80.0	81.3	81.9	82.6	83.2	83.9
100°	104.2	104.5	105.2	106.7	108.2	109.6	111.1	111.4	111.7	112.0	112.3
102.5°	135.6	135.7	136.3	137.6	138.9	140.2	141.5	142.0	142.5	143.0	143.5
105°	169.7	169.8	170.1	170.8	171.4	172.1	172.7	173.2	173.7	174.2	174.7
107.5°	205.3	205.4	205.5	205.6	205.8	205.9	206.1	206.7	207.4	208.0	208.7
110°	242.2	242.4	242.3	242.2	242.0	241.9	241.7	241.4	241.1	240.8	240.5

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	278.7	278.7	278.5	278.2	277.9	277.6	277.3	277.3	277.3	277.3	277.3
115°	316.5	316.5	316.3	316.0	315.7	315.3	315.0	314.8	314.7	314.5	314.4
117.5°	352.0	352.0	351.9	351.8	351.6	351.5	351.3	350.8	350.3	349.8	349.3
120°	390.2	390.5	390.3	389.8	389.3	388.8	388.3	387.5	386.7	385.9	385.1
122.5°	425.2	425.3	425.2	425.1	424.9	424.8	424.6	424.1	423.6	423.1	422.6
125°	460.9	460.9	460.8	460.7	460.5	460.4	460.2	459.9	459.5	459.2	458.9
127.5°	495.5	495.7	495.5	495.2	494.9	494.6	494.3	494.0	493.6	493.3	493.0
130°	530.4	530.6	530.6	530.6	530.6	530.6	530.6	530.3	529.9	529.6	529.3
132.5°	565.2	565.4	565.3	565.2	565.0	564.9	564.7	564.4	564.0	563.7	563.4
135°	598.3	598.8	598.8	598.8	598.8	598.8	598.8	598.5	598.2	597.9	597.6
137.5°	630.5	630.7	630.9	631.2	631.5	631.9	632.2	631.7	631.2	630.7	630.2
140°	663.9	664.1	664.1	664.1	664.1	664.1	664.1	663.9	663.8	663.6	663.5
142.5°	695.1	695.3	695.2	695.1	694.9	694.8	694.6	694.6	694.6	694.6	694.6
145°	724.8	725.1	725.2	725.3	725.5	725.6	725.8	725.6	725.5	725.3	725.2
147.5°	754.5	754.9	754.8	754.6	754.5	754.3	754.1	753.9	753.8	753.6	753.5
150°	780.0	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3
152.5°	803.3	803.5	803.6	803.7	803.9	804.0	804.2	804.7	805.2	805.7	806.2
155°	827.4	827.4	827.3	827.2	827.0	826.9	826.7	827.3	828.0	828.6	829.3
157.5°	848.0	847.8	847.8	847.8	847.8	847.8	847.8	848.3	848.7	849.2	849.7
160°	867.5	867.4	867.3	867.1	867.0	866.8	866.6	867.1	867.6	868.1	868.6
162.5°	883.5	883.3	883.2	883.1	882.9	882.8	882.6	883.6	884.6	885.5	886.5
165°	898.8	898.6	898.4	898.1	897.8	897.4	897.1	898.1	899.1	900.0	901.0
167.5°	910.5	910.2	910.2	910.2	910.2	910.2	910.2	911.2	912.1	913.1	914.0
170°	920.0	919.6	919.7	919.9	920.0	920.2	920.4	921.4	922.3	923.3	924.2
172.5°	927.9	927.6	927.6	927.6	927.6	927.6	927.6	928.7	929.9	931.0	932.1
175°	933.8	933.4	933.3	933.2	933.0	932.9	932.7	933.8	935.0	936.1	937.2
177.5°	936.7	936.3	936.3	936.3	936.3	936.3	936.3	937.4	938.6	939.7	940.8
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1505.0	1503.7	1497.1	1499.8	1491.8	1494.5	1498.4	1499.8	1505.0	1501.1	1499.8
5°	1412.5	1409.9	1405.9	1402.0	1400.7	1405.9	1396.7	1399.3	1402.0	1405.9	1411.2
7.5°	1337.2	1335.9	1331.9	1325.3	1322.7	1320.1	1321.4	1330.6	1329.3	1328.0	1337.2
10°	1268.5	1269.8	1261.9	1260.6	1252.7	1251.3	1252.7	1255.3	1259.3	1264.6	1265.9
12.5°	1197.2	1214.3	1199.8	1194.5	1182.6	1189.2	1191.9	1180.0	1186.6	1190.6	1210.4
15°	1152.2	1144.3	1135.1	1135.1	1129.8	1127.1	1120.5	1129.8	1135.1	1143.0	1140.3
17.5°	1090.1	1076.9	1071.6	1066.3	1067.7	1073.0	1058.4	1079.6	1079.6	1083.5	1076.9
20°	1036.0	1025.4	1018.8	1016.1	1012.2	1009.5	1008.2	1013.5	1021.4	1024.1	1030.7
22.5°	979.1	979.1	968.6	964.6	962.0	958.0	964.6	960.6	965.9	971.2	981.8
25°	931.6	931.6	927.6	922.3	918.4	915.7	919.7	918.4	922.3	928.9	931.6
27.5°	893.2	889.3	888.0	886.6	885.3	886.6	885.3	889.3	893.2	894.6	891.9
30°	860.2	856.2	857.6	857.6	858.9	857.6	856.2	860.2	861.5	858.9	860.2
32.5°	829.8	829.8	832.5	833.8	833.8	835.1	836.4	833.8	835.1	831.1	832.5
35°	804.7	807.4	810.0	811.3	812.6	811.3	814.0	812.6	810.0	807.4	806.0
37.5°	779.6	782.3	787.5	788.9	792.8	794.1	791.5	791.5	790.2	784.9	782.3
40°	753.2	755.8	762.4	766.4	769.0	773.0	770.4	770.4	765.1	759.8	755.8
42.5°	728.1	733.4	740.0	743.9	749.2	749.2	749.2	746.6	740.0	734.7	730.7
45°	703.0	704.3	713.5	720.1	725.4	725.4	725.4	721.5	717.5	706.9	701.6
47.5°	675.2	679.2	689.8	696.4	701.6	703.0	703.0	699.0	691.1	681.8	675.2
50°	644.8	651.4	663.3	672.6	679.2	681.8	677.9	675.2	666.0	655.4	647.5
52.5°	615.8	623.7	638.2	646.2	655.4	656.7	655.4	651.4	640.9	626.3	619.7
55°	586.7	593.3	609.2	622.4	630.3	632.9	630.3	623.7	610.5	595.9	589.3
57.5°	555.0	564.2	581.4	594.6	603.9	605.2	602.5	595.9	585.4	566.9	557.6
60°	521.9	533.8	551.0	564.2	576.1	577.4	574.8	565.5	552.3	533.8	525.9
62.5°	488.9	498.2	518.0	532.5	541.8	548.4	543.1	533.8	520.6	502.1	490.2
65°	450.6	463.8	481.0	494.2	504.8	506.1	503.4	495.5	481.0	461.2	451.9
67.5°	413.6	422.8	440.0	457.2	461.2	465.1	461.2	453.2	441.3	424.2	410.9
70°	368.7	376.6	397.7	409.6	414.9	418.9	416.2	408.3	397.7	381.9	371.3
72.5°	323.7	330.3	350.2	359.4	370.0	368.7	367.3	362.1	347.5	336.9	330.3
75°	276.2	284.1	297.3	309.2	313.2	313.2	313.2	309.2	300.0	282.8	276.2
77.5°	232.6	236.5	247.1	253.7	257.7	259.0	257.7	251.1	245.8	233.9	229.9
80°	178.4	189.0	196.9	198.2	203.5	203.5	203.5	200.8	195.6	183.7	182.3
82.5°	134.8	137.4	145.4	149.3	152.0	150.6	150.6	145.4	144.0	137.4	134.8
85°	91.2	95.1	93.8	99.1	100.4	97.8	97.8	100.4	93.8	95.1	91.2
87.5°	50.2	50.2	52.9	51.5	56.8	56.8	54.2	55.5	52.9	51.5	50.2
90°	20.3	20.5	20.8	21.1	21.5	21.8	21.5	21.1	20.8	20.5	20.3
92.5°	34.1	34.2	34.3	34.5	34.6	34.8	34.6	34.5	34.3	34.2	34.1
95°	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3
97.5°	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2
100°	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5
102.5°	143.7	143.8	143.9	144.1	144.2	144.4	144.2	144.1	143.9	143.8	143.7
105°	174.9	175.1	175.6	176.1	176.6	177.1	176.6	176.1	175.6	175.1	174.9
107.5°	209.0	208.9	208.8	208.6	208.5	208.3	208.5	208.6	208.8	208.9	209.0
110°	240.3	240.5	241.0	241.5	241.9	242.4	241.9	241.5	241.0	240.5	240.3

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3
115°	314.3	314.2	314.1	313.9	313.8	313.6	313.8	313.9	314.1	314.2	314.3
117.5°	349.1	348.9	348.4	347.9	347.4	346.9	347.4	347.9	348.4	348.9	349.1
120°	384.7	384.9	385.2	385.5	385.8	386.1	385.8	385.5	385.2	384.9	384.7
122.5°	422.4	422.0	421.2	420.4	419.6	418.8	419.6	420.4	421.2	422.0	422.4
125°	458.7	458.5	458.2	457.9	457.6	457.3	457.6	457.9	458.2	458.5	458.7
127.5°	492.8	492.7	492.6	492.4	492.3	492.1	492.3	492.4	492.6	492.7	492.8
130°	529.1	528.8	528.1	527.5	526.8	526.2	526.8	527.5	528.1	528.8	529.1
132.5°	563.2	563.1	563.0	562.8	562.7	562.5	562.7	562.8	563.0	563.1	563.2
135°	597.4	597.2	596.7	596.2	595.7	595.2	595.7	596.2	596.7	597.2	597.4
137.5°	630.0	630.1	630.2	630.4	630.5	630.7	630.5	630.4	630.2	630.1	630.0
140°	663.4	663.3	663.2	663.0	662.9	662.7	662.9	663.0	663.2	663.3	663.4
142.5°	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6
145°	725.1	724.9	724.4	723.9	723.4	722.9	723.4	723.9	724.4	724.9	725.1
147.5°	753.4	753.3	753.2	753.0	752.9	752.7	752.9	753.0	753.2	753.3	753.4
150°	780.3	780.2	780.0	779.9	779.7	779.5	779.7	779.9	780.0	780.2	780.3
152.5°	806.4	806.2	805.7	805.2	804.7	804.2	804.7	805.2	805.7	806.2	806.4
155°	829.6	829.3	828.6	828.0	827.3	826.7	827.3	828.0	828.6	829.3	829.6
157.5°	849.9	849.7	849.2	848.7	848.3	847.8	848.3	848.7	849.2	849.7	849.9
160°	868.8	868.4	867.6	866.8	866.0	865.2	866.0	866.8	867.6	868.4	868.8
162.5°	887.0	886.6	885.8	884.9	884.1	883.3	884.1	884.9	885.8	886.6	887.0
165°	901.5	901.2	900.5	899.9	899.2	898.6	899.2	899.9	900.5	901.2	901.5
167.5°	914.5	914.0	913.1	912.1	911.2	910.2	911.2	912.1	913.1	914.0	914.5
170°	924.7	924.1	923.0	921.9	920.7	919.6	920.7	921.9	923.0	924.1	924.7
172.5°	932.7	932.1	931.0	929.9	928.7	927.6	928.7	929.9	931.0	932.1	932.7
175°	937.8	937.2	936.1	935.0	933.8	932.7	933.8	935.0	936.1	937.2	937.8
177.5°	941.4	940.8	939.5	938.2	936.9	935.6	936.9	938.2	939.5	940.8	941.4
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1499.8	1507.7	1499.8	1505.0	1507.7	1514.3	1516.9	1528.8	1532.8	1542.0	1542.0
5°	1409.9	1413.9	1415.2	1420.5	1425.8	1439.0	1448.2	1465.4	1485.2	1487.9	1499.8
7.5°	1337.2	1343.8	1354.4	1350.4	1359.7	1379.5	1391.4	1412.5	1432.4	1442.9	1457.5
10°	1272.5	1280.4	1284.4	1288.3	1305.5	1322.7	1341.2	1355.7	1382.2	1398.0	1409.9
12.5°	1219.6	1213.0	1220.9	1235.5	1255.3	1265.9	1291.0	1313.4	1333.3	1350.4	1361.0
15°	1150.9	1156.2	1164.1	1189.2	1194.5	1220.9	1230.2	1255.3	1292.3	1308.2	1321.4
17.5°	1084.8	1102.0	1117.9	1127.1	1143.0	1164.1	1190.6	1218.3	1242.1	1260.6	1276.4
20°	1032.0	1049.2	1058.4	1065.0	1080.9	1110.0	1135.1	1169.4	1199.8	1214.3	1235.5
22.5°	989.7	989.7	1002.9	1022.7	1032.0	1059.7	1080.9	1117.9	1150.9	1169.4	1189.2
25°	936.9	944.8	955.4	972.5	985.7	1008.2	1038.6	1070.3	1106.0	1121.8	1147.0
27.5°	893.2	902.5	917.0	921.0	934.2	954.0	985.7	1020.1	1057.1	1074.3	1095.4
30°	860.2	865.5	870.8	878.7	890.6	907.8	934.2	964.6	1009.5	1022.7	1049.2
32.5°	831.1	833.8	836.4	843.0	849.6	866.8	888.0	921.0	958.0	977.8	1001.6
35°	804.7	802.1	803.4	807.4	814.0	820.6	843.0	870.8	905.1	928.9	947.4
37.5°	779.6	774.3	773.0	773.0	775.6	783.6	800.8	824.5	861.5	881.4	899.9
40°	751.9	746.6	743.9	742.6	741.3	746.6	759.8	783.6	812.6	831.1	852.3
42.5°	725.4	720.1	713.5	712.2	709.6	712.2	721.5	743.9	769.0	787.5	804.7
45°	699.0	689.8	681.8	676.5	677.9	673.9	680.5	697.7	726.8	738.6	755.8
47.5°	669.9	659.4	648.8	643.5	638.2	640.9	643.5	658.0	683.1	695.0	712.2
50°	642.2	627.7	615.8	609.2	605.2	602.5	605.2	619.7	638.2	648.8	663.3
52.5°	610.5	595.9	584.0	573.5	568.2	564.2	565.5	578.8	595.9	606.5	621.0
55°	581.4	562.9	547.0	533.8	529.9	528.5	527.2	536.5	551.0	561.6	573.5
57.5°	548.4	529.9	512.7	496.8	488.9	487.6	487.6	490.2	508.7	516.7	523.3
60°	515.3	495.5	477.0	462.5	450.6	446.6	445.3	450.6	459.8	467.8	477.0
62.5°	478.3	458.5	436.1	422.8	410.9	400.4	404.3	405.7	418.9	422.8	430.8
65°	442.7	420.2	401.7	380.6	367.3	360.7	358.1	360.7	371.3	372.6	377.9
67.5°	401.7	380.6	358.1	343.6	331.7	319.8	317.1	317.1	322.4	326.4	333.0
70°	362.1	340.9	315.8	300.0	288.1	277.5	273.5	272.2	276.2	278.8	285.4
72.5°	315.8	294.7	276.2	259.0	244.5	236.5	232.6	229.9	233.9	236.5	237.8
75°	266.9	249.7	231.2	214.1	204.8	196.9	191.6	187.6	190.3	190.3	190.3
77.5°	220.7	203.5	189.0	177.1	165.2	155.9	152.0	148.0	149.3	149.3	152.0
80°	171.8	159.9	148.0	137.4	126.9	118.9	116.3	112.3	109.7	108.4	108.4
82.5°	126.9	117.6	107.0	97.8	92.5	84.6	81.9	76.6	76.6	75.3	75.3
85°	84.6	79.3	68.7	62.1	58.1	54.2	51.5	48.9	44.9	44.9	43.6
87.5°	44.9	42.3	39.6	31.7	31.7	27.7	26.4	25.1	21.1	22.5	22.5
90°	19.8	18.9	17.9	17.0	16.0	14.7	13.4	12.1	10.8	10.2	9.3
92.5°	33.9	33.4	32.9	32.4	31.9	31.1	30.3	29.5	28.7	28.3	27.3
95°	57.1	56.6	56.1	55.7	55.2	54.1	52.9	51.8	50.7	50.1	49.4
97.5°	83.9	83.2	82.6	81.9	81.3	80.0	78.7	77.4	76.1	75.5	74.9
100°	112.3	112.0	111.7	111.4	111.1	109.6	108.2	106.7	105.2	104.5	104.2
102.5°	143.5	143.0	142.5	142.0	141.5	140.2	138.9	137.6	136.3	135.7	135.6
105°	174.7	174.2	173.7	173.2	172.7	172.1	171.4	170.8	170.1	169.8	169.7
107.5°	208.7	208.0	207.4	206.7	206.1	205.9	205.8	205.6	205.5	205.4	205.3
110°	240.5	240.8	241.1	241.4	241.7	241.9	242.0	242.2	242.3	242.4	242.2

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	277.3	277.3	277.3	277.3	277.3	277.6	277.9	278.2	278.5	278.7	278.7
115°	314.4	314.5	314.7	314.8	315.0	315.3	315.7	316.0	316.3	316.5	316.5
117.5°	349.3	349.8	350.3	350.8	351.3	351.5	351.6	351.8	351.9	352.0	352.0
120°	385.1	385.9	386.7	387.5	388.3	388.8	389.3	389.8	390.3	390.5	390.2
122.5°	422.6	423.1	423.6	424.1	424.6	424.8	424.9	425.1	425.2	425.3	425.2
125°	458.9	459.2	459.5	459.9	460.2	460.4	460.5	460.7	460.8	460.9	460.9
127.5°	493.0	493.3	493.6	494.0	494.3	494.6	494.9	495.2	495.5	495.7	495.5
130°	529.3	529.6	529.9	530.3	530.6	530.6	530.6	530.6	530.6	530.6	530.4
132.5°	563.4	563.7	564.0	564.4	564.7	564.9	565.0	565.2	565.3	565.4	565.2
135°	597.6	597.9	598.2	598.5	598.8	598.8	598.8	598.8	598.8	598.8	598.3
137.5°	630.2	630.7	631.2	631.7	632.2	631.9	631.5	631.2	630.9	630.7	630.5
140°	663.5	663.6	663.8	663.9	664.1	664.1	664.1	664.1	664.1	664.1	663.9
142.5°	694.6	694.6	694.6	694.6	694.6	694.8	694.9	695.1	695.2	695.3	695.1
145°	725.2	725.3	725.5	725.6	725.8	725.6	725.5	725.3	725.2	725.1	724.8
147.5°	753.5	753.6	753.8	753.9	754.1	754.3	754.5	754.6	754.8	754.9	754.5
150°	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.0
152.5°	806.2	805.7	805.2	804.7	804.2	804.0	803.9	803.7	803.6	803.5	803.3
155°	829.3	828.6	828.0	827.3	826.7	826.9	827.0	827.2	827.3	827.4	827.4
157.5°	849.7	849.2	848.7	848.3	847.8	847.8	847.8	847.8	847.8	847.8	848.0
160°	868.6	868.1	867.6	867.1	866.6	866.8	867.0	867.1	867.3	867.4	867.5
162.5°	886.5	885.5	884.6	883.6	882.6	882.8	882.9	883.1	883.2	883.3	883.5
165°	901.0	900.0	899.1	898.1	897.1	897.4	897.8	898.1	898.4	898.6	898.8
167.5°	914.0	913.1	912.1	911.2	910.2	910.2	910.2	910.2	910.2	910.2	910.5
170°	924.2	923.3	922.3	921.4	920.4	920.2	920.0	919.9	919.7	919.6	920.0
172.5°	932.1	931.0	929.9	928.7	927.6	927.6	927.6	927.6	927.6	927.6	927.9
175°	937.2	936.1	935.0	933.8	932.7	932.9	933.0	933.2	933.3	933.4	933.8
177.5°	940.8	939.7	938.6	937.4	936.3	936.3	936.3	936.3	936.3	936.3	936.7
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1594.9	1594.9	1594.9	1594.9
2.5°	1551.3	1564.5	1576.4	1594.9
5°	1516.9	1535.4	1560.5	1588.3
7.5°	1477.3	1506.4	1539.4	1577.7
10°	1440.3	1473.3	1515.6	1561.9
12.5°	1402.0	1441.6	1487.9	1538.1
15°	1358.4	1398.0	1449.5	1516.9
17.5°	1318.7	1366.3	1421.8	1493.2
20°	1272.5	1317.4	1378.2	1460.1
22.5°	1231.5	1283.1	1350.4	1421.8
25°	1186.6	1231.5	1298.9	1384.8
27.5°	1141.7	1197.2	1261.9	1345.2
30°	1098.1	1144.3	1214.3	1301.6
32.5°	1050.5	1106.0	1170.7	1252.7
35°	999.0	1051.8	1112.6	1201.1
37.5°	952.7	1004.2	1066.3	1144.3
40°	901.2	955.4	1012.2	1090.1
42.5°	851.0	899.9	956.7	1028.0
45°	802.1	844.4	895.9	958.0
47.5°	751.9	787.5	835.1	890.6
50°	697.7	736.0	771.7	817.9
52.5°	647.5	680.5	709.6	747.9
55°	598.6	621.0	644.8	673.9
57.5°	547.0	564.2	581.4	611.8
60°	495.5	511.4	520.6	540.4
62.5°	445.3	451.9	463.8	475.7
65°	389.8	399.1	405.7	420.2
67.5°	339.6	343.6	350.2	359.4
70°	286.7	296.0	298.6	305.2
72.5°	241.8	245.8	248.4	249.7
75°	191.6	195.6	198.2	206.1
77.5°	150.6	149.3	154.6	155.9
80°	111.0	107.0	108.4	113.6
82.5°	72.7	74.0	72.7	72.7
85°	44.9	43.6	41.0	42.3
87.5°	19.8	19.8	18.5	18.5
90°	7.5	5.8	4.0	2.2
92.5°	25.2	23.1	21.0	18.9
95°	47.9	46.4	45.0	43.5
97.5°	73.6	72.3	71.0	69.7
100°	103.5	102.9	102.2	101.6
102.5°	135.5	135.3	135.2	135.0
105°	169.6	169.4	169.3	169.1
107.5°	205.2	205.0	204.9	204.7
110°	241.9	241.6	241.3	241.0

TEST NUMBER: P1033231

CATALOG NUMBER: S124DIW-B1020D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	278.7	278.7	278.7	278.7
115°	316.5	316.5	316.5	316.5
117.5°	352.0	352.0	352.0	352.0
120°	389.5	388.9	388.2	387.6
122.5°	425.1	424.9	424.8	424.6
125°	460.9	460.9	460.9	460.9
127.5°	495.0	494.5	494.1	493.6
130°	529.9	529.4	528.9	528.4
132.5°	564.9	564.6	564.3	564.0
135°	597.4	596.4	595.5	594.5
137.5°	630.0	629.5	629.1	628.6
140°	663.6	663.3	663.0	662.7
142.5°	694.8	694.5	694.2	693.9
145°	724.1	723.5	722.8	722.2
147.5°	753.7	752.8	752.0	751.2
150°	779.3	778.7	778.0	777.4
152.5°	803.0	802.7	802.3	802.0
155°	827.4	827.4	827.4	827.4
157.5°	848.3	848.6	848.9	849.2
160°	867.6	867.8	867.9	868.1
162.5°	884.0	884.5	885.0	885.5
165°	899.3	899.8	900.3	900.8
167.5°	911.2	911.8	912.5	913.1
170°	920.8	921.7	922.5	923.3
172.5°	928.6	929.2	929.9	930.5
175°	934.6	935.4	936.2	937.0
177.5°	937.5	938.4	939.2	940.0
180°	938.5	938.5	938.5	938.5

(END OF REPORT)