

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033431

Luminaire Tested: S124DIW-B350D1340UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033431
REPORT IS A COMBINATION OF REPORTS P997393 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D1340UB40-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6868.0 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	31	31	22
1	92	88	84	81	81	78	75	72	59	57	56	43	41	40	27	27	26	26	26	19
2	83	76	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	22	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	21	20	19	19	19	14
4	70	59	52	46	61	53	47	42	41	37	33	30	27	25	19	18	16	16	16	12
5	64	53	45	39	56	47	41	36	36	32	28	27	24	21	17	16	14	14	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	16	14	12	12	12	9
7	54	42	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	11	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	10	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	9	9	7
10	43	32	25	20	38	29	23	19	22	18	15	17	14	12	11	9	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4509	4509	4509	4509
5°	4498	5174	4524	3887
10°	4465	6036	4499	3411
15°	4411	6958	4441	3051
20°	4354	7545	4385	2736
25°	4271	7459	4311	2503
30°	4189	6165	4240	2383
35°	4075	4594	4120	2310
40°	3941	3461	3980	2274
45°	3738	2777	3784	2226
50°	3494	2340	3544	2203
55°	3208	2037	3257	2178
60°	2929	1794	3015	2141
65°	2668	1544	2694	2052
70°	2360	1270	2412	1889
75°	2060	976	2046	1606
80°	1620	641	1600	1220
85°	1070	287	997	711

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5831 cd/sqm

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.8	0.8
10°-20°	166.1	2.4
20°-30°	263.9	3.8
30°-40°	293.2	4.3
40°-50°	266.7	3.9
50°-60°	217.9	3.2
60°-70°	155.6	2.3
70°-80°	85.6	1.2
80°-90°	26.7	0.4
90°-100°	57.2	0.8
100°-110°	377.1	5.5
110°-120°	720.2	10.5
120°-130°	914.2	13.3
130°-140°	978.0	14.2
140°-150°	914.5	13.3
150°-160°	737.5	10.7
160°-170°	475.6	6.9
170°-180°	163.9	2.4
0°-30°	483.9	7.0
0°-40°	777.1	11.3
0°-60°	1261.7	18.4
0°-90°	1529.6	22.3
90°-120°	1154.6	16.8
90°-150°	3961.4	57.7
90°-180°	5338.0	77.7
0°-180°	6868.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	553	553	553	553	553	
5°	551	649	554	488	551	52
15°	526	891	530	391	526	148
25°	480	946	485	318	480	221
35°	416	559	421	281	416	260
45°	332	314	336	252	332	256
55°	234	205	237	220	234	210
65°	146	132	147	176	146	144
75°	72	66	71	109	72	75
85°	15	14	14	34	15	17
90°	4	39	4	39	4	5
95°	71	37	71	37	71	88
105°	388	368	388	368	388	406
115°	725	730	725	730	725	714
125°	1019	1027	1019	1027	1019	910
135°	1265	1274	1265	1274	1265	974
145°	1458	1466	1458	1466	1458	911
155°	1599	1598	1599	1598	1599	737
165°	1686	1679	1686	1679	1686	477
175°	1725	1715	1725	1715	1725	164
180°	1725	1725	1725	1725	1725	

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	553.0	558.5	560.8	562.6	568.6	570.4	570.9	573.6	575.9	576.4	576.4
5°	550.7	559.4	566.3	572.7	582.3	586.5	591.5	597.0	604.3	608.9	611.2
7.5°	547.1	559.9	570.4	581.4	594.7	603.0	607.5	622.2	632.3	640.5	650.6
10°	541.6	558.1	573.2	589.2	608.0	618.1	628.2	646.0	660.2	676.3	689.1
12.5°	533.3	554.8	573.2	595.6	619.0	630.9	642.8	674.0	690.5	704.7	727.6
15°	526.0	547.5	573.6	596.5	625.4	643.3	660.7	680.8	707.0	737.7	759.6
17.5°	517.7	544.8	569.0	601.1	633.2	650.1	664.3	695.5	732.2	762.4	782.6
20°	506.3	533.8	565.8	599.7	637.8	651.1	669.8	711.5	744.5	774.3	807.3
22.5°	493.0	525.1	559.0	591.5	630.9	658.9	679.5	716.1	756.0	790.3	827.5
25°	480.2	515.0	544.8	589.2	630.9	649.7	673.1	716.6	760.1	801.8	839.8
27.5°	466.4	498.9	539.3	574.5	621.7	642.4	667.6	715.2	761.5	803.2	844.0
30°	451.3	486.1	519.6	561.3	607.1	633.7	657.0	708.8	756.0	799.5	837.5
32.5°	434.3	467.3	503.1	542.5	590.6	617.6	646.9	700.1	750.5	788.1	817.4
35°	416.5	449.9	481.1	521.4	570.9	597.9	626.3	685.0	734.9	765.6	782.6
37.5°	396.8	428.4	459.1	498.9	548.4	577.3	606.2	663.0	710.2	735.8	731.2
40°	378.0	406.4	434.8	472.4	524.1	554.8	580.0	637.3	678.6	689.5	674.4
42.5°	356.5	380.7	408.2	446.7	497.1	526.0	557.6	609.8	640.5	635.9	610.3
45°	332.2	353.7	381.2	417.4	468.7	498.5	525.1	574.5	597.0	585.5	538.8
47.5°	308.8	329.9	352.3	388.5	438.5	463.7	490.7	535.1	548.0	523.7	477.0
50°	283.6	301.0	324.4	358.7	405.5	432.1	454.5	490.2	494.8	465.0	416.5
52.5°	259.3	274.0	296.4	330.3	373.9	394.9	416.9	448.6	444.9	414.2	367.5
55°	233.7	247.4	268.0	299.2	337.7	357.8	376.6	404.6	396.8	365.2	324.4
57.5°	212.1	221.8	241.9	270.8	302.4	324.4	340.4	362.4	350.5	318.9	280.9
60°	187.4	199.3	216.3	239.6	270.8	285.4	299.6	314.3	306.1	275.8	241.9
62.5°	164.9	174.1	188.8	211.2	235.5	248.8	263.9	273.1	264.8	236.9	208.5
65°	145.7	153.0	164.5	182.8	206.2	217.2	225.9	234.6	227.7	201.6	181.0
67.5°	124.6	131.0	140.7	155.3	175.0	182.8	191.1	197.0	189.2	171.8	151.7
70°	105.8	110.4	119.6	130.6	144.3	151.7	158.5	164.5	157.6	142.9	127.8
72.5°	86.6	90.3	98.5	106.3	118.7	123.7	128.7	133.3	131.0	117.3	104.9
75°	71.5	72.8	78.3	84.8	92.6	98.0	101.7	104.5	102.6	91.6	83.8
77.5°	54.1	55.9	60.0	65.1	71.9	75.1	77.4	80.2	77.9	69.2	63.7
80°	39.4	39.9	42.2	46.7	51.3	51.8	54.1	57.7	56.4	50.4	46.3
82.5°	25.2	26.6	27.5	30.2	33.4	34.4	35.7	36.7	36.2	32.5	31.2
85°	14.7	14.7	15.6	17.4	18.3	19.7	20.2	20.6	21.5	19.2	17.9
87.5°	6.4	6.9	6.9	7.3	8.2	8.2	8.7	9.2	9.6	9.2	7.8
90°	3.9	7.1	10.2	13.4	16.5	18.1	19.2	21.5	23.8	26.1	28.4
92.5°	19.4	18.8	18.2	17.7	17.1	16.8	17.9	20.2	22.5	24.8	27.1
95°	71.0	61.2	51.5	41.7	32.0	27.1	27.2	27.5	27.8	28.1	28.4
97.5°	135.5	141.8	148.1	154.4	160.7	163.9	148.8	118.7	88.6	58.5	28.4
100°	211.6	216.8	221.9	227.1	232.2	234.8	215.0	175.5	135.9	96.4	56.8
102.5°	296.8	300.2	303.7	307.1	310.6	312.3	314.0	317.5	320.9	324.4	327.8
105°	388.4	390.1	391.8	393.5	395.2	396.1	396.8	398.3	399.7	401.2	402.6
107.5°	472.3	473.1	474.0	474.8	475.7	476.1	477.1	479.1	481.2	483.2	485.2
110°	557.4	558.3	559.1	560.0	560.9	561.3	562.2	563.9	565.6	567.4	569.1

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	640.0	641.7	643.5	645.2	646.9	647.8	648.1	648.6	649.2	649.7	650.3
115°	725.2	726.1	726.9	727.8	728.7	729.1	729.0	728.7	728.4	728.1	727.8
117.5°	801.3	802.5	803.6	804.8	805.9	806.5	806.9	807.8	808.6	809.5	810.3
120°	878.7	879.9	881.0	882.2	883.3	883.9	883.8	883.5	883.2	882.9	882.6
122.5°	951.0	951.6	952.2	952.7	953.3	953.6	953.9	954.5	955.0	955.6	956.2
125°	1019.4	1020.6	1021.7	1022.9	1024.0	1024.6	1024.3	1023.7	1023.2	1022.6	1022.0
127.5°	1085.2	1085.5	1085.8	1086.1	1086.4	1086.5	1087.2	1088.6	1090.1	1091.5	1092.9
130°	1148.4	1148.7	1149.0	1149.3	1149.6	1149.7	1150.1	1151.0	1151.9	1152.7	1153.6
132.5°	1206.5	1207.1	1207.7	1208.2	1208.8	1209.1	1209.7	1210.8	1211.9	1213.1	1214.2
135°	1264.6	1264.3	1264.0	1263.7	1263.4	1263.3	1263.9	1265.0	1266.1	1267.3	1268.4
137.5°	1316.2	1316.2	1316.2	1316.2	1316.2	1316.2	1316.9	1318.3	1319.8	1321.2	1322.6
140°	1366.5	1367.1	1367.7	1368.2	1368.8	1369.1	1369.4	1370.0	1370.5	1371.1	1371.7
142.5°	1411.7	1412.8	1414.0	1415.1	1416.2	1416.8	1416.9	1417.2	1417.5	1417.8	1418.1
145°	1458.1	1459.0	1459.8	1460.7	1461.6	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0
147.5°	1494.2	1495.9	1497.7	1499.4	1501.1	1502.0	1501.9	1501.6	1501.3	1501.0	1500.7
150°	1534.2	1535.4	1536.5	1537.7	1538.8	1539.4	1539.3	1539.0	1538.7	1538.4	1538.1
152.5°	1567.8	1568.7	1569.5	1570.4	1571.3	1571.7	1571.4	1570.8	1570.3	1569.7	1569.1
155°	1598.8	1599.1	1599.4	1599.7	1600.0	1600.1	1599.7	1598.8	1597.9	1597.1	1596.2
157.5°	1625.9	1625.9	1625.9	1625.9	1625.9	1625.9	1625.3	1624.2	1623.0	1621.9	1620.7
160°	1649.1	1648.2	1647.4	1646.5	1645.6	1645.2	1645.1	1644.8	1644.5	1644.2	1643.9
162.5°	1669.7	1668.6	1667.4	1666.3	1665.2	1664.6	1664.5	1664.2	1663.9	1663.6	1663.3
165°	1686.5	1685.1	1683.7	1682.2	1680.8	1680.1	1680.1	1680.1	1680.1	1680.1	1680.1
167.5°	1700.7	1699.3	1697.9	1696.4	1695.0	1694.3	1694.2	1693.9	1693.6	1693.3	1693.0
170°	1712.3	1710.6	1708.9	1707.2	1705.5	1704.6	1704.7	1705.0	1705.3	1705.6	1705.9
172.5°	1720.1	1718.4	1716.6	1714.9	1713.2	1712.3	1712.4	1712.7	1713.0	1713.3	1713.6
175°	1725.2	1723.5	1721.8	1720.1	1718.4	1717.5	1717.6	1717.9	1718.2	1718.5	1718.8
177.5°	1729.1	1727.1	1725.1	1723.1	1721.1	1720.1	1720.4	1720.9	1721.5	1722.0	1722.6
180°	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	577.8	586.0	589.7	590.6	595.6	592.4	593.8	593.3	597.0	597.5	597.5
5°	619.9	629.5	632.7	637.3	644.2	646.0	644.6	647.4	652.4	648.8	654.3
7.5°	664.3	674.9	682.2	692.3	694.6	700.5	704.2	707.4	708.3	708.8	709.7
10°	705.6	718.9	729.0	745.9	749.6	752.8	768.8	762.4	770.6	767.9	768.8
12.5°	739.0	765.1	773.4	801.8	804.5	815.5	814.6	824.7	826.5	830.2	826.5
15°	783.0	813.3	826.5	842.6	851.7	864.6	866.9	880.6	886.1	891.1	886.1
17.5°	823.3	839.4	873.3	886.1	892.1	898.9	916.3	921.4	929.6	926.4	935.6
20°	843.5	866.4	902.1	924.1	933.3	939.7	954.4	962.2	965.4	965.4	966.3
22.5°	861.4	894.4	920.9	946.1	954.4	959.0	967.7	973.6	975.0	975.9	976.8
25°	877.4	907.2	928.7	942.9	946.1	946.1	951.2	947.5	941.5	946.1	948.9
27.5°	877.4	898.5	908.1	913.1	913.1	900.8	893.4	878.3	865.5	861.8	870.1
30°	862.7	872.4	859.1	846.7	837.1	828.8	800.0	777.1	772.5	769.3	781.6
32.5°	828.8	816.5	790.3	754.6	740.4	721.6	699.2	681.8	671.2	667.6	664.8
35°	768.8	736.7	702.8	654.7	644.6	620.8	590.1	577.3	559.9	559.4	565.4
37.5°	703.3	653.8	617.2	571.3	557.1	531.9	503.1	489.8	477.9	468.7	479.7
40°	626.8	583.7	527.8	490.2	470.1	456.8	432.5	417.9	412.4	407.8	414.6
42.5°	555.3	508.1	464.6	426.1	409.6	394.5	378.4	364.2	360.1	359.7	364.7
45°	484.3	438.0	397.7	364.7	354.2	345.0	329.4	325.3	318.4	313.8	316.1
47.5°	427.5	379.8	346.4	321.2	312.0	304.2	294.1	287.3	281.3	279.5	282.2
50°	371.6	339.5	305.1	284.1	277.2	269.9	262.1	255.7	252.9	251.1	252.9
52.5°	326.7	292.3	268.9	252.0	245.1	239.6	234.1	231.4	227.7	228.6	230.5
55°	286.4	256.1	236.4	224.0	219.9	217.6	210.8	207.6	206.2	205.3	206.2
57.5°	248.3	226.3	211.7	201.1	195.6	194.3	188.8	188.8	187.4	186.0	186.5
60°	218.1	199.3	185.1	176.9	175.9	173.6	170.0	169.5	166.3	167.7	168.1
62.5°	187.4	172.3	162.7	157.6	154.4	153.5	151.2	150.7	149.4	149.8	148.9
65°	163.1	150.7	141.1	137.0	135.6	135.2	133.3	132.0	131.0	132.0	131.0
67.5°	138.8	130.6	123.2	119.1	117.3	116.8	115.5	114.5	115.0	113.6	114.5
70°	115.9	107.7	103.1	100.8	99.9	98.5	98.5	98.5	98.5	97.6	97.1
72.5°	97.6	89.3	86.1	84.8	83.8	83.4	82.0	82.5	82.0	81.6	83.4
75°	77.4	72.4	69.2	67.8	68.7	67.4	66.0	66.9	65.5	66.0	67.8
77.5°	58.6	56.4	54.5	53.6	52.7	51.8	51.8	50.9	50.9	50.9	50.9
80°	42.6	42.2	38.9	38.5	38.5	37.6	37.6	37.6	37.6	37.1	37.6
82.5°	28.4	27.9	27.0	26.6	25.7	26.1	26.1	25.2	25.2	24.7	25.2
85°	16.5	16.5	15.6	15.1	14.7	15.1	14.2	13.7	14.2	13.7	14.2
87.5°	7.8	6.9	7.3	6.9	6.0	6.4	5.5	6.0	5.5	5.0	6.0
90°	30.1	31.8	33.5	35.2	36.1	36.4	37.0	37.5	38.1	38.7	38.1
92.5°	28.8	30.5	32.2	33.9	34.8	34.8	34.8	34.8	34.8	34.8	34.8
95°	30.1	31.8	33.5	35.2	36.1	36.2	36.5	36.8	37.1	37.4	37.1
97.5°	29.8	31.2	32.7	34.1	34.8	34.9	35.2	35.5	35.8	36.1	35.8
100°	51.9	47.0	42.1	37.2	34.8	34.9	35.2	35.5	35.8	36.1	35.8
102.5°	263.3	198.7	134.2	69.7	37.4	37.4	37.4	37.4	37.4	37.4	37.4
105°	405.2	407.8	410.3	412.9	414.2	409.0	398.7	388.4	378.1	367.8	378.1
107.5°	486.6	488.0	489.5	490.9	491.6	492.2	493.3	494.5	495.6	496.8	495.6
110°	569.7	570.2	570.8	571.3	571.6	572.0	572.9	573.8	574.6	575.5	574.6

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	650.0	649.8	649.5	649.2	649.1	649.7	650.8	651.9	653.1	654.2	653.1
115°	728.4	728.9	729.5	730.0	730.3	730.3	730.3	730.3	730.3	730.3	730.3
117.5°	810.0	809.8	809.5	809.2	809.1	809.1	809.1	809.1	809.1	809.1	809.1
120°	883.2	883.8	884.3	884.9	885.2	884.9	884.3	883.8	883.2	882.6	883.2
122.5°	956.5	956.8	957.1	957.4	957.5	957.2	956.6	956.1	955.5	954.9	955.5
125°	1022.8	1023.7	1024.5	1025.4	1025.8	1025.9	1026.2	1026.5	1026.8	1027.1	1026.8
127.5°	1092.6	1092.3	1092.0	1091.7	1091.6	1091.5	1091.2	1090.9	1090.7	1090.4	1090.7
130°	1153.9	1154.2	1154.5	1154.8	1154.9	1154.9	1154.9	1154.9	1154.9	1154.9	1154.9
132.5°	1214.5	1214.8	1215.1	1215.4	1215.5	1215.4	1215.1	1214.8	1214.5	1214.2	1214.5
135°	1269.0	1269.6	1270.1	1270.7	1271.0	1271.3	1271.9	1272.4	1273.0	1273.6	1273.0
137.5°	1323.2	1323.8	1324.3	1324.9	1325.2	1325.1	1324.8	1324.5	1324.2	1323.9	1324.2
140°	1372.5	1373.4	1374.2	1375.1	1375.5	1375.6	1375.9	1376.2	1376.5	1376.8	1376.5
142.5°	1418.7	1419.3	1419.8	1420.4	1420.7	1420.7	1420.7	1420.7	1420.7	1420.7	1420.7
145°	1462.3	1462.6	1462.9	1463.2	1463.3	1463.6	1464.2	1464.7	1465.3	1465.9	1465.3
147.5°	1501.0	1501.3	1501.6	1501.9	1502.0	1502.1	1502.4	1502.7	1503.0	1503.3	1503.0
150°	1538.1	1538.1	1538.1	1538.1	1538.1	1538.2	1538.5	1538.8	1539.1	1539.4	1539.1
152.5°	1569.7	1570.3	1570.8	1571.4	1571.7	1571.6	1571.3	1571.0	1570.7	1570.4	1570.7
155°	1597.3	1598.5	1599.6	1600.7	1601.3	1600.9	1600.0	1599.2	1598.3	1597.5	1598.3
157.5°	1622.1	1623.6	1625.0	1626.5	1627.2	1626.5	1625.0	1623.6	1622.1	1620.7	1622.1
160°	1645.6	1647.4	1649.1	1650.8	1651.7	1650.8	1649.1	1647.4	1645.6	1643.9	1645.6
162.5°	1665.0	1666.7	1668.4	1670.1	1671.0	1670.0	1668.0	1666.0	1664.0	1662.0	1664.0
165°	1682.4	1684.7	1687.0	1689.3	1690.4	1689.1	1686.5	1684.0	1681.4	1678.8	1681.4
167.5°	1695.6	1698.2	1700.7	1703.3	1704.6	1703.2	1700.3	1697.4	1694.6	1691.7	1694.6
170°	1708.2	1710.5	1712.8	1715.1	1716.2	1714.8	1711.9	1709.0	1706.2	1703.3	1706.2
172.5°	1715.9	1718.2	1720.5	1722.8	1723.9	1722.3	1719.2	1716.0	1712.9	1709.7	1712.9
175°	1721.4	1724.0	1726.5	1729.1	1730.4	1728.7	1725.2	1721.8	1718.3	1714.9	1718.3
177.5°	1724.9	1727.2	1729.5	1731.8	1733.0	1731.3	1727.8	1724.4	1720.9	1717.5	1720.9
180°	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	596.5	595.2	593.3	593.3	591.0	591.0	587.4	581.0	575.5	573.6	574.5
5°	647.4	647.9	645.1	642.8	638.7	635.5	629.5	618.1	614.4	607.1	602.0
7.5°	705.6	703.8	698.7	695.0	694.1	686.8	674.0	660.2	649.2	641.9	631.4
10°	771.1	763.8	756.4	754.2	748.7	736.3	721.6	706.5	691.4	675.3	657.5
12.5°	826.1	811.9	811.4	805.9	795.4	788.5	771.1	749.6	723.5	705.6	685.4
15°	885.2	871.9	860.9	850.8	845.8	825.6	811.0	783.9	752.8	733.5	719.8
17.5°	927.3	921.4	902.6	898.0	891.1	867.8	844.4	817.8	790.8	763.8	726.7
20°	961.2	957.6	945.2	938.8	927.8	909.5	881.1	850.4	819.2	780.7	745.9
22.5°	975.9	971.3	961.2	955.7	948.9	933.3	909.0	874.2	833.4	799.1	761.9
25°	947.0	955.3	952.5	950.2	947.5	938.3	920.0	889.3	849.5	810.5	764.2
27.5°	882.0	896.2	909.9	911.8	916.3	920.0	912.7	890.7	857.2	816.0	765.1
30°	794.5	800.9	828.8	837.1	843.5	866.9	880.6	875.1	849.5	812.3	765.6
32.5°	682.2	699.2	727.6	747.3	764.7	790.8	826.5	840.7	831.6	801.3	755.1
35°	575.9	596.1	629.1	654.3	671.7	708.8	750.9	781.6	793.1	778.0	736.7
37.5°	488.9	513.2	542.5	552.1	572.3	618.1	676.3	718.9	746.8	748.2	716.1
40°	423.4	435.7	459.1	473.7	493.5	531.9	588.8	645.1	687.3	701.5	684.5
42.5°	367.9	377.5	394.9	412.8	430.7	460.0	512.2	564.9	621.7	650.1	649.7
45°	323.9	334.0	345.9	360.6	373.0	404.6	445.8	499.9	548.9	592.9	603.9
47.5°	285.4	294.1	308.8	315.2	323.5	353.3	389.0	439.4	490.2	540.6	553.5
50°	257.0	264.4	274.4	278.6	287.7	309.7	339.0	379.8	436.2	482.5	506.3
52.5°	231.4	236.9	244.7	247.9	254.3	270.8	297.4	329.4	376.2	423.8	457.3
55°	209.4	213.0	218.5	222.2	226.8	241.5	261.2	290.0	330.3	371.6	404.1
57.5°	188.8	191.5	197.0	198.8	202.5	214.0	227.7	252.0	289.1	325.8	357.4
60°	169.5	171.4	174.6	178.7	181.4	189.2	202.1	222.2	252.0	285.4	311.1
62.5°	151.2	153.9	154.9	156.7	159.0	166.3	176.4	191.1	217.2	244.7	271.7
65°	132.4	134.7	136.5	137.0	139.3	144.8	153.9	166.8	183.7	207.6	232.8
67.5°	115.0	116.4	117.3	119.1	121.4	124.2	131.5	141.1	156.7	175.9	196.1
70°	99.0	99.0	100.3	100.8	103.5	106.8	110.0	119.1	132.9	148.4	162.2
72.5°	81.6	83.8	83.4	85.7	85.2	87.5	91.6	97.6	107.7	120.0	133.3
75°	66.4	67.8	67.8	67.8	68.7	70.6	72.8	78.3	86.1	96.2	104.0
77.5°	51.8	52.7	52.7	52.7	53.1	55.0	57.3	60.9	66.4	72.4	77.0
80°	37.1	38.0	38.0	38.9	38.9	39.4	41.7	43.5	46.3	50.9	55.4
82.5°	25.2	25.7	26.6	26.6	26.1	27.0	27.5	29.3	32.1	33.0	36.2
85°	13.7	14.2	14.7	14.7	15.1	16.0	15.6	17.4	17.4	19.2	20.2
87.5°	5.5	6.4	6.4	6.0	6.4	6.4	6.4	7.3	7.8	8.2	7.8
90°	37.5	37.0	36.4	36.1	35.2	33.5	31.8	30.1	28.4	26.1	23.8
92.5°	34.8	34.8	34.8	34.8	33.9	32.2	30.5	28.8	27.1	24.8	22.5
95°	36.8	36.5	36.2	36.1	35.2	33.5	31.8	30.1	28.4	28.1	27.8
97.5°	35.5	35.2	34.9	34.8	34.1	32.7	31.2	29.8	28.4	58.5	88.6
100°	35.5	35.2	34.9	34.8	37.2	42.1	47.0	51.9	56.8	96.4	135.9
102.5°	37.4	37.4	37.4	37.4	69.7	134.2	198.7	263.3	327.8	324.4	320.9
105°	388.4	398.7	409.0	414.2	412.9	410.3	407.8	405.2	402.6	401.2	399.7
107.5°	494.5	493.3	492.2	491.6	490.9	489.5	488.0	486.6	485.2	483.2	481.2
110°	573.8	572.9	572.0	571.6	571.3	570.8	570.2	569.7	569.1	567.4	565.6

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	651.9	650.8	649.7	649.1	649.2	649.5	649.8	650.0	650.3	649.7	649.2
115°	730.3	730.3	730.3	730.3	730.0	729.5	728.9	728.4	727.8	728.1	728.4
117.5°	809.1	809.1	809.1	809.1	809.2	809.5	809.8	810.0	810.3	809.5	808.6
120°	883.8	884.3	884.9	885.2	884.9	884.3	883.8	883.2	882.6	882.9	883.2
122.5°	956.1	956.6	957.2	957.5	957.4	957.1	956.8	956.5	956.2	955.6	955.0
125°	1026.5	1026.2	1025.9	1025.8	1025.4	1024.5	1023.7	1022.8	1022.0	1022.6	1023.2
127.5°	1090.9	1091.2	1091.5	1091.6	1091.7	1092.0	1092.3	1092.6	1092.9	1091.5	1090.1
130°	1154.9	1154.9	1154.9	1154.9	1154.8	1154.5	1154.2	1153.9	1153.6	1152.7	1151.9
132.5°	1214.8	1215.1	1215.4	1215.5	1215.4	1215.1	1214.8	1214.5	1214.2	1213.1	1211.9
135°	1272.4	1271.9	1271.3	1271.0	1270.7	1270.1	1269.6	1269.0	1268.4	1267.3	1266.1
137.5°	1324.5	1324.8	1325.1	1325.2	1324.9	1324.3	1323.8	1323.2	1322.6	1321.2	1319.8
140°	1376.2	1375.9	1375.6	1375.5	1375.1	1374.2	1373.4	1372.5	1371.7	1371.1	1370.5
142.5°	1420.7	1420.7	1420.7	1420.7	1420.4	1419.8	1419.3	1418.7	1418.1	1417.8	1417.5
145°	1464.7	1464.2	1463.6	1463.3	1463.2	1462.9	1462.6	1462.3	1462.0	1462.0	1462.0
147.5°	1502.7	1502.4	1502.1	1502.0	1501.9	1501.6	1501.3	1501.0	1500.7	1501.0	1501.3
150°	1538.8	1538.5	1538.2	1538.1	1538.1	1538.1	1538.1	1538.1	1538.1	1538.4	1538.7
152.5°	1571.0	1571.3	1571.6	1571.7	1571.4	1570.8	1570.3	1569.7	1569.1	1569.7	1570.3
155°	1599.2	1600.0	1600.9	1601.3	1600.7	1599.6	1598.5	1597.3	1596.2	1597.1	1597.9
157.5°	1623.6	1625.0	1626.5	1627.2	1626.5	1625.0	1623.6	1622.1	1620.7	1621.9	1623.0
160°	1647.4	1649.1	1650.8	1651.7	1650.8	1649.1	1647.4	1645.6	1643.9	1644.2	1644.5
162.5°	1666.0	1668.0	1670.0	1671.0	1670.1	1668.4	1666.7	1665.0	1663.3	1663.6	1663.9
165°	1684.0	1686.5	1689.1	1690.4	1689.3	1687.0	1684.7	1682.4	1680.1	1680.1	1680.1
167.5°	1697.4	1700.3	1703.2	1704.6	1703.3	1700.7	1698.2	1695.6	1693.0	1693.3	1693.6
170°	1709.0	1711.9	1714.8	1716.2	1715.1	1712.8	1710.5	1708.2	1705.9	1705.6	1705.3
172.5°	1716.0	1719.2	1722.3	1723.9	1722.8	1720.5	1718.2	1715.9	1713.6	1713.3	1713.0
175°	1721.8	1725.2	1728.7	1730.4	1729.1	1726.5	1724.0	1721.4	1718.8	1718.5	1718.2
177.5°	1724.4	1727.8	1731.3	1733.0	1731.8	1729.5	1727.2	1724.9	1722.6	1722.0	1721.5
180°	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	570.4	568.6	567.2	567.2	563.1	559.0	556.7	555.8	554.8	551.2	546.1
5°	593.8	587.8	583.7	579.6	572.7	565.4	558.1	553.9	548.0	539.7	533.8
7.5°	619.9	605.7	601.1	596.1	582.3	570.0	559.9	551.2	541.6	531.0	520.5
10°	641.9	626.8	616.7	608.0	590.1	573.6	558.5	545.7	533.3	519.6	506.7
12.5°	663.0	641.4	630.9	618.1	599.3	575.5	555.8	539.7	521.4	507.2	491.6
15°	692.3	656.1	638.7	630.4	605.2	577.3	553.5	529.6	514.5	493.0	479.2
17.5°	696.9	667.6	656.1	635.0	604.8	573.2	545.7	521.9	498.9	479.7	461.8
20°	712.9	674.4	656.1	642.8	603.0	570.9	540.6	509.9	488.0	467.3	447.2
22.5°	723.0	679.5	660.2	639.1	601.1	562.6	526.9	500.3	473.3	452.2	436.2
25°	720.2	676.7	655.2	635.5	589.2	550.7	518.7	484.7	459.5	436.6	415.6
27.5°	718.9	669.8	646.9	624.9	581.4	541.1	500.8	473.3	445.3	418.8	403.2
30°	715.2	661.1	634.6	610.7	565.4	523.2	488.9	456.8	428.8	404.6	383.9
32.5°	702.8	646.5	620.8	595.2	548.0	505.8	471.0	441.2	413.3	388.1	368.4
35°	686.3	629.1	601.1	574.1	526.9	484.3	452.2	421.1	394.9	370.7	351.9
37.5°	669.8	608.9	582.8	551.6	508.1	463.7	430.7	402.7	378.4	353.3	332.6
40°	646.0	585.1	556.2	529.6	478.8	437.1	406.9	381.7	357.8	334.0	316.6
42.5°	613.5	559.0	529.2	499.9	452.2	411.0	381.7	359.2	336.8	317.1	297.8
45°	580.5	527.4	500.8	474.7	422.9	383.9	356.9	336.3	317.5	296.0	280.4
47.5°	540.6	495.7	469.2	443.5	394.5	355.5	330.8	311.6	294.1	276.3	261.6
50°	499.9	460.9	436.6	410.1	363.3	328.1	303.8	287.7	273.5	256.6	244.7
52.5°	455.9	422.0	401.4	375.7	334.5	301.9	277.2	261.2	249.2	236.9	226.3
55°	409.1	384.4	362.4	341.8	302.9	273.5	251.5	237.3	229.1	217.6	208.5
57.5°	367.0	343.2	329.9	306.5	272.6	243.7	226.3	214.4	204.8	197.9	190.6
60°	323.0	303.8	289.1	272.2	242.4	218.1	199.8	192.9	182.8	177.8	174.6
62.5°	280.9	267.1	253.4	240.5	214.0	191.1	177.3	168.6	162.7	157.6	154.9
65°	241.0	228.2	218.5	207.1	185.1	166.8	153.9	147.1	141.1	139.7	136.5
67.5°	202.1	196.6	186.0	176.9	158.1	143.9	134.2	125.5	122.3	121.0	118.2
70°	169.1	162.7	154.4	146.6	132.4	120.0	111.3	108.1	103.5	103.1	99.9
72.5°	139.3	131.5	125.5	119.6	109.0	98.0	93.5	88.9	86.6	84.8	83.4
75°	110.4	104.9	100.8	95.8	86.6	79.3	72.8	71.0	69.6	69.2	68.3
77.5°	82.5	78.8	77.0	71.9	65.5	59.1	56.4	53.6	53.6	52.7	53.1
80°	58.6	56.4	54.1	51.3	45.8	43.1	40.8	38.9	38.0	37.6	38.0
82.5°	37.1	35.7	35.3	33.4	29.8	28.4	26.6	25.2	25.2	25.2	25.2
85°	20.6	20.6	20.6	17.9	16.5	15.1	14.2	13.7	13.7	13.7	14.2
87.5°	8.7	8.7	7.3	7.3	6.9	6.0	5.5	5.5	6.0	6.0	6.4
90°	21.5	19.2	18.1	16.5	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	20.2	17.9	16.8	17.1	17.7	18.2	18.8	19.4	18.8	18.2	17.7
95°	27.5	27.2	27.1	32.0	41.7	51.5	61.2	71.0	61.2	51.5	41.7
97.5°	118.7	148.8	163.9	160.7	154.4	148.1	141.8	135.5	141.8	148.1	154.4
100°	175.5	215.0	234.8	232.2	227.1	221.9	216.8	211.6	216.8	221.9	227.1
102.5°	317.5	314.0	312.3	310.6	307.1	303.7	300.2	296.8	300.2	303.7	307.1
105°	398.3	396.8	396.1	395.2	393.5	391.8	390.1	388.4	390.1	391.8	393.5
107.5°	479.1	477.1	476.1	475.7	474.8	474.0	473.1	472.3	473.1	474.0	474.8
110°	563.9	562.2	561.3	560.9	560.0	559.1	558.3	557.4	558.3	559.1	560.0



TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	648.6	648.1	647.8	646.9	645.2	643.5	641.7	640.0	641.7	643.5	645.2
115°	728.7	729.0	729.1	728.7	727.8	726.9	726.1	725.2	726.1	726.9	727.8
117.5°	807.8	806.9	806.5	805.9	804.8	803.6	802.5	801.3	802.5	803.6	804.8
120°	883.5	883.8	883.9	883.3	882.2	881.0	879.9	878.7	879.9	881.0	882.2
122.5°	954.5	953.9	953.6	953.3	952.7	952.2	951.6	951.0	951.6	952.2	952.7
125°	1023.7	1024.3	1024.6	1024.0	1022.9	1021.7	1020.6	1019.4	1020.6	1021.7	1022.9
127.5°	1088.6	1087.2	1086.5	1086.4	1086.1	1085.8	1085.5	1085.2	1085.5	1085.8	1086.1
130°	1151.0	1150.1	1149.7	1149.6	1149.3	1149.0	1148.7	1148.4	1148.7	1149.0	1149.3
132.5°	1210.8	1209.7	1209.1	1208.8	1208.2	1207.7	1207.1	1206.5	1207.1	1207.7	1208.2
135°	1265.0	1263.9	1263.3	1263.4	1263.7	1264.0	1264.3	1264.6	1264.3	1264.0	1263.7
137.5°	1318.3	1316.9	1316.2	1316.2	1316.2	1316.2	1316.2	1316.2	1316.2	1316.2	1316.2
140°	1370.0	1369.4	1369.1	1368.8	1368.2	1367.7	1367.1	1366.5	1367.1	1367.7	1368.2
142.5°	1417.2	1416.9	1416.8	1416.2	1415.1	1414.0	1412.8	1411.7	1412.8	1414.0	1415.1
145°	1462.0	1462.0	1462.0	1461.6	1460.7	1459.8	1459.0	1458.1	1459.0	1459.8	1460.7
147.5°	1501.6	1501.9	1502.0	1501.1	1499.4	1497.7	1495.9	1494.2	1495.9	1497.7	1499.4
150°	1539.0	1539.3	1539.4	1538.8	1537.7	1536.5	1535.4	1534.2	1535.4	1536.5	1537.7
152.5°	1570.8	1571.4	1571.7	1571.3	1570.4	1569.5	1568.7	1567.8	1568.7	1569.5	1570.4
155°	1598.8	1599.7	1600.1	1600.0	1599.7	1599.4	1599.1	1598.8	1599.1	1599.4	1599.7
157.5°	1624.2	1625.3	1625.9	1625.9	1625.9	1625.9	1625.9	1625.9	1625.9	1625.9	1625.9
160°	1644.8	1645.1	1645.2	1645.6	1646.5	1647.4	1648.2	1649.1	1648.2	1647.4	1646.5
162.5°	1664.2	1664.5	1664.6	1665.2	1666.3	1667.4	1668.6	1669.7	1668.6	1667.4	1666.3
165°	1680.1	1680.1	1680.1	1680.8	1682.2	1683.7	1685.1	1686.5	1685.1	1683.7	1682.2
167.5°	1693.9	1694.2	1694.3	1695.0	1696.4	1697.9	1699.3	1700.7	1699.3	1697.9	1696.4
170°	1705.0	1704.7	1704.6	1705.5	1707.2	1708.9	1710.6	1712.3	1710.6	1708.9	1707.2
172.5°	1712.7	1712.4	1712.3	1713.2	1714.9	1716.6	1718.4	1720.1	1718.4	1716.6	1714.9
175°	1717.9	1717.6	1717.5	1718.4	1720.1	1721.8	1723.5	1725.2	1723.5	1721.8	1720.1
177.5°	1720.9	1720.4	1720.1	1721.1	1723.1	1725.1	1727.1	1729.1	1727.1	1725.1	1723.1
180°	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	544.8	542.9	543.8	539.3	535.1	529.2	524.1	523.2	522.3	525.1	523.2
5°	529.2	526.9	524.6	519.1	510.9	505.8	498.5	498.0	495.3	491.2	492.1
7.5°	512.2	510.9	507.7	498.9	491.6	482.9	477.0	471.9	469.6	466.0	464.6
10°	498.5	493.5	490.7	481.1	472.4	463.2	455.4	451.8	447.6	444.4	442.1
12.5°	479.7	478.3	470.5	462.8	455.4	444.9	438.9	428.4	422.9	425.6	424.7
15°	467.3	460.9	459.1	448.1	435.7	428.8	417.9	411.0	408.7	404.6	399.5
17.5°	450.8	446.7	440.3	430.2	416.0	406.4	398.6	392.2	389.4	383.9	379.8
20°	435.3	428.4	423.4	414.2	400.4	388.1	378.4	374.3	367.5	362.9	360.6
22.5°	421.1	416.0	408.7	394.9	383.0	371.1	359.7	353.7	347.3	344.5	340.9
25°	403.6	395.4	390.4	375.2	362.4	352.8	342.3	334.5	330.8	326.2	325.3
27.5°	386.7	378.9	373.0	359.7	344.1	331.7	325.3	319.8	313.4	313.4	311.1
30°	369.7	364.2	355.1	342.3	327.6	315.7	308.3	303.3	301.0	299.2	298.7
32.5°	352.8	345.5	340.0	322.6	311.6	300.6	295.1	290.9	288.2	287.7	288.2
35°	335.4	327.1	321.6	306.1	295.1	285.0	282.7	279.0	277.7	277.2	279.5
37.5°	317.1	310.6	303.8	290.9	278.6	272.6	268.0	266.7	266.2	268.9	269.9
40°	300.1	294.6	288.2	274.4	265.3	258.9	256.6	255.2	257.0	259.8	261.2
42.5°	284.1	276.3	271.2	258.9	250.6	247.0	244.2	244.2	246.0	249.2	251.5
45°	267.1	261.2	256.1	245.1	237.8	233.7	233.2	233.7	236.0	238.2	241.0
47.5°	250.6	244.7	239.2	230.0	223.6	221.3	220.8	221.3	225.0	228.2	231.4
50°	235.5	229.1	224.0	215.3	210.3	207.6	208.0	210.3	213.0	217.6	221.8
52.5°	217.6	213.0	208.5	200.7	196.1	194.3	195.6	197.5	202.5	205.7	210.8
55°	200.2	196.1	192.4	186.5	182.8	181.4	182.4	185.1	189.2	194.7	200.7
57.5°	184.2	179.6	175.9	171.8	167.7	168.1	168.6	172.3	177.3	182.4	189.2
60°	166.3	163.6	160.4	155.3	153.5	153.5	154.9	159.0	163.6	171.8	177.8
62.5°	150.3	146.6	144.3	141.1	138.4	138.8	142.0	145.7	151.2	158.1	165.9
65°	133.8	129.7	127.8	125.1	124.2	124.6	126.9	132.4	138.4	144.3	151.7
67.5°	115.5	114.1	112.3	109.5	110.4	110.9	113.2	117.8	124.2	130.1	138.4
70°	99.9	97.1	96.7	94.4	94.4	95.8	100.3	103.5	109.5	115.9	124.6
72.5°	83.4	81.1	81.1	79.3	80.6	82.0	84.3	88.9	94.4	100.8	108.1
75°	66.4	65.5	66.4	65.5	65.5	67.8	70.6	74.2	80.2	87.1	93.0
77.5°	51.3	51.3	50.9	52.2	52.2	53.6	57.3	60.9	65.5	71.0	77.4
80°	37.6	37.6	37.6	38.9	40.3	40.3	42.6	47.2	51.3	55.0	60.9
82.5°	25.7	25.7	25.7	26.6	28.4	28.4	31.2	33.9	38.5	41.7	44.4
85°	15.6	15.6	15.1	16.0	16.5	17.9	20.2	22.0	24.3	27.0	29.8
87.5°	6.9	6.9	7.3	7.8	8.2	9.2	10.1	11.0	13.3	14.2	15.6
90°	16.5	18.1	19.2	21.5	23.8	26.1	28.4	30.1	31.8	33.5	35.2
92.5°	17.1	16.8	17.9	20.2	22.5	24.8	27.1	28.8	30.5	32.2	33.9
95°	32.0	27.1	27.2	27.5	27.8	28.1	28.4	30.1	31.8	33.5	35.2
97.5°	160.7	163.9	148.8	118.7	88.6	58.5	28.4	29.8	31.2	32.7	34.1
100°	232.2	234.8	215.0	175.5	135.9	96.4	56.8	51.9	47.0	42.1	37.2
102.5°	310.6	312.3	314.0	317.5	320.9	324.4	327.8	263.3	198.7	134.2	69.7
105°	395.2	396.1	396.8	398.3	399.7	401.2	402.6	405.2	407.8	410.3	412.9
107.5°	475.7	476.1	477.1	479.1	481.2	483.2	485.2	486.6	488.0	489.5	490.9
110°	560.9	561.3	562.2	563.9	565.6	567.4	569.1	569.7	570.2	570.8	571.3

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	646.9	647.8	648.1	648.6	649.2	649.7	650.3	650.0	649.8	649.5	649.2
115°	728.7	729.1	729.0	728.7	728.4	728.1	727.8	728.4	728.9	729.5	730.0
117.5°	805.9	806.5	806.9	807.8	808.6	809.5	810.3	810.0	809.8	809.5	809.2
120°	883.3	883.9	883.8	883.5	883.2	882.9	882.6	883.2	883.8	884.3	884.9
122.5°	953.3	953.6	953.9	954.5	955.0	955.6	956.2	956.5	956.8	957.1	957.4
125°	1024.0	1024.6	1024.3	1023.7	1023.2	1022.6	1022.0	1022.8	1023.7	1024.5	1025.4
127.5°	1086.4	1086.5	1087.2	1088.6	1090.1	1091.5	1092.9	1092.6	1092.3	1092.0	1091.7
130°	1149.6	1149.7	1150.1	1151.0	1151.9	1152.7	1153.6	1153.9	1154.2	1154.5	1154.8
132.5°	1208.8	1209.1	1209.7	1210.8	1211.9	1213.1	1214.2	1214.5	1214.8	1215.1	1215.4
135°	1263.4	1263.3	1263.9	1265.0	1266.1	1267.3	1268.4	1269.0	1269.6	1270.1	1270.7
137.5°	1316.2	1316.2	1316.9	1318.3	1319.8	1321.2	1322.6	1323.2	1323.8	1324.3	1324.9
140°	1368.8	1369.1	1369.4	1370.0	1370.5	1371.1	1371.7	1372.5	1373.4	1374.2	1375.1
142.5°	1416.2	1416.8	1416.9	1417.2	1417.5	1417.8	1418.1	1418.7	1419.3	1419.8	1420.4
145°	1461.6	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0	1462.3	1462.6	1462.9	1463.2
147.5°	1501.1	1502.0	1501.9	1501.6	1501.3	1501.0	1500.7	1501.0	1501.3	1501.6	1501.9
150°	1538.8	1539.4	1539.3	1539.0	1538.7	1538.4	1538.1	1538.1	1538.1	1538.1	1538.1
152.5°	1571.3	1571.7	1571.4	1570.8	1570.3	1569.7	1569.1	1569.7	1570.3	1570.8	1571.4
155°	1600.0	1600.1	1599.7	1598.8	1597.9	1597.1	1596.2	1597.3	1598.5	1599.6	1600.7
157.5°	1625.9	1625.9	1625.3	1624.2	1623.0	1621.9	1620.7	1622.1	1623.6	1625.0	1626.5
160°	1645.6	1645.2	1645.1	1644.8	1644.5	1644.2	1643.9	1645.6	1647.4	1649.1	1650.8
162.5°	1665.2	1664.6	1664.5	1664.2	1663.9	1663.6	1663.3	1665.0	1666.7	1668.4	1670.1
165°	1680.8	1680.1	1680.1	1680.1	1680.1	1680.1	1680.1	1682.4	1684.7	1687.0	1689.3
167.5°	1695.0	1694.3	1694.2	1693.9	1693.6	1693.3	1693.0	1695.6	1698.2	1700.7	1703.3
170°	1705.5	1704.6	1704.7	1705.0	1705.3	1705.6	1705.9	1708.2	1710.5	1712.8	1715.1
172.5°	1713.2	1712.3	1712.4	1712.7	1713.0	1713.3	1713.6	1715.9	1718.2	1720.5	1722.8
175°	1718.4	1717.5	1717.6	1717.9	1718.2	1718.5	1718.8	1721.4	1724.0	1726.5	1729.1
177.5°	1721.1	1720.1	1720.4	1720.9	1721.5	1722.0	1722.6	1724.9	1727.2	1729.5	1731.8
180°	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	521.9	521.4	519.1	520.0	517.3	518.2	519.6	520.0	521.9	520.5	520.0
5°	489.8	488.9	487.5	486.1	485.7	487.5	484.3	485.2	486.1	487.5	489.3
7.5°	463.7	463.2	461.8	459.5	458.6	457.7	458.2	461.4	460.9	460.5	463.7
10°	439.8	440.3	437.6	437.1	434.3	433.9	434.3	435.3	436.6	438.5	438.9
12.5°	415.1	421.1	416.0	414.2	410.1	412.4	413.3	409.1	411.4	412.8	419.7
15°	399.5	396.8	393.6	393.6	391.7	390.8	388.5	391.7	393.6	396.3	395.4
17.5°	378.0	373.4	371.6	369.7	370.2	372.0	367.0	374.3	374.3	375.7	373.4
20°	359.2	355.5	353.3	352.3	351.0	350.0	349.6	351.4	354.2	355.1	357.4
22.5°	339.5	339.5	335.8	334.5	333.5	332.2	334.5	333.1	334.9	336.8	340.4
25°	323.0	323.0	321.6	319.8	318.4	317.5	318.9	318.4	319.8	322.1	323.0
27.5°	309.7	308.3	307.9	307.4	307.0	307.4	307.0	308.3	309.7	310.2	309.3
30°	298.3	296.9	297.4	297.4	297.8	297.4	296.9	298.3	298.7	297.8	298.3
32.5°	287.7	287.7	288.6	289.1	289.1	289.6	290.0	289.1	289.6	288.2	288.6
35°	279.0	279.9	280.9	281.3	281.8	281.3	282.2	281.8	280.9	279.9	279.5
37.5°	270.3	271.2	273.1	273.5	274.9	275.4	274.4	274.4	274.0	272.2	271.2
40°	261.2	262.1	264.4	265.7	266.7	268.0	267.1	267.1	265.3	263.4	262.1
42.5°	252.5	254.3	256.6	258.0	259.8	259.8	259.8	258.9	256.6	254.7	253.4
45°	243.7	244.2	247.4	249.7	251.5	251.5	251.5	250.2	248.8	245.1	243.3
47.5°	234.1	235.5	239.2	241.5	243.3	243.7	243.7	242.4	239.6	236.4	234.1
50°	223.6	225.9	230.0	233.2	235.5	236.4	235.0	234.1	230.9	227.3	224.5
52.5°	213.5	216.3	221.3	224.0	227.3	227.7	227.3	225.9	222.2	217.2	214.9
55°	203.4	205.7	211.2	215.8	218.5	219.5	218.5	216.3	211.7	206.6	204.3
57.5°	192.4	195.6	201.6	206.2	209.4	209.8	208.9	206.6	203.0	196.6	193.3
60°	181.0	185.1	191.1	195.6	199.8	200.2	199.3	196.1	191.5	185.1	182.4
62.5°	169.5	172.7	179.6	184.6	187.9	190.1	188.3	185.1	180.5	174.1	170.0
65°	156.2	160.8	166.8	171.4	175.0	175.5	174.6	171.8	166.8	159.9	156.7
67.5°	143.4	146.6	152.6	158.5	159.9	161.3	159.9	157.2	153.0	147.1	142.5
70°	127.8	130.6	137.9	142.0	143.9	145.2	144.3	141.6	137.9	132.4	128.7
72.5°	112.3	114.5	121.4	124.6	128.3	127.8	127.4	125.5	120.5	116.8	114.5
75°	95.8	98.5	103.1	107.2	108.6	108.6	108.6	107.2	104.0	98.0	95.8
77.5°	80.6	82.0	85.7	88.0	89.3	89.8	89.3	87.1	85.2	81.1	79.7
80°	61.9	65.5	68.3	68.7	70.6	70.6	70.6	69.6	67.8	63.7	63.2
82.5°	46.7	47.6	50.4	51.8	52.7	52.2	52.2	50.4	49.9	47.6	46.7
85°	31.6	33.0	32.5	34.4	34.8	33.9	33.9	34.8	32.5	33.0	31.6
87.5°	17.4	17.4	18.3	17.9	19.7	19.7	18.8	19.2	18.3	17.9	17.4
90°	36.1	36.4	37.0	37.5	38.1	38.7	38.1	37.5	37.0	36.4	36.1
92.5°	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8
95°	36.1	36.2	36.5	36.8	37.1	37.4	37.1	36.8	36.5	36.2	36.1
97.5°	34.8	34.9	35.2	35.5	35.8	36.1	35.8	35.5	35.2	34.9	34.8
100°	34.8	34.9	35.2	35.5	35.8	36.1	35.8	35.5	35.2	34.9	34.8
102.5°	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4
105°	414.2	409.0	398.7	388.4	378.1	367.8	378.1	388.4	398.7	409.0	414.2
107.5°	491.6	492.2	493.3	494.5	495.6	496.8	495.6	494.5	493.3	492.2	491.6
110°	571.6	572.0	572.9	573.8	574.6	575.5	574.6	573.8	572.9	572.0	571.6

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	649.1	649.7	650.8	651.9	653.1	654.2	653.1	651.9	650.8	649.7	649.1
115°	730.3	730.3	730.3	730.3	730.3	730.3	730.3	730.3	730.3	730.3	730.3
117.5°	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1
120°	885.2	884.9	884.3	883.8	883.2	882.6	883.2	883.8	884.3	884.9	885.2
122.5°	957.5	957.2	956.6	956.1	955.5	954.9	955.5	956.1	956.6	957.2	957.5
125°	1025.8	1025.9	1026.2	1026.5	1026.8	1027.1	1026.8	1026.5	1026.2	1025.9	1025.8
127.5°	1091.6	1091.5	1091.2	1090.9	1090.7	1090.4	1090.7	1090.9	1091.2	1091.5	1091.6
130°	1154.9	1154.9	1154.9	1154.9	1154.9	1154.9	1154.9	1154.9	1154.9	1154.9	1154.9
132.5°	1215.5	1215.4	1215.1	1214.8	1214.5	1214.2	1214.5	1214.8	1215.1	1215.4	1215.5
135°	1271.0	1271.3	1271.9	1272.4	1273.0	1273.6	1273.0	1272.4	1271.9	1271.3	1271.0
137.5°	1325.2	1325.1	1324.8	1324.5	1324.2	1323.9	1324.2	1324.5	1324.8	1325.1	1325.2
140°	1375.5	1375.6	1375.9	1376.2	1376.5	1376.8	1376.5	1376.2	1375.9	1375.6	1375.5
142.5°	1420.7	1420.7	1420.7	1420.7	1420.7	1420.7	1420.7	1420.7	1420.7	1420.7	1420.7
145°	1463.3	1463.6	1464.2	1464.7	1465.3	1465.9	1465.3	1464.7	1464.2	1463.6	1463.3
147.5°	1502.0	1502.1	1502.4	1502.7	1503.0	1503.3	1503.0	1502.7	1502.4	1502.1	1502.0
150°	1538.1	1538.2	1538.5	1538.8	1539.1	1539.4	1539.1	1538.8	1538.5	1538.2	1538.1
152.5°	1571.7	1571.6	1571.3	1571.0	1570.7	1570.4	1570.7	1571.0	1571.3	1571.6	1571.7
155°	1601.3	1600.9	1600.0	1599.2	1598.3	1597.5	1598.3	1599.2	1600.0	1600.9	1601.3
157.5°	1627.2	1626.5	1625.0	1623.6	1622.1	1620.7	1622.1	1623.6	1625.0	1626.5	1627.2
160°	1651.7	1650.8	1649.1	1647.4	1645.6	1643.9	1645.6	1647.4	1649.1	1650.8	1651.7
162.5°	1671.0	1670.0	1668.0	1666.0	1664.0	1662.0	1664.0	1666.0	1668.0	1670.0	1671.0
165°	1690.4	1689.1	1686.5	1684.0	1681.4	1678.8	1681.4	1684.0	1686.5	1689.1	1690.4
167.5°	1704.6	1703.2	1700.3	1697.4	1694.6	1691.7	1694.6	1697.4	1700.3	1703.2	1704.6
170°	1716.2	1714.8	1711.9	1709.0	1706.2	1703.3	1706.2	1709.0	1711.9	1714.8	1716.2
172.5°	1723.9	1722.3	1719.2	1716.0	1712.9	1709.7	1712.9	1716.0	1719.2	1722.3	1723.9
175°	1730.4	1728.7	1725.2	1721.8	1718.3	1714.9	1718.3	1721.8	1725.2	1728.7	1730.4
177.5°	1733.0	1731.3	1727.8	1724.4	1720.9	1717.5	1720.9	1724.4	1727.8	1731.3	1733.0
180°	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	520.0	522.8	520.0	521.9	522.8	525.1	526.0	530.1	531.5	534.7	534.7
5°	488.9	490.2	490.7	492.5	494.4	498.9	502.2	508.1	515.0	515.9	520.0
7.5°	463.7	466.0	469.6	468.3	471.5	478.3	482.5	489.8	496.7	500.3	505.4
10°	441.2	444.0	445.3	446.7	452.7	458.6	465.0	470.1	479.2	484.7	488.9
12.5°	422.9	420.6	423.4	428.4	435.3	438.9	447.6	455.4	462.3	468.3	471.9
15°	399.1	400.9	403.6	412.4	414.2	423.4	426.6	435.3	448.1	453.6	458.2
17.5°	376.2	382.1	387.6	390.8	396.3	403.6	412.8	422.4	430.7	437.1	442.6
20°	357.8	363.8	367.0	369.3	374.8	384.9	393.6	405.5	416.0	421.1	428.4
22.5°	343.2	343.2	347.8	354.6	357.8	367.5	374.8	387.6	399.1	405.5	412.4
25°	324.8	327.6	331.3	337.2	341.8	349.6	360.1	371.1	383.5	389.0	397.7
27.5°	309.7	312.9	318.0	319.3	323.9	330.8	341.8	353.7	366.5	372.5	379.8
30°	298.3	300.1	301.9	304.7	308.8	314.8	323.9	334.5	350.0	354.6	363.8
32.5°	288.2	289.1	290.0	292.3	294.6	300.6	307.9	319.3	332.2	339.0	347.3
35°	279.0	278.1	278.6	279.9	282.2	284.5	292.3	301.9	313.8	322.1	328.5
37.5°	270.3	268.5	268.0	268.0	268.9	271.7	277.7	285.9	298.7	305.6	312.0
40°	260.7	258.9	258.0	257.5	257.0	258.9	263.4	271.7	281.8	288.2	295.5
42.5°	251.5	249.7	247.4	247.0	246.0	247.0	250.2	258.0	266.7	273.1	279.0
45°	242.4	239.2	236.4	234.6	235.0	233.7	236.0	241.9	252.0	256.1	262.1
47.5°	232.3	228.6	225.0	223.1	221.3	222.2	223.1	228.2	236.9	241.0	247.0
50°	222.7	217.6	213.5	211.2	209.8	208.9	209.8	214.9	221.3	225.0	230.0
52.5°	211.7	206.6	202.5	198.8	197.0	195.6	196.1	200.7	206.6	210.3	215.3
55°	201.6	195.2	189.7	185.1	183.7	183.3	182.8	186.0	191.1	194.7	198.8
57.5°	190.1	183.7	177.8	172.3	169.5	169.1	169.1	170.0	176.4	179.1	181.4
60°	178.7	171.8	165.4	160.4	156.2	154.9	154.4	156.2	159.4	162.2	165.4
62.5°	165.9	159.0	151.2	146.6	142.5	138.8	140.2	140.7	145.2	146.6	149.4
65°	153.5	145.7	139.3	132.0	127.4	125.1	124.2	125.1	128.7	129.2	131.0
67.5°	139.3	132.0	124.2	119.1	115.0	110.9	110.0	110.0	111.8	113.2	115.5
70°	125.5	118.2	109.5	104.0	99.9	96.2	94.8	94.4	95.8	96.7	99.0
72.5°	109.5	102.2	95.8	89.8	84.8	82.0	80.6	79.7	81.1	82.0	82.5
75°	92.6	86.6	80.2	74.2	71.0	68.3	66.4	65.1	66.0	66.0	66.0
77.5°	76.5	70.6	65.5	61.4	57.3	54.1	52.7	51.3	51.8	51.8	52.7
80°	59.6	55.4	51.3	47.6	44.0	41.2	40.3	38.9	38.0	37.6	37.6
82.5°	44.0	40.8	37.1	33.9	32.1	29.3	28.4	26.6	26.6	26.1	26.1
85°	29.3	27.5	23.8	21.5	20.2	18.8	17.9	17.0	15.6	15.6	15.1
87.5°	15.6	14.7	13.7	11.0	11.0	9.6	9.2	8.7	7.3	7.8	7.8
90°	35.2	33.5	31.8	30.1	28.4	26.1	23.8	21.5	19.2	18.1	16.5
92.5°	33.9	32.2	30.5	28.8	27.1	24.8	22.5	20.2	17.9	16.8	17.1
95°	35.2	33.5	31.8	30.1	28.4	28.1	27.8	27.5	27.2	27.1	32.0
97.5°	34.1	32.7	31.2	29.8	28.4	58.5	88.6	118.7	148.8	163.9	160.7
100°	37.2	42.1	47.0	51.9	56.8	96.4	135.9	175.5	215.0	234.8	232.2
102.5°	69.7	134.2	198.7	263.3	327.8	324.4	320.9	317.5	314.0	312.3	310.6
105°	412.9	410.3	407.8	405.2	402.6	401.2	399.7	398.3	396.8	396.1	395.2
107.5°	490.9	489.5	488.0	486.6	485.2	483.2	481.2	479.1	477.1	476.1	475.7
110°	571.3	570.8	570.2	569.7	569.1	567.4	565.6	563.9	562.2	561.3	560.9

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	649.2	649.5	649.8	650.0	650.3	649.7	649.2	648.6	648.1	647.8	646.9
115°	730.0	729.5	728.9	728.4	727.8	728.1	728.4	728.7	729.0	729.1	728.7
117.5°	809.2	809.5	809.8	810.0	810.3	809.5	808.6	807.8	806.9	806.5	805.9
120°	884.9	884.3	883.8	883.2	882.6	882.9	883.2	883.5	883.8	883.9	883.3
122.5°	957.4	957.1	956.8	956.5	956.2	955.6	955.0	954.5	953.9	953.6	953.3
125°	1025.4	1024.5	1023.7	1022.8	1022.0	1022.6	1023.2	1023.7	1024.3	1024.6	1024.0
127.5°	1091.7	1092.0	1092.3	1092.6	1092.9	1091.5	1090.1	1088.6	1087.2	1086.5	1086.4
130°	1154.8	1154.5	1154.2	1153.9	1153.6	1152.7	1151.9	1151.0	1150.1	1149.7	1149.6
132.5°	1215.4	1215.1	1214.8	1214.5	1214.2	1213.1	1211.9	1210.8	1209.7	1209.1	1208.8
135°	1270.7	1270.1	1269.6	1269.0	1268.4	1267.3	1266.1	1265.0	1263.9	1263.3	1263.4
137.5°	1324.9	1324.3	1323.8	1323.2	1322.6	1321.2	1319.8	1318.3	1316.9	1316.2	1316.2
140°	1375.1	1374.2	1373.4	1372.5	1371.7	1371.1	1370.5	1370.0	1369.4	1369.1	1368.8
142.5°	1420.4	1419.8	1419.3	1418.7	1418.1	1417.8	1417.5	1417.2	1416.9	1416.8	1416.2
145°	1463.2	1462.9	1462.6	1462.3	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0	1461.6
147.5°	1501.9	1501.6	1501.3	1501.0	1500.7	1501.0	1501.3	1501.6	1501.9	1502.0	1501.1
150°	1538.1	1538.1	1538.1	1538.1	1538.1	1538.4	1538.7	1539.0	1539.3	1539.4	1538.8
152.5°	1571.4	1570.8	1570.3	1569.7	1569.1	1569.7	1570.3	1570.8	1571.4	1571.7	1571.3
155°	1600.7	1599.6	1598.5	1597.3	1596.2	1597.1	1597.9	1598.8	1599.7	1600.1	1600.0
157.5°	1626.5	1625.0	1623.6	1622.1	1620.7	1621.9	1623.0	1624.2	1625.3	1625.9	1625.9
160°	1650.8	1649.1	1647.4	1645.6	1643.9	1644.2	1644.5	1644.8	1645.1	1645.2	1645.6
162.5°	1670.1	1668.4	1666.7	1665.0	1663.3	1663.6	1663.9	1664.2	1664.5	1664.6	1665.2
165°	1689.3	1687.0	1684.7	1682.4	1680.1	1680.1	1680.1	1680.1	1680.1	1680.1	1680.8
167.5°	1703.3	1700.7	1698.2	1695.6	1693.0	1693.3	1693.6	1693.9	1694.2	1694.3	1695.0
170°	1715.1	1712.8	1710.5	1708.2	1705.9	1705.6	1705.3	1705.0	1704.7	1704.6	1705.5
172.5°	1722.8	1720.5	1718.2	1715.9	1713.6	1713.3	1713.0	1712.7	1712.4	1712.3	1713.2
175°	1729.1	1726.5	1724.0	1721.4	1718.8	1718.5	1718.2	1717.9	1717.6	1717.5	1718.4
177.5°	1731.8	1729.5	1727.2	1724.9	1722.6	1722.0	1721.5	1720.9	1720.4	1720.1	1721.1
180°	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2	1725.2

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	553.0	553.0	553.0	553.0
2.5°	537.9	542.5	546.6	553.0
5°	526.0	532.4	541.1	550.7
7.5°	512.2	522.3	533.8	547.1
10°	499.4	510.9	525.5	541.6
12.5°	486.1	499.9	515.9	533.3
15°	471.0	484.7	502.6	526.0
17.5°	457.3	473.7	493.0	517.7
20°	441.2	456.8	477.9	506.3
22.5°	427.0	444.9	468.3	493.0
25°	411.4	427.0	450.4	480.2
27.5°	395.9	415.1	437.6	466.4
30°	380.7	396.8	421.1	451.3
32.5°	364.2	383.5	405.9	434.3
35°	346.4	364.7	385.8	416.5
37.5°	330.3	348.2	369.7	396.8
40°	312.5	331.3	351.0	378.0
42.5°	295.1	312.0	331.7	356.5
45°	278.1	292.8	310.6	332.2
47.5°	260.7	273.1	289.6	308.8
50°	241.9	255.2	267.6	283.6
52.5°	224.5	236.0	246.0	259.3
55°	207.6	215.3	223.6	233.7
57.5°	189.7	195.6	201.6	212.1
60°	171.8	177.3	180.5	187.4
62.5°	154.4	156.7	160.8	164.9
65°	135.2	138.4	140.7	145.7
67.5°	117.8	119.1	121.4	124.6
70°	99.4	102.6	103.5	105.8
72.5°	83.8	85.2	86.1	86.6
75°	66.4	67.8	68.7	71.5
77.5°	52.2	51.8	53.6	54.1
80°	38.5	37.1	37.6	39.4
82.5°	25.2	25.7	25.2	25.2
85°	15.6	15.1	14.2	14.7
87.5°	6.9	6.9	6.4	6.4
90°	13.4	10.2	7.1	3.9
92.5°	17.7	18.2	18.8	19.4
95°	41.7	51.5	61.2	71.0
97.5°	154.4	148.1	141.8	135.5
100°	227.1	221.9	216.8	211.6
102.5°	307.1	303.7	300.2	296.8
105°	393.5	391.8	390.1	388.4
107.5°	474.8	474.0	473.1	472.3
110°	560.0	559.1	558.3	557.4

TEST NUMBER: P1033431

CATALOG NUMBER: S124DIW-B350D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	645.2	643.5	641.7	640.0
115°	727.8	726.9	726.1	725.2
117.5°	804.8	803.6	802.5	801.3
120°	882.2	881.0	879.9	878.7
122.5°	952.7	952.2	951.6	951.0
125°	1022.9	1021.7	1020.6	1019.4
127.5°	1086.1	1085.8	1085.5	1085.2
130°	1149.3	1149.0	1148.7	1148.4
132.5°	1208.2	1207.7	1207.1	1206.5
135°	1263.7	1264.0	1264.3	1264.6
137.5°	1316.2	1316.2	1316.2	1316.2
140°	1368.2	1367.7	1367.1	1366.5
142.5°	1415.1	1414.0	1412.8	1411.7
145°	1460.7	1459.8	1459.0	1458.1
147.5°	1499.4	1497.7	1495.9	1494.2
150°	1537.7	1536.5	1535.4	1534.2
152.5°	1570.4	1569.5	1568.7	1567.8
155°	1599.7	1599.4	1599.1	1598.8
157.5°	1625.9	1625.9	1625.9	1625.9
160°	1646.5	1647.4	1648.2	1649.1
162.5°	1666.3	1667.4	1668.6	1669.7
165°	1682.2	1683.7	1685.1	1686.5
167.5°	1696.4	1697.9	1699.3	1700.7
170°	1707.2	1708.9	1710.6	1712.3
172.5°	1714.9	1716.6	1718.4	1720.1
175°	1720.1	1721.8	1723.5	1725.2
177.5°	1723.1	1725.1	1727.1	1729.1
180°	1725.2	1725.2	1725.2	1725.2

(END OF REPORT)