

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033437

Luminaire Tested: S124DIW-B350D1340UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033437
REPORT IS A COMBINATION OF REPORTS P997402 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D1340UB50-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6641.0 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	88	84	81	81	78	75	72	59	57	56	43	41	40	27	27	26			19
2	83	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22			16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	21	20	19			14
4	70	59	52	46	61	53	47	42	41	37	33	30	27	25	19	18	16			12
5	64	53	45	39	56	47	41	36	36	32	28	27	24	21	17	16	14			10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	16	14	12			9
7	54	42	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11			8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10			7
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9			7
10	43	32	25	20	38	29	23	19	22	18	15	17	14	12	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4362	4362	4362	4362
5°	4351	5004	4376	3760
10°	4318	5838	4351	3299
15°	4266	6730	4296	2951
20°	4211	7298	4241	2646
25°	4130	7214	4170	2421
30°	4052	5963	4101	2305
35°	3941	4444	3985	2235
40°	3812	3347	3849	2200
45°	3615	2687	3660	2153
50°	3379	2264	3428	2132
55°	3102	1970	3152	2107
60°	2834	1735	2917	2072
65°	2580	1492	2606	1985
70°	2285	1228	2334	1828
75°	1991	943	1980	1552
80°	1567	620	1551	1178
85°	1033	279	968	688

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5640 cd/sqm

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	0.8
10°-20°	160.7	2.4
20°-30°	255.3	3.8
30°-40°	283.6	4.3
40°-50°	257.9	3.9
50°-60°	210.8	3.2
60°-70°	150.5	2.3
70°-80°	82.8	1.2
80°-90°	25.8	0.4
90°-100°	55.4	0.8
100°-110°	364.7	5.5
110°-120°	696.3	10.5
120°-130°	884.0	13.3
130°-140°	945.6	14.2
140°-150°	884.2	13.3
150°-160°	713.1	10.7
160°-170°	459.9	6.9
170°-180°	158.5	2.4
0°-30°	468.0	7.0
0°-40°	751.6	11.3
0°-60°	1220.4	18.4
0°-90°	1479.4	22.3
90°-120°	1116.3	16.8
90°-150°	3830.1	57.7
90°-180°	5162.0	77.7
0°-180°	6641.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	535	535	535	535	535	
5°	533	628	536	472	533	51
15°	509	862	512	378	509	144
25°	464	915	469	307	464	214
35°	403	541	407	272	403	252
45°	321	304	325	243	321	248
55°	226	198	230	212	226	203
65°	141	128	142	170	141	139
75°	69	64	69	105	69	73
85°	14	13	13	33	14	17
90°	4	37	4	37	4	4
95°	69	36	69	36	69	85
105°	376	356	376	356	376	393
115°	701	706	701	706	701	690
125°	986	993	986	993	986	880
135°	1223	1231	1223	1231	1223	942
145°	1410	1417	1410	1417	1410	881
155°	1546	1544	1546	1544	1546	713
165°	1631	1623	1631	1623	1631	461
175°	1668	1658	1668	1658	1668	159
180°	1668	1668	1668	1668	1668	

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	534.9	540.2	542.4	544.2	550.0	551.7	552.2	554.8	557.1	557.5	557.5
5°	532.7	541.1	547.7	553.9	563.3	567.2	572.1	577.4	584.5	589.0	591.2
7.5°	529.1	541.5	551.7	562.4	575.2	583.2	587.6	601.8	611.6	619.5	629.3
10°	523.8	539.8	554.4	569.9	588.1	597.8	607.6	624.9	638.6	654.1	666.5
12.5°	515.8	536.7	554.4	576.1	598.7	610.2	621.8	651.9	667.8	681.6	703.7
15°	508.7	529.6	554.8	577.0	604.9	622.2	639.0	658.5	683.8	713.5	734.8
17.5°	500.8	526.9	550.4	581.4	612.4	628.8	642.6	672.7	708.2	737.4	756.9
20°	489.7	516.3	547.3	580.1	616.9	629.7	647.9	688.2	720.1	748.9	780.8
22.5°	476.8	507.9	540.7	572.1	610.2	637.3	657.2	692.7	731.2	764.5	800.3
25°	464.4	498.1	526.9	569.9	610.2	628.4	651.0	693.1	735.2	775.5	812.3
27.5°	451.1	482.6	521.6	555.7	601.4	621.3	645.7	691.8	736.5	776.9	816.3
30°	436.5	470.2	502.5	542.9	587.2	612.9	635.5	685.6	731.2	773.3	810.1
32.5°	420.1	452.0	486.6	524.7	571.2	597.4	625.7	677.1	725.9	762.2	790.6
35°	402.8	435.2	465.3	504.3	552.2	578.3	605.8	662.5	710.8	740.5	756.9
37.5°	383.8	414.4	444.0	482.6	530.5	558.4	586.3	641.3	686.9	711.7	707.3
40°	365.6	393.1	420.6	456.9	507.0	536.7	561.0	616.4	656.3	667.0	652.3
42.5°	344.8	368.3	394.9	432.1	480.8	508.7	539.3	589.8	619.5	615.1	590.3
45°	321.3	342.1	368.7	403.7	453.4	482.2	507.9	555.7	577.4	566.4	521.2
47.5°	298.7	319.1	340.8	375.8	424.1	448.5	474.6	517.6	530.0	506.5	461.3
50°	274.3	291.2	313.8	347.0	392.2	417.9	439.6	474.2	478.6	449.8	402.8
52.5°	250.8	265.0	286.7	319.5	361.6	382.0	403.3	433.9	430.3	400.6	355.4
55°	226.0	239.3	259.2	289.4	326.6	346.1	364.3	391.3	383.8	353.2	313.8
57.5°	205.2	214.5	234.0	261.9	292.5	313.8	329.3	350.5	339.0	308.4	271.7
60°	181.3	192.8	209.2	231.8	261.9	276.1	289.8	304.0	296.0	266.8	234.0
62.5°	159.5	168.4	182.6	204.3	227.8	240.6	255.3	264.1	256.1	229.1	201.6
65°	140.9	148.0	159.1	176.8	199.4	210.1	218.5	226.9	220.3	195.0	175.0
67.5°	120.5	126.7	136.0	150.2	169.3	176.8	184.8	190.6	183.0	166.2	146.7
70°	102.4	106.8	115.7	126.3	139.6	146.7	153.3	159.1	152.4	138.3	123.6
72.5°	83.8	87.3	95.3	102.8	114.8	119.7	124.5	129.0	126.7	113.4	101.5
75°	69.1	70.5	75.8	82.0	89.5	94.8	98.4	101.0	99.3	88.6	81.1
77.5°	52.3	54.1	58.1	62.9	69.6	72.7	74.9	77.6	75.3	66.9	61.6
80°	38.1	38.6	40.8	45.2	49.6	50.1	52.3	55.8	54.5	48.7	44.8
82.5°	24.4	25.7	26.6	29.2	32.4	33.2	34.6	35.5	35.0	31.5	30.1
85°	14.2	14.2	15.1	16.8	17.7	19.1	19.5	19.9	20.8	18.6	17.3
87.5°	6.2	6.6	6.6	7.1	8.0	8.0	8.4	8.9	9.3	8.9	7.5
90°	3.7	6.8	9.8	12.9	16.0	17.5	18.6	20.8	23.0	25.2	27.4
92.5°	18.7	18.1	17.6	17.0	16.5	16.2	17.3	19.5	21.8	24.0	26.2
95°	68.6	59.2	49.8	40.3	30.9	26.2	26.3	26.6	26.9	27.1	27.4
97.5°	131.0	137.1	143.2	149.3	155.4	158.4	143.8	114.7	85.6	56.5	27.4
100°	204.6	209.6	214.6	219.6	224.6	227.1	208.0	169.7	131.4	93.2	54.9
102.5°	287.0	290.3	293.6	296.9	300.2	301.9	303.6	306.9	310.2	313.6	316.9
105°	375.5	377.2	378.8	380.5	382.2	383.0	383.7	385.1	386.5	387.9	389.3
107.5°	456.6	457.4	458.3	459.1	460.0	460.4	461.4	463.3	465.2	467.2	469.1
110°	539.0	539.8	540.6	541.5	542.3	542.7	543.5	545.2	546.9	548.5	550.2

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	618.8	620.5	622.1	623.8	625.5	626.3	626.6	627.1	627.7	628.2	628.8
115°	701.2	702.0	702.8	703.7	704.5	704.9	704.8	704.5	704.2	704.0	703.7
117.5°	774.8	775.9	777.0	778.1	779.2	779.8	780.2	781.0	781.9	782.7	783.5
120°	849.6	850.7	851.8	852.9	854.0	854.6	854.5	854.2	853.9	853.7	853.4
122.5°	919.5	920.1	920.6	921.2	921.7	922.0	922.3	922.8	923.4	923.9	924.5
125°	985.6	986.7	987.8	988.9	990.0	990.6	990.3	989.8	989.2	988.7	988.1
127.5°	1049.2	1049.5	1049.8	1050.1	1050.4	1050.5	1051.2	1052.6	1053.9	1055.3	1056.7
130°	1110.4	1110.7	1110.9	1111.2	1111.5	1111.6	1112.0	1112.9	1113.7	1114.6	1115.4
132.5°	1166.5	1167.1	1167.6	1168.2	1168.7	1169.0	1169.6	1170.7	1171.8	1172.9	1174.0
135°	1222.7	1222.4	1222.1	1221.8	1221.5	1221.4	1222.0	1223.1	1224.2	1225.3	1226.4
137.5°	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6	1273.3	1274.7	1276.0	1277.4	1278.8
140°	1321.2	1321.8	1322.3	1322.9	1323.4	1323.7	1324.0	1324.5	1325.1	1325.6	1326.2
142.5°	1364.9	1366.0	1367.1	1368.2	1369.3	1369.9	1370.0	1370.3	1370.6	1370.8	1371.1
145°	1409.8	1410.6	1411.4	1412.3	1413.1	1413.5	1413.5	1413.5	1413.5	1413.5	1413.5
147.5°	1444.7	1446.4	1448.0	1449.7	1451.4	1452.2	1452.1	1451.8	1451.5	1451.3	1451.0
150°	1483.4	1484.5	1485.6	1486.7	1487.8	1488.4	1488.3	1488.0	1487.7	1487.5	1487.2
152.5°	1515.8	1516.6	1517.5	1518.3	1519.2	1519.6	1519.3	1518.8	1518.2	1517.7	1517.1
155°	1545.8	1546.1	1546.3	1546.6	1546.9	1547.0	1546.6	1545.8	1544.9	1544.1	1543.3
157.5°	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1571.4	1570.3	1569.2	1568.1	1567.0
160°	1594.4	1593.6	1592.8	1591.9	1591.1	1590.7	1590.6	1590.3	1590.0	1589.8	1589.5
162.5°	1614.4	1613.3	1612.2	1611.1	1610.0	1609.4	1609.3	1609.0	1608.7	1608.5	1608.2
165°	1630.6	1629.2	1627.8	1626.5	1625.1	1624.4	1624.4	1624.4	1624.4	1624.4	1624.4
167.5°	1644.4	1643.0	1641.6	1640.2	1638.8	1638.1	1638.0	1637.7	1637.4	1637.2	1636.9
170°	1655.6	1653.9	1652.3	1650.6	1648.9	1648.1	1648.2	1648.5	1648.8	1649.0	1649.3
172.5°	1663.1	1661.4	1659.8	1658.1	1656.4	1655.6	1655.7	1656.0	1656.3	1656.5	1656.8
175°	1668.1	1666.4	1664.8	1663.1	1661.4	1660.6	1660.7	1661.0	1661.3	1661.5	1661.8
177.5°	1671.8	1669.9	1667.9	1666.0	1664.1	1663.1	1663.4	1663.9	1664.5	1665.0	1665.6
180°	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	558.8	566.8	570.3	571.2	576.1	573.0	574.3	573.9	577.4	577.9	577.9
5°	599.6	608.9	612.0	616.4	623.1	624.9	623.5	626.2	631.1	627.5	632.8
7.5°	642.6	652.8	659.9	669.6	671.8	677.6	681.1	684.2	685.1	685.6	686.5
10°	682.5	695.3	705.1	721.5	725.0	728.1	743.6	737.4	745.4	742.7	743.6
12.5°	714.8	740.1	748.1	775.5	778.2	788.8	787.9	797.7	799.5	803.0	799.5
15°	757.4	786.6	799.5	815.0	823.8	836.2	838.5	851.8	857.1	861.9	857.1
17.5°	796.4	811.9	844.7	857.1	862.8	869.5	886.3	891.2	899.2	896.1	904.9
20°	815.9	838.0	872.6	893.9	902.7	908.9	923.1	930.6	933.7	933.7	934.6
22.5°	833.1	865.0	890.8	915.1	923.1	927.5	936.0	941.7	943.0	943.9	944.8
25°	848.7	877.5	898.3	912.0	915.1	915.1	920.0	916.5	910.7	915.1	917.8
27.5°	848.7	869.0	878.3	883.2	883.2	871.3	864.2	849.5	837.1	833.6	841.6
30°	834.5	843.8	830.9	819.0	809.7	801.7	773.8	751.6	747.2	744.1	756.0
32.5°	801.7	789.7	764.5	729.9	716.1	698.0	676.3	659.4	649.2	645.7	643.0
35°	743.6	712.6	679.8	633.3	623.5	600.5	570.8	558.4	541.5	541.1	546.9
37.5°	680.2	632.4	596.9	552.6	538.9	514.5	486.6	473.7	462.2	453.4	464.0
40°	606.2	564.6	510.5	474.2	454.7	441.8	418.3	404.2	398.8	394.4	401.1
42.5°	537.1	491.5	449.4	412.1	396.2	381.6	366.0	352.3	348.3	347.9	352.8
45°	468.4	423.7	384.7	352.8	342.6	333.7	318.6	314.6	308.0	303.6	305.8
47.5°	413.5	367.4	335.0	310.7	301.8	294.3	284.5	277.9	272.1	270.3	273.0
50°	359.4	328.4	295.1	274.8	268.1	261.0	253.5	247.3	244.6	242.9	244.6
52.5°	316.0	282.7	260.1	243.7	237.1	231.8	226.5	223.8	220.3	221.1	222.9
55°	277.0	247.7	228.7	216.7	212.7	210.5	203.9	200.8	199.4	198.5	199.4
57.5°	240.2	218.9	204.7	194.5	189.2	187.9	182.6	182.6	181.3	179.9	180.4
60°	210.9	192.8	179.0	171.1	170.2	168.0	164.4	164.0	160.9	162.2	162.6
62.5°	181.3	166.6	157.3	152.4	149.3	148.5	146.2	145.8	144.5	144.9	144.0
65°	157.8	145.8	136.5	132.5	131.2	130.7	129.0	127.6	126.7	127.6	126.7
67.5°	134.3	126.3	119.2	115.2	113.4	113.0	111.7	110.8	111.2	109.9	110.8
70°	112.1	104.1	99.7	97.5	96.6	95.3	95.3	95.3	95.3	94.4	93.9
72.5°	94.4	86.4	83.3	82.0	81.1	80.7	79.3	79.8	79.3	78.9	80.7
75°	74.9	70.0	66.9	65.6	66.5	65.1	63.8	64.7	63.4	63.8	65.6
77.5°	56.7	54.5	52.7	51.8	51.0	50.1	50.1	49.2	49.2	49.2	49.2
80°	41.2	40.8	37.7	37.2	37.2	36.3	36.3	36.3	36.3	35.9	36.3
82.5°	27.5	27.0	26.1	25.7	24.8	25.3	25.3	24.4	24.4	23.9	24.4
85°	16.0	16.0	15.1	14.6	14.2	14.6	13.7	13.3	13.7	13.3	13.7
87.5°	7.5	6.6	7.1	6.6	5.8	6.2	5.3	5.8	5.3	4.9	5.8
90°	29.1	30.7	32.4	34.1	34.9	35.2	35.7	36.3	36.8	37.4	36.8
92.5°	27.9	29.5	31.2	32.9	33.7	33.7	33.7	33.7	33.7	33.7	33.7
95°	29.1	30.7	32.4	34.1	34.9	35.0	35.3	35.6	35.9	36.2	35.9
97.5°	28.8	30.2	31.6	33.0	33.7	33.8	34.1	34.4	34.6	34.9	34.6
100°	50.2	45.5	40.8	36.1	33.7	33.8	34.1	34.4	34.6	34.9	34.6
102.5°	254.5	192.1	129.8	67.4	36.2	36.2	36.2	36.2	36.2	36.2	36.2
105°	391.8	394.3	396.8	399.3	400.5	395.5	385.5	375.6	365.6	355.6	365.6
107.5°	470.5	471.9	473.2	474.6	475.3	475.9	477.0	478.1	479.2	480.3	479.2
110°	550.8	551.3	551.9	552.4	552.7	553.1	553.9	554.8	555.6	556.4	555.6

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	628.5	628.2	627.9	627.6	627.5	628.1	629.2	630.3	631.4	632.5	631.4
115°	704.2	704.8	705.3	705.8	706.1	706.1	706.1	706.1	706.1	706.1	706.1
117.5°	783.2	783.0	782.7	782.4	782.3	782.3	782.3	782.3	782.3	782.3	782.3
120°	854.0	854.5	855.1	855.6	855.9	855.6	855.1	854.5	854.0	853.4	854.0
122.5°	924.8	925.0	925.3	925.6	925.7	925.4	924.9	924.3	923.8	923.2	923.8
125°	988.9	989.8	990.6	991.5	991.9	992.0	992.3	992.6	992.8	993.1	992.8
127.5°	1056.4	1056.2	1055.9	1055.6	1055.5	1055.4	1055.1	1054.8	1054.5	1054.2	1054.5
130°	1115.7	1115.9	1116.2	1116.5	1116.6	1116.6	1116.6	1116.6	1116.6	1116.6	1116.6
132.5°	1174.3	1174.6	1174.9	1175.2	1175.3	1175.2	1174.9	1174.6	1174.3	1174.0	1174.3
135°	1227.0	1227.5	1228.1	1228.6	1228.9	1229.2	1229.7	1230.3	1230.8	1231.4	1230.8
137.5°	1279.4	1279.9	1280.5	1281.0	1281.3	1281.2	1280.9	1280.6	1280.3	1280.0	1280.3
140°	1327.0	1327.9	1328.7	1329.6	1330.0	1330.1	1330.4	1330.7	1330.9	1331.2	1330.9
142.5°	1371.7	1372.2	1372.8	1373.3	1373.6	1373.6	1373.6	1373.6	1373.6	1373.6	1373.6
145°	1413.8	1414.1	1414.4	1414.7	1414.8	1415.1	1415.6	1416.2	1416.7	1417.3	1416.7
147.5°	1451.3	1451.5	1451.8	1452.1	1452.2	1452.3	1452.6	1452.9	1453.2	1453.5	1453.2
150°	1487.2	1487.2	1487.2	1487.2	1487.2	1487.3	1487.6	1487.9	1488.1	1488.4	1488.1
152.5°	1517.7	1518.2	1518.8	1519.3	1519.6	1519.5	1519.2	1518.9	1518.6	1518.3	1518.6
155°	1544.4	1545.5	1546.6	1547.7	1548.3	1547.9	1547.0	1546.2	1545.3	1544.5	1545.3
157.5°	1568.4	1569.8	1571.1	1572.5	1573.2	1572.5	1571.1	1569.8	1568.4	1567.0	1568.4
160°	1591.1	1592.8	1594.4	1596.1	1596.9	1596.1	1594.4	1592.8	1591.1	1589.5	1591.1
162.5°	1609.9	1611.5	1613.2	1614.9	1615.7	1614.7	1612.8	1610.8	1608.9	1606.9	1608.9
165°	1626.6	1628.8	1631.1	1633.3	1634.4	1633.1	1630.6	1628.1	1625.6	1623.1	1625.6
167.5°	1639.4	1641.9	1644.4	1646.9	1648.1	1646.7	1643.9	1641.2	1638.4	1635.6	1638.4
170°	1651.5	1653.7	1656.0	1658.2	1659.3	1657.9	1655.1	1652.4	1649.6	1646.8	1649.6
172.5°	1659.0	1661.2	1663.5	1665.7	1666.8	1665.3	1662.2	1659.2	1656.1	1653.1	1656.1
175°	1664.3	1666.8	1669.3	1671.8	1673.0	1671.3	1668.0	1664.7	1661.4	1658.1	1661.4
177.5°	1667.8	1670.0	1672.2	1674.4	1675.5	1673.8	1670.5	1667.2	1663.9	1660.6	1663.9
180°	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	577.0	575.7	573.9	573.9	571.7	571.7	568.1	561.9	556.6	554.8	555.7
5°	626.2	626.6	624.0	621.8	617.8	614.7	608.9	597.8	594.3	587.2	582.3
7.5°	682.5	680.7	675.8	672.3	671.4	664.3	651.9	638.6	628.0	620.9	610.7
10°	745.8	738.7	731.7	729.4	724.1	712.2	698.0	683.4	668.7	653.2	635.9
12.5°	799.0	785.3	784.8	779.5	769.3	762.7	745.8	725.0	699.7	682.5	663.0
15°	856.2	843.3	832.7	822.9	818.1	798.6	784.4	758.2	728.1	709.5	696.2
17.5°	897.0	891.2	873.0	868.6	861.9	839.3	816.7	791.0	764.9	738.7	702.9
20°	929.7	926.2	914.2	908.0	897.4	879.7	852.2	822.5	792.4	755.1	721.5
22.5°	943.9	939.5	929.7	924.4	917.8	902.7	879.2	845.5	806.1	772.9	737.0
25°	916.0	924.0	921.3	919.1	916.5	907.6	889.9	860.2	821.6	783.9	739.2
27.5°	853.1	866.8	880.1	881.9	886.3	889.9	882.8	861.5	829.2	789.3	740.1
30°	768.4	774.6	801.7	809.7	815.9	838.5	851.8	846.4	821.6	785.7	740.5
32.5°	659.9	676.3	703.7	722.8	739.6	764.9	799.5	813.2	804.3	775.1	730.3
35°	557.1	576.6	608.5	632.8	649.7	685.6	726.3	756.0	767.1	752.5	712.6
37.5°	472.9	496.3	524.7	534.0	553.5	597.8	654.1	695.3	722.3	723.7	692.7
40°	409.5	421.4	444.0	458.2	477.3	514.5	569.5	624.0	664.7	678.5	662.1
42.5°	355.9	365.2	382.0	399.3	416.6	444.9	495.5	546.4	601.4	628.8	628.4
45°	313.3	323.1	334.6	348.8	360.7	391.3	431.2	483.5	530.9	573.4	584.1
47.5°	276.1	284.5	298.7	304.9	312.9	341.7	376.2	425.0	474.2	522.9	535.3
50°	248.6	255.7	265.5	269.4	278.3	299.6	327.9	367.4	421.9	466.6	489.7
52.5°	223.8	229.1	236.6	239.7	246.0	261.9	287.6	318.6	363.8	409.9	442.3
55°	202.5	206.1	211.4	214.9	219.4	233.5	252.6	280.5	319.5	359.4	390.9
57.5°	182.6	185.2	190.6	192.3	195.9	207.0	220.3	243.7	279.6	315.1	345.7
60°	164.0	165.7	168.8	172.8	175.5	183.0	195.4	214.9	243.7	276.1	300.9
62.5°	146.2	148.9	149.8	151.6	153.8	160.9	170.6	184.8	210.1	236.6	262.8
65°	128.1	130.3	132.1	132.5	134.7	140.0	148.9	161.3	177.7	200.8	225.1
67.5°	111.2	112.6	113.4	115.2	117.4	120.1	127.2	136.5	151.6	170.2	189.7
70°	95.7	95.7	97.1	97.5	100.2	103.3	106.4	115.2	128.5	143.6	156.9
72.5°	78.9	81.1	80.7	82.9	82.4	84.6	88.6	94.4	104.1	116.1	129.0
75°	64.3	65.6	65.6	65.6	66.5	68.2	70.5	75.8	83.3	93.1	100.6
77.5°	50.1	51.0	51.0	51.0	51.4	53.2	55.4	58.9	64.3	70.0	74.5
80°	35.9	36.8	36.8	37.7	37.7	38.1	40.3	42.1	44.8	49.2	53.6
82.5°	24.4	24.8	25.7	25.7	25.3	26.1	26.6	28.4	31.0	31.9	35.0
85°	13.3	13.7	14.2	14.2	14.6	15.5	15.1	16.8	16.8	18.6	19.5
87.5°	5.3	6.2	6.2	5.8	6.2	6.2	6.2	7.1	7.5	8.0	7.5
90°	36.3	35.7	35.2	34.9	34.1	32.4	30.7	29.1	27.4	25.2	23.0
92.5°	33.7	33.7	33.7	33.7	32.9	31.2	29.5	27.9	26.2	24.0	21.8
95°	35.6	35.3	35.0	34.9	34.1	32.4	30.7	29.1	27.4	27.1	26.9
97.5°	34.4	34.1	33.8	33.7	33.0	31.6	30.2	28.8	27.4	56.5	85.6
100°	34.4	34.1	33.8	33.7	36.1	40.8	45.5	50.2	54.9	93.2	131.4
102.5°	36.2	36.2	36.2	36.2	67.4	129.8	192.1	254.5	316.9	313.6	310.2
105°	375.6	385.5	395.5	400.5	399.3	396.8	394.3	391.8	389.3	387.9	386.5
107.5°	478.1	477.0	475.9	475.3	474.6	473.2	471.9	470.5	469.1	467.2	465.2
110°	554.8	553.9	553.1	552.7	552.4	551.9	551.3	550.8	550.2	548.5	546.9

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	630.3	629.2	628.1	627.5	627.6	627.9	628.2	628.5	628.8	628.2	627.7
115°	706.1	706.1	706.1	706.1	705.8	705.3	704.8	704.2	703.7	704.0	704.2
117.5°	782.3	782.3	782.3	782.3	782.4	782.7	783.0	783.2	783.5	782.7	781.9
120°	854.5	855.1	855.6	855.9	855.6	855.1	854.5	854.0	853.4	853.7	853.9
122.5°	924.3	924.9	925.4	925.7	925.6	925.3	925.0	924.8	924.5	923.9	923.4
125°	992.6	992.3	992.0	991.9	991.5	990.6	989.8	988.9	988.1	988.7	989.2
127.5°	1054.8	1055.1	1055.4	1055.5	1055.6	1055.9	1056.2	1056.4	1056.7	1055.3	1053.9
130°	1116.6	1116.6	1116.6	1116.6	1116.5	1116.2	1115.9	1115.7	1115.4	1114.6	1113.7
132.5°	1174.6	1174.9	1175.2	1175.3	1175.2	1174.9	1174.6	1174.3	1174.0	1172.9	1171.8
135°	1230.3	1229.7	1229.2	1228.9	1228.6	1228.1	1227.5	1227.0	1226.4	1225.3	1224.2
137.5°	1280.6	1280.9	1281.2	1281.3	1281.0	1280.5	1279.9	1279.4	1278.8	1277.4	1276.0
140°	1330.7	1330.4	1330.1	1330.0	1329.6	1328.7	1327.9	1327.0	1326.2	1325.6	1325.1
142.5°	1373.6	1373.6	1373.6	1373.6	1373.3	1372.8	1372.2	1371.7	1371.1	1370.8	1370.6
145°	1416.2	1415.6	1415.1	1414.8	1414.7	1414.4	1414.1	1413.8	1413.5	1413.5	1413.5
147.5°	1452.9	1452.6	1452.3	1452.2	1452.1	1451.8	1451.5	1451.3	1451.0	1451.3	1451.5
150°	1487.9	1487.6	1487.3	1487.2	1487.2	1487.2	1487.2	1487.2	1487.2	1487.5	1487.7
152.5°	1518.9	1519.2	1519.5	1519.6	1519.3	1518.8	1518.2	1517.7	1517.1	1517.7	1518.2
155°	1546.2	1547.0	1547.9	1548.3	1547.7	1546.6	1545.5	1544.4	1543.3	1544.1	1544.9
157.5°	1569.8	1571.1	1572.5	1573.2	1572.5	1571.1	1569.8	1568.4	1567.0	1568.1	1569.2
160°	1592.8	1594.4	1596.1	1596.9	1596.1	1594.4	1592.8	1591.1	1589.5	1589.8	1590.0
162.5°	1610.8	1612.8	1614.7	1615.7	1614.9	1613.2	1611.5	1609.9	1608.2	1608.5	1608.7
165°	1628.1	1630.6	1633.1	1634.4	1633.3	1631.1	1628.8	1626.6	1624.4	1624.4	1624.4
167.5°	1641.2	1643.9	1646.7	1648.1	1646.9	1644.4	1641.9	1639.4	1636.9	1637.2	1637.4
170°	1652.4	1655.1	1657.9	1659.3	1658.2	1656.0	1653.7	1651.5	1649.3	1649.0	1648.8
172.5°	1659.2	1662.2	1665.3	1666.8	1665.7	1663.5	1661.2	1659.0	1656.8	1656.5	1656.3
175°	1664.7	1668.0	1671.3	1673.0	1671.8	1669.3	1666.8	1664.3	1661.8	1661.5	1661.3
177.5°	1667.2	1670.5	1673.8	1675.5	1674.4	1672.2	1670.0	1667.8	1665.6	1665.0	1664.5
180°	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	551.7	550.0	548.6	548.6	544.6	540.7	538.4	537.6	536.7	533.1	528.2
5°	574.3	568.6	564.6	560.6	553.9	546.9	539.8	535.8	530.0	522.0	516.3
7.5°	599.6	585.9	581.4	576.6	563.3	551.3	541.5	533.1	523.8	513.6	503.4
10°	620.9	606.2	596.5	588.1	570.8	554.8	540.2	527.8	515.8	502.5	490.1
12.5°	641.3	620.4	610.2	597.8	579.7	556.6	537.6	522.0	504.3	490.6	475.5
15°	669.6	634.6	617.8	609.8	585.4	558.4	535.3	512.3	497.7	476.8	463.5
17.5°	674.0	645.7	634.6	614.2	585.0	554.4	527.8	504.8	482.6	464.0	446.7
20°	689.6	652.3	634.6	621.8	583.2	552.2	522.9	493.2	472.0	452.0	432.5
22.5°	699.3	657.2	638.6	618.2	581.4	544.2	509.6	483.9	457.8	437.4	421.9
25°	696.6	654.5	633.7	614.7	569.9	532.7	501.7	468.9	444.5	422.3	401.9
27.5°	695.3	647.9	625.7	604.5	562.4	523.4	484.4	457.8	430.8	405.0	390.0
30°	691.8	639.5	613.8	590.7	546.9	506.1	472.9	441.8	414.8	391.3	371.4
32.5°	679.8	625.3	600.5	575.7	530.0	489.2	455.6	426.8	399.7	375.4	356.3
35°	663.9	608.5	581.4	555.3	509.6	468.4	437.4	407.3	382.0	358.5	340.3
37.5°	647.9	589.0	563.7	533.6	491.5	448.5	416.6	389.5	366.0	341.7	321.7
40°	624.9	565.9	538.0	512.3	463.1	422.8	393.5	369.2	346.1	323.1	306.2
42.5°	593.4	540.7	511.8	483.5	437.4	397.5	369.2	347.4	325.7	306.7	288.1
45°	561.5	510.1	484.4	459.1	409.0	371.4	345.2	325.3	307.1	286.3	271.2
47.5°	522.9	479.5	453.8	429.0	381.6	343.9	320.0	301.3	284.5	267.2	253.0
50°	483.5	445.8	422.3	396.6	351.4	317.3	293.8	278.3	264.6	248.2	236.6
52.5°	440.9	408.1	388.2	363.4	323.5	292.0	268.1	252.6	241.1	229.1	218.9
55°	395.7	371.8	350.5	330.6	292.9	264.6	243.3	229.6	221.6	210.5	201.6
57.5°	355.0	331.9	319.1	296.5	263.7	235.8	218.9	207.4	198.1	191.4	184.4
60°	312.4	293.8	279.6	263.2	234.4	210.9	193.2	186.6	176.8	171.9	168.8
62.5°	271.7	258.4	245.1	232.7	207.0	184.8	171.5	163.1	157.3	152.4	149.8
65°	233.1	220.7	211.4	200.3	179.0	161.3	148.9	142.3	136.5	135.2	132.1
67.5°	195.4	190.1	179.9	171.1	152.9	139.2	129.8	121.4	118.3	117.0	114.3
70°	163.5	157.3	149.3	141.8	128.1	116.1	107.7	104.6	100.2	99.7	96.6
72.5°	134.7	127.2	121.4	115.7	105.5	94.8	90.4	86.0	83.8	82.0	80.7
75°	106.8	101.5	97.5	92.6	83.8	76.7	70.5	68.7	67.4	66.9	66.0
77.5°	79.8	76.2	74.5	69.6	63.4	57.2	54.5	51.8	51.8	51.0	51.4
80°	56.7	54.5	52.3	49.6	44.3	41.7	39.4	37.7	36.8	36.3	36.8
82.5°	35.9	34.6	34.1	32.4	28.8	27.5	25.7	24.4	24.4	24.4	24.4
85°	19.9	19.9	19.9	17.3	16.0	14.6	13.7	13.3	13.3	13.3	13.7
87.5°	8.4	8.4	7.1	7.1	6.6	5.8	5.3	5.3	5.8	5.8	6.2
90°	20.8	18.6	17.5	16.0	12.9	9.8	6.8	3.7	6.8	9.8	12.9
92.5°	19.5	17.3	16.2	16.5	17.0	17.6	18.1	18.7	18.1	17.6	17.0
95°	26.6	26.3	26.2	30.9	40.3	49.8	59.2	68.6	59.2	49.8	40.3
97.5°	114.7	143.8	158.4	155.4	149.3	143.2	137.1	131.0	137.1	143.2	149.3
100°	169.7	208.0	227.1	224.6	219.6	214.6	209.6	204.6	209.6	214.6	219.6
102.5°	306.9	303.6	301.9	300.2	296.9	293.6	290.3	287.0	290.3	293.6	296.9
105°	385.1	383.7	383.0	382.2	380.5	378.8	377.2	375.5	377.2	378.8	380.5
107.5°	463.3	461.4	460.4	460.0	459.1	458.3	457.4	456.6	457.4	458.3	459.1
110°	545.2	543.5	542.7	542.3	541.5	540.6	539.8	539.0	539.8	540.6	541.5

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	627.1	626.6	626.3	625.5	623.8	622.1	620.5	618.8	620.5	622.1	623.8
115°	704.5	704.8	704.9	704.5	703.7	702.8	702.0	701.2	702.0	702.8	703.7
117.5°	781.0	780.2	779.8	779.2	778.1	777.0	775.9	774.8	775.9	777.0	778.1
120°	854.2	854.5	854.6	854.0	852.9	851.8	850.7	849.6	850.7	851.8	852.9
122.5°	922.8	922.3	922.0	921.7	921.2	920.6	920.1	919.5	920.1	920.6	921.2
125°	989.8	990.3	990.6	990.0	988.9	987.8	986.7	985.6	986.7	987.8	988.9
127.5°	1052.6	1051.2	1050.5	1050.4	1050.1	1049.8	1049.5	1049.2	1049.5	1049.8	1050.1
130°	1112.9	1112.0	1111.6	1111.5	1111.2	1110.9	1110.7	1110.4	1110.7	1110.9	1111.2
132.5°	1170.7	1169.6	1169.0	1168.7	1168.2	1167.6	1167.1	1166.5	1167.1	1167.6	1168.2
135°	1223.1	1222.0	1221.4	1221.5	1221.8	1222.1	1222.4	1222.7	1222.4	1222.1	1221.8
137.5°	1274.7	1273.3	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6
140°	1324.5	1324.0	1323.7	1323.4	1322.9	1322.3	1321.8	1321.2	1321.8	1322.3	1322.9
142.5°	1370.3	1370.0	1369.9	1369.3	1368.2	1367.1	1366.0	1364.9	1366.0	1367.1	1368.2
145°	1413.5	1413.5	1413.5	1413.1	1412.3	1411.4	1410.6	1409.8	1410.6	1411.4	1412.3
147.5°	1451.8	1452.1	1452.2	1451.4	1449.7	1448.0	1446.4	1444.7	1446.4	1448.0	1449.7
150°	1488.0	1488.3	1488.4	1487.8	1486.7	1485.6	1484.5	1483.4	1484.5	1485.6	1486.7
152.5°	1518.8	1519.3	1519.6	1519.2	1518.3	1517.5	1516.6	1515.8	1516.6	1517.5	1518.3
155°	1545.8	1546.6	1547.0	1546.9	1546.6	1546.3	1546.1	1545.8	1546.1	1546.3	1546.6
157.5°	1570.3	1571.4	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0	1572.0
160°	1590.3	1590.6	1590.7	1591.1	1591.9	1592.8	1593.6	1594.4	1593.6	1592.8	1591.9
162.5°	1609.0	1609.3	1609.4	1610.0	1611.1	1612.2	1613.3	1614.4	1613.3	1612.2	1611.1
165°	1624.4	1624.4	1624.4	1625.1	1626.5	1627.8	1629.2	1630.6	1629.2	1627.8	1626.5
167.5°	1637.7	1638.0	1638.1	1638.8	1640.2	1641.6	1643.0	1644.4	1643.0	1641.6	1640.2
170°	1648.5	1648.2	1648.1	1648.9	1650.6	1652.3	1653.9	1655.6	1653.9	1652.3	1650.6
172.5°	1656.0	1655.7	1655.6	1656.4	1658.1	1659.8	1661.4	1663.1	1661.4	1659.8	1658.1
175°	1661.0	1660.7	1660.6	1661.4	1663.1	1664.8	1666.4	1668.1	1666.4	1664.8	1663.1
177.5°	1663.9	1663.4	1663.1	1664.1	1666.0	1667.9	1669.9	1671.8	1669.9	1667.9	1666.0
180°	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	526.9	525.1	526.0	521.6	517.6	511.8	507.0	506.1	505.2	507.9	506.1
5°	511.8	509.6	507.4	502.1	494.1	489.2	482.2	481.7	479.1	475.1	476.0
7.5°	495.5	494.1	491.0	482.6	475.5	467.1	461.3	456.5	454.2	450.7	449.4
10°	482.2	477.3	474.6	465.3	456.9	448.0	440.5	437.0	433.0	429.9	427.6
12.5°	464.0	462.7	455.1	447.6	440.5	430.3	424.5	414.4	409.0	411.7	410.8
15°	452.0	445.8	444.0	433.4	421.4	414.8	404.2	397.5	395.3	391.3	386.4
17.5°	436.1	432.1	425.9	416.1	402.4	393.1	385.5	379.3	376.7	371.4	367.4
20°	421.0	414.4	409.5	400.6	387.3	375.4	366.0	362.1	355.4	351.0	348.8
22.5°	407.3	402.4	395.3	382.0	370.5	359.0	347.9	342.1	335.9	333.3	329.7
25°	390.4	382.4	377.6	362.9	350.5	341.2	331.0	323.5	320.0	315.5	314.6
27.5°	374.0	366.5	360.7	347.9	332.8	320.8	314.6	309.3	303.1	303.1	300.9
30°	357.6	352.3	343.4	331.0	316.9	305.3	298.2	293.4	291.2	289.4	288.9
32.5°	341.2	334.1	328.8	312.0	301.3	290.7	285.4	281.4	278.7	278.3	278.7
35°	324.4	316.4	311.1	296.0	285.4	275.6	273.4	269.9	268.6	268.1	270.3
37.5°	306.7	300.5	293.8	281.4	269.4	263.7	259.2	257.9	257.5	260.1	261.0
40°	290.3	285.0	278.7	265.5	256.6	250.4	248.2	246.8	248.6	251.3	252.6
42.5°	274.8	267.2	262.4	250.4	242.4	238.9	236.2	236.2	238.0	241.1	243.3
45°	258.4	252.6	247.7	237.1	230.0	226.0	225.6	226.0	228.2	230.4	233.1
47.5°	242.4	236.6	231.3	222.5	216.3	214.0	213.6	214.0	217.6	220.7	223.8
50°	227.8	221.6	216.7	208.3	203.4	200.8	201.2	203.4	206.1	210.5	214.5
52.5°	210.5	206.1	201.6	194.1	189.7	187.9	189.2	191.0	195.9	199.0	203.9
55°	193.7	189.7	186.1	180.4	176.8	175.5	176.4	179.0	183.0	188.3	194.1
57.5°	178.2	173.7	170.2	166.2	162.2	162.6	163.1	166.6	171.5	176.4	183.0
60°	160.9	158.2	155.1	150.2	148.5	148.5	149.8	153.8	158.2	166.2	171.9
62.5°	145.4	141.8	139.6	136.5	133.8	134.3	137.4	140.9	146.2	152.9	160.4
65°	129.4	125.4	123.6	121.0	120.1	120.5	122.8	128.1	133.8	139.6	146.7
67.5°	111.7	110.3	108.6	105.9	106.8	107.2	109.5	113.9	120.1	125.9	133.8
70°	96.6	93.9	93.5	91.3	91.3	92.6	97.1	100.2	105.9	112.1	120.5
72.5°	80.7	78.4	78.4	76.7	78.0	79.3	81.5	86.0	91.3	97.5	104.6
75°	64.3	63.4	64.3	63.4	63.4	65.6	68.2	71.8	77.6	84.2	90.0
77.5°	49.6	49.6	49.2	50.5	50.5	51.8	55.4	58.9	63.4	68.7	74.9
80°	36.3	36.3	36.3	37.7	39.0	39.0	41.2	45.6	49.6	53.2	58.9
82.5°	24.8	24.8	24.8	25.7	27.5	27.5	30.1	32.8	37.2	40.3	43.0
85°	15.1	15.1	14.6	15.5	16.0	17.3	19.5	21.3	23.5	26.1	28.8
87.5°	6.6	6.6	7.1	7.5	8.0	8.9	9.7	10.6	12.9	13.7	15.1
90°	16.0	17.5	18.6	20.8	23.0	25.2	27.4	29.1	30.7	32.4	34.1
92.5°	16.5	16.2	17.3	19.5	21.8	24.0	26.2	27.9	29.5	31.2	32.9
95°	30.9	26.2	26.3	26.6	26.9	27.1	27.4	29.1	30.7	32.4	34.1
97.5°	155.4	158.4	143.8	114.7	85.6	56.5	27.4	28.8	30.2	31.6	33.0
100°	224.6	227.1	208.0	169.7	131.4	93.2	54.9	50.2	45.5	40.8	36.1
102.5°	300.2	301.9	303.6	306.9	310.2	313.6	316.9	254.5	192.1	129.8	67.4
105°	382.2	383.0	383.7	385.1	386.5	387.9	389.3	391.8	394.3	396.8	399.3
107.5°	460.0	460.4	461.4	463.3	465.2	467.2	469.1	470.5	471.9	473.2	474.6
110°	542.3	542.7	543.5	545.2	546.9	548.5	550.2	550.8	551.3	551.9	552.4

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	625.5	626.3	626.6	627.1	627.7	628.2	628.8	628.5	628.2	627.9	627.6
115°	704.5	704.9	704.8	704.5	704.2	704.0	703.7	704.2	704.8	705.3	705.8
117.5°	779.2	779.8	780.2	781.0	781.9	782.7	783.5	783.2	783.0	782.7	782.4
120°	854.0	854.6	854.5	854.2	853.9	853.7	853.4	854.0	854.5	855.1	855.6
122.5°	921.7	922.0	922.3	922.8	923.4	923.9	924.5	924.8	925.0	925.3	925.6
125°	990.0	990.6	990.3	989.8	989.2	988.7	988.1	988.9	989.8	990.6	991.5
127.5°	1050.4	1050.5	1051.2	1052.6	1053.9	1055.3	1056.7	1056.4	1056.2	1055.9	1055.6
130°	1111.5	1111.6	1112.0	1112.9	1113.7	1114.6	1115.4	1115.7	1115.9	1116.2	1116.5
132.5°	1168.7	1169.0	1169.6	1170.7	1171.8	1172.9	1174.0	1174.3	1174.6	1174.9	1175.2
135°	1221.5	1221.4	1222.0	1223.1	1224.2	1225.3	1226.4	1227.0	1227.5	1228.1	1228.6
137.5°	1272.6	1272.6	1273.3	1274.7	1276.0	1277.4	1278.8	1279.4	1279.9	1280.5	1281.0
140°	1323.4	1323.7	1324.0	1324.5	1325.1	1325.6	1326.2	1327.0	1327.9	1328.7	1329.6
142.5°	1369.3	1369.9	1370.0	1370.3	1370.6	1370.8	1371.1	1371.7	1372.2	1372.8	1373.3
145°	1413.1	1413.5	1413.5	1413.5	1413.5	1413.5	1413.5	1413.8	1414.1	1414.4	1414.7
147.5°	1451.4	1452.2	1452.1	1451.8	1451.5	1451.3	1451.0	1451.3	1451.5	1451.8	1452.1
150°	1487.8	1488.4	1488.3	1488.0	1487.7	1487.5	1487.2	1487.2	1487.2	1487.2	1487.2
152.5°	1519.2	1519.6	1519.3	1518.8	1518.2	1517.7	1517.1	1517.7	1518.2	1518.8	1519.3
155°	1546.9	1547.0	1546.6	1545.8	1544.9	1544.1	1543.3	1544.4	1545.5	1546.6	1547.7
157.5°	1572.0	1572.0	1571.4	1570.3	1569.2	1568.1	1567.0	1568.4	1569.8	1571.1	1572.5
160°	1591.1	1590.7	1590.6	1590.3	1590.0	1589.8	1589.5	1591.1	1592.8	1594.4	1596.1
162.5°	1610.0	1609.4	1609.3	1609.0	1608.7	1608.5	1608.2	1609.9	1611.5	1613.2	1614.9
165°	1625.1	1624.4	1624.4	1624.4	1624.4	1624.4	1624.4	1626.6	1628.8	1631.1	1633.3
167.5°	1638.8	1638.1	1638.0	1637.7	1637.4	1637.2	1636.9	1639.4	1641.9	1644.4	1646.9
170°	1648.9	1648.1	1648.2	1648.5	1648.8	1649.0	1649.3	1651.5	1653.7	1656.0	1658.2
172.5°	1656.4	1655.6	1655.7	1656.0	1656.3	1656.5	1656.8	1659.0	1661.2	1663.5	1665.7
175°	1661.4	1660.6	1660.7	1661.0	1661.3	1661.5	1661.8	1664.3	1666.8	1669.3	1671.8
177.5°	1664.1	1663.1	1663.4	1663.9	1664.5	1665.0	1665.6	1667.8	1670.0	1672.2	1674.4
180°	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	504.8	504.3	502.1	503.0	500.3	501.2	502.5	503.0	504.8	503.4	503.0
5°	473.7	472.9	471.5	470.2	469.7	471.5	468.4	469.3	470.2	471.5	473.3
7.5°	448.5	448.0	446.7	444.5	443.6	442.7	443.2	446.3	445.8	445.4	448.5
10°	425.4	425.9	423.2	422.8	420.1	419.7	420.1	421.0	422.3	424.1	424.5
12.5°	401.5	407.3	402.4	400.6	396.6	398.8	399.7	395.7	398.0	399.3	405.9
15°	386.4	383.8	380.7	380.7	378.9	378.0	375.8	378.9	380.7	383.3	382.4
17.5°	365.6	361.2	359.4	357.6	358.1	359.8	355.0	362.1	362.1	363.4	361.2
20°	347.4	343.9	341.7	340.8	339.5	338.6	338.1	339.9	342.6	343.4	345.7
22.5°	328.4	328.4	324.8	323.5	322.6	321.3	323.5	322.2	323.9	325.7	329.3
25°	312.4	312.4	311.1	309.3	308.0	307.1	308.4	308.0	309.3	311.5	312.4
27.5°	299.6	298.2	297.8	297.4	296.9	297.4	296.9	298.2	299.6	300.0	299.1
30°	288.5	287.2	287.6	287.6	288.1	287.6	287.2	288.5	288.9	288.1	288.5
32.5°	278.3	278.3	279.2	279.6	279.6	280.1	280.5	279.6	280.1	278.7	279.2
35°	269.9	270.8	271.7	272.1	272.5	272.1	273.0	272.5	271.7	270.8	270.3
37.5°	261.5	262.4	264.1	264.6	265.9	266.3	265.5	265.5	265.0	263.2	262.4
40°	252.6	253.5	255.7	257.0	257.9	259.2	258.4	258.4	256.6	254.8	253.5
42.5°	244.2	246.0	248.2	249.5	251.3	251.3	251.3	250.4	248.2	246.4	245.1
45°	235.8	236.2	239.3	241.5	243.3	243.3	243.3	242.0	240.6	237.1	235.3
47.5°	226.5	227.8	231.3	233.5	235.3	235.8	235.8	234.4	231.8	228.7	226.5
50°	216.3	218.5	222.5	225.6	227.8	228.7	227.3	226.5	223.4	219.8	217.1
52.5°	206.5	209.2	214.0	216.7	219.8	220.3	219.8	218.5	214.9	210.1	207.8
55°	196.8	199.0	204.3	208.7	211.4	212.3	211.4	209.2	204.7	199.9	197.6
57.5°	186.1	189.2	195.0	199.4	202.5	203.0	202.1	199.9	196.3	190.1	187.0
60°	175.0	179.0	184.8	189.2	193.2	193.7	192.8	189.7	185.2	179.0	176.4
62.5°	164.0	167.1	173.7	178.6	181.7	183.9	182.1	179.0	174.6	168.4	164.4
65°	151.1	155.5	161.3	165.7	169.3	169.7	168.8	166.2	161.3	154.7	151.6
67.5°	138.7	141.8	147.6	153.3	154.7	156.0	154.7	152.0	148.0	142.3	137.8
70°	123.6	126.3	133.4	137.4	139.2	140.5	139.6	136.9	133.4	128.1	124.5
72.5°	108.6	110.8	117.4	120.5	124.1	123.6	123.2	121.4	116.6	113.0	110.8
75°	92.6	95.3	99.7	103.7	105.0	105.0	105.0	103.7	100.6	94.8	92.6
77.5°	78.0	79.3	82.9	85.1	86.4	86.9	86.4	84.2	82.4	78.4	77.1
80°	59.8	63.4	66.0	66.5	68.2	68.2	68.2	67.4	65.6	61.6	61.2
82.5°	45.2	46.1	48.7	50.1	51.0	50.5	50.5	48.7	48.3	46.1	45.2
85°	30.6	31.9	31.5	33.2	33.7	32.8	32.8	33.7	31.5	31.9	30.6
87.5°	16.8	16.8	17.7	17.3	19.1	19.1	18.2	18.6	17.7	17.3	16.8
90°	34.9	35.2	35.7	36.3	36.8	37.4	36.8	36.3	35.7	35.2	34.9
92.5°	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7
95°	34.9	35.0	35.3	35.6	35.9	36.2	35.9	35.6	35.3	35.0	34.9
97.5°	33.7	33.8	34.1	34.4	34.6	34.9	34.6	34.4	34.1	33.8	33.7
100°	33.7	33.8	34.1	34.4	34.6	34.9	34.6	34.4	34.1	33.8	33.7
102.5°	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2
105°	400.5	395.5	385.5	375.6	365.6	355.6	365.6	375.6	385.5	395.5	400.5
107.5°	475.3	475.9	477.0	478.1	479.2	480.3	479.2	478.1	477.0	475.9	475.3
110°	552.7	553.1	553.9	554.8	555.6	556.4	555.6	554.8	553.9	553.1	552.7

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	627.5	628.1	629.2	630.3	631.4	632.5	631.4	630.3	629.2	628.1	627.5
115°	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1
117.5°	782.3	782.3	782.3	782.3	782.3	782.3	782.3	782.3	782.3	782.3	782.3
120°	855.9	855.6	855.1	854.5	854.0	853.4	854.0	854.5	855.1	855.6	855.9
122.5°	925.7	925.4	924.9	924.3	923.8	923.2	923.8	924.3	924.9	925.4	925.7
125°	991.9	992.0	992.3	992.6	992.8	993.1	992.8	992.6	992.3	992.0	991.9
127.5°	1055.5	1055.4	1055.1	1054.8	1054.5	1054.2	1054.5	1054.8	1055.1	1055.4	1055.5
130°	1116.6	1116.6	1116.6	1116.6	1116.6	1116.6	1116.6	1116.6	1116.6	1116.6	1116.6
132.5°	1175.3	1175.2	1174.9	1174.6	1174.3	1174.0	1174.3	1174.6	1174.9	1175.2	1175.3
135°	1228.9	1229.2	1229.7	1230.3	1230.8	1231.4	1230.8	1230.3	1229.7	1229.2	1228.9
137.5°	1281.3	1281.2	1280.9	1280.6	1280.3	1280.0	1280.3	1280.6	1280.9	1281.2	1281.3
140°	1330.0	1330.1	1330.4	1330.7	1330.9	1331.2	1330.9	1330.7	1330.4	1330.1	1330.0
142.5°	1373.6	1373.6	1373.6	1373.6	1373.6	1373.6	1373.6	1373.6	1373.6	1373.6	1373.6
145°	1414.8	1415.1	1415.6	1416.2	1416.7	1417.3	1416.7	1416.2	1415.6	1415.1	1414.8
147.5°	1452.2	1452.3	1452.6	1452.9	1453.2	1453.5	1453.2	1452.9	1452.6	1452.3	1452.2
150°	1487.2	1487.3	1487.6	1487.9	1488.1	1488.4	1488.1	1487.9	1487.6	1487.3	1487.2
152.5°	1519.6	1519.5	1519.2	1518.9	1518.6	1518.3	1518.6	1518.9	1519.2	1519.5	1519.6
155°	1548.3	1547.9	1547.0	1546.2	1545.3	1544.5	1545.3	1546.2	1547.0	1547.9	1548.3
157.5°	1573.2	1572.5	1571.1	1569.8	1568.4	1567.0	1568.4	1569.8	1571.1	1572.5	1573.2
160°	1596.9	1596.1	1594.4	1592.8	1591.1	1589.5	1591.1	1592.8	1594.4	1596.1	1596.9
162.5°	1615.7	1614.7	1612.8	1610.8	1608.9	1606.9	1608.9	1610.8	1612.8	1614.7	1615.7
165°	1634.4	1633.1	1630.6	1628.1	1625.6	1623.1	1625.6	1628.1	1630.6	1633.1	1634.4
167.5°	1648.1	1646.7	1643.9	1641.2	1638.4	1635.6	1638.4	1641.2	1643.9	1646.7	1648.1
170°	1659.3	1657.9	1655.1	1652.4	1649.6	1646.8	1649.6	1652.4	1655.1	1657.9	1659.3
172.5°	1666.8	1665.3	1662.2	1659.2	1656.1	1653.1	1656.1	1659.2	1662.2	1665.3	1666.8
175°	1673.0	1671.3	1668.0	1664.7	1661.4	1658.1	1661.4	1664.7	1668.0	1671.3	1673.0
177.5°	1675.5	1673.8	1670.5	1667.2	1663.9	1660.6	1663.9	1667.2	1670.5	1673.8	1675.5
180°	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	503.0	505.6	503.0	504.8	505.6	507.9	508.7	512.7	514.1	517.2	517.2
5°	472.9	474.2	474.6	476.4	478.2	482.6	485.7	491.5	498.1	499.0	503.0
7.5°	448.5	450.7	454.2	452.9	456.0	462.7	466.6	473.7	480.4	483.9	488.8
10°	426.8	429.4	430.8	432.1	437.8	443.6	449.8	454.7	463.5	468.9	472.9
12.5°	409.0	406.8	409.5	414.4	421.0	424.5	433.0	440.5	447.1	452.9	456.5
15°	386.0	387.8	390.4	398.8	400.6	409.5	412.6	421.0	433.4	438.7	443.2
17.5°	363.8	369.6	374.9	378.0	383.3	390.4	399.3	408.6	416.6	422.8	428.1
20°	346.1	351.9	355.0	357.2	362.5	372.3	380.7	392.2	402.4	407.3	414.4
22.5°	331.9	331.9	336.4	343.0	346.1	355.4	362.5	374.9	386.0	392.2	398.8
25°	314.2	316.9	320.4	326.2	330.6	338.1	348.3	359.0	370.9	376.2	384.7
27.5°	299.6	302.7	307.6	308.9	313.3	320.0	330.6	342.1	354.5	360.3	367.4
30°	288.5	290.3	292.0	294.7	298.7	304.5	313.3	323.5	338.6	343.0	351.9
32.5°	278.7	279.6	280.5	282.7	285.0	290.7	297.8	308.9	321.3	327.9	335.9
35°	269.9	269.0	269.4	270.8	273.0	275.2	282.7	292.0	303.6	311.5	317.7
37.5°	261.5	259.7	259.2	259.2	260.1	262.8	268.6	276.5	288.9	295.6	301.8
40°	252.2	250.4	249.5	249.1	248.6	250.4	254.8	262.8	272.5	278.7	285.8
42.5°	243.3	241.5	239.3	238.9	238.0	238.9	242.0	249.5	257.9	264.1	269.9
45°	234.4	231.3	228.7	226.9	227.3	226.0	228.2	234.0	243.7	247.7	253.5
47.5°	224.7	221.1	217.6	215.8	214.0	214.9	215.8	220.7	229.1	233.1	238.9
50°	215.4	210.5	206.5	204.3	203.0	202.1	203.0	207.8	214.0	217.6	222.5
52.5°	204.7	199.9	195.9	192.3	190.6	189.2	189.7	194.1	199.9	203.4	208.3
55°	195.0	188.8	183.5	179.0	177.7	177.3	176.8	179.9	184.8	188.3	192.3
57.5°	183.9	177.7	171.9	166.6	164.0	163.5	163.5	164.4	170.6	173.3	175.5
60°	172.8	166.2	160.0	155.1	151.1	149.8	149.3	151.1	154.2	156.9	160.0
62.5°	160.4	153.8	146.2	141.8	137.8	134.3	135.6	136.0	140.5	141.8	144.5
65°	148.5	140.9	134.7	127.6	123.2	121.0	120.1	121.0	124.5	125.0	126.7
67.5°	134.7	127.6	120.1	115.2	111.2	107.2	106.4	106.4	108.1	109.5	111.7
70°	121.4	114.3	105.9	100.6	96.6	93.1	91.7	91.3	92.6	93.5	95.7
72.5°	105.9	98.8	92.6	86.9	82.0	79.3	78.0	77.1	78.4	79.3	79.8
75°	89.5	83.8	77.6	71.8	68.7	66.0	64.3	62.9	63.8	63.8	63.8
77.5°	74.0	68.2	63.4	59.4	55.4	52.3	51.0	49.6	50.1	50.1	51.0
80°	57.6	53.6	49.6	46.1	42.5	39.9	39.0	37.7	36.8	36.3	36.3
82.5°	42.5	39.4	35.9	32.8	31.0	28.4	27.5	25.7	25.7	25.3	25.3
85°	28.4	26.6	23.0	20.8	19.5	18.2	17.3	16.4	15.1	15.1	14.6
87.5°	15.1	14.2	13.3	10.6	10.6	9.3	8.9	8.4	7.1	7.5	7.5
90°	34.1	32.4	30.7	29.1	27.4	25.2	23.0	20.8	18.6	17.5	16.0
92.5°	32.9	31.2	29.5	27.9	26.2	24.0	21.8	19.5	17.3	16.2	16.5
95°	34.1	32.4	30.7	29.1	27.4	27.1	26.9	26.6	26.3	26.2	30.9
97.5°	33.0	31.6	30.2	28.8	27.4	56.5	85.6	114.7	143.8	158.4	155.4
100°	36.1	40.8	45.5	50.2	54.9	93.2	131.4	169.7	208.0	227.1	224.6
102.5°	67.4	129.8	192.1	254.5	316.9	313.6	310.2	306.9	303.6	301.9	300.2
105°	399.3	396.8	394.3	391.8	389.3	387.9	386.5	385.1	383.7	383.0	382.2
107.5°	474.6	473.2	471.9	470.5	469.1	467.2	465.2	463.3	461.4	460.4	460.0
110°	552.4	551.9	551.3	550.8	550.2	548.5	546.9	545.2	543.5	542.7	542.3

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	627.6	627.9	628.2	628.5	628.8	628.2	627.7	627.1	626.6	626.3	625.5
115°	705.8	705.3	704.8	704.2	703.7	704.0	704.2	704.5	704.8	704.9	704.5
117.5°	782.4	782.7	783.0	783.2	783.5	782.7	781.9	781.0	780.2	779.8	779.2
120°	855.6	855.1	854.5	854.0	853.4	853.7	853.9	854.2	854.5	854.6	854.0
122.5°	925.6	925.3	925.0	924.8	924.5	923.9	923.4	922.8	922.3	922.0	921.7
125°	991.5	990.6	989.8	988.9	988.1	988.7	989.2	989.8	990.3	990.6	990.0
127.5°	1055.6	1055.9	1056.2	1056.4	1056.7	1055.3	1053.9	1052.6	1051.2	1050.5	1050.4
130°	1116.5	1116.2	1115.9	1115.7	1115.4	1114.6	1113.7	1112.9	1112.0	1111.6	1111.5
132.5°	1175.2	1174.9	1174.6	1174.3	1174.0	1172.9	1171.8	1170.7	1169.6	1169.0	1168.7
135°	1228.6	1228.1	1227.5	1227.0	1226.4	1225.3	1224.2	1223.1	1222.0	1221.4	1221.5
137.5°	1281.0	1280.5	1279.9	1279.4	1278.8	1277.4	1276.0	1274.7	1273.3	1272.6	1272.6
140°	1329.6	1328.7	1327.9	1327.0	1326.2	1325.6	1325.1	1324.5	1324.0	1323.7	1323.4
142.5°	1373.3	1372.8	1372.2	1371.7	1371.1	1370.8	1370.6	1370.3	1370.0	1369.9	1369.3
145°	1414.7	1414.4	1414.1	1413.8	1413.5	1413.5	1413.5	1413.5	1413.5	1413.5	1413.1
147.5°	1452.1	1451.8	1451.5	1451.3	1451.0	1451.3	1451.5	1451.8	1452.1	1452.2	1451.4
150°	1487.2	1487.2	1487.2	1487.2	1487.2	1487.5	1487.7	1488.0	1488.3	1488.4	1487.8
152.5°	1519.3	1518.8	1518.2	1517.7	1517.1	1517.7	1518.2	1518.8	1519.3	1519.6	1519.2
155°	1547.7	1546.6	1545.5	1544.4	1543.3	1544.1	1544.9	1545.8	1546.6	1547.0	1546.9
157.5°	1572.5	1571.1	1569.8	1568.4	1567.0	1568.1	1569.2	1570.3	1571.4	1572.0	1572.0
160°	1596.1	1594.4	1592.8	1591.1	1589.5	1589.8	1590.0	1590.3	1590.6	1590.7	1591.1
162.5°	1614.9	1613.2	1611.5	1609.9	1608.2	1608.5	1608.7	1609.0	1609.3	1609.4	1610.0
165°	1633.3	1631.1	1628.8	1626.6	1624.4	1624.4	1624.4	1624.4	1624.4	1624.4	1625.1
167.5°	1646.9	1644.4	1641.9	1639.4	1636.9	1637.2	1637.4	1637.7	1638.0	1638.1	1638.8
170°	1658.2	1656.0	1653.7	1651.5	1649.3	1649.0	1648.8	1648.5	1648.2	1648.1	1648.9
172.5°	1665.7	1663.5	1661.2	1659.0	1656.8	1656.5	1656.3	1656.0	1655.7	1655.6	1656.4
175°	1671.8	1669.3	1666.8	1664.3	1661.8	1661.5	1661.3	1661.0	1660.7	1660.6	1661.4
177.5°	1674.4	1672.2	1670.0	1667.8	1665.6	1665.0	1664.5	1663.9	1663.4	1663.1	1664.1
180°	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1	1668.1

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	534.9	534.9	534.9	534.9
2.5°	520.3	524.7	528.7	534.9
5°	508.7	515.0	523.4	532.7
7.5°	495.5	505.2	516.3	529.1
10°	483.0	494.1	508.3	523.8
12.5°	470.2	483.5	499.0	515.8
15°	455.6	468.9	486.1	508.7
17.5°	442.3	458.2	476.8	500.8
20°	426.8	441.8	462.2	489.7
22.5°	413.0	430.3	452.9	476.8
25°	398.0	413.0	435.6	464.4
27.5°	382.9	401.5	423.2	451.1
30°	368.3	383.8	407.3	436.5
32.5°	352.3	370.9	392.6	420.1
35°	335.0	352.8	373.1	402.8
37.5°	319.5	336.8	357.6	383.8
40°	302.2	320.4	339.5	365.6
42.5°	285.4	301.8	320.8	344.8
45°	269.0	283.2	300.5	321.3
47.5°	252.2	264.1	280.1	298.7
50°	234.0	246.8	258.8	274.3
52.5°	217.1	228.2	238.0	250.8
55°	200.8	208.3	216.3	226.0
57.5°	183.5	189.2	195.0	205.2
60°	166.2	171.5	174.6	181.3
62.5°	149.3	151.6	155.5	159.5
65°	130.7	133.8	136.0	140.9
67.5°	113.9	115.2	117.4	120.5
70°	96.2	99.3	100.2	102.4
72.5°	81.1	82.4	83.3	83.8
75°	64.3	65.6	66.5	69.1
77.5°	50.5	50.1	51.8	52.3
80°	37.2	35.9	36.3	38.1
82.5°	24.4	24.8	24.4	24.4
85°	15.1	14.6	13.7	14.2
87.5°	6.6	6.6	6.2	6.2
90°	12.9	9.8	6.8	3.7
92.5°	17.0	17.6	18.1	18.7
95°	40.3	49.8	59.2	68.6
97.5°	149.3	143.2	137.1	131.0
100°	219.6	214.6	209.6	204.6
102.5°	296.9	293.6	290.3	287.0
105°	380.5	378.8	377.2	375.5
107.5°	459.1	458.3	457.4	456.6
110°	541.5	540.6	539.8	539.0

TEST NUMBER: P1033437

CATALOG NUMBER: S124DIW-B350D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	623.8	622.1	620.5	618.8
115°	703.7	702.8	702.0	701.2
117.5°	778.1	777.0	775.9	774.8
120°	852.9	851.8	850.7	849.6
122.5°	921.2	920.6	920.1	919.5
125°	988.9	987.8	986.7	985.6
127.5°	1050.1	1049.8	1049.5	1049.2
130°	1111.2	1110.9	1110.7	1110.4
132.5°	1168.2	1167.6	1167.1	1166.5
135°	1221.8	1222.1	1222.4	1222.7
137.5°	1272.6	1272.6	1272.6	1272.6
140°	1322.9	1322.3	1321.8	1321.2
142.5°	1368.2	1367.1	1366.0	1364.9
145°	1412.3	1411.4	1410.6	1409.8
147.5°	1449.7	1448.0	1446.4	1444.7
150°	1486.7	1485.6	1484.5	1483.4
152.5°	1518.3	1517.5	1516.6	1515.8
155°	1546.6	1546.3	1546.1	1545.8
157.5°	1572.0	1572.0	1572.0	1572.0
160°	1591.9	1592.8	1593.6	1594.4
162.5°	1611.1	1612.2	1613.3	1614.4
165°	1626.5	1627.8	1629.2	1630.6
167.5°	1640.2	1641.6	1643.0	1644.4
170°	1650.6	1652.3	1653.9	1655.6
172.5°	1658.1	1659.8	1661.4	1663.1
175°	1663.1	1664.8	1666.4	1668.1
177.5°	1666.0	1667.9	1669.9	1671.8
180°	1668.1	1668.1	1668.1	1668.1

(END OF REPORT)