

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033530

Luminaire Tested: S124DIW-B575D1050UB27-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033530
REPORT IS A COMBINATION OF REPORTS P997609 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D1050UB27-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6776.0 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	67	63	59	56	52	47	44	42	35	34	32
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28
4	73	62	54	49	66	57	50	45	46	42	38	37	34	31	28	26	24
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	23	21	19
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7562	7562	7562	7562
5°	7543	8675	7587	6519
10°	7487	10122	7544	5719
15°	7396	11668	7448	5117
20°	7301	12653	7353	4588
25°	7161	12508	7230	4197
30°	7025	10338	7110	3996
35°	6833	7704	6908	3875
40°	6609	5803	6673	3815
45°	6267	4658	6344	3733
50°	5859	3924	5944	3695
55°	5378	3415	5463	3652
60°	4912	3008	5057	3592
65°	4474	2588	4516	3442
70°	3960	2130	4045	3169
75°	3455	1635	3432	2692
80°	2719	1074	2686	2043
85°	1790	482	1674	1193

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9779 cd/sqm

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.3	1.3
10°-20°	278.6	4.1
20°-30°	442.6	6.5
30°-40°	491.8	7.3
40°-50°	447.2	6.6
50°-60°	365.5	5.4
60°-70°	260.9	3.8
70°-80°	143.5	2.1
80°-90°	41.6	0.6
90°-100°	45.2	0.7
100°-110°	297.7	4.4
110°-120°	568.5	8.4
120°-130°	721.7	10.7
130°-140°	772.1	11.4
140°-150°	721.9	10.7
150°-160°	582.2	8.6
160°-170°	375.5	5.5
170°-180°	129.4	1.9
0°-30°	811.4	12.0
0°-40°	1303.2	19.2
0°-60°	2115.8	31.2
0°-90°	2561.8	37.8
90°-120°	911.4	13.5
90°-150°	3127.1	46.2
90°-180°	4214.0	62.2
0°-180°	6776.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	927	927	927	927	927	
5°	924	1088	929	818	924	88
15°	882	1494	888	655	882	249
25°	805	1587	813	532	805	371
35°	698	938	706	472	698	436
45°	557	526	564	422	557	430
55°	392	344	398	368	392	352
65°	244	221	247	294	244	241
75°	120	111	119	182	120	126
85°	25	23	23	57	25	29
90°	3	31	3	31	3	4
95°	56	30	56	30	56	69
105°	307	290	307	290	307	321
115°	572	576	572	576	572	563
125°	805	811	805	811	805	719
135°	998	1005	998	1005	998	769
145°	1151	1157	1151	1157	1151	719
155°	1262	1261	1262	1261	1262	582
165°	1331	1325	1331	1325	1331	376
175°	1362	1354	1362	1354	1362	130
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	927.4	936.6	940.4	943.5	953.5	956.6	957.3	961.9	965.8	966.6	966.6
5°	923.5	938.1	949.6	960.4	976.5	983.5	991.9	1001.1	1013.4	1021.1	1024.9
7.5°	917.4	938.9	956.6	975.0	997.3	1011.1	1018.8	1043.4	1060.3	1074.1	1091.0
10°	908.2	935.8	961.2	988.1	1019.6	1036.5	1053.4	1083.3	1107.2	1134.0	1155.6
12.5°	894.3	930.4	961.2	998.8	1038.0	1058.0	1078.0	1130.2	1157.9	1181.7	1220.1
15°	882.0	918.1	961.9	1000.4	1048.8	1078.7	1107.9	1141.7	1185.5	1237.0	1273.9
17.5°	868.2	913.5	954.3	1008.0	1061.8	1090.3	1114.1	1166.3	1227.8	1278.5	1312.3
20°	849.0	895.1	948.9	1005.7	1069.5	1091.8	1123.3	1193.2	1248.5	1298.5	1353.8
22.5°	826.7	880.5	937.4	991.9	1058.0	1104.8	1139.4	1200.9	1267.7	1325.4	1387.6
25°	805.2	863.6	913.5	988.1	1058.0	1089.5	1128.7	1201.7	1274.6	1344.6	1408.3
27.5°	782.2	836.7	904.3	963.5	1042.6	1077.2	1119.4	1199.4	1277.0	1346.9	1415.3
30°	756.8	815.2	871.3	941.2	1018.0	1062.6	1101.8	1188.6	1267.7	1340.7	1404.5
32.5°	728.4	783.7	843.6	909.7	990.4	1035.7	1084.9	1174.0	1258.5	1321.5	1370.7
35°	698.4	754.5	806.7	874.4	957.3	1002.7	1050.3	1148.6	1232.4	1283.9	1312.3
37.5°	665.4	718.4	769.9	836.7	919.7	968.1	1016.5	1111.8	1190.9	1233.9	1226.2
40°	633.9	681.5	729.1	792.1	879.0	930.4	972.7	1068.7	1137.9	1156.3	1131.0
42.5°	597.8	638.5	684.6	749.1	833.6	882.0	935.0	1022.6	1074.1	1066.4	1023.4
45°	557.0	593.1	639.2	699.9	786.0	835.9	880.5	963.5	1001.1	981.9	903.5
47.5°	517.8	553.2	590.8	651.5	735.3	777.5	822.9	897.4	918.9	878.2	799.8
50°	475.6	504.8	544.0	601.6	680.0	724.5	762.2	822.1	829.8	779.8	698.4
52.5°	434.9	459.5	497.1	554.0	627.0	662.3	699.2	752.2	746.0	694.6	616.2
55°	391.8	414.9	449.5	501.7	566.3	600.1	631.6	678.4	665.4	612.4	544.0
57.5°	355.7	371.9	405.7	454.1	507.1	544.0	570.9	607.7	587.8	534.8	471.0
60°	314.2	334.2	362.6	401.8	454.1	478.7	502.5	527.1	513.2	462.5	405.7
62.5°	276.6	292.0	316.5	354.2	394.9	417.2	442.6	457.9	444.1	397.2	349.6
65°	244.3	256.6	275.8	306.6	345.7	364.2	378.8	393.4	381.9	338.1	303.5
67.5°	209.0	219.7	235.9	260.5	293.5	306.6	320.4	330.4	317.3	288.1	254.3
70°	177.5	185.2	200.5	219.0	242.0	254.3	265.8	275.8	264.3	239.7	214.4
72.5°	145.2	151.4	165.2	178.3	199.0	207.4	215.9	223.6	219.7	196.7	175.9
75°	119.9	122.2	131.4	142.1	155.2	164.4	170.6	175.2	172.1	153.7	140.6
77.5°	90.7	93.7	100.7	109.1	120.6	126.0	129.8	134.5	130.6	116.0	106.8
80°	66.1	66.8	70.7	78.4	86.1	86.8	90.7	96.8	94.5	84.5	77.6
82.5°	42.3	44.6	46.1	50.7	56.1	57.6	59.9	61.5	60.7	54.6	52.2
85°	24.6	24.6	26.1	29.2	30.7	33.0	33.8	34.6	36.1	32.3	30.0
87.5°	10.8	11.5	11.5	12.3	13.8	13.8	14.6	15.4	16.1	15.4	13.1
90°	3.1	5.6	8.1	10.6	13.1	14.3	15.2	17.0	18.8	20.6	22.4
92.5°	15.3	14.8	14.4	13.9	13.4	13.2	14.1	15.9	17.8	19.6	21.4
95°	56.0	48.3	40.6	32.9	25.2	21.4	21.5	21.7	22.0	22.2	22.4
97.5°	107.0	112.0	117.0	121.9	126.9	129.4	117.5	93.7	70.0	46.2	22.4
100°	167.1	171.2	175.2	179.3	183.4	185.4	169.8	138.5	107.3	76.0	44.8
102.5°	234.3	237.0	239.7	242.4	245.1	246.5	247.9	250.6	253.3	256.0	258.7
105°	306.6	308.0	309.3	310.7	312.0	312.7	313.3	314.4	315.5	316.7	317.8
107.5°	372.8	373.5	374.2	374.9	375.6	375.9	376.7	378.3	379.8	381.4	383.0
110°	440.0	440.7	441.4	442.1	442.8	443.1	443.8	445.1	446.5	447.8	449.2



TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	505.2	506.6	507.9	509.3	510.6	511.3	511.5	512.0	512.5	512.9	513.4
115°	572.5	573.2	573.8	574.5	575.2	575.5	575.4	575.2	574.9	574.7	574.5
117.5°	632.6	633.5	634.4	635.3	636.2	636.6	636.9	637.6	638.3	639.0	639.7
120°	693.7	694.6	695.5	696.4	697.3	697.8	697.7	697.4	697.2	696.9	696.7
122.5°	750.7	751.2	751.6	752.1	752.6	752.8	753.0	753.5	753.9	754.4	754.8
125°	804.7	805.6	806.5	807.4	808.3	808.8	808.6	808.1	807.6	807.2	806.7
127.5°	856.7	856.9	857.1	857.4	857.6	857.7	858.3	859.4	860.5	861.7	862.8
130°	906.6	906.8	907.0	907.3	907.5	907.6	907.9	908.6	909.3	909.9	910.6
132.5°	952.4	952.8	953.3	953.7	954.2	954.4	954.9	955.8	956.7	957.6	958.5
135°	998.2	998.0	997.8	997.5	997.3	997.2	997.7	998.6	999.5	1000.4	1001.3
137.5°	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0	1039.6	1040.7	1041.8	1043.0	1044.1
140°	1078.7	1079.2	1079.6	1080.1	1080.6	1080.8	1081.0	1081.5	1081.9	1082.4	1082.8
142.5°	1114.4	1115.3	1116.2	1117.1	1118.0	1118.4	1118.5	1118.8	1119.0	1119.3	1119.5
145°	1151.0	1151.7	1152.4	1153.1	1153.8	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1
147.5°	1179.6	1181.0	1182.3	1183.7	1185.0	1185.7	1185.6	1185.4	1185.1	1184.9	1184.7
150°	1211.1	1212.0	1212.9	1213.8	1214.7	1215.2	1215.1	1214.9	1214.6	1214.4	1214.2
152.5°	1237.6	1238.3	1239.0	1239.7	1240.4	1240.7	1240.5	1240.0	1239.5	1239.1	1238.6
155°	1262.1	1262.3	1262.5	1262.8	1263.0	1263.1	1262.8	1262.1	1261.4	1260.7	1260.0
157.5°	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5	1283.0	1282.1	1281.2	1280.3	1279.4
160°	1301.8	1301.1	1300.4	1299.7	1299.0	1298.7	1298.6	1298.4	1298.1	1297.9	1297.7
162.5°	1318.1	1317.2	1316.3	1315.4	1314.5	1314.0	1313.9	1313.7	1313.4	1313.2	1313.0
165°	1331.3	1330.2	1329.0	1327.9	1326.8	1326.2	1326.2	1326.2	1326.2	1326.2	1326.2
167.5°	1342.5	1341.4	1340.2	1339.1	1338.0	1337.4	1337.3	1337.1	1336.8	1336.6	1336.4
170°	1351.7	1350.3	1349.0	1347.6	1346.3	1345.6	1345.7	1345.9	1346.2	1346.4	1346.6
172.5°	1357.8	1356.4	1355.1	1353.7	1352.4	1351.7	1351.8	1352.0	1352.3	1352.5	1352.7
175°	1361.9	1360.5	1359.2	1357.8	1356.5	1355.8	1355.9	1356.1	1356.4	1356.6	1356.8
177.5°	1365.0	1363.4	1361.8	1360.2	1358.6	1357.8	1358.0	1358.5	1359.0	1359.4	1359.9
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	968.9	982.7	988.8	990.4	998.8	993.4	995.7	995.0	1001.1	1001.9	1001.9
5°	1039.5	1055.7	1061.1	1068.7	1080.3	1083.3	1081.0	1085.6	1094.1	1087.9	1097.2
7.5°	1114.1	1131.7	1144.0	1160.9	1164.8	1174.8	1180.9	1186.3	1187.8	1188.6	1190.1
10°	1183.2	1205.5	1222.4	1250.8	1257.0	1262.4	1289.2	1278.5	1292.3	1287.7	1289.2
12.5°	1239.3	1283.1	1296.9	1344.6	1349.2	1367.6	1366.1	1383.0	1386.1	1392.2	1386.1
15°	1313.1	1363.8	1386.1	1412.9	1428.3	1449.8	1453.7	1476.7	1485.9	1494.4	1485.9
17.5°	1380.7	1407.6	1464.4	1485.9	1495.9	1507.5	1536.6	1545.1	1558.9	1553.5	1568.9
20°	1414.5	1452.9	1512.8	1549.7	1565.1	1575.8	1600.4	1613.5	1618.9	1618.9	1620.4
22.5°	1444.4	1499.8	1544.3	1586.6	1600.4	1608.1	1622.7	1632.7	1635.0	1636.5	1638.1
25°	1471.3	1521.3	1557.4	1581.2	1586.6	1586.6	1595.0	1588.9	1578.9	1586.6	1591.2
27.5°	1471.3	1506.7	1522.8	1531.3	1531.3	1510.5	1498.2	1472.9	1451.4	1445.2	1459.0
30°	1446.8	1462.9	1440.6	1419.9	1403.7	1389.9	1341.5	1303.1	1295.4	1290.0	1310.8
32.5°	1389.9	1369.2	1325.4	1265.4	1241.6	1210.1	1172.5	1143.3	1125.6	1119.4	1114.8
35°	1289.2	1235.5	1178.6	1097.9	1081.0	1041.1	989.6	968.1	938.9	938.1	948.1
37.5°	1179.4	1096.4	1034.9	958.1	934.3	892.0	843.6	821.3	801.4	786.0	804.4
40°	1051.1	978.8	885.1	822.1	788.3	766.0	725.3	700.7	691.5	683.8	695.3
42.5°	931.2	852.1	779.1	714.5	686.9	661.5	634.6	610.8	603.9	603.1	611.6
45°	812.1	734.5	666.9	611.6	593.9	578.5	552.4	545.5	534.0	526.3	530.1
47.5°	716.8	636.9	580.9	538.6	523.2	510.2	493.3	481.7	471.8	468.7	473.3
50°	623.1	569.3	511.7	476.4	464.8	452.5	439.5	428.7	424.1	421.0	424.1
52.5°	547.8	490.2	451.0	422.6	411.1	401.8	392.6	388.0	381.9	383.4	386.5
55°	480.2	429.5	396.5	375.7	368.8	365.0	353.4	348.1	345.7	344.2	345.7
57.5°	416.4	379.6	355.0	337.3	328.1	325.8	316.5	316.5	314.2	311.9	312.7
60°	365.7	334.2	310.4	296.6	295.0	291.2	285.0	284.3	278.9	281.2	282.0
62.5°	314.2	288.9	272.8	264.3	258.9	257.4	253.5	252.8	250.5	251.2	249.7
65°	273.5	252.8	236.6	229.7	227.4	226.7	223.6	221.3	219.7	221.3	219.7
67.5°	232.8	219.0	206.7	199.8	196.7	195.9	193.6	192.1	192.8	190.5	192.1
70°	194.4	180.6	172.9	169.0	167.5	165.2	165.2	165.2	165.2	163.7	162.9
72.5°	163.7	149.8	144.4	142.1	140.6	139.8	137.5	138.3	137.5	136.8	139.8
75°	129.8	121.4	116.0	113.7	115.2	112.9	110.6	112.2	109.9	110.6	113.7
77.5°	98.3	94.5	91.4	89.9	88.4	86.8	86.8	85.3	85.3	85.3	85.3
80°	71.5	70.7	65.3	64.5	64.5	63.0	63.0	63.0	63.0	62.2	63.0
82.5°	47.6	46.9	45.3	44.6	43.0	43.8	43.8	42.3	42.3	41.5	42.3
85°	27.7	27.7	26.1	25.4	24.6	25.4	23.8	23.0	23.8	23.0	23.8
87.5°	13.1	11.5	12.3	11.5	10.0	10.8	9.2	10.0	9.2	8.5	10.0
90°	23.8	25.1	26.5	27.8	28.5	28.7	29.2	29.7	30.1	30.6	30.1
92.5°	22.8	24.1	25.5	26.8	27.5	27.5	27.5	27.5	27.5	27.5	27.5
95°	23.8	25.1	26.5	27.8	28.5	28.6	28.8	29.1	29.3	29.5	29.3
97.5°	23.5	24.7	25.8	26.9	27.5	27.6	27.8	28.1	28.3	28.5	28.3
100°	41.0	37.1	33.3	29.4	27.5	27.6	27.8	28.1	28.3	28.5	28.3
102.5°	207.8	156.8	105.9	55.0	29.5	29.5	29.5	29.5	29.5	29.5	29.5
105°	319.8	321.9	323.9	326.0	327.0	322.9	314.8	306.6	298.5	290.3	298.5
107.5°	384.1	385.3	386.4	387.5	388.1	388.6	389.5	390.4	391.3	392.2	391.3
110°	449.6	450.1	450.5	451.0	451.2	451.5	452.2	452.9	453.6	454.3	453.6

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	513.2	513.0	512.7	512.5	512.4	512.8	513.7	514.6	515.5	516.4	515.5
115°	574.9	575.4	575.8	576.3	576.5	576.5	576.5	576.5	576.5	576.5	576.5
117.5°	639.5	639.3	639.0	638.8	638.7	638.7	638.7	638.7	638.7	638.7	638.7
120°	697.2	697.6	698.1	698.6	698.8	698.6	698.1	697.6	697.2	696.7	697.2
122.5°	755.0	755.2	755.5	755.7	755.8	755.6	755.1	754.7	754.2	753.8	754.2
125°	807.4	808.1	808.8	809.5	809.8	809.9	810.1	810.4	810.6	810.8	810.6
127.5°	862.6	862.4	862.1	861.9	861.8	861.7	861.4	861.2	860.9	860.7	860.9
130°	910.8	911.1	911.3	911.6	911.7	911.7	911.7	911.7	911.7	911.7	911.7
132.5°	958.7	958.9	959.2	959.4	959.5	959.4	959.2	958.9	958.7	958.5	958.7
135°	1001.7	1002.2	1002.6	1003.1	1003.3	1003.5	1004.0	1004.5	1004.9	1005.4	1004.9
137.5°	1044.5	1045.0	1045.4	1045.9	1046.1	1046.0	1045.8	1045.5	1045.3	1045.1	1045.3
140°	1083.5	1084.2	1084.9	1085.6	1085.9	1086.0	1086.2	1086.5	1086.7	1086.9	1086.7
142.5°	1119.9	1120.4	1120.8	1121.3	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5
145°	1154.3	1154.5	1154.8	1155.0	1155.1	1155.3	1155.8	1156.3	1156.7	1157.2	1156.7
147.5°	1184.9	1185.1	1185.4	1185.6	1185.7	1185.8	1186.0	1186.3	1186.5	1186.7	1186.5
150°	1214.2	1214.2	1214.2	1214.2	1214.2	1214.3	1214.5	1214.8	1215.0	1215.2	1215.0
152.5°	1239.1	1239.5	1240.0	1240.5	1240.7	1240.6	1240.4	1240.1	1239.9	1239.7	1239.9
155°	1260.9	1261.8	1262.7	1263.6	1264.1	1263.8	1263.1	1262.4	1261.8	1261.1	1261.8
157.5°	1280.5	1281.7	1282.8	1283.9	1284.5	1283.9	1282.8	1281.7	1280.5	1279.4	1280.5
160°	1299.1	1300.4	1301.8	1303.1	1303.8	1303.1	1301.8	1300.4	1299.1	1297.7	1299.1
162.5°	1314.4	1315.7	1317.1	1318.4	1319.1	1318.3	1316.7	1315.2	1313.6	1312.0	1313.6
165°	1328.0	1329.8	1331.7	1333.5	1334.4	1333.4	1331.3	1329.3	1327.2	1325.2	1327.2
167.5°	1338.4	1340.5	1342.5	1344.6	1345.6	1344.5	1342.2	1339.9	1337.7	1335.4	1337.7
170°	1348.4	1350.2	1352.1	1353.9	1354.8	1353.7	1351.4	1349.1	1346.9	1344.6	1346.9
172.5°	1354.5	1356.3	1358.2	1360.0	1360.9	1359.7	1357.2	1354.7	1352.2	1349.7	1352.2
175°	1358.8	1360.9	1362.9	1365.0	1366.0	1364.6	1361.9	1359.2	1356.4	1353.7	1356.4
177.5°	1361.7	1363.5	1365.3	1367.1	1368.0	1366.6	1363.9	1361.2	1358.5	1355.8	1358.5
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	1000.4	998.1	995.0	995.0	991.1	991.1	985.0	974.2	965.0	961.9	963.5
5°	1085.6	1086.4	1081.8	1078.0	1071.0	1065.7	1055.7	1036.5	1030.3	1018.0	1009.6
7.5°	1183.2	1180.1	1171.7	1165.5	1164.0	1151.7	1130.2	1107.2	1088.7	1076.4	1058.7
10°	1293.1	1280.8	1268.5	1264.7	1255.4	1234.7	1210.1	1184.8	1159.4	1132.5	1102.5
12.5°	1385.3	1361.5	1360.7	1351.5	1333.8	1322.3	1293.1	1257.0	1213.2	1183.2	1149.4
15°	1484.4	1462.1	1443.7	1426.8	1418.3	1384.5	1359.9	1314.6	1262.4	1230.1	1207.0
17.5°	1555.1	1545.1	1513.6	1505.9	1494.4	1455.2	1416.0	1371.5	1326.1	1280.8	1218.6
20°	1611.9	1605.8	1585.1	1574.3	1555.9	1525.1	1477.5	1426.0	1373.8	1309.2	1250.8
22.5°	1636.5	1628.8	1611.9	1602.7	1591.2	1565.1	1524.4	1466.0	1397.6	1340.0	1277.7
25°	1588.1	1602.0	1597.3	1593.5	1588.9	1573.5	1542.8	1491.3	1424.5	1359.2	1281.6
27.5°	1479.0	1502.8	1525.9	1529.0	1536.6	1542.8	1530.5	1493.6	1437.5	1368.4	1283.1
30°	1332.3	1343.0	1389.9	1403.7	1414.5	1453.7	1476.7	1467.5	1424.5	1362.2	1283.9
32.5°	1144.0	1172.5	1220.1	1253.1	1282.3	1326.1	1386.1	1409.9	1394.5	1343.8	1266.2
35°	965.8	999.6	1054.9	1097.2	1126.4	1188.6	1259.3	1310.8	1330.0	1304.6	1235.5
37.5°	819.8	860.5	909.7	925.8	959.6	1036.5	1134.0	1205.5	1252.4	1254.7	1200.9
40°	709.9	730.7	769.9	794.4	827.5	892.0	987.3	1081.8	1152.5	1176.3	1147.9
42.5°	617.0	633.1	662.3	692.3	722.2	771.4	859.0	947.3	1042.6	1090.3	1089.5
45°	543.2	560.1	580.1	604.7	625.4	678.4	747.6	838.2	920.5	994.2	1012.7
47.5°	478.7	493.3	517.8	528.6	542.4	592.4	652.3	736.8	822.1	906.6	928.1
50°	431.0	443.3	460.2	467.1	482.5	519.4	568.6	636.9	731.4	809.0	849.0
52.5°	388.0	397.2	410.3	415.7	426.4	454.1	498.6	552.4	630.8	710.7	766.8
55°	351.1	357.3	366.5	372.6	380.3	404.9	437.9	486.3	554.0	623.1	677.7
57.5°	316.5	321.2	330.4	333.5	339.6	358.8	381.9	422.6	484.8	546.3	599.3
60°	284.3	287.4	292.7	299.6	304.3	317.3	338.8	372.6	422.6	478.7	521.7
62.5°	253.5	258.2	259.7	262.8	266.6	278.9	295.8	320.4	364.2	410.3	455.6
65°	222.0	225.9	229.0	229.7	233.6	242.8	258.2	279.7	308.1	348.1	390.3
67.5°	192.8	195.2	196.7	199.8	203.6	208.2	220.5	236.6	262.8	295.0	328.8
70°	166.0	166.0	168.3	169.0	173.6	179.0	184.4	199.8	222.8	248.9	272.0
72.5°	136.8	140.6	139.8	143.7	142.9	146.7	153.7	163.7	180.6	201.3	223.6
75°	111.4	113.7	113.7	113.7	115.2	118.3	122.2	131.4	144.4	161.3	174.4
77.5°	86.8	88.4	88.4	88.4	89.1	92.2	96.0	102.2	111.4	121.4	129.1
80°	62.2	63.8	63.8	65.3	65.3	66.1	69.9	73.0	77.6	85.3	93.0
82.5°	42.3	43.0	44.6	44.6	43.8	45.3	46.1	49.2	53.8	55.3	60.7
85°	23.0	23.8	24.6	24.6	25.4	26.9	26.1	29.2	29.2	32.3	33.8
87.5°	9.2	10.8	10.8	10.0	10.8	10.8	10.8	12.3	13.1	13.8	13.1
90°	29.7	29.2	28.7	28.5	27.8	26.5	25.1	23.8	22.4	20.6	18.8
92.5°	27.5	27.5	27.5	27.5	26.8	25.5	24.1	22.8	21.4	19.6	17.8
95°	29.1	28.8	28.6	28.5	27.8	26.5	25.1	23.8	22.4	22.2	22.0
97.5°	28.1	27.8	27.6	27.5	26.9	25.8	24.7	23.5	22.4	46.2	70.0
100°	28.1	27.8	27.6	27.5	29.4	33.3	37.1	41.0	44.8	76.0	107.3
102.5°	29.5	29.5	29.5	29.5	55.0	105.9	156.8	207.8	258.7	256.0	253.3
105°	306.6	314.8	322.9	327.0	326.0	323.9	321.9	319.8	317.8	316.7	315.5
107.5°	390.4	389.5	388.6	388.1	387.5	386.4	385.3	384.1	383.0	381.4	379.8
110°	452.9	452.2	451.5	451.2	451.0	450.5	450.1	449.6	449.2	447.8	446.5

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	514.6	513.7	512.8	512.4	512.5	512.7	513.0	513.2	513.4	512.9	512.5
115°	576.5	576.5	576.5	576.5	576.3	575.8	575.4	574.9	574.5	574.7	574.9
117.5°	638.7	638.7	638.7	638.7	638.8	639.0	639.3	639.5	639.7	639.0	638.3
120°	697.6	698.1	698.6	698.8	698.6	698.1	697.6	697.2	696.7	696.9	697.2
122.5°	754.7	755.1	755.6	755.8	755.7	755.5	755.2	755.0	754.8	754.4	753.9
125°	810.4	810.1	809.9	809.8	809.5	808.8	808.1	807.4	806.7	807.2	807.6
127.5°	861.2	861.4	861.7	861.8	861.9	862.1	862.4	862.6	862.8	861.7	860.5
130°	911.7	911.7	911.7	911.7	911.6	911.3	911.1	910.8	910.6	909.9	909.3
132.5°	958.9	959.2	959.4	959.5	959.4	959.2	958.9	958.7	958.5	957.6	956.7
135°	1004.5	1004.0	1003.5	1003.3	1003.1	1002.6	1002.2	1001.7	1001.3	1000.4	999.5
137.5°	1045.5	1045.8	1046.0	1046.1	1045.9	1045.4	1045.0	1044.5	1044.1	1043.0	1041.8
140°	1086.5	1086.2	1086.0	1085.9	1085.6	1084.9	1084.2	1083.5	1082.8	1082.4	1081.9
142.5°	1121.5	1121.5	1121.5	1121.5	1121.3	1120.8	1120.4	1119.9	1119.5	1119.3	1119.0
145°	1156.3	1155.8	1155.3	1155.1	1155.0	1154.8	1154.5	1154.3	1154.1	1154.1	1154.1
147.5°	1186.3	1186.0	1185.8	1185.7	1185.6	1185.4	1185.1	1184.9	1184.7	1184.9	1185.1
150°	1214.8	1214.5	1214.3	1214.2	1214.2	1214.2	1214.2	1214.2	1214.2	1214.4	1214.6
152.5°	1240.1	1240.4	1240.6	1240.7	1240.5	1240.0	1239.5	1239.1	1238.6	1239.1	1239.5
155°	1262.4	1263.1	1263.8	1264.1	1263.6	1262.7	1261.8	1260.9	1260.0	1260.7	1261.4
157.5°	1281.7	1282.8	1283.9	1284.5	1283.9	1282.8	1281.7	1280.5	1279.4	1280.3	1281.2
160°	1300.4	1301.8	1303.1	1303.8	1303.1	1301.8	1300.4	1299.1	1297.7	1297.9	1298.1
162.5°	1315.2	1316.7	1318.3	1319.1	1318.4	1317.1	1315.7	1314.4	1313.0	1313.2	1313.4
165°	1329.3	1331.3	1333.4	1334.4	1333.5	1331.7	1329.8	1328.0	1326.2	1326.2	1326.2
167.5°	1339.9	1342.2	1344.5	1345.6	1344.6	1342.5	1340.5	1338.4	1336.4	1336.6	1336.8
170°	1349.1	1351.4	1353.7	1354.8	1353.9	1352.1	1350.2	1348.4	1346.6	1346.4	1346.2
172.5°	1354.7	1357.2	1359.7	1360.9	1360.0	1358.2	1356.3	1354.5	1352.7	1352.5	1352.3
175°	1359.2	1361.9	1364.6	1366.0	1365.0	1362.9	1360.9	1358.8	1356.8	1356.6	1356.4
177.5°	1361.2	1363.9	1366.6	1368.0	1367.1	1365.3	1363.5	1361.7	1359.9	1359.4	1359.0
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	956.6	953.5	951.2	951.2	944.3	937.4	933.5	932.0	930.4	924.3	915.8
5°	995.7	985.8	978.8	971.9	960.4	948.1	935.8	928.9	918.9	905.1	895.1
7.5°	1039.5	1015.7	1008.0	999.6	976.5	955.8	938.9	924.3	908.2	890.5	872.8
10°	1076.4	1051.1	1034.2	1019.6	989.6	961.9	936.6	915.1	894.3	871.3	849.8
12.5°	1111.8	1075.7	1058.0	1036.5	1005.0	965.0	932.0	905.1	874.4	850.5	824.4
15°	1160.9	1100.2	1071.0	1057.2	1015.0	968.1	928.1	888.2	862.8	826.7	803.7
17.5°	1168.6	1119.4	1100.2	1064.9	1014.2	961.2	915.1	875.1	836.7	804.4	774.5
20°	1195.5	1131.0	1100.2	1078.0	1011.1	957.3	906.6	855.1	818.3	783.7	749.9
22.5°	1212.4	1139.4	1107.2	1071.8	1008.0	943.5	883.6	839.0	793.7	758.3	731.4
25°	1207.8	1134.8	1098.7	1065.7	988.1	923.5	869.7	812.9	770.6	732.2	696.9
27.5°	1205.5	1123.3	1084.9	1048.0	975.0	907.4	839.8	793.7	746.8	702.2	676.1
30°	1199.4	1108.7	1064.1	1024.2	948.1	877.4	819.8	766.0	719.2	678.4	643.9
32.5°	1178.6	1084.1	1041.1	998.1	918.9	848.2	789.8	739.9	693.0	650.8	617.7
35°	1150.9	1054.9	1008.0	962.7	883.6	812.1	758.3	706.1	662.3	621.6	590.1
37.5°	1123.3	1021.1	977.3	925.1	852.1	777.5	722.2	675.4	634.6	592.4	557.8
40°	1083.3	981.1	932.7	888.2	802.9	733.0	682.3	640.0	600.1	560.1	530.9
42.5°	1028.8	937.4	887.4	838.2	758.3	689.2	640.0	602.4	564.7	531.7	499.4
45°	973.5	884.3	839.8	796.0	709.2	643.9	598.5	563.9	532.4	496.3	470.2
47.5°	906.6	831.3	786.8	743.7	661.5	596.2	554.7	522.5	493.3	463.3	438.7
50°	838.2	772.9	732.2	687.6	609.3	550.1	509.4	482.5	458.7	430.3	410.3
52.5°	764.5	707.6	673.1	630.0	560.9	506.3	464.8	437.9	418.0	397.2	379.6
55°	686.1	644.6	607.7	573.2	507.9	458.7	421.8	398.0	384.2	365.0	349.6
57.5°	615.4	575.5	553.2	514.0	457.2	408.7	379.6	359.6	343.4	331.9	319.6
60°	541.7	509.4	484.8	456.4	406.4	365.7	335.0	323.5	306.6	298.1	292.7
62.5°	471.0	447.9	424.9	403.4	358.8	320.4	297.3	282.7	272.8	264.3	259.7
65°	404.1	382.6	366.5	347.3	310.4	279.7	258.2	246.6	236.6	234.3	229.0
67.5°	338.8	329.6	311.9	296.6	265.1	241.3	225.1	210.5	205.1	202.8	198.2
70°	283.5	272.8	258.9	245.9	222.0	201.3	186.7	181.3	173.6	172.9	167.5
72.5°	233.6	220.5	210.5	200.5	182.9	164.4	156.7	149.1	145.2	142.1	139.8
75°	185.2	175.9	169.0	160.6	145.2	132.9	122.2	119.1	116.8	116.0	114.5
77.5°	138.3	132.2	129.1	120.6	109.9	99.1	94.5	89.9	89.9	88.4	89.1
80°	98.3	94.5	90.7	86.1	76.8	72.2	68.4	65.3	63.8	63.0	63.8
82.5°	62.2	59.9	59.2	56.1	49.9	47.6	44.6	42.3	42.3	42.3	42.3
85°	34.6	34.6	34.6	30.0	27.7	25.4	23.8	23.0	23.0	23.0	23.8
87.5°	14.6	14.6	12.3	12.3	11.5	10.0	9.2	9.2	10.0	10.0	10.8
90°	17.0	15.2	14.3	13.1	10.6	8.1	5.6	3.1	5.6	8.1	10.6
92.5°	15.9	14.1	13.2	13.4	13.9	14.4	14.8	15.3	14.8	14.4	13.9
95°	21.7	21.5	21.4	25.2	32.9	40.6	48.3	56.0	48.3	40.6	32.9
97.5°	93.7	117.5	129.4	126.9	121.9	117.0	112.0	107.0	112.0	117.0	121.9
100°	138.5	169.8	185.4	183.4	179.3	175.2	171.2	167.1	171.2	175.2	179.3
102.5°	250.6	247.9	246.5	245.1	242.4	239.7	237.0	234.3	237.0	239.7	242.4
105°	314.4	313.3	312.7	312.0	310.7	309.3	308.0	306.6	308.0	309.3	310.7
107.5°	378.3	376.7	375.9	375.6	374.9	374.2	373.5	372.8	373.5	374.2	374.9
110°	445.1	443.8	443.1	442.8	442.1	441.4	440.7	440.0	440.7	441.4	442.1

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	512.0	511.5	511.3	510.6	509.3	507.9	506.6	505.2	506.6	507.9	509.3
115°	575.2	575.4	575.5	575.2	574.5	573.8	573.2	572.5	573.2	573.8	574.5
117.5°	637.6	636.9	636.6	636.2	635.3	634.4	633.5	632.6	633.5	634.4	635.3
120°	697.4	697.7	697.8	697.3	696.4	695.5	694.6	693.7	694.6	695.5	696.4
122.5°	753.5	753.0	752.8	752.6	752.1	751.6	751.2	750.7	751.2	751.6	752.1
125°	808.1	808.6	808.8	808.3	807.4	806.5	805.6	804.7	805.6	806.5	807.4
127.5°	859.4	858.3	857.7	857.6	857.4	857.1	856.9	856.7	856.9	857.1	857.4
130°	908.6	907.9	907.6	907.5	907.3	907.0	906.8	906.6	906.8	907.0	907.3
132.5°	955.8	954.9	954.4	954.2	953.7	953.3	952.8	952.4	952.8	953.3	953.7
135°	998.6	997.7	997.2	997.3	997.5	997.8	998.0	998.2	998.0	997.8	997.5
137.5°	1040.7	1039.6	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0	1039.0
140°	1081.5	1081.0	1080.8	1080.6	1080.1	1079.6	1079.2	1078.7	1079.2	1079.6	1080.1
142.5°	1118.8	1118.5	1118.4	1118.0	1117.1	1116.2	1115.3	1114.4	1115.3	1116.2	1117.1
145°	1154.1	1154.1	1154.1	1153.8	1153.1	1152.4	1151.7	1151.0	1151.7	1152.4	1153.1
147.5°	1185.4	1185.6	1185.7	1185.0	1183.7	1182.3	1181.0	1179.6	1181.0	1182.3	1183.7
150°	1214.9	1215.1	1215.2	1214.7	1213.8	1212.9	1212.0	1211.1	1212.0	1212.9	1213.8
152.5°	1240.0	1240.5	1240.7	1240.4	1239.7	1239.0	1238.3	1237.6	1238.3	1239.0	1239.7
155°	1262.1	1262.8	1263.1	1263.0	1262.8	1262.5	1262.3	1262.1	1262.3	1262.5	1262.8
157.5°	1282.1	1283.0	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5	1283.5
160°	1298.4	1298.6	1298.7	1299.0	1299.7	1300.4	1301.1	1301.8	1301.1	1300.4	1299.7
162.5°	1313.7	1313.9	1314.0	1314.5	1315.4	1316.3	1317.2	1318.1	1317.2	1316.3	1315.4
165°	1326.2	1326.2	1326.2	1326.8	1327.9	1329.0	1330.2	1331.3	1330.2	1329.0	1327.9
167.5°	1337.1	1337.3	1337.4	1338.0	1339.1	1340.2	1341.4	1342.5	1341.4	1340.2	1339.1
170°	1345.9	1345.7	1345.6	1346.3	1347.6	1349.0	1350.3	1351.7	1350.3	1349.0	1347.6
172.5°	1352.0	1351.8	1351.7	1352.4	1353.7	1355.1	1356.4	1357.8	1356.4	1355.1	1353.7
175°	1356.1	1355.9	1355.8	1356.5	1357.8	1359.2	1360.5	1361.9	1360.5	1359.2	1357.8
177.5°	1358.5	1358.0	1357.8	1358.6	1360.2	1361.8	1363.4	1365.0	1363.4	1361.8	1360.2
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	913.5	910.5	912.0	904.3	897.4	887.4	879.0	877.4	875.9	880.5	877.4
5°	887.4	883.6	879.7	870.5	856.7	848.2	835.9	835.2	830.6	823.6	825.2
7.5°	859.0	856.7	851.3	836.7	824.4	809.8	799.8	791.4	787.5	781.4	779.1
10°	835.9	827.5	822.9	806.7	792.1	776.8	763.7	757.6	750.7	745.3	741.4
12.5°	804.4	802.1	789.1	776.0	763.7	746.0	736.1	718.4	709.2	713.8	712.2
15°	783.7	772.9	769.9	751.4	730.7	719.2	700.7	689.2	685.3	678.4	670.0
17.5°	756.0	749.1	738.4	721.5	697.6	681.5	668.4	657.7	653.1	643.9	636.9
20°	729.9	718.4	709.9	694.6	671.5	650.8	634.6	627.7	616.2	608.5	604.7
22.5°	706.1	697.6	685.3	662.3	642.3	622.3	603.1	593.1	582.4	577.8	571.6
25°	676.9	663.1	654.6	629.3	607.7	591.6	573.9	560.9	554.7	547.0	545.5
27.5°	648.5	635.4	625.4	603.1	577.0	556.3	545.5	536.3	525.5	525.5	521.7
30°	620.0	610.8	595.5	573.9	549.4	529.4	517.1	508.6	504.8	501.7	500.9
32.5°	591.6	579.3	570.1	540.9	522.5	504.0	494.8	487.9	483.3	482.5	483.3
35°	562.4	548.6	539.4	513.2	494.8	477.9	474.1	467.9	465.6	464.8	468.7
37.5°	531.7	520.9	509.4	487.9	467.1	457.2	449.5	447.2	446.4	451.0	452.5
40°	503.3	494.0	483.3	460.2	444.9	434.1	430.3	428.0	431.0	435.6	437.9
42.5°	476.4	463.3	454.8	434.1	420.3	414.1	409.5	409.5	412.6	418.0	421.8
45°	447.9	437.9	429.5	411.1	398.8	391.8	391.1	391.8	395.7	399.5	404.1
47.5°	420.3	410.3	401.1	385.7	374.9	371.1	370.3	371.1	377.2	382.6	388.0
50°	394.9	384.2	375.7	361.1	352.7	348.1	348.8	352.7	357.3	365.0	371.9
52.5°	365.0	357.3	349.6	336.5	328.8	325.8	328.1	331.1	339.6	345.0	353.4
55°	335.8	328.8	322.7	312.7	306.6	304.3	305.8	310.4	317.3	326.5	336.5
57.5°	308.9	301.2	295.0	288.1	281.2	282.0	282.7	288.9	297.3	305.8	317.3
60°	278.9	274.3	268.9	260.5	257.4	257.4	259.7	266.6	274.3	288.1	298.1
62.5°	252.0	245.9	242.0	236.6	232.0	232.8	238.2	244.3	253.5	265.1	278.1
65°	224.4	217.4	214.4	209.8	208.2	209.0	212.8	222.0	232.0	242.0	254.3
67.5°	193.6	191.3	188.2	183.6	185.2	185.9	189.8	197.5	208.2	218.2	232.0
70°	167.5	162.9	162.1	158.3	158.3	160.6	168.3	173.6	183.6	194.4	209.0
72.5°	139.8	136.0	136.0	132.9	135.2	137.5	141.4	149.1	158.3	169.0	181.3
75°	111.4	109.9	111.4	109.9	109.9	113.7	118.3	124.5	134.5	146.0	156.0
77.5°	86.1	86.1	85.3	87.6	87.6	89.9	96.0	102.2	109.9	119.1	129.8
80°	63.0	63.0	63.0	65.3	67.6	67.6	71.5	79.1	86.1	92.2	102.2
82.5°	43.0	43.0	43.0	44.6	47.6	47.6	52.2	56.9	64.5	69.9	74.5
85°	26.1	26.1	25.4	26.9	27.7	30.0	33.8	36.9	40.7	45.3	49.9
87.5°	11.5	11.5	12.3	13.1	13.8	15.4	16.9	18.4	22.3	23.8	26.1
90°	13.1	14.3	15.2	17.0	18.8	20.6	22.4	23.8	25.1	26.5	27.8
92.5°	13.4	13.2	14.1	15.9	17.8	19.6	21.4	22.8	24.1	25.5	26.8
95°	25.2	21.4	21.5	21.7	22.0	22.2	22.4	23.8	25.1	26.5	27.8
97.5°	126.9	129.4	117.5	93.7	70.0	46.2	22.4	23.5	24.7	25.8	26.9
100°	183.4	185.4	169.8	138.5	107.3	76.0	44.8	41.0	37.1	33.3	29.4
102.5°	245.1	246.5	247.9	250.6	253.3	256.0	258.7	207.8	156.8	105.9	55.0
105°	312.0	312.7	313.3	314.4	315.5	316.7	317.8	319.8	321.9	323.9	326.0
107.5°	375.6	375.9	376.7	378.3	379.8	381.4	383.0	384.1	385.3	386.4	387.5
110°	442.8	443.1	443.8	445.1	446.5	447.8	449.2	449.6	450.1	450.5	451.0

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	510.6	511.3	511.5	512.0	512.5	512.9	513.4	513.2	513.0	512.7	512.5
115°	575.2	575.5	575.4	575.2	574.9	574.7	574.5	574.9	575.4	575.8	576.3
117.5°	636.2	636.6	636.9	637.6	638.3	639.0	639.7	639.5	639.3	639.0	638.8
120°	697.3	697.8	697.7	697.4	697.2	696.9	696.7	697.2	697.6	698.1	698.6
122.5°	752.6	752.8	753.0	753.5	753.9	754.4	754.8	755.0	755.2	755.5	755.7
125°	808.3	808.8	808.6	808.1	807.6	807.2	806.7	807.4	808.1	808.8	809.5
127.5°	857.6	857.7	858.3	859.4	860.5	861.7	862.8	862.6	862.4	862.1	861.9
130°	907.5	907.6	907.9	908.6	909.3	909.9	910.6	910.8	911.1	911.3	911.6
132.5°	954.2	954.4	954.9	955.8	956.7	957.6	958.5	958.7	958.9	959.2	959.4
135°	997.3	997.2	997.7	998.6	999.5	1000.4	1001.3	1001.7	1002.2	1002.6	1003.1
137.5°	1039.0	1039.0	1039.6	1040.7	1041.8	1043.0	1044.1	1044.5	1045.0	1045.4	1045.9
140°	1080.6	1080.8	1081.0	1081.5	1081.9	1082.4	1082.8	1083.5	1084.2	1084.9	1085.6
142.5°	1118.0	1118.4	1118.5	1118.8	1119.0	1119.3	1119.5	1119.9	1120.4	1120.8	1121.3
145°	1153.8	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1	1154.3	1154.5	1154.8	1155.0
147.5°	1185.0	1185.7	1185.6	1185.4	1185.1	1184.9	1184.7	1184.9	1185.1	1185.4	1185.6
150°	1214.7	1215.2	1215.1	1214.9	1214.6	1214.4	1214.2	1214.2	1214.2	1214.2	1214.2
152.5°	1240.4	1240.7	1240.5	1240.0	1239.5	1239.1	1238.6	1239.1	1239.5	1240.0	1240.5
155°	1263.0	1263.1	1262.8	1262.1	1261.4	1260.7	1260.0	1260.9	1261.8	1262.7	1263.6
157.5°	1283.5	1283.5	1283.0	1282.1	1281.2	1280.3	1279.4	1280.5	1281.7	1282.8	1283.9
160°	1299.0	1298.7	1298.6	1298.4	1298.1	1297.9	1297.7	1299.1	1300.4	1301.8	1303.1
162.5°	1314.5	1314.0	1313.9	1313.7	1313.4	1313.2	1313.0	1314.4	1315.7	1317.1	1318.4
165°	1326.8	1326.2	1326.2	1326.2	1326.2	1326.2	1326.2	1328.0	1329.8	1331.7	1333.5
167.5°	1338.0	1337.4	1337.3	1337.1	1336.8	1336.6	1336.4	1338.4	1340.5	1342.5	1344.6
170°	1346.3	1345.6	1345.7	1345.9	1346.2	1346.4	1346.6	1348.4	1350.2	1352.1	1353.9
172.5°	1352.4	1351.7	1351.8	1352.0	1352.3	1352.5	1352.7	1354.5	1356.3	1358.2	1360.0
175°	1356.5	1355.8	1355.9	1356.1	1356.4	1356.6	1356.8	1358.8	1360.9	1362.9	1365.0
177.5°	1358.6	1357.8	1358.0	1358.5	1359.0	1359.4	1359.9	1361.7	1363.5	1365.3	1367.1
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	875.1	874.4	870.5	872.0	867.4	869.0	871.3	872.0	875.1	872.8	872.0
5°	821.3	819.8	817.5	815.2	814.4	817.5	812.1	813.7	815.2	817.5	820.6
7.5°	777.5	776.8	774.5	770.6	769.1	767.6	768.3	773.7	772.9	772.2	777.5
10°	737.6	738.4	733.7	733.0	728.4	727.6	728.4	729.9	732.2	735.3	736.1
12.5°	696.1	706.1	697.6	694.6	687.6	691.5	693.0	686.1	690.0	692.3	703.8
15°	670.0	665.4	660.0	660.0	656.9	655.4	651.5	656.9	660.0	664.6	663.1
17.5°	633.9	626.2	623.1	620.0	620.8	623.9	615.4	627.7	627.7	630.0	626.2
20°	602.4	596.2	592.4	590.8	588.5	587.0	586.2	589.3	593.9	595.5	599.3
22.5°	569.3	569.3	563.2	560.9	559.3	557.0	560.9	558.6	561.6	564.7	570.9
25°	541.7	541.7	539.4	536.3	534.0	532.4	534.8	534.0	536.3	540.1	541.7
27.5°	519.4	517.1	516.3	515.5	514.8	515.5	514.8	517.1	519.4	520.2	518.6
30°	500.2	497.9	498.6	498.6	499.4	498.6	497.9	500.2	500.9	499.4	500.2
32.5°	482.5	482.5	484.0	484.8	484.8	485.6	486.3	484.8	485.6	483.3	484.0
35°	467.9	469.4	471.0	471.8	472.5	471.8	473.3	472.5	471.0	469.4	468.7
37.5°	453.3	454.8	457.9	458.7	461.0	461.8	460.2	460.2	459.5	456.4	454.8
40°	437.9	439.5	443.3	445.6	447.2	449.5	447.9	447.9	444.9	441.8	439.5
42.5°	423.3	426.4	430.3	432.6	435.6	435.6	435.6	434.1	430.3	427.2	424.9
45°	408.7	409.5	414.9	418.7	421.8	421.8	421.8	419.5	417.2	411.1	408.0
47.5°	392.6	394.9	401.1	404.9	408.0	408.7	408.7	406.4	401.8	396.5	392.6
50°	374.9	378.8	385.7	391.1	394.9	396.5	394.1	392.6	387.2	381.1	376.5
52.5°	358.0	362.6	371.1	375.7	381.1	381.9	381.1	378.8	372.6	364.2	360.3
55°	341.1	345.0	354.2	361.9	366.5	368.0	366.5	362.6	355.0	346.5	342.7
57.5°	322.7	328.1	338.1	345.7	351.1	351.9	350.4	346.5	340.4	329.6	324.2
60°	303.5	310.4	320.4	328.1	335.0	335.8	334.2	328.8	321.2	310.4	305.8
62.5°	284.3	289.7	301.2	309.6	315.0	318.9	315.8	310.4	302.7	292.0	285.0
65°	262.0	269.7	279.7	287.4	293.5	294.3	292.7	288.1	279.7	268.1	262.8
67.5°	240.5	245.9	255.9	265.8	268.1	270.4	268.1	263.5	256.6	246.6	238.9
70°	214.4	219.0	231.3	238.2	241.3	243.6	242.0	237.4	231.3	222.0	215.9
72.5°	188.2	192.1	203.6	209.0	215.1	214.4	213.6	210.5	202.1	195.9	192.1
75°	160.6	165.2	172.9	179.8	182.1	182.1	182.1	179.8	174.4	164.4	160.6
77.5°	135.2	137.5	143.7	147.5	149.8	150.6	149.8	146.0	142.9	136.0	133.7
80°	103.7	109.9	114.5	115.2	118.3	118.3	118.3	116.8	113.7	106.8	106.0
82.5°	78.4	79.9	84.5	86.8	88.4	87.6	87.6	84.5	83.7	79.9	78.4
85°	53.0	55.3	54.6	57.6	58.4	56.9	56.9	58.4	54.6	55.3	53.0
87.5°	29.2	29.2	30.7	30.0	33.0	33.0	31.5	32.3	30.7	30.0	29.2
90°	28.5	28.7	29.2	29.7	30.1	30.6	30.1	29.7	29.2	28.7	28.5
92.5°	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5
95°	28.5	28.6	28.8	29.1	29.3	29.5	29.3	29.1	28.8	28.6	28.5
97.5°	27.5	27.6	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	27.5
100°	27.5	27.6	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	27.5
102.5°	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5
105°	327.0	322.9	314.8	306.6	298.5	290.3	298.5	306.6	314.8	322.9	327.0
107.5°	388.1	388.6	389.5	390.4	391.3	392.2	391.3	390.4	389.5	388.6	388.1
110°	451.2	451.5	452.2	452.9	453.6	454.3	453.6	452.9	452.2	451.5	451.2

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	512.4	512.8	513.7	514.6	515.5	516.4	515.5	514.6	513.7	512.8	512.4
115°	576.5	576.5	576.5	576.5	576.5	576.5	576.5	576.5	576.5	576.5	576.5
117.5°	638.7	638.7	638.7	638.7	638.7	638.7	638.7	638.7	638.7	638.7	638.7
120°	698.8	698.6	698.1	697.6	697.2	696.7	697.2	697.6	698.1	698.6	698.8
122.5°	755.8	755.6	755.1	754.7	754.2	753.8	754.2	754.7	755.1	755.6	755.8
125°	809.8	809.9	810.1	810.4	810.6	810.8	810.6	810.4	810.1	809.9	809.8
127.5°	861.8	861.7	861.4	861.2	860.9	860.7	860.9	861.2	861.4	861.7	861.8
130°	911.7	911.7	911.7	911.7	911.7	911.7	911.7	911.7	911.7	911.7	911.7
132.5°	959.5	959.4	959.2	958.9	958.7	958.5	958.7	958.9	959.2	959.4	959.5
135°	1003.3	1003.5	1004.0	1004.5	1004.9	1005.4	1004.9	1004.5	1004.0	1003.5	1003.3
137.5°	1046.1	1046.0	1045.8	1045.5	1045.3	1045.1	1045.3	1045.5	1045.8	1046.0	1046.1
140°	1085.9	1086.0	1086.2	1086.5	1086.7	1086.9	1086.7	1086.5	1086.2	1086.0	1085.9
142.5°	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5
145°	1155.1	1155.3	1155.8	1156.3	1156.7	1157.2	1156.7	1156.3	1155.8	1155.3	1155.1
147.5°	1185.7	1185.8	1186.0	1186.3	1186.5	1186.7	1186.5	1186.3	1186.0	1185.8	1185.7
150°	1214.2	1214.3	1214.5	1214.8	1215.0	1215.2	1215.0	1214.8	1214.5	1214.3	1214.2
152.5°	1240.7	1240.6	1240.4	1240.1	1239.9	1239.7	1239.9	1240.1	1240.4	1240.6	1240.7
155°	1264.1	1263.8	1263.1	1262.4	1261.8	1261.1	1261.8	1262.4	1263.1	1263.8	1264.1
157.5°	1284.5	1283.9	1282.8	1281.7	1280.5	1279.4	1280.5	1281.7	1282.8	1283.9	1284.5
160°	1303.8	1303.1	1301.8	1300.4	1299.1	1297.7	1299.1	1300.4	1301.8	1303.1	1303.8
162.5°	1319.1	1318.3	1316.7	1315.2	1313.6	1312.0	1313.6	1315.2	1316.7	1318.3	1319.1
165°	1334.4	1333.4	1331.3	1329.3	1327.2	1325.2	1327.2	1329.3	1331.3	1333.4	1334.4
167.5°	1345.6	1344.5	1342.2	1339.9	1337.7	1335.4	1337.7	1339.9	1342.2	1344.5	1345.6
170°	1354.8	1353.7	1351.4	1349.1	1346.9	1344.6	1346.9	1349.1	1351.4	1353.7	1354.8
172.5°	1360.9	1359.7	1357.2	1354.7	1352.2	1349.7	1352.2	1354.7	1357.2	1359.7	1360.9
175°	1366.0	1364.6	1361.9	1359.2	1356.4	1353.7	1356.4	1359.2	1361.9	1364.6	1366.0
177.5°	1368.0	1366.6	1363.9	1361.2	1358.5	1355.8	1358.5	1361.2	1363.9	1366.6	1368.0
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	872.0	876.7	872.0	875.1	876.7	880.5	882.0	888.9	891.3	896.6	896.6
5°	819.8	822.1	822.9	825.9	829.0	836.7	842.1	852.1	863.6	865.1	872.0
7.5°	777.5	781.4	787.5	785.2	790.6	802.1	809.0	821.3	832.9	839.0	847.5
10°	739.9	744.5	746.8	749.1	759.1	769.1	779.8	788.3	803.7	812.9	819.8
12.5°	709.2	705.3	709.9	718.4	729.9	736.1	750.7	763.7	775.2	785.2	791.4
15°	669.2	672.3	676.9	691.5	694.6	709.9	715.3	729.9	751.4	760.6	768.3
17.5°	630.8	640.8	650.0	655.4	664.6	676.9	692.3	708.4	722.2	733.0	742.2
20°	600.1	610.0	615.4	619.3	628.5	645.4	660.0	680.0	697.6	706.1	718.4
22.5°	575.5	575.5	583.2	594.7	600.1	616.2	628.5	650.0	669.2	680.0	691.5
25°	544.7	549.4	555.5	565.5	573.2	586.2	603.9	622.3	643.1	652.3	666.9
27.5°	519.4	524.8	533.2	535.5	543.2	554.7	573.2	593.1	614.7	624.6	636.9
30°	500.2	503.3	506.3	510.9	517.8	527.8	543.2	560.9	587.0	594.7	610.0
32.5°	483.3	484.8	486.3	490.2	494.0	504.0	516.3	535.5	557.0	568.6	582.4
35°	467.9	466.4	467.1	469.4	473.3	477.1	490.2	506.3	526.3	540.1	550.9
37.5°	453.3	450.2	449.5	449.5	451.0	455.6	465.6	479.4	500.9	512.5	523.2
40°	437.2	434.1	432.6	431.8	431.0	434.1	441.8	455.6	472.5	483.3	495.6
42.5°	421.8	418.7	414.9	414.1	412.6	414.1	419.5	432.6	447.2	457.9	467.9
45°	406.4	401.1	396.5	393.4	394.1	391.8	395.7	405.7	422.6	429.5	439.5
47.5°	389.5	383.4	377.2	374.2	371.1	372.6	374.2	382.6	397.2	404.1	414.1
50°	373.4	365.0	358.0	354.2	351.9	350.4	351.9	360.3	371.1	377.2	385.7
52.5°	355.0	346.5	339.6	333.5	330.4	328.1	328.8	336.5	346.5	352.7	361.1
55°	338.1	327.3	318.1	310.4	308.1	307.3	306.6	311.9	320.4	326.5	333.5
57.5°	318.9	308.1	298.1	288.9	284.3	283.5	283.5	285.0	295.8	300.4	304.3
60°	299.6	288.1	277.4	268.9	262.0	259.7	258.9	262.0	267.4	272.0	277.4
62.5°	278.1	266.6	253.5	245.9	238.9	232.8	235.1	235.9	243.6	245.9	250.5
65°	257.4	244.3	233.6	221.3	213.6	209.8	208.2	209.8	215.9	216.7	219.7
67.5°	233.6	221.3	208.2	199.8	192.8	185.9	184.4	184.4	187.5	189.8	193.6
70°	210.5	198.2	183.6	174.4	167.5	161.3	159.0	158.3	160.6	162.1	166.0
72.5°	183.6	171.3	160.6	150.6	142.1	137.5	135.2	133.7	136.0	137.5	138.3
75°	155.2	145.2	134.5	124.5	119.1	114.5	111.4	109.1	110.6	110.6	110.6
77.5°	128.3	118.3	109.9	103.0	96.0	90.7	88.4	86.1	86.8	86.8	88.4
80°	99.9	93.0	86.1	79.9	73.8	69.1	67.6	65.3	63.8	63.0	63.0
82.5°	73.8	68.4	62.2	56.9	53.8	49.2	47.6	44.6	44.6	43.8	43.8
85°	49.2	46.1	40.0	36.1	33.8	31.5	30.0	28.4	26.1	26.1	25.4
87.5°	26.1	24.6	23.0	18.4	18.4	16.1	15.4	14.6	12.3	13.1	13.1
90°	27.8	26.5	25.1	23.8	22.4	20.6	18.8	17.0	15.2	14.3	13.1
92.5°	26.8	25.5	24.1	22.8	21.4	19.6	17.8	15.9	14.1	13.2	13.4
95°	27.8	26.5	25.1	23.8	22.4	22.2	22.0	21.7	21.5	21.4	25.2
97.5°	26.9	25.8	24.7	23.5	22.4	46.2	70.0	93.7	117.5	129.4	126.9
100°	29.4	33.3	37.1	41.0	44.8	76.0	107.3	138.5	169.8	185.4	183.4
102.5°	55.0	105.9	156.8	207.8	258.7	256.0	253.3	250.6	247.9	246.5	245.1
105°	326.0	323.9	321.9	319.8	317.8	316.7	315.5	314.4	313.3	312.7	312.0
107.5°	387.5	386.4	385.3	384.1	383.0	381.4	379.8	378.3	376.7	375.9	375.6
110°	451.0	450.5	450.1	449.6	449.2	447.8	446.5	445.1	443.8	443.1	442.8

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	512.5	512.7	513.0	513.2	513.4	512.9	512.5	512.0	511.5	511.3	510.6
115°	576.3	575.8	575.4	574.9	574.5	574.7	574.9	575.2	575.4	575.5	575.2
117.5°	638.8	639.0	639.3	639.5	639.7	639.0	638.3	637.6	636.9	636.6	636.2
120°	698.6	698.1	697.6	697.2	696.7	696.9	697.2	697.4	697.7	697.8	697.3
122.5°	755.7	755.5	755.2	755.0	754.8	754.4	753.9	753.5	753.0	752.8	752.6
125°	809.5	808.8	808.1	807.4	806.7	807.2	807.6	808.1	808.6	808.8	808.3
127.5°	861.9	862.1	862.4	862.6	862.8	861.7	860.5	859.4	858.3	857.7	857.6
130°	911.6	911.3	911.1	910.8	910.6	909.9	909.3	908.6	907.9	907.6	907.5
132.5°	959.4	959.2	958.9	958.7	958.5	957.6	956.7	955.8	954.9	954.4	954.2
135°	1003.1	1002.6	1002.2	1001.7	1001.3	1000.4	999.5	998.6	997.7	997.2	997.3
137.5°	1045.9	1045.4	1045.0	1044.5	1044.1	1043.0	1041.8	1040.7	1039.6	1039.0	1039.0
140°	1085.6	1084.9	1084.2	1083.5	1082.8	1082.4	1081.9	1081.5	1081.0	1080.8	1080.6
142.5°	1121.3	1120.8	1120.4	1119.9	1119.5	1119.3	1119.0	1118.8	1118.5	1118.4	1118.0
145°	1155.0	1154.8	1154.5	1154.3	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1	1153.8
147.5°	1185.6	1185.4	1185.1	1184.9	1184.7	1184.9	1185.1	1185.4	1185.6	1185.7	1185.0
150°	1214.2	1214.2	1214.2	1214.2	1214.2	1214.4	1214.6	1214.9	1215.1	1215.2	1214.7
152.5°	1240.5	1240.0	1239.5	1239.1	1238.6	1239.1	1239.5	1240.0	1240.5	1240.7	1240.4
155°	1263.6	1262.7	1261.8	1260.9	1260.0	1260.7	1261.4	1262.1	1262.8	1263.1	1263.0
157.5°	1283.9	1282.8	1281.7	1280.5	1279.4	1280.3	1281.2	1282.1	1283.0	1283.5	1283.5
160°	1303.1	1301.8	1300.4	1299.1	1297.7	1297.9	1298.1	1298.4	1298.6	1298.7	1299.0
162.5°	1318.4	1317.1	1315.7	1314.4	1313.0	1313.2	1313.4	1313.7	1313.9	1314.0	1314.5
165°	1333.5	1331.7	1329.8	1328.0	1326.2	1326.2	1326.2	1326.2	1326.2	1326.2	1326.8
167.5°	1344.6	1342.5	1340.5	1338.4	1336.4	1336.6	1336.8	1337.1	1337.3	1337.4	1338.0
170°	1353.9	1352.1	1350.2	1348.4	1346.6	1346.4	1346.2	1345.9	1345.7	1345.6	1346.3
172.5°	1360.0	1358.2	1356.3	1354.5	1352.7	1352.5	1352.3	1352.0	1351.8	1351.7	1352.4
175°	1365.0	1362.9	1360.9	1358.8	1356.8	1356.6	1356.4	1356.1	1355.9	1355.8	1356.5
177.5°	1367.1	1365.3	1363.5	1361.7	1359.9	1359.4	1359.0	1358.5	1358.0	1357.8	1358.6
180°	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9	1361.9

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	927.4	927.4	927.4	927.4
2.5°	902.0	909.7	916.6	927.4
5°	882.0	892.8	907.4	923.5
7.5°	859.0	875.9	895.1	917.4
10°	837.5	856.7	881.3	908.2
12.5°	815.2	838.2	865.1	894.3
15°	789.8	812.9	842.9	882.0
17.5°	766.8	794.4	826.7	868.2
20°	739.9	766.0	801.4	849.0
22.5°	716.1	746.0	785.2	826.7
25°	690.0	716.1	755.3	805.2
27.5°	663.8	696.1	733.7	782.2
30°	638.5	665.4	706.1	756.8
32.5°	610.8	643.1	680.7	728.4
35°	580.9	611.6	646.9	698.4
37.5°	554.0	583.9	620.0	665.4
40°	524.0	555.5	588.5	633.9
42.5°	494.8	523.2	556.3	597.8
45°	466.4	491.0	520.9	557.0
47.5°	437.2	457.9	485.6	517.8
50°	405.7	428.0	448.7	475.6
52.5°	376.5	395.7	412.6	434.9
55°	348.1	361.1	374.9	391.8
57.5°	318.1	328.1	338.1	355.7
60°	288.1	297.3	302.7	314.2
62.5°	258.9	262.8	269.7	276.6
65°	226.7	232.0	235.9	244.3
67.5°	197.5	199.8	203.6	209.0
70°	166.7	172.1	173.6	177.5
72.5°	140.6	142.9	144.4	145.2
75°	111.4	113.7	115.2	119.9
77.5°	87.6	86.8	89.9	90.7
80°	64.5	62.2	63.0	66.1
82.5°	42.3	43.0	42.3	42.3
85°	26.1	25.4	23.8	24.6
87.5°	11.5	11.5	10.8	10.8
90°	10.6	8.1	5.6	3.1
92.5°	13.9	14.4	14.8	15.3
95°	32.9	40.6	48.3	56.0
97.5°	121.9	117.0	112.0	107.0
100°	179.3	175.2	171.2	167.1
102.5°	242.4	239.7	237.0	234.3
105°	310.7	309.3	308.0	306.6
107.5°	374.9	374.2	373.5	372.8
110°	442.1	441.4	440.7	440.0

TEST NUMBER: P1033530

CATALOG NUMBER: S124DIW-B575D1050UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	509.3	507.9	506.6	505.2
115°	574.5	573.8	573.2	572.5
117.5°	635.3	634.4	633.5	632.6
120°	696.4	695.5	694.6	693.7
122.5°	752.1	751.6	751.2	750.7
125°	807.4	806.5	805.6	804.7
127.5°	857.4	857.1	856.9	856.7
130°	907.3	907.0	906.8	906.6
132.5°	953.7	953.3	952.8	952.4
135°	997.5	997.8	998.0	998.2
137.5°	1039.0	1039.0	1039.0	1039.0
140°	1080.1	1079.6	1079.2	1078.7
142.5°	1117.1	1116.2	1115.3	1114.4
145°	1153.1	1152.4	1151.7	1151.0
147.5°	1183.7	1182.3	1181.0	1179.6
150°	1213.8	1212.9	1212.0	1211.1
152.5°	1239.7	1239.0	1238.3	1237.6
155°	1262.8	1262.5	1262.3	1262.1
157.5°	1283.5	1283.5	1283.5	1283.5
160°	1299.7	1300.4	1301.1	1301.8
162.5°	1315.4	1316.3	1317.2	1318.1
165°	1327.9	1329.0	1330.2	1331.3
167.5°	1339.1	1340.2	1341.4	1342.5
170°	1347.6	1349.0	1350.3	1351.7
172.5°	1353.7	1355.1	1356.4	1357.8
175°	1357.8	1359.2	1360.5	1361.9
177.5°	1360.2	1361.8	1363.4	1365.0
180°	1361.9	1361.9	1361.9	1361.9

(END OF REPORT)