

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033635

Luminaire Tested: S124DIW-B575D470UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033635
REPORT IS A COMBINATION OF REPORTS P997855 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D470UB40-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4452.0 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	72	85	78	73	68	68	64	60	59	56	53	50	48	46
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	42	39
4	76	66	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	33	40	34	29	35	30	26	30	26	24
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	25	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7583	7583	7583	7583
5°	7564	8699	7607	6536
10°	7507	10149	7565	5735
15°	7417	11701	7469	5132
20°	7321	12687	7374	4600
25°	7181	12542	7249	4209
30°	7044	10366	7130	4007
35°	6851	7725	6927	3884
40°	6627	5819	6692	3825
45°	6285	4670	6362	3744
50°	5875	3935	5960	3705
55°	5393	3425	5478	3661
60°	4926	3016	5069	3601
65°	4487	2595	4529	3451
70°	3971	2135	4056	3177
75°	3464	1640	3441	2700
80°	2727	1078	2694	2049
85°	1797	484	1681	1195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9805 cd/sqm

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	2.0
10°-20°	279.3	6.3
20°-30°	443.8	10.0
30°-40°	493.1	11.1
40°-50°	448.4	10.1
50°-60°	366.4	8.2
60°-70°	261.6	5.9
70°-80°	143.9	3.2
80°-90°	40.2	0.9
90°-100°	20.2	0.5
100°-110°	133.1	3.0
110°-120°	254.3	5.7
120°-130°	322.8	7.3
130°-140°	345.3	7.8
140°-150°	322.9	7.3
150°-160°	260.4	5.8
160°-170°	167.9	3.8
170°-180°	57.9	1.3
0°-30°	813.6	18.3
0°-40°	1306.7	29.4
0°-60°	2121.6	47.7
0°-90°	2567.3	57.7
90°-120°	407.6	9.2
90°-150°	1398.6	31.4
90°-180°	1885.0	42.3
0°-180°	4452.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	926	1091	931	820	926	88
15°	884	1498	891	657	884	250
25°	807	1591	815	534	807	372
35°	700	941	708	473	700	437
45°	559	528	566	423	559	431
55°	393	345	399	369	393	353
65°	245	222	247	295	245	242
75°	120	111	119	183	120	126
85°	25	23	23	57	25	29
90°	1	14	1	14	1	3
95°	25	13	25	13	25	31
105°	137	130	137	130	137	143
115°	256	258	256	258	256	252
125°	360	363	360	363	360	321
135°	446	450	446	450	446	344
145°	515	518	515	518	515	322
155°	564	564	564	564	564	260
165°	595	593	595	593	595	168
175°	609	605	609	605	609	58
180°	609	609	609	609	609	

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	929.9	939.1	943.0	946.1	956.1	959.2	959.9	964.6	968.4	969.2	969.2
5°	926.1	940.7	952.2	963.0	979.2	986.1	994.6	1003.9	1016.2	1023.9	1027.7
7.5°	919.9	941.5	959.2	977.7	1000.0	1013.9	1021.6	1046.2	1063.2	1077.1	1094.0
10°	910.6	938.4	963.8	990.8	1022.4	1039.3	1056.3	1086.3	1110.2	1137.1	1158.7
12.5°	896.8	933.0	963.8	1001.6	1040.8	1060.9	1080.9	1133.3	1161.0	1184.9	1223.4
15°	884.4	920.7	964.6	1003.1	1051.6	1081.7	1111.0	1144.9	1188.8	1240.4	1277.4
17.5°	870.6	916.0	956.9	1010.8	1064.7	1093.2	1117.1	1169.5	1231.1	1282.0	1315.9
20°	851.3	897.5	951.5	1008.5	1072.4	1094.8	1126.4	1196.5	1251.9	1302.0	1357.5
22.5°	829.0	882.9	939.9	994.6	1060.9	1107.9	1142.5	1204.2	1271.2	1329.0	1391.4
25°	807.4	866.0	916.0	990.8	1060.9	1092.5	1131.8	1204.9	1278.1	1348.2	1412.2
27.5°	784.3	839.0	906.8	966.1	1045.5	1080.1	1122.5	1202.6	1280.4	1350.6	1419.1
30°	758.9	817.4	873.7	943.8	1020.8	1065.5	1104.8	1191.8	1271.2	1344.4	1408.3
32.5°	730.4	785.8	845.9	912.2	993.1	1038.5	1087.8	1177.2	1262.0	1325.1	1374.4
35°	700.3	756.6	808.9	876.7	959.9	1005.4	1053.2	1151.8	1235.8	1287.4	1315.9
37.5°	667.2	720.3	772.0	839.0	922.2	970.7	1019.3	1114.8	1194.2	1237.3	1229.6
40°	635.6	683.4	731.1	794.3	881.4	933.0	975.4	1071.7	1141.0	1159.5	1134.1
42.5°	599.4	640.2	686.4	751.2	835.9	884.4	937.6	1025.4	1077.1	1069.3	1026.2
45°	558.6	594.8	641.0	701.9	788.1	838.2	882.9	966.1	1003.9	984.6	906.0
47.5°	519.3	554.7	592.5	653.3	737.3	779.7	825.1	899.9	921.4	880.6	802.0
50°	476.9	506.2	545.5	603.2	681.8	726.5	764.3	824.4	832.1	782.0	700.3
52.5°	436.1	460.7	498.5	555.5	628.7	664.1	701.1	754.2	748.1	696.5	617.9
55°	392.9	416.0	450.7	503.1	567.8	601.7	633.3	680.3	667.2	614.0	545.5
57.5°	356.7	372.9	406.8	455.3	508.5	545.5	572.4	609.4	589.4	536.2	472.3
60°	315.1	335.1	363.6	402.9	455.3	480.0	503.9	528.5	514.6	463.8	406.8
62.5°	277.4	292.8	317.4	355.2	396.0	418.3	443.8	459.2	445.3	398.3	350.5
65°	245.0	257.3	276.6	307.4	346.7	365.2	379.8	394.5	382.9	339.0	304.3
67.5°	209.6	220.3	236.5	261.2	294.3	307.4	321.3	331.3	318.2	288.9	255.0
70°	178.0	185.7	201.1	219.6	242.7	255.0	266.6	276.6	265.0	240.4	214.9
72.5°	145.6	151.8	165.6	178.7	199.5	208.0	216.5	224.2	220.3	197.2	176.4
75°	120.2	122.5	131.7	142.5	155.6	164.9	171.0	175.7	172.6	154.1	141.0
77.5°	90.9	94.0	100.9	109.4	121.0	126.3	130.2	134.8	131.0	116.3	107.1
80°	66.3	67.0	70.9	78.6	86.3	87.1	90.9	97.1	94.8	84.7	77.8
82.5°	42.4	44.7	46.2	50.8	56.2	57.8	60.1	61.6	60.9	54.7	52.4
85°	24.7	24.7	26.2	29.3	30.8	33.1	33.9	34.7	36.2	32.4	30.0
87.5°	10.8	11.6	11.6	12.3	13.9	13.9	14.6	15.4	16.2	15.4	13.1
90°	1.4	2.5	3.6	4.7	5.8	6.4	6.8	7.6	8.4	9.2	10.0
92.5°	6.8	6.6	6.4	6.2	6.0	5.9	6.3	7.1	8.0	8.8	9.6
95°	25.1	21.7	18.2	14.8	11.3	9.6	9.6	9.7	9.8	9.9	10.0
97.5°	47.8	50.0	52.3	54.5	56.8	57.9	52.6	41.9	31.3	20.6	10.0
100°	74.7	76.5	78.3	80.2	82.0	82.9	75.9	61.9	48.0	34.0	20.0
102.5°	104.8	106.0	107.2	108.4	109.6	110.2	110.8	112.0	113.3	114.5	115.7
105°	137.1	137.7	138.3	139.0	139.6	139.9	140.1	140.6	141.1	141.6	142.1
107.5°	166.7	167.0	167.3	167.6	167.9	168.1	168.5	169.2	169.9	170.6	171.3
110°	196.8	197.1	197.4	197.7	198.0	198.2	198.5	199.1	199.7	200.3	200.9

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	226.0	226.6	227.2	227.8	228.4	228.7	228.8	229.0	229.2	229.4	229.6
115°	256.0	256.3	256.6	256.9	257.2	257.4	257.3	257.2	257.1	257.0	256.9
117.5°	282.9	283.3	283.7	284.1	284.5	284.7	284.9	285.2	285.5	285.8	286.1
120°	310.2	310.6	311.0	311.5	311.9	312.1	312.0	311.9	311.8	311.7	311.6
122.5°	335.8	336.0	336.2	336.4	336.6	336.7	336.8	337.0	337.2	337.4	337.6
125°	359.9	360.3	360.7	361.1	361.5	361.7	361.6	361.4	361.2	361.0	360.8
127.5°	383.1	383.2	383.3	383.4	383.5	383.6	383.9	384.4	384.9	385.4	385.9
130°	405.5	405.6	405.7	405.8	405.9	405.9	406.1	406.4	406.7	407.0	407.3
132.5°	426.0	426.2	426.4	426.6	426.8	426.9	427.1	427.5	427.9	428.3	428.7
135°	446.5	446.4	446.3	446.2	446.1	446.0	446.2	446.6	447.0	447.4	447.8
137.5°	464.7	464.7	464.7	464.7	464.7	464.7	465.0	465.5	466.0	466.5	467.0
140°	482.4	482.6	482.8	483.1	483.3	483.4	483.5	483.7	483.9	484.1	484.3
142.5°	498.4	498.8	499.2	499.6	500.0	500.2	500.3	500.4	500.5	500.6	500.7
145°	514.8	515.1	515.4	515.7	516.0	516.2	516.2	516.2	516.2	516.2	516.2
147.5°	527.5	528.1	528.7	529.4	530.0	530.3	530.2	530.1	530.0	529.9	529.8
150°	541.7	542.1	542.5	542.9	543.3	543.5	543.4	543.3	543.2	543.1	543.0
152.5°	553.5	553.8	554.1	554.4	554.7	554.9	554.8	554.6	554.4	554.2	554.0
155°	564.4	564.5	564.6	564.7	564.8	564.9	564.7	564.4	564.1	563.8	563.5
157.5°	574.0	574.0	574.0	574.0	574.0	574.0	573.8	573.4	573.0	572.6	572.2
160°	582.2	581.9	581.6	581.3	581.0	580.8	580.8	580.7	580.6	580.5	580.4
162.5°	589.5	589.1	588.7	588.3	587.9	587.7	587.6	587.5	587.4	587.3	587.2
165°	595.4	594.9	594.4	593.9	593.4	593.1	593.1	593.1	593.1	593.1	593.1
167.5°	600.4	599.9	599.4	598.9	598.4	598.2	598.1	598.0	597.9	597.8	597.7
170°	604.5	603.9	603.3	602.7	602.1	601.8	601.9	602.0	602.1	602.2	602.3
172.5°	607.3	606.7	606.1	605.4	604.8	604.5	604.6	604.7	604.8	604.9	605.0
175°	609.1	608.5	607.9	607.3	606.7	606.4	606.4	606.5	606.6	606.7	606.8
177.5°	610.5	609.8	609.1	608.4	607.7	607.3	607.4	607.6	607.8	608.0	608.2
180°	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	971.5	985.4	991.5	993.1	1001.6	996.2	998.5	997.7	1003.9	1004.6	1004.6
5°	1042.4	1058.6	1064.0	1071.7	1083.2	1086.3	1084.0	1088.6	1097.1	1090.9	1100.2
7.5°	1117.1	1134.8	1147.2	1164.1	1168.0	1178.0	1184.1	1189.5	1191.1	1191.8	1193.4
10°	1186.5	1208.8	1225.7	1254.3	1260.4	1265.8	1292.8	1282.0	1295.9	1291.2	1292.8
12.5°	1242.7	1286.6	1300.5	1348.2	1352.9	1371.4	1369.8	1386.8	1389.8	1396.0	1389.8
15°	1316.7	1367.5	1389.8	1416.8	1432.2	1453.8	1457.6	1480.8	1490.0	1498.5	1490.0
17.5°	1384.5	1411.4	1468.4	1490.0	1500.0	1511.6	1540.8	1549.3	1563.2	1557.8	1573.2
20°	1418.4	1456.9	1517.0	1553.9	1569.4	1580.1	1604.8	1617.9	1623.3	1623.3	1624.8
22.5°	1448.4	1503.9	1548.6	1590.9	1604.8	1612.5	1627.1	1637.2	1639.5	1641.0	1642.5
25°	1475.4	1525.4	1561.7	1585.5	1590.9	1590.9	1599.4	1593.2	1583.2	1590.9	1595.6
27.5°	1475.4	1510.8	1527.0	1535.5	1535.5	1514.7	1502.3	1476.9	1455.3	1449.2	1463.0
30°	1450.7	1466.9	1444.5	1423.7	1407.6	1393.7	1345.2	1306.6	1298.9	1293.5	1314.3
32.5°	1393.7	1372.9	1329.0	1268.9	1245.0	1213.4	1175.7	1146.4	1128.7	1122.5	1117.9
35°	1292.8	1238.8	1181.8	1100.9	1084.0	1043.9	992.3	970.7	941.5	940.7	950.7
37.5°	1182.6	1099.4	1037.8	960.7	936.8	894.5	845.9	823.6	803.6	788.1	806.6
40°	1053.9	981.5	887.5	824.4	790.5	768.1	727.3	702.6	693.4	685.7	697.2
42.5°	933.8	854.4	781.2	716.5	688.8	663.3	636.4	612.5	605.6	604.8	613.3
45°	814.3	736.5	668.7	613.3	595.5	580.1	553.9	547.0	535.4	527.7	531.6
47.5°	718.8	638.7	582.4	540.1	524.7	511.6	494.6	483.1	473.0	470.0	474.6
50°	624.8	570.9	513.1	477.7	466.1	453.8	440.7	429.9	425.3	422.2	425.3
52.5°	549.3	491.5	452.2	423.7	412.2	402.9	393.7	389.1	382.9	384.4	387.5
55°	481.5	430.7	397.5	376.7	369.8	366.0	354.4	349.0	346.7	345.2	346.7
57.5°	417.6	380.6	355.9	338.2	329.0	326.7	317.4	317.4	315.1	312.8	313.6
60°	366.7	335.1	311.3	297.4	295.8	292.0	285.8	285.1	279.7	282.0	282.7
62.5°	315.1	289.7	273.5	265.0	259.6	258.1	254.2	253.5	251.2	251.9	250.4
65°	274.3	253.5	237.3	230.4	228.0	227.3	224.2	221.9	220.3	221.9	220.3
67.5°	233.4	219.6	207.2	200.3	197.2	196.5	194.1	192.6	193.4	191.1	192.6
70°	194.9	181.0	173.3	169.5	168.0	165.6	165.6	165.6	165.6	164.1	163.3
72.5°	164.1	150.2	144.8	142.5	141.0	140.2	137.9	138.7	137.9	137.1	140.2
75°	130.2	121.7	116.3	114.0	115.6	113.3	110.9	112.5	110.2	110.9	114.0
77.5°	98.6	94.8	91.7	90.1	88.6	87.1	87.1	85.5	85.5	85.5	85.5
80°	71.6	70.9	65.5	64.7	64.7	63.2	63.2	63.2	63.2	62.4	63.2
82.5°	47.8	47.0	45.5	44.7	43.1	43.9	43.9	42.4	42.4	41.6	42.4
85°	27.7	27.7	26.2	25.4	24.7	25.4	23.9	23.1	23.9	23.1	23.9
87.5°	13.1	11.6	12.3	11.6	10.0	10.8	9.2	10.0	9.2	8.5	10.0
90°	10.6	11.2	11.9	12.5	12.8	12.9	13.1	13.3	13.5	13.7	13.5
92.5°	10.2	10.8	11.4	12.0	12.3	12.3	12.3	12.3	12.3	12.3	12.3
95°	10.6	11.2	11.9	12.5	12.8	12.8	12.9	13.0	13.1	13.2	13.1
97.5°	10.5	11.0	11.5	12.0	12.3	12.4	12.5	12.6	12.7	12.8	12.7
100°	18.3	16.6	14.9	13.2	12.3	12.4	12.5	12.6	12.7	12.8	12.7
102.5°	92.9	70.1	47.4	24.6	13.2	13.2	13.2	13.2	13.2	13.2	13.2
105°	143.0	143.9	144.8	145.7	146.2	144.4	140.7	137.1	133.4	129.8	133.4
107.5°	171.8	172.3	172.8	173.3	173.6	173.8	174.2	174.6	175.0	175.4	175.0
110°	201.1	201.3	201.5	201.7	201.8	202.0	202.3	202.6	202.9	203.2	202.9

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	229.5	229.4	229.3	229.2	229.1	229.3	229.7	230.2	230.6	231.0	230.6
115°	257.1	257.3	257.6	257.8	257.9	257.9	257.9	257.9	257.9	257.9	257.9
117.5°	286.0	285.9	285.8	285.7	285.6	285.6	285.6	285.6	285.6	285.6	285.6
120°	311.8	312.0	312.2	312.4	312.5	312.4	312.2	312.0	311.8	311.6	311.8
122.5°	337.7	337.8	337.9	338.0	338.0	337.9	337.7	337.5	337.3	337.1	337.3
125°	361.1	361.4	361.7	362.0	362.2	362.2	362.3	362.4	362.5	362.6	362.5
127.5°	385.8	385.7	385.6	385.5	385.4	385.4	385.3	385.2	385.1	385.0	385.1
130°	407.4	407.5	407.6	407.7	407.7	407.7	407.7	407.7	407.7	407.7	407.7
132.5°	428.8	428.9	429.0	429.1	429.1	429.1	429.0	428.9	428.8	428.7	428.8
135°	448.0	448.2	448.4	448.6	448.7	448.8	449.0	449.2	449.4	449.6	449.4
137.5°	467.2	467.4	467.6	467.8	467.9	467.8	467.7	467.6	467.5	467.4	467.5
140°	484.6	484.9	485.2	485.5	485.6	485.7	485.8	485.9	486.0	486.1	486.0
142.5°	500.9	501.1	501.3	501.5	501.6	501.6	501.6	501.6	501.6	501.6	501.6
145°	516.3	516.4	516.5	516.6	516.6	516.7	516.9	517.1	517.3	517.5	517.3
147.5°	529.9	530.0	530.1	530.2	530.3	530.3	530.4	530.5	530.6	530.7	530.6
150°	543.0	543.0	543.0	543.0	543.0	543.1	543.2	543.3	543.4	543.5	543.4
152.5°	554.2	554.4	554.6	554.8	554.9	554.8	554.7	554.6	554.5	554.4	554.5
155°	563.9	564.3	564.8	565.2	565.4	565.2	564.9	564.6	564.3	564.0	564.3
157.5°	572.7	573.2	573.7	574.2	574.5	574.2	573.7	573.2	572.7	572.2	572.7
160°	581.0	581.6	582.2	582.8	583.1	582.8	582.2	581.6	581.0	580.4	581.0
162.5°	587.8	588.4	589.1	589.7	590.0	589.6	588.9	588.2	587.5	586.8	587.5
165°	593.9	594.7	595.6	596.4	596.8	596.3	595.4	594.5	593.6	592.7	593.6
167.5°	598.6	599.5	600.4	601.3	601.8	601.3	600.3	599.2	598.2	597.2	598.2
170°	603.1	603.9	604.7	605.5	605.9	605.4	604.4	603.3	602.3	601.3	602.3
172.5°	605.8	606.6	607.4	608.2	608.6	608.0	606.9	605.8	604.7	603.6	604.7
175°	607.7	608.6	609.5	610.4	610.9	610.3	609.1	607.8	606.6	605.4	606.6
177.5°	609.0	609.8	610.6	611.4	611.8	611.2	610.0	608.8	607.6	606.4	607.6
180°	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	1003.1	1000.8	997.7	997.7	993.8	993.8	987.7	976.9	967.7	964.6	966.1
5°	1088.6	1089.4	1084.8	1080.9	1074.0	1068.6	1058.6	1039.3	1033.1	1020.8	1012.3
7.5°	1186.5	1183.4	1174.9	1168.7	1167.2	1154.9	1133.3	1110.2	1091.7	1079.4	1061.6
10°	1296.6	1284.3	1272.0	1268.1	1258.9	1238.1	1213.4	1188.0	1162.6	1135.6	1105.6
12.5°	1389.1	1365.2	1364.4	1355.2	1337.5	1325.9	1296.6	1260.4	1216.5	1186.5	1152.6
15°	1488.5	1466.1	1447.6	1430.7	1422.2	1388.3	1363.7	1318.2	1265.8	1233.5	1210.3
17.5°	1559.3	1549.3	1517.7	1510.0	1498.5	1459.2	1419.9	1375.2	1329.8	1284.3	1221.9
20°	1616.4	1610.2	1589.4	1578.6	1560.1	1529.3	1481.5	1429.9	1377.5	1312.8	1254.3
22.5°	1641.0	1633.3	1616.4	1607.1	1595.6	1569.4	1528.5	1470.0	1401.4	1343.6	1281.2
25°	1592.5	1606.3	1601.7	1597.9	1593.2	1577.8	1547.0	1495.4	1428.4	1362.9	1285.1
27.5°	1483.1	1507.0	1530.1	1533.1	1540.8	1547.0	1534.7	1497.7	1441.5	1372.1	1286.6
30°	1335.9	1346.7	1393.7	1407.6	1418.4	1457.6	1480.8	1471.5	1428.4	1366.0	1287.4
32.5°	1147.2	1175.7	1223.4	1256.6	1285.8	1329.8	1389.8	1413.7	1398.3	1347.5	1269.7
35°	968.4	1002.3	1057.8	1100.2	1129.4	1191.8	1262.7	1314.3	1333.6	1308.2	1238.8
37.5°	822.0	862.9	912.2	928.4	962.3	1039.3	1137.1	1208.8	1255.8	1258.1	1204.2
40°	711.9	732.7	772.0	796.6	829.7	894.5	990.0	1084.8	1155.6	1179.5	1151.0
42.5°	618.7	634.8	664.1	694.2	724.2	773.5	861.3	949.9	1045.5	1093.2	1092.5
45°	544.7	561.6	581.7	606.3	627.1	680.3	749.6	840.5	923.0	996.9	1015.4
47.5°	480.0	494.6	519.3	530.1	543.9	594.0	654.1	738.8	824.4	909.1	930.7
50°	432.2	444.5	461.5	468.4	483.8	520.8	570.1	638.7	733.4	811.3	851.3
52.5°	389.1	398.3	411.4	416.8	427.6	455.3	500.0	553.9	632.5	712.6	768.9
55°	352.1	358.2	367.5	373.7	381.4	406.0	439.1	487.7	555.5	624.8	679.5
57.5°	317.4	322.0	331.3	334.4	340.5	359.8	382.9	423.7	486.1	547.8	600.9
60°	285.1	288.1	293.5	300.5	305.1	318.2	339.8	373.7	423.7	480.0	523.1
62.5°	254.2	258.9	260.4	263.5	267.3	279.7	296.6	321.3	365.2	411.4	456.9
65°	222.7	226.5	229.6	230.4	234.2	243.5	258.9	280.4	308.9	349.0	391.4
67.5°	193.4	195.7	197.2	200.3	204.2	208.8	221.1	237.3	263.5	295.8	329.7
70°	166.4	166.4	168.7	169.5	174.1	179.5	184.9	200.3	223.4	249.6	272.7
72.5°	137.1	141.0	140.2	144.1	143.3	147.2	154.1	164.1	181.0	201.9	224.2
75°	111.7	114.0	114.0	114.0	115.6	118.6	122.5	131.7	144.8	161.8	174.9
77.5°	87.1	88.6	88.6	88.6	89.4	92.5	96.3	102.5	111.7	121.7	129.4
80°	62.4	63.9	63.9	65.5	65.5	66.3	70.1	73.2	77.8	85.5	93.2
82.5°	42.4	43.1	44.7	44.7	43.9	45.5	46.2	49.3	53.9	55.5	60.9
85°	23.1	23.9	24.7	24.7	25.4	27.0	26.2	29.3	29.3	32.4	33.9
87.5°	9.2	10.8	10.8	10.0	10.8	10.8	10.8	12.3	13.1	13.9	13.1
90°	13.3	13.1	12.9	12.8	12.5	11.9	11.2	10.6	10.0	9.2	8.4
92.5°	12.3	12.3	12.3	12.3	12.0	11.4	10.8	10.2	9.6	8.8	8.0
95°	13.0	12.9	12.8	12.8	12.5	11.9	11.2	10.6	10.0	9.9	9.8
97.5°	12.6	12.5	12.4	12.3	12.0	11.5	11.0	10.5	10.0	20.6	31.3
100°	12.6	12.5	12.4	12.3	13.2	14.9	16.6	18.3	20.0	34.0	48.0
102.5°	13.2	13.2	13.2	13.2	24.6	47.4	70.1	92.9	115.7	114.5	113.3
105°	137.1	140.7	144.4	146.2	145.7	144.8	143.9	143.0	142.1	141.6	141.1
107.5°	174.6	174.2	173.8	173.6	173.3	172.8	172.3	171.8	171.3	170.6	169.9
110°	202.6	202.3	202.0	201.8	201.7	201.5	201.3	201.1	200.9	200.3	199.7

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	230.2	229.7	229.3	229.1	229.2	229.3	229.4	229.5	229.6	229.4	229.2
115°	257.9	257.9	257.9	257.9	257.8	257.6	257.3	257.1	256.9	257.0	257.1
117.5°	285.6	285.6	285.6	285.6	285.7	285.8	285.9	286.0	286.1	285.8	285.5
120°	312.0	312.2	312.4	312.5	312.4	312.2	312.0	311.8	311.6	311.7	311.8
122.5°	337.5	337.7	337.9	338.0	338.0	337.9	337.8	337.7	337.6	337.4	337.2
125°	362.4	362.3	362.2	362.2	362.0	361.7	361.4	361.1	360.8	361.0	361.2
127.5°	385.2	385.3	385.4	385.4	385.5	385.6	385.7	385.8	385.9	385.4	384.9
130°	407.7	407.7	407.7	407.7	407.7	407.6	407.5	407.4	407.3	407.0	406.7
132.5°	428.9	429.0	429.1	429.1	429.1	429.0	428.9	428.8	428.7	428.3	427.9
135°	449.2	449.0	448.8	448.7	448.6	448.4	448.2	448.0	447.8	447.4	447.0
137.5°	467.6	467.7	467.8	467.9	467.8	467.6	467.4	467.2	467.0	466.5	466.0
140°	485.9	485.8	485.7	485.6	485.5	485.2	484.9	484.6	484.3	484.1	483.9
142.5°	501.6	501.6	501.6	501.6	501.5	501.3	501.1	500.9	500.7	500.6	500.5
145°	517.1	516.9	516.7	516.6	516.6	516.5	516.4	516.3	516.2	516.2	516.2
147.5°	530.5	530.4	530.3	530.3	530.2	530.1	530.0	529.9	529.8	529.9	530.0
150°	543.3	543.2	543.1	543.0	543.0	543.0	543.0	543.0	543.0	543.1	543.2
152.5°	554.6	554.7	554.8	554.9	554.8	554.6	554.4	554.2	554.0	554.2	554.4
155°	564.6	564.9	565.2	565.4	565.2	564.8	564.3	563.9	563.5	563.8	564.1
157.5°	573.2	573.7	574.2	574.5	574.2	573.7	573.2	572.7	572.2	572.6	573.0
160°	581.6	582.2	582.8	583.1	582.8	582.2	581.6	581.0	580.4	580.5	580.6
162.5°	588.2	588.9	589.6	590.0	589.7	589.1	588.4	587.8	587.2	587.3	587.4
165°	594.5	595.4	596.3	596.8	596.4	595.6	594.7	593.9	593.1	593.1	593.1
167.5°	599.2	600.3	601.3	601.8	601.3	600.4	599.5	598.6	597.7	597.8	597.9
170°	603.3	604.4	605.4	605.9	605.5	604.7	603.9	603.1	602.3	602.2	602.1
172.5°	605.8	606.9	608.0	608.6	608.2	607.4	606.6	605.8	605.0	604.9	604.8
175°	607.8	609.1	610.3	610.9	610.4	609.5	608.6	607.7	606.8	606.7	606.6
177.5°	608.8	610.0	611.2	611.8	611.4	610.6	609.8	609.0	608.2	608.0	607.8
180°	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	959.2	956.1	953.8	953.8	946.9	939.9	936.1	934.5	933.0	926.8	918.3
5°	998.5	988.5	981.5	974.6	963.0	950.7	938.4	931.4	921.4	907.6	897.5
7.5°	1042.4	1018.5	1010.8	1002.3	979.2	958.4	941.5	926.8	910.6	892.9	875.2
10°	1079.4	1053.9	1037.0	1022.4	992.3	964.6	939.1	917.6	896.8	873.7	852.1
12.5°	1114.8	1078.6	1060.9	1039.3	1007.7	967.7	934.5	907.6	876.7	852.9	826.7
15°	1164.1	1103.2	1074.0	1060.1	1017.7	970.7	930.7	890.6	865.2	829.0	805.9
17.5°	1171.8	1122.5	1103.2	1067.8	1017.0	963.8	917.6	877.5	839.0	806.6	776.6
20°	1198.8	1134.1	1103.2	1080.9	1013.9	959.9	909.1	857.5	820.5	785.8	751.9
22.5°	1215.7	1142.5	1110.2	1074.7	1010.8	946.1	886.0	841.3	795.8	760.4	733.4
25°	1211.1	1137.9	1101.7	1068.6	990.8	926.1	872.1	815.1	772.7	734.2	698.8
27.5°	1208.8	1126.4	1087.8	1050.9	977.7	909.9	842.1	795.8	748.9	704.2	678.0
30°	1202.6	1111.7	1067.0	1027.0	950.7	879.8	822.0	768.1	721.1	680.3	645.6
32.5°	1181.8	1087.1	1043.9	1000.8	921.4	850.5	792.0	741.9	694.9	652.5	619.4
35°	1154.1	1057.8	1010.8	965.3	886.0	814.3	760.4	708.0	664.1	623.3	591.7
37.5°	1126.4	1023.9	980.0	927.6	854.4	779.7	724.2	677.2	636.4	594.0	559.3
40°	1086.3	983.8	935.3	890.6	805.1	735.0	684.1	641.8	601.7	561.6	532.4
42.5°	1031.6	939.9	889.8	840.5	760.4	691.1	641.8	604.0	566.3	533.1	500.8
45°	976.1	886.8	842.1	798.2	711.1	645.6	600.2	565.5	533.9	497.7	471.5
47.5°	909.1	833.6	788.9	745.8	663.3	597.8	556.2	523.9	494.6	464.6	439.9
50°	840.5	775.0	734.2	689.5	610.9	551.6	510.8	483.8	459.9	431.4	411.4
52.5°	766.6	709.6	674.9	631.7	562.4	507.7	466.1	439.1	419.1	398.3	380.6
55°	688.0	646.4	609.4	574.7	509.3	459.9	423.0	399.1	385.2	366.0	350.5
57.5°	617.1	577.0	554.7	515.4	458.4	409.9	380.6	360.6	344.4	332.8	320.5
60°	543.1	510.8	486.1	457.6	407.6	366.7	335.9	324.3	307.4	298.9	293.5
62.5°	472.3	449.2	426.0	404.5	359.8	321.3	298.2	283.5	273.5	265.0	260.4
65°	405.2	383.7	367.5	348.2	311.3	280.4	258.9	247.3	237.3	235.0	229.6
67.5°	339.8	330.5	312.8	297.4	265.8	241.9	225.7	211.1	205.7	203.4	198.8
70°	284.3	273.5	259.6	246.5	222.7	201.9	187.2	181.8	174.1	173.3	168.0
72.5°	234.2	221.1	211.1	201.1	183.4	164.9	157.2	149.5	145.6	142.5	140.2
75°	185.7	176.4	169.5	161.0	145.6	133.3	122.5	119.4	117.1	116.3	114.8
77.5°	138.7	132.5	129.4	121.0	110.2	99.4	94.8	90.1	90.1	88.6	89.4
80°	98.6	94.8	90.9	86.3	77.0	72.4	68.6	65.5	63.9	63.2	63.9
82.5°	62.4	60.1	59.3	56.2	50.1	47.8	44.7	42.4	42.4	42.4	42.4
85°	34.7	34.7	34.7	30.0	27.7	25.4	23.9	23.1	23.1	23.1	23.9
87.5°	14.6	14.6	12.3	12.3	11.6	10.0	9.2	9.2	10.0	10.0	10.8
90°	7.6	6.8	6.4	5.8	4.7	3.6	2.5	1.4	2.5	3.6	4.7
92.5°	7.1	6.3	5.9	6.0	6.2	6.4	6.6	6.8	6.6	6.4	6.2
95°	9.7	9.6	9.6	11.3	14.8	18.2	21.7	25.1	21.7	18.2	14.8
97.5°	41.9	52.6	57.9	56.8	54.5	52.3	50.0	47.8	50.0	52.3	54.5
100°	61.9	75.9	82.9	82.0	80.2	78.3	76.5	74.7	76.5	78.3	80.2
102.5°	112.0	110.8	110.2	109.6	108.4	107.2	106.0	104.8	106.0	107.2	108.4
105°	140.6	140.1	139.9	139.6	139.0	138.3	137.7	137.1	137.7	138.3	139.0
107.5°	169.2	168.5	168.1	167.9	167.6	167.3	167.0	166.7	167.0	167.3	167.6
110°	199.1	198.5	198.2	198.0	197.7	197.4	197.1	196.8	197.1	197.4	197.7

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	229.0	228.8	228.7	228.4	227.8	227.2	226.6	226.0	226.6	227.2	227.8
115°	257.2	257.3	257.4	257.2	256.9	256.6	256.3	256.0	256.3	256.6	256.9
117.5°	285.2	284.9	284.7	284.5	284.1	283.7	283.3	282.9	283.3	283.7	284.1
120°	311.9	312.0	312.1	311.9	311.5	311.0	310.6	310.2	310.6	311.0	311.5
122.5°	337.0	336.8	336.7	336.6	336.4	336.2	336.0	335.8	336.0	336.2	336.4
125°	361.4	361.6	361.7	361.5	361.1	360.7	360.3	359.9	360.3	360.7	361.1
127.5°	384.4	383.9	383.6	383.5	383.4	383.3	383.2	383.1	383.2	383.3	383.4
130°	406.4	406.1	405.9	405.9	405.8	405.7	405.6	405.5	405.6	405.7	405.8
132.5°	427.5	427.1	426.9	426.8	426.6	426.4	426.2	426.0	426.2	426.4	426.6
135°	446.6	446.2	446.0	446.1	446.2	446.3	446.4	446.5	446.4	446.3	446.2
137.5°	465.5	465.0	464.7	464.7	464.7	464.7	464.7	464.7	464.7	464.7	464.7
140°	483.7	483.5	483.4	483.3	483.1	482.8	482.6	482.4	482.6	482.8	483.1
142.5°	500.4	500.3	500.2	500.0	499.6	499.2	498.8	498.4	498.8	499.2	499.6
145°	516.2	516.2	516.2	516.0	515.7	515.4	515.1	514.8	515.1	515.4	515.7
147.5°	530.1	530.2	530.3	530.0	529.4	528.7	528.1	527.5	528.1	528.7	529.4
150°	543.3	543.4	543.5	543.3	542.9	542.5	542.1	541.7	542.1	542.5	542.9
152.5°	554.6	554.8	554.9	554.7	554.4	554.1	553.8	553.5	553.8	554.1	554.4
155°	564.4	564.7	564.9	564.8	564.7	564.6	564.5	564.4	564.5	564.6	564.7
157.5°	573.4	573.8	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0
160°	580.7	580.8	580.8	581.0	581.3	581.6	581.9	582.2	581.9	581.6	581.3
162.5°	587.5	587.6	587.7	587.9	588.3	588.7	589.1	589.5	589.1	588.7	588.3
165°	593.1	593.1	593.1	593.4	593.9	594.4	594.9	595.4	594.9	594.4	593.9
167.5°	598.0	598.1	598.2	598.4	598.9	599.4	599.9	600.4	599.9	599.4	598.9
170°	602.0	601.9	601.8	602.1	602.7	603.3	603.9	604.5	603.9	603.3	602.7
172.5°	604.7	604.6	604.5	604.8	605.4	606.1	606.7	607.3	606.7	606.1	605.4
175°	606.5	606.4	606.4	606.7	607.3	607.9	608.5	609.1	608.5	607.9	607.3
177.5°	607.6	607.4	607.3	607.7	608.4	609.1	609.8	610.5	609.8	609.1	608.4
180°	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	916.0	913.0	914.5	906.8	899.9	889.8	881.4	879.8	878.3	882.9	879.8
5°	889.8	886.0	882.1	872.9	859.0	850.5	838.2	837.5	832.8	825.9	827.4
7.5°	861.3	859.0	853.6	839.0	826.7	812.0	802.0	793.5	789.7	783.5	781.2
10°	838.2	829.7	825.1	808.9	794.3	778.9	765.8	759.6	752.7	747.3	743.5
12.5°	806.6	804.3	791.2	778.1	765.8	748.1	738.1	720.3	711.1	715.7	714.2
15°	785.8	775.0	772.0	753.5	732.7	721.1	702.6	691.1	687.2	680.3	671.8
17.5°	758.1	751.2	740.4	723.4	699.5	683.4	670.3	659.5	654.9	645.6	638.7
20°	731.9	720.3	711.9	696.5	673.4	652.5	636.4	629.4	617.9	610.2	606.3
22.5°	708.0	699.5	687.2	664.1	644.1	624.0	604.8	594.8	584.0	579.4	573.2
25°	678.7	664.9	656.4	631.0	609.4	593.2	575.5	562.4	556.2	548.5	547.0
27.5°	650.2	637.1	627.1	604.8	578.6	557.8	547.0	537.8	527.0	527.0	523.1
30°	621.7	612.5	597.1	575.5	550.9	530.8	518.5	510.0	506.2	503.1	502.3
32.5°	593.2	580.9	571.7	542.4	523.9	505.4	496.2	489.2	484.6	483.8	484.6
35°	564.0	550.1	540.8	514.6	496.2	479.2	475.4	469.2	466.9	466.1	470.0
37.5°	533.1	522.3	510.8	489.2	468.4	458.4	450.7	448.4	447.6	452.2	453.8
40°	504.6	495.4	484.6	461.5	446.1	435.3	431.4	429.1	432.2	436.8	439.1
42.5°	477.7	464.6	456.1	435.3	421.4	415.3	410.6	410.6	413.7	419.1	423.0
45°	449.2	439.1	430.7	412.2	399.9	392.9	392.1	392.9	396.8	400.6	405.2
47.5°	421.4	411.4	402.2	386.8	376.0	372.1	371.3	372.1	378.3	383.7	389.1
50°	396.0	385.2	376.7	362.1	353.6	349.0	349.8	353.6	358.2	366.0	372.9
52.5°	366.0	358.2	350.5	337.4	329.7	326.7	329.0	332.1	340.5	345.9	354.4
55°	336.7	329.7	323.6	313.6	307.4	305.1	306.6	311.3	318.2	327.4	337.4
57.5°	309.7	302.0	295.8	288.9	282.0	282.7	283.5	289.7	298.2	306.6	318.2
60°	279.7	275.0	269.6	261.2	258.1	258.1	260.4	267.3	275.0	288.9	298.9
62.5°	252.7	246.5	242.7	237.3	232.7	233.4	238.8	245.0	254.2	265.8	278.9
65°	225.0	218.0	214.9	210.3	208.8	209.6	213.4	222.7	232.7	242.7	255.0
67.5°	194.1	191.8	188.8	184.1	185.7	186.4	190.3	198.0	208.8	218.8	232.7
70°	168.0	163.3	162.6	158.7	158.7	161.0	168.7	174.1	184.1	194.9	209.6
72.5°	140.2	136.4	136.4	133.3	135.6	137.9	141.8	149.5	158.7	169.5	181.8
75°	111.7	110.2	111.7	110.2	110.2	114.0	118.6	124.8	134.8	146.4	156.4
77.5°	86.3	86.3	85.5	87.8	87.8	90.1	96.3	102.5	110.2	119.4	130.2
80°	63.2	63.2	63.2	65.5	67.8	67.8	71.6	79.4	86.3	92.5	102.5
82.5°	43.1	43.1	43.1	44.7	47.8	47.8	52.4	57.0	64.7	70.1	74.7
85°	26.2	26.2	25.4	27.0	27.7	30.0	33.9	37.0	40.8	45.5	50.1
87.5°	11.6	11.6	12.3	13.1	13.9	15.4	16.9	18.5	22.3	23.9	26.2
90°	5.8	6.4	6.8	7.6	8.4	9.2	10.0	10.6	11.2	11.9	12.5
92.5°	6.0	5.9	6.3	7.1	8.0	8.8	9.6	10.2	10.8	11.4	12.0
95°	11.3	9.6	9.6	9.7	9.8	9.9	10.0	10.6	11.2	11.9	12.5
97.5°	56.8	57.9	52.6	41.9	31.3	20.6	10.0	10.5	11.0	11.5	12.0
100°	82.0	82.9	75.9	61.9	48.0	34.0	20.0	18.3	16.6	14.9	13.2
102.5°	109.6	110.2	110.8	112.0	113.3	114.5	115.7	92.9	70.1	47.4	24.6
105°	139.6	139.9	140.1	140.6	141.1	141.6	142.1	143.0	143.9	144.8	145.7
107.5°	167.9	168.1	168.5	169.2	169.9	170.6	171.3	171.8	172.3	172.8	173.3
110°	198.0	198.2	198.5	199.1	199.7	200.3	200.9	201.1	201.3	201.5	201.7

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	228.4	228.7	228.8	229.0	229.2	229.4	229.6	229.5	229.4	229.3	229.2
115°	257.2	257.4	257.3	257.2	257.1	257.0	256.9	257.1	257.3	257.6	257.8
117.5°	284.5	284.7	284.9	285.2	285.5	285.8	286.1	286.0	285.9	285.8	285.7
120°	311.9	312.1	312.0	311.9	311.8	311.7	311.6	311.8	312.0	312.2	312.4
122.5°	336.6	336.7	336.8	337.0	337.2	337.4	337.6	337.7	337.8	337.9	338.0
125°	361.5	361.7	361.6	361.4	361.2	361.0	360.8	361.1	361.4	361.7	362.0
127.5°	383.5	383.6	383.9	384.4	384.9	385.4	385.9	385.8	385.7	385.6	385.5
130°	405.9	405.9	406.1	406.4	406.7	407.0	407.3	407.4	407.5	407.6	407.7
132.5°	426.8	426.9	427.1	427.5	427.9	428.3	428.7	428.8	428.9	429.0	429.1
135°	446.1	446.0	446.2	446.6	447.0	447.4	447.8	448.0	448.2	448.4	448.6
137.5°	464.7	464.7	465.0	465.5	466.0	466.5	467.0	467.2	467.4	467.6	467.8
140°	483.3	483.4	483.5	483.7	483.9	484.1	484.3	484.6	484.9	485.2	485.5
142.5°	500.0	500.2	500.3	500.4	500.5	500.6	500.7	500.9	501.1	501.3	501.5
145°	516.0	516.2	516.2	516.2	516.2	516.2	516.2	516.3	516.4	516.5	516.6
147.5°	530.0	530.3	530.2	530.1	530.0	529.9	529.8	529.9	530.0	530.1	530.2
150°	543.3	543.5	543.4	543.3	543.2	543.1	543.0	543.0	543.0	543.0	543.0
152.5°	554.7	554.9	554.8	554.6	554.4	554.2	554.0	554.2	554.4	554.6	554.8
155°	564.8	564.9	564.7	564.4	564.1	563.8	563.5	563.9	564.3	564.8	565.2
157.5°	574.0	574.0	573.8	573.4	573.0	572.6	572.2	572.7	573.2	573.7	574.2
160°	581.0	580.8	580.8	580.7	580.6	580.5	580.4	581.0	581.6	582.2	582.8
162.5°	587.9	587.7	587.6	587.5	587.4	587.3	587.2	587.8	588.4	589.1	589.7
165°	593.4	593.1	593.1	593.1	593.1	593.1	593.1	593.9	594.7	595.6	596.4
167.5°	598.4	598.2	598.1	598.0	597.9	597.8	597.7	598.6	599.5	600.4	601.3
170°	602.1	601.8	601.9	602.0	602.1	602.2	602.3	603.1	603.9	604.7	605.5
172.5°	604.8	604.5	604.6	604.7	604.8	604.9	605.0	605.8	606.6	607.4	608.2
175°	606.7	606.4	606.4	606.5	606.6	606.7	606.8	607.7	608.6	609.5	610.4
177.5°	607.7	607.3	607.4	607.6	607.8	608.0	608.2	609.0	609.8	610.6	611.4
180°	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	877.5	876.7	872.9	874.4	869.8	871.4	873.7	874.4	877.5	875.2	874.4
5°	823.6	822.0	819.7	817.4	816.7	819.7	814.3	815.9	817.4	819.7	822.8
7.5°	779.7	778.9	776.6	772.7	771.2	769.7	770.4	775.8	775.0	774.3	779.7
10°	739.6	740.4	735.8	735.0	730.4	729.6	730.4	731.9	734.2	737.3	738.1
12.5°	698.0	708.0	699.5	696.5	689.5	693.4	694.9	688.0	691.8	694.2	705.7
15°	671.8	667.2	661.8	661.8	658.7	657.2	653.3	658.7	661.8	666.4	664.9
17.5°	635.6	627.9	624.8	621.7	622.5	625.6	617.1	629.4	629.4	631.7	627.9
20°	604.0	597.8	594.0	592.5	590.1	588.6	587.8	590.9	595.5	597.1	600.9
22.5°	570.9	570.9	564.7	562.4	560.9	558.6	562.4	560.1	563.2	566.3	572.4
25°	543.1	543.1	540.8	537.8	535.4	533.9	536.2	535.4	537.8	541.6	543.1
27.5°	520.8	518.5	517.7	517.0	516.2	517.0	516.2	518.5	520.8	521.6	520.0
30°	501.5	499.2	500.0	500.0	500.8	500.0	499.2	501.5	502.3	500.8	501.5
32.5°	483.8	483.8	485.4	486.1	486.1	486.9	487.7	486.1	486.9	484.6	485.4
35°	469.2	470.7	472.3	473.0	473.8	473.0	474.6	473.8	472.3	470.7	470.0
37.5°	454.6	456.1	459.2	459.9	462.3	463.0	461.5	461.5	460.7	457.6	456.1
40°	439.1	440.7	444.5	446.8	448.4	450.7	449.2	449.2	446.1	443.0	440.7
42.5°	424.5	427.6	431.4	433.7	436.8	436.8	436.8	435.3	431.4	428.4	426.0
45°	409.9	410.6	416.0	419.9	423.0	423.0	423.0	420.7	418.3	412.2	409.1
47.5°	393.7	396.0	402.2	406.0	409.1	409.9	409.9	407.6	402.9	397.5	393.7
50°	376.0	379.8	386.8	392.1	396.0	397.5	395.2	393.7	388.3	382.1	377.5
52.5°	359.0	363.6	372.1	376.7	382.1	382.9	382.1	379.8	373.7	365.2	361.3
55°	342.1	345.9	355.2	362.9	367.5	369.0	367.5	363.6	355.9	347.5	343.6
57.5°	323.6	329.0	339.0	346.7	352.1	352.9	351.3	347.5	341.3	330.5	325.1
60°	304.3	311.3	321.3	329.0	335.9	336.7	335.1	329.7	322.0	311.3	306.6
62.5°	285.1	290.5	302.0	310.5	315.9	319.7	316.6	311.3	303.5	292.8	285.8
65°	262.7	270.4	280.4	288.1	294.3	295.1	293.5	288.9	280.4	268.9	263.5
67.5°	241.1	246.5	256.6	266.6	268.9	271.2	268.9	264.3	257.3	247.3	239.6
70°	214.9	219.6	231.9	238.8	241.9	244.2	242.7	238.1	231.9	222.7	216.5
72.5°	188.8	192.6	204.2	209.6	215.7	214.9	214.2	211.1	202.6	196.5	192.6
75°	161.0	165.6	173.3	180.3	182.6	182.6	182.6	180.3	174.9	164.9	161.0
77.5°	135.6	137.9	144.1	147.9	150.2	151.0	150.2	146.4	143.3	136.4	134.1
80°	104.0	110.2	114.8	115.6	118.6	118.6	118.6	117.1	114.0	107.1	106.3
82.5°	78.6	80.1	84.7	87.1	88.6	87.8	87.8	84.7	84.0	80.1	78.6
85°	53.2	55.5	54.7	57.8	58.6	57.0	57.0	58.6	54.7	55.5	53.2
87.5°	29.3	29.3	30.8	30.0	33.1	33.1	31.6	32.4	30.8	30.0	29.3
90°	12.8	12.9	13.1	13.3	13.5	13.7	13.5	13.3	13.1	12.9	12.8
92.5°	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
95°	12.8	12.8	12.9	13.0	13.1	13.2	13.1	13.0	12.9	12.8	12.8
97.5°	12.3	12.4	12.5	12.6	12.7	12.8	12.7	12.6	12.5	12.4	12.3
100°	12.3	12.4	12.5	12.6	12.7	12.8	12.7	12.6	12.5	12.4	12.3
102.5°	13.2	13.2	13.2	13.2	13.2	13.2	13.2	13.2	13.2	13.2	13.2
105°	146.2	144.4	140.7	137.1	133.4	129.8	133.4	137.1	140.7	144.4	146.2
107.5°	173.6	173.8	174.2	174.6	175.0	175.4	175.0	174.6	174.2	173.8	173.6
110°	201.8	202.0	202.3	202.6	202.9	203.2	202.9	202.6	202.3	202.0	201.8

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	229.1	229.3	229.7	230.2	230.6	231.0	230.6	230.2	229.7	229.3	229.1
115°	257.9	257.9	257.9	257.9	257.9	257.9	257.9	257.9	257.9	257.9	257.9
117.5°	285.6	285.6	285.6	285.6	285.6	285.6	285.6	285.6	285.6	285.6	285.6
120°	312.5	312.4	312.2	312.0	311.8	311.6	311.8	312.0	312.2	312.4	312.5
122.5°	338.0	337.9	337.7	337.5	337.3	337.1	337.3	337.5	337.7	337.9	338.0
125°	362.2	362.2	362.3	362.4	362.5	362.6	362.5	362.4	362.3	362.2	362.2
127.5°	385.4	385.4	385.3	385.2	385.1	385.0	385.1	385.2	385.3	385.4	385.4
130°	407.7	407.7	407.7	407.7	407.7	407.7	407.7	407.7	407.7	407.7	407.7
132.5°	429.1	429.1	429.0	428.9	428.8	428.7	428.8	428.9	429.0	429.1	429.1
135°	448.7	448.8	449.0	449.2	449.4	449.6	449.4	449.2	449.0	448.8	448.7
137.5°	467.9	467.8	467.7	467.6	467.5	467.4	467.5	467.6	467.7	467.8	467.9
140°	485.6	485.7	485.8	485.9	486.0	486.1	486.0	485.9	485.8	485.7	485.6
142.5°	501.6	501.6	501.6	501.6	501.6	501.6	501.6	501.6	501.6	501.6	501.6
145°	516.6	516.7	516.9	517.1	517.3	517.5	517.3	517.1	516.9	516.7	516.6
147.5°	530.3	530.3	530.4	530.5	530.6	530.7	530.6	530.5	530.4	530.3	530.3
150°	543.0	543.1	543.2	543.3	543.4	543.5	543.4	543.3	543.2	543.1	543.0
152.5°	554.9	554.8	554.7	554.6	554.5	554.4	554.5	554.6	554.7	554.8	554.9
155°	565.4	565.2	564.9	564.6	564.3	564.0	564.3	564.6	564.9	565.2	565.4
157.5°	574.5	574.2	573.7	573.2	572.7	572.2	572.7	573.2	573.7	574.2	574.5
160°	583.1	582.8	582.2	581.6	581.0	580.4	581.0	581.6	582.2	582.8	583.1
162.5°	590.0	589.6	588.9	588.2	587.5	586.8	587.5	588.2	588.9	589.6	590.0
165°	596.8	596.3	595.4	594.5	593.6	592.7	593.6	594.5	595.4	596.3	596.8
167.5°	601.8	601.3	600.3	599.2	598.2	597.2	598.2	599.2	600.3	601.3	601.8
170°	605.9	605.4	604.4	603.3	602.3	601.3	602.3	603.3	604.4	605.4	605.9
172.5°	608.6	608.0	606.9	605.8	604.7	603.6	604.7	605.8	606.9	608.0	608.6
175°	610.9	610.3	609.1	607.8	606.6	605.4	606.6	607.8	609.1	610.3	610.9
177.5°	611.8	611.2	610.0	608.8	607.6	606.4	607.6	608.8	610.0	611.2	611.8
180°	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	874.4	879.1	874.4	877.5	879.1	882.9	884.4	891.4	893.7	899.1	899.1
5°	822.0	824.4	825.1	828.2	831.3	839.0	844.4	854.4	866.0	867.5	874.4
7.5°	779.7	783.5	789.7	787.4	792.8	804.3	811.3	823.6	835.1	841.3	849.8
10°	741.9	746.5	748.9	751.2	761.2	771.2	782.0	790.5	805.9	815.1	822.0
12.5°	711.1	707.3	711.9	720.3	731.9	738.1	752.7	765.8	777.4	787.4	793.5
15°	671.0	674.1	678.7	693.4	696.5	711.9	717.3	731.9	753.5	762.7	770.4
17.5°	632.5	642.5	651.8	657.2	666.4	678.7	694.2	710.3	724.2	735.0	744.2
20°	601.7	611.7	617.1	621.0	630.2	647.2	661.8	681.8	699.5	708.0	720.3
22.5°	577.0	577.0	584.8	596.3	601.7	617.9	630.2	651.8	671.0	681.8	693.4
25°	546.2	550.9	557.0	567.0	574.7	587.8	605.6	624.0	644.8	654.1	668.7
27.5°	520.8	526.2	534.7	537.0	544.7	556.2	574.7	594.8	616.3	626.4	638.7
30°	501.5	504.6	507.7	512.3	519.3	529.3	544.7	562.4	588.6	596.3	611.7
32.5°	484.6	486.1	487.7	491.5	495.4	505.4	517.7	537.0	558.6	570.1	584.0
35°	469.2	467.6	468.4	470.7	474.6	478.4	491.5	507.7	527.7	541.6	552.4
37.5°	454.6	451.5	450.7	450.7	452.2	456.9	466.9	480.7	502.3	513.9	524.7
40°	438.4	435.3	433.7	433.0	432.2	435.3	443.0	456.9	473.8	484.6	496.9
42.5°	423.0	419.9	416.0	415.3	413.7	415.3	420.7	433.7	448.4	459.2	469.2
45°	407.6	402.2	397.5	394.5	395.2	392.9	396.8	406.8	423.7	430.7	440.7
47.5°	390.6	384.4	378.3	375.2	372.1	373.7	375.2	383.7	398.3	405.2	415.3
50°	374.4	366.0	359.0	355.2	352.9	351.3	352.9	361.3	372.1	378.3	386.8
52.5°	355.9	347.5	340.5	334.4	331.3	329.0	329.7	337.4	347.5	353.6	362.1
55°	339.0	328.2	319.0	311.3	308.9	308.2	307.4	312.8	321.3	327.4	334.4
57.5°	319.7	308.9	298.9	289.7	285.1	284.3	284.3	285.8	296.6	301.2	305.1
60°	300.5	288.9	278.1	269.6	262.7	260.4	259.6	262.7	268.1	272.7	278.1
62.5°	278.9	267.3	254.2	246.5	239.6	233.4	235.8	236.5	244.2	246.5	251.2
65°	258.1	245.0	234.2	221.9	214.2	210.3	208.8	210.3	216.5	217.3	220.3
67.5°	234.2	221.9	208.8	200.3	193.4	186.4	184.9	184.9	188.0	190.3	194.1
70°	211.1	198.8	184.1	174.9	168.0	161.8	159.5	158.7	161.0	162.6	166.4
72.5°	184.1	171.8	161.0	151.0	142.5	137.9	135.6	134.1	136.4	137.9	138.7
75°	155.6	145.6	134.8	124.8	119.4	114.8	111.7	109.4	110.9	110.9	110.9
77.5°	128.7	118.6	110.2	103.2	96.3	90.9	88.6	86.3	87.1	87.1	88.6
80°	100.2	93.2	86.3	80.1	74.0	69.3	67.8	65.5	63.9	63.2	63.2
82.5°	74.0	68.6	62.4	57.0	53.9	49.3	47.8	44.7	44.7	43.9	43.9
85°	49.3	46.2	40.1	36.2	33.9	31.6	30.0	28.5	26.2	26.2	25.4
87.5°	26.2	24.7	23.1	18.5	18.5	16.2	15.4	14.6	12.3	13.1	13.1
90°	12.5	11.9	11.2	10.6	10.0	9.2	8.4	7.6	6.8	6.4	5.8
92.5°	12.0	11.4	10.8	10.2	9.6	8.8	8.0	7.1	6.3	5.9	6.0
95°	12.5	11.9	11.2	10.6	10.0	9.9	9.8	9.7	9.6	9.6	11.3
97.5°	12.0	11.5	11.0	10.5	10.0	20.6	31.3	41.9	52.6	57.9	56.8
100°	13.2	14.9	16.6	18.3	20.0	34.0	48.0	61.9	75.9	82.9	82.0
102.5°	24.6	47.4	70.1	92.9	115.7	114.5	113.3	112.0	110.8	110.2	109.6
105°	145.7	144.8	143.9	143.0	142.1	141.6	141.1	140.6	140.1	139.9	139.6
107.5°	173.3	172.8	172.3	171.8	171.3	170.6	169.9	169.2	168.5	168.1	167.9
110°	201.7	201.5	201.3	201.1	200.9	200.3	199.7	199.1	198.5	198.2	198.0

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	229.2	229.3	229.4	229.5	229.6	229.4	229.2	229.0	228.8	228.7	228.4
115°	257.8	257.6	257.3	257.1	256.9	257.0	257.1	257.2	257.3	257.4	257.2
117.5°	285.7	285.8	285.9	286.0	286.1	285.8	285.5	285.2	284.9	284.7	284.5
120°	312.4	312.2	312.0	311.8	311.6	311.7	311.8	311.9	312.0	312.1	311.9
122.5°	338.0	337.9	337.8	337.7	337.6	337.4	337.2	337.0	336.8	336.7	336.6
125°	362.0	361.7	361.4	361.1	360.8	361.0	361.2	361.4	361.6	361.7	361.5
127.5°	385.5	385.6	385.7	385.8	385.9	385.4	384.9	384.4	383.9	383.6	383.5
130°	407.7	407.6	407.5	407.4	407.3	407.0	406.7	406.4	406.1	405.9	405.9
132.5°	429.1	429.0	428.9	428.8	428.7	428.3	427.9	427.5	427.1	426.9	426.8
135°	448.6	448.4	448.2	448.0	447.8	447.4	447.0	446.6	446.2	446.0	446.1
137.5°	467.8	467.6	467.4	467.2	467.0	466.5	466.0	465.5	465.0	464.7	464.7
140°	485.5	485.2	484.9	484.6	484.3	484.1	483.9	483.7	483.5	483.4	483.3
142.5°	501.5	501.3	501.1	500.9	500.7	500.6	500.5	500.4	500.3	500.2	500.0
145°	516.6	516.5	516.4	516.3	516.2	516.2	516.2	516.2	516.2	516.2	516.0
147.5°	530.2	530.1	530.0	529.9	529.8	529.9	530.0	530.1	530.2	530.3	530.0
150°	543.0	543.0	543.0	543.0	543.0	543.1	543.2	543.3	543.4	543.5	543.3
152.5°	554.8	554.6	554.4	554.2	554.0	554.2	554.4	554.6	554.8	554.9	554.7
155°	565.2	564.8	564.3	563.9	563.5	563.8	564.1	564.4	564.7	564.9	564.8
157.5°	574.2	573.7	573.2	572.7	572.2	572.6	573.0	573.4	573.8	574.0	574.0
160°	582.8	582.2	581.6	581.0	580.4	580.5	580.6	580.7	580.8	580.8	581.0
162.5°	589.7	589.1	588.4	587.8	587.2	587.3	587.4	587.5	587.6	587.7	587.9
165°	596.4	595.6	594.7	593.9	593.1	593.1	593.1	593.1	593.1	593.1	593.4
167.5°	601.3	600.4	599.5	598.6	597.7	597.8	597.9	598.0	598.1	598.2	598.4
170°	605.5	604.7	603.9	603.1	602.3	602.2	602.1	602.0	601.9	601.8	602.1
172.5°	608.2	607.4	606.6	605.8	605.0	604.9	604.8	604.7	604.6	604.5	604.8
175°	610.4	609.5	608.6	607.7	606.8	606.7	606.6	606.5	606.4	606.4	606.7
177.5°	611.4	610.6	609.8	609.0	608.2	608.0	607.8	607.6	607.4	607.3	607.7
180°	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1	609.1

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	929.9	929.9	929.9	929.9
2.5°	904.5	912.2	919.1	929.9
5°	884.4	895.2	909.9	926.1
7.5°	861.3	878.3	897.5	919.9
10°	839.8	859.0	883.7	910.6
12.5°	817.4	840.5	867.5	896.8
15°	792.0	815.1	845.2	884.4
17.5°	768.9	796.6	829.0	870.6
20°	741.9	768.1	803.6	851.3
22.5°	718.0	748.1	787.4	829.0
25°	691.8	718.0	757.3	807.4
27.5°	665.6	698.0	735.8	784.3
30°	640.2	667.2	708.0	758.9
32.5°	612.5	644.8	682.6	730.4
35°	582.4	613.3	648.7	700.3
37.5°	555.5	585.5	621.7	667.2
40°	525.4	557.0	590.1	635.6
42.5°	496.2	524.7	557.8	599.4
45°	467.6	492.3	522.3	558.6
47.5°	438.4	459.2	486.9	519.3
50°	406.8	429.1	449.9	476.9
52.5°	377.5	396.8	413.7	436.1
55°	349.0	362.1	376.0	392.9
57.5°	319.0	329.0	339.0	356.7
60°	288.9	298.2	303.5	315.1
62.5°	259.6	263.5	270.4	277.4
65°	227.3	232.7	236.5	245.0
67.5°	198.0	200.3	204.2	209.6
70°	167.2	172.6	174.1	178.0
72.5°	141.0	143.3	144.8	145.6
75°	111.7	114.0	115.6	120.2
77.5°	87.8	87.1	90.1	90.9
80°	64.7	62.4	63.2	66.3
82.5°	42.4	43.1	42.4	42.4
85°	26.2	25.4	23.9	24.7
87.5°	11.6	11.6	10.8	10.8
90°	4.7	3.6	2.5	1.4
92.5°	6.2	6.4	6.6	6.8
95°	14.8	18.2	21.7	25.1
97.5°	54.5	52.3	50.0	47.8
100°	80.2	78.3	76.5	74.7
102.5°	108.4	107.2	106.0	104.8
105°	139.0	138.3	137.7	137.1
107.5°	167.6	167.3	167.0	166.7
110°	197.7	197.4	197.1	196.8

TEST NUMBER: P1033635

CATALOG NUMBER: S124DIW-B575D470UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	227.8	227.2	226.6	226.0
115°	256.9	256.6	256.3	256.0
117.5°	284.1	283.7	283.3	282.9
120°	311.5	311.0	310.6	310.2
122.5°	336.4	336.2	336.0	335.8
125°	361.1	360.7	360.3	359.9
127.5°	383.4	383.3	383.2	383.1
130°	405.8	405.7	405.6	405.5
132.5°	426.6	426.4	426.2	426.0
135°	446.2	446.3	446.4	446.5
137.5°	464.7	464.7	464.7	464.7
140°	483.1	482.8	482.6	482.4
142.5°	499.6	499.2	498.8	498.4
145°	515.7	515.4	515.1	514.8
147.5°	529.4	528.7	528.1	527.5
150°	542.9	542.5	542.1	541.7
152.5°	554.4	554.1	553.8	553.5
155°	564.7	564.6	564.5	564.4
157.5°	574.0	574.0	574.0	574.0
160°	581.3	581.6	581.9	582.2
162.5°	588.3	588.7	589.1	589.5
165°	593.9	594.4	594.9	595.4
167.5°	598.9	599.4	599.9	600.4
170°	602.7	603.3	603.9	604.5
172.5°	605.4	606.1	606.7	607.3
175°	607.3	607.9	608.5	609.1
177.5°	608.4	609.1	609.8	610.5
180°	609.1	609.1	609.1	609.1

(END OF REPORT)