

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033660

Luminaire Tested: S124DIW-B575D770UB35-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033660
REPORT IS A COMBINATION OF REPORTS P997913 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D770UB35-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5314.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49		
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42		
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	41	40	35		
3	81	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30		
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26		
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23		
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23	20		
7	58	46	38	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18		
8	54	42	34	29	50	39	32	28	34	28	24	29	24	21	24	21	18	16		
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14		
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	21	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7660	7660	7660	7660
5°	7640	8788	7685	6603
10°	7584	10252	7641	5793
15°	7492	11819	7544	5183
20°	7395	12816	7449	4647
25°	7254	12669	7323	4252
30°	7116	10472	7202	4048
35°	6921	7803	6997	3924
40°	6694	5878	6759	3864
45°	6348	4718	6427	3781
50°	5934	3975	6020	3743
55°	5448	3459	5533	3699
60°	4976	3046	5121	3637
65°	4533	2621	4575	3486
70°	4011	2157	4098	3210
75°	3498	1657	3475	2726
80°	2751	1088	2719	2069
85°	1812	488	1696	1207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9904 cd/sqm

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.7
10°-20°	282.2	5.3
20°-30°	448.3	8.4
30°-40°	498.1	9.4
40°-50°	453.0	8.5
50°-60°	370.2	7.0
60°-70°	264.2	5.0
70°-80°	145.4	2.7
80°-90°	41.4	0.8
90°-100°	63.9	1.2
100°-110°	191.4	3.6
110°-120°	325.1	6.1
120°-130°	428.8	8.1
130°-140°	481.6	9.1
140°-150°	473.3	8.9
150°-160°	398.1	7.5
160°-170°	264.9	5.0
170°-180°	92.8	1.7
0°-30°	821.9	15.5
0°-40°	1320.0	24.8
0°-60°	2143.1	40.3
0°-90°	2594.1	48.8
90°-120°	580.4	10.9
90°-150°	1964.1	37.0
90°-180°	2720.0	51.2
0°-180°	5314.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	939	939	939	939	939	
5°	935	1102	941	828	935	89
15°	893	1514	900	664	893	252
25°	816	1607	823	539	816	376
35°	707	950	715	478	707	442
45°	564	533	571	427	564	435
55°	397	349	403	373	397	357
65°	248	224	250	298	248	244
75°	121	112	121	184	121	127
85°	25	23	23	58	25	29
90°	2	23	2	23	2	5
95°	46	60	46	60	46	49
105°	177	185	177	185	177	187
115°	330	328	330	328	330	326
125°	481	478	481	478	481	429
135°	621	622	621	622	621	480
145°	754	755	754	755	754	472
155°	864	864	864	864	864	398
165°	941	939	941	939	941	265
175°	979	974	979	974	979	93
180°	980	980	980	980	980	

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	939.3	948.7	952.6	955.7	965.8	968.9	969.7	974.3	978.2	979.0	979.0
5°	935.4	950.2	961.9	972.8	989.1	996.1	1004.7	1014.0	1026.5	1034.3	1038.2
7.5°	929.2	951.0	968.9	987.6	1010.1	1024.2	1031.9	1056.8	1074.0	1088.0	1105.1
10°	919.9	947.9	973.6	1000.8	1032.7	1049.8	1067.0	1097.3	1121.4	1148.7	1170.5
12.5°	905.9	942.4	973.6	1011.7	1051.4	1071.6	1091.9	1144.8	1172.8	1196.9	1235.8
15°	893.4	930.0	974.3	1013.3	1062.3	1092.6	1122.2	1156.5	1200.8	1253.0	1290.3
17.5°	879.4	925.3	966.6	1021.0	1075.5	1104.3	1128.4	1181.4	1243.6	1295.0	1329.2
20°	859.9	906.6	961.1	1018.7	1083.3	1105.9	1137.8	1208.6	1264.6	1315.2	1371.2
22.5°	837.4	891.9	949.4	1004.7	1071.6	1119.1	1154.1	1216.4	1284.1	1342.4	1405.5
25°	815.6	874.7	925.3	1000.8	1071.6	1103.5	1143.2	1217.2	1291.1	1361.9	1426.5
27.5°	792.2	847.5	916.0	975.9	1056.1	1091.1	1133.9	1214.8	1293.4	1364.2	1433.5
30°	766.6	825.7	882.5	953.3	1031.2	1076.3	1116.0	1203.9	1284.1	1358.0	1422.6
32.5°	737.8	793.8	854.5	921.4	1003.1	1049.1	1098.9	1189.1	1274.7	1338.6	1388.4
35°	707.4	764.2	817.1	885.6	969.7	1015.6	1063.8	1163.5	1248.3	1300.4	1329.2
37.5°	673.9	727.6	779.8	847.5	931.5	980.6	1029.6	1126.1	1206.3	1249.8	1242.1
40°	642.0	690.3	738.5	802.4	890.3	942.4	985.2	1082.5	1152.6	1171.2	1145.6
42.5°	605.5	646.7	693.4	758.8	844.4	893.4	947.1	1035.8	1088.0	1080.2	1036.6
45°	564.2	600.8	647.5	709.0	796.1	846.7	891.9	975.9	1014.0	994.6	915.2
47.5°	524.5	560.3	598.5	659.9	744.8	787.6	833.5	909.0	930.8	889.5	810.1
50°	481.7	511.3	551.0	609.4	688.7	733.9	772.0	832.7	840.5	789.9	707.4
52.5°	440.5	465.4	503.5	561.1	635.0	670.8	708.2	761.9	755.7	703.5	624.1
55°	396.9	420.2	455.3	508.2	573.6	607.8	639.7	687.2	673.9	620.3	551.0
57.5°	360.3	376.7	410.9	459.9	513.6	551.0	578.2	615.6	595.3	541.6	477.1
60°	318.3	338.5	367.3	407.0	459.9	484.8	509.0	533.9	519.9	468.5	410.9
62.5°	280.2	295.7	320.6	358.8	400.0	422.6	448.3	463.8	449.8	402.3	354.1
65°	247.5	259.9	279.4	310.5	350.2	368.9	383.7	398.5	386.8	342.4	307.4
67.5°	211.7	222.6	238.9	263.8	297.3	310.5	324.5	334.6	321.4	291.8	257.6
70°	179.8	187.6	203.1	221.8	245.1	257.6	269.3	279.4	267.7	242.8	217.1
72.5°	147.1	153.3	167.3	180.5	201.6	210.1	218.7	226.5	222.6	199.2	178.2
75°	121.4	123.7	133.1	144.0	157.2	166.5	172.8	177.4	174.3	155.6	142.4
77.5°	91.8	94.9	101.9	110.5	122.2	127.6	131.5	136.2	132.3	117.5	108.2
80°	66.9	67.7	71.6	79.4	87.2	87.9	91.8	98.1	95.7	85.6	78.6
82.5°	42.8	45.1	46.7	51.4	56.8	58.4	60.7	62.3	61.5	55.3	52.9
85°	24.9	24.9	26.5	29.6	31.1	33.5	34.2	35.0	36.6	32.7	30.4
87.5°	10.9	11.7	11.7	12.5	14.0	14.0	14.8	15.6	16.3	15.6	13.2
90°	2.3	4.1	6.0	7.8	9.7	10.6	11.3	12.6	14.0	15.3	16.7
92.5°	19.7	21.9	24.1	26.3	28.5	29.6	30.0	30.9	31.7	32.6	33.4
95°	45.5	47.0	48.5	50.0	51.5	52.3	52.9	54.1	55.2	56.4	57.6
97.5°	72.8	74.1	75.5	76.8	78.1	78.8	79.5	80.8	82.2	83.5	84.9
100°	106.1	106.8	107.5	108.2	108.9	109.2	110.0	111.5	113.0	114.5	116.0
102.5°	141.0	141.2	141.4	141.5	141.7	141.8	142.5	143.8	145.1	146.5	147.8
105°	176.6	176.8	177.0	177.1	177.3	177.4	177.7	178.4	179.1	179.7	180.4
107.5°	213.8	214.0	214.2	214.3	214.5	214.6	214.7	214.8	215.0	215.1	215.3
110°	251.7	252.0	252.4	252.7	253.0	253.2	253.1	253.0	252.8	252.7	252.5

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	291.1	291.1	291.1	291.1	291.1	291.1	290.9	290.6	290.3	289.9	289.6
115°	330.5	330.5	330.5	330.5	330.5	330.5	330.3	330.0	329.7	329.3	329.0
117.5°	367.7	367.7	367.7	367.7	367.7	367.7	367.6	367.4	367.3	367.1	366.9
120°	404.8	405.5	406.2	406.9	407.6	407.9	407.6	407.1	406.6	406.1	405.6
122.5°	443.5	443.7	443.9	444.0	444.2	444.3	444.2	444.0	443.9	443.7	443.5
125°	481.4	481.4	481.4	481.4	481.4	481.4	481.3	481.2	481.0	480.9	480.7
127.5°	515.5	516.0	516.5	517.0	517.5	517.8	517.6	517.3	517.0	516.6	516.3
130°	551.9	552.4	552.9	553.4	553.9	554.2	554.2	554.2	554.2	554.2	554.2
132.5°	589.1	589.4	589.8	590.1	590.4	590.6	590.5	590.3	590.2	590.0	589.8
135°	620.9	621.9	622.9	624.0	625.0	625.5	625.5	625.5	625.5	625.5	625.5
137.5°	656.5	657.0	657.5	658.0	658.5	658.8	659.0	659.3	659.6	660.0	660.3
140°	692.2	692.5	692.9	693.2	693.5	693.7	693.7	693.7	693.7	693.7	693.7
142.5°	724.8	725.1	725.5	725.8	726.1	726.3	726.2	726.0	725.9	725.7	725.5
145°	754.3	755.0	755.7	756.4	757.1	757.4	757.5	757.6	757.8	757.9	758.1
147.5°	784.7	785.5	786.4	787.2	788.1	788.5	788.4	788.2	788.1	787.9	787.7
150°	812.0	812.7	813.3	814.0	814.7	815.0	815.0	815.0	815.0	815.0	815.0
152.5°	837.7	838.1	838.4	838.8	839.1	839.3	839.4	839.5	839.7	839.8	840.0
155°	864.3	864.3	864.3	864.3	864.3	864.3	864.2	864.0	863.9	863.7	863.5
157.5°	887.0	886.7	886.3	886.0	885.7	885.5	885.5	885.5	885.5	885.5	885.5
160°	906.7	906.5	906.4	906.2	906.1	906.0	905.9	905.7	905.6	905.4	905.2
162.5°	924.9	924.4	923.9	923.4	922.9	922.7	922.6	922.4	922.3	922.1	921.9
165°	940.9	940.4	939.9	939.4	938.9	938.6	938.4	938.1	937.8	937.4	937.1
167.5°	953.7	953.0	952.4	951.7	951.0	950.7	950.7	950.7	950.7	950.7	950.7
170°	964.4	963.6	962.7	961.9	961.0	960.6	960.7	960.8	961.0	961.1	961.3
172.5°	971.9	971.2	970.6	969.9	969.2	968.9	968.9	968.9	968.9	968.9	968.9
175°	978.8	978.0	977.1	976.3	975.4	975.0	974.9	974.7	974.6	974.4	974.2
177.5°	981.8	981.0	980.1	979.3	978.4	978.0	978.0	978.0	978.0	978.0	978.0
180°	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	981.3	995.4	1001.6	1003.1	1011.7	1006.3	1008.6	1007.8	1014.0	1014.8	1014.8
5°	1052.9	1069.3	1074.7	1082.5	1094.2	1097.3	1095.0	1099.6	1108.2	1102.0	1111.3
7.5°	1128.4	1146.3	1158.8	1175.9	1179.8	1189.9	1196.1	1201.6	1203.1	1203.9	1205.5
10°	1198.5	1221.0	1238.2	1267.0	1273.2	1278.6	1305.9	1295.0	1309.0	1304.3	1305.9
12.5°	1255.3	1299.6	1313.7	1361.9	1366.6	1385.3	1383.7	1400.8	1403.9	1410.2	1403.9
15°	1330.0	1381.4	1403.9	1431.2	1446.7	1468.5	1472.4	1495.8	1505.1	1513.7	1505.1
17.5°	1398.5	1425.7	1483.3	1505.1	1515.2	1526.9	1556.5	1565.0	1579.0	1573.6	1589.1
20°	1432.7	1471.6	1532.3	1569.7	1585.3	1596.2	1621.1	1634.3	1639.7	1639.7	1641.3
22.5°	1463.1	1519.1	1564.2	1607.0	1621.1	1628.8	1643.6	1653.7	1656.1	1657.6	1659.2
25°	1490.3	1540.9	1577.5	1601.6	1607.0	1607.0	1615.6	1609.4	1599.3	1607.0	1611.7
27.5°	1490.3	1526.1	1542.5	1551.0	1551.0	1530.0	1517.6	1491.9	1470.1	1463.9	1477.9
30°	1465.4	1481.8	1459.2	1438.2	1421.8	1407.8	1358.8	1319.9	1312.1	1306.7	1327.7
32.5°	1407.8	1386.8	1342.4	1281.7	1257.6	1225.7	1187.6	1158.0	1140.1	1133.9	1129.2
35°	1305.9	1251.4	1193.8	1112.1	1095.0	1054.5	1002.4	980.6	951.0	950.2	960.3
37.5°	1194.6	1110.5	1048.3	970.5	946.3	903.5	854.5	831.9	811.7	796.1	814.8
40°	1064.6	991.5	896.5	832.7	798.5	775.9	734.7	709.7	700.4	692.6	704.3
42.5°	943.2	863.1	789.1	723.8	695.7	670.1	642.8	618.7	611.7	610.9	619.5
45°	822.6	744.0	675.5	619.5	601.6	586.0	559.5	552.5	540.9	533.1	537.0
47.5°	726.1	645.2	588.3	545.5	530.0	516.7	499.6	488.0	477.8	474.7	479.4
50°	631.1	576.7	518.3	482.5	470.8	458.4	445.1	434.3	429.6	426.5	429.6
52.5°	554.9	496.5	456.8	428.0	416.4	407.0	397.7	393.0	386.8	388.3	391.5
55°	486.4	435.0	401.6	380.6	373.6	369.7	358.0	352.5	350.2	348.6	350.2
57.5°	421.8	384.4	359.5	341.6	332.3	330.0	320.6	320.6	318.3	316.0	316.7
60°	370.4	338.5	314.4	300.4	298.8	294.9	288.7	287.9	282.5	284.8	285.6
62.5°	318.3	292.6	276.3	267.7	262.3	260.7	256.8	256.0	253.7	254.5	252.9
65°	277.1	256.0	239.7	232.7	230.4	229.6	226.5	224.1	222.6	224.1	222.6
67.5°	235.8	221.8	209.3	202.3	199.2	198.4	196.1	194.6	195.3	193.0	194.6
70°	196.9	182.9	175.1	171.2	169.7	167.3	167.3	167.3	167.3	165.8	165.0
72.5°	165.8	151.8	146.3	144.0	142.4	141.6	139.3	140.1	139.3	138.5	141.6
75°	131.5	123.0	117.5	115.2	116.7	114.4	112.1	113.6	111.3	112.1	115.2
77.5°	99.6	95.7	92.6	91.1	89.5	87.9	87.9	86.4	86.4	86.4	86.4
80°	72.4	71.6	66.1	65.4	65.4	63.8	63.8	63.8	63.8	63.0	63.8
82.5°	48.3	47.5	45.9	45.1	43.6	44.4	44.4	42.8	42.8	42.0	42.8
85°	28.0	28.0	26.5	25.7	24.9	25.7	24.1	23.3	24.1	23.3	24.1
87.5°	13.2	11.7	12.5	11.7	10.1	10.9	9.3	10.1	9.3	8.6	10.1
90°	17.7	18.7	19.7	20.7	21.2	21.4	21.7	22.0	22.4	22.7	22.4
92.5°	33.9	34.4	34.9	35.4	35.6	35.7	35.9	36.0	36.2	36.4	36.2
95°	58.1	58.6	59.1	59.6	59.9	59.9	59.9	59.9	59.9	59.9	59.9
97.5°	85.6	86.2	86.9	87.6	87.9	87.9	87.9	87.9	87.9	87.9	87.9
100°	116.3	116.7	117.0	117.3	117.5	117.5	117.5	117.5	117.5	117.5	117.5
102.5°	148.3	148.8	149.3	149.8	150.1	150.2	150.4	150.5	150.7	150.9	150.7
105°	180.9	181.4	181.9	182.4	182.7	183.0	183.5	184.0	184.5	185.0	184.5
107.5°	216.0	216.6	217.3	218.0	218.3	218.2	218.1	217.9	217.8	217.6	217.8
110°	252.1	251.8	251.4	251.1	250.9	251.2	251.7	252.2	252.7	253.2	252.7

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6
115°	328.8	328.7	328.5	328.4	328.3	328.2	328.0	327.9	327.7	327.5	327.7
117.5°	366.4	365.9	365.4	364.9	364.7	364.4	363.9	363.4	362.9	362.4	362.9
120°	404.8	403.9	403.1	402.2	401.8	402.0	402.3	402.6	403.0	403.3	403.0
122.5°	443.0	442.5	442.0	441.5	441.2	440.8	439.9	439.1	438.2	437.4	438.2
125°	480.3	480.0	479.6	479.3	479.1	478.9	478.6	478.3	477.9	477.6	477.9
127.5°	516.0	515.6	515.3	515.0	514.8	514.7	514.5	514.4	514.2	514.0	514.2
130°	553.9	553.5	553.2	552.9	552.7	552.4	551.7	551.0	550.4	549.7	550.4
132.5°	589.5	589.1	588.8	588.5	588.3	588.2	588.1	587.9	587.8	587.6	587.8
135°	625.1	624.8	624.4	624.1	623.9	623.7	623.2	622.7	622.2	621.7	622.2
137.5°	659.8	659.3	658.8	658.3	658.1	658.2	658.3	658.5	658.6	658.8	658.6
140°	693.5	693.3	693.2	693.0	692.9	692.8	692.7	692.5	692.4	692.2	692.4
142.5°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5
145°	757.9	757.8	757.6	757.5	757.4	757.1	756.6	756.1	755.6	755.1	755.6
147.5°	787.5	787.3	787.2	787.0	786.9	786.8	786.7	786.5	786.4	786.2	786.4
150°	815.0	815.0	815.0	815.0	815.0	814.9	814.7	814.6	814.4	814.2	814.4
152.5°	840.5	841.0	841.5	842.0	842.3	842.0	841.5	841.0	840.5	840.0	840.5
155°	864.2	864.9	865.6	866.3	866.6	866.3	865.6	864.9	864.2	863.5	864.2
157.5°	886.0	886.5	887.0	887.5	887.8	887.5	887.0	886.5	886.0	885.5	886.0
160°	905.7	906.2	906.7	907.2	907.5	907.1	906.2	905.4	904.5	903.7	904.5
162.5°	922.9	923.9	924.9	925.9	926.4	926.0	925.2	924.3	923.5	922.7	923.5
165°	938.1	939.1	940.1	941.1	941.6	941.3	940.6	939.9	939.3	938.6	939.3
167.5°	951.7	952.7	953.8	954.8	955.3	954.8	953.8	952.7	951.7	950.7	951.7
170°	962.3	963.3	964.4	965.4	965.9	965.3	964.1	963.0	961.8	960.6	961.8
172.5°	970.1	971.3	972.4	973.6	974.2	973.6	972.4	971.3	970.1	968.9	970.1
175°	975.4	976.6	977.7	978.9	979.5	978.9	977.7	976.6	975.4	974.2	975.4
177.5°	979.2	980.4	981.5	982.7	983.3	982.6	981.3	979.9	978.6	977.2	978.6
180°	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	1013.3	1010.9	1007.8	1007.8	1003.9	1003.9	997.7	986.8	977.5	974.3	975.9
5°	1099.6	1100.4	1095.7	1091.9	1084.9	1079.4	1069.3	1049.8	1043.6	1031.2	1022.6
7.5°	1198.5	1195.4	1186.8	1180.6	1179.0	1166.6	1144.8	1121.4	1102.8	1090.3	1072.4
10°	1309.8	1297.3	1284.9	1281.0	1271.6	1250.6	1225.7	1200.0	1174.4	1147.1	1116.8
12.5°	1403.2	1379.0	1378.2	1368.9	1351.0	1339.3	1309.8	1273.2	1228.8	1198.5	1164.2
15°	1503.5	1481.0	1462.3	1445.2	1436.6	1402.4	1377.5	1331.6	1278.6	1245.9	1222.6
17.5°	1575.1	1565.0	1533.1	1525.3	1513.7	1474.0	1434.3	1389.1	1343.2	1297.3	1234.3
20°	1632.7	1626.5	1605.5	1594.6	1575.9	1544.8	1496.5	1444.4	1391.5	1326.1	1267.0
22.5°	1657.6	1649.9	1632.7	1623.4	1611.7	1585.3	1544.0	1484.9	1415.6	1357.2	1294.2
25°	1608.6	1622.6	1617.9	1614.1	1609.4	1593.8	1562.7	1510.5	1442.8	1376.7	1298.1
27.5°	1498.1	1522.2	1545.6	1548.7	1556.5	1562.7	1550.2	1512.9	1456.1	1386.0	1299.6
30°	1349.5	1360.3	1407.8	1421.8	1432.7	1472.4	1495.8	1486.4	1442.8	1379.8	1300.4
32.5°	1158.8	1187.6	1235.8	1269.3	1298.9	1343.2	1403.9	1428.1	1412.5	1361.1	1282.5
35°	978.2	1012.5	1068.5	1111.3	1140.9	1203.9	1275.5	1327.7	1347.1	1321.4	1251.4
37.5°	830.4	871.6	921.4	937.8	972.0	1049.8	1148.7	1221.0	1268.5	1270.9	1216.4
40°	719.1	740.1	779.8	804.7	838.2	903.5	1000.0	1095.7	1167.3	1191.5	1162.7
42.5°	624.9	641.3	670.8	701.2	731.5	781.3	870.1	959.6	1056.1	1104.3	1103.5
45°	550.2	567.3	587.6	612.5	633.5	687.2	757.2	849.1	932.3	1007.0	1025.7
47.5°	484.8	499.6	524.5	535.4	549.4	600.0	660.7	746.3	832.7	918.3	940.1
50°	436.6	449.0	466.2	473.2	488.7	526.1	575.9	645.2	740.9	819.5	859.9
52.5°	393.0	402.3	415.6	421.0	431.9	459.9	505.1	559.5	638.9	719.9	776.7
55°	355.7	361.9	371.2	377.4	385.2	410.1	443.6	492.6	561.1	631.1	686.4
57.5°	320.6	325.3	334.6	337.8	344.0	363.4	386.8	428.0	491.1	553.3	607.0
60°	287.9	291.1	296.5	303.5	308.2	321.4	343.2	377.4	428.0	484.8	528.4
62.5°	256.8	261.5	263.0	266.2	270.0	282.5	299.6	324.5	368.9	415.6	461.5
65°	224.9	228.8	231.9	232.7	236.6	245.9	261.5	283.3	312.1	352.5	395.3
67.5°	195.3	197.7	199.2	202.3	206.2	210.9	223.4	239.7	266.2	298.8	333.1
70°	168.1	168.1	170.4	171.2	175.9	181.3	186.8	202.3	225.7	252.1	275.5
72.5°	138.5	142.4	141.6	145.5	144.8	148.6	155.6	165.8	182.9	203.9	226.5
75°	112.8	115.2	115.2	115.2	116.7	119.8	123.7	133.1	146.3	163.4	176.7
77.5°	87.9	89.5	89.5	89.5	90.3	93.4	97.3	103.5	112.8	123.0	130.7
80°	63.0	64.6	64.6	66.1	66.1	66.9	70.8	73.9	78.6	86.4	94.2
82.5°	42.8	43.6	45.1	45.1	44.4	45.9	46.7	49.8	54.5	56.0	61.5
85°	23.3	24.1	24.9	24.9	25.7	27.2	26.5	29.6	29.6	32.7	34.2
87.5°	9.3	10.9	10.9	10.1	10.9	10.9	10.9	12.5	13.2	14.0	13.2
90°	22.0	21.7	21.4	21.2	20.7	19.7	18.7	17.7	16.7	15.3	14.0
92.5°	36.0	35.9	35.7	35.6	35.4	34.9	34.4	33.9	33.4	32.6	31.7
95°	59.9	59.9	59.9	59.9	59.6	59.1	58.6	58.1	57.6	56.4	55.2
97.5°	87.9	87.9	87.9	87.9	87.6	86.9	86.2	85.6	84.9	83.5	82.2
100°	117.5	117.5	117.5	117.5	117.3	117.0	116.7	116.3	116.0	114.5	113.0
102.5°	150.5	150.4	150.2	150.1	149.8	149.3	148.8	148.3	147.8	146.5	145.1
105°	184.0	183.5	183.0	182.7	182.4	181.9	181.4	180.9	180.4	179.7	179.1
107.5°	217.9	218.1	218.2	218.3	218.0	217.3	216.6	216.0	215.3	215.1	215.0
110°	252.2	251.7	251.2	250.9	251.1	251.4	251.8	252.1	252.5	252.7	252.8

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.9	290.3
115°	327.9	328.0	328.2	328.3	328.4	328.5	328.7	328.8	329.0	329.3	329.7
117.5°	363.4	363.9	364.4	364.7	364.9	365.4	365.9	366.4	366.9	367.1	367.3
120°	402.6	402.3	402.0	401.8	402.2	403.1	403.9	404.8	405.6	406.1	406.6
122.5°	439.1	439.9	440.8	441.2	441.5	442.0	442.5	443.0	443.5	443.7	443.9
125°	478.3	478.6	478.9	479.1	479.3	479.6	480.0	480.3	480.7	480.9	481.0
127.5°	514.4	514.5	514.7	514.8	515.0	515.3	515.6	516.0	516.3	516.6	517.0
130°	551.0	551.7	552.4	552.7	552.9	553.2	553.5	553.9	554.2	554.2	554.2
132.5°	587.9	588.1	588.2	588.3	588.5	588.8	589.1	589.5	589.8	590.0	590.2
135°	622.7	623.2	623.7	623.9	624.1	624.4	624.8	625.1	625.5	625.5	625.5
137.5°	658.5	658.3	658.2	658.1	658.3	658.8	659.3	659.8	660.3	660.0	659.6
140°	692.5	692.7	692.8	692.9	693.0	693.2	693.3	693.5	693.7	693.7	693.7
142.5°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.7	725.9
145°	756.1	756.6	757.1	757.4	757.5	757.6	757.8	757.9	758.1	757.9	757.8
147.5°	786.5	786.7	786.8	786.9	787.0	787.2	787.3	787.5	787.7	787.9	788.1
150°	814.6	814.7	814.9	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0
152.5°	841.0	841.5	842.0	842.3	842.0	841.5	841.0	840.5	840.0	839.8	839.7
155°	864.9	865.6	866.3	866.6	866.3	865.6	864.9	864.2	863.5	863.7	863.9
157.5°	886.5	887.0	887.5	887.8	887.5	887.0	886.5	886.0	885.5	885.5	885.5
160°	905.4	906.2	907.1	907.5	907.2	906.7	906.2	905.7	905.2	905.4	905.6
162.5°	924.3	925.2	926.0	926.4	925.9	924.9	923.9	922.9	921.9	922.1	922.3
165°	939.9	940.6	941.3	941.6	941.1	940.1	939.1	938.1	937.1	937.4	937.8
167.5°	952.7	953.8	954.8	955.3	954.8	953.8	952.7	951.7	950.7	950.7	950.7
170°	963.0	964.1	965.3	965.9	965.4	964.4	963.3	962.3	961.3	961.1	961.0
172.5°	971.3	972.4	973.6	974.2	973.6	972.4	971.3	970.1	968.9	968.9	968.9
175°	976.6	977.7	978.9	979.5	978.9	977.7	976.6	975.4	974.2	974.4	974.6
177.5°	979.9	981.3	982.6	983.3	982.7	981.5	980.4	979.2	978.0	978.0	978.0
180°	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	968.9	965.8	963.5	963.5	956.4	949.4	945.6	944.0	942.4	936.2	927.7
5°	1008.6	998.5	991.5	984.5	972.8	960.3	947.9	940.9	930.8	916.8	906.6
7.5°	1052.9	1028.8	1021.0	1012.5	989.1	968.1	951.0	936.2	919.9	902.0	884.1
10°	1090.3	1064.6	1047.5	1032.7	1002.4	974.3	948.7	926.9	905.9	882.5	860.7
12.5°	1126.1	1089.5	1071.6	1049.8	1017.9	977.5	944.0	916.8	885.6	861.5	835.0
15°	1175.9	1114.4	1084.9	1070.8	1028.0	980.6	940.1	899.6	874.0	837.4	814.0
17.5°	1183.7	1133.9	1114.4	1078.6	1027.3	973.6	926.9	886.4	847.5	814.8	784.5
20°	1210.9	1145.6	1114.4	1091.9	1024.2	969.7	918.3	866.2	828.8	793.8	759.6
22.5°	1228.0	1154.1	1121.4	1085.6	1021.0	955.7	895.0	849.8	803.9	768.1	740.9
25°	1223.4	1149.4	1112.9	1079.4	1000.8	935.4	881.0	823.4	780.6	741.7	705.9
27.5°	1221.0	1137.8	1098.9	1061.5	987.6	919.1	850.6	803.9	756.4	711.3	684.8
30°	1214.8	1123.0	1077.9	1037.4	960.3	888.7	830.4	775.9	728.4	687.2	652.2
32.5°	1193.8	1098.1	1054.5	1010.9	930.8	859.2	800.0	749.4	702.0	659.2	625.7
35°	1165.8	1068.5	1021.0	975.1	895.0	822.6	768.1	715.2	670.8	629.6	597.7
37.5°	1137.8	1034.3	989.9	937.0	863.1	787.6	731.5	684.1	642.8	600.0	565.0
40°	1097.3	993.8	944.8	899.6	813.3	742.4	691.1	648.3	607.8	567.3	537.8
42.5°	1042.1	949.4	898.9	849.1	768.1	698.1	648.3	610.1	572.0	538.5	505.9
45°	986.0	895.7	850.6	806.2	718.3	652.2	606.2	571.2	539.3	502.7	476.3
47.5°	918.3	842.0	796.9	753.3	670.1	603.9	561.9	529.2	499.6	469.3	444.4
50°	849.1	782.9	741.7	696.5	617.1	557.2	516.0	488.7	464.6	435.8	415.6
52.5°	774.3	716.8	681.7	638.1	568.1	512.9	470.8	443.6	423.4	402.3	384.4
55°	695.0	652.9	615.6	580.6	514.4	464.6	427.2	403.1	389.1	369.7	354.1
57.5°	623.4	582.9	560.3	520.6	463.0	414.0	384.4	364.2	347.9	336.2	323.7
60°	548.7	516.0	491.1	462.3	411.7	370.4	339.3	327.6	310.5	302.0	296.5
62.5°	477.1	453.7	430.4	408.6	363.4	324.5	301.2	286.4	276.3	267.7	263.0
65°	409.3	387.6	371.2	351.8	314.4	283.3	261.5	249.8	239.7	237.4	231.9
67.5°	343.2	333.9	316.0	300.4	268.5	244.4	228.0	213.2	207.8	205.5	200.8
70°	287.2	276.3	262.3	249.0	224.9	203.9	189.1	183.7	175.9	175.1	169.7
72.5°	236.6	223.4	213.2	203.1	185.2	166.5	158.8	151.0	147.1	144.0	141.6
75°	187.6	178.2	171.2	162.7	147.1	134.6	123.7	120.6	118.3	117.5	116.0
77.5°	140.1	133.9	130.7	122.2	111.3	100.4	95.7	91.1	91.1	89.5	90.3
80°	99.6	95.7	91.8	87.2	77.8	73.2	69.3	66.1	64.6	63.8	64.6
82.5°	63.0	60.7	59.9	56.8	50.6	48.3	45.1	42.8	42.8	42.8	42.8
85°	35.0	35.0	35.0	30.4	28.0	25.7	24.1	23.3	23.3	23.3	24.1
87.5°	14.8	14.8	12.5	12.5	11.7	10.1	9.3	9.3	10.1	10.1	10.9
90°	12.6	11.3	10.6	9.7	7.8	6.0	4.1	2.3	4.1	6.0	7.8
92.5°	30.9	30.0	29.6	28.5	26.3	24.1	21.9	19.7	21.9	24.1	26.3
95°	54.1	52.9	52.3	51.5	50.0	48.5	47.0	45.5	47.0	48.5	50.0
97.5°	80.8	79.5	78.8	78.1	76.8	75.5	74.1	72.8	74.1	75.5	76.8
100°	111.5	110.0	109.2	108.9	108.2	107.5	106.8	106.1	106.8	107.5	108.2
102.5°	143.8	142.5	141.8	141.7	141.5	141.4	141.2	141.0	141.2	141.4	141.5
105°	178.4	177.7	177.4	177.3	177.1	177.0	176.8	176.6	176.8	177.0	177.1
107.5°	214.8	214.7	214.6	214.5	214.3	214.2	214.0	213.8	214.0	214.2	214.3
110°	253.0	253.1	253.2	253.0	252.7	252.4	252.0	251.7	252.0	252.4	252.7

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	290.6	290.9	291.1	291.1	291.1	291.1	291.1	291.1	291.1	291.1	291.1
115°	330.0	330.3	330.5	330.5	330.5	330.5	330.5	330.5	330.5	330.5	330.5
117.5°	367.4	367.6	367.7	367.7	367.7	367.7	367.7	367.7	367.7	367.7	367.7
120°	407.1	407.6	407.9	407.6	406.9	406.2	405.5	404.8	405.5	406.2	406.9
122.5°	444.0	444.2	444.3	444.2	444.0	443.9	443.7	443.5	443.7	443.9	444.0
125°	481.2	481.3	481.4	481.4	481.4	481.4	481.4	481.4	481.4	481.4	481.4
127.5°	517.3	517.6	517.8	517.5	517.0	516.5	516.0	515.5	516.0	516.5	517.0
130°	554.2	554.2	554.2	553.9	553.4	552.9	552.4	551.9	552.4	552.9	553.4
132.5°	590.3	590.5	590.6	590.4	590.1	589.8	589.4	589.1	589.4	589.8	590.1
135°	625.5	625.5	625.5	625.0	624.0	622.9	621.9	620.9	621.9	622.9	624.0
137.5°	659.3	659.0	658.8	658.5	658.0	657.5	657.0	656.5	657.0	657.5	658.0
140°	693.7	693.7	693.7	693.5	693.2	692.9	692.5	692.2	692.5	692.9	693.2
142.5°	726.0	726.2	726.3	726.1	725.8	725.5	725.1	724.8	725.1	725.5	725.8
145°	757.6	757.5	757.4	757.1	756.4	755.7	755.0	754.3	755.0	755.7	756.4
147.5°	788.2	788.4	788.5	788.1	787.2	786.4	785.5	784.7	785.5	786.4	787.2
150°	815.0	815.0	815.0	814.7	814.0	813.3	812.7	812.0	812.7	813.3	814.0
152.5°	839.5	839.4	839.3	839.1	838.8	838.4	838.1	837.7	838.1	838.4	838.8
155°	864.0	864.2	864.3	864.3	864.3	864.3	864.3	864.3	864.3	864.3	864.3
157.5°	885.5	885.5	885.5	885.7	886.0	886.3	886.7	887.0	886.7	886.3	886.0
160°	905.7	905.9	906.0	906.1	906.2	906.4	906.5	906.7	906.5	906.4	906.2
162.5°	922.4	922.6	922.7	922.9	923.4	923.9	924.4	924.9	924.4	923.9	923.4
165°	938.1	938.4	938.6	938.9	939.4	939.9	940.4	940.9	940.4	939.9	939.4
167.5°	950.7	950.7	950.7	951.0	951.7	952.4	953.0	953.7	953.0	952.4	951.7
170°	960.8	960.7	960.6	961.0	961.9	962.7	963.6	964.4	963.6	962.7	961.9
172.5°	968.9	968.9	968.9	969.2	969.9	970.6	971.2	971.9	971.2	970.6	969.9
175°	974.7	974.9	975.0	975.4	976.3	977.1	978.0	978.8	978.0	977.1	976.3
177.5°	978.0	978.0	978.0	978.4	979.3	980.1	981.0	981.8	981.0	980.1	979.3
180°	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	925.3	922.2	923.8	916.0	909.0	898.9	890.3	888.7	887.2	891.9	888.7
5°	898.9	895.0	891.1	881.7	867.7	859.2	846.7	845.9	841.3	834.3	835.8
7.5°	870.1	867.7	862.3	847.5	835.0	820.3	810.1	801.6	797.7	791.5	789.1
10°	846.7	838.2	833.5	817.1	802.4	786.8	773.6	767.3	760.3	754.9	751.0
12.5°	814.8	812.5	799.2	786.0	773.6	755.7	745.5	727.6	718.3	723.0	721.4
15°	793.8	782.9	779.8	761.1	740.1	728.4	709.7	698.1	694.2	687.2	678.6
17.5°	765.8	758.8	747.9	730.8	706.6	690.3	677.1	666.2	661.5	652.2	645.2
20°	739.3	727.6	719.1	703.5	680.2	659.2	642.8	635.8	624.1	616.4	612.5
22.5°	715.2	706.6	694.2	670.8	650.6	630.4	610.9	600.8	589.9	585.2	579.0
25°	685.6	671.6	663.1	637.4	615.6	599.2	581.3	568.1	561.9	554.1	552.5
27.5°	656.8	643.6	633.5	610.9	584.5	563.4	552.5	543.2	532.3	532.3	528.4
30°	628.0	618.7	603.1	581.3	556.4	536.2	523.7	515.2	511.3	508.2	507.4
32.5°	599.2	586.8	577.4	547.9	529.2	510.5	501.2	494.2	489.5	488.7	489.5
35°	569.7	555.7	546.3	519.9	501.2	484.1	480.2	473.9	471.6	470.8	474.7
37.5°	538.5	527.6	516.0	494.2	473.2	463.0	455.3	452.9	452.2	456.8	458.4
40°	509.7	500.4	489.5	466.2	450.6	439.7	435.8	433.5	436.6	441.3	443.6
42.5°	482.5	469.3	460.7	439.7	425.7	419.5	414.8	414.8	417.9	423.4	427.2
45°	453.7	443.6	435.0	416.4	403.9	396.9	396.1	396.9	400.8	404.7	409.3
47.5°	425.7	415.6	406.2	390.7	379.8	375.9	375.1	375.9	382.1	387.6	393.0
50°	400.0	389.1	380.6	365.8	357.2	352.5	353.3	357.2	361.9	369.7	376.7
52.5°	369.7	361.9	354.1	340.9	333.1	330.0	332.3	335.4	344.0	349.4	358.0
55°	340.1	333.1	326.9	316.7	310.5	308.2	309.7	314.4	321.4	330.7	340.9
57.5°	312.8	305.1	298.8	291.8	284.8	285.6	286.4	292.6	301.2	309.7	321.4
60°	282.5	277.8	272.4	263.8	260.7	260.7	263.0	270.0	277.8	291.8	302.0
62.5°	255.3	249.0	245.1	239.7	235.0	235.8	241.3	247.5	256.8	268.5	281.7
65°	227.2	220.2	217.1	212.5	210.9	211.7	215.6	224.9	235.0	245.1	257.6
67.5°	196.1	193.8	190.7	186.0	187.6	188.3	192.2	200.0	210.9	221.0	235.0
70°	169.7	165.0	164.2	160.3	160.3	162.7	170.4	175.9	186.0	196.9	211.7
72.5°	141.6	137.7	137.7	134.6	137.0	139.3	143.2	151.0	160.3	171.2	183.7
75°	112.8	111.3	112.8	111.3	111.3	115.2	119.8	126.1	136.2	147.9	158.0
77.5°	87.2	87.2	86.4	88.7	88.7	91.1	97.3	103.5	111.3	120.6	131.5
80°	63.8	63.8	63.8	66.1	68.5	68.5	72.4	80.2	87.2	93.4	103.5
82.5°	43.6	43.6	43.6	45.1	48.3	48.3	52.9	57.6	65.4	70.8	75.5
85°	26.5	26.5	25.7	27.2	28.0	30.4	34.2	37.4	41.2	45.9	50.6
87.5°	11.7	11.7	12.5	13.2	14.0	15.6	17.1	18.7	22.6	24.1	26.5
90°	9.7	10.6	11.3	12.6	14.0	15.3	16.7	17.7	18.7	19.7	20.7
92.5°	28.5	29.6	30.0	30.9	31.7	32.6	33.4	33.9	34.4	34.9	35.4
95°	51.5	52.3	52.9	54.1	55.2	56.4	57.6	58.1	58.6	59.1	59.6
97.5°	78.1	78.8	79.5	80.8	82.2	83.5	84.9	85.6	86.2	86.9	87.6
100°	108.9	109.2	110.0	111.5	113.0	114.5	116.0	116.3	116.7	117.0	117.3
102.5°	141.7	141.8	142.5	143.8	145.1	146.5	147.8	148.3	148.8	149.3	149.8
105°	177.3	177.4	177.7	178.4	179.1	179.7	180.4	180.9	181.4	181.9	182.4
107.5°	214.5	214.6	214.7	214.8	215.0	215.1	215.3	216.0	216.6	217.3	218.0
110°	253.0	253.2	253.1	253.0	252.8	252.7	252.5	252.1	251.8	251.4	251.1

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	291.1	291.1	290.9	290.6	290.3	289.9	289.6	289.6	289.6	289.6	289.6
115°	330.5	330.5	330.3	330.0	329.7	329.3	329.0	328.8	328.7	328.5	328.4
117.5°	367.7	367.7	367.6	367.4	367.3	367.1	366.9	366.4	365.9	365.4	364.9
120°	407.6	407.9	407.6	407.1	406.6	406.1	405.6	404.8	403.9	403.1	402.2
122.5°	444.2	444.3	444.2	444.0	443.9	443.7	443.5	443.0	442.5	442.0	441.5
125°	481.4	481.4	481.3	481.2	481.0	480.9	480.7	480.3	480.0	479.6	479.3
127.5°	517.5	517.8	517.6	517.3	517.0	516.6	516.3	516.0	515.6	515.3	515.0
130°	553.9	554.2	554.2	554.2	554.2	554.2	554.2	553.9	553.5	553.2	552.9
132.5°	590.4	590.6	590.5	590.3	590.2	590.0	589.8	589.5	589.1	588.8	588.5
135°	625.0	625.5	625.5	625.5	625.5	625.5	625.5	625.1	624.8	624.4	624.1
137.5°	658.5	658.8	659.0	659.3	659.6	660.0	660.3	659.8	659.3	658.8	658.3
140°	693.5	693.7	693.7	693.7	693.7	693.7	693.7	693.5	693.3	693.2	693.0
142.5°	726.1	726.3	726.2	726.0	725.9	725.7	725.5	725.5	725.5	725.5	725.5
145°	757.1	757.4	757.5	757.6	757.8	757.9	758.1	757.9	757.8	757.6	757.5
147.5°	788.1	788.5	788.4	788.2	788.1	787.9	787.7	787.5	787.3	787.2	787.0
150°	814.7	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0
152.5°	839.1	839.3	839.4	839.5	839.7	839.8	840.0	840.5	841.0	841.5	842.0
155°	864.3	864.3	864.2	864.0	863.9	863.7	863.5	864.2	864.9	865.6	866.3
157.5°	885.7	885.5	885.5	885.5	885.5	885.5	885.5	886.0	886.5	887.0	887.5
160°	906.1	906.0	905.9	905.7	905.6	905.4	905.2	905.7	906.2	906.7	907.2
162.5°	922.9	922.7	922.6	922.4	922.3	922.1	921.9	922.9	923.9	924.9	925.9
165°	938.9	938.6	938.4	938.1	937.8	937.4	937.1	938.1	939.1	940.1	941.1
167.5°	951.0	950.7	950.7	950.7	950.7	950.7	950.7	951.7	952.7	953.8	954.8
170°	961.0	960.6	960.7	960.8	961.0	961.1	961.3	962.3	963.3	964.4	965.4
172.5°	969.2	968.9	968.9	968.9	968.9	968.9	968.9	970.1	971.3	972.4	973.6
175°	975.4	975.0	974.9	974.7	974.6	974.4	974.2	975.4	976.6	977.7	978.9
177.5°	978.4	978.0	978.0	978.0	978.0	978.0	978.0	979.2	980.4	981.5	982.7
180°	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	886.4	885.6	881.7	883.3	878.6	880.2	882.5	883.3	886.4	884.1	883.3
5°	831.9	830.4	828.0	825.7	824.9	828.0	822.6	824.1	825.7	828.0	831.2
7.5°	787.6	786.8	784.5	780.6	779.0	777.5	778.2	783.7	782.9	782.1	787.6
10°	747.1	747.9	743.2	742.4	737.8	737.0	737.8	739.3	741.7	744.8	745.5
12.5°	705.1	715.2	706.6	703.5	696.5	700.4	702.0	695.0	698.9	701.2	712.9
15°	678.6	673.9	668.5	668.5	665.4	663.8	659.9	665.4	668.5	673.2	671.6
17.5°	642.0	634.3	631.1	628.0	628.8	631.9	623.4	635.8	635.8	638.1	634.3
20°	610.1	603.9	600.0	598.5	596.1	594.6	593.8	596.9	601.6	603.1	607.0
22.5°	576.7	576.7	570.4	568.1	566.6	564.2	568.1	565.8	568.9	572.0	578.2
25°	548.7	548.7	546.3	543.2	540.9	539.3	541.6	540.9	543.2	547.1	548.7
27.5°	526.1	523.7	523.0	522.2	521.4	522.2	521.4	523.7	526.1	526.9	525.3
30°	506.6	504.3	505.1	505.1	505.9	505.1	504.3	506.6	507.4	505.9	506.6
32.5°	488.7	488.7	490.3	491.1	491.1	491.8	492.6	491.1	491.8	489.5	490.3
35°	473.9	475.5	477.1	477.8	478.6	477.8	479.4	478.6	477.1	475.5	474.7
37.5°	459.2	460.7	463.8	464.6	466.9	467.7	466.2	466.2	465.4	462.3	460.7
40°	443.6	445.1	449.0	451.4	452.9	455.3	453.7	453.7	450.6	447.5	445.1
42.5°	428.8	431.9	435.8	438.1	441.3	441.3	441.3	439.7	435.8	432.7	430.4
45°	414.0	414.8	420.2	424.1	427.2	427.2	427.2	424.9	422.6	416.4	413.2
47.5°	397.7	400.0	406.2	410.1	413.2	414.0	414.0	411.7	407.0	401.6	397.7
50°	379.8	383.7	390.7	396.1	400.0	401.6	399.2	397.7	392.2	386.0	381.3
52.5°	362.7	367.3	375.9	380.6	386.0	386.8	386.0	383.7	377.4	368.9	365.0
55°	345.5	349.4	358.8	366.5	371.2	372.8	371.2	367.3	359.5	351.0	347.1
57.5°	326.9	332.3	342.4	350.2	355.7	356.4	354.9	351.0	344.8	333.9	328.4
60°	307.4	314.4	324.5	332.3	339.3	340.1	338.5	333.1	325.3	314.4	309.7
62.5°	287.9	293.4	305.1	313.6	319.1	323.0	319.9	314.4	306.6	295.7	288.7
65°	265.4	273.2	283.3	291.1	297.3	298.1	296.5	291.8	283.3	271.6	266.2
67.5°	243.6	249.0	259.2	269.3	271.6	273.9	271.6	266.9	259.9	249.8	242.0
70°	217.1	221.8	234.2	241.3	244.4	246.7	245.1	240.5	234.2	224.9	218.7
72.5°	190.7	194.6	206.2	211.7	217.9	217.1	216.3	213.2	204.7	198.4	194.6
75°	162.7	167.3	175.1	182.1	184.4	184.4	184.4	182.1	176.7	166.5	162.7
77.5°	137.0	139.3	145.5	149.4	151.8	152.5	151.8	147.9	144.8	137.7	135.4
80°	105.1	111.3	116.0	116.7	119.8	119.8	119.8	118.3	115.2	108.2	107.4
82.5°	79.4	80.9	85.6	87.9	89.5	88.7	88.7	85.6	84.8	80.9	79.4
85°	53.7	56.0	55.3	58.4	59.1	57.6	57.6	59.1	55.3	56.0	53.7
87.5°	29.6	29.6	31.1	30.4	33.5	33.5	31.9	32.7	31.1	30.4	29.6
90°	21.2	21.4	21.7	22.0	22.4	22.7	22.4	22.0	21.7	21.4	21.2
92.5°	35.6	35.7	35.9	36.0	36.2	36.4	36.2	36.0	35.9	35.7	35.6
95°	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9
97.5°	87.9	87.9	87.9	87.9	87.9	87.9	87.9	87.9	87.9	87.9	87.9
100°	117.5	117.5	117.5	117.5	117.5	117.5	117.5	117.5	117.5	117.5	117.5
102.5°	150.1	150.2	150.4	150.5	150.7	150.9	150.7	150.5	150.4	150.2	150.1
105°	182.7	183.0	183.5	184.0	184.5	185.0	184.5	184.0	183.5	183.0	182.7
107.5°	218.3	218.2	218.1	217.9	217.8	217.6	217.8	217.9	218.1	218.2	218.3
110°	250.9	251.2	251.7	252.2	252.7	253.2	252.7	252.2	251.7	251.2	250.9

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6	289.6
115°	328.3	328.2	328.0	327.9	327.7	327.5	327.7	327.9	328.0	328.2	328.3
117.5°	364.7	364.4	363.9	363.4	362.9	362.4	362.9	363.4	363.9	364.4	364.7
120°	401.8	402.0	402.3	402.6	403.0	403.3	403.0	402.6	402.3	402.0	401.8
122.5°	441.2	440.8	439.9	439.1	438.2	437.4	438.2	439.1	439.9	440.8	441.2
125°	479.1	478.9	478.6	478.3	477.9	477.6	477.9	478.3	478.6	478.9	479.1
127.5°	514.8	514.7	514.5	514.4	514.2	514.0	514.2	514.4	514.5	514.7	514.8
130°	552.7	552.4	551.7	551.0	550.4	549.7	550.4	551.0	551.7	552.4	552.7
132.5°	588.3	588.2	588.1	587.9	587.8	587.6	587.8	587.9	588.1	588.2	588.3
135°	623.9	623.7	623.2	622.7	622.2	621.7	622.2	622.7	623.2	623.7	623.9
137.5°	658.1	658.2	658.3	658.5	658.6	658.8	658.6	658.5	658.3	658.2	658.1
140°	692.9	692.8	692.7	692.5	692.4	692.2	692.4	692.5	692.7	692.8	692.9
142.5°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5
145°	757.4	757.1	756.6	756.1	755.6	755.1	755.6	756.1	756.6	757.1	757.4
147.5°	786.9	786.8	786.7	786.5	786.4	786.2	786.4	786.5	786.7	786.8	786.9
150°	815.0	814.9	814.7	814.6	814.4	814.2	814.4	814.6	814.7	814.9	815.0
152.5°	842.3	842.0	841.5	841.0	840.5	840.0	840.5	841.0	841.5	842.0	842.3
155°	866.6	866.3	865.6	864.9	864.2	863.5	864.2	864.9	865.6	866.3	866.6
157.5°	887.8	887.5	887.0	886.5	886.0	885.5	886.0	886.5	887.0	887.5	887.8
160°	907.5	907.1	906.2	905.4	904.5	903.7	904.5	905.4	906.2	907.1	907.5
162.5°	926.4	926.0	925.2	924.3	923.5	922.7	923.5	924.3	925.2	926.0	926.4
165°	941.6	941.3	940.6	939.9	939.3	938.6	939.3	939.9	940.6	941.3	941.6
167.5°	955.3	954.8	953.8	952.7	951.7	950.7	951.7	952.7	953.8	954.8	955.3
170°	965.9	965.3	964.1	963.0	961.8	960.6	961.8	963.0	964.1	965.3	965.9
172.5°	974.2	973.6	972.4	971.3	970.1	968.9	970.1	971.3	972.4	973.6	974.2
175°	979.5	978.9	977.7	976.6	975.4	974.2	975.4	976.6	977.7	978.9	979.5
177.5°	983.3	982.6	981.3	979.9	978.6	977.2	978.6	979.9	981.3	982.6	983.3
180°	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	883.3	888.0	883.3	886.4	888.0	891.9	893.4	900.4	902.7	908.2	908.2
5°	830.4	832.7	833.5	836.6	839.7	847.5	852.9	863.1	874.7	876.3	883.3
7.5°	787.6	791.5	797.7	795.4	800.8	812.5	819.5	831.9	843.6	849.8	858.4
10°	749.4	754.1	756.4	758.8	768.9	779.0	789.9	798.5	814.0	823.4	830.4
12.5°	718.3	714.4	719.1	727.6	739.3	745.5	760.3	773.6	785.2	795.4	801.6
15°	677.8	681.0	685.6	700.4	703.5	719.1	724.5	739.3	761.1	770.4	778.2
17.5°	638.9	649.0	658.4	663.8	673.2	685.6	701.2	717.5	731.5	742.4	751.8
20°	607.8	617.9	623.4	627.3	636.6	653.7	668.5	688.7	706.6	715.2	727.6
22.5°	582.9	582.9	590.7	602.4	607.8	624.1	636.6	658.4	677.8	688.7	700.4
25°	551.8	556.4	562.7	572.8	580.6	593.8	611.7	630.4	651.4	660.7	675.5
27.5°	526.1	531.5	540.1	542.4	550.2	561.9	580.6	600.8	622.6	632.7	645.2
30°	506.6	509.7	512.9	517.5	524.5	534.6	550.2	568.1	594.6	602.4	617.9
32.5°	489.5	491.1	492.6	496.5	500.4	510.5	523.0	542.4	564.2	575.9	589.9
35°	473.9	472.4	473.2	475.5	479.4	483.3	496.5	512.9	533.1	547.1	558.0
37.5°	459.2	456.0	455.3	455.3	456.8	461.5	471.6	485.6	507.4	519.1	530.0
40°	442.8	439.7	438.1	437.4	436.6	439.7	447.5	461.5	478.6	489.5	502.0
42.5°	427.2	424.1	420.2	419.5	417.9	419.5	424.9	438.1	452.9	463.8	473.9
45°	411.7	406.2	401.6	398.5	399.2	396.9	400.8	410.9	428.0	435.0	445.1
47.5°	394.6	388.3	382.1	379.0	375.9	377.4	379.0	387.6	402.3	409.3	419.5
50°	378.2	369.7	362.7	358.8	356.4	354.9	356.4	365.0	375.9	382.1	390.7
52.5°	359.5	351.0	344.0	337.8	334.6	332.3	333.1	340.9	351.0	357.2	365.8
55°	342.4	331.5	322.2	314.4	312.1	311.3	310.5	316.0	324.5	330.7	337.8
57.5°	323.0	312.1	302.0	292.6	287.9	287.2	287.2	288.7	299.6	304.3	308.2
60°	303.5	291.8	280.9	272.4	265.4	263.0	262.3	265.4	270.8	275.5	280.9
62.5°	281.7	270.0	256.8	249.0	242.0	235.8	238.1	238.9	246.7	249.0	253.7
65°	260.7	247.5	236.6	224.1	216.3	212.5	210.9	212.5	218.7	219.5	222.6
67.5°	236.6	224.1	210.9	202.3	195.3	188.3	186.8	186.8	189.9	192.2	196.1
70°	213.2	200.8	186.0	176.7	169.7	163.4	161.1	160.3	162.7	164.2	168.1
72.5°	186.0	173.5	162.7	152.5	144.0	139.3	137.0	135.4	137.7	139.3	140.1
75°	157.2	147.1	136.2	126.1	120.6	116.0	112.8	110.5	112.1	112.1	112.1
77.5°	130.0	119.8	111.3	104.3	97.3	91.8	89.5	87.2	87.9	87.9	89.5
80°	101.2	94.2	87.2	80.9	74.7	70.0	68.5	66.1	64.6	63.8	63.8
82.5°	74.7	69.3	63.0	57.6	54.5	49.8	48.3	45.1	45.1	44.4	44.4
85°	49.8	46.7	40.5	36.6	34.2	31.9	30.4	28.8	26.5	26.5	25.7
87.5°	26.5	24.9	23.3	18.7	18.7	16.3	15.6	14.8	12.5	13.2	13.2
90°	20.7	19.7	18.7	17.7	16.7	15.3	14.0	12.6	11.3	10.6	9.7
92.5°	35.4	34.9	34.4	33.9	33.4	32.6	31.7	30.9	30.0	29.6	28.5
95°	59.6	59.1	58.6	58.1	57.6	56.4	55.2	54.1	52.9	52.3	51.5
97.5°	87.6	86.9	86.2	85.6	84.9	83.5	82.2	80.8	79.5	78.8	78.1
100°	117.3	117.0	116.7	116.3	116.0	114.5	113.0	111.5	110.0	109.2	108.9
102.5°	149.8	149.3	148.8	148.3	147.8	146.5	145.1	143.8	142.5	141.8	141.7
105°	182.4	181.9	181.4	180.9	180.4	179.7	179.1	178.4	177.7	177.4	177.3
107.5°	218.0	217.3	216.6	216.0	215.3	215.1	215.0	214.8	214.7	214.6	214.5
110°	251.1	251.4	251.8	252.1	252.5	252.7	252.8	253.0	253.1	253.2	253.0

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	289.6	289.6	289.6	289.6	289.6	289.9	290.3	290.6	290.9	291.1	291.1
115°	328.4	328.5	328.7	328.8	329.0	329.3	329.7	330.0	330.3	330.5	330.5
117.5°	364.9	365.4	365.9	366.4	366.9	367.1	367.3	367.4	367.6	367.7	367.7
120°	402.2	403.1	403.9	404.8	405.6	406.1	406.6	407.1	407.6	407.9	407.6
122.5°	441.5	442.0	442.5	443.0	443.5	443.7	443.9	444.0	444.2	444.3	444.2
125°	479.3	479.6	480.0	480.3	480.7	480.9	481.0	481.2	481.3	481.4	481.4
127.5°	515.0	515.3	515.6	516.0	516.3	516.6	517.0	517.3	517.6	517.8	517.5
130°	552.9	553.2	553.5	553.9	554.2	554.2	554.2	554.2	554.2	554.2	553.9
132.5°	588.5	588.8	589.1	589.5	589.8	590.0	590.2	590.3	590.5	590.6	590.4
135°	624.1	624.4	624.8	625.1	625.5	625.5	625.5	625.5	625.5	625.5	625.0
137.5°	658.3	658.8	659.3	659.8	660.3	660.0	659.6	659.3	659.0	658.8	658.5
140°	693.0	693.2	693.3	693.5	693.7	693.7	693.7	693.7	693.7	693.7	693.5
142.5°	725.5	725.5	725.5	725.5	725.5	725.7	725.9	726.0	726.2	726.3	726.1
145°	757.5	757.6	757.8	757.9	758.1	757.9	757.8	757.6	757.5	757.4	757.1
147.5°	787.0	787.2	787.3	787.5	787.7	787.9	788.1	788.2	788.4	788.5	788.1
150°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	814.7
152.5°	842.0	841.5	841.0	840.5	840.0	839.8	839.7	839.5	839.4	839.3	839.1
155°	866.3	865.6	864.9	864.2	863.5	863.7	863.9	864.0	864.2	864.3	864.3
157.5°	887.5	887.0	886.5	886.0	885.5	885.5	885.5	885.5	885.5	885.5	885.7
160°	907.2	906.7	906.2	905.7	905.2	905.4	905.6	905.7	905.9	906.0	906.1
162.5°	925.9	924.9	923.9	922.9	921.9	922.1	922.3	922.4	922.6	922.7	922.9
165°	941.1	940.1	939.1	938.1	937.1	937.4	937.8	938.1	938.4	938.6	938.9
167.5°	954.8	953.8	952.7	951.7	950.7	950.7	950.7	950.7	950.7	950.7	951.0
170°	965.4	964.4	963.3	962.3	961.3	961.1	961.0	960.8	960.7	960.6	961.0
172.5°	973.6	972.4	971.3	970.1	968.9	968.9	968.9	968.9	968.9	968.9	969.2
175°	978.9	977.7	976.6	975.4	974.2	974.4	974.6	974.7	974.9	975.0	975.4
177.5°	982.7	981.5	980.4	979.2	978.0	978.0	978.0	978.0	978.0	978.0	978.4
180°	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3	980.3

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	939.3	939.3	939.3	939.3
2.5°	913.6	921.4	928.4	939.3
5°	893.4	904.3	919.1	935.4
7.5°	870.1	887.2	906.6	929.2
10°	848.3	867.7	892.6	919.9
12.5°	825.7	849.1	876.3	905.9
15°	800.0	823.4	853.7	893.4
17.5°	776.7	804.7	837.4	879.4
20°	749.4	775.9	811.7	859.9
22.5°	725.3	755.7	795.4	837.4
25°	698.9	725.3	765.0	815.6
27.5°	672.4	705.1	743.2	792.2
30°	646.7	673.9	715.2	766.6
32.5°	618.7	651.4	689.5	737.8
35°	588.3	619.5	655.3	707.4
37.5°	561.1	591.5	628.0	673.9
40°	530.8	562.7	596.1	642.0
42.5°	501.2	530.0	563.4	605.5
45°	472.4	497.3	527.6	564.2
47.5°	442.8	463.8	491.8	524.5
50°	410.9	433.5	454.5	481.7
52.5°	381.3	400.8	417.9	440.5
55°	352.5	365.8	379.8	396.9
57.5°	322.2	332.3	342.4	360.3
60°	291.8	301.2	306.6	318.3
62.5°	262.3	266.2	273.2	280.2
65°	229.6	235.0	238.9	247.5
67.5°	200.0	202.3	206.2	211.7
70°	168.9	174.3	175.9	179.8
72.5°	142.4	144.8	146.3	147.1
75°	112.8	115.2	116.7	121.4
77.5°	88.7	87.9	91.1	91.8
80°	65.4	63.0	63.8	66.9
82.5°	42.8	43.6	42.8	42.8
85°	26.5	25.7	24.1	24.9
87.5°	11.7	11.7	10.9	10.9
90°	7.8	6.0	4.1	2.3
92.5°	26.3	24.1	21.9	19.7
95°	50.0	48.5	47.0	45.5
97.5°	76.8	75.5	74.1	72.8
100°	108.2	107.5	106.8	106.1
102.5°	141.5	141.4	141.2	141.0
105°	177.1	177.0	176.8	176.6
107.5°	214.3	214.2	214.0	213.8
110°	252.7	252.4	252.0	251.7

TEST NUMBER: P1033660

CATALOG NUMBER: S124DIW-B575D770UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	291.1	291.1	291.1	291.1
115°	330.5	330.5	330.5	330.5
117.5°	367.7	367.7	367.7	367.7
120°	406.9	406.2	405.5	404.8
122.5°	444.0	443.9	443.7	443.5
125°	481.4	481.4	481.4	481.4
127.5°	517.0	516.5	516.0	515.5
130°	553.4	552.9	552.4	551.9
132.5°	590.1	589.8	589.4	589.1
135°	624.0	622.9	621.9	620.9
137.5°	658.0	657.5	657.0	656.5
140°	693.2	692.9	692.5	692.2
142.5°	725.8	725.5	725.1	724.8
145°	756.4	755.7	755.0	754.3
147.5°	787.2	786.4	785.5	784.7
150°	814.0	813.3	812.7	812.0
152.5°	838.8	838.4	838.1	837.7
155°	864.3	864.3	864.3	864.3
157.5°	886.0	886.3	886.7	887.0
160°	906.2	906.4	906.5	906.7
162.5°	923.4	923.9	924.4	924.9
165°	939.4	939.9	940.4	940.9
167.5°	951.7	952.4	953.0	953.7
170°	961.9	962.7	963.6	964.4
172.5°	969.9	970.6	971.2	971.9
175°	976.3	977.1	978.0	978.8
177.5°	979.3	980.1	981.0	981.8
180°	980.3	980.3	980.3	980.3

(END OF REPORT)