

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034449

Luminaire Tested: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034449
REPORT IS A COMBINATION OF REPORTS P1003322 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7598.9 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66		
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56		
2	93	85	79	74	87	81	75	70	72	67	64	63	60	57	56	53	51	47		
3	85	75	68	62	80	71	65	59	63	58	54	56	52	49	50	46	44	40		
4	78	67	59	53	73	63	56	50	57	51	46	50	46	42	44	41	38	35		
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30		
6	66	54	45	40	62	51	43	38	46	40	35	41	36	32	36	32	29	27		
7	61	49	40	35	57	46	39	34	42	35	31	37	32	29	33	29	26	24		
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	31	26	23	21		
9	53	40	33	28	50	39	31	27	35	29	25	31	26	23	28	24	21	19		
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11339	11339	11339	11339
5°	11348	12863	11358	9759
10°	11278	14662	11259	8377
15°	11195	15897	11126	7569
20°	11054	17420	10953	6910
25°	10929	19960	10729	6520
30°	10748	21057	10562	6166
35°	10463	16880	10244	5882
40°	10018	11667	9871	5582
45°	9456	8686	9349	5332
50°	8812	7150	8667	5132
55°	8118	6099	8053	4959
60°	7436	5220	7307	4825
65°	6701	4508	6593	4629
70°	5925	3743	5846	4288
75°	5104	2894	5033	3721
80°	4030	1958	3884	2736
85°	2579	980	2493	1395

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17319 cd/sqm

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.3	2.2
10°-20°	507.3	6.7
20°-30°	824.1	10.8
30°-40°	1007.2	13.3
40°-50°	913.6	12.0
50°-60°	727.7	9.6
60°-70°	506.8	6.7
70°-80°	270.0	3.6
80°-90°	68.4	0.9
90°-100°	62.0	0.8
100°-110°	184.3	2.4
110°-120°	312.5	4.1
120°-130°	411.4	5.4
130°-140°	461.1	6.1
140°-150°	451.9	5.9
150°-160°	379.6	5.0
160°-170°	252.3	3.3
170°-180°	88.3	1.2
0°-30°	1501.8	19.8
0°-40°	2509.0	33.0
0°-60°	4150.2	54.6
0°-90°	4995.4	65.7
90°-120°	558.8	7.4
90°-150°	1883.3	24.8
90°-180°	2603.0	34.3
0°-180°	7598.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1770	1770	1770	1770	1770	
5°	1768	2042	1770	1549	1768	168
15°	1699	2550	1689	1214	1699	480
25°	1564	3137	1535	1025	1564	720
35°	1361	2518	1333	877	1361	850
45°	1070	1187	1058	729	1070	824
55°	753	732	747	595	753	673
65°	466	449	458	461	466	462
75°	225	221	222	284	225	240
85°	45	50	44	71	45	54
90°	1	17	1	17	1	6
95°	47	62	47	62	47	49
105°	166	180	166	180	166	176
115°	313	316	313	316	313	310
125°	457	460	457	460	457	409
135°	594	596	594	596	594	458
145°	719	722	719	722	719	450
155°	823	823	823	823	823	379
165°	895	893	895	893	895	253
175°	931	927	931	927	931	88
180°	933	933	933	933	933	

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1772.8	1783.3	1795.3	1804.3	1819.3	1823.8	1831.4	1835.9	1840.4	1844.9	1847.9
5°	1768.3	1793.8	1816.3	1832.9	1861.4	1871.9	1885.4	1902.0	1921.5	1938.0	1948.5
7.5°	1756.2	1796.8	1826.8	1859.9	1899.0	1924.5	1938.0	1972.6	2004.1	2028.2	2059.7
10°	1741.2	1789.3	1835.9	1885.4	1941.0	1969.6	1996.6	2044.7	2088.3	2127.3	2158.9
12.5°	1724.7	1783.3	1838.9	1903.5	1978.6	2013.1	2031.2	2113.8	2167.9	2188.9	2250.5
15°	1699.1	1768.3	1847.9	1927.5	1990.6	2031.2	2080.7	2146.8	2200.9	2247.5	2297.1
17.5°	1675.1	1750.2	1831.4	1920.0	2011.6	2064.2	2101.8	2160.4	2219.0	2279.1	2325.6
20°	1636.0	1733.7	1816.3	1911.0	2019.1	2056.7	2095.8	2164.9	2228.0	2292.6	2351.2
22.5°	1604.5	1697.6	1810.3	1900.5	1992.1	2029.7	2077.7	2149.8	2225.0	2298.6	2384.2
25°	1563.9	1667.6	1765.3	1861.4	1956.0	1996.6	2040.2	2133.3	2211.4	2306.1	2400.7
27.5°	1520.4	1627.0	1724.7	1811.8	1900.5	1956.0	2002.6	2100.3	2203.9	2307.6	2430.8
30°	1473.8	1574.5	1667.6	1753.2	1850.9	1908.0	1954.5	2068.7	2184.4	2316.6	2463.8
32.5°	1424.2	1518.9	1598.5	1685.6	1789.3	1841.9	1905.0	2029.7	2166.4	2324.1	2508.9
35°	1361.1	1451.3	1521.9	1610.5	1714.2	1781.8	1847.9	1987.6	2146.8	2322.6	2534.4
37.5°	1298.0	1368.6	1436.2	1530.9	1651.1	1712.7	1781.8	1935.0	2116.8	2318.1	2545.0
40°	1222.9	1292.0	1350.6	1446.8	1573.0	1643.6	1715.7	1876.4	2082.2	2301.6	2507.4
42.5°	1147.8	1206.4	1271.0	1371.6	1493.3	1568.4	1645.1	1823.8	2037.2	2253.5	2403.7
45°	1069.7	1114.7	1185.3	1277.0	1406.2	1478.3	1565.4	1759.2	1974.1	2166.4	2241.5
47.5°	988.5	1033.6	1099.7	1188.4	1316.1	1401.7	1484.3	1678.1	1894.5	2043.2	2043.2
50°	910.4	946.5	1011.1	1099.7	1228.9	1307.0	1391.2	1597.0	1771.3	1880.9	1783.3
52.5°	826.3	866.9	920.9	1014.1	1141.8	1212.4	1304.0	1479.8	1645.1	1690.1	1539.9
55°	752.7	785.7	836.8	925.4	1044.1	1117.7	1195.9	1364.1	1503.8	1500.8	1340.1
57.5°	676.1	703.1	757.2	838.3	948.0	1014.1	1092.2	1237.9	1352.1	1311.5	1159.8
60°	605.4	625.0	677.6	743.7	848.8	910.4	985.5	1104.2	1191.4	1134.3	981.0
62.5°	531.8	554.4	596.4	661.0	754.2	803.8	859.3	979.5	1035.1	984.0	827.8
65°	465.7	483.8	521.3	575.4	659.5	704.6	752.7	851.8	904.4	830.8	701.6
67.5°	399.6	420.7	447.7	495.8	561.9	603.9	646.0	731.6	755.7	689.6	581.4
70°	338.0	356.1	381.6	416.1	471.7	509.3	540.8	611.5	628.0	566.4	480.7
72.5°	277.9	290.0	311.0	339.5	390.6	411.6	444.7	492.8	513.8	458.2	396.6
75°	225.4	234.4	247.9	268.9	303.5	326.0	353.1	398.1	396.6	357.6	314.0
77.5°	174.3	175.8	190.8	210.3	231.4	250.9	264.4	296.0	299.0	274.9	238.9
80°	124.7	129.2	135.2	150.2	168.3	175.8	192.3	211.8	214.8	196.8	172.8
82.5°	79.6	82.6	87.1	96.1	108.2	117.2	126.2	133.7	141.2	130.7	111.2
85°	45.1	46.6	51.1	54.1	60.1	64.6	72.1	79.6	78.1	70.6	64.6
87.5°	22.5	22.5	22.5	25.5	28.5	28.5	31.5	33.1	34.6	31.5	28.5
90°	0.7	2.0	3.3	4.6	5.9	6.5	7.1	8.2	9.3	10.5	11.6
92.5°	21.8	22.6	23.4	24.2	25.0	25.4	26.1	27.6	29.0	30.5	31.9
95°	47.2	47.5	47.8	48.1	48.4	48.6	49.4	51.0	52.7	54.3	55.9
97.5°	72.6	72.8	72.9	73.1	73.2	73.3	74.4	76.7	79.0	81.2	83.5
100°	101.6	101.6	101.6	101.6	101.6	101.6	102.7	104.8	106.9	109.0	111.1
102.5°	132.9	133.7	134.5	135.3	136.1	136.5	136.9	137.7	138.5	139.3	140.1
105°	165.5	166.3	167.1	167.9	168.7	169.1	169.6	170.6	171.5	172.5	173.5
107.5°	201.1	201.9	202.7	203.5	204.3	204.7	205.1	205.9	206.8	207.6	208.4
110°	238.1	238.9	239.7	240.5	241.3	241.7	241.9	242.4	242.9	243.4	243.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	275.9	276.2	276.5	276.8	277.1	277.3	277.6	278.3	278.9	279.6	280.2
115°	312.9	313.5	314.2	314.8	315.5	315.8	316.0	316.3	316.6	316.9	317.2
117.5°	350.6	350.8	351.0	351.1	351.3	351.4	351.6	351.9	352.2	352.5	352.8
120°	385.5	386.3	387.1	387.9	388.7	389.1	389.2	389.3	389.5	389.6	389.8
122.5°	423.2	423.4	423.6	423.7	423.9	424.0	424.2	424.7	425.2	425.6	426.1
125°	456.6	457.6	458.6	459.5	460.5	461.0	461.1	461.2	461.4	461.5	461.7
127.5°	493.7	494.2	494.6	495.1	495.6	495.8	495.9	496.1	496.2	496.4	496.6
130°	526.3	527.1	527.9	528.8	529.6	530.0	530.2	530.5	530.8	531.1	531.4
132.5°	559.0	560.4	561.9	563.3	564.8	565.5	565.4	565.3	565.1	565.0	564.8
135°	593.8	594.8	595.8	596.7	597.7	598.2	598.3	598.4	598.6	598.7	598.9
137.5°	626.5	627.5	628.5	629.4	630.4	630.9	631.1	631.4	631.7	632.0	632.3
140°	657.7	658.5	659.3	660.2	661.0	661.4	661.6	662.1	662.6	663.0	663.5
142.5°	688.9	689.5	690.2	690.8	691.5	691.8	692.1	692.8	693.4	694.1	694.7
145°	719.4	720.0	720.7	721.3	722.0	722.3	722.5	723.0	723.5	724.0	724.5
147.5°	747.7	748.2	748.7	749.2	749.7	749.9	750.1	750.4	750.7	751.1	751.4
150°	776.1	775.9	775.7	775.6	775.4	775.3	775.6	776.3	776.9	777.6	778.2
152.5°	799.3	799.6	799.9	800.2	800.5	800.7	800.8	801.0	801.1	801.3	801.5
155°	823.2	823.2	823.2	823.2	823.2	823.2	823.3	823.5	823.6	823.8	824.0
157.5°	845.0	844.7	844.4	844.1	843.8	843.6	843.7	843.8	844.0	844.1	844.3
160°	863.9	863.4	862.9	862.4	861.9	861.7	861.8	861.9	862.1	862.2	862.4
162.5°	880.6	880.3	879.9	879.6	879.3	879.1	879.1	879.1	879.1	879.1	879.1
165°	895.1	894.8	894.5	894.2	893.9	893.7	893.8	893.9	894.1	894.2	894.4
167.5°	908.2	907.6	906.9	906.3	905.6	905.3	905.3	905.3	905.3	905.3	905.3
170°	918.3	917.7	917.0	916.4	915.7	915.4	915.4	915.4	915.4	915.4	915.4
172.5°	925.6	925.0	924.3	923.7	923.0	922.7	922.7	922.7	922.7	922.7	922.7
175°	930.7	930.1	929.4	928.8	928.1	927.8	927.8	927.8	927.8	927.8	927.8
177.5°	934.3	933.7	933.0	932.4	931.7	931.4	931.3	931.2	931.0	930.9	930.7
180°	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1850.9	1861.4	1870.4	1877.9	1883.9	1892.9	1886.9	1888.4	1891.4	1897.5	1897.5
5°	1971.1	1987.6	1996.6	2026.7	2034.2	2032.7	2028.2	2052.2	2050.7	2041.7	2040.2
7.5°	2088.3	2116.8	2142.3	2166.4	2173.9	2193.4	2197.9	2208.4	2205.4	2220.5	2212.9
10°	2194.9	2240.0	2264.0	2300.1	2309.1	2318.1	2330.1	2336.1	2349.7	2348.2	2348.2
12.5°	2277.5	2331.6	2363.2	2372.2	2406.8	2417.3	2427.8	2447.3	2442.8	2444.3	2453.3
15°	2342.1	2394.7	2421.8	2463.8	2487.9	2499.9	2517.9	2539.0	2536.0	2549.5	2546.5
17.5°	2390.2	2439.8	2489.4	2552.5	2554.0	2585.5	2627.6	2636.6	2656.1	2642.6	2642.6
20°	2429.3	2495.4	2566.0	2647.1	2656.1	2675.7	2726.7	2761.3	2783.8	2776.3	2780.8
22.5°	2471.4	2566.0	2648.6	2729.8	2773.3	2807.9	2857.5	2911.5	2931.1	2943.1	2940.1
25°	2525.4	2624.6	2746.3	2859.0	2904.0	2970.1	3036.2	3088.8	3103.8	3136.9	3106.8
27.5°	2581.0	2720.7	2872.5	3004.7	3061.8	3115.9	3195.5	3234.5	3254.1	3269.1	3258.6
30°	2627.6	2819.9	2985.2	3106.8	3147.4	3179.0	3224.0	3233.0	3225.5	3237.5	3252.6
32.5°	2699.7	2887.5	3027.2	3085.8	3081.3	3079.8	3045.2	2997.2	2986.7	2958.1	2997.2
35°	2738.8	2889.0	2943.1	2865.0	2833.4	2776.3	2666.7	2594.5	2531.4	2517.9	2520.9
37.5°	2716.2	2774.8	2710.2	2504.4	2453.3	2366.2	2220.5	2118.3	2071.7	2035.7	2082.2
40°	2594.5	2529.9	2352.7	2101.8	2028.2	1945.5	1808.8	1753.2	1687.1	1673.6	1735.2
42.5°	2393.2	2196.4	1945.5	1751.7	1675.1	1628.5	1514.4	1461.8	1415.2	1394.2	1428.7
45°	2119.8	1880.9	1628.5	1469.3	1404.7	1349.1	1281.5	1225.9	1195.9	1186.8	1215.4
47.5°	1837.4	1585.0	1383.7	1265.0	1197.4	1155.3	1092.2	1060.7	1036.6	1039.6	1044.1
50°	1566.9	1337.1	1182.3	1063.7	1030.6	997.6	955.5	928.4	916.4	920.9	917.9
52.5°	1334.1	1147.8	1017.1	925.4	910.4	878.9	844.3	821.8	817.3	818.8	823.3
55°	1129.8	984.0	880.4	814.3	797.7	775.2	754.2	739.2	727.1	731.6	730.1
57.5°	975.0	847.3	767.7	713.6	701.6	688.1	668.5	661.0	656.5	647.5	655.0
60°	838.3	734.6	665.5	632.5	622.0	613.0	591.9	582.9	579.9	575.4	587.4
62.5°	709.1	635.5	582.9	552.9	542.3	533.3	522.8	515.3	516.8	510.8	516.8
65°	606.9	546.9	509.3	482.3	468.7	462.7	461.2	449.2	447.7	449.2	450.7
67.5°	512.3	461.2	432.7	416.1	405.6	399.6	395.1	387.6	393.6	389.1	392.1
70°	426.7	392.1	362.1	345.5	341.0	342.5	335.0	332.0	333.5	330.5	333.5
72.5°	344.0	315.5	303.5	291.5	285.4	283.9	279.4	274.9	279.4	277.9	277.9
75°	274.9	253.9	240.4	232.9	232.9	229.9	222.3	222.3	222.3	220.8	222.3
77.5°	211.8	193.8	187.8	180.3	180.3	175.8	174.3	174.3	171.3	175.8	172.8
80°	157.7	144.2	135.2	130.7	130.7	129.2	126.2	124.7	126.2	124.7	124.7
82.5°	102.2	96.1	91.6	87.1	85.6	87.1	85.6	82.6	84.1	82.6	85.6
85°	58.6	52.6	52.6	49.6	51.1	48.1	49.6	46.6	45.1	49.6	46.6
87.5°	25.5	24.0	24.0	21.0	21.0	21.0	19.5	21.0	19.5	18.0	19.5
90°	12.4	13.2	14.0	14.8	15.2	15.4	15.9	16.4	16.9	17.4	16.9
92.5°	33.0	34.2	35.3	36.4	37.0	37.2	37.5	37.8	38.2	38.5	38.2
95°	57.0	58.2	59.3	60.4	61.0	61.2	61.5	61.8	62.1	62.4	62.1
97.5°	84.5	85.4	86.4	87.3	87.8	87.9	88.1	88.2	88.4	88.6	88.4
100°	112.5	114.0	115.4	116.9	117.6	117.8	118.1	118.4	118.8	119.1	118.8
102.5°	141.7	143.3	145.0	146.6	147.4	147.6	148.1	148.6	149.0	149.5	149.0
105°	174.5	175.5	176.4	177.4	177.9	178.1	178.6	179.1	179.5	180.0	179.5
107.5°	208.9	209.3	209.8	210.3	210.5	210.5	210.5	210.5	210.5	210.5	210.5
110°	244.4	244.9	245.4	245.9	246.1	246.0	245.9	245.7	245.6	245.4	245.6

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	280.4	280.5	280.7	280.8	280.9	280.7	280.4	280.1	279.8	279.5	279.8
115°	317.0	316.9	316.7	316.6	316.5	316.4	316.3	316.1	316.0	315.8	316.0
117.5°	353.0	353.1	353.3	353.4	353.5	353.2	352.5	351.9	351.2	350.6	351.2
120°	389.8	389.8	389.8	389.8	389.8	389.5	388.8	388.2	387.5	386.9	387.5
122.5°	425.9	425.8	425.6	425.5	425.4	425.2	424.7	424.2	423.7	423.2	423.7
125°	461.4	461.1	460.8	460.5	460.3	460.2	460.0	459.9	459.7	459.5	459.7
127.5°	496.4	496.2	496.1	495.9	495.8	495.6	495.3	495.0	494.7	494.4	494.7
130°	531.2	531.1	530.9	530.8	530.7	530.5	530.2	529.9	529.5	529.2	529.5
132.5°	564.6	564.5	564.3	564.2	564.1	563.9	563.4	562.9	562.4	561.9	562.4
135°	598.9	598.9	598.9	598.9	598.9	598.6	597.9	597.3	596.6	596.0	596.6
137.5°	632.5	632.6	632.8	632.9	633.0	632.6	631.8	631.0	630.2	629.4	630.2
140°	663.8	664.2	664.5	664.8	665.0	664.6	663.8	663.0	662.2	661.4	662.2
142.5°	694.9	695.1	695.2	695.4	695.5	695.1	694.3	693.4	692.6	691.8	692.6
145°	724.5	724.5	724.5	724.5	724.5	724.3	723.8	723.3	722.8	722.3	722.8
147.5°	751.9	752.4	752.9	753.4	753.6	752.9	751.6	750.3	749.0	747.7	749.0
150°	778.2	778.2	778.2	778.2	778.2	778.0	777.7	777.4	777.1	776.8	777.1
152.5°	802.0	802.4	802.9	803.4	803.6	803.3	802.6	802.0	801.3	800.7	801.3
155°	824.6	825.3	825.9	826.6	826.9	826.5	825.7	824.8	824.0	823.2	824.0
157.5°	844.9	845.6	846.2	846.9	847.2	846.6	845.5	844.4	843.2	842.1	843.2
160°	863.0	863.7	864.3	865.0	865.3	864.9	864.1	863.3	862.5	861.7	862.5
162.5°	879.9	880.7	881.6	882.4	882.8	882.3	881.3	880.4	879.4	878.4	879.4
165°	895.0	895.7	896.3	897.0	897.3	896.8	895.8	894.9	893.9	892.9	893.9
167.5°	906.3	907.2	908.2	909.1	909.6	909.1	908.2	907.2	906.3	905.3	906.3
170°	916.4	917.4	918.3	919.3	919.8	919.2	918.1	917.0	915.8	914.7	915.8
172.5°	923.7	924.7	925.6	926.6	927.1	926.6	925.6	924.7	923.7	922.7	923.7
175°	928.8	929.7	930.7	931.6	932.1	931.5	930.4	929.3	928.2	927.1	928.2
177.5°	931.7	932.6	933.6	934.5	935.0	934.4	933.3	932.2	931.1	930.0	931.1
180°	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1894.5	1883.9	1886.9	1883.9	1876.4	1871.9	1859.9	1844.9	1838.9	1831.4	1826.8
5°	2046.2	2038.7	2037.2	2025.2	2022.2	2004.1	1974.1	1959.1	1941.0	1923.0	1905.0
7.5°	2211.4	2202.4	2172.4	2167.9	2170.9	2148.3	2109.3	2079.2	2041.7	2016.1	1981.6
10°	2348.2	2330.1	2304.6	2306.1	2295.6	2265.5	2226.5	2194.9	2140.8	2107.8	2058.2
12.5°	2430.8	2415.8	2412.8	2397.7	2388.7	2349.7	2303.1	2262.5	2222.0	2176.9	2139.3
15°	2531.4	2511.9	2498.4	2477.4	2471.4	2430.8	2379.7	2333.1	2286.6	2244.5	2164.9
17.5°	2642.6	2621.6	2570.5	2566.0	2529.9	2490.9	2441.3	2372.2	2322.6	2262.5	2203.9
20°	2768.8	2738.8	2672.7	2656.1	2627.6	2563.0	2495.4	2418.8	2339.1	2277.5	2208.4
22.5°	2910.0	2857.5	2809.4	2756.8	2735.8	2656.1	2563.0	2469.8	2373.7	2289.6	2206.9
25°	3093.3	3024.2	2956.6	2904.0	2868.0	2764.3	2639.6	2516.4	2405.2	2295.6	2187.4
27.5°	3237.5	3177.5	3103.8	3034.7	2988.2	2865.0	2722.2	2563.0	2424.8	2291.1	2175.4
30°	3248.1	3230.0	3185.0	3147.4	3096.3	2964.1	2806.4	2626.1	2454.8	2292.6	2151.4
32.5°	3051.3	3087.3	3106.8	3112.9	3102.3	3025.7	2881.5	2683.2	2481.9	2279.1	2130.3
35°	2627.6	2723.7	2842.4	2887.5	2931.1	2971.6	2896.5	2723.7	2490.9	2276.0	2097.3
37.5°	2163.4	2250.5	2447.3	2537.5	2588.5	2749.3	2810.9	2717.7	2508.9	2279.1	2065.7
40°	1745.7	1883.9	2025.2	2146.8	2226.5	2406.8	2597.5	2618.6	2483.4	2250.5	2025.2
42.5°	1469.3	1550.4	1657.1	1769.8	1840.4	2053.7	2312.1	2463.8	2403.7	2203.9	1975.6
45°	1251.5	1311.5	1412.2	1449.8	1539.9	1744.2	2017.6	2237.0	2267.0	2130.3	1918.5
47.5°	1074.2	1125.3	1189.9	1236.4	1308.5	1461.8	1693.1	1935.0	2079.2	2029.7	1838.9
50°	946.5	988.5	1042.6	1069.7	1116.2	1254.5	1428.7	1669.1	1862.9	1879.4	1735.2
52.5°	839.8	863.8	905.9	936.0	973.5	1057.6	1215.4	1413.7	1631.5	1721.7	1607.5
55°	746.7	766.2	803.8	823.3	842.8	914.9	1038.1	1218.4	1422.7	1541.4	1476.8
57.5°	662.5	679.1	710.6	728.6	739.2	808.3	902.9	1044.1	1227.4	1371.6	1335.6
60°	593.4	608.4	626.5	640.0	652.0	709.1	775.2	889.4	1053.1	1192.9	1183.8
62.5°	519.8	533.3	552.9	566.4	576.9	613.0	668.5	755.7	895.4	1024.6	1050.1
65°	455.2	465.7	479.2	485.3	498.8	525.8	570.9	649.0	763.2	878.9	896.9
67.5°	396.6	399.6	408.6	422.2	425.2	449.2	489.8	548.4	637.0	731.6	760.2
70°	333.5	338.0	345.5	356.1	362.1	377.1	411.6	450.7	527.3	610.0	631.0
72.5°	277.9	283.9	286.9	293.0	296.0	320.0	335.0	374.1	426.7	495.8	518.3
75°	225.4	231.4	232.9	235.9	238.9	249.4	270.4	294.5	338.0	383.1	413.1
77.5°	178.8	177.3	180.3	184.8	183.3	192.3	205.8	226.9	255.4	293.0	312.5
80°	126.2	126.2	130.7	135.2	133.7	142.7	147.2	162.3	186.3	210.3	217.8
82.5°	84.1	84.1	88.6	88.6	91.6	93.1	99.2	106.7	126.2	138.2	142.7
85°	48.1	48.1	49.6	49.6	49.6	52.6	57.1	60.1	66.1	73.6	76.6
87.5°	19.5	21.0	21.0	21.0	21.0	24.0	24.0	27.0	28.5	31.5	31.5
90°	16.4	15.9	15.4	15.2	14.8	14.0	13.2	12.4	11.6	10.5	9.3
92.5°	37.8	37.5	37.2	37.0	36.4	35.3	34.2	33.0	31.9	30.5	29.0
95°	61.8	61.5	61.2	61.0	60.4	59.3	58.2	57.0	55.9	54.3	52.7
97.5°	88.2	88.1	87.9	87.8	87.3	86.4	85.4	84.5	83.5	81.2	79.0
100°	118.4	118.1	117.8	117.6	116.9	115.4	114.0	112.5	111.1	109.0	106.9
102.5°	148.6	148.1	147.6	147.4	146.6	145.0	143.3	141.7	140.1	139.3	138.5
105°	179.1	178.6	178.1	177.9	177.4	176.4	175.5	174.5	173.5	172.5	171.5
107.5°	210.5	210.5	210.5	210.5	210.3	209.8	209.3	208.9	208.4	207.6	206.8
110°	245.7	245.9	246.0	246.1	245.9	245.4	244.9	244.4	243.9	243.4	242.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	280.1	280.4	280.7	280.9	280.8	280.7	280.5	280.4	280.2	279.6	278.9
115°	316.1	316.3	316.4	316.5	316.6	316.7	316.9	317.0	317.2	316.9	316.6
117.5°	351.9	352.5	353.2	353.5	353.4	353.3	353.1	353.0	352.8	352.5	352.2
120°	388.2	388.8	389.5	389.8	389.8	389.8	389.8	389.8	389.8	389.6	389.5
122.5°	424.2	424.7	425.2	425.4	425.5	425.6	425.8	425.9	426.1	425.6	425.2
125°	459.9	460.0	460.2	460.3	460.5	460.8	461.1	461.4	461.7	461.5	461.4
127.5°	495.0	495.3	495.6	495.8	495.9	496.1	496.2	496.4	496.6	496.4	496.2
130°	529.9	530.2	530.5	530.7	530.8	530.9	531.1	531.2	531.4	531.1	530.8
132.5°	562.9	563.4	563.9	564.1	564.2	564.3	564.5	564.6	564.8	565.0	565.1
135°	597.3	597.9	598.6	598.9	598.9	598.9	598.9	598.9	598.9	598.7	598.6
137.5°	631.0	631.8	632.6	633.0	632.9	632.8	632.6	632.5	632.3	632.0	631.7
140°	663.0	663.8	664.6	665.0	664.8	664.5	664.2	663.8	663.5	663.0	662.6
142.5°	693.4	694.3	695.1	695.5	695.4	695.2	695.1	694.9	694.7	694.1	693.4
145°	723.3	723.8	724.3	724.5	724.5	724.5	724.5	724.5	724.5	724.0	723.5
147.5°	750.3	751.6	752.9	753.6	753.4	752.9	752.4	751.9	751.4	751.1	750.7
150°	777.4	777.7	778.0	778.2	778.2	778.2	778.2	778.2	778.2	777.6	776.9
152.5°	802.0	802.6	803.3	803.6	803.4	802.9	802.4	802.0	801.5	801.3	801.1
155°	824.8	825.7	826.5	826.9	826.6	825.9	825.3	824.6	824.0	823.8	823.6
157.5°	844.4	845.5	846.6	847.2	846.9	846.2	845.6	844.9	844.3	844.1	844.0
160°	863.3	864.1	864.9	865.3	865.0	864.3	863.7	863.0	862.4	862.2	862.1
162.5°	880.4	881.3	882.3	882.8	882.4	881.6	880.7	879.9	879.1	879.1	879.1
165°	894.9	895.8	896.8	897.3	897.0	896.3	895.7	895.0	894.4	894.2	894.1
167.5°	907.2	908.2	909.1	909.6	909.1	908.2	907.2	906.3	905.3	905.3	905.3
170°	917.0	918.1	919.2	919.8	919.3	918.3	917.4	916.4	915.4	915.4	915.4
172.5°	924.7	925.6	926.6	927.1	926.6	925.6	924.7	923.7	922.7	922.7	922.7
175°	929.3	930.4	931.5	932.1	931.6	930.7	929.7	928.8	927.8	927.8	927.8
177.5°	932.2	933.3	934.4	935.0	934.5	933.6	932.6	931.7	930.7	930.9	931.0
180°	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1820.8	1813.3	1804.3	1804.3	1793.8	1789.3	1780.3	1777.3	1769.8	1757.7	1748.7
5°	1885.4	1865.9	1853.9	1843.4	1820.8	1804.3	1787.8	1769.8	1751.7	1730.7	1706.7
7.5°	1948.5	1912.5	1896.0	1877.9	1844.9	1810.3	1777.3	1753.2	1729.2	1696.1	1666.1
10°	2014.6	1969.6	1939.5	1915.5	1864.4	1820.8	1772.8	1738.2	1700.6	1658.6	1619.5
12.5°	2070.2	2011.6	1986.1	1941.0	1882.4	1829.9	1769.8	1717.2	1667.6	1618.0	1569.9
15°	2116.8	2061.2	1998.1	1980.1	1899.0	1823.8	1756.2	1688.6	1627.0	1577.5	1521.9
17.5°	2131.8	2061.2	2029.7	1986.1	1889.9	1811.8	1726.2	1652.6	1594.0	1520.4	1476.8
20°	2136.3	2068.7	2025.2	1984.6	1899.0	1795.3	1711.2	1621.0	1550.4	1476.8	1407.7
22.5°	2124.3	2044.7	2002.6	1963.6	1867.4	1778.8	1681.1	1582.0	1499.3	1431.7	1362.6
25°	2101.8	2008.6	1968.1	1926.0	1834.4	1736.7	1630.0	1535.4	1458.8	1377.6	1310.0
27.5°	2071.7	1965.1	1918.5	1874.9	1784.8	1693.1	1592.5	1494.8	1409.2	1323.6	1260.5
30°	2034.2	1911.0	1868.9	1811.8	1724.7	1637.6	1545.9	1448.3	1352.1	1271.0	1201.9
32.5°	1986.1	1856.9	1801.3	1747.2	1652.6	1573.0	1485.8	1394.2	1301.0	1221.4	1149.3
35°	1942.5	1795.3	1733.7	1679.6	1574.5	1490.3	1418.2	1332.6	1249.9	1167.3	1102.7
37.5°	1883.9	1733.7	1660.1	1604.5	1497.8	1412.2	1344.6	1278.5	1191.4	1111.7	1051.6
40°	1822.3	1657.1	1588.0	1532.4	1421.2	1328.1	1263.5	1204.9	1134.3	1060.7	997.6
42.5°	1766.8	1583.5	1509.9	1442.2	1329.6	1246.9	1180.8	1135.8	1071.2	1005.1	948.0
45°	1696.1	1505.3	1425.7	1355.1	1246.9	1156.8	1093.7	1057.6	1009.6	945.0	895.4
47.5°	1624.0	1421.2	1338.6	1269.5	1152.3	1072.7	1011.1	976.5	943.5	892.4	842.8
50°	1529.4	1332.6	1257.5	1177.8	1062.2	981.0	929.9	895.4	869.9	833.8	791.7
52.5°	1425.7	1240.9	1159.8	1090.7	976.5	902.9	844.3	824.8	799.2	772.2	736.1
55°	1316.1	1141.8	1063.7	996.1	890.9	815.8	767.7	746.7	727.1	706.1	682.1
57.5°	1206.4	1038.1	964.5	904.4	806.8	734.6	695.6	667.0	653.5	641.5	622.0
60°	1069.7	926.9	869.9	815.8	719.6	653.5	616.0	594.9	582.9	576.9	567.9
62.5°	949.5	832.3	769.2	716.6	640.0	581.4	545.3	528.8	518.3	515.3	504.8
65°	821.8	721.1	671.5	626.5	560.4	507.8	477.7	458.2	450.7	449.2	449.2
67.5°	701.6	620.5	570.9	539.3	482.3	435.7	407.1	399.6	395.1	389.1	387.6
70°	588.9	524.3	480.7	453.7	402.6	368.1	345.5	333.5	333.5	329.0	326.0
72.5°	489.8	425.2	396.6	374.1	332.0	302.0	285.4	282.4	271.9	270.4	270.4
75°	383.1	335.0	315.5	296.0	264.4	243.4	229.9	222.3	216.3	216.3	217.8
77.5°	288.4	255.4	237.4	222.3	199.8	186.3	175.8	172.8	166.8	166.8	166.8
80°	204.3	186.3	172.8	160.8	144.2	132.2	126.2	120.2	120.2	118.7	120.2
82.5°	132.2	117.2	109.7	108.2	93.1	88.6	81.1	82.6	78.1	76.6	79.6
85°	76.6	69.1	60.1	57.1	51.1	45.1	42.1	43.6	42.1	40.6	42.1
87.5°	30.0	25.5	24.0	24.0	19.5	18.0	16.5	18.0	15.0	15.0	16.5
90°	8.2	7.1	6.5	5.9	4.6	3.3	2.0	0.7	2.0	3.3	4.6
92.5°	27.6	26.1	25.4	25.0	24.2	23.4	22.6	21.8	22.6	23.4	24.2
95°	51.0	49.4	48.6	48.4	48.1	47.8	47.5	47.2	47.5	47.8	48.1
97.5°	76.7	74.4	73.3	73.2	73.1	72.9	72.8	72.6	72.8	72.9	73.1
100°	104.8	102.7	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6
102.5°	137.7	136.9	136.5	136.1	135.3	134.5	133.7	132.9	133.7	134.5	135.3
105°	170.6	169.6	169.1	168.7	167.9	167.1	166.3	165.5	166.3	167.1	167.9
107.5°	205.9	205.1	204.7	204.3	203.5	202.7	201.9	201.1	201.9	202.7	203.5
110°	242.4	241.9	241.7	241.3	240.5	239.7	238.9	238.1	238.9	239.7	240.5

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	278.3	277.6	277.3	277.1	276.8	276.5	276.2	275.9	276.2	276.5	276.8
115°	316.3	316.0	315.8	315.5	314.8	314.2	313.5	312.9	313.5	314.2	314.8
117.5°	351.9	351.6	351.4	351.3	351.1	351.0	350.8	350.6	350.8	351.0	351.1
120°	389.3	389.2	389.1	388.7	387.9	387.1	386.3	385.5	386.3	387.1	387.9
122.5°	424.7	424.2	424.0	423.9	423.7	423.6	423.4	423.2	423.4	423.6	423.7
125°	461.2	461.1	461.0	460.5	459.5	458.6	457.6	456.6	457.6	458.6	459.5
127.5°	496.1	495.9	495.8	495.6	495.1	494.6	494.2	493.7	494.2	494.6	495.1
130°	530.5	530.2	530.0	529.6	528.8	527.9	527.1	526.3	527.1	527.9	528.8
132.5°	565.3	565.4	565.5	564.8	563.3	561.9	560.4	559.0	560.4	561.9	563.3
135°	598.4	598.3	598.2	597.7	596.7	595.8	594.8	593.8	594.8	595.8	596.7
137.5°	631.4	631.1	630.9	630.4	629.4	628.5	627.5	626.5	627.5	628.5	629.4
140°	662.1	661.6	661.4	661.0	660.2	659.3	658.5	657.7	658.5	659.3	660.2
142.5°	692.8	692.1	691.8	691.5	690.8	690.2	689.5	688.9	689.5	690.2	690.8
145°	723.0	722.5	722.3	722.0	721.3	720.7	720.0	719.4	720.0	720.7	721.3
147.5°	750.4	750.1	749.9	749.7	749.2	748.7	748.2	747.7	748.2	748.7	749.2
150°	776.3	775.6	775.3	775.4	775.6	775.7	775.9	776.1	775.9	775.7	775.6
152.5°	801.0	800.8	800.7	800.5	800.2	799.9	799.6	799.3	799.6	799.9	800.2
155°	823.5	823.3	823.2	823.2	823.2	823.2	823.2	823.2	823.2	823.2	823.2
157.5°	843.8	843.7	843.6	843.8	844.1	844.4	844.7	845.0	844.7	844.4	844.1
160°	861.9	861.8	861.7	861.9	862.4	862.9	863.4	863.9	863.4	862.9	862.4
162.5°	879.1	879.1	879.1	879.3	879.6	879.9	880.3	880.6	880.3	879.9	879.6
165°	893.9	893.8	893.7	893.9	894.2	894.5	894.8	895.1	894.8	894.5	894.2
167.5°	905.3	905.3	905.3	905.6	906.3	906.9	907.6	908.2	907.6	906.9	906.3
170°	915.4	915.4	915.4	915.7	916.4	917.0	917.7	918.3	917.7	917.0	916.4
172.5°	922.7	922.7	922.7	923.0	923.7	924.3	925.0	925.6	925.0	924.3	923.7
175°	927.8	927.8	927.8	928.1	928.8	929.4	930.1	930.7	930.1	929.4	928.8
177.5°	931.2	931.3	931.4	931.7	932.4	933.0	933.7	934.3	933.7	933.0	932.4
180°	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1745.7	1742.7	1735.2	1730.7	1715.7	1697.6	1691.6	1676.6	1682.6	1672.1	1672.1
5°	1699.1	1685.6	1676.6	1663.1	1634.5	1615.0	1594.0	1583.5	1577.5	1569.9	1563.9
7.5°	1639.1	1628.5	1619.5	1594.0	1562.4	1535.4	1509.9	1499.3	1479.8	1466.3	1460.3
10°	1586.5	1571.4	1550.4	1520.4	1487.3	1452.8	1430.2	1407.7	1392.7	1385.2	1368.6
12.5°	1532.4	1514.4	1491.8	1448.3	1412.2	1391.2	1350.6	1329.6	1322.1	1316.1	1296.5
15°	1476.8	1457.3	1430.2	1389.7	1358.1	1308.5	1284.5	1268.0	1249.9	1248.4	1233.4
17.5°	1427.2	1403.2	1380.7	1331.1	1292.0	1248.4	1234.9	1216.9	1200.4	1182.3	1174.8
20°	1364.1	1341.6	1325.1	1271.0	1227.4	1200.4	1177.8	1162.8	1152.3	1134.3	1131.3
22.5°	1307.0	1283.0	1260.5	1219.9	1182.3	1147.8	1120.7	1104.2	1099.7	1092.2	1078.7
25°	1251.5	1227.4	1200.4	1162.8	1123.8	1099.7	1075.7	1065.2	1056.1	1044.1	1033.6
27.5°	1204.9	1182.3	1156.8	1110.2	1077.2	1059.2	1033.6	1021.6	1009.6	1003.6	999.1
30°	1149.3	1123.8	1104.2	1068.2	1032.1	1008.1	990.0	979.5	969.0	963.0	960.0
32.5°	1095.2	1071.2	1057.6	1018.6	990.0	961.5	948.0	940.5	934.5	928.4	922.4
35°	1051.6	1027.6	1006.6	970.5	942.0	922.4	911.9	899.9	895.4	889.4	889.4
37.5°	997.6	979.5	958.5	923.9	898.4	883.4	874.4	859.3	857.8	854.8	850.3
40°	951.0	933.0	913.4	883.4	860.8	842.8	830.8	823.3	818.8	815.8	812.8
42.5°	901.4	881.9	872.9	838.3	818.8	800.7	794.7	787.2	785.7	779.7	772.2
45°	853.3	836.8	818.8	793.2	776.7	761.7	752.7	746.7	739.2	737.6	733.1
47.5°	811.3	791.7	775.2	751.2	733.1	721.1	713.6	706.1	700.1	695.6	691.1
50°	757.2	742.2	728.6	703.1	688.1	676.1	665.5	659.5	653.5	653.5	653.5
52.5°	704.6	691.1	679.1	661.0	643.0	632.5	620.5	616.0	613.0	608.4	613.0
55°	653.5	640.0	628.0	614.5	593.4	584.4	572.4	567.9	569.4	569.4	573.9
57.5°	599.4	588.9	581.4	564.9	545.3	536.3	528.8	524.3	524.3	530.3	531.8
60°	546.9	536.3	522.8	507.8	495.8	485.3	480.7	482.3	482.3	485.3	492.8
62.5°	488.3	482.3	474.7	453.7	446.2	438.7	432.7	437.2	435.7	443.2	453.7
65°	434.2	428.2	417.7	407.1	398.1	390.6	389.1	390.6	393.6	401.1	413.1
67.5°	374.1	374.1	365.1	356.1	348.5	341.0	342.5	344.0	347.0	356.1	374.1
70°	324.5	318.5	309.5	303.5	297.5	294.5	291.5	297.5	306.5	312.5	326.0
72.5°	270.4	265.9	258.4	252.4	250.9	247.9	246.4	249.4	258.4	268.9	283.9
75°	213.3	214.8	210.3	205.8	205.8	201.3	204.3	204.3	213.3	223.8	235.9
77.5°	165.3	163.8	162.3	159.2	157.7	157.7	157.7	160.8	169.8	175.8	187.8
80°	117.2	118.7	114.2	115.7	114.2	115.7	115.7	121.7	126.2	133.7	142.7
82.5°	78.1	78.1	75.1	76.6	76.6	76.6	78.1	81.1	87.1	93.1	99.2
85°	43.6	45.1	42.1	45.1	45.1	45.1	46.6	48.1	52.6	54.1	60.1
87.5°	16.5	19.5	19.5	16.5	18.0	19.5	21.0	19.5	22.5	25.5	27.0
90°	5.9	6.5	7.1	8.2	9.3	10.5	11.6	12.4	13.2	14.0	14.8
92.5°	25.0	25.4	26.1	27.6	29.0	30.5	31.9	33.0	34.2	35.3	36.4
95°	48.4	48.6	49.4	51.0	52.7	54.3	55.9	57.0	58.2	59.3	60.4
97.5°	73.2	73.3	74.4	76.7	79.0	81.2	83.5	84.5	85.4	86.4	87.3
100°	101.6	101.6	102.7	104.8	106.9	109.0	111.1	112.5	114.0	115.4	116.9
102.5°	136.1	136.5	136.9	137.7	138.5	139.3	140.1	141.7	143.3	145.0	146.6
105°	168.7	169.1	169.6	170.6	171.5	172.5	173.5	174.5	175.5	176.4	177.4
107.5°	204.3	204.7	205.1	205.9	206.8	207.6	208.4	208.9	209.3	209.8	210.3
110°	241.3	241.7	241.9	242.4	242.9	243.4	243.9	244.4	244.9	245.4	245.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	277.1	277.3	277.6	278.3	278.9	279.6	280.2	280.4	280.5	280.7	280.8
115°	315.5	315.8	316.0	316.3	316.6	316.9	317.2	317.0	316.9	316.7	316.6
117.5°	351.3	351.4	351.6	351.9	352.2	352.5	352.8	353.0	353.1	353.3	353.4
120°	388.7	389.1	389.2	389.3	389.5	389.6	389.8	389.8	389.8	389.8	389.8
122.5°	423.9	424.0	424.2	424.7	425.2	425.6	426.1	425.9	425.8	425.6	425.5
125°	460.5	461.0	461.1	461.2	461.4	461.5	461.7	461.4	461.1	460.8	460.5
127.5°	495.6	495.8	495.9	496.1	496.2	496.4	496.6	496.4	496.2	496.1	495.9
130°	529.6	530.0	530.2	530.5	530.8	531.1	531.4	531.2	531.1	530.9	530.8
132.5°	564.8	565.5	565.4	565.3	565.1	565.0	564.8	564.6	564.5	564.3	564.2
135°	597.7	598.2	598.3	598.4	598.6	598.7	598.9	598.9	598.9	598.9	598.9
137.5°	630.4	630.9	631.1	631.4	631.7	632.0	632.3	632.5	632.6	632.8	632.9
140°	661.0	661.4	661.6	662.1	662.6	663.0	663.5	663.8	664.2	664.5	664.8
142.5°	691.5	691.8	692.1	692.8	693.4	694.1	694.7	694.9	695.1	695.2	695.4
145°	722.0	722.3	722.5	723.0	723.5	724.0	724.5	724.5	724.5	724.5	724.5
147.5°	749.7	749.9	750.1	750.4	750.7	751.1	751.4	751.9	752.4	752.9	753.4
150°	775.4	775.3	775.6	776.3	776.9	777.6	778.2	778.2	778.2	778.2	778.2
152.5°	800.5	800.7	800.8	801.0	801.1	801.3	801.5	802.0	802.4	802.9	803.4
155°	823.2	823.2	823.3	823.5	823.6	823.8	824.0	824.6	825.3	825.9	826.6
157.5°	843.8	843.6	843.7	843.8	844.0	844.1	844.3	844.9	845.6	846.2	846.9
160°	861.9	861.7	861.8	861.9	862.1	862.2	862.4	863.0	863.7	864.3	865.0
162.5°	879.3	879.1	879.1	879.1	879.1	879.1	879.1	879.9	880.7	881.6	882.4
165°	893.9	893.7	893.8	893.9	894.1	894.2	894.4	895.0	895.7	896.3	897.0
167.5°	905.6	905.3	905.3	905.3	905.3	905.3	905.3	906.3	907.2	908.2	909.1
170°	915.7	915.4	915.4	915.4	915.4	915.4	915.4	916.4	917.4	918.3	919.3
172.5°	923.0	922.7	922.7	922.7	922.7	922.7	922.7	923.7	924.7	925.6	926.6
175°	928.1	927.8	927.8	927.8	927.8	927.8	927.8	928.8	929.7	930.7	931.6
177.5°	931.7	931.4	931.3	931.2	931.0	930.9	930.7	931.7	932.6	933.6	934.5
180°	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1678.1	1667.6	1666.1	1669.1	1663.1	1672.1	1669.1	1672.1	1664.6	1672.1	1667.6
5°	1562.4	1559.4	1553.4	1545.9	1547.4	1548.9	1556.4	1548.9	1554.9	1556.4	1563.9
7.5°	1454.3	1448.3	1452.8	1449.8	1436.2	1433.2	1436.2	1440.7	1449.8	1455.8	1460.3
10°	1367.1	1364.1	1358.1	1353.6	1346.1	1341.6	1347.6	1341.6	1353.6	1364.1	1364.1
12.5°	1301.0	1289.0	1281.5	1280.0	1263.5	1266.5	1272.5	1277.0	1290.5	1296.5	1296.5
15°	1231.9	1222.9	1219.9	1213.9	1207.9	1213.9	1210.9	1215.4	1221.4	1227.4	1230.4
17.5°	1171.8	1170.3	1171.8	1156.8	1161.3	1153.8	1155.3	1162.8	1158.3	1162.8	1171.8
20°	1117.7	1120.7	1116.2	1110.2	1110.2	1101.2	1111.7	1108.7	1110.2	1119.2	1132.8
22.5°	1077.2	1075.7	1071.2	1066.7	1060.7	1062.2	1063.7	1060.7	1072.7	1080.2	1081.7
25°	1033.6	1030.6	1029.1	1024.6	1018.6	1024.6	1023.1	1024.6	1027.6	1039.6	1030.6
27.5°	993.0	987.0	990.0	985.5	984.0	985.5	985.5	987.0	990.0	991.5	993.0
30°	958.5	952.5	951.0	948.0	946.5	948.0	951.0	948.0	960.0	958.5	958.5
32.5°	920.9	916.4	913.4	913.4	911.9	910.4	911.9	913.4	922.4	916.4	922.4
35°	884.9	881.9	881.9	878.9	877.4	877.4	877.4	883.4	880.4	884.9	884.9
37.5°	850.3	850.3	848.8	845.8	844.3	845.8	844.3	847.3	845.8	847.3	848.8
40°	814.3	811.3	809.8	809.8	805.3	800.7	805.3	805.3	806.8	811.3	812.8
42.5°	770.7	772.2	772.2	766.2	766.2	766.2	767.7	769.2	769.2	772.2	772.2
45°	733.1	730.1	730.1	730.1	727.1	728.6	731.6	731.6	731.6	731.6	728.6
47.5°	691.1	691.1	692.6	692.6	697.1	695.6	695.6	694.1	691.1	691.1	692.6
50°	652.0	656.5	658.0	658.0	659.5	661.0	661.0	658.0	656.5	652.0	652.0
52.5°	614.5	617.5	620.5	625.0	628.0	626.5	626.5	623.5	617.5	616.0	614.5
55°	573.9	578.4	584.4	588.9	593.4	594.9	594.9	588.9	582.9	575.4	575.4
57.5°	536.3	540.8	551.4	555.9	561.9	561.9	558.9	554.4	545.3	539.3	534.8
60°	498.8	506.3	513.8	522.8	530.3	531.8	527.3	521.3	510.8	503.3	497.3
62.5°	458.2	465.7	480.7	489.8	495.8	495.8	495.8	488.3	474.7	464.2	455.2
65°	419.2	426.7	440.2	452.2	456.7	461.2	456.7	449.2	438.7	426.7	417.7
67.5°	378.6	387.6	401.1	410.1	416.1	420.7	417.7	411.6	398.1	381.6	375.6
70°	333.5	338.0	357.6	366.6	375.6	378.6	375.6	366.6	353.1	335.0	329.0
72.5°	291.5	296.0	314.0	321.5	329.0	332.0	327.5	321.5	309.5	293.0	285.4
75°	243.4	250.9	259.9	271.9	280.9	283.9	279.4	274.9	259.9	249.4	243.4
77.5°	192.3	199.8	211.8	222.3	231.4	229.9	223.8	225.4	208.8	196.8	192.3
80°	145.7	151.7	160.8	169.8	174.3	174.3	172.8	166.8	160.8	151.7	144.2
82.5°	100.7	108.2	115.7	121.7	121.7	123.2	120.2	118.7	112.7	105.2	103.7
85°	60.1	61.6	67.6	67.6	73.6	70.6	69.1	73.6	67.6	63.1	61.6
87.5°	27.0	25.5	27.0	27.0	25.5	28.5	28.5	27.0	28.5	27.0	27.0
90°	15.2	15.4	15.9	16.4	16.9	17.4	16.9	16.4	15.9	15.4	15.2
92.5°	37.0	37.2	37.5	37.8	38.2	38.5	38.2	37.8	37.5	37.2	37.0
95°	61.0	61.2	61.5	61.8	62.1	62.4	62.1	61.8	61.5	61.2	61.0
97.5°	87.8	87.9	88.1	88.2	88.4	88.6	88.4	88.2	88.1	87.9	87.8
100°	117.6	117.8	118.1	118.4	118.8	119.1	118.8	118.4	118.1	117.8	117.6
102.5°	147.4	147.6	148.1	148.6	149.0	149.5	149.0	148.6	148.1	147.6	147.4
105°	177.9	178.1	178.6	179.1	179.5	180.0	179.5	179.1	178.6	178.1	177.9
107.5°	210.5	210.5	210.5	210.5	210.5	210.5	210.5	210.5	210.5	210.5	210.5
110°	246.1	246.0	245.9	245.7	245.6	245.4	245.6	245.7	245.9	246.0	246.1

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	280.9	280.7	280.4	280.1	279.8	279.5	279.8	280.1	280.4	280.7	280.9
115°	316.5	316.4	316.3	316.1	316.0	315.8	316.0	316.1	316.3	316.4	316.5
117.5°	353.5	353.2	352.5	351.9	351.2	350.6	351.2	351.9	352.5	353.2	353.5
120°	389.8	389.5	388.8	388.2	387.5	386.9	387.5	388.2	388.8	389.5	389.8
122.5°	425.4	425.2	424.7	424.2	423.7	423.2	423.7	424.2	424.7	425.2	425.4
125°	460.3	460.2	460.0	459.9	459.7	459.5	459.7	459.9	460.0	460.2	460.3
127.5°	495.8	495.6	495.3	495.0	494.7	494.4	494.7	495.0	495.3	495.6	495.8
130°	530.7	530.5	530.2	529.9	529.5	529.2	529.5	529.9	530.2	530.5	530.7
132.5°	564.1	563.9	563.4	562.9	562.4	561.9	562.4	562.9	563.4	563.9	564.1
135°	598.9	598.6	597.9	597.3	596.6	596.0	596.6	597.3	597.9	598.6	598.9
137.5°	633.0	632.6	631.8	631.0	630.2	629.4	630.2	631.0	631.8	632.6	633.0
140°	665.0	664.6	663.8	663.0	662.2	661.4	662.2	663.0	663.8	664.6	665.0
142.5°	695.5	695.1	694.3	693.4	692.6	691.8	692.6	693.4	694.3	695.1	695.5
145°	724.5	724.3	723.8	723.3	722.8	722.3	722.8	723.3	723.8	724.3	724.5
147.5°	753.6	752.9	751.6	750.3	749.0	747.7	749.0	750.3	751.6	752.9	753.6
150°	778.2	778.0	777.7	777.4	777.1	776.8	777.1	777.4	777.7	778.0	778.2
152.5°	803.6	803.3	802.6	802.0	801.3	800.7	801.3	802.0	802.6	803.3	803.6
155°	826.9	826.5	825.7	824.8	824.0	823.2	824.0	824.8	825.7	826.5	826.9
157.5°	847.2	846.6	845.5	844.4	843.2	842.1	843.2	844.4	845.5	846.6	847.2
160°	865.3	864.9	864.1	863.3	862.5	861.7	862.5	863.3	864.1	864.9	865.3
162.5°	882.8	882.3	881.3	880.4	879.4	878.4	879.4	880.4	881.3	882.3	882.8
165°	897.3	896.8	895.8	894.9	893.9	892.9	893.9	894.9	895.8	896.8	897.3
167.5°	909.6	909.1	908.2	907.2	906.3	905.3	906.3	907.2	908.2	909.1	909.6
170°	919.8	919.2	918.1	917.0	915.8	914.7	915.8	917.0	918.1	919.2	919.8
172.5°	927.1	926.6	925.6	924.7	923.7	922.7	923.7	924.7	925.6	926.6	927.1
175°	932.1	931.5	930.4	929.3	928.2	927.1	928.2	929.3	930.4	931.5	932.1
177.5°	935.0	934.4	933.3	932.2	931.1	930.0	931.1	932.2	933.3	934.4	935.0
180°	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1681.1	1672.1	1682.6	1669.1	1672.1	1688.6	1687.1	1702.2	1711.2	1709.7	1717.2
5°	1569.9	1569.9	1574.5	1573.0	1588.0	1601.5	1619.5	1634.5	1651.1	1660.1	1670.6
7.5°	1460.3	1475.3	1478.3	1485.8	1503.8	1526.4	1544.4	1566.9	1591.0	1607.5	1619.5
10°	1370.1	1382.2	1394.2	1400.2	1419.7	1449.8	1475.3	1511.4	1541.4	1559.4	1576.0
12.5°	1290.5	1304.0	1310.0	1337.1	1350.6	1370.1	1406.2	1445.3	1478.3	1497.8	1511.4
15°	1233.4	1240.9	1254.5	1271.0	1284.5	1308.5	1338.6	1382.2	1413.7	1430.2	1476.8
17.5°	1185.3	1194.4	1201.9	1209.4	1230.4	1256.0	1284.5	1322.1	1362.6	1391.2	1415.2
20°	1135.8	1140.3	1149.3	1161.3	1176.3	1200.4	1225.9	1265.0	1301.0	1323.6	1355.1
22.5°	1077.2	1090.7	1099.7	1108.7	1125.3	1152.3	1176.3	1204.9	1249.9	1275.5	1308.5
25°	1042.6	1048.6	1054.6	1065.2	1077.2	1101.2	1128.3	1158.3	1194.4	1221.4	1249.9
27.5°	997.6	1006.6	1014.1	1027.6	1035.1	1054.6	1080.2	1110.2	1153.8	1176.3	1200.4
30°	960.0	969.0	975.0	981.0	991.5	1012.6	1036.6	1060.7	1101.2	1129.8	1153.8
32.5°	922.4	931.5	939.0	943.5	954.0	967.5	987.0	1017.1	1051.6	1071.2	1102.7
35°	889.4	889.4	898.4	904.4	913.4	925.4	943.5	966.0	1002.1	1027.6	1056.1
37.5°	851.8	853.3	860.8	865.3	874.4	886.4	904.4	925.4	955.5	975.0	1003.6
40°	812.8	817.3	820.3	827.8	838.3	842.8	860.8	884.9	914.9	933.0	957.0
42.5°	773.7	776.7	784.2	790.2	799.2	806.8	818.8	841.3	863.8	890.9	910.4
45°	730.1	737.6	742.2	752.7	757.2	764.7	776.7	794.7	821.8	838.3	860.8
47.5°	692.6	695.6	698.6	712.1	721.1	725.6	737.6	748.2	776.7	791.7	812.8
50°	652.0	652.0	656.5	662.5	673.0	682.1	692.6	704.6	727.1	742.2	763.2
52.5°	614.5	610.0	613.0	616.0	626.5	635.5	646.0	662.5	683.6	692.6	710.6
55°	573.9	566.4	570.9	575.4	578.4	590.4	602.4	613.0	629.5	643.0	659.5
57.5°	530.3	528.8	525.8	527.3	534.8	542.3	551.4	564.9	584.4	594.9	603.9
60°	491.3	482.3	479.2	482.3	486.8	491.3	503.3	515.3	531.8	542.3	552.9
62.5°	450.7	441.7	435.7	431.2	435.7	446.2	453.7	462.7	476.2	488.3	497.3
65°	411.6	398.1	392.1	389.1	387.6	395.1	401.1	413.1	425.2	429.7	440.2
67.5°	368.1	356.1	348.5	344.0	344.0	344.0	350.0	362.1	374.1	375.6	386.1
70°	324.5	311.0	303.5	297.5	294.5	297.5	305.0	306.5	317.0	320.0	326.0
72.5°	277.9	265.9	256.9	249.4	250.9	253.9	253.9	256.9	262.9	270.4	270.4
75°	234.4	217.8	213.3	207.3	204.3	204.3	204.3	210.3	214.8	220.8	219.3
77.5°	184.8	175.8	166.8	163.8	159.2	157.7	160.8	160.8	163.8	168.3	169.8
80°	142.7	132.2	126.2	123.2	117.2	115.7	117.2	117.2	121.7	120.2	121.7
82.5°	99.2	91.6	87.1	82.6	79.6	81.1	79.6	79.6	81.1	79.6	79.6
85°	57.1	55.6	52.6	51.1	49.6	46.6	49.6	48.1	46.6	45.1	48.1
87.5°	27.0	25.5	25.5	22.5	22.5	21.0	22.5	22.5	21.0	21.0	21.0
90°	14.8	14.0	13.2	12.4	11.6	10.5	9.3	8.2	7.1	6.5	5.9
92.5°	36.4	35.3	34.2	33.0	31.9	30.5	29.0	27.6	26.1	25.4	25.0
95°	60.4	59.3	58.2	57.0	55.9	54.3	52.7	51.0	49.4	48.6	48.4
97.5°	87.3	86.4	85.4	84.5	83.5	81.2	79.0	76.7	74.4	73.3	73.2
100°	116.9	115.4	114.0	112.5	111.1	109.0	106.9	104.8	102.7	101.6	101.6
102.5°	146.6	145.0	143.3	141.7	140.1	139.3	138.5	137.7	136.9	136.5	136.1
105°	177.4	176.4	175.5	174.5	173.5	172.5	171.5	170.6	169.6	169.1	168.7
107.5°	210.3	209.8	209.3	208.9	208.4	207.6	206.8	205.9	205.1	204.7	204.3
110°	245.9	245.4	244.9	244.4	243.9	243.4	242.9	242.4	241.9	241.7	241.3

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	280.8	280.7	280.5	280.4	280.2	279.6	278.9	278.3	277.6	277.3	277.1
115°	316.6	316.7	316.9	317.0	317.2	316.9	316.6	316.3	316.0	315.8	315.5
117.5°	353.4	353.3	353.1	353.0	352.8	352.5	352.2	351.9	351.6	351.4	351.3
120°	389.8	389.8	389.8	389.8	389.8	389.6	389.5	389.3	389.2	389.1	388.7
122.5°	425.5	425.6	425.8	425.9	426.1	425.6	425.2	424.7	424.2	424.0	423.9
125°	460.5	460.8	461.1	461.4	461.7	461.5	461.4	461.2	461.1	461.0	460.5
127.5°	495.9	496.1	496.2	496.4	496.6	496.4	496.2	496.1	495.9	495.8	495.6
130°	530.8	530.9	531.1	531.2	531.4	531.1	530.8	530.5	530.2	530.0	529.6
132.5°	564.2	564.3	564.5	564.6	564.8	565.0	565.1	565.3	565.4	565.5	564.8
135°	598.9	598.9	598.9	598.9	598.9	598.7	598.6	598.4	598.3	598.2	597.7
137.5°	632.9	632.8	632.6	632.5	632.3	632.0	631.7	631.4	631.1	630.9	630.4
140°	664.8	664.5	664.2	663.8	663.5	663.0	662.6	662.1	661.6	661.4	661.0
142.5°	695.4	695.2	695.1	694.9	694.7	694.1	693.4	692.8	692.1	691.8	691.5
145°	724.5	724.5	724.5	724.5	724.5	724.0	723.5	723.0	722.5	722.3	722.0
147.5°	753.4	752.9	752.4	751.9	751.4	751.1	750.7	750.4	750.1	749.9	749.7
150°	778.2	778.2	778.2	778.2	778.2	777.6	776.9	776.3	775.6	775.3	775.4
152.5°	803.4	802.9	802.4	802.0	801.5	801.3	801.1	801.0	800.8	800.7	800.5
155°	826.6	825.9	825.3	824.6	824.0	823.8	823.6	823.5	823.3	823.2	823.2
157.5°	846.9	846.2	845.6	844.9	844.3	844.1	844.0	843.8	843.7	843.6	843.8
160°	865.0	864.3	863.7	863.0	862.4	862.2	862.1	861.9	861.8	861.7	861.9
162.5°	882.4	881.6	880.7	879.9	879.1	879.1	879.1	879.1	879.1	879.1	879.3
165°	897.0	896.3	895.7	895.0	894.4	894.2	894.1	893.9	893.8	893.7	893.9
167.5°	909.1	908.2	907.2	906.3	905.3	905.3	905.3	905.3	905.3	905.3	905.6
170°	919.3	918.3	917.4	916.4	915.4	915.4	915.4	915.4	915.4	915.4	915.7
172.5°	926.6	925.6	924.7	923.7	922.7	922.7	922.7	922.7	922.7	922.7	923.0
175°	931.6	930.7	929.7	928.8	927.8	927.8	927.8	927.8	927.8	927.8	928.1
177.5°	934.5	933.6	932.6	931.7	930.7	930.9	931.0	931.2	931.3	931.4	931.7
180°	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9	932.9

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1769.8	1769.8	1769.8	1769.8
2.5°	1727.7	1742.7	1753.2	1772.8
5°	1688.6	1715.7	1741.2	1768.3
7.5°	1649.6	1681.1	1721.7	1756.2
10°	1606.0	1646.6	1694.6	1741.2
12.5°	1562.4	1610.5	1663.1	1724.7
15°	1509.9	1571.4	1633.0	1699.1
17.5°	1463.3	1526.4	1592.5	1675.1
20°	1410.7	1479.8	1551.9	1636.0
22.5°	1364.1	1440.7	1515.9	1604.5
25°	1311.5	1386.7	1469.3	1563.9
27.5°	1268.0	1337.1	1418.2	1520.4
30°	1215.4	1290.5	1371.6	1473.8
32.5°	1165.8	1237.9	1323.6	1424.2
35°	1114.7	1188.4	1265.0	1361.1
37.5°	1066.7	1129.8	1206.4	1298.0
40°	1012.6	1081.7	1150.8	1222.9
42.5°	963.0	1026.1	1090.7	1147.8
45°	907.4	961.5	1023.1	1069.7
47.5°	856.3	904.4	952.5	988.5
50°	805.3	842.8	878.9	910.4
52.5°	745.2	787.2	806.8	826.3
55°	691.1	715.1	733.1	752.7
57.5°	638.5	649.0	658.0	676.1
60°	569.4	581.4	591.9	605.4
62.5°	509.3	515.3	518.3	531.8
65°	452.2	450.7	458.2	465.7
67.5°	390.6	389.1	396.6	399.6
70°	330.5	329.0	330.5	338.0
72.5°	273.4	273.4	274.9	277.9
75°	220.8	220.8	222.3	225.4
77.5°	166.8	169.8	168.3	174.3
80°	121.7	118.7	121.7	124.7
82.5°	79.6	82.6	82.6	79.6
85°	45.1	45.1	45.1	45.1
87.5°	19.5	19.5	21.0	22.5
90°	4.6	3.3	2.0	0.7
92.5°	24.2	23.4	22.6	21.8
95°	48.1	47.8	47.5	47.2
97.5°	73.1	72.9	72.8	72.6
100°	101.6	101.6	101.6	101.6
102.5°	135.3	134.5	133.7	132.9
105°	167.9	167.1	166.3	165.5
107.5°	203.5	202.7	201.9	201.1
110°	240.5	239.7	238.9	238.1

TEST NUMBER: P1034449

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	276.8	276.5	276.2	275.9
115°	314.8	314.2	313.5	312.9
117.5°	351.1	351.0	350.8	350.6
120°	387.9	387.1	386.3	385.5
122.5°	423.7	423.6	423.4	423.2
125°	459.5	458.6	457.6	456.6
127.5°	495.1	494.6	494.2	493.7
130°	528.8	527.9	527.1	526.3
132.5°	563.3	561.9	560.4	559.0
135°	596.7	595.8	594.8	593.8
137.5°	629.4	628.5	627.5	626.5
140°	660.2	659.3	658.5	657.7
142.5°	690.8	690.2	689.5	688.9
145°	721.3	720.7	720.0	719.4
147.5°	749.2	748.7	748.2	747.7
150°	775.6	775.7	775.9	776.1
152.5°	800.2	799.9	799.6	799.3
155°	823.2	823.2	823.2	823.2
157.5°	844.1	844.4	844.7	845.0
160°	862.4	862.9	863.4	863.9
162.5°	879.6	879.9	880.3	880.6
165°	894.2	894.5	894.8	895.1
167.5°	906.3	906.9	907.6	908.2
170°	916.4	917.0	917.7	918.3
172.5°	923.7	924.3	925.0	925.6
175°	928.8	929.4	930.1	930.7
177.5°	932.4	933.0	933.7	934.3
180°	932.9	932.9	932.9	932.9

(END OF REPORT)