

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034453

Luminaire Tested: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034453
REPORT IS A COMBINATION OF REPORTS P1003328 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7999.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58
2	92	85	79	73	86	80	74	70	70	66	62	61	58	56	53	51	49
3	84	75	67	61	79	70	64	58	62	57	53	54	51	47	47	44	42
4	77	66	58	52	72	62	55	50	55	50	45	49	44	41	43	39	36
5	71	59	51	45	66	56	48	43	50	44	39	44	39	35	38	35	32
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28
7	61	48	40	34	57	46	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11339	11339	11339	11339
5°	11348	12863	11358	9759
10°	11278	14662	11259	8377
15°	11195	15897	11126	7569
20°	11054	17420	10953	6910
25°	10929	19960	10729	6520
30°	10748	21057	10562	6166
35°	10463	16880	10244	5882
40°	10018	11667	9871	5582
45°	9456	8686	9349	5332
50°	8812	7150	8667	5132
55°	8118	6099	8053	4959
60°	7436	5220	7307	4825
65°	6701	4508	6593	4629
70°	5925	3743	5846	4288
75°	5104	2894	5033	3721
80°	4030	1958	3884	2736
85°	2579	980	2493	1395

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17319 cd/sqm

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.3	2.1
10°-20°	507.3	6.3
20°-30°	824.1	10.3
30°-40°	1007.2	12.6
40°-50°	913.6	11.4
50°-60°	727.7	9.1
60°-70°	506.8	6.3
70°-80°	270.0	3.4
80°-90°	68.4	0.9
90°-100°	33.2	0.4
100°-110°	220.7	2.8
110°-120°	397.4	5.0
120°-130°	510.1	6.4
130°-140°	548.6	6.9
140°-150°	514.9	6.4
150°-160°	416.5	5.2
160°-170°	269.4	3.4
170°-180°	92.9	1.2
0°-30°	1501.8	18.8
0°-40°	2509.0	31.4
0°-60°	4150.2	51.9
0°-90°	4995.4	62.5
90°-120°	651.2	8.1
90°-150°	2224.8	27.8
90°-180°	3004.0	37.6
0°-180°	7999.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1770	1770	1770	1770	1770	
5°	1768	2042	1770	1549	1768	168
15°	1699	2550	1689	1214	1699	480
25°	1564	3137	1535	1025	1564	720
35°	1361	2518	1333	877	1361	850
45°	1070	1187	1058	729	1070	824
55°	753	732	747	595	753	673
65°	466	449	458	461	466	462
75°	225	221	222	284	225	240
85°	45	50	44	71	45	54
90°	1	17	1	17	1	5
95°	41	15	41	15	41	51
105°	213	215	213	215	213	226
115°	400	397	400	397	400	397
125°	569	569	569	569	569	508
135°	710	707	710	707	710	547
145°	823	820	823	820	823	515
155°	906	900	906	900	906	417
165°	956	951	956	951	956	270
175°	978	973	978	973	978	93
180°	978	978	978	978	978	

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1772.8	1783.3	1795.3	1804.3	1819.3	1823.8	1831.4	1835.9	1840.4	1844.9	1847.9
5°	1768.3	1793.8	1816.3	1832.9	1861.4	1871.9	1885.4	1902.0	1921.5	1938.0	1948.5
7.5°	1756.2	1796.8	1826.8	1859.9	1899.0	1924.5	1938.0	1972.6	2004.1	2028.2	2059.7
10°	1741.2	1789.3	1835.9	1885.4	1941.0	1969.6	1996.6	2044.7	2088.3	2127.3	2158.9
12.5°	1724.7	1783.3	1838.9	1903.5	1978.6	2013.1	2031.2	2113.8	2167.9	2188.9	2250.5
15°	1699.1	1768.3	1847.9	1927.5	1990.6	2031.2	2080.7	2146.8	2200.9	2247.5	2297.1
17.5°	1675.1	1750.2	1831.4	1920.0	2011.6	2064.2	2101.8	2160.4	2219.0	2279.1	2325.6
20°	1636.0	1733.7	1816.3	1911.0	2019.1	2056.7	2095.8	2164.9	2228.0	2292.6	2351.2
22.5°	1604.5	1697.6	1810.3	1900.5	1992.1	2029.7	2077.7	2149.8	2225.0	2298.6	2384.2
25°	1563.9	1667.6	1765.3	1861.4	1956.0	1996.6	2040.2	2133.3	2211.4	2306.1	2400.7
27.5°	1520.4	1627.0	1724.7	1811.8	1900.5	1956.0	2002.6	2100.3	2203.9	2307.6	2430.8
30°	1473.8	1574.5	1667.6	1753.2	1850.9	1908.0	1954.5	2068.7	2184.4	2316.6	2463.8
32.5°	1424.2	1518.9	1598.5	1685.6	1789.3	1841.9	1905.0	2029.7	2166.4	2324.1	2508.9
35°	1361.1	1451.3	1521.9	1610.5	1714.2	1781.8	1847.9	1987.6	2146.8	2322.6	2534.4
37.5°	1298.0	1368.6	1436.2	1530.9	1651.1	1712.7	1781.8	1935.0	2116.8	2318.1	2545.0
40°	1222.9	1292.0	1350.6	1446.8	1573.0	1643.6	1715.7	1876.4	2082.2	2301.6	2507.4
42.5°	1147.8	1206.4	1271.0	1371.6	1493.3	1568.4	1645.1	1823.8	2037.2	2253.5	2403.7
45°	1069.7	1114.7	1185.3	1277.0	1406.2	1478.3	1565.4	1759.2	1974.1	2166.4	2241.5
47.5°	988.5	1033.6	1099.7	1188.4	1316.1	1401.7	1484.3	1678.1	1894.5	2043.2	2043.2
50°	910.4	946.5	1011.1	1099.7	1228.9	1307.0	1391.2	1597.0	1771.3	1880.9	1783.3
52.5°	826.3	866.9	920.9	1014.1	1141.8	1212.4	1304.0	1479.8	1645.1	1690.1	1539.9
55°	752.7	785.7	836.8	925.4	1044.1	1117.7	1195.9	1364.1	1503.8	1500.8	1340.1
57.5°	676.1	703.1	757.2	838.3	948.0	1014.1	1092.2	1237.9	1352.1	1311.5	1159.8
60°	605.4	625.0	677.6	743.7	848.8	910.4	985.5	1104.2	1191.4	1134.3	981.0
62.5°	531.8	554.4	596.4	661.0	754.2	803.8	859.3	979.5	1035.1	984.0	827.8
65°	465.7	483.8	521.3	575.4	659.5	704.6	752.7	851.8	904.4	830.8	701.6
67.5°	399.6	420.7	447.7	495.8	561.9	603.9	646.0	731.6	755.7	689.6	581.4
70°	338.0	356.1	381.6	416.1	471.7	509.3	540.8	611.5	628.0	566.4	480.7
72.5°	277.9	290.0	311.0	339.5	390.6	411.6	444.7	492.8	513.8	458.2	396.6
75°	225.4	234.4	247.9	268.9	303.5	326.0	353.1	398.1	396.6	357.6	314.0
77.5°	174.3	175.8	190.8	210.3	231.4	250.9	264.4	296.0	299.0	274.9	238.9
80°	124.7	129.2	135.2	150.2	168.3	175.8	192.3	211.8	214.8	196.8	172.8
82.5°	79.6	82.6	87.1	96.1	108.2	117.2	126.2	133.7	141.2	130.7	111.2
85°	45.1	46.6	51.1	54.1	60.1	64.6	72.1	79.6	78.1	70.6	64.6
87.5°	22.5	22.5	22.5	25.5	28.5	28.5	31.5	33.1	34.6	31.5	28.5
90°	0.7	2.0	3.3	4.6	5.9	6.5	7.1	8.2	9.3	10.5	11.6
92.5°	13.8	12.3	10.9	9.4	7.9	7.2	7.7	8.7	9.6	10.6	11.6
95°	41.3	40.8	40.3	39.8	39.3	39.1	36.0	29.9	23.8	17.7	11.6
97.5°	77.6	78.6	79.5	80.5	81.4	81.9	74.2	58.9	43.6	28.3	13.0
100°	121.0	121.5	122.0	122.5	123.0	123.2	123.5	124.2	124.8	125.5	126.1
102.5°	165.3	165.9	166.6	167.2	167.9	168.2	168.4	168.7	169.0	169.3	169.6
105°	213.1	213.7	214.4	215.0	215.7	216.0	216.0	216.0	216.0	216.0	216.0
107.5°	262.4	262.4	262.4	262.4	262.4	262.4	262.6	262.9	263.2	263.5	263.8
110°	310.2	310.2	310.2	310.2	310.2	310.2	310.4	310.7	311.0	311.4	311.7

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	355.2	355.7	356.1	356.6	357.1	357.3	357.4	357.6	357.7	357.9	358.1
115°	400.1	400.9	401.7	402.5	403.3	403.7	403.8	404.0	404.1	404.3	404.5
117.5°	447.2	447.2	447.2	447.2	447.2	447.2	447.5	448.2	448.8	449.5	450.1
120°	490.7	490.5	490.4	490.2	490.1	490.0	490.2	490.7	491.2	491.7	492.2
122.5°	529.1	529.9	530.7	531.5	532.3	532.7	532.8	533.0	533.1	533.3	533.5
125°	569.0	570.1	571.3	572.4	573.5	574.1	574.1	574.1	574.1	574.1	574.1
127.5°	607.4	608.2	609.0	609.8	610.6	611.0	610.9	610.8	610.6	610.5	610.3
130°	642.2	643.0	643.8	644.6	645.4	645.8	645.9	646.0	646.2	646.3	646.5
132.5°	677.0	678.0	678.9	679.9	680.8	681.3	681.1	680.6	680.1	679.7	679.2
135°	709.6	710.6	711.5	712.5	713.4	713.9	713.7	713.4	713.1	712.8	712.5
137.5°	740.0	741.0	742.0	742.9	743.9	744.4	744.2	743.9	743.6	743.2	742.9
140°	769.8	770.1	770.4	770.7	771.0	771.2	771.1	771.0	770.8	770.7	770.5
142.5°	796.6	796.8	796.9	797.1	797.2	797.3	797.5	797.8	798.1	798.5	798.8
145°	822.7	823.0	823.3	823.6	823.9	824.1	824.1	824.1	824.1	824.1	824.1
147.5°	845.9	845.9	845.9	845.9	845.9	845.9	846.0	846.1	846.3	846.4	846.6
150°	867.6	867.3	867.0	866.7	866.4	866.2	866.4	866.7	867.0	867.3	867.6
152.5°	888.6	887.8	887.0	886.2	885.4	885.0	885.2	885.5	885.8	886.2	886.5
155°	906.0	905.0	904.1	903.1	902.2	901.7	901.9	902.2	902.5	902.8	903.1
157.5°	919.8	919.3	918.8	918.3	917.8	917.6	917.6	917.6	917.6	917.6	917.6
160°	934.3	933.3	932.3	931.4	930.4	929.9	930.0	930.2	930.3	930.5	930.7
162.5°	945.9	944.9	943.9	943.0	942.0	941.5	941.6	941.8	941.9	942.1	942.3
165°	956.0	955.0	954.1	953.1	952.2	951.7	951.8	951.9	952.1	952.2	952.4
167.5°	964.0	963.0	962.1	961.1	960.2	959.7	959.8	959.9	960.1	960.2	960.4
170°	970.5	969.4	968.3	967.2	966.1	965.5	965.6	965.7	965.9	966.0	966.2
172.5°	974.9	973.8	972.6	971.5	970.4	969.8	970.0	970.3	970.6	971.0	971.3
175°	977.8	976.8	975.8	974.9	973.9	973.4	973.5	973.7	973.8	974.0	974.2
177.5°	980.0	979.0	978.0	977.1	976.1	975.6	975.7	975.8	976.0	976.1	976.3
180°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1850.9	1861.4	1870.4	1877.9	1883.9	1892.9	1886.9	1888.4	1891.4	1897.5	1897.5
5°	1971.1	1987.6	1996.6	2026.7	2034.2	2032.7	2028.2	2052.2	2050.7	2041.7	2040.2
7.5°	2088.3	2116.8	2142.3	2166.4	2173.9	2193.4	2197.9	2208.4	2205.4	2220.5	2212.9
10°	2194.9	2240.0	2264.0	2300.1	2309.1	2318.1	2330.1	2336.1	2349.7	2348.2	2348.2
12.5°	2277.5	2331.6	2363.2	2372.2	2406.8	2417.3	2427.8	2447.3	2442.8	2444.3	2453.3
15°	2342.1	2394.7	2421.8	2463.8	2487.9	2499.9	2517.9	2539.0	2536.0	2549.5	2546.5
17.5°	2390.2	2439.8	2489.4	2552.5	2554.0	2585.5	2627.6	2636.6	2656.1	2642.6	2642.6
20°	2429.3	2495.4	2566.0	2647.1	2656.1	2675.7	2726.7	2761.3	2783.8	2776.3	2780.8
22.5°	2471.4	2566.0	2648.6	2729.8	2773.3	2807.9	2857.5	2911.5	2931.1	2943.1	2940.1
25°	2525.4	2624.6	2746.3	2859.0	2904.0	2970.1	3036.2	3088.8	3103.8	3136.9	3106.8
27.5°	2581.0	2720.7	2872.5	3004.7	3061.8	3115.9	3195.5	3234.5	3254.1	3269.1	3258.6
30°	2627.6	2819.9	2985.2	3106.8	3147.4	3179.0	3224.0	3233.0	3225.5	3237.5	3252.6
32.5°	2699.7	2887.5	3027.2	3085.8	3081.3	3079.8	3045.2	2997.2	2986.7	2958.1	2997.2
35°	2738.8	2889.0	2943.1	2865.0	2833.4	2776.3	2666.7	2594.5	2531.4	2517.9	2520.9
37.5°	2716.2	2774.8	2710.2	2504.4	2453.3	2366.2	2220.5	2118.3	2071.7	2035.7	2082.2
40°	2594.5	2529.9	2352.7	2101.8	2028.2	1945.5	1808.8	1753.2	1687.1	1673.6	1735.2
42.5°	2393.2	2196.4	1945.5	1751.7	1675.1	1628.5	1514.4	1461.8	1415.2	1394.2	1428.7
45°	2119.8	1880.9	1628.5	1469.3	1404.7	1349.1	1281.5	1225.9	1195.9	1186.8	1215.4
47.5°	1837.4	1585.0	1383.7	1265.0	1197.4	1155.3	1092.2	1060.7	1036.6	1039.6	1044.1
50°	1566.9	1337.1	1182.3	1063.7	1030.6	997.6	955.5	928.4	916.4	920.9	917.9
52.5°	1334.1	1147.8	1017.1	925.4	910.4	878.9	844.3	821.8	817.3	818.8	823.3
55°	1129.8	984.0	880.4	814.3	797.7	775.2	754.2	739.2	727.1	731.6	730.1
57.5°	975.0	847.3	767.7	713.6	701.6	688.1	668.5	661.0	656.5	647.5	655.0
60°	838.3	734.6	665.5	632.5	622.0	613.0	591.9	582.9	579.9	575.4	587.4
62.5°	709.1	635.5	582.9	552.9	542.3	533.3	522.8	515.3	516.8	510.8	516.8
65°	606.9	546.9	509.3	482.3	468.7	462.7	461.2	449.2	447.7	449.2	450.7
67.5°	512.3	461.2	432.7	416.1	405.6	399.6	395.1	387.6	393.6	389.1	392.1
70°	426.7	392.1	362.1	345.5	341.0	342.5	335.0	332.0	333.5	330.5	333.5
72.5°	344.0	315.5	303.5	291.5	285.4	283.9	279.4	274.9	279.4	277.9	277.9
75°	274.9	253.9	240.4	232.9	232.9	229.9	222.3	222.3	222.3	220.8	222.3
77.5°	211.8	193.8	187.8	180.3	180.3	175.8	174.3	174.3	171.3	175.8	172.8
80°	157.7	144.2	135.2	130.7	130.7	129.2	126.2	124.7	126.2	124.7	124.7
82.5°	102.2	96.1	91.6	87.1	85.6	87.1	85.6	82.6	84.1	82.6	85.6
85°	58.6	52.6	52.6	49.6	51.1	48.1	49.6	46.6	45.1	49.6	46.6
87.5°	25.5	24.0	24.0	21.0	21.0	21.0	19.5	21.0	19.5	18.0	19.5
90°	12.4	13.2	14.0	14.8	15.2	15.4	15.9	16.4	16.9	17.4	16.9
92.5°	12.4	13.2	14.0	14.8	15.2	15.3	15.4	15.6	15.7	15.9	15.7
95°	12.4	13.2	14.0	14.8	15.2	15.2	15.2	15.2	15.2	15.2	15.2
97.5°	13.3	13.7	14.0	14.3	14.5	14.6	14.7	14.9	15.0	15.2	15.0
100°	102.1	78.1	54.1	30.1	18.1	17.8	17.1	16.5	15.8	15.2	15.8
102.5°	169.9	170.3	170.6	170.9	171.1	164.3	150.8	137.3	123.7	110.2	123.7
105°	216.0	216.0	216.0	216.0	216.0	215.9	215.8	215.6	215.5	215.3	215.5
107.5°	264.0	264.2	264.3	264.5	264.6	264.3	263.6	263.0	262.3	261.7	262.3
110°	311.2	310.7	310.2	309.7	309.5	309.6	309.7	309.9	310.0	310.2	310.0



TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	357.5	356.8	356.2	355.5	355.2	355.0	354.7	354.4	354.0	353.7	354.0
115°	403.9	403.2	402.6	401.9	401.6	401.1	400.1	399.2	398.2	397.2	398.2
117.5°	449.1	448.2	447.2	446.3	445.8	445.6	445.3	445.0	444.6	444.3	444.6
120°	491.9	491.5	491.2	490.9	490.7	490.3	489.5	488.7	487.9	487.1	487.9
122.5°	533.2	532.8	532.5	532.2	532.0	531.5	530.6	529.6	528.7	527.7	528.7
125°	573.5	572.8	572.2	571.5	571.2	571.0	570.5	570.0	569.5	569.0	569.5
127.5°	610.0	609.7	609.4	609.1	608.9	608.3	607.0	605.7	604.4	603.1	604.4
130°	646.0	645.6	645.1	644.6	644.4	644.0	643.2	642.3	641.5	640.7	641.5
132.5°	679.2	679.2	679.2	679.2	679.2	678.8	678.0	677.1	676.3	675.5	676.3
135°	712.2	711.9	711.6	711.3	711.1	710.6	709.6	708.7	707.7	706.7	707.7
137.5°	742.9	742.9	742.9	742.9	742.9	742.5	741.7	740.9	740.1	739.3	740.1
140°	770.8	771.1	771.4	771.7	771.9	771.4	770.5	769.5	768.6	767.6	768.6
142.5°	798.8	798.8	798.8	798.8	798.8	798.3	797.3	796.4	795.4	794.4	795.4
145°	824.3	824.4	824.6	824.7	824.8	824.3	823.4	822.4	821.5	820.5	821.5
147.5°	846.8	846.9	847.1	847.2	847.3	846.7	845.6	844.5	843.3	842.2	843.3
150°	867.9	868.3	868.6	868.9	869.1	868.5	867.2	865.9	864.6	863.3	864.6
152.5°	886.8	887.1	887.4	887.7	887.9	887.3	886.2	885.1	883.9	882.8	883.9
155°	903.6	904.1	904.6	905.1	905.3	904.7	903.4	902.1	900.8	899.5	900.8
157.5°	918.1	918.6	919.1	919.6	919.8	919.2	917.9	916.6	915.3	914.0	915.3
160°	931.3	932.0	932.6	933.3	933.6	933.0	931.7	930.4	929.1	927.8	929.1
162.5°	943.3	944.2	945.2	946.1	946.6	945.9	944.4	943.0	941.5	940.1	941.5
165°	953.4	954.4	955.3	956.3	956.8	956.2	954.9	953.6	952.3	951.0	952.3
167.5°	961.5	962.7	963.8	964.9	965.5	964.8	963.3	961.8	960.4	958.9	960.4
170°	967.5	968.8	970.1	971.4	972.0	971.3	969.8	968.4	966.9	965.5	966.9
172.5°	972.4	973.5	974.6	975.7	976.3	975.6	974.1	972.7	971.2	969.8	971.2
175°	975.5	976.8	978.1	979.4	980.0	979.3	977.8	976.3	974.9	973.4	974.9
177.5°	977.4	978.6	979.7	980.8	981.4	980.8	979.5	978.2	976.9	975.6	976.9
180°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1894.5	1883.9	1886.9	1883.9	1876.4	1871.9	1859.9	1844.9	1838.9	1831.4	1826.8
5°	2046.2	2038.7	2037.2	2025.2	2022.2	2004.1	1974.1	1959.1	1941.0	1923.0	1905.0
7.5°	2211.4	2202.4	2172.4	2167.9	2170.9	2148.3	2109.3	2079.2	2041.7	2016.1	1981.6
10°	2348.2	2330.1	2304.6	2306.1	2295.6	2265.5	2226.5	2194.9	2140.8	2107.8	2058.2
12.5°	2430.8	2415.8	2412.8	2397.7	2388.7	2349.7	2303.1	2262.5	2222.0	2176.9	2139.3
15°	2531.4	2511.9	2498.4	2477.4	2471.4	2430.8	2379.7	2333.1	2286.6	2244.5	2164.9
17.5°	2642.6	2621.6	2570.5	2566.0	2529.9	2490.9	2441.3	2372.2	2322.6	2262.5	2203.9
20°	2768.8	2738.8	2672.7	2656.1	2627.6	2563.0	2495.4	2418.8	2339.1	2277.5	2208.4
22.5°	2910.0	2857.5	2809.4	2756.8	2735.8	2656.1	2563.0	2469.8	2373.7	2289.6	2206.9
25°	3093.3	3024.2	2956.6	2904.0	2868.0	2764.3	2639.6	2516.4	2405.2	2295.6	2187.4
27.5°	3237.5	3177.5	3103.8	3034.7	2988.2	2865.0	2722.2	2563.0	2424.8	2291.1	2175.4
30°	3248.1	3230.0	3185.0	3147.4	3096.3	2964.1	2806.4	2626.1	2454.8	2292.6	2151.4
32.5°	3051.3	3087.3	3106.8	3112.9	3102.3	3025.7	2881.5	2683.2	2481.9	2279.1	2130.3
35°	2627.6	2723.7	2842.4	2887.5	2931.1	2971.6	2896.5	2723.7	2490.9	2276.0	2097.3
37.5°	2163.4	2250.5	2447.3	2537.5	2588.5	2749.3	2810.9	2717.7	2508.9	2279.1	2065.7
40°	1745.7	1883.9	2025.2	2146.8	2226.5	2406.8	2597.5	2618.6	2483.4	2250.5	2025.2
42.5°	1469.3	1550.4	1657.1	1769.8	1840.4	2053.7	2312.1	2463.8	2403.7	2203.9	1975.6
45°	1251.5	1311.5	1412.2	1449.8	1539.9	1744.2	2017.6	2237.0	2267.0	2130.3	1918.5
47.5°	1074.2	1125.3	1189.9	1236.4	1308.5	1461.8	1693.1	1935.0	2079.2	2029.7	1838.9
50°	946.5	988.5	1042.6	1069.7	1116.2	1254.5	1428.7	1669.1	1862.9	1879.4	1735.2
52.5°	839.8	863.8	905.9	936.0	973.5	1057.6	1215.4	1413.7	1631.5	1721.7	1607.5
55°	746.7	766.2	803.8	823.3	842.8	914.9	1038.1	1218.4	1422.7	1541.4	1476.8
57.5°	662.5	679.1	710.6	728.6	739.2	808.3	902.9	1044.1	1227.4	1371.6	1335.6
60°	593.4	608.4	626.5	640.0	652.0	709.1	775.2	889.4	1053.1	1192.9	1183.8
62.5°	519.8	533.3	552.9	566.4	576.9	613.0	668.5	755.7	895.4	1024.6	1050.1
65°	455.2	465.7	479.2	485.3	498.8	525.8	570.9	649.0	763.2	878.9	896.9
67.5°	396.6	399.6	408.6	422.2	425.2	449.2	489.8	548.4	637.0	731.6	760.2
70°	333.5	338.0	345.5	356.1	362.1	377.1	411.6	450.7	527.3	610.0	631.0
72.5°	277.9	283.9	286.9	293.0	296.0	320.0	335.0	374.1	426.7	495.8	518.3
75°	225.4	231.4	232.9	235.9	238.9	249.4	270.4	294.5	338.0	383.1	413.1
77.5°	178.8	177.3	180.3	184.8	183.3	192.3	205.8	226.9	255.4	293.0	312.5
80°	126.2	126.2	130.7	135.2	133.7	142.7	147.2	162.3	186.3	210.3	217.8
82.5°	84.1	84.1	88.6	88.6	91.6	93.1	99.2	106.7	126.2	138.2	142.7
85°	48.1	48.1	49.6	49.6	49.6	52.6	57.1	60.1	66.1	73.6	76.6
87.5°	19.5	21.0	21.0	21.0	21.0	24.0	24.0	27.0	28.5	31.5	31.5
90°	16.4	15.9	15.4	15.2	14.8	14.0	13.2	12.4	11.6	10.5	9.3
92.5°	15.6	15.4	15.3	15.2	14.8	14.0	13.2	12.4	11.6	10.6	9.6
95°	15.2	15.2	15.2	15.2	14.8	14.0	13.2	12.4	11.6	17.7	23.8
97.5°	14.9	14.7	14.6	14.5	14.3	14.0	13.7	13.3	13.0	28.3	43.6
100°	16.5	17.1	17.8	18.1	30.1	54.1	78.1	102.1	126.1	125.5	124.8
102.5°	137.3	150.8	164.3	171.1	170.9	170.6	170.3	169.9	169.6	169.3	169.0
105°	215.6	215.8	215.9	216.0	216.0	216.0	216.0	216.0	216.0	216.0	216.0
107.5°	263.0	263.6	264.3	264.6	264.5	264.3	264.2	264.0	263.8	263.5	263.2
110°	309.9	309.7	309.6	309.5	309.7	310.2	310.7	311.2	311.7	311.4	311.0

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	354.4	354.7	355.0	355.2	355.5	356.2	356.8	357.5	358.1	357.9	357.7
115°	399.2	400.1	401.1	401.6	401.9	402.6	403.2	403.9	404.5	404.3	404.1
117.5°	445.0	445.3	445.6	445.8	446.3	447.2	448.2	449.1	450.1	449.5	448.8
120°	488.7	489.5	490.3	490.7	490.9	491.2	491.5	491.9	492.2	491.7	491.2
122.5°	529.6	530.6	531.5	532.0	532.2	532.5	532.8	533.2	533.5	533.3	533.1
125°	570.0	570.5	571.0	571.2	571.5	572.2	572.8	573.5	574.1	574.1	574.1
127.5°	605.7	607.0	608.3	608.9	609.1	609.4	609.7	610.0	610.3	610.5	610.6
130°	642.3	643.2	644.0	644.4	644.6	645.1	645.6	646.0	646.5	646.3	646.2
132.5°	677.1	678.0	678.8	679.2	679.2	679.2	679.2	679.2	679.2	679.7	680.1
135°	708.7	709.6	710.6	711.1	711.3	711.6	711.9	712.2	712.5	712.8	713.1
137.5°	740.9	741.7	742.5	742.9	742.9	742.9	742.9	742.9	742.9	743.2	743.6
140°	769.5	770.5	771.4	771.9	771.7	771.4	771.1	770.8	770.5	770.7	770.8
142.5°	796.4	797.3	798.3	798.8	798.8	798.8	798.8	798.8	798.8	798.5	798.1
145°	822.4	823.4	824.3	824.8	824.7	824.6	824.4	824.3	824.1	824.1	824.1
147.5°	844.5	845.6	846.7	847.3	847.2	847.1	846.9	846.8	846.6	846.4	846.3
150°	865.9	867.2	868.5	869.1	868.9	868.6	868.3	867.9	867.6	867.3	867.0
152.5°	885.1	886.2	887.3	887.9	887.7	887.4	887.1	886.8	886.5	886.2	885.8
155°	902.1	903.4	904.7	905.3	905.1	904.6	904.1	903.6	903.1	902.8	902.5
157.5°	916.6	917.9	919.2	919.8	919.6	919.1	918.6	918.1	917.6	917.6	917.6
160°	930.4	931.7	933.0	933.6	933.3	932.6	932.0	931.3	930.7	930.5	930.3
162.5°	943.0	944.4	945.9	946.6	946.1	945.2	944.2	943.3	942.3	942.1	941.9
165°	953.6	954.9	956.2	956.8	956.3	955.3	954.4	953.4	952.4	952.2	952.1
167.5°	961.8	963.3	964.8	965.5	964.9	963.8	962.7	961.5	960.4	960.2	960.1
170°	968.4	969.8	971.3	972.0	971.4	970.1	968.8	967.5	966.2	966.0	965.9
172.5°	972.7	974.1	975.6	976.3	975.7	974.6	973.5	972.4	971.3	971.0	970.6
175°	976.3	977.8	979.3	980.0	979.4	978.1	976.8	975.5	974.2	974.0	973.8
177.5°	978.2	979.5	980.8	981.4	980.8	979.7	978.6	977.4	976.3	976.1	976.0
180°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1820.8	1813.3	1804.3	1804.3	1793.8	1789.3	1780.3	1777.3	1769.8	1757.7	1748.7
5°	1885.4	1865.9	1853.9	1843.4	1820.8	1804.3	1787.8	1769.8	1751.7	1730.7	1706.7
7.5°	1948.5	1912.5	1896.0	1877.9	1844.9	1810.3	1777.3	1753.2	1729.2	1696.1	1666.1
10°	2014.6	1969.6	1939.5	1915.5	1864.4	1820.8	1772.8	1738.2	1700.6	1658.6	1619.5
12.5°	2070.2	2011.6	1986.1	1941.0	1882.4	1829.9	1769.8	1717.2	1667.6	1618.0	1569.9
15°	2116.8	2061.2	1998.1	1980.1	1899.0	1823.8	1756.2	1688.6	1627.0	1577.5	1521.9
17.5°	2131.8	2061.2	2029.7	1986.1	1889.9	1811.8	1726.2	1652.6	1594.0	1520.4	1476.8
20°	2136.3	2068.7	2025.2	1984.6	1899.0	1795.3	1711.2	1621.0	1550.4	1476.8	1407.7
22.5°	2124.3	2044.7	2002.6	1963.6	1867.4	1778.8	1681.1	1582.0	1499.3	1431.7	1362.6
25°	2101.8	2008.6	1968.1	1926.0	1834.4	1736.7	1630.0	1535.4	1458.8	1377.6	1310.0
27.5°	2071.7	1965.1	1918.5	1874.9	1784.8	1693.1	1592.5	1494.8	1409.2	1323.6	1260.5
30°	2034.2	1911.0	1868.9	1811.8	1724.7	1637.6	1545.9	1448.3	1352.1	1271.0	1201.9
32.5°	1986.1	1856.9	1801.3	1747.2	1652.6	1573.0	1485.8	1394.2	1301.0	1221.4	1149.3
35°	1942.5	1795.3	1733.7	1679.6	1574.5	1490.3	1418.2	1332.6	1249.9	1167.3	1102.7
37.5°	1883.9	1733.7	1660.1	1604.5	1497.8	1412.2	1344.6	1278.5	1191.4	1111.7	1051.6
40°	1822.3	1657.1	1588.0	1532.4	1421.2	1328.1	1263.5	1204.9	1134.3	1060.7	997.6
42.5°	1766.8	1583.5	1509.9	1442.2	1329.6	1246.9	1180.8	1135.8	1071.2	1005.1	948.0
45°	1696.1	1505.3	1425.7	1355.1	1246.9	1156.8	1093.7	1057.6	1009.6	945.0	895.4
47.5°	1624.0	1421.2	1338.6	1269.5	1152.3	1072.7	1011.1	976.5	943.5	892.4	842.8
50°	1529.4	1332.6	1257.5	1177.8	1062.2	981.0	929.9	895.4	869.9	833.8	791.7
52.5°	1425.7	1240.9	1159.8	1090.7	976.5	902.9	844.3	824.8	799.2	772.2	736.1
55°	1316.1	1141.8	1063.7	996.1	890.9	815.8	767.7	746.7	727.1	706.1	682.1
57.5°	1206.4	1038.1	964.5	904.4	806.8	734.6	695.6	667.0	653.5	641.5	622.0
60°	1069.7	926.9	869.9	815.8	719.6	653.5	616.0	594.9	582.9	576.9	567.9
62.5°	949.5	832.3	769.2	716.6	640.0	581.4	545.3	528.8	518.3	515.3	504.8
65°	821.8	721.1	671.5	626.5	560.4	507.8	477.7	458.2	450.7	449.2	449.2
67.5°	701.6	620.5	570.9	539.3	482.3	435.7	407.1	399.6	395.1	389.1	387.6
70°	588.9	524.3	480.7	453.7	402.6	368.1	345.5	333.5	333.5	329.0	326.0
72.5°	489.8	425.2	396.6	374.1	332.0	302.0	285.4	282.4	271.9	270.4	270.4
75°	383.1	335.0	315.5	296.0	264.4	243.4	229.9	222.3	216.3	216.3	217.8
77.5°	288.4	255.4	237.4	222.3	199.8	186.3	175.8	172.8	166.8	166.8	166.8
80°	204.3	186.3	172.8	160.8	144.2	132.2	126.2	120.2	120.2	118.7	120.2
82.5°	132.2	117.2	109.7	108.2	93.1	88.6	81.1	82.6	78.1	76.6	79.6
85°	76.6	69.1	60.1	57.1	51.1	45.1	42.1	43.6	42.1	40.6	42.1
87.5°	30.0	25.5	24.0	24.0	19.5	18.0	16.5	18.0	15.0	15.0	16.5
90°	8.2	7.1	6.5	5.9	4.6	3.3	2.0	0.7	2.0	3.3	4.6
92.5°	8.7	7.7	7.2	7.9	9.4	10.9	12.3	13.8	12.3	10.9	9.4
95°	29.9	36.0	39.1	39.3	39.8	40.3	40.8	41.3	40.8	40.3	39.8
97.5°	58.9	74.2	81.9	81.4	80.5	79.5	78.6	77.6	78.6	79.5	80.5
100°	124.2	123.5	123.2	123.0	122.5	122.0	121.5	121.0	121.5	122.0	122.5
102.5°	168.7	168.4	168.2	167.9	167.2	166.6	165.9	165.3	165.9	166.6	167.2
105°	216.0	216.0	216.0	215.7	215.0	214.4	213.7	213.1	213.7	214.4	215.0
107.5°	262.9	262.6	262.4	262.4	262.4	262.4	262.4	262.4	262.4	262.4	262.4
110°	310.7	310.4	310.2	310.2	310.2	310.2	310.2	310.2	310.2	310.2	310.2

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	357.6	357.4	357.3	357.1	356.6	356.1	355.7	355.2	355.7	356.1	356.6
115°	404.0	403.8	403.7	403.3	402.5	401.7	400.9	400.1	400.9	401.7	402.5
117.5°	448.2	447.5	447.2	447.2	447.2	447.2	447.2	447.2	447.2	447.2	447.2
120°	490.7	490.2	490.0	490.1	490.2	490.4	490.5	490.7	490.5	490.4	490.2
122.5°	533.0	532.8	532.7	532.3	531.5	530.7	529.9	529.1	529.9	530.7	531.5
125°	574.1	574.1	574.1	573.5	572.4	571.3	570.1	569.0	570.1	571.3	572.4
127.5°	610.8	610.9	611.0	610.6	609.8	609.0	608.2	607.4	608.2	609.0	609.8
130°	646.0	645.9	645.8	645.4	644.6	643.8	643.0	642.2	643.0	643.8	644.6
132.5°	680.6	681.1	681.3	680.8	679.9	678.9	678.0	677.0	678.0	678.9	679.9
135°	713.4	713.7	713.9	713.4	712.5	711.5	710.6	709.6	710.6	711.5	712.5
137.5°	743.9	744.2	744.4	743.9	742.9	742.0	741.0	740.0	741.0	742.0	742.9
140°	771.0	771.1	771.2	771.0	770.7	770.4	770.1	769.8	770.1	770.4	770.7
142.5°	797.8	797.5	797.3	797.2	797.1	796.9	796.8	796.6	796.8	796.9	797.1
145°	824.1	824.1	824.1	823.9	823.6	823.3	823.0	822.7	823.0	823.3	823.6
147.5°	846.1	846.0	845.9	845.9	845.9	845.9	845.9	845.9	845.9	845.9	845.9
150°	866.7	866.4	866.2	866.4	866.7	867.0	867.3	867.6	867.3	867.0	866.7
152.5°	885.5	885.2	885.0	885.4	886.2	887.0	887.8	888.6	887.8	887.0	886.2
155°	902.2	901.9	901.7	902.2	903.1	904.1	905.0	906.0	905.0	904.1	903.1
157.5°	917.6	917.6	917.6	917.8	918.3	918.8	919.3	919.8	919.3	918.8	918.3
160°	930.2	930.0	929.9	930.4	931.4	932.3	933.3	934.3	933.3	932.3	931.4
162.5°	941.8	941.6	941.5	942.0	943.0	943.9	944.9	945.9	944.9	943.9	943.0
165°	951.9	951.8	951.7	952.2	953.1	954.1	955.0	956.0	955.0	954.1	953.1
167.5°	959.9	959.8	959.7	960.2	961.1	962.1	963.0	964.0	963.0	962.1	961.1
170°	965.7	965.6	965.5	966.1	967.2	968.3	969.4	970.5	969.4	968.3	967.2
172.5°	970.3	970.0	969.8	970.4	971.5	972.6	973.8	974.9	973.8	972.6	971.5
175°	973.7	973.5	973.4	973.9	974.9	975.8	976.8	977.8	976.8	975.8	974.9
177.5°	975.8	975.7	975.6	976.1	977.1	978.0	979.0	980.0	979.0	978.0	977.1
180°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1745.7	1742.7	1735.2	1730.7	1715.7	1697.6	1691.6	1676.6	1682.6	1672.1	1672.1
5°	1699.1	1685.6	1676.6	1663.1	1634.5	1615.0	1594.0	1583.5	1577.5	1569.9	1563.9
7.5°	1639.1	1628.5	1619.5	1594.0	1562.4	1535.4	1509.9	1499.3	1479.8	1466.3	1460.3
10°	1586.5	1571.4	1550.4	1520.4	1487.3	1452.8	1430.2	1407.7	1392.7	1385.2	1368.6
12.5°	1532.4	1514.4	1491.8	1448.3	1412.2	1391.2	1350.6	1329.6	1322.1	1316.1	1296.5
15°	1476.8	1457.3	1430.2	1389.7	1358.1	1308.5	1284.5	1268.0	1249.9	1248.4	1233.4
17.5°	1427.2	1403.2	1380.7	1331.1	1292.0	1248.4	1234.9	1216.9	1200.4	1182.3	1174.8
20°	1364.1	1341.6	1325.1	1271.0	1227.4	1200.4	1177.8	1162.8	1152.3	1134.3	1131.3
22.5°	1307.0	1283.0	1260.5	1219.9	1182.3	1147.8	1120.7	1104.2	1099.7	1092.2	1078.7
25°	1251.5	1227.4	1200.4	1162.8	1123.8	1099.7	1075.7	1065.2	1056.1	1044.1	1033.6
27.5°	1204.9	1182.3	1156.8	1110.2	1077.2	1059.2	1033.6	1021.6	1009.6	1003.6	999.1
30°	1149.3	1123.8	1104.2	1068.2	1032.1	1008.1	990.0	979.5	969.0	963.0	960.0
32.5°	1095.2	1071.2	1057.6	1018.6	990.0	961.5	948.0	940.5	934.5	928.4	922.4
35°	1051.6	1027.6	1006.6	970.5	942.0	922.4	911.9	899.9	895.4	889.4	889.4
37.5°	997.6	979.5	958.5	923.9	898.4	883.4	874.4	859.3	857.8	854.8	850.3
40°	951.0	933.0	913.4	883.4	860.8	842.8	830.8	823.3	818.8	815.8	812.8
42.5°	901.4	881.9	872.9	838.3	818.8	800.7	794.7	787.2	785.7	779.7	772.2
45°	853.3	836.8	818.8	793.2	776.7	761.7	752.7	746.7	739.2	737.6	733.1
47.5°	811.3	791.7	775.2	751.2	733.1	721.1	713.6	706.1	700.1	695.6	691.1
50°	757.2	742.2	728.6	703.1	688.1	676.1	665.5	659.5	653.5	653.5	653.5
52.5°	704.6	691.1	679.1	661.0	643.0	632.5	620.5	616.0	613.0	608.4	613.0
55°	653.5	640.0	628.0	614.5	593.4	584.4	572.4	567.9	569.4	569.4	573.9
57.5°	599.4	588.9	581.4	564.9	545.3	536.3	528.8	524.3	524.3	530.3	531.8
60°	546.9	536.3	522.8	507.8	495.8	485.3	480.7	482.3	482.3	485.3	492.8
62.5°	488.3	482.3	474.7	453.7	446.2	438.7	432.7	437.2	435.7	443.2	453.7
65°	434.2	428.2	417.7	407.1	398.1	390.6	389.1	390.6	393.6	401.1	413.1
67.5°	374.1	374.1	365.1	356.1	348.5	341.0	342.5	344.0	347.0	356.1	374.1
70°	324.5	318.5	309.5	303.5	297.5	294.5	291.5	297.5	306.5	312.5	326.0
72.5°	270.4	265.9	258.4	252.4	250.9	247.9	246.4	249.4	258.4	268.9	283.9
75°	213.3	214.8	210.3	205.8	205.8	201.3	204.3	204.3	213.3	223.8	235.9
77.5°	165.3	163.8	162.3	159.2	157.7	157.7	157.7	160.8	169.8	175.8	187.8
80°	117.2	118.7	114.2	115.7	114.2	115.7	115.7	121.7	126.2	133.7	142.7
82.5°	78.1	78.1	75.1	76.6	76.6	76.6	78.1	81.1	87.1	93.1	99.2
85°	43.6	45.1	42.1	45.1	45.1	45.1	46.6	48.1	52.6	54.1	60.1
87.5°	16.5	19.5	19.5	16.5	18.0	19.5	21.0	19.5	22.5	25.5	27.0
90°	5.9	6.5	7.1	8.2	9.3	10.5	11.6	12.4	13.2	14.0	14.8
92.5°	7.9	7.2	7.7	8.7	9.6	10.6	11.6	12.4	13.2	14.0	14.8
95°	39.3	39.1	36.0	29.9	23.8	17.7	11.6	12.4	13.2	14.0	14.8
97.5°	81.4	81.9	74.2	58.9	43.6	28.3	13.0	13.3	13.7	14.0	14.3
100°	123.0	123.2	123.5	124.2	124.8	125.5	126.1	102.1	78.1	54.1	30.1
102.5°	167.9	168.2	168.4	168.7	169.0	169.3	169.6	169.9	170.3	170.6	170.9
105°	215.7	216.0	216.0	216.0	216.0	216.0	216.0	216.0	216.0	216.0	216.0
107.5°	262.4	262.4	262.6	262.9	263.2	263.5	263.8	264.0	264.2	264.3	264.5
110°	310.2	310.2	310.4	310.7	311.0	311.4	311.7	311.2	310.7	310.2	309.7

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	357.1	357.3	357.4	357.6	357.7	357.9	358.1	357.5	356.8	356.2	355.5
115°	403.3	403.7	403.8	404.0	404.1	404.3	404.5	403.9	403.2	402.6	401.9
117.5°	447.2	447.2	447.5	448.2	448.8	449.5	450.1	449.1	448.2	447.2	446.3
120°	490.1	490.0	490.2	490.7	491.2	491.7	492.2	491.9	491.5	491.2	490.9
122.5°	532.3	532.7	532.8	533.0	533.1	533.3	533.5	533.2	532.8	532.5	532.2
125°	573.5	574.1	574.1	574.1	574.1	574.1	574.1	573.5	572.8	572.2	571.5
127.5°	610.6	611.0	610.9	610.8	610.6	610.5	610.3	610.0	609.7	609.4	609.1
130°	645.4	645.8	645.9	646.0	646.2	646.3	646.5	646.0	645.6	645.1	644.6
132.5°	680.8	681.3	681.1	680.6	680.1	679.7	679.2	679.2	679.2	679.2	679.2
135°	713.4	713.9	713.7	713.4	713.1	712.8	712.5	712.2	711.9	711.6	711.3
137.5°	743.9	744.4	744.2	743.9	743.6	743.2	742.9	742.9	742.9	742.9	742.9
140°	771.0	771.2	771.1	771.0	770.8	770.7	770.5	770.8	771.1	771.4	771.7
142.5°	797.2	797.3	797.5	797.8	798.1	798.5	798.8	798.8	798.8	798.8	798.8
145°	823.9	824.1	824.1	824.1	824.1	824.1	824.1	824.3	824.4	824.6	824.7
147.5°	845.9	845.9	846.0	846.1	846.3	846.4	846.6	846.8	846.9	847.1	847.2
150°	866.4	866.2	866.4	866.7	867.0	867.3	867.6	867.9	868.3	868.6	868.9
152.5°	885.4	885.0	885.2	885.5	885.8	886.2	886.5	886.8	887.1	887.4	887.7
155°	902.2	901.7	901.9	902.2	902.5	902.8	903.1	903.6	904.1	904.6	905.1
157.5°	917.8	917.6	917.6	917.6	917.6	917.6	917.6	918.1	918.6	919.1	919.6
160°	930.4	929.9	930.0	930.2	930.3	930.5	930.7	931.3	932.0	932.6	933.3
162.5°	942.0	941.5	941.6	941.8	941.9	942.1	942.3	943.3	944.2	945.2	946.1
165°	952.2	951.7	951.8	951.9	952.1	952.2	952.4	953.4	954.4	955.3	956.3
167.5°	960.2	959.7	959.8	959.9	960.1	960.2	960.4	961.5	962.7	963.8	964.9
170°	966.1	965.5	965.6	965.7	965.9	966.0	966.2	967.5	968.8	970.1	971.4
172.5°	970.4	969.8	970.0	970.3	970.6	971.0	971.3	972.4	973.5	974.6	975.7
175°	973.9	973.4	973.5	973.7	973.8	974.0	974.2	975.5	976.8	978.1	979.4
177.5°	976.1	975.6	975.7	975.8	976.0	976.1	976.3	977.4	978.6	979.7	980.8
180°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1678.1	1667.6	1666.1	1669.1	1663.1	1672.1	1669.1	1672.1	1664.6	1672.1	1667.6
5°	1562.4	1559.4	1553.4	1545.9	1547.4	1548.9	1556.4	1548.9	1554.9	1556.4	1563.9
7.5°	1454.3	1448.3	1452.8	1449.8	1436.2	1433.2	1436.2	1440.7	1449.8	1455.8	1460.3
10°	1367.1	1364.1	1358.1	1353.6	1346.1	1341.6	1347.6	1341.6	1353.6	1364.1	1364.1
12.5°	1301.0	1289.0	1281.5	1280.0	1263.5	1266.5	1272.5	1277.0	1290.5	1296.5	1296.5
15°	1231.9	1222.9	1219.9	1213.9	1207.9	1213.9	1210.9	1215.4	1221.4	1227.4	1230.4
17.5°	1171.8	1170.3	1171.8	1156.8	1161.3	1153.8	1155.3	1162.8	1158.3	1162.8	1171.8
20°	1117.7	1120.7	1116.2	1110.2	1110.2	1101.2	1111.7	1108.7	1110.2	1119.2	1132.8
22.5°	1077.2	1075.7	1071.2	1066.7	1060.7	1062.2	1063.7	1060.7	1072.7	1080.2	1081.7
25°	1033.6	1030.6	1029.1	1024.6	1018.6	1024.6	1023.1	1024.6	1027.6	1039.6	1030.6
27.5°	993.0	987.0	990.0	985.5	984.0	985.5	985.5	987.0	990.0	991.5	993.0
30°	958.5	952.5	951.0	948.0	946.5	948.0	951.0	948.0	960.0	958.5	958.5
32.5°	920.9	916.4	913.4	913.4	911.9	910.4	911.9	913.4	922.4	916.4	922.4
35°	884.9	881.9	881.9	878.9	877.4	877.4	877.4	883.4	880.4	884.9	884.9
37.5°	850.3	850.3	848.8	845.8	844.3	845.8	844.3	847.3	845.8	847.3	848.8
40°	814.3	811.3	809.8	809.8	805.3	800.7	805.3	805.3	806.8	811.3	812.8
42.5°	770.7	772.2	772.2	766.2	766.2	766.2	767.7	769.2	769.2	772.2	772.2
45°	733.1	730.1	730.1	730.1	727.1	728.6	731.6	731.6	731.6	731.6	728.6
47.5°	691.1	691.1	692.6	692.6	697.1	695.6	695.6	694.1	691.1	691.1	692.6
50°	652.0	656.5	658.0	658.0	659.5	661.0	661.0	658.0	656.5	652.0	652.0
52.5°	614.5	617.5	620.5	625.0	628.0	626.5	626.5	623.5	617.5	616.0	614.5
55°	573.9	578.4	584.4	588.9	593.4	594.9	594.9	588.9	582.9	575.4	575.4
57.5°	536.3	540.8	551.4	555.9	561.9	561.9	558.9	554.4	545.3	539.3	534.8
60°	498.8	506.3	513.8	522.8	530.3	531.8	527.3	521.3	510.8	503.3	497.3
62.5°	458.2	465.7	480.7	489.8	495.8	495.8	495.8	488.3	474.7	464.2	455.2
65°	419.2	426.7	440.2	452.2	456.7	461.2	456.7	449.2	438.7	426.7	417.7
67.5°	378.6	387.6	401.1	410.1	416.1	420.7	417.7	411.6	398.1	381.6	375.6
70°	333.5	338.0	357.6	366.6	375.6	378.6	375.6	366.6	353.1	335.0	329.0
72.5°	291.5	296.0	314.0	321.5	329.0	332.0	327.5	321.5	309.5	293.0	285.4
75°	243.4	250.9	259.9	271.9	280.9	283.9	279.4	274.9	259.9	249.4	243.4
77.5°	192.3	199.8	211.8	222.3	231.4	229.9	223.8	225.4	208.8	196.8	192.3
80°	145.7	151.7	160.8	169.8	174.3	174.3	172.8	166.8	160.8	151.7	144.2
82.5°	100.7	108.2	115.7	121.7	121.7	123.2	120.2	118.7	112.7	105.2	103.7
85°	60.1	61.6	67.6	67.6	73.6	70.6	69.1	73.6	67.6	63.1	61.6
87.5°	27.0	25.5	27.0	27.0	25.5	28.5	28.5	27.0	28.5	27.0	27.0
90°	15.2	15.4	15.9	16.4	16.9	17.4	16.9	16.4	15.9	15.4	15.2
92.5°	15.2	15.3	15.4	15.6	15.7	15.9	15.7	15.6	15.4	15.3	15.2
95°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2
97.5°	14.5	14.6	14.7	14.9	15.0	15.2	15.0	14.9	14.7	14.6	14.5
100°	18.1	17.8	17.1	16.5	15.8	15.2	15.8	16.5	17.1	17.8	18.1
102.5°	171.1	164.3	150.8	137.3	123.7	110.2	123.7	137.3	150.8	164.3	171.1
105°	216.0	215.9	215.8	215.6	215.5	215.3	215.5	215.6	215.8	215.9	216.0
107.5°	264.6	264.3	263.6	263.0	262.3	261.7	262.3	263.0	263.6	264.3	264.6
110°	309.5	309.6	309.7	309.9	310.0	310.2	310.0	309.9	309.7	309.6	309.5

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	355.2	355.0	354.7	354.4	354.0	353.7	354.0	354.4	354.7	355.0	355.2
115°	401.6	401.1	400.1	399.2	398.2	397.2	398.2	399.2	400.1	401.1	401.6
117.5°	445.8	445.6	445.3	445.0	444.6	444.3	444.6	445.0	445.3	445.6	445.8
120°	490.7	490.3	489.5	488.7	487.9	487.1	487.9	488.7	489.5	490.3	490.7
122.5°	532.0	531.5	530.6	529.6	528.7	527.7	528.7	529.6	530.6	531.5	532.0
125°	571.2	571.0	570.5	570.0	569.5	569.0	569.5	570.0	570.5	571.0	571.2
127.5°	608.9	608.3	607.0	605.7	604.4	603.1	604.4	605.7	607.0	608.3	608.9
130°	644.4	644.0	643.2	642.3	641.5	640.7	641.5	642.3	643.2	644.0	644.4
132.5°	679.2	678.8	678.0	677.1	676.3	675.5	676.3	677.1	678.0	678.8	679.2
135°	711.1	710.6	709.6	708.7	707.7	706.7	707.7	708.7	709.6	710.6	711.1
137.5°	742.9	742.5	741.7	740.9	740.1	739.3	740.1	740.9	741.7	742.5	742.9
140°	771.9	771.4	770.5	769.5	768.6	767.6	768.6	769.5	770.5	771.4	771.9
142.5°	798.8	798.3	797.3	796.4	795.4	794.4	795.4	796.4	797.3	798.3	798.8
145°	824.8	824.3	823.4	822.4	821.5	820.5	821.5	822.4	823.4	824.3	824.8
147.5°	847.3	846.7	845.6	844.5	843.3	842.2	843.3	844.5	845.6	846.7	847.3
150°	869.1	868.5	867.2	865.9	864.6	863.3	864.6	865.9	867.2	868.5	869.1
152.5°	887.9	887.3	886.2	885.1	883.9	882.8	883.9	885.1	886.2	887.3	887.9
155°	905.3	904.7	903.4	902.1	900.8	899.5	900.8	902.1	903.4	904.7	905.3
157.5°	919.8	919.2	917.9	916.6	915.3	914.0	915.3	916.6	917.9	919.2	919.8
160°	933.6	933.0	931.7	930.4	929.1	927.8	929.1	930.4	931.7	933.0	933.6
162.5°	946.6	945.9	944.4	943.0	941.5	940.1	941.5	943.0	944.4	945.9	946.6
165°	956.8	956.2	954.9	953.6	952.3	951.0	952.3	953.6	954.9	956.2	956.8
167.5°	965.5	964.8	963.3	961.8	960.4	958.9	960.4	961.8	963.3	964.8	965.5
170°	972.0	971.3	969.8	968.4	966.9	965.5	966.9	968.4	969.8	971.3	972.0
172.5°	976.3	975.6	974.1	972.7	971.2	969.8	971.2	972.7	974.1	975.6	976.3
175°	980.0	979.3	977.8	976.3	974.9	973.4	974.9	976.3	977.8	979.3	980.0
177.5°	981.4	980.8	979.5	978.2	976.9	975.6	976.9	978.2	979.5	980.8	981.4
180°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8	1769.8
2.5°	1681.1	1672.1	1682.6	1669.1	1672.1	1688.6	1687.1	1702.2	1711.2	1709.7	1717.2
5°	1569.9	1569.9	1574.5	1573.0	1588.0	1601.5	1619.5	1634.5	1651.1	1660.1	1670.6
7.5°	1460.3	1475.3	1478.3	1485.8	1503.8	1526.4	1544.4	1566.9	1591.0	1607.5	1619.5
10°	1370.1	1382.2	1394.2	1400.2	1419.7	1449.8	1475.3	1511.4	1541.4	1559.4	1576.0
12.5°	1290.5	1304.0	1310.0	1337.1	1350.6	1370.1	1406.2	1445.3	1478.3	1497.8	1511.4
15°	1233.4	1240.9	1254.5	1271.0	1284.5	1308.5	1338.6	1382.2	1413.7	1430.2	1476.8
17.5°	1185.3	1194.4	1201.9	1209.4	1230.4	1256.0	1284.5	1322.1	1362.6	1391.2	1415.2
20°	1135.8	1140.3	1149.3	1161.3	1176.3	1200.4	1225.9	1265.0	1301.0	1323.6	1355.1
22.5°	1077.2	1090.7	1099.7	1108.7	1125.3	1152.3	1176.3	1204.9	1249.9	1275.5	1308.5
25°	1042.6	1048.6	1054.6	1065.2	1077.2	1101.2	1128.3	1158.3	1194.4	1221.4	1249.9
27.5°	997.6	1006.6	1014.1	1027.6	1035.1	1054.6	1080.2	1110.2	1153.8	1176.3	1200.4
30°	960.0	969.0	975.0	981.0	991.5	1012.6	1036.6	1060.7	1101.2	1129.8	1153.8
32.5°	922.4	931.5	939.0	943.5	954.0	967.5	987.0	1017.1	1051.6	1071.2	1102.7
35°	889.4	889.4	898.4	904.4	913.4	925.4	943.5	966.0	1002.1	1027.6	1056.1
37.5°	851.8	853.3	860.8	865.3	874.4	886.4	904.4	925.4	955.5	975.0	1003.6
40°	812.8	817.3	820.3	827.8	838.3	842.8	860.8	884.9	914.9	933.0	957.0
42.5°	773.7	776.7	784.2	790.2	799.2	806.8	818.8	841.3	863.8	890.9	910.4
45°	730.1	737.6	742.2	752.7	757.2	764.7	776.7	794.7	821.8	838.3	860.8
47.5°	692.6	695.6	698.6	712.1	721.1	725.6	737.6	748.2	776.7	791.7	812.8
50°	652.0	652.0	656.5	662.5	673.0	682.1	692.6	704.6	727.1	742.2	763.2
52.5°	614.5	610.0	613.0	616.0	626.5	635.5	646.0	662.5	683.6	692.6	710.6
55°	573.9	566.4	570.9	575.4	578.4	590.4	602.4	613.0	629.5	643.0	659.5
57.5°	530.3	528.8	525.8	527.3	534.8	542.3	551.4	564.9	584.4	594.9	603.9
60°	491.3	482.3	479.2	482.3	486.8	491.3	503.3	515.3	531.8	542.3	552.9
62.5°	450.7	441.7	435.7	431.2	435.7	446.2	453.7	462.7	476.2	488.3	497.3
65°	411.6	398.1	392.1	389.1	387.6	395.1	401.1	413.1	425.2	429.7	440.2
67.5°	368.1	356.1	348.5	344.0	344.0	344.0	350.0	362.1	374.1	375.6	386.1
70°	324.5	311.0	303.5	297.5	294.5	297.5	305.0	306.5	317.0	320.0	326.0
72.5°	277.9	265.9	256.9	249.4	250.9	253.9	253.9	256.9	262.9	270.4	270.4
75°	234.4	217.8	213.3	207.3	204.3	204.3	204.3	210.3	214.8	220.8	219.3
77.5°	184.8	175.8	166.8	163.8	159.2	157.7	160.8	160.8	163.8	168.3	169.8
80°	142.7	132.2	126.2	123.2	117.2	115.7	117.2	117.2	121.7	120.2	121.7
82.5°	99.2	91.6	87.1	82.6	79.6	81.1	79.6	79.6	81.1	79.6	79.6
85°	57.1	55.6	52.6	51.1	49.6	46.6	49.6	48.1	46.6	45.1	48.1
87.5°	27.0	25.5	25.5	22.5	22.5	21.0	22.5	22.5	21.0	21.0	21.0
90°	14.8	14.0	13.2	12.4	11.6	10.5	9.3	8.2	7.1	6.5	5.9
92.5°	14.8	14.0	13.2	12.4	11.6	10.6	9.6	8.7	7.7	7.2	7.9
95°	14.8	14.0	13.2	12.4	11.6	17.7	23.8	29.9	36.0	39.1	39.3
97.5°	14.3	14.0	13.7	13.3	13.0	28.3	43.6	58.9	74.2	81.9	81.4
100°	30.1	54.1	78.1	102.1	126.1	125.5	124.8	124.2	123.5	123.2	123.0
102.5°	170.9	170.6	170.3	169.9	169.6	169.3	169.0	168.7	168.4	168.2	167.9
105°	216.0	216.0	216.0	216.0	216.0	216.0	216.0	216.0	216.0	216.0	215.7
107.5°	264.5	264.3	264.2	264.0	263.8	263.5	263.2	262.9	262.6	262.4	262.4
110°	309.7	310.2	310.7	311.2	311.7	311.4	311.0	310.7	310.4	310.2	310.2

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	355.5	356.2	356.8	357.5	358.1	357.9	357.7	357.6	357.4	357.3	357.1
115°	401.9	402.6	403.2	403.9	404.5	404.3	404.1	404.0	403.8	403.7	403.3
117.5°	446.3	447.2	448.2	449.1	450.1	449.5	448.8	448.2	447.5	447.2	447.2
120°	490.9	491.2	491.5	491.9	492.2	491.7	491.2	490.7	490.2	490.0	490.1
122.5°	532.2	532.5	532.8	533.2	533.5	533.3	533.1	533.0	532.8	532.7	532.3
125°	571.5	572.2	572.8	573.5	574.1	574.1	574.1	574.1	574.1	574.1	573.5
127.5°	609.1	609.4	609.7	610.0	610.3	610.5	610.6	610.8	610.9	611.0	610.6
130°	644.6	645.1	645.6	646.0	646.5	646.3	646.2	646.0	645.9	645.8	645.4
132.5°	679.2	679.2	679.2	679.2	679.2	679.7	680.1	680.6	681.1	681.3	680.8
135°	711.3	711.6	711.9	712.2	712.5	712.8	713.1	713.4	713.7	713.9	713.4
137.5°	742.9	742.9	742.9	742.9	742.9	743.2	743.6	743.9	744.2	744.4	743.9
140°	771.7	771.4	771.1	770.8	770.5	770.7	770.8	771.0	771.1	771.2	771.0
142.5°	798.8	798.8	798.8	798.8	798.8	798.5	798.1	797.8	797.5	797.3	797.2
145°	824.7	824.6	824.4	824.3	824.1	824.1	824.1	824.1	824.1	824.1	823.9
147.5°	847.2	847.1	846.9	846.8	846.6	846.4	846.3	846.1	846.0	845.9	845.9
150°	868.9	868.6	868.3	867.9	867.6	867.3	867.0	866.7	866.4	866.2	866.4
152.5°	887.7	887.4	887.1	886.8	886.5	886.2	885.8	885.5	885.2	885.0	885.4
155°	905.1	904.6	904.1	903.6	903.1	902.8	902.5	902.2	901.9	901.7	902.2
157.5°	919.6	919.1	918.6	918.1	917.6	917.6	917.6	917.6	917.6	917.6	917.8
160°	933.3	932.6	932.0	931.3	930.7	930.5	930.3	930.2	930.0	929.9	930.4
162.5°	946.1	945.2	944.2	943.3	942.3	942.1	941.9	941.8	941.6	941.5	942.0
165°	956.3	955.3	954.4	953.4	952.4	952.2	952.1	951.9	951.8	951.7	952.2
167.5°	964.9	963.8	962.7	961.5	960.4	960.2	960.1	959.9	959.8	959.7	960.2
170°	971.4	970.1	968.8	967.5	966.2	966.0	965.9	965.7	965.6	965.5	966.1
172.5°	975.7	974.6	973.5	972.4	971.3	971.0	970.6	970.3	970.0	969.8	970.4
175°	979.4	978.1	976.8	975.5	974.2	974.0	973.8	973.7	973.5	973.4	973.9
177.5°	980.8	979.7	978.6	977.4	976.3	976.1	976.0	975.8	975.7	975.6	976.1
180°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1769.8	1769.8	1769.8	1769.8
2.5°	1727.7	1742.7	1753.2	1772.8
5°	1688.6	1715.7	1741.2	1768.3
7.5°	1649.6	1681.1	1721.7	1756.2
10°	1606.0	1646.6	1694.6	1741.2
12.5°	1562.4	1610.5	1663.1	1724.7
15°	1509.9	1571.4	1633.0	1699.1
17.5°	1463.3	1526.4	1592.5	1675.1
20°	1410.7	1479.8	1551.9	1636.0
22.5°	1364.1	1440.7	1515.9	1604.5
25°	1311.5	1386.7	1469.3	1563.9
27.5°	1268.0	1337.1	1418.2	1520.4
30°	1215.4	1290.5	1371.6	1473.8
32.5°	1165.8	1237.9	1323.6	1424.2
35°	1114.7	1188.4	1265.0	1361.1
37.5°	1066.7	1129.8	1206.4	1298.0
40°	1012.6	1081.7	1150.8	1222.9
42.5°	963.0	1026.1	1090.7	1147.8
45°	907.4	961.5	1023.1	1069.7
47.5°	856.3	904.4	952.5	988.5
50°	805.3	842.8	878.9	910.4
52.5°	745.2	787.2	806.8	826.3
55°	691.1	715.1	733.1	752.7
57.5°	638.5	649.0	658.0	676.1
60°	569.4	581.4	591.9	605.4
62.5°	509.3	515.3	518.3	531.8
65°	452.2	450.7	458.2	465.7
67.5°	390.6	389.1	396.6	399.6
70°	330.5	329.0	330.5	338.0
72.5°	273.4	273.4	274.9	277.9
75°	220.8	220.8	222.3	225.4
77.5°	166.8	169.8	168.3	174.3
80°	121.7	118.7	121.7	124.7
82.5°	79.6	82.6	82.6	79.6
85°	45.1	45.1	45.1	45.1
87.5°	19.5	19.5	21.0	22.5
90°	4.6	3.3	2.0	0.7
92.5°	9.4	10.9	12.3	13.8
95°	39.8	40.3	40.8	41.3
97.5°	80.5	79.5	78.6	77.6
100°	122.5	122.0	121.5	121.0
102.5°	167.2	166.6	165.9	165.3
105°	215.0	214.4	213.7	213.1
107.5°	262.4	262.4	262.4	262.4
110°	310.2	310.2	310.2	310.2

TEST NUMBER: P1034453

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	356.6	356.1	355.7	355.2
115°	402.5	401.7	400.9	400.1
117.5°	447.2	447.2	447.2	447.2
120°	490.2	490.4	490.5	490.7
122.5°	531.5	530.7	529.9	529.1
125°	572.4	571.3	570.1	569.0
127.5°	609.8	609.0	608.2	607.4
130°	644.6	643.8	643.0	642.2
132.5°	679.9	678.9	678.0	677.0
135°	712.5	711.5	710.6	709.6
137.5°	742.9	742.0	741.0	740.0
140°	770.7	770.4	770.1	769.8
142.5°	797.1	796.9	796.8	796.6
145°	823.6	823.3	823.0	822.7
147.5°	845.9	845.9	845.9	845.9
150°	866.7	867.0	867.3	867.6
152.5°	886.2	887.0	887.8	888.6
155°	903.1	904.1	905.0	906.0
157.5°	918.3	918.8	919.3	919.8
160°	931.4	932.3	933.3	934.3
162.5°	943.0	943.9	944.9	945.9
165°	953.1	954.1	955.0	956.0
167.5°	961.1	962.1	963.0	964.0
170°	967.2	968.3	969.4	970.5
172.5°	971.5	972.6	973.8	974.9
175°	974.9	975.8	976.8	977.8
177.5°	977.1	978.0	979.0	980.0
180°	977.8	977.8	977.8	977.8

(END OF REPORT)