

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034543

Luminaire Tested: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034543
REPORT IS A COMBINATION OF REPORTS P1003724 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6508.0 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44			37
1	95	91	87	84	86	83	79	77	67	65	63	53	51	50	39	39	38			32
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32			27
3	79	70	63	57	71	64	58	53	52	48	44	41	38	36	31	29	27			23
4	72	62	54	48	65	56	50	45	46	41	38	37	33	31	28	26	24			20
5	66	55	47	41	60	50	44	38	41	36	32	33	29	26	25	23	21			17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18			15
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16			13
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14			12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13			11
10	45	34	27	22	41	31	25	20	26	21	17	21	17	15	16	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5492	5492	5492	5492
5°	5497	6231	5501	4727
10°	5463	7102	5454	4057
15°	5423	7700	5389	3666
20°	5355	8438	5305	3347
25°	5293	9668	5197	3158
30°	5206	10200	5116	2987
35°	5068	8176	4962	2849
40°	4853	5651	4781	2704
45°	4580	4207	4529	2583
50°	4269	3464	4198	2486
55°	3932	2954	3901	2402
60°	3602	2529	3540	2337
65°	3246	2184	3194	2242
70°	2870	1813	2833	2077
75°	2473	1403	2439	1802
80°	1952	948	1881	1325
85°	1246	474	1206	676

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8389 cd/sqm

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	1.3
10°-20°	245.7	3.8
20°-30°	399.2	6.1
30°-40°	487.9	7.5
40°-50°	442.5	6.8
50°-60°	352.5	5.4
60°-70°	245.5	3.8
70°-80°	130.8	2.0
80°-90°	34.4	0.5
90°-100°	45.2	0.7
100°-110°	300.3	4.6
110°-120°	540.7	8.3
120°-130°	694.1	10.7
130°-140°	746.5	11.5
140°-150°	700.6	10.8
150°-160°	566.7	8.7
160°-170°	366.5	5.6
170°-180°	126.4	1.9
0°-30°	727.4	11.2
0°-40°	1215.3	18.7
0°-60°	2010.3	30.9
0°-90°	2421.0	37.2
90°-120°	886.2	13.6
90°-150°	3027.4	46.5
90°-180°	4087.0	62.8
0°-180°	6508.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	857	857	857	857	857	
5°	856	989	857	750	856	81
15°	823	1235	818	588	823	232
25°	758	1519	744	496	758	349
35°	659	1220	646	425	659	412
45°	518	575	512	353	518	399
55°	365	354	362	288	365	326
65°	226	218	222	223	226	224
75°	109	107	108	138	109	116
85°	22	24	21	34	22	26
90°	1	24	1	24	1	4
95°	56	21	56	21	56	69
105°	290	293	290	293	290	307
115°	544	540	544	540	544	540
125°	774	774	774	774	774	692
135°	966	962	966	962	966	744
145°	1119	1116	1119	1116	1119	700
155°	1233	1224	1233	1224	1233	568
165°	1301	1294	1301	1294	1301	367
175°	1330	1325	1330	1325	1330	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2
2.5°	858.7	863.8	869.6	874.0	881.3	883.4	887.1	889.3	891.4	893.6	895.1
5°	856.5	868.9	879.8	887.8	901.6	906.7	913.3	921.3	930.7	938.7	943.8
7.5°	850.7	870.3	884.9	900.9	919.8	932.2	938.7	955.5	970.8	982.4	997.7
10°	843.4	866.7	889.3	913.3	940.2	954.0	967.1	990.4	1011.5	1030.4	1045.7
12.5°	835.4	863.8	890.7	922.0	958.4	975.1	983.9	1023.9	1050.1	1060.3	1090.1
15°	823.0	856.5	895.1	933.6	964.2	983.9	1007.9	1039.9	1066.1	1088.6	1112.7
17.5°	811.4	847.8	887.1	930.0	974.4	999.9	1018.1	1046.4	1074.8	1103.9	1126.5
20°	792.5	839.8	879.8	925.6	978.0	996.2	1015.1	1048.6	1079.2	1110.5	1138.9
22.5°	777.2	822.3	876.9	920.5	964.9	983.1	1006.4	1041.3	1077.7	1113.4	1154.9
25°	757.5	807.8	855.1	901.6	947.5	967.1	988.2	1033.3	1071.2	1117.0	1162.9
27.5°	736.4	788.1	835.4	877.6	920.5	947.5	970.0	1017.3	1067.5	1117.8	1177.4
30°	713.9	762.6	807.8	849.2	896.5	924.2	946.7	1002.1	1058.1	1122.1	1193.4
32.5°	689.9	735.7	774.3	816.5	866.7	892.2	922.7	983.1	1049.4	1125.8	1215.3
35°	659.3	703.0	737.2	780.1	830.3	863.1	895.1	962.8	1039.9	1125.0	1227.6
37.5°	628.7	662.9	695.7	741.5	799.7	829.6	863.1	937.3	1025.3	1122.9	1232.7
40°	592.4	625.8	654.2	700.8	761.9	796.1	831.0	908.9	1008.6	1114.8	1214.5
42.5°	556.0	584.3	615.6	664.4	723.3	759.7	796.8	883.4	986.8	1091.6	1164.3
45°	518.1	540.0	574.2	618.5	681.1	716.1	758.3	852.1	956.2	1049.4	1085.7
47.5°	478.8	500.7	532.7	575.6	637.5	678.9	719.0	812.8	917.6	989.7	989.7
50°	441.0	458.5	489.7	532.7	595.3	633.1	673.9	773.6	858.0	911.1	863.8
52.5°	400.2	419.9	446.1	491.2	553.1	587.3	631.6	716.8	796.8	818.7	745.9
55°	364.6	380.6	405.3	448.3	505.8	541.4	579.3	660.8	728.4	727.0	649.1
57.5°	327.5	340.6	366.8	406.1	459.2	491.2	529.0	599.6	654.9	635.3	561.8
60°	293.3	302.7	328.2	360.2	411.2	441.0	477.4	534.9	577.1	549.4	475.2
62.5°	257.6	268.5	288.9	320.2	365.3	389.3	416.2	474.5	501.4	476.6	401.0
65°	225.6	234.3	252.5	278.7	319.5	341.3	364.6	412.6	438.1	402.4	339.8
67.5°	193.6	203.8	216.9	240.1	272.2	292.5	312.9	354.4	366.0	334.0	281.6
70°	163.7	172.5	184.8	201.6	228.5	246.7	262.0	296.2	304.2	274.3	232.9
72.5°	134.6	140.4	150.6	164.5	189.2	199.4	215.4	238.7	248.9	222.0	192.1
75°	109.2	113.5	120.1	130.3	147.0	157.9	171.0	192.8	192.1	173.2	152.1
77.5°	84.4	85.1	92.4	101.9	112.1	121.5	128.1	143.4	144.8	133.2	115.7
80°	60.4	62.6	65.5	72.8	81.5	85.1	93.1	102.6	104.1	95.3	83.7
82.5°	38.6	40.0	42.2	46.6	52.4	56.8	61.1	64.8	68.4	63.3	53.9
85°	21.8	22.6	24.7	26.2	29.1	31.3	34.9	38.6	37.8	34.2	31.3
87.5°	10.9	10.9	10.9	12.4	13.8	13.8	15.3	16.0	16.7	15.3	13.8
90°	1.0	2.8	4.5	6.3	8.0	8.9	9.7	11.2	12.7	14.3	15.8
92.5°	18.7	16.7	14.8	12.8	10.9	9.9	10.6	11.9	13.2	14.5	15.8
95°	56.2	55.6	54.9	54.3	53.6	53.3	49.1	40.8	32.5	24.1	15.8
97.5°	105.5	106.8	108.2	109.5	110.8	111.5	101.1	80.3	59.4	38.6	17.8
100°	164.7	165.4	166.0	166.7	167.4	167.7	168.1	169.0	169.9	170.7	171.6
102.5°	224.9	225.8	226.6	227.5	228.4	228.8	229.0	229.5	229.9	230.4	230.8
105°	290.0	290.9	291.7	292.6	293.5	293.9	293.9	293.9	293.9	293.9	293.9
107.5°	357.0	357.0	357.0	357.0	357.0	357.0	357.2	357.7	358.1	358.6	359.0
110°	422.1	422.1	422.1	422.1	422.1	422.1	422.3	422.8	423.2	423.7	424.1

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	483.3	483.9	484.6	485.2	485.9	486.2	486.3	486.5	486.8	487.0	487.2
115°	544.4	545.5	546.6	547.7	548.8	549.4	549.5	549.7	549.9	550.1	550.3
117.5°	608.5	608.5	608.5	608.5	608.5	608.5	608.9	609.8	610.7	611.6	612.5
120°	667.7	667.5	667.3	667.0	666.8	666.7	667.0	667.7	668.4	669.0	669.7
122.5°	720.0	721.1	722.2	723.3	724.4	724.9	725.0	725.2	725.5	725.7	725.9
125°	774.2	775.7	777.3	778.8	780.3	781.1	781.1	781.1	781.1	781.1	781.1
127.5°	826.5	827.6	828.7	829.8	830.9	831.4	831.3	831.1	830.9	830.7	830.5
130°	873.9	875.0	876.1	877.2	878.3	878.8	878.9	879.1	879.4	879.6	879.8
132.5°	921.2	922.5	923.8	925.1	926.4	927.1	926.8	926.1	925.5	924.8	924.2
135°	965.6	966.9	968.2	969.5	970.8	971.5	971.3	970.8	970.4	969.9	969.5
137.5°	1007.0	1008.3	1009.6	1010.9	1012.2	1012.9	1012.7	1012.2	1011.8	1011.3	1010.9
140°	1047.4	1047.8	1048.3	1048.7	1049.2	1049.4	1049.3	1049.1	1048.8	1048.6	1048.4
142.5°	1083.9	1084.1	1084.3	1084.6	1084.8	1084.9	1085.1	1085.6	1086.0	1086.5	1086.9
145°	1119.4	1119.8	1120.3	1120.7	1121.2	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4
147.5°	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0	1151.1	1151.3	1151.6	1151.8	1152.0
150°	1180.6	1180.2	1179.7	1179.3	1178.8	1178.6	1178.8	1179.3	1179.7	1180.2	1180.6
152.5°	1209.2	1208.1	1207.0	1205.9	1204.8	1204.3	1204.5	1204.9	1205.4	1205.8	1206.2
155°	1232.9	1231.6	1230.2	1228.9	1227.6	1226.9	1227.1	1227.6	1228.0	1228.5	1228.9
157.5°	1251.6	1250.9	1250.3	1249.6	1248.9	1248.6	1248.6	1248.6	1248.6	1248.6	1248.6
160°	1271.3	1270.0	1268.7	1267.4	1266.1	1265.4	1265.5	1265.7	1266.0	1266.2	1266.4
162.5°	1287.1	1285.8	1284.5	1283.2	1281.9	1281.2	1281.3	1281.5	1281.8	1282.0	1282.2
165°	1300.9	1299.6	1298.3	1297.0	1295.7	1295.0	1295.1	1295.3	1295.6	1295.8	1296.0
167.5°	1311.8	1310.5	1309.1	1307.8	1306.5	1305.8	1305.9	1306.1	1306.4	1306.6	1306.8
170°	1320.6	1319.1	1317.5	1316.0	1314.5	1313.7	1313.8	1314.0	1314.3	1314.5	1314.7
172.5°	1326.6	1325.1	1323.5	1322.0	1320.5	1319.7	1319.9	1320.3	1320.8	1321.2	1321.6
175°	1330.5	1329.2	1327.9	1326.6	1325.3	1324.6	1324.7	1324.9	1325.2	1325.4	1325.6
177.5°	1333.5	1332.2	1330.8	1329.5	1328.2	1327.5	1327.6	1327.8	1328.1	1328.3	1328.5
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2
2.5°	896.5	901.6	906.0	909.6	912.5	916.9	914.0	914.7	916.2	919.1	919.1
5°	954.8	962.8	967.1	981.7	985.3	984.6	982.4	994.0	993.3	989.0	988.2
7.5°	1011.5	1025.3	1037.7	1049.4	1053.0	1062.5	1064.6	1069.7	1068.3	1075.5	1071.9
10°	1063.2	1085.0	1096.7	1114.1	1118.5	1122.9	1128.7	1131.6	1138.1	1137.4	1137.4
12.5°	1103.2	1129.4	1144.7	1149.0	1165.8	1170.9	1176.0	1185.4	1183.2	1184.0	1188.3
15°	1134.5	1160.0	1173.1	1193.4	1205.1	1210.9	1219.6	1229.8	1228.4	1234.9	1233.5
17.5°	1157.8	1181.8	1205.8	1236.4	1237.1	1252.4	1272.8	1277.1	1286.6	1280.0	1280.0
20°	1176.7	1208.7	1242.9	1282.2	1286.6	1296.0	1320.8	1337.5	1348.4	1344.8	1347.0
22.5°	1197.1	1242.9	1282.9	1322.2	1343.3	1360.1	1384.1	1410.3	1419.8	1425.6	1424.1
25°	1223.3	1271.3	1330.2	1384.8	1406.7	1438.7	1470.7	1496.2	1503.4	1519.4	1504.9
27.5°	1250.2	1317.9	1391.4	1455.4	1483.1	1509.3	1547.8	1566.8	1576.2	1583.5	1578.4
30°	1272.8	1365.9	1446.0	1504.9	1524.5	1539.8	1561.7	1566.0	1562.4	1568.2	1575.5
32.5°	1307.7	1398.7	1466.3	1494.7	1492.5	1491.8	1475.1	1451.8	1446.7	1432.9	1451.8
35°	1326.6	1399.4	1425.6	1387.7	1372.5	1344.8	1291.7	1256.7	1226.2	1219.6	1221.1
37.5°	1315.7	1344.1	1312.8	1213.1	1188.3	1146.1	1075.5	1026.1	1003.5	986.0	1008.6
40°	1256.7	1225.5	1139.6	1018.1	982.4	942.4	876.2	849.2	817.2	810.7	840.5
42.5°	1159.2	1063.9	942.4	848.5	811.4	788.8	733.5	708.1	685.5	675.3	692.0
45°	1026.8	911.1	788.8	711.7	680.4	653.5	620.7	593.8	579.3	574.9	588.7
47.5°	890.0	767.7	670.2	612.7	580.0	559.6	529.0	513.8	502.1	503.6	505.8
50°	759.0	647.7	572.7	515.2	499.2	483.2	462.8	449.7	443.9	446.1	444.6
52.5°	646.2	556.0	492.7	448.3	441.0	425.7	409.0	398.1	395.9	396.6	398.8
55°	547.2	476.6	426.4	394.4	386.4	375.5	365.3	358.0	352.2	354.4	353.7
57.5°	472.3	410.4	371.9	345.7	339.8	333.3	323.8	320.2	318.0	313.6	317.3
60°	406.1	355.8	322.4	306.4	301.3	296.9	286.7	282.3	280.9	278.7	284.5
62.5°	343.5	307.8	282.3	267.8	262.7	258.3	253.2	249.6	250.3	247.4	250.3
65°	294.0	264.9	246.7	233.6	227.0	224.1	223.4	217.6	216.9	217.6	218.3
67.5°	248.1	223.4	209.6	201.6	196.5	193.6	191.4	187.7	190.7	188.5	189.9
70°	206.7	189.9	175.4	167.4	165.2	165.9	162.3	160.8	161.6	160.1	161.6
72.5°	166.6	152.8	147.0	141.2	138.3	137.5	135.4	133.2	135.4	134.6	134.6
75°	133.2	123.0	116.4	112.8	112.8	111.3	107.7	107.7	107.7	107.0	107.7
77.5°	102.6	93.9	91.0	87.3	87.3	85.1	84.4	84.4	83.0	85.1	83.7
80°	76.4	69.9	65.5	63.3	63.3	62.6	61.1	60.4	61.1	60.4	60.4
82.5°	49.5	46.6	44.4	42.2	41.5	42.2	41.5	40.0	40.8	40.0	41.5
85°	28.4	25.5	25.5	24.0	24.7	23.3	24.0	22.6	21.8	24.0	22.6
87.5°	12.4	11.6	11.6	10.2	10.2	10.2	9.5	10.2	9.5	8.7	9.5
90°	16.9	18.0	19.1	20.2	20.7	21.0	21.7	22.4	23.0	23.7	23.0
92.5°	16.9	18.0	19.1	20.2	20.7	20.8	21.0	21.3	21.5	21.7	21.5
95°	16.9	18.0	19.1	20.2	20.7	20.7	20.7	20.7	20.7	20.7	20.7
97.5°	18.2	18.6	19.1	19.5	19.7	19.8	20.0	20.3	20.5	20.7	20.5
100°	139.0	106.3	73.7	41.0	24.7	24.3	23.4	22.5	21.6	20.7	21.6
102.5°	231.2	231.7	232.1	232.6	232.8	223.6	205.2	186.7	168.3	149.9	168.3
105°	293.9	293.9	293.9	293.9	293.9	293.8	293.6	293.3	293.1	292.9	293.1
107.5°	359.2	359.4	359.7	359.9	360.0	359.6	358.7	357.8	357.0	356.1	357.0
110°	423.4	422.8	422.1	421.4	421.1	421.2	421.4	421.7	421.9	422.1	421.9

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	486.3	485.5	484.6	483.7	483.3	483.1	482.6	482.2	481.7	481.3	481.7
115°	549.4	548.6	547.7	546.8	546.4	545.7	544.4	543.1	541.8	540.5	541.8
117.5°	611.2	609.9	608.6	607.3	606.6	606.4	605.9	605.5	605.0	604.6	605.0
120°	669.3	668.8	668.4	667.9	667.7	667.2	666.1	665.0	663.9	662.8	663.9
122.5°	725.5	725.0	724.6	724.1	723.9	723.2	721.9	720.6	719.3	718.0	719.3
125°	780.2	779.4	778.5	777.6	777.2	776.9	776.2	775.5	774.9	774.2	774.9
127.5°	830.1	829.6	829.2	828.7	828.5	827.6	825.9	824.1	822.4	820.6	822.4
130°	879.1	878.5	877.8	877.1	876.8	876.3	875.2	874.1	873.0	871.9	873.0
132.5°	924.2	924.2	924.2	924.2	924.2	923.6	922.5	921.4	920.3	919.2	920.3
135°	969.1	968.6	968.2	967.7	967.5	966.8	965.5	964.2	962.9	961.6	962.9
137.5°	1010.9	1010.9	1010.9	1010.9	1010.9	1010.4	1009.3	1008.2	1007.1	1006.0	1007.1
140°	1048.8	1049.3	1049.7	1050.2	1050.4	1049.7	1048.4	1047.1	1045.8	1044.5	1045.8
142.5°	1086.9	1086.9	1086.9	1086.9	1086.9	1086.2	1084.9	1083.6	1082.3	1081.0	1082.3
145°	1121.6	1121.8	1122.1	1122.3	1122.4	1121.7	1120.4	1119.1	1117.8	1116.5	1117.8
147.5°	1152.2	1152.4	1152.7	1152.9	1153.0	1152.2	1150.7	1149.2	1147.6	1146.1	1147.6
150°	1181.0	1181.5	1181.9	1182.4	1182.6	1181.7	1180.0	1178.2	1176.5	1174.7	1176.5
152.5°	1206.6	1207.1	1207.5	1208.0	1208.2	1207.4	1205.9	1204.4	1202.8	1201.3	1202.8
155°	1229.6	1230.2	1230.9	1231.6	1231.9	1231.0	1229.3	1227.5	1225.8	1224.0	1225.8
157.5°	1249.3	1249.9	1250.6	1251.3	1251.6	1250.7	1249.0	1247.2	1245.5	1243.7	1245.5
160°	1267.3	1268.1	1269.0	1269.9	1270.3	1269.4	1267.7	1265.9	1264.2	1262.4	1264.2
162.5°	1283.5	1284.8	1286.1	1287.4	1288.1	1287.1	1285.1	1283.2	1281.2	1279.2	1281.2
165°	1297.3	1298.6	1299.9	1301.2	1301.9	1301.0	1299.3	1297.5	1295.8	1294.0	1295.8
167.5°	1308.3	1309.9	1311.4	1312.9	1313.7	1312.7	1310.8	1308.8	1306.9	1304.9	1306.9
170°	1316.5	1318.2	1320.0	1321.7	1322.6	1321.6	1319.6	1317.7	1315.7	1313.7	1315.7
172.5°	1323.1	1324.7	1326.2	1327.7	1328.5	1327.5	1325.6	1323.6	1321.7	1319.7	1321.7
175°	1327.4	1329.1	1330.9	1332.6	1333.5	1332.5	1330.5	1328.6	1326.6	1324.6	1326.6
177.5°	1330.0	1331.6	1333.1	1334.6	1335.4	1334.5	1332.8	1331.0	1329.3	1327.5	1329.3
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2
2.5°	917.6	912.5	914.0	912.5	908.9	906.7	900.9	893.6	890.7	887.1	884.9
5°	991.1	987.5	986.8	980.9	979.5	970.8	956.2	948.9	940.2	931.5	922.7
7.5°	1071.2	1066.8	1052.3	1050.1	1051.5	1040.6	1021.7	1007.1	989.0	976.6	959.8
10°	1137.4	1128.7	1116.3	1117.0	1111.9	1097.4	1078.5	1063.2	1037.0	1021.0	997.0
12.5°	1177.4	1170.2	1168.7	1161.4	1157.1	1138.1	1115.6	1095.9	1076.3	1054.4	1036.3
15°	1226.2	1216.7	1210.2	1200.0	1197.1	1177.4	1152.7	1130.1	1107.6	1087.2	1048.6
17.5°	1280.0	1269.8	1245.1	1242.9	1225.5	1206.5	1182.5	1149.0	1125.0	1095.9	1067.5
20°	1341.2	1326.6	1294.6	1286.6	1272.8	1241.5	1208.7	1171.6	1133.0	1103.2	1069.7
22.5°	1409.6	1384.1	1360.8	1335.3	1325.2	1286.6	1241.5	1196.3	1149.8	1109.0	1069.0
25°	1498.3	1464.9	1432.1	1406.7	1389.2	1339.0	1278.6	1218.9	1165.1	1111.9	1059.5
27.5°	1568.2	1539.1	1503.4	1470.0	1447.4	1387.7	1318.6	1241.5	1174.5	1109.8	1053.7
30°	1573.3	1564.6	1542.7	1524.5	1499.8	1435.8	1359.4	1272.0	1189.1	1110.5	1042.1
32.5°	1478.0	1495.4	1504.9	1507.8	1502.7	1465.6	1395.7	1299.7	1202.2	1103.9	1031.9
35°	1272.8	1319.3	1376.8	1398.7	1419.8	1439.4	1403.0	1319.3	1206.5	1102.5	1015.9
37.5°	1047.9	1090.1	1185.4	1229.1	1253.8	1331.7	1361.5	1316.4	1215.3	1103.9	1000.6
40°	845.6	912.5	980.9	1039.9	1078.5	1165.8	1258.2	1268.4	1202.9	1090.1	980.9
42.5°	711.7	751.0	802.7	857.2	891.4	994.8	1119.9	1193.4	1164.3	1067.5	956.9
45°	606.2	635.3	684.0	702.2	745.9	844.9	977.3	1083.6	1098.1	1031.9	929.3
47.5°	520.3	545.1	576.3	598.9	633.8	708.1	820.1	937.3	1007.1	983.1	890.7
50°	458.5	478.8	505.0	518.1	540.7	607.6	692.0	808.5	902.4	910.4	840.5
52.5°	406.8	418.4	438.8	453.4	471.6	512.3	588.7	684.8	790.3	834.0	778.6
55°	361.7	371.1	389.3	398.8	408.2	443.2	502.8	590.2	689.1	746.6	715.3
57.5°	320.9	328.9	344.2	352.9	358.0	391.5	437.4	505.8	594.5	664.4	646.9
60°	287.4	294.7	303.5	310.0	315.8	343.5	375.5	430.8	510.1	577.8	573.4
62.5°	251.8	258.3	267.8	274.3	279.4	296.9	323.8	366.0	433.7	496.3	508.7
65°	220.5	225.6	232.1	235.0	241.6	254.7	276.5	314.4	369.7	425.7	434.4
67.5°	192.1	193.6	197.9	204.5	205.9	217.6	237.2	265.6	308.5	354.4	368.2
70°	161.6	163.7	167.4	172.5	175.4	182.7	199.4	218.3	255.4	295.4	305.6
72.5°	134.6	137.5	139.0	141.9	143.4	155.0	162.3	181.2	206.7	240.1	251.1
75°	109.2	112.1	112.8	114.2	115.7	120.8	131.0	142.6	163.7	185.6	200.1
77.5°	86.6	85.9	87.3	89.5	88.8	93.1	99.7	109.9	123.7	141.9	151.4
80°	61.1	61.1	63.3	65.5	64.8	69.1	71.3	78.6	90.2	101.9	105.5
82.5°	40.8	40.8	42.9	42.9	44.4	45.1	48.0	51.7	61.1	66.9	69.1
85°	23.3	23.3	24.0	24.0	24.0	25.5	27.7	29.1	32.0	35.7	37.1
87.5°	9.5	10.2	10.2	10.2	10.2	11.6	11.6	13.1	13.8	15.3	15.3
90°	22.4	21.7	21.0	20.7	20.2	19.1	18.0	16.9	15.8	14.3	12.7
92.5°	21.3	21.0	20.8	20.7	20.2	19.1	18.0	16.9	15.8	14.5	13.2
95°	20.7	20.7	20.7	20.7	20.2	19.1	18.0	16.9	15.8	24.1	32.5
97.5°	20.3	20.0	19.8	19.7	19.5	19.1	18.6	18.2	17.8	38.6	59.4
100°	22.5	23.4	24.3	24.7	41.0	73.7	106.3	139.0	171.6	170.7	169.9
102.5°	186.7	205.2	223.6	232.8	232.6	232.1	231.7	231.2	230.8	230.4	229.9
105°	293.3	293.6	293.8	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9
107.5°	357.8	358.7	359.6	360.0	359.9	359.7	359.4	359.2	359.0	358.6	358.1
110°	421.7	421.4	421.2	421.1	421.4	422.1	422.8	423.4	424.1	423.7	423.2

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	482.2	482.6	483.1	483.3	483.7	484.6	485.5	486.3	487.2	487.0	486.8
115°	543.1	544.4	545.7	546.4	546.8	547.7	548.6	549.4	550.3	550.1	549.9
117.5°	605.5	605.9	606.4	606.6	607.3	608.6	609.9	611.2	612.5	611.6	610.7
120°	665.0	666.1	667.2	667.7	667.9	668.4	668.8	669.3	669.7	669.0	668.4
122.5°	720.6	721.9	723.2	723.9	724.1	724.6	725.0	725.5	725.9	725.7	725.5
125°	775.5	776.2	776.9	777.2	777.6	778.5	779.4	780.2	781.1	781.1	781.1
127.5°	824.1	825.9	827.6	828.5	828.7	829.2	829.6	830.1	830.5	830.7	830.9
130°	874.1	875.2	876.3	876.8	877.1	877.8	878.5	879.1	879.8	879.6	879.4
132.5°	921.4	922.5	923.6	924.2	924.2	924.2	924.2	924.2	924.2	924.8	925.5
135°	964.2	965.5	966.8	967.5	967.7	968.2	968.6	969.1	969.5	969.9	970.4
137.5°	1008.2	1009.3	1010.4	1010.9	1010.9	1010.9	1010.9	1010.9	1010.9	1011.3	1011.8
140°	1047.1	1048.4	1049.7	1050.4	1050.2	1049.7	1049.3	1048.8	1048.4	1048.6	1048.8
142.5°	1083.6	1084.9	1086.2	1086.9	1086.9	1086.9	1086.9	1086.9	1086.9	1086.5	1086.0
145°	1119.1	1120.4	1121.7	1122.4	1122.3	1122.1	1121.8	1121.6	1121.4	1121.4	1121.4
147.5°	1149.2	1150.7	1152.2	1153.0	1152.9	1152.7	1152.4	1152.2	1152.0	1151.8	1151.6
150°	1178.2	1180.0	1181.7	1182.6	1182.4	1181.9	1181.5	1181.0	1180.6	1180.2	1179.7
152.5°	1204.4	1205.9	1207.4	1208.2	1208.0	1207.5	1207.1	1206.6	1206.2	1205.8	1205.4
155°	1227.5	1229.3	1231.0	1231.9	1231.6	1230.9	1230.2	1229.6	1228.9	1228.5	1228.0
157.5°	1247.2	1249.0	1250.7	1251.6	1251.3	1250.6	1249.9	1249.3	1248.6	1248.6	1248.6
160°	1265.9	1267.7	1269.4	1270.3	1269.9	1269.0	1268.1	1267.3	1266.4	1266.2	1266.0
162.5°	1283.2	1285.1	1287.1	1288.1	1287.4	1286.1	1284.8	1283.5	1282.2	1282.0	1281.8
165°	1297.5	1299.3	1301.0	1301.9	1301.2	1299.9	1298.6	1297.3	1296.0	1295.8	1295.6
167.5°	1308.8	1310.8	1312.7	1313.7	1312.9	1311.4	1309.9	1308.3	1306.8	1306.6	1306.4
170°	1317.7	1319.6	1321.6	1322.6	1321.7	1320.0	1318.2	1316.5	1314.7	1314.5	1314.3
172.5°	1323.6	1325.6	1327.5	1328.5	1327.7	1326.2	1324.7	1323.1	1321.6	1321.2	1320.8
175°	1328.6	1330.5	1332.5	1333.5	1332.6	1330.9	1329.1	1327.4	1325.6	1325.4	1325.2
177.5°	1331.0	1332.8	1334.5	1335.4	1334.6	1333.1	1331.6	1330.0	1328.5	1328.3	1328.1
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2
2.5°	882.0	878.3	874.0	874.0	868.9	866.7	862.3	860.9	857.2	851.4	847.0
5°	913.3	903.8	898.0	892.9	882.0	874.0	866.0	857.2	848.5	838.3	826.7
7.5°	943.8	926.4	918.4	909.6	893.6	876.9	860.9	849.2	837.6	821.6	807.0
10°	975.9	954.0	939.5	927.8	903.1	882.0	858.7	842.0	823.8	803.4	784.5
12.5°	1002.8	974.4	962.0	940.2	911.8	886.3	857.2	831.8	807.8	783.7	760.5
15°	1025.3	998.4	967.8	959.1	919.8	883.4	850.7	817.9	788.1	764.1	737.2
17.5°	1032.6	998.4	983.1	962.0	915.5	877.6	836.1	800.5	772.1	736.4	715.3
20°	1034.8	1002.1	980.9	961.3	919.8	869.6	828.9	785.2	751.0	715.3	681.9
22.5°	1029.0	990.4	970.0	951.1	904.5	861.6	814.3	766.3	726.3	693.5	660.0
25°	1018.1	972.9	953.3	932.9	888.5	841.2	789.6	743.7	706.6	667.3	634.6
27.5°	1003.5	951.8	929.3	908.2	864.5	820.1	771.4	724.1	682.6	641.1	610.5
30°	985.3	925.6	905.3	877.6	835.4	793.2	748.8	701.5	654.9	615.6	582.2
32.5°	962.0	899.4	872.5	846.3	800.5	761.9	719.7	675.3	630.2	591.6	556.7
35°	940.9	869.6	839.8	813.6	762.6	721.9	687.0	645.5	605.5	565.4	534.1
37.5°	912.5	839.8	804.1	777.2	725.5	684.0	651.3	619.3	577.1	538.5	509.4
40°	882.7	802.7	769.2	742.3	688.4	643.3	612.0	583.6	549.4	513.8	483.2
42.5°	855.8	767.0	731.3	698.6	644.0	604.0	572.0	550.1	518.9	486.8	459.2
45°	821.6	729.2	690.6	656.4	604.0	560.3	529.8	512.3	489.0	457.7	433.7
47.5°	786.6	688.4	648.4	614.9	558.2	519.6	489.7	473.0	457.0	432.3	408.2
50°	740.8	645.5	609.1	570.5	514.5	475.2	450.4	433.7	421.3	403.9	383.5
52.5°	690.6	601.1	561.8	528.3	473.0	437.4	409.0	399.5	387.1	374.0	356.6
55°	637.5	553.1	515.2	482.5	431.5	395.1	371.9	361.7	352.2	342.0	330.4
57.5°	584.3	502.8	467.2	438.1	390.8	355.8	336.9	323.1	316.6	310.7	301.3
60°	518.1	449.0	421.3	395.1	348.6	316.6	298.4	288.2	282.3	279.4	275.1
62.5°	459.9	403.1	372.6	347.1	310.0	281.6	264.2	256.2	251.1	249.6	244.5
65°	398.1	349.3	325.3	303.5	271.4	246.0	231.4	222.0	218.3	217.6	217.6
67.5°	339.8	300.5	276.5	261.2	233.6	211.0	197.2	193.6	191.4	188.5	187.7
70°	285.3	254.0	232.9	219.8	195.0	178.3	167.4	161.6	161.6	159.4	157.9
72.5°	237.2	205.9	192.1	181.2	160.8	146.3	138.3	136.8	131.7	131.0	131.0
75°	185.6	162.3	152.8	143.4	128.1	117.9	111.3	107.7	104.8	104.8	105.5
77.5°	139.7	123.7	115.0	107.7	96.8	90.2	85.1	83.7	80.8	80.8	80.8
80°	99.0	90.2	83.7	77.9	69.9	64.0	61.1	58.2	58.2	57.5	58.2
82.5°	64.0	56.8	53.1	52.4	45.1	42.9	39.3	40.0	37.8	37.1	38.6
85°	37.1	33.5	29.1	27.7	24.7	21.8	20.4	21.1	20.4	19.6	20.4
87.5°	14.6	12.4	11.6	11.6	9.5	8.7	8.0	8.7	7.3	7.3	8.0
90°	11.2	9.7	8.9	8.0	6.3	4.5	2.8	1.0	2.8	4.5	6.3
92.5°	11.9	10.6	9.9	10.9	12.8	14.8	16.7	18.7	16.7	14.8	12.8
95°	40.8	49.1	53.3	53.6	54.3	54.9	55.6	56.2	55.6	54.9	54.3
97.5°	80.3	101.1	111.5	110.8	109.5	108.2	106.8	105.5	106.8	108.2	109.5
100°	169.0	168.1	167.7	167.4	166.7	166.0	165.4	164.7	165.4	166.0	166.7
102.5°	229.5	229.0	228.8	228.4	227.5	226.6	225.8	224.9	225.8	226.6	227.5
105°	293.9	293.9	293.9	293.5	292.6	291.7	290.9	290.0	290.9	291.7	292.6
107.5°	357.7	357.2	357.0	357.0	357.0	357.0	357.0	357.0	357.0	357.0	357.0
110°	422.8	422.3	422.1	422.1	422.1	422.1	422.1	422.1	422.1	422.1	422.1

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	486.5	486.3	486.2	485.9	485.2	484.6	483.9	483.3	483.9	484.6	485.2
115°	549.7	549.5	549.4	548.8	547.7	546.6	545.5	544.4	545.5	546.6	547.7
117.5°	609.8	608.9	608.5	608.5	608.5	608.5	608.5	608.5	608.5	608.5	608.5
120°	667.7	667.0	666.7	666.8	667.0	667.3	667.5	667.7	667.5	667.3	667.0
122.5°	725.2	725.0	724.9	724.4	723.3	722.2	721.1	720.0	721.1	722.2	723.3
125°	781.1	781.1	781.1	780.3	778.8	777.3	775.7	774.2	775.7	777.3	778.8
127.5°	831.1	831.3	831.4	830.9	829.8	828.7	827.6	826.5	827.6	828.7	829.8
130°	879.1	878.9	878.8	878.3	877.2	876.1	875.0	873.9	875.0	876.1	877.2
132.5°	926.1	926.8	927.1	926.4	925.1	923.8	922.5	921.2	922.5	923.8	925.1
135°	970.8	971.3	971.5	970.8	969.5	968.2	966.9	965.6	966.9	968.2	969.5
137.5°	1012.2	1012.7	1012.9	1012.2	1010.9	1009.6	1008.3	1007.0	1008.3	1009.6	1010.9
140°	1049.1	1049.3	1049.4	1049.2	1048.7	1048.3	1047.8	1047.4	1047.8	1048.3	1048.7
142.5°	1085.6	1085.1	1084.9	1084.8	1084.6	1084.3	1084.1	1083.9	1084.1	1084.3	1084.6
145°	1121.4	1121.4	1121.4	1121.2	1120.7	1120.3	1119.8	1119.4	1119.8	1120.3	1120.7
147.5°	1151.3	1151.1	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0
150°	1179.3	1178.8	1178.6	1178.8	1179.3	1179.7	1180.2	1180.6	1180.2	1179.7	1179.3
152.5°	1204.9	1204.5	1204.3	1204.8	1205.9	1207.0	1208.1	1209.2	1208.1	1207.0	1205.9
155°	1227.6	1227.1	1226.9	1227.6	1228.9	1230.2	1231.6	1232.9	1231.6	1230.2	1228.9
157.5°	1248.6	1248.6	1248.6	1248.9	1249.6	1250.3	1250.9	1251.6	1250.9	1250.3	1249.6
160°	1265.7	1265.5	1265.4	1266.1	1267.4	1268.7	1270.0	1271.3	1270.0	1268.7	1267.4
162.5°	1281.5	1281.3	1281.2	1281.9	1283.2	1284.5	1285.8	1287.1	1285.8	1284.5	1283.2
165°	1295.3	1295.1	1295.0	1295.7	1297.0	1298.3	1299.6	1300.9	1299.6	1298.3	1297.0
167.5°	1306.1	1305.9	1305.8	1306.5	1307.8	1309.1	1310.5	1311.8	1310.5	1309.1	1307.8
170°	1314.0	1313.8	1313.7	1314.5	1316.0	1317.5	1319.1	1320.6	1319.1	1317.5	1316.0
172.5°	1320.3	1319.9	1319.7	1320.5	1322.0	1323.5	1325.1	1326.6	1325.1	1323.5	1322.0
175°	1324.9	1324.7	1324.6	1325.3	1326.6	1327.9	1329.2	1330.5	1329.2	1327.9	1326.6
177.5°	1327.8	1327.6	1327.5	1328.2	1329.5	1330.8	1332.2	1333.5	1332.2	1330.8	1329.5
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2
2.5°	845.6	844.1	840.5	838.3	831.0	822.3	819.4	812.1	815.0	809.9	809.9
5°	823.0	816.5	812.1	805.6	791.7	782.3	772.1	767.0	764.1	760.5	757.5
7.5°	793.9	788.8	784.5	772.1	756.8	743.7	731.3	726.3	716.8	710.2	707.3
10°	768.5	761.2	751.0	736.4	720.4	703.7	692.8	681.9	674.6	670.9	662.9
12.5°	742.3	733.5	722.6	701.5	684.0	673.9	654.2	644.0	640.4	637.5	628.0
15°	715.3	705.9	692.8	673.1	657.8	633.8	622.2	614.2	605.5	604.7	597.4
17.5°	691.3	679.7	668.8	644.7	625.8	604.7	598.2	589.4	581.4	572.7	569.1
20°	660.8	649.8	641.8	615.6	594.5	581.4	570.5	563.2	558.2	549.4	548.0
22.5°	633.1	621.5	610.5	590.9	572.7	556.0	542.9	534.9	532.7	529.0	522.5
25°	606.2	594.5	581.4	563.2	544.3	532.7	521.0	515.9	511.6	505.8	500.7
27.5°	583.6	572.7	560.3	537.8	521.8	513.0	500.7	494.8	489.0	486.1	483.9
30°	556.7	544.3	534.9	517.4	499.9	488.3	479.6	474.5	469.4	466.5	465.0
32.5°	530.5	518.9	512.3	493.4	479.6	465.7	459.2	455.5	452.6	449.7	446.8
35°	509.4	497.8	487.6	470.1	456.3	446.8	441.7	435.9	433.7	430.8	430.8
37.5°	483.2	474.5	464.3	447.5	435.2	427.9	423.5	416.2	415.5	414.1	411.9
40°	460.6	451.9	442.4	427.9	417.0	408.2	402.4	398.8	396.6	395.1	393.7
42.5°	436.6	427.2	422.8	406.1	396.6	387.9	385.0	381.3	380.6	377.7	374.0
45°	413.3	405.3	396.6	384.2	376.2	368.9	364.6	361.7	358.0	357.3	355.1
47.5°	393.0	383.5	375.5	363.9	355.1	349.3	345.7	342.0	339.1	336.9	334.7
50°	366.8	359.5	352.9	340.6	333.3	327.5	322.4	319.5	316.6	316.6	316.6
52.5°	341.3	334.7	328.9	320.2	311.5	306.4	300.5	298.4	296.9	294.7	296.9
55°	316.6	310.0	304.2	297.6	287.4	283.1	277.3	275.1	275.8	275.8	278.0
57.5°	290.4	285.3	281.6	273.6	264.2	259.8	256.2	254.0	254.0	256.9	257.6
60°	264.9	259.8	253.2	246.0	240.1	235.0	232.9	233.6	233.6	235.0	238.7
62.5°	236.5	233.6	230.0	219.8	216.1	212.5	209.6	211.8	211.0	214.7	219.8
65°	210.3	207.4	202.3	197.2	192.8	189.2	188.5	189.2	190.7	194.3	200.1
67.5°	181.2	181.2	176.8	172.5	168.8	165.2	165.9	166.6	168.1	172.5	181.2
70°	157.2	154.3	149.9	147.0	144.1	142.6	141.2	144.1	148.5	151.4	157.9
72.5°	131.0	128.8	125.2	122.3	121.5	120.1	119.3	120.8	125.2	130.3	137.5
75°	103.3	104.1	101.9	99.7	99.7	97.5	99.0	99.0	103.3	108.4	114.2
77.5°	80.0	79.3	78.6	77.1	76.4	76.4	76.4	77.9	82.2	85.1	91.0
80°	56.8	57.5	55.3	56.0	55.3	56.0	56.0	58.9	61.1	64.8	69.1
82.5°	37.8	37.8	36.4	37.1	37.1	37.1	37.8	39.3	42.2	45.1	48.0
85°	21.1	21.8	20.4	21.8	21.8	21.8	22.6	23.3	25.5	26.2	29.1
87.5°	8.0	9.5	9.5	8.0	8.7	9.5	10.2	9.5	10.9	12.4	13.1
90°	8.0	8.9	9.7	11.2	12.7	14.3	15.8	16.9	18.0	19.1	20.2
92.5°	10.9	9.9	10.6	11.9	13.2	14.5	15.8	16.9	18.0	19.1	20.2
95°	53.6	53.3	49.1	40.8	32.5	24.1	15.8	16.9	18.0	19.1	20.2
97.5°	110.8	111.5	101.1	80.3	59.4	38.6	17.8	18.2	18.6	19.1	19.5
100°	167.4	167.7	168.1	169.0	169.9	170.7	171.6	139.0	106.3	73.7	41.0
102.5°	228.4	228.8	229.0	229.5	229.9	230.4	230.8	231.2	231.7	232.1	232.6
105°	293.5	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9
107.5°	357.0	357.0	357.2	357.7	358.1	358.6	359.0	359.2	359.4	359.7	359.9
110°	422.1	422.1	422.3	422.8	423.2	423.7	424.1	423.4	422.8	422.1	421.4

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	485.9	486.2	486.3	486.5	486.8	487.0	487.2	486.3	485.5	484.6	483.7
115°	548.8	549.4	549.5	549.7	549.9	550.1	550.3	549.4	548.6	547.7	546.8
117.5°	608.5	608.5	608.9	609.8	610.7	611.6	612.5	611.2	609.9	608.6	607.3
120°	666.8	666.7	667.0	667.7	668.4	669.0	669.7	669.3	668.8	668.4	667.9
122.5°	724.4	724.9	725.0	725.2	725.5	725.7	725.9	725.5	725.0	724.6	724.1
125°	780.3	781.1	781.1	781.1	781.1	781.1	781.1	780.2	779.4	778.5	777.6
127.5°	830.9	831.4	831.3	831.1	830.9	830.7	830.5	830.1	829.6	829.2	828.7
130°	878.3	878.8	878.9	879.1	879.4	879.6	879.8	879.1	878.5	877.8	877.1
132.5°	926.4	927.1	926.8	926.1	925.5	924.8	924.2	924.2	924.2	924.2	924.2
135°	970.8	971.5	971.3	970.8	970.4	969.9	969.5	969.1	968.6	968.2	967.7
137.5°	1012.2	1012.9	1012.7	1012.2	1011.8	1011.3	1010.9	1010.9	1010.9	1010.9	1010.9
140°	1049.2	1049.4	1049.3	1049.1	1048.8	1048.6	1048.4	1048.8	1049.3	1049.7	1050.2
142.5°	1084.8	1084.9	1085.1	1085.6	1086.0	1086.5	1086.9	1086.9	1086.9	1086.9	1086.9
145°	1121.2	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4	1121.6	1121.8	1122.1	1122.3
147.5°	1151.0	1151.0	1151.1	1151.3	1151.6	1151.8	1152.0	1152.2	1152.4	1152.7	1152.9
150°	1178.8	1178.6	1178.8	1179.3	1179.7	1180.2	1180.6	1181.0	1181.5	1181.9	1182.4
152.5°	1204.8	1204.3	1204.5	1204.9	1205.4	1205.8	1206.2	1206.6	1207.1	1207.5	1208.0
155°	1227.6	1226.9	1227.1	1227.6	1228.0	1228.5	1228.9	1229.6	1230.2	1230.9	1231.6
157.5°	1248.9	1248.6	1248.6	1248.6	1248.6	1248.6	1248.6	1249.3	1249.9	1250.6	1251.3
160°	1266.1	1265.4	1265.5	1265.7	1266.0	1266.2	1266.4	1267.3	1268.1	1269.0	1269.9
162.5°	1281.9	1281.2	1281.3	1281.5	1281.8	1282.0	1282.2	1283.5	1284.8	1286.1	1287.4
165°	1295.7	1295.0	1295.1	1295.3	1295.6	1295.8	1296.0	1297.3	1298.6	1299.9	1301.2
167.5°	1306.5	1305.8	1305.9	1306.1	1306.4	1306.6	1306.8	1308.3	1309.9	1311.4	1312.9
170°	1314.5	1313.7	1313.8	1314.0	1314.3	1314.5	1314.7	1316.5	1318.2	1320.0	1321.7
172.5°	1320.5	1319.7	1319.9	1320.3	1320.8	1321.2	1321.6	1323.1	1324.7	1326.2	1327.7
175°	1325.3	1324.6	1324.7	1324.9	1325.2	1325.4	1325.6	1327.4	1329.1	1330.9	1332.6
177.5°	1328.2	1327.5	1327.6	1327.8	1328.1	1328.3	1328.5	1330.0	1331.6	1333.1	1334.6
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2
2.5°	812.8	807.8	807.0	808.5	805.6	809.9	808.5	809.9	806.3	809.9	807.8
5°	756.8	755.4	752.4	748.8	749.5	750.3	753.9	750.3	753.2	753.9	757.5
7.5°	704.4	701.5	703.7	702.2	695.7	694.2	695.7	697.9	702.2	705.1	707.3
10°	662.2	660.8	657.8	655.7	652.0	649.8	652.8	649.8	655.7	660.8	660.8
12.5°	630.2	624.4	620.7	620.0	612.0	613.5	616.4	618.5	625.1	628.0	628.0
15°	596.7	592.4	590.9	588.0	585.1	588.0	586.5	588.7	591.6	594.5	596.0
17.5°	567.6	566.9	567.6	560.3	562.5	558.9	559.6	563.2	561.1	563.2	567.6
20°	541.4	542.9	540.7	537.8	537.8	533.4	538.5	537.0	537.8	542.1	548.7
22.5°	521.8	521.0	518.9	516.7	513.8	514.5	515.2	513.8	519.6	523.2	523.9
25°	500.7	499.2	498.5	496.3	493.4	496.3	495.6	496.3	497.8	503.6	499.2
27.5°	481.0	478.1	479.6	477.4	476.6	477.4	477.4	478.1	479.6	480.3	481.0
30°	464.3	461.4	460.6	459.2	458.5	459.2	460.6	459.2	465.0	464.3	464.3
32.5°	446.1	443.9	442.4	442.4	441.7	441.0	441.7	442.4	446.8	443.9	446.8
35°	428.6	427.2	427.2	425.7	425.0	425.0	425.0	427.9	426.4	428.6	428.6
37.5°	411.9	411.9	411.2	409.7	409.0	409.7	409.0	410.4	409.7	410.4	411.2
40°	394.4	393.0	392.2	392.2	390.1	387.9	390.1	390.1	390.8	393.0	393.7
42.5°	373.3	374.0	374.0	371.1	371.1	371.1	371.9	372.6	372.6	374.0	374.0
45°	355.1	353.7	353.7	353.7	352.2	352.9	354.4	354.4	354.4	354.4	352.9
47.5°	334.7	334.7	335.5	335.5	337.7	336.9	336.9	336.2	334.7	334.7	335.5
50°	315.8	318.0	318.7	318.7	319.5	320.2	320.2	318.7	318.0	315.8	315.8
52.5°	297.6	299.1	300.5	302.7	304.2	303.5	303.5	302.0	299.1	298.4	297.6
55°	278.0	280.2	283.1	285.3	287.4	288.2	288.2	285.3	282.3	278.7	278.7
57.5°	259.8	262.0	267.1	269.3	272.2	272.2	270.7	268.5	264.2	261.2	259.1
60°	241.6	245.2	248.9	253.2	256.9	257.6	255.4	252.5	247.4	243.8	240.9
62.5°	222.0	225.6	232.9	237.2	240.1	240.1	240.1	236.5	230.0	224.9	220.5
65°	203.0	206.7	213.2	219.0	221.2	223.4	221.2	217.6	212.5	206.7	202.3
67.5°	183.4	187.7	194.3	198.7	201.6	203.8	202.3	199.4	192.8	184.8	181.9
70°	161.6	163.7	173.2	177.6	181.9	183.4	181.9	177.6	171.0	162.3	159.4
72.5°	141.2	143.4	152.1	155.7	159.4	160.8	158.6	155.7	149.9	141.9	138.3
75°	117.9	121.5	125.9	131.7	136.1	137.5	135.4	133.2	125.9	120.8	117.9
77.5°	93.1	96.8	102.6	107.7	112.1	111.3	108.4	109.2	101.2	95.3	93.1
80°	70.6	73.5	77.9	82.2	84.4	84.4	83.7	80.8	77.9	73.5	69.9
82.5°	48.8	52.4	56.0	58.9	58.9	59.7	58.2	57.5	54.6	50.9	50.2
85°	29.1	29.8	32.7	32.7	35.7	34.2	33.5	35.7	32.7	30.6	29.8
87.5°	13.1	12.4	13.1	13.1	12.4	13.8	13.8	13.1	13.8	13.1	13.1
90°	20.7	21.0	21.7	22.4	23.0	23.7	23.0	22.4	21.7	21.0	20.7
92.5°	20.7	20.8	21.0	21.3	21.5	21.7	21.5	21.3	21.0	20.8	20.7
95°	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
97.5°	19.7	19.8	20.0	20.3	20.5	20.7	20.5	20.3	20.0	19.8	19.7
100°	24.7	24.3	23.4	22.5	21.6	20.7	21.6	22.5	23.4	24.3	24.7
102.5°	232.8	223.6	205.2	186.7	168.3	149.9	168.3	186.7	205.2	223.6	232.8
105°	293.9	293.8	293.6	293.3	293.1	292.9	293.1	293.3	293.6	293.8	293.9
107.5°	360.0	359.6	358.7	357.8	357.0	356.1	357.0	357.8	358.7	359.6	360.0
110°	421.1	421.2	421.4	421.7	421.9	422.1	421.9	421.7	421.4	421.2	421.1

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	483.3	483.1	482.6	482.2	481.7	481.3	481.7	482.2	482.6	483.1	483.3
115°	546.4	545.7	544.4	543.1	541.8	540.5	541.8	543.1	544.4	545.7	546.4
117.5°	606.6	606.4	605.9	605.5	605.0	604.6	605.0	605.5	605.9	606.4	606.6
120°	667.7	667.2	666.1	665.0	663.9	662.8	663.9	665.0	666.1	667.2	667.7
122.5°	723.9	723.2	721.9	720.6	719.3	718.0	719.3	720.6	721.9	723.2	723.9
125°	777.2	776.9	776.2	775.5	774.9	774.2	774.9	775.5	776.2	776.9	777.2
127.5°	828.5	827.6	825.9	824.1	822.4	820.6	822.4	824.1	825.9	827.6	828.5
130°	876.8	876.3	875.2	874.1	873.0	871.9	873.0	874.1	875.2	876.3	876.8
132.5°	924.2	923.6	922.5	921.4	920.3	919.2	920.3	921.4	922.5	923.6	924.2
135°	967.5	966.8	965.5	964.2	962.9	961.6	962.9	964.2	965.5	966.8	967.5
137.5°	1010.9	1010.4	1009.3	1008.2	1007.1	1006.0	1007.1	1008.2	1009.3	1010.4	1010.9
140°	1050.4	1049.7	1048.4	1047.1	1045.8	1044.5	1045.8	1047.1	1048.4	1049.7	1050.4
142.5°	1086.9	1086.2	1084.9	1083.6	1082.3	1081.0	1082.3	1083.6	1084.9	1086.2	1086.9
145°	1122.4	1121.7	1120.4	1119.1	1117.8	1116.5	1117.8	1119.1	1120.4	1121.7	1122.4
147.5°	1153.0	1152.2	1150.7	1149.2	1147.6	1146.1	1147.6	1149.2	1150.7	1152.2	1153.0
150°	1182.6	1181.7	1180.0	1178.2	1176.5	1174.7	1176.5	1178.2	1180.0	1181.7	1182.6
152.5°	1208.2	1207.4	1205.9	1204.4	1202.8	1201.3	1202.8	1204.4	1205.9	1207.4	1208.2
155°	1231.9	1231.0	1229.3	1227.5	1225.8	1224.0	1225.8	1227.5	1229.3	1231.0	1231.9
157.5°	1251.6	1250.7	1249.0	1247.2	1245.5	1243.7	1245.5	1247.2	1249.0	1250.7	1251.6
160°	1270.3	1269.4	1267.7	1265.9	1264.2	1262.4	1264.2	1265.9	1267.7	1269.4	1270.3
162.5°	1288.1	1287.1	1285.1	1283.2	1281.2	1279.2	1281.2	1283.2	1285.1	1287.1	1288.1
165°	1301.9	1301.0	1299.3	1297.5	1295.8	1294.0	1295.8	1297.5	1299.3	1301.0	1301.9
167.5°	1313.7	1312.7	1310.8	1308.8	1306.9	1304.9	1306.9	1308.8	1310.8	1312.7	1313.7
170°	1322.6	1321.6	1319.6	1317.7	1315.7	1313.7	1315.7	1317.7	1319.6	1321.6	1322.6
172.5°	1328.5	1327.5	1325.6	1323.6	1321.7	1319.7	1321.7	1323.6	1325.6	1327.5	1328.5
175°	1333.5	1332.5	1330.5	1328.6	1326.6	1324.6	1326.6	1328.6	1330.5	1332.5	1333.5
177.5°	1335.4	1334.5	1332.8	1331.0	1329.3	1327.5	1329.3	1331.0	1332.8	1334.5	1335.4
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2	857.2
2.5°	814.3	809.9	815.0	808.5	809.9	817.9	817.2	824.5	828.9	828.1	831.8
5°	760.5	760.5	762.6	761.9	769.2	775.7	784.5	791.7	799.7	804.1	809.2
7.5°	707.3	714.6	716.1	719.7	728.4	739.3	748.1	759.0	770.6	778.6	784.5
10°	663.7	669.5	675.3	678.2	687.7	702.2	714.6	732.1	746.6	755.4	763.4
12.5°	625.1	631.6	634.6	647.7	654.2	663.7	681.1	700.1	716.1	725.5	732.1
15°	597.4	601.1	607.6	615.6	622.2	633.8	648.4	669.5	684.8	692.8	715.3
17.5°	574.2	578.5	582.2	585.8	596.0	608.4	622.2	640.4	660.0	673.9	685.5
20°	550.1	552.3	556.7	562.5	569.8	581.4	593.8	612.7	630.2	641.1	656.4
22.5°	521.8	528.3	532.7	537.0	545.1	558.2	569.8	583.6	605.5	617.8	633.8
25°	505.0	507.9	510.8	515.9	521.8	533.4	546.5	561.1	578.5	591.6	605.5
27.5°	483.2	487.6	491.2	497.8	501.4	510.8	523.2	537.8	558.9	569.8	581.4
30°	465.0	469.4	472.3	475.2	480.3	490.5	502.1	513.8	533.4	547.2	558.9
32.5°	446.8	451.2	454.8	457.0	462.1	468.6	478.1	492.7	509.4	518.9	534.1
35°	430.8	430.8	435.2	438.1	442.4	448.3	457.0	467.9	485.4	497.8	511.6
37.5°	412.6	413.3	417.0	419.2	423.5	429.3	438.1	448.3	462.8	472.3	486.1
40°	393.7	395.9	397.3	401.0	406.1	408.2	417.0	428.6	443.2	451.9	463.5
42.5°	374.8	376.2	379.9	382.8	387.1	390.8	396.6	407.5	418.4	431.5	441.0
45°	353.7	357.3	359.5	364.6	366.8	370.4	376.2	385.0	398.1	406.1	417.0
47.5°	335.5	336.9	338.4	344.9	349.3	351.5	357.3	362.4	376.2	383.5	393.7
50°	315.8	315.8	318.0	320.9	326.0	330.4	335.5	341.3	352.2	359.5	369.7
52.5°	297.6	295.4	296.9	298.4	303.5	307.8	312.9	320.9	331.1	335.5	344.2
55°	278.0	274.3	276.5	278.7	280.2	286.0	291.8	296.9	304.9	311.5	319.5
57.5°	256.9	256.2	254.7	255.4	259.1	262.7	267.1	273.6	283.1	288.2	292.5
60°	238.0	233.6	232.1	233.6	235.8	238.0	243.8	249.6	257.6	262.7	267.8
62.5°	218.3	213.9	211.0	208.9	211.0	216.1	219.8	224.1	230.7	236.5	240.9
65°	199.4	192.8	189.9	188.5	187.7	191.4	194.3	200.1	205.9	208.1	213.2
67.5°	178.3	172.5	168.8	166.6	166.6	166.6	169.6	175.4	181.2	181.9	187.0
70°	157.2	150.6	147.0	144.1	142.6	144.1	147.7	148.5	153.5	155.0	157.9
72.5°	134.6	128.8	124.4	120.8	121.5	123.0	123.0	124.4	127.3	131.0	131.0
75°	113.5	105.5	103.3	100.4	99.0	99.0	99.0	101.9	104.1	107.0	106.2
77.5°	89.5	85.1	80.8	79.3	77.1	76.4	77.9	77.9	79.3	81.5	82.2
80°	69.1	64.0	61.1	59.7	56.8	56.0	56.8	56.8	58.9	58.2	58.9
82.5°	48.0	44.4	42.2	40.0	38.6	39.3	38.6	38.6	39.3	38.6	38.6
85°	27.7	26.9	25.5	24.7	24.0	22.6	24.0	23.3	22.6	21.8	23.3
87.5°	13.1	12.4	12.4	10.9	10.9	10.2	10.9	10.9	10.2	10.2	10.2
90°	20.2	19.1	18.0	16.9	15.8	14.3	12.7	11.2	9.7	8.9	8.0
92.5°	20.2	19.1	18.0	16.9	15.8	14.5	13.2	11.9	10.6	9.9	10.9
95°	20.2	19.1	18.0	16.9	15.8	24.1	32.5	40.8	49.1	53.3	53.6
97.5°	19.5	19.1	18.6	18.2	17.8	38.6	59.4	80.3	101.1	111.5	110.8
100°	41.0	73.7	106.3	139.0	171.6	170.7	169.9	169.0	168.1	167.7	167.4
102.5°	232.6	232.1	231.7	231.2	230.8	230.4	229.9	229.5	229.0	228.8	228.4
105°	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.5
107.5°	359.9	359.7	359.4	359.2	359.0	358.6	358.1	357.7	357.2	357.0	357.0
110°	421.4	422.1	422.8	423.4	424.1	423.7	423.2	422.8	422.3	422.1	422.1

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	483.7	484.6	485.5	486.3	487.2	487.0	486.8	486.5	486.3	486.2	485.9
115°	546.8	547.7	548.6	549.4	550.3	550.1	549.9	549.7	549.5	549.4	548.8
117.5°	607.3	608.6	609.9	611.2	612.5	611.6	610.7	609.8	608.9	608.5	608.5
120°	667.9	668.4	668.8	669.3	669.7	669.0	668.4	667.7	667.0	666.7	666.8
122.5°	724.1	724.6	725.0	725.5	725.9	725.7	725.5	725.2	725.0	724.9	724.4
125°	777.6	778.5	779.4	780.2	781.1	781.1	781.1	781.1	781.1	781.1	780.3
127.5°	828.7	829.2	829.6	830.1	830.5	830.7	830.9	831.1	831.3	831.4	830.9
130°	877.1	877.8	878.5	879.1	879.8	879.6	879.4	879.1	878.9	878.8	878.3
132.5°	924.2	924.2	924.2	924.2	924.2	924.8	925.5	926.1	926.8	927.1	926.4
135°	967.7	968.2	968.6	969.1	969.5	969.9	970.4	970.8	971.3	971.5	970.8
137.5°	1010.9	1010.9	1010.9	1010.9	1010.9	1011.3	1011.8	1012.2	1012.7	1012.9	1012.2
140°	1050.2	1049.7	1049.3	1048.8	1048.4	1048.6	1048.8	1049.1	1049.3	1049.4	1049.2
142.5°	1086.9	1086.9	1086.9	1086.9	1086.9	1086.5	1086.0	1085.6	1085.1	1084.9	1084.8
145°	1122.3	1122.1	1121.8	1121.6	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4	1121.2
147.5°	1152.9	1152.7	1152.4	1152.2	1152.0	1151.8	1151.6	1151.3	1151.1	1151.0	1151.0
150°	1182.4	1181.9	1181.5	1181.0	1180.6	1180.2	1179.7	1179.3	1178.8	1178.6	1178.8
152.5°	1208.0	1207.5	1207.1	1206.6	1206.2	1205.8	1205.4	1204.9	1204.5	1204.3	1204.8
155°	1231.6	1230.9	1230.2	1229.6	1228.9	1228.5	1228.0	1227.6	1227.1	1226.9	1227.6
157.5°	1251.3	1250.6	1249.9	1249.3	1248.6	1248.6	1248.6	1248.6	1248.6	1248.6	1248.9
160°	1269.9	1269.0	1268.1	1267.3	1266.4	1266.2	1266.0	1265.7	1265.5	1265.4	1266.1
162.5°	1287.4	1286.1	1284.8	1283.5	1282.2	1282.0	1281.8	1281.5	1281.3	1281.2	1281.9
165°	1301.2	1299.9	1298.6	1297.3	1296.0	1295.8	1295.6	1295.3	1295.1	1295.0	1295.7
167.5°	1312.9	1311.4	1309.9	1308.3	1306.8	1306.6	1306.4	1306.1	1305.9	1305.8	1306.5
170°	1321.7	1320.0	1318.2	1316.5	1314.7	1314.5	1314.3	1314.0	1313.8	1313.7	1314.5
172.5°	1327.7	1326.2	1324.7	1323.1	1321.6	1321.2	1320.8	1320.3	1319.9	1319.7	1320.5
175°	1332.6	1330.9	1329.1	1327.4	1325.6	1325.4	1325.2	1324.9	1324.7	1324.6	1325.3
177.5°	1334.6	1333.1	1331.6	1330.0	1328.5	1328.3	1328.1	1327.8	1327.6	1327.5	1328.2
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	857.2	857.2	857.2	857.2
2.5°	836.9	844.1	849.2	858.7
5°	817.9	831.0	843.4	856.5
7.5°	799.0	814.3	834.0	850.7
10°	777.9	797.6	820.9	843.4
12.5°	756.8	780.1	805.6	835.4
15°	731.3	761.2	791.0	823.0
17.5°	708.8	739.3	771.4	811.4
20°	683.3	716.8	751.7	792.5
22.5°	660.8	697.9	734.3	777.2
25°	635.3	671.7	711.7	757.5
27.5°	614.2	647.7	687.0	736.4
30°	588.7	625.1	664.4	713.9
32.5°	564.7	599.6	641.1	689.9
35°	540.0	575.6	612.7	659.3
37.5°	516.7	547.2	584.3	628.7
40°	490.5	523.9	557.4	592.4
42.5°	466.5	497.0	528.3	556.0
45°	439.5	465.7	495.6	518.1
47.5°	414.8	438.1	461.4	478.8
50°	390.1	408.2	425.7	441.0
52.5°	360.9	381.3	390.8	400.2
55°	334.7	346.4	355.1	364.6
57.5°	309.3	314.4	318.7	327.5
60°	275.8	281.6	286.7	293.3
62.5°	246.7	249.6	251.1	257.6
65°	219.0	218.3	222.0	225.6
67.5°	189.2	188.5	192.1	193.6
70°	160.1	159.4	160.1	163.7
72.5°	132.4	132.4	133.2	134.6
75°	107.0	107.0	107.7	109.2
77.5°	80.8	82.2	81.5	84.4
80°	58.9	57.5	58.9	60.4
82.5°	38.6	40.0	40.0	38.6
85°	21.8	21.8	21.8	21.8
87.5°	9.5	9.5	10.2	10.9
90°	6.3	4.5	2.8	1.0
92.5°	12.8	14.8	16.7	18.7
95°	54.3	54.9	55.6	56.2
97.5°	109.5	108.2	106.8	105.5
100°	166.7	166.0	165.4	164.7
102.5°	227.5	226.6	225.8	224.9
105°	292.6	291.7	290.9	290.0
107.5°	357.0	357.0	357.0	357.0
110°	422.1	422.1	422.1	422.1

TEST NUMBER: P1034543

CATALOG NUMBER: S125DIW-B610D1050UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	485.2	484.6	483.9	483.3
115°	547.7	546.6	545.5	544.4
117.5°	608.5	608.5	608.5	608.5
120°	667.0	667.3	667.5	667.7
122.5°	723.3	722.2	721.1	720.0
125°	778.8	777.3	775.7	774.2
127.5°	829.8	828.7	827.6	826.5
130°	877.2	876.1	875.0	873.9
132.5°	925.1	923.8	922.5	921.2
135°	969.5	968.2	966.9	965.6
137.5°	1010.9	1009.6	1008.3	1007.0
140°	1048.7	1048.3	1047.8	1047.4
142.5°	1084.6	1084.3	1084.1	1083.9
145°	1120.7	1120.3	1119.8	1119.4
147.5°	1151.0	1151.0	1151.0	1151.0
150°	1179.3	1179.7	1180.2	1180.6
152.5°	1205.9	1207.0	1208.1	1209.2
155°	1228.9	1230.2	1231.6	1232.9
157.5°	1249.6	1250.3	1250.9	1251.6
160°	1267.4	1268.7	1270.0	1271.3
162.5°	1283.2	1284.5	1285.8	1287.1
165°	1297.0	1298.3	1299.6	1300.9
167.5°	1307.8	1309.1	1310.5	1311.8
170°	1316.0	1317.5	1319.1	1320.6
172.5°	1322.0	1323.5	1325.1	1326.6
175°	1326.6	1327.9	1329.2	1330.5
177.5°	1329.5	1330.8	1332.2	1333.5
180°	1330.5	1330.5	1330.5	1330.5

(END OF REPORT)