

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034771

Luminaire Tested: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034771
REPORT IS A COMBINATION OF REPORTS P1006280 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6827.0 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	99	95	92	98	94	91	88	85	82	80	77	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56
3	87	77	70	64	82	74	67	62	67	62	57	61	56	53	55	51	49
4	80	69	61	55	75	66	58	53	60	54	49	54	50	46	49	45	42
5	73	62	53	47	69	59	51	46	54	48	43	49	44	40	44	40	37
6	68	56	47	41	64	53	46	40	49	42	38	44	39	35	40	36	33
7	63	50	42	37	60	48	41	36	44	38	33	41	35	31	37	33	29
8	58	46	38	33	55	44	37	32	41	34	30	37	32	28	34	30	26
9	55	42	34	29	52	40	33	28	37	31	27	34	29	25	31	27	24
10	51	39	31	26	48	37	30	26	34	28	24	32	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12195	12195	12195	12195
5°	12184	13744	12184	10564
10°	12116	15445	12075	9132
15°	11985	16340	11902	7951
20°	11825	17639	11720	7187
25°	11618	19966	11488	6523
30°	11408	21222	11236	6048
35°	11135	17452	10979	5605
40°	10650	11852	10561	5207
45°	10015	8520	10001	4815
50°	9363	6552	9408	4453
55°	8629	5327	8612	4103
60°	7945	4367	7907	3644
65°	7150	3638	7195	2933
70°	6491	2920	6465	2442
75°	5484	2213	5484	2007
80°	4443	1349	4392	1349
85°	3127	709	3036	802

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17358 cd/sqm

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	2.7
10°-20°	535.1	7.8
20°-30°	848.4	12.4
30°-40°	1025.2	15.0
40°-50°	912.8	13.4
50°-60°	699.9	10.3
60°-70°	454.6	6.7
70°-80°	220.6	3.2
80°-90°	52.8	0.8
90°-100°	20.9	0.3
100°-110°	139.2	2.0
110°-120°	250.7	3.7
120°-130°	321.8	4.7
130°-140°	346.1	5.1
140°-150°	324.9	4.8
150°-160°	262.8	3.8
160°-170°	169.9	2.5
170°-180°	58.6	0.9
0°-30°	1566.0	22.9
0°-40°	2591.2	38.0
0°-60°	4203.9	61.6
0°-90°	4931.9	72.2
90°-120°	410.9	6.0
90°-150°	1403.7	20.6
90°-180°	1895.0	27.8
0°-180°	6827.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1903	1903	1903	1903	1903	
5°	1899	2181	1899	1677	1899	180
15°	1819	2620	1806	1275	1819	513
25°	1663	3138	1644	1025	1663	766
35°	1449	2603	1428	836	1449	902
45°	1133	1164	1131	658	1133	874
55°	800	639	798	492	800	717
65°	497	362	500	292	497	497
75°	242	169	242	153	242	260
85°	55	36	53	41	55	62
90°	0	11	0	11	0	5
95°	26	10	26	10	26	32
105°	134	136	134	136	134	142
115°	252	251	252	251	252	250
125°	359	359	359	359	359	321
135°	448	446	448	446	448	345
145°	519	518	519	518	519	325
155°	572	568	572	568	572	263
165°	603	600	603	600	603	170
175°	617	614	617	614	617	59
180°	617	617	617	617	617	

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4FO-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1904.8	1920.5	1925.2	1937.7	1951.7	1954.8	1962.7	1973.6	1979.8	1978.3	1978.3
5°	1898.6	1925.2	1943.9	1965.8	1992.3	2003.3	2012.7	2036.1	2054.9	2065.8	2084.5
7.5°	1887.7	1926.7	1958.0	1990.8	2031.4	2050.2	2070.5	2103.3	2137.7	2159.5	2179.9
10°	1870.5	1920.5	1964.2	2012.7	2067.4	2095.5	2120.5	2170.5	2212.7	2240.8	2287.7
12.5°	1845.5	1908.0	1968.9	2033.0	2101.7	2131.4	2165.8	2220.5	2279.9	2320.5	2359.6
15°	1818.9	1893.9	1959.5	2036.1	2118.9	2164.2	2208.0	2265.8	2318.9	2364.3	2409.6
17.5°	1787.6	1867.3	1948.6	2036.1	2129.9	2175.2	2212.7	2281.4	2337.7	2383.0	2423.6
20°	1750.1	1839.2	1931.4	2028.3	2123.6	2165.8	2201.7	2276.7	2326.7	2375.2	2433.0
22.5°	1709.5	1806.4	1904.8	2000.2	2093.9	2139.2	2181.4	2247.1	2301.7	2367.4	2442.4
25°	1662.6	1768.9	1868.9	1964.2	2053.3	2095.5	2133.0	2204.9	2281.4	2364.3	2448.6
27.5°	1615.8	1718.9	1815.8	1903.3	2000.2	2039.2	2076.7	2167.4	2258.0	2345.5	2461.1
30°	1564.2	1668.9	1753.3	1834.5	1928.3	1968.9	2015.8	2118.9	2222.1	2340.8	2481.4
32.5°	1506.4	1601.7	1679.8	1764.2	1848.6	1898.6	1958.0	2070.5	2189.2	2331.4	2511.1
35°	1448.6	1525.1	1597.0	1676.7	1778.3	1831.4	1889.2	2008.0	2156.4	2326.7	2536.1
37.5°	1375.1	1448.6	1504.8	1586.1	1690.8	1753.3	1811.1	1948.6	2117.4	2315.8	2534.6
40°	1300.1	1362.6	1415.7	1500.1	1614.2	1672.0	1734.5	1884.5	2076.7	2284.6	2497.1
42.5°	1218.8	1272.0	1329.8	1411.1	1522.0	1578.3	1650.1	1825.1	2020.5	2240.8	2400.2
45°	1132.9	1184.5	1232.9	1317.3	1428.2	1489.2	1567.3	1747.0	1951.7	2148.6	2243.9
47.5°	1048.5	1093.8	1145.4	1218.8	1331.4	1398.5	1478.2	1670.4	1859.5	2025.2	2033.0
50°	967.3	1003.2	1047.0	1122.0	1239.2	1303.2	1386.0	1565.8	1750.1	1864.2	1787.6
52.5°	882.9	915.7	961.0	1026.6	1136.0	1211.0	1282.9	1462.6	1617.3	1693.9	1553.2
55°	800.1	828.2	875.1	948.5	1043.8	1101.7	1175.1	1342.3	1478.2	1479.8	1326.7
57.5°	718.8	743.8	782.9	848.5	937.6	1004.8	1072.0	1217.3	1309.5	1282.9	1112.6
60°	646.9	662.6	698.5	762.6	845.4	893.8	965.7	1087.6	1148.5	1100.1	917.3
62.5°	571.9	587.5	615.7	667.2	745.4	796.9	842.3	942.3	984.5	911.0	761.0
65°	496.9	515.7	536.0	576.6	650.1	684.4	725.1	798.5	839.1	753.2	623.5
67.5°	431.3	440.7	461.0	503.2	554.7	586.0	614.1	664.1	671.9	603.2	496.9
70°	370.3	373.5	392.2	417.2	456.3	475.0	498.5	528.2	528.2	471.9	387.5
72.5°	301.6	306.3	320.3	346.9	370.3	379.7	387.5	406.3	403.2	351.6	293.8
75°	242.2	245.3	256.3	268.8	278.1	295.3	301.6	298.5	296.9	253.1	220.3
77.5°	187.5	189.1	196.9	207.8	209.4	215.6	211.0	211.0	196.9	171.9	154.7
80°	137.5	139.1	142.2	145.3	145.3	145.3	145.3	137.5	128.1	112.5	107.8
82.5°	92.2	92.2	93.8	96.9	95.3	92.2	89.1	81.3	75.0	70.3	67.2
85°	54.7	54.7	56.3	54.7	48.4	46.9	43.8	42.2	40.6	39.1	39.1
87.5°	26.6	25.0	21.9	18.8	18.8	18.8	18.8	18.8	18.8	17.2	17.2
90°	0.5	1.3	2.1	2.9	3.7	4.1	4.5	5.2	5.9	6.6	7.3
92.5°	8.7	7.8	6.9	6.0	5.1	4.6	4.9	5.5	6.1	6.7	7.3
95°	26.1	25.8	25.5	25.2	24.9	24.7	22.8	18.9	15.0	11.2	7.3
97.5°	48.9	49.5	50.1	50.8	51.4	51.7	46.9	37.2	27.5	17.9	8.2
100°	76.4	76.7	77.0	77.3	77.6	77.7	77.9	78.3	78.8	79.2	79.6
102.5°	104.3	104.7	105.1	105.5	105.9	106.1	106.2	106.4	106.6	106.8	107.0
105°	134.5	134.9	135.3	135.7	136.1	136.3	136.3	136.3	136.3	136.3	136.3
107.5°	165.6	165.6	165.6	165.6	165.6	165.6	165.7	165.9	166.1	166.3	166.5
110°	195.7	195.7	195.7	195.7	195.7	195.7	195.8	196.0	196.2	196.4	196.6

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	224.1	224.4	224.7	225.0	225.3	225.5	225.5	225.6	225.7	225.8	225.9
115°	252.4	252.9	253.4	253.9	254.4	254.7	254.8	254.9	255.0	255.1	255.2
117.5°	282.2	282.2	282.2	282.2	282.2	282.2	282.4	282.8	283.2	283.6	284.0
120°	309.6	309.5	309.4	309.3	309.2	309.2	309.3	309.6	309.9	310.2	310.5
122.5°	333.8	334.3	334.8	335.3	335.8	336.1	336.2	336.3	336.4	336.5	336.6
125°	359.0	359.7	360.4	361.1	361.8	362.2	362.2	362.2	362.2	362.2	362.2
127.5°	383.2	383.7	384.2	384.7	385.2	385.5	385.5	385.4	385.3	385.2	385.1
130°	405.2	405.7	406.2	406.7	407.2	407.5	407.5	407.6	407.7	407.8	407.9
132.5°	427.1	427.7	428.3	429.0	429.6	429.9	429.7	429.4	429.1	428.8	428.5
135°	447.7	448.3	448.9	449.6	450.2	450.5	450.4	450.2	450.0	449.8	449.6
137.5°	466.9	467.5	468.1	468.8	469.4	469.7	469.6	469.4	469.2	469.0	468.8
140°	485.7	485.9	486.1	486.3	486.5	486.6	486.5	486.4	486.3	486.2	486.1
142.5°	502.6	502.7	502.8	502.9	503.0	503.1	503.2	503.4	503.6	503.8	504.0
145°	519.1	519.3	519.5	519.7	519.9	520.0	520.0	520.0	520.0	520.0	520.0
147.5°	533.7	533.7	533.7	533.7	533.7	533.7	533.8	533.9	534.0	534.1	534.2
150°	547.4	547.2	547.0	546.8	546.6	546.5	546.6	546.8	547.0	547.2	547.4
152.5°	560.7	560.2	559.7	559.2	558.7	558.4	558.5	558.7	558.9	559.1	559.3
155°	571.7	571.1	570.5	569.8	569.2	568.9	569.0	569.2	569.4	569.6	569.8
157.5°	580.3	580.0	579.7	579.4	579.1	579.0	579.0	579.0	579.0	579.0	579.0
160°	589.5	588.9	588.3	587.6	587.0	586.7	586.8	586.9	587.0	587.1	587.2
162.5°	596.8	596.2	595.6	595.0	594.4	594.1	594.1	594.2	594.3	594.4	594.5
165°	603.2	602.6	602.0	601.4	600.8	600.5	600.5	600.6	600.7	600.8	600.9
167.5°	608.2	607.6	607.0	606.4	605.8	605.5	605.6	605.7	605.8	605.9	606.0
170°	612.4	611.7	611.0	610.3	609.6	609.2	609.2	609.3	609.4	609.5	609.6
172.5°	615.1	614.4	613.7	613.0	612.3	611.9	612.0	612.2	612.4	612.6	612.8
175°	616.9	616.3	615.7	615.1	614.5	614.2	614.2	614.3	614.4	614.5	614.6
177.5°	618.3	617.7	617.1	616.5	615.9	615.6	615.6	615.7	615.8	615.9	616.0
180°	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4FO-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1986.1	1997.0	2006.4	2001.7	2020.5	2018.9	2022.0	2028.3	2029.9	2026.7	2020.5
5°	2093.9	2109.5	2136.1	2150.2	2147.0	2159.5	2165.8	2175.2	2184.5	2181.4	2181.4
7.5°	2214.2	2236.1	2262.7	2298.6	2303.3	2314.2	2333.0	2333.0	2343.9	2339.2	2337.7
10°	2318.9	2345.5	2387.7	2415.8	2428.3	2434.6	2453.3	2459.6	2472.1	2473.6	2473.6
12.5°	2404.9	2451.8	2479.9	2508.0	2514.3	2523.6	2537.7	2547.1	2551.8	2551.8	2547.1
15°	2450.2	2487.7	2520.5	2550.2	2567.4	2575.2	2589.3	2600.2	2606.5	2620.5	2623.6
17.5°	2468.9	2514.3	2567.4	2609.6	2639.3	2647.1	2675.2	2684.6	2697.1	2703.3	2711.2
20°	2495.5	2561.1	2625.2	2676.8	2704.9	2725.2	2754.9	2798.7	2811.2	2811.2	2806.5
22.5°	2519.0	2603.3	2690.8	2773.7	2797.1	2837.7	2892.4	2939.3	2958.0	2965.9	2959.6
25°	2547.1	2662.7	2776.8	2879.9	2944.0	2973.7	3047.1	3103.4	3125.3	3137.8	3140.9
27.5°	2595.5	2740.8	2886.2	3017.4	3083.1	3117.4	3194.0	3242.4	3269.0	3280.0	3272.1
30°	2650.2	2828.4	2997.1	3114.3	3158.1	3200.3	3250.3	3269.0	3262.8	3262.8	3286.2
32.5°	2706.5	2890.9	3040.9	3117.4	3133.1	3126.8	3106.5	3050.2	3017.4	3017.4	3037.7
35°	2737.7	2897.1	2973.7	2948.7	2887.7	2851.8	2740.8	2678.3	2608.0	2603.3	2626.8
37.5°	2720.5	2789.3	2758.0	2594.0	2511.1	2442.4	2268.9	2200.2	2148.6	2076.7	2187.7
40°	2600.2	2576.8	2414.3	2178.3	2086.1	1989.2	1851.7	1783.0	1711.1	1700.1	1726.7
42.5°	2397.1	2258.0	2020.5	1792.3	1698.6	1629.8	1525.1	1457.9	1412.6	1393.9	1425.1
45°	2143.9	1925.2	1687.6	1506.4	1403.2	1367.3	1272.0	1212.6	1178.2	1164.2	1186.0
47.5°	1834.5	1614.2	1389.2	1236.0	1175.1	1139.2	1075.1	1023.5	993.8	984.5	993.8
50°	1557.9	1331.4	1142.3	1043.8	989.1	959.5	906.3	873.5	850.1	843.8	859.4
52.5°	1318.9	1112.6	968.8	881.3	845.4	820.4	782.9	754.7	740.7	734.4	745.4
55°	1104.8	937.6	821.9	746.9	720.4	704.7	671.9	656.3	640.7	639.1	650.1
57.5°	915.7	800.1	693.8	640.7	632.9	609.4	581.3	567.2	559.4	557.9	562.5
60°	762.6	659.4	595.4	548.5	537.5	518.8	503.2	493.8	484.4	481.3	484.4
62.5°	634.4	553.2	501.6	470.4	454.7	450.0	432.8	421.9	420.3	420.3	423.5
65°	523.5	454.7	421.9	396.9	386.0	381.3	368.8	361.0	362.5	362.5	364.1
67.5°	426.6	376.6	346.9	334.4	325.0	323.5	311.0	307.8	304.7	304.7	307.8
70°	339.1	307.8	286.0	279.7	278.1	267.2	262.5	261.0	256.3	257.8	257.8
72.5°	265.6	245.3	232.8	223.5	225.0	218.8	212.5	212.5	209.4	214.1	214.1
75°	196.9	187.5	178.1	175.0	178.1	175.0	170.3	168.8	170.3	168.8	168.8
77.5°	145.3	140.6	137.5	135.9	135.9	129.7	126.6	129.7	123.4	126.6	126.6
80°	101.6	95.3	93.8	90.6	92.2	87.5	89.1	85.9	85.9	85.9	85.9
82.5°	64.1	62.5	62.5	62.5	60.9	60.9	60.9	60.9	60.9	60.9	59.4
85°	39.1	37.5	37.5	37.5	35.9	35.9	35.9	35.9	35.9	35.9	35.9
87.5°	15.6	17.2	17.2	18.8	17.2	15.6	15.6	15.6	17.2	17.2	15.6
90°	7.8	8.3	8.8	9.3	9.6	9.8	10.1	10.4	10.7	11.0	10.7
92.5°	7.8	8.3	8.8	9.3	9.6	9.7	9.8	9.9	10.0	10.1	10.0
95°	7.8	8.3	8.8	9.3	9.6	9.6	9.6	9.6	9.6	9.6	9.6
97.5°	8.4	8.6	8.8	9.0	9.1	9.2	9.3	9.4	9.5	9.6	9.5
100°	64.4	49.3	34.1	19.0	11.4	11.2	10.8	10.4	10.0	9.6	10.0
102.5°	107.2	107.4	107.6	107.8	107.9	103.6	95.1	86.6	78.0	69.5	78.0
105°	136.3	136.3	136.3	136.3	136.3	136.2	136.1	136.0	135.9	135.8	135.9
107.5°	166.6	166.7	166.8	166.9	166.9	166.7	166.3	165.9	165.5	165.1	165.5
110°	196.3	196.0	195.7	195.4	195.3	195.3	195.4	195.5	195.6	195.7	195.6

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	225.5	225.1	224.7	224.3	224.1	224.0	223.8	223.6	223.4	223.2	223.4
115°	254.8	254.4	254.0	253.6	253.4	253.1	252.5	251.8	251.2	250.6	251.2
117.5°	283.4	282.8	282.2	281.6	281.3	281.2	281.0	280.7	280.5	280.3	280.5
120°	310.3	310.1	309.9	309.7	309.6	309.3	308.8	308.3	307.8	307.3	307.8
122.5°	336.4	336.2	336.0	335.8	335.7	335.4	334.8	334.1	333.5	332.9	333.5
125°	361.8	361.4	361.0	360.6	360.4	360.2	359.9	359.6	359.3	359.0	359.3
127.5°	384.9	384.7	384.5	384.3	384.2	383.8	383.0	382.1	381.3	380.5	381.3
130°	407.6	407.3	407.0	406.7	406.6	406.3	405.8	405.3	404.8	404.3	404.8
132.5°	428.5	428.5	428.5	428.5	428.5	428.2	427.7	427.2	426.7	426.2	426.7
135°	449.4	449.2	448.9	448.7	448.6	448.3	447.7	447.1	446.5	445.9	446.5
137.5°	468.8	468.8	468.8	468.8	468.8	468.5	468.0	467.5	467.0	466.5	467.0
140°	486.3	486.5	486.8	487.0	487.1	486.8	486.2	485.5	484.9	484.3	484.9
142.5°	504.0	504.0	504.0	504.0	504.0	503.7	503.1	502.4	501.8	501.2	501.8
145°	520.1	520.2	520.3	520.4	520.4	520.1	519.5	518.9	518.3	517.7	518.3
147.5°	534.3	534.4	534.5	534.6	534.6	534.2	533.5	532.8	532.1	531.4	532.1
150°	547.6	547.8	548.0	548.2	548.3	547.9	547.1	546.3	545.5	544.7	545.5
152.5°	559.5	559.7	559.9	560.1	560.2	559.8	559.1	558.4	557.7	557.0	557.7
155°	570.1	570.4	570.7	571.0	571.2	570.8	570.0	569.1	568.3	567.5	568.3
157.5°	579.3	579.6	579.9	580.2	580.3	579.9	579.1	578.3	577.5	576.7	577.5
160°	587.6	588.0	588.4	588.8	589.0	588.6	587.8	587.0	586.2	585.4	586.2
162.5°	595.1	595.7	596.4	597.0	597.3	596.8	595.9	595.0	594.1	593.2	594.1
165°	601.5	602.1	602.8	603.4	603.7	603.3	602.5	601.6	600.8	600.0	600.8
167.5°	606.7	607.4	608.1	608.8	609.2	608.7	607.8	606.9	605.9	605.0	605.9
170°	610.4	611.2	612.1	612.9	613.3	612.8	611.9	611.0	610.1	609.2	610.1
172.5°	613.5	614.2	614.9	615.6	616.0	615.5	614.6	613.7	612.8	611.9	612.8
175°	615.4	616.2	617.1	617.9	618.3	617.8	616.9	616.0	615.1	614.2	615.1
177.5°	616.7	617.4	618.1	618.8	619.2	618.8	618.0	617.2	616.4	615.6	616.4
180°	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4FO-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	2028.3	2017.3	2022.0	2017.3	2012.7	2008.0	1997.0	1981.4	1968.9	1959.5	1958.0
5°	2184.5	2170.5	2161.1	2156.4	2147.0	2134.5	2114.2	2090.8	2062.7	2051.7	2029.9
7.5°	2328.3	2323.6	2301.7	2298.6	2292.4	2268.9	2234.6	2203.3	2167.4	2137.7	2109.5
10°	2464.3	2453.3	2437.7	2415.8	2412.7	2383.0	2350.2	2306.4	2259.6	2231.4	2181.4
12.5°	2548.6	2536.1	2519.0	2504.9	2497.1	2478.3	2433.0	2389.3	2347.1	2295.5	2251.7
15°	2609.6	2594.0	2562.7	2551.8	2542.4	2517.4	2484.6	2439.3	2383.0	2347.1	2284.6
17.5°	2692.4	2673.7	2642.4	2622.1	2604.9	2565.8	2519.0	2458.0	2404.9	2364.3	2308.0
20°	2787.7	2759.6	2719.0	2692.4	2667.4	2622.1	2556.5	2484.6	2408.0	2358.0	2300.2
22.5°	2945.5	2892.4	2828.4	2790.8	2756.5	2678.3	2600.2	2511.1	2425.2	2350.2	2279.9
25°	3098.7	3045.6	2965.9	2914.3	2861.2	2770.5	2667.4	2544.0	2434.6	2347.1	2254.9
27.5°	3240.9	3186.2	3112.7	3050.2	2998.7	2862.7	2726.8	2587.7	2448.6	2328.3	2234.6
30°	3273.7	3250.3	3194.0	3139.3	3092.4	2967.4	2809.6	2633.0	2465.8	2311.1	2206.4
32.5°	3075.2	3133.1	3147.1	3139.3	3109.6	3020.6	2875.2	2689.3	2490.8	2303.3	2159.5
35°	2662.7	2767.4	2875.2	2933.0	2961.2	2973.7	2887.7	2717.4	2508.0	2290.8	2128.3
37.5°	2208.0	2309.6	2479.9	2565.8	2661.2	2786.2	2820.5	2711.2	2500.2	2281.4	2078.3
40°	1814.2	1943.9	2084.5	2162.7	2245.5	2470.5	2640.8	2628.3	2475.2	2247.1	2039.2
42.5°	1476.7	1557.9	1681.4	1767.3	1868.9	2120.5	2348.6	2461.1	2400.2	2204.9	1989.2
45°	1231.3	1293.9	1381.4	1468.9	1531.4	1759.5	2029.9	2214.2	2272.1	2129.9	1912.7
47.5°	1037.6	1084.5	1161.0	1215.7	1282.9	1462.6	1697.0	1956.4	2078.3	2023.6	1831.4
50°	889.1	926.6	987.6	1022.0	1081.3	1236.0	1414.2	1686.1	1870.5	1876.7	1723.6
52.5°	759.4	796.9	848.5	878.2	914.1	1018.8	1198.5	1428.2	1640.8	1718.9	1600.1
55°	661.0	682.9	725.1	748.5	781.3	882.9	997.0	1192.3	1414.2	1542.3	1467.3
57.5°	570.4	593.8	620.4	639.1	662.6	743.8	846.9	993.8	1214.2	1353.2	1328.2
60°	496.9	511.0	536.0	550.0	571.9	625.1	696.9	843.8	1018.8	1150.1	1164.2
62.5°	428.2	440.7	457.8	470.4	484.4	526.6	579.7	684.4	837.6	979.8	998.5
65°	368.8	379.7	389.1	400.0	411.0	437.5	482.9	564.1	682.9	815.7	856.3
67.5°	315.7	318.8	332.8	334.4	340.7	361.0	393.8	459.4	545.4	651.6	704.7
70°	264.1	270.3	273.5	278.1	284.4	298.5	325.0	359.4	423.5	509.4	559.4
72.5°	214.1	215.6	220.3	223.5	229.7	240.6	253.1	279.7	320.3	382.8	428.2
75°	170.3	171.9	175.0	176.6	181.3	184.4	190.6	209.4	237.5	275.0	307.8
77.5°	128.1	131.3	134.4	134.4	135.9	139.1	142.2	148.4	162.5	187.5	215.6
80°	87.5	89.1	89.1	90.6	89.1	93.8	98.4	106.3	112.5	120.3	134.4
82.5°	60.9	60.9	60.9	62.5	62.5	64.1	64.1	65.6	67.2	71.9	78.1
85°	37.5	37.5	39.1	35.9	37.5	39.1	39.1	37.5	39.1	40.6	42.2
87.5°	15.6	15.6	17.2	17.2	17.2	17.2	15.6	17.2	15.6	17.2	17.2
90°	10.4	10.1	9.8	9.6	9.3	8.8	8.3	7.8	7.3	6.6	5.9
92.5°	9.9	9.8	9.7	9.6	9.3	8.8	8.3	7.8	7.3	6.7	6.1
95°	9.6	9.6	9.6	9.6	9.3	8.8	8.3	7.8	7.3	11.2	15.0
97.5°	9.4	9.3	9.2	9.1	9.0	8.8	8.6	8.4	8.2	17.9	27.5
100°	10.4	10.8	11.2	11.4	19.0	34.1	49.3	64.4	79.6	79.2	78.8
102.5°	86.6	95.1	103.6	107.9	107.8	107.6	107.4	107.2	107.0	106.8	106.6
105°	136.0	136.1	136.2	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.3
107.5°	165.9	166.3	166.7	166.9	166.9	166.8	166.7	166.6	166.5	166.3	166.1
110°	195.5	195.4	195.3	195.3	195.4	195.7	196.0	196.3	196.6	196.4	196.2



TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	223.6	223.8	224.0	224.1	224.3	224.7	225.1	225.5	225.9	225.8	225.7
115°	251.8	252.5	253.1	253.4	253.6	254.0	254.4	254.8	255.2	255.1	255.0
117.5°	280.7	281.0	281.2	281.3	281.6	282.2	282.8	283.4	284.0	283.6	283.2
120°	308.3	308.8	309.3	309.6	309.7	309.9	310.1	310.3	310.5	310.2	309.9
122.5°	334.1	334.8	335.4	335.7	335.8	336.0	336.2	336.4	336.6	336.5	336.4
125°	359.6	359.9	360.2	360.4	360.6	361.0	361.4	361.8	362.2	362.2	362.2
127.5°	382.1	383.0	383.8	384.2	384.3	384.5	384.7	384.9	385.1	385.2	385.3
130°	405.3	405.8	406.3	406.6	406.7	407.0	407.3	407.6	407.9	407.8	407.7
132.5°	427.2	427.7	428.2	428.5	428.5	428.5	428.5	428.5	428.5	428.8	429.1
135°	447.1	447.7	448.3	448.6	448.7	448.9	449.2	449.4	449.6	449.8	450.0
137.5°	467.5	468.0	468.5	468.8	468.8	468.8	468.8	468.8	468.8	469.0	469.2
140°	485.5	486.2	486.8	487.1	487.0	486.8	486.5	486.3	486.1	486.2	486.3
142.5°	502.4	503.1	503.7	504.0	504.0	504.0	504.0	504.0	504.0	503.8	503.6
145°	518.9	519.5	520.1	520.4	520.4	520.3	520.2	520.1	520.0	520.0	520.0
147.5°	532.8	533.5	534.2	534.6	534.6	534.5	534.4	534.3	534.2	534.1	534.0
150°	546.3	547.1	547.9	548.3	548.2	548.0	547.8	547.6	547.4	547.2	547.0
152.5°	558.4	559.1	559.8	560.2	560.1	559.9	559.7	559.5	559.3	559.1	558.9
155°	569.1	570.0	570.8	571.2	571.0	570.7	570.4	570.1	569.8	569.6	569.4
157.5°	578.3	579.1	579.9	580.3	580.2	579.9	579.6	579.3	579.0	579.0	579.0
160°	587.0	587.8	588.6	589.0	588.8	588.4	588.0	587.6	587.2	587.1	587.0
162.5°	595.0	595.9	596.8	597.3	597.0	596.4	595.7	595.1	594.5	594.4	594.3
165°	601.6	602.5	603.3	603.7	603.4	602.8	602.1	601.5	600.9	600.8	600.7
167.5°	606.9	607.8	608.7	609.2	608.8	608.1	607.4	606.7	606.0	605.9	605.8
170°	611.0	611.9	612.8	613.3	612.9	612.1	611.2	610.4	609.6	609.5	609.4
172.5°	613.7	614.6	615.5	616.0	615.6	614.9	614.2	613.5	612.8	612.6	612.4
175°	616.0	616.9	617.8	618.3	617.9	617.1	616.2	615.4	614.6	614.5	614.4
177.5°	617.2	618.0	618.8	619.2	618.8	618.1	617.4	616.7	616.0	615.9	615.8
180°	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1953.3	1943.9	1937.7	1936.1	1926.7	1918.9	1909.5	1908.0	1903.3	1890.8	1883.0
5°	2014.2	1992.3	1987.7	1973.6	1950.2	1933.0	1911.1	1898.6	1884.5	1861.1	1842.3
7.5°	2076.7	2047.0	2025.2	2004.8	1972.0	1940.8	1909.5	1884.5	1859.5	1825.1	1797.0
10°	2137.7	2092.4	2065.8	2036.1	1990.8	1943.9	1900.2	1864.2	1823.6	1783.0	1742.3
12.5°	2193.9	2136.1	2097.0	2054.9	1998.6	1940.8	1884.5	1834.5	1792.3	1737.6	1692.3
15°	2228.3	2164.2	2125.2	2084.5	2000.2	1936.1	1870.5	1806.4	1750.1	1692.3	1650.1
17.5°	2248.6	2176.7	2133.0	2095.5	2009.5	1922.0	1837.6	1768.9	1707.9	1639.2	1582.9
20°	2239.2	2168.9	2128.3	2092.4	1992.3	1904.8	1814.2	1734.5	1657.9	1587.6	1528.2
22.5°	2218.9	2145.5	2100.2	2067.4	1978.3	1875.2	1775.1	1689.2	1609.5	1539.2	1472.0
25°	2175.2	2103.3	2064.2	2023.6	1936.1	1837.6	1736.1	1643.9	1559.5	1484.5	1409.5
27.5°	2136.1	2048.6	2008.0	1972.0	1879.8	1792.3	1692.3	1590.8	1504.8	1426.7	1351.7
30°	2090.8	1992.3	1948.6	1900.2	1817.3	1734.5	1634.5	1540.7	1451.7	1368.9	1297.0
32.5°	2042.4	1928.3	1878.3	1823.6	1739.2	1661.1	1576.7	1484.5	1395.4	1314.2	1239.2
35°	1979.8	1858.0	1800.1	1748.6	1661.1	1582.9	1504.8	1428.2	1339.2	1253.2	1181.3
37.5°	1920.5	1786.1	1725.1	1665.8	1573.6	1498.6	1434.5	1362.6	1276.7	1193.8	1125.1
40°	1853.3	1698.6	1636.1	1581.4	1486.1	1403.2	1345.4	1289.2	1214.2	1134.5	1059.5
42.5°	1792.3	1617.3	1551.7	1495.4	1395.4	1317.3	1262.6	1215.7	1150.1	1076.6	1000.1
45°	1707.9	1529.8	1462.6	1403.2	1301.7	1228.2	1172.0	1131.3	1079.8	1011.0	942.3
47.5°	1629.8	1445.4	1372.0	1300.1	1207.9	1132.9	1081.3	1050.1	1015.7	954.8	884.4
50°	1534.5	1348.5	1273.5	1214.2	1109.5	1045.4	993.8	972.0	940.7	882.9	826.6
52.5°	1431.4	1254.8	1184.5	1112.6	1015.7	953.2	907.9	882.9	857.9	815.7	762.6
55°	1311.0	1150.1	1084.5	1020.4	923.5	865.7	825.1	798.5	784.4	745.4	706.3
57.5°	1195.4	1043.8	982.9	923.5	839.1	773.5	746.9	723.5	703.2	675.1	642.2
60°	1078.2	940.7	875.1	821.9	748.5	689.1	667.2	643.8	628.2	606.3	582.9
62.5°	943.8	826.6	776.6	726.6	664.1	617.2	592.2	573.5	553.2	539.1	518.8
65°	801.6	718.8	670.4	632.9	573.5	531.3	512.5	500.0	482.9	468.8	453.2
67.5°	668.8	603.2	582.9	542.2	496.9	459.4	445.3	429.7	415.7	407.8	393.8
70°	540.7	493.8	473.5	462.5	412.5	387.5	375.0	368.8	351.6	343.8	334.4
72.5°	418.8	401.6	387.5	373.5	340.7	325.0	311.0	304.7	292.2	286.0	282.8
75°	309.4	298.5	290.6	289.1	275.0	259.4	245.3	242.2	232.8	226.6	223.5
77.5°	217.2	214.1	212.5	214.1	204.7	195.3	192.2	189.1	178.1	176.6	176.6
80°	142.2	150.0	150.0	148.4	145.3	143.8	139.1	135.9	129.7	128.1	129.7
82.5°	87.5	92.2	93.8	96.9	95.3	93.8	90.6	89.1	90.6	87.5	89.1
85°	43.8	46.9	53.1	53.1	54.7	54.7	54.7	53.1	50.0	51.6	50.0
87.5°	17.2	18.8	18.8	18.8	17.2	21.9	23.4	23.4	23.4	20.3	20.3
90°	5.2	4.5	4.1	3.7	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	5.5	4.9	4.6	5.1	6.0	6.9	7.8	8.7	7.8	6.9	6.0
95°	18.9	22.8	24.7	24.9	25.2	25.5	25.8	26.1	25.8	25.5	25.2
97.5°	37.2	46.9	51.7	51.4	50.8	50.1	49.5	48.9	49.5	50.1	50.8
100°	78.3	77.9	77.7	77.6	77.3	77.0	76.7	76.4	76.7	77.0	77.3
102.5°	106.4	106.2	106.1	105.9	105.5	105.1	104.7	104.3	104.7	105.1	105.5
105°	136.3	136.3	136.3	136.1	135.7	135.3	134.9	134.5	134.9	135.3	135.7
107.5°	165.9	165.7	165.6	165.6	165.6	165.6	165.6	165.6	165.6	165.6	165.6
110°	196.0	195.8	195.7	195.7	195.7	195.7	195.7	195.7	195.7	195.7	195.7

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	225.6	225.5	225.5	225.3	225.0	224.7	224.4	224.1	224.4	224.7	225.0
115°	254.9	254.8	254.7	254.4	253.9	253.4	252.9	252.4	252.9	253.4	253.9
117.5°	282.8	282.4	282.2	282.2	282.2	282.2	282.2	282.2	282.2	282.2	282.2
120°	309.6	309.3	309.2	309.2	309.3	309.4	309.5	309.6	309.5	309.4	309.3
122.5°	336.3	336.2	336.1	335.8	335.3	334.8	334.3	333.8	334.3	334.8	335.3
125°	362.2	362.2	362.2	361.8	361.1	360.4	359.7	359.0	359.7	360.4	361.1
127.5°	385.4	385.5	385.5	385.2	384.7	384.2	383.7	383.2	383.7	384.2	384.7
130°	407.6	407.5	407.5	407.2	406.7	406.2	405.7	405.2	405.7	406.2	406.7
132.5°	429.4	429.7	429.9	429.6	429.0	428.3	427.7	427.1	427.7	428.3	429.0
135°	450.2	450.4	450.5	450.2	449.6	448.9	448.3	447.7	448.3	448.9	449.6
137.5°	469.4	469.6	469.7	469.4	468.8	468.1	467.5	466.9	467.5	468.1	468.8
140°	486.4	486.5	486.6	486.5	486.3	486.1	485.9	485.7	485.9	486.1	486.3
142.5°	503.4	503.2	503.1	503.0	502.9	502.8	502.7	502.6	502.7	502.8	502.9
145°	520.0	520.0	520.0	519.9	519.7	519.5	519.3	519.1	519.3	519.5	519.7
147.5°	533.9	533.8	533.7	533.7	533.7	533.7	533.7	533.7	533.7	533.7	533.7
150°	546.8	546.6	546.5	546.6	546.8	547.0	547.2	547.4	547.2	547.0	546.8
152.5°	558.7	558.5	558.4	558.7	559.2	559.7	560.2	560.7	560.2	559.7	559.2
155°	569.2	569.0	568.9	569.2	569.8	570.5	571.1	571.7	571.1	570.5	569.8
157.5°	579.0	579.0	579.0	579.1	579.4	579.7	580.0	580.3	580.0	579.7	579.4
160°	586.9	586.8	586.7	587.0	587.6	588.3	588.9	589.5	588.9	588.3	587.6
162.5°	594.2	594.1	594.1	594.4	595.0	595.6	596.2	596.8	596.2	595.6	595.0
165°	600.6	600.5	600.5	600.8	601.4	602.0	602.6	603.2	602.6	602.0	601.4
167.5°	605.7	605.6	605.5	605.8	606.4	607.0	607.6	608.2	607.6	607.0	606.4
170°	609.3	609.2	609.2	609.6	610.3	611.0	611.7	612.4	611.7	611.0	610.3
172.5°	612.2	612.0	611.9	612.3	613.0	613.7	614.4	615.1	614.4	613.7	613.0
175°	614.3	614.2	614.2	614.5	615.1	615.7	616.3	616.9	616.3	615.7	615.1
177.5°	615.7	615.6	615.6	615.9	616.5	617.1	617.7	618.3	617.7	617.1	616.5
180°	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1878.3	1872.0	1867.3	1862.6	1842.3	1820.5	1817.3	1812.6	1803.3	1814.2	1809.5
5°	1829.8	1815.8	1808.0	1787.6	1762.6	1743.9	1728.3	1709.5	1701.7	1695.4	1693.9
7.5°	1770.5	1758.0	1743.9	1723.6	1692.3	1661.1	1637.6	1618.9	1603.3	1595.4	1595.4
10°	1712.6	1697.0	1678.3	1643.9	1614.2	1575.1	1550.1	1531.4	1509.5	1497.0	1486.1
12.5°	1653.3	1636.1	1618.9	1575.1	1540.7	1500.1	1464.2	1440.7	1429.8	1415.7	1397.0
15°	1593.9	1567.3	1550.1	1506.4	1462.6	1422.0	1398.5	1373.5	1348.5	1334.5	1328.2
17.5°	1531.4	1512.6	1484.5	1437.6	1389.2	1353.2	1318.9	1295.4	1265.7	1251.7	1237.6
20°	1475.1	1447.0	1418.9	1372.0	1325.1	1276.7	1242.3	1214.2	1195.4	1184.5	1172.0
22.5°	1407.9	1381.4	1357.9	1307.9	1256.4	1211.0	1173.5	1156.3	1137.6	1120.4	1107.9
25°	1350.1	1323.5	1300.1	1245.4	1189.2	1147.0	1118.8	1097.0	1076.6	1068.8	1056.3
27.5°	1289.2	1264.2	1232.9	1178.2	1128.2	1092.3	1062.6	1042.3	1026.6	1011.0	1001.6
30°	1231.3	1203.2	1175.1	1115.7	1075.1	1039.1	1011.0	986.0	973.5	965.7	950.1
32.5°	1175.1	1139.2	1115.7	1061.0	1022.0	987.6	964.1	942.3	926.6	912.6	900.1
35°	1114.2	1075.1	1051.6	1006.3	965.7	931.3	911.0	895.4	876.6	864.1	857.9
37.5°	1056.3	1023.5	1000.1	953.2	912.6	884.4	862.6	842.3	834.4	817.3	814.1
40°	993.8	965.7	943.8	898.5	861.0	839.1	815.7	796.9	782.9	775.1	764.1
42.5°	937.6	914.1	890.7	848.5	812.6	786.0	768.8	751.6	739.1	726.6	718.8
45°	886.0	861.0	839.1	798.5	762.6	739.1	721.9	701.6	698.5	681.3	673.5
47.5°	831.3	809.4	790.7	748.5	715.7	692.2	671.9	657.9	643.8	637.6	626.6
50°	778.2	756.3	734.4	696.9	667.2	643.8	623.5	607.9	600.0	590.7	581.3
52.5°	720.4	703.2	686.0	646.9	617.2	596.9	579.7	559.4	551.6	543.8	537.5
55°	671.9	646.9	628.2	595.4	568.8	546.9	528.2	512.5	504.7	498.5	490.7
57.5°	606.3	590.7	575.0	545.4	520.4	498.5	479.7	467.2	457.8	453.2	454.7
60°	550.0	532.9	523.5	492.2	467.2	450.0	432.8	420.3	411.0	406.3	404.7
62.5°	490.7	478.2	461.0	439.1	414.1	398.5	386.0	376.6	361.0	359.4	354.7
65°	432.8	423.5	407.8	387.5	367.2	353.2	339.1	326.6	320.3	312.5	307.8
67.5°	376.6	367.2	353.2	336.0	321.9	307.8	295.3	282.8	271.9	265.6	262.5
70°	321.9	314.1	304.7	284.4	267.2	256.3	246.9	239.1	228.1	225.0	223.5
72.5°	268.8	261.0	256.3	239.1	223.5	214.1	204.7	196.9	192.2	190.6	186.0
75°	220.3	212.5	206.3	190.6	181.3	175.0	165.6	162.5	157.8	156.3	154.7
77.5°	171.9	164.1	162.5	151.6	140.6	137.5	134.4	128.1	128.1	128.1	125.0
80°	123.4	121.9	120.3	109.4	104.7	101.6	100.0	95.3	92.2	89.1	87.5
82.5°	82.8	81.3	79.7	75.0	70.3	68.8	67.2	64.1	64.1	65.6	62.5
85°	50.0	46.9	45.3	43.8	40.6	40.6	42.2	40.6	40.6	40.6	39.1
87.5°	18.8	18.8	18.8	18.8	20.3	17.2	18.8	18.8	17.2	17.2	15.6
90°	3.7	4.1	4.5	5.2	5.9	6.6	7.3	7.8	8.3	8.8	9.3
92.5°	5.1	4.6	4.9	5.5	6.1	6.7	7.3	7.8	8.3	8.8	9.3
95°	24.9	24.7	22.8	18.9	15.0	11.2	7.3	7.8	8.3	8.8	9.3
97.5°	51.4	51.7	46.9	37.2	27.5	17.9	8.2	8.4	8.6	8.8	9.0
100°	77.6	77.7	77.9	78.3	78.8	79.2	79.6	64.4	49.3	34.1	19.0
102.5°	105.9	106.1	106.2	106.4	106.6	106.8	107.0	107.2	107.4	107.6	107.8
105°	136.1	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.3
107.5°	165.6	165.6	165.7	165.9	166.1	166.3	166.5	166.6	166.7	166.8	166.9
110°	195.7	195.7	195.8	196.0	196.2	196.4	196.6	196.3	196.0	195.7	195.4

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	225.3	225.5	225.5	225.6	225.7	225.8	225.9	225.5	225.1	224.7	224.3
115°	254.4	254.7	254.8	254.9	255.0	255.1	255.2	254.8	254.4	254.0	253.6
117.5°	282.2	282.2	282.4	282.8	283.2	283.6	284.0	283.4	282.8	282.2	281.6
120°	309.2	309.2	309.3	309.6	309.9	310.2	310.5	310.3	310.1	309.9	309.7
122.5°	335.8	336.1	336.2	336.3	336.4	336.5	336.6	336.4	336.2	336.0	335.8
125°	361.8	362.2	362.2	362.2	362.2	362.2	362.2	361.8	361.4	361.0	360.6
127.5°	385.2	385.5	385.5	385.4	385.3	385.2	385.1	384.9	384.7	384.5	384.3
130°	407.2	407.5	407.5	407.6	407.7	407.8	407.9	407.6	407.3	407.0	406.7
132.5°	429.6	429.9	429.7	429.4	429.1	428.8	428.5	428.5	428.5	428.5	428.5
135°	450.2	450.5	450.4	450.2	450.0	449.8	449.6	449.4	449.2	448.9	448.7
137.5°	469.4	469.7	469.6	469.4	469.2	469.0	468.8	468.8	468.8	468.8	468.8
140°	486.5	486.6	486.5	486.4	486.3	486.2	486.1	486.3	486.5	486.8	487.0
142.5°	503.0	503.1	503.2	503.4	503.6	503.8	504.0	504.0	504.0	504.0	504.0
145°	519.9	520.0	520.0	520.0	520.0	520.0	520.0	520.1	520.2	520.3	520.4
147.5°	533.7	533.7	533.8	533.9	534.0	534.1	534.2	534.3	534.4	534.5	534.6
150°	546.6	546.5	546.6	546.8	547.0	547.2	547.4	547.6	547.8	548.0	548.2
152.5°	558.7	558.4	558.5	558.7	558.9	559.1	559.3	559.5	559.7	559.9	560.1
155°	569.2	568.9	569.0	569.2	569.4	569.6	569.8	570.1	570.4	570.7	571.0
157.5°	579.1	579.0	579.0	579.0	579.0	579.0	579.0	579.3	579.6	579.9	580.2
160°	587.0	586.7	586.8	586.9	587.0	587.1	587.2	587.6	588.0	588.4	588.8
162.5°	594.4	594.1	594.1	594.2	594.3	594.4	594.5	595.1	595.7	596.4	597.0
165°	600.8	600.5	600.5	600.6	600.7	600.8	600.9	601.5	602.1	602.8	603.4
167.5°	605.8	605.5	605.6	605.7	605.8	605.9	606.0	606.7	607.4	608.1	608.8
170°	609.6	609.2	609.2	609.3	609.4	609.5	609.6	610.4	611.2	612.1	612.9
172.5°	612.3	611.9	612.0	612.2	612.4	612.6	612.8	613.5	614.2	614.9	615.6
175°	614.5	614.2	614.2	614.3	614.4	614.5	614.6	615.4	616.2	617.1	617.9
177.5°	615.9	615.6	615.6	615.7	615.8	615.9	616.0	616.7	617.4	618.1	618.8
180°	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1801.7	1804.8	1797.0	1793.9	1787.6	1795.5	1797.0	1795.5	1809.5	1803.3	1806.4
5°	1697.0	1690.8	1686.1	1675.1	1675.1	1676.7	1681.4	1673.6	1678.3	1689.2	1687.6
7.5°	1581.4	1578.3	1579.8	1567.3	1557.9	1561.1	1557.9	1572.0	1579.8	1576.7	1582.9
10°	1476.7	1482.9	1468.9	1462.6	1456.4	1462.6	1461.1	1464.2	1473.6	1479.8	1490.7
12.5°	1392.3	1390.7	1382.9	1376.7	1365.7	1368.9	1378.2	1375.1	1376.7	1390.7	1389.2
15°	1312.6	1303.2	1297.0	1282.9	1286.0	1275.1	1284.5	1295.4	1300.1	1312.6	1320.4
17.5°	1232.9	1231.3	1223.5	1222.0	1204.8	1200.1	1209.5	1212.6	1217.3	1223.5	1234.5
20°	1165.7	1164.2	1153.2	1150.1	1136.0	1145.4	1142.3	1148.5	1151.7	1164.2	1168.8
22.5°	1104.8	1097.0	1093.8	1089.1	1084.5	1082.9	1089.1	1087.6	1098.5	1103.2	1104.8
25°	1048.5	1042.3	1040.7	1032.9	1029.8	1025.1	1029.8	1034.5	1047.0	1051.6	1057.9
27.5°	997.0	992.3	989.1	982.9	978.2	978.2	981.3	987.6	992.3	995.4	998.5
30°	950.1	947.0	937.6	934.4	929.8	929.8	929.8	932.9	940.7	950.1	954.8
32.5°	901.6	895.4	889.1	889.1	884.4	884.4	886.0	889.1	896.9	898.5	906.3
35°	854.8	848.5	843.8	840.7	842.3	836.0	839.1	843.8	853.2	856.3	861.0
37.5°	809.4	807.9	798.5	793.8	796.9	796.9	795.4	798.5	804.8	811.0	814.1
40°	759.4	756.3	756.3	751.6	753.2	746.9	751.6	754.7	757.9	764.1	768.8
42.5°	715.7	712.6	706.3	707.9	703.2	703.2	706.3	707.9	712.6	720.4	723.5
45°	668.8	668.8	665.7	661.0	662.6	657.9	661.0	662.6	668.8	676.6	673.5
47.5°	623.5	621.9	621.9	615.7	618.8	614.1	618.8	620.4	623.5	628.2	626.6
50°	579.7	575.0	576.6	575.0	573.5	573.5	576.6	576.6	579.7	579.7	584.4
52.5°	534.4	534.4	531.3	532.9	536.0	532.9	537.5	532.9	536.0	537.5	540.7
55°	493.8	490.7	492.2	490.7	496.9	492.2	496.9	493.8	496.9	495.4	498.5
57.5°	450.0	445.3	446.9	445.3	450.0	448.5	453.2	448.5	450.0	451.6	456.3
60°	400.0	400.0	400.0	396.9	401.6	401.6	400.0	400.0	406.3	409.4	407.8
62.5°	353.2	351.6	346.9	345.3	346.9	343.8	350.0	348.5	351.6	354.7	357.8
65°	301.6	298.5	296.9	293.8	293.8	292.2	293.8	300.0	301.6	303.1	311.0
67.5°	259.4	257.8	256.3	251.6	251.6	254.7	254.7	254.7	264.1	259.4	265.6
70°	221.9	218.8	215.6	214.1	214.1	215.6	217.2	218.8	217.2	223.5	225.0
72.5°	186.0	187.5	184.4	184.4	184.4	182.8	182.8	186.0	187.5	186.0	187.5
75°	154.7	154.7	153.1	154.7	154.7	153.1	153.1	156.3	156.3	154.7	159.4
77.5°	125.0	123.4	120.3	117.2	118.8	117.2	118.8	117.2	121.9	126.6	123.4
80°	87.5	85.9	85.9	85.9	87.5	85.9	89.1	85.9	87.5	87.5	89.1
82.5°	62.5	64.1	64.1	62.5	64.1	62.5	64.1	64.1	64.1	62.5	64.1
85°	40.6	40.6	40.6	40.6	39.1	40.6	40.6	40.6	42.2	40.6	42.2
87.5°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	18.8	17.2	18.8
90°	9.6	9.8	10.1	10.4	10.7	11.0	10.7	10.4	10.1	9.8	9.6
92.5°	9.6	9.7	9.8	9.9	10.0	10.1	10.0	9.9	9.8	9.7	9.6
95°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6
97.5°	9.1	9.2	9.3	9.4	9.5	9.6	9.5	9.4	9.3	9.2	9.1
100°	11.4	11.2	10.8	10.4	10.0	9.6	10.0	10.4	10.8	11.2	11.4
102.5°	107.9	103.6	95.1	86.6	78.0	69.5	78.0	86.6	95.1	103.6	107.9
105°	136.3	136.2	136.1	136.0	135.9	135.8	135.9	136.0	136.1	136.2	136.3
107.5°	166.9	166.7	166.3	165.9	165.5	165.1	165.5	165.9	166.3	166.7	166.9
110°	195.3	195.3	195.4	195.5	195.6	195.7	195.6	195.5	195.4	195.3	195.3

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	224.1	224.0	223.8	223.6	223.4	223.2	223.4	223.6	223.8	224.0	224.1
115°	253.4	253.1	252.5	251.8	251.2	250.6	251.2	251.8	252.5	253.1	253.4
117.5°	281.3	281.2	281.0	280.7	280.5	280.3	280.5	280.7	281.0	281.2	281.3
120°	309.6	309.3	308.8	308.3	307.8	307.3	307.8	308.3	308.8	309.3	309.6
122.5°	335.7	335.4	334.8	334.1	333.5	332.9	333.5	334.1	334.8	335.4	335.7
125°	360.4	360.2	359.9	359.6	359.3	359.0	359.3	359.6	359.9	360.2	360.4
127.5°	384.2	383.8	383.0	382.1	381.3	380.5	381.3	382.1	383.0	383.8	384.2
130°	406.6	406.3	405.8	405.3	404.8	404.3	404.8	405.3	405.8	406.3	406.6
132.5°	428.5	428.2	427.7	427.2	426.7	426.2	426.7	427.2	427.7	428.2	428.5
135°	448.6	448.3	447.7	447.1	446.5	445.9	446.5	447.1	447.7	448.3	448.6
137.5°	468.8	468.5	468.0	467.5	467.0	466.5	467.0	467.5	468.0	468.5	468.8
140°	487.1	486.8	486.2	485.5	484.9	484.3	484.9	485.5	486.2	486.8	487.1
142.5°	504.0	503.7	503.1	502.4	501.8	501.2	501.8	502.4	503.1	503.7	504.0
145°	520.4	520.1	519.5	518.9	518.3	517.7	518.3	518.9	519.5	520.1	520.4
147.5°	534.6	534.2	533.5	532.8	532.1	531.4	532.1	532.8	533.5	534.2	534.6
150°	548.3	547.9	547.1	546.3	545.5	544.7	545.5	546.3	547.1	547.9	548.3
152.5°	560.2	559.8	559.1	558.4	557.7	557.0	557.7	558.4	559.1	559.8	560.2
155°	571.2	570.8	570.0	569.1	568.3	567.5	568.3	569.1	570.0	570.8	571.2
157.5°	580.3	579.9	579.1	578.3	577.5	576.7	577.5	578.3	579.1	579.9	580.3
160°	589.0	588.6	587.8	587.0	586.2	585.4	586.2	587.0	587.8	588.6	589.0
162.5°	597.3	596.8	595.9	595.0	594.1	593.2	594.1	595.0	595.9	596.8	597.3
165°	603.7	603.3	602.5	601.6	600.8	600.0	600.8	601.6	602.5	603.3	603.7
167.5°	609.2	608.7	607.8	606.9	605.9	605.0	605.9	606.9	607.8	608.7	609.2
170°	613.3	612.8	611.9	611.0	610.1	609.2	610.1	611.0	611.9	612.8	613.3
172.5°	616.0	615.5	614.6	613.7	612.8	611.9	612.8	613.7	614.6	615.5	616.0
175°	618.3	617.8	616.9	616.0	615.1	614.2	615.1	616.0	616.9	617.8	618.3
177.5°	619.2	618.8	618.0	617.2	616.4	615.6	616.4	617.2	618.0	618.8	619.2
180°	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1800.1	1808.0	1801.7	1797.0	1809.5	1815.8	1815.8	1826.7	1837.6	1847.0	1848.6
5°	1689.2	1701.7	1704.8	1703.3	1722.0	1731.4	1751.7	1762.6	1778.3	1789.2	1801.7
7.5°	1587.6	1604.8	1606.4	1609.5	1637.6	1653.3	1670.4	1698.6	1720.5	1736.1	1750.1
10°	1486.1	1497.0	1507.9	1522.0	1550.1	1576.7	1601.7	1631.4	1659.5	1675.1	1695.4
12.5°	1409.5	1417.3	1429.8	1439.2	1468.9	1492.3	1525.1	1565.8	1606.4	1618.9	1643.9
15°	1329.8	1334.5	1359.5	1368.9	1393.9	1432.9	1453.2	1492.3	1536.1	1559.5	1587.6
17.5°	1237.6	1265.7	1281.4	1292.3	1323.5	1354.8	1387.6	1428.2	1484.5	1506.4	1526.7
20°	1172.0	1192.3	1209.5	1223.5	1251.7	1298.5	1328.2	1361.0	1414.2	1439.2	1468.9
22.5°	1114.2	1131.3	1147.0	1162.6	1181.3	1223.5	1257.9	1303.2	1356.4	1379.8	1414.2
25°	1059.5	1076.6	1086.0	1104.8	1129.8	1159.5	1200.1	1240.7	1293.9	1320.4	1353.2
27.5°	1006.3	1023.5	1040.7	1056.3	1073.5	1101.7	1129.8	1181.3	1236.0	1267.3	1295.4
30°	961.0	968.8	984.5	1001.6	1018.8	1045.4	1078.2	1114.2	1176.7	1204.8	1239.2
32.5°	911.0	925.1	936.0	948.5	970.4	992.3	1022.0	1067.3	1117.3	1143.8	1181.3
35°	864.1	876.6	884.4	906.3	920.4	943.8	973.5	1014.1	1056.3	1086.0	1118.8
37.5°	818.8	831.3	840.7	853.2	871.9	892.3	923.5	953.2	1003.2	1028.2	1065.7
40°	771.9	782.9	793.8	807.9	825.1	850.1	868.8	906.3	947.0	975.1	1003.2
42.5°	726.6	732.9	745.4	761.0	778.2	800.1	826.6	856.3	896.9	921.9	947.0
45°	678.2	689.1	703.2	714.1	729.7	751.6	775.1	801.6	842.3	867.3	893.8
47.5°	632.9	640.7	650.1	667.2	687.6	703.2	728.2	753.2	790.7	814.1	839.1
50°	586.0	593.8	607.9	618.8	634.4	654.7	678.2	704.7	740.7	756.3	781.3
52.5°	542.2	545.4	559.4	570.4	586.0	609.4	628.2	651.6	686.0	703.2	728.2
55°	498.5	501.6	509.4	520.4	537.5	556.3	576.6	603.2	632.9	648.5	671.9
57.5°	453.2	456.3	464.1	471.9	489.1	506.3	529.7	551.6	581.3	595.4	617.2
60°	407.8	407.8	415.7	426.6	439.1	454.7	475.0	501.6	523.5	540.7	556.3
62.5°	359.4	364.1	368.8	376.6	390.7	409.4	426.6	445.3	471.9	484.4	498.5
65°	311.0	315.7	325.0	332.8	343.8	356.3	378.2	393.8	414.1	428.2	440.7
67.5°	268.8	273.5	279.7	289.1	296.9	311.0	326.6	342.2	364.1	373.5	382.8
70°	225.0	229.7	234.4	246.9	254.7	265.6	276.6	292.2	311.0	317.2	325.0
72.5°	190.6	192.2	198.5	201.6	212.5	221.9	234.4	243.8	257.8	265.6	271.9
75°	161.0	161.0	162.5	165.6	171.9	178.1	187.5	196.9	209.4	214.1	221.9
77.5°	126.6	131.3	129.7	132.8	135.9	139.1	146.9	153.1	165.6	168.8	171.9
80°	90.6	92.2	96.9	101.6	101.6	106.3	110.9	112.5	120.3	125.0	125.0
82.5°	65.6	67.2	65.6	67.2	68.8	70.3	75.0	81.3	81.3	82.8	85.9
85°	40.6	40.6	42.2	43.8	43.8	42.2	45.3	43.8	45.3	48.4	48.4
87.5°	20.3	18.8	18.8	18.8	18.8	18.8	20.3	18.8	20.3	20.3	20.3
90°	9.3	8.8	8.3	7.8	7.3	6.6	5.9	5.2	4.5	4.1	3.7
92.5°	9.3	8.8	8.3	7.8	7.3	6.7	6.1	5.5	4.9	4.6	5.1
95°	9.3	8.8	8.3	7.8	7.3	11.2	15.0	18.9	22.8	24.7	24.9
97.5°	9.0	8.8	8.6	8.4	8.2	17.9	27.5	37.2	46.9	51.7	51.4
100°	19.0	34.1	49.3	64.4	79.6	79.2	78.8	78.3	77.9	77.7	77.6
102.5°	107.8	107.6	107.4	107.2	107.0	106.8	106.6	106.4	106.2	106.1	105.9
105°	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.1
107.5°	166.9	166.8	166.7	166.6	166.5	166.3	166.1	165.9	165.7	165.6	165.6
110°	195.4	195.7	196.0	196.3	196.6	196.4	196.2	196.0	195.8	195.7	195.7

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	224.3	224.7	225.1	225.5	225.9	225.8	225.7	225.6	225.5	225.5	225.3
115°	253.6	254.0	254.4	254.8	255.2	255.1	255.0	254.9	254.8	254.7	254.4
117.5°	281.6	282.2	282.8	283.4	284.0	283.6	283.2	282.8	282.4	282.2	282.2
120°	309.7	309.9	310.1	310.3	310.5	310.2	309.9	309.6	309.3	309.2	309.2
122.5°	335.8	336.0	336.2	336.4	336.6	336.5	336.4	336.3	336.2	336.1	335.8
125°	360.6	361.0	361.4	361.8	362.2	362.2	362.2	362.2	362.2	362.2	361.8
127.5°	384.3	384.5	384.7	384.9	385.1	385.2	385.3	385.4	385.5	385.5	385.2
130°	406.7	407.0	407.3	407.6	407.9	407.8	407.7	407.6	407.5	407.5	407.2
132.5°	428.5	428.5	428.5	428.5	428.5	428.8	429.1	429.4	429.7	429.9	429.6
135°	448.7	448.9	449.2	449.4	449.6	449.8	450.0	450.2	450.4	450.5	450.2
137.5°	468.8	468.8	468.8	468.8	468.8	469.0	469.2	469.4	469.6	469.7	469.4
140°	487.0	486.8	486.5	486.3	486.1	486.2	486.3	486.4	486.5	486.6	486.5
142.5°	504.0	504.0	504.0	504.0	504.0	503.8	503.6	503.4	503.2	503.1	503.0
145°	520.4	520.3	520.2	520.1	520.0	520.0	520.0	520.0	520.0	520.0	519.9
147.5°	534.6	534.5	534.4	534.3	534.2	534.1	534.0	533.9	533.8	533.7	533.7
150°	548.2	548.0	547.8	547.6	547.4	547.2	547.0	546.8	546.6	546.5	546.6
152.5°	560.1	559.9	559.7	559.5	559.3	559.1	558.9	558.7	558.5	558.4	558.7
155°	571.0	570.7	570.4	570.1	569.8	569.6	569.4	569.2	569.0	568.9	569.2
157.5°	580.2	579.9	579.6	579.3	579.0	579.0	579.0	579.0	579.0	579.0	579.1
160°	588.8	588.4	588.0	587.6	587.2	587.1	587.0	586.9	586.8	586.7	587.0
162.5°	597.0	596.4	595.7	595.1	594.5	594.4	594.3	594.2	594.1	594.1	594.4
165°	603.4	602.8	602.1	601.5	600.9	600.8	600.7	600.6	600.5	600.5	600.8
167.5°	608.8	608.1	607.4	606.7	606.0	605.9	605.8	605.7	605.6	605.5	605.8
170°	612.9	612.1	611.2	610.4	609.6	609.5	609.4	609.3	609.2	609.2	609.6
172.5°	615.6	614.9	614.2	613.5	612.8	612.6	612.4	612.2	612.0	611.9	612.3
175°	617.9	617.1	616.2	615.4	614.6	614.5	614.4	614.3	614.2	614.2	614.5
177.5°	618.8	618.1	617.4	616.7	616.0	615.9	615.8	615.7	615.6	615.6	615.9
180°	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9	616.9

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1903.3	1903.3	1903.3	1903.3
2.5°	1859.5	1873.6	1887.7	1904.8
5°	1822.0	1847.0	1873.6	1898.6
7.5°	1781.4	1817.3	1851.7	1887.7
10°	1736.1	1781.4	1820.5	1870.5
12.5°	1686.1	1734.5	1789.2	1845.5
15°	1636.1	1697.0	1754.8	1818.9
17.5°	1589.2	1647.0	1711.1	1787.6
20°	1532.9	1597.0	1668.9	1750.1
22.5°	1473.6	1543.9	1622.0	1709.5
25°	1423.6	1495.4	1570.4	1662.6
27.5°	1368.9	1443.9	1517.3	1615.8
30°	1306.4	1387.6	1462.6	1564.2
32.5°	1247.0	1328.2	1411.1	1506.4
35°	1189.2	1268.9	1351.7	1448.6
37.5°	1134.5	1206.3	1287.6	1375.1
40°	1082.9	1148.5	1220.4	1300.1
42.5°	1017.3	1093.8	1161.0	1218.8
45°	961.0	1023.5	1086.0	1132.9
47.5°	895.4	957.9	1011.0	1048.5
50°	840.7	890.7	934.4	967.3
52.5°	775.1	821.9	857.9	882.9
55°	711.0	751.6	782.9	800.1
57.5°	653.2	679.7	703.2	718.8
60°	589.1	609.4	629.7	646.9
62.5°	520.4	542.2	553.2	571.9
65°	459.4	473.5	490.7	496.9
67.5°	400.0	407.8	418.8	431.3
70°	337.5	342.2	353.2	370.3
72.5°	282.8	287.5	295.3	301.6
75°	225.0	229.7	236.0	242.2
77.5°	176.6	178.1	181.3	187.5
80°	128.1	132.8	135.9	137.5
82.5°	89.1	90.6	90.6	92.2
85°	56.3	53.1	53.1	54.7
87.5°	20.3	23.4	23.4	26.6
90°	2.9	2.1	1.3	0.5
92.5°	6.0	6.9	7.8	8.7
95°	25.2	25.5	25.8	26.1
97.5°	50.8	50.1	49.5	48.9
100°	77.3	77.0	76.7	76.4
102.5°	105.5	105.1	104.7	104.3
105°	135.7	135.3	134.9	134.5
107.5°	165.6	165.6	165.6	165.6
110°	195.7	195.7	195.7	195.7

TEST NUMBER: P1034771

CATALOG NUMBER: S125RDIW-B1270D470UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	225.0	224.7	224.4	224.1
115°	253.9	253.4	252.9	252.4
117.5°	282.2	282.2	282.2	282.2
120°	309.3	309.4	309.5	309.6
122.5°	335.3	334.8	334.3	333.8
125°	361.1	360.4	359.7	359.0
127.5°	384.7	384.2	383.7	383.2
130°	406.7	406.2	405.7	405.2
132.5°	429.0	428.3	427.7	427.1
135°	449.6	448.9	448.3	447.7
137.5°	468.8	468.1	467.5	466.9
140°	486.3	486.1	485.9	485.7
142.5°	502.9	502.8	502.7	502.6
145°	519.7	519.5	519.3	519.1
147.5°	533.7	533.7	533.7	533.7
150°	546.8	547.0	547.2	547.4
152.5°	559.2	559.7	560.2	560.7
155°	569.8	570.5	571.1	571.7
157.5°	579.4	579.7	580.0	580.3
160°	587.6	588.3	588.9	589.5
162.5°	595.0	595.6	596.2	596.8
165°	601.4	602.0	602.6	603.2
167.5°	606.4	607.0	607.6	608.2
170°	610.3	611.0	611.7	612.4
172.5°	613.0	613.7	614.4	615.1
175°	615.1	615.7	616.3	616.9
177.5°	616.5	617.1	617.7	618.3
180°	616.9	616.9	616.9	616.9

(END OF REPORT)