

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035033

Luminaire Tested: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035033
REPORT IS A COMBINATION OF REPORTS P1002948 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D470UB30-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6105.0 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77
1	103	99	95	92	98	94	91	88	85	82	80	77	75	73	69	67	66	66	66	62
2	94	87	81	75	89	83	77	72	75	71	67	68	64	61	61	58	56	56	56	53
3	86	77	69	63	82	73	66	61	66	61	56	60	56	52	54	51	48	48	48	45
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	49	45	42	42	42	39
5	73	61	53	46	69	58	51	45	53	47	42	48	43	39	44	40	36	36	36	34
6	67	55	46	40	64	52	45	39	48	42	37	44	39	34	40	36	32	32	32	30
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	32	29	29	29	26
8	58	45	37	32	55	43	36	31	40	34	29	37	31	27	34	29	26	26	26	24
9	54	41	34	28	51	40	33	28	37	30	26	34	28	25	31	26	23	23	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	29	24	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10129	10129	10129	10129
5°	10136	11491	10145	8717
10°	10075	13096	10057	7483
15°	10001	14200	9939	6761
20°	9874	15561	9784	6172
25°	9762	17830	9584	5823
30°	9601	18810	9435	5508
35°	9347	15079	9151	5254
40°	8949	10422	8817	4986
45°	8447	7759	8352	4764
50°	7872	6387	7741	4585
55°	7251	5448	7194	4430
60°	6642	4663	6527	4310
65°	5986	4027	5889	4135
70°	5292	3343	5222	3830
75°	4558	2586	4497	3324
80°	3600	1749	3471	2444
85°	2304	875	2224	1246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 15471 cd/sqm

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	2.5
10°-20°	453.2	7.4
20°-30°	736.1	12.1
30°-40°	899.7	14.7
40°-50°	816.1	13.4
50°-60°	650.0	10.6
60°-70°	452.7	7.4
70°-80°	241.2	4.0
80°-90°	60.7	1.0
90°-100°	39.1	0.6
100°-110°	116.3	1.9
110°-120°	197.2	3.2
120°-130°	259.7	4.3
130°-140°	291.0	4.8
140°-150°	285.2	4.7
150°-160°	239.6	3.9
160°-170°	159.2	2.6
170°-180°	55.7	0.9
0°-30°	1341.5	22.0
0°-40°	2241.2	36.7
0°-60°	3707.3	60.7
0°-90°	4461.9	73.1
90°-120°	352.7	5.8
90°-150°	1188.5	19.5
90°-180°	1643.0	26.9
0°-180°	6105.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1580	1824	1581	1384	1580	150
15°	1518	2277	1508	1084	1518	428
25°	1397	2802	1372	915	1397	643
35°	1216	2249	1190	784	1216	759
45°	956	1060	945	651	956	736
55°	672	654	667	531	672	601
65°	416	401	409	412	416	413
75°	201	197	199	254	201	214
85°	40	44	39	63	40	48
90°	0	11	0	11	0	5
95°	30	39	30	39	30	31
105°	104	114	104	114	104	111
115°	198	199	198	199	198	195
125°	288	290	288	290	288	258
135°	375	376	375	376	375	289
145°	454	456	454	456	454	284
155°	520	520	520	520	520	239
165°	565	564	565	564	565	159
175°	587	585	587	585	587	56
180°	589	589	589	589	589	

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9
2.5°	1583.6	1593.0	1603.7	1611.7	1625.2	1629.2	1635.9	1639.9	1643.9	1648.0	1650.7
5°	1579.5	1602.3	1622.5	1637.2	1662.7	1672.1	1684.2	1699.0	1716.4	1731.2	1740.6
7.5°	1568.8	1605.0	1631.9	1661.4	1696.3	1719.1	1731.2	1762.0	1790.2	1811.7	1839.9
10°	1555.4	1598.3	1639.9	1684.2	1733.9	1759.4	1783.5	1826.5	1865.4	1900.3	1928.5
12.5°	1540.6	1593.0	1642.6	1700.3	1767.4	1798.3	1814.4	1888.2	1936.5	1955.3	2010.3
15°	1517.8	1579.5	1650.7	1721.8	1778.1	1814.4	1858.7	1917.7	1966.0	2007.6	2051.9
17.5°	1496.3	1563.4	1635.9	1715.1	1796.9	1843.9	1877.5	1929.8	1982.1	2035.8	2077.4
20°	1461.4	1548.7	1622.5	1707.0	1803.6	1837.2	1872.1	1933.8	1990.2	2047.9	2100.2
22.5°	1433.3	1516.5	1617.1	1697.6	1779.5	1813.0	1856.0	1920.4	1987.5	2053.3	2129.8
25°	1397.0	1489.6	1576.8	1662.7	1747.3	1783.5	1822.4	1905.6	1975.4	2060.0	2144.5
27.5°	1358.1	1453.4	1540.6	1618.5	1697.6	1747.3	1788.9	1876.1	1968.7	2061.3	2171.4
30°	1316.5	1406.4	1489.6	1566.1	1653.3	1704.3	1745.9	1847.9	1951.3	2069.4	2200.9
32.5°	1272.2	1356.8	1427.9	1505.7	1598.3	1645.3	1701.7	1813.0	1935.2	2076.1	2241.1
35°	1215.9	1296.4	1359.4	1438.6	1531.2	1591.6	1650.7	1775.5	1917.7	2074.7	2264.0
37.5°	1159.5	1222.6	1283.0	1367.5	1474.9	1529.9	1591.6	1728.5	1890.9	2070.7	2273.3
40°	1092.4	1154.1	1206.5	1292.3	1405.1	1468.1	1532.6	1676.2	1860.0	2055.9	2239.8
42.5°	1025.3	1077.6	1135.3	1225.2	1333.9	1401.0	1469.5	1629.2	1819.8	2013.0	2147.2
45°	955.5	995.8	1058.8	1140.7	1256.1	1320.5	1398.4	1571.5	1763.4	1935.2	2002.3
47.5°	883.0	923.3	982.3	1061.5	1175.6	1252.1	1325.9	1499.0	1692.3	1825.1	1825.1
50°	813.3	845.5	903.2	982.3	1097.8	1167.5	1242.7	1426.5	1582.2	1680.2	1593.0
52.5°	738.1	774.3	822.6	905.8	1019.9	1083.0	1164.9	1321.9	1469.5	1509.7	1375.5
55°	672.3	701.9	747.5	826.7	932.7	998.4	1068.2	1218.5	1343.3	1340.7	1197.1
57.5°	603.9	628.1	676.4	748.8	846.8	905.8	975.6	1105.8	1207.8	1171.6	1036.0
60°	540.8	558.3	605.2	664.3	758.2	813.3	880.4	986.4	1064.2	1013.2	876.3
62.5°	475.1	495.2	532.8	590.5	673.7	718.0	767.6	875.0	924.6	879.0	739.4
65°	416.0	432.1	465.7	514.0	589.1	629.4	672.3	760.9	807.9	742.1	626.7
67.5°	357.0	375.8	399.9	442.9	501.9	539.5	577.1	653.6	675.0	616.0	519.4
70°	301.9	318.1	340.9	371.7	421.4	454.9	483.1	546.2	561.0	505.9	429.4
72.5°	248.3	259.0	277.8	303.3	348.9	367.7	397.2	440.2	459.0	409.3	354.3
75°	201.3	209.4	221.4	240.2	271.1	291.2	315.4	355.6	354.3	319.4	280.5
77.5°	155.7	157.0	170.4	187.9	206.7	224.1	236.2	264.4	267.1	245.6	213.4
80°	111.4	115.4	120.8	134.2	150.3	157.0	171.8	189.2	191.9	175.8	154.3
82.5°	71.1	73.8	77.8	85.9	96.6	104.7	112.7	119.4	126.1	116.8	99.3
85°	40.3	41.6	45.6	48.3	53.7	57.7	64.4	71.1	69.8	63.1	57.7
87.5°	20.1	20.1	20.1	22.8	25.5	25.5	28.2	29.5	30.9	28.2	25.5
90°	0.5	1.3	2.1	2.9	3.7	4.1	4.5	5.2	5.9	6.6	7.3
92.5°	13.7	14.2	14.7	15.2	15.7	16.0	16.5	17.4	18.3	19.3	20.2
95°	29.8	30.0	30.2	30.4	30.6	30.7	31.2	32.2	33.3	34.3	35.3
97.5°	45.8	45.9	46.0	46.1	46.2	46.3	47.0	48.4	49.9	51.3	52.7
100°	64.1	64.1	64.1	64.1	64.1	64.1	64.8	66.1	67.4	68.8	70.1
102.5°	83.8	84.3	84.8	85.3	85.8	86.1	86.4	86.9	87.4	87.9	88.4
105°	104.5	105.0	105.5	106.0	106.5	106.7	107.0	107.6	108.3	108.9	109.5
107.5°	126.9	127.4	127.9	128.4	128.9	129.2	129.5	130.0	130.5	131.0	131.5
110°	150.3	150.8	151.3	151.8	152.3	152.6	152.7	153.0	153.3	153.6	153.9

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	174.1	174.3	174.5	174.7	174.9	175.0	175.2	175.6	176.0	176.4	176.8
115°	197.5	197.9	198.3	198.7	199.1	199.3	199.4	199.6	199.8	200.0	200.2
117.5°	221.3	221.4	221.5	221.6	221.7	221.7	221.8	222.0	222.3	222.5	222.7
120°	243.3	243.8	244.3	244.8	245.3	245.6	245.6	245.7	245.8	245.9	246.0
122.5°	267.1	267.2	267.3	267.4	267.5	267.6	267.7	268.0	268.3	268.6	268.9
125°	288.2	288.8	289.4	290.0	290.6	290.9	291.0	291.1	291.2	291.3	291.4
127.5°	311.5	311.8	312.1	312.4	312.7	312.9	313.0	313.1	313.2	313.3	313.4
130°	332.2	332.7	333.2	333.7	334.2	334.5	334.6	334.8	335.0	335.2	335.4
132.5°	352.8	353.7	354.6	355.5	356.4	356.9	356.8	356.7	356.6	356.5	356.4
135°	374.8	375.4	376.0	376.6	377.2	377.5	377.6	377.7	377.8	377.9	378.0
137.5°	395.4	396.0	396.6	397.2	397.8	398.1	398.2	398.4	398.7	398.9	399.1
140°	415.1	415.6	416.1	416.6	417.1	417.4	417.6	417.9	418.2	418.5	418.8
142.5°	434.8	435.2	435.6	436.0	436.4	436.6	436.8	437.2	437.7	438.1	438.5
145°	454.0	454.4	454.8	455.3	455.7	455.9	456.0	456.3	456.6	456.9	457.2
147.5°	471.9	472.2	472.5	472.8	473.1	473.3	473.4	473.6	473.8	474.0	474.2
150°	489.8	489.7	489.6	489.5	489.4	489.3	489.5	489.9	490.3	490.7	491.1
152.5°	504.4	504.6	504.8	505.0	505.2	505.3	505.4	505.5	505.6	505.7	505.8
155°	519.5	519.5	519.5	519.5	519.5	519.5	519.6	519.7	519.8	519.9	520.0
157.5°	533.3	533.1	532.9	532.7	532.5	532.4	532.4	532.5	532.6	532.7	532.8
160°	545.2	544.9	544.6	544.3	544.0	543.8	543.9	544.0	544.1	544.2	544.3
162.5°	555.7	555.5	555.3	555.1	554.9	554.8	554.8	554.8	554.8	554.8	554.8
165°	564.9	564.7	564.5	564.3	564.1	564.0	564.0	564.1	564.2	564.3	564.4
167.5°	573.1	572.7	572.3	571.9	571.5	571.3	571.3	571.3	571.3	571.3	571.3
170°	579.6	579.2	578.8	578.3	577.9	577.7	577.7	577.7	577.7	577.7	577.7
172.5°	584.1	583.7	583.3	582.9	582.5	582.3	582.3	582.3	582.3	582.3	582.3
175°	587.4	587.0	586.6	586.1	585.7	585.5	585.5	585.5	585.5	585.5	585.5
177.5°	589.6	589.2	588.8	588.4	588.0	587.8	587.8	587.7	587.6	587.5	587.4
180°	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9
2.5°	1653.3	1662.7	1670.8	1677.5	1682.9	1690.9	1685.6	1686.9	1689.6	1694.9	1694.9
5°	1760.7	1775.5	1783.5	1810.4	1817.1	1815.7	1811.7	1833.2	1831.8	1823.8	1822.4
7.5°	1865.4	1890.9	1913.7	1935.2	1941.9	1959.3	1963.3	1972.7	1970.1	1983.5	1976.8
10°	1960.7	2000.9	2022.4	2054.6	2062.7	2070.7	2081.4	2086.8	2098.9	2097.5	2097.5
12.5°	2034.5	2082.8	2111.0	2119.0	2149.9	2159.3	2168.7	2186.1	2182.1	2183.4	2191.5
15°	2092.2	2139.1	2163.3	2200.9	2222.4	2233.1	2249.2	2268.0	2265.3	2277.4	2274.7
17.5°	2135.1	2179.4	2223.7	2280.1	2281.4	2309.6	2347.2	2355.2	2372.7	2360.6	2360.6
20°	2170.0	2229.1	2292.1	2364.6	2372.7	2390.1	2435.7	2466.6	2486.7	2480.0	2484.0
22.5°	2207.6	2292.1	2365.9	2438.4	2477.3	2508.2	2552.5	2600.8	2618.2	2629.0	2626.3
25°	2255.9	2344.5	2453.2	2553.8	2594.1	2653.1	2712.2	2759.1	2772.6	2802.1	2775.3
27.5°	2305.6	2430.4	2565.9	2684.0	2735.0	2783.3	2854.4	2889.3	2906.8	2920.2	2910.8
30°	2347.2	2518.9	2666.6	2775.3	2811.5	2839.7	2879.9	2888.0	2881.3	2892.0	2905.4
32.5°	2411.6	2579.3	2704.1	2756.5	2752.4	2751.1	2720.2	2677.3	2667.9	2642.4	2677.3
35°	2446.5	2580.7	2629.0	2559.2	2531.0	2480.0	2382.0	2317.6	2261.3	2249.2	2251.9
37.5°	2426.3	2478.7	2421.0	2237.1	2191.5	2113.6	1983.5	1892.2	1850.6	1818.4	1860.0
40°	2317.6	2259.9	2101.6	1877.5	1811.7	1737.9	1615.8	1566.1	1507.1	1495.0	1550.0
42.5°	2137.8	1962.0	1737.9	1564.8	1496.3	1454.7	1352.7	1305.8	1264.2	1245.4	1276.2
45°	1893.6	1680.2	1454.7	1312.5	1254.8	1205.1	1144.7	1095.1	1068.2	1060.2	1085.7
47.5°	1641.3	1415.8	1236.0	1130.0	1069.6	1032.0	975.6	947.5	926.0	928.7	932.7
50°	1399.7	1194.4	1056.2	950.1	920.6	891.1	853.5	829.4	818.6	822.6	820.0
52.5°	1191.7	1025.3	908.5	826.7	813.3	785.1	754.2	734.1	730.0	731.4	735.4
55°	1009.2	879.0	786.4	727.4	712.6	692.5	673.7	660.3	649.5	653.6	652.2
57.5°	871.0	756.9	685.8	637.4	626.7	614.6	597.2	590.5	586.5	578.4	585.1
60°	748.8	656.2	594.5	565.0	555.6	547.5	528.7	520.7	518.0	514.0	524.7
62.5°	633.4	567.7	520.7	493.9	484.5	476.4	467.0	460.3	461.6	456.3	461.6
65°	542.2	488.5	454.9	430.8	418.7	413.3	412.0	401.3	399.9	401.3	402.6
67.5°	457.6	412.0	386.5	371.7	362.3	357.0	352.9	346.2	351.6	347.6	350.3
70°	381.1	350.3	323.4	308.7	304.6	306.0	299.3	296.6	297.9	295.2	297.9
72.5°	307.3	281.8	271.1	260.3	255.0	253.6	249.6	245.6	249.6	248.3	248.3
75°	245.6	226.8	214.7	208.0	208.0	205.3	198.6	198.6	198.6	197.3	198.6
77.5°	189.2	173.1	167.7	161.0	161.0	157.0	155.7	155.7	153.0	157.0	154.3
80°	140.9	128.8	120.8	116.8	116.8	115.4	112.7	111.4	112.7	111.4	111.4
82.5°	91.3	85.9	81.9	77.8	76.5	77.8	76.5	73.8	75.2	73.8	76.5
85°	52.3	47.0	47.0	44.3	45.6	42.9	44.3	41.6	40.3	44.3	41.6
87.5°	22.8	21.5	21.5	18.8	18.8	18.8	17.4	18.8	17.4	16.1	17.4
90°	7.8	8.3	8.8	9.3	9.6	9.8	10.1	10.4	10.7	11.0	10.7
92.5°	20.9	21.6	22.3	23.0	23.4	23.5	23.7	23.9	24.1	24.3	24.1
95°	36.0	36.7	37.4	38.1	38.5	38.6	38.8	39.0	39.2	39.4	39.2
97.5°	53.3	53.9	54.5	55.1	55.4	55.5	55.6	55.7	55.8	55.9	55.8
100°	71.0	71.9	72.8	73.7	74.2	74.3	74.5	74.7	74.9	75.1	74.9
102.5°	89.4	90.4	91.5	92.5	93.0	93.2	93.5	93.8	94.1	94.4	94.1
105°	110.1	110.7	111.3	111.9	112.2	112.4	112.7	113.0	113.3	113.6	113.3
107.5°	131.8	132.1	132.4	132.7	132.9	132.9	132.9	132.9	132.9	132.9	132.9
110°	154.2	154.5	154.8	155.1	155.3	155.3	155.2	155.1	155.0	154.9	155.0

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	176.9	177.0	177.1	177.2	177.3	177.2	177.0	176.8	176.6	176.4	176.6
115°	200.1	200.0	199.9	199.8	199.8	199.7	199.6	199.5	199.4	199.3	199.4
117.5°	222.8	222.9	223.0	223.1	223.1	222.9	222.5	222.1	221.7	221.3	221.7
120°	246.0	246.0	246.0	246.0	246.0	245.8	245.4	245.0	244.6	244.2	244.6
122.5°	268.8	268.7	268.6	268.5	268.5	268.3	268.0	267.7	267.4	267.1	267.4
125°	291.2	291.0	290.8	290.6	290.5	290.4	290.3	290.2	290.1	290.0	290.1
127.5°	313.3	313.2	313.1	313.0	312.9	312.8	312.6	312.4	312.2	312.0	312.2
130°	335.3	335.2	335.1	335.0	334.9	334.8	334.6	334.4	334.2	334.0	334.2
132.5°	356.3	356.2	356.1	356.0	356.0	355.8	355.5	355.2	354.9	354.6	354.9
135°	378.0	378.0	378.0	378.0	378.0	377.8	377.4	376.9	376.5	376.1	376.5
137.5°	399.2	399.3	399.4	399.5	399.5	399.2	398.7	398.2	397.7	397.2	397.7
140°	419.0	419.2	419.4	419.6	419.7	419.4	418.9	418.4	417.9	417.4	417.9
142.5°	438.6	438.7	438.8	438.9	438.9	438.6	438.1	437.6	437.1	436.6	437.1
145°	457.2	457.2	457.2	457.2	457.2	457.1	456.8	456.5	456.2	455.9	456.2
147.5°	474.5	474.8	475.1	475.4	475.6	475.2	474.4	473.5	472.7	471.9	472.7
150°	491.1	491.1	491.1	491.1	491.1	491.0	490.8	490.6	490.4	490.2	490.4
152.5°	506.1	506.4	506.7	507.0	507.2	507.0	506.6	506.1	505.7	505.3	505.7
155°	520.4	520.8	521.2	521.6	521.8	521.5	521.0	520.5	520.0	519.5	520.0
157.5°	533.2	533.6	534.1	534.5	534.7	534.3	533.6	532.9	532.2	531.5	532.2
160°	544.7	545.1	545.5	545.9	546.1	545.8	545.3	544.8	544.3	543.8	544.3
162.5°	555.3	555.8	556.3	556.8	557.1	556.8	556.2	555.6	555.0	554.4	555.0
165°	564.8	565.2	565.7	566.1	566.3	566.0	565.4	564.7	564.1	563.5	564.1
167.5°	571.9	572.5	573.2	573.8	574.1	573.8	573.2	572.5	571.9	571.3	571.9
170°	578.3	578.9	579.6	580.2	580.5	580.1	579.4	578.7	578.0	577.3	578.0
172.5°	582.9	583.5	584.2	584.8	585.1	584.8	584.2	583.5	582.9	582.3	582.9
175°	586.1	586.7	587.4	588.0	588.3	587.9	587.2	586.5	585.8	585.1	585.8
177.5°	588.0	588.6	589.2	589.8	590.1	589.7	589.0	588.3	587.6	586.9	587.6
180°	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9
2.5°	1692.3	1682.9	1685.6	1682.9	1676.2	1672.1	1661.4	1648.0	1642.6	1635.9	1631.9
5°	1827.8	1821.1	1819.8	1809.0	1806.3	1790.2	1763.4	1750.0	1733.9	1717.8	1701.7
7.5°	1975.4	1967.4	1940.5	1936.5	1939.2	1919.1	1884.2	1857.3	1823.8	1801.0	1770.1
10°	2097.5	2081.4	2058.6	2060.0	2050.6	2023.7	1988.8	1960.7	1912.3	1882.8	1838.5
12.5°	2171.4	2157.9	2155.3	2141.8	2133.8	2098.9	2057.3	2021.1	1984.8	1944.6	1911.0
15°	2261.3	2243.8	2231.7	2213.0	2207.6	2171.4	2125.7	2084.1	2042.5	2004.9	1933.8
17.5°	2360.6	2341.8	2296.2	2292.1	2259.9	2225.0	2180.7	2119.0	2074.7	2021.1	1968.7
20°	2473.3	2446.5	2387.4	2372.7	2347.2	2289.5	2229.1	2160.6	2089.5	2034.5	1972.7
22.5°	2599.5	2552.5	2509.5	2462.6	2443.8	2372.7	2289.5	2206.2	2120.4	2045.2	1971.4
25°	2763.2	2701.4	2641.1	2594.1	2561.9	2469.3	2357.9	2247.8	2148.5	2050.6	1954.0
27.5°	2892.0	2838.3	2772.6	2710.8	2669.2	2559.2	2431.7	2289.5	2166.0	2046.5	1943.2
30°	2901.4	2885.3	2845.0	2811.5	2765.9	2647.8	2506.9	2345.8	2192.8	2047.9	1921.7
32.5°	2725.6	2757.8	2775.3	2780.6	2771.2	2702.8	2574.0	2396.8	2217.0	2035.8	1903.0
35°	2347.2	2433.0	2539.1	2579.3	2618.2	2654.5	2587.4	2433.0	2225.0	2033.1	1873.4
37.5°	1932.5	2010.3	2186.1	2266.6	2312.3	2455.9	2510.9	2427.7	2241.1	2035.8	1845.2
40°	1559.4	1682.9	1809.0	1917.7	1988.8	2149.9	2320.3	2339.1	2218.3	2010.3	1809.0
42.5°	1312.5	1384.9	1480.2	1580.9	1643.9	1834.5	2065.3	2200.9	2147.2	1968.7	1764.7
45°	1117.9	1171.6	1261.5	1295.0	1375.5	1558.1	1802.3	1998.2	2025.1	1903.0	1713.7
47.5°	959.5	1005.2	1062.9	1104.5	1168.9	1305.8	1512.4	1728.5	1857.3	1813.0	1642.6
50°	845.5	883.0	931.3	955.5	997.1	1120.6	1276.2	1491.0	1664.1	1678.8	1550.0
52.5°	750.2	771.6	809.2	836.1	869.6	944.8	1085.7	1262.8	1457.4	1537.9	1435.9
55°	667.0	684.4	718.0	735.4	752.9	817.3	927.3	1088.4	1270.9	1376.9	1319.2
57.5°	591.8	606.6	634.8	650.9	660.3	722.0	806.5	932.7	1096.4	1225.2	1193.0
60°	530.1	543.5	559.6	571.7	582.4	633.4	692.5	794.5	940.7	1065.5	1057.5
62.5°	464.3	476.4	493.9	505.9	515.3	547.5	597.2	675.0	799.8	915.2	938.1
65°	406.6	416.0	428.1	433.5	445.5	469.7	510.0	579.7	681.7	785.1	801.2
67.5°	354.3	357.0	365.0	377.1	379.8	401.3	437.5	489.8	569.0	653.6	679.1
70°	297.9	301.9	308.7	318.1	323.4	336.8	367.7	402.6	471.0	544.9	563.6
72.5°	248.3	253.6	256.3	261.7	264.4	285.8	299.3	334.2	381.1	442.9	463.0
75°	201.3	206.7	208.0	210.7	213.4	222.8	241.6	263.0	301.9	342.2	369.0
77.5°	159.7	158.4	161.0	165.1	163.7	171.8	183.9	202.6	228.1	261.7	279.1
80°	112.7	112.7	116.8	120.8	119.4	127.5	131.5	144.9	166.4	187.9	194.6
82.5°	75.2	75.2	79.2	79.2	81.9	83.2	88.6	95.3	112.7	123.5	127.5
85°	42.9	42.9	44.3	44.3	44.3	47.0	51.0	53.7	59.0	65.8	68.4
87.5°	17.4	18.8	18.8	18.8	18.8	21.5	21.5	24.2	25.5	28.2	28.2
90°	10.4	10.1	9.8	9.6	9.3	8.8	8.3	7.8	7.3	6.6	5.9
92.5°	23.9	23.7	23.5	23.4	23.0	22.3	21.6	20.9	20.2	19.3	18.3
95°	39.0	38.8	38.6	38.5	38.1	37.4	36.7	36.0	35.3	34.3	33.3
97.5°	55.7	55.6	55.5	55.4	55.1	54.5	53.9	53.3	52.7	51.3	49.9
100°	74.7	74.5	74.3	74.2	73.7	72.8	71.9	71.0	70.1	68.8	67.4
102.5°	93.8	93.5	93.2	93.0	92.5	91.5	90.4	89.4	88.4	87.9	87.4
105°	113.0	112.7	112.4	112.2	111.9	111.3	110.7	110.1	109.5	108.9	108.3
107.5°	132.9	132.9	132.9	132.9	132.7	132.4	132.1	131.8	131.5	131.0	130.5
110°	155.1	155.2	155.3	155.3	155.1	154.8	154.5	154.2	153.9	153.6	153.3

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	176.8	177.0	177.2	177.3	177.2	177.1	177.0	176.9	176.8	176.4	176.0
115°	199.5	199.6	199.7	199.8	199.8	199.9	200.0	200.1	200.2	200.0	199.8
117.5°	222.1	222.5	222.9	223.1	223.1	223.0	222.9	222.8	222.7	222.5	222.3
120°	245.0	245.4	245.8	246.0	246.0	246.0	246.0	246.0	246.0	245.9	245.8
122.5°	267.7	268.0	268.3	268.5	268.5	268.6	268.7	268.8	268.9	268.6	268.3
125°	290.2	290.3	290.4	290.5	290.6	290.8	291.0	291.2	291.4	291.3	291.2
127.5°	312.4	312.6	312.8	312.9	313.0	313.1	313.2	313.3	313.4	313.3	313.2
130°	334.4	334.6	334.8	334.9	335.0	335.1	335.2	335.3	335.4	335.2	335.0
132.5°	355.2	355.5	355.8	356.0	356.0	356.1	356.2	356.3	356.4	356.5	356.6
135°	376.9	377.4	377.8	378.0	378.0	378.0	378.0	378.0	378.0	377.9	377.8
137.5°	398.2	398.7	399.2	399.5	399.5	399.4	399.3	399.2	399.1	398.9	398.7
140°	418.4	418.9	419.4	419.7	419.6	419.4	419.2	419.0	418.8	418.5	418.2
142.5°	437.6	438.1	438.6	438.9	438.9	438.8	438.7	438.6	438.5	438.1	437.7
145°	456.5	456.8	457.1	457.2	457.2	457.2	457.2	457.2	457.2	456.9	456.6
147.5°	473.5	474.4	475.2	475.6	475.4	475.1	474.8	474.5	474.2	474.0	473.8
150°	490.6	490.8	491.0	491.1	491.1	491.1	491.1	491.1	491.1	490.7	490.3
152.5°	506.1	506.6	507.0	507.2	507.0	506.7	506.4	506.1	505.8	505.7	505.6
155°	520.5	521.0	521.5	521.8	521.6	521.2	520.8	520.4	520.0	519.9	519.8
157.5°	532.9	533.6	534.3	534.7	534.5	534.1	533.6	533.2	532.8	532.7	532.6
160°	544.8	545.3	545.8	546.1	545.9	545.5	545.1	544.7	544.3	544.2	544.1
162.5°	555.6	556.2	556.8	557.1	556.8	556.3	555.8	555.3	554.8	554.8	554.8
165°	564.7	565.4	566.0	566.3	566.1	565.7	565.2	564.8	564.4	564.3	564.2
167.5°	572.5	573.2	573.8	574.1	573.8	573.2	572.5	571.9	571.3	571.3	571.3
170°	578.7	579.4	580.1	580.5	580.2	579.6	578.9	578.3	577.7	577.7	577.7
172.5°	583.5	584.2	584.8	585.1	584.8	584.2	583.5	582.9	582.3	582.3	582.3
175°	586.5	587.2	587.9	588.3	588.0	587.4	586.7	586.1	585.5	585.5	585.5
177.5°	588.3	589.0	589.7	590.1	589.8	589.2	588.6	588.0	587.4	587.5	587.6
180°	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9
2.5°	1626.5	1619.8	1611.7	1611.7	1602.3	1598.3	1590.3	1587.6	1580.9	1570.1	1562.1
5°	1684.2	1666.8	1656.0	1646.6	1626.5	1611.7	1597.0	1580.9	1564.8	1546.0	1524.5
7.5°	1740.6	1708.4	1693.6	1677.5	1648.0	1617.1	1587.6	1566.1	1544.6	1515.1	1488.3
10°	1799.6	1759.4	1732.5	1711.0	1665.4	1626.5	1583.6	1552.7	1519.1	1481.6	1446.7
12.5°	1849.3	1796.9	1774.1	1733.9	1681.5	1634.6	1580.9	1533.9	1489.6	1445.3	1402.4
15°	1890.9	1841.2	1784.9	1768.8	1696.3	1629.2	1568.8	1508.4	1453.4	1409.1	1359.4
17.5°	1904.3	1841.2	1813.0	1774.1	1688.2	1618.5	1542.0	1476.2	1423.9	1358.1	1319.2
20°	1908.3	1847.9	1809.0	1772.8	1696.3	1603.7	1528.5	1448.0	1384.9	1319.2	1257.5
22.5°	1897.6	1826.5	1788.9	1754.0	1668.1	1588.9	1501.7	1413.1	1339.3	1278.9	1217.2
25°	1877.5	1794.3	1758.0	1720.4	1638.6	1551.4	1456.1	1371.5	1303.1	1230.6	1170.2
27.5°	1850.6	1755.3	1713.7	1674.8	1594.3	1512.4	1422.5	1335.3	1258.8	1182.3	1125.9
30°	1817.1	1707.0	1669.4	1618.5	1540.6	1462.8	1380.9	1293.7	1207.8	1135.3	1073.6
32.5°	1774.1	1658.7	1609.1	1560.7	1476.2	1405.1	1327.2	1245.4	1162.2	1091.0	1026.6
35°	1735.2	1603.7	1548.7	1500.4	1406.4	1331.3	1266.8	1190.4	1116.5	1042.7	985.0
37.5°	1682.9	1548.7	1482.9	1433.3	1338.0	1261.5	1201.1	1142.0	1064.2	993.1	939.4
40°	1627.8	1480.2	1418.5	1368.8	1269.5	1186.3	1128.6	1076.3	1013.2	947.5	891.1
42.5°	1578.2	1414.5	1348.7	1288.3	1187.7	1113.9	1054.8	1014.6	956.8	897.8	846.8
45°	1515.1	1344.7	1273.6	1210.5	1113.9	1033.3	977.0	944.8	901.8	844.1	799.8
47.5°	1450.7	1269.5	1195.7	1134.0	1029.3	958.2	903.2	872.3	842.8	797.1	752.9
50°	1366.2	1190.4	1123.3	1052.1	948.8	876.3	830.7	799.8	777.0	744.8	707.2
52.5°	1273.6	1108.5	1036.0	974.3	872.3	806.5	754.2	736.8	713.9	689.8	657.6
55°	1175.6	1019.9	950.1	889.7	795.8	728.7	685.8	667.0	649.5	630.7	609.3
57.5°	1077.6	927.3	861.6	807.9	720.7	656.2	621.3	595.8	583.8	573.0	555.6
60°	955.5	828.0	777.0	728.7	642.8	583.8	550.2	531.4	520.7	515.3	507.3
62.5°	848.1	743.5	687.1	640.1	571.7	519.4	487.1	472.4	463.0	460.3	450.9
65°	734.1	644.2	599.9	559.6	500.6	453.6	426.8	409.3	402.6	401.3	401.3
67.5°	626.7	554.2	510.0	481.8	430.8	389.2	363.7	357.0	352.9	347.6	346.2
70°	526.1	468.4	429.4	405.3	359.7	328.8	308.7	297.9	297.9	293.9	291.2
72.5°	437.5	379.8	354.3	334.2	296.6	269.7	255.0	252.3	242.9	241.6	241.6
75°	342.2	299.3	281.8	264.4	236.2	217.4	205.3	198.6	193.2	193.2	194.6
77.5°	257.7	228.1	212.0	198.6	178.5	166.4	157.0	154.3	149.0	149.0	149.0
80°	182.5	166.4	154.3	143.6	128.8	118.1	112.7	107.4	107.4	106.0	107.4
82.5°	118.1	104.7	98.0	96.6	83.2	79.2	72.5	73.8	69.8	68.4	71.1
85°	68.4	61.7	53.7	51.0	45.6	40.3	37.6	38.9	37.6	36.2	37.6
87.5°	26.8	22.8	21.5	21.5	17.4	16.1	14.8	16.1	13.4	13.4	14.8
90°	5.2	4.5	4.1	3.7	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	17.4	16.5	16.0	15.7	15.2	14.7	14.2	13.7	14.2	14.7	15.2
95°	32.2	31.2	30.7	30.6	30.4	30.2	30.0	29.8	30.0	30.2	30.4
97.5°	48.4	47.0	46.3	46.2	46.1	46.0	45.9	45.8	45.9	46.0	46.1
100°	66.1	64.8	64.1	64.1	64.1	64.1	64.1	64.1	64.1	64.1	64.1
102.5°	86.9	86.4	86.1	85.8	85.3	84.8	84.3	83.8	84.3	84.8	85.3
105°	107.6	107.0	106.7	106.5	106.0	105.5	105.0	104.5	105.0	105.5	106.0
107.5°	130.0	129.5	129.2	128.9	128.4	127.9	127.4	126.9	127.4	127.9	128.4
110°	153.0	152.7	152.6	152.3	151.8	151.3	150.8	150.3	150.8	151.3	151.8

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	175.6	175.2	175.0	174.9	174.7	174.5	174.3	174.1	174.3	174.5	174.7
115°	199.6	199.4	199.3	199.1	198.7	198.3	197.9	197.5	197.9	198.3	198.7
117.5°	222.0	221.8	221.7	221.7	221.6	221.5	221.4	221.3	221.4	221.5	221.6
120°	245.7	245.6	245.6	245.3	244.8	244.3	243.8	243.3	243.8	244.3	244.8
122.5°	268.0	267.7	267.6	267.5	267.4	267.3	267.2	267.1	267.2	267.3	267.4
125°	291.1	291.0	290.9	290.6	290.0	289.4	288.8	288.2	288.8	289.4	290.0
127.5°	313.1	313.0	312.9	312.7	312.4	312.1	311.8	311.5	311.8	312.1	312.4
130°	334.8	334.6	334.5	334.2	333.7	333.2	332.7	332.2	332.7	333.2	333.7
132.5°	356.7	356.8	356.9	356.4	355.5	354.6	353.7	352.8	353.7	354.6	355.5
135°	377.7	377.6	377.5	377.2	376.6	376.0	375.4	374.8	375.4	376.0	376.6
137.5°	398.4	398.2	398.1	397.8	397.2	396.6	396.0	395.4	396.0	396.6	397.2
140°	417.9	417.6	417.4	417.1	416.6	416.1	415.6	415.1	415.6	416.1	416.6
142.5°	437.2	436.8	436.6	436.4	436.0	435.6	435.2	434.8	435.2	435.6	436.0
145°	456.3	456.0	455.9	455.7	455.3	454.8	454.4	454.0	454.4	454.8	455.3
147.5°	473.6	473.4	473.3	473.1	472.8	472.5	472.2	471.9	472.2	472.5	472.8
150°	489.9	489.5	489.3	489.4	489.5	489.6	489.7	489.8	489.7	489.6	489.5
152.5°	505.5	505.4	505.3	505.2	505.0	504.8	504.6	504.4	504.6	504.8	505.0
155°	519.7	519.6	519.5	519.5	519.5	519.5	519.5	519.5	519.5	519.5	519.5
157.5°	532.5	532.4	532.4	532.5	532.7	532.9	533.1	533.3	533.1	532.9	532.7
160°	544.0	543.9	543.8	544.0	544.3	544.6	544.9	545.2	544.9	544.6	544.3
162.5°	554.8	554.8	554.8	554.9	555.1	555.3	555.5	555.7	555.5	555.3	555.1
165°	564.1	564.0	564.0	564.1	564.3	564.5	564.7	564.9	564.7	564.5	564.3
167.5°	571.3	571.3	571.3	571.5	571.9	572.3	572.7	573.1	572.7	572.3	571.9
170°	577.7	577.7	577.7	577.9	578.3	578.8	579.2	579.6	579.2	578.8	578.3
172.5°	582.3	582.3	582.3	582.5	582.9	583.3	583.7	584.1	583.7	583.3	582.9
175°	585.5	585.5	585.5	585.7	586.1	586.6	587.0	587.4	587.0	586.6	586.1
177.5°	587.7	587.8	587.8	588.0	588.4	588.8	589.2	589.6	589.2	588.8	588.4
180°	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9
2.5°	1559.4	1556.7	1550.0	1546.0	1532.6	1516.5	1511.1	1497.7	1503.0	1493.6	1493.6
5°	1517.8	1505.7	1497.7	1485.6	1460.1	1442.6	1423.9	1414.5	1409.1	1402.4	1397.0
7.5°	1464.1	1454.7	1446.7	1423.9	1395.7	1371.5	1348.7	1339.3	1321.9	1309.8	1304.4
10°	1417.2	1403.7	1384.9	1358.1	1328.6	1297.7	1277.6	1257.5	1244.0	1237.3	1222.6
12.5°	1368.8	1352.7	1332.6	1293.7	1261.5	1242.7	1206.5	1187.7	1181.0	1175.6	1158.1
15°	1319.2	1301.7	1277.6	1241.3	1213.2	1168.9	1147.4	1132.6	1116.5	1115.2	1101.8
17.5°	1274.9	1253.4	1233.3	1189.0	1154.1	1115.2	1103.1	1087.0	1072.3	1056.2	1049.4
20°	1218.5	1198.4	1183.6	1135.3	1096.4	1072.3	1052.1	1038.7	1029.3	1013.2	1010.5
22.5°	1167.5	1146.1	1125.9	1089.7	1056.2	1025.3	1001.1	986.4	982.3	975.6	963.6
25°	1117.9	1096.4	1072.3	1038.7	1003.8	982.3	960.9	951.5	943.4	932.7	923.3
27.5°	1076.3	1056.2	1033.3	991.7	962.2	946.1	923.3	912.6	901.8	896.5	892.4
30°	1026.6	1003.8	986.4	954.2	922.0	900.5	884.4	875.0	865.6	860.2	857.5
32.5°	978.3	956.8	944.8	909.9	884.4	858.9	846.8	840.1	834.7	829.4	824.0
35°	939.4	917.9	899.1	866.9	841.4	824.0	814.6	803.9	799.8	794.5	794.5
37.5°	891.1	875.0	856.2	825.3	802.5	789.1	781.0	767.6	766.3	763.6	759.6
40°	849.5	833.4	815.9	789.1	769.0	752.9	742.1	735.4	731.4	728.7	726.0
42.5°	805.2	787.8	779.7	748.8	731.4	715.3	709.9	703.2	701.9	696.5	689.8
45°	762.3	747.5	731.4	708.6	693.8	680.4	672.3	667.0	660.3	658.9	654.9
47.5°	724.7	707.2	692.5	671.0	654.9	644.2	637.4	630.7	625.4	621.3	617.3
50°	676.4	662.9	650.9	628.1	614.6	603.9	594.5	589.1	583.8	583.8	583.8
52.5°	629.4	617.3	606.6	590.5	574.4	565.0	554.2	550.2	547.5	543.5	547.5
55°	583.8	571.7	561.0	548.9	530.1	522.0	511.3	507.3	508.6	508.6	512.6
57.5°	535.5	526.1	519.4	504.6	487.1	479.1	472.4	468.4	468.4	473.7	475.1
60°	488.5	479.1	467.0	453.6	442.9	433.5	429.4	430.8	430.8	433.5	440.2
62.5°	436.1	430.8	424.1	405.3	398.6	391.9	386.5	390.5	389.2	395.9	405.3
65°	387.8	382.5	373.1	363.7	355.6	348.9	347.6	348.9	351.6	358.3	369.0
67.5°	334.2	334.2	326.1	318.1	311.3	304.6	306.0	307.3	310.0	318.1	334.2
70°	289.9	284.5	276.5	271.1	265.7	263.0	260.3	265.7	273.8	279.1	291.2
72.5°	241.6	237.5	230.8	225.5	224.1	221.4	220.1	222.8	230.8	240.2	253.6
75°	190.6	191.9	187.9	183.9	183.9	179.8	182.5	182.5	190.6	200.0	210.7
77.5°	147.6	146.3	144.9	142.3	140.9	140.9	140.9	143.6	151.6	157.0	167.7
80°	104.7	106.0	102.0	103.3	102.0	103.3	103.3	108.7	112.7	119.4	127.5
82.5°	69.8	69.8	67.1	68.4	68.4	68.4	69.8	72.5	77.8	83.2	88.6
85°	38.9	40.3	37.6	40.3	40.3	40.3	41.6	42.9	47.0	48.3	53.7
87.5°	14.8	17.4	17.4	14.8	16.1	17.4	18.8	17.4	20.1	22.8	24.2
90°	3.7	4.1	4.5	5.2	5.9	6.6	7.3	7.8	8.3	8.8	9.3
92.5°	15.7	16.0	16.5	17.4	18.3	19.3	20.2	20.9	21.6	22.3	23.0
95°	30.6	30.7	31.2	32.2	33.3	34.3	35.3	36.0	36.7	37.4	38.1
97.5°	46.2	46.3	47.0	48.4	49.9	51.3	52.7	53.3	53.9	54.5	55.1
100°	64.1	64.1	64.8	66.1	67.4	68.8	70.1	71.0	71.9	72.8	73.7
102.5°	85.8	86.1	86.4	86.9	87.4	87.9	88.4	89.4	90.4	91.5	92.5
105°	106.5	106.7	107.0	107.6	108.3	108.9	109.5	110.1	110.7	111.3	111.9
107.5°	128.9	129.2	129.5	130.0	130.5	131.0	131.5	131.8	132.1	132.4	132.7
110°	152.3	152.6	152.7	153.0	153.3	153.6	153.9	154.2	154.5	154.8	155.1

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	174.9	175.0	175.2	175.6	176.0	176.4	176.8	176.9	177.0	177.1	177.2
115°	199.1	199.3	199.4	199.6	199.8	200.0	200.2	200.1	200.0	199.9	199.8
117.5°	221.7	221.7	221.8	222.0	222.3	222.5	222.7	222.8	222.9	223.0	223.1
120°	245.3	245.6	245.6	245.7	245.8	245.9	246.0	246.0	246.0	246.0	246.0
122.5°	267.5	267.6	267.7	268.0	268.3	268.6	268.9	268.8	268.7	268.6	268.5
125°	290.6	290.9	291.0	291.1	291.2	291.3	291.4	291.2	291.0	290.8	290.6
127.5°	312.7	312.9	313.0	313.1	313.2	313.3	313.4	313.3	313.2	313.1	313.0
130°	334.2	334.5	334.6	334.8	335.0	335.2	335.4	335.3	335.2	335.1	335.0
132.5°	356.4	356.9	356.8	356.7	356.6	356.5	356.4	356.3	356.2	356.1	356.0
135°	377.2	377.5	377.6	377.7	377.8	377.9	378.0	378.0	378.0	378.0	378.0
137.5°	397.8	398.1	398.2	398.4	398.7	398.9	399.1	399.2	399.3	399.4	399.5
140°	417.1	417.4	417.6	417.9	418.2	418.5	418.8	419.0	419.2	419.4	419.6
142.5°	436.4	436.6	436.8	437.2	437.7	438.1	438.5	438.6	438.7	438.8	438.9
145°	455.7	455.9	456.0	456.3	456.6	456.9	457.2	457.2	457.2	457.2	457.2
147.5°	473.1	473.3	473.4	473.6	473.8	474.0	474.2	474.5	474.8	475.1	475.4
150°	489.4	489.3	489.5	489.9	490.3	490.7	491.1	491.1	491.1	491.1	491.1
152.5°	505.2	505.3	505.4	505.5	505.6	505.7	505.8	506.1	506.4	506.7	507.0
155°	519.5	519.5	519.6	519.7	519.8	519.9	520.0	520.4	520.8	521.2	521.6
157.5°	532.5	532.4	532.4	532.5	532.6	532.7	532.8	533.2	533.6	534.1	534.5
160°	544.0	543.8	543.9	544.0	544.1	544.2	544.3	544.7	545.1	545.5	545.9
162.5°	554.9	554.8	554.8	554.8	554.8	554.8	554.8	555.3	555.8	556.3	556.8
165°	564.1	564.0	564.0	564.1	564.2	564.3	564.4	564.8	565.2	565.7	566.1
167.5°	571.5	571.3	571.3	571.3	571.3	571.3	571.3	571.9	572.5	573.2	573.8
170°	577.9	577.7	577.7	577.7	577.7	577.7	577.7	578.3	578.9	579.6	580.2
172.5°	582.5	582.3	582.3	582.3	582.3	582.3	582.3	582.9	583.5	584.2	584.8
175°	585.7	585.5	585.5	585.5	585.5	585.5	585.5	586.1	586.7	587.4	588.0
177.5°	588.0	587.8	587.8	587.7	587.6	587.5	587.4	588.0	588.6	589.2	589.8
180°	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9
2.5°	1499.0	1489.6	1488.3	1491.0	1485.6	1493.6	1491.0	1493.6	1486.9	1493.6	1489.6
5°	1395.7	1393.0	1387.6	1380.9	1382.3	1383.6	1390.3	1383.6	1389.0	1390.3	1397.0
7.5°	1299.1	1293.7	1297.7	1295.0	1283.0	1280.3	1283.0	1287.0	1295.0	1300.4	1304.4
10°	1221.2	1218.5	1213.2	1209.1	1202.4	1198.4	1203.8	1198.4	1209.1	1218.5	1218.5
12.5°	1162.2	1151.4	1144.7	1143.4	1128.6	1131.3	1136.7	1140.7	1152.8	1158.1	1158.1
15°	1100.4	1092.4	1089.7	1084.3	1079.0	1084.3	1081.7	1085.7	1091.0	1096.4	1099.1
17.5°	1046.8	1045.4	1046.8	1033.3	1037.4	1030.7	1032.0	1038.7	1034.7	1038.7	1046.8
20°	998.4	1001.1	997.1	991.7	991.7	983.7	993.1	990.4	991.7	999.8	1011.9
22.5°	962.2	960.9	956.8	952.8	947.5	948.8	950.1	947.5	958.2	964.9	966.2
25°	923.3	920.6	919.3	915.2	909.9	915.2	913.9	915.2	917.9	928.7	920.6
27.5°	887.1	881.7	884.4	880.4	879.0	880.4	880.4	881.7	884.4	885.7	887.1
30°	856.2	850.8	849.5	846.8	845.5	846.8	849.5	846.8	857.5	856.2	856.2
32.5°	822.6	818.6	815.9	815.9	814.6	813.3	814.6	815.9	824.0	818.6	824.0
35°	790.4	787.8	787.8	785.1	783.7	783.7	783.7	789.1	786.4	790.4	790.4
37.5°	759.6	759.6	758.2	755.5	754.2	755.5	754.2	756.9	755.5	756.9	758.2
40°	727.4	724.7	723.3	723.3	719.3	715.3	719.3	719.3	720.7	724.7	726.0
42.5°	688.4	689.8	689.8	684.4	684.4	684.4	685.8	687.1	687.1	689.8	689.8
45°	654.9	652.2	652.2	652.2	649.5	650.9	653.6	653.6	653.6	653.6	650.9
47.5°	617.3	617.3	618.7	618.7	622.7	621.3	621.3	620.0	617.3	617.3	618.7
50°	582.4	586.5	587.8	587.8	589.1	590.5	590.5	587.8	586.5	582.4	582.4
52.5°	548.9	551.6	554.2	558.3	561.0	559.6	559.6	556.9	551.6	550.2	548.9
55°	512.6	516.7	522.0	526.1	530.1	531.4	531.4	526.1	520.7	514.0	514.0
57.5°	479.1	483.1	492.5	496.5	501.9	501.9	499.2	495.2	487.1	481.8	477.8
60°	445.5	452.3	459.0	467.0	473.7	475.1	471.0	465.7	456.3	449.6	444.2
62.5°	409.3	416.0	429.4	437.5	442.9	442.9	442.9	436.1	424.1	414.7	406.6
65°	374.4	381.1	393.2	403.9	408.0	412.0	408.0	401.3	391.9	381.1	373.1
67.5°	338.2	346.2	358.3	366.4	371.7	375.8	373.1	367.7	355.6	340.9	335.5
70°	297.9	301.9	319.4	327.4	335.5	338.2	335.5	327.4	315.4	299.3	293.9
72.5°	260.3	264.4	280.5	287.2	293.9	296.6	292.6	287.2	276.5	261.7	255.0
75°	217.4	224.1	232.2	242.9	251.0	253.6	249.6	245.6	232.2	222.8	217.4
77.5°	171.8	178.5	189.2	198.6	206.7	205.3	200.0	201.3	186.5	175.8	171.8
80°	130.2	135.5	143.6	151.6	155.7	155.7	154.3	149.0	143.6	135.5	128.8
82.5°	89.9	96.6	103.3	108.7	108.7	110.0	107.4	106.0	100.6	93.9	92.6
85°	53.7	55.0	60.4	60.4	65.8	63.1	61.7	65.8	60.4	56.4	55.0
87.5°	24.2	22.8	24.2	24.2	22.8	25.5	25.5	24.2	25.5	24.2	24.2
90°	9.6	9.8	10.1	10.4	10.7	11.0	10.7	10.4	10.1	9.8	9.6
92.5°	23.4	23.5	23.7	23.9	24.1	24.3	24.1	23.9	23.7	23.5	23.4
95°	38.5	38.6	38.8	39.0	39.2	39.4	39.2	39.0	38.8	38.6	38.5
97.5°	55.4	55.5	55.6	55.7	55.8	55.9	55.8	55.7	55.6	55.5	55.4
100°	74.2	74.3	74.5	74.7	74.9	75.1	74.9	74.7	74.5	74.3	74.2
102.5°	93.0	93.2	93.5	93.8	94.1	94.4	94.1	93.8	93.5	93.2	93.0
105°	112.2	112.4	112.7	113.0	113.3	113.6	113.3	113.0	112.7	112.4	112.2
107.5°	132.9	132.9	132.9	132.9	132.9	132.9	132.9	132.9	132.9	132.9	132.9
110°	155.3	155.3	155.2	155.1	155.0	154.9	155.0	155.1	155.2	155.3	155.3

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	177.3	177.2	177.0	176.8	176.6	176.4	176.6	176.8	177.0	177.2	177.3
115°	199.8	199.7	199.6	199.5	199.4	199.3	199.4	199.5	199.6	199.7	199.8
117.5°	223.1	222.9	222.5	222.1	221.7	221.3	221.7	222.1	222.5	222.9	223.1
120°	246.0	245.8	245.4	245.0	244.6	244.2	244.6	245.0	245.4	245.8	246.0
122.5°	268.5	268.3	268.0	267.7	267.4	267.1	267.4	267.7	268.0	268.3	268.5
125°	290.5	290.4	290.3	290.2	290.1	290.0	290.1	290.2	290.3	290.4	290.5
127.5°	312.9	312.8	312.6	312.4	312.2	312.0	312.2	312.4	312.6	312.8	312.9
130°	334.9	334.8	334.6	334.4	334.2	334.0	334.2	334.4	334.6	334.8	334.9
132.5°	356.0	355.8	355.5	355.2	354.9	354.6	354.9	355.2	355.5	355.8	356.0
135°	378.0	377.8	377.4	376.9	376.5	376.1	376.5	376.9	377.4	377.8	378.0
137.5°	399.5	399.2	398.7	398.2	397.7	397.2	397.7	398.2	398.7	399.2	399.5
140°	419.7	419.4	418.9	418.4	417.9	417.4	417.9	418.4	418.9	419.4	419.7
142.5°	438.9	438.6	438.1	437.6	437.1	436.6	437.1	437.6	438.1	438.6	438.9
145°	457.2	457.1	456.8	456.5	456.2	455.9	456.2	456.5	456.8	457.1	457.2
147.5°	475.6	475.2	474.4	473.5	472.7	471.9	472.7	473.5	474.4	475.2	475.6
150°	491.1	491.0	490.8	490.6	490.4	490.2	490.4	490.6	490.8	491.0	491.1
152.5°	507.2	507.0	506.6	506.1	505.7	505.3	505.7	506.1	506.6	507.0	507.2
155°	521.8	521.5	521.0	520.5	520.0	519.5	520.0	520.5	521.0	521.5	521.8
157.5°	534.7	534.3	533.6	532.9	532.2	531.5	532.2	532.9	533.6	534.3	534.7
160°	546.1	545.8	545.3	544.8	544.3	543.8	544.3	544.8	545.3	545.8	546.1
162.5°	557.1	556.8	556.2	555.6	555.0	554.4	555.0	555.6	556.2	556.8	557.1
165°	566.3	566.0	565.4	564.7	564.1	563.5	564.1	564.7	565.4	566.0	566.3
167.5°	574.1	573.8	573.2	572.5	571.9	571.3	571.9	572.5	573.2	573.8	574.1
170°	580.5	580.1	579.4	578.7	578.0	577.3	578.0	578.7	579.4	580.1	580.5
172.5°	585.1	584.8	584.2	583.5	582.9	582.3	582.9	583.5	584.2	584.8	585.1
175°	588.3	587.9	587.2	586.5	585.8	585.1	585.8	586.5	587.2	587.9	588.3
177.5°	590.1	589.7	589.0	588.3	587.6	586.9	587.6	588.3	589.0	589.7	590.1
180°	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9	1580.9
2.5°	1501.7	1493.6	1503.0	1491.0	1493.6	1508.4	1507.1	1520.5	1528.5	1527.2	1533.9
5°	1402.4	1402.4	1406.4	1405.1	1418.5	1430.6	1446.7	1460.1	1474.9	1482.9	1492.3
7.5°	1304.4	1317.8	1320.5	1327.2	1343.3	1363.5	1379.6	1399.7	1421.2	1435.9	1446.7
10°	1223.9	1234.6	1245.4	1250.7	1268.2	1295.0	1317.8	1350.1	1376.9	1393.0	1407.8
12.5°	1152.8	1164.9	1170.2	1194.4	1206.5	1223.9	1256.1	1291.0	1320.5	1338.0	1350.1
15°	1101.8	1108.5	1120.6	1135.3	1147.4	1168.9	1195.7	1234.6	1262.8	1277.6	1319.2
17.5°	1058.8	1066.9	1073.6	1080.3	1099.1	1121.9	1147.4	1181.0	1217.2	1242.7	1264.2
20°	1014.6	1018.6	1026.6	1037.4	1050.8	1072.3	1095.1	1130.0	1162.2	1182.3	1210.5
22.5°	962.2	974.3	982.3	990.4	1005.2	1029.3	1050.8	1076.3	1116.5	1139.4	1168.9
25°	931.3	936.7	942.1	951.5	962.2	983.7	1007.8	1034.7	1066.9	1091.0	1116.5
27.5°	891.1	899.1	905.8	917.9	924.6	942.1	964.9	991.7	1030.7	1050.8	1072.3
30°	857.5	865.6	871.0	876.3	885.7	904.5	926.0	947.5	983.7	1009.2	1030.7
32.5°	824.0	832.0	838.7	842.8	852.2	864.2	881.7	908.5	939.4	956.8	985.0
35°	794.5	794.5	802.5	807.9	815.9	826.7	842.8	862.9	895.1	917.9	943.4
37.5°	760.9	762.3	769.0	773.0	781.0	791.8	807.9	826.7	853.5	871.0	896.5
40°	726.0	730.0	732.7	739.4	748.8	752.9	769.0	790.4	817.3	833.4	854.9
42.5°	691.1	693.8	700.5	705.9	713.9	720.7	731.4	751.5	771.6	795.8	813.3
45°	652.2	658.9	662.9	672.3	676.4	683.1	693.8	709.9	734.1	748.8	769.0
47.5°	618.7	621.3	624.0	636.1	644.2	648.2	658.9	668.3	693.8	707.2	726.0
50°	582.4	582.4	586.5	591.8	601.2	609.3	618.7	629.4	649.5	662.9	681.7
52.5°	548.9	544.9	547.5	550.2	559.6	567.7	577.1	591.8	610.6	618.7	634.8
55°	512.6	505.9	510.0	514.0	516.7	527.4	538.1	547.5	562.3	574.4	589.1
57.5°	473.7	472.4	469.7	471.0	477.8	484.5	492.5	504.6	522.0	531.4	539.5
60°	438.8	430.8	428.1	430.8	434.8	438.8	449.6	460.3	475.1	484.5	493.9
62.5°	402.6	394.5	389.2	385.2	389.2	398.6	405.3	413.3	425.4	436.1	444.2
65°	367.7	355.6	350.3	347.6	346.2	352.9	358.3	369.0	379.8	383.8	393.2
67.5°	328.8	318.1	311.3	307.3	307.3	307.3	312.7	323.4	334.2	335.5	344.9
70°	289.9	277.8	271.1	265.7	263.0	265.7	272.4	273.8	283.2	285.8	291.2
72.5°	248.3	237.5	229.5	222.8	224.1	226.8	226.8	229.5	234.8	241.6	241.6
75°	209.4	194.6	190.6	185.2	182.5	182.5	182.5	187.9	191.9	197.3	195.9
77.5°	165.1	157.0	149.0	146.3	142.3	140.9	143.6	143.6	146.3	150.3	151.6
80°	127.5	118.1	112.7	110.0	104.7	103.3	104.7	104.7	108.7	107.4	108.7
82.5°	88.6	81.9	77.8	73.8	71.1	72.5	71.1	71.1	72.5	71.1	71.1
85°	51.0	49.7	47.0	45.6	44.3	41.6	44.3	42.9	41.6	40.3	42.9
87.5°	24.2	22.8	22.8	20.1	20.1	18.8	20.1	20.1	18.8	18.8	18.8
90°	9.3	8.8	8.3	7.8	7.3	6.6	5.9	5.2	4.5	4.1	3.7
92.5°	23.0	22.3	21.6	20.9	20.2	19.3	18.3	17.4	16.5	16.0	15.7
95°	38.1	37.4	36.7	36.0	35.3	34.3	33.3	32.2	31.2	30.7	30.6
97.5°	55.1	54.5	53.9	53.3	52.7	51.3	49.9	48.4	47.0	46.3	46.2
100°	73.7	72.8	71.9	71.0	70.1	68.8	67.4	66.1	64.8	64.1	64.1
102.5°	92.5	91.5	90.4	89.4	88.4	87.9	87.4	86.9	86.4	86.1	85.8
105°	111.9	111.3	110.7	110.1	109.5	108.9	108.3	107.6	107.0	106.7	106.5
107.5°	132.7	132.4	132.1	131.8	131.5	131.0	130.5	130.0	129.5	129.2	128.9
110°	155.1	154.8	154.5	154.2	153.9	153.6	153.3	153.0	152.7	152.6	152.3

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	177.2	177.1	177.0	176.9	176.8	176.4	176.0	175.6	175.2	175.0	174.9
115°	199.8	199.9	200.0	200.1	200.2	200.0	199.8	199.6	199.4	199.3	199.1
117.5°	223.1	223.0	222.9	222.8	222.7	222.5	222.3	222.0	221.8	221.7	221.7
120°	246.0	246.0	246.0	246.0	246.0	245.9	245.8	245.7	245.6	245.6	245.3
122.5°	268.5	268.6	268.7	268.8	268.9	268.6	268.3	268.0	267.7	267.6	267.5
125°	290.6	290.8	291.0	291.2	291.4	291.3	291.2	291.1	291.0	290.9	290.6
127.5°	313.0	313.1	313.2	313.3	313.4	313.3	313.2	313.1	313.0	312.9	312.7
130°	335.0	335.1	335.2	335.3	335.4	335.2	335.0	334.8	334.6	334.5	334.2
132.5°	356.0	356.1	356.2	356.3	356.4	356.5	356.6	356.7	356.8	356.9	356.4
135°	378.0	378.0	378.0	378.0	378.0	377.9	377.8	377.7	377.6	377.5	377.2
137.5°	399.5	399.4	399.3	399.2	399.1	398.9	398.7	398.4	398.2	398.1	397.8
140°	419.6	419.4	419.2	419.0	418.8	418.5	418.2	417.9	417.6	417.4	417.1
142.5°	438.9	438.8	438.7	438.6	438.5	438.1	437.7	437.2	436.8	436.6	436.4
145°	457.2	457.2	457.2	457.2	457.2	456.9	456.6	456.3	456.0	455.9	455.7
147.5°	475.4	475.1	474.8	474.5	474.2	474.0	473.8	473.6	473.4	473.3	473.1
150°	491.1	491.1	491.1	491.1	491.1	490.7	490.3	489.9	489.5	489.3	489.4
152.5°	507.0	506.7	506.4	506.1	505.8	505.7	505.6	505.5	505.4	505.3	505.2
155°	521.6	521.2	520.8	520.4	520.0	519.9	519.8	519.7	519.6	519.5	519.5
157.5°	534.5	534.1	533.6	533.2	532.8	532.7	532.6	532.5	532.4	532.4	532.5
160°	545.9	545.5	545.1	544.7	544.3	544.2	544.1	544.0	543.9	543.8	544.0
162.5°	556.8	556.3	555.8	555.3	554.8	554.8	554.8	554.8	554.8	554.8	554.9
165°	566.1	565.7	565.2	564.8	564.4	564.3	564.2	564.1	564.0	564.0	564.1
167.5°	573.8	573.2	572.5	571.9	571.3	571.3	571.3	571.3	571.3	571.3	571.5
170°	580.2	579.6	578.9	578.3	577.7	577.7	577.7	577.7	577.7	577.7	577.9
172.5°	584.8	584.2	583.5	582.9	582.3	582.3	582.3	582.3	582.3	582.3	582.5
175°	588.0	587.4	586.7	586.1	585.5	585.5	585.5	585.5	585.5	585.5	585.7
177.5°	589.8	589.2	588.6	588.0	587.4	587.5	587.6	587.7	587.8	587.8	588.0
180°	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7	588.7

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1580.9	1580.9	1580.9	1580.9
2.5°	1543.3	1556.7	1566.1	1583.6
5°	1508.4	1532.6	1555.4	1579.5
7.5°	1473.5	1501.7	1537.9	1568.8
10°	1434.6	1470.8	1513.8	1555.4
12.5°	1395.7	1438.6	1485.6	1540.6
15°	1348.7	1403.7	1458.8	1517.8
17.5°	1307.1	1363.5	1422.5	1496.3
20°	1260.1	1321.9	1386.3	1461.4
22.5°	1218.5	1287.0	1354.1	1433.3
25°	1171.6	1238.7	1312.5	1397.0
27.5°	1132.6	1194.4	1266.8	1358.1
30°	1085.7	1152.8	1225.2	1316.5
32.5°	1041.4	1105.8	1182.3	1272.2
35°	995.8	1061.5	1130.0	1215.9
37.5°	952.8	1009.2	1077.6	1159.5
40°	904.5	966.2	1028.0	1092.4
42.5°	860.2	916.6	974.3	1025.3
45°	810.6	858.9	913.9	955.5
47.5°	764.9	807.9	850.8	883.0
50°	719.3	752.9	785.1	813.3
52.5°	665.6	703.2	720.7	738.1
55°	617.3	638.8	654.9	672.3
57.5°	570.3	579.7	587.8	603.9
60°	508.6	519.4	528.7	540.8
62.5°	454.9	460.3	463.0	475.1
65°	403.9	402.6	409.3	416.0
67.5°	348.9	347.6	354.3	357.0
70°	295.2	293.9	295.2	301.9
72.5°	244.2	244.2	245.6	248.3
75°	197.3	197.3	198.6	201.3
77.5°	149.0	151.6	150.3	155.7
80°	108.7	106.0	108.7	111.4
82.5°	71.1	73.8	73.8	71.1
85°	40.3	40.3	40.3	40.3
87.5°	17.4	17.4	18.8	20.1
90°	2.9	2.1	1.3	0.5
92.5°	15.2	14.7	14.2	13.7
95°	30.4	30.2	30.0	29.8
97.5°	46.1	46.0	45.9	45.8
100°	64.1	64.1	64.1	64.1
102.5°	85.3	84.8	84.3	83.8
105°	106.0	105.5	105.0	104.5
107.5°	128.4	127.9	127.4	126.9
110°	151.8	151.3	150.8	150.3

TEST NUMBER: P1035033

CATALOG NUMBER: S125DIW-B1090D470UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	174.7	174.5	174.3	174.1
115°	198.7	198.3	197.9	197.5
117.5°	221.6	221.5	221.4	221.3
120°	244.8	244.3	243.8	243.3
122.5°	267.4	267.3	267.2	267.1
125°	290.0	289.4	288.8	288.2
127.5°	312.4	312.1	311.8	311.5
130°	333.7	333.2	332.7	332.2
132.5°	355.5	354.6	353.7	352.8
135°	376.6	376.0	375.4	374.8
137.5°	397.2	396.6	396.0	395.4
140°	416.6	416.1	415.6	415.1
142.5°	436.0	435.6	435.2	434.8
145°	455.3	454.8	454.4	454.0
147.5°	472.8	472.5	472.2	471.9
150°	489.5	489.6	489.7	489.8
152.5°	505.0	504.8	504.6	504.4
155°	519.5	519.5	519.5	519.5
157.5°	532.7	532.9	533.1	533.3
160°	544.3	544.6	544.9	545.2
162.5°	555.1	555.3	555.5	555.7
165°	564.3	564.5	564.7	564.9
167.5°	571.9	572.3	572.7	573.1
170°	578.3	578.8	579.2	579.6
172.5°	582.9	583.3	583.7	584.1
175°	586.1	586.6	587.0	587.4
177.5°	588.4	588.8	589.2	589.6
180°	588.7	588.7	588.7	588.7

(END OF REPORT)