

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035186

Luminaire Tested: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035186
REPORT IS A COMBINATION OF REPORTS P1003287 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D470UB35-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6867.9 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80
1	104	100	96	92	99	95	92	88	86	84	81	79	77	75	71	70	68
2	95	87	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58
3	87	77	70	64	82	74	67	62	67	62	57	62	57	54	56	53	50
4	80	69	60	54	76	66	58	53	60	54	49	55	50	46	50	46	43
5	73	61	53	47	70	59	51	45	54	48	43	50	44	40	46	41	38
6	68	55	47	41	64	53	45	40	49	42	38	45	40	35	41	37	33
7	63	50	42	36	60	48	40	35	44	38	33	41	36	31	38	33	30
8	58	46	38	32	55	44	36	31	41	34	30	38	32	28	35	30	27
9	54	42	34	29	52	40	33	28	37	31	27	35	29	25	32	27	24
10	51	38	31	26	49	37	30	25	34	28	24	32	27	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11845	11845	11845	11845
5°	11854	13437	11865	10195
10°	11782	15316	11762	8751
15°	11695	16607	11623	7907
20°	11548	18198	11442	7218
25°	11417	20852	11209	6810
30°	11228	21998	11034	6441
35°	10930	17634	10701	6144
40°	10465	12188	10311	5831
45°	9878	9073	9767	5571
50°	9206	7470	9054	5361
55°	8481	6371	8413	5181
60°	7769	5454	7633	5041
65°	7000	4710	6888	4835
70°	6190	3910	6107	4479
75°	5330	3024	5260	3888
80°	4211	2046	4059	2859
85°	2693	1023	2601	1458

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18093 cd/sqm

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	2.6
10°-20°	530.0	7.7
20°-30°	860.9	12.5
30°-40°	1052.2	15.3
40°-50°	954.4	13.9
50°-60°	760.2	11.1
60°-70°	529.4	7.7
70°-80°	282.1	4.1
80°-90°	70.9	1.0
90°-100°	39.3	0.6
100°-110°	116.8	1.7
110°-120°	198.1	2.9
120°-130°	260.8	3.8
130°-140°	292.2	4.3
140°-150°	286.4	4.2
150°-160°	240.6	3.5
160°-170°	159.9	2.3
170°-180°	56.0	0.8
0°-30°	1568.8	22.8
0°-40°	2621.0	38.2
0°-60°	4335.5	63.1
0°-90°	5217.9	76.0
90°-120°	354.2	5.2
90°-150°	1193.6	17.4
90°-180°	1650.0	24.0
0°-180°	6867.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1849	1849	1849	1849	1849	
5°	1847	2133	1849	1618	1847	175
15°	1775	2663	1764	1268	1775	501
25°	1634	3277	1604	1070	1634	752
35°	1422	2630	1392	916	1422	888
45°	1117	1240	1105	761	1117	861
55°	786	764	780	622	786	703
65°	486	469	479	482	486	483
75°	235	231	232	297	235	250
85°	47	52	46	74	47	56
90°	0	11	0	11	0	5
95°	30	40	30	40	30	31
105°	105	114	105	114	105	112
115°	198	200	198	200	198	196
125°	289	291	289	291	289	259
135°	376	378	376	378	376	290
145°	456	458	456	458	456	285
155°	522	522	522	522	522	240
165°	567	566	567	566	567	160
175°	590	588	590	588	590	56
180°	591	591	591	591	591	

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1851.9	1862.9	1875.5	1884.9	1900.6	1905.3	1913.1	1917.8	1922.5	1927.3	1930.4
5°	1847.2	1873.9	1897.4	1914.7	1944.5	1955.5	1969.6	1986.9	2007.3	2024.6	2035.5
7.5°	1834.7	1877.0	1908.4	1942.9	1983.8	2010.4	2024.6	2060.7	2093.6	2118.7	2151.7
10°	1819.0	1869.2	1917.8	1969.6	2027.7	2057.5	2085.8	2136.0	2181.5	2222.3	2255.3
12.5°	1801.7	1862.9	1921.0	1988.5	2066.9	2103.0	2121.9	2208.2	2264.7	2286.7	2351.0
15°	1775.0	1847.2	1930.4	2013.6	2079.5	2121.9	2173.7	2242.7	2299.2	2347.9	2399.7
17.5°	1749.9	1828.4	1913.1	2005.7	2101.5	2156.4	2195.6	2256.8	2318.0	2380.8	2429.5
20°	1709.1	1811.1	1897.4	1996.3	2109.3	2148.5	2189.3	2261.5	2327.5	2394.9	2456.2
22.5°	1676.1	1773.5	1891.2	1985.3	2081.1	2120.3	2170.5	2245.8	2324.3	2401.2	2490.7
25°	1633.8	1742.1	1844.1	1944.5	2043.4	2085.8	2131.3	2228.6	2310.2	2409.1	2507.9
27.5°	1588.3	1699.7	1801.7	1892.7	1985.3	2043.4	2092.0	2194.1	2302.3	2410.6	2539.3
30°	1539.6	1644.8	1742.1	1831.5	1933.5	1993.2	2041.8	2161.1	2281.9	2420.1	2573.9
32.5°	1487.8	1586.7	1669.9	1760.9	1869.2	1924.1	1990.0	2120.3	2263.1	2427.9	2620.9
35°	1421.9	1516.1	1589.8	1682.4	1790.7	1861.3	1930.4	2076.4	2242.7	2426.3	2647.6
37.5°	1356.0	1429.7	1500.4	1599.2	1724.8	1789.1	1861.3	2021.4	2211.3	2421.6	2658.6
40°	1277.5	1349.7	1410.9	1511.4	1643.2	1717.0	1792.3	1960.2	2175.2	2404.4	2619.4
42.5°	1199.0	1260.2	1327.7	1432.9	1560.0	1638.5	1718.5	1905.3	2128.1	2354.1	2511.1
45°	1117.4	1164.5	1238.3	1334.0	1469.0	1544.3	1635.3	1837.8	2062.2	2263.1	2341.6
47.5°	1032.7	1079.8	1148.8	1241.4	1374.8	1464.3	1550.6	1753.0	1979.0	2134.4	2134.4
50°	951.1	988.7	1056.2	1148.8	1283.8	1365.4	1453.3	1668.3	1850.4	1964.9	1862.9
52.5°	863.2	905.6	962.1	1059.4	1192.8	1266.5	1362.3	1545.9	1718.5	1765.6	1608.7
55°	786.3	820.8	874.2	966.8	1090.8	1167.7	1249.3	1425.0	1571.0	1567.9	1399.9
57.5°	706.2	734.5	791.0	875.7	990.3	1059.4	1141.0	1293.2	1412.5	1370.1	1211.6
60°	632.5	652.9	707.8	776.9	886.7	951.1	1029.5	1153.5	1244.6	1184.9	1024.8
62.5°	555.6	579.1	623.1	690.5	787.9	839.6	897.7	1023.3	1081.3	1028.0	864.8
65°	486.5	505.4	544.6	601.1	689.0	736.1	786.3	889.9	944.8	867.9	732.9
67.5°	417.5	439.4	467.7	517.9	587.0	630.9	674.9	764.3	789.4	720.4	607.4
70°	353.1	372.0	398.6	434.7	492.8	532.0	565.0	638.8	656.0	591.7	502.2
72.5°	290.3	302.9	324.9	354.7	408.1	430.0	464.6	514.8	536.7	478.7	414.3
75°	235.4	244.8	259.0	280.9	317.0	340.6	368.8	415.9	414.3	373.5	328.0
77.5°	182.1	183.6	199.3	219.7	241.7	262.1	276.2	309.2	312.3	287.2	249.5
80°	130.3	135.0	141.2	156.9	175.8	183.6	200.9	221.3	224.4	205.6	180.5
82.5°	83.2	86.3	91.0	100.4	113.0	122.4	131.8	139.7	147.5	136.5	116.1
85°	47.1	48.7	53.4	56.5	62.8	67.5	75.3	83.2	81.6	73.8	67.5
87.5°	23.5	23.5	23.5	26.7	29.8	29.8	33.0	34.5	36.1	33.0	29.8
90°	0.5	1.3	2.1	2.9	3.7	4.1	4.5	5.2	5.9	6.7	7.4
92.5°	13.8	14.3	14.8	15.3	15.8	16.1	16.6	17.5	18.4	19.3	20.2
95°	29.9	30.1	30.3	30.5	30.7	30.8	31.3	32.3	33.4	34.4	35.4
97.5°	46.0	46.1	46.2	46.3	46.4	46.5	47.2	48.6	50.1	51.5	52.9
100°	64.4	64.4	64.4	64.4	64.4	64.4	65.1	66.4	67.7	69.1	70.4
102.5°	84.2	84.7	85.2	85.7	86.2	86.5	86.8	87.3	87.8	88.3	88.8
105°	104.9	105.4	105.9	106.4	106.9	107.2	107.5	108.1	108.8	109.4	110.0
107.5°	127.4	127.9	128.4	128.9	129.4	129.7	130.0	130.5	131.0	131.5	132.0
110°	150.9	151.4	151.9	152.4	152.9	153.2	153.4	153.7	154.0	154.3	154.6

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	174.8	175.0	175.2	175.5	175.7	175.8	176.0	176.4	176.8	177.2	177.6
115°	198.3	198.7	199.1	199.5	199.9	200.1	200.2	200.4	200.7	200.9	201.1
117.5°	222.2	222.3	222.4	222.5	222.6	222.7	222.8	223.0	223.2	223.4	223.6
120°	244.3	244.8	245.3	245.8	246.3	246.6	246.7	246.8	246.9	247.0	247.1
122.5°	268.2	268.3	268.4	268.5	268.6	268.7	268.9	269.2	269.5	269.8	270.1
125°	289.4	290.0	290.6	291.3	291.9	292.2	292.2	292.3	292.4	292.5	292.6
127.5°	312.9	313.2	313.5	313.8	314.1	314.2	314.3	314.4	314.5	314.6	314.7
130°	333.6	334.1	334.6	335.1	335.6	335.9	336.0	336.2	336.4	336.6	336.8
132.5°	354.3	355.2	356.1	357.0	357.9	358.4	358.4	358.3	358.2	358.1	358.0
135°	376.4	377.0	377.6	378.2	378.8	379.1	379.2	379.3	379.4	379.5	379.6
137.5°	397.1	397.7	398.3	398.9	399.5	399.8	399.9	400.1	400.3	400.5	400.7
140°	416.9	417.4	417.9	418.4	418.9	419.2	419.3	419.6	419.9	420.2	420.5
142.5°	436.6	437.0	437.4	437.9	438.3	438.5	438.7	439.1	439.5	439.9	440.3
145°	456.0	456.4	456.8	457.2	457.6	457.8	458.0	458.3	458.6	458.9	459.2
147.5°	473.9	474.2	474.5	474.8	475.1	475.3	475.4	475.6	475.8	476.0	476.2
150°	491.8	491.7	491.6	491.5	491.4	491.4	491.6	492.0	492.4	492.8	493.2
152.5°	506.6	506.8	507.0	507.2	507.4	507.5	507.6	507.7	507.8	507.9	508.0
155°	521.8	521.8	521.8	521.8	521.8	521.8	521.8	521.9	522.0	522.1	522.2
157.5°	535.6	535.4	535.2	534.9	534.7	534.6	534.7	534.8	534.9	535.0	535.1
160°	547.5	547.2	546.9	546.6	546.3	546.1	546.2	546.3	546.4	546.5	546.6
162.5°	558.1	557.9	557.7	557.5	557.3	557.2	557.2	557.2	557.2	557.2	557.2
165°	567.3	567.1	566.9	566.7	566.5	566.4	566.4	566.5	566.6	566.7	566.8
167.5°	575.6	575.2	574.8	574.3	573.9	573.7	573.7	573.7	573.7	573.7	573.7
170°	582.0	581.6	581.2	580.8	580.4	580.2	580.2	580.2	580.2	580.2	580.2
172.5°	586.6	586.2	585.8	585.4	585.0	584.8	584.8	584.8	584.8	584.8	584.8
175°	589.9	589.5	589.1	588.6	588.2	588.0	588.0	588.0	588.0	588.0	588.0
177.5°	592.2	591.8	591.4	590.9	590.5	590.3	590.3	590.2	590.1	590.0	589.9
180°	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1933.5	1944.5	1953.9	1961.8	1968.1	1977.5	1971.2	1972.8	1975.9	1982.2	1982.2
5°	2059.1	2076.4	2085.8	2117.2	2125.0	2123.4	2118.7	2143.8	2142.3	2132.8	2131.3
7.5°	2181.5	2211.3	2238.0	2263.1	2271.0	2291.4	2296.1	2307.1	2303.9	2319.6	2311.8
10°	2292.9	2340.0	2365.1	2402.8	2412.2	2421.6	2434.2	2440.5	2454.6	2453.0	2453.0
12.5°	2379.2	2435.7	2468.7	2478.1	2514.2	2525.2	2536.2	2556.6	2551.9	2553.5	2562.9
15°	2446.7	2501.7	2529.9	2573.9	2599.0	2611.5	2630.4	2652.3	2649.2	2663.3	2660.2
17.5°	2497.0	2548.7	2600.5	2666.5	2668.0	2701.0	2744.9	2754.3	2774.7	2760.6	2760.6
20°	2537.8	2606.8	2680.6	2765.3	2774.7	2795.1	2848.5	2884.6	2908.1	2900.3	2905.0
22.5°	2581.7	2680.6	2766.9	2851.6	2897.2	2933.3	2985.0	3041.5	3061.9	3074.5	3071.4
25°	2638.2	2741.8	2868.9	2986.6	3033.7	3102.8	3171.8	3226.7	3242.4	3277.0	3245.6
27.5°	2696.3	2842.2	3000.7	3138.9	3198.5	3255.0	3338.2	3379.0	3399.4	3415.1	3404.1
30°	2744.9	2945.8	3118.4	3245.6	3287.9	3320.9	3368.0	3377.4	3369.6	3382.1	3397.8
32.5°	2820.3	3016.4	3162.4	3223.6	3218.9	3217.3	3181.2	3131.0	3120.0	3090.2	3131.0
35°	2861.1	3018.0	3074.5	2992.9	2959.9	2900.3	2785.7	2710.4	2644.5	2630.4	2633.5
37.5°	2837.5	2898.7	2831.2	2616.2	2562.9	2471.8	2319.6	2212.9	2164.2	2126.6	2175.2
40°	2710.4	2642.9	2457.7	2195.6	2118.7	2032.4	1889.6	1831.5	1762.5	1748.3	1812.7
42.5°	2500.1	2294.5	2032.4	1830.0	1749.9	1701.3	1582.0	1527.1	1478.4	1456.4	1492.5
45°	2214.5	1964.9	1701.3	1534.9	1467.4	1409.3	1338.7	1280.7	1249.3	1239.8	1269.7
47.5°	1919.4	1655.7	1445.4	1321.5	1250.8	1206.9	1141.0	1108.0	1082.9	1086.0	1090.8
50°	1636.9	1396.8	1235.1	1111.2	1076.6	1042.1	998.2	969.9	957.3	962.1	958.9
52.5°	1393.7	1199.0	1062.5	966.8	951.1	918.1	882.0	858.5	853.8	855.3	860.0
55°	1180.2	1028.0	919.7	850.6	833.4	809.8	787.9	772.2	759.6	764.3	762.7
57.5°	1018.6	885.2	802.0	745.5	732.9	718.8	698.4	690.5	685.8	676.4	684.3
60°	875.7	767.4	695.3	660.7	649.7	640.3	618.4	608.9	605.8	601.1	613.6
62.5°	740.8	663.9	608.9	577.5	566.6	557.1	546.2	538.3	539.9	533.6	539.9
65°	634.0	571.3	532.0	503.8	489.7	483.4	481.8	469.3	467.7	469.3	470.8
67.5°	535.2	481.8	452.0	434.7	423.7	417.5	412.8	404.9	411.2	406.5	409.6
70°	445.7	409.6	378.2	361.0	356.3	357.8	350.0	346.8	348.4	345.3	348.4
72.5°	359.4	329.6	317.0	304.5	298.2	296.6	291.9	287.2	291.9	290.3	290.3
75°	287.2	265.2	251.1	243.3	243.3	240.1	232.3	232.3	232.3	230.7	232.3
77.5°	221.3	202.5	196.2	188.3	188.3	183.6	182.1	182.1	178.9	183.6	180.5
80°	164.8	150.7	141.2	136.5	136.5	135.0	131.8	130.3	131.8	130.3	130.3
82.5°	106.7	100.4	95.7	91.0	89.5	91.0	89.5	86.3	87.9	86.3	89.5
85°	61.2	54.9	54.9	51.8	53.4	50.2	51.8	48.7	47.1	51.8	48.7
87.5°	26.7	25.1	25.1	22.0	22.0	22.0	20.4	22.0	20.4	18.8	20.4
90°	7.9	8.4	8.9	9.4	9.7	9.8	10.1	10.4	10.7	11.0	10.7
92.5°	20.9	21.7	22.4	23.1	23.5	23.6	23.8	24.0	24.2	24.4	24.2
95°	36.1	36.8	37.5	38.2	38.6	38.7	38.9	39.2	39.4	39.6	39.4
97.5°	53.5	54.1	54.8	55.4	55.7	55.7	55.8	55.9	56.0	56.1	56.0
100°	71.3	72.2	73.1	74.0	74.5	74.6	74.8	75.1	75.3	75.5	75.3
102.5°	89.8	90.8	91.9	92.9	93.4	93.6	93.9	94.2	94.5	94.8	94.5
105°	110.6	111.2	111.8	112.4	112.7	112.9	113.2	113.5	113.8	114.1	113.8
107.5°	132.3	132.6	132.9	133.2	133.4	133.4	133.4	133.4	133.4	133.4	133.4
110°	154.9	155.2	155.5	155.8	156.0	155.9	155.8	155.7	155.6	155.5	155.6

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	177.7	177.8	177.9	178.0	178.1	178.0	177.8	177.5	177.3	177.1	177.3
115°	201.0	200.9	200.8	200.7	200.6	200.5	200.4	200.3	200.2	200.1	200.2
117.5°	223.7	223.8	223.9	224.0	224.1	223.9	223.5	223.0	222.6	222.2	222.6
120°	247.1	247.1	247.1	247.1	247.1	246.9	246.5	246.0	245.6	245.2	245.6
122.5°	270.0	269.9	269.8	269.7	269.6	269.4	269.1	268.8	268.5	268.2	268.5
125°	292.4	292.2	292.0	291.8	291.7	291.6	291.5	291.4	291.3	291.2	291.3
127.5°	314.6	314.5	314.4	314.3	314.2	314.1	313.9	313.7	313.5	313.3	313.5
130°	336.7	336.6	336.5	336.4	336.3	336.2	336.0	335.8	335.6	335.4	335.6
132.5°	357.9	357.8	357.7	357.6	357.5	357.3	357.0	356.7	356.4	356.1	356.4
135°	379.6	379.6	379.6	379.6	379.6	379.4	379.0	378.5	378.1	377.7	378.1
137.5°	400.8	400.9	401.0	401.1	401.2	400.9	400.4	399.9	399.4	398.9	399.4
140°	420.7	420.9	421.2	421.4	421.5	421.2	420.7	420.2	419.7	419.2	419.7
142.5°	440.4	440.5	440.6	440.7	440.8	440.5	440.0	439.5	439.0	438.5	439.0
145°	459.2	459.2	459.2	459.2	459.2	459.0	458.7	458.4	458.1	457.8	458.1
147.5°	476.5	476.8	477.1	477.4	477.6	477.2	476.4	475.5	474.7	473.9	474.7
150°	493.2	493.2	493.2	493.2	493.2	493.1	492.9	492.7	492.5	492.3	492.5
152.5°	508.3	508.6	508.9	509.2	509.3	509.1	508.7	508.3	507.9	507.5	507.9
155°	522.6	523.0	523.5	523.9	524.1	523.8	523.3	522.8	522.3	521.8	522.3
157.5°	535.5	535.9	536.3	536.7	536.9	536.5	535.8	535.1	534.4	533.7	534.4
160°	547.0	547.4	547.8	548.2	548.4	548.1	547.6	547.1	546.6	546.1	546.6
162.5°	557.7	558.2	558.7	559.2	559.5	559.2	558.6	557.9	557.3	556.7	557.3
165°	567.2	567.6	568.1	568.5	568.7	568.4	567.8	567.1	566.5	565.9	566.5
167.5°	574.3	574.9	575.6	576.2	576.5	576.2	575.6	574.9	574.3	573.7	574.3
170°	580.8	581.4	582.0	582.6	582.9	582.5	581.8	581.1	580.4	579.7	580.4
172.5°	585.4	586.0	586.7	587.3	587.6	587.3	586.7	586.0	585.4	584.8	585.4
175°	588.6	589.2	589.9	590.5	590.8	590.4	589.7	589.0	588.3	587.6	588.3
177.5°	590.5	591.1	591.7	592.3	592.6	592.2	591.5	590.8	590.1	589.4	590.1
180°	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1979.0	1968.1	1971.2	1968.1	1960.2	1955.5	1942.9	1927.3	1921.0	1913.1	1908.4
5°	2137.6	2129.7	2128.1	2115.6	2112.4	2093.6	2062.2	2046.5	2027.7	2008.9	1990.0
7.5°	2310.2	2300.8	2269.4	2264.7	2267.8	2244.3	2203.5	2172.1	2132.8	2106.2	2070.1
10°	2453.0	2434.2	2407.5	2409.1	2398.1	2366.7	2325.9	2292.9	2236.4	2201.9	2150.1
12.5°	2539.3	2523.6	2520.5	2504.8	2495.4	2454.6	2405.9	2363.6	2321.2	2274.1	2234.9
15°	2644.5	2624.1	2610.0	2588.0	2581.7	2539.3	2486.0	2437.3	2388.7	2344.7	2261.5
17.5°	2760.6	2738.6	2685.3	2680.6	2642.9	2602.1	2550.3	2478.1	2426.3	2363.6	2302.3
20°	2892.5	2861.1	2792.0	2774.7	2744.9	2677.4	2606.8	2526.8	2443.6	2379.2	2307.1
22.5°	3040.0	2985.0	2934.8	2879.9	2857.9	2774.7	2677.4	2580.1	2479.7	2391.8	2305.5
25°	3231.4	3159.3	3088.6	3033.7	2996.0	2887.7	2757.5	2628.8	2512.7	2398.1	2285.1
27.5°	3382.1	3319.3	3242.4	3170.2	3121.6	2992.9	2843.8	2677.4	2533.1	2393.4	2272.5
30°	3393.1	3374.3	3327.2	3287.9	3234.6	3096.5	2931.7	2743.4	2564.4	2394.9	2247.4
32.5°	3187.5	3225.2	3245.6	3251.9	3240.9	3160.8	3010.2	2803.0	2592.7	2380.8	2225.4
35°	2744.9	2845.4	2969.4	3016.4	3061.9	3104.3	3025.9	2845.4	2602.1	2377.7	2190.9
37.5°	2260.0	2351.0	2556.6	2650.8	2704.1	2872.0	2936.4	2839.1	2620.9	2380.8	2158.0
40°	1823.7	1968.1	2115.6	2242.7	2325.9	2514.2	2713.5	2735.5	2594.3	2351.0	2115.6
42.5°	1534.9	1619.6	1731.1	1848.8	1922.5	2145.4	2415.3	2573.9	2511.1	2302.3	2063.8
45°	1307.3	1370.1	1475.3	1514.5	1608.7	1822.1	2107.7	2336.9	2368.3	2225.4	2004.2
47.5°	1122.1	1175.5	1243.0	1291.6	1367.0	1527.1	1768.7	2021.4	2172.1	2120.3	1921.0
50°	988.7	1032.7	1089.2	1117.4	1166.1	1310.5	1492.5	1743.6	1946.1	1963.4	1812.7
52.5°	877.3	902.4	946.4	977.8	1017.0	1104.9	1269.7	1476.8	1704.4	1798.6	1679.3
55°	780.0	800.4	839.6	860.0	880.4	955.8	1084.5	1272.8	1486.2	1610.2	1542.7
57.5°	692.1	709.4	742.3	761.2	772.2	844.4	943.2	1090.8	1282.2	1432.9	1395.2
60°	619.9	635.6	654.5	668.6	681.1	740.8	809.8	929.1	1100.2	1246.1	1236.7
62.5°	543.0	557.1	577.5	591.7	602.7	640.3	698.4	789.4	935.4	1070.3	1097.0
65°	475.5	486.5	500.6	506.9	521.0	549.3	596.4	678.0	797.3	918.1	936.9
67.5°	414.3	417.5	426.9	441.0	444.1	469.3	511.6	572.8	665.4	764.3	794.1
70°	348.4	353.1	361.0	372.0	378.2	393.9	430.0	470.8	550.9	637.2	659.2
72.5°	290.3	296.6	299.8	306.0	309.2	334.3	350.0	390.8	445.7	517.9	541.5
75°	235.4	241.7	243.3	246.4	249.5	260.5	282.5	307.6	353.1	400.2	431.6
77.5°	186.8	185.2	188.3	193.0	191.5	200.9	215.0	237.0	266.8	306.0	326.4
80°	131.8	131.8	136.5	141.2	139.7	149.1	153.8	169.5	194.6	219.7	227.6
82.5°	87.9	87.9	92.6	92.6	95.7	97.3	103.6	111.4	131.8	144.4	149.1
85°	50.2	50.2	51.8	51.8	51.8	54.9	59.6	62.8	69.1	76.9	80.0
87.5°	20.4	22.0	22.0	22.0	22.0	25.1	25.1	28.2	29.8	33.0	33.0
90°	10.4	10.1	9.8	9.7	9.4	8.9	8.4	7.9	7.4	6.7	5.9
92.5°	24.0	23.8	23.6	23.5	23.1	22.4	21.7	20.9	20.2	19.3	18.4
95°	39.2	38.9	38.7	38.6	38.2	37.5	36.8	36.1	35.4	34.4	33.4
97.5°	55.9	55.8	55.7	55.7	55.4	54.8	54.1	53.5	52.9	51.5	50.1
100°	75.1	74.8	74.6	74.5	74.0	73.1	72.2	71.3	70.4	69.1	67.7
102.5°	94.2	93.9	93.6	93.4	92.9	91.9	90.8	89.8	88.8	88.3	87.8
105°	113.5	113.2	112.9	112.7	112.4	111.8	111.2	110.6	110.0	109.4	108.8
107.5°	133.4	133.4	133.4	133.4	133.2	132.9	132.6	132.3	132.0	131.5	131.0
110°	155.7	155.8	155.9	156.0	155.8	155.5	155.2	154.9	154.6	154.3	154.0

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	177.5	177.8	178.0	178.1	178.0	177.9	177.8	177.7	177.6	177.2	176.8
115°	200.3	200.4	200.5	200.6	200.7	200.8	200.9	201.0	201.1	200.9	200.7
117.5°	223.0	223.5	223.9	224.1	224.0	223.9	223.8	223.7	223.6	223.4	223.2
120°	246.0	246.5	246.9	247.1	247.1	247.1	247.1	247.1	247.1	247.0	246.9
122.5°	268.8	269.1	269.4	269.6	269.7	269.8	269.9	270.0	270.1	269.8	269.5
125°	291.4	291.5	291.6	291.7	291.8	292.0	292.2	292.4	292.6	292.5	292.4
127.5°	313.7	313.9	314.1	314.2	314.3	314.4	314.5	314.6	314.7	314.6	314.5
130°	335.8	336.0	336.2	336.3	336.4	336.5	336.6	336.7	336.8	336.6	336.4
132.5°	356.7	357.0	357.3	357.5	357.6	357.7	357.8	357.9	358.0	358.1	358.2
135°	378.5	379.0	379.4	379.6	379.6	379.6	379.6	379.6	379.6	379.5	379.4
137.5°	399.9	400.4	400.9	401.2	401.1	401.0	400.9	400.8	400.7	400.5	400.3
140°	420.2	420.7	421.2	421.5	421.4	421.2	420.9	420.7	420.5	420.2	419.9
142.5°	439.5	440.0	440.5	440.8	440.7	440.6	440.5	440.4	440.3	439.9	439.5
145°	458.4	458.7	459.0	459.2	459.2	459.2	459.2	459.2	459.2	458.9	458.6
147.5°	475.5	476.4	477.2	477.6	477.4	477.1	476.8	476.5	476.2	476.0	475.8
150°	492.7	492.9	493.1	493.2	493.2	493.2	493.2	493.2	493.2	492.8	492.4
152.5°	508.3	508.7	509.1	509.3	509.2	508.9	508.6	508.3	508.0	507.9	507.8
155°	522.8	523.3	523.8	524.1	523.9	523.5	523.0	522.6	522.2	522.1	522.0
157.5°	535.1	535.8	536.5	536.9	536.7	536.3	535.9	535.5	535.1	535.0	534.9
160°	547.1	547.6	548.1	548.4	548.2	547.8	547.4	547.0	546.6	546.5	546.4
162.5°	557.9	558.6	559.2	559.5	559.2	558.7	558.2	557.7	557.2	557.2	557.2
165°	567.1	567.8	568.4	568.7	568.5	568.1	567.6	567.2	566.8	566.7	566.6
167.5°	574.9	575.6	576.2	576.5	576.2	575.6	574.9	574.3	573.7	573.7	573.7
170°	581.1	581.8	582.5	582.9	582.6	582.0	581.4	580.8	580.2	580.2	580.2
172.5°	586.0	586.7	587.3	587.6	587.3	586.7	586.0	585.4	584.8	584.8	584.8
175°	589.0	589.7	590.4	590.8	590.5	589.9	589.2	588.6	588.0	588.0	588.0
177.5°	590.8	591.5	592.2	592.6	592.3	591.7	591.1	590.5	589.9	590.0	590.1
180°	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1902.1	1894.3	1884.9	1884.9	1873.9	1869.2	1859.8	1856.6	1848.8	1836.2	1826.8
5°	1969.6	1949.2	1936.7	1925.7	1902.1	1884.9	1867.6	1848.8	1830.0	1808.0	1782.9
7.5°	2035.5	1997.9	1980.6	1961.8	1927.3	1891.2	1856.6	1831.5	1806.4	1771.9	1740.5
10°	2104.6	2057.5	2026.1	2001.0	1947.7	1902.1	1851.9	1815.8	1776.6	1732.6	1691.8
12.5°	2162.7	2101.5	2074.8	2027.7	1966.5	1911.6	1848.8	1793.9	1742.1	1690.3	1640.1
15°	2211.3	2153.3	2087.3	2068.5	1983.8	1905.3	1834.7	1764.0	1699.7	1647.9	1589.8
17.5°	2227.0	2153.3	2120.3	2074.8	1974.3	1892.7	1803.3	1726.4	1665.2	1588.3	1542.7
20°	2231.7	2161.1	2115.6	2073.2	1983.8	1875.5	1787.6	1693.4	1619.6	1542.7	1470.6
22.5°	2219.2	2136.0	2092.0	2051.2	1950.8	1858.2	1756.2	1652.6	1566.3	1495.7	1423.5
25°	2195.6	2098.3	2055.9	2012.0	1916.3	1814.3	1702.8	1604.0	1523.9	1439.2	1368.5
27.5°	2164.2	2052.8	2004.2	1958.6	1864.5	1768.7	1663.6	1561.6	1472.1	1382.7	1316.7
30°	2125.0	1996.3	1952.4	1892.7	1801.7	1710.7	1614.9	1512.9	1412.5	1327.7	1255.5
32.5°	2074.8	1939.8	1881.7	1825.2	1726.4	1643.2	1552.2	1456.4	1359.1	1275.9	1200.6
35°	2029.3	1875.5	1811.1	1754.6	1644.8	1556.9	1481.5	1392.1	1305.8	1219.4	1152.0
37.5°	1968.1	1811.1	1734.2	1676.1	1564.7	1475.3	1404.6	1335.6	1244.6	1161.4	1098.6
40°	1903.7	1731.1	1658.9	1600.8	1484.7	1387.4	1319.9	1258.7	1184.9	1108.0	1042.1
42.5°	1845.6	1654.2	1577.3	1506.6	1388.9	1302.6	1233.6	1186.5	1119.0	1049.9	990.3
45°	1771.9	1572.6	1489.4	1415.6	1302.6	1208.5	1142.5	1104.9	1054.7	987.2	935.4
47.5°	1696.5	1484.7	1398.4	1326.2	1203.7	1120.6	1056.2	1020.1	985.6	932.2	880.4
50°	1597.7	1392.1	1313.6	1230.4	1109.6	1024.8	971.5	935.4	908.7	871.0	827.1
52.5°	1489.4	1296.3	1211.6	1139.4	1020.1	943.2	882.0	861.6	834.9	806.7	769.0
55°	1374.8	1192.8	1111.2	1040.5	930.7	852.2	802.0	780.0	759.6	737.6	712.5
57.5°	1260.2	1084.5	1007.6	944.8	842.8	767.4	726.6	696.8	682.7	670.1	649.7
60°	1117.4	968.3	908.7	852.2	751.8	682.7	643.5	621.5	608.9	602.7	593.2
62.5°	991.9	869.5	803.5	748.6	668.6	607.4	569.7	552.4	541.5	538.3	527.3
65°	858.5	753.3	701.5	654.5	585.4	530.5	499.1	478.7	470.8	469.3	469.3
67.5°	732.9	648.2	596.4	563.4	503.8	455.1	425.3	417.5	412.8	406.5	404.9
70°	615.2	547.7	502.2	474.0	420.6	384.5	361.0	348.4	348.4	343.7	340.6
72.5°	511.6	444.1	414.3	390.8	346.8	315.5	298.2	295.1	284.1	282.5	282.5
75°	400.2	350.0	329.6	309.2	276.2	254.2	240.1	232.3	226.0	226.0	227.6
77.5°	301.3	266.8	248.0	232.3	208.7	194.6	183.6	180.5	174.2	174.2	174.2
80°	213.4	194.6	180.5	167.9	150.7	138.1	131.8	125.6	125.6	124.0	125.6
82.5°	138.1	122.4	114.6	113.0	97.3	92.6	84.7	86.3	81.6	80.0	83.2
85°	80.0	72.2	62.8	59.6	53.4	47.1	43.9	45.5	43.9	42.4	43.9
87.5°	31.4	26.7	25.1	25.1	20.4	18.8	17.3	18.8	15.7	15.7	17.3
90°	5.2	4.5	4.1	3.7	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	17.5	16.6	16.1	15.8	15.3	14.8	14.3	13.8	14.3	14.8	15.3
95°	32.3	31.3	30.8	30.7	30.5	30.3	30.1	29.9	30.1	30.3	30.5
97.5°	48.6	47.2	46.5	46.4	46.3	46.2	46.1	46.0	46.1	46.2	46.3
100°	66.4	65.1	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.4
102.5°	87.3	86.8	86.5	86.2	85.7	85.2	84.7	84.2	84.7	85.2	85.7
105°	108.1	107.5	107.2	106.9	106.4	105.9	105.4	104.9	105.4	105.9	106.4
107.5°	130.5	130.0	129.7	129.4	128.9	128.4	127.9	127.4	127.9	128.4	128.9
110°	153.7	153.4	153.2	152.9	152.4	151.9	151.4	150.9	151.4	151.9	152.4

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	176.4	176.0	175.8	175.7	175.5	175.2	175.0	174.8	175.0	175.2	175.5
115°	200.4	200.2	200.1	199.9	199.5	199.1	198.7	198.3	198.7	199.1	199.5
117.5°	223.0	222.8	222.7	222.6	222.5	222.4	222.3	222.2	222.3	222.4	222.5
120°	246.8	246.7	246.6	246.3	245.8	245.3	244.8	244.3	244.8	245.3	245.8
122.5°	269.2	268.9	268.7	268.6	268.5	268.4	268.3	268.2	268.3	268.4	268.5
125°	292.3	292.2	292.2	291.9	291.3	290.6	290.0	289.4	290.0	290.6	291.3
127.5°	314.4	314.3	314.2	314.1	313.8	313.5	313.2	312.9	313.2	313.5	313.8
130°	336.2	336.0	335.9	335.6	335.1	334.6	334.1	333.6	334.1	334.6	335.1
132.5°	358.3	358.4	358.4	357.9	357.0	356.1	355.2	354.3	355.2	356.1	357.0
135°	379.3	379.2	379.1	378.8	378.2	377.6	377.0	376.4	377.0	377.6	378.2
137.5°	400.1	399.9	399.8	399.5	398.9	398.3	397.7	397.1	397.7	398.3	398.9
140°	419.6	419.3	419.2	418.9	418.4	417.9	417.4	416.9	417.4	417.9	418.4
142.5°	439.1	438.7	438.5	438.3	437.9	437.4	437.0	436.6	437.0	437.4	437.9
145°	458.3	458.0	457.8	457.6	457.2	456.8	456.4	456.0	456.4	456.8	457.2
147.5°	475.6	475.4	475.3	475.1	474.8	474.5	474.2	473.9	474.2	474.5	474.8
150°	492.0	491.6	491.4	491.4	491.5	491.6	491.7	491.8	491.7	491.6	491.5
152.5°	507.7	507.6	507.5	507.4	507.2	507.0	506.8	506.6	506.8	507.0	507.2
155°	521.9	521.8	521.8	521.8	521.8	521.8	521.8	521.8	521.8	521.8	521.8
157.5°	534.8	534.7	534.6	534.7	534.9	535.2	535.4	535.6	535.4	535.2	534.9
160°	546.3	546.2	546.1	546.3	546.6	546.9	547.2	547.5	547.2	546.9	546.6
162.5°	557.2	557.2	557.2	557.3	557.5	557.7	557.9	558.1	557.9	557.7	557.5
165°	566.5	566.4	566.4	566.5	566.7	566.9	567.1	567.3	567.1	566.9	566.7
167.5°	573.7	573.7	573.7	573.9	574.3	574.8	575.2	575.6	575.2	574.8	574.3
170°	580.2	580.2	580.2	580.4	580.8	581.2	581.6	582.0	581.6	581.2	580.8
172.5°	584.8	584.8	584.8	585.0	585.4	585.8	586.2	586.6	586.2	585.8	585.4
175°	588.0	588.0	588.0	588.2	588.6	589.1	589.5	589.9	589.5	589.1	588.6
177.5°	590.2	590.3	590.3	590.5	590.9	591.4	591.8	592.2	591.8	591.4	590.9
180°	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1823.7	1820.5	1812.7	1808.0	1792.3	1773.5	1767.2	1751.5	1757.8	1746.8	1746.8
5°	1775.0	1760.9	1751.5	1737.4	1707.5	1687.1	1665.2	1654.2	1647.9	1640.1	1633.8
7.5°	1712.2	1701.3	1691.8	1665.2	1632.2	1604.0	1577.3	1566.3	1545.9	1531.8	1525.5
10°	1657.3	1641.6	1619.6	1588.3	1553.7	1517.6	1494.1	1470.6	1454.9	1447.0	1429.7
12.5°	1600.8	1582.0	1558.4	1512.9	1475.3	1453.3	1410.9	1388.9	1381.1	1374.8	1354.4
15°	1542.7	1522.3	1494.1	1451.7	1418.8	1367.0	1341.9	1324.6	1305.8	1304.2	1288.5
17.5°	1491.0	1465.8	1442.3	1390.5	1349.7	1304.2	1290.1	1271.2	1254.0	1235.1	1227.3
20°	1425.0	1401.5	1384.2	1327.7	1282.2	1254.0	1230.4	1214.7	1203.7	1184.9	1181.8
22.5°	1365.4	1340.3	1316.7	1274.4	1235.1	1199.0	1170.8	1153.5	1148.8	1141.0	1126.8
25°	1307.3	1282.2	1254.0	1214.7	1173.9	1148.8	1123.7	1112.7	1103.3	1090.8	1079.8
27.5°	1258.7	1235.1	1208.5	1159.8	1125.3	1106.4	1079.8	1067.2	1054.7	1048.4	1043.7
30°	1200.6	1173.9	1153.5	1115.9	1078.2	1053.1	1034.3	1023.3	1012.3	1006.0	1002.9
32.5°	1144.1	1119.0	1104.9	1064.1	1034.3	1004.4	990.3	982.5	976.2	969.9	963.6
35°	1098.6	1073.5	1051.5	1013.8	984.0	963.6	952.6	940.1	935.4	929.1	929.1
37.5°	1042.1	1023.3	1001.3	965.2	938.5	922.8	913.4	897.7	896.1	893.0	888.3
40°	993.4	974.6	954.2	922.8	899.3	880.4	867.9	860.0	855.3	852.2	849.1
42.5°	941.7	921.3	911.8	875.7	855.3	836.5	830.2	822.4	820.8	814.5	806.7
45°	891.4	874.2	855.3	828.7	811.4	795.7	786.3	780.0	772.2	770.6	765.9
47.5°	847.5	827.1	809.8	784.7	765.9	753.3	745.5	737.6	731.4	726.6	721.9
50°	791.0	775.3	761.2	734.5	718.8	706.2	695.3	689.0	682.7	682.7	682.7
52.5°	736.1	721.9	709.4	690.5	671.7	660.7	648.2	643.5	640.3	635.6	640.3
55°	682.7	668.6	656.0	641.9	619.9	610.5	598.0	593.2	594.8	594.8	599.5
57.5°	626.2	615.2	607.4	590.1	569.7	560.3	552.4	547.7	547.7	554.0	555.6
60°	571.3	560.3	546.2	530.5	517.9	506.9	502.2	503.8	503.8	506.9	514.8
62.5°	510.1	503.8	495.9	474.0	466.1	458.3	452.0	456.7	455.1	463.0	474.0
65°	453.6	447.3	436.3	425.3	415.9	408.1	406.5	408.1	411.2	419.0	431.6
67.5°	390.8	390.8	381.4	372.0	364.1	356.3	357.8	359.4	362.5	372.0	390.8
70°	339.0	332.7	323.3	317.0	310.7	307.6	304.5	310.7	320.2	326.4	340.6
72.5°	282.5	277.8	269.9	263.7	262.1	259.0	257.4	260.5	269.9	280.9	296.6
75°	222.9	224.4	219.7	215.0	215.0	210.3	213.4	213.4	222.9	233.8	246.4
77.5°	172.6	171.1	169.5	166.4	164.8	164.8	164.8	167.9	177.3	183.6	196.2
80°	122.4	124.0	119.3	120.8	119.3	120.8	120.8	127.1	131.8	139.7	149.1
82.5°	81.6	81.6	78.5	80.0	80.0	80.0	81.6	84.7	91.0	97.3	103.6
85°	45.5	47.1	43.9	47.1	47.1	47.1	48.7	50.2	54.9	56.5	62.8
87.5°	17.3	20.4	20.4	17.3	18.8	20.4	22.0	20.4	23.5	26.7	28.2
90°	3.7	4.1	4.5	5.2	5.9	6.7	7.4	7.9	8.4	8.9	9.4
92.5°	15.8	16.1	16.6	17.5	18.4	19.3	20.2	20.9	21.7	22.4	23.1
95°	30.7	30.8	31.3	32.3	33.4	34.4	35.4	36.1	36.8	37.5	38.2
97.5°	46.4	46.5	47.2	48.6	50.1	51.5	52.9	53.5	54.1	54.8	55.4
100°	64.4	64.4	65.1	66.4	67.7	69.1	70.4	71.3	72.2	73.1	74.0
102.5°	86.2	86.5	86.8	87.3	87.8	88.3	88.8	89.8	90.8	91.9	92.9
105°	106.9	107.2	107.5	108.1	108.8	109.4	110.0	110.6	111.2	111.8	112.4
107.5°	129.4	129.7	130.0	130.5	131.0	131.5	132.0	132.3	132.6	132.9	133.2
110°	152.9	153.2	153.4	153.7	154.0	154.3	154.6	154.9	155.2	155.5	155.8

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	175.7	175.8	176.0	176.4	176.8	177.2	177.6	177.7	177.8	177.9	178.0
115°	199.9	200.1	200.2	200.4	200.7	200.9	201.1	201.0	200.9	200.8	200.7
117.5°	222.6	222.7	222.8	223.0	223.2	223.4	223.6	223.7	223.8	223.9	224.0
120°	246.3	246.6	246.7	246.8	246.9	247.0	247.1	247.1	247.1	247.1	247.1
122.5°	268.6	268.7	268.9	269.2	269.5	269.8	270.1	270.0	269.9	269.8	269.7
125°	291.9	292.2	292.2	292.3	292.4	292.5	292.6	292.4	292.2	292.0	291.8
127.5°	314.1	314.2	314.3	314.4	314.5	314.6	314.7	314.6	314.5	314.4	314.3
130°	335.6	335.9	336.0	336.2	336.4	336.6	336.8	336.7	336.6	336.5	336.4
132.5°	357.9	358.4	358.4	358.3	358.2	358.1	358.0	357.9	357.8	357.7	357.6
135°	378.8	379.1	379.2	379.3	379.4	379.5	379.6	379.6	379.6	379.6	379.6
137.5°	399.5	399.8	399.9	400.1	400.3	400.5	400.7	400.8	400.9	401.0	401.1
140°	418.9	419.2	419.3	419.6	419.9	420.2	420.5	420.7	420.9	421.2	421.4
142.5°	438.3	438.5	438.7	439.1	439.5	439.9	440.3	440.4	440.5	440.6	440.7
145°	457.6	457.8	458.0	458.3	458.6	458.9	459.2	459.2	459.2	459.2	459.2
147.5°	475.1	475.3	475.4	475.6	475.8	476.0	476.2	476.5	476.8	477.1	477.4
150°	491.4	491.4	491.6	492.0	492.4	492.8	493.2	493.2	493.2	493.2	493.2
152.5°	507.4	507.5	507.6	507.7	507.8	507.9	508.0	508.3	508.6	508.9	509.2
155°	521.8	521.8	521.8	521.9	522.0	522.1	522.2	522.6	523.0	523.5	523.9
157.5°	534.7	534.6	534.7	534.8	534.9	535.0	535.1	535.5	535.9	536.3	536.7
160°	546.3	546.1	546.2	546.3	546.4	546.5	546.6	547.0	547.4	547.8	548.2
162.5°	557.3	557.2	557.2	557.2	557.2	557.2	557.2	557.7	558.2	558.7	559.2
165°	566.5	566.4	566.4	566.5	566.6	566.7	566.8	567.2	567.6	568.1	568.5
167.5°	573.9	573.7	573.7	573.7	573.7	573.7	573.7	574.3	574.9	575.6	576.2
170°	580.4	580.2	580.2	580.2	580.2	580.2	580.2	580.8	581.4	582.0	582.6
172.5°	585.0	584.8	584.8	584.8	584.8	584.8	584.8	585.4	586.0	586.7	587.3
175°	588.2	588.0	588.0	588.0	588.0	588.0	588.0	588.6	589.2	589.9	590.5
177.5°	590.5	590.3	590.3	590.2	590.1	590.0	589.9	590.5	591.1	591.7	592.3
180°	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1753.0	1742.1	1740.5	1743.6	1737.4	1746.8	1743.6	1746.8	1738.9	1746.8	1742.1
5°	1632.2	1629.1	1622.8	1614.9	1616.5	1618.1	1625.9	1618.1	1624.4	1625.9	1633.8
7.5°	1519.2	1512.9	1517.6	1514.5	1500.4	1497.2	1500.4	1505.1	1514.5	1520.8	1525.5
10°	1428.2	1425.0	1418.8	1414.1	1406.2	1401.5	1407.8	1401.5	1414.1	1425.0	1425.0
12.5°	1359.1	1346.6	1338.7	1337.2	1319.9	1323.0	1329.3	1334.0	1348.1	1354.4	1354.4
15°	1286.9	1277.5	1274.4	1268.1	1261.8	1268.1	1265.0	1269.7	1275.9	1282.2	1285.4
17.5°	1224.2	1222.6	1224.2	1208.5	1213.2	1205.3	1206.9	1214.7	1210.0	1214.7	1224.2
20°	1167.7	1170.8	1166.1	1159.8	1159.8	1150.4	1161.4	1158.2	1159.8	1169.2	1183.3
22.5°	1125.3	1123.7	1119.0	1114.3	1108.0	1109.6	1111.2	1108.0	1120.6	1128.4	1130.0
25°	1079.8	1076.6	1075.1	1070.3	1064.1	1070.3	1068.8	1070.3	1073.5	1086.0	1076.6
27.5°	1037.4	1031.1	1034.3	1029.5	1028.0	1029.5	1029.5	1031.1	1034.3	1035.8	1037.4
30°	1001.3	995.0	993.4	990.3	988.7	990.3	993.4	990.3	1002.9	1001.3	1001.3
32.5°	962.1	957.3	954.2	954.2	952.6	951.1	952.6	954.2	963.6	957.3	963.6
35°	924.4	921.3	921.3	918.1	916.5	916.5	916.5	922.8	919.7	924.4	924.4
37.5°	888.3	888.3	886.7	883.6	882.0	883.6	882.0	885.2	883.6	885.2	886.7
40°	850.6	847.5	845.9	845.9	841.2	836.5	841.2	841.2	842.8	847.5	849.1
42.5°	805.1	806.7	806.7	800.4	800.4	800.4	802.0	803.5	803.5	806.7	806.7
45°	765.9	762.7	762.7	762.7	759.6	761.2	764.3	764.3	764.3	764.3	761.2
47.5°	721.9	721.9	723.5	723.5	728.2	726.6	726.6	725.1	721.9	721.9	723.5
50°	681.1	685.8	687.4	687.4	689.0	690.5	690.5	687.4	685.8	681.1	681.1
52.5°	641.9	645.0	648.2	652.9	656.0	654.5	654.5	651.3	645.0	643.5	641.9
55°	599.5	604.2	610.5	615.2	619.9	621.5	621.5	615.2	608.9	601.1	601.1
57.5°	560.3	565.0	576.0	580.7	587.0	587.0	583.8	579.1	569.7	563.4	558.7
60°	521.0	528.9	536.7	546.2	554.0	555.6	550.9	544.6	533.6	525.8	519.5
62.5°	478.7	486.5	502.2	511.6	517.9	517.9	517.9	510.1	495.9	485.0	475.5
65°	437.9	445.7	459.8	472.4	477.1	481.8	477.1	469.3	458.3	445.7	436.3
67.5°	395.5	404.9	419.0	428.5	434.7	439.4	436.3	430.0	415.9	398.6	392.4
70°	348.4	353.1	373.5	382.9	392.4	395.5	392.4	382.9	368.8	350.0	343.7
72.5°	304.5	309.2	328.0	335.9	343.7	346.8	342.1	335.9	323.3	306.0	298.2
75°	254.2	262.1	271.5	284.1	293.5	296.6	291.9	287.2	271.5	260.5	254.2
77.5°	200.9	208.7	221.3	232.3	241.7	240.1	233.8	235.4	218.2	205.6	200.9
80°	152.2	158.5	167.9	177.3	182.1	182.1	180.5	174.2	167.9	158.5	150.7
82.5°	105.2	113.0	120.8	127.1	127.1	128.7	125.6	124.0	117.7	109.9	108.3
85°	62.8	64.3	70.6	70.6	76.9	73.8	72.2	76.9	70.6	65.9	64.3
87.5°	28.2	26.7	28.2	28.2	26.7	29.8	29.8	28.2	29.8	28.2	28.2
90°	9.7	9.8	10.1	10.4	10.7	11.0	10.7	10.4	10.1	9.8	9.7
92.5°	23.5	23.6	23.8	24.0	24.2	24.4	24.2	24.0	23.8	23.6	23.5
95°	38.6	38.7	38.9	39.2	39.4	39.6	39.4	39.2	38.9	38.7	38.6
97.5°	55.7	55.7	55.8	55.9	56.0	56.1	56.0	55.9	55.8	55.7	55.7
100°	74.5	74.6	74.8	75.1	75.3	75.5	75.3	75.1	74.8	74.6	74.5
102.5°	93.4	93.6	93.9	94.2	94.5	94.8	94.5	94.2	93.9	93.6	93.4
105°	112.7	112.9	113.2	113.5	113.8	114.1	113.8	113.5	113.2	112.9	112.7
107.5°	133.4	133.4	133.4	133.4	133.4	133.4	133.4	133.4	133.4	133.4	133.4
110°	156.0	155.9	155.8	155.7	155.6	155.5	155.6	155.7	155.8	155.9	156.0

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	178.1	178.0	177.8	177.5	177.3	177.1	177.3	177.5	177.8	178.0	178.1
115°	200.6	200.5	200.4	200.3	200.2	200.1	200.2	200.3	200.4	200.5	200.6
117.5°	224.1	223.9	223.5	223.0	222.6	222.2	222.6	223.0	223.5	223.9	224.1
120°	247.1	246.9	246.5	246.0	245.6	245.2	245.6	246.0	246.5	246.9	247.1
122.5°	269.6	269.4	269.1	268.8	268.5	268.2	268.5	268.8	269.1	269.4	269.6
125°	291.7	291.6	291.5	291.4	291.3	291.2	291.3	291.4	291.5	291.6	291.7
127.5°	314.2	314.1	313.9	313.7	313.5	313.3	313.5	313.7	313.9	314.1	314.2
130°	336.3	336.2	336.0	335.8	335.6	335.4	335.6	335.8	336.0	336.2	336.3
132.5°	357.5	357.3	357.0	356.7	356.4	356.1	356.4	356.7	357.0	357.3	357.5
135°	379.6	379.4	379.0	378.5	378.1	377.7	378.1	378.5	379.0	379.4	379.6
137.5°	401.2	400.9	400.4	399.9	399.4	398.9	399.4	399.9	400.4	400.9	401.2
140°	421.5	421.2	420.7	420.2	419.7	419.2	419.7	420.2	420.7	421.2	421.5
142.5°	440.8	440.5	440.0	439.5	439.0	438.5	439.0	439.5	440.0	440.5	440.8
145°	459.2	459.0	458.7	458.4	458.1	457.8	458.1	458.4	458.7	459.0	459.2
147.5°	477.6	477.2	476.4	475.5	474.7	473.9	474.7	475.5	476.4	477.2	477.6
150°	493.2	493.1	492.9	492.7	492.5	492.3	492.5	492.7	492.9	493.1	493.2
152.5°	509.3	509.1	508.7	508.3	507.9	507.5	507.9	508.3	508.7	509.1	509.3
155°	524.1	523.8	523.3	522.8	522.3	521.8	522.3	522.8	523.3	523.8	524.1
157.5°	536.9	536.5	535.8	535.1	534.4	533.7	534.4	535.1	535.8	536.5	536.9
160°	548.4	548.1	547.6	547.1	546.6	546.1	546.6	547.1	547.6	548.1	548.4
162.5°	559.5	559.2	558.6	557.9	557.3	556.7	557.3	557.9	558.6	559.2	559.5
165°	568.7	568.4	567.8	567.1	566.5	565.9	566.5	567.1	567.8	568.4	568.7
167.5°	576.5	576.2	575.6	574.9	574.3	573.7	574.3	574.9	575.6	576.2	576.5
170°	582.9	582.5	581.8	581.1	580.4	579.7	580.4	581.1	581.8	582.5	582.9
172.5°	587.6	587.3	586.7	586.0	585.4	584.8	585.4	586.0	586.7	587.3	587.6
175°	590.8	590.4	589.7	589.0	588.3	587.6	588.3	589.0	589.7	590.4	590.8
177.5°	592.6	592.2	591.5	590.8	590.1	589.4	590.1	590.8	591.5	592.2	592.6
180°	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1756.2	1746.8	1757.8	1743.6	1746.8	1764.0	1762.5	1778.2	1787.6	1786.0	1793.9
5°	1640.1	1640.1	1644.8	1643.2	1658.9	1673.0	1691.8	1707.5	1724.8	1734.2	1745.2
7.5°	1525.5	1541.2	1544.3	1552.2	1571.0	1594.5	1613.4	1636.9	1662.0	1679.3	1691.8
10°	1431.3	1443.9	1456.4	1462.7	1483.1	1514.5	1541.2	1578.8	1610.2	1629.1	1646.3
12.5°	1348.1	1362.3	1368.5	1396.8	1410.9	1431.3	1469.0	1509.8	1544.3	1564.7	1578.8
15°	1288.5	1296.3	1310.5	1327.7	1341.9	1367.0	1398.4	1443.9	1476.8	1494.1	1542.7
17.5°	1238.3	1247.7	1255.5	1263.4	1285.4	1312.0	1341.9	1381.1	1423.5	1453.3	1478.4
20°	1186.5	1191.2	1200.6	1213.2	1228.9	1254.0	1280.7	1321.5	1359.1	1382.7	1415.6
22.5°	1125.3	1139.4	1148.8	1158.2	1175.5	1203.7	1228.9	1258.7	1305.8	1332.4	1367.0
25°	1089.2	1095.5	1101.7	1112.7	1125.3	1150.4	1178.6	1210.0	1247.7	1275.9	1305.8
27.5°	1042.1	1051.5	1059.4	1073.5	1081.3	1101.7	1128.4	1159.8	1205.3	1228.9	1254.0
30°	1002.9	1012.3	1018.6	1024.8	1035.8	1057.8	1082.9	1108.0	1150.4	1180.2	1205.3
32.5°	963.6	973.0	980.9	985.6	996.6	1010.7	1031.1	1062.5	1098.6	1119.0	1152.0
35°	929.1	929.1	938.5	944.8	954.2	966.8	985.6	1009.1	1046.8	1073.5	1103.3
37.5°	889.9	891.4	899.3	904.0	913.4	926.0	944.8	966.8	998.2	1018.6	1048.4
40°	849.1	853.8	856.9	864.8	875.7	880.4	899.3	924.4	955.8	974.6	999.7
42.5°	808.3	811.4	819.2	825.5	834.9	842.8	855.3	878.9	902.4	930.7	951.1
45°	762.7	770.6	775.3	786.3	791.0	798.8	811.4	830.2	858.5	875.7	899.3
47.5°	723.5	726.6	729.8	743.9	753.3	758.0	770.6	781.6	811.4	827.1	849.1
50°	681.1	681.1	685.8	692.1	703.1	712.5	723.5	736.1	759.6	775.3	797.3
52.5°	641.9	637.2	640.3	643.5	654.5	663.9	674.9	692.1	714.1	723.5	742.3
55°	599.5	591.7	596.4	601.1	604.2	616.8	629.3	640.3	657.6	671.7	689.0
57.5°	554.0	552.4	549.3	550.9	558.7	566.6	576.0	590.1	610.5	621.5	630.9
60°	513.2	503.8	500.6	503.8	508.5	513.2	525.8	538.3	555.6	566.6	577.5
62.5°	470.8	461.4	455.1	450.4	455.1	466.1	474.0	483.4	497.5	510.1	519.5
65°	430.0	415.9	409.6	406.5	404.9	412.8	419.0	431.6	444.1	448.9	459.8
67.5°	384.5	372.0	364.1	359.4	359.4	359.4	365.7	378.2	390.8	392.4	403.3
70°	339.0	324.9	317.0	310.7	307.6	310.7	318.6	320.2	331.1	334.3	340.6
72.5°	290.3	277.8	268.4	260.5	262.1	265.2	265.2	268.4	274.6	282.5	282.5
75°	244.8	227.6	222.9	216.6	213.4	213.4	213.4	219.7	224.4	230.7	229.1
77.5°	193.0	183.6	174.2	171.1	166.4	164.8	167.9	167.9	171.1	175.8	177.3
80°	149.1	138.1	131.8	128.7	122.4	120.8	122.4	122.4	127.1	125.6	127.1
82.5°	103.6	95.7	91.0	86.3	83.2	84.7	83.2	83.2	84.7	83.2	83.2
85°	59.6	58.1	54.9	53.4	51.8	48.7	51.8	50.2	48.7	47.1	50.2
87.5°	28.2	26.7	26.7	23.5	23.5	22.0	23.5	23.5	22.0	22.0	22.0
90°	9.4	8.9	8.4	7.9	7.4	6.7	5.9	5.2	4.5	4.1	3.7
92.5°	23.1	22.4	21.7	20.9	20.2	19.3	18.4	17.5	16.6	16.1	15.8
95°	38.2	37.5	36.8	36.1	35.4	34.4	33.4	32.3	31.3	30.8	30.7
97.5°	55.4	54.8	54.1	53.5	52.9	51.5	50.1	48.6	47.2	46.5	46.4
100°	74.0	73.1	72.2	71.3	70.4	69.1	67.7	66.4	65.1	64.4	64.4
102.5°	92.9	91.9	90.8	89.8	88.8	88.3	87.8	87.3	86.8	86.5	86.2
105°	112.4	111.8	111.2	110.6	110.0	109.4	108.8	108.1	107.5	107.2	106.9
107.5°	133.2	132.9	132.6	132.3	132.0	131.5	131.0	130.5	130.0	129.7	129.4
110°	155.8	155.5	155.2	154.9	154.6	154.3	154.0	153.7	153.4	153.2	152.9

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	178.0	177.9	177.8	177.7	177.6	177.2	176.8	176.4	176.0	175.8	175.7
115°	200.7	200.8	200.9	201.0	201.1	200.9	200.7	200.4	200.2	200.1	199.9
117.5°	224.0	223.9	223.8	223.7	223.6	223.4	223.2	223.0	222.8	222.7	222.6
120°	247.1	247.1	247.1	247.1	247.1	247.0	246.9	246.8	246.7	246.6	246.3
122.5°	269.7	269.8	269.9	270.0	270.1	269.8	269.5	269.2	268.9	268.7	268.6
125°	291.8	292.0	292.2	292.4	292.6	292.5	292.4	292.3	292.2	292.2	291.9
127.5°	314.3	314.4	314.5	314.6	314.7	314.6	314.5	314.4	314.3	314.2	314.1
130°	336.4	336.5	336.6	336.7	336.8	336.6	336.4	336.2	336.0	335.9	335.6
132.5°	357.6	357.7	357.8	357.9	358.0	358.1	358.2	358.3	358.4	358.4	357.9
135°	379.6	379.6	379.6	379.6	379.6	379.5	379.4	379.3	379.2	379.1	378.8
137.5°	401.1	401.0	400.9	400.8	400.7	400.5	400.3	400.1	399.9	399.8	399.5
140°	421.4	421.2	420.9	420.7	420.5	420.2	419.9	419.6	419.3	419.2	418.9
142.5°	440.7	440.6	440.5	440.4	440.3	439.9	439.5	439.1	438.7	438.5	438.3
145°	459.2	459.2	459.2	459.2	459.2	458.9	458.6	458.3	458.0	457.8	457.6
147.5°	477.4	477.1	476.8	476.5	476.2	476.0	475.8	475.6	475.4	475.3	475.1
150°	493.2	493.2	493.2	493.2	493.2	492.8	492.4	492.0	491.6	491.4	491.4
152.5°	509.2	508.9	508.6	508.3	508.0	507.9	507.8	507.7	507.6	507.5	507.4
155°	523.9	523.5	523.0	522.6	522.2	522.1	522.0	521.9	521.8	521.8	521.8
157.5°	536.7	536.3	535.9	535.5	535.1	535.0	534.9	534.8	534.7	534.6	534.7
160°	548.2	547.8	547.4	547.0	546.6	546.5	546.4	546.3	546.2	546.1	546.3
162.5°	559.2	558.7	558.2	557.7	557.2	557.2	557.2	557.2	557.2	557.2	557.3
165°	568.5	568.1	567.6	567.2	566.8	566.7	566.6	566.5	566.4	566.4	566.5
167.5°	576.2	575.6	574.9	574.3	573.7	573.7	573.7	573.7	573.7	573.7	573.9
170°	582.6	582.0	581.4	580.8	580.2	580.2	580.2	580.2	580.2	580.2	580.4
172.5°	587.3	586.7	586.0	585.4	584.8	584.8	584.8	584.8	584.8	584.8	585.0
175°	590.5	589.9	589.2	588.6	588.0	588.0	588.0	588.0	588.0	588.0	588.2
177.5°	592.3	591.7	591.1	590.5	589.9	590.0	590.1	590.2	590.3	590.3	590.5
180°	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2	591.2

TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.8	1848.8	1848.8	1848.8
2.5°	1804.8	1820.5	1831.5	1851.9
5°	1764.0	1792.3	1819.0	1847.2
7.5°	1723.2	1756.2	1798.6	1834.7
10°	1677.7	1720.1	1770.3	1819.0
12.5°	1632.2	1682.4	1737.4	1801.7
15°	1577.3	1641.6	1706.0	1775.0
17.5°	1528.6	1594.5	1663.6	1749.9
20°	1473.7	1545.9	1621.2	1709.1
22.5°	1425.0	1505.1	1583.6	1676.1
25°	1370.1	1448.6	1534.9	1633.8
27.5°	1324.6	1396.8	1481.5	1588.3
30°	1269.7	1348.1	1432.9	1539.6
32.5°	1217.9	1293.2	1382.7	1487.8
35°	1164.5	1241.4	1321.5	1421.9
37.5°	1114.3	1180.2	1260.2	1356.0
40°	1057.8	1130.0	1202.2	1277.5
42.5°	1006.0	1071.9	1139.4	1199.0
45°	947.9	1004.4	1068.8	1117.4
47.5°	894.6	944.8	995.0	1032.7
50°	841.2	880.4	918.1	951.1
52.5°	778.4	822.4	842.8	863.2
55°	721.9	747.0	765.9	786.3
57.5°	667.0	678.0	687.4	706.2
60°	594.8	607.4	618.4	632.5
62.5°	532.0	538.3	541.5	555.6
65°	472.4	470.8	478.7	486.5
67.5°	408.1	406.5	414.3	417.5
70°	345.3	343.7	345.3	353.1
72.5°	285.6	285.6	287.2	290.3
75°	230.7	230.7	232.3	235.4
77.5°	174.2	177.3	175.8	182.1
80°	127.1	124.0	127.1	130.3
82.5°	83.2	86.3	86.3	83.2
85°	47.1	47.1	47.1	47.1
87.5°	20.4	20.4	22.0	23.5
90°	2.9	2.1	1.3	0.5
92.5°	15.3	14.8	14.3	13.8
95°	30.5	30.3	30.1	29.9
97.5°	46.3	46.2	46.1	46.0
100°	64.4	64.4	64.4	64.4
102.5°	85.7	85.2	84.7	84.2
105°	106.4	105.9	105.4	104.9
107.5°	128.9	128.4	127.9	127.4
110°	152.4	151.9	151.4	150.9



TEST NUMBER: P1035186

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	175.5	175.2	175.0	174.8
115°	199.5	199.1	198.7	198.3
117.5°	222.5	222.4	222.3	222.2
120°	245.8	245.3	244.8	244.3
122.5°	268.5	268.4	268.3	268.2
125°	291.3	290.6	290.0	289.4
127.5°	313.8	313.5	313.2	312.9
130°	335.1	334.6	334.1	333.6
132.5°	357.0	356.1	355.2	354.3
135°	378.2	377.6	377.0	376.4
137.5°	398.9	398.3	397.7	397.1
140°	418.4	417.9	417.4	416.9
142.5°	437.9	437.4	437.0	436.6
145°	457.2	456.8	456.4	456.0
147.5°	474.8	474.5	474.2	473.9
150°	491.5	491.6	491.7	491.8
152.5°	507.2	507.0	506.8	506.6
155°	521.8	521.8	521.8	521.8
157.5°	534.9	535.2	535.4	535.6
160°	546.6	546.9	547.2	547.5
162.5°	557.5	557.7	557.9	558.1
165°	566.7	566.9	567.1	567.3
167.5°	574.3	574.8	575.2	575.6
170°	580.8	581.2	581.6	582.0
172.5°	585.4	585.8	586.2	586.6
175°	588.6	589.1	589.5	589.9
177.5°	590.9	591.4	591.8	592.2
180°	591.2	591.2	591.2	591.2

(END OF REPORT)