

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035210

Luminaire Tested: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035210
REPORT IS A COMBINATION OF REPORTS P1003344 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D770UB30-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7904.0 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66		
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56		
2	93	85	79	74	87	81	75	70	72	67	64	63	60	57	56	53	51	47		
3	85	75	68	62	80	71	65	59	63	58	54	56	52	49	50	46	44	40		
4	78	67	59	53	73	63	56	50	57	51	46	50	46	42	44	41	38	35		
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30		
6	66	54	45	40	62	51	43	38	46	40	35	41	36	32	36	32	29	27		
7	61	49	40	35	57	46	39	34	42	35	31	37	32	29	33	29	26	24		
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	31	26	23	21		
9	53	40	33	28	50	39	31	27	35	29	25	31	26	23	28	24	21	19		
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11793	11793	11793	11793
5°	11802	13378	11812	10149
10°	11730	15249	11710	8712
15°	11644	16534	11572	7872
20°	11497	18118	11391	7186
25°	11367	20759	11159	6780
30°	11179	21901	10985	6412
35°	10882	17556	10653	6117
40°	10419	12134	10265	5806
45°	9834	9034	9724	5546
50°	9165	7437	9014	5338
55°	8443	6343	8376	5158
60°	7734	5429	7600	5018
65°	6970	4689	6858	4814
70°	6163	3893	6081	4460
75°	5307	3011	5237	3871
80°	4191	2036	4039	2846
85°	2682	1019	2590	1450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18013 cd/sqm

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.2	2.2
10°-20°	527.7	6.7
20°-30°	857.1	10.8
30°-40°	1047.5	13.3
40°-50°	950.2	12.0
50°-60°	756.8	9.6
60°-70°	527.1	6.7
70°-80°	280.8	3.6
80°-90°	71.1	0.9
90°-100°	64.5	0.8
100°-110°	191.7	2.4
110°-120°	325.1	4.1
120°-130°	428.0	5.4
130°-140°	479.6	6.1
140°-150°	470.1	5.9
150°-160°	394.9	5.0
160°-170°	262.5	3.3
170°-180°	91.9	1.2
0°-30°	1561.9	19.8
0°-40°	2609.4	33.0
0°-60°	4316.4	54.6
0°-90°	5195.5	65.7
90°-120°	581.4	7.4
90°-150°	1959.2	24.8
90°-180°	2708.0	34.3
0°-180°	7904.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1841	1841	1841	1841	1841	
5°	1839	2123	1841	1611	1839	175
15°	1767	2652	1756	1262	1767	499
25°	1627	3262	1597	1066	1627	749
35°	1416	2619	1386	912	1416	884
45°	1112	1234	1100	758	1112	857
55°	783	761	777	619	783	700
65°	484	467	477	480	484	481
75°	234	230	231	295	234	249
85°	47	52	45	73	47	56
90°	1	18	1	18	1	7
95°	49	65	49	65	49	51
105°	172	187	172	187	172	184
115°	326	328	326	328	326	322
125°	475	478	475	478	475	426
135°	618	620	618	620	618	476
145°	748	751	748	751	748	468
155°	856	856	856	856	856	394
165°	931	929	931	929	931	263
175°	968	964	968	964	968	92
180°	970	970	970	970	970	

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1843.8	1854.7	1867.2	1876.6	1892.2	1896.9	1904.7	1909.4	1914.1	1918.8	1921.9
5°	1839.1	1865.6	1889.1	1906.3	1935.9	1946.9	1960.9	1978.1	1998.4	2015.6	2026.6
7.5°	1826.6	1868.8	1900.0	1934.4	1975.0	2001.6	2015.6	2051.6	2084.4	2109.4	2142.2
10°	1810.9	1860.9	1909.4	1960.9	2018.8	2048.4	2076.6	2126.6	2171.9	2212.5	2245.3
12.5°	1793.8	1854.7	1912.5	1979.7	2057.8	2093.8	2112.5	2198.4	2254.7	2276.6	2340.6
15°	1767.2	1839.1	1921.9	2004.7	2070.3	2112.5	2164.1	2232.8	2289.1	2337.5	2389.1
17.5°	1742.2	1820.3	1904.7	1996.9	2092.2	2146.9	2185.9	2246.9	2307.8	2370.3	2418.8
20°	1701.6	1803.1	1889.1	1987.5	2100.0	2139.1	2179.7	2251.6	2317.2	2384.4	2445.3
22.5°	1668.8	1765.6	1882.8	1976.6	2071.9	2110.9	2160.9	2235.9	2314.1	2390.6	2479.7
25°	1626.6	1734.4	1835.9	1935.9	2034.4	2076.6	2121.9	2218.8	2300.0	2398.4	2496.9
27.5°	1581.3	1692.2	1793.8	1884.4	1976.6	2034.4	2082.8	2184.4	2292.2	2400.0	2528.1
30°	1532.8	1637.5	1734.4	1823.4	1925.0	1984.4	2032.8	2151.6	2271.9	2409.4	2562.5
32.5°	1481.3	1579.7	1662.5	1753.1	1860.9	1915.6	1981.3	2110.9	2253.1	2417.2	2609.4
35°	1415.6	1509.4	1582.8	1675.0	1782.8	1853.1	1921.9	2067.2	2232.8	2415.6	2635.9
37.5°	1350.0	1423.4	1493.8	1592.2	1717.2	1781.3	1853.1	2012.5	2201.6	2410.9	2646.9
40°	1271.9	1343.8	1404.7	1504.7	1635.9	1709.4	1784.4	1951.6	2165.6	2393.8	2607.8
42.5°	1193.8	1254.7	1321.9	1426.6	1553.1	1631.3	1710.9	1896.9	2118.8	2343.8	2500.0
45°	1112.5	1159.4	1232.8	1328.1	1462.5	1537.5	1628.1	1829.7	2053.1	2253.1	2331.3
47.5°	1028.1	1075.0	1143.8	1235.9	1368.8	1457.8	1543.8	1745.3	1970.3	2125.0	2125.0
50°	946.9	984.4	1051.6	1143.8	1278.1	1359.4	1446.9	1660.9	1842.2	1956.3	1854.7
52.5°	859.4	901.6	957.8	1054.7	1187.5	1260.9	1356.3	1539.1	1710.9	1757.8	1601.6
55°	782.8	817.2	870.3	962.5	1085.9	1162.5	1243.8	1418.8	1564.1	1560.9	1393.8
57.5°	703.1	731.3	787.5	871.9	985.9	1054.7	1135.9	1287.5	1406.3	1364.1	1206.3
60°	629.7	650.0	704.7	773.4	882.8	946.9	1025.0	1148.4	1239.1	1179.7	1020.3
62.5°	553.1	576.6	620.3	687.5	784.4	835.9	893.8	1018.8	1076.6	1023.4	860.9
65°	484.4	503.1	542.2	598.4	685.9	732.8	782.8	885.9	940.6	864.1	729.7
67.5°	415.6	437.5	465.6	515.6	584.4	628.1	671.9	760.9	785.9	717.2	604.7
70°	351.6	370.3	396.9	432.8	490.6	529.7	562.5	635.9	653.1	589.1	500.0
72.5°	289.1	301.6	323.4	353.1	406.3	428.1	462.5	512.5	534.4	476.6	412.5
75°	234.4	243.8	257.8	279.7	315.6	339.1	367.2	414.1	412.5	371.9	326.6
77.5°	181.3	182.8	198.4	218.8	240.6	260.9	275.0	307.8	310.9	285.9	248.4
80°	129.7	134.4	140.6	156.3	175.0	182.8	200.0	220.3	223.4	204.7	179.7
82.5°	82.8	85.9	90.6	100.0	112.5	121.9	131.3	139.1	146.9	135.9	115.6
85°	46.9	48.4	53.1	56.3	62.5	67.2	75.0	82.8	81.3	73.4	67.2
87.5°	23.4	23.4	23.4	26.6	29.7	29.7	32.8	34.4	35.9	32.8	29.7
90°	0.8	2.1	3.5	4.8	6.1	6.8	7.4	8.6	9.7	10.9	12.1
92.5°	22.7	23.5	24.3	25.2	26.0	26.4	27.2	28.7	30.2	31.7	33.2
95°	49.1	49.4	49.8	50.1	50.4	50.6	51.4	53.1	54.8	56.5	58.2
97.5°	75.5	75.7	75.9	76.0	76.2	76.3	77.5	79.8	82.2	84.5	86.9
100°	105.7	105.7	105.7	105.7	105.7	105.7	106.8	109.0	111.1	113.3	115.5
102.5°	138.2	139.0	139.9	140.7	141.6	142.0	142.4	143.3	144.1	145.0	145.8
105°	172.2	173.0	173.9	174.7	175.6	176.0	176.5	177.5	178.5	179.5	180.5
107.5°	209.2	210.0	210.9	211.7	212.6	213.0	213.4	214.2	215.1	215.9	216.7
110°	247.7	248.5	249.4	250.2	251.1	251.5	251.8	252.3	252.8	253.3	253.8

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	287.0	287.3	287.7	288.0	288.3	288.5	288.8	289.5	290.2	290.8	291.5
115°	325.5	326.2	326.8	327.5	328.2	328.5	328.7	329.0	329.3	329.7	330.0
117.5°	364.8	365.0	365.1	365.3	365.4	365.5	365.7	366.0	366.3	366.7	367.0
120°	401.0	401.8	402.7	403.5	404.4	404.8	404.9	405.1	405.2	405.4	405.6
122.5°	440.3	440.5	440.7	440.8	441.0	441.1	441.3	441.8	442.3	442.8	443.3
125°	475.0	476.0	477.0	478.1	479.1	479.6	479.7	479.8	480.0	480.1	480.3
127.5°	513.6	514.1	514.6	515.1	515.6	515.8	515.9	516.1	516.2	516.4	516.6
130°	547.5	548.3	549.2	550.0	550.9	551.3	551.5	551.8	552.1	552.5	552.8
132.5°	581.5	583.0	584.5	586.0	587.5	588.3	588.2	588.1	587.9	587.8	587.6
135°	617.8	618.8	619.8	620.8	621.8	622.3	622.4	622.6	622.7	622.9	623.1
137.5°	651.8	652.8	653.8	654.8	655.8	656.3	656.5	656.8	657.1	657.5	657.8
140°	684.2	685.0	685.9	686.7	687.6	688.0	688.3	688.8	689.3	689.8	690.3
142.5°	716.7	717.4	718.0	718.7	719.4	719.7	720.0	720.7	721.4	722.1	722.8
145°	748.4	749.1	749.7	750.4	751.1	751.4	751.7	752.2	752.7	753.2	753.7
147.5°	777.9	778.4	778.9	779.4	779.9	780.1	780.3	780.6	781.0	781.3	781.7
150°	807.3	807.1	807.0	806.8	806.7	806.6	806.9	807.6	808.3	808.9	809.6
152.5°	831.5	831.8	832.2	832.5	832.8	833.0	833.1	833.3	833.4	833.6	833.8
155°	856.4	856.4	856.4	856.4	856.4	856.4	856.5	856.7	856.8	857.0	857.2
157.5°	879.1	878.8	878.4	878.1	877.8	877.6	877.7	877.8	878.0	878.1	878.3
160°	898.7	898.2	897.7	897.2	896.7	896.5	896.6	896.7	896.9	897.0	897.2
162.5°	916.1	915.8	915.4	915.1	914.8	914.6	914.6	914.6	914.6	914.6	914.6
165°	931.2	930.9	930.5	930.2	929.9	929.7	929.8	929.9	930.1	930.2	930.4
167.5°	944.8	944.1	943.5	942.8	942.1	941.8	941.8	941.8	941.8	941.8	941.8
170°	955.4	954.7	954.0	953.3	952.6	952.3	952.3	952.3	952.3	952.3	952.3
172.5°	962.9	962.2	961.6	960.9	960.2	959.9	959.9	959.9	959.9	959.9	959.9
175°	968.2	967.5	966.9	966.2	965.5	965.2	965.2	965.2	965.2	965.2	965.2
177.5°	972.0	971.3	970.7	970.0	969.3	969.0	968.9	968.7	968.6	968.4	968.2
180°	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1925.0	1935.9	1945.3	1953.1	1959.4	1968.8	1962.5	1964.1	1967.2	1973.4	1973.4
5°	2050.0	2067.2	2076.6	2107.8	2115.6	2114.1	2109.4	2134.4	2132.8	2123.4	2121.9
7.5°	2171.9	2201.6	2228.1	2253.1	2260.9	2281.3	2285.9	2296.9	2293.8	2309.4	2301.6
10°	2282.8	2329.7	2354.7	2392.2	2401.6	2410.9	2423.4	2429.7	2443.8	2442.2	2442.2
12.5°	2368.8	2425.0	2457.8	2467.2	2503.1	2514.1	2525.0	2545.3	2540.6	2542.2	2551.6
15°	2435.9	2490.6	2518.8	2562.5	2587.5	2600.0	2618.8	2640.6	2637.5	2651.6	2648.4
17.5°	2485.9	2537.5	2589.1	2654.7	2656.3	2689.1	2732.8	2742.2	2762.5	2748.4	2748.4
20°	2526.6	2595.3	2668.8	2753.1	2762.5	2782.8	2835.9	2871.9	2895.3	2887.5	2892.2
22.5°	2570.3	2668.8	2754.7	2839.1	2884.4	2920.3	2971.9	3028.1	3048.5	3061.0	3057.8
25°	2626.6	2729.7	2856.3	2973.5	3020.3	3089.1	3157.8	3212.5	3228.1	3262.5	3231.3
27.5°	2684.4	2829.7	2987.5	3125.0	3184.4	3240.6	3323.5	3364.1	3384.4	3400.0	3389.1
30°	2732.8	2932.8	3104.7	3231.3	3273.5	3306.3	3353.1	3362.5	3354.7	3367.2	3382.8
32.5°	2807.8	3003.1	3148.5	3209.4	3204.7	3203.1	3167.2	3117.2	3106.3	3076.6	3117.2
35°	2848.4	3004.7	3061.0	2979.7	2946.9	2887.5	2773.4	2698.4	2632.8	2618.8	2621.9
37.5°	2825.0	2886.0	2818.8	2604.7	2551.6	2460.9	2309.4	2203.1	2154.7	2117.2	2165.6
40°	2698.4	2631.3	2446.9	2185.9	2109.4	2023.4	1881.3	1823.4	1754.7	1740.6	1804.7
42.5°	2489.1	2284.4	2023.4	1821.9	1742.2	1693.8	1575.0	1520.3	1471.9	1450.0	1485.9
45°	2204.7	1956.3	1693.8	1528.1	1460.9	1403.1	1332.8	1275.0	1243.8	1234.4	1264.1
47.5°	1910.9	1648.4	1439.1	1315.6	1245.3	1201.6	1135.9	1103.1	1078.1	1081.3	1085.9
50°	1629.7	1390.6	1229.7	1106.3	1071.9	1037.5	993.8	965.6	953.1	957.8	954.7
52.5°	1387.5	1193.8	1057.8	962.5	946.9	914.1	878.1	854.7	850.0	851.6	856.3
55°	1175.0	1023.4	915.6	846.9	829.7	806.3	784.4	768.8	756.3	760.9	759.4
57.5°	1014.1	881.3	798.4	742.2	729.7	715.6	695.3	687.5	682.8	673.4	681.3
60°	871.9	764.1	692.2	657.8	646.9	637.5	615.6	606.3	603.1	598.4	610.9
62.5°	737.5	660.9	606.3	575.0	564.1	554.7	543.8	535.9	537.5	531.3	537.5
65°	631.3	568.8	529.7	501.6	487.5	481.3	479.7	467.2	465.6	467.2	468.8
67.5°	532.8	479.7	450.0	432.8	421.9	415.6	410.9	403.1	409.4	404.7	407.8
70°	443.8	407.8	376.6	359.4	354.7	356.3	348.4	345.3	346.9	343.8	346.9
72.5°	357.8	328.1	315.6	303.1	296.9	295.3	290.6	285.9	290.6	289.1	289.1
75°	285.9	264.1	250.0	242.2	242.2	239.1	231.3	231.3	231.3	229.7	231.3
77.5°	220.3	201.6	195.3	187.5	187.5	182.8	181.3	181.3	178.1	182.8	179.7
80°	164.1	150.0	140.6	135.9	135.9	134.4	131.3	129.7	131.3	129.7	129.7
82.5°	106.3	100.0	95.3	90.6	89.1	90.6	89.1	85.9	87.5	85.9	89.1
85°	60.9	54.7	54.7	51.6	53.1	50.0	51.6	48.4	46.9	51.6	48.4
87.5°	26.6	25.0	25.0	21.9	21.9	21.9	20.3	21.9	20.3	18.8	20.3
90°	12.9	13.8	14.6	15.5	15.9	16.1	16.6	17.1	17.6	18.1	17.6
92.5°	34.4	35.6	36.7	37.9	38.5	38.7	39.0	39.3	39.7	40.0	39.7
95°	59.4	60.5	61.7	62.8	63.4	63.6	63.9	64.2	64.6	64.9	64.6
97.5°	87.9	88.9	89.9	90.9	91.4	91.5	91.6	91.8	91.9	92.1	91.9
100°	117.0	118.5	120.0	121.5	122.3	122.5	122.8	123.2	123.5	123.9	123.5
102.5°	147.5	149.1	150.8	152.5	153.3	153.6	154.1	154.6	155.1	155.6	155.1
105°	181.5	182.5	183.5	184.5	185.0	185.3	185.8	186.3	186.8	187.3	186.8
107.5°	217.2	217.7	218.2	218.7	219.0	219.0	219.0	219.0	219.0	219.0	219.0
110°	254.3	254.8	255.3	255.8	256.0	255.9	255.8	255.6	255.5	255.3	255.5

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	291.7	291.9	292.0	292.2	292.3	292.1	291.8	291.5	291.1	290.8	291.1
115°	329.8	329.7	329.5	329.4	329.3	329.2	329.0	328.9	328.7	328.5	328.7
117.5°	367.2	367.4	367.5	367.7	367.8	367.5	366.8	366.1	365.5	364.8	365.5
120°	405.6	405.6	405.6	405.6	405.6	405.3	404.6	403.9	403.2	402.5	403.2
122.5°	443.1	443.0	442.8	442.7	442.6	442.3	441.8	441.3	440.8	440.3	440.8
125°	480.0	479.6	479.3	479.0	478.8	478.7	478.6	478.4	478.3	478.1	478.3
127.5°	516.4	516.2	516.1	515.9	515.8	515.6	515.3	515.0	514.6	514.3	514.6
130°	552.6	552.5	552.3	552.2	552.1	551.9	551.6	551.3	550.9	550.6	550.9
132.5°	587.4	587.2	587.1	586.9	586.8	586.5	586.0	585.5	585.0	584.5	585.0
135°	623.1	623.1	623.1	623.1	623.1	622.8	622.1	621.4	620.7	620.0	620.7
137.5°	658.0	658.2	658.3	658.5	658.6	658.2	657.3	656.5	655.6	654.8	655.6
140°	690.6	691.0	691.3	691.6	691.8	691.4	690.5	689.7	688.8	688.0	688.8
142.5°	723.0	723.1	723.3	723.4	723.5	723.1	722.2	721.4	720.5	719.7	720.5
145°	753.7	753.7	753.7	753.7	753.7	753.4	752.9	752.4	751.9	751.4	751.9
147.5°	782.2	782.7	783.2	783.7	783.9	783.2	781.9	780.6	779.2	777.9	779.2
150°	809.6	809.6	809.6	809.6	809.6	809.4	809.1	808.8	808.4	808.1	808.4
152.5°	834.3	834.8	835.3	835.8	836.0	835.7	835.0	834.3	833.7	833.0	833.7
155°	857.9	858.5	859.2	859.9	860.2	859.8	858.9	858.1	857.2	856.4	857.2
157.5°	879.0	879.6	880.3	881.0	881.3	880.7	879.6	878.4	877.3	876.1	877.3
160°	897.9	898.5	899.2	899.9	900.2	899.8	899.0	898.1	897.3	896.5	897.3
162.5°	915.4	916.3	917.1	918.0	918.4	917.9	916.9	915.8	914.8	913.8	914.8
165°	931.1	931.8	932.5	933.2	933.5	933.0	932.0	930.9	929.9	928.9	929.9
167.5°	942.8	943.8	944.8	945.8	946.3	945.8	944.8	943.8	942.8	941.8	942.8
170°	953.3	954.3	955.4	956.4	956.9	956.3	955.1	954.0	952.8	951.6	952.8
172.5°	960.9	961.9	962.9	963.9	964.4	963.9	962.9	961.9	960.9	959.9	960.9
175°	966.2	967.2	968.2	969.2	969.7	969.1	967.9	966.8	965.6	964.4	965.6
177.5°	969.2	970.2	971.2	972.2	972.7	972.1	970.9	969.8	968.6	967.4	968.6
180°	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1970.3	1959.4	1962.5	1959.4	1951.6	1946.9	1934.4	1918.8	1912.5	1904.7	1900.0
5°	2128.1	2120.3	2118.8	2106.3	2103.1	2084.4	2053.1	2037.5	2018.8	2000.0	1981.3
7.5°	2300.0	2290.6	2259.4	2254.7	2257.8	2234.4	2193.8	2162.5	2123.4	2096.9	2060.9
10°	2442.2	2423.4	2396.9	2398.4	2387.5	2356.3	2315.6	2282.8	2226.6	2192.2	2140.6
12.5°	2528.1	2512.5	2509.4	2493.8	2484.4	2443.8	2395.3	2353.1	2310.9	2264.1	2225.0
15°	2632.8	2612.5	2598.4	2576.6	2570.3	2528.1	2475.0	2426.6	2378.1	2334.4	2251.6
17.5°	2748.4	2726.6	2673.4	2668.8	2631.3	2590.6	2539.1	2467.2	2415.6	2353.1	2292.2
20°	2879.7	2848.4	2779.7	2762.5	2732.8	2665.6	2595.3	2515.6	2432.8	2368.8	2296.9
22.5°	3026.6	2971.9	2921.9	2867.2	2845.3	2762.5	2665.6	2568.8	2468.8	2381.3	2295.3
25°	3217.2	3145.3	3075.0	3020.3	2982.8	2875.0	2745.3	2617.2	2501.6	2387.5	2275.0
27.5°	3367.2	3304.7	3228.1	3156.3	3107.8	2979.7	2831.3	2665.6	2521.9	2382.8	2262.5
30°	3378.1	3359.4	3312.5	3273.5	3220.3	3082.8	2918.8	2731.3	2553.1	2384.4	2237.5
32.5°	3173.5	3211.0	3231.3	3237.5	3226.6	3146.9	2996.9	2790.6	2581.3	2370.3	2215.6
35°	2732.8	2832.8	2956.3	3003.1	3048.5	3090.6	3012.5	2832.8	2590.6	2367.2	2181.3
37.5°	2250.0	2340.6	2545.3	2639.1	2692.2	2859.4	2923.5	2826.6	2609.4	2370.3	2148.4
40°	1815.6	1959.4	2106.3	2232.8	2315.6	2503.1	2701.6	2723.4	2582.8	2340.6	2106.3
42.5°	1528.1	1612.5	1723.4	1840.6	1914.1	2135.9	2404.7	2562.5	2500.0	2292.2	2054.7
45°	1301.6	1364.1	1468.8	1507.8	1601.6	1814.1	2098.4	2326.6	2357.8	2215.6	1995.3
47.5°	1117.2	1170.3	1237.5	1285.9	1360.9	1520.3	1760.9	2012.5	2162.5	2110.9	1912.5
50°	984.4	1028.1	1084.4	1112.5	1160.9	1304.7	1485.9	1735.9	1937.5	1954.7	1804.7
52.5°	873.4	898.4	942.2	973.4	1012.5	1100.0	1264.1	1470.3	1696.9	1790.6	1671.9
55°	776.6	796.9	835.9	856.3	876.6	951.6	1079.7	1267.2	1479.7	1603.1	1535.9
57.5°	689.1	706.3	739.1	757.8	768.8	840.6	939.1	1085.9	1276.6	1426.6	1389.1
60°	617.2	632.8	651.6	665.6	678.1	737.5	806.3	925.0	1095.3	1240.6	1231.3
62.5°	540.6	554.7	575.0	589.1	600.0	637.5	695.3	785.9	931.3	1065.6	1092.2
65°	473.4	484.4	498.4	504.7	518.8	546.9	593.8	675.0	793.8	914.1	932.8
67.5°	412.5	415.6	425.0	439.1	442.2	467.2	509.4	570.3	662.5	760.9	790.6
70°	346.9	351.6	359.4	370.3	376.6	392.2	428.1	468.8	548.4	634.4	656.3
72.5°	289.1	295.3	298.4	304.7	307.8	332.8	348.4	389.1	443.8	515.6	539.1
75°	234.4	240.6	242.2	245.3	248.4	259.4	281.3	306.3	351.6	398.4	429.7
77.5°	185.9	184.4	187.5	192.2	190.6	200.0	214.1	235.9	265.6	304.7	325.0
80°	131.3	131.3	135.9	140.6	139.1	148.4	153.1	168.8	193.8	218.8	226.6
82.5°	87.5	87.5	92.2	92.2	95.3	96.9	103.1	110.9	131.3	143.8	148.4
85°	50.0	50.0	51.6	51.6	51.6	54.7	59.4	62.5	68.8	76.6	79.7
87.5°	20.3	21.9	21.9	21.9	21.9	25.0	25.0	28.1	29.7	32.8	32.8
90°	17.1	16.6	16.1	15.9	15.5	14.6	13.8	12.9	12.1	10.9	9.7
92.5°	39.3	39.0	38.7	38.5	37.9	36.7	35.6	34.4	33.2	31.7	30.2
95°	64.2	63.9	63.6	63.4	62.8	61.7	60.5	59.4	58.2	56.5	54.8
97.5°	91.8	91.6	91.5	91.4	90.9	89.9	88.9	87.9	86.9	84.5	82.2
100°	123.2	122.8	122.5	122.3	121.5	120.0	118.5	117.0	115.5	113.3	111.1
102.5°	154.6	154.1	153.6	153.3	152.5	150.8	149.1	147.5	145.8	145.0	144.1
105°	186.3	185.8	185.3	185.0	184.5	183.5	182.5	181.5	180.5	179.5	178.5
107.5°	219.0	219.0	219.0	219.0	218.7	218.2	217.7	217.2	216.7	215.9	215.1
110°	255.6	255.8	255.9	256.0	255.8	255.3	254.8	254.3	253.8	253.3	252.8

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	291.5	291.8	292.1	292.3	292.2	292.0	291.9	291.7	291.5	290.8	290.2
115°	328.9	329.0	329.2	329.3	329.4	329.5	329.7	329.8	330.0	329.7	329.3
117.5°	366.1	366.8	367.5	367.8	367.7	367.5	367.4	367.2	367.0	366.7	366.3
120°	403.9	404.6	405.3	405.6	405.6	405.6	405.6	405.6	405.6	405.4	405.2
122.5°	441.3	441.8	442.3	442.6	442.7	442.8	443.0	443.1	443.3	442.8	442.3
125°	478.4	478.6	478.7	478.8	479.0	479.3	479.6	480.0	480.3	480.1	480.0
127.5°	515.0	515.3	515.6	515.8	515.9	516.1	516.2	516.4	516.6	516.4	516.2
130°	551.3	551.6	551.9	552.1	552.2	552.3	552.5	552.6	552.8	552.5	552.1
132.5°	585.5	586.0	586.5	586.8	586.9	587.1	587.2	587.4	587.6	587.8	587.9
135°	621.4	622.1	622.8	623.1	623.1	623.1	623.1	623.1	623.1	622.9	622.7
137.5°	656.5	657.3	658.2	658.6	658.5	658.3	658.2	658.0	657.8	657.5	657.1
140°	689.7	690.5	691.4	691.8	691.6	691.3	691.0	690.6	690.3	689.8	689.3
142.5°	721.4	722.2	723.1	723.5	723.4	723.3	723.1	723.0	722.8	722.1	721.4
145°	752.4	752.9	753.4	753.7	753.7	753.7	753.7	753.7	753.7	753.2	752.7
147.5°	780.6	781.9	783.2	783.9	783.7	783.2	782.7	782.2	781.7	781.3	781.0
150°	808.8	809.1	809.4	809.6	809.6	809.6	809.6	809.6	809.6	808.9	808.3
152.5°	834.3	835.0	835.7	836.0	835.8	835.3	834.8	834.3	833.8	833.6	833.4
155°	858.1	858.9	859.8	860.2	859.9	859.2	858.5	857.9	857.2	857.0	856.8
157.5°	878.4	879.6	880.7	881.3	881.0	880.3	879.6	879.0	878.3	878.1	878.0
160°	898.1	899.0	899.8	900.2	899.9	899.2	898.5	897.9	897.2	897.0	896.9
162.5°	915.8	916.9	917.9	918.4	918.0	917.1	916.3	915.4	914.6	914.6	914.6
165°	930.9	932.0	933.0	933.5	933.2	932.5	931.8	931.1	930.4	930.2	930.1
167.5°	943.8	944.8	945.8	946.3	945.8	944.8	943.8	942.8	941.8	941.8	941.8
170°	954.0	955.1	956.3	956.9	956.4	955.4	954.3	953.3	952.3	952.3	952.3
172.5°	961.9	962.9	963.9	964.4	963.9	962.9	961.9	960.9	959.9	959.9	959.9
175°	966.8	967.9	969.1	969.7	969.2	968.2	967.2	966.2	965.2	965.2	965.2
177.5°	969.8	970.9	972.1	972.7	972.2	971.2	970.2	969.2	968.2	968.4	968.6
180°	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1893.8	1885.9	1876.6	1876.6	1865.6	1860.9	1851.6	1848.4	1840.6	1828.1	1818.8
5°	1960.9	1940.6	1928.1	1917.2	1893.8	1876.6	1859.4	1840.6	1821.9	1800.0	1775.0
7.5°	2026.6	1989.1	1971.9	1953.1	1918.8	1882.8	1848.4	1823.4	1798.4	1764.1	1732.8
10°	2095.3	2048.4	2017.2	1992.2	1939.1	1893.8	1843.8	1807.8	1768.8	1725.0	1684.4
12.5°	2153.1	2092.2	2065.6	2018.8	1957.8	1903.1	1840.6	1785.9	1734.4	1682.8	1632.8
15°	2201.6	2143.8	2078.1	2059.4	1975.0	1896.9	1826.6	1756.3	1692.2	1640.6	1582.8
17.5°	2217.2	2143.8	2110.9	2065.6	1965.6	1884.4	1795.3	1718.8	1657.8	1581.3	1535.9
20°	2221.9	2151.6	2106.3	2064.1	1975.0	1867.2	1779.7	1685.9	1612.5	1535.9	1464.1
22.5°	2209.4	2126.6	2082.8	2042.2	1942.2	1850.0	1748.4	1645.3	1559.4	1489.1	1417.2
25°	2185.9	2089.1	2046.9	2003.1	1907.8	1806.3	1695.3	1596.9	1517.2	1432.8	1362.5
27.5°	2154.7	2043.8	1995.3	1950.0	1856.3	1760.9	1656.3	1554.7	1465.6	1376.6	1310.9
30°	2115.6	1987.5	1943.8	1884.4	1793.8	1703.1	1607.8	1506.3	1406.3	1321.9	1250.0
32.5°	2065.6	1931.3	1873.4	1817.2	1718.8	1635.9	1545.3	1450.0	1353.1	1270.3	1195.3
35°	2020.3	1867.2	1803.1	1746.9	1637.5	1550.0	1475.0	1385.9	1300.0	1214.1	1146.9
37.5°	1959.4	1803.1	1726.6	1668.8	1557.8	1468.8	1398.4	1329.7	1239.1	1156.3	1093.8
40°	1895.3	1723.4	1651.6	1593.8	1478.1	1381.3	1314.1	1253.1	1179.7	1103.1	1037.5
42.5°	1837.5	1646.9	1570.3	1500.0	1382.8	1296.9	1228.1	1181.3	1114.1	1045.3	985.9
45°	1764.1	1565.6	1482.8	1409.4	1296.9	1203.1	1137.5	1100.0	1050.0	982.8	931.3
47.5°	1689.1	1478.1	1392.2	1320.3	1198.4	1115.6	1051.6	1015.6	981.3	928.1	876.6
50°	1590.6	1385.9	1307.8	1225.0	1104.7	1020.3	967.2	931.3	904.7	867.2	823.4
52.5°	1482.8	1290.6	1206.3	1134.4	1015.6	939.1	878.1	857.8	831.3	803.1	765.6
55°	1368.8	1187.5	1106.3	1035.9	926.6	848.4	798.4	776.6	756.3	734.4	709.4
57.5°	1254.7	1079.7	1003.1	940.6	839.1	764.1	723.4	693.8	679.7	667.2	646.9
60°	1112.5	964.1	904.7	848.4	748.4	679.7	640.6	618.8	606.3	600.0	590.6
62.5°	987.5	865.6	800.0	745.3	665.6	604.7	567.2	550.0	539.1	535.9	525.0
65°	854.7	750.0	698.4	651.6	582.8	528.1	496.9	476.6	468.8	467.2	467.2
67.5°	729.7	645.3	593.8	560.9	501.6	453.1	423.4	415.6	410.9	404.7	403.1
70°	612.5	545.3	500.0	471.9	418.8	382.8	359.4	346.9	346.9	342.2	339.1
72.5°	509.4	442.2	412.5	389.1	345.3	314.1	296.9	293.8	282.8	281.3	281.3
75°	398.4	348.4	328.1	307.8	275.0	253.1	239.1	231.3	225.0	225.0	226.6
77.5°	300.0	265.6	246.9	231.3	207.8	193.8	182.8	179.7	173.4	173.4	173.4
80°	212.5	193.8	179.7	167.2	150.0	137.5	131.3	125.0	125.0	123.4	125.0
82.5°	137.5	121.9	114.1	112.5	96.9	92.2	84.4	85.9	81.3	79.7	82.8
85°	79.7	71.9	62.5	59.4	53.1	46.9	43.8	45.3	43.8	42.2	43.8
87.5°	31.3	26.6	25.0	25.0	20.3	18.8	17.2	18.8	15.6	15.6	17.2
90°	8.6	7.4	6.8	6.1	4.8	3.5	2.1	0.8	2.1	3.5	4.8
92.5°	28.7	27.2	26.4	26.0	25.2	24.3	23.5	22.7	23.5	24.3	25.2
95°	53.1	51.4	50.6	50.4	50.1	49.8	49.4	49.1	49.4	49.8	50.1
97.5°	79.8	77.5	76.3	76.2	76.0	75.9	75.7	75.5	75.7	75.9	76.0
100°	109.0	106.8	105.7	105.7	105.7	105.7	105.7	105.7	105.7	105.7	105.7
102.5°	143.3	142.4	142.0	141.6	140.7	139.9	139.0	138.2	139.0	139.9	140.7
105°	177.5	176.5	176.0	175.6	174.7	173.9	173.0	172.2	173.0	173.9	174.7
107.5°	214.2	213.4	213.0	212.6	211.7	210.9	210.0	209.2	210.0	210.9	211.7
110°	252.3	251.8	251.5	251.1	250.2	249.4	248.5	247.7	248.5	249.4	250.2

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	289.5	288.8	288.5	288.3	288.0	287.7	287.3	287.0	287.3	287.7	288.0
115°	329.0	328.7	328.5	328.2	327.5	326.8	326.2	325.5	326.2	326.8	327.5
117.5°	366.0	365.7	365.5	365.4	365.3	365.1	365.0	364.8	365.0	365.1	365.3
120°	405.1	404.9	404.8	404.4	403.5	402.7	401.8	401.0	401.8	402.7	403.5
122.5°	441.8	441.3	441.1	441.0	440.8	440.7	440.5	440.3	440.5	440.7	440.8
125°	479.8	479.7	479.6	479.1	478.1	477.0	476.0	475.0	476.0	477.0	478.1
127.5°	516.1	515.9	515.8	515.6	515.1	514.6	514.1	513.6	514.1	514.6	515.1
130°	551.8	551.5	551.3	550.9	550.0	549.2	548.3	547.5	548.3	549.2	550.0
132.5°	588.1	588.2	588.3	587.5	586.0	584.5	583.0	581.5	583.0	584.5	586.0
135°	622.6	622.4	622.3	621.8	620.8	619.8	618.8	617.8	618.8	619.8	620.8
137.5°	656.8	656.5	656.3	655.8	654.8	653.8	652.8	651.8	652.8	653.8	654.8
140°	688.8	688.3	688.0	687.6	686.7	685.9	685.0	684.2	685.0	685.9	686.7
142.5°	720.7	720.0	719.7	719.4	718.7	718.0	717.4	716.7	717.4	718.0	718.7
145°	752.2	751.7	751.4	751.1	750.4	749.7	749.1	748.4	749.1	749.7	750.4
147.5°	780.6	780.3	780.1	779.9	779.4	778.9	778.4	777.9	778.4	778.9	779.4
150°	807.6	806.9	806.6	806.7	806.8	807.0	807.1	807.3	807.1	807.0	806.8
152.5°	833.3	833.1	833.0	832.8	832.5	832.2	831.8	831.5	831.8	832.2	832.5
155°	856.7	856.5	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
157.5°	877.8	877.7	877.6	877.8	878.1	878.4	878.8	879.1	878.8	878.4	878.1
160°	896.7	896.6	896.5	896.7	897.2	897.7	898.2	898.7	898.2	897.7	897.2
162.5°	914.6	914.6	914.6	914.8	915.1	915.4	915.8	916.1	915.8	915.4	915.1
165°	929.9	929.8	929.7	929.9	930.2	930.5	930.9	931.2	930.9	930.5	930.2
167.5°	941.8	941.8	941.8	942.1	942.8	943.5	944.1	944.8	944.1	943.5	942.8
170°	952.3	952.3	952.3	952.6	953.3	954.0	954.7	955.4	954.7	954.0	953.3
172.5°	959.9	959.9	959.9	960.2	960.9	961.6	962.2	962.9	962.2	961.6	960.9
175°	965.2	965.2	965.2	965.5	966.2	966.9	967.5	968.2	967.5	966.9	966.2
177.5°	968.7	968.9	969.0	969.3	970.0	970.7	971.3	972.0	971.3	970.7	970.0
180°	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1815.6	1812.5	1804.7	1800.0	1784.4	1765.6	1759.4	1743.8	1750.0	1739.1	1739.1
5°	1767.2	1753.1	1743.8	1729.7	1700.0	1679.7	1657.8	1646.9	1640.6	1632.8	1626.6
7.5°	1704.7	1693.8	1684.4	1657.8	1625.0	1596.9	1570.3	1559.4	1539.1	1525.0	1518.8
10°	1650.0	1634.4	1612.5	1581.3	1546.9	1510.9	1487.5	1464.1	1448.4	1440.6	1423.4
12.5°	1593.8	1575.0	1551.6	1506.3	1468.8	1446.9	1404.7	1382.8	1375.0	1368.8	1348.4
15°	1535.9	1515.6	1487.5	1445.3	1412.5	1360.9	1335.9	1318.8	1300.0	1298.4	1282.8
17.5°	1484.4	1459.4	1435.9	1384.4	1343.8	1298.4	1284.4	1265.6	1248.4	1229.7	1221.9
20°	1418.8	1395.3	1378.1	1321.9	1276.6	1248.4	1225.0	1209.4	1198.4	1179.7	1176.6
22.5°	1359.4	1334.4	1310.9	1268.8	1229.7	1193.8	1165.6	1148.4	1143.8	1135.9	1121.9
25°	1301.6	1276.6	1248.4	1209.4	1168.8	1143.8	1118.8	1107.8	1098.4	1085.9	1075.0
27.5°	1253.1	1229.7	1203.1	1154.7	1120.3	1101.6	1075.0	1062.5	1050.0	1043.8	1039.1
30°	1195.3	1168.8	1148.4	1110.9	1073.4	1048.4	1029.7	1018.8	1007.8	1001.6	998.4
32.5°	1139.1	1114.1	1100.0	1059.4	1029.7	1000.0	985.9	978.1	971.9	965.6	959.4
35°	1093.8	1068.8	1046.9	1009.4	979.7	959.4	948.4	935.9	931.3	925.0	925.0
37.5°	1037.5	1018.8	996.9	960.9	934.4	918.8	909.4	893.8	892.2	889.1	884.4
40°	989.1	970.3	950.0	918.8	895.3	876.6	864.1	856.3	851.6	848.4	845.3
42.5°	937.5	917.2	907.8	871.9	851.6	832.8	826.6	818.8	817.2	810.9	803.1
45°	887.5	870.3	851.6	825.0	807.8	792.2	782.8	776.6	768.8	767.2	762.5
47.5°	843.8	823.4	806.3	781.3	762.5	750.0	742.2	734.4	728.1	723.4	718.8
50°	787.5	771.9	757.8	731.3	715.6	703.1	692.2	685.9	679.7	679.7	679.7
52.5°	732.8	718.8	706.3	687.5	668.8	657.8	645.3	640.6	637.5	632.8	637.5
55°	679.7	665.6	653.1	639.1	617.2	607.8	595.3	590.6	592.2	592.2	596.9
57.5°	623.4	612.5	604.7	587.5	567.2	557.8	550.0	545.3	545.3	551.6	553.1
60°	568.8	557.8	543.8	528.1	515.6	504.7	500.0	501.6	501.6	504.7	512.5
62.5°	507.8	501.6	493.8	471.9	464.1	456.3	450.0	454.7	453.1	460.9	471.9
65°	451.6	445.3	434.4	423.4	414.1	406.3	404.7	406.3	409.4	417.2	429.7
67.5°	389.1	389.1	379.7	370.3	362.5	354.7	356.3	357.8	360.9	370.3	389.1
70°	337.5	331.3	321.9	315.6	309.4	306.3	303.1	309.4	318.8	325.0	339.1
72.5°	281.3	276.6	268.8	262.5	260.9	257.8	256.3	259.4	268.8	279.7	295.3
75°	221.9	223.4	218.8	214.1	214.1	209.4	212.5	212.5	221.9	232.8	245.3
77.5°	171.9	170.3	168.8	165.6	164.1	164.1	164.1	167.2	176.6	182.8	195.3
80°	121.9	123.4	118.8	120.3	118.8	120.3	120.3	126.6	131.3	139.1	148.4
82.5°	81.3	81.3	78.1	79.7	79.7	79.7	81.3	84.4	90.6	96.9	103.1
85°	45.3	46.9	43.8	46.9	46.9	46.9	48.4	50.0	54.7	56.3	62.5
87.5°	17.2	20.3	20.3	17.2	18.8	20.3	21.9	20.3	23.4	26.6	28.1
90°	6.1	6.8	7.4	8.6	9.7	10.9	12.1	12.9	13.8	14.6	15.5
92.5°	26.0	26.4	27.2	28.7	30.2	31.7	33.2	34.4	35.6	36.7	37.9
95°	50.4	50.6	51.4	53.1	54.8	56.5	58.2	59.4	60.5	61.7	62.8
97.5°	76.2	76.3	77.5	79.8	82.2	84.5	86.9	87.9	88.9	89.9	90.9
100°	105.7	105.7	106.8	109.0	111.1	113.3	115.5	117.0	118.5	120.0	121.5
102.5°	141.6	142.0	142.4	143.3	144.1	145.0	145.8	147.5	149.1	150.8	152.5
105°	175.6	176.0	176.5	177.5	178.5	179.5	180.5	181.5	182.5	183.5	184.5
107.5°	212.6	213.0	213.4	214.2	215.1	215.9	216.7	217.2	217.7	218.2	218.7
110°	251.1	251.5	251.8	252.3	252.8	253.3	253.8	254.3	254.8	255.3	255.8

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	288.3	288.5	288.8	289.5	290.2	290.8	291.5	291.7	291.9	292.0	292.2
115°	328.2	328.5	328.7	329.0	329.3	329.7	330.0	329.8	329.7	329.5	329.4
117.5°	365.4	365.5	365.7	366.0	366.3	366.7	367.0	367.2	367.4	367.5	367.7
120°	404.4	404.8	404.9	405.1	405.2	405.4	405.6	405.6	405.6	405.6	405.6
122.5°	441.0	441.1	441.3	441.8	442.3	442.8	443.3	443.1	443.0	442.8	442.7
125°	479.1	479.6	479.7	479.8	480.0	480.1	480.3	480.0	479.6	479.3	479.0
127.5°	515.6	515.8	515.9	516.1	516.2	516.4	516.6	516.4	516.2	516.1	515.9
130°	550.9	551.3	551.5	551.8	552.1	552.5	552.8	552.6	552.5	552.3	552.2
132.5°	587.5	588.3	588.2	588.1	587.9	587.8	587.6	587.4	587.2	587.1	586.9
135°	621.8	622.3	622.4	622.6	622.7	622.9	623.1	623.1	623.1	623.1	623.1
137.5°	655.8	656.3	656.5	656.8	657.1	657.5	657.8	658.0	658.2	658.3	658.5
140°	687.6	688.0	688.3	688.8	689.3	689.8	690.3	690.6	691.0	691.3	691.6
142.5°	719.4	719.7	720.0	720.7	721.4	722.1	722.8	723.0	723.1	723.3	723.4
145°	751.1	751.4	751.7	752.2	752.7	753.2	753.7	753.7	753.7	753.7	753.7
147.5°	779.9	780.1	780.3	780.6	781.0	781.3	781.7	782.2	782.7	783.2	783.7
150°	806.7	806.6	806.9	807.6	808.3	808.9	809.6	809.6	809.6	809.6	809.6
152.5°	832.8	833.0	833.1	833.3	833.4	833.6	833.8	834.3	834.8	835.3	835.8
155°	856.4	856.4	856.5	856.7	856.8	857.0	857.2	857.9	858.5	859.2	859.9
157.5°	877.8	877.6	877.7	877.8	878.0	878.1	878.3	879.0	879.6	880.3	881.0
160°	896.7	896.5	896.6	896.7	896.9	897.0	897.2	897.9	898.5	899.2	899.9
162.5°	914.8	914.6	914.6	914.6	914.6	914.6	914.6	915.4	916.3	917.1	918.0
165°	929.9	929.7	929.8	929.9	930.1	930.2	930.4	931.1	931.8	932.5	933.2
167.5°	942.1	941.8	941.8	941.8	941.8	941.8	941.8	942.8	943.8	944.8	945.8
170°	952.6	952.3	952.3	952.3	952.3	952.3	952.3	953.3	954.3	955.4	956.4
172.5°	960.2	959.9	959.9	959.9	959.9	959.9	959.9	960.9	961.9	962.9	963.9
175°	965.5	965.2	965.2	965.2	965.2	965.2	965.2	966.2	967.2	968.2	969.2
177.5°	969.3	969.0	968.9	968.7	968.6	968.4	968.2	969.2	970.2	971.2	972.2
180°	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1745.3	1734.4	1732.8	1735.9	1729.7	1739.1	1735.9	1739.1	1731.3	1739.1	1734.4
5°	1625.0	1621.9	1615.6	1607.8	1609.4	1610.9	1618.8	1610.9	1617.2	1618.8	1626.6
7.5°	1512.5	1506.3	1510.9	1507.8	1493.8	1490.6	1493.8	1498.4	1507.8	1514.1	1518.8
10°	1421.9	1418.8	1412.5	1407.8	1400.0	1395.3	1401.6	1395.3	1407.8	1418.8	1418.8
12.5°	1353.1	1340.6	1332.8	1331.3	1314.1	1317.2	1323.4	1328.1	1342.2	1348.4	1348.4
15°	1281.3	1271.9	1268.8	1262.5	1256.3	1262.5	1259.4	1264.1	1270.3	1276.6	1279.7
17.5°	1218.8	1217.2	1218.8	1203.1	1207.8	1200.0	1201.6	1209.4	1204.7	1209.4	1218.8
20°	1162.5	1165.6	1160.9	1154.7	1154.7	1145.3	1156.3	1153.1	1154.7	1164.1	1178.1
22.5°	1120.3	1118.8	1114.1	1109.4	1103.1	1104.7	1106.3	1103.1	1115.6	1123.4	1125.0
25°	1075.0	1071.9	1070.3	1065.6	1059.4	1065.6	1064.1	1065.6	1068.8	1081.3	1071.9
27.5°	1032.8	1026.6	1029.7	1025.0	1023.4	1025.0	1025.0	1026.6	1029.7	1031.3	1032.8
30°	996.9	990.6	989.1	985.9	984.4	985.9	989.1	985.9	998.4	996.9	996.9
32.5°	957.8	953.1	950.0	950.0	948.4	946.9	948.4	950.0	959.4	953.1	959.4
35°	920.3	917.2	917.2	914.1	912.5	912.5	912.5	918.8	915.6	920.3	920.3
37.5°	884.4	884.4	882.8	879.7	878.1	879.7	878.1	881.3	879.7	881.3	882.8
40°	846.9	843.8	842.2	842.2	837.5	832.8	837.5	837.5	839.1	843.8	845.3
42.5°	801.6	803.1	803.1	796.9	796.9	796.9	798.4	800.0	800.0	803.1	803.1
45°	762.5	759.4	759.4	759.4	756.3	757.8	760.9	760.9	760.9	760.9	757.8
47.5°	718.8	718.8	720.3	720.3	725.0	723.4	723.4	721.9	718.8	718.8	720.3
50°	678.1	682.8	684.4	684.4	685.9	687.5	687.5	684.4	682.8	678.1	678.1
52.5°	639.1	642.2	645.3	650.0	653.1	651.6	651.6	648.4	642.2	640.6	639.1
55°	596.9	601.6	607.8	612.5	617.2	618.8	618.8	612.5	606.3	598.4	598.4
57.5°	557.8	562.5	573.4	578.1	584.4	584.4	581.3	576.6	567.2	560.9	556.3
60°	518.8	526.6	534.4	543.8	551.6	553.1	548.4	542.2	531.3	523.4	517.2
62.5°	476.6	484.4	500.0	509.4	515.6	515.6	515.6	507.8	493.8	482.8	473.4
65°	435.9	443.8	457.8	470.3	475.0	479.7	475.0	467.2	456.3	443.8	434.4
67.5°	393.8	403.1	417.2	426.6	432.8	437.5	434.4	428.1	414.1	396.9	390.6
70°	346.9	351.6	371.9	381.3	390.6	393.8	390.6	381.3	367.2	348.4	342.2
72.5°	303.1	307.8	326.6	334.4	342.2	345.3	340.6	334.4	321.9	304.7	296.9
75°	253.1	260.9	270.3	282.8	292.2	295.3	290.6	285.9	270.3	259.4	253.1
77.5°	200.0	207.8	220.3	231.3	240.6	239.1	232.8	234.4	217.2	204.7	200.0
80°	151.6	157.8	167.2	176.6	181.3	181.3	179.7	173.4	167.2	157.8	150.0
82.5°	104.7	112.5	120.3	126.6	126.6	128.1	125.0	123.4	117.2	109.4	107.8
85°	62.5	64.1	70.3	70.3	76.6	73.4	71.9	76.6	70.3	65.6	64.1
87.5°	28.1	26.6	28.1	28.1	26.6	29.7	29.7	28.1	29.7	28.1	28.1
90°	15.9	16.1	16.6	17.1	17.6	18.1	17.6	17.1	16.6	16.1	15.9
92.5°	38.5	38.7	39.0	39.3	39.7	40.0	39.7	39.3	39.0	38.7	38.5
95°	63.4	63.6	63.9	64.2	64.6	64.9	64.6	64.2	63.9	63.6	63.4
97.5°	91.4	91.5	91.6	91.8	91.9	92.1	91.9	91.8	91.6	91.5	91.4
100°	122.3	122.5	122.8	123.2	123.5	123.9	123.5	123.2	122.8	122.5	122.3
102.5°	153.3	153.6	154.1	154.6	155.1	155.6	155.1	154.6	154.1	153.6	153.3
105°	185.0	185.3	185.8	186.3	186.8	187.3	186.8	186.3	185.8	185.3	185.0
107.5°	219.0	219.0	219.0	219.0	219.0	219.0	219.0	219.0	219.0	219.0	219.0
110°	256.0	255.9	255.8	255.6	255.5	255.3	255.5	255.6	255.8	255.9	256.0

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	292.3	292.1	291.8	291.5	291.1	290.8	291.1	291.5	291.8	292.1	292.3
115°	329.3	329.2	329.0	328.9	328.7	328.5	328.7	328.9	329.0	329.2	329.3
117.5°	367.8	367.5	366.8	366.1	365.5	364.8	365.5	366.1	366.8	367.5	367.8
120°	405.6	405.3	404.6	403.9	403.2	402.5	403.2	403.9	404.6	405.3	405.6
122.5°	442.6	442.3	441.8	441.3	440.8	440.3	440.8	441.3	441.8	442.3	442.6
125°	478.8	478.7	478.6	478.4	478.3	478.1	478.3	478.4	478.6	478.7	478.8
127.5°	515.8	515.6	515.3	515.0	514.6	514.3	514.6	515.0	515.3	515.6	515.8
130°	552.1	551.9	551.6	551.3	550.9	550.6	550.9	551.3	551.6	551.9	552.1
132.5°	586.8	586.5	586.0	585.5	585.0	584.5	585.0	585.5	586.0	586.5	586.8
135°	623.1	622.8	622.1	621.4	620.7	620.0	620.7	621.4	622.1	622.8	623.1
137.5°	658.6	658.2	657.3	656.5	655.6	654.8	655.6	656.5	657.3	658.2	658.6
140°	691.8	691.4	690.5	689.7	688.8	688.0	688.8	689.7	690.5	691.4	691.8
142.5°	723.5	723.1	722.2	721.4	720.5	719.7	720.5	721.4	722.2	723.1	723.5
145°	753.7	753.4	752.9	752.4	751.9	751.4	751.9	752.4	752.9	753.4	753.7
147.5°	783.9	783.2	781.9	780.6	779.2	777.9	779.2	780.6	781.9	783.2	783.9
150°	809.6	809.4	809.1	808.8	808.4	808.1	808.4	808.8	809.1	809.4	809.6
152.5°	836.0	835.7	835.0	834.3	833.7	833.0	833.7	834.3	835.0	835.7	836.0
155°	860.2	859.8	858.9	858.1	857.2	856.4	857.2	858.1	858.9	859.8	860.2
157.5°	881.3	880.7	879.6	878.4	877.3	876.1	877.3	878.4	879.6	880.7	881.3
160°	900.2	899.8	899.0	898.1	897.3	896.5	897.3	898.1	899.0	899.8	900.2
162.5°	918.4	917.9	916.9	915.8	914.8	913.8	914.8	915.8	916.9	917.9	918.4
165°	933.5	933.0	932.0	930.9	929.9	928.9	929.9	930.9	932.0	933.0	933.5
167.5°	946.3	945.8	944.8	943.8	942.8	941.8	942.8	943.8	944.8	945.8	946.3
170°	956.9	956.3	955.1	954.0	952.8	951.6	952.8	954.0	955.1	956.3	956.9
172.5°	964.4	963.9	962.9	961.9	960.9	959.9	960.9	961.9	962.9	963.9	964.4
175°	969.7	969.1	967.9	966.8	965.6	964.4	965.6	966.8	967.9	969.1	969.7
177.5°	972.7	972.1	970.9	969.8	968.6	967.4	968.6	969.8	970.9	972.1	972.7
180°	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1748.4	1739.1	1750.0	1735.9	1739.1	1756.3	1754.7	1770.3	1779.7	1778.1	1785.9
5°	1632.8	1632.8	1637.5	1635.9	1651.6	1665.6	1684.4	1700.0	1717.2	1726.6	1737.5
7.5°	1518.8	1534.4	1537.5	1545.3	1564.1	1587.5	1606.3	1629.7	1654.7	1671.9	1684.4
10°	1425.0	1437.5	1450.0	1456.3	1476.6	1507.8	1534.4	1571.9	1603.1	1621.9	1639.1
12.5°	1342.2	1356.3	1362.5	1390.6	1404.7	1425.0	1462.5	1503.1	1537.5	1557.8	1571.9
15°	1282.8	1290.6	1304.7	1321.9	1335.9	1360.9	1392.2	1437.5	1470.3	1487.5	1535.9
17.5°	1232.8	1242.2	1250.0	1257.8	1279.7	1306.3	1335.9	1375.0	1417.2	1446.9	1471.9
20°	1181.3	1185.9	1195.3	1207.8	1223.4	1248.4	1275.0	1315.6	1353.1	1376.6	1409.4
22.5°	1120.3	1134.4	1143.8	1153.1	1170.3	1198.4	1223.4	1253.1	1300.0	1326.6	1360.9
25°	1084.4	1090.6	1096.9	1107.8	1120.3	1145.3	1173.4	1204.7	1242.2	1270.3	1300.0
27.5°	1037.5	1046.9	1054.7	1068.8	1076.6	1096.9	1123.4	1154.7	1200.0	1223.4	1248.4
30°	998.4	1007.8	1014.1	1020.3	1031.3	1053.1	1078.1	1103.1	1145.3	1175.0	1200.0
32.5°	959.4	968.8	976.6	981.3	992.2	1006.3	1026.6	1057.8	1093.8	1114.1	1146.9
35°	925.0	925.0	934.4	940.6	950.0	962.5	981.3	1004.7	1042.2	1068.8	1098.4
37.5°	885.9	887.5	895.3	900.0	909.4	921.9	940.6	962.5	993.8	1014.1	1043.8
40°	845.3	850.0	853.1	860.9	871.9	876.6	895.3	920.3	951.6	970.3	995.3
42.5°	804.7	807.8	815.6	821.9	831.3	839.1	851.6	875.0	898.4	926.6	946.9
45°	759.4	767.2	771.9	782.8	787.5	795.3	807.8	826.6	854.7	871.9	895.3
47.5°	720.3	723.4	726.6	740.6	750.0	754.7	767.2	778.1	807.8	823.4	845.3
50°	678.1	678.1	682.8	689.1	700.0	709.4	720.3	732.8	756.3	771.9	793.8
52.5°	639.1	634.4	637.5	640.6	651.6	660.9	671.9	689.1	710.9	720.3	739.1
55°	596.9	589.1	593.8	598.4	601.6	614.1	626.6	637.5	654.7	668.8	685.9
57.5°	551.6	550.0	546.9	548.4	556.3	564.1	573.4	587.5	607.8	618.8	628.1
60°	510.9	501.6	498.4	501.6	506.3	510.9	523.4	535.9	553.1	564.1	575.0
62.5°	468.8	459.4	453.1	448.4	453.1	464.1	471.9	481.3	495.3	507.8	517.2
65°	428.1	414.1	407.8	404.7	403.1	410.9	417.2	429.7	442.2	446.9	457.8
67.5°	382.8	370.3	362.5	357.8	357.8	357.8	364.1	376.6	389.1	390.6	401.6
70°	337.5	323.4	315.6	309.4	306.3	309.4	317.2	318.8	329.7	332.8	339.1
72.5°	289.1	276.6	267.2	259.4	260.9	264.1	264.1	267.2	273.4	281.3	281.3
75°	243.8	226.6	221.9	215.6	212.5	212.5	212.5	218.8	223.4	229.7	228.1
77.5°	192.2	182.8	173.4	170.3	165.6	164.1	167.2	167.2	170.3	175.0	176.6
80°	148.4	137.5	131.3	128.1	121.9	120.3	121.9	121.9	126.6	125.0	126.6
82.5°	103.1	95.3	90.6	85.9	82.8	84.4	82.8	82.8	84.4	82.8	82.8
85°	59.4	57.8	54.7	53.1	51.6	48.4	51.6	50.0	48.4	46.9	50.0
87.5°	28.1	26.6	26.6	23.4	23.4	21.9	23.4	23.4	21.9	21.9	21.9
90°	15.5	14.6	13.8	12.9	12.1	10.9	9.7	8.6	7.4	6.8	6.1
92.5°	37.9	36.7	35.6	34.4	33.2	31.7	30.2	28.7	27.2	26.4	26.0
95°	62.8	61.7	60.5	59.4	58.2	56.5	54.8	53.1	51.4	50.6	50.4
97.5°	90.9	89.9	88.9	87.9	86.9	84.5	82.2	79.8	77.5	76.3	76.2
100°	121.5	120.0	118.5	117.0	115.5	113.3	111.1	109.0	106.8	105.7	105.7
102.5°	152.5	150.8	149.1	147.5	145.8	145.0	144.1	143.3	142.4	142.0	141.6
105°	184.5	183.5	182.5	181.5	180.5	179.5	178.5	177.5	176.5	176.0	175.6
107.5°	218.7	218.2	217.7	217.2	216.7	215.9	215.1	214.2	213.4	213.0	212.6
110°	255.8	255.3	254.8	254.3	253.8	253.3	252.8	252.3	251.8	251.5	251.1

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	292.2	292.0	291.9	291.7	291.5	290.8	290.2	289.5	288.8	288.5	288.3
115°	329.4	329.5	329.7	329.8	330.0	329.7	329.3	329.0	328.7	328.5	328.2
117.5°	367.7	367.5	367.4	367.2	367.0	366.7	366.3	366.0	365.7	365.5	365.4
120°	405.6	405.6	405.6	405.6	405.6	405.4	405.2	405.1	404.9	404.8	404.4
122.5°	442.7	442.8	443.0	443.1	443.3	442.8	442.3	441.8	441.3	441.1	441.0
125°	479.0	479.3	479.6	480.0	480.3	480.1	480.0	479.8	479.7	479.6	479.1
127.5°	515.9	516.1	516.2	516.4	516.6	516.4	516.2	516.1	515.9	515.8	515.6
130°	552.2	552.3	552.5	552.6	552.8	552.5	552.1	551.8	551.5	551.3	550.9
132.5°	586.9	587.1	587.2	587.4	587.6	587.8	587.9	588.1	588.2	588.3	587.5
135°	623.1	623.1	623.1	623.1	623.1	622.9	622.7	622.6	622.4	622.3	621.8
137.5°	658.5	658.3	658.2	658.0	657.8	657.5	657.1	656.8	656.5	656.3	655.8
140°	691.6	691.3	691.0	690.6	690.3	689.8	689.3	688.8	688.3	688.0	687.6
142.5°	723.4	723.3	723.1	723.0	722.8	722.1	721.4	720.7	720.0	719.7	719.4
145°	753.7	753.7	753.7	753.7	753.7	753.2	752.7	752.2	751.7	751.4	751.1
147.5°	783.7	783.2	782.7	782.2	781.7	781.3	781.0	780.6	780.3	780.1	779.9
150°	809.6	809.6	809.6	809.6	809.6	808.9	808.3	807.6	806.9	806.6	806.7
152.5°	835.8	835.3	834.8	834.3	833.8	833.6	833.4	833.3	833.1	833.0	832.8
155°	859.9	859.2	858.5	857.9	857.2	857.0	856.8	856.7	856.5	856.4	856.4
157.5°	881.0	880.3	879.6	879.0	878.3	878.1	878.0	877.8	877.7	877.6	877.8
160°	899.9	899.2	898.5	897.9	897.2	897.0	896.9	896.7	896.6	896.5	896.7
162.5°	918.0	917.1	916.3	915.4	914.6	914.6	914.6	914.6	914.6	914.6	914.8
165°	933.2	932.5	931.8	931.1	930.4	930.2	930.1	929.9	929.8	929.7	929.9
167.5°	945.8	944.8	943.8	942.8	941.8	941.8	941.8	941.8	941.8	941.8	942.1
170°	956.4	955.4	954.3	953.3	952.3	952.3	952.3	952.3	952.3	952.3	952.6
172.5°	963.9	962.9	961.9	960.9	959.9	959.9	959.9	959.9	959.9	959.9	960.2
175°	969.2	968.2	967.2	966.2	965.2	965.2	965.2	965.2	965.2	965.2	965.5
177.5°	972.2	971.2	970.2	969.2	968.2	968.4	968.6	968.7	968.9	969.0	969.3
180°	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5	970.5

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1840.6	1840.6	1840.6	1840.6
2.5°	1796.9	1812.5	1823.4	1843.8
5°	1756.3	1784.4	1810.9	1839.1
7.5°	1715.6	1748.4	1790.6	1826.6
10°	1670.3	1712.5	1762.5	1810.9
12.5°	1625.0	1675.0	1729.7	1793.8
15°	1570.3	1634.4	1698.4	1767.2
17.5°	1521.9	1587.5	1656.3	1742.2
20°	1467.2	1539.1	1614.1	1701.6
22.5°	1418.8	1498.4	1576.6	1668.8
25°	1364.1	1442.2	1528.1	1626.6
27.5°	1318.8	1390.6	1475.0	1581.3
30°	1264.1	1342.2	1426.6	1532.8
32.5°	1212.5	1287.5	1376.6	1481.3
35°	1159.4	1235.9	1315.6	1415.6
37.5°	1109.4	1175.0	1254.7	1350.0
40°	1053.1	1125.0	1196.9	1271.9
42.5°	1001.6	1067.2	1134.4	1193.8
45°	943.8	1000.0	1064.1	1112.5
47.5°	890.6	940.6	990.6	1028.1
50°	837.5	876.6	914.1	946.9
52.5°	775.0	818.8	839.1	859.4
55°	718.8	743.8	762.5	782.8
57.5°	664.1	675.0	684.4	703.1
60°	592.2	604.7	615.6	629.7
62.5°	529.7	535.9	539.1	553.1
65°	470.3	468.8	476.6	484.4
67.5°	406.3	404.7	412.5	415.6
70°	343.8	342.2	343.8	351.6
72.5°	284.4	284.4	285.9	289.1
75°	229.7	229.7	231.3	234.4
77.5°	173.4	176.6	175.0	181.3
80°	126.6	123.4	126.6	129.7
82.5°	82.8	85.9	85.9	82.8
85°	46.9	46.9	46.9	46.9
87.5°	20.3	20.3	21.9	23.4
90°	4.8	3.5	2.1	0.8
92.5°	25.2	24.3	23.5	22.7
95°	50.1	49.8	49.4	49.1
97.5°	76.0	75.9	75.7	75.5
100°	105.7	105.7	105.7	105.7
102.5°	140.7	139.9	139.0	138.2
105°	174.7	173.9	173.0	172.2
107.5°	211.7	210.9	210.0	209.2
110°	250.2	249.4	248.5	247.7

TEST NUMBER: P1035210

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	288.0	287.7	287.3	287.0
115°	327.5	326.8	326.2	325.5
117.5°	365.3	365.1	365.0	364.8
120°	403.5	402.7	401.8	401.0
122.5°	440.8	440.7	440.5	440.3
125°	478.1	477.0	476.0	475.0
127.5°	515.1	514.6	514.1	513.6
130°	550.0	549.2	548.3	547.5
132.5°	586.0	584.5	583.0	581.5
135°	620.8	619.8	618.8	617.8
137.5°	654.8	653.8	652.8	651.8
140°	686.7	685.9	685.0	684.2
142.5°	718.7	718.0	717.4	716.7
145°	750.4	749.7	749.1	748.4
147.5°	779.4	778.9	778.4	777.9
150°	806.8	807.0	807.1	807.3
152.5°	832.5	832.2	831.8	831.5
155°	856.4	856.4	856.4	856.4
157.5°	878.1	878.4	878.8	879.1
160°	897.2	897.7	898.2	898.7
162.5°	915.1	915.4	915.8	916.1
165°	930.2	930.5	930.9	931.2
167.5°	942.8	943.5	944.1	944.8
170°	953.3	954.0	954.7	955.4
172.5°	960.9	961.6	962.2	962.9
175°	966.2	966.9	967.5	968.2
177.5°	970.0	970.7	971.3	972.0
180°	970.5	970.5	970.5	970.5

(END OF REPORT)