

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035269

Luminaire Tested: S125DIW-B375D1340UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035269
REPORT IS A COMBINATION OF REPORTS P1003475 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1340UB30-4F0-XX-W2A-A
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6865.0 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	30	30	22
1	92	87	84	80	81	78	75	72	59	57	55	42	41	40	27	26	26	26	26	19
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	22	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	28	21	20	19	19	19	13
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	16	16	12
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	14	14	10
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	15	14	12	12	12	9
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11	11	11	8
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10	10	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	9	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3394	3394	3394	3394
5°	3397	3851	3400	2921
10°	3376	4389	3370	2508
15°	3352	4759	3331	2266
20°	3309	5215	3279	2069
25°	3272	5975	3212	1952
30°	3218	6304	3162	1846
35°	3132	5053	3066	1760
40°	2999	3493	2955	1671
45°	2831	2600	2799	1596
50°	2638	2141	2594	1537
55°	2430	1826	2411	1485
60°	2226	1563	2187	1444
65°	2006	1350	1974	1386
70°	1774	1120	1749	1283
75°	1528	866	1508	1114
80°	1205	586	1163	819
85°	772	292	743	417

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 5185 cd/sqm

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.0	0.7
10°-20°	151.9	2.2
20°-30°	246.7	3.6
30°-40°	301.5	4.4
40°-50°	273.5	4.0
50°-60°	217.8	3.2
60°-70°	151.7	2.2
70°-80°	80.8	1.2
80°-90°	22.6	0.3
90°-100°	59.3	0.9
100°-110°	394.4	5.7
110°-120°	710.2	10.3
120°-130°	911.5	13.3
130°-140°	980.4	14.3
140°-150°	920.1	13.4
150°-160°	744.3	10.8
160°-170°	481.3	7.0
170°-180°	166.0	2.4
0°-30°	449.6	6.5
0°-40°	751.1	10.9
0°-60°	1242.4	18.1
0°-90°	1497.6	21.8
90°-120°	1163.8	17.0
90°-150°	3975.8	57.9
90°-180°	5367.0	78.2
0°-180°	6865.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	530	530	530	530	530	
5°	529	611	530	464	529	50
15°	509	763	506	363	509	144
25°	468	939	460	307	468	216
35°	408	754	399	263	408	254
45°	320	355	317	218	320	247
55°	225	219	224	178	225	202
65°	139	134	137	138	139	138
75°	68	66	67	85	68	72
85°	14	15	13	21	14	16
90°	1	31	1	31	1	5
95°	74	27	74	27	74	90
105°	381	385	381	385	381	403
115°	715	710	715	710	715	709
125°	1017	1017	1017	1017	1017	908
135°	1268	1263	1268	1263	1268	978
145°	1470	1466	1470	1466	1470	919
155°	1619	1607	1619	1607	1619	746
165°	1708	1699	1708	1699	1708	483
175°	1747	1740	1747	1740	1747	166
180°	1747	1747	1747	1747	1747	

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8
2.5°	530.7	533.8	537.4	540.1	544.6	546.0	548.2	549.6	550.9	552.3	553.2
5°	529.3	537.0	543.7	548.7	557.2	560.4	564.4	569.4	575.2	580.2	583.3
7.5°	525.7	537.9	546.9	556.8	568.5	576.1	580.2	590.5	600.0	607.1	616.6
10°	521.2	535.6	549.6	564.4	581.1	589.6	597.7	612.1	625.1	636.8	646.3
12.5°	516.3	533.8	550.5	569.8	592.3	602.7	608.0	632.8	649.0	655.3	673.7
15°	508.7	529.3	553.2	577.0	595.9	608.0	622.9	642.7	658.9	672.8	687.7
17.5°	501.5	523.9	548.2	574.8	602.2	617.9	629.2	646.7	664.3	682.3	696.2
20°	489.8	519.0	543.7	572.1	604.5	615.7	627.4	648.1	667.0	686.3	703.8
22.5°	480.3	508.2	541.9	568.9	596.4	607.6	622.0	643.6	666.1	688.1	713.7
25°	468.2	499.2	528.4	557.2	585.6	597.7	610.7	638.6	662.0	690.4	718.7
27.5°	455.1	487.1	516.3	542.4	568.9	585.6	599.5	628.7	659.8	690.8	727.7
30°	441.2	471.3	499.2	524.8	554.1	571.2	585.1	619.3	653.9	693.5	737.6
32.5°	426.4	454.7	478.5	504.6	535.6	551.4	570.3	607.6	648.5	695.7	751.1
35°	407.5	434.4	455.6	482.1	513.2	533.4	553.2	595.0	642.7	695.3	758.7
37.5°	388.6	409.7	430.0	458.3	494.3	512.7	533.4	579.3	633.7	693.9	761.9
40°	366.1	386.8	404.3	433.1	470.9	492.0	513.6	561.7	623.3	689.0	750.6
42.5°	343.6	361.1	380.5	410.6	447.0	469.5	492.5	546.0	609.8	674.6	719.6
45°	320.2	333.7	354.8	382.3	421.0	442.5	468.6	526.6	591.0	648.5	671.0
47.5°	295.9	309.4	329.2	355.7	394.0	419.6	444.3	502.4	567.1	611.6	611.6
50°	272.5	283.3	302.7	329.2	367.9	391.3	416.5	478.1	530.2	563.1	533.8
52.5°	247.4	259.5	275.7	303.6	341.8	362.9	390.4	443.0	492.5	506.0	461.0
55°	225.3	235.2	250.5	277.0	312.6	334.6	358.0	408.4	450.2	449.3	401.2
57.5°	202.4	210.5	226.7	251.0	283.8	303.6	327.0	370.6	404.8	392.6	347.2
60°	181.2	187.1	202.8	222.6	254.1	272.5	295.0	330.6	356.6	339.6	293.7
62.5°	159.2	166.0	178.5	197.9	225.8	240.6	257.3	293.2	309.9	294.6	247.8
65°	139.4	144.8	156.1	172.3	197.4	210.9	225.3	255.0	270.7	248.7	210.0
67.5°	119.6	125.9	134.0	148.4	168.2	180.8	193.4	219.0	226.2	206.4	174.0
70°	101.2	106.6	114.2	124.6	141.2	152.5	161.9	183.0	188.0	169.6	143.9
72.5°	83.2	86.8	93.1	101.6	116.9	123.2	133.1	147.5	153.8	137.2	118.7
75°	67.5	70.2	74.2	80.5	90.8	97.6	105.7	119.2	118.7	107.0	94.0
77.5°	52.2	52.6	57.1	63.0	69.3	75.1	79.2	88.6	89.5	82.3	71.5
80°	37.3	38.7	40.5	45.0	50.4	52.6	57.6	63.4	64.3	58.9	51.7
82.5°	23.8	24.7	26.1	28.8	32.4	35.1	37.8	40.0	42.3	39.1	33.3
85°	13.5	13.9	15.3	16.2	18.0	19.3	21.6	23.8	23.4	21.1	19.3
87.5°	6.7	6.7	6.7	7.6	8.5	8.5	9.4	9.9	10.3	9.4	8.5
90°	1.3	3.6	5.9	8.2	10.5	11.7	12.7	14.7	16.7	18.7	20.7
92.5°	24.6	22.0	19.4	16.9	14.3	13.0	13.9	15.6	17.3	19.0	20.7
95°	73.8	72.9	72.1	71.2	70.3	69.9	64.4	53.5	42.6	31.6	20.7
97.5°	138.6	140.3	142.1	143.8	145.5	146.4	132.7	105.4	78.0	50.7	23.3
100°	216.3	217.2	218.0	218.9	219.8	220.2	220.8	221.9	223.1	224.2	225.4
102.5°	295.3	296.5	297.6	298.8	299.9	300.5	300.8	301.4	301.9	302.5	303.1
105°	380.8	382.0	383.1	384.3	385.4	386.0	386.0	386.0	386.0	386.0	386.0
107.5°	468.9	468.9	468.9	468.9	468.9	468.9	469.2	469.8	470.3	470.9	471.5
110°	554.4	554.4	554.4	554.4	554.4	554.4	554.7	555.3	555.8	556.4	557.0



TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	634.7	635.6	636.4	637.3	638.2	638.6	638.7	639.0	639.3	639.6	639.9
115°	715.0	716.4	717.9	719.3	720.8	721.5	721.6	721.9	722.2	722.5	722.8
117.5°	799.2	799.2	799.2	799.2	799.2	799.2	799.8	800.9	802.1	803.2	804.4
120°	876.9	876.6	876.3	876.0	875.7	875.6	876.0	876.9	877.8	878.6	879.5
122.5°	945.5	946.9	948.4	949.8	951.3	952.0	952.1	952.4	952.7	953.0	953.3
125°	1016.8	1018.8	1020.8	1022.9	1024.9	1025.9	1025.9	1025.9	1025.9	1025.9	1025.9
127.5°	1085.4	1086.8	1088.3	1089.7	1091.2	1091.9	1091.8	1091.5	1091.2	1090.9	1090.6
130°	1147.6	1149.0	1150.5	1151.9	1153.4	1154.1	1154.2	1154.5	1154.8	1155.1	1155.4
132.5°	1209.8	1211.5	1213.3	1215.0	1216.7	1217.6	1217.2	1216.3	1215.4	1214.6	1213.7
135°	1268.1	1269.8	1271.5	1273.2	1274.9	1275.8	1275.5	1275.0	1274.4	1273.9	1273.3
137.5°	1322.5	1324.2	1325.9	1327.6	1329.3	1330.2	1329.9	1329.4	1328.8	1328.3	1327.7
140°	1375.6	1376.2	1376.8	1377.3	1377.9	1378.2	1378.1	1377.8	1377.5	1377.2	1376.9
142.5°	1423.5	1423.8	1424.1	1424.4	1424.7	1424.8	1425.1	1425.7	1426.2	1426.8	1427.4
145°	1470.1	1470.7	1471.3	1471.8	1472.4	1472.7	1472.7	1472.7	1472.7	1472.7	1472.7
147.5°	1511.6	1511.6	1511.6	1511.6	1511.6	1511.6	1511.7	1512.0	1512.3	1512.6	1512.9
150°	1550.4	1549.8	1549.3	1548.7	1548.2	1547.9	1548.2	1548.7	1549.3	1549.8	1550.4
152.5°	1588.0	1586.6	1585.1	1583.7	1582.2	1581.5	1581.8	1582.4	1582.9	1583.5	1584.1
155°	1619.1	1617.4	1615.6	1613.9	1612.2	1611.3	1611.6	1612.2	1612.7	1613.3	1613.9
157.5°	1643.7	1642.8	1642.0	1641.1	1640.2	1639.8	1639.8	1639.8	1639.8	1639.8	1639.8
160°	1669.6	1667.9	1666.1	1664.4	1662.7	1661.8	1661.9	1662.2	1662.5	1662.8	1663.1
162.5°	1690.3	1688.6	1686.9	1685.2	1683.5	1682.6	1682.7	1683.0	1683.3	1683.6	1683.9
165°	1708.5	1706.8	1705.0	1703.3	1701.6	1700.7	1700.8	1701.1	1701.4	1701.7	1702.0
167.5°	1722.7	1721.0	1719.2	1717.5	1715.8	1714.9	1715.0	1715.3	1715.6	1715.9	1716.2
170°	1734.4	1732.4	1730.4	1728.3	1726.3	1725.3	1725.4	1725.7	1726.0	1726.3	1726.6
172.5°	1742.1	1740.1	1738.1	1736.1	1734.1	1733.1	1733.4	1734.0	1734.5	1735.1	1735.7
175°	1747.3	1745.6	1743.9	1742.2	1740.5	1739.6	1739.7	1740.0	1740.3	1740.5	1740.8
177.5°	1751.2	1749.5	1747.7	1746.0	1744.3	1743.4	1743.5	1743.8	1744.1	1744.4	1744.7
180°	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8
2.5°	554.1	557.2	559.9	562.2	564.0	566.7	564.9	565.3	566.2	568.0	568.0
5°	590.1	595.0	597.7	606.7	608.9	608.5	607.1	614.3	613.9	611.2	610.7
7.5°	625.1	633.7	641.3	648.5	650.8	656.6	658.0	661.1	660.2	664.7	662.5
10°	657.1	670.6	677.8	688.6	691.2	693.9	697.5	699.3	703.4	702.9	702.9
12.5°	681.8	698.0	707.4	710.1	720.5	723.6	726.8	732.6	731.3	731.7	734.4
15°	701.1	716.9	725.0	737.6	744.8	748.4	753.8	760.1	759.2	763.2	762.3
17.5°	715.5	730.4	745.2	764.1	764.6	774.0	786.6	789.3	795.1	791.1	791.1
20°	727.2	747.0	768.2	792.4	795.1	801.0	816.3	826.6	833.4	831.1	832.5
22.5°	739.8	768.2	792.9	817.2	830.2	840.6	855.4	871.6	877.4	881.0	880.1
25°	756.0	785.7	822.1	855.9	869.3	889.1	908.9	924.7	929.2	939.1	930.1
27.5°	772.7	814.5	859.9	899.5	916.6	932.8	956.6	968.3	974.1	978.6	975.5
30°	786.6	844.2	893.6	930.1	942.2	951.6	965.1	967.8	965.6	969.2	973.7
32.5°	808.2	864.4	906.2	923.8	922.4	922.0	911.6	897.2	894.1	885.5	897.2
35°	819.9	864.8	881.0	857.7	848.2	831.1	798.3	776.7	757.8	753.8	754.7
37.5°	813.1	830.7	811.3	749.7	734.4	708.3	664.7	634.1	620.2	609.4	623.3
40°	776.7	757.4	704.3	629.2	607.1	582.4	541.5	524.8	505.1	501.0	519.4
42.5°	716.4	657.5	582.4	524.4	501.5	487.5	453.3	437.6	423.7	417.4	427.7
45°	634.6	563.1	487.5	439.8	420.5	403.9	383.6	367.0	358.0	355.3	363.8
47.5°	550.0	474.5	414.2	378.7	358.4	345.8	327.0	317.5	310.3	311.2	312.6
50°	469.1	400.3	353.9	318.4	308.5	298.6	286.0	277.9	274.3	275.7	274.8
52.5°	399.4	343.6	304.5	277.0	272.5	263.1	252.8	246.0	244.7	245.1	246.5
55°	338.2	294.6	263.5	243.8	238.8	232.1	225.8	221.3	217.7	219.0	218.6
57.5°	291.9	253.7	229.8	213.6	210.0	206.0	200.1	197.9	196.5	193.8	196.1
60°	251.0	219.9	199.2	189.3	186.2	183.5	177.2	174.5	173.6	172.3	175.8
62.5°	212.3	190.2	174.5	165.5	162.4	159.7	156.5	154.3	154.7	152.9	154.7
65°	181.7	163.7	152.5	144.4	140.3	138.5	138.1	134.5	134.0	134.5	134.9
67.5°	153.4	138.1	129.5	124.6	121.4	119.6	118.3	116.0	117.8	116.5	117.4
70°	127.7	117.4	108.4	103.4	102.1	102.5	100.3	99.4	99.8	98.9	99.8
72.5°	103.0	94.4	90.8	87.2	85.5	85.0	83.7	82.3	83.7	83.2	83.2
75°	82.3	76.0	72.0	69.7	69.7	68.8	66.6	66.6	66.6	66.1	66.6
77.5°	63.4	58.0	56.2	54.0	54.0	52.6	52.2	52.2	51.3	52.6	51.7
80°	47.2	43.2	40.5	39.1	39.1	38.7	37.8	37.3	37.8	37.3	37.3
82.5°	30.6	28.8	27.4	26.1	25.6	26.1	25.6	24.7	25.2	24.7	25.6
85°	17.5	15.7	15.7	14.8	15.3	14.4	14.8	13.9	13.5	14.8	13.9
87.5°	7.6	7.2	7.2	6.3	6.3	6.3	5.8	6.3	5.8	5.4	5.8
90°	22.1	23.6	25.0	26.5	27.2	27.6	28.5	29.4	30.2	31.1	30.2
92.5°	22.1	23.6	25.0	26.5	27.2	27.3	27.6	27.9	28.2	28.5	28.2
95°	22.1	23.6	25.0	26.5	27.2	27.2	27.2	27.2	27.2	27.2	27.2
97.5°	23.9	24.5	25.0	25.6	25.9	26.0	26.3	26.6	26.9	27.2	26.9
100°	182.5	139.6	96.7	53.8	32.4	31.8	30.7	29.5	28.4	27.2	28.4
102.5°	303.7	304.3	304.8	305.4	305.7	293.6	269.4	245.3	221.1	196.9	221.1
105°	386.0	386.0	386.0	386.0	386.0	385.9	385.6	385.3	385.0	384.7	385.0
107.5°	471.8	472.1	472.4	472.7	472.8	472.2	471.1	469.9	468.8	467.6	468.8
110°	556.1	555.3	554.4	553.5	553.1	553.2	553.5	553.8	554.1	554.4	554.1

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	638.7	637.6	636.4	635.3	634.7	634.4	633.8	633.3	632.7	632.1	632.7
115°	721.6	720.5	719.3	718.2	717.6	716.7	715.0	713.3	711.5	709.8	711.5
117.5°	802.7	800.9	799.2	797.5	796.6	796.3	795.7	795.2	794.6	794.0	794.6
120°	878.9	878.3	877.8	877.2	876.9	876.2	874.7	873.3	871.8	870.4	871.8
122.5°	952.7	952.1	951.6	951.0	950.7	949.8	948.1	946.4	944.7	943.0	944.7
125°	1024.7	1023.6	1022.4	1021.3	1020.7	1020.3	1019.4	1018.5	1017.7	1016.8	1017.7
127.5°	1090.0	1089.4	1088.9	1088.3	1088.0	1086.9	1084.6	1082.3	1080.0	1077.7	1080.0
130°	1154.5	1153.7	1152.8	1151.9	1151.5	1150.8	1149.3	1147.9	1146.4	1145.0	1146.4
132.5°	1213.7	1213.7	1213.7	1213.7	1213.7	1213.0	1211.5	1210.1	1208.6	1207.2	1208.6
135°	1272.7	1272.1	1271.6	1271.0	1270.7	1269.8	1268.1	1266.4	1264.6	1262.9	1264.6
137.5°	1327.7	1327.7	1327.7	1327.7	1327.7	1327.0	1325.5	1324.1	1322.6	1321.2	1322.6
140°	1377.5	1378.1	1378.6	1379.2	1379.5	1378.6	1376.9	1375.2	1373.4	1371.7	1373.4
142.5°	1427.4	1427.4	1427.4	1427.4	1427.4	1426.5	1424.8	1423.1	1421.3	1419.6	1421.3
145°	1473.0	1473.3	1473.6	1473.9	1474.0	1473.1	1471.4	1469.7	1467.9	1466.2	1467.9
147.5°	1513.2	1513.5	1513.8	1514.1	1514.2	1513.2	1511.2	1509.1	1507.1	1505.1	1507.1
150°	1551.0	1551.6	1552.1	1552.7	1553.0	1551.9	1549.6	1547.3	1545.0	1542.7	1545.0
152.5°	1584.7	1585.3	1585.8	1586.4	1586.7	1585.7	1583.7	1581.6	1579.6	1577.6	1579.6
155°	1614.8	1615.6	1616.5	1617.4	1617.8	1616.6	1614.3	1612.0	1609.7	1607.4	1609.7
157.5°	1640.7	1641.5	1642.4	1643.3	1643.7	1642.5	1640.2	1637.9	1635.6	1633.3	1635.6
160°	1664.3	1665.4	1666.6	1667.7	1668.3	1667.1	1664.8	1662.5	1660.2	1657.9	1660.2
162.5°	1685.6	1687.3	1689.0	1690.7	1691.6	1690.3	1687.7	1685.2	1682.6	1680.0	1682.6
165°	1703.7	1705.5	1707.2	1708.9	1709.8	1708.6	1706.3	1704.0	1701.7	1699.4	1701.7
167.5°	1718.2	1720.2	1722.3	1724.3	1725.3	1724.0	1721.4	1718.8	1716.2	1713.6	1716.2
170°	1728.9	1731.2	1733.5	1735.8	1737.0	1735.7	1733.1	1730.5	1727.9	1725.3	1727.9
172.5°	1737.7	1739.7	1741.7	1743.7	1744.7	1743.4	1740.8	1738.3	1735.7	1733.1	1735.7
175°	1743.1	1745.4	1747.7	1750.0	1751.2	1749.9	1747.3	1744.8	1742.2	1739.6	1742.2
177.5°	1746.7	1748.7	1750.8	1752.8	1753.8	1752.6	1750.3	1748.0	1745.7	1743.4	1745.7
180°	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8
2.5°	567.1	564.0	564.9	564.0	561.7	560.4	556.8	552.3	550.5	548.2	546.9
5°	612.5	610.3	609.8	606.2	605.3	600.0	591.0	586.5	581.1	575.7	570.3
7.5°	662.0	659.3	650.3	649.0	649.9	643.1	631.4	622.4	611.2	603.6	593.2
10°	702.9	697.5	689.9	690.4	687.2	678.2	666.5	657.1	640.9	631.0	616.1
12.5°	727.7	723.2	722.3	717.8	715.1	703.4	689.5	677.3	665.2	651.7	640.4
15°	757.8	752.0	747.9	741.6	739.8	727.7	712.4	698.4	684.5	671.9	648.1
17.5°	791.1	784.8	769.5	768.2	757.4	745.7	730.8	710.1	695.3	677.3	659.8
20°	828.9	819.9	800.1	795.1	786.6	767.3	747.0	724.1	700.2	681.8	661.1
22.5°	871.1	855.4	841.0	825.3	819.0	795.1	767.3	739.4	710.6	685.4	660.7
25°	926.0	905.3	885.1	869.3	858.6	827.5	790.2	753.3	720.0	687.2	654.8
27.5°	969.2	951.2	929.2	908.5	894.5	857.7	814.9	767.3	725.9	685.9	651.2
30°	972.3	966.9	953.4	942.2	926.9	887.3	840.1	786.1	734.9	686.3	644.0
32.5°	913.4	924.2	930.1	931.9	928.7	905.8	862.6	803.2	743.0	682.3	637.7
35°	786.6	815.4	850.9	864.4	877.4	889.6	867.1	815.4	745.7	681.4	627.8
37.5°	647.6	673.7	732.6	759.6	774.9	823.0	841.5	813.6	751.1	682.3	618.4
40°	522.6	564.0	606.2	642.7	666.5	720.5	777.6	783.9	743.4	673.7	606.2
42.5°	439.8	464.1	496.1	529.8	550.9	614.8	692.1	737.6	719.6	659.8	591.4
45°	374.6	392.6	422.8	434.0	461.0	522.1	604.0	669.7	678.7	637.7	574.3
47.5°	321.6	336.9	356.2	370.1	391.7	437.6	506.9	579.3	622.4	607.6	550.5
50°	283.3	295.9	312.1	320.2	334.2	375.5	427.7	499.7	557.7	562.6	519.4
52.5°	251.4	258.6	271.2	280.2	291.4	316.6	363.8	423.2	488.4	515.4	481.2
55°	223.5	229.4	240.6	246.5	252.3	273.9	310.8	364.7	425.9	461.4	442.1
57.5°	198.3	203.3	212.7	218.1	221.3	242.0	270.3	312.6	367.4	410.6	399.8
60°	177.6	182.1	187.5	191.6	195.2	212.3	232.1	266.2	315.3	357.1	354.4
62.5°	155.6	159.7	165.5	169.6	172.7	183.5	200.1	226.2	268.0	306.7	314.4
65°	136.3	139.4	143.5	145.3	149.3	157.4	170.9	194.3	228.5	263.1	268.5
67.5°	118.7	119.6	122.3	126.4	127.3	134.5	146.6	164.2	190.7	219.0	227.6
70°	99.8	101.2	103.4	106.6	108.4	112.9	123.2	134.9	157.9	182.6	188.9
72.5°	83.2	85.0	85.9	87.7	88.6	95.8	100.3	112.0	127.7	148.4	155.2
75°	67.5	69.3	69.7	70.6	71.5	74.7	81.0	88.1	101.2	114.7	123.7
77.5°	53.5	53.1	54.0	55.3	54.9	57.6	61.6	67.9	76.5	87.7	93.5
80°	37.8	37.8	39.1	40.5	40.0	42.7	44.1	48.6	55.8	63.0	65.2
82.5°	25.2	25.2	26.5	26.5	27.4	27.9	29.7	31.9	37.8	41.4	42.7
85°	14.4	14.4	14.8	14.8	14.8	15.7	17.1	18.0	19.8	22.0	22.9
87.5°	5.8	6.3	6.3	6.3	6.3	7.2	7.2	8.1	8.5	9.4	9.4
90°	29.4	28.5	27.6	27.2	26.5	25.0	23.6	22.1	20.7	18.7	16.7
92.5°	27.9	27.6	27.3	27.2	26.5	25.0	23.6	22.1	20.7	19.0	17.3
95°	27.2	27.2	27.2	27.2	26.5	25.0	23.6	22.1	20.7	31.6	42.6
97.5°	26.6	26.3	26.0	25.9	25.6	25.0	24.5	23.9	23.3	50.7	78.0
100°	29.5	30.7	31.8	32.4	53.8	96.7	139.6	182.5	225.4	224.2	223.1
102.5°	245.3	269.4	293.6	305.7	305.4	304.8	304.3	303.7	303.1	302.5	301.9
105°	385.3	385.6	385.9	386.0	386.0	386.0	386.0	386.0	386.0	386.0	386.0
107.5°	469.9	471.1	472.2	472.8	472.7	472.4	472.1	471.8	471.5	470.9	470.3
110°	553.8	553.5	553.2	553.1	553.5	554.4	555.3	556.1	557.0	556.4	555.8

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	633.3	633.8	634.4	634.7	635.3	636.4	637.6	638.7	639.9	639.6	639.3
115°	713.3	715.0	716.7	717.6	718.2	719.3	720.5	721.6	722.8	722.5	722.2
117.5°	795.2	795.7	796.3	796.6	797.5	799.2	800.9	802.7	804.4	803.2	802.1
120°	873.3	874.7	876.2	876.9	877.2	877.8	878.3	878.9	879.5	878.6	877.8
122.5°	946.4	948.1	949.8	950.7	951.0	951.6	952.1	952.7	953.3	953.0	952.7
125°	1018.5	1019.4	1020.3	1020.7	1021.3	1022.4	1023.6	1024.7	1025.9	1025.9	1025.9
127.5°	1082.3	1084.6	1086.9	1088.0	1088.3	1088.9	1089.4	1090.0	1090.6	1090.9	1091.2
130°	1147.9	1149.3	1150.8	1151.5	1151.9	1152.8	1153.7	1154.5	1155.4	1155.1	1154.8
132.5°	1210.1	1211.5	1213.0	1213.7	1213.7	1213.7	1213.7	1213.7	1213.7	1214.6	1215.4
135°	1266.4	1268.1	1269.8	1270.7	1271.0	1271.6	1272.1	1272.7	1273.3	1273.9	1274.4
137.5°	1324.1	1325.5	1327.0	1327.7	1327.7	1327.7	1327.7	1327.7	1327.7	1328.3	1328.8
140°	1375.2	1376.9	1378.6	1379.5	1379.2	1378.6	1378.1	1377.5	1376.9	1377.2	1377.5
142.5°	1423.1	1424.8	1426.5	1427.4	1427.4	1427.4	1427.4	1427.4	1427.4	1426.8	1426.2
145°	1469.7	1471.4	1473.1	1474.0	1473.9	1473.6	1473.3	1473.0	1472.7	1472.7	1472.7
147.5°	1509.1	1511.2	1513.2	1514.2	1514.1	1513.8	1513.5	1513.2	1512.9	1512.6	1512.3
150°	1547.3	1549.6	1551.9	1553.0	1552.7	1552.1	1551.6	1551.0	1550.4	1549.8	1549.3
152.5°	1581.6	1583.7	1585.7	1586.7	1586.4	1585.8	1585.3	1584.7	1584.1	1583.5	1582.9
155°	1612.0	1614.3	1616.6	1617.8	1617.4	1616.5	1615.6	1614.8	1613.9	1613.3	1612.7
157.5°	1637.9	1640.2	1642.5	1643.7	1643.3	1642.4	1641.5	1640.7	1639.8	1639.8	1639.8
160°	1662.5	1664.8	1667.1	1668.3	1667.7	1666.6	1665.4	1664.3	1663.1	1662.8	1662.5
162.5°	1685.2	1687.7	1690.3	1691.6	1690.7	1689.0	1687.3	1685.6	1683.9	1683.6	1683.3
165°	1704.0	1706.3	1708.6	1709.8	1708.9	1707.2	1705.5	1703.7	1702.0	1701.7	1701.4
167.5°	1718.8	1721.4	1724.0	1725.3	1724.3	1722.3	1720.2	1718.2	1716.2	1715.9	1715.6
170°	1730.5	1733.1	1735.7	1737.0	1735.8	1733.5	1731.2	1728.9	1726.6	1726.3	1726.0
172.5°	1738.3	1740.8	1743.4	1744.7	1743.7	1741.7	1739.7	1737.7	1735.7	1735.1	1734.5
175°	1744.8	1747.3	1749.9	1751.2	1750.0	1747.7	1745.4	1743.1	1740.8	1740.5	1740.3
177.5°	1748.0	1750.3	1752.6	1753.8	1752.8	1750.8	1748.7	1746.7	1744.7	1744.4	1744.1
180°	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8
2.5°	545.1	542.8	540.1	540.1	537.0	535.6	532.9	532.0	529.8	526.2	523.5
5°	564.4	558.6	555.0	551.8	545.1	540.1	535.2	529.8	524.4	518.1	510.9
7.5°	583.3	572.5	567.6	562.2	552.3	541.9	532.0	524.8	517.7	507.8	498.8
10°	603.1	589.6	580.6	573.4	558.1	545.1	530.7	520.3	509.1	496.5	484.8
12.5°	619.7	602.2	594.6	581.1	563.5	547.8	529.8	514.1	499.2	484.4	470.0
15°	633.7	617.0	598.2	592.8	568.5	546.0	525.7	505.5	487.1	472.2	455.6
17.5°	638.2	617.0	607.6	594.6	565.8	542.4	516.8	494.7	477.2	455.1	442.1
20°	639.5	619.3	606.2	594.1	568.5	537.4	512.3	485.3	464.1	442.1	421.4
22.5°	635.9	612.1	599.5	587.8	559.0	532.5	503.3	473.6	448.8	428.6	407.9
25°	629.2	601.3	589.2	576.6	549.1	519.9	488.0	459.6	436.7	412.4	392.2
27.5°	620.2	588.3	574.3	561.3	534.3	506.9	476.7	447.5	421.9	396.2	377.3
30°	608.9	572.1	559.5	542.4	516.3	490.2	462.8	433.5	404.8	380.5	359.8
32.5°	594.6	555.9	539.2	523.0	494.7	470.9	444.8	417.4	389.5	365.6	344.1
35°	581.5	537.4	519.0	502.8	471.3	446.1	424.6	398.9	374.2	349.4	330.1
37.5°	564.0	519.0	497.0	480.3	448.4	422.8	402.5	382.7	356.6	332.8	314.8
40°	545.5	496.1	475.4	458.7	425.5	397.6	378.2	360.7	339.6	317.5	298.6
42.5°	528.9	474.0	452.0	431.8	398.0	373.3	353.5	340.0	320.7	300.9	283.8
45°	507.8	450.6	426.8	405.7	373.3	346.3	327.4	316.6	302.2	282.9	268.0
47.5°	486.2	425.5	400.7	380.0	345.0	321.1	302.7	292.3	282.4	267.1	252.3
50°	457.8	398.9	376.4	352.6	318.0	293.7	278.4	268.0	260.4	249.6	237.0
52.5°	426.8	371.5	347.2	326.5	292.3	270.3	252.8	246.9	239.3	231.2	220.4
55°	394.0	341.8	318.4	298.2	266.7	244.2	229.8	223.5	217.7	211.4	204.2
57.5°	361.1	310.8	288.7	270.7	241.5	219.9	208.2	199.7	195.6	192.0	186.2
60°	320.2	277.5	260.4	244.2	215.4	195.6	184.4	178.1	174.5	172.7	170.0
62.5°	284.2	249.2	230.3	214.5	191.6	174.0	163.3	158.3	155.2	154.3	151.1
65°	246.0	215.9	201.0	187.5	167.8	152.0	143.0	137.2	134.9	134.5	134.5
67.5°	210.0	185.7	170.9	161.5	144.4	130.4	121.9	119.6	118.3	116.5	116.0
70°	176.3	157.0	143.9	135.8	120.5	110.2	103.4	99.8	99.8	98.5	97.6
72.5°	146.6	127.3	118.7	112.0	99.4	90.4	85.5	84.6	81.4	81.0	81.0
75°	114.7	100.3	94.4	88.6	79.2	72.9	68.8	66.6	64.8	64.8	65.2
77.5°	86.4	76.5	71.1	66.6	59.8	55.8	52.6	51.7	49.9	49.9	49.9
80°	61.2	55.8	51.7	48.1	43.2	39.6	37.8	36.0	36.0	35.5	36.0
82.5°	39.6	35.1	32.8	32.4	27.9	26.5	24.3	24.7	23.4	22.9	23.8
85°	22.9	20.7	18.0	17.1	15.3	13.5	12.6	13.0	12.6	12.1	12.6
87.5°	9.0	7.6	7.2	7.2	5.8	5.4	4.9	5.4	4.5	4.5	4.9
90°	14.7	12.7	11.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	15.6	13.9	13.0	14.3	16.9	19.4	22.0	24.6	22.0	19.4	16.9
95°	53.5	64.4	69.9	70.3	71.2	72.1	72.9	73.8	72.9	72.1	71.2
97.5°	105.4	132.7	146.4	145.5	143.8	142.1	140.3	138.6	140.3	142.1	143.8
100°	221.9	220.8	220.2	219.8	218.9	218.0	217.2	216.3	217.2	218.0	218.9
102.5°	301.4	300.8	300.5	299.9	298.8	297.6	296.5	295.3	296.5	297.6	298.8
105°	386.0	386.0	386.0	385.4	384.3	383.1	382.0	380.8	382.0	383.1	384.3
107.5°	469.8	469.2	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9
110°	555.3	554.7	554.4	554.4	554.4	554.4	554.4	554.4	554.4	554.4	554.4

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	639.0	638.7	638.6	638.2	637.3	636.4	635.6	634.7	635.6	636.4	637.3
115°	721.9	721.6	721.5	720.8	719.3	717.9	716.4	715.0	716.4	717.9	719.3
117.5°	800.9	799.8	799.2	799.2	799.2	799.2	799.2	799.2	799.2	799.2	799.2
120°	876.9	876.0	875.6	875.7	876.0	876.3	876.6	876.9	876.6	876.3	876.0
122.5°	952.4	952.1	952.0	951.3	949.8	948.4	946.9	945.5	946.9	948.4	949.8
125°	1025.9	1025.9	1025.9	1024.9	1022.9	1020.8	1018.8	1016.8	1018.8	1020.8	1022.9
127.5°	1091.5	1091.8	1091.9	1091.2	1089.7	1088.3	1086.8	1085.4	1086.8	1088.3	1089.7
130°	1154.5	1154.2	1154.1	1153.4	1151.9	1150.5	1149.0	1147.6	1149.0	1150.5	1151.9
132.5°	1216.3	1217.2	1217.6	1216.7	1215.0	1213.3	1211.5	1209.8	1211.5	1213.3	1215.0
135°	1275.0	1275.5	1275.8	1274.9	1273.2	1271.5	1269.8	1268.1	1269.8	1271.5	1273.2
137.5°	1329.4	1329.9	1330.2	1329.3	1327.6	1325.9	1324.2	1322.5	1324.2	1325.9	1327.6
140°	1377.8	1378.1	1378.2	1377.9	1377.3	1376.8	1376.2	1375.6	1376.2	1376.8	1377.3
142.5°	1425.7	1425.1	1424.8	1424.7	1424.4	1424.1	1423.8	1423.5	1423.8	1424.1	1424.4
145°	1472.7	1472.7	1472.7	1472.4	1471.8	1471.3	1470.7	1470.1	1470.7	1471.3	1471.8
147.5°	1512.0	1511.7	1511.6	1511.6	1511.6	1511.6	1511.6	1511.6	1511.6	1511.6	1511.6
150°	1548.7	1548.2	1547.9	1548.2	1548.7	1549.3	1549.8	1550.4	1549.8	1549.3	1548.7
152.5°	1582.4	1581.8	1581.5	1582.2	1583.7	1585.1	1586.6	1588.0	1586.6	1585.1	1583.7
155°	1612.2	1611.6	1611.3	1612.2	1613.9	1615.6	1617.4	1619.1	1617.4	1615.6	1613.9
157.5°	1639.8	1639.8	1639.8	1640.2	1641.1	1642.0	1642.8	1643.7	1642.8	1642.0	1641.1
160°	1662.2	1661.9	1661.8	1662.7	1664.4	1666.1	1667.9	1669.6	1667.9	1666.1	1664.4
162.5°	1683.0	1682.7	1682.6	1683.5	1685.2	1686.9	1688.6	1690.3	1688.6	1686.9	1685.2
165°	1701.1	1700.8	1700.7	1701.6	1703.3	1705.0	1706.8	1708.5	1706.8	1705.0	1703.3
167.5°	1715.3	1715.0	1714.9	1715.8	1717.5	1719.2	1721.0	1722.7	1721.0	1719.2	1717.5
170°	1725.7	1725.4	1725.3	1726.3	1728.3	1730.4	1732.4	1734.4	1732.4	1730.4	1728.3
172.5°	1734.0	1733.4	1733.1	1734.1	1736.1	1738.1	1740.1	1742.1	1740.1	1738.1	1736.1
175°	1740.0	1739.7	1739.6	1740.5	1742.2	1743.9	1745.6	1747.3	1745.6	1743.9	1742.2
177.5°	1743.8	1743.5	1743.4	1744.3	1746.0	1747.7	1749.5	1751.2	1749.5	1747.7	1746.0
180°	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8
2.5°	522.6	521.7	519.4	518.1	513.6	508.2	506.4	501.9	503.7	500.6	500.6
5°	508.7	504.6	501.9	497.9	489.3	483.5	477.2	474.0	472.2	470.0	468.2
7.5°	490.7	487.5	484.8	477.2	467.7	459.6	452.0	448.8	443.0	438.9	437.1
10°	474.9	470.4	464.1	455.1	445.2	434.9	428.2	421.4	416.9	414.7	409.7
12.5°	458.7	453.3	446.6	433.5	422.8	416.5	404.3	398.0	395.8	394.0	388.1
15°	442.1	436.2	428.2	416.0	406.6	391.7	384.5	379.6	374.2	373.7	369.2
17.5°	427.3	420.1	413.3	398.5	386.8	373.7	369.7	364.3	359.3	353.9	351.7
20°	408.4	401.6	396.7	380.5	367.4	359.3	352.6	348.1	345.0	339.6	338.7
22.5°	391.3	384.1	377.3	365.2	353.9	343.6	335.5	330.6	329.2	327.0	322.9
25°	374.6	367.4	359.3	348.1	336.4	329.2	322.0	318.9	316.2	312.6	309.4
27.5°	360.7	353.9	346.3	332.4	322.5	317.1	309.4	305.8	302.2	300.4	299.1
30°	344.1	336.4	330.6	319.8	309.0	301.8	296.4	293.2	290.1	288.3	287.4
32.5°	327.9	320.7	316.6	304.9	296.4	287.8	283.8	281.5	279.7	277.9	276.1
35°	314.8	307.6	301.3	290.5	282.0	276.1	273.0	269.4	268.0	266.2	266.2
37.5°	298.6	293.2	286.9	276.6	268.9	264.4	261.7	257.3	256.8	255.9	254.6
40°	284.7	279.3	273.4	264.4	257.7	252.3	248.7	246.5	245.1	244.2	243.3
42.5°	269.8	264.0	261.3	251.0	245.1	239.7	237.9	235.7	235.2	233.4	231.2
45°	255.5	250.5	245.1	237.5	232.5	228.0	225.3	223.5	221.3	220.8	219.5
47.5°	242.9	237.0	232.1	224.9	219.5	215.9	213.6	211.4	209.6	208.2	206.9
50°	226.7	222.2	218.1	210.5	206.0	202.4	199.2	197.4	195.6	195.6	195.6
52.5°	210.9	206.9	203.3	197.9	192.5	189.3	185.7	184.4	183.5	182.1	183.5
55°	195.6	191.6	188.0	183.9	177.6	174.9	171.4	170.0	170.5	170.5	171.8
57.5°	179.4	176.3	174.0	169.1	163.3	160.6	158.3	157.0	157.0	158.8	159.2
60°	163.7	160.6	156.5	152.0	148.4	145.3	143.9	144.4	144.4	145.3	147.5
62.5°	146.2	144.4	142.1	135.8	133.6	131.3	129.5	130.9	130.4	132.7	135.8
65°	130.0	128.2	125.0	121.9	119.2	116.9	116.5	116.9	117.8	120.1	123.7
67.5°	112.0	112.0	109.3	106.6	104.3	102.1	102.5	103.0	103.9	106.6	112.0
70°	97.1	95.3	92.6	90.8	89.0	88.1	87.2	89.0	91.7	93.5	97.6
72.5°	81.0	79.6	77.4	75.6	75.1	74.2	73.8	74.7	77.4	80.5	85.0
75°	63.9	64.3	63.0	61.6	61.6	60.3	61.2	61.2	63.9	67.0	70.6
77.5°	49.5	49.0	48.6	47.7	47.2	47.2	47.2	48.1	50.8	52.6	56.2
80°	35.1	35.5	34.2	34.6	34.2	34.6	34.6	36.4	37.8	40.0	42.7
82.5°	23.4	23.4	22.5	22.9	22.9	22.9	23.4	24.3	26.1	27.9	29.7
85°	13.0	13.5	12.6	13.5	13.5	13.5	13.9	14.4	15.7	16.2	18.0
87.5°	4.9	5.8	5.8	4.9	5.4	5.8	6.3	5.8	6.7	7.6	8.1
90°	10.5	11.7	12.7	14.7	16.7	18.7	20.7	22.1	23.6	25.0	26.5
92.5°	14.3	13.0	13.9	15.6	17.3	19.0	20.7	22.1	23.6	25.0	26.5
95°	70.3	69.9	64.4	53.5	42.6	31.6	20.7	22.1	23.6	25.0	26.5
97.5°	145.5	146.4	132.7	105.4	78.0	50.7	23.3	23.9	24.5	25.0	25.6
100°	219.8	220.2	220.8	221.9	223.1	224.2	225.4	182.5	139.6	96.7	53.8
102.5°	299.9	300.5	300.8	301.4	301.9	302.5	303.1	303.7	304.3	304.8	305.4
105°	385.4	386.0	386.0	386.0	386.0	386.0	386.0	386.0	386.0	386.0	386.0
107.5°	468.9	468.9	469.2	469.8	470.3	470.9	471.5	471.8	472.1	472.4	472.7
110°	554.4	554.4	554.7	555.3	555.8	556.4	557.0	556.1	555.3	554.4	553.5

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	638.2	638.6	638.7	639.0	639.3	639.6	639.9	638.7	637.6	636.4	635.3
115°	720.8	721.5	721.6	721.9	722.2	722.5	722.8	721.6	720.5	719.3	718.2
117.5°	799.2	799.2	799.8	800.9	802.1	803.2	804.4	802.7	800.9	799.2	797.5
120°	875.7	875.6	876.0	876.9	877.8	878.6	879.5	878.9	878.3	877.8	877.2
122.5°	951.3	952.0	952.1	952.4	952.7	953.0	953.3	952.7	952.1	951.6	951.0
125°	1024.9	1025.9	1025.9	1025.9	1025.9	1025.9	1025.9	1024.7	1023.6	1022.4	1021.3
127.5°	1091.2	1091.9	1091.8	1091.5	1091.2	1090.9	1090.6	1090.0	1089.4	1088.9	1088.3
130°	1153.4	1154.1	1154.2	1154.5	1154.8	1155.1	1155.4	1154.5	1153.7	1152.8	1151.9
132.5°	1216.7	1217.6	1217.2	1216.3	1215.4	1214.6	1213.7	1213.7	1213.7	1213.7	1213.7
135°	1274.9	1275.8	1275.5	1275.0	1274.4	1273.9	1273.3	1272.7	1272.1	1271.6	1271.0
137.5°	1329.3	1330.2	1329.9	1329.4	1328.8	1328.3	1327.7	1327.7	1327.7	1327.7	1327.7
140°	1377.9	1378.2	1378.1	1377.8	1377.5	1377.2	1376.9	1377.5	1378.1	1378.6	1379.2
142.5°	1424.7	1424.8	1425.1	1425.7	1426.2	1426.8	1427.4	1427.4	1427.4	1427.4	1427.4
145°	1472.4	1472.7	1472.7	1472.7	1472.7	1472.7	1472.7	1473.0	1473.3	1473.6	1473.9
147.5°	1511.6	1511.6	1511.7	1512.0	1512.3	1512.6	1512.9	1513.2	1513.5	1513.8	1514.1
150°	1548.2	1547.9	1548.2	1548.7	1549.3	1549.8	1550.4	1551.0	1551.6	1552.1	1552.7
152.5°	1582.2	1581.5	1581.8	1582.4	1582.9	1583.5	1584.1	1584.7	1585.3	1585.8	1586.4
155°	1612.2	1611.3	1611.6	1612.2	1612.7	1613.3	1613.9	1614.8	1615.6	1616.5	1617.4
157.5°	1640.2	1639.8	1639.8	1639.8	1639.8	1639.8	1639.8	1640.7	1641.5	1642.4	1643.3
160°	1662.7	1661.8	1661.9	1662.2	1662.5	1662.8	1663.1	1664.3	1665.4	1666.6	1667.7
162.5°	1683.5	1682.6	1682.7	1683.0	1683.3	1683.6	1683.9	1685.6	1687.3	1689.0	1690.7
165°	1701.6	1700.7	1700.8	1701.1	1701.4	1701.7	1702.0	1703.7	1705.5	1707.2	1708.9
167.5°	1715.8	1714.9	1715.0	1715.3	1715.6	1715.9	1716.2	1718.2	1720.2	1722.3	1724.3
170°	1726.3	1725.3	1725.4	1725.7	1726.0	1726.3	1726.6	1728.9	1731.2	1733.5	1735.8
172.5°	1734.1	1733.1	1733.4	1734.0	1734.5	1735.1	1735.7	1737.7	1739.7	1741.7	1743.7
175°	1740.5	1739.6	1739.7	1740.0	1740.3	1740.5	1740.8	1743.1	1745.4	1747.7	1750.0
177.5°	1744.3	1743.4	1743.5	1743.8	1744.1	1744.4	1744.7	1746.7	1748.7	1750.8	1752.8
180°	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8
2.5°	502.4	499.2	498.8	499.7	497.9	500.6	499.7	500.6	498.3	500.6	499.2
5°	467.7	466.8	465.0	462.8	463.2	463.7	465.9	463.7	465.5	465.9	468.2
7.5°	435.3	433.5	434.9	434.0	430.0	429.1	430.0	431.3	434.0	435.8	437.1
10°	409.3	408.4	406.6	405.2	403.0	401.6	403.4	401.6	405.2	408.4	408.4
12.5°	389.5	385.9	383.6	383.2	378.2	379.1	380.9	382.3	386.3	388.1	388.1
15°	368.8	366.1	365.2	363.4	361.6	363.4	362.5	363.8	365.6	367.4	368.3
17.5°	350.8	350.3	350.8	346.3	347.6	345.4	345.8	348.1	346.7	348.1	350.8
20°	334.6	335.5	334.2	332.4	332.4	329.7	332.8	331.9	332.4	335.1	339.1
22.5°	322.5	322.0	320.7	319.3	317.5	318.0	318.4	317.5	321.1	323.4	323.8
25°	309.4	308.5	308.1	306.7	304.9	306.7	306.3	306.7	307.6	311.2	308.5
27.5°	297.3	295.5	296.4	295.0	294.6	295.0	295.0	295.5	296.4	296.8	297.3
30°	286.9	285.1	284.7	283.8	283.3	283.8	284.7	283.8	287.4	286.9	286.9
32.5°	275.7	274.3	273.4	273.4	273.0	272.5	273.0	273.4	276.1	274.3	276.1
35°	264.9	264.0	264.0	263.1	262.6	262.6	262.6	264.4	263.5	264.9	264.9
37.5°	254.6	254.6	254.1	253.2	252.8	253.2	252.8	253.7	253.2	253.7	254.1
40°	243.8	242.9	242.4	242.4	241.1	239.7	241.1	241.1	241.5	242.9	243.3
42.5°	230.7	231.2	231.2	229.4	229.4	229.4	229.8	230.3	230.3	231.2	231.2
45°	219.5	218.6	218.6	218.6	217.7	218.1	219.0	219.0	219.0	219.0	218.1
47.5°	206.9	206.9	207.3	207.3	208.7	208.2	208.2	207.8	206.9	206.9	207.3
50°	195.2	196.5	197.0	197.0	197.4	197.9	197.9	197.0	196.5	195.2	195.2
52.5°	183.9	184.8	185.7	187.1	188.0	187.5	187.5	186.6	184.8	184.4	183.9
55°	171.8	173.1	174.9	176.3	177.6	178.1	178.1	176.3	174.5	172.3	172.3
57.5°	160.6	161.9	165.1	166.4	168.2	168.2	167.3	166.0	163.3	161.5	160.1
60°	149.3	151.6	153.8	156.5	158.8	159.2	157.9	156.1	152.9	150.7	148.9
62.5°	137.2	139.4	143.9	146.6	148.4	148.4	148.4	146.2	142.1	139.0	136.3
65°	125.5	127.7	131.8	135.4	136.7	138.1	136.7	134.5	131.3	127.7	125.0
67.5°	113.3	116.0	120.1	122.8	124.6	125.9	125.0	123.2	119.2	114.2	112.4
70°	99.8	101.2	107.0	109.7	112.4	113.3	112.4	109.7	105.7	100.3	98.5
72.5°	87.2	88.6	94.0	96.2	98.5	99.4	98.0	96.2	92.6	87.7	85.5
75°	72.9	75.1	77.8	81.4	84.1	85.0	83.7	82.3	77.8	74.7	72.9
77.5°	57.6	59.8	63.4	66.6	69.3	68.8	67.0	67.5	62.5	58.9	57.6
80°	43.6	45.4	48.1	50.8	52.2	52.2	51.7	49.9	48.1	45.4	43.2
82.5°	30.1	32.4	34.6	36.4	36.4	36.9	36.0	35.5	33.7	31.5	31.0
85°	18.0	18.4	20.2	20.2	22.0	21.1	20.7	22.0	20.2	18.9	18.4
87.5°	8.1	7.6	8.1	8.1	7.6	8.5	8.5	8.1	8.5	8.1	8.1
90°	27.2	27.6	28.5	29.4	30.2	31.1	30.2	29.4	28.5	27.6	27.2
92.5°	27.2	27.3	27.6	27.9	28.2	28.5	28.2	27.9	27.6	27.3	27.2
95°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2
97.5°	25.9	26.0	26.3	26.6	26.9	27.2	26.9	26.6	26.3	26.0	25.9
100°	32.4	31.8	30.7	29.5	28.4	27.2	28.4	29.5	30.7	31.8	32.4
102.5°	305.7	293.6	269.4	245.3	221.1	196.9	221.1	245.3	269.4	293.6	305.7
105°	386.0	385.9	385.6	385.3	385.0	384.7	385.0	385.3	385.6	385.9	386.0
107.5°	472.8	472.2	471.1	469.9	468.8	467.6	468.8	469.9	471.1	472.2	472.8
110°	553.1	553.2	553.5	553.8	554.1	554.4	554.1	553.8	553.5	553.2	553.1

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	634.7	634.4	633.8	633.3	632.7	632.1	632.7	633.3	633.8	634.4	634.7
115°	717.6	716.7	715.0	713.3	711.5	709.8	711.5	713.3	715.0	716.7	717.6
117.5°	796.6	796.3	795.7	795.2	794.6	794.0	794.6	795.2	795.7	796.3	796.6
120°	876.9	876.2	874.7	873.3	871.8	870.4	871.8	873.3	874.7	876.2	876.9
122.5°	950.7	949.8	948.1	946.4	944.7	943.0	944.7	946.4	948.1	949.8	950.7
125°	1020.7	1020.3	1019.4	1018.5	1017.7	1016.8	1017.7	1018.5	1019.4	1020.3	1020.7
127.5°	1088.0	1086.9	1084.6	1082.3	1080.0	1077.7	1080.0	1082.3	1084.6	1086.9	1088.0
130°	1151.5	1150.8	1149.3	1147.9	1146.4	1145.0	1146.4	1147.9	1149.3	1150.8	1151.5
132.5°	1213.7	1213.0	1211.5	1210.1	1208.6	1207.2	1208.6	1210.1	1211.5	1213.0	1213.7
135°	1270.7	1269.8	1268.1	1266.4	1264.6	1262.9	1264.6	1266.4	1268.1	1269.8	1270.7
137.5°	1327.7	1327.0	1325.5	1324.1	1322.6	1321.2	1322.6	1324.1	1325.5	1327.0	1327.7
140°	1379.5	1378.6	1376.9	1375.2	1373.4	1371.7	1373.4	1375.2	1376.9	1378.6	1379.5
142.5°	1427.4	1426.5	1424.8	1423.1	1421.3	1419.6	1421.3	1423.1	1424.8	1426.5	1427.4
145°	1474.0	1473.1	1471.4	1469.7	1467.9	1466.2	1467.9	1469.7	1471.4	1473.1	1474.0
147.5°	1514.2	1513.2	1511.2	1509.1	1507.1	1505.1	1507.1	1509.1	1511.2	1513.2	1514.2
150°	1553.0	1551.9	1549.6	1547.3	1545.0	1542.7	1545.0	1547.3	1549.6	1551.9	1553.0
152.5°	1586.7	1585.7	1583.7	1581.6	1579.6	1577.6	1579.6	1581.6	1583.7	1585.7	1586.7
155°	1617.8	1616.6	1614.3	1612.0	1609.7	1607.4	1609.7	1612.0	1614.3	1616.6	1617.8
157.5°	1643.7	1642.5	1640.2	1637.9	1635.6	1633.3	1635.6	1637.9	1640.2	1642.5	1643.7
160°	1668.3	1667.1	1664.8	1662.5	1660.2	1657.9	1660.2	1662.5	1664.8	1667.1	1668.3
162.5°	1691.6	1690.3	1687.7	1685.2	1682.6	1680.0	1682.6	1685.2	1687.7	1690.3	1691.6
165°	1709.8	1708.6	1706.3	1704.0	1701.7	1699.4	1701.7	1704.0	1706.3	1708.6	1709.8
167.5°	1725.3	1724.0	1721.4	1718.8	1716.2	1713.6	1716.2	1718.8	1721.4	1724.0	1725.3
170°	1737.0	1735.7	1733.1	1730.5	1727.9	1725.3	1727.9	1730.5	1733.1	1735.7	1737.0
172.5°	1744.7	1743.4	1740.8	1738.3	1735.7	1733.1	1735.7	1738.3	1740.8	1743.4	1744.7
175°	1751.2	1749.9	1747.3	1744.8	1742.2	1739.6	1742.2	1744.8	1747.3	1749.9	1751.2
177.5°	1753.8	1752.6	1750.3	1748.0	1745.7	1743.4	1745.7	1748.0	1750.3	1752.6	1753.8
180°	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8	529.8
2.5°	503.3	500.6	503.7	499.7	500.6	505.5	505.1	509.6	512.3	511.8	514.1
5°	470.0	470.0	471.3	470.9	475.4	479.4	484.8	489.3	494.3	497.0	500.1
7.5°	437.1	441.6	442.5	444.8	450.2	456.9	462.3	469.1	476.3	481.2	484.8
10°	410.2	413.8	417.4	419.2	425.0	434.0	441.6	452.4	461.4	466.8	471.8
12.5°	386.3	390.4	392.2	400.3	404.3	410.2	421.0	432.6	442.5	448.4	452.4
15°	369.2	371.5	375.5	380.5	384.5	391.7	400.7	413.8	423.2	428.2	442.1
17.5°	354.8	357.5	359.8	362.0	368.3	376.0	384.5	395.8	407.9	416.5	423.7
20°	340.0	341.4	344.1	347.6	352.1	359.3	367.0	378.7	389.5	396.2	405.7
22.5°	322.5	326.5	329.2	331.9	336.9	345.0	352.1	360.7	374.2	381.8	391.7
25°	312.1	313.9	315.7	318.9	322.5	329.7	337.8	346.7	357.5	365.6	374.2
27.5°	298.6	301.3	303.6	307.6	309.9	315.7	323.4	332.4	345.4	352.1	359.3
30°	287.4	290.1	291.9	293.7	296.8	303.1	310.3	317.5	329.7	338.2	345.4
32.5°	276.1	278.8	281.1	282.4	285.6	289.6	295.5	304.5	314.8	320.7	330.1
35°	266.2	266.2	268.9	270.7	273.4	277.0	282.4	289.2	300.0	307.6	316.2
37.5°	255.0	255.5	257.7	259.1	261.7	265.3	270.7	277.0	286.0	291.9	300.4
40°	243.3	244.7	245.6	247.8	251.0	252.3	257.7	264.9	273.9	279.3	286.5
42.5°	231.6	232.5	234.8	236.6	239.3	241.5	245.1	251.9	258.6	266.7	272.5
45°	218.6	220.8	222.2	225.3	226.7	228.9	232.5	237.9	246.0	251.0	257.7
47.5°	207.3	208.2	209.1	213.2	215.9	217.2	220.8	224.0	232.5	237.0	243.3
50°	195.2	195.2	196.5	198.3	201.5	204.2	207.3	210.9	217.7	222.2	228.5
52.5°	183.9	182.6	183.5	184.4	187.5	190.2	193.4	198.3	204.6	207.3	212.7
55°	171.8	169.6	170.9	172.3	173.1	176.7	180.3	183.5	188.4	192.5	197.4
57.5°	158.8	158.3	157.4	157.9	160.1	162.4	165.1	169.1	174.9	178.1	180.8
60°	147.1	144.4	143.5	144.4	145.7	147.1	150.7	154.3	159.2	162.4	165.5
62.5°	134.9	132.2	130.4	129.1	130.4	133.6	135.8	138.5	142.6	146.2	148.9
65°	123.2	119.2	117.4	116.5	116.0	118.3	120.1	123.7	127.3	128.6	131.8
67.5°	110.2	106.6	104.3	103.0	103.0	103.0	104.8	108.4	112.0	112.4	115.6
70°	97.1	93.1	90.8	89.0	88.1	89.0	91.3	91.7	94.9	95.8	97.6
72.5°	83.2	79.6	76.9	74.7	75.1	76.0	76.0	76.9	78.7	81.0	81.0
75°	70.2	65.2	63.9	62.1	61.2	61.2	61.2	63.0	64.3	66.1	65.7
77.5°	55.3	52.6	49.9	49.0	47.7	47.2	48.1	48.1	49.0	50.4	50.8
80°	42.7	39.6	37.8	36.9	35.1	34.6	35.1	35.1	36.4	36.0	36.4
82.5°	29.7	27.4	26.1	24.7	23.8	24.3	23.8	23.8	24.3	23.8	23.8
85°	17.1	16.6	15.7	15.3	14.8	13.9	14.8	14.4	13.9	13.5	14.4
87.5°	8.1	7.6	7.6	6.7	6.7	6.3	6.7	6.7	6.3	6.3	6.3
90°	26.5	25.0	23.6	22.1	20.7	18.7	16.7	14.7	12.7	11.7	10.5
92.5°	26.5	25.0	23.6	22.1	20.7	19.0	17.3	15.6	13.9	13.0	14.3
95°	26.5	25.0	23.6	22.1	20.7	31.6	42.6	53.5	64.4	69.9	70.3
97.5°	25.6	25.0	24.5	23.9	23.3	50.7	78.0	105.4	132.7	146.4	145.5
100°	53.8	96.7	139.6	182.5	225.4	224.2	223.1	221.9	220.8	220.2	219.8
102.5°	305.4	304.8	304.3	303.7	303.1	302.5	301.9	301.4	300.8	300.5	299.9
105°	386.0	386.0	386.0	386.0	386.0	386.0	386.0	386.0	386.0	386.0	385.4
107.5°	472.7	472.4	472.1	471.8	471.5	470.9	470.3	469.8	469.2	468.9	468.9
110°	553.5	554.4	555.3	556.1	557.0	556.4	555.8	555.3	554.7	554.4	554.4

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	635.3	636.4	637.6	638.7	639.9	639.6	639.3	639.0	638.7	638.6	638.2
115°	718.2	719.3	720.5	721.6	722.8	722.5	722.2	721.9	721.6	721.5	720.8
117.5°	797.5	799.2	800.9	802.7	804.4	803.2	802.1	800.9	799.8	799.2	799.2
120°	877.2	877.8	878.3	878.9	879.5	878.6	877.8	876.9	876.0	875.6	875.7
122.5°	951.0	951.6	952.1	952.7	953.3	953.0	952.7	952.4	952.1	952.0	951.3
125°	1021.3	1022.4	1023.6	1024.7	1025.9	1025.9	1025.9	1025.9	1025.9	1025.9	1024.9
127.5°	1088.3	1088.9	1089.4	1090.0	1090.6	1090.9	1091.2	1091.5	1091.8	1091.9	1091.2
130°	1151.9	1152.8	1153.7	1154.5	1155.4	1155.1	1154.8	1154.5	1154.2	1154.1	1153.4
132.5°	1213.7	1213.7	1213.7	1213.7	1213.7	1214.6	1215.4	1216.3	1217.2	1217.6	1216.7
135°	1271.0	1271.6	1272.1	1272.7	1273.3	1273.9	1274.4	1275.0	1275.5	1275.8	1274.9
137.5°	1327.7	1327.7	1327.7	1327.7	1327.7	1328.3	1328.8	1329.4	1329.9	1330.2	1329.3
140°	1379.2	1378.6	1378.1	1377.5	1376.9	1377.2	1377.5	1377.8	1378.1	1378.2	1377.9
142.5°	1427.4	1427.4	1427.4	1427.4	1427.4	1426.8	1426.2	1425.7	1425.1	1424.8	1424.7
145°	1473.9	1473.6	1473.3	1473.0	1472.7	1472.7	1472.7	1472.7	1472.7	1472.7	1472.4
147.5°	1514.1	1513.8	1513.5	1513.2	1512.9	1512.6	1512.3	1512.0	1511.7	1511.6	1511.6
150°	1552.7	1552.1	1551.6	1551.0	1550.4	1549.8	1549.3	1548.7	1548.2	1547.9	1548.2
152.5°	1586.4	1585.8	1585.3	1584.7	1584.1	1583.5	1582.9	1582.4	1581.8	1581.5	1582.2
155°	1617.4	1616.5	1615.6	1614.8	1613.9	1613.3	1612.7	1612.2	1611.6	1611.3	1612.2
157.5°	1643.3	1642.4	1641.5	1640.7	1639.8	1639.8	1639.8	1639.8	1639.8	1639.8	1640.2
160°	1667.7	1666.6	1665.4	1664.3	1663.1	1662.8	1662.5	1662.2	1661.9	1661.8	1662.7
162.5°	1690.7	1689.0	1687.3	1685.6	1683.9	1683.6	1683.3	1683.0	1682.7	1682.6	1683.5
165°	1708.9	1707.2	1705.5	1703.7	1702.0	1701.7	1701.4	1701.1	1700.8	1700.7	1701.6
167.5°	1724.3	1722.3	1720.2	1718.2	1716.2	1715.9	1715.6	1715.3	1715.0	1714.9	1715.8
170°	1735.8	1733.5	1731.2	1728.9	1726.6	1726.3	1726.0	1725.7	1725.4	1725.3	1726.3
172.5°	1743.7	1741.7	1739.7	1737.7	1735.7	1735.1	1734.5	1734.0	1733.4	1733.1	1734.1
175°	1750.0	1747.7	1745.4	1743.1	1740.8	1740.5	1740.3	1740.0	1739.7	1739.6	1740.5
177.5°	1752.8	1750.8	1748.7	1746.7	1744.7	1744.4	1744.1	1743.8	1743.5	1743.4	1744.3
180°	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3	1747.3

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	529.8	529.8	529.8	529.8
2.5°	517.2	521.7	524.8	530.7
5°	505.5	513.6	521.2	529.3
7.5°	493.8	503.3	515.4	525.7
10°	480.8	492.9	507.3	521.2
12.5°	467.7	482.1	497.9	516.3
15°	452.0	470.4	488.9	508.7
17.5°	438.0	456.9	476.7	501.5
20°	422.3	443.0	464.6	489.8
22.5°	408.4	431.3	453.8	480.3
25°	392.6	415.1	439.8	468.2
27.5°	379.6	400.3	424.6	455.1
30°	363.8	386.3	410.6	441.2
32.5°	349.0	370.6	396.2	426.4
35°	333.7	355.7	378.7	407.5
37.5°	319.3	338.2	361.1	388.6
40°	303.1	323.8	344.5	366.1
42.5°	288.3	307.2	326.5	343.6
45°	271.6	287.8	306.3	320.2
47.5°	256.4	270.7	285.1	295.9
50°	241.1	252.3	263.1	272.5
52.5°	223.1	235.7	241.5	247.4
55°	206.9	214.1	219.5	225.3
57.5°	191.1	194.3	197.0	202.4
60°	170.5	174.0	177.2	181.2
62.5°	152.5	154.3	155.2	159.2
65°	135.4	134.9	137.2	139.4
67.5°	116.9	116.5	118.7	119.6
70°	98.9	98.5	98.9	101.2
72.5°	81.9	81.9	82.3	83.2
75°	66.1	66.1	66.6	67.5
77.5°	49.9	50.8	50.4	52.2
80°	36.4	35.5	36.4	37.3
82.5°	23.8	24.7	24.7	23.8
85°	13.5	13.5	13.5	13.5
87.5°	5.8	5.8	6.3	6.7
90°	8.2	5.9	3.6	1.3
92.5°	16.9	19.4	22.0	24.6
95°	71.2	72.1	72.9	73.8
97.5°	143.8	142.1	140.3	138.6
100°	218.9	218.0	217.2	216.3
102.5°	298.8	297.6	296.5	295.3
105°	384.3	383.1	382.0	380.8
107.5°	468.9	468.9	468.9	468.9
110°	554.4	554.4	554.4	554.4

TEST NUMBER: P1035269

CATALOG NUMBER: S125DIW-B375D1340UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	637.3	636.4	635.6	634.7
115°	719.3	717.9	716.4	715.0
117.5°	799.2	799.2	799.2	799.2
120°	876.0	876.3	876.6	876.9
122.5°	949.8	948.4	946.9	945.5
125°	1022.9	1020.8	1018.8	1016.8
127.5°	1089.7	1088.3	1086.8	1085.4
130°	1151.9	1150.5	1149.0	1147.6
132.5°	1215.0	1213.3	1211.5	1209.8
135°	1273.2	1271.5	1269.8	1268.1
137.5°	1327.6	1325.9	1324.2	1322.5
140°	1377.3	1376.8	1376.2	1375.6
142.5°	1424.4	1424.1	1423.8	1423.5
145°	1471.8	1471.3	1470.7	1470.1
147.5°	1511.6	1511.6	1511.6	1511.6
150°	1548.7	1549.3	1549.8	1550.4
152.5°	1583.7	1585.1	1586.6	1588.0
155°	1613.9	1615.6	1617.4	1619.1
157.5°	1641.1	1642.0	1642.8	1643.7
160°	1664.4	1666.1	1667.9	1669.6
162.5°	1685.2	1686.9	1688.6	1690.3
165°	1703.3	1705.0	1706.8	1708.5
167.5°	1717.5	1719.2	1721.0	1722.7
170°	1728.3	1730.4	1732.4	1734.4
172.5°	1736.1	1738.1	1740.1	1742.1
175°	1742.2	1743.9	1745.6	1747.3
177.5°	1746.0	1747.7	1749.5	1751.2
180°	1747.3	1747.3	1747.3	1747.3

(END OF REPORT)