

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035309

Luminaire Tested: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035309
REPORT IS A COMBINATION OF REPORTS P1003560 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1560UB40-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6947.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30
1	91	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	25
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18
4	69	59	52	46	61	53	46	42	41	36	33	29	26	24	19	17	16
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14
6	58	47	39	34	52	42	35	31	32	28	24	24	20	18	15	13	12
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3377	3377	3377	3377
5°	3379	3830	3382	2906
10°	3359	4366	3353	2494
15°	3333	4733	3313	2253
20°	3291	5187	3262	2057
25°	3254	5943	3195	1941
30°	3200	6270	3145	1836
35°	3116	5026	3050	1751
40°	2983	3474	2939	1662
45°	2816	2586	2784	1588
50°	2624	2129	2580	1528
55°	2417	1816	2398	1476
60°	2215	1554	2175	1437
65°	1996	1343	1963	1378
70°	1763	1114	1741	1276
75°	1519	862	1499	1108
80°	1199	582	1157	815
85°	766	292	743	415

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 5157 cd/sqm

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	0.7
10°-20°	151.1	2.2
20°-30°	245.4	3.5
30°-40°	299.9	4.3
40°-50°	272.0	3.9
50°-60°	216.7	3.1
60°-70°	150.9	2.2
70°-80°	80.4	1.2
80°-90°	23.0	0.3
90°-100°	130.0	1.9
100°-110°	386.3	5.6
110°-120°	655.1	9.4
120°-130°	862.4	12.4
130°-140°	966.4	13.9
140°-150°	947.2	13.6
150°-160°	795.6	11.5
160°-170°	528.9	7.6
170°-180°	185.1	2.7
0°-30°	447.2	6.4
0°-40°	747.1	10.8
0°-60°	1235.8	17.8
0°-90°	1490.0	21.4
90°-120°	1171.4	16.9
90°-150°	3947.4	56.8
90°-180°	5457.0	78.6
0°-180°	6947.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	526	608	527	461	526	50
15°	506	759	503	361	506	143
25°	466	934	457	305	466	214
35°	405	750	397	261	405	253
45°	318	353	315	217	318	245
55°	224	218	222	177	224	200
65°	139	134	136	137	139	138
75°	67	66	66	84	67	71
85°	13	15	13	21	13	16
90°	2	36	2	36	2	8
95°	99	131	99	131	99	103
105°	347	377	347	377	347	370
115°	656	662	656	662	656	649
125°	957	963	957	963	957	858
135°	1245	1249	1245	1249	1245	959
145°	1508	1514	1508	1514	1508	943
155°	1726	1726	1726	1726	1726	795
165°	1876	1872	1876	1872	1876	529
175°	1951	1943	1951	1943	1951	185
180°	1955	1955	1955	1955	1955	

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0
2.5°	527.9	531.0	534.6	537.2	541.7	543.1	545.3	546.6	548.0	549.3	550.2
5°	526.5	534.1	540.8	545.7	554.2	557.4	561.4	566.3	572.1	577.1	580.2
7.5°	522.9	535.0	544.0	553.8	565.4	573.0	577.1	587.3	596.7	603.9	613.3
10°	518.5	532.8	546.6	561.4	578.0	586.5	594.5	608.8	621.8	633.4	642.8
12.5°	513.5	531.0	547.5	566.8	589.1	599.4	604.8	629.4	645.5	651.8	670.1
15°	505.9	526.5	550.2	573.9	592.7	604.8	619.6	639.2	655.3	669.2	684.0
17.5°	498.8	521.1	545.3	571.7	599.0	614.6	625.8	643.3	660.7	678.6	692.5
20°	487.1	516.2	540.8	569.0	601.2	612.4	624.0	644.6	663.4	682.6	700.1
22.5°	477.8	505.5	539.0	565.9	593.2	604.3	618.7	640.1	662.5	684.4	709.9
25°	465.7	496.5	525.6	554.2	582.4	594.5	607.5	635.2	658.5	686.7	714.8
27.5°	452.7	484.5	513.5	539.5	565.9	582.4	596.3	625.4	656.2	687.1	723.8
30°	438.8	468.8	496.5	522.0	551.1	568.1	582.0	616.0	650.4	689.8	733.6
32.5°	424.1	452.3	476.0	501.9	532.8	548.4	567.2	604.3	645.1	692.0	747.0
35°	405.3	432.1	453.1	479.5	510.4	530.5	550.2	591.8	639.2	691.6	754.7
37.5°	386.5	407.5	427.7	455.8	491.6	510.0	530.5	576.2	630.3	690.2	757.8
40°	364.1	384.7	402.2	430.8	468.4	489.4	510.9	558.7	620.0	685.3	746.6
42.5°	341.8	359.2	378.4	408.4	444.6	467.0	489.8	543.1	606.6	671.0	715.7
45°	318.5	331.9	352.9	380.2	418.7	440.2	466.1	523.8	587.8	645.1	667.4
47.5°	294.3	307.8	327.4	353.8	391.9	417.4	442.0	499.7	564.1	608.4	608.4
50°	271.1	281.8	301.1	327.4	365.9	389.2	414.2	475.5	527.4	560.1	531.0
52.5°	246.0	258.1	274.2	301.9	340.0	361.0	388.3	440.6	489.8	503.2	458.5
55°	224.1	234.0	249.2	275.6	310.9	332.8	356.1	406.2	447.8	446.9	399.0
57.5°	201.3	209.4	225.5	249.6	282.3	301.9	325.2	368.6	402.6	390.5	345.3
60°	180.3	186.1	201.7	221.4	252.7	271.1	293.5	328.8	354.7	337.7	292.1
62.5°	158.4	165.1	177.6	196.8	224.6	239.3	255.9	291.7	308.2	293.0	246.5
65°	138.7	144.0	155.2	171.3	196.4	209.8	224.1	253.6	269.3	247.4	208.9
67.5°	119.0	125.3	133.3	147.6	167.3	179.8	192.4	217.9	225.0	205.3	173.1
70°	100.6	106.0	113.6	123.9	140.5	151.6	161.0	182.1	187.0	168.6	143.1
72.5°	82.8	86.3	92.6	101.1	116.3	122.6	132.4	146.7	153.0	136.4	118.1
75°	67.1	69.8	73.8	80.1	90.4	97.1	105.1	118.5	118.1	106.5	93.5
77.5°	51.9	52.3	56.8	62.6	68.9	74.7	78.7	88.1	89.0	81.9	71.1
80°	37.1	38.5	40.3	44.7	50.1	52.3	57.3	63.1	64.0	58.6	51.4
82.5°	23.7	24.6	25.9	28.6	32.2	34.9	37.6	39.8	42.0	38.9	33.1
85°	13.4	13.9	15.2	16.1	17.9	19.2	21.5	23.7	23.3	21.0	19.2
87.5°	6.7	6.7	6.7	7.6	8.5	8.5	9.4	9.8	10.3	9.4	8.5
90°	1.5	4.2	6.9	9.6	12.3	13.7	14.9	17.2	19.6	21.9	24.3
92.5°	45.6	47.3	49.0	50.7	52.4	53.3	54.8	57.9	60.9	64.0	67.0
95°	98.9	99.6	100.2	100.9	101.6	101.9	103.6	107.0	110.4	113.8	117.2
97.5°	152.2	152.5	152.9	153.2	153.5	153.7	156.1	160.8	165.5	170.3	175.0
100°	213.0	213.0	213.0	213.0	213.0	213.0	215.2	219.6	224.0	228.4	232.8
102.5°	278.5	280.2	281.9	283.6	285.3	286.1	286.9	288.6	290.3	292.0	293.7
105°	346.9	348.6	350.3	352.0	353.7	354.5	355.5	357.6	359.6	361.7	363.7
107.5°	421.5	423.2	424.9	426.6	428.3	429.1	429.9	431.6	433.3	435.0	436.7
110°	499.1	500.8	502.5	504.2	505.9	506.7	507.2	508.2	509.3	510.3	511.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	578.2	578.9	579.6	580.3	581.0	581.3	582.0	583.3	584.6	586.0	587.3
115°	655.8	657.2	658.5	659.9	661.2	661.9	662.2	662.9	663.6	664.2	664.9
117.5°	734.9	735.3	735.6	736.0	736.3	736.5	736.8	737.5	738.2	738.8	739.5
120°	808.0	809.7	811.4	813.1	814.8	815.6	815.8	816.1	816.4	816.8	817.1
122.5°	887.1	887.4	887.8	888.1	888.4	888.6	889.1	890.1	891.2	892.2	893.2
125°	957.1	959.1	961.1	963.2	965.2	966.2	966.4	966.7	967.0	967.4	967.7
127.5°	1034.7	1035.7	1036.7	1037.8	1038.8	1039.3	1039.5	1039.8	1040.1	1040.5	1040.8
130°	1103.2	1104.9	1106.6	1108.3	1110.0	1110.8	1111.1	1111.8	1112.5	1113.1	1113.8
132.5°	1171.6	1174.6	1177.7	1180.7	1183.8	1185.3	1185.1	1184.8	1184.5	1184.1	1183.8
135°	1244.7	1246.7	1248.7	1250.8	1252.8	1253.8	1254.0	1254.3	1254.6	1255.0	1255.3
137.5°	1313.1	1315.1	1317.2	1319.2	1321.3	1322.3	1322.6	1323.3	1324.0	1324.6	1325.3
140°	1378.6	1380.3	1382.0	1383.7	1385.4	1386.2	1386.7	1387.7	1388.7	1389.7	1390.7
142.5°	1444.0	1445.4	1446.7	1448.1	1449.4	1450.1	1450.8	1452.1	1453.5	1454.8	1456.2
145°	1507.9	1509.3	1510.6	1512.0	1513.3	1514.0	1514.5	1515.5	1516.6	1517.6	1518.6
147.5°	1567.2	1568.2	1569.2	1570.3	1571.3	1571.8	1572.1	1572.8	1573.5	1574.2	1574.9
150°	1626.6	1626.3	1625.9	1625.6	1625.3	1625.1	1625.8	1627.1	1628.5	1629.8	1631.2
152.5°	1675.3	1676.0	1676.6	1677.3	1678.0	1678.3	1678.5	1678.8	1679.1	1679.5	1679.8
155°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.7	1726.0	1726.3	1726.7	1727.0
157.5°	1771.1	1770.4	1769.8	1769.1	1768.4	1768.1	1768.3	1768.6	1768.9	1769.3	1769.6
160°	1810.7	1809.7	1808.7	1807.6	1806.6	1806.1	1806.3	1806.6	1807.0	1807.3	1807.7
162.5°	1845.7	1845.0	1844.4	1843.7	1843.0	1842.7	1842.7	1842.7	1842.7	1842.7	1842.7
165°	1876.1	1875.4	1874.8	1874.1	1873.4	1873.1	1873.3	1873.6	1873.9	1874.3	1874.6
167.5°	1903.5	1902.1	1900.8	1899.4	1898.1	1897.4	1897.4	1897.4	1897.4	1897.4	1897.4
170°	1924.8	1923.4	1922.1	1920.7	1919.4	1918.7	1918.7	1918.7	1918.7	1918.7	1918.7
172.5°	1940.0	1938.7	1937.3	1936.0	1934.7	1934.0	1934.0	1934.0	1934.0	1934.0	1934.0
175°	1950.7	1949.3	1948.0	1946.6	1945.3	1944.6	1944.6	1944.6	1944.6	1944.6	1944.6
177.5°	1958.3	1956.9	1955.6	1954.2	1952.9	1952.2	1952.0	1951.7	1951.4	1951.0	1950.7
180°	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0
2.5°	551.1	554.2	556.9	559.2	561.0	563.6	561.9	562.3	563.2	565.0	565.0
5°	586.9	591.8	594.5	603.5	605.7	605.2	603.9	611.1	610.6	607.9	607.5
7.5°	621.8	630.3	637.9	645.1	647.3	653.1	654.4	657.6	656.7	661.2	658.9
10°	653.6	667.0	674.1	684.9	687.6	690.2	693.8	695.6	699.6	699.2	699.2
12.5°	678.2	694.3	703.7	706.3	716.6	719.8	722.9	728.7	727.4	727.8	730.5
15°	697.4	713.0	721.1	733.6	740.8	744.4	749.7	756.0	755.1	759.1	758.2
17.5°	711.7	726.5	741.2	760.0	760.5	769.9	782.4	785.1	790.9	786.9	786.9
20°	723.3	743.0	764.0	788.2	790.9	796.7	811.9	822.2	828.9	826.7	828.0
22.5°	735.9	764.0	788.6	812.8	825.8	836.1	850.8	866.9	872.7	876.3	875.4
25°	752.0	781.5	817.7	851.3	864.7	884.4	904.1	919.7	924.2	934.0	925.1
27.5°	768.5	810.1	855.3	894.7	911.7	927.8	951.5	963.1	968.9	973.4	970.3
30°	782.4	839.6	888.9	925.1	937.2	946.6	960.0	962.7	960.4	964.0	968.5
32.5°	803.9	859.8	901.4	918.8	917.5	917.0	906.7	892.4	889.3	880.8	892.4
35°	815.5	860.2	876.3	853.1	843.7	826.7	794.0	772.5	753.8	749.7	750.6
37.5°	808.8	826.2	807.0	745.7	730.5	704.5	661.2	630.7	616.9	606.1	620.0
40°	772.5	753.3	700.5	625.8	603.9	579.3	538.6	522.0	502.4	498.3	516.7
42.5°	712.6	654.0	579.3	521.6	498.8	484.9	450.9	435.3	421.4	415.1	425.4
45°	631.2	560.1	484.9	437.5	418.3	401.7	381.6	365.0	356.1	353.4	361.9
47.5°	547.1	471.9	412.0	376.7	356.5	344.0	325.2	315.8	308.7	309.6	310.9
50°	466.6	398.1	352.1	316.7	306.9	297.0	284.5	276.5	272.9	274.2	273.3
52.5°	397.2	341.8	302.8	275.6	271.1	261.7	251.4	244.7	243.3	243.8	245.1
55°	336.4	293.0	262.1	242.5	237.5	230.8	224.6	220.1	216.5	217.9	217.4
57.5°	290.3	252.3	228.6	212.5	208.9	204.9	199.1	196.8	195.5	192.8	195.0
60°	249.6	218.7	198.2	188.3	185.2	182.5	176.2	173.6	172.7	171.3	174.9
62.5°	211.1	189.2	173.6	164.6	161.5	158.8	155.7	153.4	153.9	152.1	153.9
65°	180.7	162.8	151.6	143.6	139.6	137.8	137.3	133.8	133.3	133.8	134.2
67.5°	152.5	137.3	128.8	123.9	120.8	119.0	117.6	115.4	117.2	115.9	116.8
70°	127.0	116.8	107.8	102.9	101.5	102.0	99.8	98.9	99.3	98.4	99.3
72.5°	102.4	93.9	90.4	86.8	85.0	84.5	83.2	81.9	83.2	82.8	82.8
75°	81.9	75.6	71.6	69.3	69.3	68.4	66.2	66.2	66.2	65.8	66.2
77.5°	63.1	57.7	55.9	53.7	53.7	52.3	51.9	51.9	51.0	52.3	51.4
80°	47.0	42.9	40.3	38.9	38.9	38.5	37.6	37.1	37.6	37.1	37.1
82.5°	30.4	28.6	27.3	25.9	25.5	25.9	25.5	24.6	25.1	24.6	25.5
85°	17.4	15.7	15.7	14.8	15.2	14.3	14.8	13.9	13.4	14.8	13.9
87.5°	7.6	7.2	7.2	6.3	6.3	6.3	5.8	6.3	5.8	5.4	5.8
90°	26.0	27.7	29.4	31.1	32.0	32.5	33.5	34.5	35.5	36.5	35.5
92.5°	69.4	71.7	74.1	76.4	77.6	77.9	78.6	79.3	79.9	80.6	79.9
95°	119.6	121.9	124.3	126.6	127.8	128.1	128.8	129.5	130.2	130.9	130.2
97.5°	177.0	179.0	181.1	183.1	184.1	184.3	184.6	184.9	185.3	185.6	185.3
100°	235.8	238.9	241.9	245.0	246.5	246.8	247.5	248.2	248.8	249.5	248.8
102.5°	297.1	300.5	303.8	307.2	308.9	309.4	310.4	311.4	312.4	313.4	312.4
105°	365.7	367.7	369.8	371.8	372.8	373.3	374.3	375.4	376.4	377.4	376.4
107.5°	437.7	438.7	439.8	440.8	441.3	441.3	441.3	441.3	441.3	441.3	441.3
110°	512.3	513.3	514.3	515.3	515.8	515.6	515.3	515.0	514.6	514.3	514.6

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	587.7	588.0	588.4	588.7	588.9	588.6	587.9	587.2	586.5	585.8	586.5
115°	664.6	664.2	663.9	663.6	663.4	663.2	662.9	662.6	662.2	661.9	662.2
117.5°	739.8	740.2	740.5	740.8	741.0	740.3	739.0	737.6	736.3	734.9	736.3
120°	817.1	817.1	817.1	817.1	817.1	816.4	815.1	813.7	812.4	811.0	812.4
122.5°	892.9	892.5	892.2	891.9	891.7	891.2	890.2	889.1	888.1	887.1	888.1
125°	967.0	966.4	965.7	965.0	964.7	964.5	964.2	963.9	963.5	963.2	963.5
127.5°	1040.5	1040.1	1039.8	1039.5	1039.3	1039.0	1038.3	1037.6	1036.9	1036.2	1036.9
130°	1113.5	1113.1	1112.8	1112.5	1112.3	1112.0	1111.3	1110.6	1109.9	1109.2	1109.9
132.5°	1183.5	1183.1	1182.8	1182.5	1182.3	1181.8	1180.8	1179.7	1178.7	1177.7	1178.7
135°	1255.3	1255.3	1255.3	1255.3	1255.3	1254.6	1253.3	1251.9	1250.6	1249.2	1250.6
137.5°	1325.6	1326.0	1326.3	1326.6	1326.8	1326.0	1324.3	1322.6	1320.9	1319.2	1320.9
140°	1391.4	1392.1	1392.8	1393.5	1393.8	1393.0	1391.3	1389.6	1387.9	1386.2	1387.9
142.5°	1456.5	1456.9	1457.2	1457.5	1457.7	1456.9	1455.2	1453.5	1451.8	1450.1	1451.8
145°	1518.6	1518.6	1518.6	1518.6	1518.6	1518.1	1517.1	1516.0	1515.0	1514.0	1515.0
147.5°	1575.9	1576.9	1577.9	1578.9	1579.4	1578.0	1575.3	1572.6	1569.9	1567.2	1569.9
150°	1631.2	1631.2	1631.2	1631.2	1631.2	1630.9	1630.2	1629.5	1628.8	1628.1	1628.8
152.5°	1680.8	1681.8	1682.9	1683.9	1684.4	1683.7	1682.4	1681.0	1679.7	1678.3	1679.7
155°	1728.4	1729.7	1731.1	1732.4	1733.1	1732.3	1730.6	1728.9	1727.2	1725.5	1727.2
157.5°	1771.0	1772.3	1773.7	1775.0	1775.7	1774.5	1772.2	1769.8	1767.5	1765.1	1767.5
160°	1809.0	1810.4	1811.7	1813.0	1813.7	1812.9	1811.2	1809.5	1807.8	1806.1	1807.8
162.5°	1844.4	1846.1	1847.8	1849.5	1850.3	1849.3	1847.2	1845.2	1843.1	1841.1	1843.1
165°	1876.0	1877.3	1878.7	1880.0	1880.7	1879.7	1877.7	1875.6	1873.6	1871.6	1873.6
167.5°	1899.4	1901.5	1903.5	1905.6	1906.6	1905.6	1903.5	1901.5	1899.4	1897.4	1899.4
170°	1920.7	1922.8	1924.8	1926.9	1927.9	1926.7	1924.3	1922.0	1919.6	1917.2	1919.6
172.5°	1936.0	1938.0	1940.1	1942.1	1943.1	1942.1	1940.1	1938.0	1936.0	1934.0	1936.0
175°	1946.6	1948.6	1950.7	1952.7	1953.7	1952.5	1950.2	1947.8	1945.5	1943.1	1945.5
177.5°	1952.7	1954.7	1956.8	1958.8	1959.8	1958.6	1956.3	1953.9	1951.6	1949.2	1951.6
180°	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0
2.5°	564.1	561.0	561.9	561.0	558.7	557.4	553.8	549.3	547.5	545.3	544.0
5°	609.3	607.0	606.6	603.0	602.1	596.7	587.8	583.3	578.0	572.6	567.2
7.5°	658.5	655.8	646.8	645.5	646.4	639.7	628.1	619.1	607.9	600.3	590.0
10°	699.2	693.8	686.2	686.7	683.5	674.6	662.9	653.6	637.4	627.6	612.8
12.5°	723.8	719.3	718.4	713.9	711.3	699.6	685.8	673.7	661.6	648.2	637.0
15°	753.8	747.9	743.9	737.7	735.9	723.8	708.6	694.7	680.8	668.3	644.6
17.5°	786.9	780.6	765.4	764.0	753.3	741.7	726.9	706.3	691.6	673.7	656.2
20°	824.4	815.5	795.8	790.9	782.4	763.2	743.0	720.2	696.5	678.2	657.6
22.5°	866.5	850.8	836.5	820.9	814.6	790.9	763.2	735.4	706.8	681.7	657.1
25°	921.1	900.5	880.4	864.7	854.0	823.1	786.0	749.3	716.2	683.5	651.3
27.5°	964.0	946.1	924.2	903.6	889.7	853.1	810.6	763.2	722.0	682.2	647.7
30°	967.1	961.8	948.3	937.2	922.0	882.6	835.6	781.9	730.9	682.6	640.6
32.5°	908.5	919.3	925.1	926.9	923.7	900.9	858.0	798.9	739.0	678.6	634.3
35°	782.4	811.0	846.4	859.8	872.7	884.8	862.5	811.0	741.7	677.7	624.5
37.5°	644.2	670.1	728.7	755.5	770.8	818.6	837.0	809.2	747.0	678.6	615.1
40°	519.8	561.0	603.0	639.2	662.9	716.6	773.4	779.7	739.4	670.1	603.0
42.5°	437.5	461.6	493.4	527.0	548.0	611.5	688.4	733.6	715.7	656.2	588.2
45°	372.6	390.5	420.5	431.7	458.5	519.4	600.8	666.1	675.0	634.3	571.2
47.5°	319.8	335.1	354.3	368.2	389.6	435.3	504.1	576.2	619.1	604.3	547.5
50°	281.8	294.3	310.4	318.5	332.4	373.5	425.4	497.0	554.7	559.6	516.7
52.5°	250.1	257.2	269.7	278.7	289.9	314.9	361.9	420.9	485.8	512.6	478.6
55°	222.3	228.1	239.3	245.1	251.0	272.4	309.1	362.8	423.6	459.0	439.7
57.5°	197.3	202.2	211.6	217.0	220.1	240.7	268.8	310.9	365.5	408.4	397.7
60°	176.7	181.2	186.5	190.6	194.1	211.1	230.8	264.8	313.6	355.2	352.5
62.5°	154.8	158.8	164.6	168.6	171.8	182.5	199.1	225.0	266.6	305.1	312.7
65°	135.5	138.7	142.7	144.5	148.5	156.6	170.0	193.2	227.2	261.7	267.1
67.5°	118.1	119.0	121.7	125.7	126.6	133.8	145.8	163.3	189.7	217.9	226.4
70°	99.3	100.6	102.9	106.0	107.8	112.3	122.6	134.2	157.0	181.6	187.9
72.5°	82.8	84.5	85.4	87.2	88.1	95.3	99.8	111.4	127.0	147.6	154.3
75°	67.1	68.9	69.3	70.2	71.1	74.3	80.5	87.7	100.6	114.1	123.0
77.5°	53.2	52.8	53.7	55.0	54.6	57.3	61.3	67.5	76.0	87.2	93.0
80°	37.6	37.6	38.9	40.3	39.8	42.5	43.8	48.3	55.5	62.6	64.9
82.5°	25.1	25.1	26.4	26.4	27.3	27.7	29.5	31.8	37.6	41.2	42.5
85°	14.3	14.3	14.8	14.8	14.8	15.7	17.0	17.9	19.7	21.9	22.8
87.5°	5.8	6.3	6.3	6.3	6.3	7.2	7.2	8.1	8.5	9.4	9.4
90°	34.5	33.5	32.5	32.0	31.1	29.4	27.7	26.0	24.3	21.9	19.6
92.5°	79.3	78.6	77.9	77.6	76.4	74.1	71.7	69.4	67.0	64.0	60.9
95°	129.5	128.8	128.1	127.8	126.6	124.3	121.9	119.6	117.2	113.8	110.4
97.5°	184.9	184.6	184.3	184.1	183.1	181.1	179.0	177.0	175.0	170.3	165.5
100°	248.2	247.5	246.8	246.5	245.0	241.9	238.9	235.8	232.8	228.4	224.0
102.5°	311.4	310.4	309.4	308.9	307.2	303.8	300.5	297.1	293.7	292.0	290.3
105°	375.4	374.3	373.3	372.8	371.8	369.8	367.7	365.7	363.7	361.7	359.6
107.5°	441.3	441.3	441.3	441.3	440.8	439.8	438.7	437.7	436.7	435.0	433.3
110°	515.0	515.3	515.6	515.8	515.3	514.3	513.3	512.3	511.3	510.3	509.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	587.2	587.9	588.6	588.9	588.7	588.4	588.0	587.7	587.3	586.0	584.6
115°	662.6	662.9	663.2	663.4	663.6	663.9	664.2	664.6	664.9	664.2	663.6
117.5°	737.6	739.0	740.3	741.0	740.8	740.5	740.2	739.8	739.5	738.8	738.2
120°	813.7	815.1	816.4	817.1	817.1	817.1	817.1	817.1	817.1	816.8	816.4
122.5°	889.1	890.2	891.2	891.7	891.9	892.2	892.5	892.9	893.2	892.2	891.2
125°	963.9	964.2	964.5	964.7	965.0	965.7	966.4	967.0	967.7	967.4	967.0
127.5°	1037.6	1038.3	1039.0	1039.3	1039.5	1039.8	1040.1	1040.5	1040.8	1040.5	1040.1
130°	1110.6	1111.3	1112.0	1112.3	1112.5	1112.8	1113.1	1113.5	1113.8	1113.1	1112.5
132.5°	1179.7	1180.8	1181.8	1182.3	1182.5	1182.8	1183.1	1183.5	1183.8	1184.1	1184.5
135°	1251.9	1253.3	1254.6	1255.3	1255.3	1255.3	1255.3	1255.3	1255.3	1255.0	1254.6
137.5°	1322.6	1324.3	1326.0	1326.8	1326.6	1326.3	1326.0	1325.6	1325.3	1324.6	1324.0
140°	1389.6	1391.3	1393.0	1393.8	1393.5	1392.8	1392.1	1391.4	1390.7	1389.7	1388.7
142.5°	1453.5	1455.2	1456.9	1457.7	1457.5	1457.2	1456.9	1456.5	1456.2	1454.8	1453.5
145°	1516.0	1517.1	1518.1	1518.6	1518.6	1518.6	1518.6	1518.6	1518.6	1517.6	1516.6
147.5°	1572.6	1575.3	1578.0	1579.4	1578.9	1577.9	1576.9	1575.9	1574.9	1574.2	1573.5
150°	1629.5	1630.2	1630.9	1631.2	1631.2	1631.2	1631.2	1631.2	1631.2	1629.8	1628.5
152.5°	1681.0	1682.4	1683.7	1684.4	1683.9	1682.9	1681.8	1680.8	1679.8	1679.5	1679.1
155°	1728.9	1730.6	1732.3	1733.1	1732.4	1731.1	1729.7	1728.4	1727.0	1726.7	1726.3
157.5°	1769.8	1772.2	1774.5	1775.7	1775.0	1773.7	1772.3	1771.0	1769.6	1769.3	1768.9
160°	1809.5	1811.2	1812.9	1813.7	1813.0	1811.7	1810.4	1809.0	1807.7	1807.3	1807.0
162.5°	1845.2	1847.2	1849.3	1850.3	1849.5	1847.8	1846.1	1844.4	1842.7	1842.7	1842.7
165°	1875.6	1877.7	1879.7	1880.7	1880.0	1878.7	1877.3	1876.0	1874.6	1874.3	1873.9
167.5°	1901.5	1903.5	1905.6	1906.6	1905.6	1903.5	1901.5	1899.4	1897.4	1897.4	1897.4
170°	1922.0	1924.3	1926.7	1927.9	1926.9	1924.8	1922.8	1920.7	1918.7	1918.7	1918.7
172.5°	1938.0	1940.1	1942.1	1943.1	1942.1	1940.1	1938.0	1936.0	1934.0	1934.0	1934.0
175°	1947.8	1950.2	1952.5	1953.7	1952.7	1950.7	1948.6	1946.6	1944.6	1944.6	1944.6
177.5°	1953.9	1956.3	1958.6	1959.8	1958.8	1956.8	1954.7	1952.7	1950.7	1951.0	1951.4
180°	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0
2.5°	542.2	539.9	537.2	537.2	534.1	532.8	530.1	529.2	527.0	523.4	520.7
5°	561.4	555.6	552.0	548.9	542.2	537.2	532.3	527.0	521.6	515.3	508.2
7.5°	580.2	569.5	564.5	559.2	549.3	539.0	529.2	522.0	514.9	505.0	496.1
10°	599.9	586.5	577.5	570.3	555.1	542.2	527.9	517.6	506.4	493.9	482.2
12.5°	616.4	599.0	591.4	578.0	560.5	544.9	527.0	511.3	496.5	481.8	467.5
15°	630.3	613.7	595.0	589.6	565.4	543.1	522.9	502.8	484.5	469.7	453.1
17.5°	634.8	613.7	604.3	591.4	562.7	539.5	514.0	492.1	474.6	452.7	439.7
20°	636.1	616.0	603.0	590.9	565.4	534.6	509.5	482.7	461.6	439.7	419.2
22.5°	632.5	608.8	596.3	584.7	556.0	529.6	500.6	471.0	446.4	426.3	405.7
25°	625.8	598.1	586.0	573.5	546.2	517.1	485.4	457.2	434.4	410.2	390.1
27.5°	616.9	585.1	571.2	558.3	531.4	504.1	474.2	445.1	419.6	394.1	375.3
30°	605.7	569.0	556.5	539.5	513.5	487.6	460.3	431.2	402.6	378.4	357.9
32.5°	591.4	552.9	536.4	520.2	492.1	468.4	442.4	415.1	387.4	363.7	342.2
35°	578.4	534.6	516.2	500.1	468.8	443.8	422.3	396.8	372.2	347.6	328.3
37.5°	561.0	516.2	494.3	477.8	446.0	420.5	400.4	380.7	354.7	331.0	313.1
40°	542.6	493.4	472.8	456.3	423.2	395.4	376.2	358.8	337.7	315.8	297.0
42.5°	526.1	471.5	449.6	429.4	395.9	371.3	351.6	338.2	318.9	299.3	282.3
45°	505.0	448.2	424.5	403.5	371.3	344.4	325.7	314.9	300.6	281.4	266.6
47.5°	483.6	423.2	398.6	378.0	343.1	319.4	301.1	290.8	280.9	265.7	251.0
50°	455.4	396.8	374.4	350.7	316.3	292.1	276.9	266.6	259.0	248.3	235.7
52.5°	424.5	369.5	345.3	324.8	290.8	268.8	251.4	245.6	238.0	229.9	219.2
55°	391.9	340.0	316.7	296.6	265.3	242.9	228.6	222.3	216.5	210.2	203.1
57.5°	359.2	309.1	287.2	269.3	240.2	218.7	207.1	198.6	194.6	191.0	185.2
60°	318.5	276.0	259.0	242.9	214.3	194.6	183.4	177.1	173.6	171.8	169.1
62.5°	282.7	247.8	229.0	213.4	190.6	173.1	162.4	157.5	154.3	153.4	150.3
65°	244.7	214.7	200.0	186.5	166.9	151.2	142.3	136.4	134.2	133.8	133.8
67.5°	208.9	184.7	170.0	160.6	143.6	129.7	121.2	119.0	117.6	115.9	115.4
70°	175.4	156.1	143.1	135.1	119.9	109.6	102.9	99.3	99.3	98.0	97.1
72.5°	145.8	126.6	118.1	111.4	98.9	89.9	85.0	84.1	81.0	80.5	80.5
75°	114.1	99.8	93.9	88.1	78.7	72.5	68.4	66.2	64.4	64.4	64.9
77.5°	85.9	76.0	70.7	66.2	59.5	55.5	52.3	51.4	49.7	49.7	49.7
80°	60.8	55.5	51.4	47.9	42.9	39.4	37.6	35.8	35.8	35.3	35.8
82.5°	39.4	34.9	32.7	32.2	27.7	26.4	24.2	24.6	23.3	22.8	23.7
85°	22.8	20.6	17.9	17.0	15.2	13.4	12.5	13.0	12.5	12.1	12.5
87.5°	8.9	7.6	7.2	7.2	5.8	5.4	4.9	5.4	4.5	4.5	4.9
90°	17.2	14.9	13.7	12.3	9.6	6.9	4.2	1.5	4.2	6.9	9.6
92.5°	57.9	54.8	53.3	52.4	50.7	49.0	47.3	45.6	47.3	49.0	50.7
95°	107.0	103.6	101.9	101.6	100.9	100.2	99.6	98.9	99.6	100.2	100.9
97.5°	160.8	156.1	153.7	153.5	153.2	152.9	152.5	152.2	152.5	152.9	153.2
100°	219.6	215.2	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0
102.5°	288.6	286.9	286.1	285.3	283.6	281.9	280.2	278.5	280.2	281.9	283.6
105°	357.6	355.5	354.5	353.7	352.0	350.3	348.6	346.9	348.6	350.3	352.0
107.5°	431.6	429.9	429.1	428.3	426.6	424.9	423.2	421.5	423.2	424.9	426.6
110°	508.2	507.2	506.7	505.9	504.2	502.5	500.8	499.1	500.8	502.5	504.2

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	583.3	582.0	581.3	581.0	580.3	579.6	578.9	578.2	578.9	579.6	580.3
115°	662.9	662.2	661.9	661.2	659.9	658.5	657.2	655.8	657.2	658.5	659.9
117.5°	737.5	736.8	736.5	736.3	736.0	735.6	735.3	734.9	735.3	735.6	736.0
120°	816.1	815.8	815.6	814.8	813.1	811.4	809.7	808.0	809.7	811.4	813.1
122.5°	890.1	889.1	888.6	888.4	888.1	887.8	887.4	887.1	887.4	887.8	888.1
125°	966.7	966.4	966.2	965.2	963.2	961.1	959.1	957.1	959.1	961.1	963.2
127.5°	1039.8	1039.5	1039.3	1038.8	1037.8	1036.7	1035.7	1034.7	1035.7	1036.7	1037.8
130°	1111.8	1111.1	1110.8	1110.0	1108.3	1106.6	1104.9	1103.2	1104.9	1106.6	1108.3
132.5°	1184.8	1185.1	1185.3	1183.8	1180.7	1177.7	1174.6	1171.6	1174.6	1177.7	1180.7
135°	1254.3	1254.0	1253.8	1252.8	1250.8	1248.7	1246.7	1244.7	1246.7	1248.7	1250.8
137.5°	1323.3	1322.6	1322.3	1321.3	1319.2	1317.2	1315.1	1313.1	1315.1	1317.2	1319.2
140°	1387.7	1386.7	1386.2	1385.4	1383.7	1382.0	1380.3	1378.6	1380.3	1382.0	1383.7
142.5°	1452.1	1450.8	1450.1	1449.4	1448.1	1446.7	1445.4	1444.0	1445.4	1446.7	1448.1
145°	1515.5	1514.5	1514.0	1513.3	1512.0	1510.6	1509.3	1507.9	1509.3	1510.6	1512.0
147.5°	1572.8	1572.1	1571.8	1571.3	1570.3	1569.2	1568.2	1567.2	1568.2	1569.2	1570.3
150°	1627.1	1625.8	1625.1	1625.3	1625.6	1625.9	1626.3	1626.6	1626.3	1625.9	1625.6
152.5°	1678.8	1678.5	1678.3	1678.0	1677.3	1676.6	1676.0	1675.3	1676.0	1676.6	1677.3
155°	1726.0	1725.7	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
157.5°	1768.6	1768.3	1768.1	1768.4	1769.1	1769.8	1770.4	1771.1	1770.4	1769.8	1769.1
160°	1806.6	1806.3	1806.1	1806.6	1807.6	1808.7	1809.7	1810.7	1809.7	1808.7	1807.6
162.5°	1842.7	1842.7	1842.7	1843.0	1843.7	1844.4	1845.0	1845.7	1845.0	1844.4	1843.7
165°	1873.6	1873.3	1873.1	1873.4	1874.1	1874.8	1875.4	1876.1	1875.4	1874.8	1874.1
167.5°	1897.4	1897.4	1897.4	1898.1	1899.4	1900.8	1902.1	1903.5	1902.1	1900.8	1899.4
170°	1918.7	1918.7	1918.7	1919.4	1920.7	1922.1	1923.4	1924.8	1923.4	1922.1	1920.7
172.5°	1934.0	1934.0	1934.0	1934.7	1936.0	1937.3	1938.7	1940.0	1938.7	1937.3	1936.0
175°	1944.6	1944.6	1944.6	1945.3	1946.6	1948.0	1949.3	1950.7	1949.3	1948.0	1946.6
177.5°	1951.7	1952.0	1952.2	1952.9	1954.2	1955.6	1956.9	1958.3	1956.9	1955.6	1954.2
180°	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0
2.5°	519.8	518.9	516.7	515.3	510.9	505.5	503.7	499.2	501.0	497.9	497.9
5°	505.9	501.9	499.2	495.2	486.7	480.9	474.6	471.5	469.7	467.5	465.7
7.5°	488.0	484.9	482.2	474.6	465.2	457.2	449.6	446.4	440.6	436.6	434.8
10°	472.4	467.9	461.6	452.7	442.9	432.6	425.9	419.2	414.7	412.4	407.5
12.5°	456.3	450.9	444.2	431.2	420.5	414.2	402.2	395.9	393.7	391.9	386.0
15°	439.7	433.9	425.9	413.8	404.4	389.6	382.5	377.5	372.2	371.7	367.3
17.5°	425.0	417.8	411.1	396.3	384.7	371.7	367.7	362.3	357.4	352.1	349.8
20°	406.2	399.5	394.5	378.4	365.5	357.4	350.7	346.2	343.1	337.7	336.8
22.5°	389.2	382.0	375.3	363.2	352.1	341.8	333.7	328.8	327.4	325.2	321.2
25°	372.6	365.5	357.4	346.2	334.6	327.4	320.3	317.2	314.5	310.9	307.8
27.5°	358.8	352.1	344.4	330.6	320.7	315.4	307.8	304.2	300.6	298.8	297.5
30°	342.2	334.6	328.8	318.1	307.3	300.2	294.8	291.7	288.5	286.7	285.8
32.5°	326.1	318.9	314.9	303.3	294.8	286.3	282.3	280.0	278.2	276.5	274.7
35°	313.1	306.0	299.7	289.0	280.5	274.7	271.5	268.0	266.6	264.8	264.8
37.5°	297.0	291.7	285.4	275.1	267.5	263.0	260.3	255.9	255.4	254.5	253.2
40°	283.2	277.8	272.0	263.0	256.3	251.0	247.4	245.1	243.8	242.9	242.0
42.5°	268.4	262.6	259.9	249.6	243.8	238.4	236.6	234.4	234.0	232.2	229.9
45°	254.1	249.2	243.8	236.2	231.3	226.8	224.1	222.3	220.1	219.6	218.3
47.5°	241.6	235.7	230.8	223.7	218.3	214.7	212.5	210.2	208.5	207.1	205.8
50°	225.5	221.0	217.0	209.4	204.9	201.3	198.2	196.4	194.6	194.6	194.6
52.5°	209.8	205.8	202.2	196.8	191.5	188.3	184.7	183.4	182.5	181.2	182.5
55°	194.6	190.6	187.0	183.0	176.7	174.0	170.4	169.1	169.5	169.5	170.9
57.5°	178.5	175.4	173.1	168.2	162.4	159.7	157.5	156.1	156.1	157.9	158.4
60°	162.8	159.7	155.7	151.2	147.6	144.5	143.1	143.6	143.6	144.5	146.7
62.5°	145.4	143.6	141.4	135.1	132.9	130.6	128.8	130.2	129.7	132.0	135.1
65°	129.3	127.5	124.4	121.2	118.5	116.3	115.9	116.3	117.2	119.4	123.0
67.5°	111.4	111.4	108.7	106.0	103.8	101.5	102.0	102.4	103.3	106.0	111.4
70°	96.6	94.8	92.2	90.4	88.6	87.7	86.8	88.6	91.3	93.0	97.1
72.5°	80.5	79.2	76.9	75.2	74.7	73.8	73.4	74.3	76.9	80.1	84.5
75°	63.5	64.0	62.6	61.3	61.3	59.9	60.8	60.8	63.5	66.7	70.2
77.5°	49.2	48.8	48.3	47.4	47.0	47.0	47.0	47.9	50.5	52.3	55.9
80°	34.9	35.3	34.0	34.4	34.0	34.4	34.4	36.2	37.6	39.8	42.5
82.5°	23.3	23.3	22.4	22.8	22.8	22.8	23.3	24.2	25.9	27.7	29.5
85°	13.0	13.4	12.5	13.4	13.4	13.4	13.9	14.3	15.7	16.1	17.9
87.5°	4.9	5.8	5.8	4.9	5.4	5.8	6.3	5.8	6.7	7.6	8.1
90°	12.3	13.7	14.9	17.2	19.6	21.9	24.3	26.0	27.7	29.4	31.1
92.5°	52.4	53.3	54.8	57.9	60.9	64.0	67.0	69.4	71.7	74.1	76.4
95°	101.6	101.9	103.6	107.0	110.4	113.8	117.2	119.6	121.9	124.3	126.6
97.5°	153.5	153.7	156.1	160.8	165.5	170.3	175.0	177.0	179.0	181.1	183.1
100°	213.0	213.0	215.2	219.6	224.0	228.4	232.8	235.8	238.9	241.9	245.0
102.5°	285.3	286.1	286.9	288.6	290.3	292.0	293.7	297.1	300.5	303.8	307.2
105°	353.7	354.5	355.5	357.6	359.6	361.7	363.7	365.7	367.7	369.8	371.8
107.5°	428.3	429.1	429.9	431.6	433.3	435.0	436.7	437.7	438.7	439.8	440.8
110°	505.9	506.7	507.2	508.2	509.3	510.3	511.3	512.3	513.3	514.3	515.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	581.0	581.3	582.0	583.3	584.6	586.0	587.3	587.7	588.0	588.4	588.7
115°	661.2	661.9	662.2	662.9	663.6	664.2	664.9	664.6	664.2	663.9	663.6
117.5°	736.3	736.5	736.8	737.5	738.2	738.8	739.5	739.8	740.2	740.5	740.8
120°	814.8	815.6	815.8	816.1	816.4	816.8	817.1	817.1	817.1	817.1	817.1
122.5°	888.4	888.6	889.1	890.1	891.2	892.2	893.2	892.9	892.5	892.2	891.9
125°	965.2	966.2	966.4	966.7	967.0	967.4	967.7	967.0	966.4	965.7	965.0
127.5°	1038.8	1039.3	1039.5	1039.8	1040.1	1040.5	1040.8	1040.5	1040.1	1039.8	1039.5
130°	1110.0	1110.8	1111.1	1111.8	1112.5	1113.1	1113.8	1113.5	1113.1	1112.8	1112.5
132.5°	1183.8	1185.3	1185.1	1184.8	1184.5	1184.1	1183.8	1183.5	1183.1	1182.8	1182.5
135°	1252.8	1253.8	1254.0	1254.3	1254.6	1255.0	1255.3	1255.3	1255.3	1255.3	1255.3
137.5°	1321.3	1322.3	1322.6	1323.3	1324.0	1324.6	1325.3	1325.6	1326.0	1326.3	1326.6
140°	1385.4	1386.2	1386.7	1387.7	1388.7	1389.7	1390.7	1391.4	1392.1	1392.8	1393.5
142.5°	1449.4	1450.1	1450.8	1452.1	1453.5	1454.8	1456.2	1456.5	1456.9	1457.2	1457.5
145°	1513.3	1514.0	1514.5	1515.5	1516.6	1517.6	1518.6	1518.6	1518.6	1518.6	1518.6
147.5°	1571.3	1571.8	1572.1	1572.8	1573.5	1574.2	1574.9	1575.9	1576.9	1577.9	1578.9
150°	1625.3	1625.1	1625.8	1627.1	1628.5	1629.8	1631.2	1631.2	1631.2	1631.2	1631.2
152.5°	1678.0	1678.3	1678.5	1678.8	1679.1	1679.5	1679.8	1680.8	1681.8	1682.9	1683.9
155°	1725.5	1725.5	1725.7	1726.0	1726.3	1726.7	1727.0	1728.4	1729.7	1731.1	1732.4
157.5°	1768.4	1768.1	1768.3	1768.6	1768.9	1769.3	1769.6	1771.0	1772.3	1773.7	1775.0
160°	1806.6	1806.1	1806.3	1806.6	1807.0	1807.3	1807.7	1809.0	1810.4	1811.7	1813.0
162.5°	1843.0	1842.7	1842.7	1842.7	1842.7	1842.7	1842.7	1844.4	1846.1	1847.8	1849.5
165°	1873.4	1873.1	1873.3	1873.6	1873.9	1874.3	1874.6	1876.0	1877.3	1878.7	1880.0
167.5°	1898.1	1897.4	1897.4	1897.4	1897.4	1897.4	1897.4	1899.4	1901.5	1903.5	1905.6
170°	1919.4	1918.7	1918.7	1918.7	1918.7	1918.7	1918.7	1920.7	1922.8	1924.8	1926.9
172.5°	1934.7	1934.0	1934.0	1934.0	1934.0	1934.0	1934.0	1936.0	1938.0	1940.1	1942.1
175°	1945.3	1944.6	1944.6	1944.6	1944.6	1944.6	1944.6	1946.6	1948.6	1950.7	1952.7
177.5°	1952.9	1952.2	1952.0	1951.7	1951.4	1951.0	1950.7	1952.7	1954.7	1956.8	1958.8
180°	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0
2.5°	499.7	496.5	496.1	497.0	495.2	497.9	497.0	497.9	495.6	497.9	496.5
5°	465.2	464.3	462.5	460.3	460.8	461.2	463.4	461.2	463.0	463.4	465.7
7.5°	433.0	431.2	432.6	431.7	427.7	426.8	427.7	429.0	431.7	433.5	434.8
10°	407.1	406.2	404.4	403.0	400.8	399.5	401.3	399.5	403.0	406.2	406.2
12.5°	387.4	383.8	381.6	381.1	376.2	377.1	378.9	380.2	384.3	386.0	386.0
15°	366.8	364.1	363.2	361.4	359.7	361.4	360.6	361.9	363.7	365.5	366.4
17.5°	348.9	348.5	348.9	344.4	345.8	343.6	344.0	346.2	344.9	346.2	348.9
20°	332.8	333.7	332.4	330.6	330.6	327.9	331.0	330.1	330.6	333.3	337.3
22.5°	320.7	320.3	318.9	317.6	315.8	316.3	316.7	315.8	319.4	321.6	322.1
25°	307.8	306.9	306.4	305.1	303.3	305.1	304.6	305.1	306.0	309.6	306.9
27.5°	295.7	293.9	294.8	293.5	293.0	293.5	293.5	293.9	294.8	295.2	295.7
30°	285.4	283.6	283.2	282.3	281.8	282.3	283.2	282.3	285.8	285.4	285.4
32.5°	274.2	272.9	272.0	272.0	271.5	271.1	271.5	272.0	274.7	272.9	274.7
35°	263.5	262.6	262.6	261.7	261.2	261.2	261.2	263.0	262.1	263.5	263.5
37.5°	253.2	253.2	252.7	251.8	251.4	251.8	251.4	252.3	251.8	252.3	252.7
40°	242.5	241.6	241.1	241.1	239.8	238.4	239.8	239.8	240.2	241.6	242.0
42.5°	229.5	229.9	229.9	228.1	228.1	228.1	228.6	229.0	229.0	229.9	229.9
45°	218.3	217.4	217.4	217.4	216.5	217.0	217.9	217.9	217.9	217.9	217.0
47.5°	205.8	205.8	206.2	206.2	207.6	207.1	207.1	206.7	205.8	205.8	206.2
50°	194.1	195.5	195.9	195.9	196.4	196.8	196.8	195.9	195.5	194.1	194.1
52.5°	183.0	183.9	184.7	186.1	187.0	186.5	186.5	185.6	183.9	183.4	183.0
55°	170.9	172.2	174.0	175.4	176.7	177.1	177.1	175.4	173.6	171.3	171.3
57.5°	159.7	161.0	164.2	165.5	167.3	167.3	166.4	165.1	162.4	160.6	159.3
60°	148.5	150.8	153.0	155.7	157.9	158.4	157.0	155.2	152.1	149.9	148.1
62.5°	136.4	138.7	143.1	145.8	147.6	147.6	147.6	145.4	141.4	138.2	135.5
65°	124.8	127.0	131.1	134.6	136.0	137.3	136.0	133.8	130.6	127.0	124.4
67.5°	112.7	115.4	119.4	122.1	123.9	125.3	124.4	122.6	118.5	113.6	111.8
70°	99.3	100.6	106.5	109.1	111.8	112.7	111.8	109.1	105.1	99.8	98.0
72.5°	86.8	88.1	93.5	95.7	98.0	98.9	97.5	95.7	92.2	87.2	85.0
75°	72.5	74.7	77.4	81.0	83.7	84.5	83.2	81.9	77.4	74.3	72.5
77.5°	57.3	59.5	63.1	66.2	68.9	68.4	66.7	67.1	62.2	58.6	57.3
80°	43.4	45.2	47.9	50.5	51.9	51.9	51.4	49.7	47.9	45.2	42.9
82.5°	30.0	32.2	34.4	36.2	36.2	36.7	35.8	35.3	33.5	31.3	30.9
85°	17.9	18.3	20.1	20.1	21.9	21.0	20.6	21.9	20.1	18.8	18.3
87.5°	8.1	7.6	8.1	8.1	7.6	8.5	8.5	8.1	8.5	8.1	8.1
90°	32.0	32.5	33.5	34.5	35.5	36.5	35.5	34.5	33.5	32.5	32.0
92.5°	77.6	77.9	78.6	79.3	79.9	80.6	79.9	79.3	78.6	77.9	77.6
95°	127.8	128.1	128.8	129.5	130.2	130.9	130.2	129.5	128.8	128.1	127.8
97.5°	184.1	184.3	184.6	184.9	185.3	185.6	185.3	184.9	184.6	184.3	184.1
100°	246.5	246.8	247.5	248.2	248.8	249.5	248.8	248.2	247.5	246.8	246.5
102.5°	308.9	309.4	310.4	311.4	312.4	313.4	312.4	311.4	310.4	309.4	308.9
105°	372.8	373.3	374.3	375.4	376.4	377.4	376.4	375.4	374.3	373.3	372.8
107.5°	441.3	441.3	441.3	441.3	441.3	441.3	441.3	441.3	441.3	441.3	441.3
110°	515.8	515.6	515.3	515.0	514.6	514.3	514.6	515.0	515.3	515.6	515.8

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	588.9	588.6	587.9	587.2	586.5	585.8	586.5	587.2	587.9	588.6	588.9
115°	663.4	663.2	662.9	662.6	662.2	661.9	662.2	662.6	662.9	663.2	663.4
117.5°	741.0	740.3	739.0	737.6	736.3	734.9	736.3	737.6	739.0	740.3	741.0
120°	817.1	816.4	815.1	813.7	812.4	811.0	812.4	813.7	815.1	816.4	817.1
122.5°	891.7	891.2	890.2	889.1	888.1	887.1	888.1	889.1	890.2	891.2	891.7
125°	964.7	964.5	964.2	963.9	963.5	963.2	963.5	963.9	964.2	964.5	964.7
127.5°	1039.3	1039.0	1038.3	1037.6	1036.9	1036.2	1036.9	1037.6	1038.3	1039.0	1039.3
130°	1112.3	1112.0	1111.3	1110.6	1109.9	1109.2	1109.9	1110.6	1111.3	1112.0	1112.3
132.5°	1182.3	1181.8	1180.8	1179.7	1178.7	1177.7	1178.7	1179.7	1180.8	1181.8	1182.3
135°	1255.3	1254.6	1253.3	1251.9	1250.6	1249.2	1250.6	1251.9	1253.3	1254.6	1255.3
137.5°	1326.8	1326.0	1324.3	1322.6	1320.9	1319.2	1320.9	1322.6	1324.3	1326.0	1326.8
140°	1393.8	1393.0	1391.3	1389.6	1387.9	1386.2	1387.9	1389.6	1391.3	1393.0	1393.8
142.5°	1457.7	1456.9	1455.2	1453.5	1451.8	1450.1	1451.8	1453.5	1455.2	1456.9	1457.7
145°	1518.6	1518.1	1517.1	1516.0	1515.0	1514.0	1515.0	1516.0	1517.1	1518.1	1518.6
147.5°	1579.4	1578.0	1575.3	1572.6	1569.9	1567.2	1569.9	1572.6	1575.3	1578.0	1579.4
150°	1631.2	1630.9	1630.2	1629.5	1628.8	1628.1	1628.8	1629.5	1630.2	1630.9	1631.2
152.5°	1684.4	1683.7	1682.4	1681.0	1679.7	1678.3	1679.7	1681.0	1682.4	1683.7	1684.4
155°	1733.1	1732.3	1730.6	1728.9	1727.2	1725.5	1727.2	1728.9	1730.6	1732.3	1733.1
157.5°	1775.7	1774.5	1772.2	1769.8	1767.5	1765.1	1767.5	1769.8	1772.2	1774.5	1775.7
160°	1813.7	1812.9	1811.2	1809.5	1807.8	1806.1	1807.8	1809.5	1811.2	1812.9	1813.7
162.5°	1850.3	1849.3	1847.2	1845.2	1843.1	1841.1	1843.1	1845.2	1847.2	1849.3	1850.3
165°	1880.7	1879.7	1877.7	1875.6	1873.6	1871.6	1873.6	1875.6	1877.7	1879.7	1880.7
167.5°	1906.6	1905.6	1903.5	1901.5	1899.4	1897.4	1899.4	1901.5	1903.5	1905.6	1906.6
170°	1927.9	1926.7	1924.3	1922.0	1919.6	1917.2	1919.6	1922.0	1924.3	1926.7	1927.9
172.5°	1943.1	1942.1	1940.1	1938.0	1936.0	1934.0	1936.0	1938.0	1940.1	1942.1	1943.1
175°	1953.7	1952.5	1950.2	1947.8	1945.5	1943.1	1945.5	1947.8	1950.2	1952.5	1953.7
177.5°	1959.8	1958.6	1956.3	1953.9	1951.6	1949.2	1951.6	1953.9	1956.3	1958.6	1959.8
180°	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0	527.0
2.5°	500.6	497.9	501.0	497.0	497.9	502.8	502.4	506.8	509.5	509.1	511.3
5°	467.5	467.5	468.8	468.4	472.8	476.9	482.2	486.7	491.6	494.3	497.4
7.5°	434.8	439.3	440.2	442.4	447.8	454.5	459.9	466.6	473.7	478.6	482.2
10°	408.0	411.5	415.1	416.9	422.7	431.7	439.3	450.0	459.0	464.3	469.3
12.5°	384.3	388.3	390.1	398.1	402.2	408.0	418.7	430.3	440.2	446.0	450.0
15°	367.3	369.5	373.5	378.4	382.5	389.6	398.6	411.5	420.9	425.9	439.7
17.5°	352.9	355.6	357.9	360.1	366.4	374.0	382.5	393.7	405.7	414.2	421.4
20°	338.2	339.5	342.2	345.8	350.3	357.4	365.0	376.7	387.4	394.1	403.5
22.5°	320.7	324.8	327.4	330.1	335.1	343.1	350.3	358.8	372.2	379.8	389.6
25°	310.4	312.2	314.0	317.2	320.7	327.9	335.9	344.9	355.6	363.7	372.2
27.5°	297.0	299.7	301.9	306.0	308.2	314.0	321.6	330.6	343.6	350.3	357.4
30°	285.8	288.5	290.3	292.1	295.2	301.5	308.7	315.8	327.9	336.4	343.6
32.5°	274.7	277.3	279.6	280.9	284.1	288.1	293.9	302.8	313.1	318.9	328.3
35°	264.8	264.8	267.5	269.3	272.0	275.6	280.9	287.6	298.4	306.0	314.5
37.5°	253.6	254.1	256.3	257.7	260.3	263.9	269.3	275.6	284.5	290.3	298.8
40°	242.0	243.3	244.2	246.5	249.6	251.0	256.3	263.5	272.4	277.8	285.0
42.5°	230.4	231.3	233.5	235.3	238.0	240.2	243.8	250.5	257.2	265.3	271.1
45°	217.4	219.6	221.0	224.1	225.5	227.7	231.3	236.6	244.7	249.6	256.3
47.5°	206.2	207.1	208.0	212.0	214.7	216.1	219.6	222.8	231.3	235.7	242.0
50°	194.1	194.1	195.5	197.3	200.4	203.1	206.2	209.8	216.5	221.0	227.2
52.5°	183.0	181.6	182.5	183.4	186.5	189.2	192.4	197.3	203.5	206.2	211.6
55°	170.9	168.6	170.0	171.3	172.2	175.8	179.4	182.5	187.4	191.5	196.4
57.5°	157.9	157.5	156.6	157.0	159.3	161.5	164.2	168.2	174.0	177.1	179.8
60°	146.3	143.6	142.7	143.6	144.9	146.3	149.9	153.4	158.4	161.5	164.6
62.5°	134.2	131.5	129.7	128.4	129.7	132.9	135.1	137.8	141.8	145.4	148.1
65°	122.6	118.5	116.8	115.9	115.4	117.6	119.4	123.0	126.6	127.9	131.1
67.5°	109.6	106.0	103.8	102.4	102.4	102.4	104.2	107.8	111.4	111.8	115.0
70°	96.6	92.6	90.4	88.6	87.7	88.6	90.8	91.3	94.4	95.3	97.1
72.5°	82.8	79.2	76.5	74.3	74.7	75.6	75.6	76.5	78.3	80.5	80.5
75°	69.8	64.9	63.5	61.7	60.8	60.8	60.8	62.6	64.0	65.8	65.3
77.5°	55.0	52.3	49.7	48.8	47.4	47.0	47.9	47.9	48.8	50.1	50.5
80°	42.5	39.4	37.6	36.7	34.9	34.4	34.9	34.9	36.2	35.8	36.2
82.5°	29.5	27.3	25.9	24.6	23.7	24.2	23.7	23.7	24.2	23.7	23.7
85°	17.0	16.6	15.7	15.2	14.8	13.9	14.8	14.3	13.9	13.4	14.3
87.5°	8.1	7.6	7.6	6.7	6.7	6.3	6.7	6.7	6.3	6.3	6.3
90°	31.1	29.4	27.7	26.0	24.3	21.9	19.6	17.2	14.9	13.7	12.3
92.5°	76.4	74.1	71.7	69.4	67.0	64.0	60.9	57.9	54.8	53.3	52.4
95°	126.6	124.3	121.9	119.6	117.2	113.8	110.4	107.0	103.6	101.9	101.6
97.5°	183.1	181.1	179.0	177.0	175.0	170.3	165.5	160.8	156.1	153.7	153.5
100°	245.0	241.9	238.9	235.8	232.8	228.4	224.0	219.6	215.2	213.0	213.0
102.5°	307.2	303.8	300.5	297.1	293.7	292.0	290.3	288.6	286.9	286.1	285.3
105°	371.8	369.8	367.7	365.7	363.7	361.7	359.6	357.6	355.5	354.5	353.7
107.5°	440.8	439.8	438.7	437.7	436.7	435.0	433.3	431.6	429.9	429.1	428.3
110°	515.3	514.3	513.3	512.3	511.3	510.3	509.3	508.2	507.2	506.7	505.9

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	588.7	588.4	588.0	587.7	587.3	586.0	584.6	583.3	582.0	581.3	581.0
115°	663.6	663.9	664.2	664.6	664.9	664.2	663.6	662.9	662.2	661.9	661.2
117.5°	740.8	740.5	740.2	739.8	739.5	738.8	738.2	737.5	736.8	736.5	736.3
120°	817.1	817.1	817.1	817.1	817.1	816.8	816.4	816.1	815.8	815.6	814.8
122.5°	891.9	892.2	892.5	892.9	893.2	892.2	891.2	890.1	889.1	888.6	888.4
125°	965.0	965.7	966.4	967.0	967.7	967.4	967.0	966.7	966.4	966.2	965.2
127.5°	1039.5	1039.8	1040.1	1040.5	1040.8	1040.5	1040.1	1039.8	1039.5	1039.3	1038.8
130°	1112.5	1112.8	1113.1	1113.5	1113.8	1113.1	1112.5	1111.8	1111.1	1110.8	1110.0
132.5°	1182.5	1182.8	1183.1	1183.5	1183.8	1184.1	1184.5	1184.8	1185.1	1185.3	1183.8
135°	1255.3	1255.3	1255.3	1255.3	1255.3	1255.0	1254.6	1254.3	1254.0	1253.8	1252.8
137.5°	1326.6	1326.3	1326.0	1325.6	1325.3	1324.6	1324.0	1323.3	1322.6	1322.3	1321.3
140°	1393.5	1392.8	1392.1	1391.4	1390.7	1389.7	1388.7	1387.7	1386.7	1386.2	1385.4
142.5°	1457.5	1457.2	1456.9	1456.5	1456.2	1454.8	1453.5	1452.1	1450.8	1450.1	1449.4
145°	1518.6	1518.6	1518.6	1518.6	1518.6	1517.6	1516.6	1515.5	1514.5	1514.0	1513.3
147.5°	1578.9	1577.9	1576.9	1575.9	1574.9	1574.2	1573.5	1572.8	1572.1	1571.8	1571.3
150°	1631.2	1631.2	1631.2	1631.2	1631.2	1629.8	1628.5	1627.1	1625.8	1625.1	1625.3
152.5°	1683.9	1682.9	1681.8	1680.8	1679.8	1679.5	1679.1	1678.8	1678.5	1678.3	1678.0
155°	1732.4	1731.1	1729.7	1728.4	1727.0	1726.7	1726.3	1726.0	1725.7	1725.5	1725.5
157.5°	1775.0	1773.7	1772.3	1771.0	1769.6	1769.3	1768.9	1768.6	1768.3	1768.1	1768.4
160°	1813.0	1811.7	1810.4	1809.0	1807.7	1807.3	1807.0	1806.6	1806.3	1806.1	1806.6
162.5°	1849.5	1847.8	1846.1	1844.4	1842.7	1842.7	1842.7	1842.7	1842.7	1842.7	1843.0
165°	1880.0	1878.7	1877.3	1876.0	1874.6	1874.3	1873.9	1873.6	1873.3	1873.1	1873.4
167.5°	1905.6	1903.5	1901.5	1899.4	1897.4	1897.4	1897.4	1897.4	1897.4	1897.4	1898.1
170°	1926.9	1924.8	1922.8	1920.7	1918.7	1918.7	1918.7	1918.7	1918.7	1918.7	1919.4
172.5°	1942.1	1940.1	1938.0	1936.0	1934.0	1934.0	1934.0	1934.0	1934.0	1934.0	1934.7
175°	1952.7	1950.7	1948.6	1946.6	1944.6	1944.6	1944.6	1944.6	1944.6	1944.6	1945.3
177.5°	1958.8	1956.8	1954.7	1952.7	1950.7	1951.0	1951.4	1951.7	1952.0	1952.2	1952.9
180°	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3	1955.3

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	527.0	527.0	527.0	527.0
2.5°	514.4	518.9	522.0	527.9
5°	502.8	510.9	518.5	526.5
7.5°	491.2	500.6	512.6	522.9
10°	478.2	490.3	504.6	518.5
12.5°	465.2	479.5	495.2	513.5
15°	449.6	467.9	486.3	505.9
17.5°	435.7	454.5	474.2	498.8
20°	420.0	440.6	462.1	487.1
22.5°	406.2	429.0	451.4	477.8
25°	390.5	412.9	437.5	465.7
27.5°	377.5	398.1	422.3	452.7
30°	361.9	384.3	408.4	438.8
32.5°	347.1	368.6	394.1	424.1
35°	331.9	353.8	376.7	405.3
37.5°	317.6	336.4	359.2	386.5
40°	301.5	322.1	342.7	364.1
42.5°	286.7	305.5	324.8	341.8
45°	270.2	286.3	304.6	318.5
47.5°	255.0	269.3	283.6	294.3
50°	239.8	251.0	261.7	271.1
52.5°	221.9	234.4	240.2	246.0
55°	205.8	212.9	218.3	224.1
57.5°	190.1	193.2	195.9	201.3
60°	169.5	173.1	176.2	180.3
62.5°	151.6	153.4	154.3	158.4
65°	134.6	134.2	136.4	138.7
67.5°	116.3	115.9	118.1	119.0
70°	98.4	98.0	98.4	100.6
72.5°	81.4	81.4	81.9	82.8
75°	65.8	65.8	66.2	67.1
77.5°	49.7	50.5	50.1	51.9
80°	36.2	35.3	36.2	37.1
82.5°	23.7	24.6	24.6	23.7
85°	13.4	13.4	13.4	13.4
87.5°	5.8	5.8	6.3	6.7
90°	9.6	6.9	4.2	1.5
92.5°	50.7	49.0	47.3	45.6
95°	100.9	100.2	99.6	98.9
97.5°	153.2	152.9	152.5	152.2
100°	213.0	213.0	213.0	213.0
102.5°	283.6	281.9	280.2	278.5
105°	352.0	350.3	348.6	346.9
107.5°	426.6	424.9	423.2	421.5
110°	504.2	502.5	500.8	499.1

TEST NUMBER: P1035309

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	580.3	579.6	578.9	578.2
115°	659.9	658.5	657.2	655.8
117.5°	736.0	735.6	735.3	734.9
120°	813.1	811.4	809.7	808.0
122.5°	888.1	887.8	887.4	887.1
125°	963.2	961.1	959.1	957.1
127.5°	1037.8	1036.7	1035.7	1034.7
130°	1108.3	1106.6	1104.9	1103.2
132.5°	1180.7	1177.7	1174.6	1171.6
135°	1250.8	1248.7	1246.7	1244.7
137.5°	1319.2	1317.2	1315.1	1313.1
140°	1383.7	1382.0	1380.3	1378.6
142.5°	1448.1	1446.7	1445.4	1444.0
145°	1512.0	1510.6	1509.3	1507.9
147.5°	1570.3	1569.2	1568.2	1567.2
150°	1625.6	1625.9	1626.3	1626.6
152.5°	1677.3	1676.6	1676.0	1675.3
155°	1725.5	1725.5	1725.5	1725.5
157.5°	1769.1	1769.8	1770.4	1771.1
160°	1807.6	1808.7	1809.7	1810.7
162.5°	1843.7	1844.4	1845.0	1845.7
165°	1874.1	1874.8	1875.4	1876.1
167.5°	1899.4	1900.8	1902.1	1903.5
170°	1920.7	1922.1	1923.4	1924.8
172.5°	1936.0	1937.3	1938.7	1940.0
175°	1946.6	1948.0	1949.3	1950.7
177.5°	1954.2	1955.6	1956.9	1958.3
180°	1955.3	1955.3	1955.3	1955.3

(END OF REPORT)