

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035386

Luminaire Tested: S125DIW-B610D1050UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035386
REPORT IS A COMBINATION OF REPORTS P1003739 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D1050UB30-4F0-XX-W2A-A
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6768.0 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44
1	95	91	87	84	86	83	79	77	67	65	63	53	51	50	39	39	38
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	63	57	71	64	58	53	52	48	44	41	38	36	31	29	27
4	72	62	54	48	65	56	50	45	46	41	38	37	33	31	28	26	24
5	66	55	47	41	60	50	44	38	41	36	32	33	29	26	25	23	21
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13
10	45	34	27	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5711	5711	5711	5711
5°	5715	6478	5720	4914
10°	5680	7383	5670	4218
15°	5638	8006	5603	3812
20°	5567	8773	5516	3480
25°	5504	10052	5403	3283
30°	5413	10604	5319	3105
35°	5269	8501	5159	2962
40°	5045	5875	4971	2811
45°	4762	4374	4708	2685
50°	4438	3601	4364	2585
55°	4088	3072	4055	2497
60°	3745	2629	3680	2430
65°	3374	2270	3321	2331
70°	2983	1884	2945	2160
75°	2570	1458	2536	1874
80°	2029	986	1955	1378
85°	1298	494	1252	703

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8722 cd/sqm

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	1.3
10°-20°	255.5	3.8
20°-30°	415.0	6.1
30°-40°	507.2	7.5
40°-50°	460.1	6.8
50°-60°	366.5	5.4
60°-70°	255.2	3.8
70°-80°	136.0	2.0
80°-90°	35.8	0.5
90°-100°	47.0	0.7
100°-110°	312.3	4.6
110°-120°	562.4	8.3
120°-130°	721.9	10.7
130°-140°	776.5	11.5
140°-150°	728.7	10.8
150°-160°	589.5	8.7
160°-170°	381.2	5.6
170°-180°	131.5	1.9
0°-30°	756.3	11.2
0°-40°	1263.5	18.7
0°-60°	2090.1	30.9
0°-90°	2517.1	37.2
90°-120°	921.7	13.6
90°-150°	3148.8	46.5
90°-180°	4251.0	62.8
0°-180°	6768.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	891	891	891	891	891	
5°	890	1028	891	780	890	85
15°	856	1284	850	611	856	241
25°	788	1580	773	516	788	363
35°	686	1268	671	442	686	428
45°	539	598	533	367	539	415
55°	379	368	376	300	379	339
65°	234	226	231	232	234	233
75°	114	111	112	143	114	121
85°	23	25	22	36	23	27
90°	1	25	1	25	1	4
95°	58	22	58	22	58	72
105°	302	305	302	305	302	320
115°	566	562	566	562	566	561
125°	805	805	805	805	805	719
135°	1004	1000	1004	1000	1004	774
145°	1164	1161	1164	1161	1164	728
155°	1282	1273	1282	1273	1282	591
165°	1353	1346	1353	1346	1353	382
175°	1384	1378	1384	1378	1384	132
180°	1384	1384	1384	1384	1384	

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	892.8	898.1	904.1	908.7	916.2	918.5	922.3	924.5	926.8	929.1	930.6
5°	890.5	903.4	914.7	923.0	937.4	942.7	949.5	957.8	967.7	976.0	981.3
7.5°	884.4	904.9	920.0	936.7	956.3	969.2	976.0	993.4	1009.3	1021.4	1037.3
10°	876.9	901.1	924.5	949.5	977.5	991.9	1005.5	1029.7	1051.7	1071.3	1087.2
12.5°	868.6	898.1	926.1	958.6	996.4	1013.8	1022.9	1064.5	1091.8	1102.3	1133.4
15°	855.7	890.5	930.6	970.7	1002.5	1022.9	1047.9	1081.2	1108.4	1131.9	1156.8
17.5°	843.6	881.4	922.3	966.9	1013.1	1039.5	1058.5	1088.0	1117.5	1147.7	1171.2
20°	823.9	873.1	914.7	962.4	1016.9	1035.8	1055.4	1090.2	1122.0	1154.5	1184.1
22.5°	808.0	854.9	911.7	957.1	1003.2	1022.1	1046.4	1082.7	1120.5	1157.6	1200.7
25°	787.6	839.8	889.0	937.4	985.1	1005.5	1027.4	1074.4	1113.7	1161.4	1209.0
27.5°	765.7	819.4	868.6	912.4	957.1	985.1	1008.5	1057.7	1109.9	1162.1	1224.2
30°	742.2	792.9	839.8	882.9	932.1	960.9	984.3	1041.8	1100.1	1166.7	1240.8
32.5°	717.2	764.9	805.0	848.9	901.1	927.6	959.4	1022.1	1091.0	1170.4	1263.5
35°	685.5	730.9	766.4	811.1	863.3	897.3	930.6	1001.0	1081.2	1169.7	1276.4
37.5°	653.7	689.2	723.3	771.0	831.5	862.5	897.3	974.5	1066.0	1167.4	1281.7
40°	615.9	650.7	680.2	728.6	792.1	827.7	864.0	945.0	1048.6	1159.1	1262.7
42.5°	578.0	607.5	640.1	690.8	752.0	789.9	828.5	918.5	1025.9	1134.9	1210.5
45°	538.7	561.4	596.9	643.1	708.2	744.5	788.4	886.0	994.2	1091.0	1128.8
47.5°	497.8	520.5	553.8	598.5	662.8	705.9	747.5	845.1	954.1	1029.0	1029.0
50°	458.5	476.6	509.2	553.8	618.9	658.2	700.6	804.3	892.0	947.2	898.1
52.5°	416.1	436.5	463.8	510.7	575.0	610.6	656.7	745.2	828.5	851.2	775.5
55°	379.0	395.7	421.4	466.1	525.8	562.9	602.2	687.0	757.3	755.8	674.9
57.5°	340.5	354.1	381.3	422.2	477.4	510.7	550.0	623.4	680.9	660.5	584.1
60°	304.9	314.7	341.2	374.5	427.5	458.5	496.3	556.1	600.0	571.2	494.1
62.5°	267.8	279.2	300.4	332.9	379.8	404.8	432.8	493.3	521.3	495.6	416.9
65°	234.5	243.6	262.5	289.8	332.1	354.8	379.0	429.0	455.5	418.4	353.3
67.5°	201.3	211.8	225.5	249.7	283.0	304.1	325.3	368.5	380.6	347.3	292.8
70°	170.2	179.3	192.2	209.6	237.6	256.5	272.4	307.9	316.3	285.2	242.1
72.5°	140.0	146.0	156.6	171.0	196.7	207.3	223.9	248.2	258.8	230.8	199.7
75°	113.5	118.0	124.8	135.4	152.8	164.2	177.8	200.5	199.7	180.1	158.1
77.5°	87.8	88.5	96.1	105.9	116.5	126.3	133.2	149.0	150.6	138.5	120.3
80°	62.8	65.1	68.1	75.7	84.7	88.5	96.8	106.7	108.2	99.1	87.0
82.5°	40.1	41.6	43.9	48.4	54.5	59.0	63.6	67.3	71.1	65.8	56.0
85°	22.7	23.5	25.7	27.2	30.3	32.5	36.3	40.1	39.3	35.6	32.5
87.5°	11.3	11.3	11.3	12.9	14.4	14.4	15.9	16.6	17.4	15.9	14.4
90°	1.0	2.8	4.6	6.5	8.3	9.2	10.0	11.6	13.2	14.8	16.4
92.5°	19.5	17.5	15.4	13.4	11.3	10.3	11.0	12.3	13.7	15.0	16.4
95°	58.5	57.8	57.1	56.4	55.7	55.4	51.1	42.4	33.7	25.1	16.4
97.5°	109.8	111.2	112.5	113.9	115.2	115.9	105.1	83.4	61.8	40.1	18.5
100°	171.3	172.0	172.7	173.4	174.1	174.4	174.9	175.8	176.7	177.6	178.5
102.5°	233.9	234.8	235.7	236.6	237.5	238.0	238.2	238.7	239.1	239.6	240.0
105°	301.6	302.5	303.4	304.3	305.2	305.7	305.7	305.7	305.7	305.7	305.7
107.5°	371.4	371.4	371.4	371.4	371.4	371.4	371.6	372.1	372.5	373.0	373.4
110°	439.1	439.1	439.1	439.1	439.1	439.1	439.3	439.8	440.2	440.7	441.1

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	502.7	503.4	504.0	504.7	505.4	505.7	505.8	506.1	506.3	506.6	506.8
115°	566.3	567.4	568.6	569.7	570.8	571.4	571.5	571.7	572.0	572.2	572.4
117.5°	632.9	632.9	632.9	632.9	632.9	632.9	633.4	634.3	635.2	636.2	637.1
120°	694.5	694.3	694.1	693.8	693.6	693.5	693.8	694.5	695.2	695.8	696.5
122.5°	748.9	750.0	751.2	752.3	753.4	754.0	754.1	754.3	754.6	754.8	755.0
125°	805.3	806.9	808.5	810.1	811.7	812.5	812.5	812.5	812.5	812.5	812.5
127.5°	859.7	860.8	862.0	863.1	864.2	864.8	864.7	864.5	864.2	864.0	863.8
130°	908.9	910.0	911.2	912.3	913.4	914.0	914.1	914.4	914.6	914.9	915.1
132.5°	958.1	959.5	960.9	962.2	963.6	964.3	964.0	963.3	962.6	961.9	961.2
135°	1004.3	1005.7	1007.1	1008.4	1009.8	1010.5	1010.3	1009.8	1009.3	1008.9	1008.4
137.5°	1047.4	1048.8	1050.1	1051.5	1052.8	1053.5	1053.3	1052.8	1052.4	1051.9	1051.5
140°	1089.4	1089.9	1090.3	1090.8	1091.3	1091.5	1091.4	1091.2	1090.9	1090.7	1090.5
142.5°	1127.4	1127.6	1127.8	1128.1	1128.3	1128.4	1128.6	1129.1	1129.6	1130.0	1130.5
145°	1164.3	1164.8	1165.2	1165.7	1166.2	1166.4	1166.4	1166.4	1166.4	1166.4	1166.4
147.5°	1197.2	1197.2	1197.2	1197.2	1197.2	1197.2	1197.3	1197.5	1197.8	1198.0	1198.2
150°	1227.9	1227.5	1227.0	1226.6	1226.1	1225.9	1226.1	1226.6	1227.0	1227.5	1227.9
152.5°	1257.7	1256.6	1255.4	1254.3	1253.2	1252.6	1252.8	1253.3	1253.7	1254.2	1254.6
155°	1282.3	1280.9	1279.6	1278.2	1276.9	1276.2	1276.4	1276.9	1277.3	1277.8	1278.2
157.5°	1301.8	1301.1	1300.4	1299.7	1299.0	1298.7	1298.7	1298.7	1298.7	1298.7	1298.7
160°	1322.3	1320.9	1319.6	1318.2	1316.9	1316.2	1316.3	1316.5	1316.8	1317.0	1317.2
162.5°	1338.7	1337.3	1336.0	1334.6	1333.3	1332.6	1332.7	1332.9	1333.2	1333.4	1333.6
165°	1353.1	1351.7	1350.3	1349.0	1347.6	1346.9	1347.0	1347.3	1347.5	1347.8	1348.0
167.5°	1364.4	1363.0	1361.6	1360.3	1358.9	1358.2	1358.3	1358.5	1358.8	1359.0	1359.2
170°	1373.6	1372.0	1370.4	1368.8	1367.2	1366.4	1366.5	1366.8	1367.0	1367.3	1367.5
172.5°	1379.8	1378.2	1376.6	1375.0	1373.4	1372.6	1372.8	1373.3	1373.7	1374.2	1374.6
175°	1383.9	1382.5	1381.1	1379.8	1378.4	1377.7	1377.8	1378.0	1378.3	1378.5	1378.7
177.5°	1386.9	1385.5	1384.2	1382.8	1381.5	1380.8	1380.9	1381.1	1381.4	1381.6	1381.8
180°	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	932.1	937.4	941.9	945.7	948.8	953.3	950.3	951.0	952.5	955.6	955.6
5°	992.6	1001.0	1005.5	1020.6	1024.4	1023.7	1021.4	1033.5	1032.7	1028.2	1027.4
7.5°	1051.7	1066.0	1078.9	1091.0	1094.8	1104.6	1106.9	1112.2	1110.7	1118.2	1114.5
10°	1105.4	1128.1	1140.2	1158.3	1162.9	1167.4	1173.5	1176.5	1183.3	1182.5	1182.5
12.5°	1147.0	1174.2	1190.1	1194.6	1212.0	1217.3	1222.6	1232.5	1230.2	1231.0	1235.5
15°	1179.5	1206.0	1219.6	1240.8	1252.9	1259.0	1268.0	1278.6	1277.1	1283.9	1282.4
17.5°	1203.7	1228.7	1253.7	1285.4	1286.2	1302.1	1323.3	1327.8	1337.6	1330.8	1330.8
20°	1223.4	1256.7	1292.2	1333.1	1337.6	1347.5	1373.2	1390.6	1402.0	1398.2	1400.4
22.5°	1244.6	1292.2	1333.9	1374.7	1396.7	1414.1	1439.0	1466.3	1476.1	1482.2	1480.6
25°	1271.8	1321.8	1383.0	1439.8	1462.5	1495.8	1529.1	1555.5	1563.1	1579.8	1564.6
27.5°	1299.8	1370.2	1446.6	1513.2	1541.9	1569.2	1609.3	1628.9	1638.8	1646.3	1641.0
30°	1323.3	1420.1	1503.3	1564.6	1585.0	1600.9	1623.6	1628.2	1624.4	1630.4	1638.0
32.5°	1359.6	1454.2	1524.5	1554.0	1551.8	1551.0	1533.6	1509.4	1504.1	1489.7	1509.4
35°	1379.3	1454.9	1482.2	1442.8	1426.9	1398.2	1342.9	1306.6	1274.8	1268.0	1269.6
37.5°	1367.9	1397.4	1364.9	1261.2	1235.5	1191.6	1118.2	1066.8	1043.3	1025.2	1048.6
40°	1306.6	1274.1	1184.8	1058.5	1021.4	979.8	910.9	882.9	849.6	842.8	873.9
42.5°	1205.2	1106.1	979.8	882.2	843.6	820.1	762.6	736.2	712.7	702.1	719.5
45°	1067.5	947.2	820.1	739.9	707.4	679.4	645.4	617.4	602.2	597.7	612.1
47.5°	925.3	798.2	696.8	637.0	603.0	581.8	550.0	534.1	522.0	523.6	525.8
50°	789.1	673.4	595.4	535.7	519.0	502.4	481.2	467.6	461.5	463.8	462.3
52.5°	671.8	578.0	512.2	466.1	458.5	442.6	425.2	413.9	411.6	412.3	414.6
55°	569.0	495.6	443.4	410.1	401.7	390.4	379.8	372.2	366.2	368.5	367.7
57.5°	491.0	426.7	386.6	359.4	353.3	346.5	336.7	332.9	330.6	326.1	329.9
60°	422.2	370.0	335.2	318.5	313.2	308.7	298.1	293.6	292.0	289.8	295.8
62.5°	357.1	320.0	293.6	278.4	273.1	268.6	263.3	259.5	260.3	257.2	260.3
65°	305.7	275.4	256.5	242.9	236.1	233.0	232.3	226.2	225.5	226.2	227.0
67.5°	258.0	232.3	217.9	209.6	204.3	201.3	199.0	195.2	198.2	196.0	197.5
70°	214.9	197.5	182.3	174.0	171.7	172.5	168.7	167.2	168.0	166.4	168.0
72.5°	173.3	158.9	152.8	146.8	143.8	143.0	140.7	138.5	140.7	140.0	140.0
75°	138.5	127.9	121.1	117.3	117.3	115.8	112.0	112.0	112.0	111.2	112.0
77.5°	106.7	97.6	94.6	90.8	90.8	88.5	87.8	87.8	86.3	88.5	87.0
80°	79.4	72.6	68.1	65.8	65.8	65.1	63.6	62.8	63.6	62.8	62.8
82.5°	51.4	48.4	46.2	43.9	43.1	43.9	43.1	41.6	42.4	41.6	43.1
85°	29.5	26.5	26.5	25.0	25.7	24.2	25.0	23.5	22.7	25.0	23.5
87.5°	12.9	12.1	12.1	10.6	10.6	10.6	9.8	10.6	9.8	9.1	9.8
90°	17.5	18.7	19.8	20.9	21.5	21.8	22.5	23.2	23.9	24.6	23.9
92.5°	17.5	18.7	19.8	20.9	21.5	21.6	21.9	22.1	22.4	22.6	22.4
95°	17.5	18.7	19.8	20.9	21.5	21.5	21.5	21.5	21.5	21.5	21.5
97.5°	18.9	19.4	19.8	20.3	20.5	20.6	20.8	21.1	21.3	21.5	21.3
100°	144.5	110.5	76.6	42.6	25.6	25.1	24.2	23.3	22.4	21.5	22.4
102.5°	240.5	240.9	241.4	241.9	242.1	232.5	213.4	194.2	175.1	155.9	175.1
105°	305.7	305.7	305.7	305.7	305.7	305.6	305.4	305.1	304.9	304.7	304.9
107.5°	373.6	373.8	374.1	374.3	374.4	373.9	373.0	372.1	371.2	370.3	371.2
110°	440.4	439.7	439.0	438.3	438.0	438.1	438.4	438.6	438.9	439.1	438.9

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	505.9	505.0	504.1	503.2	502.7	502.5	502.0	501.5	501.1	500.6	501.1
115°	571.5	570.6	569.7	568.8	568.3	567.6	566.3	564.9	563.6	562.2	563.6
117.5°	635.7	634.3	633.0	631.6	630.9	630.7	630.2	629.7	629.3	628.8	629.3
120°	696.1	695.6	695.2	694.7	694.5	693.9	692.8	691.7	690.5	689.4	690.5
122.5°	754.6	754.1	753.7	753.2	753.0	752.3	750.9	749.6	748.2	746.8	748.2
125°	811.6	810.7	809.8	808.9	808.4	808.1	807.4	806.7	806.0	805.3	806.0
127.5°	863.3	862.9	862.4	861.9	861.7	860.8	859.0	857.1	855.3	853.5	855.3
130°	914.4	913.7	913.0	912.3	912.0	911.4	910.3	909.1	908.0	906.8	908.0
132.5°	961.2	961.2	961.2	961.2	961.2	960.6	959.5	958.4	957.2	956.1	957.2
135°	1008.0	1007.5	1007.1	1006.6	1006.4	1005.7	1004.3	1003.0	1001.6	1000.2	1001.6
137.5°	1051.5	1051.5	1051.5	1051.5	1051.5	1050.9	1049.8	1048.7	1047.5	1046.4	1047.5
140°	1090.9	1091.4	1091.8	1092.3	1092.5	1091.8	1090.5	1089.1	1087.8	1086.4	1087.8
142.5°	1130.5	1130.5	1130.5	1130.5	1130.5	1129.8	1128.4	1127.1	1125.7	1124.3	1125.7
145°	1166.6	1166.8	1167.1	1167.3	1167.4	1166.7	1165.4	1164.0	1162.7	1161.3	1162.7
147.5°	1198.4	1198.6	1198.9	1199.1	1199.2	1198.4	1196.8	1195.2	1193.6	1192.0	1193.6
150°	1228.4	1228.8	1229.3	1229.8	1230.0	1229.1	1227.3	1225.4	1223.6	1221.8	1223.6
152.5°	1255.1	1255.5	1256.0	1256.5	1256.7	1255.9	1254.3	1252.7	1251.1	1249.5	1251.1
155°	1278.9	1279.6	1280.3	1281.0	1281.3	1280.4	1278.6	1276.7	1274.9	1273.1	1274.9
157.5°	1299.4	1300.1	1300.8	1301.5	1301.8	1300.9	1299.1	1297.2	1295.4	1293.6	1295.4
160°	1318.1	1319.0	1319.9	1320.8	1321.3	1320.4	1318.6	1316.7	1314.9	1313.1	1314.9
162.5°	1335.0	1336.4	1337.7	1339.1	1339.8	1338.8	1336.7	1334.6	1332.6	1330.5	1332.6
165°	1349.4	1350.7	1352.1	1353.4	1354.1	1353.2	1351.4	1349.5	1347.7	1345.9	1347.7
167.5°	1360.8	1362.4	1364.0	1365.6	1366.4	1365.4	1363.3	1361.3	1359.2	1357.2	1359.2
170°	1369.3	1371.1	1373.0	1374.8	1375.7	1374.7	1372.6	1370.5	1368.5	1366.4	1368.5
172.5°	1376.2	1377.8	1379.4	1381.0	1381.8	1380.8	1378.7	1376.7	1374.6	1372.6	1374.6
175°	1380.5	1382.3	1384.2	1386.0	1386.9	1385.9	1383.8	1381.8	1379.7	1377.7	1379.7
177.5°	1383.4	1385.0	1386.6	1388.2	1389.0	1388.1	1386.3	1384.4	1382.6	1380.8	1382.6
180°	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	954.1	948.8	950.3	948.8	945.0	942.7	936.7	929.1	926.1	922.3	920.0
5°	1030.5	1026.7	1025.9	1019.9	1018.4	1009.3	994.2	986.6	977.5	968.4	959.4
7.5°	1113.7	1109.2	1094.0	1091.8	1093.3	1081.9	1062.2	1047.1	1028.2	1015.3	997.9
10°	1182.5	1173.5	1160.6	1161.4	1156.1	1140.9	1121.3	1105.4	1078.1	1061.5	1036.5
12.5°	1224.2	1216.6	1215.1	1207.5	1203.0	1183.3	1159.8	1139.4	1119.0	1096.3	1077.4
15°	1274.8	1265.0	1258.2	1247.6	1244.6	1224.2	1198.4	1175.0	1151.5	1130.3	1090.2
17.5°	1330.8	1320.2	1294.5	1292.2	1274.1	1254.4	1229.5	1194.6	1169.7	1139.4	1109.9
20°	1394.4	1379.3	1346.0	1337.6	1323.3	1290.7	1256.7	1218.1	1178.0	1147.0	1112.2
22.5°	1465.5	1439.0	1414.8	1388.3	1377.7	1337.6	1290.7	1243.8	1195.4	1153.0	1111.4
25°	1557.8	1523.0	1489.0	1462.5	1444.3	1392.1	1329.3	1267.3	1211.3	1156.1	1101.6
27.5°	1630.4	1600.2	1563.1	1528.3	1504.8	1442.8	1370.9	1290.7	1221.1	1153.8	1095.5
30°	1635.7	1626.7	1604.0	1585.0	1559.3	1492.7	1413.3	1322.5	1236.3	1154.5	1083.4
32.5°	1536.6	1554.8	1564.6	1567.6	1562.3	1523.8	1451.1	1351.3	1249.9	1147.7	1072.8
35°	1323.3	1371.7	1431.5	1454.2	1476.1	1496.5	1458.7	1371.7	1254.4	1146.2	1056.2
37.5°	1089.5	1133.4	1232.5	1277.9	1303.6	1384.6	1415.6	1368.7	1263.5	1147.7	1040.3
40°	879.2	948.8	1019.9	1081.2	1121.3	1212.0	1308.1	1318.7	1250.6	1133.4	1019.9
42.5°	739.9	780.8	834.5	891.3	926.8	1034.3	1164.4	1240.8	1210.5	1109.9	994.9
45°	630.2	660.5	711.2	730.1	775.5	878.4	1016.1	1126.6	1141.7	1072.8	966.2
47.5°	541.0	566.7	599.2	622.7	659.0	736.2	852.7	974.5	1047.1	1022.1	926.1
50°	476.6	497.8	525.1	538.7	562.1	631.7	719.5	840.6	938.2	946.5	873.9
52.5°	422.9	435.0	456.2	471.4	490.3	532.6	612.1	711.9	821.7	867.0	809.5
55°	376.0	385.9	404.8	414.6	424.4	460.8	522.8	613.6	716.5	776.3	743.7
57.5°	333.7	342.0	357.9	366.9	372.2	407.0	454.7	525.8	618.1	690.8	672.6
60°	298.9	306.4	315.5	322.3	328.4	357.1	390.4	447.9	530.4	600.7	596.2
62.5°	261.8	268.6	278.4	285.2	290.5	308.7	336.7	380.6	450.9	516.0	528.9
65°	229.2	234.5	241.4	244.4	251.2	264.8	287.5	326.8	384.3	442.6	451.7
67.5°	199.7	201.3	205.8	212.6	214.1	226.2	246.6	276.2	320.8	368.5	382.8
70°	168.0	170.2	174.0	179.3	182.3	189.9	207.3	227.0	265.6	307.2	317.8
72.5°	140.0	143.0	144.5	147.5	149.0	161.2	168.7	188.4	214.9	249.7	261.0
75°	113.5	116.5	117.3	118.8	120.3	125.6	136.2	148.3	170.2	192.9	208.1
77.5°	90.0	89.3	90.8	93.1	92.3	96.8	103.7	114.2	128.6	147.5	157.4
80°	63.6	63.6	65.8	68.1	67.3	71.9	74.1	81.7	93.8	105.9	109.7
82.5°	42.4	42.4	44.6	44.6	46.2	46.9	49.9	53.7	63.6	69.6	71.9
85°	24.2	24.2	25.0	25.0	25.0	26.5	28.8	30.3	33.3	37.1	38.6
87.5°	9.8	10.6	10.6	10.6	10.6	12.1	12.1	13.6	14.4	15.9	15.9
90°	23.2	22.5	21.8	21.5	20.9	19.8	18.7	17.5	16.4	14.8	13.2
92.5°	22.1	21.9	21.6	21.5	20.9	19.8	18.7	17.5	16.4	15.0	13.7
95°	21.5	21.5	21.5	21.5	20.9	19.8	18.7	17.5	16.4	25.1	33.7
97.5°	21.1	20.8	20.6	20.5	20.3	19.8	19.4	18.9	18.5	40.1	61.8
100°	23.3	24.2	25.1	25.6	42.6	76.6	110.5	144.5	178.5	177.6	176.7
102.5°	194.2	213.4	232.5	242.1	241.9	241.4	240.9	240.5	240.0	239.6	239.1
105°	305.1	305.4	305.6	305.7	305.7	305.7	305.7	305.7	305.7	305.7	305.7
107.5°	372.1	373.0	373.9	374.4	374.3	374.1	373.8	373.6	373.4	373.0	372.5
110°	438.6	438.4	438.1	438.0	438.3	439.0	439.7	440.4	441.1	440.7	440.2

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	501.5	502.0	502.5	502.7	503.2	504.1	505.0	505.9	506.8	506.6	506.3
115°	564.9	566.3	567.6	568.3	568.8	569.7	570.6	571.5	572.4	572.2	572.0
117.5°	629.7	630.2	630.7	630.9	631.6	633.0	634.3	635.7	637.1	636.2	635.2
120°	691.7	692.8	693.9	694.5	694.7	695.2	695.6	696.1	696.5	695.8	695.2
122.5°	749.6	750.9	752.3	753.0	753.2	753.7	754.1	754.6	755.0	754.8	754.6
125°	806.7	807.4	808.1	808.4	808.9	809.8	810.7	811.6	812.5	812.5	812.5
127.5°	857.1	859.0	860.8	861.7	861.9	862.4	862.9	863.3	863.8	864.0	864.2
130°	909.1	910.3	911.4	912.0	912.3	913.0	913.7	914.4	915.1	914.9	914.6
132.5°	958.4	959.5	960.6	961.2	961.2	961.2	961.2	961.2	961.2	961.9	962.6
135°	1003.0	1004.3	1005.7	1006.4	1006.6	1007.1	1007.5	1008.0	1008.4	1008.9	1009.3
137.5°	1048.7	1049.8	1050.9	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.9	1052.4
140°	1089.1	1090.5	1091.8	1092.5	1092.3	1091.8	1091.4	1090.9	1090.5	1090.7	1090.9
142.5°	1127.1	1128.4	1129.8	1130.5	1130.5	1130.5	1130.5	1130.5	1130.5	1130.0	1129.6
145°	1164.0	1165.4	1166.7	1167.4	1167.3	1167.1	1166.8	1166.6	1166.4	1166.4	1166.4
147.5°	1195.2	1196.8	1198.4	1199.2	1199.1	1198.9	1198.6	1198.4	1198.2	1198.0	1197.8
150°	1225.4	1227.3	1229.1	1230.0	1229.8	1229.3	1228.8	1228.4	1227.9	1227.5	1227.0
152.5°	1252.7	1254.3	1255.9	1256.7	1256.5	1256.0	1255.5	1255.1	1254.6	1254.2	1253.7
155°	1276.7	1278.6	1280.4	1281.3	1281.0	1280.3	1279.6	1278.9	1278.2	1277.8	1277.3
157.5°	1297.2	1299.1	1300.9	1301.8	1301.5	1300.8	1300.1	1299.4	1298.7	1298.7	1298.7
160°	1316.7	1318.6	1320.4	1321.3	1320.8	1319.9	1319.0	1318.1	1317.2	1317.0	1316.8
162.5°	1334.6	1336.7	1338.8	1339.8	1339.1	1337.7	1336.4	1335.0	1333.6	1333.4	1333.2
165°	1349.5	1351.4	1353.2	1354.1	1353.4	1352.1	1350.7	1349.4	1348.0	1347.8	1347.5
167.5°	1361.3	1363.3	1365.4	1366.4	1365.6	1364.0	1362.4	1360.8	1359.2	1359.0	1358.8
170°	1370.5	1372.6	1374.7	1375.7	1374.8	1373.0	1371.1	1369.3	1367.5	1367.3	1367.0
172.5°	1376.7	1378.7	1380.8	1381.8	1381.0	1379.4	1377.8	1376.2	1374.6	1374.2	1373.7
175°	1381.8	1383.8	1385.9	1386.9	1386.0	1384.2	1382.3	1380.5	1378.7	1378.5	1378.3
177.5°	1384.4	1386.3	1388.1	1389.0	1388.2	1386.6	1385.0	1383.4	1381.8	1381.6	1381.4
180°	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	917.0	913.2	908.7	908.7	903.4	901.1	896.6	895.0	891.3	885.2	880.7
5°	949.5	939.7	933.6	928.3	917.0	908.7	900.3	891.3	882.2	871.6	859.5
7.5°	981.3	963.1	954.8	945.7	929.1	911.7	895.0	882.9	870.8	854.2	839.1
10°	1014.6	991.9	976.8	964.6	938.9	917.0	892.8	875.4	856.5	835.3	815.6
12.5°	1042.6	1013.1	1000.2	977.5	948.0	921.5	891.3	864.8	839.8	814.8	790.6
15°	1066.0	1038.0	1006.3	997.2	956.3	918.5	884.4	850.4	819.4	794.4	766.4
17.5°	1073.6	1038.0	1022.1	1000.2	951.8	912.4	869.3	832.2	802.7	765.7	743.7
20°	1075.9	1041.8	1019.9	999.4	956.3	904.1	861.8	816.4	780.8	743.7	708.9
22.5°	1069.8	1029.7	1008.5	988.9	940.4	895.8	846.6	796.7	755.1	721.0	686.2
25°	1058.5	1011.6	991.1	969.9	923.8	874.6	820.9	773.2	734.6	693.8	659.7
27.5°	1043.3	989.6	966.2	944.2	898.8	852.7	802.0	752.8	709.7	666.6	634.8
30°	1024.4	962.4	941.2	912.4	868.6	824.7	778.5	729.3	680.9	640.1	605.3
32.5°	1000.2	935.1	907.1	879.9	832.2	792.1	748.3	702.1	655.2	615.1	578.8
35°	978.3	904.1	873.1	845.9	792.9	750.5	714.2	671.1	629.5	587.9	555.3
37.5°	948.8	873.1	836.0	808.0	754.3	711.2	677.1	643.9	600.0	559.9	529.6
40°	917.7	834.5	799.7	771.7	715.7	668.8	636.3	606.8	571.2	534.1	502.4
42.5°	889.7	797.4	760.4	726.3	669.6	628.0	594.7	572.0	539.4	506.2	477.4
45°	854.2	758.1	718.0	682.4	628.0	582.6	550.8	532.6	508.4	475.9	450.9
47.5°	817.9	715.7	674.1	639.3	580.3	540.2	509.2	491.8	475.1	449.4	424.4
50°	770.2	671.1	633.3	593.2	534.9	494.1	468.3	450.9	438.1	419.9	398.7
52.5°	718.0	624.9	584.1	549.3	491.8	454.7	425.2	415.4	402.5	388.9	370.7
55°	662.8	575.0	535.7	501.6	448.7	410.8	386.6	376.0	366.2	355.6	343.5
57.5°	607.5	522.8	485.7	455.5	406.3	370.0	350.3	335.9	329.1	323.1	313.2
60°	538.7	466.8	438.1	410.8	362.4	329.1	310.2	299.6	293.6	290.5	286.0
62.5°	478.2	419.1	387.4	360.9	322.3	292.8	274.6	266.3	261.0	259.5	254.2
65°	413.9	363.2	338.2	315.5	282.2	255.7	240.6	230.8	227.0	226.2	226.2
67.5°	353.3	312.5	287.5	271.6	242.9	219.4	205.0	201.3	199.0	196.0	195.2
70°	296.6	264.0	242.1	228.5	202.8	185.4	174.0	168.0	168.0	165.7	164.2
72.5°	246.6	214.1	199.7	188.4	167.2	152.1	143.8	142.2	136.9	136.2	136.2
75°	192.9	168.7	158.9	149.0	133.2	122.6	115.8	112.0	108.9	108.9	109.7
77.5°	145.3	128.6	119.5	112.0	100.6	93.8	88.5	87.0	84.0	84.0	84.0
80°	102.9	93.8	87.0	81.0	72.6	66.6	63.6	60.5	60.5	59.8	60.5
82.5°	66.6	59.0	55.2	54.5	46.9	44.6	40.9	41.6	39.3	38.6	40.1
85°	38.6	34.8	30.3	28.8	25.7	22.7	21.2	21.9	21.2	20.4	21.2
87.5°	15.1	12.9	12.1	12.1	9.8	9.1	8.3	9.1	7.6	7.6	8.3
90°	11.6	10.0	9.2	8.3	6.5	4.6	2.8	1.0	2.8	4.6	6.5
92.5°	12.3	11.0	10.3	11.3	13.4	15.4	17.5	19.5	17.5	15.4	13.4
95°	42.4	51.1	55.4	55.7	56.4	57.1	57.8	58.5	57.8	57.1	56.4
97.5°	83.4	105.1	115.9	115.2	113.9	112.5	111.2	109.8	111.2	112.5	113.9
100°	175.8	174.9	174.4	174.1	173.4	172.7	172.0	171.3	172.0	172.7	173.4
102.5°	238.7	238.2	238.0	237.5	236.6	235.7	234.8	233.9	234.8	235.7	236.6
105°	305.7	305.7	305.7	305.2	304.3	303.4	302.5	301.6	302.5	303.4	304.3
107.5°	372.1	371.6	371.4	371.4	371.4	371.4	371.4	371.4	371.4	371.4	371.4
110°	439.8	439.3	439.1	439.1	439.1	439.1	439.1	439.1	439.1	439.1	439.1

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	506.1	505.8	505.7	505.4	504.7	504.0	503.4	502.7	503.4	504.0	504.7
115°	571.7	571.5	571.4	570.8	569.7	568.6	567.4	566.3	567.4	568.6	569.7
117.5°	634.3	633.4	632.9	632.9	632.9	632.9	632.9	632.9	632.9	632.9	632.9
120°	694.5	693.8	693.5	693.6	693.8	694.1	694.3	694.5	694.3	694.1	693.8
122.5°	754.3	754.1	754.0	753.4	752.3	751.2	750.0	748.9	750.0	751.2	752.3
125°	812.5	812.5	812.5	811.7	810.1	808.5	806.9	805.3	806.9	808.5	810.1
127.5°	864.5	864.7	864.8	864.2	863.1	862.0	860.8	859.7	860.8	862.0	863.1
130°	914.4	914.1	914.0	913.4	912.3	911.2	910.0	908.9	910.0	911.2	912.3
132.5°	963.3	964.0	964.3	963.6	962.2	960.9	959.5	958.1	959.5	960.9	962.2
135°	1009.8	1010.3	1010.5	1009.8	1008.4	1007.1	1005.7	1004.3	1005.7	1007.1	1008.4
137.5°	1052.8	1053.3	1053.5	1052.8	1051.5	1050.1	1048.8	1047.4	1048.8	1050.1	1051.5
140°	1091.2	1091.4	1091.5	1091.3	1090.8	1090.3	1089.9	1089.4	1089.9	1090.3	1090.8
142.5°	1129.1	1128.6	1128.4	1128.3	1128.1	1127.8	1127.6	1127.4	1127.6	1127.8	1128.1
145°	1166.4	1166.4	1166.4	1166.2	1165.7	1165.2	1164.8	1164.3	1164.8	1165.2	1165.7
147.5°	1197.5	1197.3	1197.2	1197.2	1197.2	1197.2	1197.2	1197.2	1197.2	1197.2	1197.2
150°	1226.6	1226.1	1225.9	1226.1	1226.6	1227.0	1227.5	1227.9	1227.5	1227.0	1226.6
152.5°	1253.3	1252.8	1252.6	1253.2	1254.3	1255.4	1256.6	1257.7	1256.6	1255.4	1254.3
155°	1276.9	1276.4	1276.2	1276.9	1278.2	1279.6	1280.9	1282.3	1280.9	1279.6	1278.2
157.5°	1298.7	1298.7	1298.7	1299.0	1299.7	1300.4	1301.1	1301.8	1301.1	1300.4	1299.7
160°	1316.5	1316.3	1316.2	1316.9	1318.2	1319.6	1320.9	1322.3	1320.9	1319.6	1318.2
162.5°	1332.9	1332.7	1332.6	1333.3	1334.6	1336.0	1337.3	1338.7	1337.3	1336.0	1334.6
165°	1347.3	1347.0	1346.9	1347.6	1349.0	1350.3	1351.7	1353.1	1351.7	1350.3	1349.0
167.5°	1358.5	1358.3	1358.2	1358.9	1360.3	1361.6	1363.0	1364.4	1363.0	1361.6	1360.3
170°	1366.8	1366.5	1366.4	1367.2	1368.8	1370.4	1372.0	1373.6	1372.0	1370.4	1368.8
172.5°	1373.3	1372.8	1372.6	1373.4	1375.0	1376.6	1378.2	1379.8	1378.2	1376.6	1375.0
175°	1378.0	1377.8	1377.7	1378.4	1379.8	1381.1	1382.5	1383.9	1382.5	1381.1	1379.8
177.5°	1381.1	1380.9	1380.8	1381.5	1382.8	1384.2	1385.5	1386.9	1385.5	1384.2	1382.8
180°	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	879.2	877.6	873.9	871.6	864.0	854.9	851.9	844.3	847.4	842.1	842.1
5°	855.7	848.9	844.3	837.5	823.2	813.3	802.7	797.4	794.4	790.6	787.6
7.5°	825.4	820.1	815.6	802.7	786.8	773.2	760.4	755.1	745.2	738.4	735.4
10°	799.0	791.4	780.8	765.7	749.0	731.6	720.3	708.9	701.4	697.6	689.2
12.5°	771.7	762.6	751.3	729.3	711.2	700.6	680.2	669.6	665.8	662.8	652.9
15°	743.7	733.9	720.3	699.8	684.0	659.0	646.9	638.6	629.5	628.7	621.2
17.5°	718.8	706.7	695.3	670.3	650.7	628.7	621.9	612.8	604.5	595.4	591.6
20°	687.0	675.6	667.3	640.1	618.1	604.5	593.2	585.6	580.3	571.2	569.7
22.5°	658.2	646.1	634.8	614.3	595.4	578.0	564.4	556.1	553.8	550.0	543.2
25°	630.2	618.1	604.5	585.6	565.9	553.8	541.7	536.4	531.9	525.8	520.5
27.5°	606.8	595.4	582.6	559.1	542.5	533.4	520.5	514.5	508.4	505.4	503.1
30°	578.8	565.9	556.1	537.9	519.8	507.7	498.6	493.3	488.0	485.0	483.5
32.5°	551.6	539.4	532.6	513.0	498.6	484.2	477.4	473.6	470.6	467.6	464.5
35°	529.6	517.5	506.9	488.8	474.4	464.5	459.2	453.2	450.9	447.9	447.9
37.5°	502.4	493.3	482.7	465.3	452.4	444.9	440.3	432.8	432.0	430.5	428.2
40°	478.9	469.8	460.0	444.9	433.5	424.4	418.4	414.6	412.3	410.8	409.3
42.5°	454.0	444.1	439.6	422.2	412.3	403.3	400.2	396.5	395.7	392.7	388.9
45°	429.7	421.4	412.3	399.5	391.2	383.6	379.0	376.0	372.2	371.5	369.2
47.5°	408.6	398.7	390.4	378.3	369.2	363.2	359.4	355.6	352.6	350.3	348.0
50°	381.3	373.8	366.9	354.1	346.5	340.5	335.2	332.1	329.1	329.1	329.1
52.5°	354.8	348.0	342.0	332.9	323.8	318.5	312.5	310.2	308.7	306.4	308.7
55°	329.1	322.3	316.3	309.4	298.9	294.3	288.3	286.0	286.7	286.7	289.0
57.5°	301.9	296.6	292.8	284.5	274.6	270.1	266.3	264.0	264.0	267.1	267.8
60°	275.4	270.1	263.3	255.7	249.7	244.4	242.1	242.9	242.9	244.4	248.2
62.5°	245.9	242.9	239.1	228.5	224.7	220.9	217.9	220.2	219.4	223.2	228.5
65°	218.7	215.6	210.3	205.0	200.5	196.7	196.0	196.7	198.2	202.0	208.1
67.5°	188.4	188.4	183.9	179.3	175.5	171.7	172.5	173.3	174.8	179.3	188.4
70°	163.4	160.4	155.9	152.8	149.8	148.3	146.8	149.8	154.3	157.4	164.2
72.5°	136.2	133.9	130.1	127.1	126.3	124.8	124.1	125.6	130.1	135.4	143.0
75°	107.4	108.2	105.9	103.7	103.7	101.4	102.9	102.9	107.4	112.7	118.8
77.5°	83.2	82.5	81.7	80.2	79.4	79.4	79.4	81.0	85.5	88.5	94.6
80°	59.0	59.8	57.5	58.3	57.5	58.3	58.3	61.3	63.6	67.3	71.9
82.5°	39.3	39.3	37.8	38.6	38.6	38.6	39.3	40.9	43.9	46.9	49.9
85°	21.9	22.7	21.2	22.7	22.7	22.7	23.5	24.2	26.5	27.2	30.3
87.5°	8.3	9.8	9.8	8.3	9.1	9.8	10.6	9.8	11.3	12.9	13.6
90°	8.3	9.2	10.0	11.6	13.2	14.8	16.4	17.5	18.7	19.8	20.9
92.5°	11.3	10.3	11.0	12.3	13.7	15.0	16.4	17.5	18.7	19.8	20.9
95°	55.7	55.4	51.1	42.4	33.7	25.1	16.4	17.5	18.7	19.8	20.9
97.5°	115.2	115.9	105.1	83.4	61.8	40.1	18.5	18.9	19.4	19.8	20.3
100°	174.1	174.4	174.9	175.8	176.7	177.6	178.5	144.5	110.5	76.6	42.6
102.5°	237.5	238.0	238.2	238.7	239.1	239.6	240.0	240.5	240.9	241.4	241.9
105°	305.2	305.7	305.7	305.7	305.7	305.7	305.7	305.7	305.7	305.7	305.7
107.5°	371.4	371.4	371.6	372.1	372.5	373.0	373.4	373.6	373.8	374.1	374.3
110°	439.1	439.1	439.3	439.8	440.2	440.7	441.1	440.4	439.7	439.0	438.3

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	505.4	505.7	505.8	506.1	506.3	506.6	506.8	505.9	505.0	504.1	503.2
115°	570.8	571.4	571.5	571.7	572.0	572.2	572.4	571.5	570.6	569.7	568.8
117.5°	632.9	632.9	633.4	634.3	635.2	636.2	637.1	635.7	634.3	633.0	631.6
120°	693.6	693.5	693.8	694.5	695.2	695.8	696.5	696.1	695.6	695.2	694.7
122.5°	753.4	754.0	754.1	754.3	754.6	754.8	755.0	754.6	754.1	753.7	753.2
125°	811.7	812.5	812.5	812.5	812.5	812.5	812.5	811.6	810.7	809.8	808.9
127.5°	864.2	864.8	864.7	864.5	864.2	864.0	863.8	863.3	862.9	862.4	861.9
130°	913.4	914.0	914.1	914.4	914.6	914.9	915.1	914.4	913.7	913.0	912.3
132.5°	963.6	964.3	964.0	963.3	962.6	961.9	961.2	961.2	961.2	961.2	961.2
135°	1009.8	1010.5	1010.3	1009.8	1009.3	1008.9	1008.4	1008.0	1007.5	1007.1	1006.6
137.5°	1052.8	1053.5	1053.3	1052.8	1052.4	1051.9	1051.5	1051.5	1051.5	1051.5	1051.5
140°	1091.3	1091.5	1091.4	1091.2	1090.9	1090.7	1090.5	1090.9	1091.4	1091.8	1092.3
142.5°	1128.3	1128.4	1128.6	1129.1	1129.6	1130.0	1130.5	1130.5	1130.5	1130.5	1130.5
145°	1166.2	1166.4	1166.4	1166.4	1166.4	1166.4	1166.4	1166.6	1166.8	1167.1	1167.3
147.5°	1197.2	1197.2	1197.3	1197.5	1197.8	1198.0	1198.2	1198.4	1198.6	1198.9	1199.1
150°	1226.1	1225.9	1226.1	1226.6	1227.0	1227.5	1227.9	1228.4	1228.8	1229.3	1229.8
152.5°	1253.2	1252.6	1252.8	1253.3	1253.7	1254.2	1254.6	1255.1	1255.5	1256.0	1256.5
155°	1276.9	1276.2	1276.4	1276.9	1277.3	1277.8	1278.2	1278.9	1279.6	1280.3	1281.0
157.5°	1299.0	1298.7	1298.7	1298.7	1298.7	1298.7	1298.7	1299.4	1300.1	1300.8	1301.5
160°	1316.9	1316.2	1316.3	1316.5	1316.8	1317.0	1317.2	1318.1	1319.0	1319.9	1320.8
162.5°	1333.3	1332.6	1332.7	1332.9	1333.2	1333.4	1333.6	1335.0	1336.4	1337.7	1339.1
165°	1347.6	1346.9	1347.0	1347.3	1347.5	1347.8	1348.0	1349.4	1350.7	1352.1	1353.4
167.5°	1358.9	1358.2	1358.3	1358.5	1358.8	1359.0	1359.2	1360.8	1362.4	1364.0	1365.6
170°	1367.2	1366.4	1366.5	1366.8	1367.0	1367.3	1367.5	1369.3	1371.1	1373.0	1374.8
172.5°	1373.4	1372.6	1372.8	1373.3	1373.7	1374.2	1374.6	1376.2	1377.8	1379.4	1381.0
175°	1378.4	1377.7	1377.8	1378.0	1378.3	1378.5	1378.7	1380.5	1382.3	1384.2	1386.0
177.5°	1381.5	1380.8	1380.9	1381.1	1381.4	1381.6	1381.8	1383.4	1385.0	1386.6	1388.2
180°	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	845.1	839.8	839.1	840.6	837.5	842.1	840.6	842.1	838.3	842.1	839.8
5°	786.8	785.3	782.3	778.5	779.3	780.0	783.8	780.0	783.1	783.8	787.6
7.5°	732.4	729.3	731.6	730.1	723.3	721.8	723.3	725.6	730.1	733.1	735.4
10°	688.5	687.0	684.0	681.7	677.9	675.6	678.7	675.6	681.7	687.0	687.0
12.5°	655.2	649.2	645.4	644.6	636.3	637.8	640.8	643.1	649.9	652.9	652.9
15°	620.4	615.9	614.3	611.3	608.3	611.3	609.8	612.1	615.1	618.1	619.6
17.5°	590.1	589.4	590.1	582.6	584.8	581.1	581.8	585.6	583.3	585.6	590.1
20°	562.9	564.4	562.1	559.1	559.1	554.6	559.9	558.4	559.1	563.7	570.5
22.5°	542.5	541.7	539.4	537.2	534.1	534.9	535.7	534.1	540.2	544.0	544.7
25°	520.5	519.0	518.3	516.0	513.0	516.0	515.2	516.0	517.5	523.6	519.0
27.5°	500.1	497.1	498.6	496.3	495.6	496.3	496.3	497.1	498.6	499.3	500.1
30°	482.7	479.7	478.9	477.4	476.6	477.4	478.9	477.4	483.5	482.7	482.7
32.5°	463.8	461.5	460.0	460.0	459.2	458.5	459.2	460.0	464.5	461.5	464.5
35°	445.6	444.1	444.1	442.6	441.8	441.8	441.8	444.9	443.4	445.6	445.6
37.5°	428.2	428.2	427.5	426.0	425.2	426.0	425.2	426.7	426.0	426.7	427.5
40°	410.1	408.6	407.8	407.8	405.5	403.3	405.5	405.5	406.3	408.6	409.3
42.5°	388.1	388.9	388.9	385.9	385.9	385.9	386.6	387.4	387.4	388.9	388.9
45°	369.2	367.7	367.7	367.7	366.2	366.9	368.5	368.5	368.5	368.5	366.9
47.5°	348.0	348.0	348.8	348.8	351.1	350.3	350.3	349.5	348.0	348.0	348.8
50°	328.4	330.6	331.4	331.4	332.1	332.9	332.9	331.4	330.6	328.4	328.4
52.5°	309.4	311.0	312.5	314.7	316.3	315.5	315.5	314.0	311.0	310.2	309.4
55°	289.0	291.3	294.3	296.6	298.9	299.6	299.6	296.6	293.6	289.8	289.8
57.5°	270.1	272.4	277.7	279.9	283.0	283.0	281.4	279.2	274.6	271.6	269.3
60°	251.2	255.0	258.8	263.3	267.1	267.8	265.6	262.5	257.2	253.5	250.4
62.5°	230.8	234.5	242.1	246.6	249.7	249.7	249.7	245.9	239.1	233.8	229.2
65°	211.1	214.9	221.7	227.7	230.0	232.3	230.0	226.2	220.9	214.9	210.3
67.5°	190.7	195.2	202.0	206.5	209.6	211.8	210.3	207.3	200.5	192.2	189.1
70°	168.0	170.2	180.1	184.6	189.1	190.7	189.1	184.6	177.8	168.7	165.7
72.5°	146.8	149.0	158.1	161.9	165.7	167.2	164.9	161.9	155.9	147.5	143.8
75°	122.6	126.3	130.9	136.9	141.5	143.0	140.7	138.5	130.9	125.6	122.6
77.5°	96.8	100.6	106.7	112.0	116.5	115.8	112.7	113.5	105.2	99.1	96.8
80°	73.4	76.4	81.0	85.5	87.8	87.8	87.0	84.0	81.0	76.4	72.6
82.5°	50.7	54.5	58.3	61.3	61.3	62.0	60.5	59.8	56.7	53.0	52.2
85°	30.3	31.0	34.0	34.0	37.1	35.6	34.8	37.1	34.0	31.8	31.0
87.5°	13.6	12.9	13.6	13.6	12.9	14.4	14.4	13.6	14.4	13.6	13.6
90°	21.5	21.8	22.5	23.2	23.9	24.6	23.9	23.2	22.5	21.8	21.5
92.5°	21.5	21.6	21.9	22.1	22.4	22.6	22.4	22.1	21.9	21.6	21.5
95°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5
97.5°	20.5	20.6	20.8	21.1	21.3	21.5	21.3	21.1	20.8	20.6	20.5
100°	25.6	25.1	24.2	23.3	22.4	21.5	22.4	23.3	24.2	25.1	25.6
102.5°	242.1	232.5	213.4	194.2	175.1	155.9	175.1	194.2	213.4	232.5	242.1
105°	305.7	305.6	305.4	305.1	304.9	304.7	304.9	305.1	305.4	305.6	305.7
107.5°	374.4	373.9	373.0	372.1	371.2	370.3	371.2	372.1	373.0	373.9	374.4
110°	438.0	438.1	438.4	438.6	438.9	439.1	438.9	438.6	438.4	438.1	438.0

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	502.7	502.5	502.0	501.5	501.1	500.6	501.1	501.5	502.0	502.5	502.7
115°	568.3	567.6	566.3	564.9	563.6	562.2	563.6	564.9	566.3	567.6	568.3
117.5°	630.9	630.7	630.2	629.7	629.3	628.8	629.3	629.7	630.2	630.7	630.9
120°	694.5	693.9	692.8	691.7	690.5	689.4	690.5	691.7	692.8	693.9	694.5
122.5°	753.0	752.3	750.9	749.6	748.2	746.8	748.2	749.6	750.9	752.3	753.0
125°	808.4	808.1	807.4	806.7	806.0	805.3	806.0	806.7	807.4	808.1	808.4
127.5°	861.7	860.8	859.0	857.1	855.3	853.5	855.3	857.1	859.0	860.8	861.7
130°	912.0	911.4	910.3	909.1	908.0	906.8	908.0	909.1	910.3	911.4	912.0
132.5°	961.2	960.6	959.5	958.4	957.2	956.1	957.2	958.4	959.5	960.6	961.2
135°	1006.4	1005.7	1004.3	1003.0	1001.6	1000.2	1001.6	1003.0	1004.3	1005.7	1006.4
137.5°	1051.5	1050.9	1049.8	1048.7	1047.5	1046.4	1047.5	1048.7	1049.8	1050.9	1051.5
140°	1092.5	1091.8	1090.5	1089.1	1087.8	1086.4	1087.8	1089.1	1090.5	1091.8	1092.5
142.5°	1130.5	1129.8	1128.4	1127.1	1125.7	1124.3	1125.7	1127.1	1128.4	1129.8	1130.5
145°	1167.4	1166.7	1165.4	1164.0	1162.7	1161.3	1162.7	1164.0	1165.4	1166.7	1167.4
147.5°	1199.2	1198.4	1196.8	1195.2	1193.6	1192.0	1193.6	1195.2	1196.8	1198.4	1199.2
150°	1230.0	1229.1	1227.3	1225.4	1223.6	1221.8	1223.6	1225.4	1227.3	1229.1	1230.0
152.5°	1256.7	1255.9	1254.3	1252.7	1251.1	1249.5	1251.1	1252.7	1254.3	1255.9	1256.7
155°	1281.3	1280.4	1278.6	1276.7	1274.9	1273.1	1274.9	1276.7	1278.6	1280.4	1281.3
157.5°	1301.8	1300.9	1299.1	1297.2	1295.4	1293.6	1295.4	1297.2	1299.1	1300.9	1301.8
160°	1321.3	1320.4	1318.6	1316.7	1314.9	1313.1	1314.9	1316.7	1318.6	1320.4	1321.3
162.5°	1339.8	1338.8	1336.7	1334.6	1332.6	1330.5	1332.6	1334.6	1336.7	1338.8	1339.8
165°	1354.1	1353.2	1351.4	1349.5	1347.7	1345.9	1347.7	1349.5	1351.4	1353.2	1354.1
167.5°	1366.4	1365.4	1363.3	1361.3	1359.2	1357.2	1359.2	1361.3	1363.3	1365.4	1366.4
170°	1375.7	1374.7	1372.6	1370.5	1368.5	1366.4	1368.5	1370.5	1372.6	1374.7	1375.7
172.5°	1381.8	1380.8	1378.7	1376.7	1374.6	1372.6	1374.6	1376.7	1378.7	1380.8	1381.8
175°	1386.9	1385.9	1383.8	1381.8	1379.7	1377.7	1379.7	1381.8	1383.8	1385.9	1386.9
177.5°	1389.0	1388.1	1386.3	1384.4	1382.6	1380.8	1382.6	1384.4	1386.3	1388.1	1389.0
180°	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	846.6	842.1	847.4	840.6	842.1	850.4	849.6	857.2	861.8	861.0	864.8
5°	790.6	790.6	792.9	792.1	799.7	806.5	815.6	823.2	831.5	836.0	841.3
7.5°	735.4	743.0	744.5	748.3	757.3	768.7	777.8	789.1	801.2	809.5	815.6
10°	690.0	696.1	702.1	705.1	715.0	730.1	743.0	761.1	776.3	785.3	793.7
12.5°	649.9	656.7	659.7	673.4	680.2	690.0	708.2	727.8	744.5	754.3	761.1
15°	621.2	624.9	631.7	640.1	646.9	659.0	674.1	696.1	711.9	720.3	743.7
17.5°	596.9	601.5	605.3	609.1	619.6	632.5	646.9	665.8	686.2	700.6	712.7
20°	572.0	574.2	578.8	584.8	592.4	604.5	617.4	637.0	655.2	666.6	682.4
22.5°	542.5	549.3	553.8	558.4	566.7	580.3	592.4	606.8	629.5	642.3	659.0
25°	525.1	528.1	531.1	536.4	542.5	554.6	568.2	583.3	601.5	615.1	629.5
27.5°	502.4	506.9	510.7	517.5	521.3	531.1	544.0	559.1	581.1	592.4	604.5
30°	483.5	488.0	491.0	494.1	499.3	509.9	522.0	534.1	554.6	569.0	581.1
32.5°	464.5	469.1	472.9	475.1	480.4	487.2	497.1	512.2	529.6	539.4	555.3
35°	447.9	447.9	452.4	455.5	460.0	466.1	475.1	486.5	504.6	517.5	531.9
37.5°	429.0	429.7	433.5	435.8	440.3	446.4	455.5	466.1	481.2	491.0	505.4
40°	409.3	411.6	413.1	416.9	422.2	424.4	433.5	445.6	460.8	469.8	481.9
42.5°	389.6	391.2	394.9	398.0	402.5	406.3	412.3	423.7	435.0	448.7	458.5
45°	367.7	371.5	373.8	379.0	381.3	385.1	391.2	400.2	413.9	422.2	433.5
47.5°	348.8	350.3	351.8	358.6	363.2	365.4	371.5	376.8	391.2	398.7	409.3
50°	328.4	328.4	330.6	333.7	339.0	343.5	348.8	354.8	366.2	373.8	384.3
52.5°	309.4	307.2	308.7	310.2	315.5	320.0	325.3	333.7	344.2	348.8	357.9
55°	289.0	285.2	287.5	289.8	291.3	297.3	303.4	308.7	317.0	323.8	332.1
57.5°	267.1	266.3	264.8	265.6	269.3	273.1	277.7	284.5	294.3	299.6	304.1
60°	247.4	242.9	241.4	242.9	245.1	247.4	253.5	259.5	267.8	273.1	278.4
62.5°	227.0	222.4	219.4	217.1	219.4	224.7	228.5	233.0	239.8	245.9	250.4
65°	207.3	200.5	197.5	196.0	195.2	199.0	202.0	208.1	214.1	216.4	221.7
67.5°	185.4	179.3	175.5	173.3	173.3	173.3	176.3	182.3	188.4	189.1	194.4
70°	163.4	156.6	152.8	149.8	148.3	149.8	153.6	154.3	159.6	161.2	164.2
72.5°	140.0	133.9	129.4	125.6	126.3	127.9	127.9	129.4	132.4	136.2	136.2
75°	118.0	109.7	107.4	104.4	102.9	102.9	102.9	105.9	108.2	111.2	110.5
77.5°	93.1	88.5	84.0	82.5	80.2	79.4	81.0	81.0	82.5	84.7	85.5
80°	71.9	66.6	63.6	62.0	59.0	58.3	59.0	59.0	61.3	60.5	61.3
82.5°	49.9	46.2	43.9	41.6	40.1	40.9	40.1	40.1	40.9	40.1	40.1
85°	28.8	28.0	26.5	25.7	25.0	23.5	25.0	24.2	23.5	22.7	24.2
87.5°	13.6	12.9	12.9	11.3	11.3	10.6	11.3	11.3	10.6	10.6	10.6
90°	20.9	19.8	18.7	17.5	16.4	14.8	13.2	11.6	10.0	9.2	8.3
92.5°	20.9	19.8	18.7	17.5	16.4	15.0	13.7	12.3	11.0	10.3	11.3
95°	20.9	19.8	18.7	17.5	16.4	25.1	33.7	42.4	51.1	55.4	55.7
97.5°	20.3	19.8	19.4	18.9	18.5	40.1	61.8	83.4	105.1	115.9	115.2
100°	42.6	76.6	110.5	144.5	178.5	177.6	176.7	175.8	174.9	174.4	174.1
102.5°	241.9	241.4	240.9	240.5	240.0	239.6	239.1	238.7	238.2	238.0	237.5
105°	305.7	305.7	305.7	305.7	305.7	305.7	305.7	305.7	305.7	305.7	305.2
107.5°	374.3	374.1	373.8	373.6	373.4	373.0	372.5	372.1	371.6	371.4	371.4
110°	438.3	439.0	439.7	440.4	441.1	440.7	440.2	439.8	439.3	439.1	439.1

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	503.2	504.1	505.0	505.9	506.8	506.6	506.3	506.1	505.8	505.7	505.4
115°	568.8	569.7	570.6	571.5	572.4	572.2	572.0	571.7	571.5	571.4	570.8
117.5°	631.6	633.0	634.3	635.7	637.1	636.2	635.2	634.3	633.4	632.9	632.9
120°	694.7	695.2	695.6	696.1	696.5	695.8	695.2	694.5	693.8	693.5	693.6
122.5°	753.2	753.7	754.1	754.6	755.0	754.8	754.6	754.3	754.1	754.0	753.4
125°	808.9	809.8	810.7	811.6	812.5	812.5	812.5	812.5	812.5	812.5	811.7
127.5°	861.9	862.4	862.9	863.3	863.8	864.0	864.2	864.5	864.7	864.8	864.2
130°	912.3	913.0	913.7	914.4	915.1	914.9	914.6	914.4	914.1	914.0	913.4
132.5°	961.2	961.2	961.2	961.2	961.2	961.9	962.6	963.3	964.0	964.3	963.6
135°	1006.6	1007.1	1007.5	1008.0	1008.4	1008.9	1009.3	1009.8	1010.3	1010.5	1009.8
137.5°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.9	1052.4	1052.8	1053.3	1053.5	1052.8
140°	1092.3	1091.8	1091.4	1090.9	1090.5	1090.7	1090.9	1091.2	1091.4	1091.5	1091.3
142.5°	1130.5	1130.5	1130.5	1130.5	1130.5	1130.0	1129.6	1129.1	1128.6	1128.4	1128.3
145°	1167.3	1167.1	1166.8	1166.6	1166.4	1166.4	1166.4	1166.4	1166.4	1166.4	1166.2
147.5°	1199.1	1198.9	1198.6	1198.4	1198.2	1198.0	1197.8	1197.5	1197.3	1197.2	1197.2
150°	1229.8	1229.3	1228.8	1228.4	1227.9	1227.5	1227.0	1226.6	1226.1	1225.9	1226.1
152.5°	1256.5	1256.0	1255.5	1255.1	1254.6	1254.2	1253.7	1253.3	1252.8	1252.6	1253.2
155°	1281.0	1280.3	1279.6	1278.9	1278.2	1277.8	1277.3	1276.9	1276.4	1276.2	1276.9
157.5°	1301.5	1300.8	1300.1	1299.4	1298.7	1298.7	1298.7	1298.7	1298.7	1298.7	1299.0
160°	1320.8	1319.9	1319.0	1318.1	1317.2	1317.0	1316.8	1316.5	1316.3	1316.2	1316.9
162.5°	1339.1	1337.7	1336.4	1335.0	1333.6	1333.4	1333.2	1332.9	1332.7	1332.6	1333.3
165°	1353.4	1352.1	1350.7	1349.4	1348.0	1347.8	1347.5	1347.3	1347.0	1346.9	1347.6
167.5°	1365.6	1364.0	1362.4	1360.8	1359.2	1359.0	1358.8	1358.5	1358.3	1358.2	1358.9
170°	1374.8	1373.0	1371.1	1369.3	1367.5	1367.3	1367.0	1366.8	1366.5	1366.4	1367.2
172.5°	1381.0	1379.4	1377.8	1376.2	1374.6	1374.2	1373.7	1373.3	1372.8	1372.6	1373.4
175°	1386.0	1384.2	1382.3	1380.5	1378.7	1378.5	1378.3	1378.0	1377.8	1377.7	1378.4
177.5°	1388.2	1386.6	1385.0	1383.4	1381.8	1381.6	1381.4	1381.1	1380.9	1380.8	1381.5
180°	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9	1383.9

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	891.3	891.3	891.3	891.3
2.5°	870.1	877.6	882.9	892.8
5°	850.4	864.0	876.9	890.5
7.5°	830.7	846.6	867.0	884.4
10°	808.8	829.2	853.4	876.9
12.5°	786.8	811.1	837.5	868.6
15°	760.4	791.4	822.4	855.7
17.5°	736.9	768.7	802.0	843.6
20°	710.4	745.2	781.6	823.9
22.5°	687.0	725.6	763.4	808.0
25°	660.5	698.3	739.9	787.6
27.5°	638.6	673.4	714.2	765.7
30°	612.1	649.9	690.8	742.2
32.5°	587.1	623.4	666.6	717.2
35°	561.4	598.5	637.0	685.5
37.5°	537.2	569.0	607.5	653.7
40°	509.9	544.7	579.5	615.9
42.5°	485.0	516.7	549.3	578.0
45°	457.0	484.2	515.2	538.7
47.5°	431.3	455.5	479.7	497.8
50°	405.5	424.4	442.6	458.5
52.5°	375.3	396.5	406.3	416.1
55°	348.0	360.1	369.2	379.0
57.5°	321.5	326.8	331.4	340.5
60°	286.7	292.8	298.1	304.9
62.5°	256.5	259.5	261.0	267.8
65°	227.7	227.0	230.8	234.5
67.5°	196.7	196.0	199.7	201.3
70°	166.4	165.7	166.4	170.2
72.5°	137.7	137.7	138.5	140.0
75°	111.2	111.2	112.0	113.5
77.5°	84.0	85.5	84.7	87.8
80°	61.3	59.8	61.3	62.8
82.5°	40.1	41.6	41.6	40.1
85°	22.7	22.7	22.7	22.7
87.5°	9.8	9.8	10.6	11.3
90°	6.5	4.6	2.8	1.0
92.5°	13.4	15.4	17.5	19.5
95°	56.4	57.1	57.8	58.5
97.5°	113.9	112.5	111.2	109.8
100°	173.4	172.7	172.0	171.3
102.5°	236.6	235.7	234.8	233.9
105°	304.3	303.4	302.5	301.6
107.5°	371.4	371.4	371.4	371.4
110°	439.1	439.1	439.1	439.1

TEST NUMBER: P1035386

CATALOG NUMBER: S125DIW-B610D1050UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	504.7	504.0	503.4	502.7
115°	569.7	568.6	567.4	566.3
117.5°	632.9	632.9	632.9	632.9
120°	693.8	694.1	694.3	694.5
122.5°	752.3	751.2	750.0	748.9
125°	810.1	808.5	806.9	805.3
127.5°	863.1	862.0	860.8	859.7
130°	912.3	911.2	910.0	908.9
132.5°	962.2	960.9	959.5	958.1
135°	1008.4	1007.1	1005.7	1004.3
137.5°	1051.5	1050.1	1048.8	1047.4
140°	1090.8	1090.3	1089.9	1089.4
142.5°	1128.1	1127.8	1127.6	1127.4
145°	1165.7	1165.2	1164.8	1164.3
147.5°	1197.2	1197.2	1197.2	1197.2
150°	1226.6	1227.0	1227.5	1227.9
152.5°	1254.3	1255.4	1256.6	1257.7
155°	1278.2	1279.6	1280.9	1282.3
157.5°	1299.7	1300.4	1301.1	1301.8
160°	1318.2	1319.6	1320.9	1322.3
162.5°	1334.6	1336.0	1337.3	1338.7
165°	1349.0	1350.3	1351.7	1353.1
167.5°	1360.3	1361.6	1363.0	1364.4
170°	1368.8	1370.4	1372.0	1373.6
172.5°	1375.0	1376.6	1378.2	1379.8
175°	1379.8	1381.1	1382.5	1383.9
177.5°	1382.8	1384.2	1385.5	1386.9
180°	1383.9	1383.9	1383.9	1383.9

(END OF REPORT)