

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035428

Luminaire Tested: S125DIW-B610D1340UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035428
REPORT IS A COMBINATION OF REPORTS P1003823 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D1340UB40-4F0-XX-W2A-A
Description: Define 5 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7841.0 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34
2	86	78	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	24
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5679	5679	5679	5679
5°	5683	6442	5688	4887
10°	5648	7343	5639	4195
15°	5607	7961	5572	3790
20°	5536	8724	5485	3460
25°	5473	9996	5373	3265
30°	5383	10546	5290	3088
35°	5240	8454	5130	2946
40°	5017	5843	4943	2795
45°	4736	4350	4683	2671
50°	4413	3581	4340	2570
55°	4065	3054	4033	2483
60°	3724	2615	3659	2416
65°	3356	2258	3302	2318
70°	2968	1874	2927	2147
75°	2556	1450	2522	1864
80°	2016	980	1945	1371
85°	1292	490	1246	699

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8673 cd/sqm

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.3	1.1
10°-20°	254.1	3.2
20°-30°	412.7	5.3
30°-40°	504.4	6.4
40°-50°	457.5	5.8
50°-60°	364.4	4.6
60°-70°	253.8	3.2
70°-80°	135.2	1.7
80°-90°	36.1	0.5
90°-100°	59.0	0.8
100°-110°	392.1	5.0
110°-120°	706.2	9.0
120°-130°	906.4	11.6
130°-140°	974.9	12.4
140°-150°	915.0	11.7
150°-160°	740.1	9.4
160°-170°	478.7	6.1
170°-180°	165.1	2.1
0°-30°	752.1	9.6
0°-40°	1256.5	16.0
0°-60°	2078.4	26.5
0°-90°	2503.6	31.9
90°-120°	1157.3	14.8
90°-150°	3953.6	50.4
90°-180°	5337.0	68.1
0°-180°	7841.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	886	886	886	886	886	
5°	886	1022	886	776	886	84
15°	851	1277	846	608	851	240
25°	783	1571	769	513	783	361
35°	682	1261	667	439	682	426
45°	536	594	530	365	536	413
55°	377	366	374	298	377	337
65°	233	225	230	231	233	231
75°	113	111	111	142	113	120
85°	23	25	22	35	23	27
90°	1	31	1	31	1	5
95°	73	27	73	27	73	90
105°	379	382	379	382	379	401
115°	711	706	711	706	711	705
125°	1011	1011	1011	1011	1011	903
135°	1261	1256	1261	1256	1261	972
145°	1462	1458	1462	1458	1462	914
155°	1610	1598	1610	1598	1610	742
165°	1699	1690	1699	1690	1699	480
175°	1738	1730	1738	1730	1738	165
180°	1738	1738	1738	1738	1738	

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3
2.5°	887.8	893.1	899.1	903.6	911.1	913.4	917.1	919.4	921.7	923.9	925.4
5°	885.5	898.3	909.6	917.9	932.2	937.5	944.2	952.5	962.3	970.6	975.8
7.5°	879.5	899.8	914.9	931.4	951.0	963.8	970.6	987.9	1003.7	1015.7	1031.5
10°	872.0	896.1	919.4	944.2	972.1	986.4	999.9	1024.0	1045.8	1065.4	1081.2
12.5°	863.7	893.1	920.9	953.3	990.9	1008.2	1017.2	1058.6	1085.7	1096.2	1127.1
15°	850.9	885.5	925.4	965.3	996.9	1017.2	1042.0	1075.1	1102.2	1125.6	1150.4
17.5°	838.9	876.5	917.1	961.5	1007.4	1033.8	1052.6	1081.9	1111.3	1141.4	1164.7
20°	819.3	868.2	909.6	957.0	1011.2	1030.0	1049.6	1084.2	1115.8	1148.1	1177.5
22.5°	803.5	850.2	906.6	951.8	997.6	1016.5	1040.5	1076.6	1114.3	1151.1	1194.0
25°	783.2	835.1	884.0	932.2	979.6	999.9	1021.7	1068.4	1107.5	1154.9	1202.3
27.5°	761.4	814.8	863.7	907.4	951.8	979.6	1002.9	1051.8	1103.7	1155.6	1217.3
30°	738.1	788.5	835.1	878.0	926.9	955.5	978.8	1036.0	1094.0	1160.2	1233.9
32.5°	713.3	760.6	800.5	844.2	896.1	922.4	954.0	1016.5	1084.9	1163.9	1256.5
35°	681.7	726.8	762.2	806.5	858.5	892.3	925.4	995.4	1075.1	1163.2	1269.3
37.5°	650.1	685.4	719.3	766.7	826.9	857.7	892.3	969.1	1060.1	1160.9	1274.5
40°	612.4	647.0	676.4	724.5	787.7	823.1	859.2	939.7	1042.8	1152.6	1255.7
42.5°	574.8	604.2	636.5	686.9	747.9	785.5	823.8	913.4	1020.2	1128.6	1203.8
45°	535.7	558.3	593.6	639.5	704.2	740.3	784.0	881.0	988.6	1084.9	1122.5
47.5°	495.1	517.6	550.7	595.1	659.1	702.0	743.3	840.4	948.7	1023.2	1023.2
50°	455.9	474.0	506.3	550.7	615.4	654.6	696.7	799.8	887.0	942.0	893.1
52.5°	413.8	434.1	461.2	507.9	571.8	607.2	653.1	741.1	823.8	846.4	771.2
55°	376.9	393.5	419.1	463.5	522.9	559.8	598.9	683.2	753.1	751.6	671.1
57.5°	338.6	352.1	379.2	419.8	474.7	507.9	547.0	620.0	677.1	656.8	580.8
60°	303.2	313.0	339.3	372.4	425.1	455.9	493.6	553.0	596.6	568.0	491.3
62.5°	266.3	277.6	298.7	331.0	377.7	402.5	430.4	490.5	518.4	492.8	414.6
65°	233.2	242.3	261.1	288.2	330.3	352.9	376.9	426.6	452.9	416.1	351.4
67.5°	200.1	210.7	224.2	248.3	281.4	302.5	323.5	366.4	378.4	345.3	291.2
70°	169.3	178.3	191.1	208.4	236.2	255.1	270.9	306.2	314.5	283.6	240.8
72.5°	139.2	145.2	155.7	170.0	195.6	206.2	222.7	246.8	257.3	229.5	198.6
75°	112.9	117.4	124.1	134.7	152.0	163.3	176.8	199.4	198.6	179.1	157.2
77.5°	87.3	88.0	95.6	105.3	115.9	125.6	132.4	148.2	149.7	137.7	119.6
80°	62.4	64.7	67.7	75.2	84.3	88.0	96.3	106.1	107.6	98.6	86.5
82.5°	39.9	41.4	43.6	48.2	54.2	58.7	63.2	67.0	70.7	65.5	55.7
85°	22.6	23.3	25.6	27.1	30.1	32.4	36.1	39.9	39.1	35.4	32.4
87.5°	11.3	11.3	11.3	12.8	14.3	14.3	15.8	16.6	17.3	15.8	14.3
90°	1.3	3.6	5.9	8.2	10.5	11.6	12.6	14.6	16.6	18.6	20.6
92.5°	24.5	21.9	19.3	16.8	14.2	12.9	13.8	15.5	17.2	18.9	20.6
95°	73.4	72.6	71.7	70.9	70.0	69.6	64.2	53.3	42.4	31.5	20.6
97.5°	137.8	139.5	141.2	142.9	144.6	145.5	131.9	104.7	77.6	50.4	23.2
100°	215.1	216.0	216.8	217.7	218.6	219.0	219.6	220.7	221.8	223.0	224.1
102.5°	293.7	294.8	296.0	297.1	298.2	298.8	299.1	299.7	300.2	300.8	301.4
105°	378.7	379.8	381.0	382.1	383.2	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	466.3	466.3	466.3	466.3	466.3	466.3	466.6	467.1	467.7	468.2	468.8
110°	551.3	551.3	551.3	551.3	551.3	551.3	551.6	552.2	552.7	553.3	553.9

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	631.1	632.0	632.8	633.7	634.6	635.0	635.1	635.4	635.7	636.0	636.3
115°	711.0	712.4	713.8	715.3	716.7	717.4	717.5	717.8	718.1	718.4	718.7
117.5°	794.7	794.7	794.7	794.7	794.7	794.7	795.3	796.4	797.6	798.7	799.9
120°	872.0	871.7	871.4	871.1	870.8	870.7	871.1	872.0	872.9	873.7	874.6
122.5°	940.3	941.7	943.1	944.6	946.0	946.7	946.8	947.1	947.4	947.7	948.0
125°	1011.1	1013.1	1015.1	1017.1	1019.1	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1
127.5°	1079.4	1080.8	1082.2	1083.7	1085.1	1085.8	1085.7	1085.4	1085.1	1084.8	1084.5
130°	1141.2	1142.6	1144.0	1145.5	1146.9	1147.6	1147.7	1148.0	1148.3	1148.6	1148.9
132.5°	1203.0	1204.7	1206.5	1208.2	1209.9	1210.8	1210.4	1209.5	1208.6	1207.8	1206.9
135°	1261.0	1262.7	1264.4	1266.1	1267.8	1268.7	1268.4	1267.8	1267.3	1266.7	1266.1
137.5°	1315.1	1316.8	1318.5	1320.2	1321.9	1322.8	1322.5	1321.9	1321.4	1320.8	1320.2
140°	1367.9	1368.5	1369.1	1369.6	1370.2	1370.5	1370.4	1370.1	1369.8	1369.5	1369.2
142.5°	1415.6	1415.9	1416.1	1416.4	1416.7	1416.8	1417.1	1417.7	1418.2	1418.8	1419.4
145°	1461.9	1462.5	1463.1	1463.6	1464.2	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5
147.5°	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.2	1503.5	1503.8	1504.1	1504.4
150°	1541.8	1541.2	1540.6	1540.1	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8
152.5°	1579.1	1577.7	1576.3	1574.8	1573.4	1572.7	1573.0	1573.6	1574.1	1574.7	1575.3
155°	1610.0	1608.3	1606.6	1604.9	1603.2	1602.3	1602.6	1603.2	1603.7	1604.3	1604.9
157.5°	1634.5	1633.7	1632.8	1632.0	1631.1	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7
160°	1660.3	1658.6	1656.9	1655.2	1653.5	1652.6	1652.7	1653.0	1653.3	1653.5	1653.8
162.5°	1680.9	1679.2	1677.5	1675.8	1674.1	1673.2	1673.3	1673.6	1673.9	1674.1	1674.4
165°	1698.9	1697.2	1695.5	1693.8	1692.1	1691.2	1691.3	1691.6	1691.9	1692.2	1692.5
167.5°	1713.1	1711.4	1709.7	1708.0	1706.3	1705.4	1705.5	1705.8	1706.1	1706.3	1706.6
170°	1724.7	1722.7	1720.7	1718.7	1716.7	1715.7	1715.8	1716.1	1716.4	1716.7	1717.0
172.5°	1732.4	1730.4	1728.4	1726.4	1724.4	1723.4	1723.7	1724.3	1724.8	1725.4	1726.0
175°	1737.6	1735.9	1734.1	1732.4	1730.7	1729.8	1729.9	1730.2	1730.5	1730.8	1731.1
177.5°	1741.4	1739.7	1738.0	1736.3	1734.6	1733.7	1733.8	1734.1	1734.4	1734.7	1735.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3
2.5°	926.9	932.2	936.7	940.5	943.5	948.0	945.0	945.7	947.2	950.2	950.2
5°	987.1	995.4	999.9	1015.0	1018.7	1018.0	1015.7	1027.7	1027.0	1022.5	1021.7
7.5°	1045.8	1060.1	1072.9	1084.9	1088.7	1098.5	1100.7	1106.0	1104.5	1112.0	1108.2
10°	1099.2	1121.8	1133.8	1151.9	1156.4	1160.9	1166.9	1169.9	1176.7	1176.0	1176.0
12.5°	1140.6	1167.7	1183.5	1188.0	1205.3	1210.6	1215.8	1225.6	1223.4	1224.1	1228.6
15°	1173.0	1199.3	1212.8	1233.9	1245.9	1252.0	1261.0	1271.5	1270.0	1276.8	1275.3
17.5°	1197.0	1221.9	1246.7	1278.3	1279.0	1294.8	1315.9	1320.4	1330.2	1323.4	1323.4
20°	1216.6	1249.7	1285.1	1325.7	1330.2	1340.0	1365.6	1382.9	1394.1	1390.4	1392.6
22.5°	1237.7	1285.1	1326.4	1367.1	1388.9	1406.2	1431.0	1458.1	1467.9	1473.9	1472.4
25°	1264.7	1314.4	1375.3	1431.8	1454.3	1487.4	1520.5	1546.9	1554.4	1571.0	1555.9
27.5°	1292.6	1362.5	1438.5	1504.7	1533.3	1560.4	1600.3	1619.9	1629.6	1637.2	1631.9
30°	1315.9	1412.2	1495.0	1555.9	1576.2	1592.0	1614.6	1619.1	1615.3	1621.4	1628.9
32.5°	1352.0	1446.1	1516.0	1545.4	1543.1	1542.4	1525.1	1501.0	1495.7	1481.4	1501.0
35°	1371.6	1446.8	1473.9	1434.8	1419.0	1390.4	1335.5	1299.3	1267.7	1261.0	1262.5
37.5°	1360.3	1389.6	1357.3	1254.2	1228.6	1185.0	1112.0	1060.8	1037.5	1019.5	1042.8
40°	1299.3	1267.0	1178.2	1052.6	1015.7	974.3	905.9	878.0	844.9	838.1	869.0
42.5°	1198.5	1100.0	974.3	877.3	838.9	815.6	758.4	732.1	708.7	698.2	715.5
45°	1061.6	942.0	815.6	735.8	703.5	675.6	641.8	613.9	598.9	594.4	608.7
47.5°	920.2	793.8	692.9	633.5	599.6	578.6	547.0	531.2	519.1	520.6	522.9
50°	784.7	669.6	592.1	532.7	516.1	499.6	478.5	465.0	458.9	461.2	459.7
52.5°	668.1	574.8	509.4	463.5	455.9	440.1	422.8	411.5	409.3	410.0	412.3
55°	565.8	492.8	440.9	407.8	399.5	388.2	377.7	370.2	364.1	366.4	365.7
57.5°	488.3	424.3	384.5	357.4	351.4	344.6	334.8	331.0	328.8	324.3	328.0
60°	419.8	367.9	333.3	316.7	311.5	307.0	296.4	291.9	290.4	288.2	294.2
62.5°	355.1	318.3	291.9	276.9	271.6	267.1	261.8	258.1	258.8	255.8	258.8
65°	304.0	273.9	255.1	241.5	234.7	231.7	231.0	225.0	224.2	225.0	225.7
67.5°	256.6	231.0	216.7	208.4	203.1	200.1	197.9	194.1	197.1	194.9	196.4
70°	213.7	196.4	181.3	173.0	170.8	171.5	167.8	166.3	167.0	165.5	167.0
72.5°	172.3	158.0	152.0	146.0	143.0	142.2	139.9	137.7	139.9	139.2	139.2
75°	137.7	127.2	120.4	116.6	116.6	115.1	111.4	111.4	111.4	110.6	111.4
77.5°	106.1	97.1	94.0	90.3	90.3	88.0	87.3	87.3	85.8	88.0	86.5
80°	79.0	72.2	67.7	65.5	65.5	64.7	63.2	62.4	63.2	62.4	62.4
82.5°	51.2	48.2	45.9	43.6	42.9	43.6	42.9	41.4	42.1	41.4	42.9
85°	29.3	26.3	26.3	24.8	25.6	24.1	24.8	23.3	22.6	24.8	23.3
87.5°	12.8	12.0	12.0	10.5	10.5	10.5	9.8	10.5	9.8	9.0	9.8
90°	22.0	23.4	24.9	26.3	27.0	27.4	28.3	29.2	30.0	30.9	30.0
92.5°	22.0	23.4	24.9	26.3	27.0	27.1	27.4	27.7	28.0	28.3	28.0
95°	22.0	23.4	24.9	26.3	27.0	27.0	27.0	27.0	27.0	27.0	27.0
97.5°	23.8	24.4	24.9	25.5	25.8	25.9	26.2	26.5	26.7	27.0	26.7
100°	181.5	138.8	96.2	53.5	32.2	31.6	30.5	29.3	28.2	27.0	28.2
102.5°	302.0	302.6	303.1	303.7	304.0	292.0	267.9	243.9	219.8	195.8	219.8
105°	383.8	383.8	383.8	383.8	383.8	383.7	383.4	383.1	382.8	382.5	382.8
107.5°	469.1	469.4	469.7	470.0	470.1	469.5	468.4	467.3	466.1	465.0	466.1
110°	553.0	552.2	551.3	550.4	550.0	550.1	550.4	550.7	551.0	551.3	551.0

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	635.1	634.0	632.8	631.7	631.1	630.8	630.3	629.7	629.2	628.6	629.2
115°	717.6	716.4	715.3	714.2	713.6	712.7	711.0	709.3	707.5	705.8	707.5
117.5°	798.2	796.4	794.7	793.0	792.1	791.8	791.3	790.7	790.2	789.6	790.2
120°	874.0	873.4	872.9	872.3	872.0	871.3	869.9	868.4	867.0	865.6	867.0
122.5°	947.4	946.8	946.3	945.7	945.4	944.5	942.8	941.1	939.4	937.7	939.4
125°	1019.0	1017.8	1016.7	1015.6	1015.0	1014.6	1013.7	1012.8	1012.0	1011.1	1012.0
127.5°	1083.9	1083.4	1082.8	1082.3	1082.0	1080.8	1078.5	1076.2	1073.9	1071.6	1073.9
130°	1148.1	1147.2	1146.4	1145.5	1145.1	1144.4	1142.9	1141.5	1140.0	1138.6	1140.0
132.5°	1206.9	1206.9	1206.9	1206.9	1206.9	1206.2	1204.8	1203.3	1201.9	1200.5	1201.9
135°	1265.5	1265.0	1264.4	1263.9	1263.6	1262.7	1261.0	1259.3	1257.5	1255.8	1257.5
137.5°	1320.2	1320.2	1320.2	1320.2	1320.2	1319.5	1318.1	1316.6	1315.2	1313.8	1315.2
140°	1369.8	1370.4	1370.9	1371.5	1371.8	1370.9	1369.2	1367.5	1365.7	1364.0	1365.7
142.5°	1419.4	1419.4	1419.4	1419.4	1419.4	1418.5	1416.8	1415.1	1413.4	1411.7	1413.4
145°	1464.8	1465.1	1465.4	1465.7	1465.8	1464.9	1463.2	1461.5	1459.8	1458.1	1459.8
147.5°	1504.7	1505.0	1505.3	1505.6	1505.7	1504.7	1502.7	1500.7	1498.7	1496.7	1498.7
150°	1542.4	1543.0	1543.5	1544.1	1544.4	1543.3	1541.0	1538.7	1536.4	1534.1	1536.4
152.5°	1575.9	1576.4	1577.0	1577.5	1577.8	1576.8	1574.8	1572.8	1570.8	1568.8	1570.8
155°	1605.8	1606.6	1607.5	1608.4	1608.8	1607.7	1605.4	1603.1	1600.8	1598.5	1600.8
157.5°	1631.5	1632.4	1633.2	1634.1	1634.5	1633.4	1631.1	1628.8	1626.5	1624.2	1626.5
160°	1655.0	1656.1	1657.3	1658.4	1659.0	1657.9	1655.6	1653.3	1651.0	1648.7	1651.0
162.5°	1676.1	1677.9	1679.6	1681.3	1682.2	1680.9	1678.3	1675.8	1673.2	1670.6	1673.2
165°	1694.2	1695.9	1697.6	1699.3	1700.2	1699.1	1696.8	1694.5	1692.2	1689.9	1692.2
167.5°	1708.6	1710.6	1712.7	1714.7	1715.7	1714.4	1711.8	1709.3	1706.7	1704.1	1706.7
170°	1719.3	1721.6	1723.9	1726.2	1727.3	1726.0	1723.4	1720.9	1718.3	1715.7	1718.3
172.5°	1728.0	1730.0	1732.0	1734.0	1735.0	1733.7	1731.1	1728.6	1726.0	1723.4	1726.0
175°	1733.4	1735.7	1738.0	1740.3	1741.4	1740.1	1737.5	1735.0	1732.4	1729.8	1732.4
177.5°	1737.0	1739.0	1741.0	1743.0	1744.0	1742.9	1740.6	1738.3	1736.0	1733.7	1736.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3
2.5°	948.7	943.5	945.0	943.5	939.7	937.5	931.4	923.9	920.9	917.1	914.9
5°	1024.7	1021.0	1020.2	1014.2	1012.7	1003.7	988.6	981.1	972.1	963.0	954.0
7.5°	1107.5	1103.0	1087.9	1085.7	1087.2	1075.9	1056.3	1041.3	1022.5	1009.7	992.4
10°	1176.0	1166.9	1154.1	1154.9	1149.6	1134.6	1115.0	1099.2	1072.1	1055.6	1030.8
12.5°	1217.3	1209.8	1208.3	1200.8	1196.3	1176.7	1153.4	1133.1	1112.8	1090.2	1071.4
15°	1267.7	1258.0	1251.2	1240.7	1237.7	1217.3	1191.8	1168.4	1145.1	1124.0	1084.2
17.5°	1323.4	1312.9	1287.3	1285.1	1267.0	1247.4	1222.6	1188.0	1163.2	1133.1	1103.7
20°	1386.6	1371.6	1338.5	1330.2	1315.9	1283.5	1249.7	1211.3	1171.4	1140.6	1106.0
22.5°	1457.3	1431.0	1406.9	1380.6	1370.1	1330.2	1283.5	1236.9	1188.8	1146.6	1105.2
25°	1549.1	1514.5	1480.7	1454.3	1436.3	1384.4	1321.9	1260.2	1204.6	1149.6	1095.5
27.5°	1621.4	1591.3	1554.4	1519.8	1496.5	1434.8	1363.3	1283.5	1214.3	1147.4	1089.4
30°	1626.6	1617.6	1595.0	1576.2	1550.6	1484.4	1405.4	1315.1	1229.4	1148.1	1077.4
32.5°	1528.1	1546.1	1555.9	1558.9	1553.7	1515.3	1443.1	1343.7	1242.9	1141.4	1066.9
35°	1315.9	1364.1	1423.5	1446.1	1467.9	1488.2	1450.6	1364.1	1247.4	1139.8	1050.3
37.5°	1083.4	1127.1	1225.6	1270.8	1296.3	1376.8	1407.7	1361.0	1256.5	1141.4	1034.5
40°	874.3	943.5	1014.2	1075.1	1115.0	1205.3	1300.9	1311.4	1243.7	1127.1	1014.2
42.5°	735.8	776.4	829.9	886.3	921.7	1028.5	1157.9	1233.9	1203.8	1103.7	989.4
45°	626.7	656.8	707.2	726.0	771.2	873.5	1010.4	1120.3	1135.3	1066.9	960.8
47.5°	537.9	563.5	595.9	619.2	655.3	732.1	847.9	969.1	1041.3	1016.5	920.9
50°	474.0	495.1	522.1	535.7	559.0	628.2	715.5	835.9	932.9	941.2	869.0
52.5°	420.6	432.6	453.7	468.7	487.5	529.7	608.7	708.0	817.1	862.2	805.0
55°	373.9	383.7	402.5	412.3	422.1	458.2	519.9	610.2	712.5	771.9	739.6
57.5°	331.8	340.1	355.9	364.9	370.2	404.8	452.2	522.9	614.7	686.9	668.9
60°	297.2	304.7	313.7	320.5	326.5	355.1	388.2	445.4	527.4	597.4	592.9
62.5°	260.3	267.1	276.9	283.6	288.9	307.0	334.8	378.4	448.4	513.1	525.9
65°	228.0	233.2	240.0	243.0	249.8	263.3	285.9	325.0	382.2	440.1	449.2
67.5°	198.6	200.1	204.6	211.4	212.9	225.0	245.3	274.6	319.0	366.4	380.7
70°	167.0	169.3	173.0	178.3	181.3	188.8	206.2	225.7	264.1	305.5	316.0
72.5°	139.2	142.2	143.7	146.7	148.2	160.3	167.8	187.3	213.7	248.3	259.6
75°	112.9	115.9	116.6	118.1	119.6	124.9	135.4	147.5	169.3	191.9	206.9
77.5°	89.5	88.8	90.3	92.5	91.8	96.3	103.1	113.6	127.9	146.7	156.5
80°	63.2	63.2	65.5	67.7	67.0	71.5	73.7	81.3	93.3	105.3	109.1
82.5°	42.1	42.1	44.4	44.4	45.9	46.6	49.7	53.4	63.2	69.2	71.5
85°	24.1	24.1	24.8	24.8	24.8	26.3	28.6	30.1	33.1	36.9	38.4
87.5°	9.8	10.5	10.5	10.5	10.5	12.0	12.0	13.5	14.3	15.8	15.8
90°	29.2	28.3	27.4	27.0	26.3	24.9	23.4	22.0	20.6	18.6	16.6
92.5°	27.7	27.4	27.1	27.0	26.3	24.9	23.4	22.0	20.6	18.9	17.2
95°	27.0	27.0	27.0	27.0	26.3	24.9	23.4	22.0	20.6	31.5	42.4
97.5°	26.5	26.2	25.9	25.8	25.5	24.9	24.4	23.8	23.2	50.4	77.6
100°	29.3	30.5	31.6	32.2	53.5	96.2	138.8	181.5	224.1	223.0	221.8
102.5°	243.9	267.9	292.0	304.0	303.7	303.1	302.6	302.0	301.4	300.8	300.2
105°	383.1	383.4	383.7	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	467.3	468.4	469.5	470.1	470.0	469.7	469.4	469.1	468.8	468.2	467.7
110°	550.7	550.4	550.1	550.0	550.4	551.3	552.2	553.0	553.9	553.3	552.7

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	629.7	630.3	630.8	631.1	631.7	632.8	634.0	635.1	636.3	636.0	635.7
115°	709.3	711.0	712.7	713.6	714.2	715.3	716.4	717.6	718.7	718.4	718.1
117.5°	790.7	791.3	791.8	792.1	793.0	794.7	796.4	798.2	799.9	798.7	797.6
120°	868.4	869.9	871.3	872.0	872.3	872.9	873.4	874.0	874.6	873.7	872.9
122.5°	941.1	942.8	944.5	945.4	945.7	946.3	946.8	947.4	948.0	947.7	947.4
125°	1012.8	1013.7	1014.6	1015.0	1015.6	1016.7	1017.8	1019.0	1020.1	1020.1	1020.1
127.5°	1076.2	1078.5	1080.8	1082.0	1082.3	1082.8	1083.4	1083.9	1084.5	1084.8	1085.1
130°	1141.5	1142.9	1144.4	1145.1	1145.5	1146.4	1147.2	1148.1	1148.9	1148.6	1148.3
132.5°	1203.3	1204.8	1206.2	1206.9	1206.9	1206.9	1206.9	1206.9	1206.9	1207.8	1208.6
135°	1259.3	1261.0	1262.7	1263.6	1263.9	1264.4	1265.0	1265.5	1266.1	1266.7	1267.3
137.5°	1316.6	1318.1	1319.5	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.8	1321.4
140°	1367.5	1369.2	1370.9	1371.8	1371.5	1370.9	1370.4	1369.8	1369.2	1369.5	1369.8
142.5°	1415.1	1416.8	1418.5	1419.4	1419.4	1419.4	1419.4	1419.4	1419.4	1418.8	1418.2
145°	1461.5	1463.2	1464.9	1465.8	1465.7	1465.4	1465.1	1464.8	1464.5	1464.5	1464.5
147.5°	1500.7	1502.7	1504.7	1505.7	1505.6	1505.3	1505.0	1504.7	1504.4	1504.1	1503.8
150°	1538.7	1541.0	1543.3	1544.4	1544.1	1543.5	1543.0	1542.4	1541.8	1541.2	1540.6
152.5°	1572.8	1574.8	1576.8	1577.8	1577.5	1577.0	1576.4	1575.9	1575.3	1574.7	1574.1
155°	1603.1	1605.4	1607.7	1608.8	1608.4	1607.5	1606.6	1605.8	1604.9	1604.3	1603.7
157.5°	1628.8	1631.1	1633.4	1634.5	1634.1	1633.2	1632.4	1631.5	1630.7	1630.7	1630.7
160°	1653.3	1655.6	1657.9	1659.0	1658.4	1657.3	1656.1	1655.0	1653.8	1653.5	1653.3
162.5°	1675.8	1678.3	1680.9	1682.2	1681.3	1679.6	1677.9	1676.1	1674.4	1674.1	1673.9
165°	1694.5	1696.8	1699.1	1700.2	1699.3	1697.6	1695.9	1694.2	1692.5	1692.2	1691.9
167.5°	1709.3	1711.8	1714.4	1715.7	1714.7	1712.7	1710.6	1708.6	1706.6	1706.3	1706.1
170°	1720.9	1723.4	1726.0	1727.3	1726.2	1723.9	1721.6	1719.3	1717.0	1716.7	1716.4
172.5°	1728.6	1731.1	1733.7	1735.0	1734.0	1732.0	1730.0	1728.0	1726.0	1725.4	1724.8
175°	1735.0	1737.5	1740.1	1741.4	1740.3	1738.0	1735.7	1733.4	1731.1	1730.8	1730.5
177.5°	1738.3	1740.6	1742.9	1744.0	1743.0	1741.0	1739.0	1737.0	1735.0	1734.7	1734.4
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3
2.5°	911.9	908.1	903.6	903.6	898.3	896.1	891.6	890.1	886.3	880.3	875.8
5°	944.2	934.4	928.4	923.2	911.9	903.6	895.3	886.3	877.3	866.7	854.7
7.5°	975.8	957.8	949.5	940.5	923.9	906.6	890.1	878.0	866.0	849.4	834.4
10°	1008.9	986.4	971.3	959.3	933.7	911.9	887.8	870.5	851.7	830.6	811.1
12.5°	1036.8	1007.4	994.6	972.1	942.7	916.4	886.3	860.0	835.1	810.3	786.2
15°	1060.1	1032.3	1000.7	991.6	951.0	913.4	879.5	845.7	814.8	790.0	762.2
17.5°	1067.6	1032.3	1016.5	994.6	946.5	907.4	864.5	827.6	798.3	761.4	739.6
20°	1069.9	1036.0	1014.2	993.9	951.0	899.1	857.0	811.8	776.4	739.6	705.0
22.5°	1063.9	1024.0	1002.9	983.4	935.2	890.8	841.9	792.2	750.9	717.0	682.4
25°	1052.6	1005.9	985.6	964.5	918.6	869.7	816.3	768.9	730.6	689.9	656.1
27.5°	1037.5	984.1	960.8	939.0	893.8	847.9	797.5	748.6	705.7	662.8	631.2
30°	1018.7	957.0	936.0	907.4	863.7	820.1	774.2	725.3	677.1	636.5	601.9
32.5°	994.6	929.9	902.1	875.0	827.6	787.7	744.1	698.2	651.6	611.7	575.6
35°	972.8	899.1	868.2	841.2	788.5	746.4	710.2	667.4	626.0	584.6	552.2
37.5°	943.5	868.2	831.4	803.5	750.1	707.2	673.4	640.3	596.6	556.8	526.7
40°	912.6	829.9	795.3	767.4	711.7	665.1	632.7	603.4	568.0	531.2	499.6
42.5°	884.8	793.0	756.1	722.3	665.9	624.5	591.4	568.8	536.4	503.3	474.7
45°	849.4	753.9	714.0	678.6	624.5	579.3	547.7	529.7	505.6	473.2	448.4
47.5°	813.3	711.7	670.4	635.8	577.1	537.2	506.3	489.0	472.5	446.9	422.1
50°	765.9	667.4	629.7	589.9	531.9	491.3	465.7	448.4	435.6	417.6	396.5
52.5°	714.0	621.5	580.8	546.2	489.0	452.2	422.8	413.1	400.3	386.7	368.7
55°	659.1	571.8	532.7	498.8	446.2	408.5	384.5	373.9	364.1	353.6	341.6
57.5°	604.2	519.9	483.0	452.9	404.0	367.9	348.3	334.1	327.3	321.3	311.5
60°	535.7	464.2	435.6	408.5	360.4	327.3	308.5	297.9	291.9	288.9	284.4
62.5°	475.5	416.8	385.2	358.9	320.5	291.2	273.1	264.8	259.6	258.1	252.8
65°	411.5	361.1	336.3	313.7	280.6	254.3	239.3	229.5	225.7	225.0	225.0
67.5°	351.4	310.7	285.9	270.1	241.5	218.2	203.9	200.1	197.9	194.9	194.1
70°	294.9	262.6	240.8	227.2	201.6	184.3	173.0	167.0	167.0	164.8	163.3
72.5°	245.3	212.9	198.6	187.3	166.3	151.2	143.0	141.4	136.2	135.4	135.4
75°	191.9	167.8	158.0	148.2	132.4	121.9	115.1	111.4	108.3	108.3	109.1
77.5°	144.5	127.9	118.9	111.4	100.1	93.3	88.0	86.5	83.5	83.5	83.5
80°	102.3	93.3	86.5	80.5	72.2	66.2	63.2	60.2	60.2	59.4	60.2
82.5°	66.2	58.7	54.9	54.2	46.6	44.4	40.6	41.4	39.1	38.4	39.9
85°	38.4	34.6	30.1	28.6	25.6	22.6	21.1	21.8	21.1	20.3	21.1
87.5°	15.0	12.8	12.0	12.0	9.8	9.0	8.3	9.0	7.5	7.5	8.3
90°	14.6	12.6	11.6	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	15.5	13.8	12.9	14.2	16.8	19.3	21.9	24.5	21.9	19.3	16.8
95°	53.3	64.2	69.6	70.0	70.9	71.7	72.6	73.4	72.6	71.7	70.9
97.5°	104.7	131.9	145.5	144.6	142.9	141.2	139.5	137.8	139.5	141.2	142.9
100°	220.7	219.6	219.0	218.6	217.7	216.8	216.0	215.1	216.0	216.8	217.7
102.5°	299.7	299.1	298.8	298.2	297.1	296.0	294.8	293.7	294.8	296.0	297.1
105°	383.8	383.8	383.8	383.2	382.1	381.0	379.8	378.7	379.8	381.0	382.1
107.5°	467.1	466.6	466.3	466.3	466.3	466.3	466.3	466.3	466.3	466.3	466.3
110°	552.2	551.6	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	635.4	635.1	635.0	634.6	633.7	632.8	632.0	631.1	632.0	632.8	633.7
115°	717.8	717.5	717.4	716.7	715.3	713.8	712.4	711.0	712.4	713.8	715.3
117.5°	796.4	795.3	794.7	794.7	794.7	794.7	794.7	794.7	794.7	794.7	794.7
120°	872.0	871.1	870.7	870.8	871.1	871.4	871.7	872.0	871.7	871.4	871.1
122.5°	947.1	946.8	946.7	946.0	944.6	943.1	941.7	940.3	941.7	943.1	944.6
125°	1020.1	1020.1	1020.1	1019.1	1017.1	1015.1	1013.1	1011.1	1013.1	1015.1	1017.1
127.5°	1085.4	1085.7	1085.8	1085.1	1083.7	1082.2	1080.8	1079.4	1080.8	1082.2	1083.7
130°	1148.0	1147.7	1147.6	1146.9	1145.5	1144.0	1142.6	1141.2	1142.6	1144.0	1145.5
132.5°	1209.5	1210.4	1210.8	1209.9	1208.2	1206.5	1204.7	1203.0	1204.7	1206.5	1208.2
135°	1267.8	1268.4	1268.7	1267.8	1266.1	1264.4	1262.7	1261.0	1262.7	1264.4	1266.1
137.5°	1321.9	1322.5	1322.8	1321.9	1320.2	1318.5	1316.8	1315.1	1316.8	1318.5	1320.2
140°	1370.1	1370.4	1370.5	1370.2	1369.6	1369.1	1368.5	1367.9	1368.5	1369.1	1369.6
142.5°	1417.7	1417.1	1416.8	1416.7	1416.4	1416.1	1415.9	1415.6	1415.9	1416.1	1416.4
145°	1464.5	1464.5	1464.5	1464.2	1463.6	1463.1	1462.5	1461.9	1462.5	1463.1	1463.6
147.5°	1503.5	1503.2	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1
150°	1540.1	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8	1541.2	1540.6	1540.1
152.5°	1573.6	1573.0	1572.7	1573.4	1574.8	1576.3	1577.7	1579.1	1577.7	1576.3	1574.8
155°	1603.2	1602.6	1602.3	1603.2	1604.9	1606.6	1608.3	1610.0	1608.3	1606.6	1604.9
157.5°	1630.7	1630.7	1630.7	1631.1	1632.0	1632.8	1633.7	1634.5	1633.7	1632.8	1632.0
160°	1653.0	1652.7	1652.6	1653.5	1655.2	1656.9	1658.6	1660.3	1658.6	1656.9	1655.2
162.5°	1673.6	1673.3	1673.2	1674.1	1675.8	1677.5	1679.2	1680.9	1679.2	1677.5	1675.8
165°	1691.6	1691.3	1691.2	1692.1	1693.8	1695.5	1697.2	1698.9	1697.2	1695.5	1693.8
167.5°	1705.8	1705.5	1705.4	1706.3	1708.0	1709.7	1711.4	1713.1	1711.4	1709.7	1708.0
170°	1716.1	1715.8	1715.7	1716.7	1718.7	1720.7	1722.7	1724.7	1722.7	1720.7	1718.7
172.5°	1724.3	1723.7	1723.4	1724.4	1726.4	1728.4	1730.4	1732.4	1730.4	1728.4	1726.4
175°	1730.2	1729.9	1729.8	1730.7	1732.4	1734.1	1735.9	1737.6	1735.9	1734.1	1732.4
177.5°	1734.1	1733.8	1733.7	1734.6	1736.3	1738.0	1739.7	1741.4	1739.7	1738.0	1736.3
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3
2.5°	874.3	872.8	869.0	866.7	859.2	850.2	847.2	839.6	842.7	837.4	837.4
5°	850.9	844.2	839.6	832.9	818.6	808.8	798.3	793.0	790.0	786.2	783.2
7.5°	820.8	815.6	811.1	798.3	782.5	768.9	756.1	750.9	741.1	734.3	731.3
10°	794.5	787.0	776.4	761.4	744.9	727.5	716.3	705.0	697.5	693.7	685.4
12.5°	767.4	758.4	747.1	725.3	707.2	696.7	676.4	665.9	662.1	659.1	649.3
15°	739.6	729.8	716.3	695.9	680.1	655.3	643.3	635.0	626.0	625.2	617.7
17.5°	714.8	702.7	691.4	666.6	647.0	625.2	618.5	609.4	601.1	592.1	588.4
20°	683.2	671.9	663.6	636.5	614.7	601.1	589.9	582.3	577.1	568.0	566.5
22.5°	654.6	642.5	631.2	610.9	592.1	574.8	561.3	553.0	550.7	547.0	540.2
25°	626.7	614.7	601.1	582.3	562.8	550.7	538.7	533.4	528.9	522.9	517.6
27.5°	603.4	592.1	579.3	556.0	539.5	530.4	517.6	511.6	505.6	502.6	500.3
30°	575.6	562.8	553.0	534.9	516.9	504.8	495.8	490.5	485.3	482.3	480.8
32.5°	548.5	536.4	529.7	510.1	495.8	481.5	474.7	471.0	468.0	465.0	462.0
35°	526.7	514.6	504.1	486.0	471.7	462.0	456.7	450.7	448.4	445.4	445.4
37.5°	499.6	490.5	480.0	462.7	449.9	442.4	437.9	430.4	429.6	428.1	425.8
40°	476.3	467.2	457.4	442.4	431.1	422.1	416.1	412.3	410.0	408.5	407.0
42.5°	451.4	441.6	437.1	419.8	410.0	401.0	398.0	394.2	393.5	390.5	386.7
45°	427.3	419.1	410.0	397.3	389.0	381.5	376.9	373.9	370.2	369.4	367.2
47.5°	406.3	396.5	388.2	376.2	367.2	361.1	357.4	353.6	350.6	348.3	346.1
50°	379.2	371.7	364.9	352.1	344.6	338.6	333.3	330.3	327.3	327.3	327.3
52.5°	352.9	346.1	340.1	331.0	322.0	316.7	310.7	308.5	307.0	304.7	307.0
55°	327.3	320.5	314.5	307.7	297.2	292.7	286.7	284.4	285.1	285.1	287.4
57.5°	300.2	294.9	291.2	282.9	273.1	268.6	264.8	262.6	262.6	265.6	266.3
60°	273.9	268.6	261.8	254.3	248.3	243.0	240.8	241.5	241.5	243.0	246.8
62.5°	244.5	241.5	237.8	227.2	223.5	219.7	216.7	218.9	218.2	222.0	227.2
65°	217.4	214.4	209.2	203.9	199.4	195.6	194.9	195.6	197.1	200.9	206.9
67.5°	187.3	187.3	182.8	178.3	174.6	170.8	171.5	172.3	173.8	178.3	187.3
70°	162.5	159.5	155.0	152.0	149.0	147.5	146.0	149.0	153.5	156.5	163.3
72.5°	135.4	133.2	129.4	126.4	125.6	124.1	123.4	124.9	129.4	134.7	142.2
75°	106.8	107.6	105.3	103.1	103.1	100.8	102.3	102.3	106.8	112.1	118.1
77.5°	82.8	82.0	81.3	79.8	79.0	79.0	79.0	80.5	85.0	88.0	94.0
80°	58.7	59.4	57.2	57.9	57.2	57.9	57.9	60.9	63.2	67.0	71.5
82.5°	39.1	39.1	37.6	38.4	38.4	38.4	39.1	40.6	43.6	46.6	49.7
85°	21.8	22.6	21.1	22.6	22.6	22.6	23.3	24.1	26.3	27.1	30.1
87.5°	8.3	9.8	9.8	8.3	9.0	9.8	10.5	9.8	11.3	12.8	13.5
90°	10.5	11.6	12.6	14.6	16.6	18.6	20.6	22.0	23.4	24.9	26.3
92.5°	14.2	12.9	13.8	15.5	17.2	18.9	20.6	22.0	23.4	24.9	26.3
95°	70.0	69.6	64.2	53.3	42.4	31.5	20.6	22.0	23.4	24.9	26.3
97.5°	144.6	145.5	131.9	104.7	77.6	50.4	23.2	23.8	24.4	24.9	25.5
100°	218.6	219.0	219.6	220.7	221.8	223.0	224.1	181.5	138.8	96.2	53.5
102.5°	298.2	298.8	299.1	299.7	300.2	300.8	301.4	302.0	302.6	303.1	303.7
105°	383.2	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	466.3	466.3	466.6	467.1	467.7	468.2	468.8	469.1	469.4	469.7	470.0
110°	551.3	551.3	551.6	552.2	552.7	553.3	553.9	553.0	552.2	551.3	550.4

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	634.6	635.0	635.1	635.4	635.7	636.0	636.3	635.1	634.0	632.8	631.7
115°	716.7	717.4	717.5	717.8	718.1	718.4	718.7	717.6	716.4	715.3	714.2
117.5°	794.7	794.7	795.3	796.4	797.6	798.7	799.9	798.2	796.4	794.7	793.0
120°	870.8	870.7	871.1	872.0	872.9	873.7	874.6	874.0	873.4	872.9	872.3
122.5°	946.0	946.7	946.8	947.1	947.4	947.7	948.0	947.4	946.8	946.3	945.7
125°	1019.1	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1	1019.0	1017.8	1016.7	1015.6
127.5°	1085.1	1085.8	1085.7	1085.4	1085.1	1084.8	1084.5	1083.9	1083.4	1082.8	1082.3
130°	1146.9	1147.6	1147.7	1148.0	1148.3	1148.6	1148.9	1148.1	1147.2	1146.4	1145.5
132.5°	1209.9	1210.8	1210.4	1209.5	1208.6	1207.8	1206.9	1206.9	1206.9	1206.9	1206.9
135°	1267.8	1268.7	1268.4	1267.8	1267.3	1266.7	1266.1	1265.5	1265.0	1264.4	1263.9
137.5°	1321.9	1322.8	1322.5	1321.9	1321.4	1320.8	1320.2	1320.2	1320.2	1320.2	1320.2
140°	1370.2	1370.5	1370.4	1370.1	1369.8	1369.5	1369.2	1369.8	1370.4	1370.9	1371.5
142.5°	1416.7	1416.8	1417.1	1417.7	1418.2	1418.8	1419.4	1419.4	1419.4	1419.4	1419.4
145°	1464.2	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5	1464.8	1465.1	1465.4	1465.7
147.5°	1503.1	1503.1	1503.2	1503.5	1503.8	1504.1	1504.4	1504.7	1505.0	1505.3	1505.6
150°	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8	1542.4	1543.0	1543.5	1544.1
152.5°	1573.4	1572.7	1573.0	1573.6	1574.1	1574.7	1575.3	1575.9	1576.4	1577.0	1577.5
155°	1603.2	1602.3	1602.6	1603.2	1603.7	1604.3	1604.9	1605.8	1606.6	1607.5	1608.4
157.5°	1631.1	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7	1631.5	1632.4	1633.2	1634.1
160°	1653.5	1652.6	1652.7	1653.0	1653.3	1653.5	1653.8	1655.0	1656.1	1657.3	1658.4
162.5°	1674.1	1673.2	1673.3	1673.6	1673.9	1674.1	1674.4	1676.1	1677.9	1679.6	1681.3
165°	1692.1	1691.2	1691.3	1691.6	1691.9	1692.2	1692.5	1694.2	1695.9	1697.6	1699.3
167.5°	1706.3	1705.4	1705.5	1705.8	1706.1	1706.3	1706.6	1708.6	1710.6	1712.7	1714.7
170°	1716.7	1715.7	1715.8	1716.1	1716.4	1716.7	1717.0	1719.3	1721.6	1723.9	1726.2
172.5°	1724.4	1723.4	1723.7	1724.3	1724.8	1725.4	1726.0	1728.0	1730.0	1732.0	1734.0
175°	1730.7	1729.8	1729.9	1730.2	1730.5	1730.8	1731.1	1733.4	1735.7	1738.0	1740.3
177.5°	1734.6	1733.7	1733.8	1734.1	1734.4	1734.7	1735.0	1737.0	1739.0	1741.0	1743.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3
2.5°	840.4	835.1	834.4	835.9	832.9	837.4	835.9	837.4	833.6	837.4	835.1
5°	782.5	781.0	778.0	774.2	774.9	775.7	779.5	775.7	778.7	779.5	783.2
7.5°	728.3	725.3	727.5	726.0	719.3	717.8	719.3	721.5	726.0	729.1	731.3
10°	684.7	683.2	680.1	677.9	674.1	671.9	674.9	671.9	677.9	683.2	683.2
12.5°	651.6	645.5	641.8	641.0	632.7	634.3	637.3	639.5	646.3	649.3	649.3
15°	616.9	612.4	610.9	607.9	604.9	607.9	606.4	608.7	611.7	614.7	616.2
17.5°	586.9	586.1	586.9	579.3	581.6	577.8	578.6	582.3	580.1	582.3	586.9
20°	559.8	561.3	559.0	556.0	556.0	551.5	556.8	555.3	556.0	560.5	567.3
22.5°	539.5	538.7	536.4	534.2	531.2	531.9	532.7	531.2	537.2	541.0	541.7
25°	517.6	516.1	515.4	513.1	510.1	513.1	512.4	513.1	514.6	520.6	516.1
27.5°	497.3	494.3	495.8	493.6	492.8	493.6	493.6	494.3	495.8	496.6	497.3
30°	480.0	477.0	476.3	474.7	474.0	474.7	476.3	474.7	480.8	480.0	480.0
32.5°	461.2	458.9	457.4	457.4	456.7	455.9	456.7	457.4	462.0	458.9	462.0
35°	443.1	441.6	441.6	440.1	439.4	439.4	439.4	442.4	440.9	443.1	443.1
37.5°	425.8	425.8	425.1	423.6	422.8	423.6	422.8	424.3	423.6	424.3	425.1
40°	407.8	406.3	405.5	405.5	403.3	401.0	403.3	403.3	404.0	406.3	407.0
42.5°	386.0	386.7	386.7	383.7	383.7	383.7	384.5	385.2	385.2	386.7	386.7
45°	367.2	365.7	365.7	365.7	364.1	364.9	366.4	366.4	366.4	366.4	364.9
47.5°	346.1	346.1	346.8	346.8	349.1	348.3	348.3	347.6	346.1	346.1	346.8
50°	326.5	328.8	329.5	329.5	330.3	331.0	331.0	329.5	328.8	326.5	326.5
52.5°	307.7	309.2	310.7	313.0	314.5	313.7	313.7	312.2	309.2	308.5	307.7
55°	287.4	289.7	292.7	294.9	297.2	297.9	297.9	294.9	291.9	288.2	288.2
57.5°	268.6	270.9	276.1	278.4	281.4	281.4	279.9	277.6	273.1	270.1	267.8
60°	249.8	253.5	257.3	261.8	265.6	266.3	264.1	261.1	255.8	252.0	249.0
62.5°	229.5	233.2	240.8	245.3	248.3	248.3	248.3	244.5	237.8	232.5	228.0
65°	209.9	213.7	220.4	226.5	228.7	231.0	228.7	225.0	219.7	213.7	209.2
67.5°	189.6	194.1	200.9	205.4	208.4	210.7	209.2	206.2	199.4	191.1	188.1
70°	167.0	169.3	179.1	183.6	188.1	189.6	188.1	183.6	176.8	167.8	164.8
72.5°	146.0	148.2	157.2	161.0	164.8	166.3	164.0	161.0	155.0	146.7	143.0
75°	121.9	125.6	130.2	136.2	140.7	142.2	139.9	137.7	130.2	124.9	121.9
77.5°	96.3	100.1	106.1	111.4	115.9	115.1	112.1	112.9	104.6	98.6	96.3
80°	73.0	76.0	80.5	85.0	87.3	87.3	86.5	83.5	80.5	76.0	72.2
82.5°	50.4	54.2	57.9	60.9	60.9	61.7	60.2	59.4	56.4	52.7	51.9
85°	30.1	30.8	33.9	33.9	36.9	35.4	34.6	36.9	33.9	31.6	30.8
87.5°	13.5	12.8	13.5	13.5	12.8	14.3	14.3	13.5	14.3	13.5	13.5
90°	27.0	27.4	28.3	29.2	30.0	30.9	30.0	29.2	28.3	27.4	27.0
92.5°	27.0	27.1	27.4	27.7	28.0	28.3	28.0	27.7	27.4	27.1	27.0
95°	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0
97.5°	25.8	25.9	26.2	26.5	26.7	27.0	26.7	26.5	26.2	25.9	25.8
100°	32.2	31.6	30.5	29.3	28.2	27.0	28.2	29.3	30.5	31.6	32.2
102.5°	304.0	292.0	267.9	243.9	219.8	195.8	219.8	243.9	267.9	292.0	304.0
105°	383.8	383.7	383.4	383.1	382.8	382.5	382.8	383.1	383.4	383.7	383.8
107.5°	470.1	469.5	468.4	467.3	466.1	465.0	466.1	467.3	468.4	469.5	470.1
110°	550.0	550.1	550.4	550.7	551.0	551.3	551.0	550.7	550.4	550.1	550.0

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	631.1	630.8	630.3	629.7	629.2	628.6	629.2	629.7	630.3	630.8	631.1
115°	713.6	712.7	711.0	709.3	707.5	705.8	707.5	709.3	711.0	712.7	713.6
117.5°	792.1	791.8	791.3	790.7	790.2	789.6	790.2	790.7	791.3	791.8	792.1
120°	872.0	871.3	869.9	868.4	867.0	865.6	867.0	868.4	869.9	871.3	872.0
122.5°	945.4	944.5	942.8	941.1	939.4	937.7	939.4	941.1	942.8	944.5	945.4
125°	1015.0	1014.6	1013.7	1012.8	1012.0	1011.1	1012.0	1012.8	1013.7	1014.6	1015.0
127.5°	1082.0	1080.8	1078.5	1076.2	1073.9	1071.6	1073.9	1076.2	1078.5	1080.8	1082.0
130°	1145.1	1144.4	1142.9	1141.5	1140.0	1138.6	1140.0	1141.5	1142.9	1144.4	1145.1
132.5°	1206.9	1206.2	1204.8	1203.3	1201.9	1200.5	1201.9	1203.3	1204.8	1206.2	1206.9
135°	1263.6	1262.7	1261.0	1259.3	1257.5	1255.8	1257.5	1259.3	1261.0	1262.7	1263.6
137.5°	1320.2	1319.5	1318.1	1316.6	1315.2	1313.8	1315.2	1316.6	1318.1	1319.5	1320.2
140°	1371.8	1370.9	1369.2	1367.5	1365.7	1364.0	1365.7	1367.5	1369.2	1370.9	1371.8
142.5°	1419.4	1418.5	1416.8	1415.1	1413.4	1411.7	1413.4	1415.1	1416.8	1418.5	1419.4
145°	1465.8	1464.9	1463.2	1461.5	1459.8	1458.1	1459.8	1461.5	1463.2	1464.9	1465.8
147.5°	1505.7	1504.7	1502.7	1500.7	1498.7	1496.7	1498.7	1500.7	1502.7	1504.7	1505.7
150°	1544.4	1543.3	1541.0	1538.7	1536.4	1534.1	1536.4	1538.7	1541.0	1543.3	1544.4
152.5°	1577.8	1576.8	1574.8	1572.8	1570.8	1568.8	1570.8	1572.8	1574.8	1576.8	1577.8
155°	1608.8	1607.7	1605.4	1603.1	1600.8	1598.5	1600.8	1603.1	1605.4	1607.7	1608.8
157.5°	1634.5	1633.4	1631.1	1628.8	1626.5	1624.2	1626.5	1628.8	1631.1	1633.4	1634.5
160°	1659.0	1657.9	1655.6	1653.3	1651.0	1648.7	1651.0	1653.3	1655.6	1657.9	1659.0
162.5°	1682.2	1680.9	1678.3	1675.8	1673.2	1670.6	1673.2	1675.8	1678.3	1680.9	1682.2
165°	1700.2	1699.1	1696.8	1694.5	1692.2	1689.9	1692.2	1694.5	1696.8	1699.1	1700.2
167.5°	1715.7	1714.4	1711.8	1709.3	1706.7	1704.1	1706.7	1709.3	1711.8	1714.4	1715.7
170°	1727.3	1726.0	1723.4	1720.9	1718.3	1715.7	1718.3	1720.9	1723.4	1726.0	1727.3
172.5°	1735.0	1733.7	1731.1	1728.6	1726.0	1723.4	1726.0	1728.6	1731.1	1733.7	1735.0
175°	1741.4	1740.1	1737.5	1735.0	1732.4	1729.8	1732.4	1735.0	1737.5	1740.1	1741.4
177.5°	1744.0	1742.9	1740.6	1738.3	1736.0	1733.7	1736.0	1738.3	1740.6	1742.9	1744.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3	886.3
2.5°	841.9	837.4	842.7	835.9	837.4	845.7	844.9	852.4	857.0	856.2	860.0
5°	786.2	786.2	788.5	787.7	795.3	802.0	811.1	818.6	826.9	831.4	836.6
7.5°	731.3	738.8	740.3	744.1	753.1	764.4	773.4	784.7	796.8	805.0	811.1
10°	686.2	692.2	698.2	701.2	711.0	726.0	738.8	756.9	771.9	781.0	789.2
12.5°	646.3	653.1	656.1	669.6	676.4	686.2	704.2	723.8	740.3	750.1	756.9
15°	617.7	621.5	628.2	636.5	643.3	655.3	670.4	692.2	708.0	716.3	739.6
17.5°	593.6	598.1	601.9	605.7	616.2	629.0	643.3	662.1	682.4	696.7	708.7
20°	568.8	571.1	575.6	581.6	589.1	601.1	613.9	633.5	651.6	662.8	678.6
22.5°	539.5	546.2	550.7	555.3	563.5	577.1	589.1	603.4	626.0	638.8	655.3
25°	522.1	525.2	528.2	533.4	539.5	551.5	565.0	580.1	598.1	611.7	626.0
27.5°	499.6	504.1	507.9	514.6	518.4	528.2	541.0	556.0	577.8	589.1	601.1
30°	480.8	485.3	488.3	491.3	496.6	507.1	519.1	531.2	551.5	565.8	577.8
32.5°	462.0	466.5	470.2	472.5	477.8	484.5	494.3	509.4	526.7	536.4	552.2
35°	445.4	445.4	449.9	452.9	457.4	463.5	472.5	483.8	501.8	514.6	528.9
37.5°	426.6	427.3	431.1	433.4	437.9	443.9	452.9	463.5	478.5	488.3	502.6
40°	407.0	409.3	410.8	414.6	419.8	422.1	431.1	443.1	458.2	467.2	479.3
42.5°	387.5	389.0	392.7	395.7	400.3	404.0	410.0	421.3	432.6	446.2	455.9
45°	365.7	369.4	371.7	376.9	379.2	383.0	389.0	398.0	411.5	419.8	431.1
47.5°	346.8	348.3	349.9	356.6	361.1	363.4	369.4	374.7	389.0	396.5	407.0
50°	326.5	326.5	328.8	331.8	337.1	341.6	346.8	352.9	364.1	371.7	382.2
52.5°	307.7	305.5	307.0	308.5	313.7	318.3	323.5	331.8	342.3	346.8	355.9
55°	287.4	283.6	285.9	288.2	289.7	295.7	301.7	307.0	315.2	322.0	330.3
57.5°	265.6	264.8	263.3	264.1	267.8	271.6	276.1	282.9	292.7	297.9	302.5
60°	246.0	241.5	240.0	241.5	243.8	246.0	252.0	258.1	266.3	271.6	276.9
62.5°	225.7	221.2	218.2	215.9	218.2	223.5	227.2	231.7	238.5	244.5	249.0
65°	206.2	199.4	196.4	194.9	194.1	197.9	200.9	206.9	212.9	215.2	220.4
67.5°	184.3	178.3	174.6	172.3	172.3	172.3	175.3	181.3	187.3	188.1	193.4
70°	162.5	155.7	152.0	149.0	147.5	149.0	152.7	153.5	158.8	160.3	163.3
72.5°	139.2	133.2	128.7	124.9	125.6	127.2	127.2	128.7	131.7	135.4	135.4
75°	117.4	109.1	106.8	103.8	102.3	102.3	102.3	105.3	107.6	110.6	109.8
77.5°	92.5	88.0	83.5	82.0	79.8	79.0	80.5	80.5	82.0	84.3	85.0
80°	71.5	66.2	63.2	61.7	58.7	57.9	58.7	58.7	60.9	60.2	60.9
82.5°	49.7	45.9	43.6	41.4	39.9	40.6	39.9	39.9	40.6	39.9	39.9
85°	28.6	27.8	26.3	25.6	24.8	23.3	24.8	24.1	23.3	22.6	24.1
87.5°	13.5	12.8	12.8	11.3	11.3	10.5	11.3	11.3	10.5	10.5	10.5
90°	26.3	24.9	23.4	22.0	20.6	18.6	16.6	14.6	12.6	11.6	10.5
92.5°	26.3	24.9	23.4	22.0	20.6	18.9	17.2	15.5	13.8	12.9	14.2
95°	26.3	24.9	23.4	22.0	20.6	31.5	42.4	53.3	64.2	69.6	70.0
97.5°	25.5	24.9	24.4	23.8	23.2	50.4	77.6	104.7	131.9	145.5	144.6
100°	53.5	96.2	138.8	181.5	224.1	223.0	221.8	220.7	219.6	219.0	218.6
102.5°	303.7	303.1	302.6	302.0	301.4	300.8	300.2	299.7	299.1	298.8	298.2
105°	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.2
107.5°	470.0	469.7	469.4	469.1	468.8	468.2	467.7	467.1	466.6	466.3	466.3
110°	550.4	551.3	552.2	553.0	553.9	553.3	552.7	552.2	551.6	551.3	551.3

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	631.7	632.8	634.0	635.1	636.3	636.0	635.7	635.4	635.1	635.0	634.6
115°	714.2	715.3	716.4	717.6	718.7	718.4	718.1	717.8	717.5	717.4	716.7
117.5°	793.0	794.7	796.4	798.2	799.9	798.7	797.6	796.4	795.3	794.7	794.7
120°	872.3	872.9	873.4	874.0	874.6	873.7	872.9	872.0	871.1	870.7	870.8
122.5°	945.7	946.3	946.8	947.4	948.0	947.7	947.4	947.1	946.8	946.7	946.0
125°	1015.6	1016.7	1017.8	1019.0	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1	1019.1
127.5°	1082.3	1082.8	1083.4	1083.9	1084.5	1084.8	1085.1	1085.4	1085.7	1085.8	1085.1
130°	1145.5	1146.4	1147.2	1148.1	1148.9	1148.6	1148.3	1148.0	1147.7	1147.6	1146.9
132.5°	1206.9	1206.9	1206.9	1206.9	1206.9	1207.8	1208.6	1209.5	1210.4	1210.8	1209.9
135°	1263.9	1264.4	1265.0	1265.5	1266.1	1266.7	1267.3	1267.8	1268.4	1268.7	1267.8
137.5°	1320.2	1320.2	1320.2	1320.2	1320.2	1320.8	1321.4	1321.9	1322.5	1322.8	1321.9
140°	1371.5	1370.9	1370.4	1369.8	1369.2	1369.5	1369.8	1370.1	1370.4	1370.5	1370.2
142.5°	1419.4	1419.4	1419.4	1419.4	1419.4	1418.8	1418.2	1417.7	1417.1	1416.8	1416.7
145°	1465.7	1465.4	1465.1	1464.8	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5	1464.2
147.5°	1505.6	1505.3	1505.0	1504.7	1504.4	1504.1	1503.8	1503.5	1503.2	1503.1	1503.1
150°	1544.1	1543.5	1543.0	1542.4	1541.8	1541.2	1540.6	1540.1	1539.5	1539.2	1539.5
152.5°	1577.5	1577.0	1576.4	1575.9	1575.3	1574.7	1574.1	1573.6	1573.0	1572.7	1573.4
155°	1608.4	1607.5	1606.6	1605.8	1604.9	1604.3	1603.7	1603.2	1602.6	1602.3	1603.2
157.5°	1634.1	1633.2	1632.4	1631.5	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7	1631.1
160°	1658.4	1657.3	1656.1	1655.0	1653.8	1653.5	1653.3	1653.0	1652.7	1652.6	1653.5
162.5°	1681.3	1679.6	1677.9	1676.1	1674.4	1674.1	1673.9	1673.6	1673.3	1673.2	1674.1
165°	1699.3	1697.6	1695.9	1694.2	1692.5	1692.2	1691.9	1691.6	1691.3	1691.2	1692.1
167.5°	1714.7	1712.7	1710.6	1708.6	1706.6	1706.3	1706.1	1705.8	1705.5	1705.4	1706.3
170°	1726.2	1723.9	1721.6	1719.3	1717.0	1716.7	1716.4	1716.1	1715.8	1715.7	1716.7
172.5°	1734.0	1732.0	1730.0	1728.0	1726.0	1725.4	1724.8	1724.3	1723.7	1723.4	1724.4
175°	1740.3	1738.0	1735.7	1733.4	1731.1	1730.8	1730.5	1730.2	1729.9	1729.8	1730.7
177.5°	1743.0	1741.0	1739.0	1737.0	1735.0	1734.7	1734.4	1734.1	1733.8	1733.7	1734.6
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	886.3	886.3	886.3	886.3
2.5°	865.2	872.8	878.0	887.8
5°	845.7	859.2	872.0	885.5
7.5°	826.1	841.9	862.2	879.5
10°	804.3	824.6	848.7	872.0
12.5°	782.5	806.5	832.9	863.7
15°	756.1	787.0	817.8	850.9
17.5°	732.8	764.4	797.5	838.9
20°	706.5	741.1	777.2	819.3
22.5°	683.2	721.5	759.1	803.5
25°	656.8	694.4	735.8	783.2
27.5°	635.0	669.6	710.2	761.4
30°	608.7	646.3	686.9	738.1
32.5°	583.8	620.0	662.8	713.3
35°	558.3	595.1	633.5	681.7
37.5°	534.2	565.8	604.2	650.1
40°	507.1	541.7	576.3	612.4
42.5°	482.3	513.9	546.2	574.8
45°	454.4	481.5	512.4	535.7
47.5°	428.9	452.9	477.0	495.1
50°	403.3	422.1	440.1	455.9
52.5°	373.2	394.2	404.0	413.8
55°	346.1	358.1	367.2	376.9
57.5°	319.8	325.0	329.5	338.6
60°	285.1	291.2	296.4	303.2
62.5°	255.1	258.1	259.6	266.3
65°	226.5	225.7	229.5	233.2
67.5°	195.6	194.9	198.6	200.1
70°	165.5	164.8	165.5	169.3
72.5°	136.9	136.9	137.7	139.2
75°	110.6	110.6	111.4	112.9
77.5°	83.5	85.0	84.3	87.3
80°	60.9	59.4	60.9	62.4
82.5°	39.9	41.4	41.4	39.9
85°	22.6	22.6	22.6	22.6
87.5°	9.8	9.8	10.5	11.3
90°	8.2	5.9	3.6	1.3
92.5°	16.8	19.3	21.9	24.5
95°	70.9	71.7	72.6	73.4
97.5°	142.9	141.2	139.5	137.8
100°	217.7	216.8	216.0	215.1
102.5°	297.1	296.0	294.8	293.7
105°	382.1	381.0	379.8	378.7
107.5°	466.3	466.3	466.3	466.3
110°	551.3	551.3	551.3	551.3

TEST NUMBER: P1035428

CATALOG NUMBER: S125DIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	633.7	632.8	632.0	631.1
115°	715.3	713.8	712.4	711.0
117.5°	794.7	794.7	794.7	794.7
120°	871.1	871.4	871.7	872.0
122.5°	944.6	943.1	941.7	940.3
125°	1017.1	1015.1	1013.1	1011.1
127.5°	1083.7	1082.2	1080.8	1079.4
130°	1145.5	1144.0	1142.6	1141.2
132.5°	1208.2	1206.5	1204.7	1203.0
135°	1266.1	1264.4	1262.7	1261.0
137.5°	1320.2	1318.5	1316.8	1315.1
140°	1369.6	1369.1	1368.5	1367.9
142.5°	1416.4	1416.1	1415.9	1415.6
145°	1463.6	1463.1	1462.5	1461.9
147.5°	1503.1	1503.1	1503.1	1503.1
150°	1540.1	1540.6	1541.2	1541.8
152.5°	1574.8	1576.3	1577.7	1579.1
155°	1604.9	1606.6	1608.3	1610.0
157.5°	1632.0	1632.8	1633.7	1634.5
160°	1655.2	1656.9	1658.6	1660.3
162.5°	1675.8	1677.5	1679.2	1680.9
165°	1693.8	1695.5	1697.2	1698.9
167.5°	1708.0	1709.7	1711.4	1713.1
170°	1718.7	1720.7	1722.7	1724.7
172.5°	1726.4	1728.4	1730.4	1732.4
175°	1732.4	1734.1	1735.9	1737.6
177.5°	1736.3	1738.0	1739.7	1741.4
180°	1737.6	1737.6	1737.6	1737.6

(END OF REPORT)