

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035756

Luminaire Tested: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035756
REPORT IS A COMBINATION OF REPORTS P1006115 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D770UB30-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7359.0 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	57	55	54
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46
3	84	74	67	62	78	70	63	58	61	56	52	53	49	46	45	42	40
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	45	66	56	48	43	49	43	39	42	38	35	37	33	30
6	65	53	45	39	61	50	43	38	44	38	34	38	34	30	33	30	27
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	28	24	31	25	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10470	10470	10470	10470
5°	10462	11801	10462	9071
10°	10403	13262	10368	7842
15°	10291	14030	10220	6827
20°	10154	15145	10063	6171
25°	9976	17143	9864	5601
30°	9795	18222	9649	5192
35°	9561	14986	9427	4812
40°	9145	10176	9068	4471
45°	8600	7316	8587	4134
50°	8039	5625	8078	3823
55°	7410	4575	7394	3524
60°	6823	3750	6790	3128
65°	6140	3124	6179	2518
70°	5574	2507	5551	2097
75°	4710	1899	4710	1724
80°	3816	1159	3771	1159
85°	2687	610	2607	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14904 cd/sqm

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	2.1
10°-20°	459.5	6.2
20°-30°	728.5	9.9
30°-40°	880.3	12.0
40°-50°	783.7	10.7
50°-60°	601.0	8.2
60°-70°	390.3	5.3
70°-80°	189.4	2.6
80°-90°	46.1	0.6
90°-100°	34.5	0.5
100°-110°	229.5	3.1
110°-120°	413.3	5.6
120°-130°	530.4	7.2
130°-140°	570.5	7.8
140°-150°	535.5	7.3
150°-160°	433.1	5.9
160°-170°	280.1	3.8
170°-180°	96.6	1.3
0°-30°	1344.7	18.3
0°-40°	2225.0	30.2
0°-60°	3609.7	49.1
0°-90°	4235.5	57.6
90°-120°	677.3	9.2
90°-150°	2313.7	31.4
90°-180°	3123.0	42.4
0°-180°	7359.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1634	1634	1634	1634	1634	
5°	1630	1873	1630	1440	1630	155
15°	1562	2250	1551	1095	1562	440
25°	1428	2694	1412	880	1428	658
35°	1244	2235	1226	718	1244	774
45°	973	1000	971	565	973	751
55°	687	549	686	423	687	616
65°	427	311	429	251	427	427
75°	208	145	208	132	208	223
85°	47	31	46	35	47	53
90°	1	18	1	18	1	5
95°	43	16	43	16	43	53
105°	222	224	222	224	222	235
115°	416	413	416	413	416	412
125°	592	592	592	592	592	529
135°	738	735	738	735	738	569
145°	856	853	856	853	856	535
155°	942	935	942	935	942	434
165°	994	989	994	989	994	281
175°	1017	1012	1017	1012	1017	97
180°	1017	1017	1017	1017	1017	

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2
2.5°	1635.6	1649.0	1653.0	1663.8	1675.8	1678.5	1685.2	1694.6	1700.0	1698.7	1698.7
5°	1630.2	1653.0	1669.1	1687.9	1710.7	1720.1	1728.2	1748.3	1764.4	1773.8	1789.9
7.5°	1620.8	1654.4	1681.2	1709.4	1744.3	1760.4	1777.8	1806.0	1835.5	1854.3	1871.7
10°	1606.1	1649.0	1686.6	1728.2	1775.1	1799.3	1820.8	1863.7	1899.9	1924.1	1964.3
12.5°	1584.6	1638.3	1690.6	1745.6	1804.6	1830.1	1859.7	1906.6	1957.6	1992.5	2026.0
15°	1561.8	1626.2	1682.6	1748.3	1819.4	1858.3	1895.9	1945.5	1991.2	2030.1	2069.0
17.5°	1535.0	1603.4	1673.2	1748.3	1828.8	1867.7	1899.9	1959.0	2007.3	2046.2	2081.0
20°	1502.8	1579.2	1658.4	1741.6	1823.4	1859.7	1890.5	1954.9	1997.9	2039.5	2089.1
22.5°	1467.9	1551.1	1635.6	1717.4	1797.9	1836.9	1873.1	1929.4	1976.4	2032.7	2097.2
25°	1427.6	1518.9	1604.7	1686.6	1763.1	1799.3	1831.5	1893.2	1959.0	2030.1	2102.5
27.5°	1387.4	1475.9	1559.1	1634.2	1717.4	1751.0	1783.2	1861.0	1938.8	2014.0	2113.3
30°	1343.1	1433.0	1505.4	1575.2	1655.7	1690.6	1730.9	1819.4	1908.0	2009.9	2130.7
32.5°	1293.4	1375.3	1442.4	1514.8	1587.3	1630.2	1681.2	1777.8	1879.8	2001.9	2156.2
35°	1243.8	1309.5	1371.3	1439.7	1526.9	1572.5	1622.2	1724.1	1851.6	1997.9	2177.7
37.5°	1180.7	1243.8	1292.1	1361.9	1451.8	1505.4	1555.1	1673.2	1818.1	1988.5	2176.3
40°	1116.3	1170.0	1215.6	1288.1	1386.0	1435.7	1489.3	1618.1	1783.2	1961.6	2144.1
42.5°	1046.6	1092.2	1141.8	1211.6	1306.9	1355.2	1416.9	1567.2	1734.9	1924.1	2060.9
45°	972.8	1017.0	1058.6	1131.1	1226.4	1278.7	1345.8	1500.1	1675.8	1844.9	1926.7
47.5°	900.3	939.2	983.5	1046.6	1143.2	1200.9	1269.3	1434.3	1596.7	1738.9	1745.6
50°	830.5	861.4	899.0	963.4	1064.0	1119.0	1190.1	1344.4	1502.8	1600.7	1535.0
52.5°	758.1	786.3	825.2	881.5	975.5	1039.9	1101.6	1255.9	1388.7	1454.5	1333.7
55°	687.0	711.1	751.4	814.4	896.3	945.9	1009.0	1152.6	1269.3	1270.6	1139.1
57.5°	617.2	638.7	672.2	728.6	805.0	862.7	920.4	1045.2	1124.4	1101.6	955.3
60°	555.5	568.9	599.8	654.8	725.9	767.5	829.2	933.9	986.2	944.6	787.6
62.5°	491.1	504.5	528.6	572.9	640.0	684.3	723.2	809.1	845.3	782.2	653.4
65°	426.7	442.8	460.2	495.1	558.2	587.7	622.6	685.6	720.5	646.7	535.4
67.5°	370.3	378.4	395.8	432.0	476.3	503.2	527.3	570.2	577.0	517.9	426.7
70°	318.0	320.7	336.8	358.2	391.8	407.9	428.0	453.5	453.5	405.2	332.8
72.5°	259.0	263.0	275.1	297.9	318.0	326.0	332.8	348.9	346.2	301.9	252.2
75°	208.0	210.7	220.0	230.8	238.8	253.6	259.0	256.3	254.9	217.4	189.2
77.5°	161.0	162.4	169.1	178.5	179.8	185.2	181.1	181.1	169.1	147.6	132.8
80°	118.1	119.4	122.1	124.8	124.8	124.8	124.8	118.1	110.0	96.6	92.6
82.5°	79.2	79.2	80.5	83.2	81.8	79.2	76.5	69.8	64.4	60.4	57.7
85°	47.0	47.0	48.3	47.0	41.6	40.3	37.6	36.2	34.9	33.5	33.5
87.5°	22.8	21.5	18.8	16.1	16.1	16.1	16.1	16.1	16.1	14.8	14.8
90°	0.8	2.1	3.5	4.8	6.1	6.8	7.4	8.6	9.7	10.9	12.1
92.5°	14.3	12.8	11.3	9.8	8.3	7.5	8.0	9.0	10.1	11.1	12.1
95°	43.0	42.5	42.0	41.5	41.0	40.7	37.5	31.2	24.8	18.5	12.1
97.5°	80.7	81.7	82.7	83.7	84.7	85.2	77.2	61.3	45.4	29.5	13.6
100°	125.9	126.4	126.9	127.4	127.9	128.1	128.4	129.1	129.8	130.5	131.2
102.5°	171.9	172.6	173.2	173.9	174.6	174.9	175.1	175.4	175.7	176.1	176.4
105°	221.6	222.3	222.9	223.6	224.3	224.6	224.6	224.6	224.6	224.6	224.6
107.5°	272.9	272.9	272.9	272.9	272.9	272.9	273.1	273.4	273.7	274.1	274.4
110°	322.6	322.6	322.6	322.6	322.6	322.6	322.8	323.1	323.4	323.8	324.1

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	369.3	369.8	370.3	370.8	371.3	371.6	371.7	371.9	372.0	372.2	372.4
115°	416.1	416.9	417.7	418.6	419.4	419.8	419.9	420.1	420.2	420.4	420.6
117.5°	465.1	465.1	465.1	465.1	465.1	465.1	465.4	466.1	466.8	467.4	468.1
120°	510.3	510.1	509.9	509.8	509.6	509.5	509.8	510.3	510.8	511.3	511.8
122.5°	550.2	551.0	551.9	552.7	553.6	554.0	554.1	554.3	554.4	554.6	554.8
125°	591.7	592.9	594.1	595.2	596.4	597.0	597.0	597.0	597.0	597.0	597.0
127.5°	631.7	632.5	633.3	634.2	635.0	635.4	635.3	635.2	635.0	634.9	634.7
130°	667.8	668.6	669.5	670.3	671.2	671.6	671.7	671.9	672.0	672.2	672.4
132.5°	704.0	705.0	706.0	707.0	708.0	708.5	708.3	707.8	707.3	706.8	706.3
135°	737.9	738.9	739.9	741.0	742.0	742.5	742.3	742.0	741.7	741.3	741.0
137.5°	769.6	770.6	771.6	772.6	773.6	774.1	773.9	773.6	773.3	772.9	772.6
140°	800.5	800.8	801.2	801.5	801.8	802.0	801.9	801.8	801.6	801.5	801.3
142.5°	828.4	828.6	828.7	828.9	829.0	829.1	829.3	829.6	830.0	830.3	830.7
145°	855.5	855.8	856.2	856.5	856.8	857.0	857.0	857.0	857.0	857.0	857.0
147.5°	879.6	879.6	879.6	879.6	879.6	879.6	879.7	879.9	880.0	880.2	880.4
150°	902.3	902.0	901.6	901.3	901.0	900.8	901.0	901.3	901.6	902.0	902.3
152.5°	924.1	923.3	922.4	921.6	920.7	920.3	920.5	920.8	921.2	921.5	921.9
155°	942.2	941.2	940.2	939.2	938.2	937.7	937.9	938.2	938.5	938.9	939.2
157.5°	956.5	956.0	955.5	955.0	954.5	954.3	954.3	954.3	954.3	954.3	954.3
160°	971.6	970.6	969.6	968.6	967.6	967.1	967.2	967.3	967.5	967.6	967.8
162.5°	983.7	982.7	981.7	980.6	979.6	979.1	979.2	979.4	979.5	979.7	979.9
165°	994.2	993.2	992.2	991.2	990.2	989.7	989.8	989.9	990.1	990.2	990.4
167.5°	1002.5	1001.5	1000.5	999.5	998.5	998.0	998.1	998.2	998.4	998.5	998.7
170°	1009.3	1008.1	1006.9	1005.8	1004.6	1004.0	1004.1	1004.3	1004.4	1004.6	1004.8
172.5°	1013.8	1012.6	1011.4	1010.3	1009.1	1008.5	1008.7	1009.0	1009.3	1009.7	1010.0
175°	1016.8	1015.8	1014.8	1013.8	1012.8	1012.3	1012.4	1012.6	1012.7	1012.9	1013.1
177.5°	1019.1	1018.1	1017.1	1016.1	1015.1	1014.6	1014.7	1014.8	1015.0	1015.1	1015.3
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2
2.5°	1705.4	1714.8	1722.8	1718.8	1734.9	1733.5	1736.2	1741.6	1742.9	1740.2	1734.9
5°	1797.9	1811.4	1834.2	1846.2	1843.6	1854.3	1859.7	1867.7	1875.8	1873.1	1873.1
7.5°	1901.3	1920.0	1942.8	1973.7	1977.7	1987.1	2003.2	2003.2	2012.6	2008.6	2007.3
10°	1991.2	2014.0	2050.2	2074.3	2085.1	2090.4	2106.5	2111.9	2122.6	2124.0	2124.0
12.5°	2064.9	2105.2	2129.4	2153.5	2158.9	2166.9	2179.0	2187.0	2191.1	2191.1	2187.0
15°	2103.9	2136.1	2164.2	2189.7	2204.5	2211.2	2223.3	2232.7	2238.0	2250.1	2252.8
17.5°	2120.0	2158.9	2204.5	2240.7	2266.2	2272.9	2297.1	2305.1	2315.9	2321.2	2327.9
20°	2142.8	2199.1	2254.1	2298.4	2322.6	2340.0	2365.5	2403.1	2413.8	2413.8	2409.8
22.5°	2162.9	2235.4	2310.5	2381.6	2401.7	2436.6	2483.6	2523.8	2539.9	2546.6	2541.3
25°	2187.0	2286.3	2384.3	2472.8	2527.9	2553.3	2616.4	2664.7	2683.5	2694.2	2696.9
27.5°	2228.6	2353.4	2478.2	2590.9	2647.3	2676.8	2742.5	2784.1	2806.9	2816.3	2809.6
30°	2275.6	2428.6	2573.5	2674.1	2711.7	2747.9	2790.8	2806.9	2801.6	2801.6	2821.7
32.5°	2323.9	2482.2	2611.0	2676.8	2690.2	2684.8	2667.4	2619.1	2590.9	2590.9	2608.4
35°	2350.7	2487.6	2553.3	2531.9	2479.5	2448.7	2353.4	2299.8	2239.4	2235.4	2255.5
37.5°	2336.0	2395.0	2368.2	2227.3	2156.2	2097.2	1948.2	1889.2	1844.9	1783.2	1878.4
40°	2232.7	2212.5	2073.0	1870.4	1791.2	1708.0	1590.0	1530.9	1469.2	1459.8	1482.6
42.5°	2058.2	1938.8	1734.9	1539.0	1458.5	1399.4	1309.5	1251.9	1212.9	1196.8	1223.7
45°	1840.9	1653.0	1449.1	1293.4	1204.9	1174.0	1092.2	1041.2	1011.7	999.6	1018.4
47.5°	1575.2	1386.0	1192.8	1061.3	1009.0	978.1	923.1	878.8	853.4	845.3	853.4
50°	1337.7	1143.2	980.8	896.3	849.3	823.8	778.2	750.0	729.9	724.5	738.0
52.5°	1132.4	955.3	831.9	756.7	725.9	704.4	672.2	648.1	636.0	630.6	640.0
55°	948.6	805.0	705.8	641.4	618.5	605.1	577.0	563.5	550.1	548.8	558.2
57.5°	786.3	687.0	595.7	550.1	543.4	523.3	499.1	487.1	480.3	479.0	483.0
60°	654.8	566.2	511.2	471.0	461.6	445.5	432.0	424.0	415.9	413.3	415.9
62.5°	544.7	475.0	430.7	403.9	390.4	386.4	371.7	362.3	360.9	360.9	363.6
65°	449.5	390.4	362.3	340.8	331.4	327.4	316.7	309.9	311.3	311.3	312.6
67.5°	366.3	323.4	297.9	287.1	279.1	277.7	267.0	264.3	261.6	261.6	264.3
70°	291.2	264.3	245.5	240.2	238.8	229.4	225.4	224.1	220.0	221.4	221.4
72.5°	228.1	210.7	199.9	191.9	193.2	187.8	182.5	182.5	179.8	183.8	183.8
75°	169.1	161.0	153.0	150.3	153.0	150.3	146.3	144.9	146.3	144.9	144.9
77.5°	124.8	120.8	118.1	116.7	116.7	111.4	108.7	111.4	106.0	108.7	108.7
80°	87.2	81.8	80.5	77.8	79.2	75.1	76.5	73.8	73.8	73.8	73.8
82.5°	55.0	53.7	53.7	53.7	52.3	52.3	52.3	52.3	52.3	52.3	51.0
85°	33.5	32.2	32.2	32.2	30.9	30.9	30.9	30.9	30.9	30.9	30.9
87.5°	13.4	14.8	14.8	16.1	14.8	13.4	13.4	13.4	14.8	14.8	13.4
90°	12.9	13.7	14.6	15.4	15.8	16.1	16.6	17.1	17.6	18.1	17.6
92.5°	12.9	13.7	14.6	15.4	15.8	15.9	16.1	16.2	16.4	16.6	16.4
95°	12.9	13.7	14.6	15.4	15.8	15.8	15.8	15.8	15.8	15.8	15.8
97.5°	13.9	14.3	14.6	14.9	15.1	15.2	15.3	15.5	15.6	15.8	15.6
100°	106.2	81.2	56.3	31.3	18.8	18.5	17.8	17.1	16.5	15.8	16.5
102.5°	176.7	177.1	177.4	177.7	177.9	170.9	156.8	142.7	128.7	114.6	128.7
105°	224.6	224.6	224.6	224.6	224.6	224.5	224.4	224.2	224.1	223.9	224.1
107.5°	274.6	274.7	274.9	275.0	275.1	274.8	274.1	273.4	272.8	272.1	272.8
110°	323.6	323.1	322.6	322.1	321.9	322.0	322.1	322.3	322.4	322.6	322.4

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	371.7	371.0	370.3	369.6	369.3	369.1	368.8	368.5	368.1	367.8	368.1
115°	419.9	419.3	418.6	417.9	417.6	417.1	416.1	415.1	414.1	413.1	414.1
117.5°	467.1	466.1	465.1	464.1	463.6	463.4	463.1	462.8	462.4	462.1	462.4
120°	511.5	511.1	510.8	510.5	510.3	509.9	509.0	508.2	507.3	506.5	507.3
122.5°	554.5	554.1	553.8	553.5	553.3	552.8	551.8	550.7	549.7	548.7	549.7
125°	596.3	595.7	595.0	594.3	594.0	593.7	593.2	592.7	592.2	591.7	592.2
127.5°	634.4	634.0	633.7	633.4	633.2	632.5	631.2	629.8	628.5	627.1	628.5
130°	671.9	671.4	670.9	670.4	670.1	669.7	668.8	668.0	667.1	666.3	667.1
132.5°	706.3	706.3	706.3	706.3	706.3	705.9	705.0	704.2	703.3	702.5	703.3
135°	740.6	740.3	739.9	739.6	739.4	738.9	737.9	736.9	735.9	734.9	735.9
137.5°	772.6	772.6	772.6	772.6	772.6	772.2	771.3	770.5	769.6	768.8	769.6
140°	801.6	802.0	802.3	802.6	802.8	802.3	801.3	800.2	799.2	798.2	799.2
142.5°	830.7	830.7	830.7	830.7	830.7	830.2	829.2	828.1	827.1	826.1	827.1
145°	857.2	857.4	857.5	857.7	857.8	857.3	856.3	855.3	854.3	853.3	854.3
147.5°	880.6	880.8	880.9	881.1	881.2	880.6	879.4	878.3	877.1	875.9	877.1
150°	902.6	903.0	903.3	903.6	903.8	903.1	901.8	900.4	899.1	897.7	899.1
152.5°	922.2	922.6	922.9	923.2	923.4	922.8	921.6	920.5	919.3	918.1	919.3
155°	939.7	940.2	940.7	941.2	941.5	940.8	939.5	938.1	936.8	935.4	936.8
157.5°	954.8	955.3	955.8	956.3	956.5	955.8	954.5	953.2	951.8	950.5	951.8
160°	968.5	969.2	969.9	970.6	970.9	970.2	968.9	967.5	966.2	964.8	966.2
162.5°	980.9	981.9	982.9	983.9	984.4	983.6	982.1	980.6	979.1	977.6	979.1
165°	991.4	992.4	993.5	994.5	995.0	994.3	993.0	991.6	990.3	988.9	990.3
167.5°	999.9	1001.1	1002.2	1003.4	1004.0	1003.2	1001.7	1000.2	998.7	997.2	998.7
170°	1006.1	1007.5	1008.8	1010.1	1010.8	1010.0	1008.5	1007.0	1005.5	1004.0	1005.5
172.5°	1011.2	1012.4	1013.5	1014.7	1015.3	1014.5	1013.0	1011.5	1010.0	1008.5	1010.0
175°	1014.4	1015.8	1017.1	1018.4	1019.1	1018.3	1016.8	1015.3	1013.8	1012.3	1013.8
177.5°	1016.5	1017.7	1018.8	1020.0	1020.6	1019.9	1018.6	1017.3	1015.9	1014.6	1015.9
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2
2.5°	1741.6	1732.2	1736.2	1732.2	1728.2	1724.1	1714.8	1701.3	1690.6	1682.6	1681.2
5°	1875.8	1863.7	1855.6	1851.6	1843.6	1832.8	1815.4	1795.3	1771.1	1761.7	1742.9
7.5°	1999.2	1995.2	1976.4	1973.7	1968.3	1948.2	1918.7	1891.9	1861.0	1835.5	1811.4
10°	2115.9	2106.5	2093.1	2074.3	2071.7	2046.2	2018.0	1980.4	1940.2	1916.0	1873.1
12.5°	2188.4	2177.7	2162.9	2150.8	2144.1	2128.0	2089.1	2051.5	2015.3	1971.0	1933.5
15°	2240.7	2227.3	2200.5	2191.1	2183.0	2161.6	2133.4	2094.5	2046.2	2015.3	1961.6
17.5°	2311.8	2295.7	2268.9	2251.5	2236.7	2203.1	2162.9	2110.6	2064.9	2030.1	1981.8
20°	2393.7	2369.5	2334.6	2311.8	2290.4	2251.5	2195.1	2133.4	2067.6	2024.7	1975.1
22.5°	2529.2	2483.6	2428.6	2396.4	2366.8	2299.8	2232.7	2156.2	2082.4	2018.0	1957.6
25°	2660.7	2615.1	2546.6	2502.4	2456.7	2378.9	2290.4	2184.4	2090.4	2015.3	1936.1
27.5°	2782.8	2735.8	2672.8	2619.1	2574.8	2458.1	2341.3	2221.9	2102.5	1999.2	1918.7
30°	2811.0	2790.8	2742.5	2695.6	2655.3	2548.0	2412.5	2260.8	2117.3	1984.4	1894.5
32.5°	2640.6	2690.2	2702.3	2695.6	2670.1	2593.6	2468.8	2309.1	2138.7	1977.7	1854.3
35°	2286.3	2376.2	2468.8	2518.5	2542.6	2553.3	2479.5	2333.3	2153.5	1967.0	1827.5
37.5°	1895.9	1983.1	2129.4	2203.1	2285.0	2392.3	2421.9	2327.9	2146.8	1959.0	1784.5
40°	1557.8	1669.1	1789.9	1857.0	1928.1	2121.3	2267.6	2256.8	2125.3	1929.4	1751.0
42.5°	1268.0	1337.7	1443.7	1517.5	1604.7	1820.8	2016.6	2113.3	2060.9	1893.2	1708.0
45°	1057.3	1111.0	1186.1	1261.2	1314.9	1510.8	1742.9	1901.3	1950.9	1828.8	1642.3
47.5°	890.9	931.2	996.9	1043.9	1101.6	1255.9	1457.1	1679.9	1784.5	1737.6	1572.5
50°	763.5	795.7	848.0	877.5	928.5	1061.3	1214.3	1447.7	1606.1	1611.4	1479.9
52.5°	652.1	684.3	728.6	754.1	784.9	874.8	1029.1	1226.4	1408.8	1475.9	1373.9
55°	567.6	586.3	622.6	642.7	670.9	758.1	856.0	1023.8	1214.3	1324.3	1259.9
57.5°	489.7	509.9	532.7	548.8	568.9	638.7	727.2	853.4	1042.5	1162.0	1140.5
60°	426.7	438.8	460.2	472.3	491.1	536.7	598.4	724.5	874.8	987.5	999.6
62.5°	367.6	378.4	393.1	403.9	415.9	452.2	497.8	587.7	719.2	841.3	857.4
65°	316.7	326.0	334.1	343.5	352.9	375.7	414.6	484.4	586.3	700.4	735.3
67.5°	271.0	273.7	285.8	287.1	292.5	309.9	338.1	394.5	468.3	559.5	605.1
70°	226.8	232.1	234.8	238.8	244.2	256.3	279.1	308.6	363.6	437.4	480.3
72.5°	183.8	185.2	189.2	191.9	197.2	206.6	217.4	240.2	275.1	328.7	367.6
75°	146.3	147.6	150.3	151.6	155.6	158.3	163.7	179.8	203.9	236.1	264.3
77.5°	110.0	112.7	115.4	115.4	116.7	119.4	122.1	127.5	139.5	161.0	185.2
80°	75.1	76.5	76.5	77.8	76.5	80.5	84.5	91.2	96.6	103.3	115.4
82.5°	52.3	52.3	52.3	53.7	53.7	55.0	55.0	56.4	57.7	61.7	67.1
85°	32.2	32.2	33.5	30.9	32.2	33.5	33.5	32.2	33.5	34.9	36.2
87.5°	13.4	13.4	14.8	14.8	14.8	14.8	13.4	14.8	13.4	14.8	14.8
90°	17.1	16.6	16.1	15.8	15.4	14.6	13.7	12.9	12.1	10.9	9.7
92.5°	16.2	16.1	15.9	15.8	15.4	14.6	13.7	12.9	12.1	11.1	10.1
95°	15.8	15.8	15.8	15.8	15.4	14.6	13.7	12.9	12.1	18.5	24.8
97.5°	15.5	15.3	15.2	15.1	14.9	14.6	14.3	13.9	13.6	29.5	45.4
100°	17.1	17.8	18.5	18.8	31.3	56.3	81.2	106.2	131.2	130.5	129.8
102.5°	142.7	156.8	170.9	177.9	177.7	177.4	177.1	176.7	176.4	176.1	175.7
105°	224.2	224.4	224.5	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6
107.5°	273.4	274.1	274.8	275.1	275.0	274.9	274.7	274.6	274.4	274.1	273.7
110°	322.3	322.1	322.0	321.9	322.1	322.6	323.1	323.6	324.1	323.8	323.4

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	368.5	368.8	369.1	369.3	369.6	370.3	371.0	371.7	372.4	372.2	372.0
115°	415.1	416.1	417.1	417.6	417.9	418.6	419.3	419.9	420.6	420.4	420.2
117.5°	462.8	463.1	463.4	463.6	464.1	465.1	466.1	467.1	468.1	467.4	466.8
120°	508.2	509.0	509.9	510.3	510.5	510.8	511.1	511.5	511.8	511.3	510.8
122.5°	550.7	551.8	552.8	553.3	553.5	553.8	554.1	554.5	554.8	554.6	554.4
125°	592.7	593.2	593.7	594.0	594.3	595.0	595.7	596.3	597.0	597.0	597.0
127.5°	629.8	631.2	632.5	633.2	633.4	633.7	634.0	634.4	634.7	634.9	635.0
130°	668.0	668.8	669.7	670.1	670.4	670.9	671.4	671.9	672.4	672.2	672.0
132.5°	704.2	705.0	705.9	706.3	706.3	706.3	706.3	706.3	706.3	706.8	707.3
135°	736.9	737.9	738.9	739.4	739.6	739.9	740.3	740.6	741.0	741.3	741.7
137.5°	770.5	771.3	772.2	772.6	772.6	772.6	772.6	772.6	772.6	772.9	773.3
140°	800.2	801.3	802.3	802.8	802.6	802.3	802.0	801.6	801.3	801.5	801.6
142.5°	828.1	829.2	830.2	830.7	830.7	830.7	830.7	830.7	830.7	830.3	830.0
145°	855.3	856.3	857.3	857.8	857.7	857.5	857.4	857.2	857.0	857.0	857.0
147.5°	878.3	879.4	880.6	881.2	881.1	880.9	880.8	880.6	880.4	880.2	880.0
150°	900.4	901.8	903.1	903.8	903.6	903.3	903.0	902.6	902.3	902.0	901.6
152.5°	920.5	921.6	922.8	923.4	923.2	922.9	922.6	922.2	921.9	921.5	921.2
155°	938.1	939.5	940.8	941.5	941.2	940.7	940.2	939.7	939.2	938.9	938.5
157.5°	953.2	954.5	955.8	956.5	956.3	955.8	955.3	954.8	954.3	954.3	954.3
160°	967.5	968.9	970.2	970.9	970.6	969.9	969.2	968.5	967.8	967.6	967.5
162.5°	980.6	982.1	983.6	984.4	983.9	982.9	981.9	980.9	979.9	979.7	979.5
165°	991.6	993.0	994.3	995.0	994.5	993.5	992.4	991.4	990.4	990.2	990.1
167.5°	1000.2	1001.7	1003.2	1004.0	1003.4	1002.2	1001.1	999.9	998.7	998.5	998.4
170°	1007.0	1008.5	1010.0	1010.8	1010.1	1008.8	1007.5	1006.1	1004.8	1004.6	1004.4
172.5°	1011.5	1013.0	1014.5	1015.3	1014.7	1013.5	1012.4	1011.2	1010.0	1009.7	1009.3
175°	1015.3	1016.8	1018.3	1019.1	1018.4	1017.1	1015.8	1014.4	1013.1	1012.9	1012.7
177.5°	1017.3	1018.6	1019.9	1020.6	1020.0	1018.8	1017.7	1016.5	1015.3	1015.1	1015.0
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2
2.5°	1677.2	1669.1	1663.8	1662.4	1654.4	1647.7	1639.6	1638.3	1634.2	1623.5	1616.8
5°	1729.5	1710.7	1706.7	1694.6	1674.5	1659.7	1641.0	1630.2	1618.1	1598.0	1581.9
7.5°	1783.2	1757.7	1738.9	1721.5	1693.3	1666.4	1639.6	1618.1	1596.7	1567.2	1543.0
10°	1835.5	1796.6	1773.8	1748.3	1709.4	1669.1	1631.6	1600.7	1565.8	1530.9	1496.0
12.5°	1883.8	1834.2	1800.6	1764.4	1716.1	1666.4	1618.1	1575.2	1539.0	1492.0	1453.1
15°	1913.3	1858.3	1824.8	1789.9	1717.4	1662.4	1606.1	1551.1	1502.8	1453.1	1416.9
17.5°	1930.8	1869.1	1831.5	1799.3	1725.5	1650.3	1577.9	1518.9	1466.5	1407.5	1359.2
20°	1922.7	1862.3	1827.5	1796.6	1710.7	1635.6	1557.8	1489.3	1423.6	1363.2	1312.2
22.5°	1905.3	1842.2	1803.3	1775.1	1698.7	1610.1	1524.2	1450.4	1382.0	1321.6	1263.9
25°	1867.7	1806.0	1772.4	1737.6	1662.4	1577.9	1490.7	1411.5	1339.1	1274.7	1210.3
27.5°	1834.2	1759.0	1724.1	1693.3	1614.1	1539.0	1453.1	1365.9	1292.1	1225.0	1160.6
30°	1795.3	1710.7	1673.2	1631.6	1560.5	1489.3	1403.5	1323.0	1246.5	1175.4	1113.7
32.5°	1753.7	1655.7	1612.8	1565.8	1493.4	1426.3	1353.8	1274.7	1198.2	1128.4	1064.0
35°	1700.0	1595.3	1545.7	1501.4	1426.3	1359.2	1292.1	1226.4	1149.9	1076.1	1014.4
37.5°	1649.0	1533.6	1481.3	1430.3	1351.1	1286.7	1231.7	1170.0	1096.2	1025.1	966.1
40°	1591.3	1458.5	1404.8	1357.8	1276.0	1204.9	1155.2	1106.9	1042.5	974.1	909.7
42.5°	1539.0	1388.7	1332.4	1284.1	1198.2	1131.1	1084.1	1043.9	987.5	924.5	858.7
45°	1466.5	1313.6	1255.9	1204.9	1117.7	1054.6	1006.3	971.4	927.1	868.1	809.1
47.5°	1399.4	1241.1	1178.1	1116.3	1037.2	972.8	928.5	901.7	872.1	819.8	759.4
50°	1317.6	1157.9	1093.5	1042.5	952.6	897.6	853.4	834.6	807.7	758.1	709.8
52.5°	1229.0	1077.4	1017.0	955.3	872.1	818.5	779.6	758.1	736.6	700.4	654.8
55°	1125.7	987.5	931.2	876.2	793.0	743.3	708.4	685.6	673.6	640.0	606.5
57.5°	1026.4	896.3	844.0	793.0	720.5	664.2	641.4	621.2	603.8	579.6	551.5
60°	925.8	807.7	751.4	705.8	642.7	591.7	572.9	552.8	539.4	520.6	500.5
62.5°	810.4	709.8	666.8	623.9	570.2	530.0	508.5	492.4	475.0	462.9	445.5
65°	688.3	617.2	575.6	543.4	492.4	456.2	440.1	429.4	414.6	402.5	389.1
67.5°	574.3	517.9	500.5	465.6	426.7	394.5	382.4	369.0	356.9	350.2	338.1
70°	464.2	424.0	406.5	397.2	354.2	332.8	322.0	316.7	301.9	295.2	287.1
72.5°	359.6	344.8	332.8	320.7	292.5	279.1	267.0	261.6	250.9	245.5	242.9
75°	265.7	256.3	249.6	248.2	236.1	222.7	210.7	208.0	199.9	194.6	191.9
77.5°	186.5	183.8	182.5	183.8	175.8	167.7	165.0	162.4	153.0	151.6	151.6
80°	122.1	128.8	128.8	127.5	124.8	123.4	119.4	116.7	111.4	110.0	111.4
82.5°	75.1	79.2	80.5	83.2	81.8	80.5	77.8	76.5	77.8	75.1	76.5
85°	37.6	40.3	45.6	45.6	47.0	47.0	47.0	45.6	42.9	44.3	42.9
87.5°	14.8	16.1	16.1	16.1	14.8	18.8	20.1	20.1	20.1	17.4	17.4
90°	8.6	7.4	6.8	6.1	4.8	3.5	2.1	0.8	2.1	3.5	4.8
92.5°	9.0	8.0	7.5	8.3	9.8	11.3	12.8	14.3	12.8	11.3	9.8
95°	31.2	37.5	40.7	41.0	41.5	42.0	42.5	43.0	42.5	42.0	41.5
97.5°	61.3	77.2	85.2	84.7	83.7	82.7	81.7	80.7	81.7	82.7	83.7
100°	129.1	128.4	128.1	127.9	127.4	126.9	126.4	125.9	126.4	126.9	127.4
102.5°	175.4	175.1	174.9	174.6	173.9	173.2	172.6	171.9	172.6	173.2	173.9
105°	224.6	224.6	224.6	224.3	223.6	222.9	222.3	221.6	222.3	222.9	223.6
107.5°	273.4	273.1	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.9
110°	323.1	322.8	322.6	322.6	322.6	322.6	322.6	322.6	322.6	322.6	322.6

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	371.9	371.7	371.6	371.3	370.8	370.3	369.8	369.3	369.8	370.3	370.8
115°	420.1	419.9	419.8	419.4	418.6	417.7	416.9	416.1	416.9	417.7	418.6
117.5°	466.1	465.4	465.1	465.1	465.1	465.1	465.1	465.1	465.1	465.1	465.1
120°	510.3	509.8	509.5	509.6	509.8	509.9	510.1	510.3	510.1	509.9	509.8
122.5°	554.3	554.1	554.0	553.6	552.7	551.9	551.0	550.2	551.0	551.9	552.7
125°	597.0	597.0	597.0	596.4	595.2	594.1	592.9	591.7	592.9	594.1	595.2
127.5°	635.2	635.3	635.4	635.0	634.2	633.3	632.5	631.7	632.5	633.3	634.2
130°	671.9	671.7	671.6	671.2	670.3	669.5	668.6	667.8	668.6	669.5	670.3
132.5°	707.8	708.3	708.5	708.0	707.0	706.0	705.0	704.0	705.0	706.0	707.0
135°	742.0	742.3	742.5	742.0	741.0	739.9	738.9	737.9	738.9	739.9	741.0
137.5°	773.6	773.9	774.1	773.6	772.6	771.6	770.6	769.6	770.6	771.6	772.6
140°	801.8	801.9	802.0	801.8	801.5	801.2	800.8	800.5	800.8	801.2	801.5
142.5°	829.6	829.3	829.1	829.0	828.9	828.7	828.6	828.4	828.6	828.7	828.9
145°	857.0	857.0	857.0	856.8	856.5	856.2	855.8	855.5	855.8	856.2	856.5
147.5°	879.9	879.7	879.6	879.6	879.6	879.6	879.6	879.6	879.6	879.6	879.6
150°	901.3	901.0	900.8	901.0	901.3	901.6	902.0	902.3	902.0	901.6	901.3
152.5°	920.8	920.5	920.3	920.7	921.6	922.4	923.3	924.1	923.3	922.4	921.6
155°	938.2	937.9	937.7	938.2	939.2	940.2	941.2	942.2	941.2	940.2	939.2
157.5°	954.3	954.3	954.3	954.5	955.0	955.5	956.0	956.5	956.0	955.5	955.0
160°	967.3	967.2	967.1	967.6	968.6	969.6	970.6	971.6	970.6	969.6	968.6
162.5°	979.4	979.2	979.1	979.6	980.6	981.7	982.7	983.7	982.7	981.7	980.6
165°	989.9	989.8	989.7	990.2	991.2	992.2	993.2	994.2	993.2	992.2	991.2
167.5°	998.2	998.1	998.0	998.5	999.5	1000.5	1001.5	1002.5	1001.5	1000.5	999.5
170°	1004.3	1004.1	1004.0	1004.6	1005.8	1006.9	1008.1	1009.3	1008.1	1006.9	1005.8
172.5°	1009.0	1008.7	1008.5	1009.1	1010.3	1011.4	1012.6	1013.8	1012.6	1011.4	1010.3
175°	1012.6	1012.4	1012.3	1012.8	1013.8	1014.8	1015.8	1016.8	1015.8	1014.8	1013.8
177.5°	1014.8	1014.7	1014.6	1015.1	1016.1	1017.1	1018.1	1019.1	1018.1	1017.1	1016.1
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2
2.5°	1612.8	1607.4	1603.4	1599.4	1581.9	1563.1	1560.5	1556.4	1548.4	1557.8	1553.7
5°	1571.2	1559.1	1552.4	1535.0	1513.5	1497.4	1484.0	1467.9	1461.2	1455.8	1454.5
7.5°	1520.2	1509.5	1497.4	1479.9	1453.1	1426.3	1406.2	1390.0	1376.6	1369.9	1369.9
10°	1470.6	1457.1	1441.0	1411.5	1386.0	1352.5	1331.0	1314.9	1296.1	1285.4	1276.0
12.5°	1419.6	1404.8	1390.0	1352.5	1323.0	1288.1	1257.2	1237.1	1227.7	1215.6	1199.5
15°	1368.6	1345.8	1331.0	1293.4	1255.9	1221.0	1200.9	1179.4	1157.9	1145.9	1140.5
17.5°	1314.9	1298.8	1274.7	1234.4	1192.8	1162.0	1132.4	1112.3	1086.8	1074.7	1062.7
20°	1266.6	1242.5	1218.3	1178.1	1137.8	1096.2	1066.7	1042.5	1026.4	1017.0	1006.3
22.5°	1208.9	1186.1	1166.0	1123.0	1078.8	1039.9	1007.7	992.9	976.8	962.0	951.3
25°	1159.3	1136.5	1116.3	1069.4	1021.1	984.8	960.7	941.9	924.5	917.8	907.0
27.5°	1106.9	1085.5	1058.6	1011.7	968.7	937.9	912.4	894.9	881.5	868.1	860.1
30°	1057.3	1033.1	1009.0	958.0	923.1	892.3	868.1	846.6	835.9	829.2	815.8
32.5°	1009.0	978.1	958.0	911.0	877.5	848.0	827.9	809.1	795.7	783.6	772.8
35°	956.7	923.1	903.0	864.1	829.2	799.7	782.2	768.8	752.7	742.0	736.6
37.5°	907.0	878.8	858.7	818.5	783.6	759.4	740.6	723.2	716.5	701.7	699.1
40°	853.4	829.2	810.4	771.5	739.3	720.5	700.4	684.3	672.2	665.5	656.1
42.5°	805.0	784.9	764.8	728.6	697.7	674.9	660.1	645.4	634.6	623.9	617.2
45°	760.8	739.3	720.5	685.6	654.8	634.6	619.9	602.4	599.8	585.0	578.3
47.5°	713.8	695.0	678.9	642.7	614.5	594.4	577.0	564.9	552.8	547.4	538.0
50°	668.2	649.4	630.6	598.4	572.9	552.8	535.4	521.9	515.2	507.2	499.1
52.5°	618.5	603.8	589.0	555.5	530.0	512.5	497.8	480.3	473.6	466.9	461.6
55°	577.0	555.5	539.4	511.2	488.4	469.6	453.5	440.1	433.4	428.0	421.3
57.5°	520.6	507.2	493.8	468.3	446.8	428.0	411.9	401.2	393.1	389.1	390.4
60°	472.3	457.5	449.5	422.7	401.2	386.4	371.7	360.9	352.9	348.9	347.5
62.5°	421.3	410.6	395.8	377.0	355.6	342.1	331.4	323.4	309.9	308.6	304.6
65°	371.7	363.6	350.2	332.8	315.3	303.2	291.2	280.4	275.1	268.3	264.3
67.5°	323.4	315.3	303.2	288.5	276.4	264.3	253.6	242.9	233.5	228.1	225.4
70°	276.4	269.7	261.6	244.2	229.4	220.0	212.0	205.3	195.9	193.2	191.9
72.5°	230.8	224.1	220.0	205.3	191.9	183.8	175.8	169.1	165.0	163.7	159.7
75°	189.2	182.5	177.1	163.7	155.6	150.3	142.2	139.5	135.5	134.2	132.8
77.5°	147.6	140.9	139.5	130.1	120.8	118.1	115.4	110.0	110.0	110.0	107.3
80°	106.0	104.7	103.3	93.9	89.9	87.2	85.9	81.8	79.2	76.5	75.1
82.5°	71.1	69.8	68.4	64.4	60.4	59.0	57.7	55.0	55.0	56.4	53.7
85°	42.9	40.3	38.9	37.6	34.9	34.9	36.2	34.9	34.9	34.9	33.5
87.5°	16.1	16.1	16.1	16.1	17.4	14.8	16.1	16.1	14.8	14.8	13.4
90°	6.1	6.8	7.4	8.6	9.7	10.9	12.1	12.9	13.7	14.6	15.4
92.5°	8.3	7.5	8.0	9.0	10.1	11.1	12.1	12.9	13.7	14.6	15.4
95°	41.0	40.7	37.5	31.2	24.8	18.5	12.1	12.9	13.7	14.6	15.4
97.5°	84.7	85.2	77.2	61.3	45.4	29.5	13.6	13.9	14.3	14.6	14.9
100°	127.9	128.1	128.4	129.1	129.8	130.5	131.2	106.2	81.2	56.3	31.3
102.5°	174.6	174.9	175.1	175.4	175.7	176.1	176.4	176.7	177.1	177.4	177.7
105°	224.3	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6
107.5°	272.9	272.9	273.1	273.4	273.7	274.1	274.4	274.6	274.7	274.9	275.0
110°	322.6	322.6	322.8	323.1	323.4	323.8	324.1	323.6	323.1	322.6	322.1

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	371.3	371.6	371.7	371.9	372.0	372.2	372.4	371.7	371.0	370.3	369.6
115°	419.4	419.8	419.9	420.1	420.2	420.4	420.6	419.9	419.3	418.6	417.9
117.5°	465.1	465.1	465.4	466.1	466.8	467.4	468.1	467.1	466.1	465.1	464.1
120°	509.6	509.5	509.8	510.3	510.8	511.3	511.8	511.5	511.1	510.8	510.5
122.5°	553.6	554.0	554.1	554.3	554.4	554.6	554.8	554.5	554.1	553.8	553.5
125°	596.4	597.0	597.0	597.0	597.0	597.0	597.0	596.3	595.7	595.0	594.3
127.5°	635.0	635.4	635.3	635.2	635.0	634.9	634.7	634.4	634.0	633.7	633.4
130°	671.2	671.6	671.7	671.9	672.0	672.2	672.4	671.9	671.4	670.9	670.4
132.5°	708.0	708.5	708.3	707.8	707.3	706.8	706.3	706.3	706.3	706.3	706.3
135°	742.0	742.5	742.3	742.0	741.7	741.3	741.0	740.6	740.3	739.9	739.6
137.5°	773.6	774.1	773.9	773.6	773.3	772.9	772.6	772.6	772.6	772.6	772.6
140°	801.8	802.0	801.9	801.8	801.6	801.5	801.3	801.6	802.0	802.3	802.6
142.5°	829.0	829.1	829.3	829.6	830.0	830.3	830.7	830.7	830.7	830.7	830.7
145°	856.8	857.0	857.0	857.0	857.0	857.0	857.0	857.2	857.4	857.5	857.7
147.5°	879.6	879.6	879.7	879.9	880.0	880.2	880.4	880.6	880.8	880.9	881.1
150°	901.0	900.8	901.0	901.3	901.6	902.0	902.3	902.6	903.0	903.3	903.6
152.5°	920.7	920.3	920.5	920.8	921.2	921.5	921.9	922.2	922.6	922.9	923.2
155°	938.2	937.7	937.9	938.2	938.5	938.9	939.2	939.7	940.2	940.7	941.2
157.5°	954.5	954.3	954.3	954.3	954.3	954.3	954.3	954.8	955.3	955.8	956.3
160°	967.6	967.1	967.2	967.3	967.5	967.6	967.8	968.5	969.2	969.9	970.6
162.5°	979.6	979.1	979.2	979.4	979.5	979.7	979.9	980.9	981.9	982.9	983.9
165°	990.2	989.7	989.8	989.9	990.1	990.2	990.4	991.4	992.4	993.5	994.5
167.5°	998.5	998.0	998.1	998.2	998.4	998.5	998.7	999.9	1001.1	1002.2	1003.4
170°	1004.6	1004.0	1004.1	1004.3	1004.4	1004.6	1004.8	1006.1	1007.5	1008.8	1010.1
172.5°	1009.1	1008.5	1008.7	1009.0	1009.3	1009.7	1010.0	1011.2	1012.4	1013.5	1014.7
175°	1012.8	1012.3	1012.4	1012.6	1012.7	1012.9	1013.1	1014.4	1015.8	1017.1	1018.4
177.5°	1015.1	1014.6	1014.7	1014.8	1015.0	1015.1	1015.3	1016.5	1017.7	1018.8	1020.0
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2
2.5°	1547.0	1549.7	1543.0	1540.3	1535.0	1541.7	1543.0	1541.7	1553.7	1548.4	1551.1
5°	1457.1	1451.8	1447.7	1438.4	1438.4	1439.7	1443.7	1437.0	1441.0	1450.4	1449.1
7.5°	1357.8	1355.2	1356.5	1345.8	1337.7	1340.4	1337.7	1349.8	1356.5	1353.8	1359.2
10°	1268.0	1273.3	1261.2	1255.9	1250.5	1255.9	1254.5	1257.2	1265.3	1270.6	1280.0
12.5°	1195.5	1194.2	1187.4	1182.1	1172.7	1175.4	1183.4	1180.7	1182.1	1194.2	1192.8
15°	1127.1	1119.0	1113.7	1101.6	1104.3	1094.9	1102.9	1112.3	1116.3	1127.1	1133.8
17.5°	1058.6	1057.3	1050.6	1049.2	1034.5	1030.5	1038.5	1041.2	1045.2	1050.6	1060.0
20°	1000.9	999.6	990.2	987.5	975.5	983.5	980.8	986.2	988.9	999.6	1003.6
22.5°	948.6	941.9	939.2	935.2	931.2	929.8	935.2	933.9	943.2	947.3	948.6
25°	900.3	894.9	893.6	886.9	884.2	880.2	884.2	888.2	899.0	903.0	908.4
27.5°	856.0	852.0	849.3	844.0	839.9	839.9	842.6	848.0	852.0	854.7	857.4
30°	815.8	813.1	805.0	802.4	798.3	798.3	798.3	801.0	807.7	815.8	819.8
32.5°	774.2	768.8	763.5	763.5	759.4	759.4	760.8	763.5	770.2	771.5	778.2
35°	733.9	728.6	724.5	721.9	723.2	717.8	720.5	724.5	732.6	735.3	739.3
37.5°	695.0	693.7	685.6	681.6	684.3	684.3	682.9	685.6	691.0	696.4	699.1
40°	652.1	649.4	649.4	645.4	646.7	641.4	645.4	648.1	650.7	656.1	660.1
42.5°	614.5	611.8	606.5	607.8	603.8	603.8	606.5	607.8	611.8	618.5	621.2
45°	574.3	574.3	571.6	567.6	568.9	564.9	567.6	568.9	574.3	581.0	578.3
47.5°	535.4	534.0	534.0	528.6	531.3	527.3	531.3	532.7	535.4	539.4	538.0
50°	497.8	493.8	495.1	493.8	492.4	492.4	495.1	495.1	497.8	497.8	501.8
52.5°	458.9	458.9	456.2	457.5	460.2	457.5	461.6	457.5	460.2	461.6	464.2
55°	424.0	421.3	422.7	421.3	426.7	422.7	426.7	424.0	426.7	425.3	428.0
57.5°	386.4	382.4	383.7	382.4	386.4	385.1	389.1	385.1	386.4	387.8	391.8
60°	343.5	343.5	343.5	340.8	344.8	344.8	343.5	343.5	348.9	351.5	350.2
62.5°	303.2	301.9	297.9	296.5	297.9	295.2	300.6	299.2	301.9	304.6	307.3
65°	259.0	256.3	254.9	252.2	252.2	250.9	252.2	257.6	259.0	260.3	267.0
67.5°	222.7	221.4	220.0	216.0	216.0	218.7	218.7	218.7	226.8	222.7	228.1
70°	190.5	187.8	185.2	183.8	183.8	185.2	186.5	187.8	186.5	191.9	193.2
72.5°	159.7	161.0	158.3	158.3	158.3	157.0	157.0	159.7	161.0	159.7	161.0
75°	132.8	132.8	131.5	132.8	132.8	131.5	131.5	134.2	134.2	132.8	136.9
77.5°	107.3	106.0	103.3	100.6	102.0	100.6	102.0	100.6	104.7	108.7	106.0
80°	75.1	73.8	73.8	73.8	75.1	73.8	76.5	73.8	75.1	75.1	76.5
82.5°	53.7	55.0	55.0	53.7	55.0	53.7	55.0	55.0	55.0	53.7	55.0
85°	34.9	34.9	34.9	34.9	33.5	34.9	34.9	34.9	36.2	34.9	36.2
87.5°	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8	16.1	14.8	16.1
90°	15.8	16.1	16.6	17.1	17.6	18.1	17.6	17.1	16.6	16.1	15.8
92.5°	15.8	15.9	16.1	16.2	16.4	16.6	16.4	16.2	16.1	15.9	15.8
95°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
97.5°	15.1	15.2	15.3	15.5	15.6	15.8	15.6	15.5	15.3	15.2	15.1
100°	18.8	18.5	17.8	17.1	16.5	15.8	16.5	17.1	17.8	18.5	18.8
102.5°	177.9	170.9	156.8	142.7	128.7	114.6	128.7	142.7	156.8	170.9	177.9
105°	224.6	224.5	224.4	224.2	224.1	223.9	224.1	224.2	224.4	224.5	224.6
107.5°	275.1	274.8	274.1	273.4	272.8	272.1	272.8	273.4	274.1	274.8	275.1
110°	321.9	322.0	322.1	322.3	322.4	322.6	322.4	322.3	322.1	322.0	321.9

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	369.3	369.1	368.8	368.5	368.1	367.8	368.1	368.5	368.8	369.1	369.3
115°	417.6	417.1	416.1	415.1	414.1	413.1	414.1	415.1	416.1	417.1	417.6
117.5°	463.6	463.4	463.1	462.8	462.4	462.1	462.4	462.8	463.1	463.4	463.6
120°	510.3	509.9	509.0	508.2	507.3	506.5	507.3	508.2	509.0	509.9	510.3
122.5°	553.3	552.8	551.8	550.7	549.7	548.7	549.7	550.7	551.8	552.8	553.3
125°	594.0	593.7	593.2	592.7	592.2	591.7	592.2	592.7	593.2	593.7	594.0
127.5°	633.2	632.5	631.2	629.8	628.5	627.1	628.5	629.8	631.2	632.5	633.2
130°	670.1	669.7	668.8	668.0	667.1	666.3	667.1	668.0	668.8	669.7	670.1
132.5°	706.3	705.9	705.0	704.2	703.3	702.5	703.3	704.2	705.0	705.9	706.3
135°	739.4	738.9	737.9	736.9	735.9	734.9	735.9	736.9	737.9	738.9	739.4
137.5°	772.6	772.2	771.3	770.5	769.6	768.8	769.6	770.5	771.3	772.2	772.6
140°	802.8	802.3	801.3	800.2	799.2	798.2	799.2	800.2	801.3	802.3	802.8
142.5°	830.7	830.2	829.2	828.1	827.1	826.1	827.1	828.1	829.2	830.2	830.7
145°	857.8	857.3	856.3	855.3	854.3	853.3	854.3	855.3	856.3	857.3	857.8
147.5°	881.2	880.6	879.4	878.3	877.1	875.9	877.1	878.3	879.4	880.6	881.2
150°	903.8	903.1	901.8	900.4	899.1	897.7	899.1	900.4	901.8	903.1	903.8
152.5°	923.4	922.8	921.6	920.5	919.3	918.1	919.3	920.5	921.6	922.8	923.4
155°	941.5	940.8	939.5	938.1	936.8	935.4	936.8	938.1	939.5	940.8	941.5
157.5°	956.5	955.8	954.5	953.2	951.8	950.5	951.8	953.2	954.5	955.8	956.5
160°	970.9	970.2	968.9	967.5	966.2	964.8	966.2	967.5	968.9	970.2	970.9
162.5°	984.4	983.6	982.1	980.6	979.1	977.6	979.1	980.6	982.1	983.6	984.4
165°	995.0	994.3	993.0	991.6	990.3	988.9	990.3	991.6	993.0	994.3	995.0
167.5°	1004.0	1003.2	1001.7	1000.2	998.7	997.2	998.7	1000.2	1001.7	1003.2	1004.0
170°	1010.8	1010.0	1008.5	1007.0	1005.5	1004.0	1005.5	1007.0	1008.5	1010.0	1010.8
172.5°	1015.3	1014.5	1013.0	1011.5	1010.0	1008.5	1010.0	1011.5	1013.0	1014.5	1015.3
175°	1019.1	1018.3	1016.8	1015.3	1013.8	1012.3	1013.8	1015.3	1016.8	1018.3	1019.1
177.5°	1020.6	1019.9	1018.6	1017.3	1015.9	1014.6	1015.9	1017.3	1018.6	1019.9	1020.6
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2	1634.2
2.5°	1545.7	1552.4	1547.0	1543.0	1553.7	1559.1	1559.1	1568.5	1577.9	1585.9	1587.3
5°	1450.4	1461.2	1463.8	1462.5	1478.6	1486.7	1504.1	1513.5	1526.9	1536.3	1547.0
7.5°	1363.2	1378.0	1379.3	1382.0	1406.2	1419.6	1434.3	1458.5	1477.3	1490.7	1502.8
10°	1276.0	1285.4	1294.8	1306.9	1331.0	1353.8	1375.3	1400.8	1424.9	1438.4	1455.8
12.5°	1210.3	1217.0	1227.7	1235.7	1261.2	1281.4	1309.5	1344.4	1379.3	1390.0	1411.5
15°	1141.8	1145.9	1167.3	1175.4	1196.8	1230.4	1247.8	1281.4	1318.9	1339.1	1363.2
17.5°	1062.7	1086.8	1100.2	1109.6	1136.5	1163.3	1191.5	1226.4	1274.7	1293.4	1310.9
20°	1006.3	1023.8	1038.5	1050.6	1074.7	1115.0	1140.5	1168.7	1214.3	1235.7	1261.2
22.5°	956.7	971.4	984.8	998.3	1014.4	1050.6	1080.1	1119.0	1164.6	1184.8	1214.3
25°	909.7	924.5	932.5	948.6	970.1	995.6	1030.5	1065.3	1111.0	1133.8	1162.0
27.5°	864.1	878.8	893.6	907.0	921.8	945.9	970.1	1014.4	1061.3	1088.2	1112.3
30°	825.2	831.9	845.3	860.1	874.8	897.6	925.8	956.7	1010.3	1034.5	1064.0
32.5°	782.2	794.3	803.7	814.4	833.2	852.0	877.5	916.4	959.3	982.2	1014.4
35°	742.0	752.7	759.4	778.2	790.3	810.4	835.9	870.8	907.0	932.5	960.7
37.5°	703.1	713.8	721.9	732.6	748.7	766.1	793.0	818.5	861.4	882.9	915.1
40°	662.8	672.2	681.6	693.7	708.4	729.9	746.0	778.2	813.1	837.3	861.4
42.5°	623.9	629.3	640.0	653.4	668.2	687.0	709.8	735.3	770.2	791.6	813.1
45°	582.3	591.7	603.8	613.2	626.6	645.4	665.5	688.3	723.2	744.7	767.5
47.5°	543.4	550.1	558.2	572.9	590.4	603.8	625.3	646.7	678.9	699.1	720.5
50°	503.2	509.9	521.9	531.3	544.7	562.2	582.3	605.1	636.0	649.4	670.9
52.5°	465.6	468.3	480.3	489.7	503.2	523.3	539.4	559.5	589.0	603.8	625.3
55°	428.0	430.7	437.4	446.8	461.6	477.7	495.1	517.9	543.4	556.8	577.0
57.5°	389.1	391.8	398.5	405.2	420.0	434.7	454.9	473.6	499.1	511.2	530.0
60°	350.2	350.2	356.9	366.3	377.0	390.4	407.9	430.7	449.5	464.2	477.7
62.5°	308.6	312.6	316.7	323.4	335.4	351.5	366.3	382.4	405.2	415.9	428.0
65°	267.0	271.0	279.1	285.8	295.2	305.9	324.7	338.1	355.6	367.6	378.4
67.5°	230.8	234.8	240.2	248.2	254.9	267.0	280.4	293.8	312.6	320.7	328.7
70°	193.2	197.2	201.3	212.0	218.7	228.1	237.5	250.9	267.0	272.4	279.1
72.5°	163.7	165.0	170.4	173.1	182.5	190.5	201.3	209.3	221.4	228.1	233.5
75°	138.2	138.2	139.5	142.2	147.6	153.0	161.0	169.1	179.8	183.8	190.5
77.5°	108.7	112.7	111.4	114.0	116.7	119.4	126.1	131.5	142.2	144.9	147.6
80°	77.8	79.2	83.2	87.2	87.2	91.2	95.3	96.6	103.3	107.3	107.3
82.5°	56.4	57.7	56.4	57.7	59.0	60.4	64.4	69.8	69.8	71.1	73.8
85°	34.9	34.9	36.2	37.6	37.6	36.2	38.9	37.6	38.9	41.6	41.6
87.5°	17.4	16.1	16.1	16.1	16.1	16.1	17.4	16.1	17.4	17.4	17.4
90°	15.4	14.6	13.7	12.9	12.1	10.9	9.7	8.6	7.4	6.8	6.1
92.5°	15.4	14.6	13.7	12.9	12.1	11.1	10.1	9.0	8.0	7.5	8.3
95°	15.4	14.6	13.7	12.9	12.1	18.5	24.8	31.2	37.5	40.7	41.0
97.5°	14.9	14.6	14.3	13.9	13.6	29.5	45.4	61.3	77.2	85.2	84.7
100°	31.3	56.3	81.2	106.2	131.2	130.5	129.8	129.1	128.4	128.1	127.9
102.5°	177.7	177.4	177.1	176.7	176.4	176.1	175.7	175.4	175.1	174.9	174.6
105°	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.3
107.5°	275.0	274.9	274.7	274.6	274.4	274.1	273.7	273.4	273.1	272.9	272.9
110°	322.1	322.6	323.1	323.6	324.1	323.8	323.4	323.1	322.8	322.6	322.6

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	369.6	370.3	371.0	371.7	372.4	372.2	372.0	371.9	371.7	371.6	371.3
115°	417.9	418.6	419.3	419.9	420.6	420.4	420.2	420.1	419.9	419.8	419.4
117.5°	464.1	465.1	466.1	467.1	468.1	467.4	466.8	466.1	465.4	465.1	465.1
120°	510.5	510.8	511.1	511.5	511.8	511.3	510.8	510.3	509.8	509.5	509.6
122.5°	553.5	553.8	554.1	554.5	554.8	554.6	554.4	554.3	554.1	554.0	553.6
125°	594.3	595.0	595.7	596.3	597.0	597.0	597.0	597.0	597.0	597.0	596.4
127.5°	633.4	633.7	634.0	634.4	634.7	634.9	635.0	635.2	635.3	635.4	635.0
130°	670.4	670.9	671.4	671.9	672.4	672.2	672.0	671.9	671.7	671.6	671.2
132.5°	706.3	706.3	706.3	706.3	706.3	706.8	707.3	707.8	708.3	708.5	708.0
135°	739.6	739.9	740.3	740.6	741.0	741.3	741.7	742.0	742.3	742.5	742.0
137.5°	772.6	772.6	772.6	772.6	772.6	772.9	773.3	773.6	773.9	774.1	773.6
140°	802.6	802.3	802.0	801.6	801.3	801.5	801.6	801.8	801.9	802.0	801.8
142.5°	830.7	830.7	830.7	830.7	830.7	830.3	830.0	829.6	829.3	829.1	829.0
145°	857.7	857.5	857.4	857.2	857.0	857.0	857.0	857.0	857.0	857.0	856.8
147.5°	881.1	880.9	880.8	880.6	880.4	880.2	880.0	879.9	879.7	879.6	879.6
150°	903.6	903.3	903.0	902.6	902.3	902.0	901.6	901.3	901.0	900.8	901.0
152.5°	923.2	922.9	922.6	922.2	921.9	921.5	921.2	920.8	920.5	920.3	920.7
155°	941.2	940.7	940.2	939.7	939.2	938.9	938.5	938.2	937.9	937.7	938.2
157.5°	956.3	955.8	955.3	954.8	954.3	954.3	954.3	954.3	954.3	954.3	954.5
160°	970.6	969.9	969.2	968.5	967.8	967.6	967.5	967.3	967.2	967.1	967.6
162.5°	983.9	982.9	981.9	980.9	979.9	979.7	979.5	979.4	979.2	979.1	979.6
165°	994.5	993.5	992.4	991.4	990.4	990.2	990.1	989.9	989.8	989.7	990.2
167.5°	1003.4	1002.2	1001.1	999.9	998.7	998.5	998.4	998.2	998.1	998.0	998.5
170°	1010.1	1008.8	1007.5	1006.1	1004.8	1004.6	1004.4	1004.3	1004.1	1004.0	1004.6
172.5°	1014.7	1013.5	1012.4	1011.2	1010.0	1009.7	1009.3	1009.0	1008.7	1008.5	1009.1
175°	1018.4	1017.1	1015.8	1014.4	1013.1	1012.9	1012.7	1012.6	1012.4	1012.3	1012.8
177.5°	1020.0	1018.8	1017.7	1016.5	1015.3	1015.1	1015.0	1014.8	1014.7	1014.6	1015.1
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1634.2	1634.2	1634.2	1634.2
2.5°	1596.7	1608.8	1620.8	1635.6
5°	1564.5	1585.9	1608.8	1630.2
7.5°	1529.6	1560.5	1590.0	1620.8
10°	1490.7	1529.6	1563.1	1606.1
12.5°	1447.7	1489.3	1536.3	1584.6
15°	1404.8	1457.1	1506.8	1561.8
17.5°	1364.6	1414.2	1469.2	1535.0
20°	1316.3	1371.3	1433.0	1502.8
22.5°	1265.3	1325.6	1392.7	1467.9
25°	1222.3	1284.1	1348.5	1427.6
27.5°	1175.4	1239.8	1302.8	1387.4
30°	1121.7	1191.5	1255.9	1343.1
32.5°	1070.7	1140.5	1211.6	1293.4
35°	1021.1	1089.5	1160.6	1243.8
37.5°	974.1	1035.8	1105.6	1180.7
40°	929.8	986.2	1047.9	1116.3
42.5°	873.5	939.2	996.9	1046.6
45°	825.2	878.8	932.5	972.8
47.5°	768.8	822.5	868.1	900.3
50°	721.9	764.8	802.4	830.5
52.5°	665.5	705.8	736.6	758.1
55°	610.5	645.4	672.2	687.0
57.5°	560.9	583.7	603.8	617.2
60°	505.8	523.3	540.7	555.5
62.5°	446.8	465.6	475.0	491.1
65°	394.5	406.5	421.3	426.7
67.5°	343.5	350.2	359.6	370.3
70°	289.8	293.8	303.2	318.0
72.5°	242.9	246.9	253.6	259.0
75°	193.2	197.2	202.6	208.0
77.5°	151.6	153.0	155.6	161.0
80°	110.0	114.0	116.7	118.1
82.5°	76.5	77.8	77.8	79.2
85°	48.3	45.6	45.6	47.0
87.5°	17.4	20.1	20.1	22.8
90°	4.8	3.5	2.1	0.8
92.5°	9.8	11.3	12.8	14.3
95°	41.5	42.0	42.5	43.0
97.5°	83.7	82.7	81.7	80.7
100°	127.4	126.9	126.4	125.9
102.5°	173.9	173.2	172.6	171.9
105°	223.6	222.9	222.3	221.6
107.5°	272.9	272.9	272.9	272.9
110°	322.6	322.6	322.6	322.6



TEST NUMBER: P1035756

CATALOG NUMBER: S125RDIW-B1090D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	370.8	370.3	369.8	369.3
115°	418.6	417.7	416.9	416.1
117.5°	465.1	465.1	465.1	465.1
120°	509.8	509.9	510.1	510.3
122.5°	552.7	551.9	551.0	550.2
125°	595.2	594.1	592.9	591.7
127.5°	634.2	633.3	632.5	631.7
130°	670.3	669.5	668.6	667.8
132.5°	707.0	706.0	705.0	704.0
135°	741.0	739.9	738.9	737.9
137.5°	772.6	771.6	770.6	769.6
140°	801.5	801.2	800.8	800.5
142.5°	828.9	828.7	828.6	828.4
145°	856.5	856.2	855.8	855.5
147.5°	879.6	879.6	879.6	879.6
150°	901.3	901.6	902.0	902.3
152.5°	921.6	922.4	923.3	924.1
155°	939.2	940.2	941.2	942.2
157.5°	955.0	955.5	956.0	956.5
160°	968.6	969.6	970.6	971.6
162.5°	980.6	981.7	982.7	983.7
165°	991.2	992.2	993.2	994.2
167.5°	999.5	1000.5	1001.5	1002.5
170°	1005.8	1006.9	1008.1	1009.3
172.5°	1010.3	1011.4	1012.6	1013.8
175°	1013.8	1014.8	1015.8	1016.8
177.5°	1016.1	1017.1	1018.1	1019.1
180°	1016.8	1016.8	1016.8	1016.8

(END OF REPORT)