

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035862

Luminaire Tested: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035862
REPORT IS A COMBINATION OF REPORTS P1006347 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D770UB40-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8010.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66
1	101	97	93	90	94	91	87	84	79	77	75	69	67	66	60	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	47	45	42
4	77	67	59	53	72	63	56	51	56	50	46	49	45	41	43	39	37
5	71	60	52	46	67	56	49	44	50	44	40	44	40	36	39	35	32
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	44	37	31	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	33	28	49	38	32	27	34	29	25	31	26	23	27	23	21
10	49	37	30	25	46	35	29	24	32	26	22	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12125	12125	12125	12125
5°	12115	13665	12115	10504
10°	12047	15357	12006	9080
15°	11917	16247	11834	7906
20°	11758	17539	11653	7146
25°	11553	19852	11422	6486
30°	11343	21101	11173	6013
35°	11072	17354	10916	5573
40°	10590	11785	10501	5177
45°	9958	8471	9944	4787
50°	9310	6514	9354	4427
55°	8580	5297	8564	4080
60°	7901	4342	7862	3623
65°	7110	3618	7154	2916
70°	6454	2904	6428	2428
75°	5452	2199	5452	1996
80°	4417	1342	4369	1342
85°	3110	705	3019	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17260 cd/sqm

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.5	2.3
10°-20°	532.1	6.6
20°-30°	843.6	10.5
30°-40°	1019.4	12.7
40°-50°	907.6	11.3
50°-60°	696.0	8.7
60°-70°	452.0	5.6
70°-80°	219.4	2.7
80°-90°	53.1	0.7
90°-100°	34.3	0.4
100°-110°	228.2	2.8
110°-120°	410.9	5.1
120°-130°	527.4	6.6
130°-140°	567.2	7.1
140°-150°	532.4	6.6
150°-160°	430.6	5.4
160°-170°	278.5	3.5
170°-180°	96.0	1.2
0°-30°	1557.1	19.4
0°-40°	2576.5	32.2
0°-60°	4180.0	52.2
0°-90°	4904.5	61.2
90°-120°	673.4	8.4
90°-150°	2300.3	28.7
90°-180°	3106.0	38.8
0°-180°	8010.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1892	1892	1892	1892	1892	
5°	1888	2169	1888	1667	1888	179
15°	1809	2606	1796	1268	1809	510
25°	1653	3120	1634	1019	1653	762
35°	1440	2589	1420	831	1440	897
45°	1126	1158	1125	654	1126	869
55°	796	636	794	489	796	713
65°	494	360	497	291	494	494
75°	241	168	241	152	241	258
85°	54	36	53	40	54	62
90°	1	18	1	18	1	6
95°	43	16	43	16	43	52
105°	220	223	220	223	220	233
115°	414	411	414	411	414	410
125°	588	588	588	588	588	526
135°	734	731	734	731	734	566
145°	851	848	851	848	851	532
155°	937	930	937	930	937	432
165°	988	983	988	983	988	279
175°	1011	1006	1011	1006	1011	96
180°	1011	1011	1011	1011	1011	

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1894.0	1909.6	1914.2	1926.7	1940.6	1943.7	1951.5	1962.4	1968.6	1967.1	1967.1
5°	1887.8	1914.2	1932.9	1954.6	1981.0	1991.9	2001.2	2024.5	2043.2	2054.1	2072.7
7.5°	1876.9	1915.8	1946.9	1979.5	2019.9	2038.5	2058.7	2091.4	2125.5	2147.3	2167.5
10°	1859.8	1909.6	1953.1	2001.2	2055.6	2083.6	2108.4	2158.2	2200.1	2228.1	2274.7
12.5°	1835.0	1897.1	1957.7	2021.4	2089.8	2119.3	2153.5	2207.9	2266.9	2307.3	2346.2
15°	1808.6	1883.1	1948.4	2024.5	2106.9	2151.9	2195.5	2252.9	2305.8	2350.8	2395.9
17.5°	1777.5	1856.7	1937.5	2024.5	2117.8	2162.8	2200.1	2268.5	2324.4	2369.5	2409.9
20°	1740.2	1828.8	1920.4	2016.8	2111.5	2153.5	2189.2	2263.8	2313.5	2361.7	2419.2
22.5°	1699.8	1796.1	1894.0	1988.8	2082.0	2127.1	2169.0	2234.3	2288.7	2353.9	2428.5
25°	1653.2	1758.8	1858.3	1953.1	2041.6	2083.6	2120.9	2192.3	2268.5	2350.8	2434.7
27.5°	1606.6	1709.1	1805.5	1892.5	1988.8	2027.6	2064.9	2155.1	2245.2	2332.2	2447.2
30°	1555.3	1659.4	1743.3	1824.1	1917.3	1957.7	2004.3	2106.9	2209.4	2327.5	2467.4
32.5°	1497.8	1592.6	1670.3	1754.2	1838.1	1887.8	1946.9	2058.7	2176.8	2318.2	2496.9
35°	1440.3	1516.5	1587.9	1667.2	1768.2	1821.0	1878.5	1996.6	2144.2	2313.5	2521.7
37.5°	1367.3	1440.3	1496.3	1577.1	1681.2	1743.3	1800.8	1937.5	2105.3	2302.7	2520.2
40°	1292.7	1354.9	1407.7	1491.6	1605.0	1662.5	1724.7	1873.8	2064.9	2271.6	2482.9
42.5°	1211.9	1264.8	1322.2	1403.0	1513.4	1569.3	1640.8	1814.8	2009.0	2228.1	2386.6
45°	1126.5	1177.7	1225.9	1309.8	1420.1	1480.7	1558.4	1737.1	1940.6	2136.4	2231.2
47.5°	1042.6	1087.6	1138.9	1211.9	1323.8	1390.6	1469.8	1661.0	1849.0	2013.7	2021.4
50°	961.8	997.5	1041.0	1115.6	1232.1	1295.8	1378.2	1556.9	1740.2	1853.6	1777.5
52.5°	877.9	910.5	955.6	1020.8	1129.6	1204.2	1275.6	1454.3	1608.1	1684.3	1544.4
55°	795.5	823.5	870.1	943.1	1037.9	1095.4	1168.4	1334.7	1469.8	1471.4	1319.1
57.5°	714.7	739.6	778.4	843.7	932.3	999.1	1065.9	1210.4	1302.0	1275.6	1106.3
60°	643.3	658.8	694.5	758.2	840.6	888.7	960.2	1081.4	1142.0	1093.8	912.1
62.5°	568.7	584.2	612.2	663.5	741.1	792.4	837.5	936.9	978.9	905.8	756.7
65°	494.1	512.7	532.9	573.3	646.4	680.5	720.9	794.0	834.4	748.9	619.9
67.5°	428.8	438.2	458.4	500.3	551.6	582.7	610.6	660.3	668.1	599.7	494.1
70°	368.2	371.3	390.0	414.9	453.7	472.3	495.6	525.2	525.2	469.2	385.3
72.5°	299.9	304.5	318.5	344.9	368.2	377.6	385.3	404.0	400.9	349.6	292.1
75°	240.8	243.9	254.8	267.2	276.6	293.7	299.9	296.8	295.2	251.7	219.1
77.5°	186.5	188.0	195.8	206.6	208.2	214.4	209.8	209.8	195.8	170.9	153.8
80°	136.7	138.3	141.4	144.5	144.5	144.5	144.5	136.7	127.4	111.9	107.2
82.5°	91.7	91.7	93.2	96.3	94.8	91.7	88.6	80.8	74.6	69.9	66.8
85°	54.4	54.4	55.9	54.4	48.2	46.6	43.5	42.0	40.4	38.8	38.8
87.5°	26.4	24.9	21.8	18.6	18.6	18.6	18.6	18.6	18.6	17.1	17.1
90°	0.7	2.0	3.4	4.7	6.0	6.7	7.3	8.5	9.6	10.8	12.0
92.5°	14.2	12.7	11.2	9.7	8.2	7.5	8.0	9.0	10.0	11.0	12.0
95°	42.7	42.2	41.7	41.2	40.7	40.5	37.3	31.0	24.7	18.3	12.0
97.5°	80.2	81.2	82.2	83.2	84.2	84.7	76.8	61.0	45.1	29.3	13.5
100°	125.2	125.7	126.2	126.7	127.2	127.4	127.7	128.4	129.1	129.7	130.4
102.5°	170.9	171.6	172.2	172.9	173.6	173.9	174.1	174.4	174.7	175.1	175.4
105°	220.3	221.0	221.6	222.3	223.0	223.3	223.3	223.3	223.3	223.3	223.3
107.5°	271.3	271.3	271.3	271.3	271.3	271.3	271.5	271.8	272.1	272.5	272.8
110°	320.8	320.8	320.8	320.8	320.8	320.8	321.0	321.3	321.6	322.0	322.3

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	367.2	367.7	368.2	368.7	369.2	369.5	369.6	369.7	369.9	370.0	370.2
115°	413.7	414.5	415.3	416.2	417.0	417.4	417.5	417.7	417.8	418.0	418.2
117.5°	462.4	462.4	462.4	462.4	462.4	462.4	462.7	463.4	464.1	464.7	465.4
120°	507.4	507.2	507.0	506.9	506.7	506.6	506.9	507.4	507.9	508.4	508.9
122.5°	547.1	547.9	548.7	549.6	550.4	550.8	550.9	551.1	551.2	551.4	551.6
125°	588.3	589.5	590.6	591.8	592.9	593.5	593.5	593.5	593.5	593.5	593.5
127.5°	628.0	628.8	629.7	630.5	631.4	631.8	631.7	631.5	631.4	631.2	631.0
130°	664.0	664.8	665.6	666.5	667.3	667.7	667.8	668.0	668.1	668.3	668.5
132.5°	700.0	701.0	702.0	703.0	704.0	704.5	704.2	703.7	703.2	702.7	702.2
135°	733.7	734.7	735.7	736.7	737.7	738.2	738.0	737.7	737.4	737.0	736.7
137.5°	765.2	766.2	767.2	768.2	769.2	769.7	769.5	769.2	768.9	768.5	768.2
140°	795.9	796.2	796.6	796.9	797.2	797.4	797.3	797.1	797.0	796.8	796.6
142.5°	823.6	823.8	824.0	824.1	824.3	824.4	824.6	824.9	825.2	825.6	825.9
145°	850.6	850.9	851.3	851.6	851.9	852.1	852.1	852.1	852.1	852.1	852.1
147.5°	874.6	874.6	874.6	874.6	874.6	874.6	874.7	874.8	875.0	875.1	875.3
150°	897.1	896.8	896.4	896.1	895.8	895.6	895.8	896.1	896.4	896.8	897.1
152.5°	918.8	918.0	917.1	916.3	915.4	915.0	915.2	915.5	915.8	916.2	916.5
155°	936.8	935.8	934.8	933.8	932.8	932.3	932.5	932.8	933.1	933.5	933.8
157.5°	951.0	950.5	950.0	949.5	949.0	948.8	948.8	948.8	948.8	948.8	948.8
160°	966.0	965.0	964.0	963.0	962.0	961.5	961.6	961.8	961.9	962.1	962.3
162.5°	978.0	977.0	976.0	975.0	974.0	973.5	973.6	973.8	973.9	974.1	974.3
165°	988.5	987.5	986.5	985.5	984.5	984.0	984.1	984.2	984.4	984.5	984.7
167.5°	996.7	995.7	994.7	993.7	992.7	992.2	992.3	992.5	992.6	992.8	993.0
170°	1003.5	1002.3	1001.1	1000.0	998.8	998.2	998.3	998.5	998.6	998.8	999.0
172.5°	1008.0	1006.8	1005.6	1004.5	1003.3	1002.7	1002.9	1003.2	1003.5	1003.9	1004.2
175°	1011.0	1010.0	1009.0	1008.0	1007.0	1006.5	1006.6	1006.7	1006.9	1007.0	1007.2
177.5°	1013.2	1012.2	1011.2	1010.2	1009.2	1008.7	1008.8	1009.0	1009.1	1009.3	1009.5
180°	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1974.8	1985.7	1995.0	1990.4	2009.0	2007.4	2010.6	2016.8	2018.3	2015.2	2009.0
5°	2082.0	2097.6	2124.0	2138.0	2134.9	2147.3	2153.5	2162.8	2172.1	2169.0	2169.0
7.5°	2201.7	2223.4	2249.8	2285.6	2290.2	2301.1	2319.8	2319.8	2330.6	2326.0	2324.4
10°	2305.8	2332.2	2374.1	2402.1	2414.5	2420.7	2439.4	2445.6	2458.0	2459.6	2459.6
12.5°	2391.2	2437.8	2465.8	2493.8	2500.0	2509.3	2523.3	2532.6	2537.3	2537.3	2532.6
15°	2436.3	2473.6	2506.2	2535.7	2552.8	2560.6	2574.6	2585.4	2591.7	2605.6	2608.7
17.5°	2454.9	2500.0	2552.8	2594.8	2624.3	2632.1	2660.0	2669.3	2681.8	2688.0	2695.8
20°	2481.3	2546.6	2610.3	2661.6	2689.5	2709.7	2739.3	2782.8	2795.2	2795.2	2790.5
22.5°	2504.6	2588.6	2675.6	2757.9	2781.2	2821.6	2876.0	2922.6	2941.3	2949.0	2942.8
25°	2532.6	2647.6	2761.0	2863.6	2927.3	2956.8	3029.8	3085.8	3107.5	3119.9	3123.0
27.5°	2580.8	2725.3	2869.8	3000.3	3065.6	3099.7	3175.9	3224.0	3250.4	3261.3	3253.6
30°	2635.2	2812.3	2980.1	3096.6	3140.1	3182.1	3231.8	3250.4	3244.2	3244.2	3267.5
32.5°	2691.1	2874.4	3023.6	3099.7	3115.3	3109.1	3088.9	3032.9	3000.3	3000.3	3020.5
35°	2722.2	2880.7	2956.8	2931.9	2871.3	2835.6	2725.3	2663.1	2593.2	2588.6	2611.9
37.5°	2705.1	2773.4	2742.4	2579.2	2496.9	2428.5	2256.0	2187.7	2136.4	2064.9	2175.3
40°	2585.4	2562.1	2400.5	2165.9	2074.3	1977.9	1841.2	1772.8	1701.4	1690.5	1716.9
42.5°	2383.5	2245.2	2009.0	1782.2	1688.9	1620.6	1516.5	1449.7	1404.6	1385.9	1417.0
45°	2131.7	1914.2	1678.1	1497.8	1395.3	1359.5	1264.8	1205.7	1171.5	1157.5	1179.3
47.5°	1824.1	1605.0	1381.3	1229.0	1168.4	1132.7	1069.0	1017.7	988.2	978.9	988.2
50°	1549.1	1323.8	1135.8	1037.9	983.5	954.0	901.2	868.5	845.2	839.0	854.6
52.5°	1311.4	1106.3	963.3	876.3	840.6	815.7	778.4	750.5	736.5	730.3	741.1
55°	1098.5	932.3	817.3	742.7	716.3	700.7	668.1	652.6	637.0	635.5	646.4
57.5°	910.5	795.5	689.9	637.0	629.3	606.0	578.0	564.0	556.2	554.7	559.4
60°	758.2	655.7	592.0	545.4	534.5	515.8	500.3	491.0	481.7	478.6	481.7
62.5°	630.8	550.0	498.8	467.7	452.1	447.5	430.4	419.5	418.0	418.0	421.1
65°	520.5	452.1	419.5	394.7	383.8	379.1	366.7	358.9	360.5	360.5	362.0
67.5°	424.2	374.5	344.9	332.5	323.2	321.6	309.2	306.1	303.0	303.0	306.1
70°	337.2	306.1	284.3	278.1	276.6	265.7	261.0	259.5	254.8	256.4	256.4
72.5°	264.1	243.9	231.5	222.2	223.7	217.5	211.3	211.3	208.2	212.9	212.9
75°	195.8	186.5	177.1	174.0	177.1	174.0	169.4	167.8	169.4	167.8	167.8
77.5°	144.5	139.8	136.7	135.2	135.2	129.0	125.9	129.0	122.7	125.9	125.9
80°	101.0	94.8	93.2	90.1	91.7	87.0	88.6	85.5	85.5	85.5	85.5
82.5°	63.7	62.2	62.2	62.2	60.6	60.6	60.6	60.6	60.6	60.6	59.0
85°	38.8	37.3	37.3	37.3	35.7	35.7	35.7	35.7	35.7	35.7	35.7
87.5°	15.5	17.1	17.1	18.6	17.1	15.5	15.5	15.5	17.1	17.1	15.5
90°	12.8	13.6	14.5	15.3	15.7	16.0	16.5	17.0	17.5	18.0	17.5
92.5°	12.8	13.6	14.5	15.3	15.7	15.8	16.0	16.1	16.3	16.5	16.3
95°	12.8	13.6	14.5	15.3	15.7	15.7	15.7	15.7	15.7	15.7	15.7
97.5°	13.8	14.2	14.5	14.8	15.0	15.1	15.2	15.4	15.5	15.7	15.5
100°	105.6	80.8	55.9	31.1	18.7	18.4	17.7	17.0	16.4	15.7	16.4
102.5°	175.7	176.1	176.4	176.7	176.9	169.9	155.9	141.9	127.9	113.9	127.9
105°	223.3	223.3	223.3	223.3	223.3	223.2	223.1	222.9	222.8	222.6	222.8
107.5°	273.0	273.1	273.3	273.4	273.5	273.2	272.5	271.8	271.2	270.5	271.2
110°	321.8	321.3	320.8	320.3	320.0	320.1	320.3	320.4	320.6	320.8	320.6

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	369.5	368.9	368.2	367.5	367.2	367.0	366.7	366.4	366.0	365.7	366.0
115°	417.5	416.9	416.2	415.5	415.2	414.7	413.7	412.7	411.7	410.7	411.7
117.5°	464.4	463.4	462.4	461.4	460.9	460.7	460.4	460.1	459.7	459.4	459.7
120°	508.6	508.2	507.9	507.6	507.4	507.0	506.1	505.3	504.4	503.6	504.4
122.5°	551.3	550.9	550.6	550.3	550.1	549.6	548.6	547.6	546.6	545.6	546.6
125°	592.8	592.2	591.5	590.8	590.5	590.3	589.8	589.3	588.8	588.3	588.8
127.5°	630.7	630.3	630.0	629.7	629.5	628.8	627.5	626.2	624.8	623.5	624.8
130°	668.0	667.5	667.0	666.5	666.2	665.8	665.0	664.1	663.3	662.5	663.3
132.5°	702.2	702.2	702.2	702.2	702.2	701.8	701.0	700.1	699.3	698.5	699.3
135°	736.4	736.0	735.7	735.4	735.2	734.7	733.7	732.7	731.7	730.7	731.7
137.5°	768.2	768.2	768.2	768.2	768.2	767.8	766.9	766.1	765.2	764.4	765.2
140°	796.9	797.3	797.6	797.9	798.1	797.6	796.6	795.6	794.6	793.6	794.6
142.5°	825.9	825.9	825.9	825.9	825.9	825.4	824.4	823.4	822.4	821.4	822.4
145°	852.3	852.4	852.6	852.7	852.8	852.3	851.3	850.3	849.3	848.3	849.3
147.5°	875.5	875.7	875.8	876.0	876.1	875.5	874.3	873.2	872.0	870.8	872.0
150°	897.4	897.8	898.1	898.4	898.6	897.9	896.6	895.3	893.9	892.6	893.9
152.5°	916.8	917.2	917.5	917.8	918.0	917.4	916.3	915.1	914.0	912.8	914.0
155°	934.3	934.8	935.3	935.8	936.0	935.3	934.0	932.7	931.3	930.0	931.3
157.5°	949.3	949.8	950.3	950.8	951.0	950.3	949.0	947.7	946.3	945.0	946.3
160°	963.0	963.6	964.3	965.0	965.3	964.6	963.3	962.0	960.6	959.3	960.6
162.5°	975.3	976.3	977.2	978.2	978.7	978.0	976.5	975.0	973.5	972.0	973.5
165°	985.7	986.7	987.7	988.7	989.2	988.5	987.2	985.9	984.5	983.2	984.5
167.5°	994.2	995.3	996.5	997.6	998.2	997.5	996.0	994.5	993.0	991.5	993.0
170°	1000.3	1001.7	1003.0	1004.3	1005.0	1004.2	1002.7	1001.2	999.7	998.2	999.7
172.5°	1005.4	1006.6	1007.7	1008.9	1009.5	1008.7	1007.2	1005.7	1004.2	1002.7	1004.2
175°	1008.5	1009.9	1011.2	1012.5	1013.2	1012.5	1011.0	1009.5	1008.0	1006.5	1008.0
177.5°	1010.7	1011.8	1013.0	1014.1	1014.7	1014.0	1012.7	1011.4	1010.0	1008.7	1010.0
180°	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	2016.8	2005.9	2010.6	2005.9	2001.2	1996.6	1985.7	1970.2	1957.7	1948.4	1946.9
5°	2172.1	2158.2	2148.8	2144.2	2134.9	2122.4	2102.2	2078.9	2051.0	2040.1	2018.3
7.5°	2315.1	2310.4	2288.7	2285.6	2279.4	2256.0	2221.9	2190.8	2155.1	2125.5	2097.6
10°	2450.3	2439.4	2423.9	2402.1	2399.0	2369.5	2336.8	2293.3	2246.7	2218.8	2169.0
12.5°	2534.2	2521.7	2504.6	2490.7	2482.9	2464.3	2419.2	2375.7	2333.7	2282.5	2239.0
15°	2594.8	2579.2	2548.2	2537.3	2528.0	2503.1	2470.5	2425.4	2369.5	2333.7	2271.6
17.5°	2677.1	2658.5	2627.4	2607.2	2590.1	2551.3	2504.6	2444.1	2391.2	2350.8	2294.9
20°	2771.9	2743.9	2703.5	2677.1	2652.3	2607.2	2541.9	2470.5	2394.3	2344.6	2287.1
22.5°	2928.8	2876.0	2812.3	2775.0	2740.8	2663.1	2585.4	2496.9	2411.4	2336.8	2266.9
25°	3081.1	3028.3	2949.0	2897.7	2844.9	2754.8	2652.3	2529.5	2420.7	2333.7	2242.1
27.5°	3222.5	3168.1	3095.1	3032.9	2981.7	2846.5	2711.3	2573.0	2434.7	2315.1	2221.9
30°	3255.1	3231.8	3175.9	3121.5	3074.9	2950.6	2793.6	2618.1	2451.8	2298.0	2193.9
32.5°	3057.8	3115.3	3129.3	3121.5	3092.0	3003.4	2858.9	2674.0	2476.7	2290.2	2147.3
35°	2647.6	2751.7	2858.9	2916.4	2944.4	2956.8	2871.3	2702.0	2493.8	2277.8	2116.2
37.5°	2195.5	2296.4	2465.8	2551.3	2646.0	2770.3	2804.5	2695.8	2486.0	2268.5	2066.5
40°	1803.9	1932.9	2072.7	2150.4	2232.7	2456.5	2625.8	2613.4	2461.1	2234.3	2027.6
42.5°	1468.3	1549.1	1671.8	1757.3	1858.3	2108.4	2335.3	2447.2	2386.6	2192.3	1977.9
45°	1224.4	1286.5	1373.5	1460.5	1522.7	1749.5	2018.3	2201.7	2259.2	2117.8	1901.8
47.5°	1031.7	1078.3	1154.4	1208.8	1275.6	1454.3	1687.4	1945.3	2066.5	2012.1	1821.0
50°	884.1	921.4	982.0	1016.2	1075.2	1229.0	1406.1	1676.5	1859.8	1866.1	1713.8
52.5°	755.1	792.4	843.7	873.2	908.9	1013.0	1191.7	1420.1	1631.4	1709.1	1591.0
55°	657.2	679.0	720.9	744.2	776.9	877.9	991.3	1185.5	1406.1	1533.6	1459.0
57.5°	567.1	590.4	616.8	635.5	658.8	739.6	842.1	988.2	1207.3	1345.5	1320.7
60°	494.1	508.1	532.9	546.9	568.7	621.5	693.0	839.0	1013.0	1143.6	1157.5
62.5°	425.7	438.2	455.2	467.7	481.7	523.6	576.4	680.5	832.8	974.2	992.8
65°	366.7	377.6	386.9	397.8	408.6	435.1	480.1	560.9	679.0	811.1	851.5
67.5°	313.9	317.0	330.9	332.5	338.7	358.9	391.5	456.8	542.3	647.9	700.7
70°	262.6	268.8	271.9	276.6	282.8	296.8	323.2	357.4	421.1	506.5	556.2
72.5°	212.9	214.4	219.1	222.2	228.4	239.3	251.7	278.1	318.5	380.7	425.7
75°	169.4	170.9	174.0	175.6	180.2	183.3	189.6	208.2	236.2	273.5	306.1
77.5°	127.4	130.5	133.6	133.6	135.2	138.3	141.4	147.6	161.6	186.5	214.4
80°	87.0	88.6	88.6	90.1	88.6	93.2	97.9	105.7	111.9	119.6	133.6
82.5°	60.6	60.6	60.6	62.2	62.2	63.7	63.7	65.3	66.8	71.5	77.7
85°	37.3	37.3	38.8	35.7	37.3	38.8	38.8	37.3	38.8	40.4	42.0
87.5°	15.5	15.5	17.1	17.1	17.1	17.1	15.5	17.1	15.5	17.1	17.1
90°	17.0	16.5	16.0	15.7	15.3	14.5	13.6	12.8	12.0	10.8	9.6
92.5°	16.1	16.0	15.8	15.7	15.3	14.5	13.6	12.8	12.0	11.0	10.0
95°	15.7	15.7	15.7	15.7	15.3	14.5	13.6	12.8	12.0	18.3	24.7
97.5°	15.4	15.2	15.1	15.0	14.8	14.5	14.2	13.8	13.5	29.3	45.1
100°	17.0	17.7	18.4	18.7	31.1	55.9	80.8	105.6	130.4	129.7	129.1
102.5°	141.9	155.9	169.9	176.9	176.7	176.4	176.1	175.7	175.4	175.1	174.7
105°	222.9	223.1	223.2	223.3	223.3	223.3	223.3	223.3	223.3	223.3	223.3
107.5°	271.8	272.5	273.2	273.5	273.4	273.3	273.1	273.0	272.8	272.5	272.1
110°	320.4	320.3	320.1	320.0	320.3	320.8	321.3	321.8	322.3	322.0	321.6



TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	366.4	366.7	367.0	367.2	367.5	368.2	368.9	369.5	370.2	370.0	369.9
115°	412.7	413.7	414.7	415.2	415.5	416.2	416.9	417.5	418.2	418.0	417.8
117.5°	460.1	460.4	460.7	460.9	461.4	462.4	463.4	464.4	465.4	464.7	464.1
120°	505.3	506.1	507.0	507.4	507.6	507.9	508.2	508.6	508.9	508.4	507.9
122.5°	547.6	548.6	549.6	550.1	550.3	550.6	550.9	551.3	551.6	551.4	551.2
125°	589.3	589.8	590.3	590.5	590.8	591.5	592.2	592.8	593.5	593.5	593.5
127.5°	626.2	627.5	628.8	629.5	629.7	630.0	630.3	630.7	631.0	631.2	631.4
130°	664.1	665.0	665.8	666.2	666.5	667.0	667.5	668.0	668.5	668.3	668.1
132.5°	700.1	701.0	701.8	702.2	702.2	702.2	702.2	702.2	702.2	702.7	703.2
135°	732.7	733.7	734.7	735.2	735.4	735.7	736.0	736.4	736.7	737.0	737.4
137.5°	766.1	766.9	767.8	768.2	768.2	768.2	768.2	768.2	768.2	768.5	768.9
140°	795.6	796.6	797.6	798.1	797.9	797.6	797.3	796.9	796.6	796.8	797.0
142.5°	823.4	824.4	825.4	825.9	825.9	825.9	825.9	825.9	825.9	825.6	825.2
145°	850.3	851.3	852.3	852.8	852.7	852.6	852.4	852.3	852.1	852.1	852.1
147.5°	873.2	874.3	875.5	876.1	876.0	875.8	875.7	875.5	875.3	875.1	875.0
150°	895.3	896.6	897.9	898.6	898.4	898.1	897.8	897.4	897.1	896.8	896.4
152.5°	915.1	916.3	917.4	918.0	917.8	917.5	917.2	916.8	916.5	916.2	915.8
155°	932.7	934.0	935.3	936.0	935.8	935.3	934.8	934.3	933.8	933.5	933.1
157.5°	947.7	949.0	950.3	951.0	950.8	950.3	949.8	949.3	948.8	948.8	948.8
160°	962.0	963.3	964.6	965.3	965.0	964.3	963.6	963.0	962.3	962.1	961.9
162.5°	975.0	976.5	978.0	978.7	978.2	977.2	976.3	975.3	974.3	974.1	973.9
165°	985.9	987.2	988.5	989.2	988.7	987.7	986.7	985.7	984.7	984.5	984.4
167.5°	994.5	996.0	997.5	998.2	997.6	996.5	995.3	994.2	993.0	992.8	992.6
170°	1001.2	1002.7	1004.2	1005.0	1004.3	1003.0	1001.7	1000.3	999.0	998.8	998.6
172.5°	1005.7	1007.2	1008.7	1009.5	1008.9	1007.7	1006.6	1005.4	1004.2	1003.9	1003.5
175°	1009.5	1011.0	1012.5	1013.2	1012.5	1011.2	1009.9	1008.5	1007.2	1007.0	1006.9
177.5°	1011.4	1012.7	1014.0	1014.7	1014.1	1013.0	1011.8	1010.7	1009.5	1009.3	1009.1
180°	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1942.2	1932.9	1926.7	1925.1	1915.8	1908.0	1898.7	1897.1	1892.5	1880.0	1872.3
5°	2002.8	1981.0	1976.4	1962.4	1939.1	1922.0	1900.2	1887.8	1873.8	1850.5	1831.9
7.5°	2064.9	2035.4	2013.7	1993.5	1960.8	1929.8	1898.7	1873.8	1849.0	1814.8	1786.8
10°	2125.5	2080.5	2054.1	2024.5	1979.5	1932.9	1889.4	1853.6	1813.2	1772.8	1732.4
12.5°	2181.5	2124.0	2085.1	2043.2	1987.2	1929.8	1873.8	1824.1	1782.2	1727.8	1682.7
15°	2215.7	2151.9	2113.1	2072.7	1988.8	1925.1	1859.8	1796.1	1740.2	1682.7	1640.8
17.5°	2235.8	2164.4	2120.9	2083.6	1998.1	1911.1	1827.2	1758.8	1698.3	1629.9	1574.0
20°	2226.5	2156.6	2116.2	2080.5	1981.0	1894.0	1803.9	1724.7	1648.5	1578.6	1519.6
22.5°	2206.3	2133.3	2088.2	2055.6	1967.1	1864.5	1765.1	1679.6	1600.4	1530.4	1463.6
25°	2162.8	2091.4	2052.5	2012.1	1925.1	1827.2	1726.2	1634.5	1550.6	1476.1	1401.5
27.5°	2124.0	2037.0	1996.6	1960.8	1869.2	1782.2	1682.7	1581.7	1496.3	1418.6	1344.0
30°	2078.9	1981.0	1937.5	1889.4	1807.0	1724.7	1625.2	1532.0	1443.4	1361.1	1289.6
32.5°	2030.8	1917.3	1867.6	1813.2	1729.3	1651.6	1567.7	1476.1	1387.5	1306.7	1232.1
35°	1968.6	1847.4	1789.9	1738.6	1651.6	1574.0	1496.3	1420.1	1331.6	1246.1	1174.6
37.5°	1909.6	1775.9	1715.3	1656.3	1564.6	1490.0	1426.3	1354.9	1269.4	1187.1	1118.7
40°	1842.7	1688.9	1626.8	1572.4	1477.6	1395.3	1337.8	1281.8	1207.3	1128.0	1053.4
42.5°	1782.2	1608.1	1542.9	1486.9	1387.5	1309.8	1255.4	1208.8	1143.6	1070.5	994.4
45°	1698.3	1521.1	1454.3	1395.3	1294.3	1221.2	1165.3	1124.9	1073.6	1005.3	936.9
47.5°	1620.6	1437.2	1364.2	1292.7	1201.1	1126.5	1075.2	1044.1	1009.9	949.3	879.4
50°	1525.8	1340.9	1266.3	1207.3	1103.2	1039.5	988.2	966.4	935.4	877.9	821.9
52.5°	1423.2	1247.7	1177.7	1106.3	1009.9	947.8	902.7	877.9	853.0	811.1	758.2
55°	1303.6	1143.6	1078.3	1014.6	918.3	860.8	820.4	794.0	780.0	741.1	702.3
57.5°	1188.6	1037.9	977.3	918.3	834.4	769.1	742.7	719.4	699.2	671.2	638.6
60°	1072.1	935.4	870.1	817.3	744.2	685.2	663.5	640.1	624.6	602.9	579.5
62.5°	938.5	821.9	772.2	722.5	660.3	613.7	588.9	570.2	550.0	536.0	515.8
65°	797.1	714.7	666.6	629.3	570.2	528.3	509.6	497.2	480.1	466.1	450.6
67.5°	665.0	599.7	579.5	539.2	494.1	456.8	442.8	427.3	413.3	405.5	391.5
70°	537.6	491.0	470.8	459.9	410.2	385.3	372.9	366.7	349.6	341.8	332.5
72.5°	416.4	399.3	385.3	371.3	338.7	323.2	309.2	303.0	290.6	284.3	281.2
75°	307.6	296.8	289.0	287.4	273.5	257.9	243.9	240.8	231.5	225.3	222.2
77.5°	216.0	212.9	211.3	212.9	203.5	194.2	191.1	188.0	177.1	175.6	175.6
80°	141.4	149.2	149.2	147.6	144.5	142.9	138.3	135.2	129.0	127.4	129.0
82.5°	87.0	91.7	93.2	96.3	94.8	93.2	90.1	88.6	90.1	87.0	88.6
85°	43.5	46.6	52.8	52.8	54.4	54.4	54.4	52.8	49.7	51.3	49.7
87.5°	17.1	18.6	18.6	18.6	17.1	21.8	23.3	23.3	23.3	20.2	20.2
90°	8.5	7.3	6.7	6.0	4.7	3.4	2.0	0.7	2.0	3.4	4.7
92.5°	9.0	8.0	7.5	8.2	9.7	11.2	12.7	14.2	12.7	11.2	9.7
95°	31.0	37.3	40.5	40.7	41.2	41.7	42.2	42.7	42.2	41.7	41.2
97.5°	61.0	76.8	84.7	84.2	83.2	82.2	81.2	80.2	81.2	82.2	83.2
100°	128.4	127.7	127.4	127.2	126.7	126.2	125.7	125.2	125.7	126.2	126.7
102.5°	174.4	174.1	173.9	173.6	172.9	172.2	171.6	170.9	171.6	172.2	172.9
105°	223.3	223.3	223.3	223.0	222.3	221.6	221.0	220.3	221.0	221.6	222.3
107.5°	271.8	271.5	271.3	271.3	271.3	271.3	271.3	271.3	271.3	271.3	271.3
110°	321.3	321.0	320.8	320.8	320.8	320.8	320.8	320.8	320.8	320.8	320.8

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	369.7	369.6	369.5	369.2	368.7	368.2	367.7	367.2	367.7	368.2	368.7
115°	417.7	417.5	417.4	417.0	416.2	415.3	414.5	413.7	414.5	415.3	416.2
117.5°	463.4	462.7	462.4	462.4	462.4	462.4	462.4	462.4	462.4	462.4	462.4
120°	507.4	506.9	506.6	506.7	506.9	507.0	507.2	507.4	507.2	507.0	506.9
122.5°	551.1	550.9	550.8	550.4	549.6	548.7	547.9	547.1	547.9	548.7	549.6
125°	593.5	593.5	593.5	592.9	591.8	590.6	589.5	588.3	589.5	590.6	591.8
127.5°	631.5	631.7	631.8	631.4	630.5	629.7	628.8	628.0	628.8	629.7	630.5
130°	668.0	667.8	667.7	667.3	666.5	665.6	664.8	664.0	664.8	665.6	666.5
132.5°	703.7	704.2	704.5	704.0	703.0	702.0	701.0	700.0	701.0	702.0	703.0
135°	737.7	738.0	738.2	737.7	736.7	735.7	734.7	733.7	734.7	735.7	736.7
137.5°	769.2	769.5	769.7	769.2	768.2	767.2	766.2	765.2	766.2	767.2	768.2
140°	797.1	797.3	797.4	797.2	796.9	796.6	796.2	795.9	796.2	796.6	796.9
142.5°	824.9	824.6	824.4	824.3	824.1	824.0	823.8	823.6	823.8	824.0	824.1
145°	852.1	852.1	852.1	851.9	851.6	851.3	850.9	850.6	850.9	851.3	851.6
147.5°	874.8	874.7	874.6	874.6	874.6	874.6	874.6	874.6	874.6	874.6	874.6
150°	896.1	895.8	895.6	895.8	896.1	896.4	896.8	897.1	896.8	896.4	896.1
152.5°	915.5	915.2	915.0	915.4	916.3	917.1	918.0	918.8	918.0	917.1	916.3
155°	932.8	932.5	932.3	932.8	933.8	934.8	935.8	936.8	935.8	934.8	933.8
157.5°	948.8	948.8	948.8	949.0	949.5	950.0	950.5	951.0	950.5	950.0	949.5
160°	961.8	961.6	961.5	962.0	963.0	964.0	965.0	966.0	965.0	964.0	963.0
162.5°	973.8	973.6	973.5	974.0	975.0	976.0	977.0	978.0	977.0	976.0	975.0
165°	984.2	984.1	984.0	984.5	985.5	986.5	987.5	988.5	987.5	986.5	985.5
167.5°	992.5	992.3	992.2	992.7	993.7	994.7	995.7	996.7	995.7	994.7	993.7
170°	998.5	998.3	998.2	998.8	1000.0	1001.1	1002.3	1003.5	1002.3	1001.1	1000.0
172.5°	1003.2	1002.9	1002.7	1003.3	1004.5	1005.6	1006.8	1008.0	1006.8	1005.6	1004.5
175°	1006.7	1006.6	1006.5	1007.0	1008.0	1009.0	1010.0	1011.0	1010.0	1009.0	1008.0
177.5°	1009.0	1008.8	1008.7	1009.2	1010.2	1011.2	1012.2	1013.2	1012.2	1011.2	1010.2
180°	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1867.6	1861.4	1856.7	1852.1	1831.9	1810.1	1807.0	1802.4	1793.0	1803.9	1799.2
5°	1819.4	1805.5	1797.7	1777.5	1752.6	1734.0	1718.4	1699.8	1692.0	1685.8	1684.3
7.5°	1760.4	1748.0	1734.0	1713.8	1682.7	1651.6	1628.3	1609.7	1594.1	1586.4	1586.4
10°	1702.9	1687.4	1668.7	1634.5	1605.0	1566.2	1541.3	1522.7	1500.9	1488.5	1477.6
12.5°	1643.9	1626.8	1609.7	1566.2	1532.0	1491.6	1455.9	1432.6	1421.7	1407.7	1389.1
15°	1584.8	1558.4	1541.3	1497.8	1454.3	1413.9	1390.6	1365.7	1340.9	1326.9	1320.7
17.5°	1522.7	1504.0	1476.1	1429.5	1381.3	1345.5	1311.4	1288.1	1258.5	1244.6	1230.6
20°	1466.7	1438.8	1410.8	1364.2	1317.6	1269.4	1235.2	1207.3	1188.6	1177.7	1165.3
22.5°	1399.9	1373.5	1350.2	1300.5	1249.2	1204.2	1166.9	1149.8	1131.1	1114.0	1101.6
25°	1342.4	1316.0	1292.7	1238.3	1182.4	1140.5	1112.5	1090.7	1070.5	1062.8	1050.3
27.5°	1281.8	1257.0	1225.9	1171.5	1121.8	1086.1	1056.6	1036.4	1020.8	1005.3	996.0
30°	1224.4	1196.4	1168.4	1109.4	1069.0	1033.2	1005.3	980.4	968.0	960.2	944.7
32.5°	1168.4	1132.7	1109.4	1055.0	1016.2	982.0	958.7	936.9	921.4	907.4	895.0
35°	1107.8	1069.0	1045.7	1000.6	960.2	926.0	905.8	890.3	871.7	859.2	853.0
37.5°	1050.3	1017.7	994.4	947.8	907.4	879.4	857.7	837.5	829.7	812.6	809.5
40°	988.2	960.2	938.5	893.4	856.1	834.4	811.1	792.4	778.4	770.7	759.8
42.5°	932.3	908.9	885.6	843.7	808.0	781.5	764.4	747.4	734.9	722.5	714.7
45°	881.0	856.1	834.4	794.0	758.2	734.9	717.8	697.6	694.5	677.4	669.7
47.5°	826.6	804.8	786.2	744.2	711.6	688.3	668.1	654.1	640.1	633.9	623.1
50°	773.8	752.0	730.3	693.0	663.5	640.1	619.9	604.4	596.6	587.3	578.0
52.5°	716.3	699.2	682.1	643.3	613.7	593.5	576.4	556.2	548.5	540.7	534.5
55°	668.1	643.3	624.6	592.0	565.6	543.8	525.2	509.6	501.9	495.6	487.9
57.5°	602.9	587.3	571.8	542.3	517.4	495.6	477.0	464.6	455.2	450.6	452.1
60°	546.9	529.8	520.5	489.4	464.6	447.5	430.4	418.0	408.6	404.0	402.4
62.5°	487.9	475.4	458.4	436.6	411.7	396.2	383.8	374.5	358.9	357.4	352.7
65°	430.4	421.1	405.5	385.3	365.1	351.1	337.2	324.7	318.5	310.8	306.1
67.5°	374.5	365.1	351.1	334.1	320.1	306.1	293.7	281.2	270.4	264.1	261.0
70°	320.1	312.3	303.0	282.8	265.7	254.8	245.5	237.7	226.8	223.7	222.2
72.5°	267.2	259.5	254.8	237.7	222.2	212.9	203.5	195.8	191.1	189.6	184.9
75°	219.1	211.3	205.1	189.6	180.2	174.0	164.7	161.6	156.9	155.4	153.8
77.5°	170.9	163.1	161.6	150.7	139.8	136.7	133.6	127.4	127.4	127.4	124.3
80°	122.7	121.2	119.6	108.8	104.1	101.0	99.4	94.8	91.7	88.6	87.0
82.5°	82.3	80.8	79.2	74.6	69.9	68.4	66.8	63.7	63.7	65.3	62.2
85°	49.7	46.6	45.1	43.5	40.4	40.4	42.0	40.4	40.4	40.4	38.8
87.5°	18.6	18.6	18.6	18.6	20.2	17.1	18.6	18.6	17.1	17.1	15.5
90°	6.0	6.7	7.3	8.5	9.6	10.8	12.0	12.8	13.6	14.5	15.3
92.5°	8.2	7.5	8.0	9.0	10.0	11.0	12.0	12.8	13.6	14.5	15.3
95°	40.7	40.5	37.3	31.0	24.7	18.3	12.0	12.8	13.6	14.5	15.3
97.5°	84.2	84.7	76.8	61.0	45.1	29.3	13.5	13.8	14.2	14.5	14.8
100°	127.2	127.4	127.7	128.4	129.1	129.7	130.4	105.6	80.8	55.9	31.1
102.5°	173.6	173.9	174.1	174.4	174.7	175.1	175.4	175.7	176.1	176.4	176.7
105°	223.0	223.3	223.3	223.3	223.3	223.3	223.3	223.3	223.3	223.3	223.3
107.5°	271.3	271.3	271.5	271.8	272.1	272.5	272.8	273.0	273.1	273.3	273.4
110°	320.8	320.8	321.0	321.3	321.6	322.0	322.3	321.8	321.3	320.8	320.3

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	369.2	369.5	369.6	369.7	369.9	370.0	370.2	369.5	368.9	368.2	367.5
115°	417.0	417.4	417.5	417.7	417.8	418.0	418.2	417.5	416.9	416.2	415.5
117.5°	462.4	462.4	462.7	463.4	464.1	464.7	465.4	464.4	463.4	462.4	461.4
120°	506.7	506.6	506.9	507.4	507.9	508.4	508.9	508.6	508.2	507.9	507.6
122.5°	550.4	550.8	550.9	551.1	551.2	551.4	551.6	551.3	550.9	550.6	550.3
125°	592.9	593.5	593.5	593.5	593.5	593.5	593.5	592.8	592.2	591.5	590.8
127.5°	631.4	631.8	631.7	631.5	631.4	631.2	631.0	630.7	630.3	630.0	629.7
130°	667.3	667.7	667.8	668.0	668.1	668.3	668.5	668.0	667.5	667.0	666.5
132.5°	704.0	704.5	704.2	703.7	703.2	702.7	702.2	702.2	702.2	702.2	702.2
135°	737.7	738.2	738.0	737.7	737.4	737.0	736.7	736.4	736.0	735.7	735.4
137.5°	769.2	769.7	769.5	769.2	768.9	768.5	768.2	768.2	768.2	768.2	768.2
140°	797.2	797.4	797.3	797.1	797.0	796.8	796.6	796.9	797.3	797.6	797.9
142.5°	824.3	824.4	824.6	824.9	825.2	825.6	825.9	825.9	825.9	825.9	825.9
145°	851.9	852.1	852.1	852.1	852.1	852.1	852.1	852.3	852.4	852.6	852.7
147.5°	874.6	874.6	874.7	874.8	875.0	875.1	875.3	875.5	875.7	875.8	876.0
150°	895.8	895.6	895.8	896.1	896.4	896.8	897.1	897.4	897.8	898.1	898.4
152.5°	915.4	915.0	915.2	915.5	915.8	916.2	916.5	916.8	917.2	917.5	917.8
155°	932.8	932.3	932.5	932.8	933.1	933.5	933.8	934.3	934.8	935.3	935.8
157.5°	949.0	948.8	948.8	948.8	948.8	948.8	948.8	949.3	949.8	950.3	950.8
160°	962.0	961.5	961.6	961.8	961.9	962.1	962.3	963.0	963.6	964.3	965.0
162.5°	974.0	973.5	973.6	973.8	973.9	974.1	974.3	975.3	976.3	977.2	978.2
165°	984.5	984.0	984.1	984.2	984.4	984.5	984.7	985.7	986.7	987.7	988.7
167.5°	992.7	992.2	992.3	992.5	992.6	992.8	993.0	994.2	995.3	996.5	997.6
170°	998.8	998.2	998.3	998.5	998.6	998.8	999.0	1000.3	1001.7	1003.0	1004.3
172.5°	1003.3	1002.7	1002.9	1003.2	1003.5	1003.9	1004.2	1005.4	1006.6	1007.7	1008.9
175°	1007.0	1006.5	1006.6	1006.7	1006.9	1007.0	1007.2	1008.5	1009.9	1011.2	1012.5
177.5°	1009.2	1008.7	1008.8	1009.0	1009.1	1009.3	1009.5	1010.7	1011.8	1013.0	1014.1
180°	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1791.5	1794.6	1786.8	1783.7	1777.5	1785.3	1786.8	1785.3	1799.2	1793.0	1796.1
5°	1687.4	1681.2	1676.5	1665.6	1665.6	1667.2	1671.8	1664.1	1668.7	1679.6	1678.1
7.5°	1572.4	1569.3	1570.8	1558.4	1549.1	1552.2	1549.1	1563.1	1570.8	1567.7	1574.0
10°	1468.3	1474.5	1460.5	1454.3	1448.1	1454.3	1452.8	1455.9	1465.2	1471.4	1482.3
12.5°	1384.4	1382.8	1375.1	1368.9	1358.0	1361.1	1370.4	1367.3	1368.9	1382.8	1381.3
15°	1305.2	1295.8	1289.6	1275.6	1278.7	1267.9	1277.2	1288.1	1292.7	1305.2	1312.9
17.5°	1225.9	1224.4	1216.6	1215.0	1197.9	1193.3	1202.6	1205.7	1210.4	1216.6	1227.5
20°	1159.1	1157.5	1146.7	1143.6	1129.6	1138.9	1135.8	1142.0	1145.1	1157.5	1162.2
22.5°	1098.5	1090.7	1087.6	1083.0	1078.3	1076.8	1083.0	1081.4	1092.3	1096.9	1098.5
25°	1042.6	1036.4	1034.8	1027.0	1023.9	1019.3	1023.9	1028.6	1041.0	1045.7	1051.9
27.5°	991.3	986.6	983.5	977.3	972.6	972.6	975.8	982.0	986.6	989.7	992.8
30°	944.7	941.6	932.3	929.1	924.5	924.5	924.5	927.6	935.4	944.7	949.3
32.5°	896.5	890.3	884.1	884.1	879.4	879.4	881.0	884.1	891.9	893.4	901.2
35°	849.9	843.7	839.0	835.9	837.5	831.3	834.4	839.0	848.3	851.5	856.1
37.5°	804.8	803.3	794.0	789.3	792.4	792.4	790.9	794.0	800.2	806.4	809.5
40°	755.1	752.0	752.0	747.4	748.9	742.7	747.4	750.5	753.6	759.8	764.4
42.5°	711.6	708.5	702.3	703.8	699.2	699.2	702.3	703.8	708.5	716.3	719.4
45°	665.0	665.0	661.9	657.2	658.8	654.1	657.2	658.8	665.0	672.8	669.7
47.5°	619.9	618.4	618.4	612.2	615.3	610.6	615.3	616.8	619.9	624.6	623.1
50°	576.4	571.8	573.3	571.8	570.2	570.2	573.3	573.3	576.4	576.4	581.1
52.5°	531.4	531.4	528.3	529.8	532.9	529.8	534.5	529.8	532.9	534.5	537.6
55°	491.0	487.9	489.4	487.9	494.1	489.4	494.1	491.0	494.1	492.5	495.6
57.5°	447.5	442.8	444.4	442.8	447.5	445.9	450.6	445.9	447.5	449.0	453.7
60°	397.8	397.8	397.8	394.7	399.3	399.3	397.8	397.8	404.0	407.1	405.5
62.5°	351.1	349.6	344.9	343.4	344.9	341.8	348.0	346.5	349.6	352.7	355.8
65°	299.9	296.8	295.2	292.1	292.1	290.6	292.1	298.3	299.9	301.4	309.2
67.5°	257.9	256.4	254.8	250.2	250.2	253.3	253.3	253.3	262.6	257.9	264.1
70°	220.6	217.5	214.4	212.9	212.9	214.4	216.0	217.5	216.0	222.2	223.7
72.5°	184.9	186.5	183.3	183.3	183.3	181.8	181.8	184.9	186.5	184.9	186.5
75°	153.8	153.8	152.3	153.8	153.8	152.3	152.3	155.4	155.4	153.8	158.5
77.5°	124.3	122.7	119.6	116.5	118.1	116.5	118.1	116.5	121.2	125.9	122.7
80°	87.0	85.5	85.5	85.5	87.0	85.5	88.6	85.5	87.0	87.0	88.6
82.5°	62.2	63.7	63.7	62.2	63.7	62.2	63.7	63.7	63.7	62.2	63.7
85°	40.4	40.4	40.4	40.4	38.8	40.4	40.4	40.4	42.0	40.4	42.0
87.5°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	18.6	17.1	18.6
90°	15.7	16.0	16.5	17.0	17.5	18.0	17.5	17.0	16.5	16.0	15.7
92.5°	15.7	15.8	16.0	16.1	16.3	16.5	16.3	16.1	16.0	15.8	15.7
95°	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7
97.5°	15.0	15.1	15.2	15.4	15.5	15.7	15.5	15.4	15.2	15.1	15.0
100°	18.7	18.4	17.7	17.0	16.4	15.7	16.4	17.0	17.7	18.4	18.7
102.5°	176.9	169.9	155.9	141.9	127.9	113.9	127.9	141.9	155.9	169.9	176.9
105°	223.3	223.2	223.1	222.9	222.8	222.6	222.8	222.9	223.1	223.2	223.3
107.5°	273.5	273.2	272.5	271.8	271.2	270.5	271.2	271.8	272.5	273.2	273.5
110°	320.0	320.1	320.3	320.4	320.6	320.8	320.6	320.4	320.3	320.1	320.0

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	367.2	367.0	366.7	366.4	366.0	365.7	366.0	366.4	366.7	367.0	367.2
115°	415.2	414.7	413.7	412.7	411.7	410.7	411.7	412.7	413.7	414.7	415.2
117.5°	460.9	460.7	460.4	460.1	459.7	459.4	459.7	460.1	460.4	460.7	460.9
120°	507.4	507.0	506.1	505.3	504.4	503.6	504.4	505.3	506.1	507.0	507.4
122.5°	550.1	549.6	548.6	547.6	546.6	545.6	546.6	547.6	548.6	549.6	550.1
125°	590.5	590.3	589.8	589.3	588.8	588.3	588.8	589.3	589.8	590.3	590.5
127.5°	629.5	628.8	627.5	626.2	624.8	623.5	624.8	626.2	627.5	628.8	629.5
130°	666.2	665.8	665.0	664.1	663.3	662.5	663.3	664.1	665.0	665.8	666.2
132.5°	702.2	701.8	701.0	700.1	699.3	698.5	699.3	700.1	701.0	701.8	702.2
135°	735.2	734.7	733.7	732.7	731.7	730.7	731.7	732.7	733.7	734.7	735.2
137.5°	768.2	767.8	766.9	766.1	765.2	764.4	765.2	766.1	766.9	767.8	768.2
140°	798.1	797.6	796.6	795.6	794.6	793.6	794.6	795.6	796.6	797.6	798.1
142.5°	825.9	825.4	824.4	823.4	822.4	821.4	822.4	823.4	824.4	825.4	825.9
145°	852.8	852.3	851.3	850.3	849.3	848.3	849.3	850.3	851.3	852.3	852.8
147.5°	876.1	875.5	874.3	873.2	872.0	870.8	872.0	873.2	874.3	875.5	876.1
150°	898.6	897.9	896.6	895.3	893.9	892.6	893.9	895.3	896.6	897.9	898.6
152.5°	918.0	917.4	916.3	915.1	914.0	912.8	914.0	915.1	916.3	917.4	918.0
155°	936.0	935.3	934.0	932.7	931.3	930.0	931.3	932.7	934.0	935.3	936.0
157.5°	951.0	950.3	949.0	947.7	946.3	945.0	946.3	947.7	949.0	950.3	951.0
160°	965.3	964.6	963.3	962.0	960.6	959.3	960.6	962.0	963.3	964.6	965.3
162.5°	978.7	978.0	976.5	975.0	973.5	972.0	973.5	975.0	976.5	978.0	978.7
165°	989.2	988.5	987.2	985.9	984.5	983.2	984.5	985.9	987.2	988.5	989.2
167.5°	998.2	997.5	996.0	994.5	993.0	991.5	993.0	994.5	996.0	997.5	998.2
170°	1005.0	1004.2	1002.7	1001.2	999.7	998.2	999.7	1001.2	1002.7	1004.2	1005.0
172.5°	1009.5	1008.7	1007.2	1005.7	1004.2	1002.7	1004.2	1005.7	1007.2	1008.7	1009.5
175°	1013.2	1012.5	1011.0	1009.5	1008.0	1006.5	1008.0	1009.5	1011.0	1012.5	1013.2
177.5°	1014.7	1014.0	1012.7	1011.4	1010.0	1008.7	1010.0	1011.4	1012.7	1014.0	1014.7
180°	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1789.9	1797.7	1791.5	1786.8	1799.2	1805.5	1805.5	1816.3	1827.2	1836.5	1838.1
5°	1679.6	1692.0	1695.1	1693.6	1712.2	1721.6	1741.8	1752.6	1768.2	1779.0	1791.5
7.5°	1578.6	1595.7	1597.3	1600.4	1628.3	1643.9	1661.0	1688.9	1710.7	1726.2	1740.2
10°	1477.6	1488.5	1499.4	1513.4	1541.3	1567.7	1592.6	1622.1	1650.1	1665.6	1685.8
12.5°	1401.5	1409.3	1421.7	1431.0	1460.5	1483.8	1516.5	1556.9	1597.3	1609.7	1634.5
15°	1322.2	1326.9	1351.8	1361.1	1385.9	1424.8	1445.0	1483.8	1527.3	1550.6	1578.6
17.5°	1230.6	1258.5	1274.1	1285.0	1316.0	1347.1	1379.7	1420.1	1476.1	1497.8	1518.0
20°	1165.3	1185.5	1202.6	1216.6	1244.6	1291.2	1320.7	1353.3	1406.1	1431.0	1460.5
22.5°	1107.8	1124.9	1140.5	1156.0	1174.6	1216.6	1250.8	1295.8	1348.7	1372.0	1406.1
25°	1053.4	1070.5	1079.9	1098.5	1123.4	1152.9	1193.3	1233.7	1286.5	1312.9	1345.5
27.5°	1000.6	1017.7	1034.8	1050.3	1067.4	1095.4	1123.4	1174.6	1229.0	1260.1	1288.1
30°	955.6	963.3	978.9	996.0	1013.0	1039.5	1072.1	1107.8	1170.0	1197.9	1232.1
32.5°	905.8	919.8	930.7	943.1	964.9	986.6	1016.2	1061.2	1110.9	1137.3	1174.6
35°	859.2	871.7	879.4	901.2	915.2	938.5	968.0	1008.4	1050.3	1079.9	1112.5
37.5°	814.2	826.6	835.9	848.3	867.0	887.2	918.3	947.8	997.5	1022.4	1059.7
40°	767.6	778.4	789.3	803.3	820.4	845.2	863.9	901.2	941.6	969.5	997.5
42.5°	722.5	728.7	741.1	756.7	773.8	795.5	821.9	851.5	891.9	916.7	941.6
45°	674.3	685.2	699.2	710.1	725.6	747.4	770.7	797.1	837.5	862.3	888.7
47.5°	629.3	637.0	646.4	663.5	683.7	699.2	724.0	748.9	786.2	809.5	834.4
50°	582.7	590.4	604.4	615.3	630.8	651.0	674.3	700.7	736.5	752.0	776.9
52.5°	539.2	542.3	556.2	567.1	582.7	606.0	624.6	647.9	682.1	699.2	724.0
55°	495.6	498.8	506.5	517.4	534.5	553.1	573.3	599.7	629.3	644.8	668.1
57.5°	450.6	453.7	461.5	469.2	486.3	503.4	526.7	548.5	578.0	592.0	613.7
60°	405.5	405.5	413.3	424.2	436.6	452.1	472.3	498.8	520.5	537.6	553.1
62.5°	357.4	362.0	366.7	374.5	388.4	407.1	424.2	442.8	469.2	481.7	495.6
65°	309.2	313.9	323.2	330.9	341.8	354.3	376.0	391.5	411.7	425.7	438.2
67.5°	267.2	271.9	278.1	287.4	295.2	309.2	324.7	340.3	362.0	371.3	380.7
70°	223.7	228.4	233.1	245.5	253.3	264.1	275.0	290.6	309.2	315.4	323.2
72.5°	189.6	191.1	197.3	200.4	211.3	220.6	233.1	242.4	256.4	264.1	270.4
75°	160.0	160.0	161.6	164.7	170.9	177.1	186.5	195.8	208.2	212.9	220.6
77.5°	125.9	130.5	129.0	132.1	135.2	138.3	146.1	152.3	164.7	167.8	170.9
80°	90.1	91.7	96.3	101.0	101.0	105.7	110.3	111.9	119.6	124.3	124.3
82.5°	65.3	66.8	65.3	66.8	68.4	69.9	74.6	80.8	80.8	82.3	85.5
85°	40.4	40.4	42.0	43.5	43.5	42.0	45.1	43.5	45.1	48.2	48.2
87.5°	20.2	18.6	18.6	18.6	18.6	18.6	20.2	18.6	20.2	20.2	20.2
90°	15.3	14.5	13.6	12.8	12.0	10.8	9.6	8.5	7.3	6.7	6.0
92.5°	15.3	14.5	13.6	12.8	12.0	11.0	10.0	9.0	8.0	7.5	8.2
95°	15.3	14.5	13.6	12.8	12.0	18.3	24.7	31.0	37.3	40.5	40.7
97.5°	14.8	14.5	14.2	13.8	13.5	29.3	45.1	61.0	76.8	84.7	84.2
100°	31.1	55.9	80.8	105.6	130.4	129.7	129.1	128.4	127.7	127.4	127.2
102.5°	176.7	176.4	176.1	175.7	175.4	175.1	174.7	174.4	174.1	173.9	173.6
105°	223.3	223.3	223.3	223.3	223.3	223.3	223.3	223.3	223.3	223.3	223.0
107.5°	273.4	273.3	273.1	273.0	272.8	272.5	272.1	271.8	271.5	271.3	271.3
110°	320.3	320.8	321.3	321.8	322.3	322.0	321.6	321.3	321.0	320.8	320.8

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	367.5	368.2	368.9	369.5	370.2	370.0	369.9	369.7	369.6	369.5	369.2
115°	415.5	416.2	416.9	417.5	418.2	418.0	417.8	417.7	417.5	417.4	417.0
117.5°	461.4	462.4	463.4	464.4	465.4	464.7	464.1	463.4	462.7	462.4	462.4
120°	507.6	507.9	508.2	508.6	508.9	508.4	507.9	507.4	506.9	506.6	506.7
122.5°	550.3	550.6	550.9	551.3	551.6	551.4	551.2	551.1	550.9	550.8	550.4
125°	590.8	591.5	592.2	592.8	593.5	593.5	593.5	593.5	593.5	593.5	592.9
127.5°	629.7	630.0	630.3	630.7	631.0	631.2	631.4	631.5	631.7	631.8	631.4
130°	666.5	667.0	667.5	668.0	668.5	668.3	668.1	668.0	667.8	667.7	667.3
132.5°	702.2	702.2	702.2	702.2	702.2	702.7	703.2	703.7	704.2	704.5	704.0
135°	735.4	735.7	736.0	736.4	736.7	737.0	737.4	737.7	738.0	738.2	737.7
137.5°	768.2	768.2	768.2	768.2	768.2	768.5	768.9	769.2	769.5	769.7	769.2
140°	797.9	797.6	797.3	796.9	796.6	796.8	797.0	797.1	797.3	797.4	797.2
142.5°	825.9	825.9	825.9	825.9	825.9	825.6	825.2	824.9	824.6	824.4	824.3
145°	852.7	852.6	852.4	852.3	852.1	852.1	852.1	852.1	852.1	852.1	851.9
147.5°	876.0	875.8	875.7	875.5	875.3	875.1	875.0	874.8	874.7	874.6	874.6
150°	898.4	898.1	897.8	897.4	897.1	896.8	896.4	896.1	895.8	895.6	895.8
152.5°	917.8	917.5	917.2	916.8	916.5	916.2	915.8	915.5	915.2	915.0	915.4
155°	935.8	935.3	934.8	934.3	933.8	933.5	933.1	932.8	932.5	932.3	932.8
157.5°	950.8	950.3	949.8	949.3	948.8	948.8	948.8	948.8	948.8	948.8	949.0
160°	965.0	964.3	963.6	963.0	962.3	962.1	961.9	961.8	961.6	961.5	962.0
162.5°	978.2	977.2	976.3	975.3	974.3	974.1	973.9	973.8	973.6	973.5	974.0
165°	988.7	987.7	986.7	985.7	984.7	984.5	984.4	984.2	984.1	984.0	984.5
167.5°	997.6	996.5	995.3	994.2	993.0	992.8	992.6	992.5	992.3	992.2	992.7
170°	1004.3	1003.0	1001.7	1000.3	999.0	998.8	998.6	998.5	998.3	998.2	998.8
172.5°	1008.9	1007.7	1006.6	1005.4	1004.2	1003.9	1003.5	1003.2	1002.9	1002.7	1003.3
175°	1012.5	1011.2	1009.9	1008.5	1007.2	1007.0	1006.9	1006.7	1006.6	1006.5	1007.0
177.5°	1014.1	1013.0	1011.8	1010.7	1009.5	1009.3	1009.1	1009.0	1008.8	1008.7	1009.2
180°	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0	1011.0

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1892.5	1892.5	1892.5	1892.5
2.5°	1849.0	1862.9	1876.9	1894.0
5°	1811.7	1836.5	1862.9	1887.8
7.5°	1771.3	1807.0	1841.2	1876.9
10°	1726.2	1771.3	1810.1	1859.8
12.5°	1676.5	1724.7	1779.0	1835.0
15°	1626.8	1687.4	1744.9	1808.6
17.5°	1580.2	1637.7	1701.4	1777.5
20°	1524.2	1587.9	1659.4	1740.2
22.5°	1465.2	1535.1	1612.8	1699.8
25°	1415.5	1486.9	1561.5	1653.2
27.5°	1361.1	1435.7	1508.7	1606.6
30°	1298.9	1379.7	1454.3	1555.3
32.5°	1239.9	1320.7	1403.0	1497.8
35°	1182.4	1261.6	1344.0	1440.3
37.5°	1128.0	1199.5	1280.3	1367.3
40°	1076.8	1142.0	1213.5	1292.7
42.5°	1011.5	1087.6	1154.4	1211.9
45°	955.6	1017.7	1079.9	1126.5
47.5°	890.3	952.4	1005.3	1042.6
50°	835.9	885.6	929.1	961.8
52.5°	770.7	817.3	853.0	877.9
55°	707.0	747.4	778.4	795.5
57.5°	649.5	675.9	699.2	714.7
60°	585.8	606.0	626.2	643.3
62.5°	517.4	539.2	550.0	568.7
65°	456.8	470.8	487.9	494.1
67.5°	397.8	405.5	416.4	428.8
70°	335.6	340.3	351.1	368.2
72.5°	281.2	285.9	293.7	299.9
75°	223.7	228.4	234.6	240.8
77.5°	175.6	177.1	180.2	186.5
80°	127.4	132.1	135.2	136.7
82.5°	88.6	90.1	90.1	91.7
85°	55.9	52.8	52.8	54.4
87.5°	20.2	23.3	23.3	26.4
90°	4.7	3.4	2.0	0.7
92.5°	9.7	11.2	12.7	14.2
95°	41.2	41.7	42.2	42.7
97.5°	83.2	82.2	81.2	80.2
100°	126.7	126.2	125.7	125.2
102.5°	172.9	172.2	171.6	170.9
105°	222.3	221.6	221.0	220.3
107.5°	271.3	271.3	271.3	271.3
110°	320.8	320.8	320.8	320.8

TEST NUMBER: P1035862

CATALOG NUMBER: S125RDIW-B1270D770UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	368.7	368.2	367.7	367.2
115°	416.2	415.3	414.5	413.7
117.5°	462.4	462.4	462.4	462.4
120°	506.9	507.0	507.2	507.4
122.5°	549.6	548.7	547.9	547.1
125°	591.8	590.6	589.5	588.3
127.5°	630.5	629.7	628.8	628.0
130°	666.5	665.6	664.8	664.0
132.5°	703.0	702.0	701.0	700.0
135°	736.7	735.7	734.7	733.7
137.5°	768.2	767.2	766.2	765.2
140°	796.9	796.6	796.2	795.9
142.5°	824.1	824.0	823.8	823.6
145°	851.6	851.3	850.9	850.6
147.5°	874.6	874.6	874.6	874.6
150°	896.1	896.4	896.8	897.1
152.5°	916.3	917.1	918.0	918.8
155°	933.8	934.8	935.8	936.8
157.5°	949.5	950.0	950.5	951.0
160°	963.0	964.0	965.0	966.0
162.5°	975.0	976.0	977.0	978.0
165°	985.5	986.5	987.5	988.5
167.5°	993.7	994.7	995.7	996.7
170°	1000.0	1001.1	1002.3	1003.5
172.5°	1004.5	1005.6	1006.8	1008.0
175°	1008.0	1009.0	1010.0	1011.0
177.5°	1010.2	1011.2	1012.2	1013.2
180°	1011.0	1011.0	1011.0	1011.0

(END OF REPORT)