

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036000

Luminaire Tested: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036000
REPORT IS A COMBINATION OF REPORTS P1006655 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1340UB40-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7714.0 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31		
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	26		
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23		
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	26	24	19		
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	23	21	17		
5	66	54	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15		
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13		
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	12		
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10		
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	15	13	12	9		
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5871	5871	5871	5871
5°	5866	6617	5866	5086
10°	5833	7436	5813	4397
15°	5770	7866	5730	3828
20°	5693	8492	5643	3460
25°	5594	9613	5530	3140
30°	5492	10217	5410	2911
35°	5361	8403	5286	2698
40°	5127	5706	5085	2507
45°	4821	4102	4815	2318
50°	4508	3155	4529	2144
55°	4155	2565	4146	1976
60°	3826	2102	3808	1754
65°	3442	1751	3463	1412
70°	3125	1405	3111	1176
75°	2640	1066	2640	966
80°	2139	650	2117	650
85°	1504	342	1464	387

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8357 cd/sqm

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	1.1
10°-20°	257.6	3.3
20°-30°	408.5	5.3
30°-40°	493.6	6.4
40°-50°	439.4	5.7
50°-60°	337.0	4.4
60°-70°	218.9	2.8
70°-80°	106.2	1.4
80°-90°	27.6	0.4
90°-100°	59.0	0.8
100°-110°	392.1	5.1
110°-120°	706.2	9.2
120°-130°	906.4	11.8
130°-140°	974.9	12.6
140°-150°	915.0	11.9
150°-160°	740.1	9.6
160°-170°	478.7	6.2
170°-180°	165.1	2.1
0°-30°	754.0	9.8
0°-40°	1247.5	16.2
0°-60°	2024.0	26.2
0°-90°	2376.6	30.8
90°-120°	1157.3	15.0
90°-150°	3953.6	51.3
90°-180°	5337.0	69.2
0°-180°	7714.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	916	916	916	916	916	
5°	914	1050	914	807	914	87
15°	876	1262	870	614	876	247
25°	800	1511	791	494	800	369
35°	697	1253	688	402	697	434
45°	545	560	545	317	545	421
55°	385	308	384	237	385	345
65°	239	174	241	141	239	239
75°	117	81	117	74	117	125
85°	26	17	26	20	26	30
90°	1	31	1	31	1	5
95°	73	27	73	27	73	90
105°	379	382	379	382	379	401
115°	711	706	711	706	711	705
125°	1011	1011	1011	1011	1011	903
135°	1261	1256	1261	1256	1261	972
145°	1462	1458	1462	1458	1462	914
155°	1610	1598	1610	1598	1610	742
165°	1699	1690	1699	1690	1699	480
175°	1738	1730	1738	1730	1738	165
180°	1738	1738	1738	1738	1738	

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3
2.5°	917.1	924.6	926.9	932.9	939.6	941.1	944.9	950.2	953.2	952.4	952.4
5°	914.1	926.9	935.9	946.4	959.2	964.5	969.0	980.3	989.3	994.6	1003.6
7.5°	908.8	927.6	942.7	958.5	978.0	987.0	996.8	1012.6	1029.2	1039.7	1049.5
10°	900.5	924.6	945.7	969.0	995.3	1008.9	1020.9	1045.0	1065.3	1078.8	1101.4
12.5°	888.5	918.6	947.9	978.8	1011.9	1026.2	1042.7	1069.0	1097.6	1117.2	1136.0
15°	875.7	911.8	943.4	980.3	1020.1	1042.0	1063.0	1090.9	1116.4	1138.3	1160.1
17.5°	860.6	899.0	938.1	980.3	1025.4	1047.2	1065.3	1098.4	1125.5	1147.3	1166.8
20°	842.6	885.5	929.9	976.5	1022.4	1042.7	1060.0	1096.1	1120.2	1143.5	1171.4
22.5°	823.0	869.7	917.1	963.0	1008.1	1029.9	1050.2	1081.8	1108.2	1139.8	1175.9
25°	800.5	851.6	899.8	945.7	988.5	1008.9	1026.9	1061.5	1098.4	1138.3	1178.9
27.5°	777.9	827.5	874.2	916.3	963.0	981.8	999.8	1043.5	1087.1	1129.2	1184.9
30°	753.1	803.5	844.1	883.2	928.4	947.9	970.5	1020.1	1069.8	1127.0	1194.7
32.5°	725.2	771.1	808.7	849.4	890.0	914.1	942.7	996.8	1054.0	1122.5	1209.0
35°	697.4	734.3	768.9	807.2	856.1	881.7	909.6	966.7	1038.2	1120.2	1221.0
37.5°	662.0	697.4	724.5	763.6	814.0	844.1	871.9	938.1	1019.4	1114.9	1220.3
40°	625.9	656.0	681.6	722.2	777.1	805.0	835.1	907.3	999.8	1099.9	1202.2
42.5°	586.8	612.4	640.2	679.3	732.8	759.8	794.4	878.7	972.7	1078.8	1155.6
45°	545.4	570.3	593.6	634.2	687.6	717.0	754.6	841.1	939.6	1034.4	1080.3
47.5°	504.8	526.6	551.4	586.8	641.0	673.3	711.7	804.2	895.3	975.0	978.8
50°	465.7	483.0	504.1	540.2	596.6	627.4	667.3	753.8	842.6	897.5	860.6
52.5°	425.1	440.9	462.7	494.3	546.9	583.0	617.7	704.2	778.6	815.5	747.8
55°	385.2	398.7	421.3	456.7	502.5	530.4	565.7	646.2	711.7	712.4	638.7
57.5°	346.1	358.1	376.9	408.5	451.4	483.7	516.1	586.1	630.4	617.7	535.6
60°	311.5	319.0	336.3	367.1	407.0	430.3	464.9	523.6	553.0	529.6	441.6
62.5°	275.3	282.9	296.4	321.2	358.9	383.7	405.5	453.6	474.0	438.6	366.4
65°	239.2	248.3	258.0	277.6	313.0	329.5	349.1	384.4	404.0	362.6	300.2
67.5°	207.6	212.2	221.9	242.2	267.1	282.1	295.7	319.7	323.5	290.4	239.2
70°	178.3	179.8	188.8	200.9	219.7	228.7	240.0	254.3	254.3	227.2	186.6
72.5°	145.2	147.5	154.2	167.0	178.3	182.8	186.6	195.6	194.1	169.3	141.4
75°	116.6	118.1	123.4	129.4	133.9	142.2	145.2	143.7	142.9	121.9	106.1
77.5°	90.3	91.0	94.8	100.1	100.8	103.8	101.6	101.6	94.8	82.8	74.5
80°	66.2	67.0	68.5	70.0	70.0	70.0	70.0	66.2	61.7	54.2	51.9
82.5°	44.4	44.4	45.1	46.6	45.9	44.4	42.9	39.1	36.1	33.9	32.3
85°	26.3	26.3	27.1	26.3	23.3	22.6	21.1	20.3	19.6	18.8	18.8
87.5°	12.8	12.0	10.5	9.0	9.0	9.0	9.0	9.0	9.0	8.3	8.3
90°	1.3	3.6	5.9	8.2	10.5	11.6	12.6	14.6	16.6	18.6	20.6
92.5°	24.5	21.9	19.3	16.8	14.2	12.9	13.8	15.5	17.2	18.9	20.6
95°	73.4	72.6	71.7	70.9	70.0	69.6	64.2	53.3	42.4	31.5	20.6
97.5°	137.8	139.5	141.2	142.9	144.6	145.5	131.9	104.7	77.6	50.4	23.2
100°	215.1	216.0	216.8	217.7	218.6	219.0	219.6	220.7	221.8	223.0	224.1
102.5°	293.7	294.8	296.0	297.1	298.2	298.8	299.1	299.7	300.2	300.8	301.4
105°	378.7	379.8	381.0	382.1	383.2	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	466.3	466.3	466.3	466.3	466.3	466.3	466.6	467.1	467.7	468.2	468.8
110°	551.3	551.3	551.3	551.3	551.3	551.3	551.6	552.2	552.7	553.3	553.9

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	631.1	632.0	632.8	633.7	634.6	635.0	635.1	635.4	635.7	636.0	636.3
115°	711.0	712.4	713.8	715.3	716.7	717.4	717.5	717.8	718.1	718.4	718.7
117.5°	794.7	794.7	794.7	794.7	794.7	794.7	795.3	796.4	797.6	798.7	799.9
120°	872.0	871.7	871.4	871.1	870.8	870.7	871.1	872.0	872.9	873.7	874.6
122.5°	940.3	941.7	943.1	944.6	946.0	946.7	946.8	947.1	947.4	947.7	948.0
125°	1011.1	1013.1	1015.1	1017.1	1019.1	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1
127.5°	1079.4	1080.8	1082.2	1083.7	1085.1	1085.8	1085.7	1085.4	1085.1	1084.8	1084.5
130°	1141.2	1142.6	1144.0	1145.5	1146.9	1147.6	1147.7	1148.0	1148.3	1148.6	1148.9
132.5°	1203.0	1204.7	1206.5	1208.2	1209.9	1210.8	1210.4	1209.5	1208.6	1207.8	1206.9
135°	1261.0	1262.7	1264.4	1266.1	1267.8	1268.7	1268.4	1267.8	1267.3	1266.7	1266.1
137.5°	1315.1	1316.8	1318.5	1320.2	1321.9	1322.8	1322.5	1321.9	1321.4	1320.8	1320.2
140°	1367.9	1368.5	1369.1	1369.6	1370.2	1370.5	1370.4	1370.1	1369.8	1369.5	1369.2
142.5°	1415.6	1415.9	1416.1	1416.4	1416.7	1416.8	1417.1	1417.7	1418.2	1418.8	1419.4
145°	1461.9	1462.5	1463.1	1463.6	1464.2	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5
147.5°	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.2	1503.5	1503.8	1504.1	1504.4
150°	1541.8	1541.2	1540.6	1540.1	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8
152.5°	1579.1	1577.7	1576.3	1574.8	1573.4	1572.7	1573.0	1573.6	1574.1	1574.7	1575.3
155°	1610.0	1608.3	1606.6	1604.9	1603.2	1602.3	1602.6	1603.2	1603.7	1604.3	1604.9
157.5°	1634.5	1633.7	1632.8	1632.0	1631.1	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7
160°	1660.3	1658.6	1656.9	1655.2	1653.5	1652.6	1652.7	1653.0	1653.3	1653.5	1653.8
162.5°	1680.9	1679.2	1677.5	1675.8	1674.1	1673.2	1673.3	1673.6	1673.9	1674.1	1674.4
165°	1698.9	1697.2	1695.5	1693.8	1692.1	1691.2	1691.3	1691.6	1691.9	1692.2	1692.5
167.5°	1713.1	1711.4	1709.7	1708.0	1706.3	1705.4	1705.5	1705.8	1706.1	1706.3	1706.6
170°	1724.7	1722.7	1720.7	1718.7	1716.7	1715.7	1715.8	1716.1	1716.4	1716.7	1717.0
172.5°	1732.4	1730.4	1728.4	1726.4	1724.4	1723.4	1723.7	1724.3	1724.8	1725.4	1726.0
175°	1737.6	1735.9	1734.1	1732.4	1730.7	1729.8	1729.9	1730.2	1730.5	1730.8	1731.1
177.5°	1741.4	1739.7	1738.0	1736.3	1734.6	1733.7	1733.8	1734.1	1734.4	1734.7	1735.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3
2.5°	956.2	961.5	966.0	963.7	972.7	972.0	973.5	976.5	977.3	975.8	972.7
5°	1008.1	1015.6	1028.4	1035.2	1033.7	1039.7	1042.7	1047.2	1051.7	1050.2	1050.2
7.5°	1066.0	1076.6	1089.4	1106.7	1108.9	1114.2	1123.2	1123.2	1128.5	1126.2	1125.5
10°	1116.4	1129.2	1149.5	1163.1	1169.1	1172.1	1181.1	1184.1	1190.2	1190.9	1190.9
12.5°	1157.8	1180.4	1193.9	1207.5	1210.5	1215.0	1221.8	1226.3	1228.5	1228.5	1226.3
15°	1179.6	1197.7	1213.5	1227.8	1236.1	1239.8	1246.6	1251.9	1254.9	1261.6	1263.1
17.5°	1188.7	1210.5	1236.1	1256.4	1270.7	1274.4	1288.0	1292.5	1298.5	1301.5	1305.3
20°	1201.4	1233.0	1263.9	1288.7	1302.3	1312.0	1326.3	1347.4	1353.4	1353.4	1351.2
22.5°	1212.7	1253.4	1295.5	1335.4	1346.6	1366.2	1392.5	1415.1	1424.1	1427.9	1424.9
25°	1226.3	1281.9	1336.9	1386.5	1417.4	1431.7	1467.0	1494.1	1504.6	1510.7	1512.2
27.5°	1249.6	1319.6	1389.5	1452.7	1484.3	1500.9	1537.7	1561.1	1573.8	1579.1	1575.4
30°	1275.9	1361.7	1442.9	1499.4	1520.4	1540.7	1564.8	1573.8	1570.8	1570.8	1582.1
32.5°	1303.0	1391.8	1464.0	1500.9	1508.4	1505.4	1495.6	1468.5	1452.7	1452.7	1462.5
35°	1318.1	1394.8	1431.7	1419.6	1390.3	1373.0	1319.6	1289.5	1255.6	1253.4	1264.6
37.5°	1309.8	1342.9	1327.8	1248.8	1209.0	1175.9	1092.4	1059.3	1034.4	999.8	1053.2
40°	1251.9	1240.6	1162.3	1048.7	1004.3	957.7	891.5	858.4	823.8	818.5	831.3
42.5°	1154.1	1087.1	972.7	862.9	817.8	784.7	734.3	701.9	680.1	671.1	686.1
45°	1032.2	926.9	812.5	725.2	675.6	658.3	612.4	583.8	567.2	560.5	571.0
47.5°	883.2	777.1	668.8	595.1	565.7	548.4	517.6	492.8	478.5	474.0	478.5
50°	750.1	641.0	549.9	502.5	476.2	461.9	436.3	420.5	409.3	406.3	413.8
52.5°	635.0	535.6	466.4	424.3	407.0	395.0	376.9	363.4	356.6	353.6	358.9
55°	531.9	451.4	395.7	359.6	346.8	339.3	323.5	316.0	308.4	307.7	313.0
57.5°	440.9	385.2	334.0	308.4	304.7	293.4	279.9	273.1	269.3	268.6	270.8
60°	367.1	317.5	286.6	264.1	258.8	249.8	242.2	237.7	233.2	231.7	233.2
62.5°	305.4	266.3	241.5	226.4	218.9	216.7	208.4	203.1	202.4	202.4	203.9
65°	252.0	218.9	203.1	191.1	185.8	183.6	177.5	173.8	174.5	174.5	175.3
67.5°	205.4	181.3	167.0	161.0	156.5	155.7	149.7	148.2	146.7	146.7	148.2
70°	163.3	148.2	137.7	134.7	133.9	128.6	126.4	125.6	123.4	124.1	124.1
72.5°	127.9	118.1	112.1	107.6	108.3	105.3	102.3	102.3	100.8	103.1	103.1
75°	94.8	90.3	85.8	84.3	85.8	84.3	82.0	81.3	82.0	81.3	81.3
77.5°	70.0	67.7	66.2	65.5	65.5	62.4	60.9	62.4	59.4	60.9	60.9
80°	48.9	45.9	45.1	43.6	44.4	42.1	42.9	41.4	41.4	41.4	41.4
82.5°	30.8	30.1	30.1	30.1	29.3	29.3	29.3	29.3	29.3	29.3	28.6
85°	18.8	18.1	18.1	18.1	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	7.5	8.3	8.3	9.0	8.3	7.5	7.5	7.5	8.3	8.3	7.5
90°	22.0	23.4	24.9	26.3	27.0	27.4	28.3	29.2	30.0	30.9	30.0
92.5°	22.0	23.4	24.9	26.3	27.0	27.1	27.4	27.7	28.0	28.3	28.0
95°	22.0	23.4	24.9	26.3	27.0	27.0	27.0	27.0	27.0	27.0	27.0
97.5°	23.8	24.4	24.9	25.5	25.8	25.9	26.2	26.5	26.7	27.0	26.7
100°	181.5	138.8	96.2	53.5	32.2	31.6	30.5	29.3	28.2	27.0	28.2
102.5°	302.0	302.6	303.1	303.7	304.0	292.0	267.9	243.9	219.8	195.8	219.8
105°	383.8	383.8	383.8	383.8	383.8	383.7	383.4	383.1	382.8	382.5	382.8
107.5°	469.1	469.4	469.7	470.0	470.1	469.5	468.4	467.3	466.1	465.0	466.1
110°	553.0	552.2	551.3	550.4	550.0	550.1	550.4	550.7	551.0	551.3	551.0

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	635.1	634.0	632.8	631.7	631.1	630.8	630.3	629.7	629.2	628.6	629.2
115°	717.6	716.4	715.3	714.2	713.6	712.7	711.0	709.3	707.5	705.8	707.5
117.5°	798.2	796.4	794.7	793.0	792.1	791.8	791.3	790.7	790.2	789.6	790.2
120°	874.0	873.4	872.9	872.3	872.0	871.3	869.9	868.4	867.0	865.6	867.0
122.5°	947.4	946.8	946.3	945.7	945.4	944.5	942.8	941.1	939.4	937.7	939.4
125°	1019.0	1017.8	1016.7	1015.6	1015.0	1014.6	1013.7	1012.8	1012.0	1011.1	1012.0
127.5°	1083.9	1083.4	1082.8	1082.3	1082.0	1080.8	1078.5	1076.2	1073.9	1071.6	1073.9
130°	1148.1	1147.2	1146.4	1145.5	1145.1	1144.4	1142.9	1141.5	1140.0	1138.6	1140.0
132.5°	1206.9	1206.9	1206.9	1206.9	1206.9	1206.2	1204.8	1203.3	1201.9	1200.5	1201.9
135°	1265.5	1265.0	1264.4	1263.9	1263.6	1262.7	1261.0	1259.3	1257.5	1255.8	1257.5
137.5°	1320.2	1320.2	1320.2	1320.2	1320.2	1319.5	1318.1	1316.6	1315.2	1313.8	1315.2
140°	1369.8	1370.4	1370.9	1371.5	1371.8	1370.9	1369.2	1367.5	1365.7	1364.0	1365.7
142.5°	1419.4	1419.4	1419.4	1419.4	1419.4	1418.5	1416.8	1415.1	1413.4	1411.7	1413.4
145°	1464.8	1465.1	1465.4	1465.7	1465.8	1464.9	1463.2	1461.5	1459.8	1458.1	1459.8
147.5°	1504.7	1505.0	1505.3	1505.6	1505.7	1504.7	1502.7	1500.7	1498.7	1496.7	1498.7
150°	1542.4	1543.0	1543.5	1544.1	1544.4	1543.3	1541.0	1538.7	1536.4	1534.1	1536.4
152.5°	1575.9	1576.4	1577.0	1577.5	1577.8	1576.8	1574.8	1572.8	1570.8	1568.8	1570.8
155°	1605.8	1606.6	1607.5	1608.4	1608.8	1607.7	1605.4	1603.1	1600.8	1598.5	1600.8
157.5°	1631.5	1632.4	1633.2	1634.1	1634.5	1633.4	1631.1	1628.8	1626.5	1624.2	1626.5
160°	1655.0	1656.1	1657.3	1658.4	1659.0	1657.9	1655.6	1653.3	1651.0	1648.7	1651.0
162.5°	1676.1	1677.9	1679.6	1681.3	1682.2	1680.9	1678.3	1675.8	1673.2	1670.6	1673.2
165°	1694.2	1695.9	1697.6	1699.3	1700.2	1699.1	1696.8	1694.5	1692.2	1689.9	1692.2
167.5°	1708.6	1710.6	1712.7	1714.7	1715.7	1714.4	1711.8	1709.3	1706.7	1704.1	1706.7
170°	1719.3	1721.6	1723.9	1726.2	1727.3	1726.0	1723.4	1720.9	1718.3	1715.7	1718.3
172.5°	1728.0	1730.0	1732.0	1734.0	1735.0	1733.7	1731.1	1728.6	1726.0	1723.4	1726.0
175°	1733.4	1735.7	1738.0	1740.3	1741.4	1740.1	1737.5	1735.0	1732.4	1729.8	1732.4
177.5°	1737.0	1739.0	1741.0	1743.0	1744.0	1742.9	1740.6	1738.3	1736.0	1733.7	1736.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3
2.5°	976.5	971.2	973.5	971.2	969.0	966.7	961.5	953.9	947.9	943.4	942.7
5°	1051.7	1045.0	1040.5	1038.2	1033.7	1027.7	1017.9	1006.6	993.1	987.8	977.3
7.5°	1121.0	1118.7	1108.2	1106.7	1103.6	1092.4	1075.8	1060.8	1043.5	1029.2	1015.6
10°	1186.4	1181.1	1173.6	1163.1	1161.6	1147.3	1131.5	1110.4	1087.8	1074.3	1050.2
12.5°	1227.0	1221.0	1212.7	1206.0	1202.2	1193.2	1171.4	1150.3	1130.0	1105.2	1084.1
15°	1256.4	1248.8	1233.8	1228.5	1224.0	1212.0	1196.2	1174.4	1147.3	1130.0	1099.9
17.5°	1296.2	1287.2	1272.2	1262.4	1254.1	1235.3	1212.7	1183.4	1157.8	1138.3	1111.2
20°	1342.1	1328.6	1309.0	1296.2	1284.2	1262.4	1230.8	1196.2	1159.3	1135.2	1107.4
22.5°	1418.1	1392.5	1361.7	1343.6	1327.1	1289.5	1251.9	1209.0	1167.6	1131.5	1097.6
25°	1491.8	1466.3	1427.9	1403.1	1377.5	1333.9	1284.2	1224.8	1172.1	1130.0	1085.6
27.5°	1560.3	1534.0	1498.6	1468.5	1443.7	1378.2	1312.8	1245.8	1178.9	1121.0	1075.8
30°	1576.1	1564.8	1537.7	1511.4	1488.8	1428.6	1352.7	1267.7	1187.2	1112.7	1062.3
32.5°	1480.6	1508.4	1515.2	1511.4	1497.1	1454.2	1384.3	1294.7	1199.2	1108.9	1039.7
35°	1281.9	1332.4	1384.3	1412.1	1425.6	1431.7	1390.3	1308.3	1207.5	1102.9	1024.7
37.5°	1063.0	1111.9	1193.9	1235.3	1281.2	1341.4	1357.9	1305.3	1203.7	1098.4	1000.6
40°	873.4	935.9	1003.6	1041.2	1081.1	1189.4	1271.4	1265.4	1191.7	1081.8	981.8
42.5°	710.9	750.1	809.5	850.9	899.8	1020.9	1130.7	1184.9	1155.6	1061.5	957.7
45°	592.8	622.9	665.0	707.2	737.3	847.1	977.3	1066.0	1093.9	1025.4	920.8
47.5°	499.5	522.1	559.0	585.3	617.7	704.2	817.0	941.9	1000.6	974.2	881.7
50°	428.1	446.1	475.5	492.0	520.6	595.1	680.8	811.7	900.5	903.5	829.8
52.5°	365.6	383.7	408.5	422.8	440.1	490.5	577.0	687.6	789.9	827.5	770.4
55°	318.2	328.8	349.1	360.4	376.2	425.1	480.0	574.0	680.8	742.5	706.4
57.5°	274.6	285.9	298.7	307.7	319.0	358.1	407.8	478.5	584.5	651.5	639.5
60°	239.2	246.0	258.0	264.8	275.3	300.9	335.5	406.3	490.5	553.7	560.5
62.5°	206.1	212.2	220.4	226.4	233.2	253.5	279.1	329.5	403.2	471.7	480.7
65°	177.5	182.8	187.3	192.6	197.9	210.6	232.5	271.6	328.8	392.7	412.3
67.5°	152.0	153.5	160.2	161.0	164.0	173.8	189.6	221.2	262.6	313.7	339.3
70°	127.1	130.2	131.7	133.9	136.9	143.7	156.5	173.0	203.9	245.3	269.3
72.5°	103.1	103.8	106.1	107.6	110.6	115.9	121.9	134.7	154.2	184.3	206.1
75°	82.0	82.8	84.3	85.0	87.3	88.8	91.8	100.8	114.4	132.4	148.2
77.5°	61.7	63.2	64.7	64.7	65.5	67.0	68.5	71.5	78.2	90.3	103.8
80°	42.1	42.9	42.9	43.6	42.9	45.1	47.4	51.2	54.2	57.9	64.7
82.5°	29.3	29.3	29.3	30.1	30.1	30.8	30.8	31.6	32.3	34.6	37.6
85°	18.1	18.1	18.8	17.3	18.1	18.8	18.8	18.1	18.8	19.6	20.3
87.5°	7.5	7.5	8.3	8.3	8.3	8.3	7.5	8.3	7.5	8.3	8.3
90°	29.2	28.3	27.4	27.0	26.3	24.9	23.4	22.0	20.6	18.6	16.6
92.5°	27.7	27.4	27.1	27.0	26.3	24.9	23.4	22.0	20.6	18.9	17.2
95°	27.0	27.0	27.0	27.0	26.3	24.9	23.4	22.0	20.6	31.5	42.4
97.5°	26.5	26.2	25.9	25.8	25.5	24.9	24.4	23.8	23.2	50.4	77.6
100°	29.3	30.5	31.6	32.2	53.5	96.2	138.8	181.5	224.1	223.0	221.8
102.5°	243.9	267.9	292.0	304.0	303.7	303.1	302.6	302.0	301.4	300.8	300.2
105°	383.1	383.4	383.7	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	467.3	468.4	469.5	470.1	470.0	469.7	469.4	469.1	468.8	468.2	467.7
110°	550.7	550.4	550.1	550.0	550.4	551.3	552.2	553.0	553.9	553.3	552.7

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	629.7	630.3	630.8	631.1	631.7	632.8	634.0	635.1	636.3	636.0	635.7
115°	709.3	711.0	712.7	713.6	714.2	715.3	716.4	717.6	718.7	718.4	718.1
117.5°	790.7	791.3	791.8	792.1	793.0	794.7	796.4	798.2	799.9	798.7	797.6
120°	868.4	869.9	871.3	872.0	872.3	872.9	873.4	874.0	874.6	873.7	872.9
122.5°	941.1	942.8	944.5	945.4	945.7	946.3	946.8	947.4	948.0	947.7	947.4
125°	1012.8	1013.7	1014.6	1015.0	1015.6	1016.7	1017.8	1019.0	1020.1	1020.1	1020.1
127.5°	1076.2	1078.5	1080.8	1082.0	1082.3	1082.8	1083.4	1083.9	1084.5	1084.8	1085.1
130°	1141.5	1142.9	1144.4	1145.1	1145.5	1146.4	1147.2	1148.1	1148.9	1148.6	1148.3
132.5°	1203.3	1204.8	1206.2	1206.9	1206.9	1206.9	1206.9	1206.9	1206.9	1207.8	1208.6
135°	1259.3	1261.0	1262.7	1263.6	1263.9	1264.4	1265.0	1265.5	1266.1	1266.7	1267.3
137.5°	1316.6	1318.1	1319.5	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.8	1321.4
140°	1367.5	1369.2	1370.9	1371.8	1371.5	1370.9	1370.4	1369.8	1369.2	1369.5	1369.8
142.5°	1415.1	1416.8	1418.5	1419.4	1419.4	1419.4	1419.4	1419.4	1419.4	1418.8	1418.2
145°	1461.5	1463.2	1464.9	1465.8	1465.7	1465.4	1465.1	1464.8	1464.5	1464.5	1464.5
147.5°	1500.7	1502.7	1504.7	1505.7	1505.6	1505.3	1505.0	1504.7	1504.4	1504.1	1503.8
150°	1538.7	1541.0	1543.3	1544.4	1544.1	1543.5	1543.0	1542.4	1541.8	1541.2	1540.6
152.5°	1572.8	1574.8	1576.8	1577.8	1577.5	1577.0	1576.4	1575.9	1575.3	1574.7	1574.1
155°	1603.1	1605.4	1607.7	1608.8	1608.4	1607.5	1606.6	1605.8	1604.9	1604.3	1603.7
157.5°	1628.8	1631.1	1633.4	1634.5	1634.1	1633.2	1632.4	1631.5	1630.7	1630.7	1630.7
160°	1653.3	1655.6	1657.9	1659.0	1658.4	1657.3	1656.1	1655.0	1653.8	1653.5	1653.3
162.5°	1675.8	1678.3	1680.9	1682.2	1681.3	1679.6	1677.9	1676.1	1674.4	1674.1	1673.9
165°	1694.5	1696.8	1699.1	1700.2	1699.3	1697.6	1695.9	1694.2	1692.5	1692.2	1691.9
167.5°	1709.3	1711.8	1714.4	1715.7	1714.7	1712.7	1710.6	1708.6	1706.6	1706.3	1706.1
170°	1720.9	1723.4	1726.0	1727.3	1726.2	1723.9	1721.6	1719.3	1717.0	1716.7	1716.4
172.5°	1728.6	1731.1	1733.7	1735.0	1734.0	1732.0	1730.0	1728.0	1726.0	1725.4	1724.8
175°	1735.0	1737.5	1740.1	1741.4	1740.3	1738.0	1735.7	1733.4	1731.1	1730.8	1730.5
177.5°	1738.3	1740.6	1742.9	1744.0	1743.0	1741.0	1739.0	1737.0	1735.0	1734.7	1734.4
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3
2.5°	940.4	935.9	932.9	932.1	927.6	923.8	919.3	918.6	916.3	910.3	906.5
5°	969.7	959.2	956.9	950.2	938.9	930.6	920.1	914.1	907.3	896.0	887.0
7.5°	999.8	985.5	975.0	965.2	949.4	934.4	919.3	907.3	895.3	878.7	865.2
10°	1029.2	1007.4	994.6	980.3	958.5	935.9	914.8	897.5	878.0	858.4	838.8
12.5°	1056.3	1028.4	1009.6	989.3	962.2	934.4	907.3	883.2	862.9	836.6	814.8
15°	1072.8	1042.0	1023.2	1003.6	963.0	932.1	900.5	869.7	842.6	814.8	794.4
17.5°	1082.6	1048.0	1026.9	1008.9	967.5	925.3	884.7	851.6	822.3	789.2	762.1
20°	1078.1	1044.2	1024.7	1007.4	959.2	917.1	873.4	835.1	798.2	764.4	735.8
22.5°	1068.3	1032.9	1011.1	995.3	952.4	902.8	854.6	813.3	774.9	741.0	708.7
25°	1047.2	1012.6	993.8	974.2	932.1	884.7	835.8	791.4	750.8	714.7	678.6
27.5°	1028.4	986.3	966.7	949.4	905.0	862.9	814.8	765.9	724.5	686.9	650.8
30°	1006.6	959.2	938.1	914.8	874.9	835.1	786.9	741.8	698.9	659.0	624.4
32.5°	983.3	928.4	904.3	878.0	837.3	799.7	759.1	714.7	671.8	632.7	596.6
35°	953.2	894.5	866.7	841.8	799.7	762.1	724.5	687.6	644.7	603.4	568.8
37.5°	924.6	859.9	830.6	802.0	757.6	721.5	690.6	656.0	614.6	574.8	541.7
40°	892.2	817.8	787.7	761.3	715.5	675.6	647.7	620.7	584.5	546.2	510.1
42.5°	862.9	778.6	747.1	720.0	671.8	634.2	607.9	585.3	553.7	518.3	481.5
45°	822.3	736.5	704.2	675.6	626.7	591.3	564.2	544.7	519.9	486.7	453.6
47.5°	784.7	695.9	660.5	625.9	581.5	545.4	520.6	505.6	489.0	459.7	425.8
50°	738.8	649.2	613.1	584.5	534.1	503.3	478.5	467.9	452.9	425.1	398.0
52.5°	689.1	604.1	570.3	535.6	489.0	458.9	437.1	425.1	413.0	392.7	367.1
55°	631.2	553.7	522.1	491.3	444.6	416.8	397.2	384.4	377.7	358.9	340.0
57.5°	575.5	502.5	473.2	444.6	404.0	372.4	359.6	348.3	338.5	325.0	309.2
60°	519.1	452.9	421.3	395.7	360.4	331.8	321.2	310.0	302.4	291.9	280.6
62.5°	454.4	398.0	373.9	349.8	319.7	297.2	285.1	276.1	266.3	259.5	249.8
65°	385.9	346.1	322.7	304.7	276.1	255.8	246.8	240.7	232.5	225.7	218.2
67.5°	322.0	290.4	280.6	261.1	239.2	221.2	214.4	206.9	200.1	196.4	189.6
70°	260.3	237.7	228.0	222.7	198.6	186.6	180.6	177.5	169.3	165.5	161.0
72.5°	201.6	193.3	186.6	179.8	164.0	156.5	149.7	146.7	140.7	137.7	136.2
75°	149.0	143.7	139.9	139.2	132.4	124.9	118.1	116.6	112.1	109.1	107.6
77.5°	104.6	103.1	102.3	103.1	98.6	94.0	92.5	91.0	85.8	85.0	85.0
80°	68.5	72.2	72.2	71.5	70.0	69.2	67.0	65.5	62.4	61.7	62.4
82.5°	42.1	44.4	45.1	46.6	45.9	45.1	43.6	42.9	43.6	42.1	42.9
85°	21.1	22.6	25.6	25.6	26.3	26.3	26.3	25.6	24.1	24.8	24.1
87.5°	8.3	9.0	9.0	9.0	8.3	10.5	11.3	11.3	11.3	9.8	9.8
90°	14.6	12.6	11.6	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	15.5	13.8	12.9	14.2	16.8	19.3	21.9	24.5	21.9	19.3	16.8
95°	53.3	64.2	69.6	70.0	70.9	71.7	72.6	73.4	72.6	71.7	70.9
97.5°	104.7	131.9	145.5	144.6	142.9	141.2	139.5	137.8	139.5	141.2	142.9
100°	220.7	219.6	219.0	218.6	217.7	216.8	216.0	215.1	216.0	216.8	217.7
102.5°	299.7	299.1	298.8	298.2	297.1	296.0	294.8	293.7	294.8	296.0	297.1
105°	383.8	383.8	383.8	383.2	382.1	381.0	379.8	378.7	379.8	381.0	382.1
107.5°	467.1	466.6	466.3	466.3	466.3	466.3	466.3	466.3	466.3	466.3	466.3
110°	552.2	551.6	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	635.4	635.1	635.0	634.6	633.7	632.8	632.0	631.1	632.0	632.8	633.7
115°	717.8	717.5	717.4	716.7	715.3	713.8	712.4	711.0	712.4	713.8	715.3
117.5°	796.4	795.3	794.7	794.7	794.7	794.7	794.7	794.7	794.7	794.7	794.7
120°	872.0	871.1	870.7	870.8	871.1	871.4	871.7	872.0	871.7	871.4	871.1
122.5°	947.1	946.8	946.7	946.0	944.6	943.1	941.7	940.3	941.7	943.1	944.6
125°	1020.1	1020.1	1020.1	1019.1	1017.1	1015.1	1013.1	1011.1	1013.1	1015.1	1017.1
127.5°	1085.4	1085.7	1085.8	1085.1	1083.7	1082.2	1080.8	1079.4	1080.8	1082.2	1083.7
130°	1148.0	1147.7	1147.6	1146.9	1145.5	1144.0	1142.6	1141.2	1142.6	1144.0	1145.5
132.5°	1209.5	1210.4	1210.8	1209.9	1208.2	1206.5	1204.7	1203.0	1204.7	1206.5	1208.2
135°	1267.8	1268.4	1268.7	1267.8	1266.1	1264.4	1262.7	1261.0	1262.7	1264.4	1266.1
137.5°	1321.9	1322.5	1322.8	1321.9	1320.2	1318.5	1316.8	1315.1	1316.8	1318.5	1320.2
140°	1370.1	1370.4	1370.5	1370.2	1369.6	1369.1	1368.5	1367.9	1368.5	1369.1	1369.6
142.5°	1417.7	1417.1	1416.8	1416.7	1416.4	1416.1	1415.9	1415.6	1415.9	1416.1	1416.4
145°	1464.5	1464.5	1464.5	1464.2	1463.6	1463.1	1462.5	1461.9	1462.5	1463.1	1463.6
147.5°	1503.5	1503.2	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1
150°	1540.1	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8	1541.2	1540.6	1540.1
152.5°	1573.6	1573.0	1572.7	1573.4	1574.8	1576.3	1577.7	1579.1	1577.7	1576.3	1574.8
155°	1603.2	1602.6	1602.3	1603.2	1604.9	1606.6	1608.3	1610.0	1608.3	1606.6	1604.9
157.5°	1630.7	1630.7	1630.7	1631.1	1632.0	1632.8	1633.7	1634.5	1633.7	1632.8	1632.0
160°	1653.0	1652.7	1652.6	1653.5	1655.2	1656.9	1658.6	1660.3	1658.6	1656.9	1655.2
162.5°	1673.6	1673.3	1673.2	1674.1	1675.8	1677.5	1679.2	1680.9	1679.2	1677.5	1675.8
165°	1691.6	1691.3	1691.2	1692.1	1693.8	1695.5	1697.2	1698.9	1697.2	1695.5	1693.8
167.5°	1705.8	1705.5	1705.4	1706.3	1708.0	1709.7	1711.4	1713.1	1711.4	1709.7	1708.0
170°	1716.1	1715.8	1715.7	1716.7	1718.7	1720.7	1722.7	1724.7	1722.7	1720.7	1718.7
172.5°	1724.3	1723.7	1723.4	1724.4	1726.4	1728.4	1730.4	1732.4	1730.4	1728.4	1726.4
175°	1730.2	1729.9	1729.8	1730.7	1732.4	1734.1	1735.9	1737.6	1735.9	1734.1	1732.4
177.5°	1734.1	1733.8	1733.7	1734.6	1736.3	1738.0	1739.7	1741.4	1739.7	1738.0	1736.3
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3
2.5°	904.3	901.3	899.0	896.8	887.0	876.4	874.9	872.7	868.2	873.4	871.2
5°	881.0	874.2	870.4	860.6	848.6	839.6	832.1	823.0	819.3	816.3	815.5
7.5°	852.4	846.4	839.6	829.8	814.8	799.7	788.4	779.4	771.9	768.1	768.1
10°	824.5	817.0	808.0	791.4	777.1	758.3	746.3	737.3	726.7	720.7	715.5
12.5°	796.0	787.7	779.4	758.3	741.8	722.2	704.9	693.6	688.4	681.6	672.6
15°	767.4	754.6	746.3	725.2	704.2	684.6	673.3	661.3	649.2	642.5	639.5
17.5°	737.3	728.2	714.7	692.1	668.8	651.5	635.0	623.7	609.4	602.6	595.8
20°	710.2	696.6	683.1	660.5	638.0	614.6	598.1	584.5	575.5	570.3	564.2
22.5°	677.8	665.0	653.8	629.7	604.9	583.0	565.0	556.7	547.7	539.4	533.4
25°	650.0	637.2	625.9	599.6	572.5	552.2	538.7	528.1	518.3	514.6	508.6
27.5°	620.7	608.6	593.6	567.2	543.2	525.9	511.6	501.8	494.3	486.7	482.2
30°	592.8	579.3	565.7	537.2	517.6	500.3	486.7	474.7	468.7	464.9	457.4
32.5°	565.7	548.4	537.2	510.8	492.0	475.5	464.2	453.6	446.1	439.4	433.3
35°	536.4	517.6	506.3	484.5	464.9	448.4	438.6	431.1	422.0	416.0	413.0
37.5°	508.6	492.8	481.5	458.9	439.4	425.8	415.3	405.5	401.7	393.5	392.0
40°	478.5	464.9	454.4	432.6	414.5	404.0	392.7	383.7	376.9	373.1	367.9
42.5°	451.4	440.1	428.8	408.5	391.2	378.4	370.1	361.9	355.8	349.8	346.1
45°	426.6	414.5	404.0	384.4	367.1	355.8	347.6	337.8	336.3	328.0	324.2
47.5°	400.2	389.7	380.7	360.4	344.6	333.3	323.5	316.7	310.0	306.9	301.7
50°	374.7	364.1	353.6	335.5	321.2	310.0	300.2	292.7	288.9	284.4	279.9
52.5°	346.8	338.5	330.3	311.5	297.2	287.4	279.1	269.3	265.6	261.8	258.8
55°	323.5	311.5	302.4	286.6	273.8	263.3	254.3	246.8	243.0	240.0	236.2
57.5°	291.9	284.4	276.9	262.6	250.5	240.0	231.0	224.9	220.4	218.2	218.9
60°	264.8	256.5	252.0	237.0	224.9	216.7	208.4	202.4	197.9	195.6	194.8
62.5°	236.2	230.2	221.9	211.4	199.4	191.8	185.8	181.3	173.8	173.0	170.8
65°	208.4	203.9	196.4	186.6	176.8	170.0	163.3	157.2	154.2	150.5	148.2
67.5°	181.3	176.8	170.0	161.7	155.0	148.2	142.2	136.2	130.9	127.9	126.4
70°	155.0	151.2	146.7	136.9	128.6	123.4	118.9	115.1	109.8	108.3	107.6
72.5°	129.4	125.6	123.4	115.1	107.6	103.1	98.6	94.8	92.5	91.8	89.5
75°	106.1	102.3	99.3	91.8	87.3	84.3	79.7	78.2	76.0	75.2	74.5
77.5°	82.8	79.0	78.2	73.0	67.7	66.2	64.7	61.7	61.7	61.7	60.2
80°	59.4	58.7	57.9	52.7	50.4	48.9	48.1	45.9	44.4	42.9	42.1
82.5°	39.9	39.1	38.4	36.1	33.9	33.1	32.3	30.8	30.8	31.6	30.1
85°	24.1	22.6	21.8	21.1	19.6	19.6	20.3	19.6	19.6	19.6	18.8
87.5°	9.0	9.0	9.0	9.0	9.8	8.3	9.0	9.0	8.3	8.3	7.5
90°	10.5	11.6	12.6	14.6	16.6	18.6	20.6	22.0	23.4	24.9	26.3
92.5°	14.2	12.9	13.8	15.5	17.2	18.9	20.6	22.0	23.4	24.9	26.3
95°	70.0	69.6	64.2	53.3	42.4	31.5	20.6	22.0	23.4	24.9	26.3
97.5°	144.6	145.5	131.9	104.7	77.6	50.4	23.2	23.8	24.4	24.9	25.5
100°	218.6	219.0	219.6	220.7	221.8	223.0	224.1	181.5	138.8	96.2	53.5
102.5°	298.2	298.8	299.1	299.7	300.2	300.8	301.4	302.0	302.6	303.1	303.7
105°	383.2	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	466.3	466.3	466.6	467.1	467.7	468.2	468.8	469.1	469.4	469.7	470.0
110°	551.3	551.3	551.6	552.2	552.7	553.3	553.9	553.0	552.2	551.3	550.4

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	634.6	635.0	635.1	635.4	635.7	636.0	636.3	635.1	634.0	632.8	631.7
115°	716.7	717.4	717.5	717.8	718.1	718.4	718.7	717.6	716.4	715.3	714.2
117.5°	794.7	794.7	795.3	796.4	797.6	798.7	799.9	798.2	796.4	794.7	793.0
120°	870.8	870.7	871.1	872.0	872.9	873.7	874.6	874.0	873.4	872.9	872.3
122.5°	946.0	946.7	946.8	947.1	947.4	947.7	948.0	947.4	946.8	946.3	945.7
125°	1019.1	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1	1019.0	1017.8	1016.7	1015.6
127.5°	1085.1	1085.8	1085.7	1085.4	1085.1	1084.8	1084.5	1083.9	1083.4	1082.8	1082.3
130°	1146.9	1147.6	1147.7	1148.0	1148.3	1148.6	1148.9	1148.1	1147.2	1146.4	1145.5
132.5°	1209.9	1210.8	1210.4	1209.5	1208.6	1207.8	1206.9	1206.9	1206.9	1206.9	1206.9
135°	1267.8	1268.7	1268.4	1267.8	1267.3	1266.7	1266.1	1265.5	1265.0	1264.4	1263.9
137.5°	1321.9	1322.8	1322.5	1321.9	1321.4	1320.8	1320.2	1320.2	1320.2	1320.2	1320.2
140°	1370.2	1370.5	1370.4	1370.1	1369.8	1369.5	1369.2	1369.8	1370.4	1370.9	1371.5
142.5°	1416.7	1416.8	1417.1	1417.7	1418.2	1418.8	1419.4	1419.4	1419.4	1419.4	1419.4
145°	1464.2	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5	1464.8	1465.1	1465.4	1465.7
147.5°	1503.1	1503.1	1503.2	1503.5	1503.8	1504.1	1504.4	1504.7	1505.0	1505.3	1505.6
150°	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8	1542.4	1543.0	1543.5	1544.1
152.5°	1573.4	1572.7	1573.0	1573.6	1574.1	1574.7	1575.3	1575.9	1576.4	1577.0	1577.5
155°	1603.2	1602.3	1602.6	1603.2	1603.7	1604.3	1604.9	1605.8	1606.6	1607.5	1608.4
157.5°	1631.1	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7	1631.5	1632.4	1633.2	1634.1
160°	1653.5	1652.6	1652.7	1653.0	1653.3	1653.5	1653.8	1655.0	1656.1	1657.3	1658.4
162.5°	1674.1	1673.2	1673.3	1673.6	1673.9	1674.1	1674.4	1676.1	1677.9	1679.6	1681.3
165°	1692.1	1691.2	1691.3	1691.6	1691.9	1692.2	1692.5	1694.2	1695.9	1697.6	1699.3
167.5°	1706.3	1705.4	1705.5	1705.8	1706.1	1706.3	1706.6	1708.6	1710.6	1712.7	1714.7
170°	1716.7	1715.7	1715.8	1716.1	1716.4	1716.7	1717.0	1719.3	1721.6	1723.9	1726.2
172.5°	1724.4	1723.4	1723.7	1724.3	1724.8	1725.4	1726.0	1728.0	1730.0	1732.0	1734.0
175°	1730.7	1729.8	1729.9	1730.2	1730.5	1730.8	1731.1	1733.4	1735.7	1738.0	1740.3
177.5°	1734.6	1733.7	1733.8	1734.1	1734.4	1734.7	1735.0	1737.0	1739.0	1741.0	1743.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3
2.5°	867.4	868.9	865.2	863.7	860.6	864.4	865.2	864.4	871.2	868.2	869.7
5°	817.0	814.0	811.7	806.5	806.5	807.2	809.5	805.7	808.0	813.3	812.5
7.5°	761.3	759.8	760.6	754.6	750.1	751.6	750.1	756.8	760.6	759.1	762.1
10°	710.9	713.9	707.2	704.2	701.2	704.2	703.4	704.9	709.4	712.4	717.7
12.5°	670.3	669.6	665.8	662.8	657.5	659.0	663.5	662.0	662.8	669.6	668.8
15°	631.9	627.4	624.4	617.7	619.2	613.9	618.4	623.7	625.9	631.9	635.7
17.5°	593.6	592.8	589.1	588.3	580.0	577.8	582.3	583.8	586.1	589.1	594.3
20°	561.2	560.5	555.2	553.7	546.9	551.4	549.9	553.0	554.5	560.5	562.7
22.5°	531.9	528.1	526.6	524.4	522.1	521.4	524.4	523.6	528.9	531.1	531.9
25°	504.8	501.8	501.0	497.3	495.8	493.5	495.8	498.0	504.1	506.3	509.3
27.5°	480.0	477.7	476.2	473.2	471.0	471.0	472.5	475.5	477.7	479.2	480.7
30°	457.4	455.9	451.4	449.9	447.6	447.6	447.6	449.1	452.9	457.4	459.7
32.5°	434.1	431.1	428.1	428.1	425.8	425.8	426.6	428.1	431.8	432.6	436.3
35°	411.5	408.5	406.3	404.7	405.5	402.5	404.0	406.3	410.8	412.3	414.5
37.5°	389.7	388.9	384.4	382.2	383.7	383.7	382.9	384.4	387.4	390.5	392.0
40°	365.6	364.1	364.1	361.9	362.6	359.6	361.9	363.4	364.9	367.9	370.1
42.5°	344.6	343.1	340.0	340.8	338.5	338.5	340.0	340.8	343.1	346.8	348.3
45°	322.0	322.0	320.5	318.2	319.0	316.7	318.2	319.0	322.0	325.8	324.2
47.5°	300.2	299.4	299.4	296.4	297.9	295.7	297.9	298.7	300.2	302.4	301.7
50°	279.1	276.9	277.6	276.9	276.1	276.1	277.6	277.6	279.1	279.1	281.4
52.5°	257.3	257.3	255.8	256.5	258.0	256.5	258.8	256.5	258.0	258.8	260.3
55°	237.7	236.2	237.0	236.2	239.2	237.0	239.2	237.7	239.2	238.5	240.0
57.5°	216.7	214.4	215.2	214.4	216.7	215.9	218.2	215.9	216.7	217.4	219.7
60°	192.6	192.6	192.6	191.1	193.3	193.3	192.6	192.6	195.6	197.1	196.4
62.5°	170.0	169.3	167.0	166.3	167.0	165.5	168.5	167.8	169.3	170.8	172.3
65°	145.2	143.7	142.9	141.4	141.4	140.7	141.4	144.4	145.2	145.9	149.7
67.5°	124.9	124.1	123.4	121.1	121.1	122.6	122.6	122.6	127.1	124.9	127.9
70°	106.8	105.3	103.8	103.1	103.1	103.8	104.6	105.3	104.6	107.6	108.3
72.5°	89.5	90.3	88.8	88.8	88.8	88.0	88.0	89.5	90.3	89.5	90.3
75°	74.5	74.5	73.7	74.5	74.5	73.7	73.7	75.2	75.2	74.5	76.7
77.5°	60.2	59.4	57.9	56.4	57.2	56.4	57.2	56.4	58.7	60.9	59.4
80°	42.1	41.4	41.4	41.4	42.1	41.4	42.9	41.4	42.1	42.1	42.9
82.5°	30.1	30.8	30.8	30.1	30.8	30.1	30.8	30.8	30.8	30.1	30.8
85°	19.6	19.6	19.6	19.6	18.8	19.6	19.6	19.6	20.3	19.6	20.3
87.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.0	8.3	9.0
90°	27.0	27.4	28.3	29.2	30.0	30.9	30.0	29.2	28.3	27.4	27.0
92.5°	27.0	27.1	27.4	27.7	28.0	28.3	28.0	27.7	27.4	27.1	27.0
95°	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0
97.5°	25.8	25.9	26.2	26.5	26.7	27.0	26.7	26.5	26.2	25.9	25.8
100°	32.2	31.6	30.5	29.3	28.2	27.0	28.2	29.3	30.5	31.6	32.2
102.5°	304.0	292.0	267.9	243.9	219.8	195.8	219.8	243.9	267.9	292.0	304.0
105°	383.8	383.7	383.4	383.1	382.8	382.5	382.8	383.1	383.4	383.7	383.8
107.5°	470.1	469.5	468.4	467.3	466.1	465.0	466.1	467.3	468.4	469.5	470.1
110°	550.0	550.1	550.4	550.7	551.0	551.3	551.0	550.7	550.4	550.1	550.0

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	631.1	630.8	630.3	629.7	629.2	628.6	629.2	629.7	630.3	630.8	631.1
115°	713.6	712.7	711.0	709.3	707.5	705.8	707.5	709.3	711.0	712.7	713.6
117.5°	792.1	791.8	791.3	790.7	790.2	789.6	790.2	790.7	791.3	791.8	792.1
120°	872.0	871.3	869.9	868.4	867.0	865.6	867.0	868.4	869.9	871.3	872.0
122.5°	945.4	944.5	942.8	941.1	939.4	937.7	939.4	941.1	942.8	944.5	945.4
125°	1015.0	1014.6	1013.7	1012.8	1012.0	1011.1	1012.0	1012.8	1013.7	1014.6	1015.0
127.5°	1082.0	1080.8	1078.5	1076.2	1073.9	1071.6	1073.9	1076.2	1078.5	1080.8	1082.0
130°	1145.1	1144.4	1142.9	1141.5	1140.0	1138.6	1140.0	1141.5	1142.9	1144.4	1145.1
132.5°	1206.9	1206.2	1204.8	1203.3	1201.9	1200.5	1201.9	1203.3	1204.8	1206.2	1206.9
135°	1263.6	1262.7	1261.0	1259.3	1257.5	1255.8	1257.5	1259.3	1261.0	1262.7	1263.6
137.5°	1320.2	1319.5	1318.1	1316.6	1315.2	1313.8	1315.2	1316.6	1318.1	1319.5	1320.2
140°	1371.8	1370.9	1369.2	1367.5	1365.7	1364.0	1365.7	1367.5	1369.2	1370.9	1371.8
142.5°	1419.4	1418.5	1416.8	1415.1	1413.4	1411.7	1413.4	1415.1	1416.8	1418.5	1419.4
145°	1465.8	1464.9	1463.2	1461.5	1459.8	1458.1	1459.8	1461.5	1463.2	1464.9	1465.8
147.5°	1505.7	1504.7	1502.7	1500.7	1498.7	1496.7	1498.7	1500.7	1502.7	1504.7	1505.7
150°	1544.4	1543.3	1541.0	1538.7	1536.4	1534.1	1536.4	1538.7	1541.0	1543.3	1544.4
152.5°	1577.8	1576.8	1574.8	1572.8	1570.8	1568.8	1570.8	1572.8	1574.8	1576.8	1577.8
155°	1608.8	1607.7	1605.4	1603.1	1600.8	1598.5	1600.8	1603.1	1605.4	1607.7	1608.8
157.5°	1634.5	1633.4	1631.1	1628.8	1626.5	1624.2	1626.5	1628.8	1631.1	1633.4	1634.5
160°	1659.0	1657.9	1655.6	1653.3	1651.0	1648.7	1651.0	1653.3	1655.6	1657.9	1659.0
162.5°	1682.2	1680.9	1678.3	1675.8	1673.2	1670.6	1673.2	1675.8	1678.3	1680.9	1682.2
165°	1700.2	1699.1	1696.8	1694.5	1692.2	1689.9	1692.2	1694.5	1696.8	1699.1	1700.2
167.5°	1715.7	1714.4	1711.8	1709.3	1706.7	1704.1	1706.7	1709.3	1711.8	1714.4	1715.7
170°	1727.3	1726.0	1723.4	1720.9	1718.3	1715.7	1718.3	1720.9	1723.4	1726.0	1727.3
172.5°	1735.0	1733.7	1731.1	1728.6	1726.0	1723.4	1726.0	1728.6	1731.1	1733.7	1735.0
175°	1741.4	1740.1	1737.5	1735.0	1732.4	1729.8	1732.4	1735.0	1737.5	1740.1	1741.4
177.5°	1744.0	1742.9	1740.6	1738.3	1736.0	1733.7	1736.0	1738.3	1740.6	1742.9	1744.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3	916.3
2.5°	866.7	870.4	867.4	865.2	871.2	874.2	874.2	879.5	884.7	889.2	890.0
5°	813.3	819.3	820.8	820.0	829.1	833.6	843.3	848.6	856.1	861.4	867.4
7.5°	764.4	772.6	773.4	774.9	788.4	796.0	804.2	817.8	828.3	835.8	842.6
10°	715.5	720.7	726.0	732.8	746.3	759.1	771.1	785.4	799.0	806.5	816.3
12.5°	678.6	682.4	688.4	692.9	707.2	718.5	734.3	753.8	773.4	779.4	791.4
15°	640.2	642.5	654.5	659.0	671.1	689.9	699.7	718.5	739.5	750.8	764.4
17.5°	595.8	609.4	616.9	622.2	637.2	652.3	668.1	687.6	714.7	725.2	735.0
20°	564.2	574.0	582.3	589.1	602.6	625.2	639.5	655.3	680.8	692.9	707.2
22.5°	536.4	544.7	552.2	559.7	568.8	589.1	605.6	627.4	653.0	664.3	680.8
25°	510.1	518.3	522.9	531.9	543.9	558.2	577.8	597.3	622.9	635.7	651.5
27.5°	484.5	492.8	501.0	508.6	516.8	530.4	543.9	568.8	595.1	610.1	623.7
30°	462.7	466.4	474.0	482.2	490.5	503.3	519.1	536.4	566.5	580.0	596.6
32.5°	438.6	445.4	450.6	456.7	467.2	477.7	492.0	513.8	537.9	550.7	568.8
35°	416.0	422.0	425.8	436.3	443.1	454.4	468.7	488.3	508.6	522.9	538.7
37.5°	394.2	400.2	404.7	410.8	419.8	429.6	444.6	458.9	483.0	495.0	513.1
40°	371.6	376.9	382.2	388.9	397.2	409.3	418.3	436.3	455.9	469.4	483.0
42.5°	349.8	352.8	358.9	366.4	374.7	385.2	398.0	412.3	431.8	443.9	455.9
45°	326.5	331.8	338.5	343.8	351.3	361.9	373.1	385.9	405.5	417.5	430.3
47.5°	304.7	308.4	313.0	321.2	331.0	338.5	350.6	362.6	380.7	392.0	404.0
50°	282.1	285.9	292.7	297.9	305.4	315.2	326.5	339.3	356.6	364.1	376.2
52.5°	261.1	262.6	269.3	274.6	282.1	293.4	302.4	313.7	330.3	338.5	350.6
55°	240.0	241.5	245.3	250.5	258.8	267.8	277.6	290.4	304.7	312.2	323.5
57.5°	218.2	219.7	223.4	227.2	235.5	243.8	255.0	265.6	279.9	286.6	297.2
60°	196.4	196.4	200.1	205.4	211.4	218.9	228.7	241.5	252.0	260.3	267.8
62.5°	173.0	175.3	177.5	181.3	188.1	197.1	205.4	214.4	227.2	233.2	240.0
65°	149.7	152.0	156.5	160.2	165.5	171.5	182.1	189.6	199.4	206.1	212.2
67.5°	129.4	131.7	134.7	139.2	142.9	149.7	157.2	164.8	175.3	179.8	184.3
70°	108.3	110.6	112.8	118.9	122.6	127.9	133.2	140.7	149.7	152.7	156.5
72.5°	91.8	92.5	95.5	97.0	102.3	106.8	112.8	117.4	124.1	127.9	130.9
75°	77.5	77.5	78.2	79.7	82.8	85.8	90.3	94.8	100.8	103.1	106.8
77.5°	60.9	63.2	62.4	63.9	65.5	67.0	70.7	73.7	79.7	81.3	82.8
80°	43.6	44.4	46.6	48.9	48.9	51.2	53.4	54.2	57.9	60.2	60.2
82.5°	31.6	32.3	31.6	32.3	33.1	33.9	36.1	39.1	39.1	39.9	41.4
85°	19.6	19.6	20.3	21.1	21.1	20.3	21.8	21.1	21.8	23.3	23.3
87.5°	9.8	9.0	9.0	9.0	9.0	9.0	9.8	9.0	9.8	9.8	9.8
90°	26.3	24.9	23.4	22.0	20.6	18.6	16.6	14.6	12.6	11.6	10.5
92.5°	26.3	24.9	23.4	22.0	20.6	18.9	17.2	15.5	13.8	12.9	14.2
95°	26.3	24.9	23.4	22.0	20.6	31.5	42.4	53.3	64.2	69.6	70.0
97.5°	25.5	24.9	24.4	23.8	23.2	50.4	77.6	104.7	131.9	145.5	144.6
100°	53.5	96.2	138.8	181.5	224.1	223.0	221.8	220.7	219.6	219.0	218.6
102.5°	303.7	303.1	302.6	302.0	301.4	300.8	300.2	299.7	299.1	298.8	298.2
105°	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.2
107.5°	470.0	469.7	469.4	469.1	468.8	468.2	467.7	467.1	466.6	466.3	466.3
110°	550.4	551.3	552.2	553.0	553.9	553.3	552.7	552.2	551.6	551.3	551.3

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	631.7	632.8	634.0	635.1	636.3	636.0	635.7	635.4	635.1	635.0	634.6
115°	714.2	715.3	716.4	717.6	718.7	718.4	718.1	717.8	717.5	717.4	716.7
117.5°	793.0	794.7	796.4	798.2	799.9	798.7	797.6	796.4	795.3	794.7	794.7
120°	872.3	872.9	873.4	874.0	874.6	873.7	872.9	872.0	871.1	870.7	870.8
122.5°	945.7	946.3	946.8	947.4	948.0	947.7	947.4	947.1	946.8	946.7	946.0
125°	1015.6	1016.7	1017.8	1019.0	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1	1019.1
127.5°	1082.3	1082.8	1083.4	1083.9	1084.5	1084.8	1085.1	1085.4	1085.7	1085.8	1085.1
130°	1145.5	1146.4	1147.2	1148.1	1148.9	1148.6	1148.3	1148.0	1147.7	1147.6	1146.9
132.5°	1206.9	1206.9	1206.9	1206.9	1206.9	1207.8	1208.6	1209.5	1210.4	1210.8	1209.9
135°	1263.9	1264.4	1265.0	1265.5	1266.1	1266.7	1267.3	1267.8	1268.4	1268.7	1267.8
137.5°	1320.2	1320.2	1320.2	1320.2	1320.2	1320.8	1321.4	1321.9	1322.5	1322.8	1321.9
140°	1371.5	1370.9	1370.4	1369.8	1369.2	1369.5	1369.8	1370.1	1370.4	1370.5	1370.2
142.5°	1419.4	1419.4	1419.4	1419.4	1419.4	1418.8	1418.2	1417.7	1417.1	1416.8	1416.7
145°	1465.7	1465.4	1465.1	1464.8	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5	1464.2
147.5°	1505.6	1505.3	1505.0	1504.7	1504.4	1504.1	1503.8	1503.5	1503.2	1503.1	1503.1
150°	1544.1	1543.5	1543.0	1542.4	1541.8	1541.2	1540.6	1540.1	1539.5	1539.2	1539.5
152.5°	1577.5	1577.0	1576.4	1575.9	1575.3	1574.7	1574.1	1573.6	1573.0	1572.7	1573.4
155°	1608.4	1607.5	1606.6	1605.8	1604.9	1604.3	1603.7	1603.2	1602.6	1602.3	1603.2
157.5°	1634.1	1633.2	1632.4	1631.5	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7	1631.1
160°	1658.4	1657.3	1656.1	1655.0	1653.8	1653.5	1653.3	1653.0	1652.7	1652.6	1653.5
162.5°	1681.3	1679.6	1677.9	1676.1	1674.4	1674.1	1673.9	1673.6	1673.3	1673.2	1674.1
165°	1699.3	1697.6	1695.9	1694.2	1692.5	1692.2	1691.9	1691.6	1691.3	1691.2	1692.1
167.5°	1714.7	1712.7	1710.6	1708.6	1706.6	1706.3	1706.1	1705.8	1705.5	1705.4	1706.3
170°	1726.2	1723.9	1721.6	1719.3	1717.0	1716.7	1716.4	1716.1	1715.8	1715.7	1716.7
172.5°	1734.0	1732.0	1730.0	1728.0	1726.0	1725.4	1724.8	1724.3	1723.7	1723.4	1724.4
175°	1740.3	1738.0	1735.7	1733.4	1731.1	1730.8	1730.5	1730.2	1729.9	1729.8	1730.7
177.5°	1743.0	1741.0	1739.0	1737.0	1735.0	1734.7	1734.4	1734.1	1733.8	1733.7	1734.6
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	916.3	916.3	916.3	916.3
2.5°	895.3	902.0	908.8	917.1
5°	877.2	889.2	902.0	914.1
7.5°	857.6	874.9	891.5	908.8
10°	835.8	857.6	876.4	900.5
12.5°	811.7	835.1	861.4	888.5
15°	787.7	817.0	844.9	875.7
17.5°	765.1	792.9	823.8	860.6
20°	738.0	768.9	803.5	842.6
22.5°	709.4	743.3	780.9	823.0
25°	685.4	720.0	756.1	800.5
27.5°	659.0	695.1	730.5	777.9
30°	628.9	668.1	704.2	753.1
32.5°	600.3	639.5	679.3	725.2
35°	572.5	610.9	650.8	697.4
37.5°	546.2	580.8	619.9	662.0
40°	521.4	553.0	587.6	625.9
42.5°	489.8	526.6	559.0	586.8
45°	462.7	492.8	522.9	545.4
47.5°	431.1	461.2	486.7	504.8
50°	404.7	428.8	449.9	465.7
52.5°	373.1	395.7	413.0	425.1
55°	342.3	361.9	376.9	385.2
57.5°	314.5	327.3	338.5	346.1
60°	283.6	293.4	303.2	311.5
62.5°	250.5	261.1	266.3	275.3
65°	221.2	228.0	236.2	239.2
67.5°	192.6	196.4	201.6	207.6
70°	162.5	164.8	170.0	178.3
72.5°	136.2	138.4	142.2	145.2
75°	108.3	110.6	113.6	116.6
77.5°	85.0	85.8	87.3	90.3
80°	61.7	63.9	65.5	66.2
82.5°	42.9	43.6	43.6	44.4
85°	27.1	25.6	25.6	26.3
87.5°	9.8	11.3	11.3	12.8
90°	8.2	5.9	3.6	1.3
92.5°	16.8	19.3	21.9	24.5
95°	70.9	71.7	72.6	73.4
97.5°	142.9	141.2	139.5	137.8
100°	217.7	216.8	216.0	215.1
102.5°	297.1	296.0	294.8	293.7
105°	382.1	381.0	379.8	378.7
107.5°	466.3	466.3	466.3	466.3
110°	551.3	551.3	551.3	551.3

TEST NUMBER: P1036000

CATALOG NUMBER: S125RDIW-B610D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	633.7	632.8	632.0	631.1
115°	715.3	713.8	712.4	711.0
117.5°	794.7	794.7	794.7	794.7
120°	871.1	871.4	871.7	872.0
122.5°	944.6	943.1	941.7	940.3
125°	1017.1	1015.1	1013.1	1011.1
127.5°	1083.7	1082.2	1080.8	1079.4
130°	1145.5	1144.0	1142.6	1141.2
132.5°	1208.2	1206.5	1204.7	1203.0
135°	1266.1	1264.4	1262.7	1261.0
137.5°	1320.2	1318.5	1316.8	1315.1
140°	1369.6	1369.1	1368.5	1367.9
142.5°	1416.4	1416.1	1415.9	1415.6
145°	1463.6	1463.1	1462.5	1461.9
147.5°	1503.1	1503.1	1503.1	1503.1
150°	1540.1	1540.6	1541.2	1541.8
152.5°	1574.8	1576.3	1577.7	1579.1
155°	1604.9	1606.6	1608.3	1610.0
157.5°	1632.0	1632.8	1633.7	1634.5
160°	1655.2	1656.9	1658.6	1660.3
162.5°	1675.8	1677.5	1679.2	1680.9
165°	1693.8	1695.5	1697.2	1698.9
167.5°	1708.0	1709.7	1711.4	1713.1
170°	1718.7	1720.7	1722.7	1724.7
172.5°	1726.4	1728.4	1730.4	1732.4
175°	1732.4	1734.1	1735.9	1737.6
177.5°	1736.3	1738.0	1739.7	1741.4
180°	1737.6	1737.6	1737.6	1737.6

(END OF REPORT)