

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036046

Luminaire Tested: S125RDIW-B610D770UB27-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036046
REPORT IS A COMBINATION OF REPORTS P1006755 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D770UB27-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5465.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43		
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37		
2	88	81	75	70	81	75	69	65	62	58	55	50	48	46	40	38	37	32		
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	36	33	32	27		
4	74	64	56	50	67	58	52	47	49	44	40	40	37	34	32	29	27	24		
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21		
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	26	23	21	18		
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19	16		
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15		
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13		
10	47	35	28	23	43	32	26	22	28	23	19	23	19	16	19	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5854	5854	5854	5854
5°	5849	6597	5849	5071
10°	5816	7414	5797	4384
15°	5753	7843	5713	3817
20°	5676	8467	5626	3450
25°	5577	9584	5514	3131
30°	5476	10187	5394	2903
35°	5345	8378	5270	2690
40°	5113	5689	5069	2499
45°	4807	4090	4801	2311
50°	4494	3145	4516	2138
55°	4143	2557	4134	1970
60°	3814	2096	3795	1749
65°	3432	1746	3453	1408
70°	3117	1402	3103	1172
75°	2633	1062	2633	963
80°	2133	648	2110	648
85°	1504	342	1458	385

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8332 cd/sqm

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.6	1.6
10°-20°	256.9	4.7
20°-30°	407.3	7.5
30°-40°	492.1	9.0
40°-50°	438.1	8.0
50°-60°	336.0	6.1
60°-70°	218.2	4.0
70°-80°	105.9	1.9
80°-90°	26.4	0.5
90°-100°	34.2	0.6
100°-110°	227.5	4.2
110°-120°	409.7	7.5
120°-130°	525.9	9.6
130°-140°	565.6	10.3
140°-150°	530.8	9.7
150°-160°	429.4	7.9
160°-170°	277.7	5.1
170°-180°	95.8	1.8
0°-30°	751.7	13.8
0°-40°	1243.9	22.8
0°-60°	2018.0	36.9
0°-90°	2368.5	43.3
90°-120°	671.4	12.3
90°-150°	2293.7	42.0
90°-180°	3097.0	56.7
0°-180°	5465.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	914	914	914	914	914	
5°	911	1047	911	805	911	87
15°	873	1258	867	612	873	246
25°	798	1506	789	492	798	368
35°	695	1250	686	401	695	433
45°	544	559	543	316	544	420
55°	384	307	383	236	384	344
65°	238	174	240	140	238	238
75°	116	81	116	74	116	125
85°	26	17	26	20	26	30
90°	1	18	1	18	1	4
95°	43	16	43	16	43	52
105°	220	222	220	222	220	233
115°	412	410	412	410	412	409
125°	587	587	587	587	587	524
135°	732	729	732	729	732	564
145°	848	846	848	846	848	530
155°	934	927	934	927	934	430
165°	986	980	986	980	986	278
175°	1008	1004	1008	1004	1008	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	914.4	921.9	924.1	930.1	936.9	938.4	942.1	947.4	950.4	949.6	949.6
5°	911.4	924.1	933.1	943.6	956.4	961.6	966.1	977.4	986.4	991.6	1000.6
7.5°	906.1	924.9	939.9	955.6	975.1	984.1	993.9	1009.6	1026.1	1036.6	1046.4
10°	897.9	921.9	942.9	966.1	992.4	1005.9	1017.9	1041.9	1062.1	1075.6	1098.1
12.5°	885.9	915.9	945.1	975.9	1008.9	1023.1	1039.6	1065.9	1094.4	1113.9	1132.6
15°	873.1	909.1	940.6	977.4	1017.1	1038.9	1059.9	1087.6	1113.1	1134.9	1156.7
17.5°	858.1	896.4	935.4	977.4	1022.4	1044.1	1062.1	1095.1	1122.1	1143.9	1163.4
20°	840.1	882.9	927.1	973.6	1019.4	1039.6	1056.9	1092.9	1116.9	1140.1	1167.9
22.5°	820.6	867.1	914.4	960.1	1005.1	1026.9	1047.1	1078.6	1104.9	1136.4	1172.4
25°	798.1	849.1	897.1	942.9	985.6	1005.9	1023.9	1058.4	1095.1	1134.9	1175.4
27.5°	775.6	825.1	871.6	913.6	960.1	978.9	996.9	1040.4	1083.9	1125.9	1181.4
30°	750.8	801.1	841.6	880.6	925.6	945.1	967.6	1017.1	1066.6	1123.6	1191.2
32.5°	723.1	768.9	806.4	846.9	887.4	911.4	939.9	993.9	1050.9	1119.1	1205.4
35°	695.3	732.1	766.6	804.9	853.6	879.1	906.9	963.9	1035.1	1116.9	1217.4
37.5°	660.1	695.3	722.3	761.3	811.6	841.6	869.4	935.4	1016.4	1111.6	1216.7
40°	624.1	654.1	679.6	720.1	774.9	802.6	832.6	904.6	996.9	1096.6	1198.7
42.5°	585.1	610.6	638.3	677.3	730.6	757.6	792.1	876.1	969.9	1075.6	1152.2
45°	543.8	568.6	591.8	632.3	685.6	714.8	752.3	838.6	936.9	1031.4	1077.1
47.5°	503.3	525.1	549.8	585.1	639.1	671.3	709.6	801.9	892.6	972.1	975.9
50°	464.3	481.6	502.6	538.6	594.8	625.6	665.3	751.6	840.1	894.9	858.1
52.5°	423.8	439.6	461.3	492.8	545.3	581.3	615.8	702.1	776.4	813.1	745.6
55°	384.1	397.6	420.1	455.3	501.1	528.8	564.1	644.3	709.6	710.3	636.8
57.5°	345.0	357.0	375.8	407.3	450.1	482.3	514.6	584.3	628.6	615.8	534.1
60°	310.5	318.0	335.3	366.0	405.8	429.1	463.6	522.1	551.3	528.1	440.3
62.5°	274.5	282.0	295.5	320.3	357.8	382.6	404.3	452.3	472.6	437.3	365.3
65°	238.5	247.5	257.3	276.8	312.0	328.5	348.0	383.3	402.8	361.5	299.3
67.5°	207.0	211.5	221.3	241.5	266.3	281.3	294.8	318.8	322.5	289.5	238.5
70°	177.8	179.3	188.3	200.3	219.0	228.0	239.3	253.5	253.5	226.5	186.0
72.5°	144.8	147.0	153.8	166.5	177.8	182.3	186.0	195.0	193.5	168.8	141.0
75°	116.3	117.8	123.0	129.0	133.5	141.8	144.8	143.3	142.5	121.5	105.8
77.5°	90.0	90.8	94.5	99.8	100.5	103.5	101.3	101.3	94.5	82.5	74.3
80°	66.0	66.8	68.3	69.8	69.8	69.8	69.8	66.0	61.5	54.0	51.8
82.5°	44.3	44.3	45.0	46.5	45.8	44.3	42.8	39.0	36.0	33.8	32.3
85°	26.3	26.3	27.0	26.3	23.3	22.5	21.0	20.3	19.5	18.8	18.8
87.5°	12.8	12.0	10.5	9.0	9.0	9.0	9.0	9.0	9.0	8.3	8.3
90°	0.7	2.0	3.4	4.7	6.0	6.7	7.3	8.5	9.6	10.8	12.0
92.5°	14.2	12.7	11.2	9.7	8.2	7.5	8.0	9.0	10.0	11.0	12.0
95°	42.6	42.1	41.6	41.1	40.6	40.4	37.2	30.9	24.6	18.3	12.0
97.5°	80.0	81.0	82.0	82.9	83.9	84.4	76.5	60.8	45.0	29.3	13.5
100°	124.8	125.3	125.8	126.3	126.8	127.0	127.3	128.0	128.7	129.3	130.0
102.5°	170.4	171.1	171.7	172.4	173.1	173.4	173.6	173.9	174.2	174.6	174.9
105°	219.7	220.4	221.0	221.7	222.4	222.7	222.7	222.7	222.7	222.7	222.7
107.5°	270.5	270.5	270.5	270.5	270.5	270.5	270.7	271.0	271.3	271.7	272.0
110°	319.8	319.8	319.8	319.8	319.8	319.8	320.0	320.3	320.6	321.0	321.3

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	366.2	366.7	367.2	367.7	368.2	368.4	368.5	368.6	368.8	368.9	369.1
115°	412.5	413.3	414.1	415.0	415.8	416.2	416.3	416.5	416.6	416.8	417.0
117.5°	461.1	461.1	461.1	461.1	461.1	461.1	461.4	462.1	462.7	463.4	464.0
120°	505.9	505.7	505.5	505.4	505.2	505.1	505.4	505.9	506.4	506.9	507.4
122.5°	545.5	546.3	547.1	548.0	548.8	549.2	549.3	549.5	549.6	549.8	550.0
125°	586.6	587.8	588.9	590.1	591.2	591.8	591.8	591.8	591.8	591.8	591.8
127.5°	626.2	627.0	627.8	628.7	629.5	629.9	629.8	629.7	629.5	629.4	629.2
130°	662.1	662.9	663.7	664.6	665.4	665.8	665.9	666.1	666.2	666.4	666.6
132.5°	697.9	698.9	699.9	700.9	701.9	702.4	702.2	701.7	701.2	700.7	700.2
135°	731.6	732.6	733.6	734.5	735.5	736.0	735.8	735.5	735.2	734.9	734.6
137.5°	762.9	763.9	764.9	765.9	766.9	767.4	767.2	766.9	766.6	766.2	765.9
140°	793.6	793.9	794.3	794.6	794.9	795.1	795.0	794.8	794.7	794.5	794.3
142.5°	821.2	821.4	821.6	821.7	821.9	822.0	822.2	822.5	822.8	823.2	823.5
145°	848.1	848.4	848.8	849.1	849.4	849.6	849.6	849.6	849.6	849.6	849.6
147.5°	872.0	872.0	872.0	872.0	872.0	872.0	872.1	872.3	872.4	872.6	872.8
150°	894.5	894.2	893.8	893.5	893.2	893.0	893.2	893.5	893.8	894.2	894.5
152.5°	916.1	915.3	914.5	913.6	912.8	912.4	912.6	912.9	913.2	913.6	913.9
155°	934.1	933.1	932.1	931.1	930.1	929.6	929.8	930.1	930.4	930.8	931.1
157.5°	948.3	947.8	947.3	946.8	946.3	946.0	946.0	946.0	946.0	946.0	946.0
160°	963.2	962.2	961.2	960.2	959.2	958.7	958.8	959.0	959.1	959.3	959.5
162.5°	975.2	974.2	973.2	972.2	971.2	970.7	970.8	970.9	971.1	971.2	971.4
165°	985.6	984.6	983.6	982.6	981.6	981.1	981.2	981.4	981.5	981.7	981.9
167.5°	993.8	992.8	991.8	990.9	989.9	989.4	989.5	989.6	989.8	989.9	990.1
170°	1000.6	999.4	998.2	997.1	995.9	995.3	995.4	995.6	995.7	995.9	996.1
172.5°	1005.1	1003.9	1002.7	1001.6	1000.4	999.8	1000.0	1000.3	1000.6	1001.0	1001.3
175°	1008.0	1007.0	1006.0	1005.1	1004.1	1003.6	1003.7	1003.8	1004.0	1004.1	1004.3
177.5°	1010.3	1009.3	1008.3	1007.3	1006.3	1005.8	1005.9	1006.1	1006.2	1006.4	1006.6
180°	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	953.4	958.6	963.1	960.9	969.9	969.1	970.6	973.6	974.4	972.9	969.9
5°	1005.1	1012.6	1025.4	1032.1	1030.6	1036.6	1039.6	1044.1	1048.6	1047.1	1047.1
7.5°	1062.9	1073.4	1086.1	1103.4	1105.6	1110.9	1119.9	1119.9	1125.1	1122.9	1122.1
10°	1113.1	1125.9	1146.1	1159.7	1165.7	1168.7	1177.7	1180.7	1186.7	1187.4	1187.4
12.5°	1154.4	1176.9	1190.4	1203.9	1206.9	1211.4	1218.2	1222.7	1224.9	1224.9	1222.7
15°	1176.2	1194.2	1209.9	1224.2	1232.4	1236.2	1242.9	1248.2	1251.2	1257.9	1259.4
17.5°	1185.2	1206.9	1232.4	1252.7	1266.9	1270.7	1284.2	1288.7	1294.7	1297.7	1301.4
20°	1197.9	1229.4	1260.2	1284.9	1298.4	1308.2	1322.4	1343.4	1349.4	1349.4	1347.2
22.5°	1209.2	1249.7	1291.7	1331.4	1342.7	1362.2	1388.4	1410.9	1419.9	1423.7	1420.7
25°	1222.7	1278.2	1332.9	1382.4	1413.2	1427.4	1462.7	1489.7	1500.2	1506.2	1507.7
27.5°	1245.9	1315.7	1385.4	1448.4	1479.9	1496.4	1533.2	1556.5	1569.2	1574.5	1570.7
30°	1272.2	1357.7	1438.7	1494.9	1515.9	1536.2	1560.2	1569.2	1566.2	1566.2	1577.5
32.5°	1299.2	1387.7	1459.7	1496.4	1503.9	1500.9	1491.2	1464.2	1448.4	1448.4	1458.2
35°	1314.2	1390.7	1427.4	1415.4	1386.2	1368.9	1315.7	1285.7	1251.9	1249.7	1260.9
37.5°	1305.9	1338.9	1323.9	1245.2	1205.4	1172.4	1089.1	1056.1	1031.4	996.9	1050.1
40°	1248.2	1236.9	1158.9	1045.6	1001.4	954.9	888.9	855.9	821.4	816.1	828.9
42.5°	1150.7	1083.9	969.9	860.4	815.4	782.4	732.1	699.8	678.1	669.1	684.1
45°	1029.1	924.1	810.1	723.1	673.6	656.3	610.6	582.1	565.6	558.8	569.3
47.5°	880.6	774.9	666.8	593.3	564.1	546.8	516.1	491.3	477.1	472.6	477.1
50°	747.8	639.1	548.3	501.1	474.8	460.6	435.1	419.3	408.1	405.1	412.6
52.5°	633.1	534.1	465.1	423.1	405.8	393.8	375.8	362.3	355.5	352.5	357.8
55°	530.3	450.1	394.6	358.5	345.8	338.3	322.5	315.0	307.5	306.8	312.0
57.5°	439.6	384.1	333.0	307.5	303.8	292.5	279.0	272.3	268.5	267.8	270.0
60°	366.0	316.5	285.8	263.3	258.0	249.0	241.5	237.0	232.5	231.0	232.5
62.5°	304.5	265.5	240.8	225.8	218.3	216.0	207.8	202.5	201.8	201.8	203.3
65°	251.3	218.3	202.5	190.5	185.3	183.0	177.0	173.3	174.0	174.0	174.8
67.5°	204.8	180.8	166.5	160.5	156.0	155.3	149.3	147.8	146.3	146.3	147.8
70°	162.8	147.8	137.3	134.3	133.5	128.3	126.0	125.3	123.0	123.8	123.8
72.5°	127.5	117.8	111.8	107.3	108.0	105.0	102.0	102.0	100.5	102.8	102.8
75°	94.5	90.0	85.5	84.0	85.5	84.0	81.8	81.0	81.8	81.0	81.0
77.5°	69.8	67.5	66.0	65.3	65.3	62.3	60.8	62.3	59.3	60.8	60.8
80°	48.8	45.8	45.0	43.5	44.3	42.0	42.8	41.3	41.3	41.3	41.3
82.5°	30.8	30.0	30.0	30.0	29.3	29.3	29.3	29.3	29.3	29.3	28.5
85°	18.8	18.0	18.0	18.0	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	7.5	8.3	8.3	9.0	8.3	7.5	7.5	7.5	8.3	8.3	7.5
90°	12.8	13.6	14.5	15.3	15.7	15.9	16.4	16.9	17.4	17.9	17.4
92.5°	12.8	13.6	14.5	15.3	15.7	15.8	15.9	16.1	16.2	16.4	16.2
95°	12.8	13.6	14.5	15.3	15.7	15.7	15.7	15.7	15.7	15.7	15.7
97.5°	13.8	14.1	14.4	14.7	14.9	15.0	15.2	15.3	15.5	15.7	15.5
100°	105.3	80.5	55.8	31.1	18.7	18.4	17.7	17.0	16.4	15.7	16.4
102.5°	175.2	175.6	175.9	176.2	176.4	169.4	155.5	141.5	127.6	113.6	127.6
105°	222.7	222.7	222.7	222.7	222.7	222.6	222.4	222.3	222.1	221.9	222.1
107.5°	272.2	272.3	272.5	272.6	272.7	272.4	271.7	271.1	270.4	269.8	270.4
110°	320.8	320.3	319.8	319.3	319.1	319.2	319.3	319.5	319.6	319.8	319.6

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	368.5	367.8	367.2	366.5	366.2	366.0	365.7	365.4	365.0	364.7	365.0
115°	416.3	415.7	415.0	414.3	414.0	413.5	412.5	411.5	410.5	409.5	410.5
117.5°	463.0	462.0	461.1	460.1	459.6	459.4	459.1	458.8	458.4	458.1	458.4
120°	507.1	506.7	506.4	506.1	505.9	505.5	504.7	503.8	503.0	502.2	503.0
122.5°	549.7	549.3	549.0	548.7	548.5	548.0	547.0	546.0	545.0	544.0	545.0
125°	591.1	590.5	589.8	589.1	588.8	588.6	588.1	587.6	587.1	586.6	587.1
127.5°	628.9	628.5	628.2	627.9	627.7	627.0	625.7	624.4	623.0	621.7	623.0
130°	666.1	665.6	665.1	664.6	664.3	663.9	663.1	662.2	661.4	660.6	661.4
132.5°	700.2	700.2	700.2	700.2	700.2	699.8	698.9	698.1	697.2	696.4	697.2
135°	734.3	733.9	733.6	733.3	733.1	732.6	731.6	730.6	729.6	728.6	729.6
137.5°	765.9	765.9	765.9	765.9	765.9	765.5	764.7	763.8	763.0	762.2	763.0
140°	794.6	795.0	795.3	795.6	795.8	795.3	794.3	793.3	792.3	791.3	792.3
142.5°	823.5	823.5	823.5	823.5	823.5	823.0	822.0	821.0	820.0	819.0	820.0
145°	849.8	850.0	850.1	850.3	850.4	849.9	848.9	847.9	846.9	845.9	846.9
147.5°	873.0	873.1	873.3	873.4	873.5	872.9	871.8	870.6	869.5	868.3	869.5
150°	894.8	895.2	895.5	895.8	896.0	895.3	894.0	892.7	891.3	890.0	891.3
152.5°	914.2	914.6	914.9	915.2	915.4	914.8	913.7	912.5	911.4	910.2	911.4
155°	931.6	932.1	932.6	933.1	933.3	932.6	931.3	930.0	928.6	927.3	928.6
157.5°	946.5	947.0	947.5	948.0	948.3	947.6	946.3	945.0	943.6	942.3	943.6
160°	960.2	960.8	961.5	962.2	962.5	961.8	960.5	959.2	957.8	956.5	957.8
162.5°	972.4	973.4	974.4	975.4	975.9	975.2	973.7	972.2	970.7	969.2	970.7
165°	982.9	983.9	984.9	985.9	986.4	985.7	984.4	983.1	981.7	980.4	981.7
167.5°	991.3	992.4	993.6	994.7	995.3	994.6	993.1	991.6	990.1	988.6	990.1
170°	997.4	998.8	1000.1	1001.4	1002.1	1001.3	999.8	998.3	996.8	995.3	996.8
172.5°	1002.5	1003.7	1004.8	1006.0	1006.6	1005.8	1004.3	1002.8	1001.3	999.8	1001.3
175°	1005.6	1007.0	1008.3	1009.6	1010.3	1009.6	1008.1	1006.6	1005.1	1003.6	1005.1
177.5°	1007.8	1008.9	1010.1	1011.2	1011.8	1011.1	1009.8	1008.5	1007.1	1005.8	1007.1
180°	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	973.6	968.4	970.6	968.4	966.1	963.9	958.6	951.1	945.1	940.6	939.9
5°	1048.6	1041.9	1037.4	1035.1	1030.6	1024.6	1014.9	1003.6	990.1	984.9	974.4
7.5°	1117.6	1115.4	1104.9	1103.4	1100.4	1089.1	1072.6	1057.6	1040.4	1026.1	1012.6
10°	1182.9	1177.7	1170.2	1159.7	1158.2	1143.9	1128.1	1107.1	1084.6	1071.1	1047.1
12.5°	1223.4	1217.4	1209.2	1202.4	1198.7	1189.7	1167.9	1146.9	1126.6	1101.9	1080.9
15°	1252.7	1245.2	1230.2	1224.9	1220.4	1208.4	1192.7	1170.9	1143.9	1126.6	1096.6
17.5°	1292.4	1283.4	1268.4	1258.7	1250.4	1231.7	1209.2	1179.9	1154.4	1134.9	1107.9
20°	1338.2	1324.7	1305.2	1292.4	1280.4	1258.7	1227.2	1192.7	1155.9	1131.9	1104.1
22.5°	1413.9	1388.4	1357.7	1339.7	1323.2	1285.7	1248.2	1205.4	1164.2	1128.1	1094.4
25°	1487.4	1461.9	1423.7	1398.9	1373.4	1329.9	1280.4	1221.2	1168.7	1126.6	1082.4
27.5°	1555.7	1529.5	1494.2	1464.2	1439.4	1374.2	1308.9	1242.2	1175.4	1117.6	1072.6
30°	1571.5	1560.2	1533.2	1506.9	1484.4	1424.4	1348.7	1263.9	1183.7	1109.4	1059.1
32.5°	1476.2	1503.9	1510.7	1506.9	1492.7	1449.9	1380.2	1290.9	1195.7	1105.6	1036.6
35°	1278.2	1328.4	1380.2	1407.9	1421.4	1427.4	1386.2	1304.4	1203.9	1099.6	1021.6
37.5°	1059.9	1108.6	1190.4	1231.7	1277.4	1337.4	1353.9	1301.4	1200.2	1095.1	997.6
40°	870.9	933.1	1000.6	1038.1	1077.9	1185.9	1267.7	1261.7	1188.2	1078.6	978.9
42.5°	708.8	747.8	807.1	848.4	897.1	1017.9	1127.4	1181.4	1152.2	1058.4	954.9
45°	591.1	621.1	663.1	705.1	735.1	844.6	974.4	1062.9	1090.6	1022.4	918.1
47.5°	498.1	520.6	557.3	583.6	615.8	702.1	814.6	939.1	997.6	971.4	879.1
50°	426.8	444.8	474.1	490.6	519.1	593.3	678.8	809.4	897.9	900.9	827.4
52.5°	364.5	382.6	407.3	421.6	438.8	489.1	575.3	685.6	787.6	825.1	768.1
55°	317.3	327.8	348.0	359.3	375.0	423.8	478.6	572.3	678.8	740.3	704.3
57.5°	273.8	285.0	297.8	306.8	318.0	357.0	406.6	477.1	582.8	649.6	637.6
60°	238.5	245.3	257.3	264.0	274.5	300.0	334.5	405.1	489.1	552.1	558.8
62.5°	205.5	211.5	219.8	225.8	232.5	252.8	278.3	328.5	402.1	470.3	479.3
65°	177.0	182.3	186.8	192.0	197.3	210.0	231.8	270.8	327.8	391.6	411.1
67.5°	151.5	153.0	159.8	160.5	163.5	173.3	189.0	220.5	261.8	312.8	338.3
70°	126.8	129.8	131.3	133.5	136.5	143.3	156.0	172.5	203.3	244.5	268.5
72.5°	102.8	103.5	105.8	107.3	110.3	115.5	121.5	134.3	153.8	183.8	205.5
75°	81.8	82.5	84.0	84.8	87.0	88.5	91.5	100.5	114.0	132.0	147.8
77.5°	61.5	63.0	64.5	64.5	65.3	66.8	68.3	71.3	78.0	90.0	103.5
80°	42.0	42.8	42.8	43.5	42.8	45.0	47.3	51.0	54.0	57.8	64.5
82.5°	29.3	29.3	29.3	30.0	30.0	30.8	30.8	31.5	32.3	34.5	37.5
85°	18.0	18.0	18.8	17.3	18.0	18.8	18.8	18.0	18.8	19.5	20.3
87.5°	7.5	7.5	8.3	8.3	8.3	8.3	7.5	8.3	7.5	8.3	8.3
90°	16.9	16.4	15.9	15.7	15.3	14.5	13.6	12.8	12.0	10.8	9.6
92.5°	16.1	15.9	15.8	15.7	15.3	14.5	13.6	12.8	12.0	11.0	10.0
95°	15.7	15.7	15.7	15.7	15.3	14.5	13.6	12.8	12.0	18.3	24.6
97.5°	15.3	15.2	15.0	14.9	14.7	14.4	14.1	13.8	13.5	29.3	45.0
100°	17.0	17.7	18.4	18.7	31.1	55.8	80.5	105.3	130.0	129.3	128.7
102.5°	141.5	155.5	169.4	176.4	176.2	175.9	175.6	175.2	174.9	174.6	174.2
105°	222.3	222.4	222.6	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7
107.5°	271.1	271.7	272.4	272.7	272.6	272.5	272.3	272.2	272.0	271.7	271.3
110°	319.5	319.3	319.2	319.1	319.3	319.8	320.3	320.8	321.3	321.0	320.6



TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	365.4	365.7	366.0	366.2	366.5	367.2	367.8	368.5	369.1	368.9	368.8
115°	411.5	412.5	413.5	414.0	414.3	415.0	415.7	416.3	417.0	416.8	416.6
117.5°	458.8	459.1	459.4	459.6	460.1	461.1	462.0	463.0	464.0	463.4	462.7
120°	503.8	504.7	505.5	505.9	506.1	506.4	506.7	507.1	507.4	506.9	506.4
122.5°	546.0	547.0	548.0	548.5	548.7	549.0	549.3	549.7	550.0	549.8	549.6
125°	587.6	588.1	588.6	588.8	589.1	589.8	590.5	591.1	591.8	591.8	591.8
127.5°	624.4	625.7	627.0	627.7	627.9	628.2	628.5	628.9	629.2	629.4	629.5
130°	662.2	663.1	663.9	664.3	664.6	665.1	665.6	666.1	666.6	666.4	666.2
132.5°	698.1	698.9	699.8	700.2	700.2	700.2	700.2	700.2	700.2	700.7	701.2
135°	730.6	731.6	732.6	733.1	733.3	733.6	733.9	734.3	734.6	734.9	735.2
137.5°	763.8	764.7	765.5	765.9	765.9	765.9	765.9	765.9	765.9	766.2	766.6
140°	793.3	794.3	795.3	795.8	795.6	795.3	795.0	794.6	794.3	794.5	794.7
142.5°	821.0	822.0	823.0	823.5	823.5	823.5	823.5	823.5	823.5	823.2	822.8
145°	847.9	848.9	849.9	850.4	850.3	850.1	850.0	849.8	849.6	849.6	849.6
147.5°	870.6	871.8	872.9	873.5	873.4	873.3	873.1	873.0	872.8	872.6	872.4
150°	892.7	894.0	895.3	896.0	895.8	895.5	895.2	894.8	894.5	894.2	893.8
152.5°	912.5	913.7	914.8	915.4	915.2	914.9	914.6	914.2	913.9	913.6	913.2
155°	930.0	931.3	932.6	933.3	933.1	932.6	932.1	931.6	931.1	930.8	930.4
157.5°	945.0	946.3	947.6	948.3	948.0	947.5	947.0	946.5	946.0	946.0	946.0
160°	959.2	960.5	961.8	962.5	962.2	961.5	960.8	960.2	959.5	959.3	959.1
162.5°	972.2	973.7	975.2	975.9	975.4	974.4	973.4	972.4	971.4	971.2	971.1
165°	983.1	984.4	985.7	986.4	985.9	984.9	983.9	982.9	981.9	981.7	981.5
167.5°	991.6	993.1	994.6	995.3	994.7	993.6	992.4	991.3	990.1	989.9	989.8
170°	998.3	999.8	1001.3	1002.1	1001.4	1000.1	998.8	997.4	996.1	995.9	995.7
172.5°	1002.8	1004.3	1005.8	1006.6	1006.0	1004.8	1003.7	1002.5	1001.3	1001.0	1000.6
175°	1006.6	1008.1	1009.6	1010.3	1009.6	1008.3	1007.0	1005.6	1004.3	1004.1	1004.0
177.5°	1008.5	1009.8	1011.1	1011.8	1011.2	1010.1	1008.9	1007.8	1006.6	1006.4	1006.2
180°	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	937.6	933.1	930.1	929.4	924.9	921.1	916.6	915.9	913.6	907.6	903.9
5°	966.9	956.4	954.1	947.4	936.1	927.9	917.4	911.4	904.6	893.4	884.4
7.5°	996.9	982.6	972.1	962.4	946.6	931.6	916.6	904.6	892.6	876.1	862.6
10°	1026.1	1004.4	991.6	977.4	955.6	933.1	912.1	894.9	875.4	855.9	836.4
12.5°	1053.1	1025.4	1006.6	986.4	959.4	931.6	904.6	880.6	860.4	834.1	812.4
15°	1069.6	1038.9	1020.1	1000.6	960.1	929.4	897.9	867.1	840.1	812.4	792.1
17.5°	1079.4	1044.9	1023.9	1005.9	964.6	922.6	882.1	849.1	819.9	786.9	759.8
20°	1074.9	1041.1	1021.6	1004.4	956.4	914.4	870.9	832.6	795.9	762.1	733.6
22.5°	1065.1	1029.9	1008.1	992.4	949.6	900.1	852.1	810.9	772.6	738.8	706.6
25°	1044.1	1009.6	990.9	971.4	929.4	882.1	833.4	789.1	748.6	712.6	676.6
27.5°	1025.4	983.4	963.9	946.6	902.4	860.4	812.4	763.6	722.3	684.8	648.8
30°	1003.6	956.4	935.4	912.1	872.4	832.6	784.6	739.6	696.8	657.1	622.6
32.5°	980.4	925.6	901.6	875.4	834.9	797.4	756.8	712.6	669.8	630.8	594.8
35°	950.4	891.9	864.1	839.4	797.4	759.8	722.3	685.6	642.8	601.6	567.1
37.5°	921.9	857.4	828.1	799.6	755.3	719.3	688.6	654.1	612.8	573.1	540.1
40°	889.6	815.4	785.4	759.1	713.3	673.6	645.8	618.8	582.8	544.6	508.6
42.5°	860.4	776.4	744.8	717.8	669.8	632.3	606.1	583.6	552.1	516.8	480.1
45°	819.9	734.3	702.1	673.6	624.8	589.6	562.6	543.1	518.3	485.3	452.3
47.5°	782.4	693.8	658.6	624.1	579.8	543.8	519.1	504.1	487.6	458.3	424.6
50°	736.6	647.3	611.3	582.8	532.6	501.8	477.1	466.6	451.6	423.8	396.8
52.5°	687.1	602.3	568.6	534.1	487.6	457.6	435.8	423.8	411.8	391.6	366.0
55°	629.3	552.1	520.6	489.8	443.3	415.6	396.1	383.3	376.5	357.8	339.0
57.5°	573.8	501.1	471.8	443.3	402.8	371.3	358.5	347.3	337.5	324.0	308.3
60°	517.6	451.6	420.1	394.6	359.3	330.8	320.3	309.0	301.5	291.0	279.8
62.5°	453.1	396.8	372.8	348.8	318.8	296.3	284.3	275.3	265.5	258.8	249.0
65°	384.8	345.0	321.8	303.8	275.3	255.0	246.0	240.0	231.8	225.0	217.5
67.5°	321.0	289.5	279.8	260.3	238.5	220.5	213.8	206.3	199.5	195.8	189.0
70°	259.5	237.0	227.3	222.0	198.0	186.0	180.0	177.0	168.8	165.0	160.5
72.5°	201.0	192.8	186.0	179.3	163.5	156.0	149.3	146.3	140.3	137.3	135.8
75°	148.5	143.3	139.5	138.8	132.0	124.5	117.8	116.3	111.8	108.8	107.3
77.5°	104.3	102.8	102.0	102.8	98.3	93.8	92.3	90.8	85.5	84.8	84.8
80°	68.3	72.0	72.0	71.3	69.8	69.0	66.8	65.3	62.3	61.5	62.3
82.5°	42.0	44.3	45.0	46.5	45.8	45.0	43.5	42.8	43.5	42.0	42.8
85°	21.0	22.5	25.5	25.5	26.3	26.3	26.3	25.5	24.0	24.8	24.0
87.5°	8.3	9.0	9.0	9.0	8.3	10.5	11.3	11.3	11.3	9.8	9.8
90°	8.5	7.3	6.7	6.0	4.7	3.4	2.0	0.7	2.0	3.4	4.7
92.5°	9.0	8.0	7.5	8.2	9.7	11.2	12.7	14.2	12.7	11.2	9.7
95°	30.9	37.2	40.4	40.6	41.1	41.6	42.1	42.6	42.1	41.6	41.1
97.5°	60.8	76.5	84.4	83.9	82.9	82.0	81.0	80.0	81.0	82.0	82.9
100°	128.0	127.3	127.0	126.8	126.3	125.8	125.3	124.8	125.3	125.8	126.3
102.5°	173.9	173.6	173.4	173.1	172.4	171.7	171.1	170.4	171.1	171.7	172.4
105°	222.7	222.7	222.7	222.4	221.7	221.0	220.4	219.7	220.4	221.0	221.7
107.5°	271.0	270.7	270.5	270.5	270.5	270.5	270.5	270.5	270.5	270.5	270.5
110°	320.3	320.0	319.8	319.8	319.8	319.8	319.8	319.8	319.8	319.8	319.8

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	368.6	368.5	368.4	368.2	367.7	367.2	366.7	366.2	366.7	367.2	367.7
115°	416.5	416.3	416.2	415.8	415.0	414.1	413.3	412.5	413.3	414.1	415.0
117.5°	462.1	461.4	461.1	461.1	461.1	461.1	461.1	461.1	461.1	461.1	461.1
120°	505.9	505.4	505.1	505.2	505.4	505.5	505.7	505.9	505.7	505.5	505.4
122.5°	549.5	549.3	549.2	548.8	548.0	547.1	546.3	545.5	546.3	547.1	548.0
125°	591.8	591.8	591.8	591.2	590.1	588.9	587.8	586.6	587.8	588.9	590.1
127.5°	629.7	629.8	629.9	629.5	628.7	627.8	627.0	626.2	627.0	627.8	628.7
130°	666.1	665.9	665.8	665.4	664.6	663.7	662.9	662.1	662.9	663.7	664.6
132.5°	701.7	702.2	702.4	701.9	700.9	699.9	698.9	697.9	698.9	699.9	700.9
135°	735.5	735.8	736.0	735.5	734.5	733.6	732.6	731.6	732.6	733.6	734.5
137.5°	766.9	767.2	767.4	766.9	765.9	764.9	763.9	762.9	763.9	764.9	765.9
140°	794.8	795.0	795.1	794.9	794.6	794.3	793.9	793.6	793.9	794.3	794.6
142.5°	822.5	822.2	822.0	821.9	821.7	821.6	821.4	821.2	821.4	821.6	821.7
145°	849.6	849.6	849.6	849.4	849.1	848.8	848.4	848.1	848.4	848.8	849.1
147.5°	872.3	872.1	872.0	872.0	872.0	872.0	872.0	872.0	872.0	872.0	872.0
150°	893.5	893.2	893.0	893.2	893.5	893.8	894.2	894.5	894.2	893.8	893.5
152.5°	912.9	912.6	912.4	912.8	913.6	914.5	915.3	916.1	915.3	914.5	913.6
155°	930.1	929.8	929.6	930.1	931.1	932.1	933.1	934.1	933.1	932.1	931.1
157.5°	946.0	946.0	946.0	946.3	946.8	947.3	947.8	948.3	947.8	947.3	946.8
160°	959.0	958.8	958.7	959.2	960.2	961.2	962.2	963.2	962.2	961.2	960.2
162.5°	970.9	970.8	970.7	971.2	972.2	973.2	974.2	975.2	974.2	973.2	972.2
165°	981.4	981.2	981.1	981.6	982.6	983.6	984.6	985.6	984.6	983.6	982.6
167.5°	989.6	989.5	989.4	989.9	990.9	991.8	992.8	993.8	992.8	991.8	990.9
170°	995.6	995.4	995.3	995.9	997.1	998.2	999.4	1000.6	999.4	998.2	997.1
172.5°	1000.3	1000.0	999.8	1000.4	1001.6	1002.7	1003.9	1005.1	1003.9	1002.7	1001.6
175°	1003.8	1003.7	1003.6	1004.1	1005.1	1006.0	1007.0	1008.0	1007.0	1006.0	1005.1
177.5°	1006.1	1005.9	1005.8	1006.3	1007.3	1008.3	1009.3	1010.3	1009.3	1008.3	1007.3
180°	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	901.6	898.6	896.4	894.1	884.4	873.9	872.4	870.1	865.6	870.9	868.6
5°	878.4	871.6	867.9	858.1	846.1	837.1	829.6	820.6	816.9	813.9	813.1
7.5°	849.9	843.9	837.1	827.4	812.4	797.4	786.1	777.1	769.6	765.9	765.9
10°	822.1	814.6	805.6	789.1	774.9	756.1	744.1	735.1	724.6	718.6	713.3
12.5°	793.6	785.4	777.1	756.1	739.6	720.1	702.8	691.6	686.3	679.6	670.6
15°	765.1	752.3	744.1	723.1	702.1	682.6	671.3	659.3	647.3	640.6	637.6
17.5°	735.1	726.1	712.6	690.1	666.8	649.6	633.1	621.8	607.6	600.8	594.1
20°	708.1	694.6	681.1	658.6	636.1	612.8	596.3	582.8	573.8	568.6	562.6
22.5°	675.8	663.1	651.8	627.8	603.1	581.3	563.3	555.1	546.1	537.8	531.8
25°	648.1	635.3	624.1	597.8	570.8	550.6	537.1	526.6	516.8	513.1	507.1
27.5°	618.8	606.8	591.8	565.6	541.6	524.3	510.1	500.3	492.8	485.3	480.8
30°	591.1	577.6	564.1	535.6	516.1	498.8	485.3	473.3	467.3	463.6	456.1
32.5°	564.1	546.8	535.6	509.3	490.6	474.1	462.8	452.3	444.8	438.1	432.1
35°	534.8	516.1	504.8	483.1	463.6	447.1	437.3	429.8	420.8	414.8	411.8
37.5°	507.1	491.3	480.1	457.6	438.1	424.6	414.1	404.3	400.6	392.3	390.8
40°	477.1	463.6	453.1	431.3	413.3	402.8	391.6	382.6	375.8	372.0	366.8
42.5°	450.1	438.8	427.6	407.3	390.1	377.3	369.0	360.8	354.8	348.8	345.0
45°	425.3	413.3	402.8	383.3	366.0	354.8	346.5	336.8	335.3	327.0	323.3
47.5°	399.1	388.6	379.5	359.3	343.5	332.3	322.5	315.8	309.0	306.0	300.8
50°	373.5	363.0	352.5	334.5	320.3	309.0	299.3	291.8	288.0	283.5	279.0
52.5°	345.8	337.5	329.3	310.5	296.3	286.5	278.3	268.5	264.8	261.0	258.0
55°	322.5	310.5	301.5	285.8	273.0	262.5	253.5	246.0	242.3	239.3	235.5
57.5°	291.0	283.5	276.0	261.8	249.8	239.3	230.3	224.3	219.8	217.5	218.3
60°	264.0	255.8	251.3	236.3	224.3	216.0	207.8	201.8	197.3	195.0	194.3
62.5°	235.5	229.5	221.3	210.8	198.8	191.3	185.3	180.8	173.3	172.5	170.3
65°	207.8	203.3	195.8	186.0	176.3	169.5	162.8	156.8	153.8	150.0	147.8
67.5°	180.8	176.3	169.5	161.3	154.5	147.8	141.8	135.8	130.5	127.5	126.0
70°	154.5	150.8	146.3	136.5	128.3	123.0	118.5	114.8	109.5	108.0	107.3
72.5°	129.0	125.3	123.0	114.8	107.3	102.8	98.3	94.5	92.3	91.5	89.3
75°	105.8	102.0	99.0	91.5	87.0	84.0	79.5	78.0	75.8	75.0	74.3
77.5°	82.5	78.8	78.0	72.8	67.5	66.0	64.5	61.5	61.5	61.5	60.0
80°	59.3	58.5	57.8	52.5	50.3	48.8	48.0	45.8	44.3	42.8	42.0
82.5°	39.8	39.0	38.3	36.0	33.8	33.0	32.3	30.8	30.8	31.5	30.0
85°	24.0	22.5	21.8	21.0	19.5	19.5	20.3	19.5	19.5	19.5	18.8
87.5°	9.0	9.0	9.0	9.0	9.8	8.3	9.0	9.0	8.3	8.3	7.5
90°	6.0	6.7	7.3	8.5	9.6	10.8	12.0	12.8	13.6	14.5	15.3
92.5°	8.2	7.5	8.0	9.0	10.0	11.0	12.0	12.8	13.6	14.5	15.3
95°	40.6	40.4	37.2	30.9	24.6	18.3	12.0	12.8	13.6	14.5	15.3
97.5°	83.9	84.4	76.5	60.8	45.0	29.3	13.5	13.8	14.1	14.4	14.7
100°	126.8	127.0	127.3	128.0	128.7	129.3	130.0	105.3	80.5	55.8	31.1
102.5°	173.1	173.4	173.6	173.9	174.2	174.6	174.9	175.2	175.6	175.9	176.2
105°	222.4	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7
107.5°	270.5	270.5	270.7	271.0	271.3	271.7	272.0	272.2	272.3	272.5	272.6
110°	319.8	319.8	320.0	320.3	320.6	321.0	321.3	320.8	320.3	319.8	319.3

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	368.2	368.4	368.5	368.6	368.8	368.9	369.1	368.5	367.8	367.2	366.5
115°	415.8	416.2	416.3	416.5	416.6	416.8	417.0	416.3	415.7	415.0	414.3
117.5°	461.1	461.1	461.4	462.1	462.7	463.4	464.0	463.0	462.0	461.1	460.1
120°	505.2	505.1	505.4	505.9	506.4	506.9	507.4	507.1	506.7	506.4	506.1
122.5°	548.8	549.2	549.3	549.5	549.6	549.8	550.0	549.7	549.3	549.0	548.7
125°	591.2	591.8	591.8	591.8	591.8	591.8	591.8	591.1	590.5	589.8	589.1
127.5°	629.5	629.9	629.8	629.7	629.5	629.4	629.2	628.9	628.5	628.2	627.9
130°	665.4	665.8	665.9	666.1	666.2	666.4	666.6	666.1	665.6	665.1	664.6
132.5°	701.9	702.4	702.2	701.7	701.2	700.7	700.2	700.2	700.2	700.2	700.2
135°	735.5	736.0	735.8	735.5	735.2	734.9	734.6	734.3	733.9	733.6	733.3
137.5°	766.9	767.4	767.2	766.9	766.6	766.2	765.9	765.9	765.9	765.9	765.9
140°	794.9	795.1	795.0	794.8	794.7	794.5	794.3	794.6	795.0	795.3	795.6
142.5°	821.9	822.0	822.2	822.5	822.8	823.2	823.5	823.5	823.5	823.5	823.5
145°	849.4	849.6	849.6	849.6	849.6	849.6	849.6	849.8	850.0	850.1	850.3
147.5°	872.0	872.0	872.1	872.3	872.4	872.6	872.8	873.0	873.1	873.3	873.4
150°	893.2	893.0	893.2	893.5	893.8	894.2	894.5	894.8	895.2	895.5	895.8
152.5°	912.8	912.4	912.6	912.9	913.2	913.6	913.9	914.2	914.6	914.9	915.2
155°	930.1	929.6	929.8	930.1	930.4	930.8	931.1	931.6	932.1	932.6	933.1
157.5°	946.3	946.0	946.0	946.0	946.0	946.0	946.0	946.5	947.0	947.5	948.0
160°	959.2	958.7	958.8	959.0	959.1	959.3	959.5	960.2	960.8	961.5	962.2
162.5°	971.2	970.7	970.8	970.9	971.1	971.2	971.4	972.4	973.4	974.4	975.4
165°	981.6	981.1	981.2	981.4	981.5	981.7	981.9	982.9	983.9	984.9	985.9
167.5°	989.9	989.4	989.5	989.6	989.8	989.9	990.1	991.3	992.4	993.6	994.7
170°	995.9	995.3	995.4	995.6	995.7	995.9	996.1	997.4	998.8	1000.1	1001.4
172.5°	1000.4	999.8	1000.0	1000.3	1000.6	1001.0	1001.3	1002.5	1003.7	1004.8	1006.0
175°	1004.1	1003.6	1003.7	1003.8	1004.0	1004.1	1004.3	1005.6	1007.0	1008.3	1009.6
177.5°	1006.3	1005.8	1005.9	1006.1	1006.2	1006.4	1006.6	1007.8	1008.9	1010.1	1011.2
180°	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	864.9	866.4	862.6	861.1	858.1	861.9	862.6	861.9	868.6	865.6	867.1
5°	814.6	811.6	809.4	804.1	804.1	804.9	807.1	803.4	805.6	810.9	810.1
7.5°	759.1	757.6	758.3	752.3	747.8	749.3	747.8	754.6	758.3	756.8	759.8
10°	708.8	711.8	705.1	702.1	699.1	702.1	701.3	702.8	707.3	710.3	715.6
12.5°	668.3	667.6	663.8	660.8	655.6	657.1	661.6	660.1	660.8	667.6	666.8
15°	630.1	625.6	622.6	615.8	617.3	612.1	616.6	621.8	624.1	630.1	633.8
17.5°	591.8	591.1	587.3	586.6	578.3	576.1	580.6	582.1	584.3	587.3	592.6
20°	559.6	558.8	553.6	552.1	545.3	549.8	548.3	551.3	552.8	558.8	561.1
22.5°	530.3	526.6	525.1	522.8	520.6	519.8	522.8	522.1	527.3	529.6	530.3
25°	503.3	500.3	499.6	495.8	494.3	492.1	494.3	496.6	502.6	504.8	507.8
27.5°	478.6	476.3	474.8	471.8	469.6	469.6	471.1	474.1	476.3	477.8	479.3
30°	456.1	454.6	450.1	448.6	446.3	446.3	446.3	447.8	451.6	456.1	458.3
32.5°	432.8	429.8	426.8	426.8	424.6	424.6	425.3	426.8	430.6	431.3	435.1
35°	410.3	407.3	405.1	403.6	404.3	401.3	402.8	405.1	409.6	411.1	413.3
37.5°	388.6	387.8	383.3	381.0	382.6	382.6	381.8	383.3	386.3	389.3	390.8
40°	364.5	363.0	363.0	360.8	361.5	358.5	360.8	362.3	363.8	366.8	369.0
42.5°	343.5	342.0	339.0	339.8	337.5	337.5	339.0	339.8	342.0	345.8	347.3
45°	321.0	321.0	319.5	317.3	318.0	315.8	317.3	318.0	321.0	324.8	323.3
47.5°	299.3	298.5	298.5	295.5	297.0	294.8	297.0	297.8	299.3	301.5	300.8
50°	278.3	276.0	276.8	276.0	275.3	275.3	276.8	276.8	278.3	278.3	280.5
52.5°	256.5	256.5	255.0	255.8	257.3	255.8	258.0	255.8	257.3	258.0	259.5
55°	237.0	235.5	236.3	235.5	238.5	236.3	238.5	237.0	238.5	237.8	239.3
57.5°	216.0	213.8	214.5	213.8	216.0	215.3	217.5	215.3	216.0	216.8	219.0
60°	192.0	192.0	192.0	190.5	192.8	192.8	192.0	192.0	195.0	196.5	195.8
62.5°	169.5	168.8	166.5	165.8	166.5	165.0	168.0	167.3	168.8	170.3	171.8
65°	144.8	143.3	142.5	141.0	141.0	140.3	141.0	144.0	144.8	145.5	149.3
67.5°	124.5	123.8	123.0	120.8	120.8	122.3	122.3	122.3	126.8	124.5	127.5
70°	106.5	105.0	103.5	102.8	102.8	103.5	104.3	105.0	104.3	107.3	108.0
72.5°	89.3	90.0	88.5	88.5	88.5	87.8	87.8	89.3	90.0	89.3	90.0
75°	74.3	74.3	73.5	74.3	74.3	73.5	73.5	75.0	75.0	74.3	76.5
77.5°	60.0	59.3	57.8	56.3	57.0	56.3	57.0	56.3	58.5	60.8	59.3
80°	42.0	41.3	41.3	41.3	42.0	41.3	42.8	41.3	42.0	42.0	42.8
82.5°	30.0	30.8	30.8	30.0	30.8	30.0	30.8	30.8	30.8	30.0	30.8
85°	19.5	19.5	19.5	19.5	18.8	19.5	19.5	19.5	20.3	19.5	20.3
87.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.0	8.3	9.0
90°	15.7	15.9	16.4	16.9	17.4	17.9	17.4	16.9	16.4	15.9	15.7
92.5°	15.7	15.8	15.9	16.1	16.2	16.4	16.2	16.1	15.9	15.8	15.7
95°	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7
97.5°	14.9	15.0	15.2	15.3	15.5	15.7	15.5	15.3	15.2	15.0	14.9
100°	18.7	18.4	17.7	17.0	16.4	15.7	16.4	17.0	17.7	18.4	18.7
102.5°	176.4	169.4	155.5	141.5	127.6	113.6	127.6	141.5	155.5	169.4	176.4
105°	222.7	222.6	222.4	222.3	222.1	221.9	222.1	222.3	222.4	222.6	222.7
107.5°	272.7	272.4	271.7	271.1	270.4	269.8	270.4	271.1	271.7	272.4	272.7
110°	319.1	319.2	319.3	319.5	319.6	319.8	319.6	319.5	319.3	319.2	319.1

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	366.2	366.0	365.7	365.4	365.0	364.7	365.0	365.4	365.7	366.0	366.2
115°	414.0	413.5	412.5	411.5	410.5	409.5	410.5	411.5	412.5	413.5	414.0
117.5°	459.6	459.4	459.1	458.8	458.4	458.1	458.4	458.8	459.1	459.4	459.6
120°	505.9	505.5	504.7	503.8	503.0	502.2	503.0	503.8	504.7	505.5	505.9
122.5°	548.5	548.0	547.0	546.0	545.0	544.0	545.0	546.0	547.0	548.0	548.5
125°	588.8	588.6	588.1	587.6	587.1	586.6	587.1	587.6	588.1	588.6	588.8
127.5°	627.7	627.0	625.7	624.4	623.0	621.7	623.0	624.4	625.7	627.0	627.7
130°	664.3	663.9	663.1	662.2	661.4	660.6	661.4	662.2	663.1	663.9	664.3
132.5°	700.2	699.8	698.9	698.1	697.2	696.4	697.2	698.1	698.9	699.8	700.2
135°	733.1	732.6	731.6	730.6	729.6	728.6	729.6	730.6	731.6	732.6	733.1
137.5°	765.9	765.5	764.7	763.8	763.0	762.2	763.0	763.8	764.7	765.5	765.9
140°	795.8	795.3	794.3	793.3	792.3	791.3	792.3	793.3	794.3	795.3	795.8
142.5°	823.5	823.0	822.0	821.0	820.0	819.0	820.0	821.0	822.0	823.0	823.5
145°	850.4	849.9	848.9	847.9	846.9	845.9	846.9	847.9	848.9	849.9	850.4
147.5°	873.5	872.9	871.8	870.6	869.5	868.3	869.5	870.6	871.8	872.9	873.5
150°	896.0	895.3	894.0	892.7	891.3	890.0	891.3	892.7	894.0	895.3	896.0
152.5°	915.4	914.8	913.7	912.5	911.4	910.2	911.4	912.5	913.7	914.8	915.4
155°	933.3	932.6	931.3	930.0	928.6	927.3	928.6	930.0	931.3	932.6	933.3
157.5°	948.3	947.6	946.3	945.0	943.6	942.3	943.6	945.0	946.3	947.6	948.3
160°	962.5	961.8	960.5	959.2	957.8	956.5	957.8	959.2	960.5	961.8	962.5
162.5°	975.9	975.2	973.7	972.2	970.7	969.2	970.7	972.2	973.7	975.2	975.9
165°	986.4	985.7	984.4	983.1	981.7	980.4	981.7	983.1	984.4	985.7	986.4
167.5°	995.3	994.6	993.1	991.6	990.1	988.6	990.1	991.6	993.1	994.6	995.3
170°	1002.1	1001.3	999.8	998.3	996.8	995.3	996.8	998.3	999.8	1001.3	1002.1
172.5°	1006.6	1005.8	1004.3	1002.8	1001.3	999.8	1001.3	1002.8	1004.3	1005.8	1006.6
175°	1010.3	1009.6	1008.1	1006.6	1005.1	1003.6	1005.1	1006.6	1008.1	1009.6	1010.3
177.5°	1011.8	1011.1	1009.8	1008.5	1007.1	1005.8	1007.1	1008.5	1009.8	1011.1	1011.8
180°	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	864.1	867.9	864.9	862.6	868.6	871.6	871.6	876.9	882.1	886.6	887.4
5°	810.9	816.9	818.4	817.6	826.6	831.1	840.9	846.1	853.6	858.9	864.9
7.5°	762.1	770.4	771.1	772.6	786.1	793.6	801.9	815.4	825.9	833.4	840.1
10°	713.3	718.6	723.8	730.6	744.1	756.8	768.9	783.1	796.6	804.1	813.9
12.5°	676.6	680.3	686.3	690.8	705.1	716.3	732.1	751.6	771.1	777.1	789.1
15°	638.3	640.6	652.6	657.1	669.1	687.8	697.6	716.3	737.3	748.6	762.1
17.5°	594.1	607.6	615.1	620.3	635.3	650.3	666.1	685.6	712.6	723.1	732.8
20°	562.6	572.3	580.6	587.3	600.8	623.3	637.6	653.3	678.8	690.8	705.1
22.5°	534.8	543.1	550.6	558.1	567.1	587.3	603.8	625.6	651.1	662.3	678.8
25°	508.6	516.8	521.3	530.3	542.3	556.6	576.1	595.6	621.1	633.8	649.6
27.5°	483.1	491.3	499.6	507.1	515.3	528.8	542.3	567.1	593.3	608.3	621.8
30°	461.3	465.1	472.6	480.8	489.1	501.8	517.6	534.8	564.8	578.3	594.8
32.5°	437.3	444.1	449.3	455.3	465.8	476.3	490.6	512.3	536.3	549.1	567.1
35°	414.8	420.8	424.6	435.1	441.8	453.1	467.3	486.8	507.1	521.3	537.1
37.5°	393.1	399.1	403.6	409.6	418.6	428.3	443.3	457.6	481.6	493.6	511.6
40°	370.5	375.8	381.0	387.8	396.1	408.1	417.1	435.1	454.6	468.1	481.6
42.5°	348.8	351.8	357.8	365.3	373.5	384.1	396.8	411.1	430.6	442.6	454.6
45°	325.5	330.8	337.5	342.8	350.3	360.8	372.0	384.8	404.3	416.3	429.1
47.5°	303.8	307.5	312.0	320.3	330.0	337.5	349.5	361.5	379.5	390.8	402.8
50°	281.3	285.0	291.8	297.0	304.5	314.3	325.5	338.3	355.5	363.0	375.0
52.5°	260.3	261.8	268.5	273.8	281.3	292.5	301.5	312.8	329.3	337.5	349.5
55°	239.3	240.8	244.5	249.8	258.0	267.0	276.8	289.5	303.8	311.3	322.5
57.5°	217.5	219.0	222.8	226.5	234.8	243.0	254.3	264.8	279.0	285.8	296.3
60°	195.8	195.8	199.5	204.8	210.8	218.3	228.0	240.8	251.3	259.5	267.0
62.5°	172.5	174.8	177.0	180.8	187.5	196.5	204.8	213.8	226.5	232.5	239.3
65°	149.3	151.5	156.0	159.8	165.0	171.0	181.5	189.0	198.8	205.5	211.5
67.5°	129.0	131.3	134.3	138.8	142.5	149.3	156.8	164.3	174.8	179.3	183.8
70°	108.0	110.3	112.5	118.5	122.3	127.5	132.8	140.3	149.3	152.3	156.0
72.5°	91.5	92.3	95.3	96.8	102.0	106.5	112.5	117.0	123.8	127.5	130.5
75°	77.3	77.3	78.0	79.5	82.5	85.5	90.0	94.5	100.5	102.8	106.5
77.5°	60.8	63.0	62.3	63.8	65.3	66.8	70.5	73.5	79.5	81.0	82.5
80°	43.5	44.3	46.5	48.8	48.8	51.0	53.3	54.0	57.8	60.0	60.0
82.5°	31.5	32.3	31.5	32.3	33.0	33.8	36.0	39.0	39.0	39.8	41.3
85°	19.5	19.5	20.3	21.0	21.0	20.3	21.8	21.0	21.8	23.3	23.3
87.5°	9.8	9.0	9.0	9.0	9.0	9.0	9.8	9.0	9.8	9.8	9.8
90°	15.3	14.5	13.6	12.8	12.0	10.8	9.6	8.5	7.3	6.7	6.0
92.5°	15.3	14.5	13.6	12.8	12.0	11.0	10.0	9.0	8.0	7.5	8.2
95°	15.3	14.5	13.6	12.8	12.0	18.3	24.6	30.9	37.2	40.4	40.6
97.5°	14.7	14.4	14.1	13.8	13.5	29.3	45.0	60.8	76.5	84.4	83.9
100°	31.1	55.8	80.5	105.3	130.0	129.3	128.7	128.0	127.3	127.0	126.8
102.5°	176.2	175.9	175.6	175.2	174.9	174.6	174.2	173.9	173.6	173.4	173.1
105°	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.7	222.4
107.5°	272.6	272.5	272.3	272.2	272.0	271.7	271.3	271.0	270.7	270.5	270.5
110°	319.3	319.8	320.3	320.8	321.3	321.0	320.6	320.3	320.0	319.8	319.8

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	366.5	367.2	367.8	368.5	369.1	368.9	368.8	368.6	368.5	368.4	368.2
115°	414.3	415.0	415.7	416.3	417.0	416.8	416.6	416.5	416.3	416.2	415.8
117.5°	460.1	461.1	462.0	463.0	464.0	463.4	462.7	462.1	461.4	461.1	461.1
120°	506.1	506.4	506.7	507.1	507.4	506.9	506.4	505.9	505.4	505.1	505.2
122.5°	548.7	549.0	549.3	549.7	550.0	549.8	549.6	549.5	549.3	549.2	548.8
125°	589.1	589.8	590.5	591.1	591.8	591.8	591.8	591.8	591.8	591.8	591.2
127.5°	627.9	628.2	628.5	628.9	629.2	629.4	629.5	629.7	629.8	629.9	629.5
130°	664.6	665.1	665.6	666.1	666.6	666.4	666.2	666.1	665.9	665.8	665.4
132.5°	700.2	700.2	700.2	700.2	700.2	700.7	701.2	701.7	702.2	702.4	701.9
135°	733.3	733.6	733.9	734.3	734.6	734.9	735.2	735.5	735.8	736.0	735.5
137.5°	765.9	765.9	765.9	765.9	765.9	766.2	766.6	766.9	767.2	767.4	766.9
140°	795.6	795.3	795.0	794.6	794.3	794.5	794.7	794.8	795.0	795.1	794.9
142.5°	823.5	823.5	823.5	823.5	823.5	823.2	822.8	822.5	822.2	822.0	821.9
145°	850.3	850.1	850.0	849.8	849.6	849.6	849.6	849.6	849.6	849.6	849.4
147.5°	873.4	873.3	873.1	873.0	872.8	872.6	872.4	872.3	872.1	872.0	872.0
150°	895.8	895.5	895.2	894.8	894.5	894.2	893.8	893.5	893.2	893.0	893.2
152.5°	915.2	914.9	914.6	914.2	913.9	913.6	913.2	912.9	912.6	912.4	912.8
155°	933.1	932.6	932.1	931.6	931.1	930.8	930.4	930.1	929.8	929.6	930.1
157.5°	948.0	947.5	947.0	946.5	946.0	946.0	946.0	946.0	946.0	946.0	946.3
160°	962.2	961.5	960.8	960.2	959.5	959.3	959.1	959.0	958.8	958.7	959.2
162.5°	975.4	974.4	973.4	972.4	971.4	971.2	971.1	970.9	970.8	970.7	971.2
165°	985.9	984.9	983.9	982.9	981.9	981.7	981.5	981.4	981.2	981.1	981.6
167.5°	994.7	993.6	992.4	991.3	990.1	989.9	989.8	989.6	989.5	989.4	989.9
170°	1001.4	1000.1	998.8	997.4	996.1	995.9	995.7	995.6	995.4	995.3	995.9
172.5°	1006.0	1004.8	1003.7	1002.5	1001.3	1001.0	1000.6	1000.3	1000.0	999.8	1000.4
175°	1009.6	1008.3	1007.0	1005.6	1004.3	1004.1	1004.0	1003.8	1003.7	1003.6	1004.1
177.5°	1011.2	1010.1	1008.9	1007.8	1006.6	1006.4	1006.2	1006.1	1005.9	1005.8	1006.3
180°	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0	1008.0

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	913.6	913.6	913.6	913.6
2.5°	892.6	899.4	906.1	914.4
5°	874.6	886.6	899.4	911.4
7.5°	855.1	872.4	888.9	906.1
10°	833.4	855.1	873.9	897.9
12.5°	809.4	832.6	858.9	885.9
15°	785.4	814.6	842.4	873.1
17.5°	762.8	790.6	821.4	858.1
20°	735.8	766.6	801.1	840.1
22.5°	707.3	741.1	778.6	820.6
25°	683.3	717.8	753.8	798.1
27.5°	657.1	693.1	728.3	775.6
30°	627.1	666.1	702.1	750.8
32.5°	598.6	637.6	677.3	723.1
35°	570.8	609.1	648.8	695.3
37.5°	544.6	579.1	618.1	660.1
40°	519.8	551.3	585.8	624.1
42.5°	488.3	525.1	557.3	585.1
45°	461.3	491.3	521.3	543.8
47.5°	429.8	459.8	485.3	503.3
50°	403.6	427.6	448.6	464.3
52.5°	372.0	394.6	411.8	423.8
55°	341.3	360.8	375.8	384.1
57.5°	313.5	326.3	337.5	345.0
60°	282.8	292.5	302.3	310.5
62.5°	249.8	260.3	265.5	274.5
65°	220.5	227.3	235.5	238.5
67.5°	192.0	195.8	201.0	207.0
70°	162.0	164.3	169.5	177.8
72.5°	135.8	138.0	141.8	144.8
75°	108.0	110.3	113.3	116.3
77.5°	84.8	85.5	87.0	90.0
80°	61.5	63.8	65.3	66.0
82.5°	42.8	43.5	43.5	44.3
85°	27.0	25.5	25.5	26.3
87.5°	9.8	11.3	11.3	12.8
90°	4.7	3.4	2.0	0.7
92.5°	9.7	11.2	12.7	14.2
95°	41.1	41.6	42.1	42.6
97.5°	82.9	82.0	81.0	80.0
100°	126.3	125.8	125.3	124.8
102.5°	172.4	171.7	171.1	170.4
105°	221.7	221.0	220.4	219.7
107.5°	270.5	270.5	270.5	270.5
110°	319.8	319.8	319.8	319.8

TEST NUMBER: P1036046

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	367.7	367.2	366.7	366.2
115°	415.0	414.1	413.3	412.5
117.5°	461.1	461.1	461.1	461.1
120°	505.4	505.5	505.7	505.9
122.5°	548.0	547.1	546.3	545.5
125°	590.1	588.9	587.8	586.6
127.5°	628.7	627.8	627.0	626.2
130°	664.6	663.7	662.9	662.1
132.5°	700.9	699.9	698.9	697.9
135°	734.5	733.6	732.6	731.6
137.5°	765.9	764.9	763.9	762.9
140°	794.6	794.3	793.9	793.6
142.5°	821.7	821.6	821.4	821.2
145°	849.1	848.8	848.4	848.1
147.5°	872.0	872.0	872.0	872.0
150°	893.5	893.8	894.2	894.5
152.5°	913.6	914.5	915.3	916.1
155°	931.1	932.1	933.1	934.1
157.5°	946.8	947.3	947.8	948.3
160°	960.2	961.2	962.2	963.2
162.5°	972.2	973.2	974.2	975.2
165°	982.6	983.6	984.6	985.6
167.5°	990.9	991.8	992.8	993.8
170°	997.1	998.2	999.4	1000.6
172.5°	1001.6	1002.7	1003.9	1005.1
175°	1005.1	1006.0	1007.0	1008.0
177.5°	1007.3	1008.3	1009.3	1010.3
180°	1008.0	1008.0	1008.0	1008.0

(END OF REPORT)