

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036050

Luminaire Tested: S125RDIW-B610D770UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036050
REPORT IS A COMBINATION OF REPORTS P1006775 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D770UB30-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5513.0 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	70	81	75	69	65	62	58	55	50	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	36	33	32
4	74	64	56	50	67	58	52	47	49	44	40	40	37	34	32	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	23	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5905	5905	5905	5905
5°	5901	6656	5901	5116
10°	5867	7479	5848	4422
15°	5804	7913	5764	3850
20°	5727	8542	5676	3480
25°	5627	9669	5563	3159
30°	5524	10277	5442	2929
35°	5392	8452	5317	2714
40°	5158	5739	5114	2521
45°	4850	4126	4843	2332
50°	4534	3173	4556	2156
55°	4179	2580	4171	1987
60°	3848	2115	3830	1765
65°	3462	1762	3485	1420
70°	3145	1414	3131	1182
75°	2656	1071	2656	973
80°	2152	653	2126	653
85°	1515	344	1469	389

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8406 cd/sqm

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	1.6
10°-20°	259.1	4.7
20°-30°	410.9	7.5
30°-40°	496.5	9.0
40°-50°	442.0	8.0
50°-60°	339.0	6.1
60°-70°	220.1	4.0
70°-80°	106.8	1.9
80°-90°	26.6	0.5
90°-100°	34.5	0.6
100°-110°	229.5	4.2
110°-120°	413.3	7.5
120°-130°	530.4	9.6
130°-140°	570.5	10.3
140°-150°	535.5	9.7
150°-160°	433.1	7.9
160°-170°	280.1	5.1
170°-180°	96.6	1.8
0°-30°	758.4	13.8
0°-40°	1254.9	22.8
0°-60°	2035.9	36.9
0°-90°	2389.5	43.3
90°-120°	677.3	12.3
90°-150°	2313.7	42.0
90°-180°	3123.0	56.6
0°-180°	5513.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	922	922	922	922	922	
5°	920	1056	920	812	920	87
15°	881	1269	875	618	881	248
25°	805	1520	796	496	805	371
35°	702	1261	692	405	702	437
45°	549	564	548	319	549	423
55°	388	310	387	238	388	347
65°	241	176	242	142	241	241
75°	117	82	117	74	117	126
85°	26	17	26	20	26	30
90°	1	18	1	18	1	4
95°	43	16	43	16	43	53
105°	222	224	222	224	222	235
115°	416	413	416	413	416	412
125°	592	592	592	592	592	529
135°	738	735	738	735	738	569
145°	856	853	856	853	856	535
155°	942	935	942	935	942	434
165°	994	989	994	989	994	281
175°	1017	1012	1017	1012	1017	97
180°	1017	1017	1017	1017	1017	

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7
2.5°	922.5	930.0	932.3	938.4	945.2	946.7	950.5	955.8	958.8	958.0	958.0
5°	919.5	932.3	941.4	952.0	964.9	970.2	974.7	986.0	995.1	1000.4	1009.5
7.5°	914.2	933.1	948.2	964.1	983.8	992.9	1002.7	1018.6	1035.2	1045.8	1055.7
10°	905.8	930.0	951.2	974.7	1001.2	1014.8	1026.9	1051.1	1071.6	1085.2	1107.9
12.5°	893.7	924.0	953.5	984.5	1017.8	1032.2	1048.9	1075.3	1104.1	1123.8	1142.7
15°	880.9	917.2	949.0	986.0	1026.2	1048.1	1069.3	1097.3	1123.0	1145.0	1166.9
17.5°	865.7	904.3	943.7	986.0	1031.5	1053.4	1071.6	1104.9	1132.1	1154.0	1173.7
20°	847.6	890.7	935.3	982.3	1028.4	1048.9	1066.3	1102.6	1126.8	1150.3	1178.3
22.5°	827.9	874.8	922.5	968.6	1014.0	1036.0	1056.4	1088.2	1114.7	1146.5	1182.8
25°	805.2	856.6	905.1	951.2	994.4	1014.8	1033.0	1067.8	1104.9	1145.0	1185.8
27.5°	782.5	832.4	879.3	921.7	968.6	987.6	1005.7	1049.6	1093.5	1135.9	1191.9
30°	757.5	808.2	849.1	888.4	933.8	953.5	976.2	1026.2	1076.1	1133.6	1201.7
32.5°	729.5	775.7	813.5	854.4	895.2	919.5	948.2	1002.7	1060.2	1129.1	1216.1
35°	701.5	738.6	773.4	812.0	861.2	886.9	914.9	972.4	1044.3	1126.8	1228.2
37.5°	665.9	701.5	728.8	768.1	818.8	849.1	877.1	943.7	1025.4	1121.5	1227.5
40°	629.6	659.9	685.6	726.5	781.7	809.7	840.0	912.6	1005.7	1106.4	1209.3
42.5°	590.3	616.0	644.0	683.3	737.1	764.3	799.1	883.9	978.5	1085.2	1162.4
45°	548.6	573.6	597.1	637.9	691.7	721.2	759.0	846.0	945.2	1040.5	1086.7
47.5°	507.8	529.7	554.7	590.3	644.8	677.3	715.9	809.0	900.5	980.8	984.5
50°	468.4	485.8	507.0	543.3	600.1	631.1	671.2	758.3	847.6	902.8	865.7
52.5°	427.6	443.5	465.4	497.2	550.2	586.5	621.3	708.3	783.2	820.3	752.2
55°	387.5	401.1	423.8	459.3	505.5	533.5	569.1	650.1	715.9	716.6	642.5
57.5°	348.1	360.2	379.1	410.9	454.1	486.6	519.1	589.5	634.2	621.3	538.8
60°	313.3	320.9	338.3	369.3	409.4	432.9	467.7	526.7	556.2	532.8	444.2
62.5°	277.0	284.5	298.2	323.1	361.0	385.9	407.9	456.3	476.8	441.2	368.5
65°	240.6	249.7	259.6	279.2	314.8	331.5	351.1	386.7	406.4	364.8	301.9
67.5°	208.9	213.4	223.2	243.7	268.6	283.8	297.4	321.6	325.4	292.1	240.6
70°	179.4	180.9	189.9	202.1	221.0	230.1	241.4	255.8	255.8	228.5	187.7
72.5°	146.1	148.3	155.1	168.0	179.4	183.9	187.7	196.8	195.2	170.3	142.3
75°	117.3	118.8	124.1	130.2	134.7	143.0	146.1	144.5	143.8	122.6	106.7
77.5°	90.8	91.6	95.4	100.6	101.4	104.4	102.2	102.2	95.4	83.2	74.9
80°	66.6	67.4	68.9	70.4	70.4	70.4	70.4	66.6	62.1	54.5	52.2
82.5°	44.6	44.6	45.4	46.9	46.2	44.6	43.1	39.4	36.3	34.1	32.5
85°	26.5	26.5	27.2	26.5	23.5	22.7	21.2	20.4	19.7	18.9	18.9
87.5°	12.9	12.1	10.6	9.1	9.1	9.1	9.1	9.1	9.1	8.3	8.3
90°	0.8	2.1	3.5	4.8	6.1	6.8	7.4	8.6	9.7	10.9	12.1
92.5°	14.3	12.8	11.3	9.8	8.3	7.5	8.0	9.0	10.1	11.1	12.1
95°	43.0	42.5	42.0	41.5	41.0	40.7	37.5	31.2	24.8	18.5	12.1
97.5°	80.7	81.7	82.7	83.7	84.7	85.2	77.2	61.3	45.4	29.5	13.6
100°	125.9	126.4	126.9	127.4	127.9	128.1	128.4	129.1	129.8	130.5	131.2
102.5°	171.9	172.6	173.2	173.9	174.6	174.9	175.1	175.4	175.7	176.1	176.4
105°	221.6	222.3	222.9	223.6	224.3	224.6	224.6	224.6	224.6	224.6	224.6
107.5°	272.9	272.9	272.9	272.9	272.9	272.9	273.1	273.4	273.7	274.1	274.4
110°	322.6	322.6	322.6	322.6	322.6	322.6	322.8	323.1	323.4	323.8	324.1

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	369.3	369.8	370.3	370.8	371.3	371.6	371.7	371.9	372.0	372.2	372.4
115°	416.1	416.9	417.7	418.6	419.4	419.8	419.9	420.1	420.2	420.4	420.6
117.5°	465.1	465.1	465.1	465.1	465.1	465.1	465.4	466.1	466.8	467.4	468.1
120°	510.3	510.1	509.9	509.8	509.6	509.5	509.8	510.3	510.8	511.3	511.8
122.5°	550.2	551.0	551.9	552.7	553.6	554.0	554.1	554.3	554.4	554.6	554.8
125°	591.7	592.9	594.1	595.2	596.4	597.0	597.0	597.0	597.0	597.0	597.0
127.5°	631.7	632.5	633.3	634.2	635.0	635.4	635.3	635.2	635.0	634.9	634.7
130°	667.8	668.6	669.5	670.3	671.2	671.6	671.7	671.9	672.0	672.2	672.4
132.5°	704.0	705.0	706.0	707.0	708.0	708.5	708.3	707.8	707.3	706.8	706.3
135°	737.9	738.9	739.9	741.0	742.0	742.5	742.3	742.0	741.7	741.3	741.0
137.5°	769.6	770.6	771.6	772.6	773.6	774.1	773.9	773.6	773.3	772.9	772.6
140°	800.5	800.8	801.2	801.5	801.8	802.0	801.9	801.8	801.6	801.5	801.3
142.5°	828.4	828.6	828.7	828.9	829.0	829.1	829.3	829.6	830.0	830.3	830.7
145°	855.5	855.8	856.2	856.5	856.8	857.0	857.0	857.0	857.0	857.0	857.0
147.5°	879.6	879.6	879.6	879.6	879.6	879.6	879.7	879.9	880.0	880.2	880.4
150°	902.3	902.0	901.6	901.3	901.0	900.8	901.0	901.3	901.6	902.0	902.3
152.5°	924.1	923.3	922.4	921.6	920.7	920.3	920.5	920.8	921.2	921.5	921.9
155°	942.2	941.2	940.2	939.2	938.2	937.7	937.9	938.2	938.5	938.9	939.2
157.5°	956.5	956.0	955.5	955.0	954.5	954.3	954.3	954.3	954.3	954.3	954.3
160°	971.6	970.6	969.6	968.6	967.6	967.1	967.2	967.3	967.5	967.6	967.8
162.5°	983.7	982.7	981.7	980.6	979.6	979.1	979.2	979.4	979.5	979.7	979.9
165°	994.2	993.2	992.2	991.2	990.2	989.7	989.8	989.9	990.1	990.2	990.4
167.5°	1002.5	1001.5	1000.5	999.5	998.5	998.0	998.1	998.2	998.4	998.5	998.7
170°	1009.3	1008.1	1006.9	1005.8	1004.6	1004.0	1004.1	1004.3	1004.4	1004.6	1004.8
172.5°	1013.8	1012.6	1011.4	1010.3	1009.1	1008.5	1008.7	1009.0	1009.3	1009.7	1010.0
175°	1016.8	1015.8	1014.8	1013.8	1012.8	1012.3	1012.4	1012.6	1012.7	1012.9	1013.1
177.5°	1019.1	1018.1	1017.1	1016.1	1015.1	1014.6	1014.7	1014.8	1015.0	1015.1	1015.3
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7
2.5°	961.8	967.1	971.7	969.4	978.5	977.7	979.2	982.3	983.0	981.5	978.5
5°	1014.0	1021.6	1034.5	1041.3	1039.8	1045.8	1048.9	1053.4	1057.9	1056.4	1056.4
7.5°	1072.3	1082.9	1095.8	1113.2	1115.5	1120.8	1129.8	1129.8	1135.1	1132.9	1132.1
10°	1123.0	1135.9	1156.3	1169.9	1176.0	1179.0	1188.1	1191.1	1197.2	1197.9	1197.9
12.5°	1164.6	1187.3	1201.0	1214.6	1217.6	1222.2	1229.0	1233.5	1235.8	1235.8	1233.5
15°	1186.6	1204.8	1220.6	1235.0	1243.3	1247.1	1253.9	1259.2	1262.3	1269.1	1270.6
17.5°	1195.7	1217.6	1243.3	1263.8	1278.2	1281.9	1295.6	1300.1	1306.2	1309.2	1313.0
20°	1208.5	1240.3	1271.3	1296.3	1309.9	1319.8	1334.2	1355.3	1361.4	1361.4	1359.1
22.5°	1219.9	1260.8	1303.1	1343.2	1354.6	1374.3	1400.7	1423.5	1432.5	1436.3	1433.3
25°	1233.5	1289.5	1344.8	1394.7	1425.7	1440.1	1475.7	1502.9	1513.5	1519.6	1521.1
27.5°	1257.0	1327.3	1397.7	1461.3	1493.1	1509.7	1546.8	1570.3	1583.1	1588.4	1584.6
30°	1283.5	1369.7	1451.5	1508.2	1529.4	1549.8	1574.0	1583.1	1580.1	1580.1	1591.5
32.5°	1310.7	1400.0	1472.6	1509.7	1517.3	1514.3	1504.4	1477.2	1461.3	1461.3	1471.1
35°	1325.8	1403.0	1440.1	1428.0	1398.5	1381.1	1327.3	1297.1	1263.0	1260.8	1272.1
37.5°	1317.5	1350.8	1335.7	1256.2	1216.1	1182.8	1098.8	1065.5	1040.5	1005.7	1059.5
40°	1259.2	1247.9	1169.2	1054.9	1010.3	963.3	896.8	863.5	828.6	823.3	836.2
42.5°	1160.9	1093.5	978.5	868.0	822.6	789.3	738.6	706.1	684.1	675.0	690.2
45°	1038.3	932.3	817.3	729.5	679.6	662.2	616.0	587.2	570.6	563.8	574.4
47.5°	888.4	781.7	672.8	598.6	569.1	551.7	520.6	495.7	481.3	476.8	481.3
50°	754.5	644.8	553.2	505.5	479.0	464.6	438.9	423.0	411.7	408.6	416.2
52.5°	638.7	538.8	469.2	426.8	409.4	397.3	379.1	365.5	358.7	355.7	361.0
55°	535.0	454.1	398.1	361.7	348.9	341.3	325.4	317.8	310.3	309.5	314.8
57.5°	443.5	387.5	336.0	310.3	306.5	295.1	281.5	274.7	270.9	270.2	272.4
60°	369.3	319.3	288.3	265.6	260.3	251.2	243.7	239.1	234.6	233.1	234.6
62.5°	307.2	267.9	242.9	227.8	220.2	217.9	209.6	204.3	203.6	203.6	205.1
65°	253.5	220.2	204.3	192.2	186.9	184.6	178.6	174.8	175.6	175.6	176.3
67.5°	206.6	182.4	168.0	161.9	157.4	156.6	150.6	149.1	147.6	147.6	149.1
70°	164.2	149.1	138.5	135.5	134.7	129.4	127.1	126.4	124.1	124.9	124.9
72.5°	128.6	118.8	112.8	108.2	109.0	105.9	102.9	102.9	101.4	103.7	103.7
75°	95.4	90.8	86.3	84.8	86.3	84.8	82.5	81.7	82.5	81.7	81.7
77.5°	70.4	68.1	66.6	65.8	65.8	62.8	61.3	62.8	59.8	61.3	61.3
80°	49.2	46.2	45.4	43.9	44.6	42.4	43.1	41.6	41.6	41.6	41.6
82.5°	31.0	30.3	30.3	30.3	29.5	29.5	29.5	29.5	29.5	29.5	28.8
85°	18.9	18.2	18.2	18.2	17.4	17.4	17.4	17.4	17.4	17.4	17.4
87.5°	7.6	8.3	8.3	9.1	8.3	7.6	7.6	7.6	8.3	8.3	7.6
90°	12.9	13.7	14.6	15.4	15.8	16.1	16.6	17.1	17.6	18.1	17.6
92.5°	12.9	13.7	14.6	15.4	15.8	15.9	16.1	16.2	16.4	16.6	16.4
95°	12.9	13.7	14.6	15.4	15.8	15.8	15.8	15.8	15.8	15.8	15.8
97.5°	13.9	14.3	14.6	14.9	15.1	15.2	15.3	15.5	15.6	15.8	15.6
100°	106.2	81.2	56.3	31.3	18.8	18.5	17.8	17.1	16.5	15.8	16.5
102.5°	176.7	177.1	177.4	177.7	177.9	170.9	156.8	142.7	128.7	114.6	128.7
105°	224.6	224.6	224.6	224.6	224.6	224.5	224.4	224.2	224.1	223.9	224.1
107.5°	274.6	274.7	274.9	275.0	275.1	274.8	274.1	273.4	272.8	272.1	272.8
110°	323.6	323.1	322.6	322.1	321.9	322.0	322.1	322.3	322.4	322.6	322.4

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	371.7	371.0	370.3	369.6	369.3	369.1	368.8	368.5	368.1	367.8	368.1
115°	419.9	419.3	418.6	417.9	417.6	417.1	416.1	415.1	414.1	413.1	414.1
117.5°	467.1	466.1	465.1	464.1	463.6	463.4	463.1	462.8	462.4	462.1	462.4
120°	511.5	511.1	510.8	510.5	510.3	509.9	509.0	508.2	507.3	506.5	507.3
122.5°	554.5	554.1	553.8	553.5	553.3	552.8	551.8	550.7	549.7	548.7	549.7
125°	596.3	595.7	595.0	594.3	594.0	593.7	593.2	592.7	592.2	591.7	592.2
127.5°	634.4	634.0	633.7	633.4	633.2	632.5	631.2	629.8	628.5	627.1	628.5
130°	671.9	671.4	670.9	670.4	670.1	669.7	668.8	668.0	667.1	666.3	667.1
132.5°	706.3	706.3	706.3	706.3	706.3	705.9	705.0	704.2	703.3	702.5	703.3
135°	740.6	740.3	739.9	739.6	739.4	738.9	737.9	736.9	735.9	734.9	735.9
137.5°	772.6	772.6	772.6	772.6	772.6	772.2	771.3	770.5	769.6	768.8	769.6
140°	801.6	802.0	802.3	802.6	802.8	802.3	801.3	800.2	799.2	798.2	799.2
142.5°	830.7	830.7	830.7	830.7	830.7	830.2	829.2	828.1	827.1	826.1	827.1
145°	857.2	857.4	857.5	857.7	857.8	857.3	856.3	855.3	854.3	853.3	854.3
147.5°	880.6	880.8	880.9	881.1	881.2	880.6	879.4	878.3	877.1	875.9	877.1
150°	902.6	903.0	903.3	903.6	903.8	903.1	901.8	900.4	899.1	897.7	899.1
152.5°	922.2	922.6	922.9	923.2	923.4	922.8	921.6	920.5	919.3	918.1	919.3
155°	939.7	940.2	940.7	941.2	941.5	940.8	939.5	938.1	936.8	935.4	936.8
157.5°	954.8	955.3	955.8	956.3	956.5	955.8	954.5	953.2	951.8	950.5	951.8
160°	968.5	969.2	969.9	970.6	970.9	970.2	968.9	967.5	966.2	964.8	966.2
162.5°	980.9	981.9	982.9	983.9	984.4	983.6	982.1	980.6	979.1	977.6	979.1
165°	991.4	992.4	993.5	994.5	995.0	994.3	993.0	991.6	990.3	988.9	990.3
167.5°	999.9	1001.1	1002.2	1003.4	1004.0	1003.2	1001.7	1000.2	998.7	997.2	998.7
170°	1006.1	1007.5	1008.8	1010.1	1010.8	1010.0	1008.5	1007.0	1005.5	1004.0	1005.5
172.5°	1011.2	1012.4	1013.5	1014.7	1015.3	1014.5	1013.0	1011.5	1010.0	1008.5	1010.0
175°	1014.4	1015.8	1017.1	1018.4	1019.1	1018.3	1016.8	1015.3	1013.8	1012.3	1013.8
177.5°	1016.5	1017.7	1018.8	1020.0	1020.6	1019.9	1018.6	1017.3	1015.9	1014.6	1015.9
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7
2.5°	982.3	977.0	979.2	977.0	974.7	972.4	967.1	959.6	953.5	949.0	948.2
5°	1057.9	1051.1	1046.6	1044.3	1039.8	1033.7	1023.9	1012.5	998.9	993.6	983.0
7.5°	1127.6	1125.3	1114.7	1113.2	1110.2	1098.8	1082.2	1067.0	1049.6	1035.2	1021.6
10°	1193.4	1188.1	1180.5	1169.9	1168.4	1154.0	1138.2	1117.0	1094.3	1080.6	1056.4
12.5°	1234.3	1228.2	1219.9	1213.1	1209.3	1200.2	1178.3	1157.1	1136.6	1111.7	1090.5
15°	1263.8	1256.2	1241.1	1235.8	1231.2	1219.1	1203.2	1181.3	1154.0	1136.6	1106.4
17.5°	1303.9	1294.8	1279.7	1269.8	1261.5	1242.6	1219.9	1190.4	1164.6	1145.0	1117.7
20°	1350.0	1336.4	1316.8	1303.9	1291.8	1269.8	1238.0	1203.2	1166.2	1141.9	1113.9
22.5°	1426.5	1400.7	1369.7	1351.6	1334.9	1297.1	1259.2	1216.1	1174.5	1138.2	1104.1
25°	1500.6	1474.9	1436.3	1411.3	1385.6	1341.7	1291.8	1232.0	1179.0	1136.6	1092.0
27.5°	1569.5	1543.0	1507.5	1477.2	1452.2	1386.4	1320.5	1253.2	1185.8	1127.6	1082.2
30°	1585.4	1574.0	1546.8	1520.3	1497.6	1437.1	1360.6	1275.1	1194.2	1119.2	1068.5
32.5°	1489.3	1517.3	1524.1	1520.3	1505.9	1462.8	1392.4	1302.4	1206.3	1115.5	1045.8
35°	1289.5	1340.2	1392.4	1420.4	1434.0	1440.1	1398.5	1316.0	1214.6	1109.4	1030.7
37.5°	1069.3	1118.5	1201.0	1242.6	1288.8	1349.3	1365.9	1313.0	1210.8	1104.9	1006.5
40°	878.6	941.4	1009.5	1047.3	1087.5	1196.4	1278.9	1272.9	1198.7	1088.2	987.6
42.5°	715.1	754.5	814.3	855.9	905.1	1026.9	1137.4	1191.9	1162.4	1067.8	963.3
45°	596.3	626.6	669.0	711.3	741.6	852.1	983.0	1072.3	1100.3	1031.5	926.3
47.5°	502.5	525.2	562.3	588.8	621.3	708.3	821.8	947.5	1006.5	980.0	886.9
50°	430.6	448.8	478.3	494.9	523.7	598.6	684.9	816.5	905.8	908.9	834.7
52.5°	367.8	385.9	410.9	425.3	442.7	493.4	580.4	691.7	794.6	832.4	774.9
55°	320.1	330.7	351.1	362.5	378.4	427.6	482.8	577.4	684.9	746.9	710.6
57.5°	276.2	287.6	300.4	309.5	320.9	360.2	410.2	481.3	588.0	655.3	643.2
60°	240.6	247.5	259.6	266.4	277.0	302.7	337.5	408.6	493.4	557.0	563.8
62.5°	207.4	213.4	221.7	227.8	234.6	255.0	280.8	331.5	405.6	474.5	483.6
65°	178.6	183.9	188.4	193.7	199.0	211.9	233.8	273.2	330.7	395.0	414.7
67.5°	152.9	154.4	161.2	161.9	165.0	174.8	190.7	222.5	264.1	315.6	341.3
70°	127.9	130.9	132.4	134.7	137.7	144.5	157.4	174.1	205.1	246.7	270.9
72.5°	103.7	104.4	106.7	108.2	111.2	116.5	122.6	135.5	155.1	185.4	207.4
75°	82.5	83.2	84.8	85.5	87.8	89.3	92.3	101.4	115.0	133.2	149.1
77.5°	62.1	63.6	65.1	65.1	65.8	67.4	68.9	71.9	78.7	90.8	104.4
80°	42.4	43.1	43.1	43.9	43.1	45.4	47.7	51.5	54.5	58.3	65.1
82.5°	29.5	29.5	29.5	30.3	30.3	31.0	31.0	31.8	32.5	34.8	37.8
85°	18.2	18.2	18.9	17.4	18.2	18.9	18.9	18.2	18.9	19.7	20.4
87.5°	7.6	7.6	8.3	8.3	8.3	8.3	7.6	8.3	7.6	8.3	8.3
90°	17.1	16.6	16.1	15.8	15.4	14.6	13.7	12.9	12.1	10.9	9.7
92.5°	16.2	16.1	15.9	15.8	15.4	14.6	13.7	12.9	12.1	11.1	10.1
95°	15.8	15.8	15.8	15.8	15.4	14.6	13.7	12.9	12.1	18.5	24.8
97.5°	15.5	15.3	15.2	15.1	14.9	14.6	14.3	13.9	13.6	29.5	45.4
100°	17.1	17.8	18.5	18.8	31.3	56.3	81.2	106.2	131.2	130.5	129.8
102.5°	142.7	156.8	170.9	177.9	177.7	177.4	177.1	176.7	176.4	176.1	175.7
105°	224.2	224.4	224.5	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6
107.5°	273.4	274.1	274.8	275.1	275.0	274.9	274.7	274.6	274.4	274.1	273.7
110°	322.3	322.1	322.0	321.9	322.1	322.6	323.1	323.6	324.1	323.8	323.4

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	368.5	368.8	369.1	369.3	369.6	370.3	371.0	371.7	372.4	372.2	372.0
115°	415.1	416.1	417.1	417.6	417.9	418.6	419.3	419.9	420.6	420.4	420.2
117.5°	462.8	463.1	463.4	463.6	464.1	465.1	466.1	467.1	468.1	467.4	466.8
120°	508.2	509.0	509.9	510.3	510.5	510.8	511.1	511.5	511.8	511.3	510.8
122.5°	550.7	551.8	552.8	553.3	553.5	553.8	554.1	554.5	554.8	554.6	554.4
125°	592.7	593.2	593.7	594.0	594.3	595.0	595.7	596.3	597.0	597.0	597.0
127.5°	629.8	631.2	632.5	633.2	633.4	633.7	634.0	634.4	634.7	634.9	635.0
130°	668.0	668.8	669.7	670.1	670.4	670.9	671.4	671.9	672.4	672.2	672.0
132.5°	704.2	705.0	705.9	706.3	706.3	706.3	706.3	706.3	706.3	706.8	707.3
135°	736.9	737.9	738.9	739.4	739.6	739.9	740.3	740.6	741.0	741.3	741.7
137.5°	770.5	771.3	772.2	772.6	772.6	772.6	772.6	772.6	772.6	772.9	773.3
140°	800.2	801.3	802.3	802.8	802.6	802.3	802.0	801.6	801.3	801.5	801.6
142.5°	828.1	829.2	830.2	830.7	830.7	830.7	830.7	830.7	830.7	830.3	830.0
145°	855.3	856.3	857.3	857.8	857.7	857.5	857.4	857.2	857.0	857.0	857.0
147.5°	878.3	879.4	880.6	881.2	881.1	880.9	880.8	880.6	880.4	880.2	880.0
150°	900.4	901.8	903.1	903.8	903.6	903.3	903.0	902.6	902.3	902.0	901.6
152.5°	920.5	921.6	922.8	923.4	923.2	922.9	922.6	922.2	921.9	921.5	921.2
155°	938.1	939.5	940.8	941.5	941.2	940.7	940.2	939.7	939.2	938.9	938.5
157.5°	953.2	954.5	955.8	956.5	956.3	955.8	955.3	954.8	954.3	954.3	954.3
160°	967.5	968.9	970.2	970.9	970.6	969.9	969.2	968.5	967.8	967.6	967.5
162.5°	980.6	982.1	983.6	984.4	983.9	982.9	981.9	980.9	979.9	979.7	979.5
165°	991.6	993.0	994.3	995.0	994.5	993.5	992.4	991.4	990.4	990.2	990.1
167.5°	1000.2	1001.7	1003.2	1004.0	1003.4	1002.2	1001.1	999.9	998.7	998.5	998.4
170°	1007.0	1008.5	1010.0	1010.8	1010.1	1008.8	1007.5	1006.1	1004.8	1004.6	1004.4
172.5°	1011.5	1013.0	1014.5	1015.3	1014.7	1013.5	1012.4	1011.2	1010.0	1009.7	1009.3
175°	1015.3	1016.8	1018.3	1019.1	1018.4	1017.1	1015.8	1014.4	1013.1	1012.9	1012.7
177.5°	1017.3	1018.6	1019.9	1020.6	1020.0	1018.8	1017.7	1016.5	1015.3	1015.1	1015.0
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7
2.5°	945.9	941.4	938.4	937.6	933.1	929.3	924.8	924.0	921.7	915.7	911.9
5°	975.5	964.9	962.6	955.8	944.4	936.1	925.5	919.5	912.6	901.3	892.2
7.5°	1005.7	991.3	980.8	970.9	955.0	939.9	924.8	912.6	900.5	883.9	870.3
10°	1035.2	1013.3	1000.4	986.0	964.1	941.4	920.2	902.8	883.1	863.5	843.8
12.5°	1062.5	1034.5	1015.6	995.1	967.9	939.9	912.6	888.4	868.0	841.5	819.6
15°	1079.1	1048.1	1029.2	1009.5	968.6	937.6	905.8	874.8	847.6	819.6	799.1
17.5°	1089.0	1054.2	1033.0	1014.8	973.2	930.8	889.9	856.6	827.1	793.8	766.6
20°	1084.4	1050.4	1030.7	1013.3	964.9	922.5	878.6	840.0	802.9	768.9	740.1
22.5°	1074.6	1039.0	1017.1	1001.2	958.0	908.1	859.7	818.0	779.5	745.4	712.9
25°	1053.4	1018.6	999.7	980.0	937.6	889.9	840.8	796.1	755.2	718.9	682.6
27.5°	1034.5	992.1	972.4	955.0	910.4	868.0	819.6	770.4	728.8	690.9	654.6
30°	1012.5	964.9	943.7	920.2	880.1	840.0	791.6	746.2	703.0	662.9	628.1
32.5°	989.1	933.8	909.6	883.1	842.3	804.4	763.6	718.9	675.8	636.4	600.1
35°	958.8	899.8	871.8	846.8	804.4	766.6	728.8	691.7	648.5	606.9	572.1
37.5°	930.0	865.0	835.5	806.7	762.1	725.7	694.7	659.9	618.3	578.2	544.9
40°	897.5	822.6	792.3	765.8	719.7	679.6	651.6	624.3	588.0	549.4	513.1
42.5°	868.0	783.2	751.5	724.2	675.8	637.9	611.5	588.8	557.0	521.4	484.3
45°	827.1	740.9	708.3	679.6	630.4	594.8	567.6	547.9	522.9	489.6	456.3
47.5°	789.3	700.0	664.4	629.6	585.0	548.6	523.7	508.5	491.9	462.4	428.3
50°	743.1	653.1	616.8	588.0	537.3	506.3	481.3	470.7	455.6	427.6	400.3
52.5°	693.2	607.7	573.6	538.8	491.9	461.6	439.7	427.6	415.5	395.0	369.3
55°	634.9	557.0	525.2	494.2	447.2	419.2	399.6	386.7	379.9	361.0	342.1
57.5°	578.9	505.5	476.0	447.2	406.4	374.6	361.7	350.4	340.5	326.9	311.0
60°	522.2	455.6	423.8	398.1	362.5	333.7	323.1	311.8	304.2	293.6	282.3
62.5°	457.1	400.3	376.1	351.9	321.6	298.9	286.8	277.7	267.9	261.1	251.2
65°	388.2	348.1	324.6	306.5	277.7	257.3	248.2	242.2	233.8	227.0	219.5
67.5°	323.9	292.1	282.3	262.6	240.6	222.5	215.7	208.1	201.3	197.5	190.7
70°	261.8	239.1	229.3	224.0	199.8	187.7	181.6	178.6	170.3	166.5	161.9
72.5°	202.8	194.5	187.7	180.9	165.0	157.4	150.6	147.6	141.5	138.5	137.0
75°	149.8	144.5	140.8	140.0	133.2	125.6	118.8	117.3	112.8	109.7	108.2
77.5°	105.2	103.7	102.9	103.7	99.1	94.6	93.1	91.6	86.3	85.5	85.5
80°	68.9	72.6	72.6	71.9	70.4	69.6	67.4	65.8	62.8	62.1	62.8
82.5°	42.4	44.6	45.4	46.9	46.2	45.4	43.9	43.1	43.9	42.4	43.1
85°	21.2	22.7	25.7	25.7	26.5	26.5	26.5	25.7	24.2	25.0	24.2
87.5°	8.3	9.1	9.1	9.1	8.3	10.6	11.4	11.4	11.4	9.8	9.8
90°	8.6	7.4	6.8	6.1	4.8	3.5	2.1	0.8	2.1	3.5	4.8
92.5°	9.0	8.0	7.5	8.3	9.8	11.3	12.8	14.3	12.8	11.3	9.8
95°	31.2	37.5	40.7	41.0	41.5	42.0	42.5	43.0	42.5	42.0	41.5
97.5°	61.3	77.2	85.2	84.7	83.7	82.7	81.7	80.7	81.7	82.7	83.7
100°	129.1	128.4	128.1	127.9	127.4	126.9	126.4	125.9	126.4	126.9	127.4
102.5°	175.4	175.1	174.9	174.6	173.9	173.2	172.6	171.9	172.6	173.2	173.9
105°	224.6	224.6	224.6	224.3	223.6	222.9	222.3	221.6	222.3	222.9	223.6
107.5°	273.4	273.1	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.9
110°	323.1	322.8	322.6	322.6	322.6	322.6	322.6	322.6	322.6	322.6	322.6

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	371.9	371.7	371.6	371.3	370.8	370.3	369.8	369.3	369.8	370.3	370.8
115°	420.1	419.9	419.8	419.4	418.6	417.7	416.9	416.1	416.9	417.7	418.6
117.5°	466.1	465.4	465.1	465.1	465.1	465.1	465.1	465.1	465.1	465.1	465.1
120°	510.3	509.8	509.5	509.6	509.8	509.9	510.1	510.3	510.1	509.9	509.8
122.5°	554.3	554.1	554.0	553.6	552.7	551.9	551.0	550.2	551.0	551.9	552.7
125°	597.0	597.0	597.0	596.4	595.2	594.1	592.9	591.7	592.9	594.1	595.2
127.5°	635.2	635.3	635.4	635.0	634.2	633.3	632.5	631.7	632.5	633.3	634.2
130°	671.9	671.7	671.6	671.2	670.3	669.5	668.6	667.8	668.6	669.5	670.3
132.5°	707.8	708.3	708.5	708.0	707.0	706.0	705.0	704.0	705.0	706.0	707.0
135°	742.0	742.3	742.5	742.0	741.0	739.9	738.9	737.9	738.9	739.9	741.0
137.5°	773.6	773.9	774.1	773.6	772.6	771.6	770.6	769.6	770.6	771.6	772.6
140°	801.8	801.9	802.0	801.8	801.5	801.2	800.8	800.5	800.8	801.2	801.5
142.5°	829.6	829.3	829.1	829.0	828.9	828.7	828.6	828.4	828.6	828.7	828.9
145°	857.0	857.0	857.0	856.8	856.5	856.2	855.8	855.5	855.8	856.2	856.5
147.5°	879.9	879.7	879.6	879.6	879.6	879.6	879.6	879.6	879.6	879.6	879.6
150°	901.3	901.0	900.8	901.0	901.3	901.6	902.0	902.3	902.0	901.6	901.3
152.5°	920.8	920.5	920.3	920.7	921.6	922.4	923.3	924.1	923.3	922.4	921.6
155°	938.2	937.9	937.7	938.2	939.2	940.2	941.2	942.2	941.2	940.2	939.2
157.5°	954.3	954.3	954.3	954.5	955.0	955.5	956.0	956.5	956.0	955.5	955.0
160°	967.3	967.2	967.1	967.6	968.6	969.6	970.6	971.6	970.6	969.6	968.6
162.5°	979.4	979.2	979.1	979.6	980.6	981.7	982.7	983.7	982.7	981.7	980.6
165°	989.9	989.8	989.7	990.2	991.2	992.2	993.2	994.2	993.2	992.2	991.2
167.5°	998.2	998.1	998.0	998.5	999.5	1000.5	1001.5	1002.5	1001.5	1000.5	999.5
170°	1004.3	1004.1	1004.0	1004.6	1005.8	1006.9	1008.1	1009.3	1008.1	1006.9	1005.8
172.5°	1009.0	1008.7	1008.5	1009.1	1010.3	1011.4	1012.6	1013.8	1012.6	1011.4	1010.3
175°	1012.6	1012.4	1012.3	1012.8	1013.8	1014.8	1015.8	1016.8	1015.8	1014.8	1013.8
177.5°	1014.8	1014.7	1014.6	1015.1	1016.1	1017.1	1018.1	1019.1	1018.1	1017.1	1016.1
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7
2.5°	909.6	906.6	904.3	902.0	892.2	881.6	880.1	877.8	873.3	878.6	876.3
5°	886.2	879.3	875.6	865.7	853.6	844.5	837.0	827.9	824.1	821.1	820.3
7.5°	857.4	851.3	844.5	834.7	819.6	804.4	793.1	784.0	776.4	772.6	772.6
10°	829.4	821.8	812.8	796.1	781.7	762.8	750.7	741.6	731.0	725.0	719.7
12.5°	800.6	792.3	784.0	762.8	746.2	726.5	709.1	697.7	692.4	685.6	676.5
15°	771.9	759.0	750.7	729.5	708.3	688.6	677.3	665.2	653.1	646.3	643.2
17.5°	741.6	732.5	718.9	696.2	672.8	655.3	638.7	627.3	613.0	606.2	599.3
20°	714.4	700.8	687.1	664.4	641.7	618.3	601.6	588.0	578.9	573.6	567.6
22.5°	681.8	669.0	657.6	633.4	608.4	586.5	568.3	560.0	550.9	542.6	536.5
25°	653.8	641.0	629.6	603.1	575.9	555.5	541.8	531.2	521.4	517.6	511.6
27.5°	624.3	612.2	597.1	570.6	546.4	529.0	514.6	504.8	497.2	489.6	485.1
30°	596.3	582.7	569.1	540.3	520.6	503.2	489.6	477.5	471.5	467.7	460.1
32.5°	569.1	551.7	540.3	513.8	494.9	478.3	466.9	456.3	448.8	441.9	435.9
35°	539.6	520.6	509.3	487.3	467.7	451.0	441.2	433.6	424.5	418.5	415.5
37.5°	511.6	495.7	484.3	461.6	441.9	428.3	417.7	407.9	404.1	395.8	394.3
40°	481.3	467.7	457.1	435.1	417.0	406.4	395.0	385.9	379.1	375.3	370.1
42.5°	454.1	442.7	431.3	410.9	393.5	380.6	372.3	364.0	357.9	351.9	348.1
45°	429.1	417.0	406.4	386.7	369.3	357.9	349.6	339.8	338.3	329.9	326.2
47.5°	402.6	392.0	382.9	362.5	346.6	335.2	325.4	318.6	311.8	308.8	303.5
50°	376.9	366.3	355.7	337.5	323.1	311.8	301.9	294.4	290.6	286.1	281.5
52.5°	348.9	340.5	332.2	313.3	298.9	289.1	280.8	270.9	267.1	263.4	260.3
55°	325.4	313.3	304.2	288.3	275.5	264.9	255.8	248.2	244.4	241.4	237.6
57.5°	293.6	286.1	278.5	264.1	252.0	241.4	232.3	226.3	221.7	219.5	220.2
60°	266.4	258.1	253.5	238.4	226.3	217.9	209.6	203.6	199.0	196.8	196.0
62.5°	237.6	231.6	223.2	212.6	200.5	193.0	186.9	182.4	174.8	174.1	171.8
65°	209.6	205.1	197.5	187.7	177.8	171.0	164.2	158.2	155.1	151.4	149.1
67.5°	182.4	177.8	171.0	162.7	155.9	149.1	143.0	137.0	131.7	128.6	127.1
70°	155.9	152.1	147.6	137.7	129.4	124.1	119.6	115.8	110.5	109.0	108.2
72.5°	130.2	126.4	124.1	115.8	108.2	103.7	99.1	95.4	93.1	92.3	90.1
75°	106.7	102.9	99.9	92.3	87.8	84.8	80.2	78.7	76.4	75.7	74.9
77.5°	83.2	79.5	78.7	73.4	68.1	66.6	65.1	62.1	62.1	62.1	60.5
80°	59.8	59.0	58.3	53.0	50.7	49.2	48.4	46.2	44.6	43.1	42.4
82.5°	40.1	39.4	38.6	36.3	34.1	33.3	32.5	31.0	31.0	31.8	30.3
85°	24.2	22.7	21.9	21.2	19.7	19.7	20.4	19.7	19.7	19.7	18.9
87.5°	9.1	9.1	9.1	9.1	9.8	8.3	9.1	9.1	8.3	8.3	7.6
90°	6.1	6.8	7.4	8.6	9.7	10.9	12.1	12.9	13.7	14.6	15.4
92.5°	8.3	7.5	8.0	9.0	10.1	11.1	12.1	12.9	13.7	14.6	15.4
95°	41.0	40.7	37.5	31.2	24.8	18.5	12.1	12.9	13.7	14.6	15.4
97.5°	84.7	85.2	77.2	61.3	45.4	29.5	13.6	13.9	14.3	14.6	14.9
100°	127.9	128.1	128.4	129.1	129.8	130.5	131.2	106.2	81.2	56.3	31.3
102.5°	174.6	174.9	175.1	175.4	175.7	176.1	176.4	176.7	177.1	177.4	177.7
105°	224.3	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6
107.5°	272.9	272.9	273.1	273.4	273.7	274.1	274.4	274.6	274.7	274.9	275.0
110°	322.6	322.6	322.8	323.1	323.4	323.8	324.1	323.6	323.1	322.6	322.1

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	371.3	371.6	371.7	371.9	372.0	372.2	372.4	371.7	371.0	370.3	369.6
115°	419.4	419.8	419.9	420.1	420.2	420.4	420.6	419.9	419.3	418.6	417.9
117.5°	465.1	465.1	465.4	466.1	466.8	467.4	468.1	467.1	466.1	465.1	464.1
120°	509.6	509.5	509.8	510.3	510.8	511.3	511.8	511.5	511.1	510.8	510.5
122.5°	553.6	554.0	554.1	554.3	554.4	554.6	554.8	554.5	554.1	553.8	553.5
125°	596.4	597.0	597.0	597.0	597.0	597.0	597.0	596.3	595.7	595.0	594.3
127.5°	635.0	635.4	635.3	635.2	635.0	634.9	634.7	634.4	634.0	633.7	633.4
130°	671.2	671.6	671.7	671.9	672.0	672.2	672.4	671.9	671.4	670.9	670.4
132.5°	708.0	708.5	708.3	707.8	707.3	706.8	706.3	706.3	706.3	706.3	706.3
135°	742.0	742.5	742.3	742.0	741.7	741.3	741.0	740.6	740.3	739.9	739.6
137.5°	773.6	774.1	773.9	773.6	773.3	772.9	772.6	772.6	772.6	772.6	772.6
140°	801.8	802.0	801.9	801.8	801.6	801.5	801.3	801.6	802.0	802.3	802.6
142.5°	829.0	829.1	829.3	829.6	830.0	830.3	830.7	830.7	830.7	830.7	830.7
145°	856.8	857.0	857.0	857.0	857.0	857.0	857.0	857.2	857.4	857.5	857.7
147.5°	879.6	879.6	879.7	879.9	880.0	880.2	880.4	880.6	880.8	880.9	881.1
150°	901.0	900.8	901.0	901.3	901.6	902.0	902.3	902.6	903.0	903.3	903.6
152.5°	920.7	920.3	920.5	920.8	921.2	921.5	921.9	922.2	922.6	922.9	923.2
155°	938.2	937.7	937.9	938.2	938.5	938.9	939.2	939.7	940.2	940.7	941.2
157.5°	954.5	954.3	954.3	954.3	954.3	954.3	954.3	954.8	955.3	955.8	956.3
160°	967.6	967.1	967.2	967.3	967.5	967.6	967.8	968.5	969.2	969.9	970.6
162.5°	979.6	979.1	979.2	979.4	979.5	979.7	979.9	980.9	981.9	982.9	983.9
165°	990.2	989.7	989.8	989.9	990.1	990.2	990.4	991.4	992.4	993.5	994.5
167.5°	998.5	998.0	998.1	998.2	998.4	998.5	998.7	999.9	1001.1	1002.2	1003.4
170°	1004.6	1004.0	1004.1	1004.3	1004.4	1004.6	1004.8	1006.1	1007.5	1008.8	1010.1
172.5°	1009.1	1008.5	1008.7	1009.0	1009.3	1009.7	1010.0	1011.2	1012.4	1013.5	1014.7
175°	1012.8	1012.3	1012.4	1012.6	1012.7	1012.9	1013.1	1014.4	1015.8	1017.1	1018.4
177.5°	1015.1	1014.6	1014.7	1014.8	1015.0	1015.1	1015.3	1016.5	1017.7	1018.8	1020.0
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7
2.5°	872.5	874.0	870.3	868.8	865.7	869.5	870.3	869.5	876.3	873.3	874.8
5°	821.8	818.8	816.5	811.2	811.2	812.0	814.3	810.5	812.8	818.0	817.3
7.5°	765.8	764.3	765.1	759.0	754.5	756.0	754.5	761.3	765.1	763.6	766.6
10°	715.1	718.2	711.3	708.3	705.3	708.3	707.6	709.1	713.6	716.6	721.9
12.5°	674.3	673.5	669.7	666.7	661.4	662.9	667.5	665.9	666.7	673.5	672.8
15°	635.7	631.1	628.1	621.3	622.8	617.5	622.1	627.3	629.6	635.7	639.5
17.5°	597.1	596.3	592.5	591.8	583.5	581.2	585.7	587.2	589.5	592.5	597.8
20°	564.5	563.8	558.5	557.0	550.2	554.7	553.2	556.2	557.7	563.8	566.1
22.5°	535.0	531.2	529.7	527.5	525.2	524.4	527.5	526.7	532.0	534.3	535.0
25°	507.8	504.8	504.0	500.2	498.7	496.4	498.7	501.0	507.0	509.3	512.3
27.5°	482.8	480.5	479.0	476.0	473.7	473.7	475.2	478.3	480.5	482.1	483.6
30°	460.1	458.6	454.1	452.5	450.3	450.3	450.3	451.8	455.6	460.1	462.4
32.5°	436.6	433.6	430.6	430.6	428.3	428.3	429.1	430.6	434.4	435.1	438.9
35°	413.9	410.9	408.6	407.1	407.9	404.9	406.4	408.6	413.2	414.7	417.0
37.5°	392.0	391.2	386.7	384.4	385.9	385.9	385.2	386.7	389.7	392.8	394.3
40°	367.8	366.3	366.3	364.0	364.8	361.7	364.0	365.5	367.0	370.1	372.3
42.5°	346.6	345.1	342.1	342.8	340.5	340.5	342.1	342.8	345.1	348.9	350.4
45°	323.9	323.9	322.4	320.1	320.9	318.6	320.1	320.9	323.9	327.7	326.2
47.5°	301.9	301.2	301.2	298.2	299.7	297.4	299.7	300.4	301.9	304.2	303.5
50°	280.8	278.5	279.2	278.5	277.7	277.7	279.2	279.2	280.8	280.8	283.0
52.5°	258.8	258.8	257.3	258.1	259.6	258.1	260.3	258.1	259.6	260.3	261.8
55°	239.1	237.6	238.4	237.6	240.6	238.4	240.6	239.1	240.6	239.9	241.4
57.5°	217.9	215.7	216.4	215.7	217.9	217.2	219.5	217.2	217.9	218.7	221.0
60°	193.7	193.7	193.7	192.2	194.5	194.5	193.7	193.7	196.8	198.3	197.5
62.5°	171.0	170.3	168.0	167.2	168.0	166.5	169.5	168.8	170.3	171.8	173.3
65°	146.1	144.5	143.8	142.3	142.3	141.5	142.3	145.3	146.1	146.8	150.6
67.5°	125.6	124.9	124.1	121.8	121.8	123.4	123.4	123.4	127.9	125.6	128.6
70°	107.5	105.9	104.4	103.7	103.7	104.4	105.2	105.9	105.2	108.2	109.0
72.5°	90.1	90.8	89.3	89.3	89.3	88.5	88.5	90.1	90.8	90.1	90.8
75°	74.9	74.9	74.2	74.9	74.9	74.2	74.2	75.7	75.7	74.9	77.2
77.5°	60.5	59.8	58.3	56.8	57.5	56.8	57.5	56.8	59.0	61.3	59.8
80°	42.4	41.6	41.6	41.6	42.4	41.6	43.1	41.6	42.4	42.4	43.1
82.5°	30.3	31.0	31.0	30.3	31.0	30.3	31.0	31.0	31.0	30.3	31.0
85°	19.7	19.7	19.7	19.7	18.9	19.7	19.7	19.7	20.4	19.7	20.4
87.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.1	8.3	9.1
90°	15.8	16.1	16.6	17.1	17.6	18.1	17.6	17.1	16.6	16.1	15.8
92.5°	15.8	15.9	16.1	16.2	16.4	16.6	16.4	16.2	16.1	15.9	15.8
95°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
97.5°	15.1	15.2	15.3	15.5	15.6	15.8	15.6	15.5	15.3	15.2	15.1
100°	18.8	18.5	17.8	17.1	16.5	15.8	16.5	17.1	17.8	18.5	18.8
102.5°	177.9	170.9	156.8	142.7	128.7	114.6	128.7	142.7	156.8	170.9	177.9
105°	224.6	224.5	224.4	224.2	224.1	223.9	224.1	224.2	224.4	224.5	224.6
107.5°	275.1	274.8	274.1	273.4	272.8	272.1	272.8	273.4	274.1	274.8	275.1
110°	321.9	322.0	322.1	322.3	322.4	322.6	322.4	322.3	322.1	322.0	321.9

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	369.3	369.1	368.8	368.5	368.1	367.8	368.1	368.5	368.8	369.1	369.3
115°	417.6	417.1	416.1	415.1	414.1	413.1	414.1	415.1	416.1	417.1	417.6
117.5°	463.6	463.4	463.1	462.8	462.4	462.1	462.4	462.8	463.1	463.4	463.6
120°	510.3	509.9	509.0	508.2	507.3	506.5	507.3	508.2	509.0	509.9	510.3
122.5°	553.3	552.8	551.8	550.7	549.7	548.7	549.7	550.7	551.8	552.8	553.3
125°	594.0	593.7	593.2	592.7	592.2	591.7	592.2	592.7	593.2	593.7	594.0
127.5°	633.2	632.5	631.2	629.8	628.5	627.1	628.5	629.8	631.2	632.5	633.2
130°	670.1	669.7	668.8	668.0	667.1	666.3	667.1	668.0	668.8	669.7	670.1
132.5°	706.3	705.9	705.0	704.2	703.3	702.5	703.3	704.2	705.0	705.9	706.3
135°	739.4	738.9	737.9	736.9	735.9	734.9	735.9	736.9	737.9	738.9	739.4
137.5°	772.6	772.2	771.3	770.5	769.6	768.8	769.6	770.5	771.3	772.2	772.6
140°	802.8	802.3	801.3	800.2	799.2	798.2	799.2	800.2	801.3	802.3	802.8
142.5°	830.7	830.2	829.2	828.1	827.1	826.1	827.1	828.1	829.2	830.2	830.7
145°	857.8	857.3	856.3	855.3	854.3	853.3	854.3	855.3	856.3	857.3	857.8
147.5°	881.2	880.6	879.4	878.3	877.1	875.9	877.1	878.3	879.4	880.6	881.2
150°	903.8	903.1	901.8	900.4	899.1	897.7	899.1	900.4	901.8	903.1	903.8
152.5°	923.4	922.8	921.6	920.5	919.3	918.1	919.3	920.5	921.6	922.8	923.4
155°	941.5	940.8	939.5	938.1	936.8	935.4	936.8	938.1	939.5	940.8	941.5
157.5°	956.5	955.8	954.5	953.2	951.8	950.5	951.8	953.2	954.5	955.8	956.5
160°	970.9	970.2	968.9	967.5	966.2	964.8	966.2	967.5	968.9	970.2	970.9
162.5°	984.4	983.6	982.1	980.6	979.1	977.6	979.1	980.6	982.1	983.6	984.4
165°	995.0	994.3	993.0	991.6	990.3	988.9	990.3	991.6	993.0	994.3	995.0
167.5°	1004.0	1003.2	1001.7	1000.2	998.7	997.2	998.7	1000.2	1001.7	1003.2	1004.0
170°	1010.8	1010.0	1008.5	1007.0	1005.5	1004.0	1005.5	1007.0	1008.5	1010.0	1010.8
172.5°	1015.3	1014.5	1013.0	1011.5	1010.0	1008.5	1010.0	1011.5	1013.0	1014.5	1015.3
175°	1019.1	1018.3	1016.8	1015.3	1013.8	1012.3	1013.8	1015.3	1016.8	1018.3	1019.1
177.5°	1020.6	1019.9	1018.6	1017.3	1015.9	1014.6	1015.9	1017.3	1018.6	1019.9	1020.6
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7	921.7
2.5°	871.8	875.6	872.5	870.3	876.3	879.3	879.3	884.6	889.9	894.5	895.2
5°	818.0	824.1	825.6	824.9	833.9	838.5	848.3	853.6	861.2	866.5	872.5
7.5°	768.9	777.2	777.9	779.5	793.1	800.6	809.0	822.6	833.2	840.8	847.6
10°	719.7	725.0	730.3	737.1	750.7	763.6	775.7	790.1	803.7	811.2	821.1
12.5°	682.6	686.4	692.4	697.0	711.3	722.7	738.6	758.3	777.9	784.0	796.1
15°	644.0	646.3	658.4	662.9	675.0	693.9	703.8	722.7	743.9	755.2	768.9
17.5°	599.3	613.0	620.5	625.8	641.0	656.1	672.0	691.7	718.9	729.5	739.3
20°	567.6	577.4	585.7	592.5	606.2	628.9	643.2	659.1	684.9	697.0	711.3
22.5°	539.6	547.9	555.5	563.0	572.1	592.5	609.2	631.1	656.9	668.2	684.9
25°	513.1	521.4	525.9	535.0	547.1	561.5	581.2	600.9	626.6	639.5	655.3
27.5°	487.3	495.7	504.0	511.6	519.9	533.5	547.1	572.1	598.6	613.7	627.3
30°	465.4	469.2	476.8	485.1	493.4	506.3	522.2	539.6	569.8	583.5	600.1
32.5°	441.2	448.0	453.3	459.3	469.9	480.5	494.9	516.9	541.1	553.9	572.1
35°	418.5	424.5	428.3	438.9	445.7	457.1	471.5	491.1	511.6	525.9	541.8
37.5°	396.5	402.6	407.1	413.2	422.3	432.1	447.2	461.6	485.8	497.9	516.1
40°	373.8	379.1	384.4	391.2	399.6	411.7	420.8	438.9	458.6	472.2	485.8
42.5°	351.9	354.9	361.0	368.5	376.9	387.5	400.3	414.7	434.4	446.5	458.6
45°	328.4	333.7	340.5	345.8	353.4	364.0	375.3	388.2	407.9	420.0	432.9
47.5°	306.5	310.3	314.8	323.1	333.0	340.5	352.6	364.8	382.9	394.3	406.4
50°	283.8	287.6	294.4	299.7	307.2	317.1	328.4	341.3	358.7	366.3	378.4
52.5°	262.6	264.1	270.9	276.2	283.8	295.1	304.2	315.6	332.2	340.5	352.6
55°	241.4	242.9	246.7	252.0	260.3	269.4	279.2	292.1	306.5	314.1	325.4
57.5°	219.5	221.0	224.8	228.5	236.9	245.2	256.5	267.1	281.5	288.3	298.9
60°	197.5	197.5	201.3	206.6	212.6	220.2	230.1	242.9	253.5	261.8	269.4
62.5°	174.1	176.3	178.6	182.4	189.2	198.3	206.6	215.7	228.5	234.6	241.4
65°	150.6	152.9	157.4	161.2	166.5	172.5	183.1	190.7	200.5	207.4	213.4
67.5°	130.2	132.4	135.5	140.0	143.8	150.6	158.2	165.7	176.3	180.9	185.4
70°	109.0	111.2	113.5	119.6	123.4	128.6	133.9	141.5	150.6	153.6	157.4
72.5°	92.3	93.1	96.1	97.6	102.9	107.5	113.5	118.1	124.9	128.6	131.7
75°	77.9	77.9	78.7	80.2	83.2	86.3	90.8	95.4	101.4	103.7	107.5
77.5°	61.3	63.6	62.8	64.3	65.8	67.4	71.1	74.2	80.2	81.7	83.2
80°	43.9	44.6	46.9	49.2	49.2	51.5	53.7	54.5	58.3	60.5	60.5
82.5°	31.8	32.5	31.8	32.5	33.3	34.1	36.3	39.4	39.4	40.1	41.6
85°	19.7	19.7	20.4	21.2	21.2	20.4	21.9	21.2	21.9	23.5	23.5
87.5°	9.8	9.1	9.1	9.1	9.1	9.1	9.8	9.1	9.8	9.8	9.8
90°	15.4	14.6	13.7	12.9	12.1	10.9	9.7	8.6	7.4	6.8	6.1
92.5°	15.4	14.6	13.7	12.9	12.1	11.1	10.1	9.0	8.0	7.5	8.3
95°	15.4	14.6	13.7	12.9	12.1	18.5	24.8	31.2	37.5	40.7	41.0
97.5°	14.9	14.6	14.3	13.9	13.6	29.5	45.4	61.3	77.2	85.2	84.7
100°	31.3	56.3	81.2	106.2	131.2	130.5	129.8	129.1	128.4	128.1	127.9
102.5°	177.7	177.4	177.1	176.7	176.4	176.1	175.7	175.4	175.1	174.9	174.6
105°	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.3
107.5°	275.0	274.9	274.7	274.6	274.4	274.1	273.7	273.4	273.1	272.9	272.9
110°	322.1	322.6	323.1	323.6	324.1	323.8	323.4	323.1	322.8	322.6	322.6

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	369.6	370.3	371.0	371.7	372.4	372.2	372.0	371.9	371.7	371.6	371.3
115°	417.9	418.6	419.3	419.9	420.6	420.4	420.2	420.1	419.9	419.8	419.4
117.5°	464.1	465.1	466.1	467.1	468.1	467.4	466.8	466.1	465.4	465.1	465.1
120°	510.5	510.8	511.1	511.5	511.8	511.3	510.8	510.3	509.8	509.5	509.6
122.5°	553.5	553.8	554.1	554.5	554.8	554.6	554.4	554.3	554.1	554.0	553.6
125°	594.3	595.0	595.7	596.3	597.0	597.0	597.0	597.0	597.0	597.0	596.4
127.5°	633.4	633.7	634.0	634.4	634.7	634.9	635.0	635.2	635.3	635.4	635.0
130°	670.4	670.9	671.4	671.9	672.4	672.2	672.0	671.9	671.7	671.6	671.2
132.5°	706.3	706.3	706.3	706.3	706.3	706.8	707.3	707.8	708.3	708.5	708.0
135°	739.6	739.9	740.3	740.6	741.0	741.3	741.7	742.0	742.3	742.5	742.0
137.5°	772.6	772.6	772.6	772.6	772.6	772.9	773.3	773.6	773.9	774.1	773.6
140°	802.6	802.3	802.0	801.6	801.3	801.5	801.6	801.8	801.9	802.0	801.8
142.5°	830.7	830.7	830.7	830.7	830.7	830.3	830.0	829.6	829.3	829.1	829.0
145°	857.7	857.5	857.4	857.2	857.0	857.0	857.0	857.0	857.0	857.0	856.8
147.5°	881.1	880.9	880.8	880.6	880.4	880.2	880.0	879.9	879.7	879.6	879.6
150°	903.6	903.3	903.0	902.6	902.3	902.0	901.6	901.3	901.0	900.8	901.0
152.5°	923.2	922.9	922.6	922.2	921.9	921.5	921.2	920.8	920.5	920.3	920.7
155°	941.2	940.7	940.2	939.7	939.2	938.9	938.5	938.2	937.9	937.7	938.2
157.5°	956.3	955.8	955.3	954.8	954.3	954.3	954.3	954.3	954.3	954.3	954.5
160°	970.6	969.9	969.2	968.5	967.8	967.6	967.5	967.3	967.2	967.1	967.6
162.5°	983.9	982.9	981.9	980.9	979.9	979.7	979.5	979.4	979.2	979.1	979.6
165°	994.5	993.5	992.4	991.4	990.4	990.2	990.1	989.9	989.8	989.7	990.2
167.5°	1003.4	1002.2	1001.1	999.9	998.7	998.5	998.4	998.2	998.1	998.0	998.5
170°	1010.1	1008.8	1007.5	1006.1	1004.8	1004.6	1004.4	1004.3	1004.1	1004.0	1004.6
172.5°	1014.7	1013.5	1012.4	1011.2	1010.0	1009.7	1009.3	1009.0	1008.7	1008.5	1009.1
175°	1018.4	1017.1	1015.8	1014.4	1013.1	1012.9	1012.7	1012.6	1012.4	1012.3	1012.8
177.5°	1020.0	1018.8	1017.7	1016.5	1015.3	1015.1	1015.0	1014.8	1014.7	1014.6	1015.1
180°	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8	1016.8

TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	921.7	921.7	921.7	921.7
2.5°	900.5	907.3	914.2	922.5
5°	882.4	894.5	907.3	919.5
7.5°	862.7	880.1	896.8	914.2
10°	840.8	862.7	881.6	905.8
12.5°	816.5	840.0	866.5	893.7
15°	792.3	821.8	849.8	880.9
17.5°	769.6	797.6	828.6	865.7
20°	742.4	773.4	808.2	847.6
22.5°	713.6	747.7	785.5	827.9
25°	689.4	724.2	760.5	805.2
27.5°	662.9	699.2	734.8	782.5
30°	632.6	672.0	708.3	757.5
32.5°	603.9	643.2	683.3	729.5
35°	575.9	614.5	654.6	701.5
37.5°	549.4	584.2	623.6	665.9
40°	524.4	556.2	591.0	629.6
42.5°	492.6	529.7	562.3	590.3
45°	465.4	495.7	525.9	548.6
47.5°	433.6	463.9	489.6	507.8
50°	407.1	431.3	452.5	468.4
52.5°	375.3	398.1	415.5	427.6
55°	344.3	364.0	379.1	387.5
57.5°	316.3	329.2	340.5	348.1
60°	285.3	295.1	305.0	313.3
62.5°	252.0	262.6	267.9	277.0
65°	222.5	229.3	237.6	240.6
67.5°	193.7	197.5	202.8	208.9
70°	163.5	165.7	171.0	179.4
72.5°	137.0	139.2	143.0	146.1
75°	109.0	111.2	114.3	117.3
77.5°	85.5	86.3	87.8	90.8
80°	62.1	64.3	65.8	66.6
82.5°	43.1	43.9	43.9	44.6
85°	27.2	25.7	25.7	26.5
87.5°	9.8	11.4	11.4	12.9
90°	4.8	3.5	2.1	0.8
92.5°	9.8	11.3	12.8	14.3
95°	41.5	42.0	42.5	43.0
97.5°	83.7	82.7	81.7	80.7
100°	127.4	126.9	126.4	125.9
102.5°	173.9	173.2	172.6	171.9
105°	223.6	222.9	222.3	221.6
107.5°	272.9	272.9	272.9	272.9
110°	322.6	322.6	322.6	322.6



TEST NUMBER: P1036050

CATALOG NUMBER: S125RDIW-B610D770UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	370.8	370.3	369.8	369.3
115°	418.6	417.7	416.9	416.1
117.5°	465.1	465.1	465.1	465.1
120°	509.8	509.9	510.1	510.3
122.5°	552.7	551.9	551.0	550.2
125°	595.2	594.1	592.9	591.7
127.5°	634.2	633.3	632.5	631.7
130°	670.3	669.5	668.6	667.8
132.5°	707.0	706.0	705.0	704.0
135°	741.0	739.9	738.9	737.9
137.5°	772.6	771.6	770.6	769.6
140°	801.5	801.2	800.8	800.5
142.5°	828.9	828.7	828.6	828.4
145°	856.5	856.2	855.8	855.5
147.5°	879.6	879.6	879.6	879.6
150°	901.3	901.6	902.0	902.3
152.5°	921.6	922.4	923.3	924.1
155°	939.2	940.2	941.2	942.2
157.5°	955.0	955.5	956.0	956.5
160°	968.6	969.6	970.6	971.6
162.5°	980.6	981.7	982.7	983.7
165°	991.2	992.2	993.2	994.2
167.5°	999.5	1000.5	1001.5	1002.5
170°	1005.8	1006.9	1008.1	1009.3
172.5°	1010.3	1011.4	1012.6	1013.8
175°	1013.8	1014.8	1015.8	1016.8
177.5°	1016.1	1017.1	1018.1	1019.1
180°	1016.8	1016.8	1016.8	1016.8

(END OF REPORT)