

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857639

Luminaire Tested: **LX4C30D010 EX4C309830 4LBWLI**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857639  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C30D010 EX4C309830 4LBWLI  
Description:  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2594.1 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 31.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857639

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBWLI

### Luminous Intensity Polar Plot






TEST NUMBER: P857639

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 106 | 101 | 97  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  |  | 93  | 90  | 88  |  | 90  |
| 3   | 100 | 93  | 87  | 83  | 98  | 92  | 86  | 82  | 89  | 85  | 81  |  | 86  | 83  | 80  |  | 84  |
| 4   | 94  | 86  | 79  | 75  | 92  | 84  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 5   | 88  | 79  | 72  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  |  | 74  | 70  | 66  |  | 73  |
| 6   | 83  | 73  | 66  | 62  | 82  | 72  | 66  | 61  | 71  | 65  | 61  |  | 69  | 64  | 60  |  | 68  |
| 7   | 78  | 68  | 61  | 56  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 64  | 59  | 55  |  | 63  |
| 8   | 74  | 63  | 56  | 52  | 72  | 62  | 56  | 51  | 61  | 55  | 51  |  | 60  | 55  | 51  |  | 59  |
| 9   | 69  | 59  | 52  | 48  | 68  | 58  | 52  | 47  | 57  | 51  | 47  |  | 56  | 51  | 47  |  | 55  |
| 10  | 66  | 55  | 48  | 44  | 65  | 54  | 48  | 44  | 53  | 48  | 44  |  | 53  | 47  | 44  |  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P857639

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBWLI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 155.4  | 6.0       |
| 10°-20°   | 490.5  | 18.9      |
| 20°-30°   | 765.2  | 29.5      |
| 30°-40°   | 744.5  | 28.7      |
| 40°-50°   | 371.9  | 14.3      |
| 50°-60°   | 57.6   | 2.2       |
| 60°-70°   | 7.0    | 0.3       |
| 70°-80°   | 1.9    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1411.2 | 54.4      |
| 0°-40°    | 2155.7 | 83.1      |
| 0°-60°    | 2585.2 | 99.7      |
| 0°-90°    | 2594.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2594.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1589 |      |
| 5°  | 1610 | 155  |
| 15° | 1732 | 491  |
| 25° | 1682 | 765  |
| 35° | 1209 | 745  |
| 45° | 466  | 372  |
| 55° | 48   | 58   |
| 65° | 6    | 7    |
| 75° | 3    | 2    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P857639

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBWLI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1589.4 |
| 2.5°  | 1595.3 |
| 5°    | 1610.2 |
| 7.5°  | 1634.0 |
| 10°   | 1663.7 |
| 12.5° | 1702.2 |
| 15°   | 1732.0 |
| 17.5° | 1755.8 |
| 20°   | 1758.8 |
| 22.5° | 1738.0 |
| 25°   | 1681.6 |
| 27.5° | 1598.3 |
| 30°   | 1494.3 |
| 32.5° | 1363.7 |
| 35°   | 1209.2 |
| 37.5° | 1039.8 |
| 40°   | 861.5  |
| 42.5° | 671.5  |
| 45°   | 466.5  |
| 47.5° | 300.1  |
| 50°   | 181.2  |
| 52.5° | 98.0   |
| 55°   | 47.6   |
| 57.5° | 20.8   |
| 60°   | 11.9   |
| 62.5° | 8.9    |
| 65°   | 6.0    |
| 67.5° | 6.0    |
| 70°   | 2.9    |
| 72.5° | 2.9    |
| 75°   | 2.9    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)