

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857964

Luminaire Tested: **LX4C40D010 EX4C409040 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409040 4LBWLI
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4047.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857964

CATALOG NUMBER: LX4C40D010 EX4C409040 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P857964

CATALOG NUMBER: LX4C40D010 EX4C409040 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P857964

CATALOG NUMBER: LX4C40D010 EX4C409040 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.5	6.0
10°-20°	765.3	18.9
20°-30°	1193.8	29.5
30°-40°	1161.6	28.7
40°-50°	580.2	14.3
50°-60°	89.8	2.2
60°-70°	10.9	0.3
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2201.5	54.4
0°-40°	3363.1	83.1
0°-60°	4033.1	99.7
0°-90°	4047.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4047.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2480	
5°	2512	242
15°	2702	765
25°	2623	1194
35°	1886	1162
45°	728	580
55°	74	90
65°	9	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P857964

CATALOG NUMBER: LX4C40D010 EX4C409040 4LBWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2479.6
2.5°	2488.9
5°	2512.1
7.5°	2549.2
10°	2595.6
12.5°	2655.7
15°	2702.1
17.5°	2739.2
20°	2743.9
22.5°	2711.4
25°	2623.4
27.5°	2493.5
30°	2331.3
32.5°	2127.5
35°	1886.4
37.5°	1622.1
40°	1344.1
42.5°	1047.5
45°	727.7
47.5°	468.1
50°	282.7
52.5°	152.9
55°	74.3
57.5°	32.5
60°	18.6
62.5°	13.9
65°	9.3
67.5°	9.3
70°	4.6
72.5°	4.6
75°	4.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)