

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212198

Luminaire Tested: **LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1836.7 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212198

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212198

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20760	20760	20760
5°	54594	19780	12914
10°	214053	17116	10752
15°	394071	13489	9528
20°	495195	9536	8660
25°	592300	6296	7728
30°	622871	3949	6779
35°	627894	2389	5866
40°	577779	1593	4995
45°	411076	1151	4137
50°	169852	889	3406
55°	9796	844	2989
60°	1143	814	2441
65°	390	963	1742
70°	482	963	1190
75°	636	1273	1273
80°	0	1897	1395
85°	0	3779	1890

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212198

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.7	1.8
10°-20°	269.1	14.7
20°-30°	556.7	30.3
30°-40°	606.0	33.0
40°-50°	332.3	18.1
50°-60°	28.8	1.6
60°-70°	4.7	0.3
70°-80°	3.4	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	859.5	46.8
0°-40°	1465.5	79.8
0°-60°	1826.6	99.4
0°-90°	1836.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1836.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	214	214	214	214	214	
5°	561	384	203	140	133	102
15°	3929	1652	134	91	95	1097
25°	5541	2197	59	55	72	2502
35°	5309	601	20	32	50	3258
45°	3000	61	8	18	30	2290
55°	58	7	5	11	18	198
65°	2	2	4	7	8	2
75°	2	2	3	5	3	1
85°	0	2	3	2	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212198

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3
2.5°	337.0	325.3	323.5	325.3	316.9	316.1	317.8	311.0	305.1	299.2	294.2
5°	561.4	537.0	529.4	519.4	494.2	485.8	484.2	457.2	431.2	406.7	384.1
7.5°	1091.0	1042.2	1016.2	965.8	888.4	853.9	835.4	747.1	664.8	590.0	522.0
10°	2176.0	2048.3	1986.1	1891.0	1722.2	1639.0	1578.4	1356.6	1138.0	927.9	743.0
12.5°	3175.4	3104.7	3013.1	2962.6	2688.7	2583.7	2483.6	2176.0	1843.2	1503.6	1166.6
15°	3929.2	3825.8	3728.4	3704.8	3489.6	3367.0	3256.0	2937.4	2541.5	2109.6	1651.5
17.5°	4372.2	4298.2	4205.8	4161.3	3909.0	3809.8	3683.8	3375.4	2990.4	2560.1	2028.1
20°	4803.4	4694.1	4563.8	4496.6	4217.5	4103.2	3960.3	3635.9	3228.2	2771.0	2239.0
22.5°	5197.5	5056.2	4871.4	4767.1	4453.7	4327.7	4167.9	3816.6	3375.4	2852.6	2256.7
25°	5541.2	5413.5	5167.2	4984.8	4615.1	4466.2	4280.6	3913.2	3428.2	2845.8	2197.0
27.5°	5606.9	5521.0	5300.1	5089.1	4671.4	4505.8	4313.3	3933.4	3391.4	2752.6	2036.4
30°	5568.2	5475.7	5298.4	5083.2	4647.8	4480.6	4280.6	3847.7	3246.8	2534.9	1742.3
32.5°	5474.9	5395.0	5183.3	4956.3	4531.8	4357.9	4146.9	3646.9	2998.9	2188.6	1281.7
35°	5309.3	5189.1	4933.5	4747.0	4347.8	4168.7	3910.7	3378.7	2628.2	1573.4	600.9
37.5°	4972.2	4855.4	4671.4	4499.0	4110.0	3899.0	3626.7	3005.5	1948.2	858.1	371.5
40°	4568.8	4467.9	4307.4	4140.2	3739.4	3496.4	3196.3	2349.1	1146.4	483.3	228.6
42.5°	4130.2	4025.8	3844.3	3649.4	3212.3	2956.0	2631.5	1520.4	604.3	285.0	124.4
45°	3000.5	2907.2	2775.2	2635.0	2381.9	2197.0	1770.1	798.4	334.5	151.4	61.4
47.5°	2053.3	1942.3	1698.6	1403.6	1138.0	973.2	732.1	346.3	171.5	75.6	36.2
50°	1127.0	1009.4	885.0	689.2	461.4	379.0	295.0	167.2	77.3	37.8	20.2
52.5°	276.6	244.6	223.6	205.9	163.0	147.0	124.4	69.8	35.3	21.0	14.2
55°	58.0	53.8	51.3	50.4	46.2	44.5	38.7	27.0	19.4	13.4	6.8
57.5°	16.9	16.0	16.9	16.9	16.9	16.0	16.0	11.8	10.9	6.8	4.2
60°	5.9	5.9	5.9	6.8	6.8	6.8	7.6	7.6	5.9	4.2	3.4
62.5°	2.5	2.5	2.5	3.4	3.4	4.2	4.2	4.2	3.4	3.4	2.5
65°	1.7	1.7	1.7	1.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5
67.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
70°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.5
80°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
85°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
87.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212198

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3
2.5°	279.8	271.4	261.4	250.4	248.8	243.0	234.6	222.8	218.5	210.1	202.6
5°	351.3	328.6	305.1	284.2	277.4	268.1	253.0	231.9	218.5	203.4	190.9
7.5°	447.1	395.0	347.1	309.3	297.5	282.4	258.9	231.9	211.8	190.9	174.0
10°	574.9	469.0	386.6	325.3	306.0	285.8	254.7	221.9	198.3	174.0	156.3
12.5°	821.2	577.4	423.6	333.6	306.8	280.7	241.2	205.9	179.0	154.6	137.0
15°	1167.4	783.4	498.4	339.5	298.4	266.5	220.2	184.1	157.1	134.5	117.6
17.5°	1459.9	978.3	598.4	356.4	292.5	247.9	195.8	158.8	132.8	112.6	99.2
20°	1602.7	1065.7	643.8	358.9	275.7	220.2	167.2	132.0	109.3	92.5	80.7
22.5°	1586.0	1036.2	601.8	314.3	232.9	185.8	138.6	106.7	87.4	73.9	65.5
25°	1473.4	908.6	490.9	240.3	181.6	150.5	108.5	83.2	68.2	58.9	52.1
27.5°	1284.3	729.6	358.1	169.8	137.8	114.3	80.7	63.8	52.1	45.4	41.2
30°	989.3	466.5	205.9	121.9	100.1	81.5	60.6	46.2	39.5	35.3	31.9
32.5°	510.1	227.0	137.0	87.4	70.6	58.9	42.0	33.6	29.4	27.0	25.2
35°	279.8	161.4	95.0	56.2	45.4	37.8	28.6	23.5	21.8	20.2	20.2
37.5°	192.5	100.1	53.0	33.6	27.8	23.5	19.4	16.9	16.0	16.0	16.0
40°	111.0	53.0	30.2	21.0	17.7	16.0	13.4	12.6	12.6	12.6	13.4
42.5°	57.2	31.1	20.2	14.2	12.6	10.9	9.3	9.3	9.3	10.1	10.9
45°	33.6	21.0	13.4	9.3	8.4	7.6	6.8	6.8	7.6	8.4	9.3
47.5°	21.0	14.2	8.4	5.9	5.0	5.0	5.0	5.0	5.9	6.8	7.6
50°	14.2	7.6	5.0	3.4	3.4	3.4	3.4	4.2	5.0	5.9	6.8
52.5°	7.6	4.2	3.4	2.5	2.5	2.5	3.4	3.4	4.2	5.0	5.9
55°	4.2	3.4	2.5	2.5	2.5	2.5	2.5	3.4	4.2	5.0	5.9
57.5°	3.4	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	5.0
60°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	5.0
62.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	4.2
65°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	4.2
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	4.2
70°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	4.2
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
75°	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	4.2
77.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4
80°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4
85°	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212198

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3
2.5°	198.3	191.7	184.9	184.9	181.6	176.5	174.8	169.8	166.4	164.7	163.0
5°	181.6	171.5	162.2	161.4	157.1	151.4	148.7	143.8	140.4	138.6	137.8
7.5°	162.2	152.2	142.9	141.2	137.8	133.6	131.1	126.9	125.2	123.5	122.7
10°	143.8	133.6	126.9	125.2	122.7	119.4	116.8	114.3	112.6	111.8	111.8
12.5°	125.2	117.6	111.8	110.2	108.5	105.8	104.2	102.6	101.7	101.7	101.7
15°	108.5	101.7	96.6	96.6	95.0	93.3	93.3	91.6	90.8	91.6	92.5
17.5°	91.6	86.6	82.4	82.4	81.5	80.7	80.7	80.7	81.5	82.4	84.0
20°	75.6	71.4	69.8	69.8	69.0	69.8	69.8	70.6	71.4	73.9	76.5
22.5°	61.4	58.9	57.2	58.0	58.0	58.9	59.7	61.4	63.0	65.5	68.2
25°	49.6	47.9	47.1	47.9	48.8	49.6	51.3	53.0	55.4	58.0	61.4
27.5°	39.5	38.7	38.7	39.5	40.3	42.0	44.5	46.2	48.8	51.3	54.6
30°	31.9	31.1	31.9	33.6	34.4	36.2	37.8	40.3	42.9	45.4	48.8
32.5°	25.2	26.1	27.0	27.8	28.6	31.1	32.8	34.4	37.0	39.5	42.9
35°	21.0	21.8	22.6	23.5	24.3	26.1	27.8	29.4	31.9	34.4	37.8
37.5°	16.9	17.7	18.5	20.2	21.0	21.8	24.3	25.2	27.8	29.4	32.8
40°	14.2	15.0	16.0	16.9	17.7	19.4	21.0	21.8	23.5	26.1	28.6
42.5°	11.8	12.6	13.4	14.2	15.0	16.9	17.7	19.4	21.0	22.6	24.3
45°	10.1	10.9	11.8	12.6	13.4	14.2	15.0	16.9	17.7	19.4	21.0
47.5°	8.4	9.3	10.9	10.9	11.8	12.6	13.4	14.2	16.0	16.9	18.5
50°	7.6	8.4	9.3	10.1	10.1	10.9	11.8	12.6	13.4	14.2	16.0
52.5°	6.8	7.6	8.4	8.4	9.3	10.1	10.9	10.9	11.8	12.6	13.4
55°	5.9	6.8	7.6	7.6	8.4	9.3	9.3	10.1	10.9	10.9	11.8
57.5°	5.9	5.9	6.8	6.8	7.6	7.6	8.4	9.3	9.3	10.1	10.9
60°	5.0	5.9	5.9	6.8	6.8	7.6	7.6	8.4	8.4	9.3	9.3
62.5°	5.0	5.0	5.9	5.9	6.8	6.8	7.6	7.6	7.6	8.4	8.4
65°	5.0	5.0	5.9	5.9	5.9	6.8	6.8	6.8	6.8	7.6	7.6
67.5°	4.2	5.0	5.0	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8
70°	4.2	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9	5.9	5.9
72.5°	4.2	4.2	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0
75°	4.2	4.2	4.2	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0
77.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
80°	3.4	3.4	3.4	3.4	3.4	4.2	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5
85°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5
87.5°	3.4	3.4	3.4	2.5	2.5	2.5	2.5	2.5	2.5	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212198

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3
2.5°	160.6	158.8	160.6	158.8	158.8	155.5	158.0	156.3
5°	135.3	133.6	135.3	134.5	132.8	132.0	133.6	132.8
7.5°	121.0	119.4	121.0	121.0	119.4	118.5	120.2	119.4
10°	110.2	109.3	110.2	110.2	109.3	108.5	110.2	109.3
12.5°	100.9	100.1	101.7	101.7	100.9	100.9	102.6	100.9
15°	92.5	92.5	94.1	94.1	94.1	94.1	95.8	95.0
17.5°	84.0	85.7	87.4	88.3	88.3	88.3	89.9	89.9
20°	77.3	79.0	80.7	81.5	82.4	82.4	84.0	84.0
22.5°	69.8	71.4	73.9	74.8	75.6	76.5	78.2	78.2
25°	63.0	64.7	67.3	68.2	69.8	70.6	72.3	72.3
27.5°	56.2	58.9	60.6	62.2	63.0	64.7	66.3	66.3
30°	50.4	53.0	54.6	56.2	57.2	58.9	60.6	60.6
32.5°	44.5	47.1	48.8	50.4	52.1	53.0	55.4	55.4
35°	39.5	41.2	43.7	44.5	46.2	47.9	49.6	49.6
37.5°	34.4	36.2	37.8	39.5	41.2	42.0	43.7	44.5
40°	30.2	31.9	33.6	34.4	36.2	37.8	38.7	39.5
42.5°	26.1	27.8	29.4	30.2	31.9	32.8	34.4	34.4
45°	22.6	24.3	25.2	26.1	27.8	28.6	30.2	30.2
47.5°	19.4	21.0	21.8	22.6	23.5	24.3	26.1	26.1
50°	16.9	17.7	18.5	19.4	20.2	21.8	22.6	22.6
52.5°	14.2	16.0	16.0	16.9	17.7	18.5	19.4	20.2
55°	12.6	13.4	14.2	14.2	15.0	16.0	16.9	17.7
57.5°	10.9	11.8	12.6	12.6	13.4	13.4	14.2	15.0
60°	10.1	10.1	10.9	10.9	10.9	11.8	11.8	12.6
62.5°	8.4	8.4	9.3	9.3	9.3	9.3	9.3	9.3
65°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
67.5°	6.8	6.8	6.8	6.8	5.9	5.9	5.9	5.9
70°	5.9	5.9	5.9	5.9	5.0	5.0	5.0	4.2
72.5°	5.0	5.0	5.0	5.0	4.2	4.2	3.4	3.4
75°	4.2	4.2	4.2	4.2	4.2	3.4	3.4	3.4
77.5°	4.2	3.4	3.4	3.4	3.4	3.4	3.4	2.5
80°	3.4	3.4	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	1.7	1.7	1.7	1.7
85°	2.5	1.7	1.7	1.7	1.7	1.7	1.7	1.7
87.5°	1.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)