

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212254

Luminaire Tested: **LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2300.2 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212254

CATALOG NUMBER: LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212254

CATALOG NUMBER: LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	26011	26011	26011
5°	68373	24778	16172
10°	268078	21435	13467
15°	493531	16889	11935
20°	620164	11938	10845
25°	741807	7878	9674
30°	780070	4944	8479
35°	786378	2992	7344
40°	723602	1998	6260
45°	514828	1452	5179
50°	212744	1100	4295
55°	12262	1064	3733
60°	1414	1008	3061
65°	481	1192	2178
70°	595	1190	1473
75°	786	1572	1572
80°	0	2343	1729
85°	0	4668	2334

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212254

CATALOG NUMBER: LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	1.8
10°-20°	337.1	14.7
20°-30°	697.2	30.3
30°-40°	759.0	33.0
40°-50°	416.1	18.1
50°-60°	36.0	1.6
60°-70°	5.9	0.3
70°-80°	4.2	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.4	46.8
0°-40°	1835.4	79.8
0°-60°	2287.5	99.4
0°-90°	2300.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2300.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	268	268	268	268	268	
5°	703	481	255	176	166	128
15°	4921	2068	168	114	119	1374
25°	6940	2752	74	70	90	3134
35°	6649	753	25	40	62	4081
45°	3758	77	11	22	38	2868
55°	73	8	6	14	22	248
65°	2	3	5	8	10	3
75°	2	3	4	6	4	1
85°	0	2	4	3	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212254

CATALOG NUMBER: LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5
2.5°	422.1	407.4	405.3	407.4	396.8	395.8	397.9	389.5	382.1	374.8	368.4
5°	703.1	672.6	663.1	650.6	619.0	608.4	606.3	572.6	540.0	509.4	481.1
7.5°	1366.3	1305.3	1272.6	1209.4	1112.6	1069.4	1046.3	935.7	832.6	738.9	653.7
10°	2725.2	2565.2	2487.3	2368.4	2156.7	2052.6	1976.8	1698.8	1425.2	1162.1	930.5
12.5°	3976.8	3888.3	3773.6	3710.4	3367.3	3235.7	3110.5	2725.2	2308.3	1883.1	1461.0
15°	4920.9	4791.4	4669.4	4639.8	4370.4	4216.7	4077.8	3678.8	3183.1	2642.0	2068.4
17.5°	5475.7	5383.0	5267.2	5211.5	4895.7	4771.5	4613.5	4227.2	3745.1	3206.2	2539.9
20°	6015.6	5878.8	5715.7	5631.4	5282.0	5138.8	4959.9	4553.5	4043.0	3470.4	2804.2
22.5°	6509.4	6332.5	6100.9	5970.3	5577.8	5419.8	5219.9	4779.8	4227.2	3572.5	2826.3
25°	6939.9	6779.8	6471.4	6243.0	5779.8	5593.6	5360.9	4900.9	4293.6	3564.1	2751.5
27.5°	7021.9	6914.6	6637.7	6373.6	5850.3	5643.1	5402.0	4926.2	4247.2	3447.3	2550.5
30°	6973.5	6857.7	6635.6	6366.1	5820.9	5611.5	5360.9	4818.8	4066.1	3174.7	2182.0
32.5°	6856.6	6756.7	6491.3	6207.2	5675.7	5457.8	5193.5	4567.2	3755.7	2741.0	1605.2
35°	6649.4	6498.8	6178.8	5945.2	5445.2	5220.9	4897.8	4231.4	3291.5	1970.5	752.6
37.5°	6227.2	6080.9	5850.3	5634.6	5147.2	4883.0	4542.0	3764.1	2439.9	1074.6	465.2
40°	5721.9	5595.7	5394.7	5185.2	4683.0	4378.9	4003.0	2942.1	1435.7	605.2	286.4
42.5°	5172.5	5042.0	4814.7	4570.4	4023.1	3702.1	3295.7	1904.2	756.8	356.8	155.8
45°	3757.8	3641.0	3475.8	3299.9	2983.1	2751.5	2216.8	1000.0	418.9	189.4	76.9
47.5°	2571.6	2432.5	2127.3	1757.8	1425.2	1218.9	916.8	433.6	214.7	94.7	45.3
50°	1411.6	1264.2	1108.4	863.1	577.9	474.7	369.4	209.5	96.8	47.3	25.3
52.5°	346.3	306.3	280.0	257.9	204.2	184.2	155.8	87.4	44.2	26.3	17.9
55°	72.6	67.4	64.2	63.1	57.9	55.8	48.4	33.7	24.2	16.8	8.4
57.5°	21.0	19.9	21.0	21.0	21.0	19.9	19.9	14.7	13.7	8.4	5.2
60°	7.3	7.3	7.3	8.4	8.4	8.4	9.5	9.5	7.3	5.2	4.2
62.5°	3.1	3.1	3.1	4.2	4.2	5.2	5.2	5.2	4.2	4.2	3.1
65°	2.1	2.1	2.1	2.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
67.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1
80°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	2.1
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
85°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
87.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212254

CATALOG NUMBER: LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5
2.5°	350.5	340.0	327.3	313.7	311.5	304.2	293.7	278.9	273.7	263.1	253.7
5°	440.0	411.6	382.1	355.8	347.3	335.8	316.9	290.5	273.7	254.8	239.0
7.5°	560.0	494.7	434.6	387.3	372.6	353.6	324.2	290.5	265.2	239.0	217.9
10°	719.9	587.3	484.2	407.4	383.2	357.9	319.0	277.8	248.4	217.9	195.8
12.5°	1028.4	723.1	530.5	417.8	384.2	351.6	302.1	257.9	224.2	193.7	171.5
15°	1462.1	981.0	624.2	425.3	373.7	333.7	275.8	230.5	196.8	168.4	147.4
17.5°	1828.4	1225.2	749.5	446.3	366.3	310.5	245.2	198.9	166.3	141.0	124.2
20°	2007.4	1334.7	806.3	449.4	345.3	275.8	209.5	165.3	136.9	115.8	101.1
22.5°	1986.3	1297.9	753.6	393.7	291.6	232.6	173.7	133.7	109.5	92.6	82.1
25°	1845.2	1137.9	614.7	301.1	227.4	188.4	135.8	104.2	85.3	73.7	65.2
27.5°	1608.3	913.7	448.4	212.6	172.6	143.1	101.1	80.0	65.2	56.8	51.6
30°	1238.9	584.2	257.9	152.7	125.3	102.1	75.8	57.9	49.5	44.2	40.0
32.5°	638.9	284.2	171.5	109.5	88.4	73.7	52.6	42.1	36.8	33.7	31.6
35°	350.5	202.1	119.0	70.6	56.8	47.3	35.8	29.5	27.4	25.3	25.3
37.5°	241.1	125.3	66.3	42.1	34.7	29.5	24.2	21.0	19.9	19.9	19.9
40°	138.9	66.3	37.8	26.3	22.1	19.9	16.8	15.8	15.8	15.8	16.8
42.5°	71.6	39.0	25.3	17.9	15.8	13.7	11.6	11.6	11.6	12.7	13.7
45°	42.1	26.3	16.8	11.6	10.6	9.5	8.4	8.4	9.5	10.6	11.6
47.5°	26.3	17.9	10.6	7.3	6.3	6.3	6.3	6.3	7.3	8.4	9.5
50°	17.9	9.5	6.3	4.2	4.2	4.2	4.2	5.2	6.3	7.3	8.4
52.5°	9.5	5.2	4.2	3.1	3.1	3.1	4.2	4.2	5.2	6.3	7.3
55°	5.2	4.2	3.1	3.1	3.1	3.1	3.1	4.2	5.2	6.3	7.3
57.5°	4.2	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	5.2	6.3
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	5.2	6.3
62.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	5.2	5.2
65°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	5.2	5.2
67.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	5.2
70°	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	5.2
72.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2
75°	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	5.2
77.5°	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2
80°	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2
82.5°	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2
85°	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2
87.5°	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212254

CATALOG NUMBER: LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5
2.5°	248.4	240.0	231.6	231.6	227.4	221.0	218.9	212.6	208.4	206.3	204.2
5°	227.4	214.7	203.1	202.1	196.8	189.4	186.3	180.0	175.8	173.7	172.6
7.5°	203.1	190.5	179.0	176.9	172.6	167.4	164.2	158.9	156.8	154.7	153.7
10°	180.0	167.4	158.9	156.8	153.7	149.5	146.4	143.1	141.0	140.0	140.0
12.5°	156.8	147.4	140.0	137.9	135.8	132.6	130.6	128.4	127.3	127.3	127.3
15°	135.8	127.3	121.0	121.0	119.0	116.9	116.9	114.8	113.6	114.8	115.8
17.5°	114.8	108.4	103.2	103.2	102.1	101.1	101.1	101.1	102.1	103.2	105.2
20°	94.7	89.5	87.4	87.4	86.4	87.4	87.4	88.4	89.5	92.6	95.7
22.5°	76.9	73.7	71.6	72.6	72.6	73.7	74.7	76.9	78.9	82.1	85.3
25°	62.1	60.0	59.0	60.0	61.1	62.1	64.2	66.3	69.5	72.6	76.9
27.5°	49.5	48.4	48.4	49.5	50.5	52.6	55.8	57.9	61.1	64.2	68.4
30°	40.0	39.0	40.0	42.1	43.2	45.3	47.3	50.5	53.7	56.8	61.1
32.5°	31.6	32.6	33.7	34.7	35.8	39.0	41.1	43.2	46.3	49.5	53.7
35°	26.3	27.4	28.5	29.5	30.5	32.6	34.7	36.8	40.0	43.2	47.3
37.5°	21.0	22.1	23.2	25.3	26.3	27.4	30.5	31.6	34.7	36.8	41.1
40°	17.9	18.9	19.9	21.0	22.1	24.2	26.3	27.4	29.5	32.6	35.8
42.5°	14.7	15.8	16.8	17.9	18.9	21.0	22.1	24.2	26.3	28.5	30.5
45°	12.7	13.7	14.7	15.8	16.8	17.9	18.9	21.0	22.1	24.2	26.3
47.5°	10.6	11.6	13.7	13.7	14.7	15.8	16.8	17.9	19.9	21.0	23.2
50°	9.5	10.6	11.6	12.7	12.7	13.7	14.7	15.8	16.8	17.9	19.9
52.5°	8.4	9.5	10.6	10.6	11.6	12.7	13.7	13.7	14.7	15.8	16.8
55°	7.3	8.4	9.5	9.5	10.6	11.6	11.6	12.7	13.7	13.7	14.7
57.5°	7.3	7.3	8.4	8.4	9.5	9.5	10.6	11.6	11.6	12.7	13.7
60°	6.3	7.3	7.3	8.4	8.4	9.5	9.5	10.6	10.6	11.6	11.6
62.5°	6.3	6.3	7.3	7.3	8.4	8.4	9.5	9.5	9.5	10.6	10.6
65°	6.3	6.3	7.3	7.3	7.3	8.4	8.4	8.4	8.4	9.5	9.5
67.5°	5.2	6.3	6.3	7.3	7.3	7.3	7.3	7.3	8.4	8.4	8.4
70°	5.2	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3	7.3	7.3
72.5°	5.2	5.2	5.2	5.2	6.3	6.3	6.3	6.3	6.3	6.3	6.3
75°	5.2	5.2	5.2	5.2	5.2	6.3	6.3	6.3	6.3	6.3	6.3
77.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
80°	4.2	4.2	4.2	4.2	4.2	5.2	4.2	4.2	4.2	4.2	4.2
82.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	3.1	3.1
85°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	3.1	3.1	3.1	3.1
87.5°	4.2	4.2	4.2	3.1	3.1	3.1	3.1	3.1	3.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212254

CATALOG NUMBER: LDSQA4A25930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	268.5	268.5	268.5	268.5	268.5	268.5	268.5	268.5
2.5°	201.1	198.9	201.1	198.9	198.9	194.8	197.9	195.8
5°	169.5	167.4	169.5	168.4	166.3	165.3	167.4	166.3
7.5°	151.6	149.5	151.6	151.6	149.5	148.4	150.5	149.5
10°	137.9	136.9	137.9	137.9	136.9	135.8	137.9	136.9
12.5°	126.3	125.3	127.3	127.3	126.3	126.3	128.4	126.3
15°	115.8	115.8	117.9	117.9	117.9	117.9	120.0	119.0
17.5°	105.2	107.4	109.5	110.5	110.5	110.5	112.6	112.6
20°	96.8	98.9	101.1	102.1	103.2	103.2	105.2	105.2
22.5°	87.4	89.5	92.6	93.7	94.7	95.7	97.9	97.9
25°	78.9	81.0	84.2	85.3	87.4	88.4	90.5	90.5
27.5°	70.6	73.7	75.8	77.9	78.9	81.0	83.1	83.1
30°	63.1	66.3	68.4	70.6	71.6	73.7	75.8	75.8
32.5°	55.8	59.0	61.1	63.1	65.2	66.3	69.5	69.5
35°	49.5	51.6	54.8	55.8	57.9	60.0	62.1	62.1
37.5°	43.2	45.3	47.3	49.5	51.6	52.6	54.8	55.8
40°	37.8	40.0	42.1	43.2	45.3	47.3	48.4	49.5
42.5°	32.6	34.7	36.8	37.8	40.0	41.1	43.2	43.2
45°	28.5	30.5	31.6	32.6	34.7	35.8	37.8	37.8
47.5°	24.2	26.3	27.4	28.5	29.5	30.5	32.6	32.6
50°	21.0	22.1	23.2	24.2	25.3	27.4	28.5	28.5
52.5°	17.9	19.9	19.9	21.0	22.1	23.2	24.2	25.3
55°	15.8	16.8	17.9	17.9	18.9	19.9	21.0	22.1
57.5°	13.7	14.7	15.8	15.8	16.8	16.8	17.9	18.9
60°	12.7	12.7	13.7	13.7	13.7	14.7	14.7	15.8
62.5°	10.6	10.6	11.6	11.6	11.6	11.6	11.6	11.6
65°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
67.5°	8.4	8.4	8.4	8.4	7.3	7.3	7.3	7.3
70°	7.3	7.3	7.3	7.3	6.3	6.3	6.3	5.2
72.5°	6.3	6.3	6.3	6.3	5.2	5.2	4.2	4.2
75°	5.2	5.2	5.2	5.2	5.2	4.2	4.2	4.2
77.5°	5.2	4.2	4.2	4.2	4.2	4.2	4.2	3.1
80°	4.2	4.2	3.1	3.1	3.1	3.1	3.1	3.1
82.5°	3.1	3.1	3.1	3.1	2.1	2.1	2.1	2.1
85°	3.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
87.5°	2.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)