

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212272

Luminaire Tested: **LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2084.0 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212272

CATALOG NUMBER: LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212272

CATALOG NUMBER: LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	105	102		103	101	99		99	98	96		96	94	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	84
3	99	91	85	81	97	90	84	80		87	83	79		85	81	77		82	79	76
4	92	83	77	72	90	82	76	71		80	75	70		78	73	70		76	72	69
5	86	76	69	64	85	75	69	64		73	68	63		72	67	63		70	66	62
6	81	70	63	58	79	69	62	57		67	61	57		66	61	57		64	60	56
7	75	64	57	52	74	63	57	52		62	56	51		61	55	51		59	55	51
8	70	59	52	47	69	58	51	47		57	51	46		56	50	46		55	50	46
9	66	54	47	42	65	54	47	42		53	46	42		52	46	42		51	46	42
10	62	50	43	38	60	50	43	38		49	42	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	21797	21797	21797
5°	41747	20762	16843
10°	136498	18395	14342
15°	334276	15194	12667
20°	629834	11598	11361
25°	1054322	8220	9941
30°	1335622	5649	8479
35°	1216998	3666	7190
40°	801490	2618	6095
45°	347192	1740	5028
50°	61581	1206	4160
55°	9897	963	3496
60°	2461	891	2674
65°	779	1054	2109
70°	651	1303	1614
75°	861	1273	1273
80°	0	1897	1283
85°	0	3779	1223



TEST NUMBER: P1212272

CATALOG NUMBER: LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.9	1.4
10°-20°	231.8	11.1
20°-30°	698.3	33.5
30°-40°	794.7	38.1
40°-50°	293.9	14.1
50°-60°	23.3	1.1
60°-70°	6.3	0.3
70°-80°	4.4	0.2
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	958.9	46.0
0°-40°	1753.7	84.1
0°-60°	2070.9	99.4
0°-90°	2084.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2084.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	225	225	225	225	225	
5°	429	316	214	179	173	70
15°	3333	1126	152	119	126	1045
25°	9864	1646	77	75	93	4502
35°	10291	576	31	42	61	6118
45°	2534	68	13	23	37	2146
55°	59	13	6	14	21	96
65°	3	3	5	9	9	5
75°	2	3	3	6	3	2
85°	0	2	3	3	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212272

CATALOG NUMBER: LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0
2.5°	289.2	291.6	289.2	284.6	284.6	278.9	276.6	274.3	268.6	265.1	260.5
5°	429.3	422.4	416.6	402.8	398.3	385.6	376.4	363.9	346.6	331.7	315.6
7.5°	734.5	724.2	702.3	661.1	635.8	604.9	580.7	540.6	489.0	446.4	404.0
10°	1387.6	1342.8	1291.2	1198.2	1130.5	1058.2	1000.8	893.0	763.3	656.5	553.2
12.5°	2235.8	2239.2	2142.9	1985.6	1860.4	1733.1	1634.4	1434.7	1205.1	1004.3	805.7
15°	3333.0	3269.9	3170.1	2929.0	2678.8	2494.1	2336.8	2033.8	1708.9	1415.2	1125.9
17.5°	4488.8	4515.2	4282.2	3888.5	3492.6	3215.9	2978.4	2519.2	2133.6	1769.8	1416.3
20°	6109.4	5928.1	5595.2	4957.1	4341.8	3941.3	3589.0	2993.3	2455.0	1992.4	1595.3
22.5°	7977.9	7685.2	7008.1	6109.4	5178.6	4624.2	4133.0	3313.5	2659.3	2106.1	1656.2
25°	9863.6	9639.8	8560.9	7218.1	5884.4	5165.9	4530.2	3530.4	2756.9	2132.5	1645.8
27.5°	11319.0	10954.0	9724.8	7974.5	6305.7	5457.5	4714.9	3597.0	2736.2	2068.2	1548.3
30°	11939.9	11478.5	10116.1	8146.6	6309.1	5409.3	4623.0	3465.0	2589.2	1905.3	1364.6
32.5°	11556.5	11024.0	9650.1	7670.4	5877.5	5032.8	4268.4	3179.2	2346.0	1649.4	1025.0
35°	10290.6	9760.4	8487.5	6730.4	5189.0	4450.9	3786.4	2806.2	1998.2	1222.4	576.1
37.5°	8426.6	7974.5	7064.3	5641.1	4372.9	3773.8	3220.6	2364.4	1488.6	701.2	289.2
40°	6337.8	6019.9	5473.5	4473.8	3539.6	3083.9	2638.6	1811.1	904.5	352.4	164.2
42.5°	4393.6	4187.0	3912.6	3310.1	2730.4	2417.1	2060.2	1209.7	464.8	194.0	102.1
45°	2534.2	2404.5	2328.8	2071.6	1845.6	1692.9	1377.2	651.9	235.2	115.9	67.7
47.5°	1119.0	1032.9	996.2	888.4	826.4	785.0	623.3	277.8	126.3	74.6	56.2
50°	408.6	408.6	409.8	360.4	295.0	265.1	207.8	122.8	71.1	58.6	41.3
52.5°	144.6	142.4	148.1	140.0	122.8	110.2	91.9	62.0	43.6	36.7	23.0
55°	58.6	56.2	58.6	55.1	51.6	48.2	42.5	33.3	27.6	23.0	12.7
57.5°	26.5	26.5	27.6	26.5	26.5	24.0	21.8	25.3	19.5	12.7	8.0
60°	12.7	12.7	13.8	13.8	13.8	12.7	12.7	13.8	11.5	8.0	5.7
62.5°	5.7	5.7	6.9	6.9	6.9	6.9	6.9	8.0	5.7	4.6	3.4
65°	3.4	2.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
67.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4	3.4
70°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4
72.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4
75°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	3.4
80°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.3	2.3	2.3
82.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.3	2.3	2.3
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212272

CATALOG NUMBER: LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0
2.5°	255.9	252.5	245.6	242.2	237.5	234.1	231.9	227.3	222.7	219.2	216.9
5°	300.7	288.1	273.2	261.7	252.5	246.7	237.5	229.6	220.4	213.5	207.8
7.5°	366.2	335.1	301.8	278.9	266.3	254.8	238.7	225.0	212.4	203.1	195.1
10°	468.3	401.7	343.2	298.4	276.6	260.5	235.2	215.8	199.7	187.0	179.0
12.5°	638.2	501.5	398.3	322.5	289.2	265.1	229.6	203.1	183.6	171.0	160.7
15°	871.2	648.4	474.0	351.2	304.1	269.7	220.4	188.2	166.5	151.5	142.4
17.5°	1090.4	802.2	560.1	385.6	319.0	272.0	207.8	168.7	145.8	132.0	122.8
20°	1228.1	902.2	617.5	405.1	323.7	265.1	190.5	148.1	125.1	112.5	103.2
22.5°	1260.2	913.6	612.9	386.7	304.1	244.5	166.5	127.4	105.5	94.2	86.1
25°	1213.1	849.3	548.6	334.0	259.4	205.4	138.9	103.2	87.2	76.9	71.1
27.5°	1095.0	723.1	433.8	251.3	194.0	151.5	105.5	80.4	70.0	62.0	58.6
30°	882.6	508.5	272.0	156.1	123.9	99.8	75.8	62.0	53.9	50.5	47.0
32.5°	534.8	261.7	143.5	93.0	78.1	67.7	55.1	45.9	41.3	39.0	37.8
35°	254.8	137.7	88.4	63.1	55.1	48.2	40.1	34.4	32.2	31.0	31.0
37.5°	144.6	89.5	59.7	42.5	37.8	33.3	29.9	26.5	25.3	25.3	25.3
40°	91.9	57.3	39.0	31.0	27.6	25.3	23.0	20.7	20.7	20.7	20.7
42.5°	59.7	41.3	29.9	23.0	20.7	19.5	17.2	16.1	16.1	16.1	17.2
45°	47.0	34.4	24.0	18.4	16.1	14.9	13.8	12.7	12.7	12.7	13.8
47.5°	40.1	24.0	16.1	12.7	10.4	10.4	9.2	9.2	9.2	10.4	11.5
50°	24.0	14.9	10.4	8.0	6.9	6.9	6.9	6.9	6.9	8.0	9.2
52.5°	13.8	9.2	6.9	5.7	4.6	4.6	4.6	4.6	5.7	6.9	6.9
55°	9.2	6.9	4.6	4.6	3.4	3.4	3.4	4.6	4.6	5.7	6.9
57.5°	5.7	4.6	3.4	3.4	3.4	3.4	3.4	3.4	4.6	5.7	5.7
60°	4.6	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	5.7
62.5°	3.4	3.4	4.6	3.4	3.4	3.4	3.4	3.4	4.6	4.6	5.7
65°	3.4	3.4	4.6	4.6	3.4	3.4	3.4	3.4	3.4	4.6	5.7
67.5°	3.4	3.4	4.6	4.6	4.6	4.6	3.4	3.4	3.4	4.6	4.6
70°	3.4	4.6	4.6	4.6	4.6	4.6	4.6	3.4	3.4	4.6	4.6
72.5°	3.4	4.6	4.6	4.6	4.6	4.6	4.6	3.4	3.4	4.6	4.6
75°	3.4	3.4	4.6	4.6	4.6	4.6	4.6	3.4	3.4	3.4	4.6
77.5°	3.4	3.4	4.6	4.6	4.6	4.6	4.6	3.4	3.4	3.4	4.6
80°	3.4	3.4	3.4	4.6	3.4	4.6	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
85°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212272

CATALOG NUMBER: LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0
2.5°	213.5	211.2	207.8	206.6	207.8	206.6	200.8	199.7	197.4	197.4	197.4
5°	202.0	198.6	194.0	191.7	191.7	189.3	183.6	182.5	179.0	179.0	177.9
7.5°	188.2	183.6	177.9	175.7	175.7	173.2	167.5	165.3	163.0	163.0	161.9
10°	172.1	166.5	160.7	159.6	158.4	154.9	151.5	150.4	146.9	148.1	146.9
12.5°	153.8	149.2	144.6	142.4	142.4	138.9	136.6	135.4	134.3	134.3	134.3
15°	136.6	130.8	126.3	125.1	125.1	123.9	121.6	121.6	119.3	121.6	121.6
17.5°	117.0	112.5	111.3	109.1	110.2	109.1	106.7	108.0	108.0	109.1	110.2
20°	98.7	95.3	94.2	93.0	94.2	94.2	93.0	94.2	95.3	98.7	101.0
22.5°	82.7	80.4	80.4	79.2	80.4	81.5	80.4	82.7	84.9	87.2	90.6
25°	68.9	67.7	67.7	67.7	68.9	70.0	71.1	73.4	74.6	78.1	80.4
27.5°	56.2	56.2	56.2	57.3	58.6	59.7	60.8	64.3	65.4	68.9	71.1
30°	47.0	45.9	47.0	48.2	49.3	51.6	52.8	55.1	56.2	59.7	62.0
32.5°	37.8	39.0	40.1	41.3	42.5	43.6	44.8	47.0	49.3	51.6	53.9
35°	32.2	32.2	33.3	34.4	35.5	37.8	39.0	40.1	42.5	44.8	45.9
37.5°	26.5	27.6	28.7	29.9	31.0	32.2	33.3	34.4	35.5	37.8	40.1
40°	21.8	23.0	24.0	25.3	25.3	27.6	27.6	29.9	31.0	33.3	35.5
42.5°	18.4	19.5	20.7	21.8	21.8	23.0	24.0	25.3	26.5	28.7	31.0
45°	14.9	16.1	17.2	18.4	18.4	19.5	20.7	21.8	23.0	25.3	26.5
47.5°	12.7	13.8	14.9	16.1	16.1	17.2	18.4	19.5	19.5	21.8	23.0
50°	10.4	11.5	12.7	13.8	13.8	14.9	16.1	17.2	17.2	18.4	19.5
52.5°	8.0	9.2	11.5	11.5	12.7	13.8	13.8	14.9	14.9	16.1	17.2
55°	8.0	9.2	10.4	10.4	11.5	12.7	12.7	13.8	13.8	13.8	14.9
57.5°	6.9	8.0	9.2	10.4	10.4	11.5	11.5	11.5	11.5	12.7	12.7
60°	6.9	8.0	8.0	9.2	9.2	10.4	10.4	10.4	10.4	11.5	11.5
62.5°	6.9	6.9	8.0	8.0	9.2	9.2	9.2	10.4	10.4	10.4	10.4
65°	5.7	6.9	8.0	8.0	8.0	9.2	9.2	9.2	9.2	9.2	9.2
67.5°	5.7	6.9	6.9	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
70°	5.7	5.7	6.9	6.9	6.9	8.0	8.0	8.0	6.9	8.0	6.9
72.5°	4.6	5.7	5.7	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
75°	4.6	5.7	5.7	5.7	5.7	6.9	6.9	5.7	5.7	5.7	5.7
77.5°	4.6	4.6	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	4.6
80°	4.6	4.6	4.6	4.6	5.7	5.7	4.6	4.6	4.6	4.6	4.6
82.5°	3.4	4.6	4.6	4.6	4.6	4.6	4.6	4.6	3.4	3.4	3.4
85°	3.4	3.4	4.6	4.6	4.6	4.6	3.4	3.4	3.4	3.4	2.3
87.5°	3.4	3.4	3.4	4.6	3.4	3.4	3.4	3.4	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212272

CATALOG NUMBER: LDSQA4A25940D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	225.0	225.0	225.0	225.0	225.0	225.0	225.0	225.0
2.5°	194.0	192.8	194.0	192.8	192.8	194.0	190.5	192.8
5°	175.7	173.2	174.5	173.2	172.1	173.2	171.0	173.2
7.5°	159.6	158.4	158.4	158.4	157.3	158.4	156.1	158.4
10°	145.8	144.6	144.6	144.6	144.6	145.8	143.5	145.8
12.5°	132.0	132.0	133.1	132.0	133.1	134.3	132.0	134.3
15°	120.5	121.6	122.8	122.8	123.9	125.1	123.9	126.3
17.5°	111.3	112.5	114.8	114.8	115.9	118.2	117.0	119.3
20°	102.1	103.2	105.5	105.5	106.7	109.1	108.0	110.2
22.5°	91.9	94.2	95.3	96.5	97.6	99.8	98.7	101.0
25°	81.5	84.9	86.1	87.2	88.4	90.6	90.6	93.0
27.5°	73.4	75.8	76.9	78.1	80.4	82.7	82.7	83.8
30°	64.3	66.6	68.9	70.0	71.1	73.4	73.4	75.8
32.5°	56.2	58.6	59.7	60.8	63.1	65.4	66.6	67.7
35°	48.2	51.6	52.8	55.1	56.2	59.7	59.7	60.8
37.5°	42.5	44.8	47.0	48.2	50.5	52.8	52.8	55.1
40°	37.8	40.1	41.3	42.5	44.8	47.0	47.0	48.2
42.5°	32.2	35.5	36.7	37.8	39.0	41.3	42.5	43.6
45°	28.7	29.9	31.0	32.2	33.3	35.5	35.5	36.7
47.5°	24.0	25.3	26.5	27.6	28.7	29.9	31.0	32.2
50°	20.7	21.8	23.0	23.0	24.0	26.5	26.5	27.6
52.5°	17.2	18.4	19.5	19.5	20.7	23.0	23.0	24.0
55°	14.9	16.1	17.2	17.2	18.4	19.5	19.5	20.7
57.5°	13.8	13.8	14.9	14.9	16.1	16.1	17.2	17.2
60°	11.5	12.7	12.7	12.7	13.8	13.8	13.8	13.8
62.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	11.5
65°	9.2	9.2	9.2	9.2	9.2	9.2	8.0	9.2
67.5°	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.9
70°	6.9	6.9	6.9	6.9	6.9	5.7	5.7	5.7
72.5°	5.7	5.7	5.7	5.7	5.7	4.6	4.6	4.6
75°	5.7	5.7	4.6	4.6	4.6	4.6	4.6	3.4
77.5°	4.6	4.6	4.6	4.6	3.4	3.4	3.4	3.4
80°	3.4	3.4	3.4	3.4	3.4	3.4	2.3	2.3
82.5°	3.4	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	2.3	2.3	2.3	2.3	1.1	1.1	1.1	1.1
87.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)