

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212280

Luminaire Tested: **LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2286.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212280

CATALOG NUMBER: LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212280

CATALOG NUMBER: LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	106	104	110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	85
3	99	91	86	81	97	90	85	80		87	83	79		85	81	78		82	79	76
4	93	84	77	72	91	83	76	72		80	75	71		78	74	70		76	72	69
5	87	77	70	65	85	76	69	64		74	68	64		72	67	63		70	66	63
6	81	70	63	58	79	69	63	58		68	62	57		66	61	57		65	60	57
7	76	65	57	52	74	64	57	52		62	56	52		61	56	52		60	55	51
8	71	59	52	47	69	59	52	47		58	51	47		57	51	47		55	50	47
9	66	55	48	43	65	54	48	43		53	47	43		52	47	43		51	46	42
10	62	51	44	39	61	50	44	39		49	43	39		48	43	39		48	42	39

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	24684	24684	24684
5°	55255	23222	16629
10°	216670	20323	13093
15°	470353	16468	11393
20°	701680	12186	10289
25°	912661	8594	8957
30°	1020977	5772	7830
35°	918821	3394	6646
40°	749843	2327	5805
45°	430544	1576	4713
50°	125934	1206	3994
55°	14542	963	3293
60°	3119	1104	2674
65°	1054	1054	1834
70°	963	1303	1303
75°	861	1722	1273
80°	0	2566	1283
85°	0	5113	1223



TEST NUMBER: P1212280

CATALOG NUMBER: LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.5	1.6
10°-20°	313.0	13.7
20°-30°	746.5	32.7
30°-40°	787.9	34.5
40°-50°	357.3	15.6
50°-60°	31.3	1.4
60°-70°	6.6	0.3
70°-80°	4.3	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1096.0	47.9
0°-40°	1883.9	82.4
0°-60°	2272.5	99.4
0°-90°	2286.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2286.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	255	255	255	255	255	
5°	568	417	239	184	171	102
15°	4690	1649	164	112	114	1364
25°	8538	2270	80	69	84	3879
35°	7769	627	29	39	56	4798
45°	3143	88	12	22	34	2491
55°	86	14	6	13	20	172
65°	5	5	5	9	8	6
75°	2	2	5	6	3	2
85°	0	2	5	3	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212280

CATALOG NUMBER: LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8
2.5°	378.7	381.0	370.8	371.9	361.6	366.2	362.7	353.5	346.6	335.1	330.5
5°	568.2	571.6	548.6	541.8	517.6	517.6	507.4	483.2	461.4	434.9	416.6
7.5°	1038.8	1052.5	983.7	932.0	856.2	837.9	802.3	719.6	651.9	583.0	531.4
10°	2202.6	2177.3	2035.0	1918.0	1722.9	1650.4	1554.1	1316.5	1098.5	881.5	711.6
12.5°	3473.2	3554.6	3280.3	3185.1	2876.4	2810.9	2605.4	2217.5	1849.1	1465.7	1125.9
15°	4689.8	4713.9	4474.0	4319.1	3942.7	3857.7	3605.2	3149.4	2653.7	2118.8	1649.4
17.5°	5666.6	5763.0	5410.6	5244.2	4755.3	4618.7	4321.4	3767.0	3214.9	2630.7	2074.0
20°	6806.3	6831.5	6413.8	6093.5	5454.2	5246.5	4890.7	4203.2	3545.5	2878.6	2303.6
22.5°	7842.8	7837.0	7299.9	6847.6	6038.5	5790.5	5350.9	4536.0	3771.6	2988.8	2325.3
25°	8538.3	8556.6	7981.6	7446.8	6453.9	6118.8	5623.0	4709.3	3848.5	2985.4	2270.3
27.5°	8909.0	8890.7	8274.3	7702.7	6606.6	6231.3	5693.0	4715.1	3778.5	2868.2	2105.0
30°	9127.1	8881.5	8223.8	7630.4	6503.3	6117.7	5570.2	4533.7	3545.5	2606.5	1810.0
32.5°	8544.0	8448.8	7876.1	7246.0	6147.5	5765.3	5224.7	4148.1	3175.9	2206.0	1297.0
35°	7769.3	7772.8	7213.8	6625.0	5589.7	5256.8	4699.1	3678.7	2724.9	1533.4	626.7
37.5°	6956.7	6968.2	6436.7	5889.2	4967.6	4617.5	4095.2	3143.7	1960.4	780.4	377.6
40°	5929.4	5953.5	5495.6	5055.9	4205.5	3868.0	3402.0	2379.4	1096.2	436.2	256.0
42.5°	4844.8	4874.6	4468.3	4078.1	3354.9	3077.1	2664.0	1473.8	544.0	282.4	150.4
45°	3142.6	3228.7	2926.9	2762.7	2343.7	2178.5	1738.9	751.8	328.3	165.3	88.4
47.5°	1798.5	1799.7	1544.9	1237.3	1014.7	882.7	689.8	342.1	191.7	93.0	53.9
50°	835.6	856.2	678.3	564.7	404.0	342.1	281.2	184.8	101.0	53.9	33.3
52.5°	243.3	257.1	232.9	211.2	179.0	159.6	136.6	90.7	52.8	32.2	20.7
55°	86.1	91.9	86.1	80.4	72.3	65.4	58.6	43.6	29.9	19.5	13.8
57.5°	35.5	36.7	35.5	34.4	32.2	32.2	28.7	24.0	18.4	12.7	9.2
60°	16.1	17.2	16.1	17.2	16.1	16.1	16.1	17.2	11.5	8.0	6.9
62.5°	6.9	8.0	8.0	8.0	8.0	9.2	9.2	8.0	6.9	5.7	4.6
65°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
67.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
70°	3.4	3.4	3.4	3.4	3.4	3.4	2.3	2.3	3.4	3.4	3.4
72.5°	3.4	3.4	3.4	3.4	2.3	2.3	2.3	2.3	2.3	3.4	3.4
75°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3
80°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.3	2.3	2.3
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.3	2.3	2.3
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212280

CATALOG NUMBER: LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8
2.5°	324.8	314.5	298.4	288.1	283.5	276.6	272.1	260.5	256.0	246.7	243.3
5°	399.4	378.7	354.7	335.1	322.5	308.8	288.1	265.1	253.6	238.8	230.7
7.5°	484.3	439.7	397.1	362.7	346.6	328.3	301.8	266.3	244.5	225.0	213.5
10°	592.2	500.4	433.8	378.7	354.7	330.5	298.4	257.1	229.6	206.6	194.0
12.5°	844.7	603.7	467.1	388.0	357.0	327.1	286.9	244.5	212.4	185.9	172.1
15°	1215.5	843.6	556.7	396.0	348.9	312.2	266.3	223.9	190.5	164.2	150.4
17.5°	1543.8	1075.4	680.6	425.9	346.6	295.0	241.1	197.4	165.3	140.1	128.6
20°	1722.9	1197.1	763.3	444.2	336.3	268.6	212.4	171.0	140.1	118.2	108.0
22.5°	1726.2	1190.2	733.4	404.0	296.2	232.9	183.6	144.6	117.0	97.6	89.5
25°	1623.0	1061.7	611.8	317.9	242.2	197.4	153.8	120.5	95.3	80.4	73.4
27.5°	1430.1	863.1	449.9	229.6	189.4	159.6	124.0	96.5	74.6	65.4	59.7
30°	1124.8	562.4	262.8	171.0	146.9	122.8	94.2	67.7	58.6	51.6	47.0
32.5°	603.7	273.2	183.6	126.3	104.4	86.1	62.0	49.3	42.5	37.8	36.7
35°	315.6	199.7	122.8	80.4	66.6	56.2	42.5	34.4	31.0	28.7	28.7
37.5°	226.2	125.1	78.1	51.6	43.6	35.5	29.9	25.3	23.0	23.0	23.0
40°	134.3	76.9	47.0	33.3	28.7	25.3	21.8	18.4	18.4	18.4	18.4
42.5°	81.5	48.2	33.3	23.0	20.7	18.4	16.1	14.9	13.8	13.8	14.9
45°	50.5	33.3	21.8	17.2	16.1	13.8	12.7	11.5	11.5	11.5	12.7
47.5°	32.2	24.0	16.1	11.5	10.4	9.2	8.0	8.0	9.2	9.2	10.4
50°	24.0	14.9	10.4	8.0	6.9	6.9	5.7	6.9	6.9	8.0	9.2
52.5°	13.8	9.2	6.9	5.7	5.7	4.6	4.6	5.7	5.7	6.9	8.0
55°	9.2	6.9	5.7	4.6	4.6	4.6	4.6	4.6	5.7	5.7	6.9
57.5°	6.9	5.7	4.6	4.6	4.6	3.4	4.6	4.6	4.6	5.7	6.9
60°	5.7	4.6	4.6	4.6	4.6	3.4	3.4	4.6	4.6	5.7	5.7
62.5°	4.6	4.6	4.6	4.6	4.6	3.4	4.6	4.6	4.6	4.6	5.7
65°	3.4	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	5.7
67.5°	3.4	3.4	4.6	4.6	4.6	3.4	4.6	4.6	4.6	4.6	5.7
70°	3.4	3.4	3.4	4.6	4.6	3.4	4.6	4.6	4.6	4.6	4.6
72.5°	3.4	3.4	3.4	4.6	4.6	3.4	4.6	4.6	4.6	4.6	4.6
75°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6
77.5°	3.4	3.4	3.4	3.4	4.6	3.4	4.6	4.6	4.6	4.6	4.6
80°	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6	4.6
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6
85°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6
87.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212280

CATALOG NUMBER: LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8
2.5°	234.1	230.7	223.9	222.7	221.5	216.9	213.5	210.1	210.1	206.6	204.3
5°	216.9	211.2	203.1	199.7	198.6	192.8	188.2	184.8	183.6	180.2	176.7
7.5°	198.6	191.7	182.5	179.0	177.9	172.1	167.5	164.2	161.9	158.4	156.1
10°	179.0	171.0	163.0	159.6	158.4	152.7	149.2	145.8	143.5	141.2	138.9
12.5°	158.4	151.5	143.5	140.1	138.9	134.3	130.8	128.6	127.4	125.1	124.0
15°	137.7	130.8	124.0	121.6	120.5	117.0	114.8	113.6	112.5	112.5	111.3
17.5°	117.0	111.3	105.5	104.4	103.2	101.0	99.8	98.7	99.8	99.8	101.0
20°	97.6	93.0	88.4	88.4	87.2	86.1	86.1	86.1	88.4	89.5	91.9
22.5°	80.4	76.9	73.4	73.4	73.4	73.4	73.4	75.8	78.1	80.4	81.5
25°	66.6	63.1	62.0	62.0	62.0	63.1	64.3	66.6	68.9	71.1	73.4
27.5°	53.9	51.6	51.6	51.6	52.8	53.9	55.1	57.3	60.8	63.1	65.4
30°	43.6	42.5	42.5	43.6	44.8	45.9	48.2	50.5	52.8	55.1	57.3
32.5°	34.4	35.5	35.5	36.7	37.8	39.0	41.4	43.6	45.9	48.2	49.3
35°	28.7	28.7	29.9	31.0	32.2	33.3	35.5	37.8	39.0	41.4	43.6
37.5°	23.0	24.0	25.3	26.5	27.6	28.7	29.9	32.2	33.3	35.5	37.8
40°	19.5	20.7	21.8	23.0	23.0	25.3	25.3	27.6	28.7	31.0	33.3
42.5°	16.1	17.2	18.4	19.5	19.5	20.7	21.8	23.0	25.3	26.5	28.7
45°	12.7	13.8	14.9	16.1	17.2	18.4	18.4	20.7	21.8	23.0	25.3
47.5°	11.5	12.7	13.8	13.8	14.9	16.1	16.1	18.4	19.5	20.7	21.8
50°	9.2	10.4	11.5	12.7	12.7	13.8	14.9	16.1	17.2	18.4	18.4
52.5°	8.0	9.2	10.4	10.4	11.5	12.7	12.7	13.8	14.9	14.9	16.1
55°	8.0	9.2	9.2	10.4	10.4	11.5	11.5	12.7	12.7	13.8	13.8
57.5°	6.9	8.0	8.0	9.2	9.2	10.4	10.4	11.5	11.5	11.5	12.7
60°	6.9	6.9	8.0	8.0	9.2	9.2	9.2	10.4	10.4	10.4	11.5
62.5°	5.7	6.9	6.9	8.0	8.0	8.0	9.2	9.2	9.2	10.4	10.4
65°	5.7	6.9	6.9	8.0	8.0	8.0	8.0	8.0	9.2	9.2	9.2
67.5°	5.7	5.7	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.0	8.0
70°	5.7	5.7	5.7	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
72.5°	4.6	5.7	5.7	5.7	5.7	6.9	6.9	6.9	6.9	6.9	5.7
75°	4.6	4.6	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
77.5°	4.6	4.6	4.6	5.7	5.7	5.7	5.7	5.7	5.7	4.6	4.6
80°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	3.4
82.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	3.4	3.4	3.4
85°	4.6	3.4	4.6	4.6	4.6	3.4	3.4	3.4	3.4	3.4	2.3
87.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212280

CATALOG NUMBER: LDSQA4A25940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	254.8	254.8	254.8	254.8	254.8	254.8	254.8	254.8
2.5°	202.0	199.7	200.8	200.8	198.6	197.4	197.4	198.6
5°	174.5	172.1	173.4	173.4	171.0	169.8	169.8	171.0
7.5°	153.8	151.5	152.7	152.7	150.4	150.4	150.4	150.4
10°	137.7	136.6	136.6	136.6	134.3	135.4	134.3	133.1
12.5°	122.8	122.8	122.8	122.8	121.6	122.8	121.6	121.6
15°	111.3	111.3	112.5	112.5	112.5	113.6	113.6	113.6
17.5°	102.1	103.2	104.4	105.5	105.5	106.7	106.7	106.7
20°	93.0	95.3	96.5	97.6	97.6	99.8	98.7	99.8
22.5°	83.8	86.1	87.2	88.4	89.5	90.7	90.7	91.9
25°	75.8	78.1	79.2	80.4	81.5	83.8	83.8	83.8
27.5°	67.7	70.0	71.1	73.4	74.6	76.9	76.9	76.9
30°	59.7	62.0	63.1	64.3	66.6	68.9	68.9	70.0
32.5°	51.6	55.1	56.2	57.3	59.7	62.0	63.1	63.1
35°	45.9	48.2	49.3	51.6	52.8	56.2	56.2	56.2
37.5°	40.1	42.5	44.8	45.9	47.0	49.3	50.5	51.6
40°	35.5	37.8	39.0	40.1	42.5	44.8	45.9	45.9
42.5°	31.0	33.3	34.4	35.5	36.7	39.0	39.0	39.0
45°	27.6	28.7	29.9	31.0	32.2	33.3	34.4	34.4
47.5°	23.0	25.3	25.3	26.5	27.6	29.9	29.9	31.0
50°	19.5	21.8	21.8	23.0	24.0	25.3	26.5	26.5
52.5°	17.2	18.4	19.5	19.5	20.7	21.8	23.0	23.0
55°	14.9	16.1	16.1	17.2	17.2	18.4	19.5	19.5
57.5°	12.7	13.8	14.9	14.9	14.9	16.1	16.1	17.2
60°	11.5	12.7	12.7	12.7	12.7	13.8	13.8	13.8
62.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
65°	9.2	9.2	9.2	9.2	8.0	8.0	8.0	8.0
67.5°	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.9
70°	6.9	6.9	6.9	6.9	5.7	5.7	5.7	4.6
72.5°	5.7	5.7	5.7	5.7	5.7	4.6	4.6	4.6
75°	5.7	4.6	4.6	4.6	4.6	4.6	3.4	3.4
77.5°	4.6	4.6	4.6	3.4	3.4	3.4	3.4	3.4
80°	3.4	3.4	3.4	3.4	3.4	2.3	2.3	2.3
82.5°	3.4	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	2.3	2.3	2.3	2.3	1.1	1.1	1.1	1.1
87.5°	2.3	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)