

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212294

Luminaire Tested: **LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212294
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2381.6 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212294

CATALOG NUMBER: LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212294

CATALOG NUMBER: LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	106	104	110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	85
3	99	91	86	81	97	90	85	80		87	83	79		85	81	78		82	79	76
4	93	84	77	72	91	83	76	72		80	75	71		78	74	70		76	72	69
5	87	77	70	65	85	76	69	64		74	68	64		72	67	63		70	66	63
6	81	70	63	58	79	69	63	58		68	62	57		66	61	57		65	60	57
7	76	65	57	52	74	64	57	52		62	56	52		61	56	52		60	55	51
8	71	59	52	47	69	59	52	47		58	51	47		57	51	47		55	50	47
9	66	55	48	43	65	54	48	43		53	47	43		52	47	43		51	46	42
10	62	51	44	39	61	50	44	39		49	43	39		48	43	39		48	42	39

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	25711	25711	25711
5°	57560	24185	17329
10°	225739	21179	13654
15°	490041	17150	11875
20°	731051	12701	10732
25°	950863	8947	9332
30°	1063719	6018	8166
35°	957280	3536	6930
40°	781231	2415	6045
45°	448574	1644	4905
50°	131209	1266	4145
55°	15150	1013	3429
60°	3236	1163	2790
65°	1077	1077	1926
70°	1020	1331	1331
75°	898	1759	1347
80°	0	2622	1339
85°	0	5224	1334

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212294

CATALOG NUMBER: LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.0	1.6
10°-20°	326.1	13.7
20°-30°	777.8	32.7
30°-40°	820.8	34.5
40°-50°	372.3	15.6
50°-60°	32.6	1.4
60°-70°	6.8	0.3
70°-80°	4.5	0.2
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1141.9	47.9
0°-40°	1962.7	82.4
0°-60°	2367.6	99.4
0°-90°	2381.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2381.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	265	265	265	265	265	
5°	592	434	249	191	178	106
15°	4886	1718	171	117	118	1422
25°	8896	2365	84	72	87	4041
35°	8094	653	30	41	59	4999
45°	3274	92	12	23	36	2596
55°	90	14	6	13	20	179
65°	5	5	5	10	8	6
75°	2	2	5	6	4	2
85°	0	2	5	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212294

CATALOG NUMBER: LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4
2.5°	394.6	397.0	386.2	387.5	376.6	381.5	377.9	368.3	361.1	349.2	344.4
5°	591.9	595.5	571.6	564.4	539.3	539.3	528.5	503.4	480.7	453.2	434.0
7.5°	1082.2	1096.6	1024.8	971.0	892.1	872.9	835.9	749.8	679.2	607.5	553.7
10°	2294.8	2268.5	2120.2	1998.2	1794.9	1719.6	1619.2	1371.6	1144.4	918.4	741.4
12.5°	3618.6	3703.5	3417.7	3318.4	2996.8	2928.5	2714.5	2310.3	1926.4	1527.1	1173.1
15°	4886.1	4911.2	4661.2	4499.9	4107.7	4019.2	3756.0	3281.3	2764.8	2207.5	1718.4
17.5°	5903.8	6004.3	5637.1	5463.7	4954.3	4812.0	4502.3	3924.7	3349.4	2740.8	2160.8
20°	7091.2	7117.5	6682.3	6348.6	5682.5	5466.0	5095.4	4379.1	3693.9	2999.1	2400.0
22.5°	8171.0	8165.0	7605.4	7134.3	6291.2	6032.8	5574.9	4725.9	3929.5	3113.9	2422.7
25°	8895.7	8914.8	8315.7	7758.5	6724.1	6374.9	5858.3	4906.5	4009.6	3110.3	2365.3
27.5°	9281.9	9262.8	8620.7	8025.1	6883.2	6492.1	5931.3	4912.4	3936.6	2988.4	2193.1
30°	9509.2	9253.2	8568.0	7949.8	6775.5	6373.7	5803.3	4723.5	3693.9	2715.7	1885.9
32.5°	8901.7	8802.4	8205.7	7549.2	6404.8	6006.6	5443.3	4321.7	3308.9	2298.3	1351.3
35°	8094.5	8098.0	7515.7	6902.3	5823.7	5476.9	4895.7	3832.6	2838.9	1597.6	652.9
37.5°	7247.8	7259.8	6706.1	6135.8	5175.5	4810.7	4266.7	3275.3	2042.5	813.1	393.5
40°	6177.6	6202.7	5725.6	5267.6	4381.5	4029.9	3544.4	2478.9	1142.0	454.4	266.7
42.5°	5047.6	5078.7	4655.3	4248.7	3495.4	3206.0	2775.5	1535.4	566.8	294.1	156.6
45°	3274.2	3363.8	3049.3	2878.3	2441.8	2269.6	1811.6	783.3	342.1	172.2	92.1
47.5°	1873.9	1875.0	1609.6	1289.1	1057.1	919.6	718.7	356.4	199.7	96.8	56.2
50°	870.6	892.1	706.7	588.4	420.9	356.4	293.0	192.6	105.2	56.2	34.7
52.5°	253.5	267.8	242.7	220.0	186.6	166.2	142.3	94.5	55.0	33.4	21.5
55°	89.7	95.7	89.7	83.7	75.4	68.1	61.0	45.4	31.1	20.3	14.4
57.5°	37.1	38.3	37.1	35.8	33.4	33.4	29.9	25.1	19.1	13.1	9.6
60°	16.7	18.0	16.7	18.0	16.7	16.7	16.7	18.0	12.0	8.4	7.1
62.5°	7.1	8.4	8.4	8.4	8.4	9.6	9.6	8.4	7.1	6.0	4.7
65°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
70°	3.6	3.6	3.6	3.6	3.6	3.6	2.4	2.4	3.6	3.6	3.6
72.5°	3.6	3.6	3.6	3.6	2.4	2.4	2.4	2.4	2.4	3.6	3.6
75°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
77.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.4	2.4	2.4
80°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.4	2.4	2.4
82.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.4	2.4	2.4
85°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.4	2.4	2.4
87.5°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212294

CATALOG NUMBER: LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4
2.5°	338.4	327.7	310.9	300.1	295.4	288.2	283.4	271.4	266.7	257.1	253.5
5°	416.2	394.6	369.5	349.2	336.1	321.7	300.1	276.3	264.3	248.7	240.4
7.5°	504.7	458.0	413.8	377.9	361.1	342.1	314.5	277.4	254.7	234.4	222.4
10°	617.1	521.4	452.0	394.6	369.5	344.4	310.9	267.8	239.1	215.3	202.0
12.5°	880.2	629.0	486.7	404.2	371.9	340.8	299.0	254.7	221.3	193.7	179.3
15°	1266.4	878.9	579.9	412.6	363.5	325.2	277.4	233.2	198.5	171.0	156.6
17.5°	1608.3	1120.5	709.1	443.6	361.1	307.4	251.1	205.7	172.2	145.9	133.9
20°	1794.9	1247.3	795.2	462.7	350.4	279.8	221.3	178.2	145.9	123.2	112.4
22.5°	1798.5	1240.1	764.1	420.9	308.5	242.7	191.3	150.6	121.9	101.7	93.2
25°	1690.9	1106.2	637.3	331.2	252.3	205.7	160.2	125.5	99.2	83.7	76.5
27.5°	1490.0	899.3	468.7	239.1	197.3	166.2	129.2	100.5	77.7	68.1	62.1
30°	1171.9	585.9	273.8	178.2	153.1	127.9	98.1	70.5	61.0	53.8	49.0
32.5°	629.0	284.6	191.3	131.5	108.8	89.7	64.5	51.4	44.3	39.4	38.3
35°	328.8	208.0	127.9	83.7	69.4	58.6	44.3	35.8	32.3	29.9	29.9
37.5°	235.6	130.3	81.4	53.8	45.4	37.1	31.1	26.3	24.0	24.0	24.0
40°	139.9	80.1	49.0	34.7	29.9	26.3	22.7	19.1	19.1	19.1	19.1
42.5°	84.9	50.2	34.7	24.0	21.5	19.1	16.7	15.6	14.4	14.4	15.6
45°	52.7	34.7	22.7	18.0	16.7	14.4	13.1	12.0	12.0	12.0	13.1
47.5°	33.4	25.1	16.7	12.0	10.7	9.6	8.4	8.4	9.6	9.6	10.7
50°	25.1	15.6	10.7	8.4	7.1	7.1	6.0	7.1	7.1	8.4	9.6
52.5°	14.4	9.6	7.1	6.0	6.0	4.7	4.7	6.0	6.0	7.1	8.4
55°	9.6	7.1	6.0	4.7	4.7	4.7	4.7	4.7	6.0	6.0	7.1
57.5°	7.1	6.0	4.7	4.7	4.7	3.6	4.7	4.7	4.7	6.0	7.1
60°	6.0	4.7	4.7	4.7	4.7	3.6	3.6	4.7	4.7	6.0	6.0
62.5°	4.7	4.7	4.7	4.7	4.7	3.6	4.7	4.7	4.7	4.7	6.0
65°	3.6	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.0
67.5°	3.6	3.6	4.7	4.7	4.7	3.6	4.7	4.7	4.7	4.7	6.0
70°	3.6	3.6	3.6	4.7	4.7	3.6	4.7	4.7	4.7	4.7	4.7
72.5°	3.6	3.6	3.6	4.7	4.7	3.6	4.7	4.7	4.7	4.7	4.7
75°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7
77.5°	3.6	3.6	3.6	3.6	4.7	3.6	4.7	4.7	4.7	4.7	4.7
80°	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	4.7	4.7
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	4.7
85°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	4.7
87.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212294

CATALOG NUMBER: LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4
2.5°	244.0	240.4	233.2	232.0	230.7	226.0	222.4	218.9	218.9	215.3	212.9
5°	226.0	220.0	211.6	208.0	206.9	200.9	196.2	192.6	191.3	187.7	184.2
7.5°	206.9	199.7	190.2	186.6	185.3	179.3	174.6	171.0	168.6	165.0	162.6
10°	186.6	178.2	169.8	166.2	165.0	159.0	155.5	151.9	149.5	147.1	144.6
12.5°	165.0	157.9	149.5	145.9	144.6	139.9	136.3	133.9	132.8	130.3	129.2
15°	143.5	136.3	129.2	126.8	125.5	121.9	119.6	118.4	117.2	117.2	115.9
17.5°	121.9	115.9	110.1	108.8	107.6	105.2	104.1	102.8	104.1	104.1	105.2
20°	101.7	96.8	92.1	92.1	90.9	89.7	89.7	89.7	92.1	93.2	95.7
22.5°	83.7	80.1	76.5	76.5	76.5	76.5	76.5	78.9	81.4	83.7	84.9
25°	69.4	65.8	64.5	64.5	64.5	65.8	67.0	69.4	71.8	74.1	76.5
27.5°	56.2	53.8	53.8	53.8	55.0	56.2	57.4	59.8	63.4	65.8	68.1
30°	45.4	44.3	44.3	45.4	46.7	47.8	50.2	52.7	55.0	57.4	59.8
32.5°	35.8	37.1	37.1	38.3	39.4	40.7	43.1	45.4	47.8	50.2	51.4
35°	29.9	29.9	31.1	32.3	33.4	34.7	37.1	39.4	40.7	43.1	45.4
37.5°	24.0	25.1	26.3	27.5	28.7	29.9	31.1	33.4	34.7	37.1	39.4
40°	20.3	21.5	22.7	24.0	24.0	26.3	26.3	28.7	29.9	32.3	34.7
42.5°	16.7	18.0	19.1	20.3	20.3	21.5	22.7	24.0	26.3	27.5	29.9
45°	13.1	14.4	15.6	16.7	18.0	19.1	19.1	21.5	22.7	24.0	26.3
47.5°	12.0	13.1	14.4	14.4	15.6	16.7	16.7	19.1	20.3	21.5	22.7
50°	9.6	10.7	12.0	13.1	13.1	14.4	15.6	16.7	18.0	19.1	19.1
52.5°	8.4	9.6	10.7	10.7	12.0	13.1	13.1	14.4	15.6	15.6	16.7
55°	8.4	9.6	9.6	10.7	10.7	12.0	12.0	13.1	13.1	14.4	14.4
57.5°	7.1	8.4	8.4	9.6	9.6	10.7	10.7	12.0	12.0	12.0	13.1
60°	7.1	7.1	8.4	8.4	9.6	9.6	9.6	10.7	10.7	10.7	12.0
62.5°	6.0	7.1	7.1	8.4	8.4	8.4	9.6	9.6	9.6	10.7	10.7
65°	6.0	7.1	7.1	8.4	8.4	8.4	8.4	8.4	9.6	9.6	9.6
67.5°	6.0	6.0	7.1	7.1	7.1	7.1	8.4	8.4	8.4	8.4	8.4
70°	6.0	6.0	6.0	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
72.5°	4.7	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1	7.1	6.0
75°	4.7	4.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
77.5°	4.7	4.7	4.7	6.0	6.0	6.0	6.0	6.0	6.0	4.7	4.7
80°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.6
82.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.6	3.6	3.6
85°	4.7	3.6	4.7	4.7	4.7	3.6	3.6	3.6	3.6	3.6	2.4
87.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212294

CATALOG NUMBER: LDSQA4A30927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	265.4	265.4	265.4	265.4	265.4	265.4	265.4	265.4
2.5°	210.5	208.0	209.3	209.3	206.9	205.7	205.7	206.9
5°	181.8	179.3	180.6	180.6	178.2	177.0	177.0	178.2
7.5°	160.2	157.9	159.0	159.0	156.6	156.6	156.6	156.6
10°	143.5	142.3	142.3	142.3	139.9	141.1	139.9	138.8
12.5°	127.9	127.9	127.9	127.9	126.8	127.9	126.8	126.8
15°	115.9	115.9	117.2	117.2	117.2	118.4	118.4	118.4
17.5°	106.4	107.6	108.8	110.1	110.1	111.2	111.2	111.2
20°	96.8	99.2	100.5	101.7	101.7	104.1	102.8	104.1
22.5°	87.3	89.7	90.9	92.1	93.2	94.5	94.5	95.7
25°	78.9	81.4	82.5	83.7	84.9	87.3	87.3	87.3
27.5°	70.5	73.0	74.1	76.5	77.7	80.1	80.1	80.1
30°	62.1	64.5	65.8	67.0	69.4	71.8	71.8	73.0
32.5°	53.8	57.4	58.6	59.8	62.1	64.5	65.8	65.8
35°	47.8	50.2	51.4	53.8	55.0	58.6	58.6	58.6
37.5°	41.8	44.3	46.7	47.8	49.0	51.4	52.7	53.8
40°	37.1	39.4	40.7	41.8	44.3	46.7	47.8	47.8
42.5°	32.3	34.7	35.8	37.1	38.3	40.7	40.7	40.7
45°	28.7	29.9	31.1	32.3	33.4	34.7	35.8	35.8
47.5°	24.0	26.3	26.3	27.5	28.7	31.1	31.1	32.3
50°	20.3	22.7	22.7	24.0	25.1	26.3	27.5	27.5
52.5°	18.0	19.1	20.3	20.3	21.5	22.7	24.0	24.0
55°	15.6	16.7	16.7	18.0	18.0	19.1	20.3	20.3
57.5°	13.1	14.4	15.6	15.6	15.6	16.7	16.7	18.0
60°	12.0	13.1	13.1	13.1	13.1	14.4	14.4	14.4
62.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
65°	9.6	9.6	9.6	9.6	8.4	8.4	8.4	8.4
67.5°	8.4	8.4	8.4	8.4	7.1	7.1	7.1	7.1
70°	7.1	7.1	7.1	7.1	6.0	6.0	6.0	4.7
72.5°	6.0	6.0	6.0	6.0	6.0	4.7	4.7	4.7
75°	6.0	4.7	4.7	4.7	4.7	4.7	3.6	3.6
77.5°	4.7	4.7	4.7	3.6	3.6	3.6	3.6	3.6
80°	3.6	3.6	3.6	3.6	3.6	2.4	2.4	2.4
82.5°	3.6	2.4	2.4	2.4	2.4	2.4	2.4	2.4
85°	2.4	2.4	2.4	2.4	1.2	1.2	1.2	1.2
87.5°	2.4	1.2	1.2	1.2	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)