

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212298

Luminaire Tested: **LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212298
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2427.1 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212298

CATALOG NUMBER: LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212298

CATALOG NUMBER: LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	29072	29072	29072
5°	68140	27443	19187
10°	269229	24110	15995
15°	498255	19316	14031
20°	638876	14052	12701
25°	764404	9962	11245
30°	812801	6544	9900
35°	833010	3950	8621
40°	762540	2567	7398
45°	550230	1795	6069
50°	240219	1447	5034
55°	16569	1199	4239
60°	3023	1163	3488
65°	1077	1077	2453
70°	1020	1331	1699
75°	898	1759	1759
80°	0	2622	2008
85°	0	5224	1334

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212298

CATALOG NUMBER: LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.7	1.8
10°-20°	343.6	14.2
20°-30°	719.2	29.6
30°-40°	800.6	33.0
40°-50°	459.6	18.9
50°-60°	45.9	1.9
60°-70°	7.2	0.3
70°-80°	4.5	0.2
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1106.5	45.6
0°-40°	1907.1	78.6
0°-60°	2412.6	99.4
0°-90°	2427.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2427.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	300	300	300	300	300	
5°	701	483	282	206	197	128
15°	4968	1984	193	135	140	1404
25°	7151	2730	93	82	105	3238
35°	7044	833	33	48	73	4301
45°	4016	100	13	26	44	3066
55°	98	14	7	16	25	293
65°	5	4	5	10	11	6
75°	2	2	5	6	5	2
85°	0	2	5	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212298

CATALOG NUMBER: LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	448.4	438.8	429.3	423.3	417.3	425.7	419.7	417.3	400.6	392.2	385.0
5°	700.7	682.7	656.4	634.9	613.4	618.1	601.4	581.0	539.2	509.4	483.1
7.5°	1352.3	1308.1	1226.7	1147.9	1069.0	1054.6	1002.0	911.1	793.9	705.5	629.0
10°	2736.9	2603.0	2453.6	2292.1	2103.2	2050.6	1920.2	1674.0	1404.9	1097.6	875.2
12.5°	4040.2	3979.2	3803.5	3594.2	3389.8	3264.2	3129.1	2722.5	2295.7	1800.7	1387.0
15°	4968.0	4931.0	4776.7	4586.6	4366.5	4285.3	4120.3	3715.0	3175.8	2583.9	1983.6
17.5°	5655.5	5592.1	5430.8	5223.9	4963.2	4893.9	4696.6	4293.7	3734.1	3139.8	2473.8
20°	6197.1	6157.7	5948.4	5699.7	5387.7	5304.0	5073.2	4653.6	4044.9	3413.6	2735.7
22.5°	6683.8	6616.8	6359.8	6063.2	5707.0	5617.2	5360.2	4899.9	4245.9	3542.8	2782.3
25°	7151.3	7049.6	6737.6	6349.0	5930.5	5808.5	5526.4	5038.6	4320.0	3553.5	2729.7
27.5°	7287.6	7236.2	6948.0	6496.0	6011.8	5874.3	5580.2	5069.6	4292.4	3455.5	2540.8
30°	7266.1	7223.1	6982.7	6510.4	5997.5	5852.8	5553.8	4974.0	4132.2	3199.6	2207.2
32.5°	7197.9	7181.2	6890.6	6386.1	5863.6	5705.7	5382.9	4736.1	3832.2	2809.9	1613.0
35°	7043.7	6978.0	6615.6	6141.0	5638.8	5465.4	5100.7	4395.2	3436.3	2045.8	833.4
37.5°	6591.7	6540.3	6254.5	5838.5	5349.4	5127.0	4742.0	3955.2	2660.4	1163.3	498.6
40°	6029.8	6004.7	5779.8	5408.1	4885.6	4634.5	4215.9	3236.7	1623.7	661.2	328.8
42.5°	5453.5	5446.3	5205.9	4817.3	4250.6	3962.5	3528.4	2183.3	863.3	399.3	190.1
45°	4016.2	4059.3	3891.9	3658.7	3225.9	3016.6	2453.6	1125.1	497.4	221.3	100.5
47.5°	2817.0	2769.2	2472.7	2065.0	1669.1	1413.3	1069.0	532.1	265.4	115.9	57.4
50°	1593.9	1602.2	1334.4	1079.7	707.8	560.8	425.7	267.8	127.9	61.0	34.7
52.5°	416.1	435.3	375.4	322.8	275.0	223.6	180.6	115.9	61.0	35.8	22.7
55°	98.1	101.6	94.5	88.5	83.7	74.1	65.8	50.2	33.4	22.7	14.4
57.5°	34.7	35.8	34.7	34.7	33.4	32.3	29.9	26.3	20.3	14.4	9.6
60°	15.6	16.7	15.6	16.7	16.7	16.7	16.7	16.7	12.0	8.4	6.0
62.5°	7.1	7.1	7.1	7.1	8.4	8.4	9.6	9.6	7.1	6.0	4.7
65°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.6
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
70°	3.6	3.6	3.6	2.4	2.4	2.4	2.4	2.4	2.4	2.4	3.6
72.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
75°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
77.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.4	2.4	2.4	2.4
80°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.4	2.4	2.4
82.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.4	2.4	2.4
85°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.4	2.4	2.4
87.5°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212298

CATALOG NUMBER: LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	371.9	370.6	357.5	347.9	343.2	335.9	327.6	315.6	302.5	290.5	285.8
5°	452.0	436.4	408.9	386.2	375.4	364.7	345.6	324.0	303.7	282.2	271.4
7.5°	556.0	510.5	456.7	414.9	397.0	379.0	351.5	321.6	294.1	265.4	249.8
10°	698.2	593.0	499.8	432.8	406.6	382.6	343.2	306.1	276.2	245.1	224.8
12.5°	998.4	737.8	545.2	441.2	406.6	375.4	327.6	284.5	251.1	218.8	199.7
15°	1438.4	996.0	644.4	449.6	398.2	358.7	303.7	257.1	221.3	192.6	174.6
17.5°	1793.5	1234.0	767.6	471.1	387.4	335.9	272.7	223.6	190.1	163.8	149.5
20°	1972.9	1334.4	823.8	474.7	361.1	300.1	235.5	188.9	159.0	136.3	124.3
22.5°	1969.3	1302.1	773.6	416.1	316.9	259.4	198.4	155.5	131.5	113.6	104.1
25°	1845.0	1152.6	645.7	332.4	255.8	215.3	161.4	125.5	106.4	93.2	84.9
27.5°	1611.7	936.2	481.8	246.3	199.7	169.8	125.5	100.5	84.9	75.4	69.4
30°	1265.0	626.6	303.7	182.9	151.9	127.9	96.8	77.7	67.0	58.5	55.0
32.5°	697.1	326.5	204.4	133.9	111.2	93.2	71.8	56.2	49.0	43.1	41.8
35°	385.0	230.7	145.9	89.7	74.1	63.4	49.0	40.7	35.8	33.4	33.4
37.5°	272.7	148.3	87.2	56.2	47.8	41.8	33.4	28.7	27.5	26.3	26.3
40°	163.8	87.2	52.7	37.1	32.3	28.7	25.1	21.5	21.5	20.3	21.5
42.5°	89.7	52.7	35.8	26.3	22.7	21.5	18.0	16.7	16.7	16.7	18.0
45°	53.8	34.7	25.1	19.1	16.7	14.4	13.1	12.0	13.1	13.1	14.4
47.5°	34.7	25.1	16.7	12.0	10.7	9.6	8.4	9.6	9.6	10.7	12.0
50°	24.0	15.6	10.7	7.1	7.1	6.0	7.1	7.1	8.4	9.6	10.7
52.5°	15.6	10.7	7.1	6.0	4.7	4.7	4.7	6.0	7.1	8.4	9.6
55°	9.6	7.1	6.0	4.7	4.7	4.7	4.7	4.7	6.0	7.1	8.4
57.5°	7.1	6.0	4.7	3.6	3.6	3.6	4.7	4.7	6.0	6.0	7.1
60°	4.7	4.7	3.6	3.6	3.6	3.6	3.6	4.7	4.7	6.0	7.1
62.5°	4.7	4.7	3.6	3.6	3.6	3.6	4.7	4.7	4.7	6.0	6.0
65°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	6.0
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	6.0
70°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	6.0
72.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7
75°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	4.7
77.5°	2.4	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	4.7
80°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	4.7
82.5°	2.4	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	4.7
85°	2.4	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7	4.7
87.5°	2.4	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.7	4.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212298

CATALOG NUMBER: LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	279.8	271.4	264.2	266.7	261.8	253.5	251.1	245.1	238.0	236.7	236.7
5°	259.4	246.3	235.5	234.4	229.6	220.0	217.6	211.6	205.7	204.4	203.3
7.5°	234.4	220.0	210.4	208.0	204.4	196.1	194.9	188.9	185.3	182.9	182.9
10°	209.3	196.1	187.7	186.6	184.1	177.0	175.7	171.0	167.4	166.2	165.0
12.5°	185.3	174.6	167.4	166.2	163.8	157.9	156.6	153.0	150.6	149.5	149.5
15°	162.6	153.0	147.0	145.9	144.6	138.7	138.7	136.3	135.1	135.1	136.3
17.5°	139.9	131.5	126.8	125.5	125.5	120.8	121.9	120.8	120.8	120.8	123.2
20°	117.2	109.9	106.4	107.6	105.2	104.1	105.2	105.2	105.2	107.6	111.2
22.5°	98.1	92.1	88.5	89.7	89.7	88.5	89.7	90.9	93.2	96.8	100.5
25°	80.1	75.4	74.1	75.4	75.4	75.4	77.7	80.1	82.5	86.1	89.7
27.5°	64.5	61.0	61.0	62.1	63.4	63.4	67.0	69.4	72.9	76.5	80.1
30°	51.4	50.2	50.2	52.7	52.7	53.8	58.5	61.0	63.4	67.0	70.5
32.5°	40.7	40.7	41.8	44.3	44.3	46.7	50.2	52.7	55.0	58.5	62.1
35°	33.4	34.7	35.8	37.1	38.3	39.4	43.1	45.4	47.8	51.4	53.8
37.5°	27.5	28.7	29.9	32.3	32.3	33.4	37.1	39.4	40.7	44.3	47.8
40°	22.7	24.0	25.1	27.5	27.5	28.7	32.3	33.4	34.7	38.3	41.8
42.5°	19.1	20.3	21.5	22.7	24.0	25.1	27.5	28.7	31.1	33.4	35.8
45°	15.6	16.7	18.0	19.1	20.3	21.5	22.7	25.1	26.3	28.7	31.1
47.5°	13.1	14.4	15.6	16.7	18.0	18.0	20.3	21.5	22.7	25.1	27.5
50°	12.0	13.1	14.4	14.4	15.6	16.7	18.0	19.1	20.3	21.5	24.0
52.5°	9.6	10.7	12.0	13.1	13.1	14.4	15.6	16.7	18.0	19.1	20.3
55°	9.6	9.6	10.7	12.0	12.0	13.1	14.4	15.6	15.6	16.7	18.0
57.5°	8.4	9.6	9.6	10.7	10.7	12.0	13.1	13.1	14.4	14.4	15.6
60°	7.1	8.4	9.6	9.6	9.6	10.7	10.7	12.0	12.0	13.1	13.1
62.5°	7.1	8.4	8.4	9.6	9.6	9.6	10.7	10.7	10.7	12.0	12.0
65°	7.1	7.1	8.4	8.4	8.4	8.4	9.6	9.6	9.6	10.7	10.7
67.5°	6.0	7.1	7.1	7.1	8.4	8.4	8.4	8.4	8.4	9.6	9.6
70°	6.0	6.0	7.1	7.1	7.1	7.1	7.1	8.4	8.4	8.4	8.4
72.5°	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1	7.1	7.1	7.1
75°	4.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
77.5°	4.7	4.7	4.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
80°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
82.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.6	3.6
85°	4.7	4.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
87.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212298

CATALOG NUMBER: LDSQA4A30927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	300.1	300.1	300.1	300.1	300.1	300.1	300.1	300.1
2.5°	232.0	229.6	228.4	232.0	227.1	229.6	228.4	229.6
5°	199.7	197.3	196.1	199.7	194.9	197.3	194.9	197.3
7.5°	179.3	178.2	177.0	179.3	175.7	178.2	177.0	178.2
10°	162.6	161.4	160.2	163.8	160.2	162.6	161.4	162.6
12.5°	148.3	148.3	147.0	149.5	147.0	149.5	148.3	149.5
15°	135.1	136.3	135.1	137.5	136.3	138.7	137.5	139.9
17.5°	124.3	125.5	125.5	129.2	127.9	131.5	130.3	131.5
20°	113.6	114.8	115.9	118.4	118.4	121.9	120.8	123.2
22.5°	102.8	105.2	105.2	108.8	108.8	112.4	112.4	113.6
25°	92.1	95.6	96.8	99.2	100.5	104.1	104.1	105.2
27.5°	83.7	86.1	87.2	90.9	92.1	95.6	95.6	98.1
30°	74.1	77.7	78.9	81.4	82.5	86.1	86.1	88.5
32.5°	65.8	68.1	70.5	72.9	74.1	77.7	77.7	80.1
35°	57.4	61.0	62.1	64.5	67.0	70.5	70.5	72.9
37.5°	50.2	53.8	55.0	57.4	59.8	63.4	63.4	65.8
40°	44.3	47.8	49.0	51.4	52.7	57.4	57.4	58.5
42.5°	39.4	41.8	43.1	45.4	46.7	49.0	49.0	51.4
45°	33.4	35.8	37.1	38.3	40.7	43.1	43.1	44.3
47.5°	28.7	31.1	32.3	33.4	34.7	37.1	37.1	39.4
50°	25.1	26.3	27.5	28.7	29.9	32.3	32.3	33.4
52.5°	21.5	22.7	24.0	25.1	26.3	27.5	28.7	29.9
55°	19.1	20.3	20.3	21.5	22.7	24.0	24.0	25.1
57.5°	16.7	18.0	18.0	18.0	19.1	20.3	20.3	21.5
60°	14.4	15.6	15.6	15.6	16.7	16.7	16.7	18.0
62.5°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1
65°	10.7	10.7	10.7	10.7	10.7	10.7	9.6	10.7
67.5°	9.6	9.6	9.6	8.4	8.4	8.4	8.4	8.4
70°	8.4	8.4	8.4	7.1	7.1	7.1	6.0	6.0
72.5°	7.1	7.1	7.1	6.0	6.0	6.0	4.7	4.7
75°	6.0	6.0	6.0	6.0	4.7	4.7	4.7	4.7
77.5°	4.7	4.7	4.7	4.7	4.7	4.7	3.6	3.6
80°	4.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	2.4	2.4	2.4	2.4
85°	2.4	2.4	2.4	2.4	2.4	2.4	1.2	1.2
87.5°	2.4	1.2	1.2	1.2	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)