

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212336

Luminaire Tested: **LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2716.4 lumens
Efficiency: N/A
Efficacy: 68.3 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212336

CATALOG NUMBER: LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212336

CATALOG NUMBER: LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	29324	29324	29324
5°	65660	27589	19760
10°	257464	24150	15562
15°	558912	19557	13540
20°	833803	14485	12227
25°	1084497	10208	10646
30°	1213212	6868	9307
35°	1091816	4033	7900
40°	891025	2757	6905
45°	511609	1877	5603
50°	149641	1432	4732
55°	17278	1149	3918
60°	3701	1318	3178
65°	1238	1238	2178
70°	1161	1530	1530
75°	1011	2021	1535
80°	0	3013	1506
85°	0	6002	1556

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212336

CATALOG NUMBER: LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	1.6
10°-20°	371.9	13.7
20°-30°	887.1	32.7
30°-40°	936.2	34.5
40°-50°	424.6	15.6
50°-60°	37.2	1.4
60°-70°	7.8	0.3
70°-80°	5.1	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1302.4	47.9
0°-40°	2238.6	82.4
0°-60°	2700.4	99.4
0°-90°	2716.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2716.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	303	303	303	303	303	
5°	675	495	284	218	203	121
15°	5573	1960	195	134	135	1621
25°	10146	2698	96	82	100	4609
35°	9232	745	34	46	67	5701
45°	3734	105	14	26	41	2961
55°	102	16	7	15	23	204
65°	5	5	5	11	10	7
75°	3	3	5	7	4	2
85°	0	3	5	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212336

CATALOG NUMBER: LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7
2.5°	450.1	452.8	440.6	441.9	429.6	435.0	431.0	420.0	411.9	398.2	392.8
5°	675.2	679.2	651.9	643.8	615.1	615.1	602.9	574.2	548.3	516.9	495.1
7.5°	1234.3	1250.7	1168.9	1107.5	1017.5	995.6	953.4	855.2	774.7	692.8	631.4
10°	2617.3	2587.2	2418.2	2279.1	2047.2	1961.2	1846.6	1564.4	1305.3	1047.5	845.6
12.5°	4127.1	4223.9	3897.9	3784.8	3417.9	3340.2	3096.0	2635.0	2197.2	1741.7	1337.9
15°	5572.8	5601.5	5316.4	5132.3	4685.0	4584.1	4283.9	3742.4	3153.3	2517.8	1959.9
17.5°	6733.6	6848.0	6429.4	6231.6	5650.6	5488.3	5135.1	4476.3	3820.2	3126.0	2464.5
20°	8087.9	8117.8	7621.4	7240.8	6481.2	6234.3	5811.5	4994.6	4213.1	3420.6	2737.3
22.5°	9319.4	9312.6	8674.3	8136.9	7175.4	6880.8	6358.4	5390.1	4481.7	3551.6	2763.2
25°	10145.9	10167.7	9484.4	8848.9	7669.1	7270.9	6681.7	5596.0	4573.1	3547.5	2697.8
27.5°	10586.5	10564.7	9832.2	9153.0	7850.6	7404.6	6764.9	5602.9	4489.9	3408.3	2501.4
30°	10845.6	10553.7	9772.2	9067.1	7727.7	7269.5	6619.0	5387.4	4213.1	3097.3	2150.8
32.5°	10152.7	10039.6	9359.0	8610.3	7305.0	6850.9	6208.4	4929.1	3773.9	2621.4	1541.2
35°	9232.1	9236.3	8572.1	7872.4	6642.1	6246.6	5583.8	4371.3	3237.9	1822.1	744.7
37.5°	8266.5	8280.2	7648.6	6998.1	5902.9	5486.9	4866.3	3735.7	2329.5	927.4	448.7
40°	7045.8	7074.5	6530.3	6007.9	4997.3	4596.3	4042.6	2827.4	1302.6	518.3	304.2
42.5°	5757.0	5792.4	5309.6	4845.9	3986.6	3656.6	3165.6	1751.3	646.5	335.5	178.7
45°	3734.3	3836.6	3477.9	3282.9	2785.0	2588.6	2066.3	893.4	390.1	196.4	105.0
47.5°	2137.2	2138.5	1835.8	1470.2	1205.7	1048.9	819.7	406.5	227.8	110.5	64.1
50°	992.9	1017.5	806.0	671.0	480.1	406.5	334.1	219.6	120.0	64.1	39.6
52.5°	289.2	305.6	276.8	251.0	212.8	189.6	162.3	107.8	62.7	38.2	24.5
55°	102.3	109.2	102.3	95.5	85.9	77.7	69.6	51.9	35.5	23.2	16.4
57.5°	42.3	43.6	42.3	40.9	38.2	38.2	34.1	28.6	21.8	15.0	11.0
60°	19.1	20.5	19.1	20.5	19.1	19.1	19.1	20.5	13.7	9.5	8.1
62.5°	8.1	9.5	9.5	9.5	9.5	11.0	11.0	9.5	8.1	6.8	5.4
65°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
67.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
70°	4.1	4.1	4.1	4.1	4.1	4.1	2.7	2.7	4.1	4.1	4.1
72.5°	4.1	4.1	4.1	4.1	2.7	2.7	2.7	2.7	2.7	4.1	4.1
75°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
77.5°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.7	2.7	2.7
80°	0.0	0.0	0.0	0.0	1.4	1.4	1.4	1.4	2.7	2.7	2.7
82.5°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.7	2.7	2.7
85°	0.0	0.0	0.0	0.0	1.4	1.4	1.4	1.4	2.7	2.7	2.7
87.5°	0.0	0.0	0.0	0.0	1.4	1.4	1.4	1.4	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212336

CATALOG NUMBER: LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7
2.5°	386.0	373.7	354.6	342.4	336.9	328.7	323.3	309.6	304.2	293.2	289.2
5°	474.6	450.1	421.5	398.2	383.3	366.9	342.4	315.0	301.4	283.7	274.1
7.5°	575.5	522.4	471.9	431.0	411.9	390.1	358.7	316.4	290.5	267.4	253.7
10°	703.8	594.6	515.5	450.1	421.5	392.8	354.6	305.6	272.8	245.5	230.5
12.5°	1003.8	717.4	555.1	461.0	424.2	388.7	340.9	290.5	252.3	220.9	204.5
15°	1444.4	1002.4	661.5	470.5	414.6	371.0	316.4	266.0	226.5	195.0	178.7
17.5°	1834.4	1277.9	808.7	506.0	411.9	350.5	286.5	234.6	196.4	166.4	152.8
20°	2047.2	1422.6	906.9	527.8	399.6	319.1	252.3	203.2	166.4	140.5	128.3
22.5°	2051.3	1414.3	871.6	480.1	351.9	276.8	218.2	171.9	139.1	115.9	106.3
25°	1928.6	1261.6	726.9	377.8	287.8	234.6	182.7	143.2	113.2	95.5	87.2
27.5°	1699.4	1025.6	534.6	272.8	225.1	189.6	147.4	114.6	88.7	77.7	71.0
30°	1336.6	668.3	312.3	203.2	174.6	145.9	111.9	80.5	69.6	61.4	55.9
32.5°	717.4	324.6	218.2	150.1	124.1	102.3	73.7	58.6	50.5	45.0	43.6
35°	375.0	237.3	145.9	95.5	79.1	66.8	50.5	40.9	36.8	34.1	34.1
37.5°	268.7	148.7	92.8	61.4	51.9	42.3	35.5	30.1	27.2	27.2	27.2
40°	159.6	91.4	55.9	39.6	34.1	30.1	25.9	21.8	21.8	21.8	21.8
42.5°	96.8	57.3	39.6	27.2	24.5	21.8	19.1	17.7	16.4	16.4	17.7
45°	60.0	39.6	25.9	20.5	19.1	16.4	15.0	13.7	13.7	13.7	15.0
47.5°	38.2	28.6	19.1	13.7	12.3	11.0	9.5	9.5	11.0	11.0	12.3
50°	28.6	17.7	12.3	9.5	8.1	8.1	6.8	8.1	8.1	9.5	11.0
52.5°	16.4	11.0	8.1	6.8	6.8	5.4	5.4	6.8	6.8	8.1	9.5
55°	11.0	8.1	6.8	5.4	5.4	5.4	5.4	5.4	6.8	6.8	8.1
57.5°	8.1	6.8	5.4	5.4	5.4	4.1	5.4	5.4	5.4	6.8	8.1
60°	6.8	5.4	5.4	5.4	5.4	4.1	4.1	5.4	5.4	6.8	6.8
62.5°	5.4	5.4	5.4	5.4	5.4	4.1	5.4	5.4	5.4	5.4	6.8
65°	4.1	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	6.8
67.5°	4.1	4.1	5.4	5.4	5.4	4.1	5.4	5.4	5.4	5.4	6.8
70°	4.1	4.1	4.1	5.4	5.4	4.1	5.4	5.4	5.4	5.4	5.4
72.5°	4.1	4.1	4.1	5.4	5.4	4.1	5.4	5.4	5.4	5.4	5.4
75°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4
77.5°	4.1	4.1	4.1	4.1	5.4	4.1	5.4	5.4	5.4	5.4	5.4
80°	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4	5.4
82.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4
85°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4
87.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212336

CATALOG NUMBER: LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7
2.5°	278.2	274.1	266.0	264.6	263.2	257.8	253.7	249.6	249.6	245.5	242.7
5°	257.8	251.0	241.4	237.3	235.9	229.2	223.6	219.6	218.2	214.1	210.1
7.5°	235.9	227.8	216.8	212.8	211.4	204.5	199.1	195.0	192.3	188.3	185.4
10°	212.8	203.2	193.7	189.6	188.3	181.4	177.3	173.2	170.5	167.8	165.0
12.5°	188.3	180.0	170.5	166.4	165.0	159.6	155.5	152.8	151.4	148.7	147.4
15°	163.6	155.5	147.4	144.5	143.2	139.1	136.4	135.0	133.7	133.7	132.3
17.5°	139.1	132.3	125.4	124.1	122.7	120.0	118.6	117.3	118.6	118.6	120.0
20°	115.9	110.5	105.0	105.0	103.6	102.3	102.3	102.3	105.0	106.3	109.2
22.5°	95.5	91.4	87.2	87.2	87.2	87.2	87.2	90.1	92.8	95.5	96.8
25°	79.1	75.0	73.7	73.7	73.7	75.0	76.4	79.1	81.8	84.5	87.2
27.5°	64.1	61.4	61.4	61.4	62.7	64.1	65.4	68.1	72.3	75.0	77.7
30°	51.9	50.5	50.5	51.9	53.2	54.6	57.3	60.0	62.7	65.4	68.1
32.5°	40.9	42.3	42.3	43.6	45.0	46.3	49.2	51.9	54.6	57.3	58.6
35°	34.1	34.1	35.5	36.8	38.2	39.6	42.3	45.0	46.3	49.2	51.9
37.5°	27.2	28.6	30.1	31.4	32.8	34.1	35.5	38.2	39.6	42.3	45.0
40°	23.2	24.5	25.9	27.2	27.2	30.1	30.1	32.8	34.1	36.8	39.6
42.5°	19.1	20.5	21.8	23.2	23.2	24.5	25.9	27.2	30.1	31.4	34.1
45°	15.0	16.4	17.7	19.1	20.5	21.8	21.8	24.5	25.9	27.2	30.1
47.5°	13.7	15.0	16.4	16.4	17.7	19.1	19.1	21.8	23.2	24.5	25.9
50°	11.0	12.3	13.7	15.0	15.0	16.4	17.7	19.1	20.5	21.8	21.8
52.5°	9.5	11.0	12.3	12.3	13.7	15.0	15.0	16.4	17.7	17.7	19.1
55°	9.5	11.0	11.0	12.3	12.3	13.7	13.7	15.0	15.0	16.4	16.4
57.5°	8.1	9.5	9.5	11.0	11.0	12.3	12.3	13.7	13.7	13.7	15.0
60°	8.1	8.1	9.5	9.5	11.0	11.0	11.0	12.3	12.3	12.3	13.7
62.5°	6.8	8.1	8.1	9.5	9.5	9.5	11.0	11.0	11.0	12.3	12.3
65°	6.8	8.1	8.1	9.5	9.5	9.5	9.5	9.5	11.0	11.0	11.0
67.5°	6.8	6.8	8.1	8.1	8.1	8.1	9.5	9.5	9.5	9.5	9.5
70°	6.8	6.8	6.8	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
72.5°	5.4	6.8	6.8	6.8	6.8	8.1	8.1	8.1	8.1	8.1	6.8
75°	5.4	5.4	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
77.5°	5.4	5.4	5.4	6.8	6.8	6.8	6.8	6.8	6.8	5.4	5.4
80°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	4.1
82.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	4.1	4.1	4.1
85°	5.4	4.1	5.4	5.4	5.4	4.1	4.1	4.1	4.1	4.1	2.7
87.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212336

CATALOG NUMBER: LDSQA4A30940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	302.7	302.7	302.7	302.7	302.7	302.7	302.7	302.7
2.5°	240.0	237.3	238.7	238.7	235.9	234.6	234.6	235.9
5°	207.4	204.5	206.0	206.0	203.2	201.8	201.8	203.2
7.5°	182.7	180.0	181.4	181.4	178.7	178.7	178.7	178.7
10°	163.6	162.3	162.3	162.3	159.6	160.9	159.6	158.2
12.5°	145.9	145.9	145.9	145.9	144.5	145.9	144.5	144.5
15°	132.3	132.3	133.7	133.7	133.7	135.0	135.0	135.0
17.5°	121.4	122.7	124.1	125.4	125.4	126.8	126.8	126.8
20°	110.5	113.2	114.6	115.9	115.9	118.6	117.3	118.6
22.5°	99.6	102.3	103.6	105.0	106.3	107.8	107.8	109.2
25°	90.1	92.8	94.1	95.5	96.8	99.6	99.6	99.6
27.5°	80.5	83.2	84.5	87.2	88.7	91.4	91.4	91.4
30°	71.0	73.7	75.0	76.4	79.1	81.8	81.8	83.2
32.5°	61.4	65.4	66.8	68.1	71.0	73.7	75.0	75.0
35°	54.6	57.3	58.6	61.4	62.7	66.8	66.8	66.8
37.5°	47.7	50.5	53.2	54.6	55.9	58.6	60.0	61.4
40°	42.3	45.0	46.3	47.7	50.5	53.2	54.6	54.6
42.5°	36.8	39.6	40.9	42.3	43.6	46.3	46.3	46.3
45°	32.8	34.1	35.5	36.8	38.2	39.6	40.9	40.9
47.5°	27.2	30.1	30.1	31.4	32.8	35.5	35.5	36.8
50°	23.2	25.9	25.9	27.2	28.6	30.1	31.4	31.4
52.5°	20.5	21.8	23.2	23.2	24.5	25.9	27.2	27.2
55°	17.7	19.1	19.1	20.5	20.5	21.8	23.2	23.2
57.5°	15.0	16.4	17.7	17.7	17.7	19.1	19.1	20.5
60°	13.7	15.0	15.0	15.0	15.0	16.4	16.4	16.4
62.5°	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
65°	11.0	11.0	11.0	11.0	9.5	9.5	9.5	9.5
67.5°	9.5	9.5	9.5	9.5	8.1	8.1	8.1	8.1
70°	8.1	8.1	8.1	8.1	6.8	6.8	6.8	5.4
72.5°	6.8	6.8	6.8	6.8	6.8	5.4	5.4	5.4
75°	6.8	5.4	5.4	5.4	5.4	5.4	4.1	4.1
77.5°	5.4	5.4	5.4	4.1	4.1	4.1	4.1	4.1
80°	4.1	4.1	4.1	4.1	4.1	2.7	2.7	2.7
82.5°	4.1	2.7	2.7	2.7	2.7	2.7	2.7	2.7
85°	2.7	2.7	2.7	2.7	1.4	1.4	1.4	1.4
87.5°	2.7	1.4	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)