

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212354

Luminaire Tested: **LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212354
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2822.3 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212354

CATALOG NUMBER: LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1212354

CATALOG NUMBER: LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	71	90	82	76	71	80	74	70		78	73	69		76
5	86	76	69	64	84	75	68	64	73	67	63		71	66	62		70
6	80	70	62	57	79	69	62	57	67	61	57		66	60	56		64
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59
8	70	59	52	47	69	58	51	46	57	51	46		56	50	46		55
9	66	54	47	42	64	54	47	42	53	46	42		52	46	42		51
10	62	50	43	38	60	50	43	38	49	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33810	33810	33810
5°	79236	31906	22308
10°	313062	28035	18602
15°	579392	22456	16308
20°	742917	16340	14763
25°	888878	11587	13073
30°	945157	7607	11511
35°	968657	4600	10029
40°	886700	2997	8599
45°	639829	2096	7056
50°	279329	1688	5863
55°	19254	1385	4932
60°	3507	1337	4049
65°	1261	1261	2865
70°	1190	1558	1954
75°	1048	2059	2059
80°	0	3068	2343
85°	0	6113	1667



TEST NUMBER: P1212354

CATALOG NUMBER: LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	1.8
10°-20°	399.5	14.2
20°-30°	836.3	29.6
30°-40°	931.0	33.0
40°-50°	534.4	18.9
50°-60°	53.4	1.9
60°-70°	8.4	0.3
70°-80°	5.3	0.2
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1286.7	45.6
0°-40°	2217.6	78.6
0°-60°	2805.4	99.4
0°-90°	2822.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2822.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	349	349	349	349	349	
5°	815	562	328	239	229	149
15°	5777	2307	224	157	163	1633
25°	8316	3174	108	96	122	3766
35°	8191	969	39	56	85	5001
45°	4670	117	15	31	52	3566
55°	114	17	8	18	29	340
65°	6	4	6	11	12	7
75°	3	3	6	7	6	2
85°	0	3	6	4	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212354

CATALOG NUMBER: LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0
2.5°	521.4	510.2	499.2	492.2	485.2	495.0	488.0	485.2	465.8	456.1	447.7
5°	814.8	793.9	763.3	738.3	713.2	718.8	699.3	675.7	627.1	592.3	561.7
7.5°	1572.5	1521.1	1426.5	1334.7	1243.0	1226.3	1165.2	1059.4	923.2	820.3	731.4
10°	3182.5	3026.8	2853.1	2665.3	2445.6	2384.5	2232.9	1946.5	1633.7	1276.3	1017.7
12.5°	4698.1	4627.1	4422.8	4179.5	3941.7	3795.8	3638.6	3165.8	2669.5	2093.9	1612.8
15°	5777.0	5733.9	5554.6	5333.4	5077.6	4983.1	4791.2	4319.9	3692.9	3004.6	2306.6
17.5°	6576.4	6502.7	6315.1	6074.5	5771.4	5690.8	5461.3	4992.8	4342.1	3651.1	2876.6
20°	7206.3	7160.4	6917.0	6627.8	6265.0	6167.6	5899.3	5411.3	4703.6	3969.4	3181.2
22.5°	7772.2	7694.3	7395.3	7050.6	6636.2	6531.9	6233.0	5697.8	4937.2	4119.7	3235.4
25°	8315.8	8197.5	7834.7	7382.9	6896.2	6754.3	6426.3	5859.0	5023.4	4132.2	3174.3
27.5°	8474.3	8414.5	8079.4	7553.8	6990.8	6830.8	6488.8	5895.1	4991.4	4018.2	2954.5
30°	8449.3	8399.2	8119.7	7570.5	6974.1	6805.9	6458.2	5783.9	4805.0	3720.6	2566.6
32.5°	8369.9	8350.5	8012.6	7425.9	6818.3	6634.8	6259.4	5507.3	4456.1	3267.4	1875.6
35°	8190.7	8114.2	7692.8	7140.9	6557.0	6355.3	5931.2	5110.9	3995.9	2378.9	969.1
37.5°	7665.1	7605.3	7273.0	6789.1	6220.5	5961.9	5514.2	4599.3	3093.5	1352.8	579.8
40°	7011.6	6982.4	6721.0	6288.7	5681.1	5389.1	4902.4	3763.7	1888.1	768.8	382.4
42.5°	6341.5	6333.1	6053.6	5601.7	4942.8	4607.7	4103.0	2538.8	1003.9	464.4	221.0
45°	4670.2	4720.3	4525.7	4254.4	3751.2	3507.9	2853.1	1308.4	578.5	257.3	116.8
47.5°	3275.7	3220.1	2875.3	2401.2	1940.9	1643.4	1243.0	618.7	308.6	134.8	66.7
50°	1853.4	1863.1	1551.7	1255.5	823.1	652.1	495.0	311.4	148.8	71.0	40.4
52.5°	483.8	506.2	436.5	375.4	319.8	260.0	209.9	134.8	71.0	41.7	26.4
55°	114.0	118.1	109.9	102.9	97.4	86.2	76.5	58.3	38.9	26.4	16.7
57.5°	40.4	41.7	40.4	40.4	38.9	37.6	34.8	30.6	23.7	16.7	11.2
60°	18.1	19.4	18.1	19.4	19.4	19.4	19.4	19.4	13.9	9.7	6.9
62.5°	8.2	8.2	8.2	8.2	9.7	9.7	11.2	11.2	8.2	6.9	5.5
65°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.2
67.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
70°	4.2	4.2	4.2	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.2
72.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
75°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
77.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8	2.8
80°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.8	2.8	2.8
82.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.8	2.8	2.8
85°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8
87.5°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212354

CATALOG NUMBER: LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0
2.5°	432.5	431.0	415.7	404.6	399.1	390.6	380.9	367.0	351.8	337.8	332.3
5°	525.6	507.5	475.5	449.1	436.5	424.1	401.8	376.8	353.2	328.1	315.7
7.5°	646.5	593.6	531.1	482.5	461.6	440.7	408.8	374.0	342.0	308.6	290.5
10°	811.9	689.6	581.2	503.3	472.7	444.9	399.1	355.9	321.1	285.0	261.3
12.5°	1160.9	857.9	634.0	513.0	472.7	436.5	380.9	330.8	292.0	254.4	232.2
15°	1672.6	1158.1	749.3	522.8	463.0	417.0	353.2	298.9	257.3	223.9	203.0
17.5°	2085.6	1434.9	892.6	547.8	450.4	390.6	317.0	260.0	221.0	190.5	173.8
20°	2294.1	1551.7	957.9	552.0	420.0	349.0	273.8	219.7	184.9	158.5	144.5
22.5°	2289.9	1514.1	899.6	483.8	368.4	301.7	230.8	180.8	152.9	132.1	121.0
25°	2145.4	1340.3	750.8	386.6	297.5	250.3	187.6	146.0	123.8	108.4	98.7
27.5°	1874.1	1088.6	560.3	286.5	232.2	197.5	146.0	116.8	98.7	87.7	80.7
30°	1471.0	728.6	353.2	212.7	176.6	148.8	112.6	90.4	77.9	68.0	64.0
32.5°	810.6	379.6	237.7	155.7	129.3	108.4	83.4	65.3	57.0	50.1	48.6
35°	447.7	268.3	169.7	104.3	86.2	73.7	57.0	47.3	41.7	38.9	38.9
37.5°	317.0	172.4	101.5	65.3	55.6	48.6	38.9	33.4	31.9	30.6	30.6
40°	190.5	101.5	61.2	43.1	37.6	33.4	29.2	25.0	25.0	23.7	25.0
42.5°	104.3	61.2	41.7	30.6	26.4	25.0	20.9	19.4	19.4	19.4	20.9
45°	62.6	40.4	29.2	22.2	19.4	16.7	15.3	13.9	15.3	15.3	16.7
47.5°	40.4	29.2	19.4	13.9	12.5	11.2	9.7	11.2	11.2	12.5	13.9
50°	27.9	18.1	12.5	8.2	8.2	6.9	8.2	8.2	9.7	11.2	12.5
52.5°	18.1	12.5	8.2	6.9	5.5	5.5	5.5	6.9	8.2	9.7	11.2
55°	11.2	8.2	6.9	5.5	5.5	5.5	5.5	5.5	6.9	8.2	9.7
57.5°	8.2	6.9	5.5	4.2	4.2	4.2	5.5	5.5	6.9	6.9	8.2
60°	5.5	5.5	4.2	4.2	4.2	4.2	4.2	5.5	5.5	6.9	8.2
62.5°	5.5	5.5	4.2	4.2	4.2	4.2	5.5	5.5	5.5	6.9	6.9
65°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	6.9
67.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	6.9
70°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	6.9
72.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5
75°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5
77.5°	2.8	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5
80°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5
82.5°	2.8	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5
85°	2.8	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5
87.5°	2.8	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212354

CATALOG NUMBER: LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0
2.5°	325.4	315.7	307.2	310.1	304.5	294.7	292.0	285.0	276.7	275.3	275.3
5°	301.7	286.5	273.8	272.5	267.0	255.9	253.1	246.1	239.1	237.7	236.4
7.5°	272.5	255.9	244.7	241.9	237.7	228.0	226.7	219.7	215.5	212.7	212.7
10°	243.4	228.0	218.3	217.0	214.0	205.8	204.3	198.8	194.6	193.3	191.8
12.5°	215.5	203.0	194.6	193.3	190.5	183.6	182.1	177.9	175.1	173.8	173.8
15°	189.1	177.9	171.0	169.7	168.2	161.3	161.3	158.5	157.2	157.2	158.5
17.5°	162.6	152.9	147.5	146.0	146.0	140.5	141.8	140.5	140.5	140.5	143.2
20°	136.3	127.8	123.8	125.1	122.3	121.0	122.3	122.3	122.3	125.1	129.3
22.5°	114.0	107.1	102.9	104.3	104.3	102.9	104.3	105.6	108.4	112.6	116.8
25°	93.1	87.7	86.2	87.7	87.7	87.7	90.4	93.1	95.9	100.2	104.3
27.5°	75.0	71.0	71.0	72.3	73.7	73.7	77.9	80.7	84.8	89.0	93.1
30°	59.8	58.3	58.3	61.2	61.2	62.6	68.0	71.0	73.7	77.9	82.0
32.5°	47.3	47.3	48.6	51.5	51.5	54.2	58.3	61.2	64.0	68.0	72.3
35°	38.9	40.4	41.7	43.1	44.5	45.8	50.1	52.9	55.6	59.8	62.6
37.5°	31.9	33.4	34.8	37.6	37.6	38.9	43.1	45.8	47.3	51.5	55.6
40°	26.4	27.9	29.2	31.9	31.9	33.4	37.6	38.9	40.4	44.5	48.6
42.5°	22.2	23.7	25.0	26.4	27.9	29.2	31.9	33.4	36.1	38.9	41.7
45°	18.1	19.4	20.9	22.2	23.7	25.0	26.4	29.2	30.6	33.4	36.1
47.5°	15.3	16.7	18.1	19.4	20.9	20.9	23.7	25.0	26.4	29.2	31.9
50°	13.9	15.3	16.7	16.7	18.1	19.4	20.9	22.2	23.7	25.0	27.9
52.5°	11.2	12.5	13.9	15.3	15.3	16.7	18.1	19.4	20.9	22.2	23.7
55°	11.2	11.2	12.5	13.9	13.9	15.3	16.7	18.1	18.1	19.4	20.9
57.5°	9.7	11.2	11.2	12.5	12.5	13.9	15.3	15.3	16.7	16.7	18.1
60°	8.2	9.7	11.2	11.2	11.2	12.5	12.5	13.9	13.9	15.3	15.3
62.5°	8.2	9.7	9.7	11.2	11.2	11.2	12.5	12.5	12.5	13.9	13.9
65°	8.2	8.2	9.7	9.7	9.7	9.7	11.2	11.2	11.2	12.5	12.5
67.5°	6.9	8.2	8.2	8.2	9.7	9.7	9.7	9.7	9.7	11.2	11.2
70°	6.9	6.9	8.2	8.2	8.2	8.2	8.2	9.7	9.7	9.7	9.7
72.5°	6.9	6.9	6.9	6.9	8.2	8.2	8.2	8.2	8.2	8.2	8.2
75°	5.5	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
77.5°	5.5	5.5	5.5	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
80°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
82.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.2	4.2
85°	5.5	5.5	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
87.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212354

CATALOG NUMBER: LDSQA4A35927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	349.0	349.0	349.0	349.0	349.0	349.0	349.0	349.0
2.5°	269.7	267.0	265.6	269.7	264.1	267.0	265.6	267.0
5°	232.2	229.4	228.0	232.2	226.7	229.4	226.7	229.4
7.5°	208.6	207.2	205.8	208.6	204.3	207.2	205.8	207.2
10°	189.1	187.6	186.3	190.5	186.3	189.1	187.6	189.1
12.5°	172.4	172.4	171.0	173.8	171.0	173.8	172.4	173.8
15°	157.2	158.5	157.2	159.9	158.5	161.3	159.9	162.6
17.5°	144.5	146.0	146.0	150.2	148.8	152.9	151.5	152.9
20°	132.1	133.5	134.8	137.7	137.7	141.8	140.5	143.2
22.5°	119.6	122.3	122.3	126.5	126.5	130.7	130.7	132.1
25°	107.1	111.2	112.6	115.3	116.8	121.0	121.0	122.3
27.5°	97.4	100.2	101.5	105.6	107.1	111.2	111.2	114.0
30°	86.2	90.4	91.7	94.6	95.9	100.2	100.2	102.9
32.5°	76.5	79.2	82.0	84.8	86.2	90.4	90.4	93.1
35°	66.7	71.0	72.3	75.0	77.9	82.0	82.0	84.8
37.5°	58.3	62.6	64.0	66.7	69.5	73.7	73.7	76.5
40°	51.5	55.6	57.0	59.8	61.2	66.7	66.7	68.0
42.5°	45.8	48.6	50.1	52.9	54.2	57.0	57.0	59.8
45°	38.9	41.7	43.1	44.5	47.3	50.1	50.1	51.5
47.5°	33.4	36.1	37.6	38.9	40.4	43.1	43.1	45.8
50°	29.2	30.6	31.9	33.4	34.8	37.6	37.6	38.9
52.5°	25.0	26.4	27.9	29.2	30.6	31.9	33.4	34.8
55°	22.2	23.7	23.7	25.0	26.4	27.9	27.9	29.2
57.5°	19.4	20.9	20.9	20.9	22.2	23.7	23.7	25.0
60°	16.7	18.1	18.1	18.1	19.4	19.4	19.4	20.9
62.5°	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3
65°	12.5	12.5	12.5	12.5	12.5	12.5	11.2	12.5
67.5°	11.2	11.2	11.2	9.7	9.7	9.7	9.7	9.7
70°	9.7	9.7	9.7	8.2	8.2	8.2	6.9	6.9
72.5°	8.2	8.2	8.2	6.9	6.9	6.9	5.5	5.5
75°	6.9	6.9	6.9	6.9	5.5	5.5	5.5	5.5
77.5°	5.5	5.5	5.5	5.5	5.5	5.5	4.2	4.2
80°	5.5	4.2	4.2	4.2	4.2	4.2	4.2	4.2
82.5°	4.2	4.2	4.2	4.2	2.8	2.8	2.8	2.8
85°	2.8	2.8	2.8	2.8	2.8	2.8	1.5	1.5
87.5°	2.8	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)