

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212380

Luminaire Tested: **LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3209.1 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212380

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212380

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	105	102		103	101	99		99	98	96		96	94	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	84
3	99	91	85	81	97	90	84	80		87	83	79		85	81	77		82	79	76
4	92	83	77	72	91	82	76	71		80	75	71		78	73	70		76	72	69
5	86	76	69	64	85	75	69	64		74	68	63		72	67	63		70	66	62
6	81	70	63	58	79	69	62	58		68	62	57		66	61	57		65	60	56
7	75	64	57	52	74	64	57	52		62	56	52		61	55	51		60	55	51
8	71	59	52	47	69	59	52	47		57	51	47		56	51	47		55	50	46
9	66	55	48	43	65	54	47	43		53	47	43		52	46	42		51	46	42
10	62	50	44	39	61	50	43	39		49	43	39		48	43	39		47	42	39

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	36280	36280	36280
5°	95388	34551	22571
10°	373983	29895	18779
15°	688490	23559	16639
20°	865154	16649	15144
25°	1034836	10988	13500
30°	1088228	6891	11835
35°	1097008	4163	10242
40°	1009457	2782	8726
45°	718195	2014	7247
50°	296781	1537	5983
55°	17109	1486	5219
60°	1976	1434	4263
65°	665	1696	3049
70°	821	1671	2096
75°	1085	2208	2208
80°	0	3292	2510
85°	0	6558	3223

TEST NUMBER: P1212380

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	1.8
10°-20°	470.2	14.7
20°-30°	972.6	30.3
30°-40°	1058.8	33.0
40°-50°	580.5	18.1
50°-60°	50.3	1.6
60°-70°	8.2	0.3
70°-80°	5.9	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1501.7	46.8
0°-40°	2560.4	79.8
0°-60°	3191.2	99.4
0°-90°	3209.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3209.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	374	374	374	374	374	
5°	981	671	355	245	232	179
15°	6865	2885	235	159	166	1917
25°	9681	3838	103	97	126	4372
35°	9276	1050	35	56	87	5693
45°	5242	107	15	31	53	4001
55°	101	12	9	19	31	346
65°	3	4	7	12	13	4
75°	3	4	6	9	6	2
85°	0	3	6	4	3	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212380

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5
2.5°	588.8	568.3	565.3	568.3	553.6	552.2	555.0	543.3	533.1	522.7	513.9
5°	980.9	938.3	925.1	907.5	863.4	848.7	845.9	798.8	753.3	710.7	671.1
7.5°	1906.0	1820.8	1775.4	1687.2	1552.1	1491.9	1459.6	1305.5	1161.6	1030.8	911.9
10°	3801.8	3578.5	3469.9	3303.9	3008.8	2863.5	2757.7	2370.1	1988.2	1621.1	1298.1
12.5°	5547.7	5424.3	5264.2	5176.2	4697.4	4514.0	4339.2	3801.8	3220.2	2627.0	2038.2
15°	6864.8	6684.2	6513.9	6472.8	6096.8	5882.5	5688.7	5132.1	4440.5	3685.8	2885.4
17.5°	7638.6	7509.5	7348.0	7270.1	6829.7	6656.4	6436.1	5897.2	5224.6	4472.9	3543.3
20°	8392.0	8201.0	7973.5	7856.0	7368.5	7168.8	6919.2	6352.4	5640.2	4841.4	3911.9
22.5°	9080.7	8834.0	8510.9	8328.9	7781.1	7560.9	7281.9	6668.2	5897.2	4983.9	3942.7
25°	9681.3	9458.0	9027.8	8709.2	8063.1	7803.2	7478.6	6837.0	5989.7	4972.0	3838.5
27.5°	9795.9	9646.1	9259.9	8891.3	8161.5	7872.2	7535.9	6872.2	5925.1	4809.1	3557.9
30°	9728.3	9566.7	9256.8	8881.0	8120.4	7828.2	7478.6	6722.4	5672.5	4428.7	3044.0
32.5°	9565.3	9425.8	9055.7	8659.3	7917.8	7613.7	7245.1	6371.4	5239.3	3823.7	2239.3
35°	9276.0	9066.1	8619.5	8293.6	7596.1	7283.4	6832.5	5903.0	4591.8	2748.9	1049.9
37.5°	8687.1	8483.0	8161.5	7860.5	7180.6	6812.1	6336.3	5251.0	3403.8	1499.3	649.0
40°	7982.3	7806.1	7525.6	7233.4	6532.9	6108.6	5584.4	4104.3	2002.9	844.4	399.5
42.5°	7215.8	7033.7	6716.5	6375.9	5612.4	5164.4	4597.7	2656.4	1055.8	497.7	217.3
45°	5242.2	5079.3	4848.7	4603.5	4161.4	3838.5	3092.5	1395.0	584.4	264.4	107.2
47.5°	3587.4	3393.6	2967.7	2452.3	1988.2	1700.5	1279.0	605.0	299.6	132.2	63.2
50°	1969.2	1763.5	1546.2	1204.1	806.1	662.3	515.4	292.2	135.0	66.1	35.2
52.5°	483.2	427.3	390.6	359.7	284.8	257.0	217.3	121.9	61.6	36.6	25.0
55°	101.3	94.0	89.6	88.2	80.8	77.8	67.5	47.0	33.8	23.5	11.7
57.5°	29.4	27.9	29.4	29.4	29.4	27.9	27.9	20.5	19.1	11.7	7.4
60°	10.2	10.2	10.2	11.7	11.7	11.7	13.3	13.3	10.2	7.4	5.9
62.5°	4.5	4.5	4.5	5.9	5.9	7.4	7.4	7.4	5.9	5.9	4.5
65°	2.9	2.9	2.9	2.9	4.5	4.5	4.5	4.5	4.5	4.5	4.5
67.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	4.5
70°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	4.5
72.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	4.5
75°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	4.5
77.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.9	2.9	2.9	4.5
80°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.9	2.9	2.9	2.9
82.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.9	2.9	2.9
85°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.9	2.9	2.9
87.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.9	2.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212380

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5
2.5°	489.0	474.4	456.6	437.6	434.6	424.4	409.7	389.1	381.9	367.1	353.8
5°	613.8	574.1	533.1	496.3	484.6	468.4	442.0	405.2	381.9	355.3	333.4
7.5°	781.2	690.1	606.4	540.3	519.8	493.4	452.3	405.2	370.0	333.4	303.9
10°	1004.4	819.4	675.5	568.3	534.5	499.3	444.9	387.6	346.5	303.9	273.2
12.5°	1434.6	1008.8	740.1	583.1	536.0	490.5	421.4	359.7	312.7	270.2	239.4
15°	2039.6	1368.5	870.8	593.3	521.3	465.5	384.7	321.6	274.6	234.9	205.6
17.5°	2550.6	1709.2	1045.6	622.5	511.0	433.3	342.2	277.5	232.1	196.7	173.3
20°	2800.3	1861.9	1124.8	627.1	481.6	384.7	292.2	230.6	190.9	161.5	141.0
22.5°	2770.9	1810.5	1051.3	549.3	406.8	324.6	242.3	186.4	152.7	129.1	114.6
25°	2574.1	1587.3	857.5	420.0	317.2	262.8	189.5	145.3	118.9	102.8	91.0
27.5°	2243.8	1274.6	625.6	296.6	240.8	199.7	141.0	111.5	91.0	79.2	72.0
30°	1728.3	815.0	359.7	212.9	174.8	142.4	105.8	80.8	69.0	61.6	55.8
32.5°	891.3	396.5	239.4	152.7	123.4	102.8	73.4	58.8	51.4	47.0	44.0
35°	489.0	282.0	165.9	98.4	79.2	66.1	49.9	41.1	38.3	35.2	35.2
37.5°	336.2	174.8	92.5	58.8	48.5	41.1	33.8	29.4	27.9	27.9	27.9
40°	193.8	92.5	52.9	36.6	30.9	27.9	23.5	22.0	22.0	22.0	23.5
42.5°	99.9	54.2	35.2	25.0	22.0	19.1	16.1	16.1	16.1	17.6	19.1
45°	58.8	36.6	23.5	16.1	14.7	13.3	11.7	11.7	13.3	14.7	16.1
47.5°	36.6	25.0	14.7	10.2	8.8	8.8	8.8	8.8	10.2	11.7	13.3
50°	25.0	13.3	8.8	5.9	5.9	5.9	5.9	7.4	8.8	10.2	11.7
52.5°	13.3	7.4	5.9	4.5	4.5	4.5	5.9	5.9	7.4	8.8	10.2
55°	7.4	5.9	4.5	4.5	4.5	4.5	4.5	5.9	7.4	8.8	10.2
57.5°	5.9	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	7.4	8.8
60°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	7.4	8.8
62.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	7.4	7.4
65°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	7.4	7.4
67.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	7.4
70°	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9	7.4
72.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9
75°	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9	5.9	7.4
77.5°	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9	5.9
80°	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9	5.9
82.5°	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9	5.9
85°	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9	5.9	5.9
87.5°	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212380

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5
2.5°	346.5	334.8	323.1	323.1	317.2	308.4	305.4	296.6	290.8	287.8	284.8
5°	317.2	299.6	283.5	282.0	274.6	264.4	259.9	251.1	245.2	242.3	240.8
7.5°	283.5	265.8	249.7	246.7	240.8	233.5	229.0	221.7	218.8	215.9	214.5
10°	251.1	233.5	221.7	218.8	214.5	208.6	204.0	199.7	196.7	195.3	195.3
12.5°	218.8	205.6	195.3	192.4	189.5	185.0	182.1	179.1	177.7	177.7	177.7
15°	189.5	177.7	168.8	168.8	165.9	162.9	162.9	160.0	158.6	160.0	161.5
17.5°	160.0	151.3	143.9	143.9	142.4	141.0	141.0	141.0	142.4	143.9	146.9
20°	132.2	124.8	121.9	121.9	120.4	121.9	121.9	123.4	124.8	129.1	133.7
22.5°	107.2	102.8	99.9	101.3	101.3	102.8	104.2	107.2	110.1	114.6	118.9
25°	86.6	83.7	82.3	83.7	85.1	86.6	89.6	92.5	96.9	101.3	107.2
27.5°	69.0	67.5	67.5	69.0	70.4	73.4	77.8	80.8	85.1	89.6	95.4
30°	55.8	54.2	55.8	58.8	60.2	63.2	66.1	70.4	74.9	79.2	85.1
32.5°	44.0	45.5	47.0	48.5	49.9	54.2	57.3	60.2	64.7	69.0	74.9
35°	36.6	38.3	39.7	41.1	42.6	45.5	48.5	51.4	55.8	60.2	66.1
37.5°	29.4	30.9	32.3	35.2	36.6	38.3	42.6	44.0	48.5	51.4	57.3
40°	25.0	26.4	27.9	29.4	30.9	33.8	36.6	38.3	41.1	45.5	49.9
42.5°	20.5	22.0	23.5	25.0	26.4	29.4	30.9	33.8	36.6	39.7	42.6
45°	17.6	19.1	20.5	22.0	23.5	25.0	26.4	29.4	30.9	33.8	36.6
47.5°	14.7	16.1	19.1	19.1	20.5	22.0	23.5	25.0	27.9	29.4	32.3
50°	13.3	14.7	16.1	17.6	17.6	19.1	20.5	22.0	23.5	25.0	27.9
52.5°	11.7	13.3	14.7	14.7	16.1	17.6	19.1	19.1	20.5	22.0	23.5
55°	10.2	11.7	13.3	13.3	14.7	16.1	16.1	17.6	19.1	19.1	20.5
57.5°	10.2	10.2	11.7	11.7	13.3	13.3	14.7	16.1	16.1	17.6	19.1
60°	8.8	10.2	10.2	11.7	11.7	13.3	13.3	14.7	14.7	16.1	16.1
62.5°	8.8	8.8	10.2	10.2	11.7	11.7	13.3	13.3	13.3	14.7	14.7
65°	8.8	8.8	10.2	10.2	10.2	11.7	11.7	11.7	11.7	13.3	13.3
67.5°	7.4	8.8	8.8	10.2	10.2	10.2	10.2	10.2	11.7	11.7	11.7
70°	7.4	8.8	8.8	8.8	8.8	10.2	10.2	10.2	10.2	10.2	10.2
72.5°	7.4	7.4	7.4	7.4	8.8	8.8	8.8	8.8	8.8	8.8	8.8
75°	7.4	7.4	7.4	7.4	7.4	8.8	8.8	8.8	8.8	8.8	8.8
77.5°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
80°	5.9	5.9	5.9	5.9	5.9	7.4	5.9	5.9	5.9	5.9	5.9
82.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	4.5	4.5
85°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	4.5	4.5	4.5	4.5
87.5°	5.9	5.9	5.9	4.5	4.5	4.5	4.5	4.5	4.5	2.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212380

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	374.5	374.5	374.5	374.5	374.5	374.5	374.5	374.5
2.5°	280.4	277.5	280.4	277.5	277.5	271.6	276.1	273.2
5°	236.4	233.5	236.4	234.9	232.1	230.6	233.5	232.1
7.5°	211.4	208.6	211.4	211.4	208.6	207.1	209.9	208.6
10°	192.4	190.9	192.4	192.4	190.9	189.5	192.4	190.9
12.5°	176.2	174.8	177.7	177.7	176.2	176.2	179.1	176.2
15°	161.5	161.5	164.5	164.5	164.5	164.5	167.4	165.9
17.5°	146.9	149.8	152.7	154.1	154.1	154.1	157.2	157.2
20°	135.0	138.0	141.0	142.4	143.9	143.9	146.9	146.9
22.5°	121.9	124.8	129.1	130.7	132.2	133.7	136.5	136.5
25°	110.1	113.0	117.5	118.9	121.9	123.4	126.3	126.3
27.5°	98.4	102.8	105.8	108.7	110.1	113.0	116.0	116.0
30°	88.2	92.5	95.4	98.4	99.9	102.8	105.8	105.8
32.5°	77.8	82.3	85.1	88.2	91.0	92.5	96.9	96.9
35°	69.0	72.0	76.4	77.8	80.8	83.7	86.6	86.6
37.5°	60.2	63.2	66.1	69.0	72.0	73.4	76.4	77.8
40°	52.9	55.8	58.8	60.2	63.2	66.1	67.5	69.0
42.5°	45.5	48.5	51.4	52.9	55.8	57.3	60.2	60.2
45°	39.7	42.6	44.0	45.5	48.5	49.9	52.9	52.9
47.5°	33.8	36.6	38.3	39.7	41.1	42.6	45.5	45.5
50°	29.4	30.9	32.3	33.8	35.2	38.3	39.7	39.7
52.5°	25.0	27.9	27.9	29.4	30.9	32.3	33.8	35.2
55°	22.0	23.5	25.0	25.0	26.4	27.9	29.4	30.9
57.5°	19.1	20.5	22.0	22.0	23.5	23.5	25.0	26.4
60°	17.6	17.6	19.1	19.1	19.1	20.5	20.5	22.0
62.5°	14.7	14.7	16.1	16.1	16.1	16.1	16.1	16.1
65°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3
67.5°	11.7	11.7	11.7	11.7	10.2	10.2	10.2	10.2
70°	10.2	10.2	10.2	10.2	8.8	8.8	8.8	7.4
72.5°	8.8	8.8	8.8	8.8	7.4	7.4	5.9	5.9
75°	7.4	7.4	7.4	7.4	7.4	5.9	5.9	5.9
77.5°	7.4	5.9	5.9	5.9	5.9	5.9	5.9	4.5
80°	5.9	5.9	4.5	4.5	4.5	4.5	4.5	4.5
82.5°	4.5	4.5	4.5	4.5	2.9	2.9	2.9	2.9
85°	4.5	2.9	2.9	2.9	2.9	2.9	2.9	2.9
87.5°	2.9	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)