

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212390

Luminaire Tested: **LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3401.3 lumens
Efficiency: N/A
Efficacy: 71.3 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212390

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212390

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34400	34400	34400
5°	76153	32548	22872
10°	304868	28272	19103
15°	702742	22486	16789
20°	1049030	15959	14969
25°	1375912	10636	13329
30°	1579426	6723	11656
35°	1448190	4293	10088
40°	1187591	2782	8599
45°	688493	1945	6905
50°	195126	1432	5697
55°	17869	1334	4797
60°	2751	1531	3972
65°	711	1444	2888
70°	878	1784	2238
75°	1160	2358	2358
80°	0	3515	1729
85°	0	7003	1778

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212390

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.5	1.5
10°-20°	452.3	13.3
20°-30°	1102.1	32.4
30°-40°	1194.4	35.1
40°-50°	541.2	15.9
50°-60°	41.9	1.2
60°-70°	8.6	0.3
70°-80°	6.3	0.2
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1604.9	47.2
0°-40°	2799.3	82.3
0°-60°	3382.3	99.4
0°-90°	3401.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3401.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	355	355	355	355	355	
5°	783	578	335	253	235	141
15°	7007	2292	224	163	167	2036
25°	12872	3292	100	98	125	5867
35°	12246	837	36	57	85	7532
45°	5025	106	14	32	50	3967
55°	106	14	8	19	28	242
65°	3	5	6	13	13	5
75°	3	5	6	10	6	2
85°	0	5	6	5	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1212390

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1
2.5°	532.0	522.6	527.3	514.7	506.8	500.5	503.6	500.5	480.0	475.3	459.5
5°	783.1	769.0	769.0	742.0	713.6	696.3	696.3	675.8	631.5	611.0	577.9
7.5°	1403.6	1375.1	1351.4	1267.7	1158.8	1097.3	1081.6	994.7	882.6	811.5	727.8
10°	3099.2	2980.8	2897.1	2679.2	2387.2	2205.7	2128.3	1828.3	1471.4	1203.1	959.9
12.5°	5211.7	5050.7	4903.8	4547.1	4127.0	3841.3	3688.1	3246.1	2553.0	2057.2	1539.4
15°	7006.9	6833.2	6659.5	6225.4	5781.7	5533.8	5252.7	4667.0	3751.3	3047.2	2292.4
17.5°	8479.9	8382.0	8203.6	7567.3	7008.5	6621.6	6329.5	5563.8	4621.2	3817.5	2963.4
20°	10175.6	9934.0	9615.0	8843.1	8078.8	7594.1	7183.6	6250.6	5161.2	4237.6	3318.8
22.5°	11602.9	11430.8	10972.9	9954.6	8830.4	8416.8	7914.7	6792.2	5508.6	4416.0	3359.8
25°	12872.2	12602.3	12027.6	10816.6	9665.6	8961.5	8345.7	7085.7	5636.4	4428.5	3291.9
27.5°	13615.8	13263.8	12588.0	11268.1	9954.6	9176.2	8494.1	7136.3	5555.9	4261.3	3044.0
30°	14119.4	13418.6	12671.7	11273.0	9863.0	9067.3	8360.0	6882.1	5221.2	3879.2	2627.2
32.5°	13289.0	12883.3	12169.6	10824.4	9364.1	8587.3	7884.7	6331.1	4698.6	3312.3	1828.3
35°	12245.5	11917.0	11296.6	9960.9	8615.6	7883.1	7137.9	5623.8	4018.1	2276.7	836.7
37.5°	11032.9	10775.6	10107.7	8887.2	7703.2	6986.2	6239.5	4793.3	2829.3	1128.9	508.4
40°	9390.9	9173.0	8625.2	7644.7	6553.7	5871.8	5183.4	3585.5	1536.2	629.9	331.5
42.5°	7718.9	7535.8	7036.8	6189.1	5230.7	4668.6	4062.4	2185.0	764.1	396.3	184.8
45°	5025.4	4796.5	4528.0	4139.8	3666.1	3320.3	2605.2	1054.6	453.0	221.0	105.8
47.5°	2881.3	2729.8	2289.3	1806.2	1466.7	1338.8	974.2	491.1	249.4	127.8	64.8
50°	1294.7	1196.8	1004.2	817.8	592.1	462.7	393.2	246.2	123.2	69.5	44.2
52.5°	318.9	325.2	307.8	270.0	240.0	203.7	176.9	115.3	64.8	42.6	28.4
55°	105.8	107.4	97.9	93.1	85.3	79.0	72.6	52.2	39.4	37.8	14.2
57.5°	37.8	37.8	39.4	36.3	34.7	33.1	31.5	26.8	23.7	14.2	7.9
60°	14.2	14.2	14.2	15.8	15.8	15.8	17.4	15.8	11.0	7.9	6.3
62.5°	6.3	6.3	6.3	6.3	7.9	7.9	9.5	7.9	6.3	6.3	4.7
65°	3.1	3.1	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
67.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7	4.7
70°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7	4.7
72.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7	4.7
75°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7
77.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1	4.7
80°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1	4.7
82.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1	4.7
85°	0.0	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	4.7
87.5°	0.0	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212390

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1
2.5°	443.6	434.1	415.2	401.1	390.0	388.4	378.9	363.2	356.8	345.7	336.2
5°	546.3	522.6	492.6	464.2	443.6	432.6	399.5	369.5	352.0	334.7	318.9
7.5°	656.7	603.1	550.9	505.2	476.8	459.5	420.0	371.1	339.4	314.2	293.7
10°	795.8	685.3	595.2	524.1	486.3	462.7	415.2	356.8	317.3	287.4	266.9
12.5°	1113.1	811.5	636.3	533.6	486.3	453.0	396.3	337.8	293.7	257.4	235.2
15°	1656.2	1133.6	754.6	538.4	470.6	432.6	367.9	306.3	262.1	224.2	203.7
17.5°	2167.7	1492.0	942.5	571.6	461.1	402.6	330.0	270.0	224.2	187.9	170.5
20°	2433.0	1670.4	1046.7	596.8	445.2	364.8	285.8	230.5	186.3	154.8	140.5
22.5°	2439.3	1654.6	996.3	538.4	386.8	312.6	244.7	189.5	151.5	124.7	113.7
25°	2289.3	1463.5	819.4	420.0	312.6	262.1	203.7	154.8	118.4	99.5	91.6
27.5°	2006.8	1184.2	604.7	303.2	244.7	208.4	159.5	118.4	90.0	77.4	72.6
30°	1552.0	732.6	334.7	224.2	184.8	156.4	115.3	79.0	68.0	60.1	56.9
32.5°	770.5	358.4	236.8	159.5	126.3	99.5	72.6	58.5	52.2	47.3	45.7
35°	418.4	257.4	148.3	96.3	75.8	63.2	48.9	41.0	37.8	36.3	36.3
37.5°	292.1	153.2	90.0	58.5	47.3	42.6	34.7	29.9	28.4	28.4	28.4
40°	161.1	91.6	55.3	37.8	31.5	28.4	23.7	22.0	22.0	22.0	23.7
42.5°	93.1	56.9	37.8	26.8	22.0	20.5	17.4	15.8	17.4	17.4	18.9
45°	60.1	42.6	25.3	18.9	15.8	14.2	12.6	12.6	14.2	14.2	15.8
47.5°	42.6	29.9	17.4	12.6	9.5	9.5	9.5	9.5	11.0	12.6	14.2
50°	25.3	15.8	9.5	7.9	6.3	6.3	6.3	7.9	9.5	9.5	11.0
52.5°	14.2	9.5	6.3	6.3	4.7	4.7	6.3	6.3	7.9	9.5	11.0
55°	7.9	6.3	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9	9.5
57.5°	6.3	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9	7.9
60°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9	7.9
62.5°	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	7.9
65°	4.7	4.7	4.7	6.3	4.7	6.3	6.3	6.3	6.3	6.3	7.9
67.5°	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.9
70°	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.9
72.5°	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.9
75°	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
77.5°	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
80°	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
82.5°	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
85°	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
87.5°	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212390

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1
2.5°	333.1	322.1	314.2	311.1	304.7	306.3	301.6	298.4	288.9	288.9	282.7
5°	307.8	293.7	284.2	279.5	273.2	271.6	266.9	262.1	252.6	251.0	246.2
7.5°	281.0	266.9	255.9	251.0	244.7	243.1	236.8	233.6	225.7	224.2	219.4
10°	252.6	236.8	227.3	222.6	216.3	216.3	211.6	208.4	202.1	202.1	198.9
12.5°	222.6	208.4	202.1	195.8	192.6	192.6	189.5	186.3	181.6	183.2	181.6
15°	191.0	180.0	173.7	170.5	169.0	169.0	167.4	165.9	162.6	165.9	162.6
17.5°	161.1	153.2	148.3	146.8	145.2	145.2	145.2	146.8	145.2	148.3	148.3
20°	132.6	126.3	123.2	123.2	121.5	124.7	124.7	127.8	127.8	132.6	134.2
22.5°	108.9	104.2	102.6	102.6	102.6	105.8	107.4	110.5	112.1	116.8	119.9
25°	86.9	85.3	85.3	85.3	86.9	90.0	93.1	96.3	97.9	104.2	105.8
27.5°	71.1	69.5	71.1	71.1	72.6	77.4	80.5	83.7	86.9	91.6	94.8
30°	56.9	56.9	58.5	60.1	61.6	64.8	69.5	72.6	75.8	80.5	83.7
32.5°	45.7	47.3	48.9	50.4	50.4	55.3	58.5	63.2	64.8	69.5	72.6
35°	37.8	39.4	41.0	42.6	42.6	47.3	50.4	53.7	56.9	60.1	63.2
37.5°	29.9	31.5	34.7	36.3	36.3	41.0	42.6	45.7	48.9	52.2	55.3
40°	25.3	26.8	29.9	29.9	31.5	34.7	36.3	39.4	42.6	45.7	48.9
42.5°	20.5	22.0	25.3	26.8	26.8	29.9	31.5	34.7	36.3	39.4	41.0
45°	18.9	18.9	22.0	22.0	23.7	25.3	28.4	29.9	31.5	34.7	36.3
47.5°	15.8	17.4	18.9	20.5	20.5	22.0	23.7	25.3	26.8	29.9	31.5
50°	12.6	14.2	17.4	17.4	17.4	20.5	22.0	23.7	23.7	25.3	26.8
52.5°	12.6	12.6	14.2	15.8	15.8	17.4	18.9	20.5	20.5	22.0	23.7
55°	11.0	11.0	12.6	14.2	14.2	15.8	17.4	17.4	18.9	18.9	20.5
57.5°	9.5	11.0	12.6	12.6	12.6	14.2	15.8	15.8	17.4	17.4	18.9
60°	9.5	11.0	11.0	12.6	12.6	14.2	14.2	14.2	15.8	15.8	15.8
62.5°	9.5	9.5	11.0	11.0	11.0	12.6	12.6	14.2	14.2	14.2	14.2
65°	9.5	9.5	11.0	11.0	11.0	12.6	12.6	12.6	12.6	12.6	12.6
67.5°	7.9	9.5	9.5	9.5	11.0	11.0	11.0	11.0	11.0	11.0	11.0
70°	7.9	7.9	9.5	9.5	9.5	11.0	11.0	11.0	11.0	11.0	11.0
72.5°	7.9	7.9	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
75°	7.9	7.9	7.9	7.9	7.9	9.5	9.5	9.5	9.5	7.9	7.9
77.5°	6.3	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	6.3
80°	6.3	6.3	7.9	6.3	7.9	7.9	7.9	7.9	6.3	6.3	6.3
82.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	4.7	4.7
85°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	4.7	4.7	4.7	3.1
87.5°	6.3	6.3	6.3	6.3	6.3	6.3	4.7	4.7	4.7	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212390

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	355.1	355.1	355.1	355.1	355.1	355.1	355.1	355.1
2.5°	279.5	282.7	279.5	282.7	274.8	277.9	281.0	273.2
5°	243.1	240.0	241.5	244.7	238.3	240.0	241.5	235.2
7.5°	217.8	219.4	216.3	219.4	214.7	216.3	217.8	213.2
10°	197.4	198.9	197.4	198.9	194.2	197.4	198.9	194.2
12.5°	178.4	181.6	180.0	183.2	178.4	181.6	184.8	178.4
15°	164.2	167.4	165.9	169.0	165.9	169.0	172.1	167.4
17.5°	149.9	153.2	153.2	156.4	154.8	158.0	161.1	156.4
20°	135.7	140.5	140.5	143.6	143.6	145.2	149.9	145.2
22.5°	123.2	127.8	127.8	131.0	131.0	134.2	137.3	134.2
25°	108.9	115.3	116.8	119.9	119.9	123.2	127.8	124.7
27.5°	99.5	104.2	105.8	108.9	110.5	113.7	116.8	113.7
30°	86.9	93.1	94.8	97.9	99.5	104.2	105.8	104.2
32.5°	77.4	82.1	83.7	86.9	90.0	93.1	96.3	94.8
35°	68.0	72.6	74.2	77.4	79.0	83.7	86.9	85.3
37.5°	60.1	64.8	66.4	68.0	69.5	74.2	77.4	75.8
40°	52.2	55.3	56.9	60.1	61.6	64.8	68.0	68.0
42.5°	45.7	48.9	50.4	52.2	53.7	56.9	60.1	58.5
45°	39.4	42.6	44.2	45.7	47.3	48.9	52.2	50.4
47.5°	33.1	36.3	37.8	39.4	41.0	42.6	45.7	44.2
50°	28.4	31.5	31.5	33.1	34.7	36.3	39.4	37.8
52.5°	25.3	26.8	28.4	28.4	29.9	31.5	34.7	33.1
55°	22.0	23.7	23.7	25.3	25.3	26.8	28.4	28.4
57.5°	18.9	20.5	20.5	22.0	22.0	23.7	25.3	25.3
60°	17.4	17.4	18.9	18.9	18.9	20.5	20.5	20.5
62.5°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
65°	12.6	12.6	12.6	12.6	12.6	12.6	12.6	12.6
67.5°	11.0	11.0	11.0	11.0	11.0	9.5	9.5	9.5
70°	9.5	9.5	9.5	9.5	9.5	7.9	7.9	7.9
72.5°	9.5	9.5	7.9	7.9	7.9	7.9	7.9	6.3
75°	7.9	7.9	7.9	7.9	6.3	6.3	6.3	6.3
77.5°	6.3	6.3	6.3	6.3	4.7	4.7	4.7	4.7
80°	6.3	4.7	4.7	4.7	4.7	4.7	4.7	3.1
82.5°	4.7	4.7	4.7	3.1	3.1	3.1	3.1	3.1
85°	3.1	3.1	3.1	3.1	1.6	1.6	1.6	1.6
87.5°	3.1	1.6	1.6	1.6	1.6	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)