

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212394

Luminaire Tested: **LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3464.7 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212394

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212394

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39167	39167	39167
5°	102993	37313	24360
10°	403789	32285	20284
15°	743380	25444	17962
20°	934133	17979	16350
25°	1117345	11865	14580
30°	1174977	7450	12775
35°	1184476	4506	11069
40°	1089937	3010	9421
45°	775462	2178	7809
50°	320443	1658	6466
55°	18477	1605	5607
60°	2131	1531	4611
65°	711	1811	3278
70°	878	1784	2238
75°	1160	2358	2358
80°	0	3515	2622
85°	0	7003	3446

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212394

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.5	1.8
10°-20°	507.7	14.7
20°-30°	1050.1	30.3
30°-40°	1143.2	33.0
40°-50°	626.8	18.1
50°-60°	54.2	1.6
60°-70°	8.8	0.3
70°-80°	6.3	0.2
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1621.4	46.8
0°-40°	2764.5	79.8
0°-60°	3445.6	99.4
0°-90°	3464.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3464.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	404	404	404	404	404	
5°	1059	724	384	265	250	193
15°	7412	3116	254	171	179	2070
25°	10453	4144	111	105	136	4720
35°	10016	1134	38	60	94	6147
45°	5660	116	16	33	57	4320
55°	109	13	10	21	33	374
65°	3	5	8	13	14	4
75°	3	5	6	10	6	2
85°	0	3	6	5	3	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212394

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3
2.5°	635.8	613.6	610.4	613.6	597.7	596.2	599.3	586.6	575.5	564.5	554.9
5°	1059.1	1013.1	998.9	979.9	932.3	916.4	913.2	862.5	813.4	767.4	724.5
7.5°	2058.0	1966.0	1916.8	1821.7	1675.9	1610.8	1576.0	1409.6	1254.1	1113.0	984.6
10°	4104.8	3863.8	3746.5	3567.4	3248.7	3091.7	2977.5	2559.0	2146.8	1750.4	1401.5
12.5°	5990.0	5856.8	5684.0	5588.8	5072.0	4873.8	4685.1	4104.8	3477.0	2836.4	2200.7
15°	7412.1	7217.1	7033.2	6988.9	6583.0	6351.5	6142.1	5541.3	4794.5	3979.6	3115.5
17.5°	8247.7	8108.2	7933.8	7849.7	7374.2	7187.1	6949.2	6367.4	5641.1	4829.3	3825.9
20°	9061.1	8854.9	8609.2	8482.4	7956.0	7740.4	7470.9	6858.8	6089.9	5227.4	4223.7
22.5°	9804.7	9538.3	9189.5	8992.9	8401.4	8163.7	7862.5	7199.7	6367.4	5381.1	4257.1
25°	10453.2	10212.1	9747.6	9403.5	8705.9	8425.2	8074.9	7382.1	6467.2	5368.5	4144.5
27.5°	10576.8	10415.1	9998.1	9600.1	8812.2	8499.9	8136.7	7420.0	6397.5	5192.6	3841.6
30°	10503.8	10329.5	9994.9	9589.1	8767.8	8452.3	8074.9	7258.4	6124.7	4781.8	3286.7
32.5°	10327.9	10177.2	9777.8	9349.6	8549.0	8220.7	7822.8	6879.4	5657.1	4128.6	2417.9
35°	10015.6	9788.8	9306.8	8954.9	8201.7	7864.0	7377.3	6373.7	4957.9	2968.0	1133.6
37.5°	9379.7	9159.4	8812.2	8487.1	7753.0	7355.1	6841.3	5669.6	3675.1	1618.8	700.7
40°	8618.7	8428.5	8125.6	7810.1	7053.8	6595.6	6029.6	4431.5	2162.6	911.6	431.3
42.5°	7791.1	7594.6	7252.0	6884.2	6059.8	5576.3	4964.1	2868.2	1140.0	537.4	234.7
45°	5660.2	5484.3	5235.3	4970.5	4493.2	4144.5	3339.0	1506.2	631.0	285.4	115.8
47.5°	3873.4	3664.1	3204.3	2647.7	2146.8	1836.0	1381.0	653.2	323.4	142.7	68.2
50°	2126.2	1904.1	1669.6	1300.1	870.4	715.1	556.5	315.5	145.9	71.3	38.1
52.5°	521.7	461.4	421.8	388.4	307.6	277.5	234.7	131.5	66.6	39.7	26.9
55°	109.4	101.5	96.7	95.1	87.2	84.1	72.9	50.7	36.5	25.3	12.8
57.5°	31.7	30.1	31.7	31.7	31.7	30.1	30.1	22.2	20.7	12.8	7.9
60°	11.0	11.0	11.0	12.8	12.8	12.8	14.3	14.3	11.0	7.9	6.3
62.5°	4.7	4.7	4.7	6.3	6.3	7.9	7.9	7.9	6.3	6.3	4.7
65°	3.1	3.1	3.1	3.1	4.7	4.7	4.7	4.7	4.7	4.7	4.7
67.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7
70°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7
72.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7
75°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7
77.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1	4.7
80°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1	3.1
82.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	1.6	3.1	3.1	3.1
85°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	1.6	3.1	3.1	3.1
87.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	1.6	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212394

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3
2.5°	527.9	512.1	493.1	472.5	469.4	458.2	442.3	420.2	412.2	396.5	382.1
5°	662.8	619.9	575.5	535.8	523.3	505.7	477.3	437.6	412.2	383.7	359.9
7.5°	843.4	745.2	654.7	583.4	561.2	532.7	488.3	437.6	399.6	359.9	328.2
10°	1084.4	884.7	729.3	613.6	577.1	539.0	480.4	418.5	374.2	328.2	294.8
12.5°	1549.1	1089.2	799.1	629.4	578.7	529.5	455.0	388.4	337.7	291.7	258.5
15°	2202.3	1477.7	940.2	640.6	562.8	502.6	415.4	347.2	296.5	253.7	221.9
17.5°	2754.0	1845.5	1128.9	672.3	551.7	467.8	369.4	299.6	250.5	212.5	187.1
20°	3023.5	2010.4	1214.5	677.0	520.1	415.4	315.5	248.9	206.2	174.4	152.1
22.5°	2991.8	1954.9	1135.1	593.0	439.2	350.5	261.6	201.3	164.9	139.6	123.7
25°	2779.4	1713.8	926.0	453.5	342.4	283.8	204.6	157.0	128.4	111.0	98.3
27.5°	2422.7	1376.1	675.4	320.3	260.0	215.6	152.1	120.5	98.3	85.7	77.7
30°	1866.2	880.0	388.4	230.0	188.7	153.7	114.2	87.2	74.5	66.6	60.3
32.5°	962.4	428.1	258.5	164.9	133.2	111.0	79.2	63.4	55.5	50.7	47.6
35°	527.9	304.5	179.1	106.1	85.7	71.3	53.9	44.4	41.2	38.1	38.1
37.5°	363.0	188.7	99.9	63.4	52.3	44.4	36.5	31.7	30.1	30.1	30.1
40°	209.3	99.9	57.0	39.7	33.2	30.1	25.3	23.8	23.8	23.8	25.3
42.5°	107.7	58.6	38.1	26.9	23.8	20.7	17.4	17.4	17.4	19.1	20.7
45°	63.4	39.7	25.3	17.4	15.9	14.3	12.8	12.8	14.3	15.9	17.4
47.5°	39.7	26.9	15.9	11.0	9.5	9.5	9.5	9.5	11.0	12.8	14.3
50°	26.9	14.3	9.5	6.3	6.3	6.3	6.3	7.9	9.5	11.0	12.8
52.5°	14.3	7.9	6.3	4.7	4.7	4.7	6.3	6.3	7.9	9.5	11.0
55°	7.9	6.3	4.7	4.7	4.7	4.7	4.7	6.3	7.9	9.5	11.0
57.5°	6.3	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9	9.5
60°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9	9.5
62.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9	7.9
65°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9	7.9
67.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	7.9
70°	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	7.9
72.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3
75°	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	7.9
77.5°	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3
80°	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3
82.5°	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3
85°	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3	6.3
87.5°	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212394

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3
2.5°	374.2	361.5	348.9	348.9	342.4	333.0	329.8	320.3	313.9	310.8	307.6
5°	342.4	323.4	306.0	304.5	296.5	285.4	280.7	271.0	264.8	261.6	260.0
7.5°	306.0	287.0	269.5	266.4	260.0	252.1	247.3	239.4	236.2	233.1	231.6
10°	271.0	252.1	239.4	236.2	231.6	225.1	220.4	215.6	212.5	210.9	210.9
12.5°	236.2	221.9	210.9	207.8	204.6	199.7	196.6	193.4	191.8	191.8	191.8
15°	204.6	191.8	182.4	182.4	179.1	175.9	175.9	172.8	171.2	172.8	174.4
17.5°	172.8	163.3	155.3	155.3	153.7	152.1	152.1	152.1	153.7	155.3	158.6
20°	142.7	134.8	131.5	131.5	129.9	131.5	131.5	133.2	134.8	139.6	144.2
22.5°	115.8	111.0	107.7	109.4	109.4	111.0	112.6	115.8	118.9	123.7	128.4
25°	93.6	90.4	88.8	90.4	92.0	93.6	96.7	99.9	104.6	109.4	115.8
27.5°	74.5	72.9	72.9	74.5	76.1	79.2	84.1	87.2	92.0	96.7	103.0
30°	60.3	58.6	60.3	63.4	65.0	68.2	71.3	76.1	80.8	85.7	92.0
32.5°	47.6	49.1	50.7	52.3	53.9	58.6	61.9	65.0	69.8	74.5	80.8
35°	39.7	41.2	42.9	44.4	46.0	49.1	52.3	55.5	60.3	65.0	71.3
37.5°	31.7	33.2	34.8	38.1	39.7	41.2	46.0	47.6	52.3	55.5	61.9
40°	26.9	28.5	30.1	31.7	33.2	36.5	39.7	41.2	44.4	49.1	53.9
42.5°	22.2	23.8	25.3	26.9	28.5	31.7	33.2	36.5	39.7	42.9	46.0
45°	19.1	20.7	22.2	23.8	25.3	26.9	28.5	31.7	33.2	36.5	39.7
47.5°	15.9	17.4	20.7	20.7	22.2	23.8	25.3	26.9	30.1	31.7	34.8
50°	14.3	15.9	17.4	19.1	19.1	20.7	22.2	23.8	25.3	26.9	30.1
52.5°	12.8	14.3	15.9	15.9	17.4	19.1	20.7	20.7	22.2	23.8	25.3
55°	11.0	12.8	14.3	14.3	15.9	17.4	17.4	19.1	20.7	20.7	22.2
57.5°	11.0	11.0	12.8	12.8	14.3	14.3	15.9	17.4	17.4	19.1	20.7
60°	9.5	11.0	11.0	12.8	12.8	14.3	14.3	15.9	15.9	17.4	17.4
62.5°	9.5	9.5	11.0	11.0	12.8	12.8	14.3	14.3	14.3	15.9	15.9
65°	9.5	9.5	11.0	11.0	11.0	12.8	12.8	12.8	12.8	14.3	14.3
67.5°	7.9	9.5	9.5	11.0	11.0	11.0	11.0	11.0	12.8	12.8	12.8
70°	7.9	9.5	9.5	9.5	9.5	11.0	11.0	11.0	11.0	11.0	11.0
72.5°	7.9	7.9	7.9	7.9	9.5	9.5	9.5	9.5	9.5	9.5	9.5
75°	7.9	7.9	7.9	7.9	7.9	9.5	9.5	9.5	9.5	9.5	9.5
77.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
80°	6.3	6.3	6.3	6.3	6.3	7.9	6.3	6.3	6.3	6.3	6.3
82.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	4.7	4.7
85°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	4.7	4.7	4.7	4.7
87.5°	6.3	6.3	6.3	4.7	4.7	4.7	4.7	4.7	4.7	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212394

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	404.3	404.3	404.3	404.3	404.3	404.3	404.3	404.3
2.5°	302.9	299.6	302.9	299.6	299.6	293.3	298.0	294.8
5°	255.3	252.1	255.3	253.7	250.5	248.9	252.1	250.5
7.5°	228.3	225.1	228.3	228.3	225.1	223.5	226.7	225.1
10°	207.8	206.2	207.8	207.8	206.2	204.6	207.8	206.2
12.5°	190.2	188.7	191.8	191.8	190.2	190.2	193.4	190.2
15°	174.4	174.4	177.5	177.5	177.5	177.5	180.8	179.1
17.5°	158.6	161.8	164.9	166.5	166.5	166.5	169.7	169.7
20°	145.9	149.0	152.1	153.7	155.3	155.3	158.6	158.6
22.5°	131.5	134.8	139.6	141.1	142.7	144.2	147.5	147.5
25°	118.9	122.1	126.8	128.4	131.5	133.2	136.4	136.4
27.5°	106.1	111.0	114.2	117.3	118.9	122.1	125.2	125.2
30°	95.1	99.9	103.0	106.1	107.7	111.0	114.2	114.2
32.5°	84.1	88.8	92.0	95.1	98.3	99.9	104.6	104.6
35°	74.5	77.7	82.4	84.1	87.2	90.4	93.6	93.6
37.5°	65.0	68.2	71.3	74.5	77.7	79.2	82.4	84.1
40°	57.0	60.3	63.4	65.0	68.2	71.3	72.9	74.5
42.5°	49.1	52.3	55.5	57.0	60.3	61.9	65.0	65.0
45°	42.9	46.0	47.6	49.1	52.3	53.9	57.0	57.0
47.5°	36.5	39.7	41.2	42.9	44.4	46.0	49.1	49.1
50°	31.7	33.2	34.8	36.5	38.1	41.2	42.9	42.9
52.5°	26.9	30.1	30.1	31.7	33.2	34.8	36.5	38.1
55°	23.8	25.3	26.9	26.9	28.5	30.1	31.7	33.2
57.5°	20.7	22.2	23.8	23.8	25.3	25.3	26.9	28.5
60°	19.1	19.1	20.7	20.7	20.7	22.2	22.2	23.8
62.5°	15.9	15.9	17.4	17.4	17.4	17.4	17.4	17.4
65°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
67.5°	12.8	12.8	12.8	12.8	11.0	11.0	11.0	11.0
70°	11.0	11.0	11.0	11.0	9.5	9.5	9.5	7.9
72.5°	9.5	9.5	9.5	9.5	7.9	7.9	6.3	6.3
75°	7.9	7.9	7.9	7.9	7.9	6.3	6.3	6.3
77.5°	7.9	6.3	6.3	6.3	6.3	6.3	6.3	4.7
80°	6.3	6.3	4.7	4.7	4.7	4.7	4.7	4.7
82.5°	4.7	4.7	4.7	4.7	3.1	3.1	3.1	3.1
85°	4.7	3.1	3.1	3.1	3.1	3.1	3.1	3.1
87.5°	3.1	1.6	1.6	1.6	1.6	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)