

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212396

Luminaire Tested: **LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3218.9 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212396

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212396

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38556	38556	38556
5°	90370	36389	25439
10°	357063	31980	21209
15°	660819	25605	18614
20°	847329	18639	16835
25°	1013800	13222	14922
30°	1077982	8692	13121
35°	1104778	5251	11436
40°	1011316	3402	9826
45°	729758	2384	8056
50°	318589	1929	6692
55°	21974	1605	5607
60°	4011	1531	4611
65°	1444	1444	3278
70°	1331	1784	2238
75°	1160	2358	2358
80°	0	3515	2622
85°	0	7003	1778



TEST NUMBER: P1212396

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	1.8
10°-20°	455.6	14.2
20°-30°	953.9	29.6
30°-40°	1061.8	33.0
40°-50°	609.5	18.9
50°-60°	60.9	1.9
60°-70°	9.5	0.3
70°-80°	6.0	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1467.5	45.6
0°-40°	2529.3	78.6
0°-60°	3199.7	99.4
0°-90°	3218.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3218.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	398	398	398	398	398	
5°	929	641	374	273	262	170
15°	6589	2631	255	179	186	1863
25°	9484	3620	124	109	140	4295
35°	9342	1105	44	63	97	5704
45°	5327	133	17	35	59	4067
55°	130	19	10	21	33	388
65°	6	5	6	13	14	8
75°	3	3	6	8	6	2
85°	0	3	6	5	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212396

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0
2.5°	594.7	582.0	569.3	561.4	553.5	564.5	556.6	553.5	531.2	520.1	510.6
5°	929.3	905.5	870.5	842.0	813.5	819.8	797.6	770.7	715.2	675.5	640.7
7.5°	1793.5	1734.8	1627.0	1522.4	1417.7	1398.6	1328.8	1208.4	1052.9	935.6	834.1
10°	3629.8	3452.2	3254.0	3039.9	2789.3	2719.6	2546.8	2220.1	1863.3	1455.8	1160.8
12.5°	5358.3	5277.4	5044.3	4766.8	4495.7	4329.1	4150.0	3610.7	3044.7	2388.2	1839.5
15°	6588.9	6539.8	6335.2	6083.0	5791.2	5683.4	5464.6	4927.0	4211.7	3426.9	2630.8
17.5°	7500.7	7416.6	7202.5	6928.2	6582.5	6490.6	6228.9	5694.5	4952.3	4164.2	3280.9
20°	8219.1	8166.8	7889.3	7559.4	7145.5	7034.5	6728.5	6171.9	5364.7	4527.4	3628.2
22.5°	8864.5	8775.7	8434.7	8041.4	7568.9	7450.0	7109.0	6498.5	5631.0	4698.6	3690.1
25°	9484.5	9349.8	8935.9	8420.5	7865.5	7703.7	7329.5	6682.5	5729.4	4713.0	3620.4
27.5°	9665.3	9597.1	9214.9	8615.5	7973.2	7791.0	7400.8	6723.7	5692.9	4582.9	3369.8
30°	9636.7	9579.7	9260.9	8634.6	7954.3	7762.3	7365.9	6596.8	5480.4	4243.6	2927.3
32.5°	9546.4	9524.2	9138.9	8469.7	7776.6	7567.3	7139.1	6281.2	5082.4	3726.5	2139.2
35°	9341.7	9254.6	8774.1	8144.5	7478.5	7248.5	6764.8	5829.3	4557.5	2713.3	1105.4
37.5°	8742.3	8674.2	8295.1	7743.3	7094.8	6799.8	6289.2	5245.8	3528.4	1542.9	661.2
40°	7997.0	7963.8	7665.6	7172.5	6479.5	6146.5	5591.4	4292.7	2153.5	876.9	436.1
42.5°	7232.6	7223.2	6904.4	6389.0	5637.4	5255.2	4679.7	2895.7	1144.9	529.7	252.1
45°	5326.6	5383.8	5161.7	4852.5	4278.4	4000.8	3254.0	1492.2	659.6	293.4	133.2
47.5°	3736.1	3672.6	3279.4	2738.7	2213.7	1874.4	1417.7	705.6	352.0	153.9	76.1
50°	2113.9	2125.0	1769.7	1432.0	938.7	743.7	564.5	355.1	169.7	80.8	46.0
52.5°	551.9	577.2	497.9	428.1	364.8	296.6	239.4	153.9	80.8	47.6	30.1
55°	130.1	134.8	125.2	117.3	111.0	98.3	87.2	66.6	44.4	30.1	19.1
57.5°	46.0	47.6	46.0	46.0	44.4	42.9	39.7	35.0	26.9	19.1	12.8
60°	20.7	22.2	20.7	22.2	22.2	22.2	22.2	22.2	15.9	11.0	7.9
62.5°	9.5	9.5	9.5	9.5	11.0	11.0	12.8	12.8	9.5	7.9	6.3
65°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	4.7
67.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
70°	4.7	4.7	4.7	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.7
72.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
75°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
77.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1	3.1
80°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	1.6	3.1	3.1	3.1
82.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	1.6	3.1	3.1	3.1
85°	0.0	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1
87.5°	0.0	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212396

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0
2.5°	493.1	491.6	474.1	461.5	455.2	445.6	434.6	418.7	401.1	385.4	378.9
5°	599.5	578.8	542.3	512.2	497.9	483.7	458.3	429.8	402.7	374.2	360.0
7.5°	737.4	677.1	605.8	550.3	526.5	502.8	466.2	426.5	390.1	352.0	331.4
10°	926.1	786.6	662.9	574.1	539.1	507.5	455.2	405.9	366.3	325.1	298.1
12.5°	1324.1	978.4	723.1	585.1	539.1	497.9	434.6	377.4	333.0	290.1	264.8
15°	1907.6	1320.9	854.8	596.3	528.1	475.7	402.7	341.0	293.4	255.3	231.6
17.5°	2378.6	1636.4	1018.1	624.8	513.8	445.6	361.6	296.6	252.1	217.2	198.3
20°	2616.5	1769.7	1092.6	629.6	479.0	398.0	312.4	250.6	210.9	180.8	164.9
22.5°	2611.7	1726.9	1025.9	551.9	420.2	344.1	263.2	206.2	174.5	150.6	138.0
25°	2446.8	1528.7	856.4	440.8	339.4	285.4	214.0	166.5	141.1	123.7	112.6
27.5°	2137.6	1241.6	639.1	326.7	264.8	225.2	166.5	133.2	112.6	99.9	92.0
30°	1677.7	831.0	402.7	242.6	201.4	169.7	128.5	103.0	88.8	77.7	72.9
32.5°	924.5	433.0	271.2	177.7	147.5	123.7	95.1	74.5	65.0	57.0	55.5
35°	510.6	306.0	193.4	118.9	98.3	84.1	65.0	53.9	47.6	44.4	44.4
37.5°	361.6	196.6	115.8	74.5	63.4	55.5	44.4	38.1	36.5	35.0	35.0
40°	217.2	115.8	69.8	49.1	42.9	38.1	33.2	28.5	28.5	26.9	28.5
42.5°	118.9	69.8	47.6	35.0	30.1	28.5	23.8	22.2	22.2	22.2	23.8
45°	71.3	46.0	33.2	25.3	22.2	19.1	17.4	15.9	17.4	17.4	19.1
47.5°	46.0	33.2	22.2	15.9	14.3	12.8	11.0	12.8	12.8	14.3	15.9
50°	31.7	20.7	14.3	9.5	9.5	7.9	9.5	9.5	11.0	12.8	14.3
52.5°	20.7	14.3	9.5	7.9	6.3	6.3	6.3	7.9	9.5	11.0	12.8
55°	12.8	9.5	7.9	6.3	6.3	6.3	6.3	6.3	7.9	9.5	11.0
57.5°	9.5	7.9	6.3	4.7	4.7	4.7	6.3	6.3	7.9	7.9	9.5
60°	6.3	6.3	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9	9.5
62.5°	6.3	6.3	4.7	4.7	4.7	4.7	6.3	6.3	6.3	7.9	7.9
65°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	7.9
67.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9
70°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	7.9
72.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3
75°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3
77.5°	3.1	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3
80°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3
82.5°	3.1	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3
85°	3.1	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3
87.5°	3.1	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212396

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0
2.5°	371.1	360.0	350.5	353.6	347.3	336.1	333.0	325.1	315.7	314.0	314.0
5°	344.1	326.7	312.4	310.8	304.5	291.9	288.6	280.7	272.8	271.2	269.7
7.5°	310.8	291.9	279.1	275.9	271.2	260.0	258.5	250.6	245.9	242.6	242.6
10°	277.5	260.0	249.0	247.4	244.3	234.7	233.1	226.8	222.1	220.4	218.8
12.5°	245.9	231.6	222.1	220.4	217.2	209.3	207.8	203.0	199.9	198.3	198.3
15°	215.6	203.0	195.0	193.4	191.8	184.0	184.0	180.8	179.2	179.2	180.8
17.5°	185.6	174.5	168.0	166.5	166.5	160.2	161.8	160.2	160.2	160.2	163.3
20°	155.4	145.9	141.1	142.7	139.6	138.0	139.6	139.6	139.6	142.7	147.5
22.5°	130.1	122.1	117.3	118.9	118.9	117.3	118.9	120.5	123.7	128.5	133.2
25°	106.3	99.9	98.3	99.9	99.9	99.9	103.0	106.3	109.4	114.2	118.9
27.5°	85.7	80.8	80.8	82.5	84.1	84.1	88.8	92.0	96.7	101.5	106.3
30°	68.2	66.6	66.6	69.8	69.8	71.3	77.7	80.8	84.1	88.8	93.6
32.5°	53.9	53.9	55.5	58.8	58.8	61.9	66.6	69.8	72.9	77.7	82.5
35°	44.4	46.0	47.6	49.1	50.7	52.3	57.0	60.3	63.4	68.2	71.3
37.5°	36.5	38.1	39.7	42.9	42.9	44.4	49.1	52.3	53.9	58.8	63.4
40°	30.1	31.7	33.2	36.5	36.5	38.1	42.9	44.4	46.0	50.7	55.5
42.5°	25.3	26.9	28.5	30.1	31.7	33.2	36.5	38.1	41.2	44.4	47.6
45°	20.7	22.2	23.8	25.3	26.9	28.5	30.1	33.2	35.0	38.1	41.2
47.5°	17.4	19.1	20.7	22.2	23.8	23.8	26.9	28.5	30.1	33.2	36.5
50°	15.9	17.4	19.1	19.1	20.7	22.2	23.8	25.3	26.9	28.5	31.7
52.5°	12.8	14.3	15.9	17.4	17.4	19.1	20.7	22.2	23.8	25.3	26.9
55°	12.8	12.8	14.3	15.9	15.9	17.4	19.1	20.7	20.7	22.2	23.8
57.5°	11.0	12.8	12.8	14.3	14.3	15.9	17.4	17.4	19.1	19.1	20.7
60°	9.5	11.0	12.8	12.8	12.8	14.3	14.3	15.9	15.9	17.4	17.4
62.5°	9.5	11.0	11.0	12.8	12.8	12.8	14.3	14.3	14.3	15.9	15.9
65°	9.5	9.5	11.0	11.0	11.0	11.0	12.8	12.8	12.8	14.3	14.3
67.5°	7.9	9.5	9.5	9.5	11.0	11.0	11.0	11.0	11.0	12.8	12.8
70°	7.9	7.9	9.5	9.5	9.5	9.5	9.5	11.0	11.0	11.0	11.0
72.5°	7.9	7.9	7.9	7.9	9.5	9.5	9.5	9.5	9.5	9.5	9.5
75°	6.3	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
77.5°	6.3	6.3	6.3	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
80°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
82.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	4.7	4.7
85°	6.3	6.3	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
87.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212396

CATALOG NUMBER: LDSQA4A35940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0
2.5°	307.6	304.5	302.9	307.6	301.3	304.5	302.9	304.5
5°	264.8	261.6	260.0	264.8	258.5	261.6	258.5	261.6
7.5°	237.8	236.2	234.7	237.8	233.1	236.2	234.7	236.2
10°	215.6	214.0	212.5	217.2	212.5	215.6	214.0	215.6
12.5°	196.6	196.6	195.0	198.3	195.0	198.3	196.6	198.3
15°	179.2	180.8	179.2	182.4	180.8	184.0	182.4	185.6
17.5°	164.9	166.5	166.5	171.2	169.7	174.5	172.8	174.5
20°	150.6	152.3	153.9	157.0	157.0	161.8	160.2	163.3
22.5°	136.4	139.6	139.6	144.2	144.2	149.0	149.0	150.6
25°	122.1	126.8	128.5	131.7	133.2	138.0	138.0	139.6
27.5°	111.0	114.2	115.8	120.5	122.1	126.8	126.8	130.1
30°	98.3	103.0	104.8	107.9	109.4	114.2	114.2	117.3
32.5°	87.2	90.4	93.6	96.7	98.3	103.0	103.0	106.3
35°	76.1	80.8	82.5	85.7	88.8	93.6	93.6	96.7
37.5°	66.6	71.3	72.9	76.1	79.2	84.1	84.1	87.2
40°	58.8	63.4	65.0	68.2	69.8	76.1	76.1	77.7
42.5°	52.3	55.5	57.0	60.3	61.9	65.0	65.0	68.2
45°	44.4	47.6	49.1	50.7	53.9	57.0	57.0	58.8
47.5°	38.1	41.2	42.9	44.4	46.0	49.1	49.1	52.3
50°	33.2	35.0	36.5	38.1	39.7	42.9	42.9	44.4
52.5°	28.5	30.1	31.7	33.2	35.0	36.5	38.1	39.7
55°	25.3	26.9	26.9	28.5	30.1	31.7	31.7	33.2
57.5°	22.2	23.8	23.8	23.8	25.3	26.9	26.9	28.5
60°	19.1	20.7	20.7	20.7	22.2	22.2	22.2	23.8
62.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
65°	14.3	14.3	14.3	14.3	14.3	14.3	12.8	14.3
67.5°	12.8	12.8	12.8	11.0	11.0	11.0	11.0	11.0
70°	11.0	11.0	11.0	9.5	9.5	9.5	7.9	7.9
72.5°	9.5	9.5	9.5	7.9	7.9	7.9	6.3	6.3
75°	7.9	7.9	7.9	7.9	6.3	6.3	6.3	6.3
77.5°	6.3	6.3	6.3	6.3	6.3	6.3	4.7	4.7
80°	6.3	4.7	4.7	4.7	4.7	4.7	4.7	4.7
82.5°	4.7	4.7	4.7	4.7	3.1	3.1	3.1	3.1
85°	3.1	3.1	3.1	3.1	3.1	3.1	1.6	1.6
87.5°	3.1	1.6	1.6	1.6	1.6	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)