

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219575

Luminaire Tested: **LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3537.4 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219575

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219575

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35776	35776	35776
5°	79197	33851	23786
10°	317066	29403	19871
15°	730854	23388	17461
20°	1090989	16598	15567
25°	1430950	11063	13864
30°	1642606	6991	12126
35°	1506116	4470	10490
40°	1235090	2896	8941
45°	716030	2028	7179
50°	202933	1492	5923
55°	18579	1385	4982
60°	2868	1589	4127
65°	734	1513	3003
70°	906	1869	2323
75°	1198	2470	2470
80°	0	3682	1785
85°	0	7336	1890

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219575

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	1.5
10°-20°	470.4	13.3
20°-30°	1146.2	32.4
30°-40°	1242.2	35.1
40°-50°	562.8	15.9
50°-60°	43.5	1.2
60°-70°	9.0	0.3
70°-80°	6.6	0.2
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1669.1	47.2
0°-40°	2911.3	82.3
0°-60°	3517.6	99.4
0°-90°	3537.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3537.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	369	369	369	369	369	
5°	814	601	348	263	245	147
15°	7287	2384	233	169	174	2118
25°	13387	3424	104	102	130	6102
35°	12735	870	38	59	89	7834
45°	5226	110	15	33	52	4126
55°	110	15	8	20	30	252
65°	3	5	7	13	13	5
75°	3	5	7	10	7	2
85°	0	5	7	5	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1219575

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3
2.5°	553.3	543.5	548.4	535.3	527.1	520.5	523.7	520.5	499.2	494.3	477.9
5°	814.4	799.8	799.8	771.7	742.1	724.2	724.2	702.8	656.8	635.4	601.0
7.5°	1459.7	1430.1	1405.5	1318.4	1205.2	1141.2	1124.9	1034.5	917.9	844.0	756.9
10°	3223.2	3100.0	3013.0	2786.4	2482.7	2293.9	2213.4	1901.4	1530.3	1251.2	998.3
12.5°	5420.2	5252.7	5100.0	4729.0	4292.1	3995.0	3835.6	3375.9	2655.1	2139.5	1601.0
15°	7287.2	7106.5	6925.9	6474.4	6013.0	5755.2	5462.8	4853.7	3901.4	3169.1	2384.1
17.5°	8819.1	8717.3	8531.7	7870.0	7288.8	6886.5	6582.7	5786.4	4806.0	3970.2	3081.9
20°	10582.6	10331.4	9999.6	9196.8	8402.0	7897.9	7470.9	6500.6	5367.6	4407.1	3451.6
22.5°	12067.0	11888.0	11411.8	10352.8	9183.6	8753.5	8231.3	7063.9	5728.9	4592.6	3494.2
25°	13387.1	13106.4	12508.7	11249.3	10052.2	9320.0	8679.5	7369.1	5861.9	4605.6	3423.6
27.5°	14160.4	13794.4	13091.5	11718.8	10352.8	9543.2	8833.9	7421.8	5778.1	4431.8	3165.8
30°	14684.2	13955.3	13178.6	11723.9	10257.5	9430.0	8694.4	7157.4	5430.0	4034.4	2732.3
32.5°	13820.6	13398.6	12656.4	11257.4	9738.7	8930.8	8200.1	6584.3	4886.5	3444.8	1901.4
35°	12735.3	12393.7	11748.5	10359.3	8960.2	8198.4	7423.4	5848.8	4178.8	2367.8	870.2
37.5°	11474.2	11206.6	10512.0	9242.7	8011.3	7265.6	6489.1	4985.0	2942.5	1174.1	528.7
40°	9766.5	9539.9	8970.2	7950.5	6815.8	6106.7	5390.7	3728.9	1597.6	655.1	344.8
42.5°	8027.7	7837.2	7318.3	6436.7	5439.9	4855.3	4224.9	2272.4	794.7	412.2	192.2
45°	5226.4	4988.4	4709.1	4305.4	3812.7	3453.1	2709.4	1096.8	471.1	229.8	110.0
47.5°	2996.6	2839.0	2380.9	1878.4	1525.4	1392.4	1013.2	510.7	259.4	132.9	67.4
50°	1346.5	1244.7	1044.4	850.5	615.8	481.2	408.9	256.0	128.1	72.3	46.0
52.5°	331.7	338.2	320.1	280.8	249.6	211.8	184.0	119.9	67.4	44.3	29.5
55°	110.0	111.7	101.8	96.8	88.7	82.2	75.5	54.3	41.0	39.3	14.8
57.5°	39.3	39.3	41.0	37.8	36.1	34.4	32.8	27.9	24.6	14.8	8.2
60°	14.8	14.8	14.8	16.4	16.4	16.4	18.1	16.4	11.4	8.2	6.6
62.5°	6.6	6.6	6.6	6.6	8.2	8.2	9.9	8.2	6.6	6.6	4.9
65°	3.2	3.2	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
67.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9	4.9
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9	4.9
72.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9	4.9
75°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9
77.5°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2	4.9
80°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2	4.9
82.5°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2	4.9
85°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	4.9
87.5°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219575

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3
2.5°	461.3	451.5	431.8	417.1	405.6	403.9	394.1	377.7	371.1	359.5	349.6
5°	568.2	543.5	512.3	482.8	461.3	449.9	415.5	384.3	366.1	348.1	331.7
7.5°	683.0	627.2	572.9	525.4	495.9	477.9	436.8	385.9	353.0	326.8	305.4
10°	827.6	712.7	619.0	545.1	505.8	481.2	431.8	371.1	330.0	298.9	277.6
12.5°	1157.6	844.0	661.8	554.9	505.8	471.1	412.2	351.3	305.4	267.7	244.6
15°	1722.4	1178.9	784.8	559.9	489.4	449.9	382.6	318.6	272.6	233.2	211.8
17.5°	2254.4	1551.7	980.2	594.5	479.5	418.7	343.2	280.8	233.2	195.4	177.3
20°	2530.3	1737.2	1088.6	620.7	463.0	379.4	297.2	239.7	193.8	161.0	146.1
22.5°	2536.9	1720.8	1036.2	559.9	402.3	325.1	254.5	197.1	157.6	129.7	118.2
25°	2380.9	1522.0	852.2	436.8	325.1	272.6	211.8	161.0	123.1	103.5	95.3
27.5°	2087.1	1231.6	628.9	315.3	254.5	216.7	165.9	123.1	93.6	80.5	75.5
30°	1614.1	761.9	348.1	233.2	192.2	162.7	119.9	82.2	70.7	62.5	59.2
32.5°	801.3	372.7	246.3	165.9	131.4	103.5	75.5	60.8	54.3	49.2	47.5
35°	435.1	267.7	154.2	100.2	78.8	65.7	50.9	42.6	39.3	37.8	37.8
37.5°	303.8	159.3	93.6	60.8	49.2	44.3	36.1	31.1	29.5	29.5	29.5
40°	167.5	95.3	57.5	39.3	32.8	29.5	24.6	22.9	22.9	22.9	24.6
42.5°	96.8	59.2	39.3	27.9	22.9	21.3	18.1	16.4	18.1	18.1	19.7
45°	62.5	44.3	26.3	19.7	16.4	14.8	13.1	13.1	14.8	14.8	16.4
47.5°	44.3	31.1	18.1	13.1	9.9	9.9	9.9	9.9	11.4	13.1	14.8
50°	26.3	16.4	9.9	8.2	6.6	6.6	6.6	8.2	9.9	9.9	11.4
52.5°	14.8	9.9	6.6	6.6	4.9	4.9	6.6	6.6	8.2	9.9	11.4
55°	8.2	6.6	4.9	4.9	4.9	4.9	4.9	6.6	6.6	8.2	9.9
57.5°	6.6	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	8.2	8.2
60°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	8.2	8.2
62.5°	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6	8.2
65°	4.9	4.9	4.9	6.6	4.9	6.6	6.6	6.6	6.6	6.6	8.2
67.5°	4.9	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	8.2
70°	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	8.2
72.5°	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	8.2
75°	4.9	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
77.5°	4.9	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
80°	4.9	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
82.5°	4.9	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
85°	4.9	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
87.5°	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219575

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3
2.5°	346.4	335.0	326.8	323.5	316.9	318.6	313.7	310.3	300.5	300.5	294.0
5°	320.1	305.4	295.6	290.7	284.1	282.5	277.6	272.6	262.7	261.0	256.0
7.5°	292.2	277.6	266.1	261.0	254.5	252.8	246.3	242.9	234.7	233.2	228.2
10°	262.7	246.3	236.4	231.5	225.0	225.0	220.1	216.7	210.2	210.2	206.9
12.5°	231.5	216.7	210.2	203.6	200.3	200.3	197.1	193.8	188.9	190.5	188.9
15°	198.6	187.2	180.6	177.3	175.8	175.8	174.1	172.5	169.1	172.5	169.1
17.5°	167.5	159.3	154.2	152.7	151.0	151.0	151.0	152.7	151.0	154.2	154.2
20°	137.9	131.4	128.1	128.1	126.4	129.7	129.7	132.9	132.9	137.9	139.6
22.5°	113.3	108.4	106.7	106.7	106.7	110.0	111.7	114.9	116.6	121.5	124.7
25°	90.4	88.7	88.7	88.7	90.4	93.6	96.8	100.2	101.8	108.4	110.0
27.5°	73.9	72.3	73.9	73.9	75.5	80.5	83.7	87.0	90.4	95.3	98.6
30°	59.2	59.2	60.8	62.5	64.1	67.4	72.3	75.5	78.8	83.7	87.0
32.5°	47.5	49.2	50.9	52.4	52.4	57.5	60.8	65.7	67.4	72.3	75.5
35°	39.3	41.0	42.6	44.3	44.3	49.2	52.4	55.8	59.2	62.5	65.7
37.5°	31.1	32.8	36.1	37.8	37.8	42.6	44.3	47.5	50.9	54.3	57.5
40°	26.3	27.9	31.1	31.1	32.8	36.1	37.8	41.0	44.3	47.5	50.9
42.5°	21.3	22.9	26.3	27.9	27.9	31.1	32.8	36.1	37.8	41.0	42.6
45°	19.7	19.7	22.9	22.9	24.6	26.3	29.5	31.1	32.8	36.1	37.8
47.5°	16.4	18.1	19.7	21.3	21.3	22.9	24.6	26.3	27.9	31.1	32.8
50°	13.1	14.8	18.1	18.1	18.1	21.3	22.9	24.6	24.6	26.3	27.9
52.5°	13.1	13.1	14.8	16.4	16.4	18.1	19.7	21.3	21.3	22.9	24.6
55°	11.4	11.4	13.1	14.8	14.8	16.4	18.1	18.1	19.7	19.7	21.3
57.5°	9.9	11.4	13.1	13.1	13.1	14.8	16.4	16.4	18.1	18.1	19.7
60°	9.9	11.4	11.4	13.1	13.1	14.8	14.8	14.8	16.4	16.4	16.4
62.5°	9.9	9.9	11.4	11.4	11.4	13.1	13.1	14.8	14.8	14.8	14.8
65°	9.9	9.9	11.4	11.4	11.4	13.1	13.1	13.1	13.1	13.1	13.1
67.5°	8.2	9.9	9.9	9.9	11.4	11.4	11.4	11.4	11.4	11.4	11.4
70°	8.2	8.2	9.9	9.9	9.9	11.4	11.4	11.4	11.4	11.4	11.4
72.5°	8.2	8.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
75°	8.2	8.2	8.2	8.2	8.2	9.9	9.9	9.9	9.9	8.2	8.2
77.5°	6.6	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	6.6
80°	6.6	6.6	8.2	6.6	8.2	8.2	8.2	8.2	6.6	6.6	6.6
82.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9
85°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9	4.9	3.2
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9	4.9	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219575

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	369.3	369.3	369.3	369.3	369.3	369.3	369.3	369.3
2.5°	290.7	294.0	290.7	294.0	285.8	289.0	292.2	284.1
5°	252.8	249.6	251.2	254.5	247.8	249.6	251.2	244.6
7.5°	226.5	228.2	225.0	228.2	223.3	225.0	226.5	221.7
10°	205.3	206.9	205.3	206.9	202.0	205.3	206.9	202.0
12.5°	185.5	188.9	187.2	190.5	185.5	188.9	192.2	185.5
15°	170.8	174.1	172.5	175.8	172.5	175.8	179.0	174.1
17.5°	155.9	159.3	159.3	162.7	161.0	164.3	167.5	162.7
20°	141.1	146.1	146.1	149.3	149.3	151.0	155.9	151.0
22.5°	128.1	132.9	132.9	136.2	136.2	139.6	142.8	139.6
25°	113.3	119.9	121.5	124.7	124.7	128.1	132.9	129.7
27.5°	103.5	108.4	110.0	113.3	114.9	118.2	121.5	118.2
30°	90.4	96.8	98.6	101.8	103.5	108.4	110.0	108.4
32.5°	80.5	85.4	87.0	90.4	93.6	96.8	100.2	98.6
35°	70.7	75.5	77.2	80.5	82.2	87.0	90.4	88.7
37.5°	62.5	67.4	69.1	70.7	72.3	77.2	80.5	78.8
40°	54.3	57.5	59.2	62.5	64.1	67.4	70.7	70.7
42.5°	47.5	50.9	52.4	54.3	55.8	59.2	62.5	60.8
45°	41.0	44.3	46.0	47.5	49.2	50.9	54.3	52.4
47.5°	34.4	37.8	39.3	41.0	42.6	44.3	47.5	46.0
50°	29.5	32.8	32.8	34.4	36.1	37.8	41.0	39.3
52.5°	26.3	27.9	29.5	29.5	31.1	32.8	36.1	34.4
55°	22.9	24.6	24.6	26.3	26.3	27.9	29.5	29.5
57.5°	19.7	21.3	21.3	22.9	22.9	24.6	26.3	26.3
60°	18.1	18.1	19.7	19.7	19.7	21.3	21.3	21.3
62.5°	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.4
65°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1
67.5°	11.4	11.4	11.4	11.4	11.4	9.9	9.9	9.9
70°	9.9	9.9	9.9	9.9	9.9	8.2	8.2	8.2
72.5°	9.9	9.9	8.2	8.2	8.2	8.2	8.2	6.6
75°	8.2	8.2	8.2	8.2	6.6	6.6	6.6	6.6
77.5°	6.6	6.6	6.6	6.6	4.9	4.9	4.9	4.9
80°	6.6	4.9	4.9	4.9	4.9	4.9	4.9	3.2
82.5°	4.9	4.9	4.9	3.2	3.2	3.2	3.2	3.2
85°	3.2	3.2	3.2	3.2	1.7	1.7	1.7	1.7
87.5°	3.2	1.7	1.7	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)